




---

 PRODUCT-DETAILS

# OT160EVSUR6TZ

## OT160EVSUR6TZ Safety switch




---

**General Information**

Extended Product Type	OT160EVSUR6TZ
Product ID	1SCA125650R1001
EAN	6417019557021
Catalog Description	OT160EVSUR6TZ Safety switch
Long Description	<p>Safety switch, 6-p. 415V AC23 160A, 80kW. Mounted auxiliary contact: 4NO2NC. Stainless steel enclosure. IP65. StainlessSteel Pistol handle. Interlocked cover. Defeatable interlocking. The enclosure and handle of the OT series is made of rigid acid proof steel, class AISI316L. The enclosure has a hinged door, with door lock. The cover is interlocked, and can not be opened when switch is on. The interlock function can be defeated for thermographing. The cover has also a gas pressure releaf function, to protect the user in case of internal arc. Suitable for outdoor and indoor use. The cable entries holes are prepared for cable flanges. The cable flanges (KOT61007 or KOT62296 (for EMC)) and the covers for the holes (KOT61008), have to be bought separately. The switch can be used in EMC applications, if EMC ring flanges are used. PE terminals and auxiliary contacts are included.</p>

---

**Material Compliance**

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC340076D0201
RoHS Declaration	1SCC340075D0201

RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC340095D0201

## Popular Downloads

Data Sheet, Technical Information	1SCC340015C0201
Instructions and Manuals	1SCC340008M0004

## Environmental

Degree of Protection	acc. to IEC 60529 IP65
Pollution Degree	3

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363090
Country or Territory of Origin	Finland

## Dimensions

Product Net Width	800 mm
Product Net Height	800 mm
Product Net Depth / Length	230 mm
Product Net Weight	38.5 kg

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	815 mm
Package Level 1 Depth / Length	910 mm
Package Level 1 Height	325 mm
Package Level 1 Gross Weight	43 kg
Package Level 1 EAN	6417019557021

## Technical

Cable Entry Position	Bottom/Bottom
Cable Outlets Per Side	Blank / 8xring-flange+ø25.5mm
Color	Stainless
Connecting Capacity Main Circuit	Hole Diameter 8 mm Screw Clamp / PE Terminal 4pc,10 ... 70 mm²
Conventional Thermal Current ( $I_{the}$ )	Fully Enclosed 160 A
Degree of Protection	acc. to IEC 60529 IP65
Enclosure Material	Stainless steel
Handle Color	Stainless Steel
Handle Type	Pistol handle
Impact Resistance Rating	Housing IK09
Maximum Mounted	4 NO, 2 NC

**Auxiliary Contacts**

Mounted Auxiliary Contacts	4 NO, 2 NC
Number of Auxiliary Contacts NC	2
Number of Auxiliary Contacts NO	4
Number of Poles	6P
Pollution Degree	3
Power Loss	at Rated Operating Conditions per Pole 3.2 W
Rated Conditional Short-Circuit Current ( $I_{nc}$ )	40.5 kA
Rated Insulation Voltage ( $U_i$ )	acc. to IEC/EN 60664-1 750 V
Rated Operational Current AC-22A ( $I_e$ )	(380 ... 415 V) 160 A (500 V) 160 A (690 V) 160 A
Rated Operational Current AC-23A ( $I_e$ )	(380 ... 415 V) 160 A (500 V) 160 A (690 V) 160 A
Rated Operational Power AC-23A ( $P_e$ )	(380 ... 415 V) 80 kW (500 V) 112 kW (690 V) 144 kW
Rated Operational Voltage	Main Circuit 750 V
Rated Short-Circuit Making Capacity ( $I_{cm}$ )	(1000 V AC) 30 kA
Rated Short-time Withstand Current Low Voltage ( $I_{cw}$ )	for 1 s 8 kA
Recommended Screw Driver	Main Circuit M8
Special Functions	EMC
Standards	IEC 60947-1, -3
<b>Tightening Torque</b>	<b>Main Circuit 6 N·m</b>

**Technical UL/CSA**

Recommended Screw Driver	Main Circuit M8
<b>Tightening Torque</b>	<b>Main Circuit 6 N·m</b>

**Certificates and Declarations**

Declaration of Conformity - CE	1SCC340002D2703
--------------------------------	-----------------

**External Classifications and Standards**

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122205
IDEA Granular Category Code (IGCC)	5166 >> Safety switch
eClass	V11.1 : 27371403
<b>WEEE Category</b>	<b>4. Large Equipment (Any External Dimension More Than 50 cm)</b>

---

## Categories

---

Low Voltage Products and Systems → Enclosed Switches → Enclosed Safety Switches → Enclosed Safety Switches

