

## SAFETY DATA SHEET

### GLASS CLEANER 692-924-0001

RS REACH MSDS Date 01/01/08

#### 1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND COMPANY/UNDERTAKING

PRODUCT NAME GLASS CLEANER 692-924-0001

PRODUCT NO.

Supplier: RS Components Ltd,  
Birchington Road,  
Corby, Northants,  
NN17 9RS,

Tel: +44 (0) 1536 402888 (8am to 8pm)

Fax: +44 (0) 1536 401588

Email: technical.help@rs-components.com

#### 2 HAZARDS IDENTIFICATION

Extremely flammable. Vapours may cause drowsiness and dizziness. Irritating to eyes.

CLASSIFICATION Xi;R36. F+;R12. R67.

#### 3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
AMMONIA ...%	215-647-6	1336-21-6	< 1%	C;R34 N;R50
BUTANE	203-448-7	106-97-8	1-5%	F+;R12
ISOBUTANE	200-857-2	75-28-5	1-5%	F+;R12
PROPAN-2-OL	200-661-7	67-63-0	30-60%	F;R11 Xi;R36 R67
PROPANE	200-827-9	74-98-6	1-5%	F+;R12

The Full Text for all R-Phrases are Displayed in Section 16

#### 4 FIRST-AID MEASURES

##### GENERAL INFORMATION

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

##### INHALATION

Move the exposed person to fresh air at once. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Keep the affected person warm and at rest. Get prompt medical attention.

##### INGESTION

DO NOT INDUCE VOMITING! Rinse mouth thoroughly with water and give large amounts of milk or water to people not unconscious. Get medical attention if any discomfort continues.

##### SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

##### EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

#### 5 FIRE-FIGHTING MEASURES

##### EXTINGUISHING MEDIA

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

##### SPECIAL FIRE FIGHTING PROCEDURES

Containers close to fire should be removed or cooled with water. Use water to keep fire exposed containers cool and disperse vapours.

##### UNUSUAL FIRE & EXPLOSION HAZARDS

Aerosol cans may explode in a fire.

#### 6 ACCIDENTAL RELEASE MEASURES

##### SPILL CLEAN UP METHODS

Wear necessary protective equipment. Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Let evaporate. Keep out of confined spaces because of explosion risk. If leakage cannot be stopped, evacuate area.

**GLASS CLEANER 692-924-0001**

**7 HANDLING AND STORAGE**

**USAGE PRECAUTIONS**

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

**STORAGE PRECAUTIONS**

Aerosol cans: Must not be exposed to direct sunlight or temperatures above 50°C.

**8 EXPOSURE CONTROLS/PERSONAL PROTECTION**

Name	Std	LT - ppm	LT - mg/m3	ST - ppm	ST - mg/m3
BUTANE	WEL	600 ppm	1450 mg/m3	750 ppm	1810 mg/m3
ISOBUTANE	WEL	800 ppm		800 ppm	
PROPAN-2-OL	WEL	400 ppm	999 mg/m3	500 ppm	1250 mg/m3
PROPANE		Asphyxiating	Asphyxiating	Asphyxiating	Asphyxiating

**INGREDIENT COMMENTS**

WEL = Workplace Exposure Limits

**PROTECTIVE EQUIPMENT**



**ENGINEERING MEASURES**

Provide adequate general and local exhaust ventilation.

**RESPIRATORY EQUIPMENT**

No specific recommendation made, but respiratory protection must be used if the general level exceeds the Recommended Workplace Exposure Limit. Use chemical cartridge protection with appropriate cartridge.

**HAND PROTECTION**

Use protective gloves.

**EYE PROTECTION**

Use approved safety goggles or face shield.

**OTHER PROTECTION**

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

**HYGIENE MEASURES**

DO NOT SMOKE IN WORK AREA! Wash at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

**9 PHYSICAL AND CHEMICAL PROPERTIES**

APPEARANCE	Aerosol		
COLOUR	Colourless		
ODOUR	Lemon		
SOLUBILITY	Soluble in water		
FLAMMABILITY LIMIT - LOWER(%)	0.8	FLAMMABILITY LIMIT - UPPER(%)	12.0

**10 STABILITY AND REACTIVITY**

**STABILITY**

Stable under normal temperature conditions.

**CONDITIONS TO AVOID**

Avoid heat, flames and other sources of ignition. Avoid contact with: Strong oxidising agents. Strong alkalis. Strong mineral acids.

**HAZARDOUS DECOMPOSITION PRODUCTS**

Fire creates: Vapours/gases/fumes of: Carbon monoxide (CO). Carbon dioxide (CO2).

**11 TOXICOLOGICAL INFORMATION**

**GLASS CLEANER 692-924-0001**

**INHALATION**

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. Prolonged inhalation of high concentrations may damage respiratory system. Irritating to respiratory system.

**INGESTION**

May cause discomfort if swallowed. May cause stomach pain or vomiting. Gastrointestinal symptoms, including upset stomach.

**SKIN CONTACT**

Prolonged or repeated exposure may cause severe irritation. Acts as a defatting agent on skin. May cause cracking of skin, and eczema. May cause allergic contact eczema. May cause sensitisation by skin contact. Irritating to skin.

**EYE CONTACT**

Irritating to eyes. May cause chemical eye burns.

**ROUTE OF ENTRY**

Inhalation. Skin and/or eye contact.

**12 ECOLOGICAL INFORMATION**

**ECOTOXICITY**

Dangerous for the environment if discharged into watercourses.

**DEGRADABILITY**

The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

**13 DISPOSAL CONSIDERATIONS**

**DISPOSAL METHODS**

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

**14 TRANSPORT INFORMATION**



UK ROAD CLASS	2		
PROPER SHIPPING NAME	AEROSOLS		
UN NO. ROAD	1950	UK ROAD PACK GR.	N/A
ADR CLASS NO.	2	ADR CLASS	Class 2: Gases
ADR PACK GROUP	N/A	ADR LABEL NO.	2.1
RID CLASS NO.	2	RID PACK GROUP	N/A
UN NO. SEA	1950	IMDG CLASS	2.1
IMDG PACK GR.	Not Applicable	EMS	F-D, S-U
MFAG	See Guide	MARINE POLLUTANT	No.
UN NO. AIR	1950	AIR CLASS	2.1
AIR PACK GR.	N/A		

**15 REGULATORY INFORMATION**

**LABELLING**



Irritant



Extremely Flammable

**RISK PHRASES**

R12	Extremely flammable.
R36	Irritating to eyes.
R67	Vapours may cause drowsiness and dizziness.

### GLASS CLEANER 692-924-0001

#### SAFETY PHRASES

S2	Keep out of the reach of children
S16	Keep away from sources of ignition - No smoking.
S23	Do not breathe vapour/spray.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S51	Use only in well-ventilated areas.

#### DETERGENT LABELLING

< 5%	Perfumes
Contains	d-LIMONENE

#### UK REGULATORY REFERENCES

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002.

The Control of Substances Hazardous to Health Regulations 2002.

#### STATUTORY INSTRUMENTS

The Control of Substances Hazardous to Health Regulations 2002.

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002.

#### APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply.

#### GUIDANCE NOTES

Workplace Exposure Limits EH40.

Introduction to Local Exhaust Ventilation HS(G)37.

CHIP for everyone HSG(108).

---

### 16 OTHER INFORMATION

---

REVISION DATE 09/01/2008

REV. NO./REPL. SDS GENERATED 9

#### RISK PHRASES IN FULL

R11	Highly flammable.
R12	Extremely flammable.
R34	Causes burns.
R36	Irritating to eyes.
R37	Irritating to respiratory system.
R50	Very toxic to aquatic organisms.
R67	Vapours may cause drowsiness and dizziness.

#### DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.