

Miniature circuit breaker 230/400 V 6kA, 1-pole, B, 10 A



Model	
Product brand name	SETRON
Product designation	Miniature circuit breaker
Design of the product	5SL miniature circuit breakers
General technical data	
Number of poles	1
Number of poles / Note	1P
Tripping characteristic class	B
circuit-breaker / Design	5SL6
Mechanical service life (switching cycles) / typical	10 000
Overvoltage category	3
Voltage	
Insulation voltage	
<ul style="list-style-type: none"> <li>with single-phase operation / at AC / rated value</li> </ul>	250 V
<ul style="list-style-type: none"> <li>with multi-phase operation / at AC / rated value</li> </ul>	440 V
Supply voltage	
Type of voltage	AC

Current / at AC / rated value	10 A
Supply voltage / at AC / rated value	400 V
Supply voltage frequency	
• rated value	50 Hz

### Protection class

Protection class IP	IP20, with connected conductors
---------------------	---------------------------------

### Switching capacity

Switching capacity current	
• acc. to EN 60898 / rated value	6 kA
• acc. to IEC 60947-2 / rated value	6 kA
Energy limiting class	3

### Dissipation

Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1.6 W
---	-------

### Current

Tripping residual / rated value / derated current / at 40 Cel	9.51662 A
---	-----------

### Main circuit

Operating voltage	
• at DC / rated value / maximum	60 V
• with multi-phase operation / at AC / maximum	440 V
Suitability for operation	Residential buildings/infrastructure

### Product details

Product function / neutral conductor switching	No
Product feature / Touch protection	Yes
Product feature	
• halogen-free	Yes
• sealable	Yes
• silicon-free	Yes
Product extension / can be installed / supplementary devices	Yes

### Connections

• Connectable conductor cross-section	
_____	0.75 ... 25 mm <sup>2</sup>
— stranded	
_____	0.75 ... 25 mm <sup>2</sup>
• Connectable conductor cross-section / finely stranded / with core end processing	
_____	0.75 ... 25 mm <sup>2</sup>
Tightening torque / with screw-type terminals	

2.5 ... 3 N·m

### Mechanical Design

Height	90 mm
Width	18 mm
Depth	76 mm
Installation depth	70 mm
Number of width units	1
Mounting position	any
Net weight	120 g

### Environmental conditions

Influence of the surrounding temperature	Periodically +55°C, max. 95% humidity
Ambient temperature	-25 ... +45 °C
	-40 ... +75 °C

### Certificates

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

#### General Product Approval



[TSE](#)

#### Declaration of Conformity



### Further information

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SL6110-6>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SL6110-6>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SL6110-6](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SL6110-6)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://www.siemens.com/specifications>



