

# HC-KIT-B10-R01 - Connector set

1409697

<https://www.phoenixcontact.com/gb/products/1409697>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector set, consisting of: B10 sleeve housing and panel mounting base, 10-pos. plug and socket insert, M25 cable gland

## Commercial data

Item number	1409697
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF7AFX
Product key	BF7AFX
GTIN	4046356752442
Weight per piece (including packing)	500.34 g
Weight per piece (excluding packing)	470 g
Customs tariff number	85366990
Country of origin	CN

# HC-KIT-B10-R01 - Connector set



1409697

<https://www.phoenixcontact.com/gb/products/1409697>

## Set consists of

### G-INS-M25-M68N-NNES-S - Cable gland

1411165

<https://www.phoenixcontact.com/gb/products/1411165>



Cable gland, material for screw connection: Brass, nickel-plated, application: Standard, external cable diameter 11 mm ... 17 mm, shielding: no, connecting thread: M25 x 1.5, color: silver, with O-ring

---

### HC-B 10-I-UT-M - Contact insert

1648173

<https://www.phoenixcontact.com/gb/products/1648173>



Contact insert, number of positions: 10+PE, size: B10, number of connections per position: 1, Pin, Screw connection, 500 V, 16 A, 0.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, application: Power

# HC-KIT-B10-R01 - Connector set

1409697

<https://www.phoenixcontact.com/gb/products/1409697>



## HC-STA-B10-HLFS-1TTM25-EL-AL - Housing

1412630

<https://www.phoenixcontact.com/gb/products/1412630>



Sleeve housing B10, for single locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, straight, 1x M25, height: 57 mm, cable gland: none, Standard

---

## HC-STA-B10-BWSC-ELC-AL - Housing

1411321

<https://www.phoenixcontact.com/gb/products/1411321>



Panel mounting base B10, with single locking latch, material: Die-cast aluminum, salt water resistant, protective cover material: PC, height: 30.5 mm, cable gland: none, protective cover: yes, Standard, with flat gasket

# HC-KIT-B10-R01 - Connector set

1409697

<https://www.phoenixcontact.com/gb/products/1409697>



## HC-B 10-I-UT-F - Contact insert

1648186

<https://www.phoenixcontact.com/gb/products/1648186>



Contact insert, number of positions: 10+PE, size: B10, number of connections per position: 1, Socket, Screw connection, 500 V, 16 A, 0.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, application: Power

# HC-KIT-B10-R01 - Connector set

1409697

<https://www.phoenixcontact.com/gb/products/1409697>



## Technical data

### Product properties

Product type	Connector set
Housing type	Complete housing
Application	Power
Type	B10
Number of positions	10
Connection profile	10+PE
No. of cable outlets	1
Seal present	yes
Protective cover	yes
Contact material type	turned
Cable outlet	straight

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated voltage (III/3)	500 V
Rated surge voltage	6 kV
Rated current	24 A
Nominal voltage $U_N$	500 V
Nominal current $I_N$	16 A

### Connection data

Connection method	Screw connection
Connection technology	Screw connection
Connection in acc. with standard	IEC / EN
Conductor cross section	0.5 mm² ... 2.5 mm² (applies to stranded conductors with ferrules) 0.5 mm² ... 2.5 mm² (applies to stranded conductors with ferrules)
Connection cross section AWG	20 ... 14
Tightening torque	0.8 Nm ... 1.2 Nm (PE connection) 0.5 Nm ... 0.8 Nm (Mounting screws for mounting in the HEAVYCON housing) 0.5 Nm ... 0.8 Nm

### Dimensions

Dimensional drawing	
---------------------	--

# HC-KIT-B10-R01 - Connector set



1409697

<https://www.phoenixcontact.com/gb/products/1409697>

Width	43 mm
Height	123 mm
Length	93 mm

## Installation dimensions

Width of the assembly cutout	35 mm
Length of the assembly cutout	65 mm

## Material specifications

Material Housing	Die-cast aluminum
Flammability rating according to UL 94	V0
Seal material	NBR, conductive
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC
Locking latch material	PA

## Cable/line

External cable diameter	11 mm ... 17 mm
	14 mm ... 17 mm (for UL 514 B)
External cable diameter	11 mm ... 16 mm

## Mechanical properties

### Mechanical data

Locking type	Latch
--------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
Impact strength	IK09
Ambient temperature (operation)	-40 °C ... 100 °C

## Mounting

Mounting type	Screw mounting
---------------	----------------

# HC-KIT-B10-R01 - Connector set


1409697

<https://www.phoenixcontact.com/gb/products/1409697>



## Drawings

Dimensional drawing



Dimensional drawing

# HC-KIT-B10-R01 - Connector set



1409697

<https://www.phoenixcontact.com/gb/products/1409697>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1409697>



**EAC**

Approval ID: RU C-DE.BL08.B.00511



# HC-KIT-B10-R01 - Connector set



1409697

<https://www.phoenixcontact.com/gb/products/1409697>

## Classifications

### ECLASS

ECLASS-11.0	27440101
ECLASS-12.0	27440113
ECLASS-13.0	27440113

### ETIM

ETIM 9.0	EC002636
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# HC-KIT-B10-R01 - Connector set

1409697

<https://www.phoenixcontact.com/gb/products/1409697>



## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	54139e29-16a0-4805-93b8-cd875338d950

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)