

M18 BQSS-O

M18™ QUARTER SHEET SANDER

- High performance motor delivers 11,000 to 13,000 sanding strokes per minute for faster material removal
- Variable speed wheel with 6 speed settings allows the correct speed to be set for different types of material
- Universal hook and loop sanding pad allows easy changing of sanding sheets
- Paper retention clips for use with standard sheet sand paper
- Low profile pommel height with rubberised textured grip provides enhanced ergonomics
- Anti swirl orbital motion ensures flawless finishes delivered with low vibration at only 5.23 m/s²
- Hole punch supplied for use with standard sheet sand paper
- Premium 4-pole brushed motor, REDLITHIUM™ battery pack and REDLINK™ electronic delivering the needed power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



No load speed (rpm)	11,000 - 13,000
Oscillation diameter (mm)	1.6
Sanding pad size (mm)	113 x 104
Weight with battery pack (EPTA) (kg)	1.9 (M18 B5)
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article Number	4933479966