



DeWalt DCBP034-B1

20V MAX XRP COMPACT BATTERY-SINGLE PACK

Introduction

The **20V MAX* XR® compact battery** delivers 50% more power and a longer lifespan. Engineered with pouch cell technology, our best performing 20V MAX* compact battery” Powers through tough jobs, day in and day out. XR® batteries are a part of our best performing line of 20V MAX* batteries” and are compatible with 20V MAX* tools.

Key Features

- **50% more power** - tackle tough jobs with 50% more power.
- **Longer lifespan** - help maximize longevity day in and day out with these batteries that deliver an increase of charge cycles over the lifetime of the batteries.
- **Compact size** - work in tight spaces with an ergonomic design that enhances manoeuvrability without sacrificing power.
- **Resists wear-and-tear** - take on the elements with a durable, overmolded base designed to provide a high level of impact resistance.
- **State-of-charge** - get quick visibility to your batteries' state-of-charge with the LED indicator to help avoid interruptions.
- **Part of our best performing line of 20V MAX* batteries** - innovative battery technologies designed to deliver certainty for the world’s toughest pros.

Specifications Table

Feature	Specification
Product Type	Battery
Voltage	20V
Cordless or Corded	Cordless
Power Source	Battery
Total Number of Batteries	1
Battery Amp Hours	1.7Ah
Charger Included	No
Piece Count	1
Assembled Product Length	5.9-in
Assembled Product Weight	0.8-lbs
Assembled Product Width	2.56-in
Assembled Product Height	7.6-in
Country Of Origin	China
Barcode	885911782319
Individual or Set	Individual

DeWalt DWE7492-IN

2000W 250mm table saw

Introduction

The DWE7492-IN 250mm Professional Table Saw from DEWALT is a compact, highly precise, and powerful jobsite saw designed for professional carpenters and demanding woodworkers. Featuring a high-torque 2000W motor and an industry-leading rack-and-pinion fence system, this saw delivers outstanding cutting performance and flawless accuracy when ripping through thick hardwoods or large sheet goods, making it ideal for high-precision woodwork on any busy jobsite.

Key Features

- **RACK & PINION FENCE:** Front and rear fence lock, with a large clear scale for an extremely accurate and easy to use saw
- **STEEL ROLL CAGE:** Protects against jobsite drops and impacts
- **CAST TABLE TOP:** Designed to ensure accuracy and precision
- **SIMPLE BEVEL LOCK:** Quick bevel lock with large scale for easy, accurate adjustments
- **OVERLOAD PROTECTION:** Ensures powerful performance in hard, wet or frozen woods
- **3 YEAR GUARANTEE:** Tool covered by extended warranty, subject to registration

Specifications Table

Feature	Specification
Blade Bore [Metric]	30 mm
Product Width [Metric]	650 mm
No Load Speed (RPM)	4800
Product Height [Metric]	330 mm
Product Weight [Metric]	26.5 Kg
Blade Diameter [Metric]	250 mm
Max. Depth of Cut at 45° [Metric]	55 mm
Max. Depth of Cut at 90° [Metric]	77 mm
Depth [Metric]	650 mm
Power Source	Corded
Max. Ripping Capacity [Right] [Metric]	825 mm
Packaging	Carton
Power Input	2000 W
Product Length [Metric]	680 mm



DeWalt DCBP320-B1

POWERSTACK 20V MAX 3.5AH BATTERY

Introduction

The **20V MAX* XR® 3.5ah battery** delivers 50% more power and a longer lifespan. Engineered with pouch cell technology, our best performing 20V MAX* 3.5ah battery” Powers through tough jobs, day in and day out. XR® batteries are a part of our best performing line of 20V MAX* batteries" and are compatible with 20V MAX* tools.

Key Features

- **50% more power** - tackle tough jobs with 50% more power.
- **Longer lifespan** - help maximize longevity day in and day out with this battery that delivers longer life than traditional cylindrical batteries.
- **Compact size** - work in tight spaces with an ergonomic design that enhances maneuverability without sacrificing power.
- **Resists wear-and-tear** - take on the elements with a durable, overmolded base designed to provide a high level of impact resistance.
- **State-of-charge** - get quick visibility to your battery's state-of-charge with the LED indicator to help avoid interruptions.
- **Part of our best performing line of 20V MAX batteries*** - these XR® batteries are compatible with 20V MAX* tools and chargers.

Specifications Table

<u>Feature</u>	<u>Specification</u>
Specification Item	Value
Product Type	Battery
Voltage	20V
Cordless or Corded	Cordless
Power Source	Battery
Total Number of Batteries	1
Battery Amp Hours	3.5Ah
Charger Included	No
Piece Count	1
Compatibility	20V MAX* Tools
Assembled Product Length	5.24-in
Assembled Product Weight	1.19-lbs
Assembled Product Width	2.52-in
Assembled Product Height	4.8-in
Country Of Origin	Mexico
Barcode	885911958073
Individual or Set	Individual



DeWalt DCBP520-B1

POWERSTACK 20V MAX 5Ah Battery

Introduction

The **20V MAX* XR® 5ah battery** delivers 50% more power and a longer lifespan. Engineered with pouch cell technology, our best performing 20V MAX* 5ah battery” Powers through tough jobs, day in and day out. XR® batteries are a part of our best performing line of 20V MAX* batteries” and are compatible with 20V MAX* tools.

Key Features

- 50% more power - tackle tough jobs with 50% more power.
- Longer lifespan - help maximize longevity day in and day out with this battery that delivers an increase of charge cycles over the lifetime of battery.
- Compact size - work in tight spaces with an ergonomic design that enhances manoeuvrability without sacrificing power.
- Resists wear-and-tear - take on the elements with a durable, overmolded base designed to provide a high level of impact resistance.
- State-of-charge - get quick visibility to your batteries' state-of-charge with the LED indicator to help avoid interruptions.
- Part of our best performing line of 20V MAX* batteries” - innovative battery technologies designed to deliver certainty for the world’s toughest pros.

Specifications Table

<u>Feature</u>	<u>Specification</u>
Product Type	Battery
Voltage	20V
Cordless or Corded	Cordless
Power Source	Battery
Total Number of Batteries	1
Battery Amp Hours	5.0Ah
Charger Included	No
Charge Time	90
Piece Count	1
Compatibility	20V MAX* Tools
Assembled Product Length	7.06-in
Assembled Product Weight	1.75-lbs
Assembled Product Width	3.5-in
Assembled Product Height	7.5-in
Country Of Origin	China
Barcode	885911834919
Individual or Set	Individual



DeWalt DCB2108-B1

20V MAX XR 8 AH BATTERY - TABLESS

Introduction

The **20V MAX* XR® 8ah battery** delivers 50% more power and a longer lifespan. Engineered with tabless cell technology, our best performing 20V MAX* 8ah battery" Powers through tough jobs, day in and day out. XR® batteries are a part of our best performing line of 20V MAX* batteries" and are compatible with 20V MAX* tools.

Key Features

- **50% more power** - tackle tough jobs with 50% more power.
- **Longer lifespan** - help maximize longevity day in and day out with this battery that delivers longer life than traditional cylindrical batteries.
- **Resists wear-and-tear** - take on the elements with a durable, overmolded base designed to provide a high level of impact resistance.
- **State-of-charge** - get quick visibility to your battery's state-of-charge with the LED indicator to help avoid interruptions.
- **Part of our best performing line of 20V MAX* batteries** - these XR® batteries are compatible with 20V MAX* tools and chargers.

Specifications Table

Feature	Specification
Product Type	Battery
Voltage	20V
Cordless or Corded	Cordless
Power Source	Battery
Total Number of Batteries	1
Battery Amp Hours	8.0Ah
Charger Included	No
Piece Count	1
Compatibility	20V MAX* Tools
Assembled Product Length	5.88-in
Assembled Product Weight	2.2-lbs
Assembled Product Width	3.8-in
Assembled Product Height	5.6-in
Country Of Origin	Mexico
Barcode	885911963350
Individual or Set	Individual

DeWalt DCD240X2-GB

60V XR Paddle Mixer 9.0Ah x2

Introduction

Introducing the world's first **60V cordless paddle mixer** with the power of corded. Ideal for on-site mixing applications such as plaster, render and epoxy. 54V brushless motor for extended runtime, dual handle design and 5 speed settings for increased control in various materials.

Key Features

- Standard M14 paddle connection for user prefer paddle
- 160mm centre pull down swirl paddle for quick and consistent mixing

Specifications Table

<u>Feature</u>	<u>Specification</u>
No Load Speed (RPM)	0-725
Battery Capacity	9 Ah
Product Weight [Metric]	5.8 Kg
Number of Speed Settings	5
Max Torque [Metric]	50 Nm
Power Source	Cordless
Specification Item	Value

DeWalt DCH733N-XJ

60V MAX XR 48mm SDS-Max Hammer

Introduction

The **DEWALT 60V brushless motor** and high-capacity battery delivers 13.3 Joules of impact energy which offers a maximum drilling capacity of 48mm in solid concrete. Despite its high performance the DCH733 features class leading vibration of 9.0m/s² thanks to Perform and Protect features including an Active Vibration Control handle and an anti-rotation system which detects a loss of tool control and reacts instantly by cutting power. Bare unit, batteries and charger sold separately.

Key Features

- An anti-rotation system detects a loss of tool control, and reacts by instantly cutting the power
- Active vibration control system incorporating a floating handle delivers extremely low vibration of 9.6m/s² when drilling in concrete and 9m/s² when in chiselling mode. Reduces fatigue whilst increasing safety, comfort and productivity
- Rotation-stop for demolition applications in brick, masonry and light chasing in concrete
- Perform & Protect: low vibration at 9m/s², minimising user fatigue
- Brushless motor for improved runtime and reduced maintenance
- Electronic speed and impact energy control
- Ideal for drilling anchor fixing and through holes in concrete and masonry up to 48 mm in diameter. Core drilling up to 125 mm
- Anti-Rotation and service indicators
- LED service indicator

Specifications Table

<u>Feature</u>	<u>Specification</u>
Product Type	Rotary Hammer Drill
Voltage	54V
Cordless or Corded	Cordless
Power Source	Battery
Motor Type	Brushless
Tool Only	Yes
Total Number of Batteries	0
Charger Included	No
Total Number of Batteries	0

DeWalt DCH773N-XJ

60V MAX XR 10Kg SDS Combination Hammer

Introduction

The hardest hitting cordless **SDS Max hammer** on the market. The DEWALT 54V brushless motor and XR FLEXVOLT high-capacity battery delivers 19.4 Joules of impact energy which offers a maximum drilling capacity of 52mm in solid concrete. Despite its high performance the DCH733 features class leading vibration of 10.1m/s² thanks to Perform and Protect features including an Active Vibration Control handle and an anti-rotation system which detects a loss of tool control and reacts instantly by cutting power. Bare unit, batteries and charger sold separately.

Key Features

- **True corded performance**
- **An anti-rotation system detects a loss of tool control, and reacts by instantly cutting the power**
- **Active vibration control system incorporating a floating rear handle and damped side handle to reduce vibration**
- **Perform & protect: low vibration at 10.1m/s², minimizing user fatigue**
- **Brushless motor for improved runtime and reduced maintenance**
- **LED service indicator**

Specifications Table

Specification	Details
Product Type	Rotary Hammer Drill
Voltage	54 V
Cordless or Corded	Cordless
Power Source	Battery
Motor Type	Brushless
Tool Only	Yes
Total Number of Batteries	0
Charger Included	No
Piece Count	1
Assembled Product Height	24.13-cm
Assembled Product Weight	0.06-kg
Barcode	5035048715710
Country Of Origin	Belgium

DeWalt DCM572N-XJ

60V MAX Brushless Blower

Introduction

Clear jobsite debris with the powerful **60V MAX Brushless Blower**. The high-efficiency brushless motor maximizes runtime and motor life, and it moves 423 CFM of air at 129 MPH. The lightweight, ergonomic design enhances control and minimizes stress on the forearm. Use the flat concentrator nozzle to power through the most stubborn debris like wood scraps and trash with air speed up to 175 MPH. Variable speed trigger and speed lock give you precise power control and runtime management. Bare unit, batteries and charger sold separately.

Key Features

- **Compact & Lightweight Design:** Only 6.9" front to back and weighing just 1.2 kg (tool only), perfect for confined spaces and reduces user fatigue.
- **Brushless Motor Technology:** Provides increased efficiency, longer runtime, and enhanced durability.
- **Hammer Function:** Enables efficient drilling in masonry and concrete.
- **High Performance:** Delivers up to 65 Nm of torque for tough drilling and fastening tasks.
- **2-Speed Transmission:** Optimizes speed and control for a variety of applications.
- **Ergonomic Handle:** Ensures comfort and control during extended use.
- **LED Work Light:** Illuminates the work area for improved visibility.
- **20V MAX Compatibility:** Works with all DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Battery Voltage	54 V
Noise Level	99.5
Secondary Handle	No
CE Mark	Yes
Battery Capacity	5 Ah
Product Weight [Metric]	3.2 Kg
Battery Included	No
Number of Pieces	1
Product Pack Quantity	1
Power Source	Cordless
Packaging	Carton
Power	54
Battery Capacity	5 Ah

DeWalt DCMBA572N-KR

60V MAX AXIAL BLOWER

Introduction

Designed for the fast and effective removal of construction debris, workshop waste, leaves, twigs, moss and other stubborn garden matter, this versatile and powerful cordless blower will be welcomed by an array of professional users including construction teams, carpenters, metal and woodworkers, gardeners, landscapers, park clean-up workers and clearance specialists. Bare unit, batteries and charger sold separately.

Key Features

- **BALANCED DESIGN:** Ergonomically designed with an axial, in-line fan to optimise the working angle. The lightweight design at only 3.1kg (without battery) minimises fatigue during extended operation.
- **3 YEAR GUARANTEE:** Tool covered by extended warranty, subject to registration.
- **PART OF THE CORDLESS 54V XR FLEXVOLT SYSTEM:** Power of Corded. Freedom Of Cordless.

Specifications Table

Specification	Details
Battery Voltage	54 V
Noise Level	107
Secondary Handle	No
CE Mark	Yes
Product Weight [Metric]	3.1 Kg
Battery Included	No
Power Source	Cordless
Packaging	Carton
Power	54



DeWalt DCS7485T2-GB

60V MAX XR Table Saw Kitted (6.0Ah x2)

Introduction

The world's first cordless table saw is powerful enough to cut 92m of 19mm OSB board in a single charge. With a cut depth of 65mm at 90°, a 610mm rip capacity and 1220 x 2440mm capacity when used without the fence its a breakthrough in cordless power tool technology. With 2 X 6Ah batteries and charger.

Key Features

- **COMPACT DESIGN:** 22kg weight and optimised footprint make this a super portable saw
- **RACK & PINION FENCE:** Front and rear fence lock, with a large clear scale for an extremely accurate and easy to use saw
- **STEEL ROLL CAGE:** Protects against jobsite drops and impacts
- **CAST TABLE TOP:** Designed to ensure accuracy and precision
- **OVERLOAD PROTECTION:** Ensures powerful performance in hard, wet or frozen woods
- **SIMPLE BEVEL LOCK:** Quick bevel lock with large scale for easy, accurate adjustments
- **3 YEAR GUARANTEE:** Tool and battery covered by extended warranty, subject to registration
- **PART OF THE CORDLESS 54V XR FLEXVOLT SYSTEM:** Power of Corded. Freedom Of Cordless

Specifications Table

Specification	Details
Depth [Metric]	605 mm
Max. Ripping Capacity [Left] [Metric]	318 mm
Power Source	Cordless
Voltage	54 V
Product Height [Metric]	330 mm
Product Weight [Metric]	21.5 Kg
Max. Depth of Cut at 45° [Metric]	45 mm
Max. Depth of Cut at 90° [Metric]	65 mm
Weight (Including Battery) [Metric]	23 Kg
Blade Diameter [Metric]	210 mm
Max. Ripping Capacity [Right] [Metric]	610 mm
Packaging	Carton
Product Length [Metric]	605 mm
Product Width [Metric]	605 mm
Blade Bore [Metric]	30 mm
Table size [Metric]	485 x 485 mm
Battery Capacity	6 Ah



DeWalt DCD701N-KR

12V Brushless Subcompact Drill Driver

Introduction

The **DCD701 12V Brushless Subcompact Drill Driver** is designed for precision applications like small pilot holes, but also can handle up to a 20mm drill bit into Timber. Small enough to fit in the tightest places at only 152mm long and enough power to get the job done with 57.5Nm of torque and a 2 speed transmission. It also features a bright LED positioned on the foot to illuminate all work areas.

Key Features

- Efficient brushless motor gives 15% more runtime than previous generation
- Only 0.9kg (tool only) for ultimate portability and ease of use
- 15 position adjustable torque control for consistent screw driving into a variety of materials
- 10mm single sleeve keyless chuck with automatic spindle lock for quick and easy bit change

Specifications Table

Specification	Details
Battery Voltage	12 V
Chuck Capacity [Metric]	10 mm
No Load Speed (RPM)	0-425/0-1500
Battery Capacity	2 Ah
Product Weight [Metric]	0.87 Kg
Product Height [Metric]	185 mm
Power Output	250 W
Max Torque [Metric]	57.5 Nm
Maximum Drilling Diameter [Steel] [Metric]	10 mm
Variable Speed	Yes , Yes
Depth [Metric]	60 mm
Maximum Drilling Diameter [Wood] [Metric]	20 mm
Max. Drilling Capacity (Wood) [Metric]	20 mm
Product Length [Metric]	152 mm

DeWalt DCK2111L2T-B1

12V Brushless Twin Kit DCD706 + DCF801

Introduction

12V XR Brushless twin kit including, DCD706 Hammer Drill Driver, DCF801 Impact Driver, 2 X DCB124 3Ah Batteries, DCB112 charger and TSTAK Kitbox.

Key Features

- **Kit contains the following:** Brushless Sub-Compact Hammer Drill Driver, Brushless Sub-Compact Impact Driver, 3.0Ah Batteries, Multi-voltage charger, TSTAK II Kit Box
- The innovative grooving stop allows the adjustment of the cutting depth for grooving and rebating applications
- Linear horizontal rails utilise bronze guides to provide maximum precision when cutting materials up to 345 mm wide

Specifications Table

Specification	Details
Battery Voltage	12 V
Battery Capacity	3 Ah
No Load Speed (RPM)	0-400/1200/1900
Power Type	Cordless
Number of Pieces	3
Power Source	Cordless

DeWalt DCB090-KR

10.8V-18V USB Power Source

Introduction

The DCB090 allows your DEWALT batteries to be used as a portable USB charger. Features 2 USB outputs to charge portable electronic devices anywhere. Compatible with 12V XR, 18V XR and XR FLEXVOLT batteries

Key Features

- Two USB outlets allow charging of wide range of small electronic devices
- Bright and highly visible state of charge indicator
- Transforms your XR battery into a portable charger
- Multi-voltage - compatible with 10.8V, 12V, 14.4V and 18V XR battery packs
- New 12V tools and batteries are 100% compatible with your existing 10.8V products

Specifications Table

Specification	Details
Product Width [Metric]	62 mm
Product Height [Metric]	39 mm
Product Weight [Metric]	0.09 Kg
Product Length [Metric]	97 mm

DeWalt DCB1104-B1

12V/20V XR 4A Compact Charger

Introduction

Charge your **DEWALT® 12V MAX, DEWALT® 20V MAX*, and FLEXVOLT® batteries** with the **DCB1104 charger**. This charger has a two-stage LED state of charge indicator to display when it is fully charged. The DCB1104 4a charger is 15% smaller than DCB115 4a charger making it portable. It also includes a mounting capability for a two screw wall mount (screws sold separately.)

Key Features

- **State of charge indicator:** two-stage LED state of charge indicator
- **Compatibility:** DEWALT® 12V MAX, DEWALT® 20V MAX*, and FLEXVOLT® batteries
- **Portability:** DCB1104 4a charger is 15% smaller than DCB115 4a charger.
- **Mounting capability:** two screw wall mounts (screws sold separately)

Specifications Table

Specification	Details
Product Type	Charger
Voltage	12V
Cordless or Corded	Corded
Power Source	Electric
Total Number of Batteries	0
Charger Included	Yes
Piece Count	1
Compatibility	DEWALT 12 to 20 Volt Lithium Ion Slide Packs
Assembled Product Length	5.63-in
Assembled Product Weight	1.3-lbs
Assembled Product Width	3.38-in
Assembled Product Height	6.5-in
Country Of Origin	United States
Barcode	885911790031
Individual or Set	Individual

DeWalt DCB126G-B1

12V MAX OIL-RESISTANT 5AH BATTERY

Introduction

Power your Xtreme™ 12V MAX tools with this **12V MAX oil-resistant 5ah battery** that features the runtime and performance needed for jobs in tight spots. This battery is compatible with Xtreme™ 12V MAX tools and 12V MAX chargers.

Key Features

- **Reliable runtime** - take on tough jobs with this battery that delivers a 5ah capacity for consistent runtime on the jobsite.
- **Combat harsh environments** - resist damage from oil, grease, and solvents with an oil-resistant housing.
- **State-of-charge** - get quick visibility to your battery's state-of-charge with the LED indicator to help avoid interruptions.
- **12V MAX compatibility** - this battery is compatible with Xtreme™ 12V MAX tools and 12V MAX chargers.

Specifications Table

Specification	Details
Product Type	Battery
Voltage	12V
Cordless or Corded	Cordless
Power Source	Battery
Total Number of Batteries	1
Battery Amp Hours	5.0Ah
Charger Included	No
Piece Count	1
Compatibility	12V MAX*
Assembled Product Length	3.5-in
Assembled Product Weight	0.97-lbs
Assembled Product Width	3-in
Assembled Product Height	4.19-in
Country Of Origin	China
Barcode	885911728423
Individual or Set	Individual

DeWalt DCB240-B1

20V Max 4.0Ah FlatÂ battery

Introduction

Power your 20V MAX* tools with this **20V MAX* 4Ah Battery** that features the runtime and performance needed for tough jobs. This battery is compatible with 20V MAX* tools and chargers.

Key Features

- **Reliable Runtime** - Take on tough jobs with this battery that delivers a 4Ah capacity for consistent runtime on the jobsite
- **State-Of-Charge** - Get quick visibility to your battery's state-of-charge with the LED indicator to help avoid interruptions
- **Part Of The 20V MAX* System** - This battery is compatible with 20V MAX* tools and chargers

Specifications Table

Specification	Details
Battery Capacity	4 Ah
Voltage	20 V
Number of Pieces	1
Product Length [Imperial]	7.375 in
Charge Time	45 min
Product Height [Imperial]	7 in
Product Width [Imperial]	3.5 in
Battery Type	20V MAX*
Battery Voltage	20 V
Product Weight [Imperial]	1.15 lbs

DeWalt DCE531B

20V MAX Pencil Vibrator

Introduction

Ideal for both industrial and residential jobsites the durable **20V MAX* pencil vibrator** offers 14,000 VPM under load for outstanding efficiency. The portable design offers ease of mobility and the isolated motor offers reliable durability. As a part of the expanding 20V MAX* system, this tool is compatible with all 20V MAX* batteries and chargers. Battery and charger sold separately

Key Features

- 1- 1/8 " diameter vibrator delivers maximum consolidation power
- 4 foot long flexible shaft for easy use and long reach
- 14,000 VPM (under load) delivers maximum consolidation efficiency

Specifications Table

Specification	Details
Product Type	Concrete Vibrator
Voltage	20V
Cordless or Corded	Cordless
Power Source	Battery
Tool Only	Yes
Motor Type	Brushed
Total Number of Batteries	0
Charger Included	No
Assembled Product Length	20.63-in
Assembled Product Weight	9.1-lbs
Assembled Product Width	21.17-in
Assembled Product Height	4.13-in
Country Of Origin	Mexico
Barcode	885911428101
Individual or Set	Individual

DeWalt DCS438N-XJ

20V MAX 76MM Cut Off Tool

Introduction

High performance 76mm Cutoff tool for professionals

Key Features

- **18V brushless motor:** enhanced efficiency and durability
- **Maximized cutting depth:** 22mm cutting depth capacity
- **Switchable blade direction:** forward or reverse cutting allows sparks and debris to be directed away from the user
- **Tool-free detent guard:** quickly adjust the guard to suit cutting direction and application
- **LED work light:** illuminates blade and workpiece for confident and accurate cutting
- **Lanyard ready™** attachment point is designed for users to utilize a lanyard to tether the tool and battery to rigid structures on jobsites
- **TOOL CONNECT™** chip pocket allows user to track and manage 18V cordless tools via app
- Lanyard ready connection protects user & tool from accidental drops when working overhead

Specifications Table

Specification	Details
Product Type	Cut-Off Tool
Voltage	18V
Cordless or Corded	Cordless
Power Source	Battery
Tool Only	Yes
Motor Type	Brushless
Total Number of Batteries	0
Charger Included	No
Variable Speed	No
Maximum Speed	333-Hz
Piece Count	1
Assembled Product Length	28.26-cm
Assembled Product Weight	1.18-kg
Assembled Product Width	15.4-cm
Assembled Product Height	12.38-cm
Country Of Origin	Mexico

DeWalt DCW210N-XJ

20V MAX Brushless Random Orbital Sander

Introduction

Our **20V MAX Brushless Random Orbital Sander** provides you with the power and runtime to get the job done. A 2.6mm orbit and variable speed control provides a high surface finish in all applications. Use the included dust bag or switch to an extractor with the Airlock compatible outlet.

Key Features

- Cordless technology for more user freedom
- Brushless Motor Technology for excellent efficiency
- Low vibration allowing for extended usage without fatigue
- Built in dust extraction port allowing direct connection to dust extractor, or DEWALT AirLock system
- Textured anti-slip top and body grip provides ultimate comfort and control during use
- Dust-sealed switch prevents contamination
- Dust sealed bearings and components for a long product life
- Uses hook and loop paper for consistent adhesion and fast changing

Specifications Table

Specification	Details
No Load Speed (RPM)	0-550
Product Weight [Metric]	0.93 Kg
Power Source	Corded , Corded
Power	1700 W

DeWalt DCF510

Cordless Sealed Head Ratchet

Introduction

The **DCF510 20V MAX XR® Brushless 3/8" & 1/2" Sealed Head Ratchet** from DEWALT is a versatile, high-performance cordless ratchet designed for automotive, maintenance, and repair professionals. Featuring a brushless motor and sealed head design, this tool delivers powerful fastening, extended runtime, and increased durability, even in demanding environments. The interchangeable anvil system allows users to switch between 3/8" and 1/2" drive sizes for maximum flexibility.

Key Features

- **Brushless Motor:** Provides longer runtime, increased efficiency, and extended tool life.
- **Sealed Head Design:** Protects internal components from dust, debris, and oils for enhanced durability.
- **Interchangeable Anvil System:** Easily switch between 3/8" and 1/2" drive sizes.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries for maximum portability.
- **Variable Speed Trigger:** Offers precise control over fastening speed.
- **LED Work Light:** Illuminates the work area for improved visibility.
- **Ergonomic Grip:** Ensures comfort and control during extended use.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Drive Size	3/8" (9.5 mm) & 1/2" (12.7 mm) interchangeable
Max Torque	70 Nm (3/8"), 95 Nm (1/2")
No Load Speed	0-300 rpm
Head Type	Sealed
LED Work Light	Yes
Weight (tool only)	Approx. 1.2 kg
Accessories Included	3/8" and 1/2" anvils (battery and charger sold separately)

DeWalt DCF630

Cordless Sealed Head Ratchet

Introduction

The **DCF630 20V MAX XR® Brushless Drywall Screwgun** from DEWALT is a high-performance, cordless screwgun designed for professional drywall installers and contractors. Featuring a powerful brushless motor and lightweight, ergonomic design, this tool delivers fast, efficient, and consistent screw driving with extended runtime. Its cordless convenience and advanced features make it ideal for large drywall projects and overhead applications.

Key Features

- **Brushless Motor:** Provides longer runtime, increased efficiency, and extended tool life.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries for maximum portability.
- **High Speed:** Delivers up to 4,500 rpm for fast and efficient drywall installation.
- **Ergonomic Design:** Lightweight and comfortable grip for reduced user fatigue.
- **Lock-On Nose Cone:** Maintains consistent screw depth and allows for quick removal.
- **LED Work Light:** Illuminates the work area for improved visibility.
- **Compatible with Collated Magazine Attachment:** For increased productivity (sold separately).

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
No Load Speed	0-4,500 rpm
Chuck Type	1/4" Hex
Nose Cone	Removable, lock-on
LED Work Light	Yes
Weight (tool only)	Approx. 1.1 kg
Accessories Included	Belt hook (battery and charger sold separately)

DeWalt DCF845

Cordless Impact Driver

Introduction

The **DCF845 20V MAX XR® 3-Speed 1/4" Impact Driver** from DEWALT is a high-performance, compact, and versatile cordless impact driver designed for professional contractors and serious DIY users. Featuring a powerful brushless motor and three speed settings, this tool delivers outstanding torque, control, and runtime for a wide range of fastening applications. Its ergonomic design and advanced features make it ideal for demanding job site tasks.

Key Features

- **Brushless Motor:** Provides longer runtime, increased efficiency, and extended tool life.
- **3-Speed Settings:** Offers optimal control for a variety of fastening applications.
- **High Torque Output:** Delivers up to 205 Nm of torque for tough jobs.
- **Compact & Lightweight Design:** Ideal for working in tight spaces and overhead applications.
- **LED Work Light:** Illuminates the work area for improved visibility.
- **Ergonomic Grip:** Ensures comfort and control during extended use.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries for maximum portability.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Max Torque	205 Nm
No Load Speed	0-1,000 / 0-2,800 / 0-3,250 rpm (3-speed)
Impact Rate	0-1,900 / 0-3,300 / 0-3,800 ipm (3-speed)
Chuck Type	1/4" Hex
LED Work Light	Yes
Weight (tool only)	Approx. 1.0 kg
Accessories Included	Belt hook (battery and charger sold separately)

DeWalt DCF850

Cordless Impact Driver

Introduction

The **DCF850 20V MAX XR® 3-Speed 1/4" Impact Driver** from DEWALT is an ultra-compact, high-performance cordless impact driver designed for professional contractors and demanding users. Featuring a powerful brushless motor and three speed settings, this tool delivers exceptional torque, control, and runtime in a compact form factor, making it ideal for tight spaces and overhead applications.

Key Features

- **Ultra-Compact Design:** Only 100 mm (3.97") in length for access in confined spaces.
- **Brushless Motor:** Provides longer runtime, increased efficiency, and extended tool life.
- **3-Speed Settings:** Offers optimal control for a variety of fastening applications.
- **High Torque Output:** Delivers up to 205 Nm of torque for tough jobs.
- **LED Work Light:** Illuminates the work area for improved visibility.
- **Ergonomic Grip:** Ensures comfort and control during extended use.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries for maximum portability.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Max Torque	205 Nm
No Load Speed	0-1,000 / 0-2,800 / 0-3,250 rpm (3-speed)
Impact Rate	0-1,950 / 0-3,400 / 0-3,800 ipm (3-speed)
Chuck Type	1/4" Hex
Tool Length	100 mm (3.97")
LED Work Light	Yes
Weight (tool only)	Approx. 1.0 kg
Accessories Included	Belt hook (battery and charger sold separately)

DeWalt DCF860

Cordless High Torque Impact Driver

Introduction

The **DCF860 20V MAX XR® Brushless High Torque Impact Driver** from DEWALT is engineered for professional contractors and users who require maximum fastening power in a compact, cordless tool. Featuring a robust brushless motor, this impact driver delivers exceptional torque, speed, and runtime for heavy-duty applications. Its ergonomic design and advanced features make it ideal for demanding job site tasks.

Key Features

- **Brushless Motor:** Provides longer runtime, increased efficiency, and extended tool life.
- **High Torque Output:** Delivers up to 270 Nm of torque for the toughest fastening jobs.
- **Variable Speed Trigger:** Offers precise control for a variety of applications.
- **Compact & Lightweight Design:** Ideal for working in tight spaces and overhead applications.
- **LED Work Light:** Illuminates the work area for improved visibility.
- **Ergonomic Grip:** Ensures comfort and control during extended use.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries for maximum portability.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Max Torque	270 Nm
No Load Speed	0-3,400 rpm
Impact Rate	0-4,200 ipm
Chuck Type	1/4" Hex
LED Work Light	Yes
Weight (tool only)	Approx. 1.2 kg
Accessories Included	Belt hook (battery and charger sold separately)

DeWalt DCF870

Cordless Hydraulic Impact Driver

Introduction

The **DCF870 20V MAX Brushless Hydraulic Impact Driver** from DEWALT is designed for professionals who need powerful fastening with reduced noise and vibration. Featuring DEWALT’s innovative hydraulic mechanism and a brushless motor, this tool delivers smooth, quiet operation and high performance for demanding fastening applications. Its compact, ergonomic design makes it ideal for use in tight spaces and extended periods.

Key Features

- **Hydraulic Mechanism:** Provides quieter operation and less vibration compared to standard impact drivers.
- **Brushless Motor:** Delivers longer runtime, increased efficiency, and extended tool life.
- **High Torque Output:** Suitable for a wide range of fastening tasks.
- **Compact & Lightweight Design:** Ideal for working in confined spaces and overhead applications.
- **Variable Speed Trigger:** Offers precise control for different applications.
- **LED Work Light:** Illuminates the work area for improved visibility.
- **Ergonomic Grip:** Ensures comfort and control during extended use.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries for maximum portability.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Max Torque	226 Nm
No Load Speed	0-3,200 rpm
Impact Rate	0-3,800 ipm
Chuck Type	1/4" Hex
LED Work Light	Yes
Weight (tool only)	Approx. 1.0 kg
Accessories Included	Belt hook (battery and charger sold separately)

DeWalt DCF923

Cordless Impact Driver

Introduction

The **DCF923 20V MAX ATOMIC™ 3/8 in. Cordless Impact Wrench (Hog Ring)** from DEWALT is a compact, lightweight, and powerful solution for fastening and loosening tasks in tight spaces. Designed for professional mechanics, contractors, and serious DIY users, this impact wrench features a brushless motor for extended runtime and durability. The ATOMIC™ design delivers high performance in a compact form, making it ideal for automotive, maintenance, and assembly applications.

Key Features

- **Compact ATOMIC™ Design:** Only 5.1" in length for access in confined spaces.
- **Brushless Motor:** Provides longer runtime, increased efficiency, and extended tool life.
- **3/8" Hog Ring Anvil:** Allows for quick and easy socket changes.
- **High Torque Output:** Delivers up to 300 Nm (221 ft-lbs) of max fastening torque.
- **Variable Speed Trigger:** Offers precise control for a variety of applications.
- **LED Work Light:** Illuminates the work area for improved visibility.
- **Ergonomic Grip:** Ensures comfort and control during extended use.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries for maximum portability.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Drive Size	3/8" (9.5 mm) Hog Ring
Max Fastening Torque	300 Nm (221 ft-lbs)
No Load Speed	0-2,850 rpm
Impact Rate	0-3,250 ipm
Tool Length	5.1" (130 mm)
LED Work Light	Yes
Weight (tool only)	Approx. 1.1 kg
Accessories Included	Belt hook (battery and charger sold separately)

DeWalt DCF911

Cordless Impact Wrench

Introduction

The **DCF911 20V MAX Brushless 1/2" Hog Ring Impact Wrench** from DEWALT is a compact, high-torque cordless impact wrench designed for professional mechanics, contractors, and serious DIY users. Featuring a powerful brushless motor and a convenient hog ring anvil, this tool delivers up to 338 Nm of fastening torque in a lightweight, ergonomic package. Its compact design makes it ideal for use in tight spaces and overhead applications.

Key Features

- **Brushless Motor:** Provides longer runtime, increased efficiency, and extended tool life.
- **High Torque Output:** Delivers up to 338 Nm of max fastening torque for demanding applications.
- **1/2" Hog Ring Anvil:** Allows for quick and easy socket changes.
- **Compact & Lightweight Design:** Ideal for working in confined spaces and overhead tasks.
- **Variable Speed Trigger:** Offers precise control for a variety of fastening jobs.
- **LED Work Light:** Illuminates the work area for improved visibility.
- **Ergonomic Grip:** Ensures comfort and control during extended use.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries for maximum portability.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Drive Size	1/2" (12.7 mm) Hog Ring
Max Fastening Torque	338 Nm
No Load Speed	0-2,500 rpm
Impact Rate	0-3,600 ipm
Tool Length	Approx. 125 mm
LED Work Light	Yes
Weight (tool only)	Approx. 1.3 kg
Accessories Included	Belt hook (battery and charger sold separately)

DeWalt DCF921

Cordless Impact Wrench

The **DCF921 20V MAX 1/2" Impact Wrench Hog Ring** from DEWALT is a compact, high-performance cordless impact wrench designed for professional mechanics, contractors, and serious DIY users. Featuring a powerful brushless motor and a convenient hog ring anvil, this tool delivers impressive torque and speed for fastening and loosening tasks. The kit includes a 20V MAX battery and charger, providing everything you need for efficient operation on the job site.

Key Features

- **Brushless Motor:** Delivers longer runtime, increased efficiency, and extended tool life.
- **High Torque Output:** Up to 406 Nm of max fastening torque for demanding applications.
- **1/2" Hog Ring Anvil:** Allows for quick and easy socket changes.
- **Compact & Lightweight Design:** Ideal for working in tight spaces and overhead tasks.
- **Variable Speed Trigger:** Offers precise control for a variety of fastening jobs.
- **LED Work Light:** Illuminates the work area for improved visibility.
- **Ergonomic Grip:** Ensures comfort and control during extended use.
- **Complete Kit:** Includes 20V MAX battery and charger for immediate use.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (included)
Motor Type	Brushless
Drive Size	1/2" (12.7 mm) Hog Ring
Max Fastening Torque	406 Nm
No Load Speed	0-2,500 rpm
Impact Rate	0-3,600 ipm
Tool Length	Approx. 125 mm
LED Work Light	Yes
Weight (tool only)	Approx. 1.5 kg
Accessories Included	1 x 20V MAX battery, charger, belt hook

DeWalt DCF922

Cordless Impact Wrench

Introduction

The **DCF922 20V MAX Brushless ATOMIC™ 1/2" Detent Pin Impact Wrench** from DEWALT is a compact, high-torque cordless impact wrench designed for professional mechanics, contractors, and serious DIY users. Featuring a powerful brushless motor and ATOMIC™ compact design, this tool delivers up to 406 Nm of fastening torque in a lightweight, ergonomic package. The detent pin anvil ensures secure socket retention, making it ideal for automotive, maintenance, and assembly applications.

Key Features

- **ATOMIC™ Compact Design:** Only 125 mm in length for access in confined spaces.
- **Brushless Motor:** Provides longer runtime, increased efficiency, and extended tool life.
- **High Torque Output:** Delivers up to 406 Nm of max fastening torque for demanding applications.
- **1/2" Detent Pin Anvil:** Ensures secure socket retention for heavy-duty tasks.
- **Variable Speed Trigger:** Offers precise control for a variety of fastening jobs.
- **LED Work Light:** Illuminates the work area for improved visibility.
- **Ergonomic Grip:** Ensures comfort and control during extended use.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries for maximum portability.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Drive Size	1/2" (12.7 mm) Detent Pin
Max Fastening Torque	406 Nm
No Load Speed	0-2,500 rpm
Impact Rate	0-3,600 ipm
Tool Length	125 mm
LED Work Light	Yes
Weight (tool only)	Approx. 1.5 kg
Accessories Included	Belt hook (battery and charger sold separately)

DeWalt DCF900

Cordless Impact Wrench

Introduction

The **DCF900 20V MAX Brushless 1/2" Hog Ring Impact Wrench** delivers extreme torque and durability for heavy-duty fastening and loosening applications. Designed for professional mechanics and contractors, this tool features a powerful brushless motor and a convenient hog ring anvil for quick socket changes. The kit includes two 20V MAX batteries, charger, and TSTAK case.

Key Features

- **Brushless Motor:** Delivers up to 1396 Nm of max fastening torque.
- **1/2" Hog Ring Anvil:** Quick and easy socket changes.
- **Variable Speed Trigger:** Precise control for various applications.
- **LED Work Light:** Illuminates work area.
- **Ergonomic Design:** Comfortable grip for extended use.
- **Complete Kit:** Includes 2 batteries, charger, and TSTAK case.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (included)
Motor Type	Brushless
Drive Size	1/2" Hog Ring
Max Fastening Torque	1396 Nm
No Load Speed	0-650 / 0-1200 / 0-1750 rpm (3-speed)
Impact Rate	0-2400 ipm
LED Work Light	Yes
Weight (tool only)	Approx. 3.0 kg
Accessories Included	2 x 20V MAX batteries, charger, TSTAK case

DeWalt DCF961

Cordless Impact Wrench

Introduction

The **DCF961 20V MAX XR® Brushless 1/2" Hog Ring Impact Wrench** is engineered for the most demanding fastening jobs, offering up to 1626 Nm of torque. Its brushless motor and robust design ensure reliability and power for industrial and automotive applications. Supplied in a TSTAK case for easy transport and storage.

Key Features

- **Extreme Torque:** Up to 1626 Nm for heavy-duty applications.
- **Brushless Motor:** Enhanced efficiency and durability.
- **1/2" Hog Ring Anvil:** Fast socket changes.
- **Variable Speed Trigger:** Precise control.
- **LED Work Light:** Improved visibility.
- **TSTAK Case:** Convenient storage and transport.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Drive Size	1/2" Hog Ring
Max Fastening Torque	1626 Nm
No Load Speed	0-650 / 0-1200 / 0-1750 rpm (3-speed)
Impact Rate	0-2400 ipm
LED Work Light	Yes
Weight (tool only)	Approx. 3.1 kg
Accessories Included	TSTAK case

DeWalt DCF964

Cordless High Torque Impact Wrench

Introduction

The **DCF964 20V MAX XR® Brushless 3/4" Hog Ring High Torque Impact Wrench** is built for industrial-grade fastening, delivering up to 1925 Nm of torque. Its brushless motor and 3/4" hog ring anvil make it ideal for heavy machinery and construction tasks. Comes in a TSTAK case for protection and portability.

Key Features

- **Maximum Torque:** Up to 1925 Nm for the toughest jobs.
- **Brushless Motor:** Superior power and longevity.
- **3/4" Hog Ring Anvil:** Quick socket changes.
- **Variable Speed Trigger:** Enhanced control.
- **LED Work Light:** Better visibility.
- **TSTAK Case:** Secure storage and transport.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Drive Size	3/4" Hog Ring
Max Fastening Torque	1925 Nm
No Load Speed	0-650 / 0-1200 / 0-1750 rpm (3-speed)
Impact Rate	0-2400 ipm
LED Work Light	Yes
Weight (tool only)	Approx. 3.5 kg
Accessories Included	TSTAK case

DeWalt DCG407

Cordless Angle Grinder

Introduction

The **DCG407 20V MAX Brushless XR® 4" Slide Switch Small Angle Grinder** is designed for professional cutting and grinding applications. Its brushless motor delivers high performance and extended runtime, while the slide switch offers easy operation. The kit includes two batteries, charger, and TSTAK case.

Key Features

- **Brushless Motor:** High efficiency and durability.
- **Slide Switch:** Easy on/off operation.
- **4" (100 mm) Wheel Capacity:** Versatile for various tasks.
- **Electronic Brake:** Enhanced safety.
- **Ergonomic Design:** Comfortable grip.
- **Complete Kit:** Includes 2 batteries, charger, TSTAK case.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (included)
Motor Type	Brushless
Wheel Diameter	4" (100 mm)
No Load Speed	9,000 rpm
Switch Type	Slide switch
Electronic Brake	Yes
Weight (tool only)	Approx. 1.8 kg
Accessories Included	2 x 20V MAX batteries, charger, TSTAK case

DeWalt DCG408

Cordless Angle Grinder

Introduction

The **DCG408 20V MAX Brushless XR® 4" Paddle Switch Small Angle Grinder** is a compact, high-performance grinder ideal for cutting and grinding in tight spaces. The brushless motor ensures long life and consistent power, while the paddle switch provides enhanced control and safety.

Key Features

- **Brushless Motor:** Delivers longer runtime and durability.
- **Paddle Switch:** Improved control and safety.
- **4" (100 mm) Wheel Capacity:** Suitable for various materials.
- **Electronic Brake:** Stops the wheel quickly.
- **Ergonomic Design:** Comfortable for extended use.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Wheel Diameter	4" (100 mm)
No Load Speed	9,000 rpm
Switch Type	Paddle switch
Electronic Brake	Yes
Weight (tool only)	Approx. 1.8 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCG413

Cordless Angle Grinder

Introduction

The **DCG413 20V MAX Brushless XR® 4.5" Paddle Switch Small Angle Grinder*** is designed for professional cutting and grinding applications. Its brushless motor delivers high performance and extended runtime, while the paddle switch provides enhanced control and safety. The compact design makes it ideal for use in tight spaces.

Key Features

- **Brushless Motor:** Delivers longer runtime, increased efficiency, and extended tool life.
- **Paddle Switch:** Enhanced control and safety.
- **4.5" (115 mm) Wheel Capacity:** Versatile for various cutting and grinding tasks.
- **Electronic Brake:** Stops the wheel quickly for improved safety.
- **Kickback Brake:** Engages in the event of a pinch, stall, or bind-up.
- **Ergonomic Design:** Comfortable grip for extended use.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Wheel Diameter	4.5" (115 mm)
No Load Speed	9,000 rpm
Switch Type	Paddle switch
Electronic Brake	Yes
Kickback Brake	Yes
Weight (tool only)	Approx. 1.75 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCG426

Cordless Die Grinder

Introduction

The **DCG426 20V MAX Brushless Die Grinder** features a dead man's switch for enhanced safety and control. Its brushless motor provides powerful performance and extended runtime, making it ideal for metalworking, fabrication, and maintenance tasks.

Key Features

- **Brushless Motor:** Delivers longer runtime and durability.
- **Dead Man's Switch:** Enhanced safety and control.
- **Variable Speed:** Allows for precise control over grinding applications.
- **LED Work Light:** Illuminates the work area.
- **Ergonomic Design:** Comfortable grip for extended use.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Collet Size	1/4" (6 mm)
No Load Speed	0-25,000 rpm (variable speed)
Switch Type	Dead man's switch
LED Work Light	Yes
Weight (tool only)	Approx. 1.2 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCGG571

Cordless Grease Gun

Introduction

The **DCGG571 20V MAX Cordless Grease Gun** is designed for fast and efficient lubrication in automotive, agricultural, and industrial applications. Its powerful motor delivers up to 10,000 PSI, and the 42" flexible hose allows access to hard-to-reach fittings.

Key Features

- **High Pressure Output:** Up to 10,000 PSI for tough grease applications.
- **42" Flexible Hose:** Reaches difficult fittings.
- **LED Work Light:** Illuminates fittings and work area.
- **Variable Speed Trigger:** Precise control of grease flow.
- **Ergonomic Design:** Comfortable grip for extended use.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Max Pressure	10,000 PSI
Hose Length	42" (1067 mm)
Grease Flow Rate	Up to 5 oz/min (142 g/min)
LED Work Light	Yes
Weight (tool only)	Approx. 3.6 kg
Accessories Included	Shoulder strap (battery and charger sold separately)

DeWalt DCH133

Cordless SDS-Plus Rotary Hammer

Introduction

The **DCH133 20V MAX Brushless 26mm SDS-Plus Rotary Hammer** is a compact and powerful tool for drilling and chiseling in concrete, masonry, and stone. Its brushless motor delivers high performance and extended runtime, making it ideal for construction and renovation projects.

Key Features

- **Brushless Motor:** Increased efficiency and longer runtime.
- **SDS-Plus Chuck:** Quick and secure bit changes.
- **3-Mode Operation:** Drill, hammer drill, and chisel.
- **Compact Design:** Easy to handle in tight spaces.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Chuck Type	SDS-Plus
Max Drilling Capacity	Concrete: 26 mm
Impact Energy	2.6 Joules
No Load Speed	0-1,550 rpm
Impact Rate	0-5,680 bpm
Weight (tool only)	Approx. 2.3 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCH263

Cordless SDS-Plus Rotary Hammer

Introduction

The **DCH263 20V MAX Brushless 28mm SDS+ 3 Mode Rotary Hammer** is engineered for heavy-duty drilling and chiseling in concrete and masonry. Its brushless motor and 3-mode operation provide versatility and power for demanding construction tasks.

Key Features

- **Brushless Motor:** Delivers high efficiency and extended tool life.
- **SDS+ Chuck:** Quick and secure bit changes.
- **3-Mode Operation:** Drill, hammer drill, and chisel.
- **High Impact Energy:** Up to 3.0 Joules for tough applications.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Chuck Type	SDS+
Max Drilling Capacity	Concrete: 28 mm
Impact Energy	3.0 Joules
No Load Speed	0-1,160 rpm
Impact Rate	0-4,600 bpm
Weight (tool only)	Approx. 3.6 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCH273

Cordless SDS-Plus Rotary Hammer

Introduction

The **DCH273 20V MAX Brushless 24mm SDS-Plus Rotary Hammer** is a compact, high-performance tool designed for drilling and light chiseling in concrete, masonry, and stone. Its brushless motor delivers extended runtime and durability, making it ideal for professional construction and renovation tasks.

Key Features

- **Brushless Motor:** Increased efficiency and longer runtime.
- **SDS-Plus Chuck:** Quick and secure bit changes.
- **3-Mode Operation:** Drill, hammer drill, and chisel.
- **Low Vibration:** Enhanced comfort during extended use.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Chuck Type	SDS-Plus
Max Drilling Capacity	Concrete: 24 mm
Impact Energy	2.1 Joules
No Load Speed	0-1,100 rpm
Impact Rate	0-4,600 bpm
Weight (tool only)	Approx. 2.5 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCK2050P1E1

Cordless SDS-Plus Rotary Hammer

Introduction

The **DCK2050P1E1 20V MAX Brushless ATOMIC™ Combo Kit** from DEWALT is a compact, high-performance cordless tool set designed for professionals and serious DIY users. This kit includes two ATOMIC™ series tools—a drill/driver and an impact driver—both featuring brushless motors for increased efficiency, longer runtime, and enhanced durability. The kit also includes two batteries, a charger, and a TSTAK case for convenient storage and transport, making it ideal for a wide range of drilling and fastening applications.

Key Features

- **ATOMIC™ Compact Design:** Lightweight and easy to use in tight spaces.
- **Brushless Motors:** Provide longer runtime, increased efficiency, and extended tool life.
- **Versatile Kit:** Includes both a drill/driver and an impact driver for a variety of tasks.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries for maximum portability.
- **LED Work Lights:** Illuminate the work area for improved visibility.
- **Ergonomic Grip:** Ensures comfort and control during extended use.
- **Complete Kit:** Includes two batteries, charger, and TSTAK case.

Specifications Table

Specification	Drill/Driver (DCD708)	Impact Driver (DCF809)
Power Source	20V MAX Lithium-Ion Battery (included)	20V MAX Lithium-Ion Battery (included)
Motor Type	Brushless	Brushless
Max Torque	65 Nm	170 Nm
No Load Speed	0-450 / 0-1,650 rpm (2-speed)	0-2,800 rpm
Chuck Size	13 mm (1/2")	1/4" Hex
Max Drilling Capacity	Wood: 30 mm / Metal: 13 mm	-
Impact Rate	-	0-3,200 ipm
Tool Length	160 mm	130 mm
Weight (tool only)	Approx. 1.1 kg	Approx. 1.0 kg
LED Work Light	Yes	Yes
Accessories Included	1 x 5.0Ah battery, 1 x 2.0Ah battery, charger, TSTAK case, belt hooks	

DeWalt DCN623

Cordless Pin Nailer

Introduction

The **DCN623 20V MAX XR® Brushless 23GA. Pin Nailer** is designed for precision fastening in trim, cabinetry, and woodworking. Its brushless motor provides consistent power and extended runtime, while the cordless design offers maximum portability.

Key Features

- **Brushless Motor:** Longer runtime and durability.
- **23GA. Pin Capacity:** For fine finish work.
- **Tool-Free Jam Release:** Quick and easy maintenance.
- **LED Work Light:** Illuminates the work area.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Nail Gauge	23GA
Nail Length Range	12 mm – 30 mm
Magazine Capacity	135 pins
Weight (tool only)	Approx. 2.0 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCN890

Cordless Concrete Nailer

Introduction

The **DCN890 18V Cordless Concrete Nailer** is engineered for direct fastening into concrete and steel. Its powerful motor and cordless design make it ideal for construction, electrical, and plumbing installations.

Key Features

- **Cordless Operation:** No gas, hoses, or compressors required.
- **High Power:** Drives nails into concrete and steel.
- **Tool-Free Jam Release:** Easy maintenance.
- **LED Work Light:** Improved visibility.
- **Ergonomic Design:** Comfortable grip.

Specifications Table

Specification	Details
Power Source	18V Lithium-Ion Battery (not included)
Nail Length Range	13 mm – 57 mm
Magazine Capacity	30 nails
Weight (tool only)	Approx. 4.2 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCL045

Cordless Under Bonnet Light

Introduction

The **DCL045 12V-20V MAX XR® Under Bonnet Light** provides powerful, adjustable illumination for automotive and maintenance tasks. Its flexible design fits most bonnets and operates on DEWALT 12V, 18V, and 20V MAX batteries.

Key Features

- **Wide Compatibility:** Works with 12V, 18V, and 20V MAX batteries.
- **High Lumen Output:** Up to 1,700 lumens.
- **Adjustable Arms:** Fits most vehicle bonnets.
- **Multiple Brightness Settings:** For optimal visibility.
- **Cordless Convenience:** Portable and easy to use.

Specifications Table

Specification	Details
Power Source	12V/18V/20V MAX Lithium-Ion Battery (not included)
Lumen Output	Up to 1,700 lumens
Runtime	Up to 5 hours (with 5.0Ah battery)
Weight (tool only)	Approx. 2.0 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCL079

Cordless Tripod Light

DCL079 20V MAX Tripod Light

Introduction

The **DCL079 20V MAX Tripod Light** is a portable, adjustable work light designed for job sites and workshops. Its telescoping tripod provides stable, elevated lighting, and the cordless design offers maximum flexibility.

Key Features

- **High Lumen Output:** Up to 3,000 lumens.
- **Telescoping Tripod:** Adjustable height up to 2.2 meters.
- **Multiple Brightness Settings:** For optimal visibility.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Lumen Output	Up to 3,000 lumens
Runtime	Up to 11 hours (low setting, 5.0Ah battery)
Height	Up to 2.2 meters
Weight (tool only)	Approx. 7.0 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCLE34021

Cordless Compact Cross Line Laser Green

Introduction

The **DCLE34021 20V MAX Compact Cross Line Laser Green** provides bright, accurate laser lines for layout and alignment tasks. Its compact, durable design is ideal for construction and remodeling.

Key Features

- **Green Laser Technology:** Brighter and more visible lines.
- **Self-Leveling:** Accurate and easy setup.
- **Cordless Operation:** Runs on DEWALT 20V MAX batteries.
- **Durable Housing:** Withstands job site conditions.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Laser Color	Green
Range	Up to 30 meters
Accuracy	±3 mm @ 10 meters
Weight (tool only)	Approx. 1.5 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCM200

Cordless Bandfile

Introduction

The **DCM200 20V MAX XR® Brushless 18" Bandfile** is designed for metalworking, fabrication, and finishing tasks. Its brushless motor delivers consistent power and extended runtime, while the slim design allows access to tight spaces.

Key Features

- **Brushless Motor:** Longer runtime and durability.
- **18" Bandfile:** For precise grinding and finishing.
- **Variable Speed Control:** Optimizes performance for different materials.
- **LED Work Light:** Illuminates the work area.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Belt Size	18" (457 mm)
No Load Speed	0-3,600 rpm
Weight (tool only)	Approx. 1.5 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCS334

Cordless Jigsaw

Introduction

The **DCS334 20V MAX XR® Brushless Jigsaw** is a versatile, high-performance tool for cutting wood, metal, and plastics. Its brushless motor provides extended runtime and durability, while the variable speed trigger and orbital action offer precise control.

Key Features

- **Brushless Motor:** Longer runtime and durability.
- **Variable Speed Trigger:** Precise control over cutting speed.
- **Orbital Action:** For faster, smoother cuts.
- **Tool-Free Blade Change:** Quick and easy blade swaps.
- **LED Work Light:** Illuminates the cutting area.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Stroke Length	25 mm
No Load Speed	0-3,200 spm
Bevel Capacity	0-45°
Weight (tool only)	Approx. 1.9 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCS334

Cordless Jigsaw

Introduction

The **DCS335 20V MAX XR® Body Grip Jigsaw** offers the same high performance as the DCS334, with a body grip design for enhanced control and comfort during intricate cuts.

Key Features

- **Body Grip Design:** Improved control for detailed work.
- **Brushless Motor:** Longer runtime and durability.
- **Variable Speed Trigger:** Precise cutting speed control.
- **Orbital Action:** For faster, smoother cuts.
- **Tool-Free Blade Change:** Quick and easy blade swaps.
- **LED Work Light:** Illuminates the cutting area.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Stroke Length	25 mm
No Load Speed	0-3,200 spm
Bevel Capacity	0-45°
Weight (tool only)	Approx. 1.9 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCS367

Cordless Reciprocating Saw

Introduction

The **DCS367 20V MAX XR® Brushless Compact Reciprocating Saw** is designed for fast, efficient cutting in wood, metal, and plastics. Its compact, lightweight design allows for easy use in tight spaces, while the brushless motor delivers extended runtime and durability.

Key Features

- **Compact Design:** Easy to use in confined spaces.
- **Brushless Motor:** Longer runtime and durability.
- **Tool-Free Blade Change:** Quick and easy blade swaps.
- **Variable Speed Trigger:** Precise control over cutting speed.
- **LED Work Light:** Illuminates the cutting area.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Stroke Length	28.6 mm
No Load Speed	0-2,900 spm
Weight (tool only)	Approx. 2.3 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCS373

Cordless Metal Cutting Circular Saw

Introduction
The **DCS373 20V MAX XR® 140mm Metal Cutting Circular Saw** is designed for fast, accurate cutting of metal materials. Its powerful motor and optimized blade deliver clean cuts in steel, aluminum, and other metals, making it ideal for construction and fabrication professionals.

- Key Features**
- **Brushless Motor:** Delivers longer runtime and durability.
 - **140mm Blade:** Optimized for metal cutting.
 - **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.
 - **Ergonomic Design:** Comfortable grip for extended use.
 - **LED Work Light:** Illuminates the cutting area.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Blade Diameter	140 mm
Max Cutting Depth	46 mm
No Load Speed	3,700 rpm
Weight (tool only)	Approx. 3.7 kg
Accessories Included	Metal cutting blade (battery and charger sold separately)

DeWalt DCS382

Cordless Reciprocating Saw

Introduction

The **DCS382 20V MAX Brushless XR® Reciprocating Saw** is a compact, high-performance saw for cutting wood, metal, and plastics. Its brushless motor provides extended runtime and durability, while the lightweight design allows for easy use in tight spaces.

Key Features

- **Brushless Motor:** Longer runtime and durability.
- **Compact Design:** Easy to use in confined spaces.
- **Tool-Free Blade Change:** Quick and easy blade swaps.
- **Variable Speed Trigger:** Precise control over cutting speed.
- **LED Work Light:** Illuminates the cutting area.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Stroke Length	29 mm
No Load Speed	0-3,000 spm
Weight (tool only)	Approx. 2.3 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCS570

Cordless Circular Saw

Introduction

The **DCS570 20V MAX Brushless XR® 184mm Circular Saw** is engineered for fast, accurate cutting in wood and other materials. Its brushless motor delivers high power and extended runtime, while the 184mm blade provides deep cuts for framing and carpentry.

Key Features

- **Brushless Motor:** High efficiency and durability.
- **184mm Blade:** Deep cutting capacity.
- **Bevel Capacity:** Up to 57° for versatile angled cuts.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.
- **Ergonomic Design:** Comfortable grip.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Blade Diameter	184 mm
Max Cutting Depth	64 mm @ 90°
No Load Speed	5,500 rpm
Bevel Capacity	0-57°
Weight (tool only)	Approx. 3.6 kg
Accessories Included	Blade, blade wrench (battery and charger sold separately)

DeWalt DCS571

Cordless Angle Circular Saw

Introduction

The **DCS571 20V MAX XR® Brushless Compact 115mm Angle Circular Saw** is designed for precision cutting in wood, metal, and plastics. Its compact size and brushless motor make it ideal for tight spaces and overhead applications.

Key Features

- **Brushless Motor:** Longer runtime and durability.
- **115mm Blade:** Compact for precision cuts.
- **Ergonomic Design:** Lightweight and easy to handle.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Blade Diameter	115 mm
Max Cutting Depth	38 mm
No Load Speed	4,500 rpm
Weight (tool only)	Approx. 2.5 kg
Accessories Included	Blade, blade wrench (battery and charger sold separately)

DeWalt DCW220

Cordless Belt Sander

Introduction

The **DCW220 20V MAX XR® Brushless Belt Sander** is designed for fast material removal and surface finishing. Its brushless motor and variable speed control provide consistent performance for woodworking and carpentry.

Key Features

- **Brushless Motor:** Longer runtime and durability.
- **Variable Speed Control:** Optimizes sanding for different materials.
- **Large Sanding Area:** 75mm x 533mm belt size.
- **Dust Collection:** Integrated port for cleaner work.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Belt Size	75mm x 533mm
No Load Speed	0-320 m/min
Weight (tool only)	Approx. 3.5 kg
Accessories Included	Dust bag (battery and charger sold separately)

DeWalt DCE100

Cordless Belt Sander

Introduction

The **DCE100 20V MAX Compact Jobsite Blower** is a lightweight, portable blower for quick cleanup of debris and dust on job sites. Its compact design and variable speed trigger make it easy to use in tight spaces.

Key Features

- **Compact Design:** Lightweight and easy to maneuver.
- **Variable Speed Trigger:** Precise control over airflow.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.
- **Multiple Nozzle Attachments:** For versatile use.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Air Volume	Up to 100 CFM
Air Speed	Up to 160 km/h
Weight (tool only)	Approx. 1.3 kg
Accessories Included	3 nozzle attachments (battery and charger sold separately)

DeWalt DCE512

Cordless Jobsite Fan

Introduction

The **DCE512 20V MAX Jobsite Fan** provides powerful, portable cooling for job sites and workshops. Its adjustable head and multiple speed settings offer flexible airflow wherever you need it.

Key Features

- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.
- **Adjustable Head:** Directs airflow where needed.
- **Multiple Speed Settings:** For optimal comfort.
- **Compact Design:** Easy to transport and position.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Airflow	Up to 500 CFM
Speed Settings	3
Weight (tool only)	Approx. 2.6 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCE512

Cordless String Trimmer

Introduction

The **DCMST561 20V MAX XR® String Trimmer** is designed for efficient trimming and edging of lawns and gardens. Its brushless motor and lightweight design provide extended runtime and easy maneuverability.

Key Features

- **Brushless Motor:** Longer runtime and durability.
- **14" Cutting Swath:** Covers more area quickly.
- **Variable Speed Trigger:** Optimizes power and runtime.
- **Ergonomic Design:** Comfortable grip and balance.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Cutting Swath	14" (355 mm)
Line Diameter	2.0 mm
Weight (tool only)	Approx. 3.5 kg
Accessories Included	Spool (battery and charger sold separately)

DeWalt DCM565

Cordless 10" Chainsaw

Introduction

The **DCM565 20V MAX Brushless XR® 10" Chainsaw** is a compact, powerful tool for pruning, limbing, and cutting small trees. Its brushless motor delivers high performance and extended runtime, while the 10" bar and chain provide clean, efficient cuts.

Key Features

- **Brushless Motor:** Longer runtime and durability.
- **10" (300mm) Bar and Chain:** For efficient cutting.
- **Automatic Oiling System:** Ensures constant lubrication.
- **Tool-Free Chain Tensioning:** Quick adjustments.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Bar Length	10" (300 mm)
Chain Speed	7.68 m/s
Weight (tool only)	Approx. 3.3 kg
Accessories Included	Bar cover (battery and charger sold separately)

DeWalt DCMPP568

Cordless 38mm Pruner

Introduction

The **DCMPP568 20V MAX Brushless XR® 38mm Pruner** is designed for fast, effortless pruning of branches and shrubs. Its brushless motor and ergonomic design make it ideal for landscaping and gardening professionals.

Key Features

- **Brushless Motor:** Longer runtime and durability.
- **38mm Cutting Capacity:** Handles thick branches.
- **Tool-Free Blade Change:** Quick and easy maintenance.
- **Ergonomic Design:** Comfortable grip for extended use.
- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Max Cutting Capacity	38 mm
Weight (tool only)	Approx. 1.5 kg
Accessories Included	Blade (battery and charger sold separately)

DeWalt DCV580

Cordless Wet-Dry Vacuum

Introduction

The **DCV580 20V MAX Cordless Wet-Dry Vacuum** is a portable, powerful solution for jobsite cleanup. Designed for both wet and dry applications, it offers cordless convenience and easy portability for professionals and DIY users.

Key Features

- **Cordless Operation:** Runs on DEWALT 20V MAX batteries.
- **Wet & Dry Capability:** Handles spills and debris.
- **Washable Filter:** Easy maintenance and reuse.
- **Integrated Hose & Accessory Storage:** Keeps everything organized.
- **Heavy-Duty Construction:** Built for jobsite durability.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Tank Capacity	2 gallons (7.5 liters)
Hose Length	5 feet (1.5 m)
Airflow	31 CFM
Weight (tool only)	Approx. 4.7 kg
Accessories Included	Hose, crevice tool, wide nozzle (battery and charger sold separately)

DeWalt DCV501

Cordless Stick Vacuum

Introduction

The **DCV501 20V MAX Brushed ATOMIC Stick Vacuum** is a lightweight, cordless stick vacuum designed for quick cleanup on jobsites, workshops, and around the home. Its compact design and powerful suction make it ideal for dust and debris.

Key Features

- **Cordless Convenience:** Operates on DEWALT 20V MAX batteries.
- **Lightweight & Compact:** Easy to maneuver and store.
- **HEPA Filter:** Captures fine dust particles.
- **Multiple Attachments:** For versatile cleaning.

Specifications Table

Specification	Details
Power Source	20V MAX Lithium-Ion Battery (not included)
Motor Type	Brushed
Filter Type	HEPA
Weight (tool only)	Approx. 1.5 kg
Accessories Included	Floor head, crevice tool (battery and charger sold separately)

DeWalt DCD700

Cordless Drill Driver

Introduction

The **DCD700 12V MAX XR® Drill Driver** is a compact, lightweight drill designed for precision drilling and fastening in tight spaces. Its efficient motor and ergonomic design make it ideal for professionals and DIY users.

Key Features

- **Compact & Lightweight:** Easy to use in confined spaces.
- **Efficient Motor:** Delivers reliable performance.
- **Ergonomic Grip:** Comfortable for extended use.
- **LED Work Light:** Illuminates the work area.

Specifications Table

Specification	Details
Power Source	12V MAX Lithium-Ion Battery (not included)
Chuck Size	10 mm (3/8")
No Load Speed	0-425 / 0-1,500 rpm (2-speed)
Max Torque	34 Nm
Weight (tool only)	Approx. 1.0 kg
Accessories Included	Belt hook (battery and charger sold separately)

DeWalt DCD703

Cordless Drill Driver

Introduction

The **DCD703 12V MAX Brushless XTREME™ 5-in-1 Drill Driver** offers unmatched versatility with five interchangeable heads for drilling and fastening in various materials and angles. Its brushless motor provides extended runtime and durability.

Key Features

- **5-in-1 Design:** Includes offset, right angle, 1/4" hex, 3/8" chuck, and screwdriver heads.
- **Brushless Motor:** Longer runtime and tool life.
- **Compact & Lightweight:** Ideal for tight spaces.
- **LED Work Light:** Improved visibility.

Specifications Table

Specification	Details
Power Source	12V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Max Torque	34 Nm
No Load Speed	0-425 / 0-1,500 rpm (2-speed)
Chuck Size	10 mm (3/8")
Weight (tool only)	Approx. 1.0 kg
Accessories Included	5 heads, belt hook (battery and charger sold separately)

DeWalt DCD706

Cordless Sub-Compact Hammer Drill

Introduction

The **DCD706 12V MAX Brushless XTREME™ Sub-Compact Hammer Drill** is designed for drilling in wood, metal, and masonry. Its brushless motor and compact size make it perfect for overhead and tight-space applications.

Key Features

- **Brushless Motor:** Longer runtime and durability.
- **Hammer Function:** For masonry drilling.
- **Compact & Lightweight:** Easy to handle.
- **LED Work Light:** Illuminates the work area.

Specifications Table

Specification	Details
Power Source	12V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Max Torque	32 Nm
No Load Speed	0-425 / 0-1,500 rpm (2-speed)
Chuck Size	10 mm (3/8")
Hammer Action	Yes
Weight (tool only)	Approx. 1.0 kg
Accessories Included	Belt hook, kit box (battery and charger sold separately)

DeWalt DCD716

Cordless Hammer Drill Driver

Introduction

The **DCD716 12V MAX 10MM Hammer Drill Driver** is a compact, versatile tool for drilling and fastening in wood, metal, and masonry. Its lightweight design and hammer function make it ideal for a variety of tasks.

Key Features

- **Hammer Function:** For masonry drilling.
- **Compact & Lightweight:** Easy to use in tight spaces.
- **LED Work Light:** Improved visibility.
- **Ergonomic Grip:** Comfortable for extended use.

Specifications Table

Specification	Details
Power Source	12V MAX Lithium-Ion Battery (not included)
Chuck Size	10 mm (3/8")
No Load Speed	0-400 / 0-1,500 rpm (2-speed)
Max Torque	30 Nm
Hammer Action	Yes
Weight (tool only)	Approx. 1.1 kg
Accessories Included	Belt hook (battery and charger sold separately)

DeWalt DCF500

Cordless Sealed Head Ratchet

Introduction

The **DCF500 12V MAX XR Brushless 1/4" & 3/8" Sealed Head Ratchet** is a versatile, high-performance ratchet for automotive and maintenance professionals. Its brushless motor and sealed head design ensure durability and long life.

Key Features

- **Brushless Motor:** Longer runtime and tool life.
- **Sealed Head Design:** Protects against dust and debris.
- **Interchangeable Anvil:** Switch between 1/4" and 3/8" drive sizes.
- **LED Work Light:** Illuminates the work area.

Specifications Table

Specification	Details
Power Source	12V MAX Lithium-Ion Battery (not included)
Motor Type	Brushless
Drive Size	1/4" & 3/8" interchangeable
Max Torque	40 Nm (3/8"), 30 Nm (1/4")
No Load Speed	0-250 rpm
Weight (tool only)	Approx. 0.9 kg
Accessories Included	1/4" & 3/8" anvils (battery and charger sold separately)

DeWalt DCF503

Cordless Ratchet

Introduction

The **DCF503 12V 3/8 Cordless Ratchet** is a compact, lightweight ratchet designed for fast, efficient fastening in tight spaces. Its cordless design offers maximum portability for automotive and maintenance tasks.

Key Features

- **Compact & Lightweight:** Easy to use in confined spaces.
- **Variable Speed Trigger:** Precise control.
- **LED Work Light:** Illuminates the work area.

Specifications Table

Specification	Details
Power Source	12V MAX Lithium-Ion Battery (not included)
Drive Size	3/8"
Max Torque	40 Nm
No Load Speed	0-250 rpm
Weight (tool only)	Approx. 0.9 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCF805

Cordless Impact Driver

Introduction
The **DCF805 12V MAX Impact Driver** is a compact, powerful tool for fastening screws and bolts. Its lightweight design and efficient motor make it ideal for overhead and tight-space applications.

- Key Features**
- **Compact & Lightweight:** Easy to use in confined spaces.
 - **Efficient Motor:** Delivers reliable performance.
 - **LED Work Light:** Illuminates the work area.

Specifications Table

Specification	Details
Power Source	12V MAX Lithium-Ion Battery (not included)
Chuck Type	1/4" Hex
Max Torque	105 Nm
No Load Speed	0-950 / 0-2,850 rpm (2-speed)
Impact Rate	0-3,600 ipm
Weight (tool only)	Approx. 0.8 kg
Accessories Included	Belt hook (battery and charger sold separately)

DeWalt DCF902

Cordless Impact Wrench

Introduction

The **DCF902 12V XR BL Sub-Compact 3/8 Impact Wrench** is a powerful, lightweight tool for fastening and loosening bolts in tight spaces. Its brushless motor delivers high torque and extended runtime.

Key Features

- **Brushless Motor:** Longer runtime and durability.
- **Compact & Lightweight:** Ideal for tight spaces.
- **LED Work Light:** Illuminates the work area.

Specifications Table

Specification	Details
Power Source	12V MAX Lithium-Ion Battery (not included)
Drive Size	3/8"
Max Torque	168 Nm
No Load Speed	0-2850 rpm
Impact Rate	0-3600 ipm
Weight (tool only)	Approx. 0.9 kg
Accessories Included	Belt hook (battery and charger sold separately)

DeWalt DCF901

Cordless Impact Wrench

Introduction

The **DeWalt DCF901 12V 1/2" Impact Wrench** is a compact, high-torque tool designed for automotive, maintenance, and assembly professionals. Its lightweight design and powerful motor make it ideal for fastening and loosening bolts in tight spaces.

Key Features

- Compact & lightweight for confined spaces
- High torque output up to 168 Nm
- LED work light for improved visibility
- Variable speed trigger for precise control

Specifications Table

Specification	Details
Power Source	12V MAX Lithium-Ion Battery (not included)
Drive Size	1/2"
Max Torque	168 Nm
No Load Speed	0-2850 rpm
Impact Rate	0-3600 ipm
Weight (tool only)	Approx. 1.0 kg
Accessories Included	Belt hook (battery and charger sold separately)

DeWalt DCF901

Cordless 12V MAX Combo

Introduction

The **DeWalt DCK211D2T-B1 12V MAX Combo Kit** includes a drill driver and an impact driver, both compact and lightweight for versatile use. The kit comes with batteries, charger, and a clear TSTAK case for convenient storage and transport.

Key Features

- Compact & lightweight for tight spaces and overhead work
- Brushless motors for longer runtime and durability
- LED work lights for improved visibility
- Complete kit with batteries, charger, and TSTAK case

Specifications Table

Specification	Drill Driver (DCD710)	Impact Driver (DCF815)
Power Source	12V MAX Lithium-Ion Battery (included)	12V MAX Lithium-Ion Battery (included)
Chuck Size	10 mm (3/8")	1/4" Hex
Max Torque	24 Nm	107 Nm
No Load Speed	0-400 / 0-1,500 rpm (2-speed)	0-2,450 rpm
Impact Rate	-	0-3,400 ipm
Weight (tool only)	Approx. 1.1 kg	Approx. 0.9 kg
Accessories Included	2 x batteries, charger, TSTAK case	2 x batteries, charger, TSTAK case

DeWalt DCS310

Cordless Reciprocating Saw

Introduction

The **DeWalt DCS310 12V MAX Brushless XTREME™ One Handed Reciprocating Saw** is designed for fast, efficient cutting in wood, metal, and plastics. Its compact, lightweight design allows for easy use in tight spaces and one-handed operation.

Key Features

- Brushless motor for longer runtime and durability
- One-handed operation for compact and lightweight use
- Tool-free blade change for quick swaps
- LED work light for improved visibility

Specifications Table

Specification	Details
Power Source	12V MAX Lithium-Ion Battery (not included)
Stroke Length	16 mm
No Load Speed	0-2,800 spm
Weight (tool only)	Approx. 1.2 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCS312

Cordless Reciprocating Saw

Introduction

The **DeWalt DCS312 12V MAX Compact Recip Saw** is a lightweight, versatile saw for cutting wood, metal, and plastics. Its compact design and variable speed trigger make it ideal for overhead and tight-space applications.

Key Features

- Compact & lightweight for confined spaces
- Variable speed trigger for precise control
- Tool-free blade change for quick swaps
- LED work light for improved visibility

Specifications Table

Specification	Details
Power Source	12V MAX Lithium-Ion Battery (not included)
Stroke Length	16 mm
No Load Speed	0-2,800 spm
Weight (tool only)	Approx. 1.2 kg
Accessories Included	N/A (battery and charger sold separately)

DeWalt DCS353

Cordless Oscillating Tool

Introduction

The **DeWalt DCS353 12V MAX Brushless Oscillating Tool** is a versatile, multi-purpose tool for cutting, sanding, scraping, and more. Its brushless motor and compact design make it ideal for a variety of applications.

Key Features

- Brushless motor for longer runtime and durability
- Variable speed control for optimized performance
- Tool-free accessory change for quick swaps
- LED work light for improved visibility

Specifications Table

Specification	Details
Power Source	12V MAX Lithium-Ion Battery (not included)
Oscillation Rate	0-18,000 opm
Weight (tool only)	Approx. 1.0 kg
Accessories Included	Universal accessory adapter (battery and charger sold separately)

DeWalt DWE4118

Cordless Angle Grinder

Introduction

The **DeWalt DWE4118 950W 4" Variable Speed Small Angle Grinder** is designed for professional cutting and grinding applications. Its powerful motor and variable speed control provide versatility for different materials.

Key Features

- Variable speed control for optimized performance
- 4" (100 mm) wheel capacity for versatile cutting and grinding
- Ergonomic design for comfortable grip
- Spindle lock for easy wheel changes

Specifications Table

Specification	Details
Power Source	Corded (220-240V)
Power	950W
Wheel Diameter	4" (100 mm)
No Load Speed	2,800-11,800 rpm
Weight	Approx. 1.7 kg
Accessories Included	Guard, side handle, wrench

DeWalt D28720

Corded Chopsaw

Introduction

The **DeWalt D28720 2200W 14" Corded Chopsaw** is a powerful, durable tool for cutting metal pipes, rods, and profiles. Its robust motor and large cutting capacity make it ideal for industrial and construction applications.

Key Features

- High power motor (2,200W) for tough cutting tasks
- 14" (355 mm) blade for large cutting capacity
- Quick-lock vise for fast and secure material clamping
- Ergonomic handle for comfortable use

Specifications Table

Specification	Details
Power Source	Corded (220-240V)
Power	2,200W
Blade Diameter	14" (355 mm)
Max Cutting Capacity	130 mm (round), 115 mm (square)
No Load Speed	3,800 rpm
Weight	Approx. 18.0 kg
Accessories Included	Blade, wrench

DeWalt D25614K

Corded SDS Max Combination Hammer

Introduction

The **DeWalt D25614K 1350W 45mm SDS Max Combination Hammer** is engineered for heavy-duty drilling and chiseling in concrete and masonry. Its powerful motor and high impact energy make it ideal for construction and demolition.

Key Features

- High impact energy (10.5 Joules) for tough applications
- SDS Max chuck for quick and secure bit changes
- Variable speed for optimized performance
- Anti-vibration system for enhanced comfort

Specifications Table

Specification	Details
Power Source	Corded (220-240V)
Power	1,350W
Chuck Type	SDS Max
Max Drilling Capacity	45 mm
Impact Energy	10.5 Joules
No Load Speed	210-415 rpm
Impact Rate	1,430-2,840 bpm
Weight	Approx. 6.8 kg
Accessories Included	Side handle, depth rod, kit box

DeWalt D25811K

Corded Demolition Hammer

Introduction

The **DeWalt D25811K 1050W 17mm Hex Demolition Hammer** is designed for light to medium demolition tasks in concrete and masonry. Its powerful motor and compact design make it ideal for renovation and construction.

Key Features

- High impact energy (7.1 Joules) for effective demolition
- 17mm hex chuck for secure bit retention
- Compact & lightweight for easy handling
- Anti-vibration system for enhanced comfort

Specifications Table

Specification	Details
Power Source	Corded (220-240V)
Power	1,050W
Chuck Type	17mm Hex
Impact Energy	7.1 Joules
Impact Rate	2,840 bpm
Weight	Approx. 5.0 kg
Accessories Included	Side handle, kit box

DeWalt D25881K

Corded Demolition Hammer

Introduction

The **DeWalt D25881K 1600W SDS-MAX Demolition Hammer** is built for heavy-duty demolition in concrete and masonry. Its high impact energy and robust construction make it ideal for demanding jobsite conditions.

Key Features

- Extreme impact energy (17.5 Joules) for tough demolition
- SDS-MAX chuck for quick and secure bit changes
- Heavy-duty construction for durability
- Anti-vibration system for enhanced comfort

Specifications Table

Specification	Details
Power Source	Corded (220-240V)
Power	1,600W
Chuck Type	SDS-MAX
Impact Energy	17.5 Joules
Impact Rate	1,500 bpm
Weight	Approx. 10.0 kg
Accessories Included	Side handle, kit box

DeWalt D25911K

Corded Demolition Hammer

Introduction

The **DeWalt D25911K 1700W 11Kg 27J Inline Brushless Demolition Hammer** is engineered for heavy-duty demolition tasks in concrete and masonry. Its powerful brushless motor delivers high impact energy and durability, while the inline design provides improved control and comfort for demanding jobsite conditions.

Key Features

- **Brushless Motor:** Delivers longer runtime, increased efficiency, and extended tool life.
- **High Impact Energy:** 27 Joules for tough demolition applications.
- **Inline Design:** Enhanced control and ergonomics.
- **Heavy-Duty Construction:** Built for durability in harsh environments.
- **Anti-Vibration System:** Reduces user fatigue.

Specifications Table

Specification	Details
Power Source	Corded (220-240V)
Power	1700W
Impact Energy	27 Joules
Impact Rate	1050-2100 bpm
Weight	11 kg
Accessories Included	Side handle, kit box

DeWalt DCL182

Rechargeable LED Task Light

Introduction

The **DeWalt DCL182 Rechargeable LED Task Light** is a compact, portable lighting solution for job sites, workshops, and home use. Its rechargeable battery and bright LED output make it ideal for illuminating work areas with ease.

Key Features

- **Rechargeable Battery:** Convenient USB charging.
- **Bright LED Output:** Up to 1,000 lumens for clear visibility.
- **Adjustable Head:** Directs light where needed.
- **Compact & Lightweight:** Easy to carry and position.
- **Multiple Brightness Settings:** For optimal illumination.

Specifications Table

Specification	Details
Power Source	Rechargeable battery (USB charging)
Lumen Output	Up to 1,000 lumens
Runtime	Up to 6 hours (low setting)
Weight	Approx. 0.5 kg
Accessories Included	USB charging cable

DeWalt DCL183

Rechargeable Flashlight

Introduction

The **DeWalt DCL183 USB-C Rechargeable Flashlight** is a rugged, high-output flashlight designed for professionals and outdoor enthusiasts. Its USB-C rechargeable battery and durable construction make it ideal for job sites, camping, and emergency use.

Key Features

- **USB-C Rechargeable Battery:** Fast and convenient charging.
- **High Lumen Output:** Up to 1,000 lumens for powerful illumination.
- **Multiple Modes:** Adjustable brightness settings.
- **Durable Construction:** Water and impact resistant.
- **Compact Design:** Easy to carry and store.

Specifications Table

Specification	Details
Power Source	Rechargeable battery (USB-C charging)
Lumen Output	Up to 1,000 lumens
Runtime	Up to 6 hours (low setting)
Weight	Approx. 0.3 kg
Accessories Included	USB-C charging cable

DeWalt DCR009

Rechargeable Bluetooth Speaker

Introduction

The **DeWalt DCR009 USB-C Rechargeable Bluetooth Speaker** is a compact, durable speaker designed for job sites, workshops, and outdoor use. Its USB-C rechargeable battery and Bluetooth connectivity provide convenient, high-quality audio wherever you need it.

Key Features

- **USB-C Rechargeable Battery:** Provides hours of playback.
- **Bluetooth Connectivity:** Stream music wirelessly from your devices.
- **Rugged Design:** Built to withstand jobsite conditions.
- **Compact & Portable:** Easy to carry and position.
- **Clear Sound Quality:** Delivers rich, powerful audio.

Specifications Table

Specification	Details
Power Source	Rechargeable battery (USB-C charging)
Connectivity	Bluetooth
Playback Time	Up to 8 hours
Weight	Approx. 0.7 kg
Accessories Included	USB-C charging cable