


HDC




INSERTI 1/4" CON RIVESTIMENTO AL DIAMANTE 1/4" bits with diamond coating



Rivestimento diamante elettrodepositato
Electro-deposited diamond coating



RIDUZIONE DELL'EFFETTO COME-OUT Reduced come-out effect



Applicazioni applications



Le minuscole particelle di diamante fanno presa nella cava della vite, si riduce l'effetto come-out, l'operatore può avvitare con meno forza e più sicurezza.

The tiny diamond particles make grip in the screw recess, reducing the come-out recess effect; the operator may tighten with less force and more safety.



L'inserto non scivola dalla vite, diminuisce il rischio di rovinare sia la punta dell'utensile che la testa della vite.

The bit does not slip from the screw, which reduces the risk of damaging the tool tip and screw head.




L'ottimo grip che esercita questo rivestimento permette di utilizzare gli inserti HDC anche per svitare viti danneggiate o arrugginite.

The excellent grip exerted by this coating allows using HDC bits also to unscrew damaged or rusty screws.

**61310****PH HDC** **INSERTI 1/4" C PHILLIPS® - CON RIVESTIMENTO AL DIAMANTE**
1/4" C PHILLIPS® BITS - WITH DIAMOND COATING**58/60 HRC****EASYPACK** | sacchetto PVC con Euro-hole • PVC bags with Euro-hole

	L mm	PCS.	COD.
PH1	25	10	61310005
PH2	25	10	61310010
PH3	25	10	61310015




	L mm	COD.
PH1	25	61310005002
PH2	25	61310010002
PH3	25	61310015002

SELPACK
2 pcs.

	L mm	COD.
PH1	25	61310005010
PH2	25	61310010010
PH3	25	61310015010

MINIBOX
10 pcs.**61311****PH HDC** **LAME 1/4" E PHILLIPS® - CON RIVESTIMENTO AL DIAMANTE**
1/4" E PHILLIPS® POWER BITS - WITH DIAMOND COATING**58/60 HRC****EASYPACK** | sacchetto PVC con Euro-hole • PVC bags with Euro-hole

	L mm	PCS.	COD.
PH1	50	5	61311005
PH2	50	5	61311010
PH3	50	5	61311015



	L mm	COD.
PH1	50	61311005002
PH2	50	61311010002
PH3	50	61311015002

SELPACK
2 pcs.

	L mm	COD.
PH1	50	61311005005
PH2	50	61311010005
PH3	50	61311015005

MINIBOX
5 pcs.




61320

PZ HDC

INSERTI 1/4" C POZIDRIV® - CON RIVESTIMENTO AL DIAMANTE
1/4" C POZIDRIV® BITS - WITH DIAMOND COATING

58/60 HRC

EASYPACK | sacchetto PVC con Euro-hole • PVC bags with Euro-hole



	L mm	PCS.	COD.
PZ1	25	10	61320005
PZ2	25	10	61320010
PZ3	25	10	61320015



	L mm	COD.
PZ1	25	61320005002
PZ2	25	61320010002
PZ3	25	61320015002

SELPACK
2 pcs.



	L mm	COD.
PZ1	25	61320005010
PZ2	25	61320010010
PZ3	25	61320015010

MINIBOX
10 pcs.


61321

PZ HDC

LAME 1/4" E POZIDRIV® - CON RIVESTIMENTO AL DIAMANTE
1/4" E POZIDRIV® POWER BITS - WITH DIAMOND COATING

58/60 HRC

EASYPACK | sacchetto PVC con Euro-hole • PVC bags with Euro-hole



	L mm	PCS.	COD.
PZ1	50	5	61321005
PZ2	50	5	61321010
PZ3	50	5	61321015



	L mm	COD.
PZ1	50	61321005002
PZ2	50	61321010002
PZ3	50	61321015002

SELPACK
2 pcs.



	L mm	COD.
PZ1	50	61321005005
PZ2	50	61321010005
PZ3	50	61321015005

MINIBOX
5 pcs.




61330

TX HDC

INSERTI 1/4" C PER VITI TORX® - CON RIVESTIMENTO AL DIAMANTE
1/4" C BITS FOR TORX® SCREWS - WITH DIAMOND COATING

58/60 HRC



EASYPACK | sacchetto PVC con Euro-hole • PVC bags with Euro-hole

	L mm	PCS.	COD.
TX10	25	10	61330005
TX15	25	10	61330010
TX20	25	10	61330015
TX25	25	10	61330020
TX30	25	10	61330030
TX40	25	10	61330035

	L mm	COD.
TX10	25	61330005002
TX15	25	61330010002
TX20	25	61330015002
TX25	25	61330020002
TX30	25	61330030002
TX40	25	61330035002



SELPACK
2 pcs.



MINIBOX
10 pcs.


	L mm	COD.
TX10	25	61330005010
TX15	25	61330010010
TX20	25	61330015010
TX25	25	61330020010
TX30	25	61330030010
TX40	25	61330035010

61305

TAGLIO HDC

INSERTI 1/4" C A TAGLIO - CON RIVESTIMENTO AL DIAMANTE
1/4" C SLOTTED BITS - WITH DIAMOND COATING

58/60 HRC



EASYPACK | sacchetto PVC con Euro-hole • PVC bags with Euro-hole

	Ø mm	L mm	PCS.	COD.
0,5	3	25	10	61305005
0,6	4	25	10	61305010
0,6	4,5	25	10	61305015
0,8	5,5	25	10	61305020
1,2	6,5	25	10	61305025

	Ø mm	L mm	COD.
0,5	3	25	61305005002
0,6	4	25	61305010002
0,6	4,5	25	61305015002
0,8	5,5	25	61305020002
1,2	6,5	25	61305025002



SELPACK
2 pcs.



MINIBOX
10 pcs.

	Ø mm	L mm	COD.
0,5	3	25	61305005010
0,6	4	25	61305010010
0,6	4,5	25	61305015010
0,8	5,5	25	61305020010
1,2	6,5	25	61305025010



66002

MYBIT 7 ASSORTIMENTI HDC

ASSORTIMENTO 7 PCS. - INSERTI + PORTAINSERTI
7 PCS. SET - BITS + BIT-HOLDER



7
pcs.



100 X 120 mm



COD. **66002380**



PH1
1pc.



PH2
1pc.



PZ1
1pc.



PZ2
1pc.



0,6x4,5
1pc.

1,2x6,5
1pc.

COD. **66002385**



TX10
1pc.

TX15
1pc.

TX20
1pc.

TX25
1pc.

TX30
1pc.

TX40
1pc.

COD. **66002390**



PH1
1pc.



PH2
1pc.



PZ1
1pc.



PZ2
1pc.



TX25
1pc.

TX30
1pc.

INCLUSO
INCLUDED
COD. 62015010



66002

DISPLAY MYBIT 7 HDC

ESPOSITORE DA BANCO PER 12 BIT-SETS
12 PCS. BIT-SET DISPLAY



12
pcs.

150 X 40 X 195 mm

COD. **66002384**



12 pcs.
COD. 66002380

COD. **66002389**



12 pcs.
COD. 66002385

COD. **66002394**



12 pcs.
COD. 66002390



66007

MYBIT 7 POWER ASSORTIMENTI HDC

ASSORTIMENTO 7 PCS. - INSERTI
7 PCS. SET - BITS



7
pcs.

COD. **66007385**

61311 L=50mm



PH1
1pc.

PH2
2pcs.

PH3
1pc.

61321 L=50mm



PZ1
1pc.

PZ2
1pc.

PZ3
1pc.



100 X 120 mm





66005

MYBIT 10 ASSORTIMENTI HDC

ASSORTIMENTO 10 PCS. - INSERTI + PORTAINSERTI
10 PCS. SET - BITS + BIT-HOLDER



10 pcs.



100 X 120 mm



INCLUSO
INCLUDED
COD. 62015010



COD. **66005380**

61310			61320			61305		
PH1	PH2	PH3	PZ1	PZ2	PZ3	0,6x4,5	0,8x5,5	1,2x6,5
1pc.	1pc.	1pc.	1pc.	1pc.	1pc.	1pc.	1pc.	1pc.

COD. **66005385**

61310			61320			61330		
PH1	PH2	PH3	PZ1	PZ2	PZ3	TX25	TX30	TX40
1pc.	1pc.	1pc.	1pc.	1pc.	1pc.	1pc.	1pc.	1pc.

66005

DISPLAY MYBIT 10 HDC

ESPOSITORE DA BANCO PER 12 BIT-SETS
12 PCS. BIT-SET DISPLAY



12 pcs.

150 X 40 X 195 mm

COD. **66005384**



12 pcs.
COD. 66005380

COD. **66005389**



12 pcs.
COD. 66005385



66006

MYBIT¹⁵ ASSORTIMENTI HDC

ASSORTIMENTO 15 PCS. - INSERTI + PORTAINSERI
15 PCS. SET - BITS + BIT-HOLDER



15 pcs.



100 X 167 mm



INCLUSO
INCLUDED
COD. 62015010



COD. **66006320**

61310			61320		
PH1 1pc.	PH2 1pc.	PH3 1pc.	PZ1 1pc.	PZ2 1pc.	PZ3 1pc.
61330			61305		
TX20 1pc.	TX25 1pc.	TX30 1pc.	0,6x4,0 1pc.	0,8x5,5 1pc.	1,2x6,5 1pc.
61311			61321		
PH2 1pc.			PZ2 1pc.		

66006

DISPLAY MYBIT¹⁵ HDC

ESPOSITORE DA BANCO PER 12 BIT-SETS
12 PCS. BIT-SET DISPLAY



12 pcs.

COD. **66006324**



12 pcs.
COD. 66006320

185 X 40 X 195 mm



66006

MYBIT/4 HDC CON CRICCHETTO

ASSORTIMENTO 14 PCS. HDC / CRICCHETTO

14 PCS. SET - BITS + BIT HOLDER AND RATCHET

COD. **66006515**

14 pcs.



100 X 170 mm



61310			61320		
PH1 1pc.	PH2 1pc.	PH3 1pc.	PZ1 1pc.	PZ2 1pc.	PZ3 1pc.
61330			61305		
TX20 1pc.	TX25 1pc.	TX30 1pc.	4x0,6 1pc.	5,5x0,8 1pc.	6,5x1,2 1pc.

INCLUSO
INCLUDED

COD. 62015010

COD. 64221030

66010

ASSORTIMENTI HDC

ASSORTIMENTO 31 PCS. - INSERTI + PORTAINSERTI

31 PCS. SET - BITS + BIT-HOLDER

COD. **66010040**

31 pcs.



80 X 115 X 30 mm

61310			61320		
PH1 2pcs.	PH2 2pcs.	PH3 2pcs.	PZ1 2pcs.	PZ2 2pcs.	PZ3 2pcs.
61330			61305		
TX10 1pc.	TX15 1pc.	TX20 1pc.	TX25 2pcs.	TX30 2pcs.	TX40 2pcs.
0,5x3,0 1pc.	0,6x4,0 2pcs.	0,6x4,5 2pcs.	0,8x5,5 2pcs.	1,2x6,5 2pcs.	

INCLUSO
INCLUDED

COD. 62015010



66001

STORE 9 ASSORTIMENTI HDC

CASSETTIERA CON 9 SCOMPARTI PER ESPOSITORE MULTISTORE
DRAWERS WITH 9 COMPARTMENTS FOR MULTISTORE DISPLAY

110
pcs.



600 X 90 X 65 mm

COD. **66001070**

61310		61320		61330			61305	
PH2	PH3	PZ2	PZ3	TX25	TX30	TX40	0,6x4,5	1,2x6,5
20pcs.	10pcs.	20pcs.	10pcs.	10pcs.	10pcs.	10pcs.	10pcs.	10pcs.

COD. **66001071**

61310		61320		61330		
PH1	PH2	PZ1	PZ2	TX25	TX30	TX40
10pcs.	20pcs.	10pcs.	20pcs.	10pcs.	10pcs.	10pcs.

61311		61321	
PH2		PZ2	
10pcs.		10pcs.	



MULTI STORE

COD. 66001005VC

**66001****MULTI BIT ESPOSITORE INSERTI HDC****ESPOSITORE DA BANCO CON 25 SCOMPARTI**
DISPLAY WITH 25 COMPARTMENTS**265**
pcs.

445 X 465 X 210 mm

STRUTTURA IN POLIPROPILENE ALVEOLARE AUTOPORTANTE, 25 SCOMPARTI.
SELF-SUPPORTING POLYPROPYLENE HONEYCOMB STRUCTURE, 25 COMPARTMENTS.COD. **66001320**

61310   PH1 10pcs. PH2 20pcs. PH3 10pcs.			61320   PZ1 10pcs. PZ2 20pcs. PZ3 10pcs.		
61330   TX10 10pcs. TX15 10pcs. TX20 10pcs. TX25 10pcs. TX30 10pcs. TX40 10pcs.					
61311   PH1 10pcs. PH2 10pcs. PH3 10pcs.			61321   PZ1 10pcs. PZ2 10pcs. PZ3 10pcs.		
61305   0,5x3,0 10pcs. 0,6x4,0 10pcs. 0,6x4,5 10pcs. 0,8x5,5 10pcs. 1,2x6,5 10pcs.					
62015010     10pcs.			62022005     5pcs		

**66001****MULTI BOX ESPOSITORE MINIBOX HDC****ESPOSITORE DA BANCO PER MINIBOX
DISPLAY STAND FOR MINIBOX****138
pcs.**COD. **66001525**

			L mm	COD.	box
10 pcs.		PH1	25	61310005010	1
10 pcs.		PH2	25	61310010010	2
10 pcs.		PH3	25	61310015010	1
5 pcs.		PH2	50	61311010005	1
10 pcs.		PZ1	25	61320005010	1
10 pcs.		PZ2	25	61320010010	2
10 pcs.		PZ3	25	61320015010	1
5 pcs.		PZ2	50	61321010005	1
10 pcs.		TX30	25	61330030010	1
10 pcs.		TX40	25	61330035010	1
10 pcs.		0,6 X 4,5	25	61305015010	1
10 pcs.		0,8 X 5,5	25	61305020010	1
1 pc.		MYBIT 7		66002380	1
1 pc.		MYBIT 7 POWER		66007385	1
1 pc.				62015005001	3
1 pc.				62029005	3

370 X 545 X 220 mm

STRUTTURA IN FILO METALLICO DA BANCO ED APPENDIBILE ADADTA AD ACCOGLIERE
20 MISURE DIVERSE DI INSERTI CONFEZIONATI IN MINIBOX E DUE ARTICOLI ACCESSORI.
COUNTERTOP OR WALL-MOUNTED METAL WIRE STRUCTURE, SUITABLE FOR HOLDING BITS
IN 20 DIFFERENT SIZES, MINIBOX PACKED AND TWO ACCESSORIES.

SCHEDE TECNICHE TECHNICAL DATASHEETS

PHILLIPS®

A REGISTERED TRADEMARK OF PHILLIPS SCREW COMPANY





IN ACCORDO A NORME INTERNAZIONALI
IN ACCORDANCE WITH INTERNATIONAL STANDARDS

COPPIA DI TORSIONE SECONDO NORME
TIGHTENING TORQUE IN ACCORDANCE WITH THE STANDARDS

**DIN 5260
ISO 8764**

**DIN 5261*
ISO 8764***



+	A	Ø	Nm	Nm	Autofilettanti per metallo Self-tapping for metal			Autofilettanti per legno Self-tapping for wood			Metriche Metrics			
					ISO 7049 = DIN 7981	ISO 7050 = DIN 7982	ISO 7051 = DIN 7983	DIN 7996	DIN 7997	DIN 7995	ISO 7045 = DIN 7985	ISO 7046 = DIN 965	ISO 7047 = DIN 966	
PH0	0,84	3	1,0	1,0	2,2	2,2	2,2	2,0	2,0	2,0	2,0	2,0	2,0	2,0
PH1	1,30	4,5	3,5	3,8	2,2 2,9	2,2 2,9	2,2 2,9	2,5 3,0	2,5 3,0	2,5 3,0	2,5 3,0	2,5 3,0	2,5 3,0	2,5 3,0
PH2	2,31	6	8,2	10,3	3,5 4,8	3,5 4,8	3,5 4,8	3,5 5,0	3,5 5,0	3,5 5,0	4,0 5,0	4,0 5,0	4,0 5,0	4,0 5,0
PH3	3,84	8	19,5	32,0	5,5 6,3	5,5 6,3	5,5 6,3	5,5 7,0	5,5 7,0	5,5 7,0	6,0	6,0	6,0	6,0
PH4	5,11	10	38,0	88,7	8,0 9,5	8,0 9,5	8,0 9,5	8,0	8,0	8,0	8,0 10,0	8,0 10,0	8,0 10,0	8,0 10,0

* LE NORME PREVEDONO CHE SOTTO IL VALORE DI COPPIA INDICATA IL PROFILO DELL'UTENSILE NON PRESENTI ALCUNA DEFORMAZIONE

* THE STANDARDS REQUIRE THAT THE TOOL PROFILE DOES NOT DEFORM UNDER THE INDICATED TORQUE VALUES

SCHEDE TECNICHE TECHNICAL DATASHEETS

POZIDRIV®

A REGISTERED TRADEMARK OF PHILLIPS SCREW COMPANY




IN ACCORDO A NORME INTERNAZIONALI
IN ACCORDANCE WITH INTERNATIONAL STANDARDS

COPPIA DI TORSIONE SECONDO NORME
TIGHTENING TORQUE IN ACCORDANCE WITH THE STANDARDS

**DIN 5260
ISO 8764**

**DIN 5261*
ISO 8764***



+	A	Ø	Nm	Nm	Autofilettanti per metallo Self-tapping for metal			Autofilettanti per legno Self-tapping for wood			Metriche Metrics		
					ISO 7049 = DIN 7981	ISO 7050 = DIN 7982	ISO 7051 = DIN 7983	DIN 7996	DIN 7997	DIN 7995	ISO 7045 = DIN 7985	ISO 7046 = DIN 965	ISO 7047 = DIN 966
PZ0	0,45	3	1,0	1,0	2,2	2,2	2,2	2,0	2,0	2,0	2,0	2,0	2,0
PZ1	0,71	4,5	3,5	3,8	2,2 2,9	2,2 2,9	2,2 2,9	2,5 3,0	2,5 3,0	2,5 3,0	2,5 3,0	2,5 3,0	2,5 3,0
PZ2	1,00	6	8,2	10,3	3,5 4,8	3,5 4,8	3,5 4,8	3,5 5,0	3,5 5,0	3,5 5,0	4,0 5,0	4,0 5,0	4,0 5,0
PZ3	1,38	8	19,5	32,0	5,5 6,3	5,5 6,3	5,5 6,3	5,5 7,0	5,5 7,0	5,5 7,0	6,0	6,0	6,0
PZ4	2,10	10	38,0	88,7	8,0 9,5	8,0 9,5	8,0 9,5	8,0	8,0	8,0	8,0 10,0	8,0 10,0	8,0 10,0

* LE NORME PREVEDONO CHE SOTTO IL VALORE DI COPPIA INDICATA IL PROFILO DELL'UTENSILE NON PRESENTI ALCUNA DEFORMAZIONE

* THE STANDARDS REQUIRE THAT THE TOOL PROFILE DOES NOT DEFORM UNDER THE INDICATED TORQUE VALUES

SCHEDE TECNICHE TECHNICAL DATASHEETS

TORX®

A REGISTERED TRADEMARK OF ACCUMENT GLOBAL TECHNOLOGIES




IN ACCORDO A NORME INTERNAZIONALI
IN ACCORDANCE WITH INTERNATIONAL STANDARDS

COPPIA DI TORSIONE SECONDO NORME
TIGHTENING TORQUE IN ACCORDANCE WITH THE STANDARDS

TMD-702

TMD-702*



Torx Symbol	A	J	Hand icon	Torque icon	Torque icon	Autofilettanti per metallo Self-tapping for metal			Autofilettanti per legno Self-tapping for wood			Metriche Metrics					
						ISO 7049 = DIN 7981	ISO 7050 = DIN 7982	ISO 7051 = DIN 7983	DIN 7996	DIN 7997	DIN 7995	ISO 7045 = DIN 7985	ISO 7046 = DIN 965	ISO 7047 = DIN 966	DIN 912 = 7984 = 6912	ISO 4762 = DIN 912	ISO 10642 = DIN 7991
TX03	1,12			0,25								1,2	1,4	1,4	1,2		
TX04	1,30			0,37													
TX05	1,37		0,43	0,51								1,4 1,6	1,8		1,4 1,6		
TX06	1,65		0,75	0,91		2,2	2,2					1,3 2,0	2,0		1,3 2,0		
TX07	1,97		1,4	1,7													
TX08	2,30	0,74	2,2	2,6	2,2	2,9	2,9	2,9				2,5	2,5	2,5		2,5	
TX09	2,48	0,81	2,8	3,4	2,9	2,9											
TX10	2,27	0,94	3,7	4,5	3,8	3,5	3,5	3,5	3,0	3,0		3,0	3,0	3,0	3,0	3,0	3,0
TX15	3,26	1,19	6,4	7,7	6,5	3,9	3,9	3,9	3,5	3,5		3,5	3,5	3,5	3,5		
TX20	3,84	1,57	10,5	12,7	10,8	4,2	4,2	4,2	4,0 4,5	4,0 4,5	4,5	4,0	4,0	4,0	4,0	4,0	4,0
TX25	4,40	1,96	15,9	19,0	16,1	4,8 5,5	4,8 5,5	4,8 5,5	4,5 6,0	4,5 5,0	4,5	5,0	5,0	5,0	4,0 5,0	5,0	5,0
TX27	4,96	2,21	22,5	26,9	22,9										4,3 5,0		
TX30	5,49	2,72	31,1	37,4	31,8	6,3	6,3	6,3	6,0	6,0		6,0	6,0	6,0	6,0	6,0	6,0
TX40	6,60	3,15	54,1	65,1	55,3	8,0				8,0 10,0		8,0	8,0	8,0	8,0		8,0
TX45	7,77	3,40	86,0	104,0	88,0											8,0	
TX50	8,79	3,73	132,0	159,0	135,0	10,0						10,0	10,0	10,0	10,0	10,0	10,0
TX55	11,17	4,75		257,0	218,0	12,0									12,0	12,0	
TX60	13,20	5,56		445,0	379,0										14,0	14,0	
TX70	15,49	6,73		701,0	596,0												

* PER QUESTO PROFILO I VALORI DI COPPIA INDICATI CORRISPONDONO AL VALORE MINIMO DI ROTTURA
* THE TORQUE VALUES INDICATED FOR THIS PROFILE CORRESPOND TO THE MINIMUM BREAKING VALUE

SCHEDE TECNICHE TECHNICAL DATASHEETS

TORX-PLUS®

TORX-PLUS® TAMPER RESISTANT

A REGISTERED TRADEMARK OF ACCUMENT GLOBAL TECHNOLOGIES




IN ACCORDO A NORME INTERNAZIONALI
IN ACCORDANCE WITH INTERNATIONAL STANDARDS

COPPIA DI TORSIONE SECONDO NORME
TIGHTENING TORQUE IN ACCORDANCE WITH THE STANDARDS

NMD-702
NMD-602

NMD-702*
NMD-602*



** DIAMETRO CIRCOSCRITTO · ** CIRCUMSCRIBED DIAMETER ·

		Autofilettanti per metallo Self-tapping for metal			Metriche Metrics										
	A			A	J		ISO 7049 = DIN 7981	ISO 7050 = DIN 7982	ISO 7051 = DIN 7983	ISO 7045 = DIN 7985	ISO 7046 = DIN 965	ISO 7047 = DIN 966	DIN 912 7984 6912	ISO 4762 = DIN 912	ISO 10642 = DIN 7991
10IP	2,72	5,42	10IPR	2,72	0,91	4,3	3,5	3,5	2,9 3,5	3,0	3,0	3,0	3,0	3,0	5,0
15IP	3,25	9,62	15IPR	3,25	1,17	7,3	3,9	3,9	3,5 3,9	3,5	3,5 4,0	3,5			6,0
20IP	3,84	16,15	20IPR	3,84	1,55	11,9	4,2	4,2	4,2	4,0	4,0 5,0	4,0	4,0	4,0	6,0
25IP	4,39	23,50	25IPR	4,39	1,93	17,4	4,8 5,5	4,8 5,5	4,8 5,5	5,0	5,0 6,0	5,0	5,0	5,0	7,0 8,0
27IP	4,95	34,62	27IPR	4,95	2,18	25,1									8,0
30IP	5,49	47,18	30IPR	5,49	2,57	33,5	6,3	6,3	6,3	6,0	6,0	6,0	8,0	6,0	
40IP	6,60	82,08	40IPR	6,60	2,92	59,4			8,0		8,0	8,0	8,0	8,0	10,0

* PER QUESTO PROFILO I VALORI DI COPPIA INDICATI CORRISPONDONO AL VALORE MINIMO DI ROTTURA

* THE TORQUE VALUES INDICATED FOR THIS PROFILE CORRESPOND TO THE MINIMUM BREAKING VALUE

SCHEDE TECNICHE TECHNICAL DATASHEETS

ESAGONO




IN ACCORDO A NORME INTERNAZIONALI
IN ACCORDANCE WITH INTERNATIONAL STANDARDS

COPPIA DI TORSIONE SECONDO NORME
TIGHTENING TORQUE IN ACCORDANCE WITH THE STANDARDS

DIN 911
DIN 7426

DIN 7426*
ISO 2936*



Ø	A	B _{MIN}	Nm	Nm	Metriche Metrics				
					DIN 7984	ISO 4762 = DIN 7984	ISO 10642 = DIN 7991	DIN 908	DIN 913 914 DIN 915 916
0,7	0,7	1,6	0,08						1,4 1,8
0,9	0,9	1,8	0,18						2,0
1,3	1,3	2,0	0,53			1,4			2,5
1,5	1,5	2,3	0,82	0,95		1,6 2,0			3,0
2,0	2,0	3,0	1,9	2,3	3,0	2,5	3,0		4,0
2,5	2,5	3,8	3,4	4,4	4,0	3,0	4,0		5,0
3,0	3,0	4,5	6,6	7,6	5,0	4,0	5,0		6,0
4,0	4,0	6,0	16,0	18,0	6,0	5,0	6,0		8,0
5,0	5,0	7,5	30,0	35,0	8,0	6,0	8,0	10,0	10,0
6,0	6,0	9,0	52,0	61,0		8,0	10,0	12,0 14,0	12,0 14,0
7,0	7,0	10,5	78,0	97,0	10,0				
8,0	8,0	12,0	120,0	140,0	12,0	10,0	12,0	16,0 18,0	16,0 18,0
10,0	10,0	16,0	220,0	280,0	14,0	12,0	14,0 16,0	20,0 22,0	20,0 22,0
12,0	12,0	18,0	370,0	480,0	16,0 18,0	14,0	18,0 20,0	24,0 26,0	24,0 26,0
14,0	14,0	25,0	590,0		20,0 22,0	16,0 18,0	22,0 24,0		

* LE NORME PREVEDONO CHE SOTTO IL VALORE DI COPPIA INDICATA IL PROFILO DELL'UTENSILE NON PRESENTI ALCUNA DEFORMAZIONE

* THE STANDARDS REQUIRE THAT THE TOOL PROFILE DOES NOT DEFORM UNDER THE INDICATED TORQUE VALUES

SCHEDE TECNICHE TECHNICAL DATASHEETS

TAGLIO




IN ACCORDO A NORME INTERNAZIONALI
IN ACCORDANCE WITH INTERNATIONAL STANDARDS

COPPIA DI TORSIONE SECONDO NORME
TIGHTENING TORQUE IN ACCORDANCE WITH THE STANDARDS

DIN-ISO 2380

DIN-ISO 2380*



Ø	A	T	Nm	Nm	Autofilettanti per metallo Self-tapping for metal			Autofilettanti per legno Self-tapping for wood			Metriche Metrics						
					ISO 1481 = DIN 7971	ISO 1482 = DIN 7972	ISO 1483 = DIN 7973	DIN 96	DIN 97	DIN 95	ISO 1207 = DIN 84	ISO 1580 = DIN 85	ISO 2009 = DIN 963	ISO 2010 = DIN 964	ISO 4766 7435 = DIN 417-427		
1,5	0,30	0,50		0,15													
1,8	0,37	0,50		0,28							1,2 1,4						
2,0	0,40	0,70	0,3	0,35				1,6	1,6				1,6			2,5 3,0	
2,5	0,40	0,70	0,4	0,45				2,0		1,6	1,6 1,8			1,6		3,5	
3,0	0,50	0,90	0,7	0,8		2,2	2,2		2,0	2,0	2,0		2,0	2,0	2,0	4,0	
3,5	0,60	1,10	1,3	1,4	2,2			2,5	2,5	2,5	2,5		2,5	2,5			
4,0	0,50	0,90		1,1				2,0									
4,0	0,80	1,40	2,6	2,9	2,9	2,9	2,9	3,0 3,5	3,0 3,5	3,0 3,5	3,0	3,0	3,0 3,5	3,0 3,5	5,0 6,0		
4,5	0,60	1,10		1,8	2,2			2,5			2,5						
5,0	0,80	1,40	3,2	3,6													
5,5	0,80	1,40	3,5	3,9				3,5		3,5	3,0	3,5	3,5	3,5			
5,5	1,00	1,80	5,5	6,2	3,5 3,9	3,5 3,9	3,5 3,9	4,0 4,5	4,0 4,5	4,0 4,5	3,5	3,5	4,0	4,0			
6,0	1,00	1,80		6,7													
6,5	1,20	2,20	9,4	10,5		4,2 4,8	4,2	5,0 5,5	5,0	5,0	4,0		5,0	5,0	8,0		
7,0	1,20	2,20	10,0	11,3													
8,0	1,20	2,20	11,5	12,9	4,2		4,8		5,5	5,5	5,0	4,0					
8,0	1,60	2,90	20,5	22,9	4,8	5,5 6,3	5,5	6,0	6,0	6,0		5,0	6,0	6,0	10,0 12,0		
10,0	1,60	2,90	25,6	28,7	5,5 6,3		6,3		7,0 8,0	7,0	6,0				14,0		
13,0	2,00	3,60	52,0	58,0				8,0	10,0		8,0	8,0	8,0	8,0	16,0		

* LE NORME PREVEDONO CHE SOTTO IL VALORE DI COPPIA INDICATA IL PROFILO DELL'UTENSILE NON PRESENTI ALCUNA DEFORMAZIONE

* THE STANDARDS REQUIRE THAT THE TOOL PROFILE DOES NOT DEFORM UNDER THE INDICATED TORQUE VALUES


SCHEDE TECNICHE TECHNICAL DATASHEETS

TORX®

A REGISTERED TRADEMARK OF ACCUMENT GLOBAL TECHNOLOGIES



IN ACCORDO A SPECIFICA ACCUMENT GLOBAL TECHNOLOGIES
IN ACCORDANCE WITH THE SPECIFICATIONS OF ACCUMENT GLOBAL TECHNOLOGIES



Metriche
Metrics



	A	Metriche Metrics	
		ISO 4014 - 4017 = DIN 931 - 933	ISO 8100 = DIN 6921
	A		
E5	4,72	4,0	
E6	5,69	5,0	4,0
E7	6,17		
E8	7,47	6,0 7,0	5,0
E10	9,37	8,0	6,0
E11	10,03		
E12	11,12	10,0 11,0	8,0
E14	12,85	12,0	10,0
E16	14,71		
E18	16,64	14,0	12,0
E20	18,41	16,0	14,0
E22	20,24		
E24	22,09	18,0 20,0	

SCHEDE TECNICHE TECHNICAL DATASHEETS

ESAGONO




IN ACCORDO A NORME INTERNAZIONALI
IN ACCORDANCE WITH INTERNATIONAL STANDARDS

COPPIA DI TORSIONE SECONDO NORME
TIGHTENING TORQUE IN ACCORDANCE WITH THE STANDARDS

DIN 3129

DIN-ISO 1711*



			Autofilettanti per metallo <i>Self-tapping for metal</i>	Autofilettanti per legno <i>Self-tapping for wood</i>	Metriche <i>Metrics</i>		
	 Nm	 Nm	ISO 1479 = DIN 7976	DIN 571	ISO 4014 4016 4017	ISO 4035 4036 = DIN 439	ISO 4032 4033 = DIN 934
4		10,4			2,0	2,0	2,0
4,5		12,6			2,3		
5	11,5	15,1	2,9		2,5	2,5	2,5
5,5	14,4	17,8	3,5		3,0	3,0	3,0
6	17,6	23,2			3,5	3,5	3,5
7	25,2	33,2	3,9 4,2	4,0	4,0	4,0	4,0
8*	34,5	94,1	4,8 5,5	5,0	5,0	5,0	5,0
9*	45,4	119,2					
10*	58,1	147,0	6,3	6,0	6,0	6,0	6,0
11*	72,7	178,0			7,0		7,0
12*	89,1	212,0		7,0			
13*	107,0	249,0	8,0	8,0	8,0	8,0	8,0
14*	128,0	288,0					

* VALUTARE ANCHE RESISTENZA ATTACCO


* ALSO EVALUATE ATTACHMENT RESISTANCE

SCHEDE TECNICHE

TECHNICAL DATASHEETS

ATTACCHI MASCHIO STANDARD, APPLICAZIONI, RESISTENZE

STANDARD MALE ATTACHMENTS, APPLICATIONS, RESISTANCES

	 A  B		APPLICAZIONE APPLICATION	STANDARDS	Nm
	A=3mm			DIN 3126 Form A3	7,6
	A=4mm - 5/32"			DIN 3126 Form C4	18,0
	A=5,5mm			DIN 3126 Form A5,5	47,0
	B=VARIE			LTI	N.A.
	B=7mm			LTI	N.A.
	A=6,35mm - 1/4"			DIN 3126 Form C6,3	71,0
	A=6,35mm - 1/4"			DIN 3126 Form E6,3	71,0
	A=7,93mm - 5/16"			DIN 3126 Form C8	144,0
	A=7,93mm - 5/16"			FIAM-DESOUTTER	144,0
	A=9,52mm - 3/8"			AUTOMOTIVE	280,0
	A=11,2mm - 7/16"			DIN 3126 Form E11,2	396,0
	B=M4x0,7			ISO 724 - DIN 13.1	7,0
	B=M5x0,8			ISO 724 - DIN 13.1	18,0
	B=M6x1			ISO 724 - DIN 13.1	25,0
	B=10x32 UNF			ISO 724 - DIN 13.1	18,0
	B=BSF 3/16x32 Whitworth			ISO 724 - DIN 13.1	18,0


SCHEDE TECNICHE

TECHNICAL DATASHEETS

ATTACCHI QUADRO STANDARD, APPLICAZIONI, RESISTENZE

STANDARD SQUARE ATTACHMENTS, APPLICATIONS, RESISTANCES

			APPLICAZIONE APPLICATION	STANDARDS	Nm
	A=6,35mm - 1/4"			DIN 3121 Form G6,3	68,6
	A=9,52mm - 3/8"			DIN 3121 Form G10	225,0
	A=12,70mm - 1/2"			DIN 3121 Form G12,5	569,0
	A=19,05mm - 3/4"			DIN 3121 Form H20	1569,0
	A=25,40mm - 1"			DIN 3121 Form H25	2795,0
	A=38,10mm - 1-1/2"			DIN 3121 Form H40	

			APPLICAZIONE APPLICATION	STANDARDS	Nm
	A=6,35mm - 1/4"			DIN 3121 Form G6,3	62,0
	A=9,52mm - 3/8"			DIN 3121 Form G10	202,0
	A=12,70mm - 1/2"			DIN 3121 Form G12,5	512,0
	A=19,05mm - 3/4"			DIN 3121 Form D20	1412,0