

RODAC

SAM GROUP

POWERFUL DEALS

PROMOTIONS-INNOVATIONS-NEW PRODUCTS



YOUR EVERYDAY
PARTNER



7 GOOD REASONS TO CHOOSE RODAC SAM GROUP

1 NON-STOP INFORMATION ON OUR WEBSITE!

You'll find all our interactive catalogues, information and technical data sheets, our product videos, on rodac.com as well as on sam.eu! Sign up for our newsletter to get all the latest news in real time on our new offers and products.



2 WE'RE ALL EARS!

You can contact us by phone from 8am to 5pm for all your questions **+32 (0)2 331 34 34**. It'll be our pleasure to keep you informed.



3 SUPPORT IN THE FIELD!

Our field sales staff are at the service of our customers. You want us to visit you for a product demo? **Contact us!**



4 OUR AFTER-SALES SERVICE!

As we have our own after-sales technical department we are in a position to provide you fast, professional expertise at a fair price. This ensures you'll only have to wait the shortest possible time. We are aware that your tools are essential, we'll do all we can to offer the service you're entitled to expect!



5 LOGISTICS!

A modern logistics infrastructure based in the Netherlands and in France for greater responsiveness.

6 DELIVERY!

Orders processed in under 24 hours and delivery within a week.

7 AN INNOVATIVE PRODUCT APPROACH!

All our products are developed with our partner customers. They have been selected among the leaders in their sectors of activity.



INNOVATION OUR DNA



Kap'SAM
THE SMART
JUMP STARTER

STARTS AN INFINITE
NUMBER OF VEHICLES:
1,000,000 CYCLES

P.45

DYNASAM 4.0
COMMUNICATING TORQUE WRENCHES
OPTIMISED TRACEABILITY

P.71



XDRAINER
THE STANDALONE
BLEEDER

GUARANTEES
HANDS-FREE
DRAINING
AND FILLING

P.36




CONTENTS

IMPACT WRENCHES	P. 4	
SOCKETS	P. 7	
ACCESSORIES FOR IMPACT WRENCHES	P. 8	
NUT EXTRACTOR KIT	P. 9	
RATCHET WRENCHES	P. 10	
POWER DRILLS & SCREWDRIVERS	P. 12	
MATERIAL REMOVAL	P. 14	
MAINTENANCE	P. 16	
BODYWORK - CUTTING	P. 18	
SANDING / POLISHING / DEBOSSING	P. 22	
LIFTING	P. 26	
REELS	P. 30	
AIR TREATMENT & ACCESSORIES	P. 32	
ATOMISERS & SUCTION UNITS	P. 34	
COOLING CIRCUIT DRAINER, XDRAINER®	P. 35	
GARAGE AND WORKSHOP EQUIPMENT	P. 37	
INFLATORS	P. 39	
BLOWGUNS	P. 40	
LAMPS	P. 42	
BOOSTERS, KAP'SAM®	P. 44	
UNIVERSAL PRESSURE TESTER	P. 46	
INSULATED TOOLS	P. 48	
SERVICE PANELS	P. 56	
STORAGE	P. 60	
TOOLBOXES	P. 67	
TORQUE WRENCHES & BITS / DYNASAM®	P. 69	

LEGEND

			
Height MM	Length MM	Air consumption L/MIN	Fitting MM
			
Cutting capacity MM	Drive square INCH	Tightening capacity MM	Dimension of the paper MM
			
Min. pipe diameter MM	Piston stroke MM	Power KW	Rotation speed RPM
			
Weight KG	Max. torque NM	Traction force KG-MM	Disc dimensions MM
			
Off-centre travel	Capacity KG	Vibrations M/S.2	

SL RANGE



The 'Y' point means perfect machine balancing between the body, handle and nose.

IMPACT WRENCHES

RODAC superior range. Powerful ergonomically designed machines. High manufacturing quality and extended lifetime. Unique design!

REF.		NM	L/MIN	RPM	KG	
RC2690	3/8"	434	118	7.500	1,3	
RC2780	1/2"	1.350	153	10.000	2,0	
RC2780T	1/2"	90-130	153	6.500	2,0	
RC3780	3/4"	1.492	139	5.000	2,6	
RC8880	1"	1.500	250	5.000	2,0	

BESTSELLER

L = 12 cm !



STUBBY

The most compact 1/2" impact wrench

Twin hammer = Double strike = Fewer vibrations for a 650Nm power rating when loosening!
Lightweight. Can be used with just one hand. Composite body.
Also exists in 3/8" version: RC2690
Torque: 434Nm. Unique design!

RC2751	1/2"	610	120	9.000	1,3	
--------	------	-----	-----	-------	-----	--



1/2" IMPACT WRENCHES IN A CASE

RC2751BC: 13 to 19, 21 and 24 mm impact sockets (photo on the left)
RC2780BC: 17, 19, 21 mm impact sockets with plastic protection + 22, 23, 24 mm impact sockets (photo on the right)

REF.		NM	L/MIN	RPM	KG	PRICE
RC2751BC	1/2"	610	120	9.000	1,1	
RC2780BC	1/2"	1.350	153	10.000	1,1	

1/2" IMPACT WRENCH

1 Max. torque 550 Nm
2 rotation speeds 9000 rpm
Air consumption 120 l/min
Weight 1.3 Kg.
Ideal for confined spaces.
Head tiltable through 360°.
2-Year guarantee.

RC2851



BLACKLINE

THE PREMIUM LINE

For intensive use, a double-strike mechanism, composite body, lightweight and long-lasting!

Suitable for the most demanding professional user!

- TWIN HAMMER
- LIGHTWEIGHT
- VERY POWERFUL
- HIGH QUALITY MATERIALS



3/8" IMPACT WRENCH

REF.						PRICE
	NM	L/MIN	RPM	KG		
RC660	3/8"	583	260	12.000	1,2	



1/2" IMPACT WRENCH COMPACT!

REF.						PRICE
	NM	L/MIN	RPM	KG		
RC2850	1/2"	624	260	12.000	1,2	



1/2" IMPACT WRENCH

REF.						PRICE
	NM	L/MIN	RPM	KG		
RC2890	1/2"	1.400	260	8.000	1,9	



3/4" IMPACT WRENCH

REF.						PRICE
	NM	L/MIN	RPM	KG		
RC3850	3/4"	2.035	475	5.000	3,4	



1" IMPACT WRENCH

REF.						PRICE
	NM	L/MIN	RPM	KG		
RC8850	1"	2.035	475	5.000	3,5	

1/4" VIBRO-EXTRACTOR WITH ACCESSORIES IN A CASE

Ideal for loosening glow plugs, adjustable torque: 10-20-30-40 NM



REF.						PRICE
	NM	L/MIN	RPM	KG		
RC630BC	1/4"	10,20,30,40	150	10.000	4,6	

1/2" IMPACT WRENCH COMPOSITE 1054 Nm

Max. torque: 1054 Nm.
Twin Hammer
3 positions to the right, 1 to the left



REF.						PRICE
	NM	L/MIN	RPM	KG		
RC2775	1/2"	1.054	125	9.000	2	

1" IMPACT WRENCHES 3800 Nm

Powerful tool.
1007400A short axis: 335 mm
1007400AL long axis: 520 mm



REF.						PRICE
	NM	L/MIN	RPM	KG		
1007400A	1"	3.800	700	4.100	9,3	
1007400AL	1"	3.800	700	4.100	9,3	

1" IMPACT WRENCHES 2241 Nm

Extra lightweight. Ergonomic design with long axis for hard-to-access places. Length 21 cm.



REF.						PRICE
	NM	L/MIN	RPM	KG		
RC766	1"	2441	282	6.000	7,8	

COMPACT 3/8" IMPACT WRENCH



REF.						PRICE
	NM	L/MIN	RPM	KG		
RC632	3/8"	75	170	9.000	1,1	

LONG 1" IMPACT WRENCH 2441 Nm

QUALITY FOR AN AFFORDABLE PRICE



REF.						PRICE
	NM	L/MIN	RPM	KG		
RC762L	1"	2.441	222	4.200	11,2	

1" IMPACT WRENCHES 3000 Nm

Modern design
Powerful tool.
Available with long or short axis.
RC765B: Length 420 mm
RC765BL: Length 520 mm



REF.						PRICE
	NM	L/MIN	RPM	KG		
RC765B	1"	3.000	380	4.800	8,3	
RC765BL	1"	3.000	380	4.800	8,3	

1" IMPACT WRENCHES 3800 Nm

Compact design with short axis



THE MOST POWERFUL WRENCH IN THE RANGE!

REF.						PRICE
	NM	L/MIN	RPM	KG		
1007401A	1"	3.800	700	4.100	8,9	

SET OF FIVE 1/2" SOCKETS WITH PLASTIC PROTECTION

**LENGTH
15 MM**
max. 200 nm



RAG499815



**LENGTH
17 MM**
max. 200 nm



RAG499817



**LENGTH
19 MM**
max. 200 nm



RAG499819



**LENGTH
21 MM**
max. 200 nm



RAG499821



EXISTS IN A CASE

CASE OF 3 1/2" SOCKETS

3 sockets 17-19-21 mm, with plastic protection, thin wall with stop, max 200 nm, CR-MO

RA8681



CASE OF 5 1/2" SOCKETS

5 sockets 15-17-19-21-22 mm, with plastic protection, CR-MO max. 200 nm.

RA86815



SET OF 9 SOCKETS FOR DIFFICULT NUT EXTRACTION

3/8" 2, 3, 4, 5, 6 mm,
1/2" 8, 10, 12, 14 mm on rail.



RA8690



SET OF 9 IMPACT SOCKETS, 1/2"

13, 14, 15, 16, 17, 18, 19,
21, 24 mm on rail.

RA8679



SET OF 8 IMPACT SOCKETS, 1/2"

8 impact sockets:
12, 13, 14, 15, 17, 19, 21 and 22 mm

RA8692



SET OF 15 IMPACT SOCKETS, 1/2"

13 impact sockets: 10, 11, 12, 13,
14, 17, 19, 21, 22, 24, 27 30, 32 mm
+ 1 universal joint.
+ 1 x 125 mm extension.

RA8691



SET OF IMPACT REDUCER FITTINGS

Reducer fitting 1/2" - 3/4"
Reducer fitting 3/4" - 1/2"
Reducer fitting 1/2" - 3/8"
Reducer fitting 1/4" - 3/8"
Reducer fitting 3/8" - 1/4"
Reducer fitting 3/8" - 1/2"

20029S00A





CLEANING KIT FOR WHEEL HUBS

Cleaning discs, use with 1/2" impact wrench

RR275140



1/2" RACHET ADAPTER

50 MM TWIST-ON TRAY

For twist-on discs, use with a 1/2" impact wrench

RR275141



1/2" ADAPTOR WITH 75 MM VELCRO TRAY

For twist-on discs, use with 1/2" impact wrench

RR275143

SET OF 6 DISCS WITH UNIVERSAL MOUNT

Wheel hub cleaning kit
50x12 - 50x13 - 50x14 - 60x16 - 60x22 - 60x28

RR275130



WHEEL HUB CLEANING KIT

For RR275140, 5 parts

RR27514ASET



DISC 160 MM X 65 M

RR275150A



DISC 200 MM X 75 M

RR275150B



UNIVERSAL DISC MOUNT

RR275150H



1/2" STRIPPING DISC

For brakes (with reinforced centre)

RRNC27515H



SET OF 3 DISCS

RRNC27515SET



PNEUMATIC UNIVERSAL JOINT BELLOWS EXPANDER

No longer any need to remove the universal joint 1/4" connection
Suitable for all cars and 4x4 vehicles.

RCBS03



SWAY-BRACE POST FOR STEERING AXIAL BEARING

Interchangeable head: one tool covers spherical bearings from 28 to 45 mm diameter. Compact, self-tightening tool for quick and easy removal of axial ball joints on cars and trucks.

Allows to work on different size steering ball joints thanks to the 3 interchangeable colour coded cages:
 Red - Ø 28-34 mm. Maximum torque: 80 Nm
 Blue - Ø 34-39 mm. Max torque: 100 Nm
 Green - Ø 39-45 mm. Max torque: 150 Nm



732-DA2

TORQUE MULTIPLIER WRENCH HGV 1" - 2800 NM

Force multiplier 1" impact socket
 34/27/30/32/33/36mm
 Handle/210mm extension, 1" square, ext and int, multiplication ratio: 1:64
 Output torque 4000 nm max
 Input torque 62.5 nm max
 Square drive: 1.




RQDM-PL

1/2" BRUSHLESS 18 V IMPACT WRENCH

Square drive: 1/2" (12.7 mm). Maximum torque: 1,000 Nm.
 Speed (rpm): 0 to 900 / 1,200 / 1,900.
 Impact (hits/min): 1,200-1,600/2,400.

Battery: Lithium-ion, 18 V / 4 Ah Minimum amperage: 4 Ah.
 Battery level indicator. Ideal for working on wheel wells, brakes, ball joints, suspension arm triangles...

Body and batteries resistant to workshop solvents and hydrocarbons.
 Supplied in a shockproof case with 2 Lithium-ion batteries and a charger.
 The batteries are compatible with the rest of the range. IP54.
 Charging time: 90 min.



RB210KZ2

WITH 2 BATTERIES AND A CHARGER

NEW-GENERATION TAMPER-PROOF NUT EXTRACTION KIT

- 4 nylon internal centring guides
- 3 metallic external centring guides
- 1 metallic centring guide
- 2 special ultra-resistant drill bits
- 4 extractors
- 1 impact extractor support
- 1 impact extractor removal tool.

RA9900

SUITABLE FOR ALL TYPES OF TAMPER-PROOF BOLTS WHATEVER THE BRAND OF VEHICLE.

THE MOST COMPLETE SET ON THE MARKET.

CAN ALSO BE USED FOR DAMAGED OR WORN NUTS.

HUGE TIME-SAVINGS WITHOUT DAMAGING THE WHEEL.

STRONG AND PRACTICAL CASE.



GO TO WWW.RODAC.COM TRAINING & DEMONSTRATION VIDEO



1/4" RATCHET WRENCH 34 Nm

Super mini,
ideal for narrow spaces.



REF.							PRICE
	NM	L/MIN	RPM	CM	KG		
1013300A	1/4"	34	108	260	13	0,45	
1014300A	3/8"	34	108	260	13	0,45	

1/4" ratchet wrench 41 Nm

Mini, powerful and compact.
With up / down switch.
Adjustable torque.



REF.							PRICE
	NM	L/MIN	RPM	CM	KG		
RC583	1/4"	41	113	200	19,6	0,5	
RC584	3/8"	41	113	200	19,6	0,5	

1/2" RATCHET WRENCH 68 Nm

Limited torque for delicate tightening. With up / down switch.
Adjustable torque. Also suitable in combination with sound-absorbing hose.



REF.							PRICE
	NM	L/MIN	RPM	CM	KG		
RC590	1/2"	68	113	150	25,6	1,2	

1/2" RATCHET WRENCH 140 Nm

Suitable for heavier vehicles.



REF.							PRICE
	NM	L/MIN	RPM	CM	KG		
RC468	1/2"	140	140	150	36	2,0	



1/2" / 3/8" RATCHET WRENCHES



REF.							PRICE
	NM	L/MIN	RPM	CM	KG		
1015100A	1/2"	122	105	160	25	1,25	
1014100A	3/8"	122	105	160	25	1,25	

1/2" IMPACT RATCHET WRENCH 102 Nm

Intensive industrial use.
Also suitable in combination with sound-absorbing hose.



REF.							PRICE
	NM	L/MIN	RPM	CM	KG		
1015400A	1/2"	102	113	400	28	1,28	
1014400A	3/8"	102	140	400	28	1,28	

COMPLETE!

1/4" + 3/8" RATCHET WRENCH IN A CASE

Contents:

- X1 RC582 open-ended pneumatic ratchet wrench
- X1 Interchangeable 1/4" + 3/8" ratchet head
- X1 Bit-holder ratchet head
- X1 1/4" ratchet
- X10 1/4" sockets 5.5-6-7-8-9-10-11-12-13-14 mm
- X1 1/4" universal joint
- X1 1/4" bit holder with blocking
- X1 1/4" extension with blocking
- X1 1/4" fitted extension
- X1 1/4" bit 25 mm

REF.							PRICE
	NM	L/MIN	RPM	CM	KG		
RC582BC	1/4" + 3/8"	41	113	850	40	0,5	



1/4" - 3/8" MINI RATCHET WRENCH

ADAPTABLE : Can switch between 1/4" and 3/8" to adapt to each situation. Its compact size enables the user to work within confined areas.

EASY TO USE : Easy to handle thanks to its light weight (500 g).

REF.							PRICE
	NM	L/MIN	RPM	CM	KG		
RC582	1/4" - 3/8"	41	113	850	40	0,5	



PREMIUM LINE



10 mm DRILL

Aluminium body
Intensive industrial use



3 AIR CONNECTION
POSSIBILITIES

REF.	RPM	KW	KG	PRICE
RC2020A	1600	0,2	0,6	

13 mm DRILL

Aluminium body with handle
Intensive industrial use



REF.	RPM	KW	KG	PRICE
RC2022A	750	0,4	0,9	

DRILL GUN 6 mm

Fast-tightening chuck.



REF.	RPM	KW	KG	PRICE
RC203A	2.900	0,6	0,6	

ANGLE DRILL 6 mm

Fast-tightening chuck.
Rotating left and right.



REF.	RPM	KW	KG	PRICE
RC208RA	1.400	0,50	0,9	

10 mm STRAIGHT DRILL

Air consumption: 190 L/M.



REF.	RPM	KW	KG	PRICE
RC217A	4.500	0,50	0,9	

DRILL GUN 10 mm

No-key automatic chuck reversible.
Air consumption: 113 L/M.



REF.	RPM	KW	KG	PRICE
RC2110	2.000	0,37	1,0	

DRILL GUN WITH HANDLE 13 mm

With handle.
With safety lever and steel quick-release chuck.
Rotating left and right.
Air consumption: 200 L/M.



REF.	RPM	KW	KG	PRICE
RC214A	800	0,55	1,6	

DRILL GUN 13 mm

No-key automatic chuck reversible.
Air consumption: 113 L/M.



REF.	RPM	KW	KG	PRICE
RC2113	800	0,37	1,3	

COMPLETE!

10 mm DRILL IN A CASE

11 drill bits 1.5, 2, 2.5, 3, 3.2, 3.5, 4, 4.5, 4.8, 5, 5.5, 6, 6.5 mm



REF.	RPM	KW	KG	PRICE
RC206ABC	1800	0,50	1,4	

POWER SCREWDRIVER GUN 1700 RPM

Rotating left and right.
Air consumption: 550 L/M.



REF.	RPM	NM	KG	PRICE
RC3403	1.700	1-6	0,85	

POWER SCREWDRIVER GUN 1800 RPM

Rotating left and right. Air consumption: 113 L/M.

TORQUE ADJUSTABLE FROM THE EXTERIOR



REF.	RPM	NM	KG	PRICE
RC3418	1.800	2,2-5,6	1,1	

STRAIGHT POWER SCREWDRIVER 550 RPM

Adjustable torque, for industrial use

PUSH TO START



REF.	RPM	NM	CM	KG	PRICE
RC3460	550	1,5-9,5	21,5	0,79	

Find all the accessories for your pneumatic tools on RODAC.com



RODAC International B.V.

Offers a two-year guarantee for manufacturing and material-related failures, not for the wear of parts. Overhauls are not covered by the guarantee, these are normal maintenance operations which can also be carried out by us. It is often possible to avoid repairs with suitable high-quality greasing (with appropriate grease) and a good air supply. If in doubt, contact our administrative service to obtain advice.



HEXAGONAL CHIPPER

Including spring RA8620
Air consumption: 240 L/M.

REF.	BPM	MM	MM	KG	PRICE
RC275HR	2.500	11	67	1,7	



CHISELS IN A CASE

RC275BCB : has an air consumption of 240 L/M.
RC293HBCB : has an air consumption of 280 L/M.

REF.	BPM	MM	MM	KG	PRICE
RC275BCB	2.500	11,0	67	1,7	
RC293HBCB	3.200	11,0	66	2,56	



GUARANTEED
2
YEARS

HEXAGONAL CHIPPER

Including metallic retaining bushing RA293
Air consumption: 240 L/M.

REF.	BPM	MM	MM	KG	PRICE
RC293H	3.200	11	66	2,56	

CHIPPER

Suitable for cylindrical chisels
Reduced vibrations 8.2 m/s. 2 springs included.
Air consumption: 396 L/M.

CHISELS AVAILABLE
ON REQUEST!



REF.	BPM	MM	MM	KG	PRICE
RC299	3.000	11,1	67	1,7	

CHIPPER

For metal works - 5 chisels included
Air consumption: 240 L/M.



REF.	BPM	MM	MM	KG	PRICE
RC275BC	2.500	11,0	67	1,7	

CHIPPER

For metal works - 5 chisels included
Air consumption: 280 L/M.



RC293HBC	3.200	11,0	66	2,5	
----------	-------	------	----	-----	--

CHIPPER

For metal works - 5 chisels included
Air consumption: 113 L/M.



RC296BC	2.600	11,0	73	2,2	
---------	-------	------	----	-----	--

BESTSELLERS

STRAIGHT RUST REMOVER

19 needles 3 mm
Air consumption: 113 L/M.



REF.	BPM	CM	MM	KG	PRICE
RC4117	3.700	375	33	2,7	

RUST REMOVER GUN

19 needles 3 mm
Air consumption: 113 L/M.



REF.	BPM	CM	MM	KG	PRICE
RC4115	3.000	290	11	2,6	

NEW



ULTRA-COMPACT RUST REMOVER

Compact rust remover with 13 tapered needles, dia. 1.4 mm


Used for optimum cleaning of small objects.
The needle descaler has a vibration-reducing coating and only weighs 0.48 kg. You can hold this tool like a pencil, allowing you to work very precisely.

3000 hits/min.
22mm piston stroke.
Air connection, 1/4".
Operating pressure 6.3 Bar.
max - 89 DBA.

REF.	L/MIN	MM	M/S.2	KG	PRICE
RC4113	1/4"	48	235	6,9	0,48



WITH BUILT-IN REDUCER NOZZLE



EXTRUSION GUN CARTRIDGES OR BAGS

REF.	L/MIN	CM	KG	PRICE
RC119N	200	55	1,4	



EXTRUSION GUN BAGS

WITH BUILT-IN REDUCER NOZZLE



REF.	L/MIN	CM	KG	PRICE
RC120N	200	46	1,1	



EXTRUSION GUN CARTRIDGES 310 ML

REF.	L/MIN	CM	KG	PRICE
RC107	200	32	1,2	



BALANCERS

Cable capacity from 1 to 5 kg

REF.	KG KG	CABLE CM	PRICE
RASB2000	1 - 2	160	
RASB3000	1,5 - 3	160	
RASB5000	3 - 5	160	



INTENSIVE INSERT RIVETER IN A CASE

REF.	RPM	L/MIN	CM	KG KG	PRICE
1086100ABC	600	160	16	1,27	



LIQUIDS GUN

1 litre capacity

REF.	CM	KG KG	PRICE
RC175	26	0,11	



GREASE GUN

0.4 litre capacity with uninterrupted supply
For loose and cartridge grease

REF.	CM	KG KG	PRICE
RC1170	15,7	1,4	



PROTECTION TREATMENT GUN

Totreat all protection surfaces and coatings. 1 litre capacity. Also suitable for screw sockets. Supplied with probes RA12901, RA12902 and RA12903.

REF.	CM	KG KG	PRICE
RC129	39	1,6	



STICKER-REMOVAL GRINDER

Includes rubber disc RA53336 for stickers

REF.	RPM	L/MIN	CM	KG KG	PRICE
RC533	4.000	350	20	1,0	



HVLP PAINT GUN

For water-based and conventional paint. 1.4 mm nozzle included, 1.3 + 1.7 + 2.0 - 2.5 mm nozzle option. 600 cc pot

RC1200H



PREMIUM LINE

HVLP PAINT GUN

For water-based and conventional paint. 1.4 mm nozzle included, 1.3 + 1.7 + 2.0 - 2.5 mm nozzle option. 600 cc pot

RC1300H



WINDSCREEN KNIFE SUPPLIED WITHOUT A BLADE

Including sound-absorbing hose.



REF.	CM	L/MIN	KG	PRICE
RC332	24	360	1,0	

SEE OUR LARGE CHOICE
OF KNIVES AT OUR WEBSHOP:
WWW.RODAC.COM



WINDSCREEN SUPPORT TABLE



REF.	CM	CM	KG	PRICE
RQ371080	40	80	9,3	

WING PROTECTION



RAMG5050

FRONT COVER

Dirt-repellent and washable.



RAMG5060

SEAT PROTECTION COVER

Dirt-repellent and washable.



RAMG5070

SHEET-METAL SAW +5 BLADES 24 TEETH +5 BLADES 32 TEETH



REF.	BPM	MM	L/MIN	KG	PRICE
RC312SET	9.000	1,6	270	0,5	



RIVETER IN A CASE 2.4 - 6.4 MM

Intensive use, 2,4/ 3,0-3,2/4,0/ 4,8/ 5,5/ 6,4 rivets

REF.	KG-MM	KG	PRICE
RC192BC	10.900	2,8	

NEW



PNEUMATIC SHEET-METAL SAW

The perfect tool for cutting composite materials and metal (sheet), in the automotive and industrial sectors.

New design of the geared transmission: cutting capacity doubled with respect to standard pneumatic saws (5 mm metal or composite sheets).

Highly reliable 0.5 hp pneumatic motor with precision-machined cylinder and rotor.

360° rotary air outlet.
Trigger with safety latch.

RC320

**WITH ERGONOMIC
PU COMPOSITE HANDLE**

RIVETER 2.4 - 4.8 MM

2,4 / 3,0-3,2 / 4,0 / 4,8 rivets

REF.	KG-MM	KG	PRICE
RC191	8.300	1,9	



RIVETER 2.4 - 6.4 MM

Intensive use, 2,4/ 3,0-3,2/4,0/ 4,8/ 5,5/ 6,4 rivets

REF.	KG-MM	KG	PRICE
RC192	10.900	2,8	



PUNCH



REF.	L/MIN	MM	CM	KG	PRICE
RC236	113	1 - 5	25	1,2	

ETCHING PENCIL

Suitable for various materials. Speed is adjustable.



REF.	BPM	L/MIN	CM	KG	PRICE
RC361	500	30	17	1,2	

CHISEL



REF.	L/MIN	MM	CM	KG	PRICE
RC224	115	1,8	25,8	1,2	

NIBBLER



REF.	L/MIN	MM	CM	KG	PRICE
RC4005	220	1,25	18	0,9	

WELD-SPOT REMOVER

INCLUDED: RA350F06: 6 mm
+ RA350F08: 8 mm
Dia. 6.0 - 8.0 mm
OPTION: 75/135 mm arc



REF.	BPM	L/MIN	KG	PRICE
RC355	1.600	230	2	

NEW


ANGLE GRINDER

3-position adjustable head. The tool can turn to the right and left to direct the stream of sparks.

0.8 hp pneumatic motor delivers a higher torque for a greater cutting capacity.

360° rotary protection cap to allow you to change speed.

Fast-clearance design simplifying the adjustment of the position of the flexible head.



REF.	L/MIN	RPM	CM	M/S.2	KG	PRICE
RC274	1/4"	200	16.000	245	4,9	1,3



LONG ANGLE GRINDER FOR Ø 75 MM DISCS

REF.	RPM	KW	L/MIN	KG	PRICE
RC2675	16.000	0,7	160	1,4	

ANGLE GRINDER FOR Ø 75 MM DISCS

REF.	RPM	KW	L/MIN	KG	PRICE
RC269	22.000	0,37	350	0,82	



ANGLE GRINDER FOR Ø 75 MM DISCS

Left/right rotation with adjustable protection, reduced air consumption 115L/min. Lower trigger for greater comfort.

REF.	RPM	KW	L/MIN	KG	PRICE
RC267	18.000	0,34	115	0,97	



ANGLE GRINDER FOR Ø 50 MM DISCS

Suitable for cutting and crushing
Reduced air consumption: 113L/min.
Low sound level: 83dB MINI: 129mm.

REF.	RPM	KW	L/MIN	KG	PRICE
RC272	20.000	0,25	113	0,5	



ANGLE GRINDER FOR Ø 75 mm discs

ECONOMICAL CHOICE!

REF.	RPM	KW	L/MIN	KG	PRICE
RC268	22.000	0,3	300	0,7	



LONG ANGLE GRINDER FOR Ø 100 MM DISCS

Reduced air consumption - 377 mm long
Shaft blocking button
Adjustable protection casing (126° - 11 positions)
Suitable for deep cutting and places that are difficult to access

REF.	RPM	KW	L/MIN	KG	PRICE
RC261	14.000	0,7	113	1,7	



ANGLE GRINDER FOR Ø 125 mm discs

REF.	RPM	KW	L/MIN	KG	PRICE
RC26125	12.000	0,8	280	1,7	



6 MM GRINDER, 90°



REF.	RPM	KW	L/MIN	KG	PRICE
RC535	4.500	0,35	230	0,8	

6 MM GRINDER, 45°

Suitable for sound-absorbing hose with ref. RH100.
Speed adjustable.



REF.	RPM	KW	L/MIN	KG	PRICE
RC534	22.000	0,34	113	0,7	

LONG 6 MM GRINDER

Suitable for sound-absorbing hose with ref. RH100.
Speed adjustable.



REF.	RPM	KW	L/MIN	KG	PRICE
RC133	25.000	0,15	200	0,4	

COMPACT 6 MM GRINDER

MINIMUM: 172 mm! Suitable for sound-absorbing hose with ref. RH100. Speed adjustable.



REF.	RPM	KW	L/MIN	KG	PRICE
RC138	22.000	0,15	200	0,6	

6 MM GRINDER

Reduced air consumption: 113L/min.
Low sound level: 79dB



REF.	RPM	KW	L/MIN	KG	PRICE
RC128	22.000	0,25	140	0,3	

6 MM GRINDER, 90°

Suitable for sound-absorbing hose with ref. RH100.
Speed adjustable.



REF.	RPM	KW	L/MIN	KG	PRICE
RC139	22.000	0,15	200	0,6	

LONG 6 MM GRINDER



REF.	RPM	KW	L/MIN	KG	PRICE
RC530L	22.000	0,37	200	0,6	

6 MM GRINDER

Suitable for sound-absorbing hose with ref. RH100.
Speed adjustable.



REF.	RPM	KW	L/MIN	KG	PRICE
RC133L	25.000	0,15	200	0,9	

6 MM GRINDER

ECONOMIC



AVAILABLE IN A CASE!

Suitable for sound-absorbing hose with ref. RH100. Speed adjustable.



REF.	RPM	KW	L/MIN	KG	PRICE
RC530	22.000	0,37	200	0,5	

RC530BC

6 MM MICRO-GRINDER

Adjustable rotation speed. Supplied with 10 grindstones (3 mm) in a case.



REF.	RPM	MM	L/MIN	KG	PRICE
RC161BC	20.000	0,37	113	0,7	

GRINDER WITH BRUSHES AND DISCS IN A CASE

Air consumption: 115 L/M. The set contains: 1x grinding machine, 2x foil wiper, 4x brush belts (each 2x narrow and coarse and each 2x wide and fine), 5x cleaning disc black, various holders for accessories. Ideally suited for bodyshop.



REF.	RPM	KG	PRICE
RC380BC2	3.500	4,2	

VULCANIZING GRINDER

With soundproofing tube. Option accessories: RA521 tire rougher attachment.



REF.	RPM	KW	L/MIN	KG	PRICE
RC537	2.600	0,30	350	0,5	

VULCANIZING GRINDER

Option accessories: RA521 tire rougher attachment.



REF.	RPM	KW	L/MIN	KG	PRICE
RC536	2.500	0,3	350	1,18	

GRINDER FOR DISCS Ø 115-125 MM, FAST NUT M14

Option: sound-absorbing hose RA7701.



REF.	RPM	KW	L/MIN	KG	PRICE
RC7720	10.000	0,51	500	1,8	

M14 GRINDER FOR Ø 180 MM DISCS



REF.	RPM	KW	L/MIN	KG	PRICE
RC7725	7.000	0,85	800	3,5	

SANDER WITH 50 & 75 MM DISCS

Speed adjustable.
ROLOC system.



REF.	RPM	MM	L/MIN	KG	PRICE
RC163	15.000	50+75	190	0,8	

ORBITAL SANDER WITH 50 & 75 MM DISCS

With Velcro tray.
Speed adjustable.



REF.	RPM	MM	MM	L/MIN	KG	PRICE
RC169	15.000	50+75	4	190	0,8	

POLISHER 75 MM DISC

With Velcro tray.
Speed adjustable.



REF.	RPM	MM	L/MIN	KG	PRICE
RC166	2.500	75	190	0,8	

AVAILABLE IN CASES!

SANDER WITH 50 & 75 MM DISCS (IN A CASE)

Includes: 34 50mm sanding discs
34 75mm sanding discs.
Speed adjustable. ROLOC system.



RC163BC



ORBITAL SANDER WITH 50 & 75 MM DISCS (IN A CASE)

Includes:
15 50mm sanding discs
15 75mm sanding discs

RC169BC

POLISHER 75 MM DISCS (IN A CASE)

Includes: 2 sponges and
1 polishing buff 75 mm.
Speed adjustable. Including
accessories.



RC166BC



BELT SANDERS 10 AND 20 MM.

RC8430: supplied with 2 abrasive belts, 10 x 328 mm
RC8440A: supplied with 2 abrasive belts, 20 x 520 mm

REF.	RPM	MM	L/MIN	KG	PRICE
RC8430	18.000	10x328	350	0,9	
RC8440A	18.000	20x520	350	0,9	

ORBITAL SANDER Ø 32 MM

with Velcro tray



REF.	RPM	MM	L/MIN	KG	PRICE
RC9330	7.500	32	113	0,6	

SANDER FOR SUPPLE DISCS

One disc: RA8609 (75 mm) /
RA8610 (115 mm) / RA8611 (140 mm)



REF.	RPM	MM	L/MIN	KG	PRICE
RC265	18.000	75/115/140	425	0,6	

ORBITAL SANDERS Ø 150 MM

No oil, only 76 and 84 dB(A)
With suction
Speed adjustable.



REF.	RPM	MM	MM	L/MIN	KG	PRICE
RC92461S	12.000	150	5	57	0,7	
RC92462S	12.000	150	2,5	57	0,7	
RC92463S	12.000	150	10	57	0,7	

ORBITAL SANDER Ø 77 MM

No oil, only 76 dB(A). Speed adjustable.



REF.	RPM	MM	MM	L/MIN	KG	PRICE
RC92332S	12.000	77	2,5	57	0,6	

ORBITAL SANDER Ø 150 MM

Only 76 dB(A). With suction and Velcro tray
Speed adjustable.



REF.	RPM	MM	MM	L/MIN	KG	PRICE
RC9461S	12.000	150	5	57	0,7	

ORBITAL SANDER Ø 150 MM

No oil, only 76 dB(A). With suction and Velcro tray.
Speed adjustable.



RC927V	7.000	150	10	115	1,8	
--------	-------	-----	----	-----	-----	--

ORBITAL SANDER Ø 150 MM

Only 76 dB(A). with Velcro tray.
Speed adjustable.



RC9361S	12.000	150	5	57	0,6	
---------	--------	-----	---	----	-----	--

ORBITAL SANDER Ø 77 MM

with Velcro tray. Speed adjustable.



RC9332S	12.000	77	2,5	57	0,6	
---------	--------	----	-----	----	-----	--

SANDER Ø 150 MM

with Velcro tray.
Accessories available separately.



REF.	RPM	MM	L/MIN	KG	PRICE
RC7236	3.500	150	110	1	


FILE SANDER 70x400 MM



REF.	RPM	MM	L/MIN	MM	KG	PRICE
RC8950	3.000	70x400	230	26	3	

VIBRATING SANDER, SUCTION, MADE OF COMPOSITE - 90X175 MM

Speed controllable and dust extraction.



REF.	RPM	MM	L/MIN	KG	PRICE
RC8975	10.000	90x175	400	1	

MAKE YOUR HEADLIGHTS SHINE

HEADLIGHT INSERT REPAIR KIT

RC1669SET



Visual	REF.	Designation
	RC169	Orbital sander
	RC166	Sander
	1565-930	Microfibre cloth
	1565-935	Protection spray
	1565-931 STEP1 1565-932 STEP2	Polishing liquid
	1346-930	Set of 2 interfaces foam d.75 mm
	1346-931	Set of 50 abrasives disc for sender gr.500 d.75
	1346-932	Set of 50 abrasives disc for sender gr.800 d.75
	1346-933	Abrasive disc for sender gr.1500 d.75
	1346-934	Abrasive disc for sender gr.3000 d.75
	1346-935	50 m de cinta de 25 mm
	1565-933	Medium white polishing foam d.75 for polishing
	1565-934	Soft black polishing foam d.75

1/ SANDING

DRY SANDING WITH P500 DISCS



ORBITAL SANDER RC169

2/ SANDING

DRY SANDING WITH P800 DISCS



ORBITAL SANDER RC169

3/ CLEANING

WIPE WITH MICROFIBRE CLOTH



4/ SANDING

SAND WITH WATER USING THE NORTON ICE® GR1500 DISCS



ORBITAL SANDER RC169

5/ SANDING

SAND WITH WATER USING THE NORTON ICE® GR3000 DISCS



ORBITAL SANDER RC169

6/ CLEANING

WIPE WITH MICROFIBRE CLOTH



7/ BUFFING

BUFF WITH LIQUID ICE "STEP 1"



ORBITAL SANDER RC166

8/ BUFFING

BUFF WITH LIQUID ICE "STEP 2"



ORBITAL SANDER RC166

9/ CLEANING

WIPE WITH MICROFIBRE CLOTH



HYDRAULIC BODYWORK JACKS 4 OR 10 TONNES

For debossing, separating and clamping.

IN A STRONG METAL CASE



4 TONNES
TL804N




10 TONNES
TL810N



POLISHER Ø150 MM M14 CONNECTION

Fitted with an anti-vibration handle.
Accessories available separately.

WITH
VELCRO TRAY



REF.	RPM	MM	KW	L/MIN	KG	PRICE
RC7242	2.500	150	0,55	170	2	


OLEOPNEUMATIC PEDAL PUMP

RQAB71



CYLINDER JACKS

The jacks are electrostatically painted in order to avoid corrosion.



REF.	T	A	B	C	D	E	F	KG	PRICE
TL102N	2	168	108	48	316	94,5	78	2/2,21	
TL104N	4	185	115	60	363	108,5	87	2,8/2,97	
TL106N	6	207	125	70	402	117	97	3,7/3,92	
TL108N	8	222	145	80	447	124	106	4,8/4,94	
TL112N	12	230	150	80	460	134,5	114	6/6,18	
TL120N	20	240	150	60	450	160	140	8,6/9	

OLEO PNEUMATIC JACKS

20-40 TONNES RQGCL215L
Min. height: 150 mm.
Max. height: 300 mm

19-33-66 TONNES RQGCL315L
Min. height: 150 mm.
Max. height: 335 mm

20-40 TONNES RQGCL215N
Min. height: 150 mm.
Max. height: 300mm



TROLLEY JACK 2 TONNES

Min. height: 200 mm.
Max. height: 560 mm.
Weight: 18 kg.

RBALLOON3



ALUMINIUM TROLLEY JACK 1.5 TONNES WITH DOUBLE CYLINDER

Min. height: 90 mm.
Max. height: 358 mm.
Weight: 14.3 kg.

TL8115



ALUMINIUM TROLLEY JACK 2.5 TONNES WITH DOUBLE CYLINDER

Min. height: 100 mm.
Max. height: 460 mm.
Weight: 26.4 kg.

TL8125



TROLLEY JACK 3 TONNES

With quick lift pedal.
Min. height: 145 mm. Max. height: 500 mm.
Weight: 38 kg.

REQ3008



PREMIUM LINE

**TROLLEY JACK
2.5 TONNES**

Min. height: 75 mm.
Max. height: 515 mm.
Weight: 33.8 kg.
Includes protective pad

REQ3025



EXTRA FLAT!
MIN. HEIGHT 75 MM



2-PART JACK STAND



CAPACITY 2 TONNES

Min. height 278 mm
Max. height 420 mm
Weight: 5.1 kg.

TLGSC62



CAPACITY 6 TONNES

Min. height 395 mm
Max. height 605 mm
Weight: 12.9 kg.

TLGSC66



CAPACITY 3 TONNES

Min. height 288 mm
Max. height 425 mm
Weight: 6.4 kg.

TLGSC63



CAPACITY 10 TONNES

Min. height 468 mm
Max. height 718 mm
Weight: 27.5 kg.

TLGSC10



**JACK STAND
2.5 TONNES**

Min. height: 1240 mm
Max. height: 1950 mm
Weight: 17 kg

RCSHS2



**JACK STAND
3 TONNES**

Min. height: 516 mm
Max. height: 855 mm
Weight: 10 kg

RCMS3



**JACK STAND
5 TONNES**

Min. height: 720 mm
Max. height: 1085 mm
Weight: 10 kg

RCTH5



500 KG REPAIR PIT JACK

Min. height: 1140 mm
Max. height: 1945 mm
Weight: 27 kg

TL666



TROLLEY JACK, 1.5T TO 20T

PRACTICAL: Rubber protection on all the jack heads. Hydraulic travel limiter. **COMFORT AND SPEED:** Polyamide wheels on models lower than 6T; floor protection. Cups fitted with rubber pads to protect the contact surface. The ergonomic handle with grips enables a quick approach whatever the position. The quick-approach pedal allows you to make direct contact. Additional central wheel to facilitate the manoeuvres on model CR-15-B and CR-20-BP. **SAFETY:** Safety pedal: authorises the jack to descend on the user's initiative. Anti-overloading safety valve. Safety device in the case of uncontrolled lowering: "dead man's handle" device - safety valve in the case of overloading - conform to standard EC EN 1494.



RQGCRB2 / RQGCRB3

RQGCR2HN

RQGC6N / RQGC10N

HYDRAULIC BENCH PRESS

Indispensable for pressing, bending and punching. Ideal for installing or removing bolts, bearings and shafts. All presses are equipped with a lead screw for quick contact and fine adjustment with the workpiece. The piston retracts automatically when the relief valve is opened. The presses are delivered complete and ready for use. CE certified by agency Veritas. European quality. Punch set available separately with article number RQAP5600.



RQPBR15

RQPPAR30 / RQPPAR30V

RQPPSR50

RQPPSP50

REF.	Designation	PRICE
RQGCRB2	2-tonne floor jack	
RQGCR2HN	2-tonne ultra-flat floor jack	
RQGCRB3	3-tonne floor jack	
RQGC6N	6-tonne floor jack	
RQGC10N	10-tonne floor jack	

REF.	Designation	PRICE
RQPBR15	15-tonne bench press	
RQPPAR30	20-tonne bench press	
RQPPAR30V	30-tonne hydro-pneumatic press	
RQPPSR50	50-tonne hydraulic press	
RQPPSP50	Hydraulic press with pedal 50-tonne	

HANDLING TROLLEY 250 MM

Max. force 1380 kg, Weight 18 kg,
Min. height 350 mm, max. height 640 mm



TL30900



TL30900SET

SET OF 2:

HANDLING TROLLEY 250 MM

To move a vehicle effortlessly.
For 29" wheels max. with a max. width of 250 mm
Weight 23.5 kg.



MAX. FORCE
570 KG

RQWD200

TROLLEY FOR MOVING BODYWORK

Width: 920 - 1.420 mm - Height: 350 - 400 mm
Max. force: 1200 kg



TL20900

LIFTING PACK : JACK 3T + JACK STANDS 3T

Contains:
3T trolley jack
Pair of 3T jack stands

Productivity: lifting and blocking in 30 seconds
Safety: fully secured by valve and protection pin.
Comfort: ultra-compact and lightweight.

PACK-LEV1



LIFTING PACK : JACK 3T + JACK STANDS 3T + JACK 500 KG + CRANE 1T

Contains:
3T trolley jack
Pair of 3T jack stands
500 kg pit cylinder
1T folding mobile crane

PACK-LEV2



FOLDING WORKSHOP CRANE MAX. 1000 KG


Min. height 25 mm
Max. height 2080 mm
Weight: 80 kg.

Designed to facilitate lifting and moving engines and other transmissions.
Also useful in the industrial sector for machining, reconstruction and maintenance jobs.
Quick piston rise and precise lowering controlled by the user thanks to an ergonomic handle. Dead man's handle principle: halts the movement when the user loses control of the operation.

The cranes are equipped with a safety valve calibrated to the nominal force of 50% above the recommended weight.

Device automatically adjusts the descent speed according to the load.
Hydraulic unit swivelling through 135° enables a better user positioning for lifting and lowering operations.

The extensible arm is equipped with a handle in order to facilitate its positioning on the elevator arm. Includes 3 or 4 notches to indicate the lifting force on each point. Silent, non-corrodible polyamide wheels.
Allows the passage of a Euro-type pallet



TL999



BASIC LINE



REELS

PU hose
10 to 20 metres
For air and water

REF.	MM	M	KG	PRICE
RA8834	6x10	10	5	
RA8830	8x12	15	5	
RA8831	10x15	20	5	
RA8833	13x18	12	5	

REEL

Polyurethane (PU) hose 8x12 mm, 30 metres
on rotating plate. Suitable for air and water.

RA8665



ELECTRIC REELS

15 metres

1.5 mm² H05VV-F

RA8890



HP - 2.5 mm² H07RN-F

RA8894



ELECTRIC REELS

3x1.5 mm²
Breflex vinyl

25 METRES

RA88250



50 METRES

RA88500



FLEXIBLE SPIRAL HOSE

Polyurethane (PU) hose 8x12, 7.5 metres - RA8633.

Polyurethane (PU) hose 8x12, 12.5 metres - RA8634.
With 360° connector.

7.5 METRES

RA8633



12.5 METRES

RA8634



NEW



20-METRE REELS

Air inlet: 3/8"

LOW-PRESSURE AIR / WATER REEL

REF.	INLET/ OUTLET BSPT	working pressure BAR	working temperature CENTIGRADE	Material	Hose capacity I.D	M	PRICE
RA8863	3/8"	20	-20°C-+60°C	Hybrid polymer	3/8"	20	

MEDIUM-PRESSURE WATER/OIL REEL

REF.	INLET/ OUTLET BSPT	working pressure BAR	working temperature CENTIGRADE	Material	Hose capacity I.D	M	PRICE
RA8865	3/8"	180	-40°C-+99°C	SAE R1	3/8"	20	

REEL FOR GREASE AND OIL (HYDRAULIC)

REF.	INLET/ OUTLET BSPT	working pressure BAR	working temperature CENTIGRADE	Material	Hose capacity I.D	M	PRICE
RA8867	3/8"	330	-40°C-+99°C	SAE R2	3/8"	20	

**220 V CLEANING TANK
75 LITRES**

Used to clean small mechanical parts quickly. The cleaning liquid is sucked in by the electrical system. Brush included.

TL220N



**ENGINE MOUNTING SUPPORT
MAX. 450 KG**

Dimensions: 933 x 780 x 898 mm
working height: 880 mm.
Weight: 21 kg

TL2000



15-METRE REELS

Hybrid polymer hoses, 10 x15 mm, 15 metres. The reel is equipped with a high-quality rubber hose that can be used for air and water. It is fitted with a ball stop with a blocking device, making it possible to pull out the desired length of hose, where the hose stops. When storing, the hose is reeled in in an ordered way by means of a guide, preventing the hose from being damaged and guaranteeing its long life.

RA8870



OILS

Viscosity 32, 1 litre

PNEUMATIC OIL

to protect your precious pneumatic tools.

RA8658N



HYDRAULIC ANTI-WEAR OIL

RA8659N

MAGNETIC SUPPORT 1/2" IMPACT WRENCH

Version with 4 magnets for greater stability

RAMG8001

1/4" MINI OILER

RA8640



MAGNETIC PLATES



150 x 30 MM

RAMG1000



240 x 140 x 42 MM

RAMG2000



360 x 160 x 42 MM

RAMG3000

TELESCOPIC MIRROR

220 x 925 x 32 mm



RAMG6003

TELESCOPIC MAGNETS

RAMG6001: 180x880x17 mm/max. 2.0 kg
RAMG6002: 180x760x19 mm/max. 4.3 kg



RAMG6001

RAMG6002

MAGNET

50 x 56 mm/ max. 2.0 kg

RAMG6090



360° ROTARY CONNECTION



1/2"

RA8640N12

1/4"

RA8640N14

3/8"

RA8640N38

1/4" AIR REGULATOR



RA8625

PURIFICATION BLOCK

COMPLETE SEPARATE RANGE AVAILABLE



REF.	Designation	Capacity	Max. inlet	Outlet	Filter	PRICE
RASG1000-1	For 1"	8.000 l/min	14 bar	0-12 bar	10 micron	
RASG1000-12	For 1/2"	5.000 l/min	14 bar	0-12 bar	10 micron	
RASG1000-14	For 1/4"	1.800 l/min	14 bar	0-12 bar	10 micron	
RASG1000-38	For 3/8"	5.000 l/min	14 bar	0-12 bar	10 micron	

ALUMINIUM SUPPORTS FOR HOSES



186 x 57 x 75 MM

RQN9060

248 x 79 x 96 MM

RQN9070



NEW



COMPRESSED AIR HOSE

Polyurethane (TPU) air hose, 8x12 mm.
Air inlet: 1/4".

Max. service pressure: 300 PSI/ 20 bar.

3-YEAR GUARANTEE.

15 METRES

RR7020

23 METRES

RR7023

30 METRES

RR7030

- **VERY LONG-LIFE** - The curvature restrictors reduce creasing and help to extend the air hose's life-time
- **LIGHTWEIGHT** - Multi-reinforced. The urethane (PU) material ensures this air hose to be durable and reliable, the hose resists abrasion.
- **HIGH-QUALITY PRODUCT** - With shiny surface treatment.
- **EFFORTLESS REELING** - the hose is made of a non-memory material and can therefore be reeled in and out without any effort.
- **ECO-FRIENDLY** - The material is ecological, non-toxic and odour-free.
- **APPLICATIONS** - Designed for compressed air applications.
- **TEMPERATURE RANGE** - -40 °C to 65 °C / -40 °F to 150 °F.



NEW



COMPRESSED AIR HOSE

Hybrid polymer compressed air hose, 9.5x15 mm.

Air inlet: 3/8"

Max. service pressure: 300 PSI/ 20 bar.

3-YEAR GUARANTEE.

15 METRES

RR7040

23 METRES

RR7043

30 METRES

RR7045

- **EXTREMELY FLEXIBLE** - Flexibility whatever the weather conditions (-40 °C to 80 °C).
- **HIGHLY DURABLE** - Tested thoroughly for breakage and hose connection.
- **PERFECTLY COATED** - High-quality hose coating for maximum protection.





ATOMISER 24 liters

395 x 330 x 790 mm.
Caution: you must never use flammable or corrosive liquids.

RQN5010

RECUPERATOR, 50 liters

470 x 400 x 1030 mm.
Caution: you must never use flammable or corrosive liquids.

RQN5025

RECUPERATOR, 65 liters

Height 1150-1730 mm.
Weight 27.5 kg.

RQN1053

SUCTION UNIT - RECUPERATOR, 65 liters

Height 1150-1730 mm.
Weight 27.5 kg.

RQN1063



PNEUMATIC OIL PUMP 24 liters

Height: 780 mm.
Hose length: 1.56 metre

RQN8010



OIL SUCTION UNIT 24 liters

Weight: 16 kg.

RQN1021



MANUAL DISTRIBUTOR, 16 liters

300 x 330 x 530 mm

FOR OIL
RQN7620

FOR GREASE
RQN7610



OIL RECOVERY PANS

5 liters

Plastic model for recovering oil and anti-freeze

RQN8070



8 liters

Plastic model for recovering oil and anti-freeze

RQN8080



17 liters

Plastic model with metallic mesh

RQN8060



30 liters

Plastic model for recovering oil and anti-freeze with 4 wheels.

RQN8090



7.6 liters

Plastic model with metallic mesh


RQN8050



200 liters

Plastic tank
1330 x 680 x 410 mm.

RQN7780



WRINGER ROLLER

For installation on a wall with a bracket, excluding the pan.

430 x 400 x 140
Weight: 9 kg.

RQN1000



4-BAR BRAKE BLEEDER WITH 220 V ELECTRIC PUMP

Not suitable for synthetic fluids. DOT3, DOT4, DOT5. Optionally available including adapter set, with article number RQNA4100.

H x W x D: 830 x 330 x 400 mm.
 Tank: 10 litres
 Mains connection: 230V / 50-60Hz / 120W.
 Working temperature 0°C to +45°C.
 Length of the mains cable: 5M. Length of the filler hose: 3.5M.
 Pulsating flow.
 Tested and certified for operation in complete safety.
 The choice of absolute peace of mind.

RQN3154



PNEUMATIC BRAKE BLEEDER

With 5 adaptors, universal adaptor RQNA4025N and 2 cans. Max. pressure: 6 BAR. DOT3, DOT4, DOT5.1, tank capacity 5 litres. Not suitable for synthetic fluids.

RQN4080



UNIVERSAL PLUG
RQNA4025N



NEW

ELECTRIC BRAKE BLEEDER 10 LTR

Not suitable for synthetic fluids. DOT3, DOT4, DOT5. Optionally available including adapter set, with article number RQNA4100.

RQN4110



BRAKE BLEED KIT FOR MOTORBIKES

Capacity: 1 litre
 Hose length: 1 metre

RC014



BRAKE BLEED KIT

Capacity: 1 litre
 Hose length: 1 metre

RC011N



FLUID EVACUATION TANK

Can be used for transmission, brake, cooling fluids, engine and gearbox oil.



MANUAL
RC030



PNEUMATIC OR MANUAL
RC035

BOX OF 10 CONNECTION PLUGS

Designed for use with RQN4048, RQN4075, RQN4076, QN4010, RQN4020, including the European adaptors, miscellaneous vehicles, BMW, Audi, Nissan, Toyota, Mazda and Honda.

This new kit contains adaptors specific to manufacturers. Supplied in a pre-formed case, a syringe is provided for bleeding and filling.

RQNA4100



NEW

**COOLING CIRCUIT
DRAINER**

XDC-50



3 GOOD REASONS TO ORDER

- 1 COMPATIBLE ON ALL TYPES OF VEHICLE EVEN HYBRID AND ELECTRIC**
- 2 INCREASED PRODUCTIVITY: 5 TASKS WITH JUST ONE MACHINE**
- 3 PROTECTION OF THE ENVIRONMENT AND THE OPERATOR**



SAM IN FRANCE FRENCH MADE

COMFORT:
Fluid transfer in few minutes

ENVIRONMENT:
No soil pollution in the workshop

PREVENTION OF MSDS:
Improvement of work posture

INNOVATION:
"BOOST" function for express oil changes

LIFETIME:
10 years: French design and manufacture

TIME SAVING:
max purge time 20 minutes

AUTONOMY:
Emptying in masked time. Totally autonomous device

DIGITAL REFRACTOMETER

Automotive Digital Refractometer is designed to accurately measures the strength of battery fluid, screenwash, antifreeze and AdBlue® by measuring the refractive index of light passing through the mixture and digitally displayed in color LCD TFT.

It is suitable for synthetic antifreeze mixtures including long life OAT (Organic Acid Technology), G13 and aqueous/urea content of AdBlue®. It is a great accuracy tool in modern vehicle repairs.



913-22C

HIGH-POWER PNEUMATIC ACTUATOR SPRING COMPRESSOR (2.5T) + ACCESSORIES

Universal pneumatic compressor for suspensions.
 Foot operated with pneumatic control pedal.
 Double tubular door for protecting the operator. Equipped with an air supply cut-out on opening the grate.
 Two-position cup support to increase the working travel range.
 Increased safety on opening the grate thanks to a new spring system.
 Safety valve to stop the machine on grate opening. Protection bushing.
 This spring compressor is supplied with 2 cups Ø 78-130 mm / 105 - 182 mm. 300 PSI/ 20 bar.

Riser integrated in the chassis to avoid working with your back bent.
 All the other accessories are optional and can be mounted on this version, such as the strut vice, additional cups. Ideal for replacing all types of shock absorbers available on the market.

ACCESSORIES INCLUDED



3240-01



3240-02



3240-03



3240-29



3240-30



3241N

HEADLIGHT ADJUSTOR

Equipment conform to the regulatory directives relative to headlight adjustment, including by the German TÜV. Used to adjust the brightness.
 Also suitable for trucks, and for all light sources: HALOGEN, XENON, BI-XENON, LED and BI-LED

OPTIONS



V-SHAPED LIGHT RAILS
 (the floor must be perfectly flat)



REINFORCED RAILS
 adjustable to enable perfect flatness of the test area

RQHL06



HEADLAMP ADJUSTMENT DEVICE LASER + CAMERA

Suitable for checking and adjusting any type of headlight including xenon, LED or matrix headlights.
 Suitable for light and commercial vehicles as well as heavyweights.
 Connection to PC computers via USB, Bluetooth and Wi-Fi.
 Connect to any printer via USB, Bluetooth or Wi-Fi.
 Laser alignment sight + laser pointer centrally for easy positioning of the device at the front of the vehicle.
 Headlight adjustment device 360° rotatable on the mast. Height adjustment system with lock.
 Power supply: Li-Ion batteries with input for external battery charger 230V AC. Comfortable to use
 Thanks to the three wheels.
 Sturdy anti-tilt base.
 Supplied with assembly instructions, for use and calibration.
 High-quality 1.3 megapixel CMOS camera.
 All software is easy to use (with guided menus).
 Measure resolution: 0.1%

RGLF-3



WORKSHOP WHEELED STRETCHER

Dimensions: 930 x 440 x 100 mm.
Capacity: 90 kg.



TL3040

WORKSHOP WHEELED STRETCHER

7 swivel wheels and one 3-position tilting cushion.
Dimensions: 1.190 x 455 x 150 mm.
Capacity: 90 kg.



TL3000N

FITTER'S CHAIR

Min. height 450 mm
Max. height 560 mm
Ø 360 mm seat
Max. capacity 115 kg
Storage area magnetic for screws, etc.



TL3050

FITTER'S CHAIR

Min. height 435 mm
Max. height 555 mm
Ø 380 mm seat
Max. capacity 90 kg



TL3010N

RUBBER WEDGES

Dimensions: 129 x 78 x 60 mm.
Weight: 0.5 kg. 2 parts.



TLGS100B

STEEL RISER RAMPS


Dimensions: 200 x 200 x 800 mm.
Capacity 2000 kg, 2 parts.



TL80050N

RISER RAMPS MADE OF PLASTIC

Dimensions: 900 x 330 x 220 mm.
2 parts, Weight per part 4 kg.
Capacity: 2500 kg.



TL80051

ENGINE SUPPORT BEAM

Max. capacity 500 kg
Weight: 16 kg



TL22500A

ENGINE LIFTING BEAM

Max. capacity 500 kg



TL68010

COMPLETE CALIBRATED INFLATOR 15 LITERS

Bar 0-8.
Weight: 8.9 kg.

THE IDEAL SOLUTION FOR PETROL STATIONS AND GARAGES PNEUMATIC PUMP AND AIR TANK. THE FILLING FITTING MAKES THIS INFLATOR EXTREMELY FLEXIBLE AND MEANS IT CAN BE USED ANYWHERE!



RQN2017

OPTIONS:

RQNA2000 FILLING SYSTEM



RQNA2020 WALL MOUNT



RQNA2030 FLOOR MOUNT



CALIBRATED INFLATOR WITH DUAL READING SCALE

0-10 bar / 0-140 PSI


RC116D



CALIBRATED INFLATOR

Hose length:
1 metre - 0-10 bar.

RC1164



CALIBRATED INFLATOR

IDEAL FOR TPMS - PRECISE TO 2 DECIMAL POINTS

0-10 bar
Choice between BAR, PSI, KG and KPA
1-Metre hose

RC1155




PREMIUM LINE

CALIBRATED INFLATOR

Hose length:
1.5 metre - 0.7-11 bar.

RC1100



THE PERFECT PAIR FOR CLEANING

MULTI-PURPOSE VENTURI GUN

Also suitable for damp surfaces.

RC109N



+ PNEUMATIC CLEANING GUN

The gun creates an air vortex mixed with cleaning product that forms micro-droplets, sweeping everything away as it passes. Ideal for cleaning inside vehicles, dashboards, air ducts, around seats, glove boxes, gear levers, petrol tanks, registration plates, pedals, seats, carpets and mats. To be used with conventional or special (anti-odour) cleaning products.

RC740



GUARANTEED
2
YEARS

SHORT BLOWGUN LONG NOZZLE INCLUDED

Aluminium
Nozzle length 160 mm.

RC113C



EXTRA-LONG BLOWGUN

Length 1000 mm.

EXTRA-LONG

RC096




BLOWGUN

High-quality ergonomic
1/4" air intake, industrial use.

Composite body.
Precise air flow handle = Optimum utilisation comfort.
Reduction to 90% of the cold in the handle.
Nozzle tilted at 30° for greater precision.

RC099



HGV BLOWGUN

Hose length: 4 metres.
Ideal for trucks and HGVs.

RC123



BLOWGUN

Fitted with a rubber tip.
Available for EURO or ORION connection.



RC006EU (EURO)
RC006OR (ORION)

LONG BLOWGUN

Aluminium blowgun.
Length 300 mm.



SHORT BLOWGUN

Aluminium blowgun.
Length 130 mm.

RC113+114



SANDING GUN

Capacity 1 litre - Weight 1 kg
Contains: RC188N + 4 nozzles
+ RA188 (700 g sanding abrasive)

RC188NSET

NEW

BLOWGUN IN A CASE

RODAC has brought together two sets of blowguns for you. The RC057SET is a 7 in 1, in a clever storage case. Ideal for workshops, garages, industrial environments or simply in the home. Can be used to remove dust and dirt or to dry wet or damp surfaces, for example in places that are difficult to access inside cars, engine compartments, etc.

A practical and efficient tool for lightening your workload and creating clean working surroundings. With interchangeable attachments adjustable in 6 positions which also allows you to blow in places that are difficult to reach.


Air intake, 1/4" BSP
Max. operating pressure: 15.4 bar
Air consumption: 215 l/min

RC057SET



WITH 7 ACCESSORIES!

1. 6 mm steel nozzle, 320 mm.
2. 100 mm plastic nozzle, ideal for mirror surfaces and non-conducting electric cars.
3. Turbo nozzle, air flow multiplied by 3 for a wide range of cleaning operations.
4. 42 mm (1-1/4") fan nozzle, ideal for blowing dust and water.
5. Top-of-the-range, low-noise safety ventilation nozzle.
6. 16 mm rubber tip for watertightness zones (to be fitted on to the steel nozzle).
7. Top-of-the-range, low-noise safety vented tip (to be fitted on to the steel nozzle).



NEW



BLOWGUN

RODAC has brought together two sets of blowguns for you. The 5 in 1 RC055SET in a practical blister pack. Ideal for workshops, garages, industrial environments or simply in the home. Can be used to remove dust and dirt or to dry wet or damp surfaces, for example in places that are difficult to access inside cars, engine compartments, etc.

A practical and efficient tool for lightening your workload and creating clean working surroundings. With interchangeable attachments adjustable in 6 positions which also allows you to blow in places that are difficult to reach.


Air intake, 1/4" BSP Maximum service pressure: 15.4 bar.
Air consumption: 215 l/min

RC055SET

WITH 5 BLISTER-PACKED ACCESSORIES



1. 6 mm steel nozzle, length 100 mm.
2. 6 mm steel nozzle, length 160 mm.
3. 6 mm steel nozzle, length 320 mm.
4. 100 mm plastic nozzle, ideal for mirror surfaces and non-conducting electric cars.
5. Turbo nozzle, air flow multiplied by 3 for a wide range of cleaning operations.



RECHARGEABLE INSPECTION LAMP WITH CHARGING STATION

- Very high quality
- Adjustable.
- 100% sand- and waterproof.
- 120° lighting.
- Side lamp **50-500 lumen**.
- Headlamp **300 lumen**.
- Suspension hook and magnet.



RALA999

EXTENSIBLE AND MAGNETIC MINI TORCH

- Aluminium.
- Magnetic head, force 800 gr.
- 1XAA battery not supplied.
- Waterproof.



RAM677700

INSPECTION MIRROR EXTENSIBLE WITH LED

Mirror dimensions: 50x80 mm.
2 cr1632 batteries included, extensible by 89 cm with 2 LEDs.



RAM666600

DUAL-FUNCTION RECHARGEABLE INSPECTION LAMP

Material: aluminium support.
Rechargeable 230V.
Battery life of 1h30 to 5h.
Lamp on swivel support.
120° diffusion, natural light.
Li-ion type 3.7 V 2600 mAh.
Charging time: 4 hours.



RALA133



EXTENSIBLE LAMP FOR BONNET AND WARNING

- Material: ABS.
- 40 SMD-LEDs.
- 2 lighting modes: strong and weak.
- Rechargeable: 12v and 230v.
- Battery life: 1h30-4h.
- Flashing light function.
- **1400 lumen**.




RALA135

VARIABLE BRIGHTNESS RECHARGEABLE LED INSPECTION LAMP

- 12 LEDs 0-400 lumen,
- 1 LED 70 lumen,
- Magnetic hook on the back



RALA850



LED LAMP, RECHARGEABLE WITH 15 LEDs

2 lighting intensities: 100% - 50%.
Ideal for confined spaces.
Built-in hook on the top of the inspection lamp.
Magnetic base. 230V via USB.
Li-ion battery.
Charging indicator LEDs
Dimensions: 22 x 25 x 340 mm



RALA750

NEW



RECHARGEABLE LAMP KIT

- 3 interchangeable lamp attachments.
- Suspension hook and magnet on the bottom.
- Rotation: 360° + 90°.
- IP44 battery: 18650 Li-ion type 3.7 V 2600 mAh.
- Charging time: 4 hours.

RALABOX

MOUNT THE ACCESSORY YOU NEED!

- **SLIM DESIGN:** three types of lighting. Press the On/Off switch once to change lighting mode. The following settings are proposed: 100%, energy saving, off.
- **TORCH:** three types of lighting. Press the On/Off switch once to change lighting mode. The following settings are proposed: 100%, energy saving, off.
- **INSPECTION LAMP:** two types of lighting. Press the On/Off switch once to change to the other lighting mode. The following setting is proposed: 100%, off.

TORCH



SLIM DESIGN



INSPECTION LAMP



RECHARGEABLE INSPECTION LAMP + HEADLAMP

- Polycarbonate.
- 400 lumen.
- ABS and resistant rubber.
- 12 SMD-LEDs.
- Rechargeable: USB 12-24v and 230v.
- 360° hook.
- Waterproof.
- Shockproof.



INCLUDED:

HEADLAMP
80 LUMEN



MAGNETIC MOUNT



RALA103



LED HEAD LAMP WITH MOVEMENT SENSOR

FRONT-7



- 165 lumen: Battery life: 4hr15
- 75 lumen: Battery life: 8hr30
- 35 lumen: Battery life: 18hr
- Movement sensor technology enabling the lamp to be switched on and off by passing a hand in front of the lamp.
- Battery: lithium-ion: Rechargeable on mains and USB.



FOLDING INSPECTION LAMP

- 180° rotary - Ultra slim design
- Suspension hook and magnet on the base
- LED: 3W COB.
- Lighting power: 300/100 lumen.
- Battery: Li-ion, type 18650, 3.7 V, 2200 mAh.
- Lighting times:
3 hours for 300 lumen,
6 hours for 100 lumen.
- Charging time: 4 hours.
- IP20.

RALA860



3 POSITIONS
POSSIBLE!
50%, 100%, OFF.



NEW

MULTIFUNCTION LITHIUM BOOSTER 1200A -12V-24V

- Lithium-Ion (LFP) • Back-up starter for 12 V and 24 V vehicles • Can be used to operate or recharge USB-compatible equipment • To power 12 V automotive or 12 V electronic products such as inflators, electric iceboxes, OBD II memory backup devices, etc.
- The kit includes a USB cable with several terminals and a mains charger. • Flashing LED light.

TECHNICAL CHARACTERISTICS:

- Dimensions: 292 x 233 x 79 mm / Weight: 2680 g.
- Starter current: 12 V, 600 A; 24 V, 300 A.
- Peak current: 12 V, 1200 A; 24 V, 600 A.
- Lithium iron phosphate battery: 35 000 mAh.
- Output power 12 VDC: 10 A.
- USB output: 5 VDC, 1 x 2 A and 1 x 1 A.
- Flashing LED light: 3 W/250 lumen.
- Complete battery charge time: About 7 hours.
- Lifetime >2000 cycles.

SUPPLIED WITH CHARGING ADAPTOR FOR TABLET, PHONE...



SUITABLE FOR ALL TYPES OF VEHICLE!



VMDS122401



5 GOOD REASONS TO CHOOSE this booster

- 1 WEIGHT: 3 TIMES LIGHTER THAN A LEAD BOOSTER**
- 2 DELIVERS MORE POWER WHEN STARTING**
- 3 MORE CHARGE/DISCHARGE CYCLES**
- 4 DISCHARGE TO 5V AND RETURN TO 100%**
- 5 STORAGE TIME: 120 DAYS WITHOUT MAINTENANCE**

12V STARTER BOOSTER

Voltage: 12V, 1150 A - 3500 A (starting-peak).
Clamp: 25mm²-copper.
Weight: 11.5 kg.



RABST12A

12V/24V STARTER BOOSTER

1150/2300 A-3500/7000 A (starting-peak).
Clamp 50mm² - copper.
Weight: 21 kg.



RABST1224A

MULTI-FUNCTION 12V MINI BOOSTER

- 12V petrol car - output: 5V/1A / mobile phone and 12V 7.5 litre diesel. 5V/2a tablet or digital device.
- 18000 mah battery 12V 10a electrical device.
- LED lamp with SOS 19V /3.5A laptop 12v booster function.
- Input: 12v 10a electrical device.
- Weight 610 grammes - l x w x h: 224x87x29 mm.

SUPPLIED WITH CHARGING ADAPTOR FOR TABLET, PHONE...



RABST12700

NEW

Kap'SAM
NEW BATTERY TESTER



UNAFFECTED BY EXTREME TEMPERATURES
-20°C TO +40°C



STARTS AN INFINITE NUMBER OF VEHICLES:
1,000,000 cycles.
5-Year guarantee.

INNOVATION:
Battery and charging circuit tester included.
Suitable for all types of battery including Start&Stop up to 12 V.



RELIABILITY:
Temperature sensor fitted in the clips for enhanced overall accuracy of the results.
Made in SAM.

AUTONOMY:
No mains supply connection / Automatic recharging in 30 seconds.



STARTS ALL VEHICLES EQUIPPED WITH A 12 V BATTERY

TECHNICAL APPROVALS

STELLANTIS

RENAULT



Kap'SAM
500 Farad - 12 V
XCAP-500



> 2000 amperes on start-up, 9000 amperes at peak level.

> Secure electronic control: anti-reversal of polarity, anti-peak, override function.

> Unaffected by extreme temperatures.

> Easy to handle and accessible with 35 mm² all-copper cables 140 cm in length. Fully insulated clips with curved tips.

> Lightweight: 8.5 kg, 50% lighter than a traditional booster.

> Dimensions: Length 41 cm / Width 23 cm / Depth 20 cm.

NEW

DIGITAL UNIVERSAL PRESSURE TESTER

Automobile diagnosis requires increasingly precise measurements, perfect connections and very often the possibility of saving or printing data.

In the past pressure measurements were taken using a variety of analogue pressure gauges, each one being designed for a different application. The best known were the petrol and diesel compression gauges, oil pressure testers, petrol pressure and vacuum testers.

Today, it is important to measure other pressures as well, such as petrol and diesel high injection pressures, the pressures in the cooling circuits or of the AdBlue.

This universal tester makes it possible to replace all the old analogue testers with a single digital tester, guaranteeing very high measurement accuracy and adaptors identical to those originally mounted, by means of a tablet.

SUITABLE FOR:

- Petrol and diesel compression measurements
- Oil pressure
- Turbo pressure
- Air conditioning pressure
- AdBlue pressure
- Common rail pressure
- Fuel low pressure
- Heavy-duty touch tablet, 7" colour TFT
- Battery: LiPo 3.7V / 2000mA
- USB port for charging the tablet with LED charge indicator
- Connection to the PC via a USB port
- Protection bumper
- All the screws are mounted on a brass insert
- Brass insert with 1/4" thread on the back to fasten suction pads.

ACCESSORIES:

- 300 bar sensor
- Sensor -1 > 3 bar
- Universal adaptor for diesel compression measurement
- Universal adaptor for petrol compression measurement
- Other adaptors for the various functions

C-375-DC



**HIGH PRESSURE DIESEL
KIT FOR DIGITAL PRESSURE
TESTER FOR C-375-DC**

C-375-DC2



**12 COMMON RAIL BLANKING
CAPS FOR C-375-DCZ**

C-375-DC3



**COMMON RAIL REGULATOR
KIT FOR DIGITAL PRESSURE
TESTER**

C-375-DC4



**CYLINDER SEALING TESTER
FOR C-375DCZ**

C-375-DC5



ADAPTER MITYVAC 2.0

C-375-DC12



**COOLING SYSTEM ADAPTER
FOR C-375-DC**

C-375-DC13



**SCHRADER ADAPTER 7/16''
X20 UNF FOR C-375-DC**

C-375-DC14



**SCHRADER ADAPTER M8X100
FOR C-375-DC**

C-375-DC16



**90° COMMON RAIL
ADAPTERS (6 PCS)
FOR C-375-DC**

C-375-DC28



**GASOLINE HIGH PRESSURE ADAPTER
(5 PIECES) FOR C-375-DC**

C-375-DC29




**ENGINE & TURBO OIL PRESSURE
ADAPTERS SET (15 PCS)**

C-375-DC33



**UNIVERSAL T ADAPTERS
(2 PCS)**

C-375-DC41





ROBUST : All the tools that need it have a multilayer coating. White shell: insulating, unbreakable, non-removable, ensuring total and definitive insulation of the tool. Orange shell: non-removable and non-flammable, ensuring comfort and safe handling.



HANDY : Oversize end-stop to avoid any risk of slipping.



SAFETY AND PRECISION: SAM pliers very widely meet the requirements of the manufacturing standards. That's the guarantee of a high-quality product.

ROBUST: Thanks to the case-hardening process used on the teeth SAM pliers are highly wear resistant with a longer lifetime.



12 SOCK. + ACCES 1/2" INSULATED

ZS-J12PCE



Composition :

- X9 1000 v insulated 1/2" sockets
8 - 9 - 10 - 11 - 12 - 13 - 14 - 17 - 19
- X1 1000 v insulated 1/2" ratchet
- X2 1000 v insulated 1/2" extensions 125mm et 250mm

17 SOCK. + ACCES 3/8" INSULATED

ZJH-J17PCE



Composition:

- X9 1000 v insulated 3/8" short sockets : 8 - 10 - 11 - 12 - 13 - 14 - 16 - 17 - 19 mm
- X1 1000 v insulated 3/8" ratchet
- X2 1000 v insulated 3/8" extension 125 and 250mm
- X5 1000 v insulated 3/8" hexagonal screwdriver-socket

3/8" 1000 V INSULATED TORQUE WRENCH

Z-854-J



1,000V-insulated torque wrench with fixed ratchet.
Used for controlled tightening operations in live areas, electrical cabinets or machines in operation. Quick setting of the torque value using the knob on the end of the wrench. The wrench is supplied in a box with its certificate of conformity. Precision: +/- 4%.

RECHARGEABLE LITHIUM SOLDERING IRON + ACCESSORIES

- 3 quarter-turn irons: Universal iron, fine-tipped iron and iron for heat-shrink sheath.
- Micro-USB charging cable.
- Soldering iron rest.
- Ø 1.0 mm soldering wire.
- Clean sponge.
- Heat protection cap and contact-cutout.



R-SOL030



WALL PANEL FOR WORK ON HYBRID AND ELECTRIC VEHICLES

PAN-HYB

Panel dimensions: 100 x 60 mm.
Round holes.
Use with hooks 920C1 to 920C9.
Set of hooks included with the tool set.
Wall mounting rail supplied with the panel.

3 GOOD REASONS TO ORDER THIS PANEL

- 1 TOOLS ARE CLEARLY VISIBLE AND EASY TO REACH**
- 2 1000V INSULATED TOOLS COMPLIANT WITH STANDARD IEC 60900**
- 3 UNIVERSAL - CAN BE USED FOR ALL TYPES OF HYBRID AND ELECTRIC VEHICLES**



1000-VOLT TOOL KIT

	ZJH-10	3/8" insulated short hexagonal socket 10 mm
	ZJH-11	3/8" insulated short hexagonal socket 11 mm
	ZJH-12	3/8" insulated short hexagonal socket 12 mm
	ZJH-13	3/8" insulated short hexagonal socket 13 mm
	ZJ-159	3/8" multilayer 1000-volt insulated ratchet
	ZJ-210	3/8" multilayer 1000-volt insulated 130 mm extension bar
	Z-10-10	1000-V insulated single open-ended spanner 10 mm
	Z-239-20	1000-V insulated offset half round nose pliers

LOCKOUT KIT

	CAD-60	"Red" lockout padlock shell with two stickers, shackle dia.: 5 mm H.: 43 mm
	CAD-60C	Plastic tag diam. 80 mm "device locked out, do not operate"
	Z-427	Insulating bag for connector
	913-VAT1	Voltage detector. Visual and audible continuity test. Phase rotation indicator and single-pole phase detection test. Supplied with protected contact tips. Standards: IEC-1010 (+ IEC-6010-1, IEC61243-3, EC610110-031, IEC60529 (IP64) + CAT III 600 V

PERSONAL PROTECTIVE EQUIPMENT KIT

	Z-421-A9	Outer gloves Size 9 Standard EN 388 / EN 420 EC 2111
	Z-421-A3	Insulated protective gloves Size 9 Standard EN60903-2003 / IEC 60903--2002
	2856	Face shield Standard EN 166-1B Scale No: 2-1.2 (EN 170)
	Z-420	Insulating mat. Maximum operating voltage 26500 VAC. IEC 61111: 2009. Standard IEC 31111 (class 3 moulded rubber 0.5x1 m thickness 3 mm).
	Z-428	Rescue or body stick Standard IEC 61230

WORK AREA MARKING KIT

	2861	Chain 25 metres
	2860	Electrical zone barrier post Supplied with 6 posts
	2364	C1 type safety signs supplied with 4 signs

NEW

CREATE YOUR OWNPACK!

AN EMPTY TOOL TROLLEY + A CHOICE OF MODULES

TOOL TROLLEY ONLY

INTRODUCING THE TOOL TROLLEY

Empty trolley 41 series

SERVI-HYB



STAINLESS STEEL TOP

Extremely hard-wearing

**5 DRAWERS:
3 modules per drawer.**

Drawer measurements:
435 x 510 mm.



BAC-HYB



Warning post holder for tool trolley 41.
6 spaces available.

DIMENSIONS:

Height: 1000 mm.
Width: 834 mm.
Depth: 510 mm.



3 GOOD REASONS

TO ORDER THIS TOOL TROLLEY

- 1 LARGE VOLUME TROLLEY
- 2 OPTIMISES THE WORKSTATION
- 3 TOOLS ARE CLEARLY VISIBLE AND EASY TO REACH

FEATURES



SAFE
Protective bumpers to absorb impacts. Centralised locking with key.



COMFORTABLE
Flush fit handle.



EASY TO HANDLE
2 fixed wheels, 2 swivel wheels, including 1 braked wheel. Dia. 125 mm wheels to facilitate movements.



SAFETY
Single drawer opening system. As soon as a drawer is opened, the anti-tipping system is triggered and the other drawers are locked.

MODULES ONLY

CHECK OUT ALL THE TOOLS

With these tools, you will be able to work in compliance with the requirements of standard NF C18-550, and they are the ideal tools to be stored in our 41-series 5-drawer tool trolley.

MODULE 1

Set of 25 insulated tools for work on live equipment

CP-1000V



-  X1 3/8" multilayer 1000-V insulated ratchet
-  X1 3/8" multilayer 1000V insulated 130 mm extension
-  X4 3/8" insulated short hexagonal socket 10 - 11 - 12 - 13 mm
-  X1 Insulated head open-end spanner 10 mm
-  X3 Insulated head counter-cranked ring spanner 10 - 12 - 13 mm
-  X4 1000-V insulated slotted screwdriver - No 3 - No 3.5 No 4 - No 5.5
-  X2 1000-V insulated Phillips screwdriver No 1 - No 2
-  X1 Insulated slotted screwdriver 5.5x150 mm
-  X1 Insulated Phillips® screwdriver n°2
-  X1 Insulated 45° angled pliers with wire cutter, 165 mm
-  X1 Insulated end wire cutter, 160 mm
-  X1 Insulated diagonal cable cutter, 160 mm
-  X1 Insulated straight half round nose pliers, 200 mm
-  X1 Insulated universal pliers, 160 mm
-  X1 Insulated stripping pliers, 160 mm
-  X1 1000 V insulated multigrip pliers

MODULE 2

Set of 13 tools for lockout/tagout and temporary protection

CP-13PRO



-  X1 Absence of voltage detector (AVT)
-  X1 Insulation tester
-  X1 Plastic tag "device locked out, do not operate"
-  X1 Red lockout padlock
-  X1 Special red padlock key cad-60
-  X1 Insulating bag for connector
-  X1 Insulating blanket
-  X1 Set of 2 insulating clips
-  X3 LV insulating CAP length 60mm int 10mm length 100mm int 15 mm length 120mm int 20mm
-  X1 Insulated handle with flexible rod and magnetic end
-  X1 Insulating lever

MODULE 3

6-piece personal and collective protective equipment (PPE/CPE) toolkit

CP-6EPI

-  X1 Insulating mat
-  X1 Silicone protective sleeve outer gloves size 10
-  X1 Insulating latex glove size 10
-  X1 3-in-1 class 00 insulating glove size 10
-  X1 Face shield for electrical work
-  X1 45kv body stick + hook and wall brackets

MODULE 4

10-piece warning and marking toolkit

CP-10SIGN

-  X1 Protective chain 25 metres
-  X6 Barrier post for electrical area
-  X1 Electrical hazard sign
-  X1 Retractable safety barrier reel 8 metres
-  X1 Flexible "do not cross" safety banner

TOOL TROLLEY + TOOL SET

CHOOSE A TOOL SET

54 tools

CPP-54HYB



MODULE 1

MODULE 2

MODULE 3

MODULE 4

54 tools designed for work on electric and hybrid vehicles.

All the tools and equipment required to work in complete safety at your disposal: tools insulated up to 1000V for work on live equipment, lockout/tagout tools, personal protective equipment and temporary protection, warning and marking tools.

38 tools

CPP-38HYB



MODULE 1


MODULE 2

Specific insulated tools and lockout/tagout tools.

All the tools and equipment required to work in complete safety at your disposal: tools insulated up to 1000V for work on live equipment and lockout/tagout tools.

16 tools

CPP-16HYB



MODULE 3

MODULE 4

Specific personal and temporary protective equipment, marking, warning and rescue equipment.

All the necessary tools and equipment at your disposal to mark out and secure your work area: personal and temporary protective equipment, marking, warning and rescue equipment.

LOCKOUT/TAGOUT AND TEMPORARY EQUIPMENT

MODULE 2

SET OF 13 TOOLS FOR LOCKOUT/ TAGOUT AND TEMPORARY PROTECTION

CP-13PRO



Tool set details:

ABSENCE OF VOLTAGE DETECTOR

913-VAT1

Two-pole low voltage detector
Complete integral AVT self-test.
Voltage testing up to 690VAC
(16 2/3-800Hz)/750VDC.
Single-pole phase test.
Checking of phase order up to 400 Hz.
Removable touch point and lead.
Supplied with leads.
Indication of dangerous voltage
levels via a red light.
Autonomy covering 7,000 measurements
lasting 10 s.
Dimensions: 163 x 64 x 40 mm.
Operating conditions:
-15°C to +45°C. CAT IV - 600V



INSULATION TESTER

913-CI

Checks that equipment and
installations are working properly
and securely.
Provides information on current
leakage from one conductor
to another.
Easy to use and robust (shockproof)
with large 22 mm LCD display screen.
Suitable for low-voltage networks (< 1000V).
2000 points, audible and visual indication
when the test is in progress.
Ohmmeter, voltmeter and continuity test
function.
Voltage measurement 700 VAC/1000 VDC.
Resistance test 200 Mohms /250V, 200
Mohms /500V, 200 Mohms /1000V.
Test time 1/4 to 1/2 minute.
RoHS quality, IEC6010 CAT III - 1000V.



ROUND TAG FOR CAD-60 LOCKOUT PADLOCK

CAD-60C



LOCKOUT PADLOCK

CAD-60

Solid brass body, hardened
steel pins and shackles.
Supplied with key.



INSULATING BAG FOR CONNECTOR

Z-427



SET OF 2 INSULATED CLIPS + INSULATING BLANKET

Z-430-KIT



LOW VOLTAGE INSULATING CAPS

Z-4...

Part No.	Length	Internal Ø
Z-424	60 mm	10 mm
Z-425	100 mm	15 mm
Z-426	120 mm	20 mm




INSULATING LEVER

Z-435



INSULATED HANDLE WITH FLEXIBLE ROD AND MAGNETIC END

Z-340



MODULE 3

PERSONAL PROTECTIVE EQUIPMENT AND COLLECTIVE PROTECTION

CP-6EPI

INSULATING MAT

Z-420



To insulate the operator from conductive elements (floors and walls).
Moulded rubber 3 mm.
Measurements: 100 x 60 mm.

FACE SHIELD FOR ELECTRICAL WORK

2856

Protects the entire face against risks of liquid splashes, electric arcs and risks in the automotive industry, chemical sector and agriculture.
3 adjustable angle positions: raised, mid-height, lowered.
The height is adjusted via the central strap (12 positions).
Antiperspirant headband, can be removed to be cleaned or replaced.
Clear polycarbonate shield. Anti-misting and anti-scratch coating. Can be fitted and removed by simply snapping it into the housing.
Complies with safety standards. ISO 9001 - Version 2000.



RESCUE STICK

Z-428



The rescue stick for switchgear is made of glass fibre reinforced polyester.
It is used to rescue an operator who is the victim of an electric arc by pulling them by the waist.
Stick length: 1.5 m

SILICONE PROTECTIVE SLEEVE OUTER GLOVES

Z-421-A...



Part No.	Size	Weight g
----------	------	----------

Z-421-A9	9	100
Z-421-A10	10	120
Z-421-A11	11	120

INSULATING LATEX GLOVES

Z-421-A...



Part No.	Size	Weight g
----------	------	----------

Z-421-A2	8	100
Z-421-A3	9	100
Z-421-A4	10	120
Z-421-A5	11	120

ARC-FLASH 3-IN-1 INSULATING COMPOSITE GLOVES

Z-426-A10



3-in-1:
Insulating + mechanical protection
+ arc-flash

MODULE 4

WARNING AND MARKING

CP-10SIGN

FLEXIBLE "DO NOT CROSS" SAFETY BANNER

2364



ELECTRICAL HAZARD SIGN

2862



25M LONG BARRIER CHAIN FOR ELECTRICAL AREA

2861



BARRIER POST FOR ELECTRICAL AREA

2860



RETRACTABLE SAFETY BARRIER REEL 8 M

2863



SET OF 123 ELECTRICIAN'S TOOLS WITH TEXTILE TROLLEY BAG

CP-ELEC2



- X7 combination spanners: 8 - 10 - 13 - 16 - 17 - 18 - 19 mm.
- X9 ball-end male wrenches 1.5 to 10 mm.
- X1 5 m tape measure.
- X1 rectangular level 400 mm.
- X9 male Torx® wrenches 1.5 to 10 mm - 8 to 40 mm.
- X1 riveting hammer 32 mm.
- X1 inspection lamp.

- X1 wide-opening adjustable spanner 8".
- X39 sockets and accessories 1/4"
- X1 cutter 25 mm + 10 blades.
- X30 screwdriver bits.
- X1 bit holder.
- X4 1000V insulated flat-blade screwdrivers
3.5 x 100 - 4 x 100 - 5.5 x 125 - 6.5 x 150.

SET OF 123 ELECTRICIAN'S TOOLS WITH TEXTILE SUITCASE

CP-ELEC1



- X1 1000V insulated stripping pliers.
- X1 1000V insulated flat-nosed pliers.
- X1 1000V insulated cutting pliers
- X1 crimping pliers.
- X1 1000V insulated multigrip pliers
- X1 cable stripping tool.
- X1 multimeter.
- X1 43 L textile toolbox or 40L trolley backpack.

SET OF 14 1000V INSULATED TOOLS IN A POUCH


CP-14ELEC



- X2 1000V insulated 3.5X100 and 55X125 electrician's flat-blade screwdriver
- X2 1000V insulated PZ1 and PZ2 Pozidriv screwdriver
- X2 Phillips PH1 and PH2 special terminal-block screwdriver
- X1 stripping tool
- X1 pen combination wrench
- X1 mechanic's 1000V insulated cutting pliers
- X1 1000V insulated straight-nose pliers
- X1 1000V insulated multigrip pliers
- X1 testing screwdriver
- X1 stripping pliers
- X1 tool holder pouch

SET OF 16 1000V INSULATED TOOLS IN A POUCH

CP-16ELEC



- X1 1000V insulated combination pliers polished varnished
- X1 1000V insulated stripping pliers - polished varnished
- X1 1000V insulated electrician's diagonal cutting pliers
- X1 electronics cutting pliers - special for production
- X1 1/2" round-nosed straight electronics pliers
- X1 crimping pliers
- X1 plumber's bag
- X1 electrician's cable-stripping knife
- X5 electrician's 1000V insulated flat-blade samsforce screwdriver
- X3 1000V insulated Phillips® samsforce screwdriver

DIGITAL MULTIMETER

FL-2010N



- Direct current intensity: 400µA - 10A.
- Alternating current intensity: 400µA - 10A.
- Direct current voltage: 400mV - 600V.
- Alternating current voltage: 400mV - 600V.
- Resistance: 400Ωm - 40MΩm.
- Continuity with Buzzer.
- Diode test.
- Frequencies: 5Hz - 50MHz.

NEW

IDEAL FOR THE ELECTRICIAN

TROLLEY CASE WITH 128 TOOLS

CP-128ELEC

3 GOOD REASONS TO ORDER THIS CASE

1 THE ESSENTIAL 1000V INSULATED TOOLS IN ONE TROLLEY CASE

2 ROBUST COMPACT TROLLEY

**3 YOUR WORKSHOP WITHIN EASY REACH:
128 ESSENTIAL TOOLS FOR
LIVE MAINTENANCE WORK.**




MODULE No 1:

- X1 electrician's slotted screwdriver 2.5 x 50
- X2 electrician's 1000V insulated slotted screwdrivers 3.5 x 75, 4 x 100.
- X2 mechanic's 1000V insulated slotted screwdrivers 5.5 x 150, 6.5 x 150.
- X3 1000V insulated PH screwdriver No 0-1-2
- X5 TORX screwdriver 6 x 50, 7 x 50, 8 x 60, 9 x 60, 10 x 80.
- X1 Mechanic's pincers
- X1 Rack of 9 hexagonal male keys
- X3 precision slotted screwdrivers 1.5, 2, 2.5.
- X1 PH 00 precision screwdriver.



MODULE No 2 :

- X1 cutter.
- X1 1000V insulated diagonal cutting pliers
- X1 1000V insulated combination pliers
- X1 1000V insulated half round-nose pliers
- X1 1000V insulated multigrip pliers
- X1 flexible ruler 300 mm.
- X1 hacksaw.
- X1 double-tip scribe.



MODULE No 3:

- X12 combination spanners: 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 mm.
- X1 adjustable wrench.
- X1 level.
- X1 testing screwdriver.
- X1 penlight.

MODULE No 4:

- X2 1/4" extensions 50 and 150 mm.
- X1 1/4" adjustable handle.
- X1 1/4" universal joint.
- X1 1/4" ratchet with bi-material handle.
- X1 1/4" extension, hafted bi-material.
- X1 1/4" screw bit holder socket.
- X2 1/2" extensions.



MODULE No 4 (cont'd):

- X1 1/2" adjustable handle.
- X1 1/2" universal joint.
- X1 1/2" ratchet with bi-material handle.
- X1 short tape measure 3 m.
- X1 SAMSOPLUS® riveting hammer.
- X1 precision chisel.
- X1 precision cape chisel.
- X2 drift punches.
- X1 1000V insulated multimeter
- X1 1/4" magnetic bit holder.
- X13 1/4" sockets: 3.2 - 4 - 5 - 5.5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 mm.
- X13 1/2" sockets: 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 24 mm.

BRAKE TOOL PANEL PAN-FRE



VISUAL	SAM REF.	NAME
BRAKE TOOL PANEL		
	PAN-FRE	"BRAKE TOOL" wall panel, with screen-printing, hooks, panels, supports and tools
TOOL SET		
	FET-4C	Brake fluid tester
	3511B	Drum caliper gauge, 300 mm
	3510B	Caliper gauge for brake discs
	76-MTVL-2	Caliper gauge for drums
	FT-4	Set of 4 clips for brake hoses
	2880	Metal brush
	2760	File for cleaning pad housing
	3108-2	Punch tool for rear hub dust cover plug
	3100	Tool for brake spring
	3100-2	Hooked handle for brake spring
	FT-2	Tool for clipped brake side spring
	FT-1	Tool for side spring with cup
	3103	Tool for hooked side spring
	208-15	Handbrake cable extension clip
	3119	Brake jaw release clip
	3113	Handbrake cable holding tool
	FHTN-10X11	Connection removal tool, 10x11 mm
	FHTN-12X14	Connection removal tool, 12x14 mm
	23-97	Punch screwdriver with set of 24 impact bits, 5/16 (PH 2/3, PZ 2/3, FLAT 9/11, HEX 4/5/6/7/8/10, TORX T25/ T27/130/140/145/150, XZN M5/M6/M8/ M10/M12)

VISUAL	SAM REF.	NAME
	104-H-8X10	Pipe wrench, 6-flat, 8 x 10 mm
	104-H-11X13	Pipe wrench, 6-flat, 11 x 13 mm
	104-H-12X14	Pipe wrench, 6-flat, 12 x 14 mm
	2610-4	Brake pin drift, dia. 4 mm
	2610-5.5	Brake pin drift, dia. 5.5 mm
	2610-6	Brake pin drift, dia. 6 mm
	3160	Bleed can with connection and hose
	FD1-PN	Brake piston pneumatic pushback actuator
	3110-2	Piston pushback kit, right and left screw with cups
	P3110-25	Universal brake piston adaptor, 2 studs
	P3110-26	Universal brake piston adaptor, 3 studs
	3122-10	5-flat bit on 1/2" socket
	3122-14	5-flat socket, 14 mm, 1/2" square
	3122-19	5-flat socket, 19 mm, 1/2" square
	3161	Syringe
	FD-J8	Brake pad thickness verification gauges
	208-23CP	Brake jaw pliers Used to install and remove all types of return springs
	3525	Comparator beam gauge

AVAILABLE IN LARGE FOAM MODULE



CPP-FREMM

SET OF 242 TOOLS FOR CARBODY WORK

CPP-242CAR

COMPOSED OF 5 FOAM MODULES 3/3 + 6-DRAWER TOOL TROLLEY :


- › SERVI-630NG
- › CP-138PM : Tightening composition
- › CP-37PM : Screwing composition
- › CP-48PM : Combination of pliers and hammers
- › 295-J9M : 9 bodywork tools
- › 295-J10M : 10 bodywork forming bars




295-J9M



295-J10M



CP-138PM




CP-37PM



CP-48PM



DRAINAGE TOOL PANEL 1 PAN-VID1



**40%
MORE
STORAGE**

VISUAL	SAM REF.	NAME
DRAINAGE TOOL PANEL 1		
	PAN-VID1	"DRAINAGE TOOL 1" wall panel, with screen-printing, hooks, panels, supports and tools
TOOL SET		
	3949C1	Strap wrench for oil filter
	3950	3/8" self-tightening oil filter wrench, capacity 65-128 mm
	3950P	Car flat-stud self-tightening oil filter wrench
	3930	Universal pliers for filters
	3952	Square strap wrench
	680-7	Transfer syringe
	3953-90	Set of 20 3/8" drainage end fittings (Hex: 8/9/10/12/14/17, Square: 7/8/11/13/15/16/18/19, Triangular, Female Hex 10, XZN 16, T45)
	628-41	Tool for removing plastic drain plugs, PSA /Ford / Mercedes / BMW
	ST-5-45	Bit 1/2" Torx T45
	ST-5-55	Bit 1/2" Torx T55
	870-5	Counter offset square drainage wrench, 10 / 8 mm
	2215	Square fixed handle, 3/8", long. 250 mm
	221-55	Articulated ratchet wrench, 3/8", long. 250 mm
	J-208	Angular extension, 3/8" 75 mm
	J-215	Angular extension, 3/8" 250 mm
	208-40	"Click" tie fastener tool
	3974	Pliers for petrol and diesel fuel connectors
	208-35	Elastic collar pliers, two gripping angles for self-tightening collars. Opening capacity: 77 mm
	628-EF	Wrench for oil filter: FIAT/OPEL/ALFA MULTIJET square 3/8"

VISUAL	SAM REF.	NAME
	SDP-16	Screwdriver socket 1/2" XZN drilled to 16 mm special drainage for VAG group
	SDP-18	Screwdriver socket 1/2" XZN drilled to 18 mm special drainage for VAG group
	208-6	Pliers for self-tightening collar tool used to install and remove self-tightening elastic collars, dia. 18 to 54 mm
	3955-4742	Oil filter cap for VW, Audi, Seat 1/2"
	628-27	27 mm cap socket for square oil filter 3/8" (PSA, Renault, Ford, BMW, Nissan, Mercedes, Opel)
	628-30	30 mm cap socket for square oil filter 3/8" (Japanese vehicles)
	628-32	32 mm cap socket for square oil filter 3/8" (VW, Opel, Ford, BMW)
	628-36	36 mm cap socket for square oil filter 3/8" (VW)
	628-38	38 mm cap socket for square oil filter 3/8" (BMW, Volvo)
	3955-106-15	Cap for oil filter dia. 106 mm 15-flat square 3/8" (Ducato, Daily, Boxer, Master, VW LT)
	3955-108-18	Cap for oil filter dia. 108 mm 18-flat square 3/8" (Master, Trafic)
	3955-TOYOT	Toyota filter wrench
	3955-108	Fuel filter wrench PSA/Renault square 3/8" dia. 108 mm
	3955-109	Fuel filter wrench PSA/Renault square 3/8" dia. 109 mm
	3957	Special socket 27 mm diesel filter PSA HDI
	628-39	U-offset wrench for removing oil filters, 27mm special PSA (3008)

AVAILABLE IN LARGE FOAM MODULE



CPP-VIDMM

NEW XXL ROLLER CABINET WITH 6 AUTOMOTIVE SERVICE MODULES 151 TOOLS

CPP-PS

Includes 6 complete modules with specific tools for oil change, maintenance, clutch, air conditioning, braking and geometry.



GEOMETRY TOOL PANEL **PAN-GEO**



VISUAL	SAM REF.	NAME
GEOMETRY TOOL PANEL		
	PAN-GEO	"MAINTENANCE TOOL" wall panel, comes complete with screen-printing, hooks, panels, supports and tools
TOOL SET		
	3204-12	Lever 310 mm for ball joint
	3204-18	Lever 460 mm for ball joint
	3204-24	Lever 610 mm for ball joint
	733-VL-1N	Car bearing extractor
	733-VL-0	Van bearing extractor
	3653-2	Bearing extractor 17/18
	3653-3	Bearing extractor 20/22
	3253	Notched socket for lower ball joint
	3251	Special socket for steering bearings
	732-DA1	Axial ball joint removal wrench
	3250-1	Axial ball joint removal wrench, dia. 28-35 mm
	2220	Set of 10 open-end wrenches 3/8", 10 to 19 mm
	2220-21	Open-end 21 mm 1/2" for geometry

VISUAL	SAM REF.	NAME
	S-600	Extender 600 mm F.1/2. M. 3/8"
	S-601	Articulated handle 600 mm M. 1/2"
	3255-85	Wheel camber setting tool for VW, Seat and Skoda
	632-10	Stillson wrench 10", 250 mm
	632-18	Stillson wrench 18", 450 mm
	1205	Pneumatic chipper
	76-NIV	Steering wheel level setting
	19220	Ball retainer
	19240	Dolly block

AVAILABLE IN LARGE FOAM MODULE



CPP-GEOMM

MAINTENANCE TOOL PANEL : **PAN-MAIN**



VISUAL	SAM REF.	NAME
MAINTENANCE TOOL PANEL		
	PAN-MAIN	"GEOMETRY TOOL" wall panel, comes complete with screen-printing, hooks, panels, supports and tools
TOOL SET		
	23-07	Flexible screwdriver socket 7 mm
	23-08	Flexible screwdriver socket 8 mm
	MAGDEM	Magnetiser / demagnetiser
	222-81	Torque wrench 10-50 Nm
	J-208	Extension 3/8", straight, length 75 mm
	J-210	Extension 3/8", straight, length 128 mm
	2216	Tee-extender 3/8"
	3851	Extender for installing sparkplug (small model)
	3852	Extender for installing sparkplug (large model)
	BDC-14-JC	3/8" articulated socket, 14 mm with retention spring
	BDC-16-JC	3/8" articulated socket, 16 mm with retention spring
	BDC-21-JC	3/8" articulated socket, 20.8 mm with retention spring
	BD-14-JC12	3/8" socket - 14 mm for sparkplug 12-flat PSA
	BD-16-JC12	3/8" socket - 14 mm for petrol sparkplug 12-flat
	3813-140	3/8" socket - 14 mm extra fine special RENAULT
	BCP-10	3/8" articulated socket, 10 mm for diesel glowplug
	BCP-12	3/8" articulated socket, 12 mm for diesel glowplug
	BCP-8	3/8" articulated socket, 8 mm for diesel glowplug
	BCP-9	3/8" articulated socket, 9 mm for diesel glowplug

VISUAL	SAM REF.	NAME
	2217-17	3/8" pipe socket, 17 mm for diesel connector. Square drive: 3/8" Hex : 17 mm. Length: 80 mm
	2217-19	3/8" pipe socket, 19 mm for diesel connector. Square drive: 3/8" Hex : 19 mm. Length: 80 mm
	1126-90P	1/4" impact wrench for removing sparkplugs
	NJ-220	3/8" impact extension 250 mm
	19143-30M	1/2" impact socket - 12-flat long slim 30 mm (universal joint nut)
	19143-32M	1/2" impact socket - 12-flat long slim 32 mm (universal joint nut)
	19143-35M	1/2" impact socket - 12-flat long slim 35 mm (universal joint nut)
	19143-36M	1/2" impact socket - 12-flat long slim 36 mm (universal joint nut)
	19143-40	1/2" impact socket - 12-flat 40 mm (universal joint nut)
	19143-41	1/2" impact socket - 12-flat 41 mm (universal joint nut, PSA 307, C4 etc.)
	344-4	Flexible magnet
	2229-10	Articulated T-wrench 10 mm
	2229-11	Articulated T-wrench 11 mm
	2229-12	Articulated T-wrench 12 mm
	913-7	Exhaust pipe cutter

AVAILABLE IN LARGE FOAM MODULE



CPP-MAIMM

SPECIAL MOTORCYCLE PANEL PAN-MOT



VISUAL	SAM REF.	NAME
SPECIAL MOTORCYCLE PANEL		
	PAN-MOT	"SPECIAL MOTORCYCLE" wall panel, comes complete with screen-printing, hooks, panels, supports and tools
TOOL SET		
	CPA-FIL	Box of oil filter caps
	114-35	Adjustable pin wrench
	870-5	Drain nut wrench, Peugeot
	23-97	Impact screwdriver
	EX-138-3	Bearing extractor
	MT-1	Steering cup extraction tube
	MT-2	Bearing installation tool
	MT-3	Flywheel extractor 24 mm
	MT-4	Flywheel extractor 26 mm
	MT-5	Flywheel extractor 28 mm
	MT-6	Flywheel extractor 35 mm
	MT-7	4 in 1 Allen socket
	3930	Oil filter pliers
	NS-36	Socket, 36 (6-flat)
	NC-46	Socket, 46 (6-flat)
	19143-39	Socket, 39 (12-flat)

VISUAL	SAM REF.	NAME
	MT-8	Oil filter wrench MP3 400
	MT-9	Oil filter wrench MP3 125
	BCP-J6	Box of sparkplug wrenches
	MT-10	Spring-puller
	MT-11	SPY joint spacer
	7-TR5A	Box of pin drifts
	MT-12	Chain brush
	385-ISO	Thread chaser
	CTF-31	Threading and tapping kit
	770-R	Set of thickness shims
	7212907	Oil syringe 200 ml
	680-1	Grease pump with extensions
	293-2	Copper-head hammer
	DYTF2-50	Torque wrench
	99-BV6	Oil drainage pan
	675-EN	Set of 6 funnels
	344	Magnetic hose
	720967007	Manual tyre remover
	720967005	Valve-puller
	913-DYN	Valve-core extractor
	675-30	Jug with hose

GENERAL MOTORCYCLE PANEL: PAN-OUT



VISUAL	SAM REF.	NAME
GENERAL MOTORCYCLE PANEL		
	PAN-OUT	"GENERAL MOTORCYCLE" wall panel, comes complete with screen-printing, hooks, panels, supports and tools
TOOL SET		
	T-4E100	Electrician's slotted screwdriver S1, 4x100
	T-55E100	Electrician's slotted screwdriver S1, 5.5x100
	T-65E150	Electrician's slotted screwdriver S1, 6.5x150
	T-8M150	Mechanic's slotted screwdriver S1, 8x150
	T-1P100	Screwdriver S1 PH No1 5x100
	T-2P125	Screwdriver S1 PH No2 6x125
	T-25E50	Slotted Tom Thumb screwdriver S1, 2.5x50
	T-4E25	Slotted Tom Thumb screwdriver S1, 4x25
	T-55E35	Slotted Tom Thumb screwdriver S1, 5.5x35
	T-1P25	Tom Thumb screwdriver S1 PH No 1, 5x25
	T-1P35	Tom Thumb screwdriver S1 PH No 2, 6x35
	72803L655	Large flat screwdriver
	EMB-23CX	Box of 25 Torx bits
	239-R20G	1/2" offset round nose pliers
	209-25B	Multigrip pliers
	204-R18G	Universal pliers, 185 mm

VISUAL	SAM REF.	NAME
	232-R16G	Diagonal wire cutter, 165 mm
	321-C	Rubber mallet
	310-45TM	SAMSOPPLUS® riveting hammer.
	359-3	Riveting pliers
	208-3	Hose pliers - 4 to 10 mm
	208-18	Hose pliers - 11 to 60 mm
	3204-12	Force lever, 310 mm
	3204-18	Force lever, 460 mm
	3204-24	Force lever, 610 mm
	1-B	Punch chisel
	54-12	Adjustable spanner, 12"
	LPM-25-ME	Medium-soft flat file, 250 mm
	791	Hacksaw
	2880	Metal brush
	781-3	Stainless steel ruler
	378-27	Cutter
	73-RJ11R	Ratchet and sockets 1/4"
	R-210	1/4" extension.

VISUAL	SAM REF.	NAME
	50-S8	Short combination spanner, 8 mm
	50-S10	Short combination spanner, 10 mm
	50-S11	Short combination spanner, 11 mm
	50-S12	Short combination spanner, 12 mm
	50-S13	Short combination spanner, 13 mm
	50-S16	Short combination spanner, 16 mm
	50-S17	Short combination spanner, 17 mm
	50-S18	Short combination spanner, 18 mm
	50-S19	Short combination spanner, 19 mm
	50A-32	Combination spanner, 32 mm
	62-R9A	Rack of 9 hexagonal male keys
	75-SH13N	Set of 13 1/2" tools supplied on a magnetic rack
	S-210	1/2" extension.
	62-CT3	Asymmetrical male wrench, 3 mm
	62-CT4	Asymmetrical male wrench, 4 mm
	62-CT5	Asymmetrical male wrench, 5 mm
	62-CT6	Asymmetrical male wrench, 6 mm
	62-CT8	Asymmetrical male wrench, 8 mm



3 GOOD REASONS TO GET ONE



Cost saving of 35% compared with a similar tool set.



New multi-purpose textile bag.



100 tools with SAM quality.

SOLUTION

PORTABLE



Large capacity solution

Seduction suit case 146 tools. ACCESS: Extra-thin combination spanners. Controlled thickness and optimised open-end width. The compact head makes it easier to work in confined spaces. COMFORT: SAMSOPLUS hammer, improves user safety. PERFORMANCE: 120-Tooth 1/2" PUSH ratchet with lever reversal. Compact head and return angle almost halved to facilitate work in restricted spaces and intervene in places where conventional ratchets can't go. COMFORT: Foam rest to improve user comfort.

CP-146

SOLUTION

COMPACT



Textile tool bag with 100 tools

- > Removable internal tool panel providing access to the most frequently used tools.
- > Pouches, mini-pouches, elastic strips and compartments fitted on the inside and outside of the bag, ready to house various tools.
- > Specific fitted locations for measures, saw frame and integrated card holder.
- > Removable protective cover for faster access to the contents.
- > Elastic loops for screwdrivers and various other tools.

COMPACT MODEL

30 L Dimensions 42 x 26 x 28 cm

BAG + TOOL SET

CP-100-BAG2N

BAG ONLY

BAG-2N



FEATURES



WATER RESISTANT
1,200 denier textile, ultra-resistant to wear and tear, withstands liquid splashing.



SAFETY
Reflecting fabric for enhanced visibility during outdoor work.



HANDY
Big zip with rubber strap for use with gloves.



COMFORT
Protective skirts to protect from outdoor surroundings.

SOLUTION

MULTI-PURPOSE



Textile bag

HANDY

- > Multiple interior and exterior storage locations for enhanced modularity.
- > Compartment for 15" laptop computer.
- > Opens fully.

COMFORT

- > Optimum accessibility of the inside contents thanks to its wide opening.
- > Non-slip carrying handle.
- > Adjustable padded shoulder strap.

16 L Dimensions
43 x 32 x 12 cm

BAG + TOOL SET

CP-100N

BAG ONLY

BAG-4N



**TOOL SET
COMPATIBLE
WITH ALL THE BAGS**

**Set of
100 tools**

- X1 1/4" and 1/2" case with 60 tools:
- X1 1/2" ratchet
- X1 1/2" sliding handle.
- X1 1/2" extension.
- X11 1/2" sockets: 10 mm -> 32 mm
- X1 1/4" ratchet
- X1 1/4" extension.
- X10 1/4" sockets: 4 mm -> 13 mm
- X1 1/4" bit holder.
- X1 1/4" fitted handle.
- X1 1/4" universal joint.
- X1 1/4" sliding handle.
- X30 screwdriver bits.
- X9 Short male wrenches, 6-flat on a rack
- X9 Short male Resitorx® wrenches in a rack
- X1 Riveting hammer 32 mm
- X1 Bodyworker's chisel
- X9 Combination spanners: 10 -> 19 mm
- X1 Cutter with self-retracting blade
- X6 Screwdrivers (3 slotted; 3 Phillips)
- X1 Cutting pliers, 160 mm
- X1 Penlight
- X1 Multigrip pliers, 250 mm
- X1 Tape measure





3 GOOD REASONS TO GET ONE



Cost saving of 35% compared with a similar tool set.



New multi-purpose textile bag.



100 tools with SAM quality.

SOLUTION

2-IN-1



Textile backpack

Converts into a wheeled trolley in under 60 seconds.

HANDY

- > Multiple pouches (X7), and interior/exterior storage locations for enhanced modularity (enables storage of tools and can house a 15" laptop computer).
- > Tool-holder bag enabling transport of the tools necessary for maintenance jobs.

40 L

Dimensions
50 x 23 x 35 cm

BAG + TOOL SET

CP-100-BAG5N

BAG ONLY

BAG-5N



SOLUTION

MULTI-FUNCTION



Long, thin textile toolbox

HANDY

- > Multiple interior and exterior storage locations for enhanced modularity.
- > Compartment for hacksaw frame.
- > Ideal for housing long tools.

COMFORT

- > Optimum accessibility of the inside contents thanks to its wide opening.
- > Non-slip carrying handle.
- > Adjustable padded shoulder strap.

30 L

Dimensions
50 x 23 x 25 cm

BAG + TOOL SET

CP-100-BAG6N

BAG ONLY

BAG-6N



FEATURES



WATER RESISTANT
1.200 denier textile, ultra-resistant to wear and tear, withstands liquid splashing.



SAFETY
Reflecting fabric for enhanced visibility during outdoor work.



HANDY
Big zip with rubber strap for use with gloves.



COMFORT
Protective skids to protect from outdoor surroundings.

SOLUTION

MOBILE
XXL



TOOL SET
COMPATIBLE
WITH ALL THE BAGS

Set of
100 tools

- X1 1/4" and 1/2" case with 60 tools:
- X1 1/2" ratchet
- X1 1/2" sliding handle.
- X1 1/2" extension.
- X11 1/2" sockets: 10 mm -> 32 mm
- X1 1/4" ratchet
- X1 1/4" extension.
- X10 1/4" sockets: 4 mm -> 13 mm
- X1 1/4" bit holder.
- X1 1/4" fitted handle.
- X1 1/4" universal joint.
- X1 1/4" sliding handle.
- X30 screwdriver bits.
- X9 Short male wrenches, 6-flat on a rack
- X9 Short male Resitorx® wrenches in a rack
- X1 Riveting hammer 32 mm
- X1 Bodyworker's chisel
- X9 Combination spanners: 10 -> 19 mm
- X1 Cutter with self-retracting blade
- X6 Screwdrivers (3 slotted; 3 Phillips)
- X1 Cutting pliers, 160 mm
- X1 Penlight
- X1 Multigrip pliers, 250 mm
- X1 Tape measure

Textile trolley

HANDY

> Multiple interior and exterior storage locations for enhanced modularity.

COMFORT

> Optimum accessibility of the inside contents thanks to its wide opening.
> Non-slip carrying handle.
> Adjustable padded shoulder strap.

33 L

Dimensions
44 x 55 x 36 cm

BAG + TOOL SET

CP-100-BAG7N

BAG ONLY

BAG-7N



NEW

IT'S ALL THERE!
NEW TOOL TROLLEY
239 TOOLS


3 GOOD REASONS TO ORDER

- 1 30% MORE SPACE**
- 2 239 TOOLS WITH SAM QUALITY**
- 3 4 DRAWERS FULL OF TOOLS AND 2 DRAWERS AVAILABLE**

CPP-239PM



FOAM NO 1: CP-138PM



FOAM NO 2: CP-48PM



FOAM NO 3: CP-27PM



FOAM NO 4: CP-16PM



COMPOSE YOUR PACK

TROLLEY (+) ABS MODULE (OR) FOAM MODULE



COMFORT
Complete solution selected by SAM.



ECONOMIC
Save 27% compared to buying the products at retail.



PRODUCTIVITY
Composition with combination ratchet wrenches. Tools stored and within easy reach.

1/ CHOOSE YOUR ROLLER CABINET

SERVI-630N

THE ECONOMIC SOLUTION



SERVI-640

THE TRADITIONAL SOLUTION



416H

THE COMFORT AND SAFETY SOLUTION



2/ CHOOSE YOUR TYPES OF MODULES

SERVI-630N

SERVI-640

416H

(+) 200 TOOLS IN FOAM MODULES

CPP-200M4



(+) 200 TOOLS IN FOAM MODULES

CPP-200M



(+) 200 TOOLS IN FOAM MODULES

416-200M



(+) 200 TOOLS IN ABS MODULES

CPP-200SV



(+) 200 TOOLS IN ABS MODULES

CPP-200SV4



(+) 200 TOOLS IN ABS MODULES

416-200SV



THE COMFORTABLE, SAFE SOLUTION



3 modules per drawer.
Drawer measurements:
435 x 590 mm.

STAINLESS STEEL TOP
Extremely hard-wearing

SAFE □

Single drawer opening system.
As soon as a drawer is opened, the anti-tipping system is triggered and the other drawers are locked.

COMFORTABLE □

Flush fit handle.

SAFE □

Protective bumpers to absorb impacts.
Centralised locking with key.

HANDY □

2 extra storage grids on the sides to store your bigger tools (torque wrenches, levels, etc.).
1 integrated screwdriver storage system,
2 three-liters side storage compartments
Supplied with 10 label-holders to identify the content of the drawers.



ALSO AVAILABLE IN WHITE, BLUE AND BLACK.

EASY TO HANDLE □
2 fixed wheels, 2 swivel wheels, including 1 braked wheel. Dia. 125 mm wheels to facilitate movements.

5-drawer version

1 x 64 mm.
2 x 104 mm.
1 x 152 mm.
1 x 254 mm.
Weight: 75 kg.



415H

6-drawer version

2 x 64 mm.
3 x 104 mm.
1 x 254 mm.
Weight: 80 kg.



416H

7-drawer version

3 x 64 mm.
3 x 104 mm.
1 x 194 mm.
Weight: 84 kg.



417H



ABS modules
+
Birght finish

3 GOOD REASONS TO ORDER THIS TOOLBOX

- 1 39 SAM quality tools at an attractive price
- 2 The essential ultra-compact tightening / screwing box
- 3 A multi-function pliers

OFFERED



INGENIOUS
integration of an LED lamp (rechargeable). Range 10m



LONGEVITY
Ratchet protection against water and sand intrusion



Pocket box with 39 tools + multi-function pliers

Includes:

- x1 watertight ratchet with two-material handle
- x1 extension with fitted two-material extension
- x2 extensions : 50 and 150 mm
- x1 universal joint
- x1 sliding handle
- x1 screw bit holder socket
- x11 sockets \varnothing 5,5 - 5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 mm
- x21 screwdriver bits:
 - \bullet 4,5 - 6,5 - 8 mm,
 - \oplus n°1 - 2 - 3,
 - \otimes n°1 - 2 - 3,
 - \circ 3 - 4 - 5 - 6 - 7 mm,
 - \otimes 10 - 15 - 20 - 25 - 27 - 30 - 40.

x39

POCKET-RJ



COMPACT
Easy storage in the lower compartment of a tool box, a trolley. Dimensions of the 1/2" enclosure: 360 x 150 x 65 mm



Bi-material handle ratchet.
ABS box: does not scratch the supports



COMPLETE FROM 8 TO 32 MM

Box of socket and accessories 1/2" 23 tools

- x1 Centre reversion 1/2" ratchet
- x2 Straight 1/2" extensions 125 mm et 250 mm.
- x1 1/2" joint
- x19 \varnothing : 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 23 - 24 - 27 - 30 - 32 mm.



Non-slip bi-material box



ACCESSIBILITY
120-tooth ratchet with 3° angle for easy access in tight spaces

75-SH23



x23



ABS modules
+
Birght finish

THE EXPERT SOLUTION 101 TOOLS

RAST91010

1/2"

- X1 1/2" ratchet
- X19 1/2" sockets: 8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-24-27-30-32 mm
- X6 1/2" long sockets: 14-15-16-17-19-22 mm
- X2 1/2" extension 125, 250 mm
- X1 1/2" 5-16" universal joint
- X5 Screwdriver bits T 40-45-50-55-60
- X3 Screwdriver bits FD 8-10-12 mm
- X2 Screwdriver bits PZ 3-4
- X2 Screwdriver bits PH 3-4
- X5 Screwdriver bits H 7-8-10-12-14 mm

1/4"

- X1 1/4" ratchet
- X13 1/4" sockets: 4-4.5-5-5.5-6-7-8-9-10-11-12-13-14 mm
- X8 1/4" long sockets: 6-7-8-9-10-11-12-13 mm
- X2 1/4" extension 50, 150 mm
- X1 1/4" extension with fitted handle 150 mm
- X1 1/4" sliding handle.
- X1 1/4" universal joint.
- X2 Screwdriver bits PZ 1-2
- X4 Screwdriver bits H 3-4-5-6 mm
- X3 Screwdriver bits FD 4-5-5-7 mm
- X2 Screwdriver bits PH 1-2
- X7 Screwdriver bits T 8-10-15-20-25-27-30 mm



THE MULTIPURPOSE PRO SOLUTION 100 TOOLS

RAST91000

1/4" TOOLS'

- X1 1/4" ratchet
- X13 1/4" sockets: 4-4.5-5-5.5-6-7-8-9-10-11-12-13-14 mm
- X2 1/4" extension 50, 150 mm
- X1 1/4" extension with fitted handle 150 mm
- X1 1/4" flexible extension 150 mm
- X1 1/4" sliding handle.
- X1 1/4" universal joint
- X17 Screwdriver bits

1/2" TOOLS

- X1 1/2" ratchet
- X18 1/2" sockets: 8-9-10-11-12-13-14-15-16-17-18-19-20-22-24-27-30-32 mm
- X2 1/2" extension 250 mm
- X1 1/2" 5-16" universal joint
- X13 Combination spanners: 6-7-8-10-11-12-13-14-15-16-17-18-19 mm
- X11 Screwdriver bits
- X1 Crimping pliers
- X1 Cutting pliers.
- X1 Multigrip pliers.
- X9 Rack of 9 male keys



THE TECHNICAL SOLUTION 86 TOOLS

RAST90860

1/4" TOOLS

- X1 1/4" ratchet
- X13 1/4" sockets: 4-4.5-5-5.5-6-7-8-9-10-11-12-13-14 mm
- X2 1/4" extension 50, 150 mm
- X1 1/4" extension with fitted handle 150 mm
- X1 1/4" flexible extension 150 mm
- X1 1/4" sliding handle.
- X1 1/4" universal joint.
- X17 Screwdriver bits

1/2" TOOLS

- X1 1/2" ratchet
- X18 1/2" sockets: 8-9-10-11-12-13-14-15-16-17-18-19-20-22-24-27-30-32 mm
- X2 1/2" extension 125, 250 mm
- X1 1/2" 5-16" universal joint
- X11 Combination spanners: 8-9-10-11-12-13-14-15-16-17-19 mm
- X15 Screwdriver bits



THE ESSENTIAL SOLUTION 78 TOOLS

RAST90780

1/4" TOOLS

- X1 1/4" extension with fitted handle 150 mm
- X1 1/4" sockets:
- X30 Screwdriver bits
- X9 Rack of 9 male keys

1/2" TOOLS

- X1 1/2" ratchet
- X18 1/2" sockets: 8-9-10-11-12-13-14-15-16-17-18-19-20-22-24-27-30-32 mm
- X1 1/2" extension 125 mm
- X1 1/2" universal joint.
- X8 Combination spanners: 8-10-11-12-13-14-17-19 mm
- X3 Screwdriver 3X100 mm - 4X100 mm - 5.5X125 mm
- X1 Screwdriver 1X100 mm - 2X125 mm
- X1 Hacksaw.
- X1 Cutting pliers.
- X1 Cutter.



THE MIXED SOLUTION 62 TOOLS

RAST90620

1/4" TOOLS

- X1 1/4" ratchet
- X13 1/4" sockets: 4-4.5-5-5.5-6-7-8-9-10-11-12-13-14 mm
- X2 1/4" extension 50, 150 mm
- X1 1/4" extension with fitted handle 150 mm
- X1 1/4" sliding handle
- X1 1/4" universal joint
- X9 Rack of 9 male keys

1/2" TOOLS

- X1 1/2" ratchet
- X19 1/2" sockets: 8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-24-27-30-32 mm
- X2 1/2" extension 125, 250 mm
- X1 1/2" universal joint
- X11 combination spanners: 8-9-10-11-12-13-14-15-16-17-19 mm



WRENCHES DYNATECH®

GREATER PRODUCTIVITY
by reduced immobilization thanks to stronger ratchets.

ALL-STEEL WRENCH
capable of withstanding all working environments.

CALIBRATION ERRORS LIMITED
thanks to the easy-to-use vernier scale adjustment.

MARKER FOR PERFECT POSITIONING
of the contact point to ensure precise tightening.



PUSHBUTTON BIT EJECTION
ensuring fast and easy changes.



EASY TO READ
under all conditions, even in direct sunlight thanks to long-lasting black inset marking on the vernier scale.

DYNATECH® WRENCHES WITH INTERCHANGEABLE RECTANGULAR BITS



REF.	Ratchet REF.	Push ratchet	Capacity Nm	Resolution Nm	Ratchet	Attachment	L mm with ratchet	PRICE
DYTC-5-1	DTC-0-R	X	1-5	0.05	1/4"	9x12	220	
DYTC-25-1	DTC-0-R	X	5-25	0.20	1/4"	9x12	270	
DYTC-50-1	DTC-0-R-J	X	10-50	0.50	3/8"	9x12	380	
DYTC-100-1	DTC-0-S	X	20-100	0.50	1/2"	9x12	470	
DYTC-200-1	DTC-S	X	40-200	1	1/2"	14x18	520	
DYTC-350-1	DTC-S-350		70-350	1	1/2"	14x18	660	

DYNATECH® WRENCH WITH FIXED RATCHET



REF.	Capacity Nm	Resolution Nm	Ratchet	L mm	PRICE
DYTF-5-1	1-5	0.05	1/4"	195	
DYTF-25-1	5-25	0.20	1/4"	245	
DYTF-50-1	10-50	0.50	3/8"	360	
DYTF-100-1	20-100	0.50	1/2"	455	
DYTF-200-1	40-200	1	1/2"	495	
DYTF-350-1	70-350	1	1/2"	630	

ECONOMICAL SOLUTION

1/2" TORQUE WRENCH

Ergonomic handle, pre-set mono-torque, with calibration certificate

120 NM



RAM12120

1/2" TORQUE WRENCH

with calibration certificate
Ratchet head, left/right lever

70 - 350 NM



RAM622284

1/2" TORQUE WRENCH, 4-80 NM

- 72-tooth ratchet with PUSH function guaranteeing secure socket fastening.
- Anti-slip two-material handle.
- Sound and visual warning when the torque value is reached.
- 4 measuring units available: Nm, Lb-ft, In-ft, Kg-m.
- Can be switched off manually or automatically after 70 seconds of inactivity.
- Ratchet supplied with a 3-point calibration certificate, in line with standard NF EN ISO 6789-1 (2017).
- Supplied with 2 AAA batteries.



RAMG-80

CASE OF 11 OPEN-END 9X12 TORQUE WRENCH BITS, IN MM

Case containing: X11 wrench fittings 9 x 12 (reference DFCO-...): 8, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19 mm.

DFCO-J11



CASE OF 9 OPEN-END 9X12 TORQUE WRENCH BITS, IN INCHES

Case containing: X9 wrench bits 9 x 12 (reference DFCO-...P): 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4".

DFCO-J9P



CASE OF 11 OFFSET RECTANGULAR EYE-END FITTINGS 9X12 IN MM

Case containing: X11 wrench bits 9 x 12 (reference DECO-...): 8, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19 mm.

DECO-J11



CASE OF 9 OFFSET RECTANGULAR EYE-END BITS 14X18, IN MM

Case containing: X9 wrench bits 14 x 18 (reference DEC-...): 13, 14, 15, 16, 17, 18, 19, 21, 24.

DEC-J10



CASE OF 10 CROWFOOT 3/8" WRENCH BITS, IN MM

Case containing: X10 wrench bits (reference JCF-...): 10, 11, 12, 13, 14, 15, 16, 17, 18, 19 mm.

JCF-J10



CASE OF 11 CROWFOOT 3/8" WRENCH BITS IN INCHES

Case containing: X11 wrench bits (reference JFC-...P): 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1".

JCF-J11P



CASE OF 11 OPEN-END 14X18 TORQUE WRENCH BITS, IN MM

Case containing: X11 wrench bits 14 x 18 (reference DFC-...): 13, 14, 15, 16, 17, 18, 19, 21, 22, 24, 27 mm.

DFC-J11



CASE OF 10 OPEN-END 14X18 TORQUE WRENCH BITS, IN INCHES

Case containing: X10 wrench bits 14 x 18 (reference DFC-...P): 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1", 1 1/4".

DFC-J10P



DYNASAM 4.0® LOW TORQUE VALUES

PERFORM PRECISION TIGHTENING OPERATIONS WITH TORQUE VALUES GOING FROM 0.4 TO 50 NM

MADE
IN FRANCE



DYMSC-4-1



DYMSC-10-1



DYMSC-50-1

DATA TRACEABILITY

VERY COMPACT WRENCHES
Ideal for restricted spaces.

TORQUE VALUE IDENTIFIED

by the colour of the ring:

0.4-4 Nm 1-10 Nm 5-50 Nm

NF EN ISO 6789-1

CHARACTERISTICS:

- > Double alert bargraph with:
 - 1/ Three coloured visual indicators: tightening ongoing, tightening conform, tightening nonconform.
 - 2/ Customisable user tolerance
- > Accuracy over the range: +/- 4%.
- > The tightening values are guaranteed by means of three alert levels: Visual alert, audible alert, sensory alert.

- tightening ongoing
- tightening conform
- tightening nonconform

REF.	Capacity Nm	Attachment	Contents	PRICE
DYMSC-4-1	0.4 - 4	9x12 mm	2 bits 1/4", 3/8" + 2 batteries + 1 charger	
DYMSC-4-2	0.4 - 4	9x12 mm	Same contents + smartphone + dedicated application	
DYMSC-10-1	1 - 10	9x12 mm	2 bits 1/4", 3/8" + 2 batteries + 1 charger	
DYMSC-10-2	1 - 10	9x12 mm	Same contents + smartphone + dedicated application	
DYMSC-50-1	5 - 50	9x12 mm	2 bits 1/4", 3/8" + 2 batteries + 1 charger	
DYMSC-50-2	5 - 50	9x12 mm	Same contents + smartphone + dedicated application	

DYNASAM 4.0® HIGH TORQUE VALUES

AN ELECTRONICALLY CONTROLLED BREAK-OVER TORQUE WRENCH TO GUARANTEE YOUR TORQUE VALUES ARE CONFORM

MADE
IN FRANCE



CONNECTED WRENCH AND DATA TRACEABILITY



DYMSC-100-1

NF EN ISO 6789-1

CHARACTERISTICS :

- > Double alert bargraph with:
 - 1/ Three coloured visual indicators: tightening ongoing, tightening conform, tightening nonconform.
 - 2/ Customisable user tolerance
- > The tightening values are guaranteed by means of two alert levels: Visual alert, mechanical triggering: 15° break.
- > Accuracy over the range: +/- 3%.

10-100 Nm

REF.	Capacity Nm	Attachment	Contents	PRICE
DYMC-100-1	10 - 100	9x12 mm	3 bits 1/4", 3/8" and 1/2" + 2 batteries + 1 charger	
DYMC-100-2	10 - 100	9x12 mm	Same contents + smartphone + dedicated application	



OPTIMISED TIGHTENING

Thanks to the 15° wide motorised break-over.

STEP INTO THE 4.0 WORKSHOP

**FULL RANGE OF SMART STORAGE,
CONNECTED VENDING MACHINES**

SAM'URAI 
UNITÉ DE RANGEMENT AUTOMATISÉE INTELLIGENTE



RODAC

SAM GROUP

RODAC INTERNATIONAL B.V.

NEDERLAND

Nijverheidsstraat 1 - 6135 KJ Sittard Nederland
T: +31 (0)46 458 2299 - info@sam-rodac.com

BELGIË / LUXEMBURG / BELGIQUE / LUXEMBOURG

T: +32 (0)2 331.34.34 - F: +32 (0)2 331.34.43 - belux@sam-rodac.com

DEUTSCHLAND

T: +49 (0)3222 1681310 - F: +49 (0)3222 1681312 - info@sam-rodac.com



RODAC
.COM