

Starrett®

SAWS & HAND TOOLS

S I N C E 1 8 8 0



This catalogue is regularly updated. For the latest version, scan the QR code above or visit starrett.co.uk/catalogues

CATALOGUE 71E



ABOUT

As specialists in power tool accessories manufacturing, Starrett offers an extensive range of high-quality products, including hole saws, reciprocating, jigsaw, hacksaw, and portable bandsaw blades, as well as drill bits. Our commitment to supplying tradespersons with the best tools ensures that each product in our power tool accessories range meets the rigorous demands of their specific industries.

Through continuous research and development, we ensure that our offerings remain at the cutting edge of the industry, constantly evolving to meet the changing needs of professionals. This catalogue provides detailed information on our comprehensive range of power tool accessories and hand tools, showcasing our proven products alongside our latest innovations.

GLOBAL PRESENCE



Distribution Centres



Manufacturing Site



Distribution Partners

HOLESAWS & ACCESSORIES

Holesaws, Arbors, Pilot Drills, Core Ejectors, and our Debris Collector are all part of our complete line of Holesaws and Accessories. All solutions to assist you in safely optimising each job while keeping the cost per cut in mind, saving you time and money.

Holesaw cutting speed recommendations (RPM) Page 24

04

DRILL BITS & CHISELS

Starrett's drill bits and chisels offer unmatched strength and durability, featuring specialized heat treatment and high-performance carbide tips. These drill bits ensure fast, clean cuts and are designed to meet DIN 338 Standards, catering to the rigorous demands of professional users.

26

HACKSAW BLADES & FRAMES

Bi-Metal Safe-Flex®, Redstripe, and high carbon Grey-Flex® blades, as well as hacksaw frames, compass, and PVC saws, are available to meet all of your sawing requirements.

33

JIGSAW BLADES

Starrett Bi-Metal Unique™ Saw Technology, with Unified Shank™ Jigsaw Blades, fits most jigsaw machines. With strong teeth, multiple cutting edges, and a split chip advantage, Starrett Jigsaw Blades typically lasting 25% longer than competitors. Our blades cut wood, metal, plastic, abrasives and many other materials.

38

RECIPROCATING BLADES

When compared to the previous line, Starrett's 3X Power blade technology provides up to three times the life and increased cutting rates. These ergonomic blades are suited to various applications and are engineered to excel in any demanding situation, providing a comprehensive set of sawing solutions.

45

HAND TOOLS

The Starrett, Starrett Exact®, and Starrett Exact® Plus product lines include a wide range of high-quality Tapes, Levels, Knives, Rules, Squares, and other tools. All are dependable, accurate, and of high build quality.

54

LASER DISTANCE METERS

Starrett Laser Distance Meters are highly accurate and advanced, with features such as IP54 protection, indirect measurement calculations, and Bluetooth® to connect to Android and IOS devices, as well as a downloadable app that allows users to control the meter via a smartphone or other compatible device.

66

PORTABLE BANDSAW BLADES

Starrett's INTENSS PRO-DIE & UNIVERZ blades fit a variety of portable bandsaw machines.

68

TOOL STORAGE & TRANSPORTATION

Toolbags in small, medium, and large sizes for all your storage and carrying needs.

69

ABRASIVE DISCS

Suitable for use in angle grinders or bench fixed machines.

70

SERVICES

Starrett offers a range of services and support to customers. Find out more on StarrNET, the new online ordering portal for our partners, as well as the Marketing and Technical Support options we have available.

71

| Hole Saw Depth | 16mm 5/8" |
|---|--------------|
| <5mm | ✓ |
| Rec. Cutting Depth | 3-13mm |
| >13mm | ✗ |
| Metal Inox (Stainless) Non Ferrous Materials | ★ |
| Fibreglass | ★ |
| Size Range | 15 - 100mm |
| Catalogue Number | SM |

| Hole Saw Depth | 25mm 1" |
|---|------------|
| <3mm | ✓ |
| Rec. Cutting Depth | 3-13mm |
| >13mm | ✓ |
| Metal Inox (Stainless) Non Ferrous Materials | ★ |
| Cast Iron | ★ |
| Fibreglass | ★ |
| Size Range | 15 - 100mm |
| Catalogue Number | CTD |

| Hole Saw Depth | 54mm 2.1/8" |
|--------------------|----------------|
| <3mm | ✓ |
| Rec. Cutting Depth | 3-13mm |
| >13mm | ✓ |
| Wood | ★ |
| Veneer | ★ |
| MDF | ★ |
| Plastic | ★ |
| Acrylic | ★ |
| Ceramic | ★ |
| Fibreglass | ★ |
| Formica | ★ |
| Plaster | ★ |
| Size Range | 19 - 159mm |
| Catalogue Number | MPH |

| Hole Saw Depth | 41mm 1.5/8" |
|--------------------|----------------|
| <3mm | ✓ |
| Rec. Cutting Depth | 3-13mm |
| >13mm | ✓ |
| Cast Iron | ★ |
| Wood | ★ |
| Nail Embedded Wood | ★ |
| Veneer | ★ |
| Plastic | ★ |
| Acrylic | ★ |
| Ceramic | ★ |
| Fibreglass | ★ |
| Formica | ★ |
| Plaster | ★ |
| Suspended Floors | ★ |
| Brick and Masonry | ★ |
| Size Range | 16 - 152mm |
| Catalogue Number | CT |

| Hole Saw Depth | 41mm 1.5/8" |
|---------------------------|----------------|
| <3mm | ✓ |
| Rec. Cutting Depth | 3-13mm |
| >13mm | ✓ |
| Ceramic | ★ |
| Porcelain / Glass / Stone | ★ |
| Marble / Granite | ★ |
| Fibreglass | ★ |
| Brick and Masonry | ★ |
| Size Range | 14 - 152mm |
| Catalogue Number | D |

| Hole Saw Depth | 20mm 25/32" |
|------------------|----------------|
| Size Range | 5 - 12mm |
| Catalogue Number | D |



| | | | | |
|---------------------|-----------|---|------|---|
| Cutting Performance | Excellent | ★ | Good | ☆ |
|---------------------|-----------|---|------|---|

| Hole Saw Depth | Diameter Dependent |
|--------------------|-------------------------------------|
| <3mm | <input type="checkbox"/> |
| Rec. Cutting Depth | |
| 3-13mm | <input type="checkbox"/> |
| >13mm | <input checked="" type="checkbox"/> |
| Brick and Masonry | ★ |
| 300mm | 22mm & 28mm |
| 150mm | ≥ 38mm |
| Size Range | 22 - 152mm |
| Catalogue Number | BMC |

Diamond
Dri-Core Drill



| Hole Saw Depth | 51mm 2" |
|-------------------------|-------------------------------------|
| <3mm | <input type="checkbox"/> |
| Rec. Cutting Depth | |
| 3-13mm | <input checked="" type="checkbox"/> |
| >13mm | <input checked="" type="checkbox"/> |
| • Metal | ★ |
| • Inox (Stainless) | ★ |
| • Non Ferrous Materials | ★ |
| Cast Iron | ★ |
| Wood | ★ |
| Veneer | ★ |
| Plastic | ★ |
| Acrylic | ★ |
| Fibreglass | ★ |
| Formica | ★ |
| Plaster | ★ |
| Suspended Floors | ★ |
| Size Range | 19 - 210mm |
| Catalogue Number | DCH |

Bi-Metal Deep Cut



| Hole Saw Depth | 41mm 1.5/8" |
|-------------------------|-------------------------------------|
| <3mm | <input checked="" type="checkbox"/> |
| Rec. Cutting Depth | |
| 3-13mm | <input checked="" type="checkbox"/> |
| >13mm | <input type="checkbox"/> |
| • Metal | ★ |
| • Inox (Stainless) | ★ |
| • Non Ferrous Materials | ★ |
| Cast Iron | ★ |
| Wood | ★ |
| Veneer | ★ |
| Plastic | ★ |
| Acrylic | ★ |
| Fibreglass | ★ |
| Formica | ★ |
| Plaster | ★ |
| Suspended Floors | ★ |
| Size Range | 14 - 210mm |
| Catalogue Number | FCH |

Bi-Metal Fast Cut




















| Hole Saw Depth | 13mm 1/2" |
|-------------------------|-------------------------------------|
| <3mm | <input checked="" type="checkbox"/> |
| Rec. Cutting Depth | |
| 3-13mm | <input type="checkbox"/> |
| >13mm | <input type="checkbox"/> |
| • Metal | ★ |
| • Inox (Stainless) | ★ |
| • Non Ferrous Materials | ★ |
| Wood | ★ |
| Veneer | ★ |
| Plastic | ★ |
| Acrylic | ★ |
| Fibreglass | ★ |
| Formica | ★ |
| Size Range | 16 - 51mm |
| Catalogue Number | CSC |

Bi-Metal
Cordless
Smooth Cut



HOLE SAWS

| HOLE SAW APPLICATION GUIDE | | | | | | | | | |
|------------------------------------|---|----------------|------------|-------------------------|----------------|-----------------|------------------|-------------------------------|--------------------------------|
| Material Thickness and Application | BI-METAL | | | TUNGSTEN CARBIDE TIPPED | | | | DIAMOND GRIT | |
| | Cordless Smooth Cut | Fast Cut | Deep Cut | Carbide Tipped | Multi Purpose | Stainless Steel | Carbide Deep Cut | Diamond Hole Saw / Tile Drill | Brick & Masonry Dri Core Drill |
| Catalogue Number | CSC | FCH | DCH | CT | MPH | SM | CTD | D | BMC |
| Hole Saw Depth | 13mm 1/2" | 41mm 1.5/8" | 51mm 2" | 41mm 1.5/8" | 54mm 2.1/8" | 16mm 5/8" | 25mm 1" | Diameter dependent | Diameter dependent |
| Recommended Cutting Depths | <3mm | ☑ | ☑ | | ☑ | ☑ | ☑ | ☑ | |
| | 3-13mm | | ☑ | ☑ | ☑ | | ☑ | ☑ | |
| | >13mm | | | ☑ | ☑ | | ☑ | ☑ | ☑ |
| • Metal |  | ★ | ★ | ★ | | ★ | ★ | | |
| • Inox (Stainless) |  | ★ | ★ | ★ | | ★ | ★ | | |
| • Non Ferrous Materials |  | | ★ | ★ | ★ | | ★ | | |
| Cast iron |  | | ★ | ★ | ★ | | ★ | | |
| Wood |  | ★ | ★ | ★ | ★ | | | | |
| Nail Embedded Wood |  | | | ★ | | | | | |
| Veneer |  | ★ | ★ | ★ | ★ | | | | |
| MDF |  | | | | ★ | | | | |
| Plastic |  | ★ | ★ | ★ | ★ | | | | |
| Acrylic |  | ★ | ★ | ★ | ★ | | | | |
| Fibreglass |  | ★ | ★ | ★ | ★ | ★ | ★ | ★ | |
| Formica |  | ★ | ★ | ★ | ★ | | | | |
| Plaster |  | | ★ | ★ | ★ | | | | |
| Suspended Floors |  | | ★ | ★ | ★ | | | | |
| Ceramic |  | | | | ★ | ★ | | ★ | |
| Porcelain / Glass / Stone |  | | | | | | | ★ | |
| Brick and Masonry |  | | | | ★ | ★ | | ★ | ★ |

Cutting Performance

Excellent



Good



For hole saw cutting speed recommendations please see page 24.

BI-METAL CSC CORDLESS SMOOTH CUT

Introducing the CSC - Cordless Smooth Cut Hole Saw: designed for maximum efficiency, it doubles the number of holes cut per battery charge compared to standard hole saws. Its flared base cap ensures a precise cutting depth of 13mm (1/2"), making it perfect for various materials, including stainless steel, mild sheet steel, plasterboard, wood, and thin non-metallics.



Built for durability, the CSC Hole Saw features hardened, abrasion-resistant high-speed steel teeth and a robust alloy body and cap. Its heat-resistant high-speed steel edge with alloy backing and constant 8 TPI pitch ensures reliable performance with battery-operated power tools.

FEATURES

- Perfect for cutting stainless steel, tool steel, mild steel sheeting, wood, and thin plastics.
- Safety stop feature ensures the saw does not travel beyond a depth of 13mm (1/2"), providing a safer and more controlled cutting experience.
- Complete assembly comes ready to use with an arbor, pilot drill, and ejector spring.
- Constant pitch teeth provide exceptionally smooth cuts with a pitch of 8 teeth per 25mm (1 inch).
- Recommended cutting depth for optimal performance is 3mm.

| Cat. No. | Item Number | Diameter | |
|----------|-------------|----------|---------|
| | | mm | Inch |
| CSC16 | BF1316 | 16mm | 5/8" |
| CSC19 | BF1319 | 19mm | 3/4" |
| CSC20 | BF1320 | 20mm | 25/32" |
| CSC22 | BF1322 | 22mm | 7/8" |
| CSC25 | BF1325 | 25mm | 1" |
| CSC27 | BF1327 | 27mm | 1.1/16" |
| CSC29 | BF1329 | 29mm | 1.1/8" |
| CSC30 | BF1330 | 30mm | 1.3/16" |
| CSC32 | BF1332 | 32mm | 1.1/4" |
| CSC35 | BF1335 | 35mm | 1.3/8" |
| CSC38 | BF1338 | 38mm | 1.1/2" |
| CSC40 | BF1341 | 40mm | 1.9/16" |
| CSC51 | BF1347 | 51mm | 2" |



General Purpose Kit 1
KCS06001

| Cutting Performance | |
|-------------------------|--|
| Excellent | ★ |
| Good | ☆ |
| Hole Saw Depth | 13mm 1/2" |
| Rec. Cutting Depth | <3mm <input checked="" type="checkbox"/> |
| • Metal | ★ |
| • Inox (Stainless) | ★ |
| • Non Ferrous Materials | ★ |
| Wood | ☆ |
| Veneer | ☆ |
| Plastic | ★ |
| Acrylic | ☆ |
| Fibreglass | ☆ |
| Formica | ☆ |

| | Description | Cat. No. | Item Number | Hole Saw Sizes | Arbors and Accessories |
|---|-----------------------|----------|-------------|---|------------------------|
| # | General Purpose Kit | KCS07011 | BF1450 | 16mm, 20mm, 25mm, 29mm, 30mm, 32mm & 38mm | A18 Dual Hex Chuck |
| | General Purpose Kit 1 | KCS06001 | BF1453 | 16mm, 20mm, 22mm, 25mm, 32mm & 40mm | - |
| | Electricians Kit | KCS03001 | BF1420 | 20mm, 25mm, & 32mm | - |

= MTO - Made to order, may be subject to longer lead times.

FAST CUT BI-METAL FCH

Introducing the FCH - Fast Cut Saw, designed for enhanced heat and wear resistance. This saw delivers smoother, faster cuts across a wide range of materials. It is specifically tailored for cutting stainless and mild steel sheets and can efficiently cut through tubes with a wall thickness of up to 3mm (1/8").

| Description | Cat No | Item Number | Hole Saw Sizes | Arbors and Accessories |
|----------------------------|----------|-------------|---|--|
| Kwik Change Fast Cut Kit | KFC03051 | KFC03051 | 20, 25 & 32mm | A6, A6-2 (x2), A6-3, A015C Pilot Drill |
| General Purpose Kit | KFC06023 | AX5421 | 22mm, 29mm, 35mm, 44mm, 51mm & 64mm | A1 & A10 Arbors |
| Electricians Kit 2 | KFC06022 | AX5406 | 16mm, 20mm, 25mm, 29mm, 44mm & 51mm | A1 & A10 Arbors |
| Electricians Kit 1 | KFC06021 | AX5400 | 16mm, 20mm, 25mm, 32mm, 40mm & 51mm | A1 & A10 Arbors |
| Ulti Mate Electricians Kit | KFC06071 | AX5403 | 16mm, 20mm, 25mm, 32mm, 40mm & 51mm | A3 Ulti Mate Arbor 6 Ulti Mate Arbor Adapters |
| Electricians Kit | KFC11021 | AX5409 | 16mm, 20mm, 22mm, 25mm, 29mm, 35mm, 44mm, 51mm, 64mm, 68mm & 76mm | A1 & A2 Arbors |
| Plumbers Kit | KFC07021 | AX5412 | 19mm, 22mm, 29mm, 38mm, 44mm, 51mm & 57mm | A1 & A10 Arbors |
| Plumbers Kit | KFC11022 | AX5415 | 16mm, 19mm, 22mm, 29mm, 35mm, 38mm, 44mm, 51mm, 57mm, 65mm & 68mm | A1 & A2 Arbors |
| Universal Kit | KFC14021 | AX5427 | 16mm, 20mm, 22mm, 25mm, 29mm, 32mm, 35mm, 38mm, 44mm, 51mm, 57mm, 64mm, 68mm & 76mm | A1 & A2 Arbors |
| # General Purpose | KFC11031 | AX5424 | 19mm, 22mm, 25mm, 32mm, 35mm, 38mm, 44mm, 51mm, 57mm, 64mm & 76mm | A1 & A2 Arbors A5 Extension |

= MTO - Made to order, may be subject to longer lead times.

| Cutting Performance | |
|-------------------------|----------------|
| Excellent | ★ |
| Good | ☆ |
| Hole Saw Depth | 41mm 1.5/8" |
| Rec. Cutting Depth | up to 13mm |
| • Metal | ★ |
| • Inox (Stainless) | ★ |
| • Non Ferrous Materials | ★ |
| Cast iron | ★ |
| Wood | ☆ |
| Veneer | ☆ |
| Plastic | ★ |
| Acrylic | ☆ |
| Fibreglass | ☆ |
| Formica | ☆ |
| Plaster | ☆ |
| Suspended Floors | ☆ |



EVA Case for Unbreakable Protection.

POS Packaging with Kit Contents.





BI-METAL HOLE SAWS



FASTER & SMOOTHER

The FCH Fast Cut Bi-Metal Hole Saws ensure a smoother and faster cut with their extra cobalt HSS tooth material and 5.5 TPI positive rake tooth design. Designed for stainless steel, metals, and mild steel sheets, these saws also cut through wood, plastic, plaster, and other materials. The recommended cutting depth is up to 13mm (1/2") in softer materials.

FEATURES

- With extra cobalt for enhanced heat and wear resistance - improving the product life.
- The 5.5 TPI positive rake tooth form provides less torque for a smoother, faster cut in all materials.
- 30% extra gullet volume for better material penetration.
- Ideal for 3mm stainless steel, mild steel sheet and tubes and other materials with a thickness of up to 13mm (1/2").
- Size range: 14mm - 210mm (9/16" - 8.9/32").
- 41mm (1.5/8") hole saw depth.

| Cat. No. | Diameter | | Appropriate Arbors |
|-----------|----------|----------|--|
| | mm | Inch | |
| FCH0096-G | 14mm | 9/16" | A1 A4 A1-1 (SDS plus) A3 & A3-3 (Ulti-Mate) A6 & A6-2 (Kwik-Change) |
| FCH0058-G | 16mm | 5/8" | |
| FCH1016-G | 17mm | 11/16" | |
| FCH0034-G | 19mm | 3/4" | |
| FCH2532-G | 20mm* | 25/32" | |
| FCH1036-G | 21mm | 13/16" | |
| FCH0078-G | 22mm | 7/8" | |
| FCH1056-G | 24mm | 15/16" | |
| FCH0100-G | 25mm* | 1" | |
| FCH0116-G | 27mm | 1.1/16" | |
| FCH0118-G | 29mm | 1.1/8" | |
| FCH0136-G | 30mm | 1.3/16" | |
| FCH0114-G | 32mm* | 1.1/4" | |
| FCH0156-G | 33mm | 1.5/16" | |
| FCH0138-G | 35mm | 1.3/8" | |
| FCH0176-G | 37mm | 1.7/16" | |
| FCH0112-G | 38mm | 1.1/2" | |
| FCH0196-G | 40mm | 1.9/16" | |
| FCH0158-G | 41mm | 1.5/8" | |
| FCH1116-G | 43mm | 1.11/16" | A2 A10 A17-38 (Locking Arbor) A2-1 (SDS plus) A3 & A3-4 (Ulti-Mate) A6 & A6-3 (Kwik-Change) |
| FCH0134-G | 44mm | 1.3/4" | |
| FCH1136-G | 46mm | 1.13/16" | |
| FCH0178-G | 48mm | 1.7/8" | |
| FCH0200-G | 51mm | 2" | |
| FCH0216-G | 52mm | 2.1/16" | |
| FCH0218-G | 54mm | 2.1/8" | |
| FCH056M-G | 56mm | 2.3/16" | |
| FCH0214-G | 57mm | 2.1/4" | |
| FCH0256-G | 59mm | 2.5/16" | |
| FCH0238-G | 60mm | 2.3/8" | |
| FCH0212-G | 64mm | 2.1/2" | |
| FCH0296-G | 65mm | 2.9/16" | |
| FCH0258-G | 67mm | 2.5/8" | |
| FCH068M-G | 68mm | 2.11/16" | |
| FCH0234-G | 70mm | 2.3/4" | |
| FCH0278-G | 73mm | 2.7/8" | |
| FCH0300-G | 76mm | 3" | |
| FCH0318-G | 79mm | 3.1/8" | |
| FCH0314-G | 83mm | 3.1/4" | A2 A10 A17-38 A2-1 A3 & A3-5 A6 A2 or A10 A17-38 A2-1 A3 & A3-5 |
| FCH0338-G | 86mm | 3.3/8" | |
| FCH0312-G | 89mm | 3.1/2" | |
| FCH0358-G | 92mm | 3.5/8" | |
| FCH0334-G | 95mm | 3.3/4" | |
| FCH0378-G | 98mm | 3.7/8" | |
| FCH0400-G | 102mm | 4" | |
| FCH0418-G | 105mm | 4.1/8" | |
| FCH0414-G | 108mm | 4.1/4" | |
| FCH0438-G | 111mm | 4.3/8" | |
| FCH0412-G | 114mm | 4.1/2" | |
| FCH0434-G | 121mm | 4.3/4" | |
| FCH0500-G | 127mm | 5" | |
| FCH0514-G | 133mm | 5.1/4" | |
| FCH0512-G | 140mm | 5.1/2" | |
| FCH0600-G | 152mm | 6" | |
| FCH160M-G | 160mm | 6.5/16" | |
| FCH168M-G | 168mm | 6.5/8" | |
| FCH177M-G | 177mm | 6.31/32" | |
| FCH210M-G | 210mm | 8.9/32" | |

* Also available in 6 packs. See page 25.

DEEP CUT BI-METAL DCH

The DCH - Deep Cut Saw with extra cobalt HSS teeth. Provides enhanced heat and wear resistance. The Deep Cut saw features an increased depth of 51mm (2") and is ideal for cutting metal and tubes with a thickness of greater than 3mm, and wood up to 51mm (2") thick.

| Description | Cat No | Item Number | Hole Saw Sizes | Arbors and Accessories |
|------------------|----------|-------------|---|------------------------|
| Electricians Kit | KDC05021 | BF7006 | 20mm, 25mm, 29mm, 44mm & 51mm | A1E & A10E Arbors |
| Electricians Kit | KDC10021 | BF7009 | 20mm, 22mm, 25mm, 29mm, 35mm, 44mm, 51mm, 64mm, 68mm & 76mm | A1E & A2E Arbors |
| # Plumbers Kit | KDC07021 | BF7012 | 19mm, 22mm, 29mm, 38mm, 44mm, 51mm & 57mm | A1E & A10E Arbors |
| Plumbers Kit | KDC10022 | BF7015 | 19mm, 22mm, 29mm, 35mm, 38mm, 44mm, 51mm, 57mm, 65mm & 68mm | A1E & A2E Arbors |
| Universal Kit | KDC13021 | BF7024 | 20mm, 22mm, 25mm, 29mm, 32mm, 35mm, 38mm, 44mm, 51mm, 57mm, 64mm, 68mm & 76mm | A1E & A2E Arbors |

= MTO - Made to order, may be subject to longer lead times.



| Cutting Performance | | |
|-------------------------|------------|---|
| Excellent | | ★ |
| Good | | ☆ |
| Hole Saw Depth | 51mm 2" | |
| Rec. Cutting Depth | 3-13mm | ☑ |
| | >13mm | ☑ |
| • Metal | | ★ |
| • Inox (Stainless) | | ★ |
| • Non Ferrous Materials | | ★ |
| Cast iron | | ★ |
| Wood | | ☆ |
| Veneer | | ☆ |
| Plastic | | ☆ |
| Acrylic | | ☆ |
| Fibreglass | | ☆ |
| Formica | | ☆ |
| Plaster | | ☆ |
| Suspended Floors | | ☆ |



EVA Case for Unbreakable Protection.

POS Packaging with Kit Contents.





BI-METAL HOLE SAWS



DEEPER & STRONGER

With a 10mm increase in cutting depth and aggressive material penetration, this hole saw offers exceptional performance with efficient kerf clearance. It is the ultimate multi-use holesaw for penetrating metals, wood, plastic, plaster, and more. Recommended cutting depth: greater than 3mm (1/8").

FEATURES

- 51mm (2") hole saw depth improves cutting performance on tubes, particularly where there is a need to cut through both sides.
- With extra cobalt for enhanced heat and wear resistance - improving the product life.
- Ideal for solid materials greater than 3mm (1/8") in thickness.
- Aggressive material penetration and kerf clearance.
- Size range: 19mm - 210mm (3/4" - 8.9/32").
- 51mm (2") hole saw depth - requires arbors with an extended length pilot drill (e.g. A1E, A2E or A17-38E etc.).

| Cat. No. | Diameter | | Appropriate Arbors |
|-----------|----------|----------|-------------------------|
| | mm | Inch | |
| DCH0034-G | 19mm | 3/4" | |
| DCH2532-G | 20mm | 25/32" | A1E |
| DCH1036-G | 21mm | 13/16" | A4E |
| DCH0078-G | 22mm | 7/8" | A1-1E (SDS-plus) |
| DCH1056-G | 24mm | 15/16" | A3 & A3-3 (Ulti-Mate) |
| DCH0100-G | 25mm | 1" | A6 & A6-2 (Kwik-Change) |
| DCH0116-G | 27mm | 1.1/16" | |
| DCH0118-G | 29mm | 1.1/8" | |
| DCH0136-G | 30mm | 1.3/16" | |
| DCH0114-G | 32mm | 1.1/4" | |
| DCH0156-G | 33mm | 1.5/16" | |
| DCH0138-G | 35mm | 1.3/8" | |
| DCH0176-G | 37mm | 1.7/16" | |
| DCH0112-G | 38mm | 1.1/2" | |
| DCH0196-G | 40mm | 1.9/16" | |
| DCH0158-G | 41mm | 1.5/8" | |
| DCH1116-G | 43mm | 1.11/16" | |
| DCH0134-G | 44mm | 1.3/4" | |
| DCH1136-G | 46mm | 1.13/16" | |
| DCH0178-G | 48mm | 1.7/8" | |
| DCH0200-G | 51mm | 2" | A2E Quick-Hitch |
| DCH0216-G | 52mm | 2.1/16" | A10E Quick-Hitch |
| DCH0218-G | 54mm | 2.1/8" | A17-38E (Locking Arbor) |
| DCH056M-G | 56mm | 2.3/16" | A2-1E (SDS plus) |
| DCH0214-G | 57mm | 2.1/4" | A3 & A3-4 (Ulti-Mate) |
| DCH0256-G | 59mm | 2.5/16" | A6 & A6-3 (Kwik-Change) |
| DCH0238-G | 60mm | 2.3/8" | |
| DCH0212-G | 64mm | 2.1/2" | |
| DCH0296-G | 65mm | 2.9/16" | |
| DCH0258-G | 67mm | 2.5/8" | |
| DCH068M-G | 68mm | 2.11/16" | |
| DCH0234-G | 70mm | 2.3/4" | |
| DCH0278-G | 73mm | 2.7/8" | |
| DCH0300-G | 76mm | 3" | |
| DCH0318-G | 79mm | 3.1/8" | |
| DCH0314-G | 83mm | 3.1/4" | |
| DCH0338-G | 86mm | 3.3/8" | |
| DCH0312-G | 89mm | 3.1/2" | |
| DCH0358-G | 92mm | 3.5/8" | |
| DCH0334-G | 95mm | 3.3/4" | |
| DCH0378-G | 98mm | 3.7/8" | |
| DCH0400-G | 102mm | 4" | |
| DCH0418-G | 105mm | 4.1/8" | A2E |
| DCH0414-G | 108mm | 4.1/4" | A10E |
| DCH0438-G | 111mm | 4.3/8" | A17-38E |
| DCH0412-G | 114mm | 4.1/2" | A2-1E (SDS-plus) |
| DCH0434-G | 121mm | 4.3/4" | A3 & A3-5 |
| DCH0500-G | 127mm | 5" | A6 |
| DCH0514-G | 133mm | 5.1/4" | |
| DCH0512-G | 140mm | 5.1/2" | |
| DCH0600-G | 152mm | 6" | |
| DCH160M-G | 160mm | 6.5/16" | A2E or A10E |
| DCH168M-G | 168mm | 6.5/8" | A17-38E |
| DCH177M-G | 177mm | 6.31/32" | A2-1E |
| DCH210M-G | 210mm | 8.9/32" | A3 & A3-5 |

CARBIDE CT

HIGH PERFORMANCE TRIPLE CHIP TUNGSTEN CARBIDE

The triple-chip Tungsten Carbide Tipped (CT) Hole Saw offers exceptional durability and performance, with a longer blade life for cutting tough materials. It effortlessly cuts through nail-embedded wood, wood and metal combinations, reinforced concrete, and fibreglass. It delivers a smooth surface finish on entry and exit holes, making it perfect for many projects including cutting traditional lath and plaster.

Tungsten Carbide Tipped Teeth



FEATURES

- A cost effective solution for cutting nail embedded wood, any wood and metal combination, reinforced concrete and fibreglass.
- Leaves high quality surface finish on entry and exit and provides a smooth cut.
- Tungsten Carbide Tipped Teeth for outstanding cutting performance and product durability.
- Suitable for use in electric and battery operated tools.
- Hole saw depth of 41mm (1-5/8").

| Cutting Performance | |
|---------------------|--|
| Excellent | ★ |
| Good | ☆ |
| Hole Saw Depth | 41mm 1.5/8" |
| | <3mm <input checked="" type="checkbox"/> |
| Rec. Cutting Depth | 3-13mm <input checked="" type="checkbox"/> |
| | >13mm <input checked="" type="checkbox"/> |
| Cast iron | ★ |
| Wood | ☆ |
| Nail Embedded Wood | ☆ |

| | |
|-------------------|---|
| Veneer | ★ |
| Plastic | ★ |
| Acrylic | ★ |
| Ceramic | ☆ |
| Fibreglass | ★ |
| Formica | ★ |
| Plaster | ★ |
| Suspended Floors | ★ |
| Brick and Masonry | ☆ |

| Cat. No. | Item Number | Diameter | | Appropriate Arbors |
|------------------|-------------|----------|---------|--|
| | | mm | Inch | |
| NEW CT058 | BF398 | 16mm | 5/8" | A1 or A4 A1-1 (SDS plus) A3 & A3-3 (Ulti-Mate) A6 & A6-2 (Kwik-Change) XA1 or XA4 (Carbide Tipped) |
| CT034 | BF400 | 19mm | 3/4" | |
| CT2532 | BF402 | 20mm | 25/32" | |
| CT078 | BF405 | 22mm | 7/8" | |
| CT100 | BF410 | 25mm | 1" | |
| CT118 | BF415 | 29mm | 1.1/8" | HSS Pilot Drill A2 A10 A17-38 (Locking Arbor) A2-1 (SDS plus) |
| CT114 | BF420 | 32mm | 1.1/4" | |
| # CT156 | BF422 | 33mm | 1.5/16" | |
| CT138 | BF425 | 35mm | 1.3/8" | |
| CT112 | BF430 | 38mm | 1.1/2" | |
| CT196 | BF432 | 40mm | 1.9/16" | Carbide Tipped Arbors XA2 XA10 XA17-38 (Locking Arbor) XA2-1 (SDS plus) |
| CT158 | BF435 | 41mm | 1.5/8" | |
| CT134 | BF440 | 44mm | 1.3/4" | |
| CT178 | BF445 | 48mm | 1.7/8" | |
| CT200 | BF450 | 51mm | 2" | |
| CT218 | BF455 | 54mm | 2.1/8" | Ulti-Mate Arbor System A3 & A3-4 for up to 102mm / 4". |
| CT056MM | BF456 | 56mm | 2.3/16" | |
| CT214 | BF460 | 57mm | 2.1/4" | |
| CT238 | BF465 | 60mm | 2.3/8" | |
| CT212 | BF470 | 64mm | 2.1/2" | |
| CT258 | BF475 | 67mm | 2.5/8" | A3 & A3-5 for 102mm / 4" and above. Kwik-Change A6 & A6-3* (* up to 100mm holesaws) |
| CT234 | BF480 | 70mm | 2.3/4" | |
| CT300 | BF485 | 76mm | 3" | |
| CT318 | BF487 | 79mm | 3.1/8" | |
| CT314 | BF490 | 83mm | 3.1/4" | |
| CT338 | BF495 | 86mm | 3.3/8" | |
| CT312 | BF500 | 89mm | 3.1/2" | |
| CT358 | BF505 | 92mm | 3.5/8" | |
| CT334 | BF510 | 95mm | 3.3/4" | |
| CT378 | BF512 | 98mm | 3.7/8" | |
| CT400 | BF515 | 102mm | 4" | |
| CT418 | BF520 | 105mm | 4.1/8" | |
| CT414 | BF525 | 108mm | 4.1/4" | |
| CT438 | BF530 | 111mm | 4.3/8" | |
| CT412 | BF535 | 114mm | 4.1/2" | |
| CT434 | BF540 | 121mm | 4.3/4" | |
| CT500 | BF545 | 127mm | 5" | |
| CT512 | BF550 | 140mm | 5.1/2" | |
| CT600 | BF555 | 152mm | 6" | |

= MTO - Made to order, may be subject to longer lead times.

CARBIDE MPH

TUNGSTEN CARBIDE TIPPED MULTI PURPOSE

Tungsten Carbide Tipped Multi Purpose (MPH) Hole Saws feature a unique tooth set for ultra-aggressive, high performance cutting of non-metallics. Cutting speeds will be up to five times faster than a bi-metal hole saw cutting the same material, offering users rapid, heat-free, stock removal of wood, MDF, plastics, and ceramic tiles. For tradespeople, our kits provide the perfect solution to all your cutting needs.

FEATURES

- Rapid, heat free stock removal of wood, MDF, plastics, plasterboard, and ceramic tiles.
- Carbide Tipped Teeth for outstanding cutting performance and product durability.
- Smooth cutting with minimal heat build up.
- Hole saw depth of 54mm (2.1/8").
- Arbors with extended length pilot drills are available, alternatively fit the longer A014CE pilot drill to our standard arbors.
- Deep gullet for easy core removal
- Suitable for use in mains and battery powered tools

| | |
|----------------------------|---|
| Hole Saw Depth | 54mm 2.1/8" |
| Rec. Cutting Depth | <3mm <input checked="" type="checkbox"/> 3-13mm <input checked="" type="checkbox"/> >13mm <input checked="" type="checkbox"/> |
| Wood | ★ |
| Veneer | ★ |
| MDF | ★ |
| Plastic | ★ |
| Acrylic | ★ |
| Ceramic | ☆ |
| Fibreglass | ☆ |
| Formica | ★ |
| Plaster | ★ |
| Cutting Performance | |
| Excellent | ★ |
| Good | ☆ |




| Description | Cat No | Item Number | Hole Saw Sizes | Arbors and Accessories |
|--------------------------|----------|-------------|--|--|
| # General Purpose Kit | KMP09021 | BF1970 | 19mm, 22mm, 29mm, 35mm, 44mm, 51mm, 57mm, 64mm & 68mm | A1E & A17-38E |
| General Purpose Kit | KMP11021 | BF1973 | 19mm, 22mm, 29mm, 35mm, 38mm, 44mm, 51mm, 57mm, 64mm, 68mm & 76mm | A1E, A17-38E, XA014C |
| # Downlight Hole Saw Kit | KMP12011 | BF1976 | 35mm, 40mm, 44mm, 51mm, 60mm, 65mm, 70mm, 73mm, 76mm, 83mm, 86mm, & 92mm | XA17-38 (fitted with a carbide tipped pilot drill) |

= MTO - Made to order, may be subject to longer lead times.

| Cat. No. | Item Number | Diameter | | Appropriate Arbors |
|----------|-------------|----------|----------|---|
| | | mm | Inch | |
| MPH0034 | BF1505 | 19mm | 3/4" | Extended Length HSS Drill A1E A4E A1-1E (SDS-plus) A3 & A3-3 (Ulti-Mate) A6 & A6-2 (Kwik-Change) |
| MPH2532 | BF1510 | 20mm | 25/32" | |
| MPH0078 | BF1515 | 22mm | 7/8" | |
| MPH0100 | BF1520 | 25mm | 1" | |
| MPH0116 | BF1525 | 27mm | 1.1/16" | Carbide Tipped Arbors XA1 XA4 |
| MPH0118 | BF1530 | 29mm | 1.1/8" | |
| MPH0136 | BF1535 | 30mm | 1.3/16" | |
| MPH0114 | BF1540 | 32mm | 1.1/4" | |
| MPH0138 | BF1545 | 35mm | 1.3/8" | Extended Length HSS Drill A2E Quick-Hitch A10E Quick-Hitch A17-38E Locking Arbor A2-1E (SDS plus) |
| MPH0112 | BF1550 | 38mm | 1.1/2" | |
| MPH0196 | BF1555 | 40mm | 1.9/16" | |
| MPH0158 | BF1560 | 41mm | 1.5/8" | |
| MPH0134 | BF1565 | 44mm | 1.3/4" | Carbide Tipped Arbors XA2 XA10 XA17-38 Locking Arbor XA2-1 (SDS plus) |
| MPH0178 | BF1570 | 48mm | 1.7/8" | |
| MPH0200 | BF1575 | 51mm | 2" | |
| MPH0218 | BF1580 | 54mm | 2.1/8" | |
| MPH0214 | BF1585 | 57mm | 2.1/4" | Carbide Tipped Arbors XA2 XA10 XA17-38 Locking Arbor XA2-1 (SDS plus) |
| MPH0238 | BF1590 | 60mm | 2.3/8" | |
| MPH0212 | BF1595 | 64mm | 2.1/2" | |
| MPH0296 | BF1600 | 65mm | 2.9/16" | |
| MPH0258 | BF1605 | 67mm | 2.5/8" | Ulti-Mate Arbor System A3 & A3-4 for up to 102mm / 4". A3 & A3-5 for 102mm / 4" and above. |
| MPH68MM | BF1607 | 68mm | 2.11/16" | |
| MPH0234 | BF1610 | 70mm | 2.3/4" | |
| MPH0278 | BF1615 | 73mm | 2.7/8" | |
| MPH0300 | BF1620 | 76mm | 3" | Kwik-Change A6 & A6-3 for up to 100mm / 4". |
| MPH0318 | BF1625 | 79mm | 3.1/8" | |
| MPH0314 | BF1630 | 83mm | 3.1/4" | |
| MPH0338 | BF1635 | 86mm | 3.3/8" | |
| MPH0312 | BF1640 | 89mm | 3.1/2" | Kwik-Change A6 & A6-3 for up to 100mm / 4". |
| MPH0358 | BF1645 | 92mm | 3.5/8" | |
| MPH0334 | BF1650 | 95mm | 3.3/4" | |
| MPH0378 | BF1655 | 98mm | 3.7/8" | |
| MPH0400 | BF1660 | 102mm | 4" | Kwik-Change A6 & A6-3 for up to 100mm / 4". |
| MPH0418 | BF1665 | 105mm | 4.1/8" | |
| MPH0414 | BF1670 | 108mm | 4.1/4" | |
| MPH0456 | BF1675 | 109mm | 4.5/16" | |
| MPH0438 | BF1680 | 111mm | 4.3/8" | Kwik-Change A6 & A6-3 for up to 100mm / 4". |
| MPH0412 | BF1685 | 114mm | 4.1/2" | |
| MPH0458 | BF1690 | 118mm | 4.5/8" | |
| MPH0434 | BF1695 | 121mm | 4.3/4" | |
| MPH0500 | BF1700 | 127mm | 5" | Kwik-Change A6 & A6-3 for up to 100mm / 4". |
| MPH0512 | BF1705 | 140mm | 5.1/2" | |
| MPH0600 | BF1710 | 152mm | 6" | |
| MPH0614 | BF1715 | 159mm | 6.1/4" | |

CARBIDE SM STAINLESS STEEL [SHEET METAL]

Tungsten Carbide Tipped Stainless Steel (Sheet Metal – SM) Hole Saws cut high-alloy and stainless steels, non-ferrous light metals, and reinforced fabrics faster than bi-metal saws. Their tough tungsten carbide tipped teeth remove chips efficiently, making them ideal for sheet metal up to 3mm (1/8") thick."







FEATURES

- Split-point drill for faster penetration and precise centering
- Ideal for production cutting, especially with limited speed control
- Tungsten carbide tipped teeth for extended product life and superior cutting
- Replacement pilot drills readily available
- Solid one-piece construction with arbor and pilot drill
- Ejector spring for effortless core removal
- Progressive carbide tooth grind for swift cuts and improved swarf removal
- Enhanced tooth strength with shallow gullet design
- Safety stop at base of hole saw for drilling within 13mm (1/2") depth
- Recommended cutting depth set at 3mm (1/8")

| Description | Cat. No. | Item Number | Hole Saw Sizes |
|-----------------------------|----------|-------------|---|
| Professional Heavy Duty Kit | KSM07001 | BF3090 | 16mm, 20mm, 22mm, 25mm, 32mm, 40mm & 50mm |

| Cat. No. | Item Number | Diameter | |
|----------|-------------|----------|----------|
| | | mm | Inch |
| SM15 | BF2015 | 15mm | 19/32" |
| SM16 | BF2016 | 16mm | 5/8" |
| SM17 | BF2017 | 17mm | 11/16" |
| SM18 | BF2018 | 18mm | 23/32" |
| SM19 | BF2019 | 19mm | 3/4" |
| SM20 | BF2020 | 20mm | 25/32" |
| SM21 | BF2021 | 21mm | 13/16" |
| SM22 | BF2022 | 22mm | 7/8" |
| SM23 | BF2023 | 23mm | 29/32" |
| SM24 | BF2024 | 24mm | 15/16" |
| SM25 | BF2025 | 25mm | 1" |
| SM26 | BF2026 | 26mm | 1.1/32" |
| SM27 | BF2027 | 27mm | 1.1/16" |
| SM28 | BF2028 | 28mm | 1.3/32" |
| SM29 | BF2029 | 29mm | 1.1/8" |
| SM30 | BF2030 | 30mm | 1.3/16" |
| SM31 | BF2031 | 31mm | 1.7/32" |
| SM32 | BF2032 | 32mm | 1.1/4" |
| SM33 | BF2033 | 33mm | 1.5/16" |
| SM34 | BF2034 | 34mm | 1.11/32" |
| SM35 | BF2035 | 35mm | 1.3/8" |
| SM36 | BF2036 | 36mm | 1.13/32" |
| SM37 | BF2037 | 37mm | 1.7/16" |
| SM38 | BF2038 | 38mm | 1.1/2" |
| SM39 | BF2039 | 39mm | 1.17/32" |
| SM40 | BF2040 | 40mm | 1.9/16" |
| SM45 | BF2045 | 45mm | 1.25/32" |
| SM50 | BF2050 | 50mm | 1.31/32" |
| SM51 | BF2051 | 51mm | 2 |
| SM55 | BF2055 | 55mm | 2.5/32" |
| SM60 | BF2060 | 60mm | 2.3/8" |
| SM65 | BF2065 | 65mm | 2.9/16" |
| SM70 | BF2070 | 70mm | 2.3/4" |
| SM75 | BF2075 | 75mm | 2.15/16" |
| SM80 | BF2080 | 80mm | 3.5/32" |
| SM85 | BF2085 | 85mm | 3.11/32" |
| SM90 | BF2090 | 90mm | 3.17/32" |
| SM95 | BF2095 | 95mm | 3.3/4" |
| SM100 | BF2100 | 100mm | 3.15/16" |

| Cat. No. | Item Number | Description |
|----------|-------------|-------------------------|
| SMD6 | BF21005 | Replacement Pilot Drill |

| | |
|-------------------------|---|
| Hole Saw Depth | 16mm 5/8" |
| Rec. Cutting Depth | ≤ 5mm <input checked="" type="checkbox"/> |
| • Metal |  ★ |
| • Inox (Stainless) |  ★ |
| • Non Ferrous Materials |  ★ |
| Fibreglass |  ★ |

Cutting Performance

Excellent




Good



CARBIDE CTD

CARBIDE TIPPED DEEP CUT







APPLICATIONS:

- Stainless Steel (up to 20mm)
- Steel
- Non Ferrous Metals
- Aluminium
- Cast Iron
- Copper

KCT08001 Hole Saw Kit

The Carbide Tipped Deep Cut (CTD) Hole Saw is designed for intensive drilling in various materials up to 25mm (1") thick. Starrett's CTD hole saws feature a unique tooth grind for fast, efficient cutting, minimal snagging, and extended lifespan.

| | |
|----------------------------|---|
| Hole Saw Depth | 25mm 1" |
| Rec. Cutting Depth | <3mm <input checked="" type="checkbox"/> |
| | 3-13mm <input checked="" type="checkbox"/> |
| | >13mm <input checked="" type="checkbox"/> |
| Metal Inox (Stainless) |  ★ |
| Non Ferrous Materials |  ★ |
| Cast iron |  ★ |
| Fibreglass |  ★ |
| Cutting Performance | |
| Excellent | ★ |
| Good | ☆ |

FEATURES

- Each tooth has a 3-ply grind for better performance and durability than 2-ply models
- Tungsten carbide tips ensure excellent heat and wear resistance
- Solid one-piece construction, no assembly required
- Compatible with fixed or portable drills, mains power, or cordless
- Includes an ejector spring for easy core removal
- Replacement pilot drills and ejector springs available
- 25mm (1") hole saw depth

| Cat. No. | Item Number | Diameter | |
|----------|-------------|----------|----------|
| | | mm | Inch |
| CTD15 | BF56115 | 15 | 19/32" |
| CTD16 | BF56116 | 16 | 5/8" |
| CTD17 | BF56117 | 17 | 11/16" |
| CTD18 | BF56118 | 18 | 22/32" |
| CTD19 | BF56119 | 19 | 3/4" |
| CTD20 | BF56120 | 20 | 25/32" |
| CTD21 | BF56121 | 21 | 13/16" |
| CTD22 | BF56122 | 22 | 7/8" |
| # CTD23 | BF56123 | 23 | 29/32" |
| CTD24 | BF56124 | 24 | 15/16" |
| CTD25 | BF56125 | 25 | 1" |
| CTD26 | BF56126 | 26 | 1.1/32" |
| CTD27 | BF56127 | 27 | 1.1/16" |
| CTD28 | BF56128 | 28 | 1.3/32" |
| CTD29 | BF56129 | 29 | 1.1/8" |
| CTD30 | BF56130 | 30 | 1.3/16" |
| CTD32 | BF56132 | 32 | 1.1/4" |
| CTD33 | BF56133 | 33 | 1.5/16" |
| CTD34 | BF56134 | 34 | 1.11/32" |
| CTD35 | BF56135 | 35 | 1.3/8" |
| # CTD36 | BF56136 | 36 | 1.13/32" |
| CTD38 | BF56138 | 38 | 1.1/2" |
| # CTD39 | BF56139 | 39 | 1.17/32" |
| CTD40 | BF56140 | 40 | 1.9/16" |
| CTD45 | BF56145 | 45 | 1.25/32" |
| CTD50 | BF56150 | 50 | 1.31/32" |
| CTD51 | BF56151 | 51 | 2" |
| CTD55 | BF56155 | 55 | 2.5/32" |
| CTD60 | BF56160 | 60 | 2.3/8" |
| CTD64 | BF56164 | 64 | 2.1/2" |
| CTD65 | BF56165 | 65 | 2.9/16" |
| CTD70 | BF56170 | 70 | 2.3/4" |
| CTD75 | BF56175 | 75 | 2.15/16" |
| CTD80 | BF56180 | 80 | 2.5/32" |
| CTD85 | BF56185 | 85 | 3.11/32" |
| CTD90 | BF56190 | 90 | 3.17/32" |
| CTD95 | BF56195 | 95 | 3.3/4" |
| CTD100 | BF56200 | 100 | 3.15/16" |

| Cat No. | Item Number | Description |
|---------|-------------|-------------------------|
| A014F | BF56300 | Replacement Pilot Drill |

| Kit Cat. No. | Item Number | No. of Saws | Hole Saw Diameters |
|--------------|-------------|-------------|---|
| KCT08001 | BF56350 | 8 | 16mm 20mm 22mm 25mm 32mm 40mm 51mm 64mm |
| # KCT07001 | BF56355 | 7 | 16mm 20mm 22mm 25mm 32mm 40mm 50mm |

= MTO - Made to order, may be subject to longer lead times.

DIAMOND D






| Cat. No. | Item Number | Diameter | | Appropriate Arbors |
|----------|-------------|----------|----------|---|
| | | mm | Inch | |
| D0096 | AY612 | 14mm | 9/16" | Carbide Tipped Arbors XA1 XA4 XA1-1 (SDS plus) |
| D0058 | AY615 | 16mm | 5/8" | |
| D1016 | AY618 | 17mm | 11/16" | |
| D0034 | AY621 | 19mm | 3/4" | |
| D2532 | AY624 | 20mm | 25/32" | |
| D1036 | AY627 | 21mm | 13/16" | Kwik-Change with Carbide Tipped Pilot Drill XA015C A6 & A6-2 |
| D0078 | AY630 | 22mm | 7/8" | |
| D1056 | AY633 | 24mm | 15/16" | |
| D0100 | AY636 | 25mm | 1" | |
| D0116 | AY639 | 27mm | 1.1/16" | |
| D0118 | AY642 | 29mm | 1.1/8" | |
| D0136 | AY645 | 30mm | 1.3/16" | |
| D0114 | AY648 | 32mm | 1.1/4" | |
| D0156 | AY651 | 33mm | 1.5/16" | |
| D0138 | AY654 | 35mm | 1.3/8" | |
| D0176 | AY657 | 37mm | 1.7/16" | |
| D0112 | AY660 | 38mm | 1.1/2" | |
| D0196 | AY663 | 40mm | 1.9/16" | |
| D0158 | AY666 | 41mm | 1.5/8" | |
| D1116 | AY669 | 43mm | 1.11/16" | |
| D0134 | AY672 | 44mm | 1.3/4" | |
| D1136 | AY675 | 46mm | 1.13/16" | |
| D0178 | AY678 | 48mm | 1.7/8" | |
| D0200 | AY681 | 51mm | 2" | |
| D0216 | AY684 | 52mm | 2.1/16" | |
| D0218 | AY687 | 54mm | 2.1/8" | |
| D56MM | AY690 | 56mm | 2.3/16" | |
| D0214 | AY693 | 57mm | 2.1/4" | |
| D0256 | AY696 | 59mm | 2.5/16" | Carbide Tipped Arbors XA2 XA10 XA17-38 Locking Arbor XA2-1 (SDS plus) |
| D0238 | AY699 | 60mm | 2.3/8" | |
| D0212 | AY702 | 64mm | 2.1/2" | |
| D0296 | AY705 | 65mm | 2.9/16" | |
| D0258 | AY708 | 67mm | 2.5/8" | |
| D68MM | AY711 | 68mm | 2.11/16" | Kwik-Change with Carbide Tipped Pilot Drill XA015C A6 & A6-3* (*up to 100mm / 4") |
| D0234 | AY717 | 70mm | 2.3/4" | |
| D0278 | AY720 | 73mm | 2.7/8" | |
| D0300 | AY723 | 76mm | 3" | |
| D0318 | AY726 | 79mm | 3.1/8" | |
| D0314 | AY729 | 83mm | 3.1/4" | |
| D0338 | AY732 | 86mm | 3.3/8" | |
| D0312 | AY735 | 89mm | 3.1/2" | |
| D0358 | AY738 | 92mm | 3.5/8" | |
| D0334 | AY741 | 95mm | 3.3/4" | |
| D0378 | AY744 | 98mm | 3.7/8" | |
| D0400 | AY747 | 102mm | 4" | |
| D0418 | AY750 | 105mm | 4.1/8" | |
| D0414 | AY753 | 108mm | 4.1/4" | |
| D0438 | AY756 | 111mm | 4.3/8" | |
| D0412 | AY759 | 114mm | 4.1/2" | |
| D0434 | AY762 | 121mm | 4.3/4" | |
| D0500 | AY765 | 127mm | 5" | |
| D0512 | AY768 | 140mm | 5.1/2" | |
| D0600 | AY771 | 152mm | 6" | |

DIAMOND GRIT HOLE SAWS

High performance Diamond Grit Hole Saws are perfect for drilling holes in non-metallics and offer the ideal cutting solution for the toughest situations. Featuring a synthetic diamond grit cutting edge permanently bonded to a tough steel body, this provides the necessary clearance for cutting at high speeds.

FEATURES

- Rapid cutting solution for non-metallics
- Smooth surface finish, ideal when cutting glass and ceramics
- Supported by a comprehensive range of arbors with carbide tipped pilot drills
- The ultimate hole saw for hard-to-cut materials
- Small diameter hole saws are perfect for kitchen and bathroom installations
- Cutting depth 38mm (1.1/2")
- Coolant should always be used with these saws

| | | |
|---------------------------|---|---------------|
| Hole Saw Depth | | 41mm (1.5/8") |
| Tile Drill Depth | | 20mm (25/32") |
| | <3mm | ☑ |
| Rec. Cutting Depth | 3-13mm | ☑ |
| | >13mm | ☑ |
| Ceramic |  | ★ |
| Porcelain / Glass / Stone |  | ★ |
| Marble / Granite |  | ★ |
| Fibreglass |  | ★ |
| Brick and Masonry |  | ★ |
| Cutting Performance | | |
| Excellent | | ★ |
| Good | | ☆ |

Note: Diamond Tile Drills and Hole Saws should always be cooled with water.



DIAMOND GRIT TILE DRILLS



- Small diameter hole saw, perfect for kitchen and bathroom installations
- Smooth surface finish, ideal when cutting non-hardened glass and porcelain
- Drive arbor and drill not required, as the tile drill is held directly in the power tool chuck
- Maximum cutting depth of 25mm (1")
- Core slot provides cooler cutting and allows for removal of debris produced during drilling

| Cat. No. | Item Number | Diameter | |
|----------|-------------|----------|--------|
| | | mm | Inch |
| D0005 | AY606 | 5mm | 3/16" |
| D0006 | AY607 | 6mm | 15/64" |
| D0065 | AY608 | 6.5mm | 1/4" |
| D0008 | AY609 | 8mm | 5/16" |
| D0010 | AY610 | 10mm | 3/8" |
| D0012 | AY611 | 12mm | 1/2" |

KIT, DRILL GUIDE, AND WATER BOTTLE

| Cat. No. | Item Number |
|----------|-------------|
| KD06041 | KD06041. |

| Cat. No. | Item Number |
|----------|-------------|
| # WCD01 | AY7851 |

| Cat. No. | Item Number | Size Range |
|----------|-------------|------------|
| DTDG01 | AY7850 | 5mm - 12mm |

= MTO - Made to order, may be subject to longer lead times.



DIAMOND BMC

DIAMOND DRI-CORE DRILLS

Diamond Brick and Masonry Dri-Core Drills are designed for intensive dry cutting on brickwork and blockwork. They are particularly suitable for plumbers, electricians and other installation engineers and an invaluable tool in the construction of flues, air vents and plumbing or electrical channels.



| | |
|----------------------------|-------|
| 22mm & 28mm Drill Depth | 300mm |
| 38mm to 152mm Drill Depth | 150mm |
| Rec. Cutting Depth | >13mm |
| Brick and Masonry | ★ |
| Cutting Performance | |
| Excellent | ★ |
| Good | ☆ |

FEATURES

- Faster rate of cut than TCT alternatives with less pressure required.
- 300mm saw length on 22 and 28mm diameter saws. 150mm saw length on all other diameters.
- **Note:** not for use on reinforced concrete.



| Cat. No. | Item Number | Size | |
|----------|-------------|-------|----------|
| | | mm | Inch |
| BMC22 | BF3110 | 22mm | 7/8" |
| BMC28 | BF3115 | 28mm | 1.3/32" |
| BMC38 | BF3120 | 38mm | 1.1/2" |
| BMC42 | BF3125 | 42mm | 1.21/32" |
| BMC48 | BF3130 | 48mm | 1.7/8" |
| BMC52 | BF3135 | 52mm | 2.1/16" |
| BMC65 | BF3140 | 65mm | 2.9/16" |
| BMC78 | BF3145 | 78mm | 3.1/16" |
| BMC102 | BF3150 | 102mm | 4" |
| BMC107 | BF3155 | 107mm | 4.7/32" |
| BMC117 | BF3160 | 117mm | 4.19/32" |
| BMC127 | BF3165 | 127mm | 5" |
| BMC152 | BF3170 | 152mm | 6" |

| Arbors & Accessories | Cat. No. | Item Number |
|--------------------------|----------|-------------|
| SDS Adapter | BMA2 | BF3205 |
| Hex Adapter | BMA1 | BF3200 |
| 240mm SDS Adapter | BMA2240 | BF3220 |
| 240mm Hex Adapter | BMA1240 | BF3210 |
| Pilot Drill - 13 x 200mm | BMA3200 | BF3225 |
| Pilot Drill - 10 x 350mm | BMA3350 | BF3230 |
| 150 mm Extension | BMA4150 | BF3232 |
| 250mm Extension | BMA4250 | BF3235 |
| # Drift Key | BMA5 | BF3240 |

= MTO - Made to order, may be subject to longer lead times.

| Description | Cat No | Item Number | Core Drill Sizes | Arbors | Accessories |
|----------------------------|--------|-------------|---------------------------------|-------------------------------|--------------------------------------|
| Diamond Dri-Core Drill Kit | BMKIT1 | BF3265 | 38mm, 52mm, 65mm, 117mm & 127mm | BMA1, BMA2, BMA1240 & BMA2240 | BMA3200 Pilot Drill & BMA5 Drift Key |



KWIK-CHANGE ARBOR SYSTEM

FAST, TOOL FREE CHANGES BETWEEN DIFFERENT SIZES AND TYPES OF HOLE SAW, PLUS A SIMPLE METHOD OF CORE EJECTION AND HOLE ENLARGEMENT.

The new Kwik-Change Arbor system from Starrett offers fast, tool free changes between different sizes and types of hole saws, plus a simple method of core ejection and hole enlargement. Suitable for the standard Starrett hole saw range up to 100mm / 4" diameter, Kwik-Change will be an invaluable addition for any regular hole saw user.



A6



A6-1



A6-2



A6-3



A015C



XA015C

Kwik-Change Arbor and Hole Saw System

| Cat No | Item Number | Description |
|----------|-------------|---|
| A6 | BF3700 | Kwik-Change Chuck - Hex Shank |
| # A6-1 | BF3705 | Kwik-Change Chuck - SDS Shank |
| A6-2 | BF3710 | Kwik-Change Collar for 14-30mm hole saws |
| A6-3 | BF3715 | Kwik-Change Collar for 32mm - 100mm hole saws |
| A015C | BF3620 | Kwik-Change High Speed Steel Pilot Drill |
| # XA015C | BF3625 | Kwik-Change Carbide Tipped Pilot Drill |

= MTO - Made to order, may be subject to longer lead times.

**KWIK-CHANGE
BETWEEN HOLE
SAWS**

**KWIK-CHANGE
PILOT DRILL**

**CORE EJECTION
& HOLE
ENLARGEMENT**

Kwik-Change Kits | Hex Shank Chuck

| Cat No | Item Number | Description | Kit Contents |
|--------|-------------|---|---|
| A6-4 | BF3735 | Kwik-Change Arbor Kit with High Speed Steel Drill | Kwik-Change Chuck, one A6-2 Collar, one A6-3 Collar, one A015C Pilot Drill |
| A6-5 | BF3740 | Kwik-Change Arbor Kit with Carbide Tipped Drill | Kwik-Change Chuck, one A6-2 Collar, one A6-3 Collar, one XA015C Pilot Drill |

Kwik-Change Kits | SDS Shank Chuck

| Cat No | Item Number | Description | Kit Contents |
|--------|-------------|---|---|
| # A6-6 | BF3745 | Kwik-Change Arbor Kit with High Speed Steel Drill | Kwik-Change Chuck, one A6-2 Collar, one A6-3 Collar, one A015C Pilot Drill |
| # A6-7 | BF3750 | Kwik-Change Arbor Kit with Carbide Tipped Drill | Kwik-Change Chuck, one A6-2 Collar, one A6-3 Collar, one XA015C Pilot Drill |

= MTO - Made to order, may be subject to longer lead times.

Starrett® KWIK-CHANGE | ARBOR


- Attach the arbors to all regularly used hole saws.
- Change between different sizes of saw at the push of a button!



Push the button on the arbor and pull the hole saw down the pilot drill. To use a new hole saw, push the button on the arbor and slide the hole saw forward to remove it.

Starrett® KWIK-CHANGE | PILOT DRILL

- Pull back the chrome collar on the chuck to change the pilot drill.
- No tools required!
- Caution: Pilot drills may be hot after use.



Pull back the collar on the chuck to remove the pilot drill, to insert a new drill pull back the collar on the chuck and insert the new drill.

Starrett® KWIK-CHANGE | HOLE ENLARGEMENT

- Attach arbors to hole saws of the same size as the existing hole and the same size as the required hole.
- Attach the larger diameter hole saw to the Kwik-Change chuck.
- Attach the smaller diameter hole saw to the drill and slide it down inside the larger diameter saw.
- Drill the hole. **This system is recommended for overhead or vertical surfaces only.**

Attach the larger hole saw to the chuck, slide the smaller of the two hole saws inside the larger hole saw and use it as a pilot for the new, larger hole.



Starrett® KWIK-CHANGE | CORE EJECTION

- If the core is stuck in the hole saw after drilling a hole, press the arbor button and slide the hole saw and attached arbor off the drill.
- The pilot drill can then be used to push the core out of the saw using the side flutes or the holes in the base of the saw.
- Caution: Cores may be hot and sharp.



ARBORS AND ACCESSORIES



| FOR USE WITH HOLE SAW TYPES | | BI-METAL FAST CUT FCH CARBIDE TIPPED CT | | BI-METAL DEEP CUT DCH TCT MULTI PURPOSE MPH | | DIAMOND GRIT D CARBIDE TIPPED CT TCT MULTI PURPOSE MPH | |
|---|--|--|----------------|--|----------------|--|----------------|
| PILOT DRILL TYPE | | STANDARD HSS PILOT DRILL | | EXTENDED LENGTH HSS PILOT DRILL | | CARBIDE TIPPED PILOT DRILL | |
| FITS HOLE SAW DIAMETERS MM (INCH) | ARBOR SHANK SIZES MM (INCH) | ARBOR CATALOGUE NUMBER | ITEM NUMBER | ARBOR CATALOGUE NUMBER | ITEM NUMBER | ARBOR CATALOGUE NUMBER | ITEM NUMBER |
| 14 - 30mm (9/16" - 1.3/16") | 8.75mm (11/32") Hex (excluding SDS-Plus Arbors) | A1 | AY1385 | A1E | AY1391 | XA1 | AY5675 |
| | | A1-1 | AY154 | A1-1E | AY1541 | XA1-1 | AY585 |
| | 6.5mm (1/4") Hex | A4 | AY1451 | A4E | AY1453 | XA4C | AY5731 |
| 32 - 210mm (1.1/4" - 8.9/32") | 11mm (7/16") Hex (excluding SDS-Plus Arbors) | A2 (Quick-Hitch) | AY141 | A2E (Quick-Hitch) | AY1411 | XA2 (Quick-Hitch) | AY569 |
| | | A2-1 (Quick-Hitch) | AY155 | A2-1E (Quick-Hitch) | AY1551 | XA2-1 (Quick-Hitch) | AY586 |
| | 8.75mm (11/32") Hex | A10 (Quick-Hitch) | AY1485 | A10E (Quick-Hitch) | AY1491 | XA10 (Quick-Hitch) | AY5775 |
| | | A17-38 Locking Arbor | AY2274 | A17-38E Locking Arbor | AY2272 | XA17-38 Locking Arbor | AY2278 |

QUICK-HITCH ARBORS

WITH HSS, HSS EXTENDED LENGTH OR CARBIDE TIPPED PILOT DRILLS

Two locating pins insert into the hole saw cap to prevent overtightening on the screw thread. This facilitates tool-free and instant hole saw changes without removing the arbor from the chuck.



SDS-PLUS ARBOR SHANKS

WITH HSS, HSS EXTENDED LENGTH OR CARBIDE TIPPED PILOT DRILLS


The SDS-Plus shank allows the arbors to be used in SDS-plus rotary hammer drills with the hammer action turned off.

LOCKING ARBORS

WITH HSS, HSS EXTENDED LENGTH OR CARBIDE TIPPED PILOT DRILLS

For hole saws with diameters ranging from 32mm to 210mm (1.1/4" to 8.9/32"), the arbor securely locks onto the saw, reducing vibration. It's essential for demanding jobs and production runs.

ARBOR PILOT DRILL



HIGH SPEED STEEL PILOT DRILLS

| Cat. No. | Item Number | Fits Starrett Arbor Nos. | For Use with Saw Types |
|----------|-------------|--|--|
| A014C | AY209 | All Arbors - Except A3 | For All FCH Saws |
| A014CE | AY2091 | Extended Length Pilot Drill Fits All Starrett Arbors except A3 Ulti Mate | For DCH and MPH Hole Saws |
| # SMD6 | BF21005 | - | Replacement drill for SM series hole saws |
| A014F | BF56300 | - | Replacement drill for CTD series hole saws |
| A015C | BF3620 | Fits Starrett A6 Kwik-Change Arbor System | For all FCH, DCH, CT and MPH hole saws |

= MTO - Made to order, may be subject to longer lead times.

CARBIDE TIPPED PILOT DRILLS

| Cat. No. | Item Number | Fits Starrett Arbor Nos. | For Use with Saw Types |
|----------|-------------|---|-----------------------------------|
| # XA014C | AY601 | All Arbors | For all CT, MPH and D Series Saws |
| # XA015C | BF3625 | Fits Starrett A6 Kwik-Change Arbor System | For all CT, MPH and D Series Saws |

= MTO - Made to order, may be subject to longer lead times.

ARBOR EXTENSIONS



300mm (12") extension bar.

| Cat. No. | Item Number | For use with... | Fits Chuck Size |
|----------|-------------|--|-----------------|
| A5 | AY219 | A2, A2E, XA2 Arbors | 13mm - 1/2" |
| A15 | AY221 | A1, A1E, XA1, A10, A10E, XA10, A17-38, A17-38E, XA17-38 Arbors | 9.5mm - 3/8" |

ARBOR ADAPTOR

Allows use of hole saws up to 152mm (6").



| Cat. No. | Item Number | Description |
|----------|-------------|--|
| KA12 | AY255 | Adaptor screws on to arbors with a 1/2" - 20 screw thread and allows use of hole saws up to 152mm (6") |

DUAL HEX ARBOR ADAPTOR



The Starrett Dual Hex Adaptor allows fast, tool free changes between our arbors with a 6.5mm (1/4") or 8.75mm (11/32") Hex Shank, without adjustment of the drill chuck.

- Robust steel construction with hardened centre shaft and nose collar for maximum product life.
- 9.5mm (3/8") Shank fits with other branded arbors.

| Cat. No. | Item Number | For Use with |
|----------|-------------|--|
| A18 | AY284 | A1, A1E, XA1, A4, A4E, XA4, A10, A10E, XA10, A17-38, A17-38E, XA17-38 & Cordless Smooth Cut (CSC) Hole Saws. |

HOLE ENLARGEMENT ARBOR

The KA19 facilitates enlarging diameters by swapping out the pilot drill on your arbor and attaching a saw of the same size as the existing hole. This saw serves as the pilot for the larger diameter saw attached to the arbor.



KA19



Please note: Hole Saws and Arbor are supplied separately.

| Cat. No. | Item Number | Minimum Hole Enlargement |
|----------|-------------|--|
| KA19 | AY228 | 4.7mm (3/16") between pilot hole saw and cutting saw diameter. |

DEBRIS COLLECTOR


NO CLEAN UP - NO DRILL DAMAGE - NO DEBRIS SPREAD

FEATURES:

- The bowl flexes with minimal pressure as the hole is cut
- Significant time savings: no need to mask areas at risk before sawing or clean up afterward
- Keeps dust and debris out of the drill motor
- Suitable for hole saws up to 121mm (4 3/4")
- **STAGE ONE** | Pass the shank of the arbor through the hole at the bottom of the DB2 and attach to the drill in the normal way. Always ensure that the Debris Collector spins freely prior to use.
- **STAGE TWO** | Site the saw for cutting the hole. The Debris Collector can be pulled down to provide a better view of the work area.
- **STAGE THREE** | Drill the hole.
- **STAGE FOUR** | All the dirt and debris from the cut hole is collected inside the Debris Collector.



| Cat No | Item Number | Description |
|--------|-------------|------------------|
| DB2 | AY2835 | Debris Collector |



HOLE SAW CORE EJECTORS

A SIMPLE, BUT HIGHLY EFFECTIVE METHOD OF EJECTING THE CORE FROM A HOLE SAW AFTER COMPLETION OF THE CUT

- Select the appropriate size of ejector for the hole saw.
- Where it is necessary to assemble the two parts of the core ejector, twist the spring on to the ejector plate until it locks in place.
- Twist the spring on the assembled core ejector over the pilot drill until the pilot drill is protruding from the plate.
- Drill the hole.
- **Please note:** Using the core ejector will reduce the saw’s cutting depth. The table below shows the recommended maximum material thickness for each type of hole saw. The core ejector can function at greater thicknesses, but its effectiveness will diminish.



- Assembled core ejector attached to a hole saw.
- After the hole has been drilled, the core can clearly be seen at the end of the pilot drill.

| Cat No | Item Number | Description |
|---------|-------------|---|
| KA8-1 | AY28501 | Core Ejector suitable for 20 - 24mm hole saws |
| KA8-2 | AY28502 | Core Ejector suitable for 25 - 38mm hole saws |
| KA8-3 | AY28503 | Core Ejector suitable for 40 - 60mm hole saws |
| KA8-4 | AY28504 | Core Ejector suitable for 64 - 86mm hole saws |
| # KA8-5 | AY28505 | Core Ejector suitable for 89 - 127mm hole saws |
| # KA8-6 | AY28506 | Core Ejector suitable for 133 - 210mm hole saws |


| Core Ejector Cutting Recommendations | |
|--------------------------------------|--|
| Hole Saw Product Code | Recommended Maximum Material Thickness |
| FCH, DCH, CT | 7mm |
| D and MPH | 5mm |

= MTO - Made to order, may be subject to longer lead times.



PLEASE NOTE

In some applications it is possible that the core may be ejected from the saw at high speed. Please always wear safety glasses and gloves and take extra care if drilling vertically.



HOLE SAW CUTTING SPEED RECOMMENDATIONS (RPM)

BI-METAL

Bi-Metal Fast Cut (FCH) & Deep Cut (DCH) Hole Saws

| Saw Diameter | | Mild Steel | Stainless & Tool Steel | Cast Iron | Brass, Copper & Aluminium | Wood & Plastic |
|--------------|-----------------|------------|------------------------|-----------|---------------------------|----------------|
| mm | inch | | | | | |
| 14 - 25 | 9/16 - 1 | 580 - 350 | 300 - 175 | 400 - 235 | 790 - 470 | 800 - 500 |
| 27 - 51 | 1.1/16 - 2 | 325 - 170 | 160 - 85 | 215 - 115 | 435 - 230 | 500 - 200 |
| 52 - 76 | 2.1/16 - 3 | 165 - 115 | 80 - 55 | 110 - 75 | 220 - 150 | 200 - 150 |
| 79 - 102 | 3.1/8 - 4 | 110 - 85 | 55 - 40 | 70 - 55 | 140 - 110 | 150 - 100 |
| 105 - 127 | 4.1/8 - 5 | 80 - 65 | 40 - 30 | 55 - 25 | 110 - 85 | 100 - 85 |
| 133 - 152 | 5.1/4 - 6 | 55 | 25 | 55 - 25 | 75 | 75 |
| 160 - 210 | 6.5/16 - 8.9/32 | 40 | 20 | 55 - 25 | 60 | 60 |

Bi-Metal Cordless Smooth Cut Hole Saws (CSC)

| Saw Diameter | | Mild Steel | Stainless & Tool Steel | Wood, Plastic & Aluminium |
|--------------|----------------|------------|------------------------|---------------------------|
| mm | inch | | | |
| 16 - 20 | 5/8 - 25/32 | 500 | 230 | 700 |
| 22 - 29 | 7/8 - 1.1/8 | 400 | 185 | 550 |
| 30 - 38 | 1.3/16 - 1.1/2 | 330 | 150 | 450 |

TUNGSTEN CARBIDE TIPPED

Carbide Tipped Hole Saws (CT)

| Saw Diameter | | Cast Iron | Wood & Plastic | Fibreglass | Aluminium | Suspended Floor |
|--------------|---------------|-----------|----------------|------------|-------------|-----------------|
| mm | Inch | | | | | |
| 16 - 25 | 3/4 - 1 | 420 - 320 | 3200 - 2800 | 800 - 500 | 1650 - 1400 | 500 - 400 |
| 29 - 51 | 1.1/8 - 2 | 300 - 160 | 2400 - 1300 | 450 - 200 | 1200 - 600 | 350 - 190 |
| 54 - 79 | 2.1/8 - 3.1/8 | 150 - 100 | 1200 - 850 | 190 - 150 | 580 - 400 | 180 - 120 |
| 83 - 102 | 3.1/4 - 4 | 90 - 80 | 800 - 650 | 140 - 100 | 380 - 300 | 110 - 95 |
| 105 - 127 | 4.1/8 - 5 | 75 - 60 | 620 - 480 | 100 - 85 | 300 - 200 | 90 - 80 |
| 140 - 152 | 5.1/2 - 6 | 50 - 40 | 420 - 350 | 80 - 75 | 180 - 120 | 70 - 60 |

TCT Multi Purpose Hole Saws (MPH)

| Saw Diameter | | All Materials |
|--------------|---------------|---------------|
| mm | Inch | |
| 19 - 27 | 3/4 - 11/16 | 1700 - 1300 |
| 29 - 51 | 1.1/8 - 2 | 1100 - 650 |
| 54 - 76 | 2.1/8 - 3 | 600 - 425 |
| 79-102 | 3.1/8 - 4 | 400 - 325 |
| 111 - 159 | 4.3/8 - 6.1/4 | 300 - 210 |

Carbide Tipped Deep Cut Hole Saws (CTD)

| Saw Diameter | | Mild Steel | Stainless & Steel | Aluminium |
|--------------|-------------------|------------|-------------------|-------------|
| mm | Inch | | | |
| 15 - 21 | 19/32 - 13/16 | 700 - 1000 | 300 - 700 | 1000 - 1400 |
| 22 - 30 | 7/8 - 1.3/16 | 500 - 800 | 200 - 450 | 800 - 1100 |
| 32 - 40 | 1.1/4 - 1.9/16 | 300 - 600 | 175 - 315 | 600 - 850 |
| 45 - 50 | 1.25/32 - 1.31/32 | 200 - 500 | 120 - 225 | 500 - 750 |
| 51 - 60 | 2 - 2.38 | 200 - 400 | 95 - 195 | 400 - 550 |
| 64 - 75 | 2.1/2 - 2.15/16 | 150 - 300 | 80 - 150 | 300 - 450 |
| 80 - 100 | 2.5/32 - 3.15/16 | 100 - 200 | 60 - 120 | 200 - 300 |

TCT Stainless Steel Hole Saws (SM)

| Saw Diameter | | Mild Steel | Stainless & Steel | Cast Iron | Fibreglass |
|--------------|------------------|------------|-------------------|-----------|------------|
| mm | inch | | | | |
| 15 - 25 | 19/32 - 1 | 800 - 640 | 460 - 370 | 420 - 320 | 800 - 500 |
| 26 - 39 | 1.1/32 - 1.17/32 | 590 - 460 | 320 - 270 | 300 - 160 | 450 - 200 |
| 40 - 55 | 1.9/16 - 2.5/32 | 400 - 320 | 220 - 170 | 300 - 160 | 450 - 200 |
| 60 - 85 | 2.3/8 - 3.23/64 | 265 - 200 | 140 - 105 | 150 - 100 | 190 - 150 |
| 90 - 100 | 3.9/16 - 4.23/32 | 175 - 130 | 90 - 65 | 90 - 80 | 140 - 100 |

DIAMOND GRIT

Diamond Grit Hole Saws (D)

| Saw Diameter | | Minimum Speed | Maximum Speed |
|--------------|----------------|---------------|---------------|
| mm | Inch | | |
| 14 - 25 | 9/16 - 1 | 500 | 1000 |
| 27 - 51 | 1.1/16 - 2 | 250 | 500 |
| 52 - 83 | 2.1/16 - 3.1/4 | 150 | 300 |
| 86 - 152 | 3.3/8 - 6 | 100 | 200 |

Diamond Grit Brick and Masonry Dri-Core Drills (BMC)



| Saw Diameter | | Minimum Speed | Maximum Speed |
|--------------|-----------------|---------------|---------------|
| mm | Inch | | |
| 22 - 52 | 9/16 - 1 | 250 | 500 |
| 65 - 78 | 2.9/16 - 3.1/16 | 150 | 300 |
| 102 - 152 | 4 - 6 | 100 | 200 |

Starrett® POWERCALC®

**Starrett's PowerCalc
helps you choose
the right Holesaw
for the job!**



DOWNLOAD NOW FOR FREE



NEW Fast Cut Holesaw 6 packs

**Available in popular sizes:
20mm, 25mm, and 32mm**

- 10% lower unit cost versus purchasing 6 single saws
- Bulk packaging designed for industrial distributors and retail
- Individual barcodes on each holesaw for easy inventory management
- Compact bulk pack design maximizes warehouse space efficiency
- Environmentally friendly packaging, 100% plastic-free

BIG SAVINGS!

WHEN COMPARED TO BUYING 6 SINGLE SAWS

| Cat No | Diameter | QTY (in box) |
|-----------|----------|--------------|
| FCH2532-6 | 20mm | 6 |
| FCH0100-6 | 25mm | 6 |
| FCH0114-6 | 32mm | 6 |





FAST CUT

NEW



DRILL BITS & CHISELS




HIGH SPEED STEEL SPLIT POINT DRILL BITS

Starrett's range of HSS Drill Bits provide users with more agility, efficiency and safety when drilling in different types of surfaces.

The high quality of the materials and the rigorous manufacturing processes, combined with the highest levels of market demand, ensure the quality and performance excellence of Starrett drill bits.

Designed to meet the requirements of professional users. Manufactured to DIN 338 Standards.



- Precision ground cutting edge for fast drilling and perfect finishing
- Maximum accuracy; fast chip removal
- **Split point 135°**: self-centering; easier hole start; less pressure required for penetration; enhanced performance
- **Suitable for**: Alloy steels, carbon steels, cast iron, hardened alloy steels, stainless steel, wood and soft materials
- High quality high speed steel
- Wide and long channels
- Processed by controlled thermal treatment
- Precise cutting geometry
- High fracture resistance
- 135° split point angle (regrinding)
- Reduced deviation of the drill due to split point design
- Metric line according to DIN 338 standard
- Precise concentricity giving high rotational accuracy

KBK13 HSS SPLIT POINT 13PC SET

- 1.5mm x 40mm
- 2mm x 49mm
- 2.5mm x 57mm
- 3mm x 61mm
- 3.2mm x 65mm
- 3.5mm x 70mm
- 4mm x 75mm
- 4.5mm x 80mm
- 4.8mm x 86mm
- 5mm x 86mm
- 5.5mm x 93mm
- 6mm x 93mm
- 6.5mm x 101 mm



| Cat No | Item Description |
|---------|--------------------------|
| KBAR020 | HSS SPLIT POINT 2X49MM |
| KBAR025 | HSS SPLIT POINT 2.5X57MM |
| KBAR030 | HSS SPLIT POINT 3X61MM |
| KBAR035 | HSS SPLIT POINT 3.5X70MM |
| KBAR040 | HSS SPLIT POINT 4X75MM |
| KBAR050 | HSS SPLIT POINT 5X86MM |
| KBAR060 | HSS SPLIT POINT 6X93MM |
| KBAR070 | HSS SPLIT POINT 7X109MM |
| KBAR080 | HSS SPLIT POINT 8X117MM |
| KBAR090 | HSS SPLIT POINT 9X125MM |
| KBAR100 | HSS SPLIT POINT 10X133MM |
| KBAR120 | HSS SPLIT POINT 12X151MM |
| KBK13 | HSS SPLIT POINT 13PC SET |



SDS PLUS SHANK 2 POINTS DRILL BIT

Superior strength drill body with specialised heat treatment to withstand the most demanding of applications, high performance carbide tips with a two channel design featuring a unique chip removal/breakage accelerator.



KBPSK09 SDS PLUS 2 POINTS 9PC SET


- 5mm x 110mm
- 5.5mm x 110mm
- 5.5mm x 160mm
- 6mm x 110mm
- 6mm x 160mm
- 7mm x 110mm
- 7mm x 160mm
- 8mm x 160mm
- 10mm x 160mm



- Special flute geometry designed to deliver cutting speed and maximum debris removal;
- 130 degree tip angle - fast drilling with hammer action
- High quality carbide tips: consistent performance
- 2 cutting edges with 1 centering point

| Cat No | Item Description |
|----------|-----------------------------|
| KBPS04B | SDS PLUS 2 POINTS 4X160MM |
| KBPS05A | SDS PLUS 2 POINTS 5X110MM |
| KBPS05B | SDS PLUS 2 POINTS 5X160MM |
| KBPS055A | SDS PLUS 2 POINTS 5.5X110MM |
| KBPS055B | SDS PLUS 2 POINTS 5.5X160MM |
| KBPS06A | SDS PLUS 2 POINTS 6X110MM |
| KBPS06B | SDS PLUS 2 POINTS 6X160MM |
| KBPS06C | SDS PLUS 2 POINTS 6X210MM |
| KBPS065B | SDS PLUS 2 POINTS 6.5X160MM |
| KBPS065C | SDS PLUS 2 POINTS 6.5X210MM |
| KBPS07A | SDS PLUS 2 POINTS 7X110MM |
| KBPS07B | SDS PLUS 2 POINTS 7X160MM |
| KBPS07C | SDS PLUS 2 POINTS 7X210MM |
| KBPS08B | SDS PLUS 2 POINTS 8X160MM |
| KBPS08C | SDS PLUS 2 POINTS 8X210MM |
| KBPS10B | SDS PLUS 2 POINTS 10X160MM |
| KBPS10C | SDS PLUS 2 POINTS 10X210MM |
| KBPS10E | SDS PLUS 2 POINTS 10X460MM |
| KBPS12B | SDS PLUS 2 POINTS 12X160MM |
| KBPS16C | SDS PLUS 2 POINTS 16X210MM |
| KBPSK09 | SDS PLUS 2 POINTS 9PC SET |





SDS PLUS SHANK 4 POINTS DRILL BIT

Superior strength drill body with specialised heat treatment to withstand the most demanding of applications; 4 high performance carbide tips with a cross-head design.



KBPXK05

SDS PLUS 4 POINTS 5PC SET

- 5mm x 160mm
- 5.5mm x 160mm
- 6mm x 160mm
- 8mm x 160mm
- 10mm x 160 mm

- Special flute geometry designed to deliver cutting speed and maximum debris removal
- 130 degree tip angle – accurate and fast drilling with hammer action
- High quality carbide tips: consistent performance
- 4 cutting edges with 1 centering point
- 4 vertical debris removal channels

| Cat No | Item Description |
|---------|----------------------------|
| KBPX12D | SDS PLUS 4 POINTS 12X260MM |
| KBPX12E | SDS PLUS 4 POINTS 12X460MM |
| KBPX14D | SDS PLUS 4 POINTS 14X260MM |
| KBPX14E | SDS PLUS 4 POINTS 14X460MM |
| KBPX16D | SDS PLUS 4 POINTS 16X260MM |
| KBPX16E | SDS PLUS 4 POINTS 16X460MM |
| KBPX20E | SDS PLUS 4 POINTS 20X460MM |
| KBPX25E | SDS PLUS 4 POINTS 25X460MM |
| KBPXK05 | SDS PLUS 4 POINTS 5PC SET |





SDS PLUS CHISEL SET

SDS Plus chisels designed for demolition and stripping on masonry and concrete materials.



- Suitable for both corded and cordless drills with hammer action
- Precision ground chisel edge with special hardening process delivering effective and efficient results
- Strong and durable in the toughest applications

| Cat No | Item Description |
|--------|-------------------------|
| KCPK03 | SDS PLUS CHISEL 3PC SET |



KCPK03
SDS PLUS CHISEL 3PC SET

- Wide chisel 250mm
- Flat chisel 250mm
- Pointed chisel 250mm



FLAT WOOD DRILL BITS - HEX SHANK

Fast and clean cutting on all wood, with a huge reduction in breakout around the hole and excellent tool life.



- Twin spurs reduce the breakout and deliver clean holes
- Precision ground face
- 6.35mm (1/4") hexagonal shank suitable to fit impact machines
- Precision ground tip enabling accurate and fast start in materials
- Reduction in heat from cutting head design
- Specialised heat treatment to increase tool life

| Cat No | Item Description |
|---------|------------------------|
| KFWD12A | FLAT WOOD HEX 12X152MM |
| KFWD16A | FLAT WOOD HEX 16X152MM |
| KFWD20A | FLAT WOOD HEX 20X152MM |
| KFWD25A | FLAT WOOD HEX 25X152MM |
| KFWD32A | FLAT WOOD HEX 32X152MM |
| KFWDK08 | FLAT WOOD HEX 8PC SET |

KFWDK08
FLAT WOOD HEX 8PC SET

- | | |
|----------------|----------------|
| • 12mm x 152mm | • 22mm x 152mm |
| • 16mm x 152mm | • 25mm x 152mm |
| • 18mm x 152mm | • 28mm x 152mm |
| • 20mm x 152mm | • 32mm x 152mm |



HSS RECOMMENDED RPM PER DRILL AND MATERIAL TYPE

| Recommended RPM per drill diameter and material type | | | | | | |
|--|------------|--------------------|----------------|-----------|--------|-------|
| Drill Diameter | Mild Steel | Free-Cut Stainless | Grey Cast Iron | Aluminium | Copper | Brass |
| 2 | 3501 | 2228 | 5252 | 6366 | 6366 | 6366 |
| 2.5 | 2801 | 1783 | 4202 | 5093 | 4093 | 5093 |
| 3 | 2334 | 1485 | 3501 | 4244 | 4244 | 4244 |
| 3.2 | 2122 | 1350 | 3183 | 3845 | 3858 | 4010 |
| 3.5 | 2000 | 1273 | 3001 | 3638 | 3638 | 3858 |
| 4 | 1750 | 1114 | 2626 | 3183 | 3183 | 3183 |
| 4.5 | 1550 | 990 | 2401 | 2829 | 2829 | 2829 |
| 4.8 | 1500 | 925 | 2200 | 2620 | 2650 | 2625 |
| 5 | 1400 | 891 | 2101 | 2546 | 2546 | 2546 |
| 5.5 | 1273 | 810 | 1910 | 2315 | 2315 | 2315 |
| 6 | 1167 | 743 | 1751 | 2122 | 2122 | 2122 |
| 6.5 | 1077 | 686 | 1616 | 1959 | 1959 | 1959 |
| 7 | 1000 | 637 | 1501 | 1819 | 1819 | 1819 |
| 8 | 875 | 557 | 1313 | 1592 | 1592 | 1592 |
| 9 | 778 | 495 | 1167 | 1415 | 1415 | 1415 |
| 10 | 700 | 446 | 1050 | 1273 | 1273 | 1273 |
| 12 | 584 | 371 | 875 | 1107 | 1107 | 1061 |

LUBRICATION WHEN USING DRILLS

- It is recommended that lubrication is used as the drilling process produces friction between the drill bit and the material being drilled, this causes wear on the drill bit.
- When lubrication is used it will extend the life of the drill, and help to maintain the sharp edge and reduce the risk of breakage.

SHARPENING DRILL BITS

- It is possible to sharpen drill bits - care should be taken in ensuring the correct cutting angles are maintained during the re sharpening process.

WANT TO KNOW MORE?

Scan the QR code to watch the drill bits & chisels in action





NEW PRODUCT DISPLAY SOLUTIONS

Say goodbye to scattered displays with Starrett's new product display solutions. Designed specifically with popular trade professions in mind, our dedicated stands ensure that your customers find what they need easily.

Included are profiles for the following sectors:

- Electrical
- Plumbing
- Engineering
- Construction



Contact our UK Sales team today to explore how this solution can improve your showroom and sales.

sales@starrett.co.uk



**VIEW THE DIGITAL
CATALOGUE**



HACKSAW BLADES & FRAMES

Starrett® bi-metal unique™ *saw technology*

Starrett Unique™ Technology is distinct from other methods of producing bi-metal saw blades. It joins two strips of high-speed steel wire to backing steel using solid-state diffusion bonding.

ADVANTAGES

- **Massive increase in resistance to tooth breakage and fracture.** Unique™ Blades feature **170% more weld contact area** than standard bi-metal blades as a result of the solid state diffusion bonding process. **This ensures exceptionally strong teeth.**
- **SMOOTHER, FASTER CUTS** - Multi Edge Performance and the Split Chip Advantage generate thinner chips which are more quickly and easily removed from the saw cut. In tests, Unique™ blades proved to be an average of **35% faster than directly competing products.**
- **LONGER BLADE LIFE** - The exceptionally strong teeth, Multi Edge Performance and Split Chip Advantage ensure that Unique™ blades last an average of **35% longer than competing blades.**
- **LOWER COST PER CUT** - The increase in resistance to tooth breakage and fracture, smoother, faster cuts and longer blade life all combine to guarantee one simple benefit - lower cost per cut.

Starrett Bi-Metal Unique™ Saw Technology is currently available in our Safe-Flex™ Hand Hacksaw Blades, Unified Shank™ Jigsaw Blades and Intenss Bandsaw Blades.

Starrett® / / / bi-metal unique® / / / Safe-Flex® Made in Brazil BS1224 300mm (12") 24T

BI-METAL UNIQUE™ HAND HACKSAW BLADES

SAFE-FLEX™ HIGH SPEED STEEL BLADES

A patented solid state diffusion process produces the industry's most advanced bi-metal hacksaw blade.



FEATURES

- Massive increase in tooth strength and reduction in tooth breakage and fracture when compared against traditional bi-metal blades.
- Excellent for interrupted cuts in cramped places or where the blade is subject to bending or twisting stresses.

| Dimensions Length x Width x Thickness | TPI (25mm) |
|---|--------------------|
| 300mm x 13mm x 0.65mm 12" x 1/2" x .025" | 18 |
| | 12" x 1/2" x .025" |
| | 32 |

| 2 Blades on card | |
|------------------|-------------|
| Cat No | Item Number |
| KBS1218-2 | AV823 |
| KBS1224-2 | AV827 |
| KBS1232-2 | AV8325 |

| 10 Blade Tube Pack | |
|--------------------|-------------|
| Cat No | Item Number |
| KBS1218-10 | AV8235 |
| KBS1224-10 | AV8315 |
| KBS1232-10 | AV8326 |

| 50 Blade Visual Pack | |
|----------------------|-------------|
| Cat No | Item Number |
| KBS1218-50 | AV82352 |
| KBS1224-50 | AV8317 |
| KBS1232-50 | AV83262 |

| 50 Blade Tube Pack | |
|--------------------|-------------|
| Cat No | Item Number |
| BS1218 | AV765 |
| BS1224 | AV767 |
| BS1232 | AV769 |

| 100 Blade Visual Pack | |
|-----------------------|-------------|
| Cat No | Item Number |
| KBS1218-100 # | AV823535 |
| KBS1224-100 | AV8320 |
| KBS1232-100 | AV83265 |

REDSTRIPE® HAND HACKSAW BLADES

SOLID HIGH SPEED STEEL BLADES



FEATURES

- Ideal when the blade is not subject to bending and twisting stresses.
- Uniformly hardened blade holds the edge when cutting hard-to-machine alloys, maintaining the straightness of the cut.

| Dimensions Length x Width x Thickness | TPI (25mm) |
|---|---------------|
| 300mm x 13mm x 0.65mm 12" x 1/2" x .025" | 18 |
| | 24 |
| | 32 |

| 2 Blades on card | |
|------------------|-------------|
| Cat. No. | Item Number |
| KRS1218-2 # | AV822 |
| KRS1224-2 # | AV826 |
| KRS1232-2 # | AV8322 |

| 10 Blade Tube Pack | |
|--------------------|-------------|
| Cat. No. | Item Number |
| KRS1218-10 # | AV8225 |
| KRS1232-10 # | AV8323 |

| 50 Blade Tube Pack | |
|--------------------|-------------|
| Cat. No. | Item Number |
| RS1218 | AV685 |
| RS1224 | AV687 |
| RS1232 | AV689 |

| 50 Blade Visual Pack | |
|----------------------|-------------|
| Cat. No. | Item Number |
| KRS1218-50 # | AV82272 |
| KRS1224-50 # | AV8307 |

= MTO - Made to order, may be subject to longer lead times.

GREY-FLEX® HAND HACKSAW BLADES

HIGH CARBON STEEL BLADES

These all-purpose blades are an economical alternative when cutting mild steel, copper, brass, aluminium and other similar materials. The blades feature an all carbon construction with a hardened cutting edge and flexible back.



| 50 Blade Tube Pack | | | |
|--------------------|-------------|---|---------------|
| Cat. No. | Item Number | Dimensions Length x Width x Thickness | TPI (25mm) |
| GF1218 | AV805 | 300mm x 13mm x 0.65mm 12" x 1/2" x .025" | 18 |
| GF1224 | AV807 | | 24 |
| GF1232 | AV809 | | 32 |


HACKSAW FRAMES

K140 CLOSED GRIP

Light duty hacksaw frame accepting 300mm (12") blades. The blades can be tensioned by a single wing nut in the front of frame.

FEATURES

- 300mm (12") Starrett Bi-Metal Unique, high speed steel Safe-Flex hacksaw blade included.




| Cat. No. | Item Number | Description |
|----------|-------------|--|
| K140 | BS535 | Non-Adjustable Light Duty Hacksaw Frame, Closed Grip |

Starrett® EXACT® PLUS K145 CLOSED GRIP - HIGH TENSION

Heavy-Duty Hacksaw Frame with Closed Grip. A professional quality, high-tension hack saw frame that is easy to use with an efficient adjustment lever.

FEATURES

- 300mm (12") Starrett Bi-Metal Unique, high speed steel Safe-Flex hacksaw blade included.
- The handle is covered by rubber overmould for comfortable grip.
- Six turns of the tensioning handle will tension the blade to the recommended point.



| Cat. No. | Item Number | Description |
|----------|-------------|--|
| K145 | BS550 | High-Tension Heavy-Duty Hacksaw Frame, Closed Grip |

146 HOBBY SAW



| Cat. No. | Item Number |
|----------|-------------|
| # 146 | BS555 |

= MTO - Made to order, may be subject to longer lead times.

Ideal for lightweight cutting, particularly suitable for cutting in restricted places, unreachable by conventional hacksaw frames. The Hobby Saw accepts 250mm or 300mm (10" or 12") blades.

HACKSAW FRAMES

K147

BI-METAL COMPASS SAW

The ideal tool for cutting plasterboard, featuring a heavy-duty, variable pitch, bi-metal blade to cut most materials and provide an extra-long cutting life.

FEATURES

- 225mm (9") Starrett Bi-Metal Unique Blade included.
- Heavy duty plastic handle for ideal comfort and the best cutting leverage provides easy cutting.
- The blade rotates full 360° to easily cut at any angle.



| Cat. No. | Item Number | Description |
|-------------|-------------|-------------------------------------|
| # K147 | BS562 | Compass Saw, Bi-Metal |
| BT91014DT-2 | BT91014DT-2 | Replacement blade for K147 (2 pack) |

= MTO - Made to order, may be subject to longer lead times.

K148

PVC SAWS

Used for cutting PVC and ABS materials. Also used for cutting plasterboard, plywood and general-purpose cutting.

FEATURES

- It is shipped with a 300mm (12") or 450mm (18") blade length.
- Featuring cast aluminium handle.



| Cat. No. | Item Number | Description |
|-----------|-------------|-------------------------------|
| # K148-12 | BS572 | Handle with 300mm (12") Blade |
| # K148-18 | BS577 | Handle with 450mm (18") Blade |

= MTO - Made to order, may be subject to longer lead times.

REPLACEMENT BLADE FOR 148

- Used for cutting plasterboard, plywood and general purpose cutting.

| Cat. No. | Item Number | Dimensions |
|----------|-------------|-------------|
| # PVC-12 | BS575 | 300mm(12") |
| # PVC-18 | BS582 | 450mm (18") |

= MTO - Made to order, may be subject to longer lead times.

149

TUBULAR HACKSAW FRAME

Knurled, closed, high-impact plastic handle ensures convenience and firmness in handling. It only allows the use of 300mm (12") saws, which can be mounted to cut in any of the four directions, tensioned by a butterfly nut.

FEATURES

- Light arch with closed handle.
- Greater robustness and rigidity.
- High-impact plastic knurled handle.
- Ensures convenience and firmness in handling.

| Cat. No. | Item Number | Depth |
|----------|-------------|---------------|
| # 149 | BS597 | 95mm (3.3/4") |

= MTO - Made to order, may be subject to longer lead times.





JIGSAWS

Starrett® bi-metal unique™ saw technology





Starrett Unique™ Technology is distinct from other methods of producing bi-metal saw blades. It joins two strips of high-speed steel wire to backing steel using solid-state diffusion bonding.

ADVANTAGES

- Massive increase in resistance to tooth breakage and fracture. Unique™ Blades feature 170% more weld contact area than standard bi-metal blades as a result of the solid state diffusion bonding process. This ensures exceptionally strong teeth.
- Smoother, faster cuts. Multi Edge Performance and the Split Chip Advantage generate thinner chips which are more quickly and easily removed from the saw cut. In tests, Unique™ blades proved to be an average of 35% faster than directly competing products.
- Longer blade life. The exceptionally strong teeth, Multi Edge Performance and Split Chip Advantage ensure that Unique™ blades last an average of 35% longer than competing blades.
- Lower cost per cut. The increase in resistance to tooth breakage and fracture, smoother, faster cuts and longer blade life all combine to guarantee one simple benefit - lower cost per cut.

Starrett Bi-Metal Unique™ Saw Technology is currently available in our Safe-Flex™ Hand Hacksaw Blades, Unified Shank™ Jigsaw Blades and Intenss Bandsaw Blades.



BI-METAL UNIQUE™ SAW TECHNOLOGY

THE BONDING PROCESS

- Two strips of high speed steel wire are joined to the backing steel in a solid phase.

THE CONTACT AREA

- 1. Traditional bi-metal blades feature one high speed steel wire, electron beam welded to the backing material.
- 2. Unique™ blades feature two wires, joined laterally to the backing steel in a solid phase, providing 170% more weld contact area.

MULTI EDGE PERFORMANCE

- After initial use the soft backing material in the centre of the blade will wear away, forming a groove which acts as a natural chip breaker, and providing the blade with multiple cutting edges - Multi Edge Performance

SPLIT CHIP ADVANTAGE

- The multiple cutting edges produce thinner chips that are more easily removed from the saw cut - The Split Chip Advantage.

Starrett® dual cut™

CLEAN CUT ON BOTH SIDES OF THE MATERIAL



dual cut
Made for
WOOD

DUAL CUT™ JIGSAW BLADES CUT SOFT & HARD WOOD, MDF, FORMICA & ACRYLIC

OUR UNIFIED SHANK® FITS ALL WELL KNOWN JIGSAW MACHINES

OUR BI-METAL UNIQUE® SAW TECHNOLOGY JIGSAW BLADES WILL LAST
25% LONGER ON AVERAGE COMPARED TO EXISTING BI-METAL BLADES



dualcut™

CLEAN CUT ON BOTH SIDES OF THE MATERIAL

DUAL CUT JIGSAW BLADES UNIFIED SHANK

For the ultimate surface finish on both sides of the material being cut, Starrett Dual Cut™ Jigsaw Blades are the ideal solution. The patented tooth design allows these blades to cut on both the upstroke and downstroke, preventing breakout and minimizing surface chipping. Made with Starrett's Bi-Metal Unique™ Saw Technology, they offer 170% greater resistance to tooth breakage, longer life, and lower cost per cut than other blades.

FEATURES

- Particularly suited to cutting soft and hard wood, MDF, acrylic, Formica, melamine, and other coated materials
- Available in standard or scroll cut format
- Lasts 25% longer than other jigsaw blades
- Fast, precise, burr-free cutting
- Dual cutting action
- 170% greater resistance to tooth breakage
- Unified shank



OUR JIGSAW BLADES LAST 25% LONGER*
STRONGER WITH 170% MORE WELD CONTACT
FASTER, SMOOTHER & MORE PRECISE CUTS**
UNBREAKABLE***

**PERFECT FINISH
ON BOTH SIDES! (A) (B)**

* On average when compared to existing bi-metal blades.

** With our Multi Edge Performance & Split Chip Advantage.

*** During normal use.

BI-METAL UNIQUE™ JIGSAW BLADES

UNIFIED SHANK™ - FITS ALL WELL KNOWN JIGSAW MACHINES

Starrett Unified Shank™ Jigsaw Blades incorporate Starrett's exclusive Bi-Metal Unique™ process technology. Blades produced using this process resist breakage, cut faster, and last longer than conventional saws. Unified Shank™ Jigsaw Blades are available in twin packs for a limited range, five-blade packs, and various assortment packs.



Competitors Jigsaw Blade Conversions**

| Cat. No. | Item Number | Blade / Application Type | TPI (25mm) | Cutting Thickness | Blades per Pack | Blade Dimensions* Length x Width x Thickness | Metabo | Makita | Lenox | Bosch |
|----------------------------|-----------------|---|------------|-------------------|-----------------|--|--------|--------------|----------------|------------------|
| WOOD CUTTING | BU2DCS-2 SA385 | Dual Cut™ Straight + Curved Cuts Smooth Finish Top & Bottom | 9-19 | 4 - 20mm | 2 | 50mm x 5mm x 1.3mm (2" x 3/16" x .050") | --- | BR-13 | --- | T101AOF |
| | BU3DC-2 SA384 | Dual Cut™ Scroll + Curved Cuts Smooth Finish Top & Bottom | 9-19 | 6 - 30mm | 2 | 75mm x 8mm x 1.5mm (3" x 5/16" x .060") | --- | --- | --- | T101BIF |
| | BU36T SA300 | Tapered Blade - Clean Cuts | 6 | 30 - 45mm | 5 | 75mm x 7.5mm x 1.3mm (3" x 5/16" x .050") | --- | --- | 456S 456J | --- |
| | BU36 SA305 | Fast Straight Cuts | 6 | 30 - 45mm | 5 | | 23976 | B-16 B-17 | 406S 486J | T144DF |
| | BU38 SA315 | Fast Straight Cuts | 8 | 30 - 45mm | 5 | | 23639 | B-25 | --- | T127D |
| | BU310T SA320 | Tapered Blade - Clean Cuts | 10 | 6 - 30mm | 5 | | 23975 | B-19 | 450S | T101BF |
| | BU310DT SA325 | Tapered Downstroke Cuts | 10 | 6 - 30mm | 5 | | 23686 | --- | 450SR | T101BRF |
| | BU46 SA310 | Fast Straight Cuts | 6 | 45 - 60mm | 5 | 100mm x 9.5mm x 1.3mm (4" x 3/8" x .050") | --- | --- | 686S 686J | T301DL |
| | BU56 SA380 | Straight Fast & Thick Cuts | 6 | 60 - 100mm | 5 | 125mm x 9.5mm x 1.3mm (5" x 3/8" x .050") | 23980 | --- | 686J | T344DF |
| | BU214 SA335 | Wood, Metal & Plastic | 14 | 3 - 30mm | 5 | 50mm x 7.5mm x 1mm (2" x 5/16" x .040") | 23973 | B-23 | 314S | T118BF U118BF |
| | BU218 SA345 | Thin Metal | 18 | 3 - 30mm | 5 | 50mm x 9.5mm x 1mm (2" x 3/8" x .040") | 23972 | --- | 318S | T118AF |
| MULTI-PURPOSE | BU214S SA340 | Scroll Cuts | 14 | 3 - 30mm | 5 | 50mm x 4.5mm x 1mm (2" x 3/16" x .040") | 23970 | B-26 | 416SC 416JC | T118BOF |
| | BU41014 SA330 | Straight Cuts | 10-14 | 4.8 - 60mm | 5 | 100mm x 9.5mm x 1mm (4" x 3/8" x .040") | 23979 | --- | --- | T123X T318B |
| | BU418 SA350 | Straight Cuts - Wood & Metal | 18 | 3.2 - 60mm | 5 | | --- | --- | 518S 518J | T318BF |
| | CTT46-2 CTT46-2 | Straight Cuts - Fibreglass & Abrasive Materials | 6 | 80mm | 2 | 130mm x 8mm x 1.26 | --- | --- | --- | --- |
| | BU224 SA355 | Thin Metal | 24 | 1.6 - 3.2mm | 5 | 50mm x 7.5mm x 1mm (2" x 5/16" x .040") | 23971 | B-22 B-27 | 324S | T118AF |
| METAL CUTTING | BU232 SA370 | Thin Curved Cuts | 32 | 0.9 - 1.6mm | 5 | 50mm x 7.5mm x 1mm (2" x 5/16" x .040") | 23636 | B-24 | 332S | T118G U118G |
| | BU224S SA360 | Scroll Cuts | 24 | 1.6 - 3.2mm | 5 | 50mm x 4.5mm x 1mm (2" x 3/16" x .040") | 23695 | --- | 320SC 320JC | T101AOF |
| | BU424 SA365 | Straight Cuts | 24 | 1.6 - 3.2mm | 5 | 100mm x 9.5mm x 1mm (4" x 3/8" x .040") | 23978 | --- | 424S 424J | T318AF |
| | CTU218-2 SA4016 | Carbide Blade - Stainless Steel Cutting | 18 | 2 - 5mm | 2 | 50mm x 7.5mm x 1mm (2" x 5/16" x .040") | 23663 | --- | --- | T118EHM |
| MULTI-PURPOSE CARBIDE GRIT | CTU224-2 SA4018 | Carbide Blade - Stainless Steel Cutting | 24 | 1.5 - 3mm | 2 | 50mm x 7.5mm x 1mm (2" x 5/16" x .040") | 23662 | --- | --- | T118AHM |
| | BU230X-2 SA374 | Carbide Grit Blade - Abrasive Materials | Coarse CG | - | 2 | 50mm x 7.5mm x 1mm (2" x 5/16" x .040") | | | | |
| | BU230X SA375 | Carbide Grit Blade - Abrasive Materials | Coarse CG | - | 5 | | | | | |

* Length dimension references tooth bearing section of jigsaws. The total length, including blade shank, is approximately 25mm (1") longer.

** Not directly comparable blades.






































2 packs, 20 packs & 100 packs are also available on request for most jigsaw blades in the range - but only whilst stocks last - please ask for details.

ASSORTMENT PACKS

WITH UNIFIED SHANK™

| Cat. No. | Item Number | Blades per Pack | Description |
|----------|-------------|-----------------|--|
| BU1 | SA390 | 5 | Wood Cutting Assortment Pack: Includes one each: BU36, BU46, BU38, BU310T and BU214S |
| BU2 | SA392 | 5 | Multi-Purpose Assortment Pack: Includes one each: BU46, BU310T, BU214, BU224S and BU232 |
| BU3 | SA394 | 5 | Metal Cutting Assortment Pack: Includes one each: BU41014, BU214, BU224, BU224S and BU232 |
| BU4 | SA395 | 19 | Multi-Purpose Assortment Pack. Includes one each: BU36T, BU36, BU46, BU56, BU38, BU310T, BU310DT, BU2DCS, BU3DC, BU41014, BU214, BU214S, BU218, BU418, BU230X, BU224, BU224S, BU424, BU232 |



| WOOD CUTTING BLADES | | | | | | | | | | MULTI USE BLADES | | | | | | METAL CUTTING BLADES | | | | | | |
|--|---|---|---|---|---|---|---|---|---|---|---|---|--|---|---|---|---|---|---|---|---|---|
| Exclusive Unified Shank Jigsaw Blades |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| Cutting length | 57 | 75 | 75 | 75 | 75 | 100 | 125 | 75 | 75 | 100 | 50 | 50 | 50 | 100 | 50 | 1.3 | 50 | 50 | 100 | 50 | 55 | 55 |
| Thickness | 1.3 | 1.3 | 1.3 | 1.3 | 1.3 | 1.3 | 1.3 | 1.3 | 1.3 | 1.0 | 1.0 | 1.0 | 1.0 | 1.0 | 1.0 | 1.3 | 1.0 | 1.0 | 1.0 | 1.0 | 1.0 | 1.0 |
| Cutting Direction | ↕ | ↕ | ↑ | ↑ | ↑ | ↑ | ↑ | ↑ | ↓ | ↑ | ↑ | ↑ | ↑ | ↑ | ↕ | ↑ | ↑ | ↑ | ↑ | ↑ | ↑ | ↑ |
|  0.9-1.6mm | | | | | | | | | | | | | | | | | | | | ✓ | ✓ | ✓ |
|  1.6-3.2mm | | | | | | | | | | ✓ | | | | | | | ✓ | ✓ | ✓ | | ✓ | ✓ |
|  3.2-4.8mm | | | | | | | | | | ✓ | | | ✓ | ✓ | | | | | | | | |
|  4.8-6.4mm | | | | | | | | | | ✓ | ✓ | ✓ | | | | | | | | | | |
| Soft | ★★ | ★★ | | ★★ | ★ | ★ | ★ | ★★ | ★★ | ★ | ★ | ★ | ★ | ★ | | ★★ | | | | | | |
| Hard | ★★ | ★★ | ★ | ★★ | ★ | ★ | ★ | ★★ | | ★ | ★ | ★ | | | | ★★ | | | | | | |
|  6-30mm | ★ | ★★ | | | ★ | | | ★★ | ★★ | ★ | ★ | ★ | ★ | ★ | | | | | | | | |
|  30-45mm | | | ★ | ★★ | ★ | | | ★★ | ★ | ★ | | | | | | | | | | | | |
| 45-60mm | | | | | | ★ | ★ | | | ★ | | | | | | | | | | | | |
| 60-100mm | | | | | | | ★ | | | | | | | | | | | | | | | |
|  3-12mm | | | | | | | | | | | ★ | ★ | | | | | | | | | | |
| 12-25mm | | | | | | | | ★★ | | ★ | | | | | | | | | | | | |
| Contour cutting | ✓ | | | | | | | | | | | ✓ | | | | | | ✓ | | | | |
| Curved cutting | | ✓ | ✓ | ✓ | ✓ | | | ✓ | ✓ | | ✓ | ✓ | ✓ | | ✓ | | ✓ | | | ✓ | | |
| Straight cutting | | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | | ✓ | | | | ✓ | ✓ | ✓ | | | ✓ | | ✓ | ✓ |
| Fast Cutting | | | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | | | | | | | ✓ | ✓ | | | | | | |
| Clean Cutting | | | | ✓ | | | | ✓ | ✓ | | | | | | | | | | | | | |
|  Acrylic | ✓ | ✓ | | ✓ | | | | ✓ | | | ✓ | ✓ | | | | ✓ | | | | | | |
|  Ceramic | | | | | | | | | | | | | | | ✓ | | | | | | | |
|  Fibreglass | | | | | | | | | | | | | | | ✓ | ✓ | | | | | | |
|  Formica | ✓ | ✓ | | ✓ | | | | ✓ | ✓ | | | | | | | | | | | | | |
|  Plaster | | | | | | | ✓ | | | | | | | | | ✓ | | | | | | |
|  MDF | ✓ | ✓ | | | | | | ✓ | ✓ | | | | ✓ | | ✓ | | ✓ | | | | | |
|  Suspended Floors | | | | | | | | | | | | | | ✓ | | | | | ✓ | | | |
|  Tubes and profiles | | | | | | | | | | ✓ | | | | ✓ | | | | | ✓ | | | |
| Cutting Performance | | | | | | | | | | Note: Use of a coolant is recommended for all metal cutting | | | | | | | | | | | | |
| Excellent | ★★ | | Satisfactory | | | | | ★ | | | | | | | | | | | | | | |

NEW

CARBIDE TIPPED JIGSAW BLADES

Designed for quick and precise cuts on tough and abrasive materials, this blade ensures an extended lifespan compared to standard options. Plus, enjoy smooth and efficient cutting that not only reduces trigger time but also minimises operator exposure to harmful vibrations.

FEATURES & BENEFITS:

- Unified shank to fit a variety of machines
- 130mm x 8mm x 1.26 x 6 TPI (4mm spacing)
- 100mm tooth bearing length
- Equivalent to T341HM
- Up to 80mm cutting ability
- Precision ground solid carbide tips
- Straight cuts with an upward stroke

IDEAL FOR CUTTING:

- Plaster Board
- Cement Board
- Fibre Glass (including marine grades)
- Carbon Fibre
- Graphite
- MDF
- Hard Woods
- Composite Decking Materials
- GRP Biax
- Aluminium

| Item Number | TPI | Blades in Pack |
|-------------|----------|----------------|
| CTT46-2 | BT96-5 | 2 |
| # CTT46-250 | 6T PK250 | 250 |

- Made to order, may be subject to longer lead times.



No Plastic - Environmentally Friendly Packaging!





RECIPROCATING SAW BLADES

NEW

EX POWER
BI-METAL

**INCREASED
PRODUCTIVITY**



FIND OUT MORE



**NEW TIP
DESIGN**

**NEW TOOTH
DESIGN**

**BEST
PERFORMANCE**

**HIGH
DURABILITY**


**CUTS 3x MORE
THAN BEFORE**

FEATURES

- Bi-metal steel blade.
- Highly resistant to breakage.
- More accurate cuts.
- Cuts in hard-to-reach places.
- One blade model for each different application - Wood, Metal, Multi Purpose and King Cut™.

SCROLL 

STRAIGHT 

TAPERED 




RECIPROCATING SAW BLADES FOR METAL

Starrett's 3X POWER Bi-Metal blade triples life and cutting speed over previous models, offering unmatched market value. Its straight and scroll designs excels in tough, tip-driven cuts, perfect for cordless saws cutting metal sheets and sections.

FEATURES

- Designed for metal cutting
- Straight and scroll blade formats
- Ideal for cordless saw machines
- Unbreakable; providing safety and reliability
- Optimised tooth pitch for a reduction in vibration, offering cleaner cuts and less fatigue
- Reinforced Shank



SCAN TO
WATCH VIDEOS



AVAILABLE IN



Available In Various Tooth Pitches
- For a variety of applications

Reinforced Shank
- To Avoid Breakage



| | Length x Width x Thickness | | TPI (25mm) | Catalogue Number | Item Number | Pack Size |
|-------|----------------------------|------------------|---------------|---------------------|----------------|--------------|
| | mm | inch | | | | |
| METAL | 102 x 19 x 0.89 | 4 x 3/4 x 0.035 | 14 | B414-5 | SA15932 | 5 |
| | 102 x 19 x 0.89 | 4 x 3/4 x 0.035 | 18 | B418-5 | SA15942 | 5 |
| | 102 x 19 x 0.89 | 4 x 3/4 x 0.035 | 24 | B424-5 | SA15952 | 5 |
| | 102 x 8 x 0.89 | 4 x 5/16 x 0.035 | 24 | SB424-5 | SA27185 | 5 |
| | 102 x 19 x 0.89 | 4 x 3/4 x 0.035 | 14 | B614-5 | SA186 | 5 |
| | 152 x 19 x 0.89 | 6 x 3/4 x 0.035 | 18 | B618-5 | SA191 | 5 |
| | 152 x 19 x 0.89 | 6 x 3/4 x 0.035 | 24 | B624-5 | SA196 | 5 |
| | 203 x 19 x 0.89 | 8 x 3/4 x 0.035 | 18 | B818-5 | SA2677 | 5 |






RECIPROCATATING SAW BLADES

MULTI-PURPOSE

Starrett's 3X POWER Bi-Metal blade triples life and cutting speed over previous models, offering unmatched market value. It has straight and tapered blade designs which excel in cutting a range of multi-materials including metal, wood, plastic, and any wood & metal combo including nail embedded wood.

FEATURES

- Designed for multi-purpose cutting
- Straight and scroll blade formats
- Ideal for cordless saw machines
- Unbreakable; providing safety and reliability
- Optimised tooth pitch for a reduction in vibration, offering cleaner cuts and less fatigue
- Reinforced Shank



SCAN TO
WATCH VIDEOS



AVAILABLE IN

- STRAIGHT
- TAPERED

Available In Various Tooth Pitches
- For a variety of applications

Reinforced & Unified Shank
- To Avoid Breakage



| | Length x Width x Thickness | | TPI (25mm) | Catalogue Number | Item Number | Pack Size |
|-------|----------------------------|------------------|---------------|---------------------|----------------|--------------|
| | mm | inch | | | | |
| MULTI | 152 x 19 x 1.27 | 6 x 3/4 x 0.050 | 6-10 | BT6610-5 | SA2266 | 5 |
| | 152 x 19 x 0.89 | 6 x 3/4 x 0.035 | 10 | B610-5 | SA181 | 5 |
| | 228 x 19 x 1.27 | 9 x 3/4 x 0.050 | 10 | BT910-5 | SA2246 | 5 |
| | 305 x 19 x 1.27 | 12 x 3/4 x 0.050 | 6-10 | BT12610-5 | SA2276 | 5 |
| | | | 10-14 | BT121014-5 | SA2296 | 5 |
| | | | 6 | VB66-5 * | SA161 | 5 |
| | 152 x 19 x 0.89 | 6 x 3/4 x 0.035 | 30 Coarse | XR6-1 ** | SA278 | 1 |
| | | | | XR6-20 ** | # SA27805 | 20 |

* "V" tooth saw blade - ideal for plasterboard cutting - image below.
 ** Carbide Grit saw blade - used on ceramic tiles, fibreglass and cement board - image below.
 # - Made to order, may be subject to longer lead times.




RECIPROCATING SAW BLADES

FOR WOOD

Starrett's 3X POWER Bi-Metal blade triples life and cutting speed over previous models, offering unmatched market value. It has straight and tapered blade designs which excel in cutting a range of wood applications including building materials, logs, and railway sleepers.

FEATURES

- Designed for wood cutting
- Straight and scroll blade formats
- Ideal for cordless saw machines
- Unbreakable; providing safety and reliability
- Optimised tooth pitch for a reduction in vibration, offering cleaner cuts and less fatigue
- Reinforced Shank



SCAN TO
WATCH VIDEOS



AVAILABLE IN

STRAIGHT 

TAPERED 

Available In Various Tooth Pitches
- For a variety of applications

Reinforced & Unified Shank
- To Avoid Breakage



| | Length x Width x Thickness | | TPI (25mm) | Catalogue Number | Item Number | Pack Size |
|------|----------------------------|------------------|---------------|---------------------|----------------|--------------|
| | mm | inch | | | | |
| WOOD | 152 x 19 x 0.89 | 6 x 3/4 x 0.035 | 6 | B66-5 | SA2626 | 5 |
| | 152 x 19 x 1.27 | 6 x 3/4 x 0.050 | 3 | BT63-5 | SA216 | 5 |
| | | | 6 | BT66-5 | SA220 | 5 |
| | 228 x 19 x 1.27 | 9 x 3/4 x 0.050 | 6 | BT96-5 | SA2241 | 5 |
| | 305 x 19 x 1.27 | 12 x 3/4 x 0.050 | 3 | BT123-5 | SA212 | 5 |
| | | | 6 | BT126-5 | SA265 | 5 |






RECIPROCATATING SAW BLADES

KING CUT

Designed for fire, rescue, and demolition, its straight and tapered blades excel in tough tasks. Ideal for cordless saw machines, these blades are unbreakable, ensuring safety and reliability. With a thicker, wider body and reinforced shank, they're built for heavy-duty work, including emergency extrication.

FEATURES

- Designed for fire, rescue and demolition
- Straight and tapered blade formats
- Ideal for cordless saw machines
- Unbreakable; providing safety and reliability
- Thicker & wider body designed for heavy-duty demolition and emergency extrication
- Reinforced Shank



**SCAN TO
WATCH VIDEOS**



Thicker & wider body
designed for heavy-duty demolition
and emergency extrication

Available In Various Tooth Pitches
- For a variety of applications

Available in: Straight and
Tapered Blade Format

Reinforced & Unified Shank
- To Avoid Breakage

AVAILABLE IN



| | Length x Width x Thickness | | TPI (25mm) | Catalogue Number | Item Number | Pack Size |
|--------------------------------------|----------------------------|------------------|---------------|---------------------|-------------|--------------|
| | mm | inch | | | | |
| KING CUT - DEMOLITION, FIRE & RESCUE | 152 x 19 x 0.89 | 6 x 3/4 x 0.035 | 18 | BR618-5 | # SA271966 | 5 |
| | | | 10-14 | BR61014-5 | SA271962 | 5 |
| | | | 10-14 | BTR61014-5 | SA2719821 | 5 |
| | 152 x 27 x 1.60 | 6 x 1 x 0.063 | 6-10 | BTR6610-5 | SA2719826 | 5 |
| | | | 18 | BR818-5 | # SA2719801 | 5 |
| | | | 10-14 | BR81014-5 | SA271971 | 5 |
| | 203 x 19 x 0.90 | 8 x 3/4 x 0.035 | 10-14 | BTR81014-5 | SA2719831 | 5 |
| | | | 6-10 | BTR8610-5 | SA22685 | 5 |
| | | | 10-14 | BR91014-5 | # SA2719806 | 5 |
| | 203 x 27 x 1.60 | 8 x 1 x 0.063 | 10-14 | BTR91014-5 | SA2719836 | 5 |
| | | | 6-10 | BTR9610-5 | SA2719841 | 5 |
| | | | 10-14 | BR121014-5 | SA2719813 | 5 |
| | 228 x 19 x 1.30 | 9 x 3/4 x 0.050 | 10-14 | BTR121014-5 | SA2719846 | 5 |
| | | | 6-10 | BTR12610-5 | SA2719851 | 5 |
| | | | 10-14 | BR121014-5 | SA2719813 | 5 |
| | 305 x 19 x 1.27 | 12 x 3/4 x 0.050 | 10-14 | BTR121014-5 | SA2719846 | 5 |
| | | | 6-10 | BTR12610-5 | SA2719851 | 5 |
| | | | 10-14 | BR121014-5 | SA2719813 | 5 |

- Made to order, may be subject to longer lead times.





RECIPROCATING SAW BLADES

CARBIDE TIPPED

Starrett's carbide tipped blades triples life and cutting speed over previous models, offering unmatched market value. This blade is ideal for car dismantling, demolition, and fire and rescue operations. It provides a longer lifespan than standard blades, reduces trigger time, and minimizes exposure to harmful vibrations.




Exclusive to
the CR128

FEATURES

- Ideal for car dismantling, demolition, and fire & rescue operations
- Provides a longer tool lifespan over standard blades
- Reduces trigger time
- Minimizes exposure to harmful vibrations



No Plastic - Environmentally Friendly Packaging!



**SCAN TO
WATCH VIDEOS**



Ideal for car dismantling, demolition, and fire & rescue operations

Longer Tool Lifespan over standard blades

Reduces trigger time

Minimizes exposure to harmful vibrations

AVAILABLE IN

STRAIGHT



| CARBIDE TIPPED | Length x Width x Thickness mm | TPI (25mm) | Catalogue Number | Item Number | Pack Size |
|----------------|----------------------------------|---------------|---------------------|-------------|--------------|
| | 152 x 24 x 1.27 | 8 | CR68 | SA271966 | 1 |
| | 228 x 24 x 1.27 | 8 | CR98 | SA271962 | 1 |
| | 300 x 24 x 1.27 | 8 | CR128 | SA2719821 | 1 |



RECIPROCATATING PALLET DISMANTLING

The pallet dismantling and repair blade range cuts all pallet and nail embedded pallet wood types effectively. Blades are unpainted with engraved identification, available in straight format with rounded tips to prevent snagging on nails or damaged pallets.

FEATURES


- Suitable for cutting all types of wood
- Blades come unpainted with identifying information engraved on them
- Available in a straight blade format
- Includes a rounded tip to prevent snagging while cutting through nails and damaged pallets

RECIPROCATATING PNEUMATIC

Starrett offers a line of Bi-Metal Unique® saw blades designed for pneumatic reciprocating saws. This line includes three blades with varying TPIs (Teeth Per Inch) suitable for metal cutting applications.

SPECIFICATIONS

- **Application:** Metal cutting
- **Application Material Thickness:** 1.6-11mm (1/16-7/16")
- **Dimensions:** 92 x 13 x .65mm (3.5/8" x 1/2" x .025")
- **TPI:** 32
- **Pack:** Plastic tube
- **Blades in Pack:** 5
- **Shank:** Unified



| Length x Width x Thickness | | TPI (25mm) | Catalogue Number | Item Number | Pack Size |
|----------------------------|-----------------|---------------|---------------------|----------------|--------------|
| mm | inch | | | | |
| 203 x 19 x 0.89 | 8 x 3/4 x 0.035 | 10 | B810P-20 | SA1967 | 20 |
| | | | B810P-250 | SA1970 | 250 |
| 228 x 19 x 0.89 | 9 x 3/4 x 0.035 | 10 | # B910P-20 | SA1975 | 20 |
| | | | # B910P-250 | SA1975 | 250 |

= MTO - Made to order, may be subject to longer lead times.



| | Length x Width x Thickness | | TPI (25mm) | Catalogue Number | Item Number | Pack Size |
|-------|----------------------------|--------------------|---------------|---------------------|----------------|--------------|
| | mm | inch | | | | |
| METAL | 92 x 13 x .65 | 3.5/8 x 1/2 x .025 | 32 | BS226-5 | SA2910 | 5 |
| | | | 24 | BS227-5 | SA2920 | 5 |
| | | | | BS227-20 | SA2923 | 20 |
| | | | 18 | BS228-5 | SA2930 | 5 |
| MULTI | | | 14-18 | BS229-5 | SA2940 | 5 |
| | | | | BS229-20 | SA2942 | 20 |

BI-METAL & CARBIDE GRIT RECIPROCATING SAW BLADE ASSORTMENT PACKS



KRB12-A

SB6-A



KRB12-A ASSORTMENT PACK (SA2905)

| | Blade Length | Blades Included | Application | TPI (25mm) |
|--------------|--------------|-----------------|-------------|------------|
| 12 BLADE SET | 150mm / 6" | BT66 | WOOD | 6 |
| | | XR6 | MULTI | 30 Coarse |
| | | VB66 | MULTI | 6 |
| | 228mm / 9" | BT910 | MULTI | 10 |
| | 102mm / 4" | B424 | METAL | 24 |
| | | B614 | METAL | 14 |
| | 150mm / 6" | B624 | METAL | 24 |
| | | BTR6610 | KING CUT | 6-10 |
| | 228mm / 9" | BTR91014 | KING CUT | 10-14 |
| | | BTR9610 | KING CUT | 6-10 |
| | | BTR121014 | KING CUT | 10-14 |
| | 300mm / 12" | BTR12610 | KING CUT | 6-10 |

SB6-A ASSORTMENT PACK (SA290)

| | Blade Length | Blades Included | Application | TPI (25mm) |
|-------------|--------------|-----------------|-------------|------------|
| 5 BLADE SET | 150mm / 6" | B66 | WOOD | 6 |
| | | B610 | MULTI | 10 |
| | | B614 | METAL | 14 |
| | | B618 | METAL | 18 |
| | | B624 | METAL | 24 |





HAND TOOLS

TAPE MEASURES



Starrett®

This value priced tape measure with high visibility ABS plastic is easy to locate and difficult to damage. Incorporates industry standard standout and positive blade lock. Includes a steel belt clip.



Starrett®
EXACT®

These tape measures, featuring a high carbon steel blade and durable ABS plastic casing, have a rubber overlay for better grip and shock absorption. Ergonomically designed for comfort and class II rated, they include industry-standard standout and enhanced blade protection.



Starrett®
EXACT® PLUS

The high carbon steel blade of the Starrett Exact Plus measuring tape, coated in yellow nylon, is up to six times more resistant to abrasion and corrosion. Its PC-ABS plastic and rubber case enhances impact resistance and grip, significantly extending product life.



| Cat. No. | Item Number | Blade L & W | Graduation* |
|------------|-------------|-------------|-------------|
| KTS34-5M-N | DV8003 | 5m x 19mm | Metric |

*Blade Graduation Style:

Metric: Graduated in Millimetres

Metric / Imperial: Graduated Millimetres and 1/16"

| Cat. No. | Item Number | Blade L & W | Graduation* |
|--------------|-------------|--------------------------|-------------------|
| KTX12-12ME-N | DV8021 | 3.5m (12') x 13mm (1/2") | Metric / Imperial |
| KTX12-3.5M-N | DV8019 | 3.5m x 13mm | Metric |
| KTX34-16ME-N | DV8024 | 5m (16') x 19mm (3/4") | Metric / Imperial |
| KTX1-26ME-N | DV8028 | 8m (26') x 25mm (1") | Metric / Imperial |
| KTX1-8M-N | DV8026 | 8m x 25mm | Metric |

| Cat. No. | Item Number | Blade L & W | Graduation* |
|-----------------|-------------|-------------------------|-------------------|
| KTXP106-16ME-N | DV8041 | 5m (16') x 27mm (1.06") | Metric / Imperial |
| KTXP106-5M-N | DV8040 | 5m x 27mm | Metric |
| KTXP106-26ME-N | DV8044 | 8m (26') x 27mm (1.06") | Metric / Imperial |
| # KTXP106-8M-N | DV8042 | 8m x 27mm | Metric |
| # KTXP106-10M-N | DV8045 | 10m x 27mm | Metric |

= MTO - Made to order, may be subject to longer lead times.

MEASURE STIX

S12 Metric / Imperial



Manufactured from high quality precision steel and with a permanent adhesive backing to provide convenient, at-a-glance measurements. Can be mounted on most surfaces like work benches, saw tables, walls, etc. Easily cut with scissors and available in left-to-right or right-to-left.

LONG TAPES

530 SERIES - STEEL BLADE (CLOSED REEL)



The closed reel steel long tape features a rugged rewind mechanism. Nylon rollers at case opening to reduce blade wear through sustained field use. Blades are produced with high visibility, easy-to-read graduations.

FEATURES

- Vinyl clad steel case.
- Easy-to-read graduations.
- Nylon rollers to reduce blade wear.
- Folding hook ring.

| Cat. No. | Item Number | Blade Size | Graduation* |
|------------|-------------|------------|-------------|
| # 530-15CM | DA49500 | 9mm x 15m | Metric |
| # 530-20CM | DA49530 | 9mm x 20m | Metric |
| # 530-30CM | DA49506 | 9mm x 30m | Metric |

*Blade Graduation Style: **Metric:** Graduated in Millimetres

= MTO - Made to order, may be subject to longer lead times.

= MTO - Made to order, may be subject to longer lead times.

PROSITE PROTRACTOR

505A-12 AND 505A-7 ALUMINIUM MITRE

The popular ProSite 505 Protractor family consists of two 300mm (12") combination protractors, a 300mm (12") mitre protractor and two 175mm (7") mitre protractors. The combination protractors take the guesswork out of these functions: mitre cuts, single cuts, compound mitre cuts, included conversion table, protractor and roof pitches. The mitre protractors are ideal for carpenters, plumbers and all building trades that require the measuring and transferring of angles.

FEATURES

- ProSite Protractors take error-prone calculations out of the process of mitre cuts.
- This easy-to-use tool has two laser engraved scales.
- Mitre cut scale transfers readings directly to the mitre saw for mitre joints.
- Single cut scale transfers readings directly to the mitre saw.
- Made from durable 6.5mm (1/4") aluminium with Teflon® "O" ring for smooth and precise operation.
- Protractor saves time and reduces waste.

| Cat. No. | Item Number | Description |
|----------|-------------|------------------------------|
| 505A-12 | DA661 | 300mm (12") Mitre Protractor |
| 505A-7 | DA6609 | 175mm (7") Mitre Protractor |

505A-12

505A-7



PROSITE PROTRACTOR

505P-7 PLASTIC MITRE

The 175mm (7") Plastic Mitre Protractor simplifies mitre cuts by eliminating error-prone calculations. Perfect for carpenters, plumbers, and other building trades, this tool excels in measuring and transferring angles. It's also invaluable for home use. This durable plastic mitre protractor delivers the same functionality as the 505A-7 aluminium protractor.



- An easy-to-use tool featuring two laser-engraved scales
- The mitre cut scale directly transfers readings to the mitre saw for precise mitre joints
- The single cut scale seamlessly transfers readings for accurate butt joints
- Saves time and minimizes waste
- Constructed from durable, 7-inch hardened plastic
- Size: 13.7 x 24 x 2.2cm

| Cat. No. | Item Number | Description |
|----------|-------------|-------------------------------------|
| 505P-7 | DA6612 | 175mm (7") Plastic Mitre Protractor |



UTILITY KNIVES



STARRETT LARGE SIZE SLIDE LOCKING

Large ABS plastic utility knife with a slide locking system.

FEATURES

- This utility knife works with 18mm (.710") blade (KS06R).
- Blade with 8 break-away segments.

| Cat. No. | Item Number | Blade Width | Description |
|------------|-------------|--------------|-----------------------------|
| # KUS045-N | DV8400 | 18mm (.710") | Large Plastic Slide Locking |

= MTO - Made to order, may be subject to longer lead times.

STARRETT EXACT



Starrett®
EXACT®



| Cat. No. | Item Number | Blade Width | Description |
|------------|-------------|-------------|---------------------------------|
| # KUX035-N | DV8414 | 9mm (3/8") | Small Plastic Automatic Locking |

= MTO - Made to order, may be subject to longer lead times.

| Cat. No. | Item Number | Blade Width | Description |
|----------|-------------|-------------|-----------------------------|
| KUX040-N | DV8415 | 9mm (3/8") | Small Plastic Screw Locking |

| Cat. No. | Item Number | Blade Width | Description |
|----------|-------------|--------------|-----------------------------------|
| KUX025-N | DV8412 | 18mm (.710") | Large Plastic - Automatic Locking |

AUTOMATIC LOCKING METAL BLADE GUIDE

Small plastic utility knife with automatic locking, metal blade guide.

FEATURES

- This utility knife works with 9mm (3/8") blade (KS05R).
- ABS plastic body and rubber plastic overmoulded.
- Blade with 13 break-away segments.

SCREW LOCKING METAL BLADE GUIDE

Small plastic utility knife with screw locking, metal blade guide.

FEATURES

- This utility knife works with 9mm (3/8") blade (KS05R).
- ABS plastic body and rubber plastic overmoulded.
- Blade with 13 break-away segments.

AUTOMATIC LOCKING METAL BLADE GUIDE

Large plastic utility knife with automatic locking metal blade guide.

FEATURES

- This utility knife works with 18mm (.710") blade (KS06R).
- ABS plastic body and rubber plastic overmoulded.
- Blade with 8 break-away segments.




S011 HIDDEN EDGE® - SAFETY KNIFE. RETRACTABLE BLADE

The blade stays safely tucked away when not in use. Release the safety lock and squeeze the lever to use. Blade changes are fast and tool-free, with a quick-release mechanism and spare storage in the body.

FEATURES

- This utility knife is supplied with 3 trapezoidal blades (KS01R).
- It also works with hook blades (KSH01R).
- Easy to use safety lock and lever allows the blade to be exposed instantly.
- Thumb wheel accurately adjusts cutting depth.
- Fast, tool-free blade changes.

Starrett®
EXACT® PLUS



| Cat. No. | Item Number | Blade Type | Description |
|----------|-------------|--------------------------------|-------------------------------|
| S011 | DA63545 | Standard Trapezoidal (or Hook) | Hidden Edge Utility Knife |
| 968 | DA63865 | - | Leather Belt Holster for S011 |

ALUMINIUM DIE-CAST BODY FOLDING KNIFE

Utility knife features a die-cast folding knife using trapezoidal or hook blade.

FEATURES

- This utility knife works with trapezoidal (KS01R) or hook blades (KSH01R).
- Supplied with 1 blade and a dispenser with 3 spare trapezoidal blades.



| Cat. No. | Item Number | Blade Type | Description |
|-----------|-------------|--------------------------------|---------------------------------|
| KUXP010-N | DV8431 | Standard Trapezoidal (or Hook) | Aluminium Die-Cast Body Folding |

ALUMINIUM RETRACTABLE KNIFE

The Exact® Plus KUXP005-S features a heavy-duty aluminum body, non-slip rubber surface, five cut levels, and an integrated three-blade dispenser. It allows for safe cutting of strings, wires, and thin cords without blade exposure. Suitable for general applications.

| Cat. No. | Item Number | Blade Type | Description |
|-------------|-------------|--------------------------------|--|
| # KUXP005-N | DV8430 | Standard Trapezoidal (or Hook) | 3 trapezoidal blades (KS01R) inside the knife dispenser and 1 already fitted. Hook blades (KSH01R) can be used. The dispenser has capacity for 4 blades. |



- Made to order, may be subject to longer lead times.

NEW

KUX001

SAFETY KNIFE

LIGHTWEIGHT DESIGN WITH AUTO RETRACT



FEATURES & BENEFITS


- Ergonomically designed for user comfort with excellent thumb and finger grip
- Lightweight construction reducing the strain on the hand when in use
- Smooth top and side slide for extending the blade
- Simple tool free case opening, and blade change
- Solid hinge design
- Auto retracting mechanism
- Built in safety features
- Can be used with 'straight' and 'hook' blades KS01R, KSB-100D, KSH01R
- Exclusive design with distinctive body
- 100% sustainable packaging made from new materials
- Full instructions included

| Item Number | Catalogue Number | Product Size | Order Qty in Multiples of.. |
|-------------|------------------|--------------|-----------------------------|
| KUX001 | KUX001 | 154x42x19 | 6 |

UTILITY KNIVES

REPLACEMENT BLADES


Ensure safe and easy blade handling with our dispensers.



| | Cat. No. | Item Number | Blade Type | Dispenser Description | Fits |
|---|---|-------------|-------------------------|--|--|
| # |  | KS01R | Standard Trapezoidal | 10 high carbon steel trapezoidal blades | S011 KUXP010-N KUXP005-N KUX001 |
| |  | KSB-100D | | 100 high carbon steel trapezoidal blades | |
| # |  | KSH01R | Hook | 10 high carbon steel hook blades | |
| # |  | KS05R | Break-away 3/8" (9mm) | 10 high carbon steel break-away blades. | KUX035-N KUX040-N KUXP020-N |
| |  | KS06R | Break-away .710" (18mm) | 10 high carbon steel break-away blades. | KUS045-N KUX025-N |

= **ITO** - Made to order, may be subject to longer lead times.





ANGLE METER

MAGNETIC ANGLE METER, 0 TO 90°

Large, readable scale for accurate readings from 0 to 90° in any quadrant. The integral magnetic base frees hands when used on ferrous surfaces.

| Cat. No. | Item Number | Description |
|----------|-------------|--------------------------------|
| AM-2 | DS0002 | Magnetic Angle Meter, 0 to 90° |

FEATURES

- Measures any angle for pitch or slope.
- Handy rise, run, angle and pitch information on back of the tool.

BE-1 BULL'S-EYE CIRCULAR LEVEL

Circular bull's-eye levels offer a full 360° large sight for easy viewing. Each level features sturdy plastic construction, ideal for home, workshop, and industry use.

| Cat. No. | Item Number | Description |
|----------|-------------|------------------------------|
| BE-1 | DS0006 | 44mm / 1-3/4" Circular Level |



CHALK LINES

Our chalk line features high impact-resistant ABS plastic cases capable of holding 120g (4 oz) of chalk and 30m (100') of line with a press-to-release feature. Manufactured with fast line rewind, each line is secured with a stainless steel hook.

Starrett®

FEATURES

- 3.5X faster line rewind.

| Cat. No. | Item Number | Size | Feet | Metres |
|----------|-------------|-------------|------|--------|
| KCS001-N | DV8300 | 120g (4 oz) | 100' | 30m |



Starrett® EXACT®

FEATURES

- Rubber plastic soft touch overmoulding.
- 50% stronger line than standard chalk lines.
- 6X faster line rewind.
- Easy feed window.

| Cat. No. | Item Number | Size | Feet | Metres |
|----------|-------------|-------------|------|--------|
| KCX001-N | DV8301 | 120g (4 oz) | 100' | 30m |

TEMPORARY CHALK

The new bottle design is formulated and coloured for distinctiveness and to lay down hard clean lines. It provides easier handling, and a no-spill cap.

| | Cat. No. | Item Number | Size | Colour |
|---|----------|-------------|---------------|--------|
| # | SC4BLU | DA6605 | 1800g (4 lbs) | Blue |
| # | SC8B | DA6601 | | Blue |
| | SC8R | DA6600 | 230g (8 oz) | Red |
| # | SC8W | DA6602 | | White |

= MTO - Made to order, may be subject to longer lead times.



RULES

STRAIGHT EDGE ALUMINIUM RULE

AMSE SERIES

Straight-edge aluminium rules are parallel, and made of anodized aluminium with smooth, square, and straight edges. They feature centimetre and millimetre graduation readings on both edges.

FEATURES

- Ideal for schools and shops, wood-workers, tinsmiths, metal workers, and bench applications.
- They lie flat, resist bending and feature large, easy to read graduations and numbers that are heavier than conventional machine graduated scales.
- Rules are 50mm (2") wide with centimetre and millimetre graduations reading on either edge.
- Accurate and flexible.



| Cat. No. | Item Number | Length | Thickness |
|-------------|-------------|--------|-----------|
| # AMSE-500 | DS0581 | 500mm | 2mm |
| # AMSE-1000 | DS0582 | 1000mm | |
| # AMSE-1500 | DS0583 | 1500mm | 3mm |
| # AMSE-2000 | DS0584 | 2000mm | |

= MTO - Made to order, may be subject to longer lead times.

ALUMINIUM METRESTICK

MS-2

Aluminium Metrestick is parallel, accurate and flexible.

FEATURES

- This rule lies flat and features large, easy to read numbers.
- Anodized aluminium.




| Cat. No. | Item Number | Length | Thickness | Description | Graduation |
|----------|-------------|----------------|------------------|---------------|---------------------|
| MS-2 | DS0597 | 1m (39.37") | 1.9mm (.075") | Ruled 2 Sides | Metric and Imperial |

SQUARES

53


CARPENTERS' TRY SQUARE



| Cat. No. | Item Number | Dimension |
|------------|-------------|-------------|
| K53M-200-S | DS0620 | 200mm (8") |
| K53M-250-S | DS06212 | 250mm (10") |
| K53M-300-S | DS06214 | 300mm (12") |
| K53M-350-S | DS0622 | 350mm (14") |

FEATURES

- Stainless steel blade.
- Graduations etched on both sides of the blade.
- 50mm (2") cast aluminium handle.



15

UNIVERSAL BEVEL

200mm (8") stainless steel blade and plastic handle with one spirit level vial.



FEATURES

- Blade lock for transferring angles.
- Handle is ABS plastic for a comfortable grip.

| Cat. No. | Item Number | Dimension |
|----------|-------------|------------|
| K15-N | DS0627 | 200mm (8") |



LASER DISTANCE METERS

STARRETT® SERIES

KLMS-30 DS24905

Our most compact model, the KLMS-30 Laser Distance Meter, fits in your pocket and is easy to store.



IP54
PROTECTION

CLASS 2

**TOTAL RANGE:
30 METRES**

*Protection IP54:
dust and splash proof.

Features

- Measuring range of 30 metres
- Laser Type 650 nm, class 2, <1mW
- Multifunction (area and volume calculation)
- Indirect Measuring (Pythagoras function)
- Addition and Subtraction
- Maximum and Minimum
- Front and back measuring references
- Ability to measure in metres, inches and feet

Benefits

- Accuracy: $\pm 2.0\text{mm}$
- Easy to read display with LED light
- Protection IP54*
- Automatic power off
- Measurement response time of 0.5 seconds

Accessories:

- 2 AAA batteries

EXACT® SERIES

Starrett®
EXACT®

KLMX-50 DS24910

The Starrett Exact Laser Distance Meter is a high-quality, lightweight, ergonomic device that provides length, area, and volume measurements with a single button.



IP54
PROTECTION

15

CLASS 2

**OVER 20 METRES OF
EXTRA RANGE
TOTAL OF
70 METRES**

*Protection IP54:
dust and splash proof.

Features

- Measuring range of 50 metres
- Laser Type 650 nm, class 2, <1mW
- Multifunction (area and volume calculation)
- Indirect Measurement (Pythagoras function)
- Addition and Subtraction
- Maximum and Minimum
- Stake out function
- 3-15 seconds timer
- Measuring reference - front, centre (for tripod) & back
- Ability to measure in metres, inches and feet

Benefits

- High accuracy: $\pm 1.5\text{mm}$
- Stores up to 10 measurement results
- Buzzer
- Easy to read display with LED light
- Tripod mountable
- Protection IP54*
- Automatic power off
- Measurement response time of 0.5 seconds

Accessories:

- 1 carrying pouch
- 2 AA batteries

LASER DISTANCE METERS

EXACT® PLUS SERIES

KLMXP-100 DS24915

The Starrett Exact Plus Laser Distance Meter is the most advanced in the Starrett range. This unit includes Bluetooth® to connect to Android and iOS devices and a downloadable app that allows users to control the meter via a smartphone or other compatible device.



*Protection IP54: dust and splash proof.

Features

- Measuring range of 100 metres
- Laser Type 650 nm, class 2, <1mW
- Multifunction (area and volume calculation)
- 3 types of indirect measuring (Pythagoras function)
- Addition and Subtraction
- Maximum and Minimum
- Stake out function
- Angle measuring
- 3-15 seconds timer
- Measuring reference - front, back and extension
- Ability to measure in metres, inches and feet

Accessories:

- 1 carrying pouch
- 2 AA batteries

Starrett®
EXACT® PLUS



IP54
PROTECTION

15

CLASS 2

Bluetooth®



Extension to start measuring from corners.

Benefits

- Bluetooth® with Android and IOS apps**
- High accuracy: $\pm 1.5\text{mm}$
- Stores up to 20 measurement results
- Buzzer
- Easy to read display with LED light
- Protection IP54*
- Automatic power off
- Measurement response time of 0.5 seconds

**The app allows users to take pictures and control the device through a smartphone, making it easier to measure and record data.



BANDSAW BLADES FOR PORTABLE MACHINES

NEW



| Item N. | Part Number | Description | QTY (Per bag/box) | Suitable for (table below) |
|-----------------|--------------------------|------------------------------|-------------------|----------------------------|
| UNZ13C1411403 | UNZ13X14/S-1,140SPJ | 1140MMX13X0.5X14 UNZ PK3 | 3 | 1 |
| UNZ13C101411403 | UNZ13X10-14/P-1,140SPJ | 1140MMX13X0.5X10-14 UNZ PK3 | 3 | 1 |
| UNZ13C1811403 | UNZ13X18/S-1,140SPJ | 1140MMX13X0.5X18 UNZ PK3 | 3 | 1 |
| UNZ13C141811403 | UNZ13X14-18/P-1,140SPJ | 1140MMX13X0.5X14-18 UNZ PK3 | 3 | 1 |
| UNZ13A148353 | UNZ13X14/S-3-0,835SPJ | 835MMX13X0.35X14 UNZ PK3 | 3 | 2 |
| UNZ13A10148353 | UNZ13X10-14/P-3-0,835SPJ | 835MMX13X0.35X10-14 UNZ PK3 | 3 | 2 |
| UNZ13A188353 | UNZ13X18/S-3-0,835SPJ | 835MMX13X0.35X18 UNZ PK3 | 3 | 2 |
| UNZ13A14188353 | UNZ13X14-18/P-3-0,835SPJ | 835MMX13X0.35X14-18 UNZ PK3 | 3 | 2 |
| UNZ13A147333 | UNZ13X14/S-3-0,733SPJ | 733MMX13X0.35X14 UNZ PK3 | 3 | 3 |
| UNZ13A10147333 | UNZ13X10-14/P-3-0,733SPJ | 733MMX13X0.35X10-14 UNZ PK3 | 3 | 3 |
| UNZ13A187333 | UNZ13X18/S-3-0,733SPJ | 733MMX13X0.35X18 UNZ PK3 | 3 | 3 |
| UNZ13A14187333 | UNZ13X14-18/P-3-0,733SPJ | 733MMX13X0.35X14-18 UNZ PK3 | 3 | 3 |
| UNZ13A10149003 | UNZ13X10-14/P-3-0,900SPJ | 900MMX13X0.35X10-14 UNZ PK3 | 3 | 4 |
| UNZ13A149003 | UNZ13X14/S-3-0,900SPJ | 900MMX13X0.35X14 UNZ PK3 | 3 | 4 |
| UNZ13A14189003 | UNZ13X14-18/P-3-0,900SPJ | 900MMX13X0.35X14-18 UNZ PK3 | 3 | 4 |
| UNZ13A189003 | UNZ13X18/S-3-0,900SPJ | 900MMX13X0.35X18 UNZ PK3 | 3 | 4 |
| IPD13F10141335S | IPD13X10-14/P-1,335SPJ | 1335MMX13X0.65X10-14 ITPD 42 | 1 | 5 |
| IPD13F181335S | IPD13X18/S-1,335SPJ | 1335MMX13X0.65X18 ITPD 42 | 1 | 5 |
| IPD13F141335S | IPD13X14/S-1,335SPJ | 1335MMX13X0.65X14 ITPD 42 | 1 | 5 |
| IPD13F8121335S | IPD13X8-12/P-1,335SPJ | 1335MMX13X0.65X8-12 ITPD 42 | 1 | 5 |
| IPD13F6101335S | IPD13X6-10/P-1,335SPJ | 1335MMX13X0.65X6-10 ITPD 42 | 1 | 5 |
| IPD13F181440S | IPD13X18/S-1,440SPJ | 1440MMX13X0.65X18 ITPD 42 | 1 | 6 |
| IPD13F141440S | IPD13X14/S-1,440SPJ | 1440MMX13X0.65X14 ITPD 42 | 1 | 6 |
| IPD13F8121440S | IPD13X8-12/P-1,440SPJ | 1440MMX13X0.65X8-12 ITPD 42 | 1 | 6 |
| IPD13F6101440S | IPD13X6-10/P-1,440SPJ | 1440MMX13X0.65X6-10 ITPD 42 | 1 | 6 |
| IPD13F10141440S | IPD13X10-14/P-1,440SPJ | 1440MMX13X0.65X10-14 ITPD 42 | 1 | 6 |
| IPD13I10141735S | IPD13X10-14/P-9-1,735SPJ | 1735MMX13X0.9X10-14 ITPD 42 | 1 | 7 |
| IPD13I8121735S | IPD13X8-12/P-9-1,735SPJ | 1735MMX13X0.9X8-12 ITPD 42 | 1 | 7 |
| IPD13I6101735S | IPD13X6-10/P-9-1,735SPJ | 1735MMX13X0.9X6-10 ITPD 42 | 1 | 7 |

| Suitable for | Machine Type |
|--------------|---|
| 1 | Makita DPB180 / Makita 2107FK / Makita XBP02Z / Milwaukee Corded & M18 Deep Cut CBS125 / M18 Fuel 2729-22 / DeWalt DC3371N / DeWalt DWM120 / Aldi Workzone / Aldi Ferrex / Scheppach 240V / Bosch GCB 120 / Bosch GCB10-S |
| 2 | Metabo MBS 18LTX 2.5 / Metabo18V 613022850 / Makita DP13181Z / Dewalt DCS371N-XJ / Makita XPB01 |
| 3 | Starrett S1005 /Bosch GCB / Hilti SB4-A22 |
| 4 | Milwaukee HD18BS / Hikoki CB18DBL / Milwaukee M18 Fuel 2829 / Milwaukee M18 2629-20 |
| 5 | 782XL / 783XL / ABS105 / SN105XL / FLEX SBG 4910 |
| 6 | Femi NG120 & NG120XL (1440) / Femi 784XL (1440) / Promac 349V & V2 |
| 7 | NG160 / 785XL |


FEATURES & BENEFITS

- High-Quality HSS Edge
- Integrated Multi-Edge and Split Chip Technologies for improved performance
- Patented technology allows for quicker and cleaner cuts
- Advanced design prolongs the life of the blade, reducing replacement frequency
- Suitable for a wide range of cutting applications

APPLICATIONS

- Electrical Conduit, Armor Cable, and PVC
- Strut, Structural, and Threaded Rod
- Pipes, Tubes, and Tubing
- Stainless Steel, Cast Iron and Non-Ferrous Metals
- Machinable and Solid Metals

WATCH
IN ACTION



SMALL TOOL BAG

Carry strap

Main compartment
with zip closure

COMPACT

Removable
shoulder strap

Velcro pocket and
external compartments

| Description | Compartments and pockets | Dimensions (mm) L x W x H | Weight (Kg) | Barcode | Catalogue No. | Item Number |
|----------------|---|------------------------------|----------------|------------------|------------------|----------------|
| Small Tool Bag | 12 external pockets 6 internal pockets | 300 x 170 x 220 | 0.833 | 0049 659 08429 8 | BGS | DT4060 |



Large internal space
and easy access

Main compartment
with zip closure

Large pockets and
external compartments

Removable
shoulder strap

MEDIUM TOOL BAG

WATERPROOF

REINFORCED BASE



| Description | Compartments and pockets | Dimensions (mm) L x W x H | Weight (Kg) | Barcode | Catalogue No. | Item Number |
|-----------------|--|------------------------------|----------------|------------------|------------------|----------------|
| Medium Tool Bag | 7 external pockets 6 internal pockets | 400 x 220 x 320 | 1.056 | 0049 659 08510 5 | BGM | DT4062 |

LARGE TOOL BAG

Quick and easy
access to tools

Various pockets,
external and internal
compartments

Removable
shoulder strap

Reinforced internal base with
ABS plastic supports

REINFORCED

RUBBER HANDLE



| Description | Compartments and pockets | Dimensions (mm) L x W x H | Weight (Kg) | Barcode | Catalogue No. | Item Number |
|----------------|---|------------------------------|----------------|------------------|------------------|----------------|
| Large Tool Bag | 21 external pockets, 5 internal 8 elasticated compartments | 410 x 240 x 270 | 1.612 | 0049 659 08567 9 | BGL | DT4064 |

12 PACK

ABRASIVE CUTTING DISCS

DAC115-14X

CUTTING PERFORMANCE

Cuts 50% faster than many
other discs on the market

CLEAN AND PRECISE CUTS

Minimal burrs and
surface damage

EXCELLENT HEAT DISSIPATION

Reduces overheating and
warping risks

VERSATILE APPLICATION

Cuts stainless, carbon steel
and non-ferrous metals



| Item Number | Cat. no. | Size (mm) | Size (Inch) | Box QTY |
|-------------|------------|----------------------|-----------------------|---------|
| DAC115-14X | DAC115-14X | 15mm x 1mm x 22.23mm | 4 1/2" x 3/64" x 7/8" | 12 |

SERVICES & SUPPORT


StarrNET is the new online ordering portal for our partners. We're delivering the same Customer Service, but with an improved ordering process. Our online portal provides the convenience and efficiency of being able to place an order or check stock, any time and any place.

StarrNET brings a wide range of benefits and time saving options to our customers:

- ✓ Real time 'traffic light' stock status
- ✓ NET pricing
- ✓ Shopping cart interface
- ✓ Portal available 24/7, 365 days a year
- ✓ CSV and TXT file ordering facility
- ✓ Instant ordering
- ✓ Quick re-order facility
- ✓ Order History
- ✓ Full MTS Catalogue
- ✓ Dispatch information
- ✓ E-Invoicing

For further information or to register, please contact our Customer Services team on 01835 863501 or email sales@starrett.co.uk, where a representative will be happy to help.

Start using StarrNET now!



Want to know more?

www.starrett.co.uk

SERVICES & SUPPORT



Based in our offices in the UK, our Marketing team are dedicated to supporting our customers throughout the country and the rest of Europe.

Marketing



Digital Catalogues

All current catalogues are available to browse and download via the Starrett website.

Marketing media & support

Further product information, video and image databases and social media materials can be provided upon request.

Merchandise displays

A number of display options are available to support retail customers. Please see page 32 or make enquiries via your local sales manager.

Events and Trade Days

We are happy to support our customers at trade days and events, we can assist with marketing materials and product demonstrations.

Product samples

If you are interested in stocking Starrett products and would like to test out some of our range, product samples can be provided. Please contact your local sales manager or sales@starrett.co.uk to discuss.

Technical Support

Got a question?

Our Technical Support team are on hand to help customers and end users with any questions or queries they have regarding our products or their applications.



Technical Queries

Appointments to speak to a technical expert can be made **via our Cutting Solutions Service**. You can book a slot to speak to a member of our team on a day and time that suits you.

Product Training

We can provide a full range of product training to customers and their teams, either online or in person.

For further information or to discuss requirements contact us on:

Phone: **01835 866205**

Email: sawsupport@starrett.co.uk

Starrett Distributor |

www.starrett.co.uk

Follow us!



The L.S. Starrett Company Ltd. Oxnam Road, Jedburgh, TD8 6LR
Tel.: +44 (0)1835 863501 | sales@starrett.co.uk