

DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board User's Guide

Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Microchip received ISO/TS-16949:2009 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.

QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV = ISO/TS 16949=

Trademarks

The Microchip name and logo, the Microchip logo, AnyRate, dsPIC, FlashFlex, flexPWR, Heldo, JukeBlox, KEELOQ, KEELOQ logo, Kleer, LANCheck, LINK MD, MediaLB, MOST, MOST logo, MPLAB, OptoLyzer, PIC, PICSTART, PIC32 logo, RightTouch, SpyNIC, SST, SST Logo, SuperFlash and UNI/O are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

ClockWorks, The Embedded Control Solutions Company, ETHERSYNCH, Hyper Speed Control, HyperLight Load, IntelliMOS, mTouch, Precision Edge, and QUIET-WIRE are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, BodyCom, chipKIT, chipKIT logo, CodeGuard, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet logo, MiWi, motorBench, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PureSilicon, RightTouch logo, REAL ICE, Ripple Blocker, Serial Quad I/O, SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

Silicon Storage Technology is a registered trademark of Microchip Technology Inc. in other countries.

GestIC is a registered trademarks of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

 $\ensuremath{\textcircled{\sc b}}$ 2016, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

ISBN: 978-1-5224-0358-6

Object of Declaration: DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board

EU Declaration of Conformity

Manufacturer: Microchip Technology Inc. 2355 W. Chandler Blvd. Chandler, Arizona, 85224-6199 USA

This declaration of conformity is issued by the manufacturer.

The development/evaluation tool is designed to be used for research and development in a laboratory environment. This development/evaluation tool is not a Finished Appliance, nor is it intended for incorporation into Finished Appliances that are made commercially available as single functional units to end users under EU EMC Directive 2004/108/EC and as supported by the European Commission's Guide for the EMC Directive 2004/108/EC (8th February 2010).

This development/evaluation tool complies with EU RoHS2 Directive 2011/65/EU.

This development/evaluation tool, when incorporating wireless and radio-telecom functionality, is in compliance with the essential requirement and other relevant provisions of the R&TTE Directive 1999/5/EC and the FCC rules as stated in the declaration of conformity provided in the module datasheet and the module product page available at www.microchip.com.

For information regarding the exclusive, limited warranties applicable to Microchip products, please see Microchip's standard terms and conditions of sale, which are printed on our sales documentation and available at www.microchip.com.

Signed for and on behalf of Microchip Technology Inc. at Chandler, Arizona, USA

Carlon

Derek Carlson VP Development Tools

<u>12-Sep - 14</u> Date

NOTES:



Table of Contents

Preface	6
Introduction	6
Document Layout	6
Conventions Used in this Guide	7
Recommended Reading	8
The Microchip Web Site	8
Customer Support	8
Document Revision History	8
Chapter 1. Product Overview	
1.1 Introduction	9
1.2 DN2470 Device Overview	9
1.3 What is the DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board?	9
1.4 What the DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board Kit Contains	10
Chapter 2. Installation and Operation	
2.1 Getting Started	11
2.2 Setup and Operation Procedure	11
Appendix A. Schematic and Layouts	
A.1 Introduction	13
A.2 Board – Schematic	14
A.3 Board – Top Silk	
A.4 Board – Top Copper and Silk	
A.5 Board – Top Copper	
A.6 Board – Bottom Copper	
Appendix B. Bill of Materials (BOM)	19
Appendix C. DN2470 Characterization Plots	
C.1 Heat Sink	
C.2 Pad Temperature	
C.3 Overtemperature Protection Using PTC	
Worldwide Sales and Service	24

NOTES:



Preface

NOTICE TO CUSTOMERS

All documentation becomes dated, and this manual is no exception. Microchip tools and documentation are constantly evolving to meet customer needs, so some actual dialogs and/or tool descriptions may differ from those in this document. Please refer to our web site (www.microchip.com) to obtain the latest documentation available.

Documents are identified with a "DS" number. This number is located on the bottom of each page, in front of the page number. The numbering convention for the DS number is "DSXXXXXXA", where "XXXXXXXX" is the document number and "A" is the revision level of the document.

For the most up-to-date information on development tools, see the MPLAB[®] IDE online help. Select the Help menu, and then Topics to open a list of available online help files.

INTRODUCTION

This chapter contains general information that will be useful to know before using the DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board User's Guide. Items discussed in this chapter include:

- Document Layout
- Conventions Used in this Guide
- Recommended Reading
- The Microchip Web Site
- Customer Support
- Document Revision History

DOCUMENT LAYOUT

This document describes how to use the DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board User's Guide as a development tool.

- Chapter 1. "Product Overview" Important information about the DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board User's Guide.
- Chapter 2. "Installation and Operation" This chapter includes a detailed description of each function of the demonstration board and instructions on how to use the board.
- Appendix A. "Schematic and Layouts" Shows the schematic and layout diagrams for the DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board User's Guide.
- Appendix B. "Bill of Materials (BOM)" Lists the parts used to build the DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board User's Guide.
- Appendix C. "DN2470 Characterization Plots" Describes the various plots and waveforms for the DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board User's Guide.

CONVENTIONS USED IN THIS GUIDE

This manual uses the following documentation conventions:

DOCUMENTATION CONVENTIONS

Description	Represents	Examples	
Arial font:			
Italic characters	Referenced books	MPLAB [®] IDE User's Guide	
	Emphasized text	is the only compiler	
Initial caps	A window	the Output window	
	A dialog	the Settings dialog	
	A menu selection	select Enable Programmer	
Quotes	A field name in a window or dialog	"Save project before build"	
Underlined, italic text with right angle bracket	A menu path	<u>File>Save</u>	
Bold characters	A dialog button	Click OK	
	A tab	Click the Power tab	
N'Rnnnn	A number in verilog format, where N is the total number of digits, R is the radix and n is a digit.	4'b0010, 2'hF1	
Text in angle brackets < >	A key on the keyboard	Press <enter>, <f1></f1></enter>	
Courier New font:	- I	•	
Plain Courier New	Sample source code	#define START	
	Filenames	autoexec.bat	
	File paths	c:\mcc18\h	
	Keywords	_asm, _endasm, static	
	Command-line options	-Opa+, -Opa-	
	Bit values	0, 1	
	Constants	OxFF, `A'	
Italic Courier New	A variable argument	<i>file.o</i> , where <i>file</i> can be any valid filename	
Square brackets []	Optional arguments	mcc18 [options] file [options]	
Curly brackets and pipe character: { }	Choice of mutually exclusive arguments; an OR selection	errorlevel {0 1}	
Ellipses	Replaces repeated text	<pre>var_name [, var_name]</pre>	
	Represents code supplied by user	void main (void) { }	

RECOMMENDED READING

This user's guide describes how to use the DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board User's Guide. Other useful documents are listed below. The following Microchip documents are available and recommended as supplemental reference resources.

DN2470 Data Sheet – "N-Channel, Depletion-Mode, Vertical DMOS FET" (DS20005410)

MCP1754 Data Sheet - "150 mA,16V, High-Performance LDO" (DS20002276)

MCP1755 Data Sheet - "300 mA,16V, High-Performance LDO" (DS25160)

MCP1790 Data Sheet - "70 mA, High Voltage Regulator" (DS20002075)

THE MICROCHIP WEB SITE

Microchip provides online support via our web site at www.microchip.com. This web site is used as a means to make files and information easily available to customers. Accessible by using your favorite Internet browser, the web site contains the following information:

- **Product Support** Data sheets and errata, application notes and sample programs, design resources, user's guides and hardware support documents, latest software releases and archived software
- General Technical Support Frequently Asked Questions (FAQs), technical support requests, online discussion groups, Microchip consultant program member listing
- Business of Microchip Product selector and ordering guides, latest Microchip press releases, listing of seminars and events, listings of Microchip sales offices, distributors and factory representatives

CUSTOMER SUPPORT

Users of Microchip products can receive assistance through several channels:

- Distributor or Representative
- Local Sales Office
- Field Application Engineer (FAE)
- Technical Support

Customers should contact their distributor, representative or field application engineer (FAE) for support. Local sales offices are also available to help customers. A listing of sales offices and locations is included in the back of this document.

Technical support is available through the web site at: http://www.microchip.com/support

DOCUMENT REVISION HISTORY

Revision A (March 2016)

· Initial release of this document.

Chapter 1. Product Overview

1.1 INTRODUCTION

This chapter provides an overview of the DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board and covers the following topics:

- DN2470 Device Overview
- What is the DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board?
- What the DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board Kit Contains

1.2 DN2470 DEVICE OVERVIEW

The DN2470 is a low-threshold depletion-mode (normally-on) vertical FET. Vertical DMOS FETs are suited for a wide range of switching and amplifying applications where high breakdown voltage, high input impedance, low input capacitance and fast switching speeds are required.

The DN2470 has a 700V voltage breakdown with a 42 ohms drain-to-source On-state resistance and 500 mA saturated drain-to-source current when operating over typical conditions. The device is packaged in a TO-252 (D-PAK) and it is designed to operate in a temperature range of -55°C to +150°C (refer to the DN2470 data sheet for more information).

1.3 WHAT IS THE DN2470 BASED LINEAR REGULATOR INPUT VOLTAGE RANGE EXTENDER EVALUATION BOARD?

The DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board presents the universal off-line linear regulation using the 700V depletion-mode FET DN2470. The board features off-line regulation using three different selectable LDOs: MCP1754, MCP1755 and MCP1790, offered in various package options. The evaluation board operates with 50 Hz 230 VAC or 60 Hz 120 VAC AC lines and sources 10 mA typical output current (LDO's output current).





FIGURE 1-1: DN2470 Evaluation Board Block Diagram.

1.3.1 Evaluation Board Features

- 120 and 230 VAC Off-line Regulation
- Typical Output Current of 10 mA
- Maximum Output Current Thermally Limited
- Transient Survivability of 2.5 kV
- Overtemperature Protection; Typically +105°C
- Output Voltage Range of 3-5V
- Three Different Selectable LDOs:
 - MCP1754 (3.3V)
 - MCP1755 (5.0V)
 - MCP1790 (3.0V)

1.4 WHAT THE DN2470 BASED LINEAR REGULATOR INPUT VOLTAGE RANGE EXTENDER EVALUATION BOARD KIT CONTAINS

The DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board kit includes:

- DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board User's Guide (ADM00682)
- Important Information Sheet

NOTES:

Chapter 2. Installation and Operation

2.1 GETTING STARTED

The DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board is fully assembled and tested.

2.1.1 Tools Required for Operation

The tools required for operation include:

- AC Line connection or DC power supply
- An oscilloscope and/or a multimeter to observe the waveforms and measure electrical parameters

2.2 SETUP AND OPERATION PROCEDURE

To prepare the DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board for operation, the steps below must be followed carefully.

WARNING

Before beginning board setup, fully read this document, the DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board User's Guide.

CAUTION

Hazardous voltages are present when connected to AC Lines.

- 1. <u>Select</u> an LDO by placing a jumper on J3 connector. If VIN1 or VIN2 are selected, SHDN must be shorted to VIN (J5 or J7).
- 2. Connect a Load if needed at VOUT.
- 3. Connect the AC Line (120 or 230 VAC) or DC power supply to J1.

Note: Do not touch exposed areas when operating the board. Avoid touching the heat sink, the drain-exposed pad or the input resistor.

Selecting Different LDO

To select a different LDO, the AC Line or DC power supply has to be removed first.



FIGURE 2-1: DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board.

Appendix A. Schematic and Layouts

A.1 INTRODUCTION

This appendix contains the following schematics and layouts for of the DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board:

- Board Schematic
- Board Top Silk
- Board Top Copper and Silk
- Board Top Copper
- Board Bottom Copper

A.2 BOARD – SCHEMATIC





A.3 BOARD – TOP SILK

A.4 BOARD – TOP COPPER AND SILK



A.5 BOARD – TOP COPPER



A.6 BOARD – BOTTOM COPPER



Appendix B. Bill of Materials (BOM)

Qty.	Reference	Description	Manufacturer	Part Number
1	C1	Capacitor 1 µF 450V	Rubycon Corporation	450PX1MEFC6.3X11
6	C2, C3, C4, C5, C6, C7	Capacitor, 1 µF 16V	Kemet	C0805C105K4RACTU
1	D1	Zener Diode 7.5V	Diodes Incorporated [®]	BZT52C7V5S-7-F
1	H1	HS1 Heat Sink	Aavid Thermalloy	573100D00000G
1	J1	Connector Terminal 1X2	PHOENIX CONTACT	1933189
3	J2, J10, J11	2 Pos. Header Connector	Molex [®]	0022284020
1	J3	6 Pos. Dual Connector	Samtec Inc	TSW-103-08-L-D
2	J4, J6	1 Pos. Header Connector - NOT INSTALLED	TE Connectivity Ltd.	5-146280-1
2	J5, J7	3 Pos. Header Connector	Samtec, Inc.	TSW-103-07-T-S
4	N/A	Hex Standoff 4-40 Nylon 1/2	Keystone Electronics Corp.	4802
4	N/A	Hex Nut 1/4" Nylon	Keystone Electronics Corp.	9605
1	N/A (Mounts on J1)	Terminal Block Plug 2 Pos.	PHOENIX CONTACT	1934861
1	PCB	DN2470 Based Linear Regulator Input Voltage Range Extender Evaluation Board – Printed Circuit Board	_	04-10446
1	Q1	DN2470	Microchip Technology Inc.	DN2470K4-G
1	R1	68 Ohms 2W	TT Electronics Plc.	ULW2-68RJA25
1	R2	Resistor 100k	Yageo Corporation	RC0805JR-07100KL
1	R3	Thermistor-100 PTC	Murata Electronics North America, Inc.	PRG18BB101MB1RB
1	U1	Rectifier 0.5A 400V	Micro Commercial Components	MB4S-TP
1	U2	MCP1755	Microchip Techonology Inc.	MCP1755T-3302E/OT
1	U3	MCP1754	Microchip Techonology Inc.	MCP1754-5002E/MC
1	U4	MCP1790	Microchip Techonology Inc.	MCP1790-3002E/DB
1	U5	Varistor 387V 4.5kA -14 mm Disc	Bourns, Inc.	MOV-14D431K

TABLE B-1: BILL OF MATERIALS (BOM)

Note 1: The components listed in this Bill of Materials are representative of the PCB assembly. The released BOM used in manufacturing uses all RoHS-compliant components.

NOTES:



Appendix C. DN2470 Characterization Plots

C.1 HEAT SINK



C.2 PAD TEMPERATURE



C.3 OVERTEMPERATURE PROTECTION USING PTC



NOTES:



Worldwide Sales and Service

AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

Cleveland Independence, OH Tel: 216-447-0464 Fax: 216-447-0643

Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Novi, MI Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608

New York, NY Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110

Canada - Toronto Tel: 905-673-0699 Fax: 905-673-6509

ASIA/PACIFIC

Asia Pacific Office Suites 3707-14, 37th Floor Tower 6, The Gateway

Harbour City, Kowloon Hong Kong Tel: 852-2943-5100 Fax: 852-2401-3431

Australia - Sydney Tel: 61-2-9868-6733 Fax: 61-2-9868-6755

China - Beijing Tel: 86-10-8569-7000 Fax: 86-10-8528-2104

China - Chengdu Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

China - Chongqing Tel: 86-23-8980-9588 Fax: 86-23-8980-9500

China - Dongguan Tel: 86-769-8702-9880

China - Hangzhou Tel: 86-571-8792-8115 Fax: 86-571-8792-8116

China - Hong Kong SAR Tel: 852-2943-5100 Fax: 852-2401-3431

China - Nanjing Tel: 86-25-8473-2460 Fax: 86-25-8473-2470

China - Qingdao Tel: 86-532-8502-7355 Fax: 86-532-8502-7205

China - Shanghai Tel: 86-21-5407-5533 Fax: 86-21-5407-5066

China - Shenyang Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

China - Shenzhen Tel: 86-755-8864-2200 Fax: 86-755-8203-1760

China - Wuhan Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

China - Xian Tel: 86-29-8833-7252 Fax: 86-29-8833-7256 ASIA/PACIFIC

China - Xiamen Tel: 86-592-2388138 Fax: 86-592-2388130

China - Zhuhai Tel: 86-756-3210040 Fax: 86-756-3210049

India - Bangalore Tel: 91-80-3090-4444 Fax: 91-80-3090-4123

India - New Delhi Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

India - Pune Tel: 91-20-3019-1500

Japan - Osaka Tel: 81-6-6152-7160 Fax: 81-6-6152-9310

Japan - Tokyo Tel: 81-3-6880- 3770 Fax: 81-3-6880-3771

Korea - Daegu Tel: 82-53-744-4301 Fax: 82-53-744-4302

Korea - Seoul Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

Malaysia - Kuala Lumpur Tel: 60-3-6201-9857 Fax: 60-3-6201-9859

Malaysia - Penang Tel: 60-4-227-8870 Fax: 60-4-227-4068

Philippines - Manila Tel: 63-2-634-9065 Fax: 63-2-634-9069

Singapore Tel: 65-6334-8870 Fax: 65-6334-8850

Taiwan - Hsin Chu Tel: 886-3-5778-366 Fax: 886-3-5770-955

Taiwan - Kaohsiung Tel: 886-7-213-7828

Taiwan - Taipei Tel: 886-2-2508-8600 Fax: 886-2-2508-0102

Thailand - Bangkok Tel: 66-2-694-1351 Fax: 66-2-694-1350

EUROPE

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

Denmark - Copenhagen Tel: 45-4450-2828 Fax: 45-4485-2829

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

Germany - Dusseldorf Tel: 49-2129-3766400

Germany - Karlsruhe Tel: 49-721-625370

Germany - Munich Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Venice Tel: 39-049-7625286

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

Poland - Warsaw Tel: 48-22-3325737

Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Stockholm Tel: 46-8-5090-4654

UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820

07/14/15