


Chip Inductors

(Chip Coils)



muRata

*Innovator
in Electronics*

**Murata
Manufacturing Co., Ltd.**

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

O05E.pdf
Nov.25,2013

Introduction

Murata has various chip inductors for every application such as power circuits and high frequency circuits.

There are 3 types of structure: wirewound, multilayer, and film.

These variations enable the best selection for every user's needs.

We will support customers using material technologies and highly developed design technologies.

Explanation of symbols in this catalog

Features of each series



New product



Reflow soldering applicable



Flow soldering applicable



Max height xxmm



Low DC resistance type



Bias current characteristics improved



E12 step inductance variation



E24 step inductance variation



Hi Q type



Tight inductance tolerance available

Features of each item



New product



Design kit available

EU RoHS Compliant

- All the products in this catalog comply with EU RoHS.
- EU RoHS is "the European Directive 2011/65/EU on the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment."
- For more details, please refer to our website 'Murata's Approach for EU RoHS' (<http://www.murata.com/info/rohs.html>).

CONTENTS

| | |
|--|---|
| Classification and Structure of Chip Inductors | 2 |
| Product Guide | 4 |
| Selection Guide | 8 |
| Product Guide by Thickness | 9 |

• Inductors for Power Lines

| | |
|------------------------------|-----|
| Introduction | 12 |
| Part Numbering | 14 |
| Product Detail | 16 |
| ⚠Caution/Notice | 100 |
| Soldering and Mounting | 102 |
| Packaging | 107 |
| Design Kits | 111 |

• Inductors for General Use

| | |
|------------------------------|-----|
| Part Numbering | 118 |
| Product Detail | 119 |
| ⚠Caution/Notice | 136 |
| Soldering and Mounting | 137 |
| Packaging | 141 |
| Design Kits | 142 |

• RF Inductors

| | |
|------------------------------|-----|
| Introduction | 146 |
| Part Numbering | 147 |
| Product Detail | 148 |
| ⚠Caution/Notice | 225 |
| Soldering and Mounting | 227 |
| Packaging | 231 |
| Design Kits | 232 |







| | | |
|-----------------------------------|----------------------------|-----|
| Part Number Quick Reference | 243 | |
| Introduction of Web Site | Design Tools | 244 |
| | EMICON-FUN! | 245 |
| | Products Information | 246 |

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.





Classification and Structure of Chip Inductors





Line Up and Applications for Chip Inductors

| | Line Up | Applications |
|---|--|--|
| For Power Lines / For Low Frequency Circuits (Under 100MHz) | Wire Wound Type Ferrite Core  LQH Series (With some exceptions.) | For Voltage Conversion For Choke For Resonance Circuits For Low Frequency Filter Circuits |
| | Multilayer Type Ferrite Core  LQM Series | |
| RF Inductors (Greater than 100MHz) | Wire Wound Type Ferrite Core for High Frequency  LQW_H Series LQH_H Series | For Impedance Matching For High Frequency Filter Circuits For RF Choke |
| | Wire Wound Type Non-magnetic Core  LQW_A Series | |
| | Multilayer Type Non-magnetic Material  LQG Series | |
| | Film Type Non-magnetic Material  LQP Series | |

Construction and Features of Chip Inductors


| | Construction | Features |
|---|---|---|
| For Power Lines / For General Circuits | Wire Wound Type  Wire Some products are coated with magnetic resin. Electrode Ferrite core | Wide inductance range Good DC bias current characteristics |
| | Multilayer Type  Coil pattern Electrode Ferrite | |

[△]Note • Please read rating and [△]CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| | Construction | Features |
|---------------------|--|--|
| RF Inductors | Wire Wound Type For Radio Frequency  <p>Resin coating on the top Non-magnetic ceramic core Wire Electrode</p> | High Q Large inductance |
| | Wire Wound Type For Intermediate Frequency  <p>Resin coating on the top Ferrite core for high frequency Wire Electrode</p> | High Q at intermediate frequency |
| | Multilayer Type  <p>Coil pattern Outer electrode Non-magnetic ceramic</p> | Industrial standard design |
| | Film Type  <p>Inner electrode, which is produced using photolithography process Outer electrode</p> | Small size, but high Q |


● Technical Data

1. Land Area and Q-F Characteristics




A : Net characteristics without land pattern

B :  Characteristic of chip mounted on land

C :  Characteristic of chip mounted on land
(in mm)

2. Coupling Coefficient Versus Distance between Parts



Note • Please read rating and **CAUTION** (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Murata's LQ□ series of chip inductors (chip coils) consists of compact, high-performance inductors. Their innovative coil and case structures mean low DC resistance and outstanding high-frequency characteristics. The series is designed for a variety of applications, facilitating component selection for individual circuit requirements.

| | Part Number | Structure | Size Code in inch (in mm) | Inductance Range (H) | | | | | | | | |
|--------------------------------|-----------------------------------|-----------------------------------|------------------------------|----------------------|-------|-------|-------|-------|-------|----|-------|--|
| | | | | 1n | 10n | 100n | 1μ | 10μ | 100μ | 1m | 10m | |
| Inductors for Power Lines | LQW15CN_00 <small>p86</small> | Wire Wound Type (Ferrite Core) | 0402 (1005) | | 18nH | | 200nH | | | | | |
| | LQW15CN_10 <small>p87</small> | | 0402 (1005) | | | 220nH | | 560nH | | | | |
| | LQW18CN_00 <small>p89</small> | | 0603 (1608) | 4.9nH | | | 650nH | | | | | |
| | LQH2MCN_02 <small>p42</small> | | 0806 (2016) | | | | 1.0μH | | 82μH | | | |
| | LQH2MCN_52 <small>p44</small> | | 0806 (2016) | | | | 1.0μH | | 22μH | | | |
| | LQH2HPN_G0 <small>p46</small> | | 1008 (2520) | | | | 2.2μH | | 100μH | | | |
| | LQH2HPN_GR <small>p48</small> | | 1008 (2520) | | | | 470nH | | 22μH | | | |
| | LQH2HPN_J0 <small>p50</small> | | 1008 (2520) | | | | 1.5μH | | 10μH | | | |
| | LQH2HPN_M0 <small>p52</small> | | 1008 (2520) | | | | 2.2μH | | 4.7μH | | | |
| | LQH3NPN_G0 <small>p59</small> | | 1212 (3030) | | | | 1.0μH | | 250μH | | | |
| | LQH3NPN_J0 <small>p57</small> | | 1212 (3030) | | | | 1.0μH | | 47μH | | | |
| | LQH3NPN_M0 <small>p53</small> | | 1212 (3030) | | | | 1.0μH | | 100μH | | | |
| | LQH3NPN_MR <small>p55</small> | | 1212 (3030) | | | | 1.0μH | | 47μH | | | |
| | LQH32PN_N0 <small>p61</small> | | 1210 (3225) | | | | 470nH | | 120μH | | | |
| | LQH32PN_NC <small>p63</small> | | 1210 (3225) | | | | 470nH | | 22μH | | | |
| | LQH32PB_N0 <small>p65</small> | | 1210 (3225) | | | | 470nH | | 120μH | | | |
| | LQH32PB_NC <small>p67</small> | | 1210 (3225) | | | | 470nH | | 22μH | | | |
| | LQH43PN_26 <small>p69</small> | | 1812 (4532) | | | | 1.0μH | | 220μH | | | |
| | LQH43PB_26 <small>p71</small> | | 1812 (4532) | | | | 1.0μH | | 220μH | | | |
| | LQH44PN_J0 <small>p75</small> | | 1515 (4040) | | | | 1.0μH | | 47μH | | | |
| | LQH44PN_P0 <small>p73</small> | | 1515 (4040) | | | | 1.0μH | | 22μH | | | |
| | LQH5BPN_T0 <small>p77</small> | | 2020 (5050) | | | | 470nH | | 22μH | | | |
| | LQH5BPN_T0 <small>p79</small> | | 2020 (5050) | | | | 470nH | | 22μH | | | |
| | LQH31CN_03 <small>p90</small> | | 1206 (3216) | | | | 120nH | | 100μH | | | |
| | LQH32CN_23/33 <small>p91</small> | | 1210 (3225) | | | | 150nH | | 560μH | | | |
| | LQH32CN_53 <small>p93</small> | | 1210 (3225) | | | | 1.0μH | | 100μH | | | |
| | LQH43CN_03 <small>p94</small> | | 1812 (4532) | | | | 1.0μH | | 470μH | | | |
| | LQH43CN_33 <small>p95</small> | | 1812 (4532) | | | | 560nH | | 3.9μH | | | |
| | LQH55DN_03 <small>p96</small> | | 2220 (5750) | | | | 120nH | | | | 10mH | |
| | LQH66SN_03 <small>p98</small> | | 2525 (6363) | | | | 270nH | | | | 10mH | |
| | LQM18PN_B0 <small>p16</small> | | 0603 (1608) | | | | | | 1.5μH | | | |
| | LQM18PN_C0 <small>p17</small> | | 0603 (1608) | | | | | | 470nH | | 2.2μH | |
| | LQM18PN_D0 <small>p18</small> | | 0603 (1608) | | | | | | 2.5μH | | | |
| | LQM18PN_F0 <small>p19</small> | | 0603 (1608) | | | | | | 1.0μH | | | |
| | LQM18PN_FR <small>p20</small> | | 0603 (1608) | | | | | | 220nH | | 4.7μH | |
| | LQM21PN_C0 <small>p22</small> | | 0805 (2012) | | | | | | 470nH | | 2.2μH | |
| | LQM21PN_G0 <small>p23</small> | | 0805 (2012) | | | | | | 470nH | | 3.3μH | |
| | LQM21PN_GS <small>p24</small> | | 0805 (2012) | | | | | | 2.2μH | | 4.7μH | |
| | LQM21PN_GC <small>p25</small> | | 0805 (2012) | | | | | | 1.0μH | | 2.2μH | |
| | LQM21PN_GR <small>p26</small> | | 0805 (2012) | | | | | | 1.0μH | | 4.7μH | |
| | LQM2MPN_G0 <small>p27</small> | | 0806 (2016) | | | | | | 470nH | | 4.7μH | |
| | LQM2MPN_GH <small>p29</small> | | 0806 (2016) | | | | | | 160nH | | 2.2μH | |
| | LQM2HPN_G0 <small>p34</small> | | 1008 (2520) | | | | | | 470nH | | 4.7μH | |
| | LQM2HPN_GS <small>p35</small> | | 1008 (2520) | | | | | | 2.2μH | | 4.7μH | |
| | LQM2HPN_GC <small>p36</small> | | 1008 (2520) | | | | | | 1.0μH | | 4.7μH | |
| LQM2HPN_GH <small>p37</small> | 1008 (2520) | | | | | | 470nH | | 2.2μH | | | |
| LQM2HPN_J0 <small>p31</small> | 1008 (2520) | | | | | | 1.0μH | | 3.3μH | | | |
| LQM2HPN_JC <small>p33</small> | 1008 (2520) | | | | | | 1.0μH | | 2.2μH | | | |
| LQM2HPN_JH <small>p32</small> | 1008 (2520) | | | | | | 470nH | | 2.2μH | | | |
| LQM2HPN_E0 <small>p38</small> | 1008 (2520) | | | | | | | | 560nH | | | |
| LQM31PN_00 <small>p39</small> | 1206 (3216) | | | | | | 470nH | | 4.7μH | | | |
| LQM31PN_C0 <small>p40</small> | 1206 (3216) | | | | | | 470nH | | 2.2μH | | | |
| LQM32PN_G0 <small>p41</small> | 1210 (3225) | | | | | | 1.0μH | | | | | |
| LQM18FN_00 <small>p81</small> | 0603 (1608) | | | | | | 1.0μH | | 10μH | | | |
| LQM21DN_00 <small>p82</small> | 0805 (2012) | | | | | | 1.0μH | | 47μH | | | |
| LQM21FN_00 <small>p83</small> | 0805 (2012) | | | | | | 1.0μH | | 47μH | | | |
| LQM21FN_70 <small>p84</small> | 0805 (2012) | | | | | | 4.7μH | | 10μH | | | |
| LQM21FN_80 <small>p85</small> | 0805 (2012) | | | | | | 4.7μH | | 10μH | | | |
| Inductors for General Use | LQB15NN_10 <small>p119</small> | Multilayer Type (Ferrite Core) | 0402 (1005) | | | 220nH | | 560nH | | | | |
| | LQB18NN_10 <small>p121</small> | | 0603 (1608) | | | 220nH | | 560nH | | | | |
| | LQM18NN_00 <small>p123</small> | | 0603 (1608) | | | 47nH | | 2.2μH | | | | |
| | LQM21NN_10 <small>p125</small> | Wire Wound Type (Ferrite Core) | 0805 (2012) | | | 100nH | | 4.7μH | | | | |
| | LQH31MN_03 <small>p127</small> | | 1206 (3216) | | | 150nH | | 100μH | | | | |
| | LQH32MN_23 <small>p129</small> | | 1210 (3225) | | | 1.0μH | | 560μH | | | | |
| | LQH43M(N)N_03 <small>p131</small> | | 1812 (4532) | | | 1.0μH | | 2.2mH | | | | |
| LQH44NN_03 <small>p134</small> | 1515 (4040) | | | | 510nH | | 470μH | | | | | |

Inductance Lineup

- : E-24 or Higher
- : E-12
- : 0.1nH Step
- : Other



*There are some items that do not match to E step.

CAUTION: Use rosin-based flux, but not strong acidic flux (with chlorine content exceeding 0.2wt%) when soldering chip inductors (chip coils). Do not use water-soluble flux.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| | Part Number | Rated Current (A) | | | | Thickness max. | Low Rdc | Bias | E-12 Step | E-24 Step | HiQ | Tight Tolerance | FlowOK | New |
|---------------------------|---------------|-------------------|-------|-------|--------|-------------------|---------|------|--------------|--------------|-----|--------------------|----------|-----|
| | | 10m | 100m | 1 | 10 | | | | | | | | | |
| Inductors for Power Lines | LQW15CN_00 | p86 | | 390mA | 1.4A | 0.6mm | | | | | | | | |
| | LQW15CN_10 | p87 | | 300mA | 450mA | 0.6mm | | | | | | | New | |
| | LQW18CN_00 | p89 | | 430mA | 2.6A | 0.95mm | | | | | | | | |
| | LQH2MCN_02 | p42 | | 90mA | 485mA | 0.95mm | | | | | | | | |
| | LQH2MCN_52 | p44 | | 130mA | 595mA | 0.7mm | | | | | | | | |
| | LQH2HPN_G0 | p46 | | 130mA | 1.0A | 1.0mm | | | | | | | | |
| | LQH2HPN_GR | p48 | | 430mA | 2.52A | 1.0mm | Low Rdc | | | | | | New | |
| | LQH2HPN_J0 | p50 | | 550mA | 1.5A | 1.2mm | | | | | | | | |
| | LQH2HPN_M0 | p52 | | 800mA | 1.25A | 1.5mm | | | | | | | | |
| | LQH3NPN_G0 | p59 | | 130mA | 1.525A | 1.0mm | | | | | | | | |
| | LQH3NPN_J0 | p57 | | 350mA | 1.62A | 1.2mm | | | | | | | | |
| | LQH3NPN_M0 | p53 | | 240mA | 2.05A | 1.5mm | | | | | | | | |
| | LQH3NPN_MR | p55 | | 460mA | 2.15A | 1.5mm | Low Rdc | | | | | | | |
| | LQH32PN_NO | p61 | | 200mA | 2.55A | 1.7mm | | | | | | | | |
| | LQH32PN_NC | p63 | | 550mA | 2.9A | 1.7mm | | Bias | | | | | | |
| | LQH32PB_NO | p65 | | 200mA | 2.55A | 1.7mm | | | | | | | | |
| | LQH32PB_NC | p67 | | 550mA | 2.9A | 1.7mm | | Bias | | | | | | |
| | LQH43PN_26 | p69 | | 240mA | 3.3A | 2.8mm | | | | | | | Flow | |
| | LQH43PB_26 | p71 | | 240mA | 3.3A | 2.8mm | | | | | | | New | |
| | LQH44PN_J0 | p75 | | 380mA | 1.53A | 1.2mm | | | | | | | | |
| | LQH44PN_P0 | p73 | | 790mA | 2.45A | 1.8mm | | | | | | | | |
| | LQH5BPN_T0 | p77 | | 1.05A | 4.0A | 2.2mm | | | | | | | | |
| | LQH5BPB_T0 | p79 | | 1.05A | 4.0A | 2.2mm | | | | | | | New | |
| | LQH31CN_03 | p90 | | 80mA | 970mA | 2.0mm | | | | | | | Flow | |
| | LQH32CN_23/33 | p91 | | 60mA | 1.45A | 2.2mm | | | | | | | Flow | |
| | LQH32CN_53 | p93 | | 100mA | 1.0A | 1.7mm | | | | | | | Flow | |
| | LQH43CN_03 | p94 | | 90mA | 1.08A | 2.8mm | | | | | | | Flow | |
| | LQH43CN_33 | p95 | | | 1.6A | 2.95A | 2.8mm | | | | | | Flow | |
| | LQH55DN_03 | p96 | | 50mA | 6.0A | 5.0mm | | | | | | | | |
| | LQH66SN_03 | p98 | | 50mA | 6.0A | 5.0mm | | | | | | | | |
| | LQM18PN_B0 | p16 | | 600mA | | 0.4mm | | | | | | | Flow | |
| | LQM18PN_C0 | p17 | | 700mA | 850mA | 0.55mm | | | | | | | Flow New | |
| | LQM18PN_D0 | p18 | | 700mA | | 0.75mm | | | | | | | Flow | |
| | LQM18PN_F0 | p19 | | 600mA | | 0.95mm | | | | | | | Flow | |
| | LQM18PN_FR | p20 | | 620mA | 1.25A | 0.95mm | Low Rdc | | | | | | Flow | |
| | LQM21PN_C0 | p22 | | 600mA | 1.1A | 0.55mm | | | | | | | Flow | |
| | LQM21PN_G0 | p23 | | 800mA | 1.3A | 1.0mm | | | | | | | Flow | |
| | LQM21PN_GS | p24 | | 750mA | 950mA | 1.0mm | | | | | | | Flow | |
| | LQM21PN_GC | p25 | | 800mA | 900mA | 1.0mm | | Bias | | | | | Flow | |
| | LQM21PN_GR | p26 | | 800mA | 1.3A | 1.0mm | Low Rdc | | | | | | Flow | |
| | LQM2MPN_G0 | p27 | | 1.1A | 1.6A | 1.0mm | | | | | | | Flow | |
| | LQM2MPN_GH | p29 | | 1.0A | 4.0A | 1.0mm | Low Rdc | Bias | | | | | New | |
| | LQM2HPN_G0 | p34 | | 1.1A | 1.8A | 1.0mm | | | | | | | Flow | |
| | LQM2HPN_GS | p35 | | 1.0A | 1.1A | 1.0mm | | | | | | | Flow | |
| | LQM2HPN_GC | p36 | | 800mA | 1.5A | 1.0mm | | Bias | | | | | Flow | |
| | LQM2HPN_GH | p37 | | 1.5A | 2.6A | 1.0mm | Low Rdc | Bias | | | | | New | |
| | LQM2HPN_J0 | p31 | | 1.0A | 1.5A | 1.2mm | | | | | | | Flow | |
| | LQM2HPN_JC | p33 | | 1.0A | 1.5A | 1.2mm | | Bias | | | | | Flow | |
| LQM2HPN_JH | p32 | | 1.5A | 2.7A | 1.2mm | Low Rdc | Bias | | | | | New | | |
| LQM2HPN_E0 | p38 | | | 1.5A | 0.8mm | | | | | | | Flow | | |
| LQM31PN_O0 | p39 | | 700mA | 1.4A | 0.95mm | | | | | | | Flow | | |
| LQM31PN_C0 | p40 | | 900mA | 1.3A | 0.55mm | | | | | | | Flow | | |
| LQM32PN_G0 | p41 | | | 1.8A | 1.0mm | | | | | | | | | |
| LQM18FN_00 | p81 | | 50mA | 150mA | 0.9mm | | | | | | | Flow | | |
| LQM21DN_00 | p82 | 7.0mA | 60mA | | 1.45mm | | | | | | | Flow | | |
| LQM21FN_00 | p83 | 7.0mA | 220mA | | 1.45mm | | | | | | | Flow | | |
| LQM21FN_70 | p84 | | 100mA | 120mA | 1.45mm | | | | | | | Flow | | |
| LQM21FN_80 | p85 | | 100mA | 120mA | 1.45mm | | | | | | | Flow | | |
| Inductors for General Use | LQB15NN_10 | p119 | | 300mA | 380mA | 0.55mm | | | E-12 | | | | New | |
| | LQB18NN_10 | p121 | | 300mA | 450mA | 0.95mm | | | E-12 | | | | Flow New | |
| | LQM18NN_00 | p123 | 15mA | 50mA | | 0.95mm | | | E-12 | | | | Flow | |
| | LQM21NN_10 | p125 | 30mA | 250mA | | 1.45mm | | | E-12 | | | | Flow | |
| | LQH31MN_03 | p127 | | 45mA | 250mA | 2.0mm | | | E-12 | | | | Flow | |
| | LQH32MN_23 | p129 | | 40mA | 445mA | 2.2mm | | | E-12 | | | | Flow | |
| | LQH43M(N)N_03 | p131 | | 30mA | 500mA | 2.8mm | | | E-12 | | | | Flow | |
| | LQH44NN_03 | p134 | | 145mA | 4.5A | 4.5mm | | | | | | | New | |

Continued on the following page. 

 Note • Please read rating and  CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



| | Part Number | Structure | Size Code in inch (in mm) | Inductance Range (H) | | | | | | | |
|--------------|--------------------------------|--|------------------------------|----------------------|-------|-------|-------|-----|------|----|-----|
| | | | | 1n | 10n | 100n | 1μ | 10μ | 100μ | 1m | 10m |
| RF Inductors | LQG15HN_02 <small>p148</small> | Multilayer Type (Non-Magnetic Core) | 0402 (1005) | 1.0nH | 120nH | | | | | | |
| | LQG15HS_02 <small>p150</small> | | 0402 (1005) | 1.0nH | 270nH | | | | | | |
| | LQG18HN_00 <small>p153</small> | | 0603 (1608) | 1.2nH | 100nH | | | | | | |
| | LQP02TN_02 <small>p155</small> | Film Type (Non-Magnetic Core) | 01005 (0402) | 0.2nH | 39nH | | | | | | |
| | LQP02TQ_02 <small>p161</small> | | 01005 (0402) | 0.4nH | 10nH | | | | | | |
| | LQP03TG_02 <small>p164</small> | | 0201 (0603) | 0.6nH | 120nH | | | | | | |
| | LQP03TN_02 <small>p169</small> | | 0201 (0603) | 0.6nH | 270nH | | | | | | |
| | LQP15MN_02 <small>p174</small> | | 0402 (1005) | 1.0nH | 33nH | | | | | | |
| | LQP18MN_02 <small>p177</small> | | 0603 (1608) | 1.3nH | 100nH | | | | | | |
| | LQW03AW_00 <small>p179</small> | Wire Wound Type (Non-Magnetic Core) | - | | 5.4nH | 13nH | | | | | |
| | LQW04AN_00 <small>p181</small> | | 03015 (0804) | 1.1nH | 33nH | | | | | | |
| | LQW15AN_00 <small>p184</small> | | 0402 (1005) | 1.5nH | 120nH | | | | | | |
| | LQW15AN_10 <small>p189</small> | | 0402 (1005) | 1.3nH | 5.6nH | | | | | | |
| | LQW15AN_80 <small>p191</small> | | 0402 (1005) | 1.3nH | 75nH | | | | | | |
| | LQW18AN_00 <small>p199</small> | | 0603 (1608) | 2.2nH | 470nH | | | | | | |
| | LQW18AN_10 <small>p203</small> | | 0603 (1608) | 2.2nH | 33nH | | | | | | |
| | LQW18AN_80 <small>p205</small> | | 0603 (1608) | 2.2nH | 390nH | | | | | | |
| | LQW2BAS_00 <small>p213</small> | | 0805 (2015) | 2.8nH | 820nH | | | | | | |
| | LQW2BHN_03 <small>p209</small> | | 0805 (2015) | 3.3nH | 470nH | | | | | | |
| | LQW2BHN_13 <small>p211</small> | | 0805 (2015) | 2.7nH | 27nH | | | | | | |
| | LQW2UAS_00 <small>p216</small> | | 1008 (2520) | | 12nH | 4.7μH | | | | | |
| | LQW31HN_03 <small>p219</small> | | 1206 (3216) | | 8.8nH | 100nH | | | | | |
| | LQW21HN_00 <small>p221</small> | | 0805 (2012) | | | 470nH | 2.2μH | | | | |
| | LQH31HN_03 <small>p223</small> | | 1206 (3216) | | | 54nH | 880nH | | | | |

Inductance Lineup

- : E-24 or Higher
- : E-12
- : 0.1nH Step
- : Other

*There are some items that do not match to E step.

CAUTION: Use rosin-based flux, but not strong acidic flux (with chlorine content exceeding 0.2wt%) when soldering chip inductors (chip coils). Do not use water-soluble flux.

Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| | Part Number | Rated Current (A) | | | | Thickness max. | Low Rdc | Bias | E-12 Step | E-24 Step | Hi Q | Tight Tolerance | Flow OK | New |
|-----------------|-----------------|-------------------|-------|-------|-------|-------------------|---------|------|--------------|--------------|--------|--------------------|---------|-----|
| | | 10m | 100m | 1 | 10 | | | | | | | | | |
| RF Inductors | LQG15HN_02 p148 | | 150mA | 300mA | | 0.55mm | | | E-12 | E-24 | | | | |
| | LQG15HS_02 p150 | | 110mA | 300mA | | 0.55mm | | | E-12 | E-24 | | | | |
| | LQG18HN_00 p153 | | | 300mA | 500mA | 0.95mm | | | E-12 | | | | | |
| | LQP02TN_02 p155 | | 90mA | 320mA | | 0.22mm | | | | E-24 | | Tight | New | |
| | LQP02TQ_02 p161 | | 170mA | 990mA | | 0.22mm | | | E-12 | E-24 | High Q | Tight | New | |
| | LQP03TG_02 p164 | | 80mA | 850mA | | 0.33mm | | | E-12 | E-24 | | Tight | New | |
| | LQP03TN_02 p169 | | 60mA | 850mA | | 0.33mm | | | | E-24 | | Tight | New | |
| | LQP15MN_02 p174 | | 60mA | 400mA | | 0.45mm | | | E-12 | E-24 | | Tight | | |
| | LQP18MN_02 p177 | | 50mA | 300mA | | 0.6mm | | | E-12 | E-24 | | Tight | | |
| | LQW03AW_00 p179 | | 280mA | 460mA | | 0.45mm | | | E-12 | E-24 | | | New | |
| | LQW04AN_00 p181 | | 140mA | 990mA | | 0.45mm | | | E-12 | E-24 | | | | |
| | LQW15AN_00 p184 | | 110mA | 1.0A | | 0.6mm | | | E-12 | E-24 | | Tight | | |
| | LQW15AN_10 p189 | | | 800mA | 1.2A | 0.6mm | Low Rdc | | E-12 | E-24 | High Q | Tight | | |
| | LQW15AN_80 p191 | | | 320mA | 3.15A | 0.6mm | Low Rdc | | E-12 | E-24 | High Q | Tight | New | |
| | LQW18AN_00 p199 | | 75mA | 850mA | | 1.0mm | | | E-12 | E-24 | | Tight | | |
| | LQW18AN_10 p203 | | | 550mA | 1.4A | 1.0mm | Low Rdc | | E-12 | | High Q | Tight | | |
| | LQW18AN_80 p205 | | 190mA | 3.2A | | 1.0mm | Low Rdc | | E-12 | E-24 | | Tight | New | |
| | LQW2BAS_00 p213 | | 180mA | 800mA | | 1.52mm | | | E-12 | E-24 | | | | |
| | LQW2BHN_03 p209 | | 160mA | 1.32A | | 1.78mm | | | E-12 | | | Tight | Flow | |
| | LQW2BHN_13 p211 | | | 900mA | 1.9A | 1.78mm | | | E-12 | | High Q | | Flow | |
| | LQW2UAS_00 p216 | | 260mA | 1.0A | | 2.03mm | | | E-12 | E-24 | | | | |
| | LQW31HN_03 p219 | | 230mA | 750mA | | 2.0mm | | | E-12 | | | | Flow | |
| | LQW21HN_00 p221 | | 75mA | 160mA | | 1.0mm | | | E-12 | | | | | |
| LQH31HN_03 p223 | | 180mA | 920mA | | 2.0mm | | | | | | | Flow | | |

Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Construction?

| Circuit Type? | Construction? | | |
|---|---|--|---|
| | Wire Wound | Multilayer | Film |
| Power Line | LQW15CN/0402(1005) p86 18–560nH/300–1400mA | LQM18PN/0603(1608) p16 0.22–4.7μH/600–1250mA | |
| | LQW18CN/0603(1608) p89 4.9–650nH/430–2600mA | LQM21PN/0805(2012) p22 0.47–4.7μH/600–1300mA(*1) | |
| | LQH2MCN/0806(2016) p42 1.0–82μH/90–595mA | LQM2MPN/0806(2016) p27 0.16–4.7μH/1100–4000mA | |
| | LQH2HPN/1008(2520) p46 0.47–100μH/130–2520mA | LQM2HPN/1008(2520) p34 0.47–4.7μH/800–2700mA | |
| | LQH3NPN/1212(3030) p59 1.0–250μH/130–2150mA | LQM31PN/1206(3216) p39 0.47–4.7μH/700–1400mA | |
| | LQH32PN/1210(3225) p61 0.47–120μH/200–2900mA | LQM32PN/1210(3225) p41 1.0μH/1800mA | |
| | LQH32PB/1210(3225) p65 0.47–120μH/200–2900mA | LQM18FN/0603(1608) p81 1.0–10μH/50–150mA | |
| | LQH43PN/1812(4532) p69 1.0–220μH/240–3300mA | LQM21DN/0805(2012) p82 1.0–47μH/7–60mA | |
| | LQH43PB/1812(4532) p71 1.0–220μH/240–3300mA | LQM21FN/0805(2012) p83 1.0–47μH/7–220mA | |
| | LQH44PN/1515(4040) p75 1.0–47μH/380–2450mA | | |
| | LQH5BPN/2020(5050) p77 0.47–22μH/1.05–4.0A | | |
| | LQH5BPB/2020(5050) p79 0.47–22μH/1.05–4.0A | | |
| | LQH31CN/1206(3216) p90 0.12–100μH/80–970mA | | |
| | LQH32CN/1210(3225) p91 0.15–560μH/60–1450mA | | |
| | LQH43CN/1812(4532) p94 0.56–470μH/90–2950mA | | |
| LQH55DN/2220(5750) p96 0.12–10000μH/0.05–6.0A | | | |
| LQH66SN/2525(6363) p98 0.27–10000μH/0.05–6.0A | | | |
| Less than 100MHz General Use | LQH31MN/1206(3216) p127 0.15–100μH/45–250mA | LQB15NN/0402(1005) p119 220–560nH/300–380mA | |
| | LQH32MN/1210(3225) p129 1.0–560μH/40–445mA | LQB18NN/0603(1608) p121 220–560nH/300–450mA | |
| | LQH43MN/1812(4532) p131 1.0–2200μH/30–500mA | LQM18NN/0603(1608) p123 47–2200nH/15–50mA | |
| | LQH44NN/1515(4040) p134 0.51–470μH/0.145–4.5A | LQM21NN/0805(2012) p125 0.1–4.7μH/30–250mA | |
| Signal Line High Frequency Greater than 100MHz | LQW03AW/- p179 5.4–13nH/280–460mA | LQG15HN/0402(1005) p148 1.0–120nH/150–300mA | LQP02TN/01005(0402) p155 0.2–39nH/90–320mA |
| | LQW04AN/03015(0804) p181 1.1–33nH/140–990mA | LQG15HS/0402(1005) p150 1.0–270nH/110–300mA | LQP02TQ/01005(0402) p161 0.4–10nH/170–990mA |
| | LQW15AN/0402(1005) p184 1.3–120nH/110–3150mA | LQG18HN/0603(1608) p153 1.2–100nH/300–500mA | LQP03TG/0201(0603) p164 0.6–120nH/80–850mA |
| | LQW18AN/0603(1608) p199 2.2–470nH/75–3200mA | | LQP03TN/0201(0603) p169 0.6–270nH/60–850mA |
| | LQW2BHN/0805(2015) p209 2.7–470nH/160–1900mA | | LQP15MN/0402(1005) p174 1.0–33nH/60–400mA |
| | LQW2BAS/0805(2015) p213 2.8–820nH/180–800mA | | LQP18MN/0603(1608) p179 1.3–100nH/50–300mA |
| | LQW2UAS/1008(2520) p216 12–4700nH/260–1000mA | | |
| | LQW31HN/1206(3216) p219 8.8–100nH/230–750mA | | |
| | LQW21HN/0805(2012) p221 0.47–2.2μH/75–160mA | | |
| | LQH31HN/1206(3216) p223 54–880nH/180–920mA | | |

Guide for Digits in this Chart:

● for LQW15CN 0402 (1005)/18–560nH/300–1400mA

Size (inch) Size (mm) Inductance Rated Current

*1 In operating temperature exceeding +85°C, derating of current is necessary for LQM21PN3R3NG0/LQM21PN3R3MG0-LQW15C series. Please apply the derating curve shown in detailed page according to the operating temperature.

⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc. • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



Which Thickness?

Inductors for Power Lines

| Which Thickness? | Inductors for Power Lines | | | |
|------------------|--|--|--|---------------------------|
| | Multilayer Type | Wire Wound Type | Multilayer Type for Choke | Wire Wound Type for Choke |
| 0.35mm | LQM18P_B0 | | | |
| 0.5mm | LQM18P_C0 / LQM21P_C0 / LQM31P_C0 | | | LQW15C |
| 0.6mm | LQM18P_D0 | | | |
| 0.65mm | | LQH2MC_52 | | |
| 0.7mm | LQM2HP_E0 | | | |
| 0.8mm | LQM18P_F0 / FR | | LQM18F | LQW18C |
| 0.85mm | LQM31P_00 | | LQM21D (1.0 to 10μH) / LQM21F_00 (1.0 to 2.2μH) | |
| 0.9mm | LQM21P_G0 / GS / GC / GR / LQM2MP_G0 / GH / LQM2HP_G0 / GS / GC / GH / LQM32P_G0 | LQH2MC_02 / LQH2HP_G0 / GR / LQH3NP_G0 | | |
| 1.1mm | LQM2HP_J0 / JH | LQH2HP_J0 / LQH3NP_J0 / LQH44P_J0 | | |
| 1.25mm | | | LQM21D (22 to 47μH) / LQM21F_00 (4.7 to 47μH) / LQM21F_70 / 80 | |
| 1.4mm | | LQH2HP_M0 / LQH3NP_M0 / MR | | |
| 1.55mm | | LQH32P_N0 / NC | | LQH32C_53 |
| 1.65mm | | LQH44P_P0 | | |
| 1.8mm | | | | LQH31C |
| 2.0mm | | LQH5BP_T0 | | LQH32C_23 / 33 |
| 2.6mm | | LQH43P_26 | | LQH43C_03 / 33 |
| 4.7mm | | | | LQH55D / LQH66S |

Which Thickness?

Inductors for General Use

RF Inductors

| Which Thickness? | Inductors for General Use | | RF Inductors | | |
|------------------|---------------------------|-----------------|-------------------|-----------|------------------|
| | Multilayer Type | Wire Wound Type | Multilayer Type | Film Type | Wire Wound Type |
| 0.2mm | | | | LQP02T | |
| 0.3mm | | | | LQP03T | |
| 0.35mm | | | | LQP15M | |
| 0.4mm | | | | LQP15T | LQW03AW / LQW04A |
| 0.5mm | LQB15N | | LQG15HN / LQG15HS | LQP18M | LQW15A |
| 0.8mm | LQB18N / LQM18N | | LQG18H | | LQW18A |
| 0.85mm | LQM21N (0.1 to 2.2μH) | | | | |
| 0.9mm | | | | | LQW21H |
| 1.25mm | LQM21N (2.7 to 4.7μH) | | | | |
| 1.42mm | | | | | LQW2BA |
| 1.7mm | | | | | LQW2BH |
| 1.8mm | | LQH31M | | | LQH31H / LQW31H |
| 1.83mm | | | | | LQW2UA |
| 2.0mm | | LQH32M | | | |
| 2.6mm | | LQH43M(N) | | | |
| 4.3mm | | LQH44N | | | |

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



Memo

● Inductors for Power Lines

| | |
|------------------------------|-----|
| Introduction | 12 |
| Part Numbering | 14 |
| Product Detail | 16 |
| ⚠Caution/Notice | 100 |
| Soldering and Mounting | 102 |
| Packaging | 107 |
| Design Kits | 111 |

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


Introduction of Power Inductors

Effect of losses in power Inductors to voltage conversion efficiency

Important factor of power Inductors changes according to working condition of power supply.


● Effect of Magnetic Loss

Magnetic loss affect to efficiency at low output condition.



● Effect of DC Resistance


DC resistance affect to efficiency at high output condition.



We design inductors to match the application using the latest simulation technology.




● Power Inductors Wire Wound Type Lineup (Core Product)




Δ Note • Please read rating and Δ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

● Power Inductors Multilayer Type Size Code: 2012 max. (Core Product)




● Power Inductors Multilayer Type Size Code: 2016 min. (Core Product)



△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Inductors for Power Lines Part Numbering



① Product ID

| Product ID | |
|------------|-----------------------------|
| LQ | Chip Inductors (Chip Coils) |

② Structure

| Code | Structure |
|------|--------------------------------|
| H | Wire Wound Type (Ferrite Core) |
| W | |
| M | Multilayer Type (Ferrite Core) |

③ Dimensions (L×W)

| Code | Dimensions (L×W) | Size Code (in inch) |
|------|------------------|---------------------|
| 15 | 1.0×0.5mm | 0402 |
| 18 | 1.6×0.8mm | 0603 |
| 21 | 2.0×1.25mm | 0805 |
| 2M | 2.0×1.6mm | 0806 |
| 2H | 2.5×2.0mm | 1008 |
| 3N | 3.0×3.0mm | 1212 |
| 31 | 3.2×1.6mm | 1206 |
| 32 | 3.2×2.5mm | 1210 |
| 43 | 4.5×3.2mm | 1812 |
| 44 | 4.0×4.0mm | 1515 |
| 5B | 5.0×5.0mm | 2020 |
| 55 | 5.7×5.0mm | 2220 |
| 66 | 6.3×6.3mm | 2525 |

④ Applications and Characteristics

| Code | Series | Applications and Characteristics |
|------|---------|---|
| D | LQM | for Choke (Low-current DC Power Supplies) |
| F | | for Choke (DC Power Supplies) |
| D | LQH | for Choke |
| S | | for Choke (Magnetically Shielded Type) |
| C | LQH/LQW | for Choke (Coating Type) |
| P | LQM/LQH | for Power Line |

⑤ Category

| Code | Category |
|------|--------------------------------|
| N | Standard Type |
| B | Special Feature Classification |

⑥ Inductance

Expressed by three-digit alphanumerics. The unit is micro-henry (μH). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two figures. If there is a decimal point, it is expressed by the capital letter "R." In this case, all figures are significant digits. If inductance is less than 0.1μH, the inductance code is expressed by a combination of two figures and the capital letter "N," and the unit of inductance is nano-henry (nH). The capital letter "N" indicates the unit of "nH," and also expresses a decimal point. In this case, all figures are significant digits.

⑦ Inductance Tolerance

| Code | Inductance Tolerance |
|------|----------------------|
| D | ±0.5nH |
| J | ±5% |
| K | ±10% |
| M | ±20% |
| N | ±30% |

⑧ Features (Except for LQH□□P/LQM□□P)

| Code | Features | Series |
|------|---------------------------------------|----------------|
| 0 | Standard Type | LQM/LQH*1 /LQW |
| 1 | Low DC Resistance | LQW |
| 2 | Standard Type | LQH32C |
| 3 | Low DC Resistance | LQH32C/43CN |
| 5 | Low Profile Type | LQH2MC/32C |
| 7 | Large Current Type | LQM21F |
| 8 | Low DC Resistance /Large Current Type | |

*1 Except for LQH32 Series

⑨ Thickness (LQH□□P/LQM□□P Only • Except for LQH43P)

| Code | Dimensions (T) |
|------|----------------|
| B | 0.35mm |
| C | 0.5mm |
| D | 0.6mm |
| E | 0.7mm |
| F | 0.8mm |
| 0 | 0.85mm |
| G | 0.9mm |
| J | 1.1mm |
| M | 1.4mm |
| N | 1.55mm |
| P | 1.65mm |
| T | 2.0mm |

⑩ Electrode (Except for LQH□□P/LQM□□P)

•Lead (Pb) Free

| Code | Electrode | Series |
|------|-----------|-------------------------|
| 0 | Sn | LQM/LQW |
| 2 | | LQH2MC |
| 3 | LF Solder | LQH (Except for LQH2MC) |

⑪ Specification (LQH□□P/LQM□□P Only • Except for LQH43P)

| Code | Specification |
|------|--|
| 0/S | Standard Type |
| C | Good Bias Current Characteristics Type |
| H | High Spec Type (Low DC Resistance/ Good Bias Current Characteristics Type) |
| R | Low DC Resistance Type |

Continued on the following page. 

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

⑧⑨ Thickness (LQH43P Only)

| Code | Dimensions (T) |
|------|----------------|
| 26 | 2.6mm |

⑩ Packaging

| Code | Packaging | Series |
|------|-------------------------------|--|
| K | Embossed Taping (ø330mm Reel) | LQH*1 /LQM21*2 |
| F | | LQH3NP_MR |
| L | Embossed Taping (ø180mm Reel) | LQH*5/LQM18P/LQM21*2 /LQM31P/LQM2HP/LQM2MP |
| E | | LQH3NP_MR |
| B | Bulk | LQH2MC/LQM/LQW |
| J | Paper Taping (ø330mm Reel) | LQM18/LQM21*3 |
| D | Paper Taping (ø180mm Reel) | LQM18/LQM21*4 /LQW |

*1 Except for LQH2MC/LQH2HP_G0/LQH3NP/LQH43C

*2 LQM21D(22 - 47μH)/LQM21F(4.7 - 47μH)

*3 LQM21D(1.0 - 10μH)/LQM21F(1.0 - 2.2μH)


*4 LQM21D(1.0 - 10μH)/LQM21F(1.0 - 2.2μH)/LQM21P

*5 Except for LQH3NP_MR

LQM18PN_B0 Series 0603/1608 (inch/mm)

Size Code 0603 (1608) in inch (in mm), 0.4mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 4000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM18PN1R5NB0□ | 1.5µH ±30% | 1MHz | 600mA | 0.35Ω ±25% | 50MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -55°C~+125°C


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM18PN_C0 Series 0603/1608 (inch/mm)

Size Code 0603 (1608) in inch (in mm), 0.55mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 4000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM18PNR47NC0□ | 0.47μH ±30% | 1MHz | 850mA | 0.15 Ω ±25% | 50MHz | New |
| LQM18PN1R0NC0□ | 1.0μH ±30% | 1MHz | 750mA | 0.20 Ω ±25% | 50MHz | New |
| LQM18PN1R5NC0□ | 1.5μH ±30% | 1MHz | 720mA | 0.22 Ω ±25% | 50MHz | New |
| LQM18PN1R8NC0□ | 1.8μH ±30% | 1MHz | 700mA | 0.24 Ω ±25% | 50MHz | Kit |
| LQM18PN2R2NC0□ | 2.2μH ±30% | 1MHz | 700mA | 0.24 Ω ±25% | 50MHz | New |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -55°C~+125°C


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM18PN_D0

Series 0603/1608 (inch/mm)

Size Code 0603 (1608) in inch (in mm), 0.75mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM18PN2R5ND0□ | 2.5μH ±30% | 1MHz | 700mA | 0.24Ω ±25% | 60MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -40°C~+85°C


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM18PN_F0 Series 0603/1608 (inch/mm)

Size Code 0603 (1608) in inch (in mm), 0.95mm max. Thickness

■ Appearance/Dimensions



(in mm)

■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 4000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM18PN1R0NF0□ | 1.0μH ±30% | 1MHz | 600mA | 0.28Ω ±25% | 50MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -55°C~+125°C


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM18PN_FR Series 0603/1608 (inch/mm)

Low DC Resistance Type


Appearance/Dimensions



(in mm)

Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 4000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM18PNR22NFR□ | 0.22μH ±30% | 1MHz | 1250mA | 0.11 Ω ±25% | 100MHz | Kit |
| LQM18PNR47NFR□ | 0.47μH ±30% | 1MHz | 1100mA | 0.15 Ω ±25% | 100MHz | Kit |
| LQM18PN1R0MFR□ | 1.0μH ±20% | 1MHz | 950mA | 0.20 Ω ±25% | 100MHz | Kit |
| LQM18PN1R5MFR□ | 1.5μH ±20% | 1MHz | 800mA | 0.23 Ω ±25% | 100MHz | Kit |
| LQM18PN2R2MFR□ | 2.2μH ±20% | 1MHz | 750mA | 0.30 Ω ±25% | 70MHz | Kit |
| LQM18PN3R3MFR□ | 3.3μH ±20% | 1MHz | 700mA | 0.35 Ω ±25% | 60MHz | Kit |
| LQM18PN4R7MFR□ | 4.7μH ±20% | 1MHz | 620mA | 0.44 Ω ±25% | 40MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -40°C~+85°C

Inductance-Frequency Characteristics (Typ.)




Inductance-Current Characteristics (Typ.)



Continued on the following page.

Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


■ Temperature Rise Characteristics (Typ.)



LQM21PN_CO Series 0805/2012 (inch/mm)

Size Code 0805 (2012) in inch (in mm), 0.55mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM21PNR47MC0□ | 0.47μH ±20% | 1MHz | 1100mA | 0.12Ω ±25% | 100MHz | Kit |
| LQM21PN1R0MC0□ | 1.0μH ±20% | 1MHz | 800mA | 0.19Ω ±25% | 90MHz | Kit |
| LQM21PN1R5MC0□ | 1.5μH ±20% | 1MHz | 700mA | 0.26Ω ±25% | 70MHz | Kit |
| LQM21PN2R2MC0□ | 2.2μH ±20% | 1MHz | 600mA | 0.34Ω ±25% | 50MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -55°C~+125°C


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM21PN_G0 Series 0805/2012 (inch/mm)

Size Code 0805 (2012) in inch (in mm), 1.0mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM21PNR47MG0□ | 0.47μH ±20% | 1MHz | 1300mA | 0.075Ω ±25% | 100MHz | Kit |
| LQM21PNR54MG0□ | 0.54μH ±20% | 1MHz | 1300mA | 0.075Ω ±25% | 100MHz | Kit |
| LQM21PN3R3MG0□ | 3.3μH ±20% | 1MHz | 800mA | 0.165Ω ±25% | 30MHz | Kit |
| LQM21PN3R3NG0□ | 3.3μH ±30% | 1MHz | 800mA | 0.165Ω ±25% | 30MHz | |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -55°C~+125°C


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




■ Derating of Rated Current

In operating temperature exceeding +85°C, derating of current is necessary for LQM21PN3R3MG0/LQM21PN3R3NG0. Please apply the derating curve shown in the chart according to the operating temperature.

Derating of Rated Current

(LQM21PN3R3MG0/LQM21PN3R3NG0)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM21PN_GS Series 0805/2012 (inch/mm)

Size Code 0805 (2012) in inch (in mm), 1.0mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ∅180mm Paper Taping | 4000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM21PN2R2MGS□ | 2.2μH ±20% | 1MHz | 950mA | 0.180Ω ±25% | 40MHz | Kit |
| LQM21PN4R7MGS□ | 4.7μH ±20% | 1MHz | 750mA | 0.290Ω ±25% | 20MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -40°C~+85°C


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM21PN_GC Series 0805/2012 (inch/mm)

Bias Current Characteristics Improved

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM21PN1R0NGC□ | 1.0μH ±30% | 1MHz | 900mA | 0.10Ω ±25% | 50MHz | Kit |
| LQM21PN2R2NGC□ | 2.2μH ±30% | 1MHz | 800mA | 0.23Ω ±25% | 40MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -55°C~+125°C


Inductance-Frequency Characteristics (Typ.)



Inductance-Current Characteristics (Typ.)



Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM21PN_GR Series 0805/2012 (inch/mm)


Low DC Resistance Type

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM21PN1R0NGR□ | 1.0μH ±30% | 1MHz | 1300mA | 0.066Ω ±25% | 50MHz | Kit |
| LQM21PN3R3MGR□ | 3.3μH ±20% | 1MHz | 1000mA | 0.150Ω ±25% | 30MHz | Kit |
| LQM21PN3R3NGR□ | 3.3μH ±30% | 1MHz | 1000mA | 0.150Ω ±25% | 30MHz | |
| LQM21PN4R7MGR□ | 4.7μH ±20% | 1MHz | 800mA | 0.23Ω ±25% | 30MHz | Kit |
| LQM21PN4R7NGR□ | 4.7μH ±30% | 1MHz | 800mA | 0.23Ω ±25% | 30MHz | |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -55°C~+125°C


Inductance-Frequency Characteristics (Typ.)



Inductance-Current Characteristics (Typ.)



Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM2MPN_G0 Series 0806/2016 (inch/mm)

Size Code 0806 (2016) in inch (in mm), 1.0mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM2MPNR47MG0□ | 0.47μH ±20% | 1MHz | 1600mA | 0.060 Ω ±25% | 100MHz | Kit |
| LQM2MPNR47NG0□ | 0.47μH ±30% | 1MHz | 1600mA | 0.060 Ω ±25% | 100MHz | |
| LQM2MPN1R0NG0□ | 1.0μH ±30% | 1MHz | 1400mA | 0.085 Ω ±25% | 60MHz | Kit |
| LQM2MPN1R5MG0□ | 1.5μH ±20% | 1MHz | 1200mA | 0.11 Ω ±25% | 50MHz | Kit |
| LQM2MPN1R5NG0□ | 1.5μH ±30% | 1MHz | 1200mA | 0.11 Ω ±25% | 50MHz | |
| LQM2MPN2R2MG0□ | 2.2μH ±20% | 1MHz | 1200mA | 0.11 Ω ±25% | 40MHz | Kit |
| LQM2MPN2R2NG0□ | 2.2μH ±30% | 1MHz | 1200mA | 0.11 Ω ±25% | 40MHz | |
| LQM2MPN3R3NG0□ | 3.3μH ±30% | 1MHz | 1200mA | 0.12 Ω ±25% | 30MHz | Kit |
| LQM2MPN4R7MG0□ | 4.7μH ±20% | 1MHz | 1100mA | 0.14 Ω ±25% | 20MHz | Kit |
| LQM2MPN4R7NG0□ | 4.7μH ±30% | 1MHz | 1100mA | 0.14 Ω ±25% | 20MHz | |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -55°C~+125°C

■ Inductance-Frequency Characteristics (Typ.)




■ Inductance-Current Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Temperature Rise Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM2MPN_GH Series 0806/2016 (inch/mm)

High Spec Type (Low DC Resistance / Good Bias Current Characteristics Type)


■ Appearance/Dimensions



(in mm)

■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | Max. of DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---|--|--------------------------|---------------------------------|-----|
| LQM2MPNR16MGH□ | 0.16μH ±20% | 5.0A(Max)/5.5A(Typ.) | 4.0A(Max)/5.0A(Typ.) | 18mΩ (Max)/14mΩ (Typ.) | 150MHz | New |
| LQM2MPNR24MGH□ | 0.24μH ±20% | 4.8A(Max)/5.0A(Typ.) | 3.4A(Max)/4.4A(Typ.) | 25mΩ (Max)/20mΩ (Typ.) | 130MHz | New |
| LQM2MPNR33MGH□ | 0.33μH ±20% | 3.7A(Max)/3.9A(Typ.) | 3.1A(Max)/4.0A(Typ.) | 30mΩ (Max)/24mΩ (Typ.) | 90MHz | New |
| LQM2MPNR47MGH□ | 0.47μH ±20% | 3.4A(Max)/3.6A(Typ.) | 2.5A(Max)/3.2A(Typ.) | 46mΩ (Max)/37mΩ (Typ.) | 80MHz | New |
| LQM2MPNR68MGH□ | 0.68μH ±20% | 3.1A(Max)/3.4A(Typ.) | 1.9A(Max)/2.5A(Typ.) | 75mΩ (Max)/60mΩ (Typ.) | 60MHz | New |
| LQM2MPN1R0MGH□ | 1.0μH ±20% | 2.0A(Max)/2.3A(Typ.) | 1.9A(Max)/2.4A(Typ.) | 80mΩ (Max)/64mΩ (Typ.) | 60MHz | New |
| LQM2MPN1R5MGH□ | 1.5μH ±20% | 1.8A(Max)/2.0A(Typ.) | 1.5A(Max)/1.9A(Typ.) | 130mΩ (Max)/104mΩ (Typ.) | 50MHz | New |
| LQM2MPN2R2MGH□ | 2.2μH ±20% | 1.3A(Max)/1.5A(Typ.) | 1.0A(Max)/1.3A(Typ.) | 263mΩ (Max)/210mΩ (Typ.) | 40MHz | New |

Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of ferrite

Operating Temperature Range: -40°C~+85°C


For reflow soldering only.

*1 When applied rated current to the products, inductance will be within -30% of initial inductance value. Typical value is actual performance.


*2 When applied rated current to the products, temperature rise caused by self heating will be 40°C or less. Typical value is actual performance.

*3 Keep the temperature of product (ambient temperature plus self-generation of heat) under 125°C.

■ Inductance-Frequency Characteristics (Typ.)




■ Inductance-Current Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Temperature Rise Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM2HPN_J0 Series 1008/2520 (inch/mm)

Size Code 1008 (2520) in inch (in mm), 1.2mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM2HPN1R0MJ0□ | 1.0μH ±20% | 1MHz | 1500mA | 0.09Ω ±25% | 70MHz | Kit |
| LQM2HPN2R2MJ0□ | 2.2μH ±20% | 1MHz | 1000mA | 0.12Ω ±25% | 40MHz | Kit |
| LQM2HPN3R3MJ0□ | 3.3μH ±20% | 1MHz | 1000mA | 0.12Ω ±25% | 30MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -55°C~+125°C


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM2HPN_JH Series 1008/2520 (inch/mm)

High Spec Type (Low DC Resistance / Good Bias Current Characteristics Type)


Appearance/Dimensions



(in mm)

Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |



Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | Max. of DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---|--|--------------------------|---------------------------------|-----|
| LQM2HPNR47MJH□ | 0.47μH ±20% | 3.2A(Max)/3.5A(Typ.) | 2.7A(Max)/3.4A(Typ.) | 46mΩ (Max)/37mΩ (Typ.) | 70MHz | New |
| LQM2HPN1R0MJH□ | 1.0μH ±20% | 2.1A(Max)/2.4A(Typ.) | 2.3A(Max)/2.9A(Typ.) | 63mΩ (Max)/50mΩ (Typ.) | 50MHz | New |
| LQM2HPN2R2MJH□ | 2.2μH ±20% | 1.4A(Max)/1.6A(Typ.) | 1.5A(Max)/1.9A(Typ.) | 138mΩ (Max)/110mΩ (Typ.) | 30MHz | New |


Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of ferrite
 Operating Temperature Range: -40°C~+85°C
 For reflow soldering only.

*1 When applied rated current to the products, inductance will be within -30% of initial inductance value. Typical value is actual performance.


*2 When applied rated current to the products, temperature rise caused by self heating will be 40°C or less. Typical value is actual performance.

*3 Keep the temperature of product (ambient temperature plus self-generation of heat) under 125°C.


Inductance-Frequency Characteristics (Typ.)



Inductance-Current Characteristics (Typ.)



Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM2HPN_JC Series 1008/2520 (inch/mm)

Bias Current Characteristics Improved

Appearance/Dimensions



(in mm)

Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM2HPN1R0MJC□ | 1.0μH ±20% | 1MHz | 1500mA | 0.086Ω ±25% | 50MHz | Kit |
| LQM2HPN2R2NJC□ | 2.2μH ±30% | 1MHz | 1000mA | 0.175Ω ±25% | 30MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -55°C~+125°C


Inductance-Frequency Characteristics (Typ.)



Inductance-Current Characteristics (Typ.)



Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM2HPN_G0 Series 1008/2520 (inch/mm)

Size Code 1008 (2520) in inch (in mm), 1.0mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM2HPNR47MG0□ | 0.47μH ±20% | 1MHz | 1800mA | 0.04 Ω ±25% | 100MHz | Kit |
| LQM2HPN1R0MG0□ | 1.0μH ±20% | 1MHz | 1600mA | 0.055 Ω ±25% | 60MHz | Kit |
| LQM2HPN1R5MG0□ | 1.5μH ±20% | 1MHz | 1500mA | 0.07 Ω ±25% | 50MHz | Kit |
| LQM2HPN2R2MG0□ | 2.2μH ±20% | 1MHz | 1300mA | 0.08 Ω ±25% | 40MHz | Kit |
| LQM2HPN3R3MG0□ | 3.3μH ±20% | 1MHz | 1200mA | 0.10 Ω ±25% | 30MHz | Kit |
| LQM2HPN4R7MG0□ | 4.7μH ±20% | 1MHz | 1100mA | 0.11 Ω ±25% | 25MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -55°C~+125°C


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM2HPN_GS Series 1008/2520 (inch/mm)

Size Code 1008 (2520) in inch (in mm), 1.0mm max. Thickness

■ Appearance/Dimensions



(in mm)

■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM2HPN2R2MGS□ | 2.2μH ±20% | 1MHz | 1100mA | 0.18Ω ±25% | 40MHz | Kit |
| LQM2HPN3R3MGS□ | 3.3μH ±20% | 1MHz | 1050mA | 0.21Ω ±25% | 20MHz | Kit |
| LQM2HPN4R7MGS□ | 4.7μH ±20% | 1MHz | 1000mA | 0.25Ω ±25% | 20MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -40°C~+85°C


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM2HPN_GC Series 1008/2520 (inch/mm)

Bias Current Characteristics Improved

Appearance/Dimensions



(in mm)

Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | Operating Temperature Range | |
|----------------|------------|---------------------------|---------------|---------------|---------------------------------|-----------------------------|-----|
| LQM2HPN1R0MGC□ | 1.0μH ±20% | 1MHz | 1500mA | 0.08Ω ±25% | 50MHz | -30°C~+85°C | Kit |
| LQM2HPN3R3MGC□ | 3.3μH ±20% | 1MHz | 1000mA | 0.16Ω ±25% | 30MHz | -55°C~+125°C | Kit |
| LQM2HPN4R7MGC□ | 4.7μH ±20% | 1MHz | 800mA | 0.18Ω ±25% | 25MHz | -55°C~+125°C | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite


Inductance-Frequency Characteristics (Typ.)



Inductance-Current Characteristics (Typ.)



Temperature Rise Characteristics (Typ.)




Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM2HPN_GH Series 1008/2520 (inch/mm)

High Spec Type (Low DC Resistance / Good Bias Current Characteristics Type)


■ Appearance/Dimensions



(in mm)

■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | Max. of DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---|--|--------------------------|---------------------------------|-----|
| LQM2HPNR47MGH□ | 0.47μH ±20% | 4.5A(Max)/4.8A(Typ.) | 2.6A(Max)/3.3A(Typ.) | 50mΩ (Max)/40mΩ (Typ.) | 80MHz | New |
| LQM2HPNR68MGH□ | 0.68μH ±20% | 4.0A(Max)/3.8A(Typ.) | 2.3A(Max)/2.9A(Typ.) | 63mΩ (Max)/50mΩ (Typ.) | 60MHz | New |
| LQM2HPN1R0MGH□ | 1.0μH ±20% | 2.0A(Max)/2.3A(Typ.) | 2.3A(Max)/2.9A(Typ.) | 63mΩ (Max)/50mΩ (Typ.) | 50MHz | New |
| LQM2HPN1R5MGH□ | 1.5μH ±20% | 1.5A(Max)/1.6A(Typ.) | 2.0A(Max)/2.6A(Typ.) | 81mΩ (Max)/65mΩ (Typ.) | 40MHz | New |
| LQM2HPN2R2MGH□ | 2.2μH ±20% | 1.5A(Max)/1.6A(Typ.) | 1.5A(Max)/1.9A(Typ.) | 138mΩ (Max)/110mΩ (Typ.) | 30MHz | New |


Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -40°C~+85°C For reflow soldering only.

*1 When applied rated current to the products, inductance will be within -30% of initial inductance value. Typical value is actual performance.


*2 When applied rated current to the products, temperature rise caused by self heating will be 40°C or less. Typical value is actual performance.

*3 Keep the temperature of product (ambient temperature plus self-generation of heat) under 125°C.


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM2HPN_E0 Series 1008/2520 (inch/mm)

Size Code 1008 (2520) in inch (in mm), 0.8mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM2HPNR56ME0□ | 0.56μH ±20% | 1MHz | 1500mA | 0.06 Ω ±25% | 70MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -55°C~+125°C


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM31PN_00 Series 1206/3216 (inch/mm)

Size Code 1206 (3216) in inch (in mm), 0.95mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM31PNR47M00□ | 0.47μH ±20% | 1MHz | 1400mA | 0.07 Ω ±25% | 80MHz | Kit |
| LQM31PN1R0M00□ | 1.0μH ±20% | 1MHz | 1200mA | 0.12 Ω ±25% | 60MHz | Kit |
| LQM31PN1R5M00□ | 1.5μH ±20% | 1MHz | 1000mA | 0.14 Ω ±25% | 50MHz | Kit |
| LQM31PN2R2M00□ | 2.2μH ±20% | 1MHz | 900mA | 0.19 Ω ±25% | 40MHz | Kit |
| LQM31PN3R3M00□ | 3.3μH ±20% | 1MHz | 800mA | 0.24 Ω ±25% | 30MHz | Kit |
| LQM31PN4R7M00□ | 4.7μH ±20% | 1MHz | 700mA | 0.30 Ω ±25% | 25MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -55°C~+125°C


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM31PN_CO Series 1206/3216 (inch/mm)

Size Code 1206 (3216) in inch (in mm), 0.55mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 4000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM31PNR47MC0□ | 0.47μH ±20% | 1MHz | 1300mA | 0.085Ω ±25% | 90MHz | Kit |
| LQM31PN1R0MC0□ | 1.0μH ±20% | 1MHz | 1100mA | 0.14Ω ±25% | 70MHz | Kit |
| LQM31PN1R5MC0□ | 1.5μH ±20% | 1MHz | 1000mA | 0.17Ω ±25% | 60MHz | Kit |
| LQM31PN2R2MC0□ | 2.2μH ±20% | 1MHz | 900mA | 0.25Ω ±25% | 50MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -55°C~+125°C


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM32PN_G0 Series 1210/3225 (inch/mm)

Size Code 1210 (3225) in inch (in mm), 0.55mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM32PN1R0MG0□ | 1.0μH ±20% | 1MHz | 1800mA | 0.048Ω ±25% | 40MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite Operating Temperature Range: -40°C~+85°C
For reflow soldering only.


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH2MCN_02 Series 0806/2016 (inch/mm)

Size Code 0806 (2016) in inch (in mm), 0.95mm max. Thickness

■ Appearance/Dimensions



(in mm)

■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |
| B | Packing in Bulk | 100 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current ^{*1} | DC Resistance | Self-Resonance Frequency (min.) | Kit |
|----------------|------------|---------------------------|-----------------------------|---------------|---------------------------------|-----|
| LQH2MCN1R0M02□ | 1.0μH ±20% | 1MHz | 485mA | 0.30Ω ±30% | 100MHz | Kit |
| LQH2MCN1R5M02□ | 1.5μH ±20% | 1MHz | 445mA | 0.40Ω ±30% | 95MHz | Kit |
| LQH2MCN2R2M02□ | 2.2μH ±20% | 1MHz | 425mA | 0.48Ω ±30% | 70MHz | Kit |
| LQH2MCN3R3M02□ | 3.3μH ±20% | 1MHz | 375mA | 0.60Ω ±30% | 65MHz | Kit |
| LQH2MCN4R7M02□ | 4.7μH ±20% | 1MHz | 300mA | 0.8Ω ±30% | 60MHz | Kit |
| LQH2MCN5R6M02□ | 5.6μH ±20% | 1MHz | 280mA | 0.9Ω ±30% | 60MHz | Kit |
| LQH2MCN6R8M02□ | 6.8μH ±20% | 1MHz | 255mA | 1.0Ω ±30% | 55MHz | Kit |
| LQH2MCN8R2M02□ | 8.2μH ±20% | 1MHz | 235mA | 1.1Ω ±30% | 50MHz | Kit |
| LQH2MCN100K02□ | 10μH ±10% | 1MHz | 225mA | 1.2Ω ±30% | 48MHz | Kit |
| LQH2MCN120K02□ | 12μH ±10% | 1MHz | 210mA | 1.4Ω ±30% | 44MHz | Kit |
| LQH2MCN150K02□ | 15μH ±10% | 1MHz | 200mA | 1.6Ω ±30% | 40MHz | Kit |
| LQH2MCN180K02□ | 18μH ±10% | 1MHz | 190mA | 1.8Ω ±30% | 35MHz | Kit |
| LQH2MCN220K02□ | 22μH ±10% | 1MHz | 185mA | 2.1Ω ±30% | 30MHz | Kit |
| LQH2MCN270K02□ | 27μH ±10% | 1MHz | 180mA | 2.5Ω ±30% | 30MHz | Kit |
| LQH2MCN330K02□ | 33μH ±10% | 1MHz | 160mA | 2.8Ω ±30% | 28MHz | Kit |
| LQH2MCN390K02□ | 39μH ±10% | 1MHz | 125mA | 4.4Ω ±30% | 24MHz | Kit |
| LQH2MCN470K02□ | 47μH ±10% | 1MHz | 120mA | 5.1Ω ±30% | 18MHz | Kit |
| LQH2MCN560K02□ | 56μH ±10% | 1MHz | 110mA | 5.7Ω ±30% | 17MHz | Kit |
| LQH2MCN680K02□ | 68μH ±10% | 1MHz | 100mA | 6.6Ω ±30% | 14MHz | Kit |
| LQH2MCN820K02□ | 82μH ±10% | 1MHz | 90mA | 7.5Ω ±30% | 14MHz | Kit |

Class of Magnetic Shield: No magnetic shield

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


For reflow soldering only.

*1 When applied rated current to the products, self-temperature rise shall be limited to 40°C max. and inductance will be within ±10% of initial inductance value.


Continued on the following page. ↗

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)



Wire Wound Type (Ferrite Core)
Inductors for Power Lines

Inductors for General Use


RF Inductors

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH2MCN_52 Series 0806/2016 (inch/mm)

Size Code 0806 (2016) in inch (in mm), 0.7mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |
| B | Packing in Bulk | 100 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current ^{*1} | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|-----------------------------|---------------|---------------------------------|-----|
| LQH2MCN1R0M52□ | 1.0μH ±20% | 1MHz | 595mA | 0.25Ω ±30% | 215MHz | Kit |
| LQH2MCN1R5M52□ | 1.5μH ±20% | 1MHz | 540mA | 0.33Ω ±30% | 165MHz | Kit |
| LQH2MCN2R2M52□ | 2.2μH ±20% | 1MHz | 500mA | 0.42Ω ±30% | 125MHz | Kit |
| LQH2MCN3R3M52□ | 3.3μH ±20% | 1MHz | 360mA | 0.74Ω ±30% | 110MHz | Kit |
| LQH2MCN4R7M52□ | 4.7μH ±20% | 1MHz | 335mA | 0.91Ω ±30% | 90MHz | Kit |
| LQH2MCN6R8M52□ | 6.8μH ±20% | 1MHz | 285mA | 1.23Ω ±30% | 65MHz | Kit |
| LQH2MCN100M52□ | 10μH ±20% | 1MHz | 200mA | 2.27Ω ±30% | 60MHz | Kit |
| LQH2MCN120M52□ | 12μH ±20% | 1MHz | 170mA | 2.4Ω ±30% | 30MHz | Kit |
| LQH2MCN150M52□ | 15μH ±20% | 1MHz | 150mA | 3.5Ω ±30% | 30MHz | Kit |
| LQH2MCN180M52□ | 18μH ±20% | 1MHz | 140mA | 4.0Ω ±30% | 30MHz | Kit |
| LQH2MCN220M52□ | 22μH ±20% | 1MHz | 130mA | 5.5Ω ±30% | 30MHz | Kit |


Class of Magnetic Shield: No magnetic shield

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


For reflow soldering only.

*1 When applied rated current to the products, self-temperature rise shall be limited to 40°C max. and inductance will be within ±10% of initial inductance value.

■ Inductance-Frequency Characteristics (Typ.)




■ Inductance-Current Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


■ Temperature Rise Characteristics (Typ.)



LQH2HPN_GO Series 1008/2520 (inch/mm)

Size Code 1008 (2520) in inch (in mm), 1.0mm max. Thickness

■ Appearance/ Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |



Refer to pages 102 to 106 for mounting information.


■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | Kit |
|----------------|------------|---|--|---------------|---------------------------------|-----|
| LQH2HPN2R2MG0□ | 2.2μH ±20% | 1640mA | 1000mA | 0.17Ω ±20% | 80MHz | Kit |
| LQH2HPN3R3MG0□ | 3.3μH ±20% | 1290mA | 810mA | 0.27Ω ±20% | 65MHz | Kit |
| LQH2HPN4R7MG0□ | 4.7μH ±20% | 1000mA | 700mA | 0.36Ω ±20% | 60MHz | Kit |
| LQH2HPN6R8MG0□ | 6.8μH ±20% | 800mA | 590mA | 0.5Ω ±20% | 10MHz | Kit |
| LQH2HPN100MG0□ | 10μH ±20% | 700mA | 490mA | 0.73Ω ±20% | 10MHz | Kit |
| LQH2HPN220MG0□ | 22μH ±20% | 490mA | 340mA | 1.6Ω ±20% | 10MHz | Kit |
| LQH2HPN101MG0□ | 100μH ±20% | 210mA | 130mA | 10.0Ω ±20% | 5MHz | Kit |


Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin
 Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C
 For reflow soldering only.

*1 When applied rated current to the products, inductance will be within -30% of minimum rated inductance value.
 *2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.
 *3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

■ Inductance-Frequency Characteristics (Typ.)




■ Inductance-Current Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


Temperature Rise Characteristics (Typ.)



LQH2HPN_GR Series 1008/2520 (inch/mm)

Size Code 1008 (2520) in inch (in mm), 1.0mm max. Thickness. Low DC resistance design

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---|--|---------------|---------------------------------|---------|
| LQH2HPNR47MGR□ | 0.47µH ±20% | 2900mA | 2520mA | 0.045 Ω ±20% | 120MHz | New |
| LQH2HPNR68MGR□ | 0.68µH ±20% | 2430mA | 2330mA | 0.055 Ω ±20% | 110MHz | New |
| LQH2HPN1R0MGR□ | 1.0µH ±20% | 2130mA | 2100mA | 0.068 Ω ±20% | 100MHz | New Kit |
| LQH2HPN1R5MGR□ | 1.5µH ±20% | 1700mA | 1850mA | 0.087 Ω ±20% | 90MHz | New |
| LQH2HPN2R2MGR□ | 2.2µH ±20% | 1550mA | 1470mA | 0.134 Ω ±20% | 80MHz | New Kit |
| LQH2HPN3R3MGR□ | 3.3µH ±20% | 1230mA | 1100mA | 0.225 Ω ±20% | 70MHz | New |
| LQH2HPN4R7MGR□ | 4.7µH ±20% | 1090mA | 1000mA | 0.300 Ω ±20% | 50MHz | New |
| LQH2HPN6R8MGR□ | 6.8µH ±20% | 830mA | 860mA | 0.395 Ω ±20% | 40MHz | New |
| LQH2HPN100MGR□ | 10µH ±20% | 700mA | 710mA | 0.560 Ω ±20% | 30MHz | New |
| LQH2HPN150MGR□ | 15µH ±20% | 570mA | 560mA | 0.925 Ω ±20% | 20MHz | New |
| LQH2HPN220MGR□ | 22µH ±20% | 460mA | 430mA | 1.360 Ω ±20% | 15MHz | New |


Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin
 Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C
 For reflow soldering only.

*1 When applied rated current to the products, inductance will be within -30% of minimum rated inductance value.


*2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.

*3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

■ Inductance-Frequency Characteristics (Typ.)




■ Inductance-Current Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


Temperature Rise Characteristics (Typ.)



LQH2HPN_J0 Series 1008/2520 (inch/mm)

Size Code 1008 (2520) in inch (in mm), 1.2mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | Kit |
|----------------|------------|---|--|---------------|---------------------------------|-----|
| LQH2HPN1R5NJ0□ | 1.5μH ±20% | 2400mA | 1500mA | 0.096 Ω ±20% | 10MHz | Kit |
| LQH2HPN2R2MJ0□ | 2.2μH ±20% | 1800mA | 1300mA | 0.132 Ω ±20% | 10MHz | Kit |
| LQH2HPN3R3MJ0□ | 3.3μH ±20% | 1500mA | 950mA | 0.230 Ω ±20% | 10MHz | Kit |
| LQH2HPN4R7MJ0□ | 4.7μH ±20% | 1250mA | 700mA | 0.330 Ω ±20% | 10MHz | Kit |
| LQH2HPN6R8MJ0□ | 6.8μH ±20% | 1100mA | 600mA | 0.448 Ω ±20% | 10MHz | Kit |
| LQH2HPN100MJ0□ | 10μH ±20% | 820mA | 550mA | 0.641 Ω ±20% | 10MHz | Kit |

Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


For reflow soldering only.

*1 When applied rated current to the products, inductance will be within -30% of minimum rated inductance value.


*2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.

*3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

■ Inductance-Frequency Characteristics (Typ.)




■ Inductance-Current Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


■ Temperature Rise Characteristics (Typ.)



LQH2HPN_M0 Series 1008/2520 (inch/mm)

Size Code 1008 (2520) in inch (in mm), 1.5mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | Kit |
|----------------|------------|---|--|---------------|---------------------------------|-----|
| LQH2HPN2R2MM0□ | 2.2μH ±20% | 1700mA | 1250mA | 0.146Ω ±20% | 10MHz | Kit |
| LQH2HPN4R7NM0□ | 4.7μH ±30% | 1200mA | 800mA | 0.342Ω ±20% | 10MHz | Kit |

Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin
 Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


For reflow soldering only.

*1 When applied rated current to the products, inductance will be within ±30% of initial inductance value.


*2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.

*3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH3NPN_M0 Series 1212/3030 (inch/mm)

Size Code 1212 (3030) in inch (in mm), 1.5mm max. Thickness

■ Appearance/ Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 1000 |
| K | ø330mm Embossed Taping | 4000 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | Kit |
|----------------|------------|---|--|---------------|---------------------------------|-----|
| LQH3NPN1R0MM0□ | 1.0μH ±20% | 1400mA | 2050mA | 0.044Ω ±20% | 130MHz | Kit |
| LQH3NPN1R0NM0□ | 1.0μH ±30% | 1400mA | 2050mA | 0.044Ω ±20% | 130MHz | |
| LQH3NPN2R2MM0□ | 2.2μH ±20% | 1250mA | 1600mA | 0.073Ω ±20% | 90MHz | Kit |
| LQH3NPN2R2NM0□ | 2.2μH ±30% | 1250mA | 1600mA | 0.073Ω ±20% | 90MHz | |
| LQH3NPN3R3MM0□ | 3.3μH ±20% | 1000mA | 1450mA | 0.092Ω ±20% | 75MHz | Kit |
| LQH3NPN3R3NM0□ | 3.3μH ±30% | 1000mA | 1450mA | 0.092Ω ±20% | 75MHz | |
| LQH3NPN4R7MM0□ | 4.7μH ±20% | 880mA | 1250mA | 0.13Ω ±20% | 65MHz | Kit |
| LQH3NPN4R7NM0□ | 4.7μH ±30% | 880mA | 1250mA | 0.13Ω ±20% | 65MHz | |
| LQH3NPN6R8MM0□ | 6.8μH ±20% | 820mA | 1000mA | 0.20Ω ±20% | 50MHz | Kit |
| LQH3NPN6R8NM0□ | 6.8μH ±30% | 820mA | 1000mA | 0.20Ω ±20% | 50MHz | |
| LQH3NPN100MM0□ | 10μH ±20% | 550mA | 870mA | 0.26Ω ±20% | 45MHz | Kit |
| LQH3NPN100NM0□ | 10μH ±30% | 550mA | 870mA | 0.26Ω ±20% | 45MHz | |
| LQH3NPN150MM0□ | 15μH ±20% | 520mA | 730mA | 0.36Ω ±20% | 30MHz | Kit |
| LQH3NPN150NM0□ | 15μH ±30% | 520mA | 730mA | 0.36Ω ±20% | 30MHz | |
| LQH3NPN220MM0□ | 22μH ±20% | 410mA | 650mA | 0.51Ω ±20% | 28MHz | Kit |
| LQH3NPN330MM0□ | 33μH ±20% | 370mA | 500mA | 0.85Ω ±20% | 22MHz | Kit |
| LQH3NPN470MM0□ | 47μH ±20% | 310mA | 410mA | 1.25Ω ±20% | 18MHz | Kit |
| LQH3NPN101MM0□ | 100μH ±20% | 200mA | 240mA | 3.50Ω ±20% | 12MHz | Kit |

Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin

Operating Temperature Range (Self-temperature rise is included): -40°C~+125°C

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

For reflow soldering only.

*1 When applied rated current to the products, inductance will be within ±30% of initial inductance value.


*2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.

*3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.


Continued on the following page. ↗

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)





⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH3NPN_MR Series 1212/3030 (inch/mm)

Low DC Resistance Type

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| E | ø180mm Embossed Taping | 2000 |
| F | ø330mm Embossed Taping | 8000 |



Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | Kit |
|----------------|------------|---|--|---------------|---------------------------------|-----|
| LQH3NPN1R0MMR□ | 1.0μH ±20% | 1600mA | 2150mA | 0.042Ω ±20% | 135MHz | Kit |
| LQH3NPN2R2MMR□ | 2.2μH ±20% | 1380mA | 1750mA | 0.068Ω ±20% | 75MHz | Kit |
| LQH3NPN3R3MMR□ | 3.3μH ±20% | 1200mA | 1550mA | 0.088Ω ±20% | 70MHz | Kit |
| LQH3NPN4R7MMR□ | 4.7μH ±20% | 950mA | 1400mA | 0.105Ω ±20% | 57MHz | Kit |
| LQH3NPN6R8MMR□ | 6.8μH ±20% | 830mA | 1250mA | 0.155Ω ±20% | 40MHz | Kit |
| LQH3NPN100MMR□ | 10μH ±20% | 590mA | 1150mA | 0.210Ω ±20% | 30MHz | Kit |
| LQH3NPN220MMR□ | 22μH ±20% | 430mA | 750mA | 0.480Ω ±20% | 20MHz | Kit |
| LQH3NPN330MMR□ | 33μH ±20% | 380mA | 600mA | 0.790Ω ±20% | 15MHz | Kit |
| LQH3NPN470MMR□ | 47μH ±20% | 320mA | 460mA | 1.140Ω ±20% | 10MHz | Kit |

Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin

Operating Temperature Range (Self-temperature rise is included): -40°C~+125°C

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


For reflow soldering only.

*1 When applied rated current to the products, inductance will be within ±30% of initial inductance value.


*2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.

*3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

Inductance-Frequency Characteristics (Typ.)




Inductance-Current Characteristics (Typ.)



Continued on the following page.

Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Temperature Rise Characteristics (Typ.)




Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH3NPN_J0 Series 1212/3030 (inch/mm)

Size Code 1212 (3030) in inch (in mm), 1.2mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 1000 |
| K | ø330mm Embossed Taping | 5000 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---|--|---------------|---------------------------------|-----|
| LQH3NPN1R0NJ0□ | 1.0μH ±30% | 1650mA | 1620mA | 0.040 Ω ±20% | 140MHz | Kit |
| LQH3NPN1R5NJ0□ | 1.5μH ±30% | 1200mA | 1500mA | 0.055 Ω ±20% | 90MHz | Kit |
| LQH3NPN2R2MJ0□ | 2.2μH ±20% | 1150mA | 1460mA | 0.069 Ω ±20% | 90MHz | Kit |
| LQH3NPN2R2NJ0□ | 2.2μH ±30% | 1150mA | 1460mA | 0.069 Ω ±20% | 90MHz | |
| LQH3NPN3R3MJ0□ | 3.3μH ±20% | 950mA | 1270mA | 0.105 Ω ±20% | 70MHz | Kit |
| LQH3NPN3R3NJ0□ | 3.3μH ±30% | 950mA | 1270mA | 0.105 Ω ±20% | 70MHz | |
| LQH3NPN4R7MJ0□ | 4.7μH ±20% | 780mA | 1120mA | 0.130 Ω ±20% | 65MHz | Kit |
| LQH3NPN4R7NJ0□ | 4.7μH ±30% | 780mA | 1120mA | 0.130 Ω ±20% | 65MHz | |
| LQH3NPN6R8MJ0□ | 6.8μH ±20% | 700mA | 850mA | 0.210 Ω ±20% | 45MHz | Kit |
| LQH3NPN6R8NJ0□ | 6.8μH ±30% | 700mA | 850mA | 0.210 Ω ±20% | 45MHz | |
| LQH3NPN100MJ0□ | 10μH ±20% | 560mA | 710mA | 0.300 Ω ±20% | 35MHz | Kit |
| LQH3NPN100NJ0□ | 10μH ±30% | 560mA | 710mA | 0.300 Ω ±20% | 35MHz | |
| LQH3NPN150MJ0□ | 15μH ±20% | 440mA | 590mA | 0.440 Ω ±20% | 30MHz | Kit |
| LQH3NPN150NJ0□ | 15μH ±30% | 440mA | 590mA | 0.440 Ω ±20% | 30MHz | |
| LQH3NPN220MJ0□ | 22μH ±20% | 350mA | 510mA | 0.600 Ω ±20% | 25MHz | Kit |
| LQH3NPN220NJ0□ | 22μH ±30% | 350mA | 510mA | 0.600 Ω ±20% | 25MHz | |
| LQH3NPN330MJ0□ | 33μH ±20% | 280mA | 410mA | 0.900 Ω ±20% | 20MHz | Kit |
| LQH3NPN330NJ0□ | 33μH ±30% | 280mA | 410mA | 0.900 Ω ±20% | 20MHz | |
| LQH3NPN470MJ0□ | 47μH ±20% | 200mA | 350mA | 1.30 Ω ±20% | 15MHz | Kit |
| LQH3NPN470NJ0□ | 47μH ±30% | 200mA | 350mA | 1.30 Ω ±20% | 15MHz | |

Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin

Operating Temperature Range (Self-temperature rise is included): -40°C~+125°C

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

For reflow soldering only.

*1 When applied rated current to the products, inductance will be within ±30% of initial inductance value.


*2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.

*3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.


Continued on the following page. ↗

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH3NPN_GO Series 1212/3030 (inch/mm)

Size Code 1212 (3030) in inch (in mm), 1.0mm max. Thickness

■ Appearance/ Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 1500 |
| K | ø330mm Embossed Taping | 6000 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---|--|---------------|---------------------------------|-----|
| LQH3NPN1R0NG0□ | 1.0μH ±30% | 1650mA | 1525mA | 0.08Ω ±20% | 160MHz | Kit |
| LQH3NPN1R5NG0□ | 1.5μH ±30% | 1300mA | 1470mA | 0.10Ω ±20% | 130MHz | Kit |
| LQH3NPN2R2NG0□ | 2.2μH ±30% | 1250mA | 1270mA | 0.14Ω ±20% | 100MHz | Kit |
| LQH3NPN3R3NG0□ | 3.3μH ±30% | 850mA | 1130mA | 0.18Ω ±20% | 75MHz | Kit |
| LQH3NPN4R7NG0□ | 4.7μH ±30% | 800mA | 925mA | 0.26Ω ±20% | 60MHz | Kit |
| LQH3NPN6R8NG0□ | 6.8μH ±30% | 650mA | 710mA | 0.45Ω ±20% | 48MHz | Kit |
| LQH3NPN100MG0□ | 10μH ±20% | 500mA | 630mA | 0.57Ω ±20% | 45MHz | Kit |
| LQH3NPN100NG0□ | 10μH ±30% | 500mA | 630mA | 0.57Ω ±20% | 45MHz | |
| LQH3NPN150NG0□ | 15μH ±30% | 370mA | 475mA | 0.91Ω ±20% | 35MHz | Kit |
| LQH3NPN220MG0□ | 22μH ±20% | 340mA | 430mA | 1.1Ω ±20% | 25MHz | Kit |
| LQH3NPN220NG0□ | 22μH ±30% | 340mA | 430mA | 1.1Ω ±20% | 25MHz | |
| LQH3NPN330MG0□ | 33μH ±20% | 250mA | 345mA | 2.1Ω ±20% | 24MHz | Kit |
| LQH3NPN330NG0□ | 33μH ±30% | 250mA | 345mA | 2.1Ω ±20% | 24MHz | |
| LQH3NPN470MG0□ | 47μH ±20% | 170mA | 270mA | 3.0Ω ±20% | 19MHz | Kit |
| LQH3NPN470NG0□ | 47μH ±30% | 170mA | 270mA | 3.0Ω ±20% | 19MHz | |
| LQH3NPN680MG0□ | 68μH ±20% | 150mA | 235mA | 4.2Ω ±20% | 16MHz | Kit |
| LQH3NPN680NG0□ | 68μH ±30% | 150mA | 235mA | 4.2Ω ±20% | 16MHz | |
| LQH3NPN101MG0□ | 100μH ±20% | 140mA | 165mA | 8.0Ω ±20% | 10MHz | Kit |
| LQH3NPN101NG0□ | 100μH ±30% | 140mA | 165mA | 8.0Ω ±20% | 10MHz | |
| LQH3NPN151MG0□ | 150μH ±20% | 110mA | 145mA | 11.0Ω ±20% | 10MHz | Kit |
| LQH3NPN151NG0□ | 150μH ±30% | 110mA | 145mA | 11.0Ω ±20% | 10MHz | |
| LQH3NPN221MG0□ | 220μH ±20% | 100mA | 130mA | 14.0Ω ±20% | 8.5MHz | Kit |
| LQH3NPN221NG0□ | 220μH ±30% | 100mA | 130mA | 14.0Ω ±20% | 8.5MHz | |
| LQH3NPN251MG0□ | 250μH ±20% | 80mA | 130mA | 15.0Ω ±20% | 8.0MHz | Kit |
| LQH3NPN251NG0□ | 250μH ±30% | 80mA | 130mA | 15.0Ω ±20% | 8.0MHz | |

Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin
Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

For reflow soldering only.

*1 When applied rated current to the products, inductance will be within ±30% of initial inductance value.


*2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.

*3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.


Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH32PN_N0 Series 1210/3225 (inch/mm)

Size Code 1210 (3225) in inch (in mm), 1.7mm max. Thickness

■ Appearance/ Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |
| K | ø330mm Embossed Taping | 7500 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | Kit |
|----------------|-------------|---|--|---------------|---------------------------------|-----|
| LQH32PNR47NN0□ | 0.47μH ±30% | 3400mA | 2550mA | 0.03Ω ±20% | 100MHz | Kit |
| LQH32PN1R0NN0□ | 1.0μH ±30% | 2300mA | 2050mA | 0.045Ω ±20% | 100MHz | Kit |
| LQH32PN1R5NN0□ | 1.5μH ±30% | 1750mA | 1750mA | 0.057Ω ±20% | 70MHz | Kit |
| LQH32PN2R2NN0□ | 2.2μH ±30% | 1550mA | 1600mA | 0.076Ω ±20% | 70MHz | Kit |
| LQH32PN3R3NN0□ | 3.3μH ±30% | 1250mA | 1200mA | 0.12Ω ±20% | 50MHz | Kit |
| LQH32PN4R7NN0□ | 4.7μH ±30% | 1000mA | 1000mA | 0.18Ω ±20% | 40MHz | Kit |
| LQH32PN6R8NN0□ | 6.8μH ±30% | 850mA | 850mA | 0.24Ω ±20% | 40MHz | Kit |
| LQH32PN100MN0□ | 10μH ±20% | 750mA | 700mA | 0.38Ω ±20% | 30MHz | Kit |
| LQH32PN150MN0□ | 15μH ±20% | 600mA | 520mA | 0.57Ω ±20% | 20MHz | Kit |
| LQH32PN220MN0□ | 22μH ±20% | 500mA | 450mA | 0.81Ω ±20% | 20MHz | Kit |
| LQH32PN330MN0□ | 33μH ±20% | 380mA | 390mA | 1.15Ω ±20% | 13MHz | Kit |
| LQH32PN470MN0□ | 47μH ±20% | 330mA | 310mA | 1.78Ω ±20% | 11MHz | Kit |
| LQH32PN680MN0□ | 68μH ±20% | 280mA | 275mA | 2.28Ω ±20% | 11MHz | Kit |
| LQH32PN101MN0□ | 100μH ±20% | 180mA | 250mA | 2.70Ω ±20% | 8MHz | Kit |
| LQH32PN121MN0□ | 120μH ±20% | 170mA | 200mA | 4.38Ω ±20% | 8MHz | Kit |


Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin
 Operating Temperature Range (Self-temperature rise is included): -40°C~+125°C
 Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C
 For reflow soldering only.

*1 When applied rated current to the products, inductance will be within ±30% of initial inductance value.
 *2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.
 *3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.


Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


■ Inductance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



■ Temperature Rise Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH32PN_NC Series 1210/3225 (inch/mm)

Bias Current Characteristics Improved

Appearance/Dimensions



(in mm)

Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |
| K | ø330mm Embossed Taping | 7500 |



Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---|--|---------------|---------------------------------|-----|
| LQH32PNR47NNC□ | 0.47μH ±30% | 4400mA | 2900mA | 0.024Ω ±20% | 100MHz | Kit |
| LQH32PN1R0NNC□ | 1.0μH ±30% | 3000mA | 2500mA | 0.036Ω ±20% | 100MHz | Kit |
| LQH32PN1R5NNC□ | 1.5μH ±30% | 2600mA | 2100mA | 0.053Ω ±20% | 70MHz | Kit |
| LQH32PN2R2NNC□ | 2.2μH ±30% | 2000mA | 1850mA | 0.064Ω ±20% | 70MHz | Kit |
| LQH32PN3R3NNC□ | 3.3μH ±30% | 1900mA | 1550mA | 0.100Ω ±20% | 50MHz | Kit |
| LQH32PN4R7NNC□ | 4.7μH ±30% | 1600mA | 1200mA | 0.155Ω ±20% | 40MHz | Kit |
| LQH32PN6R8NNC□ | 6.8μH ±30% | 1300mA | 1100mA | 0.220Ω ±20% | 40MHz | Kit |
| LQH32PN100MNC□ | 10μH ±20% | 1000mA | 900mA | 0.295Ω ±20% | 30MHz | Kit |
| LQH32PN150MNC□ | 15μH ±20% | 800mA | 700mA | 0.475Ω ±20% | 20MHz | Kit |
| LQH32PN220MNC□ | 22μH ±20% | 650mA | 550mA | 0.685Ω ±20% | 20MHz | Kit |

Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin

Operating Temperature Range (Self-temperature rise is included): -40°C~+125°C

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


For reflow soldering only.

*1 When applied rated current to the products, inductance will be within ±30% of initial inductance value.


*2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.

*3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

Inductance-Frequency Characteristics (Typ.)




Inductance-Current Characteristics (Typ.)



Continued on the following page.

Note • Please read rating and **CAUTION** (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Temperature Rise Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH32PB_N0 Series 1210/3225 (inch/mm)

1.7mm max. Thickness, 105°C

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |
| K | ø330mm Embossed Taping | 7500 |



Refer to pages 102 to 106 for mounting information.


■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---|--|---------------|---------------------------------|---------|
| LQH32PBR47NN0□ | 0.47μH ±30% | 3400mA | 2550mA | 0.030Ω ±20% | 100MHz | New Kit |
| LQH32PB1R0NN0□ | 1.0μH ±30% | 2300mA | 2050mA | 0.045Ω ±20% | 100MHz | New Kit |
| LQH32PB1R5NN0□ | 1.5μH ±30% | 1750mA | 1750mA | 0.057Ω ±20% | 70MHz | New Kit |
| LQH32PB2R2NN0□ | 2.2μH ±30% | 1550mA | 1600mA | 0.076Ω ±20% | 70MHz | New Kit |
| LQH32PB3R3NN0□ | 3.3μH ±30% | 1250mA | 1200mA | 0.12Ω ±20% | 50MHz | New Kit |
| LQH32PB4R7NN0□ | 4.7μH ±30% | 1000mA | 1000mA | 0.18Ω ±20% | 40MHz | New Kit |
| LQH32PB6R8NN0□ | 6.8μH ±30% | 850mA | 850mA | 0.24Ω ±20% | 40MHz | New Kit |
| LQH32PB100MN0□ | 10μH ±20% | 750mA | 700mA | 0.38Ω ±20% | 30MHz | New Kit |
| LQH32PB150MN0□ | 15μH ±20% | 600mA | 520mA | 0.57Ω ±20% | 20MHz | New Kit |
| LQH32PB220MN0□ | 22μH ±20% | 500mA | 450mA | 0.81Ω ±20% | 20MHz | New Kit |
| LQH32PB330MN0□ | 33μH ±20% | 380mA | 390mA | 1.15Ω ±20% | 13MHz | New Kit |
| LQH32PB470MN0□ | 47μH ±20% | 330mA | 310mA | 1.78Ω ±20% | 11MHz | New Kit |
| LQH32PB680MN0□ | 68μH ±20% | 280mA | 275mA | 2.28Ω ±20% | 11MHz | New Kit |
| LQH32PB101MN0□ | 100μH ±20% | 180mA | 250mA | 2.7Ω ±20% | 8MHz | New Kit |
| LQH32PB121MN0□ | 120μH ±20% | 170mA | 200mA | 4.38Ω ±20% | 8MHz | New Kit |


Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin
 Operating Temperature Range (Self-temperature rise is included): -40°C~+125°C
 Operating Temperature Range (Self-temperature rise is not included): -40°C~+105°C
 For reflow soldering only.

*1 When applied rated current to the products, inductance will be within ±30% of initial inductance value.
 *2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.
 *3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

■ Inductance-Frequency Characteristics (Typ.)




■ Inductance-Current Characteristics (Typ.)



Continued on the following page.


△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Temperature Rise Characteristics (Typ.)



■ Derating of Rated Current

In operating temperature exceeding +85°C, derating of current is necessary for LQH32PB_N0 series. Please apply the derating curve shown in chart according to the operating temperature.




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH32PB_NC Series 1210/3225 (inch/mm)

1.7mm max. Thickness, 105°C

■ Appearance/Dimensions



(in mm)

■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |
| K | ø330mm Embossed Taping | 7500 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---|--|---------------|---------------------------------|---------|
| LQH32PBR47NNC□ | 0.47μH ±30% | 4400mA | 2900mA | 0.024Ω ±20% | 100MHz | New Kit |
| LQH32PB1R0NNC□ | 1.0μH ±30% | 3000mA | 2500mA | 0.036Ω ±20% | 100MHz | New Kit |
| LQH32PB1R5NNC□ | 1.5μH ±30% | 2600mA | 2100mA | 0.053Ω ±20% | 70MHz | New Kit |
| LQH32PB2R2NNC□ | 2.2μH ±30% | 2000mA | 1850mA | 0.064Ω ±20% | 70MHz | New Kit |
| LQH32PB3R3NNC□ | 3.3μH ±30% | 1900mA | 1550mA | 0.1Ω ±20% | 50MHz | New Kit |
| LQH32PB4R7NNC□ | 4.7μH ±30% | 1600mA | 1200mA | 0.155Ω ±20% | 40MHz | New Kit |
| LQH32PB6R8NNC□ | 6.8μH ±30% | 1300mA | 1100mA | 0.22Ω ±20% | 40MHz | New Kit |
| LQH32PB100MNC□ | 10μH ±20% | 1000mA | 900mA | 0.295Ω ±20% | 30MHz | New Kit |
| LQH32PB150MNC□ | 15μH ±20% | 800mA | 700mA | 0.475Ω ±20% | 20MHz | New Kit |
| LQH32PB220MNC□ | 22μH ±20% | 650mA | 550mA | 0.685Ω ±20% | 20MHz | New Kit |

Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin

Operating Temperature Range (Self-temperature rise is included): -40°C~+125°C

Operating Temperature Range (Self-temperature rise is not included): -40°C~+105°C


For reflow soldering only.

*1 When applied rated current to the products, inductance will be within ±30% of initial inductance value.


*2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.

*3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

■ Inductance-Frequency Characteristics (Typ.)




■ Inductance-Current Characteristics (Typ.)



Continued on the following page.


△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Temperature Rise Characteristics (Typ.)



■ Derating of Rated Current

In operating temperature exceeding +85°C, derating of current is necessary for LQH32PB_NC series. Please apply the derating curve shown in chart according to the operating temperature.




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH43PN_26 Series 1812/4532 (inch/mm)

Size Code 1812 (4532) in inch (in mm), 2.8mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 500 |
| K | ø330mm Embossed Taping | 2500 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---|--|---------------|---------------------------------|-----|
| LQH43PN1R0N26□ | 1.0μH ±30% | 3400mA | 3300mA | 0.026Ω ±20% | 100MHz | Kit |
| LQH43PN2R2M26□ | 2.2μH ±20% | 2300mA | 2500mA | 0.042Ω ±20% | 45MHz | Kit |
| LQH43PN3R3M26□ | 3.3μH ±20% | 1800mA | 2100mA | 0.052Ω ±20% | 40MHz | Kit |
| LQH43PN4R7M26□ | 4.7μH ±20% | 1400mA | 1600mA | 0.075Ω ±20% | 35MHz | Kit |
| LQH43PN6R8M26□ | 6.8μH ±20% | 1200mA | 1400mA | 0.098Ω ±20% | 30MHz | Kit |
| LQH43PN8R2M26□ | 8.2μH ±20% | 1100mA | 1300mA | 0.128Ω ±20% | 25MHz | Kit |
| LQH43PN100M26□ | 10μH ±20% | 1050mA | 1170mA | 0.147Ω ±20% | 20MHz | Kit |
| LQH43PN220M26□ | 22μH ±20% | 700mA | 780mA | 0.327Ω ±20% | 15MHz | Kit |
| LQH43PN470M26□ | 47μH ±20% | 470mA | 520mA | 0.718Ω ±20% | 8MHz | Kit |
| LQH43PN101M26□ | 100μH ±20% | 320mA | 320mA | 1.538Ω ±20% | 4MHz | Kit |
| LQH43PN151M26□ | 150μH ±20% | 280mA | 260mA | 2.362Ω ±20% | 3MHz | Kit |
| LQH43PN221M26□ | 220μH ±20% | 220mA | 240mA | 2.900Ω ±20% | 2MHz | Kit |

Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin


Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

*1 When applied rated current to the products, inductance will be within ±30% of initial inductance value.


*2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.

*3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

■ Inductance-Frequency Characteristics (Typ.)




■ Inductance-Current Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Temperature Rise Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH43PB_26 Series 1812/4532 (inch/mm)

For Automotive Use *Expect for the portion asked for high reliability ex. power train

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 500 |
| K | ø330mm Embossed Taping | 2500 |



Refer to pages 102 to 106 for mounting information.


■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---|--|---------------|---------------------------------|-----|
| LQH43PB1R0N26□ | 1.0μH ±30% | 3400mA | 3300mA | 0.026Ω ±20% | 100MHz | New |
| LQH43PB2R2M26□ | 2.2μH ±20% | 2300mA | 2500mA | 0.042Ω ±20% | 45MHz | New |
| LQH43PB3R3M26□ | 3.3μH ±20% | 1800mA | 2100mA | 0.052Ω ±20% | 40MHz | New |
| LQH43PB4R7M26□ | 4.7μH ±20% | 1400mA | 1600mA | 0.075Ω ±20% | 35MHz | New |
| LQH43PB6R8M26□ | 6.8μH ±20% | 1200mA | 1400mA | 0.098Ω ±20% | 30MHz | New |
| LQH43PB8R2M26□ | 8.2μH ±20% | 1100mA | 1300mA | 0.128Ω ±20% | 25MHz | New |
| LQH43PB100M26□ | 10μH ±20% | 1050mA | 1170mA | 0.147Ω ±20% | 20MHz | New |
| LQH43PB220M26□ | 22μH ±20% | 700mA | 780mA | 0.327Ω ±20% | 15MHz | New |
| LQH43PB470M26□ | 47μH ±20% | 470mA | 520mA | 0.718Ω ±20% | 8MHz | New |
| LQH43PB101M26□ | 100μH ±20% | 320mA | 320mA | 1.538Ω ±20% | 4MHz | New |
| LQH43PB151M26□ | 150μH ±20% | 280mA | 260mA | 2.362Ω ±20% | 3MHz | New |
| LQH43PB221M26□ | 220μH ±20% | 220mA | 240mA | 2.900Ω ±20% | 2MHz | New |


Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin
 Operating Temperature Range (Self-temperature rise is included): -40°C~+125°C
 Operating Temperature Range (Self-temperature rise is not included): -40°C~+105°C
 For reflow soldering only.

*1 When applied rated current to the products, inductance will be within ±30% of initial inductance value.
 *2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.
 *3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

■ Inductance-Frequency Characteristics (Typ.)




■ Inductance-Current Characteristics (Typ.)



Continued on the following page.


△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Temperature Rise Characteristics (Typ.)



■ Derating of Rated Current

In operating temperature exceeding +85°C, derating of current is necessary for LQH43PB series. Please apply the derating curve shown in chart according to the operating temperature.




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH44PN_PO Series 1515/4040 (inch/mm)

Size Code 1515 (4040) in inch (in mm), 1.8mm max. Thickness

■ Appearance/Dimensions



(in mm)

■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 1000 |
| K | ø330mm Embossed Taping | 3500 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | Kit |
|----------------|------------|---|--|---------------|---------------------------------|-----|
| LQH44PN1R0NP0□ | 1.0μH ±30% | 2950mA | 2450mA | 0.030Ω ±20% | 90MHz | Kit |
| LQH44PN2R2MP0□ | 2.2μH ±20% | 2500mA | 1800mA | 0.049Ω ±20% | 70MHz | Kit |
| LQH44PN3R3MP0□ | 3.3μH ±20% | 2100mA | 1770mA | 0.065Ω ±20% | 50MHz | Kit |
| LQH44PN4R7MP0□ | 4.7μH ±20% | 1700mA | 1700mA | 0.080Ω ±20% | 40MHz | Kit |
| LQH44PN6R8MP0□ | 6.8μH ±20% | 1400mA | 1340mA | 0.12Ω ±20% | 35MHz | Kit |
| LQH44PN100MP0□ | 10μH ±20% | 1150mA | 1170mA | 0.16Ω ±20% | 25MHz | Kit |
| LQH44PN220MP0□ | 22μH ±20% | 800mA | 790mA | 0.37Ω ±20% | 17MHz | Kit |

Inductance Test Frequency: 1MHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin

Operating Temperature Range (Self-temperature rise is included): -40°C~+125°C

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


For reflow soldering only.

*1 When applied rated current to the products, inductance will be within ±30% of initial inductance value.


*2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.

*3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

■ Inductance-Frequency Characteristics (Typ.)




■ Inductance-Current Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Temperature Rise Characteristics (Typ.)




Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH44PN_J0 Series 1515/4040 (inch/mm)

Size Code 1515 (4040) in inch (in mm), 1.2mm max. Thickness

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 1000 |
| K | ø330mm Embossed Taping | 3500 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---|--|---------------|---------------------------------|-----|
| LQH44PN1R0NJ0□ | 1.0μH ±30% | 2000mA | 1530mA | 0.048Ω ±20% | 130MHz | Kit |
| LQH44PN1R5MJ0□ | 1.5μH ±20% | 1600mA | 1380mA | 0.061Ω ±20% | 90MHz | Kit |
| LQH44PN2R2MJ0□ | 2.2μH ±20% | 1320mA | 1230mA | 0.074Ω ±20% | 68MHz | Kit |
| LQH44PN3R3MJ0□ | 3.3μH ±20% | 900mA | 1000mA | 0.088Ω ±20% | 55MHz | Kit |
| LQH44PN4R7MJ0□ | 4.7μH ±20% | 840mA | 980mA | 0.117Ω ±20% | 50MHz | Kit |
| LQH44PN6R8MJ0□ | 6.8μH ±20% | 720mA | 860mA | 0.143Ω ±20% | 38MHz | Kit |
| LQH44PN100MJ0□ | 10μH ±20% | 560mA | 790mA | 0.207Ω ±20% | 30MHz | Kit |
| LQH44PN150MJ0□ | 15μH ±20% | 430mA | 610mA | 0.385Ω ±20% | 25MHz | Kit |
| LQH44PN220MJ0□ | 22μH ±20% | 400mA | 550mA | 0.480Ω ±20% | 18MHz | Kit |
| LQH44PN330MJ0□ | 33μH ±20% | 360mA | 430mA | 0.740Ω ±20% | 15MHz | Kit |
| LQH44PN470MJ0□ | 47μH ±20% | 300mA | 380mA | 1.014Ω ±20% | 13MHz | Kit |

Inductance Test Frequency: 100kHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin

Operating Temperature Range (Self-temperature rise is included): -40°C~+125°C

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


For reflow soldering only.

*1 When applied rated current to the products, inductance will be within ±30% of initial inductance value.


*2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.

*3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

■ Inductance-Frequency Characteristics (Typ.)




■ Inductance-Current Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Temperature Rise Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH5BPN_T0 Series 2020/5050 (inch/mm)

Size Code 2020 (5050) in inch (in mm), 2.2mm max. Thickness

■ Appearance/Dimensions



(in mm)

■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 500 |
| K | ø330mm Embossed Taping | 3000 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | Kit |
|----------------|-------------|---|--|---------------|---------------------------------|-----|
| LQH5BPNR47NT0□ | 0.47μH ±30% | 7.7A | 4.0A | 0.012Ω ±20% | 220MHz | Kit |
| LQH5BPN1R0NT0□ | 1.0μH ±30% | 5.8A | 3.1A | 0.019Ω ±20% | 90MHz | Kit |
| LQH5BPN1R2NT0□ | 1.2μH ±30% | 5.4A | 3.1A | 0.019Ω ±20% | 90MHz | Kit |
| LQH5BPN1R5NT0□ | 1.5μH ±30% | 5.0A | 3.0A | 0.024Ω ±20% | 70MHz | Kit |
| LQH5BPN2R2NT0□ | 2.2μH ±30% | 4.0A | 2.6A | 0.030Ω ±20% | 55MHz | Kit |
| LQH5BPN2R7NT0□ | 2.7μH ±30% | 3.8A | 2.5A | 0.035Ω ±20% | 50MHz | Kit |
| LQH5BPN3R3NT0□ | 3.3μH ±30% | 3.5A | 2.3A | 0.044Ω ±20% | 40MHz | Kit |
| LQH5BPN4R7NT0□ | 4.7μH ±30% | 3.0A | 2.0A | 0.058Ω ±20% | 40MHz | Kit |
| LQH5BPN6R8NT0□ | 6.8μH ±30% | 2.5A | 1.65A | 0.083Ω ±20% | 30MHz | Kit |
| LQH5BPN100MT0□ | 10μH ±20% | 2.0A | 1.60A | 0.106Ω ±20% | 25MHz | Kit |
| LQH5BPN150MT0□ | 15μH ±20% | 1.6A | 1.20A | 0.187Ω ±20% | 18MHz | Kit |
| LQH5BPN220MT0□ | 22μH ±20% | 1.4A | 1.05A | 0.259Ω ±20% | 15MHz | Kit |

Inductance Test Frequency: 100kHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin

Operating Temperature Range (Self-temperature rise is included): -40°C~+125°C

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


For reflow soldering only.

*1 When applied rated current to the products, inductance will be within ±30% of initial inductance value.


*2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.

*3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

■ Inductance-Frequency Characteristics (Typ.)




■ Inductance-Current Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Temperature Rise Characteristics (Typ.)




Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH5BPB_T0 Series 2020/5050 (inch/mm)

For Automotive Use *Expect for the portion asked for high reliability ex. power train

■ Appearance/Dimensions



(in mm)

■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 500 |
| K | ø330mm Embossed Taping | 3000 |



Refer to pages 102 to 106 for mounting information.


■ Rated Value (□: packaging code)

| Part Number | Inductance | Rated Current ^{*1*3} (Based on Inductance Change) | Rated Current ^{*2*3} (Based on Temperature Rise) | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---|--|---------------|---------------------------------|-----|
| LQH5BPBR47NT0□ | 0.47μH ±30% | 7.7A | 4A | 0.012Ω ±20% | 220MHz | New |
| LQH5BPB1R0NT0□ | 1μH ±30% | 5.8A | 3.1A | 0.019Ω ±20% | 90MHz | New |
| LQH5BPB1R2NT0□ | 1.2μH ±30% | 5.4A | 3.1A | 0.019Ω ±20% | 90MHz | New |
| LQH5BPB1R5NT0□ | 1.5μH ±30% | 5.0A | 3A | 0.024Ω ±20% | 70MHz | New |
| LQH5BPB2R2NT0□ | 2.2μH ±30% | 4.0A | 2.6A | 0.030Ω ±20% | 55MHz | New |
| LQH5BPB2R7NT0□ | 2.7μH ±30% | 3.8A | 2.5A | 0.035Ω ±20% | 50MHz | New |
| LQH5BPB3R3NT0□ | 3.3μH ±30% | 3.5A | 2.3A | 0.044Ω ±20% | 40MHz | New |
| LQH5BPB4R7NT0□ | 4.7μH ±30% | 3.0A | 2A | 0.058Ω ±20% | 40MHz | New |
| LQH5BPB6R8NT0□ | 6.8μH ±30% | 2.5A | 1.65A | 0.083Ω ±20% | 30MHz | New |
| LQH5BPB100MT0□ | 10μH ±20% | 2.0A | 1.6A | 0.106Ω ±20% | 25MHz | New |
| LQH5BPB150MT0□ | 15μH ±20% | 1.6A | 1.2A | 0.187Ω ±20% | 18MHz | New |
| LQH5BPB220MT0□ | 22μH ±20% | 1.4A | 1.05A | 0.259Ω ±20% | 15MHz | New |


Inductance Test Frequency: 100kHz Class of Magnetic Shield: Magnetic shield of magnetic powder in resin
 Operating Temperature Range (Self-temperature rise is included): -40°C~+125°C
 Operating Temperature Range (Self-temperature rise is not included): -40°C~+105°C
 For reflow soldering only.

*1 When applied rated current to the products, inductance will be within ±30% of initial inductance value.
 *2 When applied rated current to the products, self-temperature rise shall be limited to 40°C max.
 *3 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

■ Inductance-Frequency Characteristics (Typ.)




■ Inductance-Current Characteristics (Typ.)



Continued on the following page.


△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Temperature Rise Characteristics (Typ.)



■ Derating of Rated Current

In operating temperature exceeding +85°C, derating of current is necessary for LQH5BPB series. Please apply the derating curve shown in chart according to the operating temperature.




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM18FN_00

Series 0603/1608 (inch/mm)

Size Code 0603 (1608) in inch (in mm)

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| J | ø330mm Paper Taping | 10000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM18FN1R0M00□ | 1.0μH ±20% | 1MHz | 150mA | 0.20 Ω ±30% | 120MHz | Kit |
| LQM18FN2R2M00□ | 2.2μH ±20% | 1MHz | 120mA | 0.40 Ω ±30% | 80MHz | Kit |
| LQM18FN4R7M00□ | 4.7μH ±20% | 1MHz | 80mA | 0.60 Ω ±30% | 50MHz | Kit |
| LQM18FN100M00□ | 10μH ±20% | 1MHz | 50mA | 0.90 Ω ±30% | 30MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite
 Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C

Impedance-Frequency Characteristics (Typ.)



Inductance-Current Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM21DN_00 Series 0805/2012 (inch/mm)

Low DC Resistance Type

Appearance/Dimensions



| | | |
|----------------|-------------------------------|----------------|
| Dimension of t | Inductance: 1.0 to 10 μ H | 0.85 \pm 0.2 |
| | Inductance: 22 to 47 μ H | 1.25 \pm 0.2 |

Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------------|------------------|
| D | ϕ 180mm Paper Taping | 4000 |
| L | ϕ 180mm Embossed Taping | 3000 |
| J | ϕ 330mm Paper Taping | 10000 |
| K | ϕ 330mm Embossed Taping | 10000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Self-Resonance Frequency (min.) |
|----------------|-----------------------|---------------------------|---------------|-----------------------|---------------------------------|
| LQM21DN1R0N00□ | 1.0 μ H \pm 30% | 1MHz | 60mA | 0.10 Ω | 75MHz |
| LQM21DN2R2N00□ | 2.2 μ H \pm 30% | 1MHz | 40mA | 0.17 Ω | 50MHz |
| LQM21DN4R7N00□ | 4.7 μ H \pm 30% | 1MHz | 30mA | 0.30 Ω | 35MHz |
| LQM21DN100N00□ | 10 μ H \pm 30% | 1MHz | 15mA | 0.50 Ω | 24MHz |
| LQM21DN220N00□ | 22 μ H \pm 30% | 1MHz | 13mA | 0.65 Ω | 16MHz |
| LQM21DN470N00□ | 47 μ H \pm 30% | 1MHz | 7.0mA | 1.20 Ω | 7.5MHz |

Class of Magnetic Shield: Magnetic shield of ferrite
 Operating Temperature Range (Self-temperature rise is not included): -40 $^{\circ}$ C~+85 $^{\circ}$ C

Impedance-Frequency Characteristics (Typ.)



Inductance-Current Characteristics (Typ.)




Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM21FN_00 Series 0805/2012 (inch/mm)

Bias Current Characteristics Improved

Appearance/Dimensions



| | | |
|----------------|--------------------------|----------|
| Dimension of t | Inductance: 1.0 to 2.2μH | 0.85±0.2 |
| | Inductance: 4.7 to 47μH | 1.25±0.2 |

(in mm)

Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| L | ø180mm Embossed Taping | 3000 |
| J | ø330mm Paper Taping | 10000 |
| K | ø330mm Embossed Taping | 10000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM21FN1R0N00□ | 1.0μH ±30% | 1MHz | 220mA | 0.20 Ω ±30% | 105MHz | Kit |
| LQM21FN2R2N00□ | 2.2μH ±30% | 1MHz | 150mA | 0.28 Ω ±30% | 70MHz | Kit |
| LQM21FN4R7N00□ | 4.7μH ±30% | 1MHz | 80mA | 0.30 Ω ±30% | 25MHz | |
| LQM21FN100N00□ | 10μH ±30% | 1MHz | 60mA | 0.50 Ω ±30% | 15MHz | |
| LQM21FN220N00□ | 22μH ±30% | 1MHz | 13mA | 0.35 Ω ±30% | 15MHz | Kit |
| LQM21FN470N00□ | 47μH ±30% | 1MHz | 7.0mA | 0.60 Ω ±30% | 7.5MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite
 Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

Impedance-Frequency Characteristics (Typ.)



Inductance-Current Characteristics (Typ.)




Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM21FN_70 Series 0805/2012 (inch/mm)

Large Current

Appearance/Dimensions



(in mm)

Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM21FN4R7M70□ | 4.7μH ±20% | 1MHz | 120mA | 0.35 Ω ±30% | 25MHz | Kit |
| LQM21FN100M70□ | 10μH ±20% | 1MHz | 100mA | 0.60 Ω ±30% | 15MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite
 Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C

Impedance-Frequency Characteristics (Typ.)



Inductance-Current Characteristics (Typ.)




Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM21FN_80 Series 0805/2012 (inch/mm)

Large Current, Low DC Resistance Type

Appearance/Dimensions



(in mm)

Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |
| K | ø330mm Embossed Taping | 10000 |
| B | Packing in Bulk | 1000 |




Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|---------------|---------------------------------|-----|
| LQM21FN4R7M80□ | 4.7μH ±20% | 1MHz | 120mA | 0.18 Ω ±30% | 25MHz | Kit |
| LQM21FN100M80□ | 10μH ±20% | 1MHz | 100mA | 0.30 Ω ±30% | 15MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite
 Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C

Impedance-Frequency Characteristics (Typ.)



Inductance-Current Characteristics (Typ.)




Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQW15CN_00 Series 0402/1005 (inch/mm)

For Voltage Conversion

Appearance/Dimensions



(in mm)

Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 10000 |
| B | Packing in Bulk | 500 |



Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|---------------------------------|-----|
| LQW15CN18NJ00□ | 18nH ±5% | 100MHz | 1400mA | 0.046Ω | 3000MHz | Kit |
| LQW15CN33NJ00□ | 33nH ±5% | 100MHz | 1300mA | 0.065Ω | 1800MHz | Kit |
| LQW15CN48NJ00□ | 48nH ±5% | 100MHz | 1100mA | 0.078Ω | 1400MHz | Kit |
| LQW15CN70NJ00□ | 70nH ±5% | 100MHz | 820mA | 0.12Ω | 1300MHz | Kit |
| LQW15CN96NJ00□ | 96nH ±5% | 100MHz | 730mA | 0.16Ω | 1100MHz | Kit |
| LQW15CNR13J00□ | 130nH ±5% | 100MHz | 640mA | 0.23Ω | 1000MHz | Kit |
| LQW15CNR16J00□ | 160nH ±5% | 100MHz | 480mA | 0.33Ω | 900MHz | Kit |
| LQW15CNR20J00□ | 200nH ±5% | 100MHz | 390mA | 0.47Ω | 800MHz | Kit |


Class of Magnetic Shield: No magnetic shield

Operating Temperature Range (Self-temperature rise is included): -55°C~+135°C


Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C

For reflow soldering only.

Impedance-Frequency Characteristics (Typ.)



Inductance-Current Characteristics (Typ.)




Derating of Rated Current

In operating temperature exceeding +85°C, derating of current is necessary for LQW15C series.

Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current




Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQW15CN_10 Series 0402/1005 (inch/mm)

For RF Choke, Voltage Conversion

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 10000 |
| B | Packing in Bulk | 500 |




Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|---------------------------------|-----|
| LQW15CNR22J10□ | 220nH ±5% | 100MHz | 450mA | 0.47Ω | 1400MHz | New |
| LQW15CNR22K10□ | 220nH ±10% | 100MHz | 450mA | 0.47Ω | 1400MHz | New |
| LQW15CNR27J10□ | 270nH ±5% | 100MHz | 420mA | 0.52Ω | 830MHz | New |
| LQW15CNR27K10□ | 270nH ±10% | 100MHz | 420mA | 0.52Ω | 830MHz | New |
| LQW15CNR33J10□ | 330nH ±5% | 100MHz | 390mA | 0.56Ω | 520MHz | New |
| LQW15CNR33K10□ | 330nH ±10% | 100MHz | 390mA | 0.56Ω | 520MHz | New |
| LQW15CNR39J10□ | 390nH ±5% | 100MHz | 370mA | 0.62Ω | 450MHz | New |
| LQW15CNR39K10□ | 390nH ±10% | 100MHz | 370mA | 0.62Ω | 450MHz | Kit |
| LQW15CNR42J10□ | 420nH ±5% | 10MHz | 370mA | 0.62Ω | 400MHz | New |
| LQW15CNR42K10□ | 420nH ±10% | 10MHz | 370mA | 0.62Ω | 400MHz | New |
| LQW15CNR47J10□ | 470nH ±5% | 10MHz | 350mA | 0.66Ω | 380MHz | New |
| LQW15CNR47K10□ | 470nH ±10% | 10MHz | 350mA | 0.66Ω | 380MHz | New |
| LQW15CNR56J10□ | 560nH ±5% | 10MHz | 300mA | 0.71Ω | 300MHz | New |
| LQW15CNR56K10□ | 560nH ±10% | 10MHz | 300mA | 0.71Ω | 300MHz | Kit |

Class of Magnetic Shield: No magnetic shield
 Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
 For reflow soldering only.

■ Impedance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



Continued on the following page.


△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Derating of Rated Current

In operating temperature exceeding +85°C, derating of current is necessary for LQW15C series.

Please apply the derating curve shown in chart according to the operating temperature.


Derating of Rated Current



LQW18CN_00 Series 0603/1608 (inch/mm)

for FM/TV Band Choke

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| B | Packing in Bulk | 500 |




Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|---------------------------------|-----|
| LQW18CN4N9D00□ | 4.9nH ±0.5nH | 10MHz | 2600mA | 0.015Ω | 2300MHz | Kit |
| LQW18CN15NJ00□ | 15nH ±5% | 10MHz | 2200mA | 0.025Ω | 2000MHz | Kit |
| LQW18CN33NJ00□ | 33nH ±5% | 10MHz | 1700mA | 0.035Ω | 1800MHz | Kit |
| LQW18CN55NJ00□ | 55nH ±5% | 10MHz | 1500mA | 0.045Ω | 1600MHz | Kit |
| LQW18CN85NJ00□ | 85nH ±5% | 10MHz | 1400mA | 0.060Ω | 1380MHz | Kit |
| LQW18CNR10K00□ | 100nH ±10% | 10MHz | 1000mA | 0.10Ω | 1260MHz | Kit |
| LQW18CNR12J00□ | 120nH ±5% | 10MHz | 1100mA | 0.085Ω | 1200MHz | Kit |
| LQW18CNR16J00□ | 160nH ±5% | 10MHz | 1000mA | 0.10Ω | 900MHz | Kit |
| LQW18CNR21J00□ | 210nH ±5% | 10MHz | 800mA | 0.15Ω | 720MHz | Kit |
| LQW18CNR27J00□ | 270nH ±5% | 10MHz | 750mA | 0.16Ω | 660MHz | Kit |
| LQW18CNR33J00□ | 330nH ±5% | 10MHz | 630mA | 0.25Ω | 600MHz | Kit |
| LQW18CNR39J00□ | 390nH ±5% | 10MHz | 620mA | 0.28Ω | 570MHz | Kit |
| LQW18CNR47J00□ | 470nH ±5% | 10MHz | 500mA | 0.45Ω | 555MHz | Kit |
| LQW18CNR56J00□ | 560nH ±5% | 10MHz | 450mA | 0.48Ω | 540MHz | Kit |
| LQW18CNR65J00□ | 650nH ±5% | 10MHz | 430mA | 0.52Ω | 510MHz | Kit |

Class of Magnetic Shield: No magnetic shield
 Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C
 For reflow soldering only.

Impedance-Frequency Characteristics (Typ.)



Inductance-Current Characteristics (Typ.)




Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH31CN_03 Series 1206/3216 (inch/mm)

Size Code 1206 (3216) in inch (in mm)

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |
| K | ø330mm Embossed Taping | 7500 |



Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current ^{*1} | DC Resistance | Self-Resonance Frequency (min.) |
|----------------|-------------|---------------------------|-----------------------------|---------------|---------------------------------|
| LQH31CNR12M03□ | 0.12μH ±20% | 1MHz | 970mA | 0.08Ω ±40% | 250MHz |
| LQH31CNR22M03□ | 0.22μH ±20% | 1MHz | 850mA | 0.1Ω ±40% | 250MHz |
| LQH31CNR47M03□ | 0.47μH ±20% | 1MHz | 700mA | 0.15Ω ±40% | 180MHz |
| LQH31CN1R0M03□ | 1.0μH ±20% | 1MHz | 510mA | 0.28Ω ±30% | 100MHz |
| LQH31CN2R2M03□ | 2.2μH ±20% | 1MHz | 430mA | 0.41Ω ±30% | 50MHz |
| LQH31CN4R7M03□ | 4.7μH ±20% | 1MHz | 340mA | 0.65Ω ±30% | 31MHz |
| LQH31CN100K03□ | 10μH ±10% | 1MHz | 230mA | 1.3Ω ±30% | 20MHz |
| LQH31CN220K03□ | 22μH ±10% | 1MHz | 160mA | 3.0Ω ±30% | 14MHz |
| LQH31CN470K03□ | 47μH ±10% | 1MHz | 100mA | 8.0Ω ±30% | 10MHz |
| LQH31CN101K03□ | 100μH ±10% | 1MHz | 80mA | 12.0Ω ±30% | 7MHz |

Class of Magnetic Shield: No magnetic shield


Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

*1 When applied rated current to the products, self-temperature rise shall be limited to 35°C max. and inductance will be within ±10% of initial inductance value.

Impedance-Frequency Characteristics (Typ.)



Inductance-Current Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH32CN_23/LQH32CN_33 Series 1210/3225 (inch/mm)

Size Code 1210 (3225) in inch (in mm)

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |
| K | ø330mm Embossed Taping | 7500 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current ^{*1} | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---------------------------|-----------------------------|---------------|---------------------------------|-----|
| LQH32CN1R0M23□ | 1.0μH ±20% | 1MHz | 800mA | 0.09Ω ±30% | 96MHz | Kit |
| LQH32CN2R2M23□ | 2.2μH ±20% | 1MHz | 600mA | 0.13Ω ±30% | 64MHz | Kit |
| LQH32CN4R7M23□ | 4.7μH ±20% | 1MHz | 450mA | 0.2Ω ±30% | 43MHz | Kit |
| LQH32CN100K23□ | 10μH ±10% | 1MHz | 300mA | 0.44Ω ±30% | 26MHz | Kit |
| LQH32CN220K23□ | 22μH ±10% | 1MHz | 250mA | 0.71Ω ±30% | 19MHz | Kit |
| LQH32CN470K23□ | 47μH ±10% | 1MHz | 170mA | 1.3Ω ±30% | 15MHz | Kit |
| LQH32CN101K23□ | 100μH ±10% | 1MHz | 100mA | 3.5Ω ±30% | 10MHz | Kit |
| LQH32CN221K23□ | 220μH ±10% | 1MHz | 70mA | 8.4Ω ±30% | 6.8MHz | Kit |
| LQH32CN331K23□ | 330μH ±10% | 1MHz | 60mA | 10.0Ω ±30% | 5.6MHz | Kit |
| LQH32CN391K23□ | 390μH ±10% | 1MHz | 60mA | 17Ω ±30% | 5MHz | Kit |
| LQH32CN471K23□ | 470μH ±10% | 1kHz | 60mA | 19Ω ±30% | 5MHz | Kit |
| LQH32CN561K23□ | 560μH ±10% | 1kHz | 60mA | 22.0Ω ±30% | 5MHz | Kit |
| LQH32CNR15M33□ | 0.15μH ±20% | 1MHz | 1450mA | 0.028Ω ±30% | 400MHz | Kit |
| LQH32CNR27M33□ | 0.27μH ±20% | 1MHz | 1250mA | 0.034Ω ±30% | 250MHz | Kit |
| LQH32CNR47M33□ | 0.47μH ±20% | 1MHz | 1100mA | 0.042Ω ±30% | 150MHz | Kit |
| LQH32CN1R0M33□ | 1.0μH ±20% | 1MHz | 1000mA | 0.06Ω ±30% | 100MHz | Kit |
| LQH32CN2R2M33□ | 2.2μH ±20% | 1MHz | 790mA | 0.097Ω ±30% | 64MHz | Kit |
| LQH32CN4R7M33□ | 4.7μH ±20% | 1MHz | 650mA | 0.15Ω ±30% | 43MHz | Kit |
| LQH32CN100K33□ | 10μH ±10% | 1MHz | 450mA | 0.3Ω ±30% | 26MHz | Kit |

Class of Magnetic Shield: No magnetic shield


Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

*1 When applied rated current to the products, self-temperature rise shall be limited to 20°C max. and inductance will be within ±10% of initial inductance value.


Continued on the following page. ↗

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Impedance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH32CN_53 Series 1210/3225 (inch/mm)

Size Code 1210 (3225) in inch (in mm)

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |
| K | ø330mm Embossed Taping | 7500 |



Refer to pages 102 to 106 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current ^{*1} | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|-----------------------------|---------------|---------------------------------|-----|
| LQH32CN1R0M53□ | 1.0μH ±20% | 1MHz | 1000mA | 0.060Ω ±30% | 100MHz | Kit |
| LQH32CN2R2M53□ | 2.2μH ±20% | 1MHz | 790mA | 0.097Ω ±30% | 64MHz | Kit |
| LQH32CN3R3M53□ | 3.3μH ±20% | 1MHz | 710mA | 0.12Ω ±30% | 50MHz | |
| LQH32CN4R7M53□ | 4.7μH ±20% | 1MHz | 650mA | 0.15Ω ±30% | 43MHz | Kit |
| LQH32CN6R8M53□ | 6.8μH ±20% | 1MHz | 540mA | 0.25Ω ±30% | 32MHz | |
| LQH32CN100K53□ | 10μH ±10% | 1MHz | 450mA | 0.30Ω ±30% | 26MHz | Kit |
| LQH32CN150K53□ | 15μH ±10% | 1MHz | 300mA | 0.58Ω ±30% | 26MHz | Kit |
| LQH32CN220K53□ | 22μH ±10% | 1MHz | 250mA | 0.71Ω ±30% | 19MHz | Kit |
| LQH32CN330K53□ | 33μH ±10% | 1MHz | 200mA | 1.1Ω ±30% | 17MHz | Kit |
| LQH32CN470K53□ | 47μH ±10% | 1MHz | 170mA | 1.3Ω ±30% | 15MHz | Kit |
| LQH32CN680K53□ | 68μH ±10% | 1MHz | 130mA | 2.2Ω ±30% | 12MHz | Kit |
| LQH32CN101K53□ | 100μH ±10% | 1MHz | 100mA | 3.5Ω ±30% | 10MHz | Kit |

Class of Magnetic Shield: No magnetic shield


Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

*1 When applied rated current to the products, self-temperature rise shall be limited to 20°C max. and inductance will be within ±10% of initial inductance value.

■ Impedance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH43CN_03 Series 1812/4532 (inch/mm)

Size Code 1812 (4532) in inch (in mm)

Appearance/Dimensions



(in mm)

Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 500 |



Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current ^{*1} | Max. of DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|-----------------------------|-----------------------|---------------------------------|-----|
| LQH43CN1R0M03□ | 1.0μH ±20% | 1MHz | 1080mA | 0.08Ω | 100MHz | Kit |
| LQH43CN1R5M03□ | 1.5μH ±20% | 1MHz | 1000mA | 0.09Ω | 85MHz | Kit |
| LQH43CN2R2M03□ | 2.2μH ±20% | 1MHz | 900mA | 0.11Ω | 60MHz | Kit |
| LQH43CN3R3M03□ | 3.3μH ±20% | 1MHz | 800mA | 0.13Ω | 47MHz | Kit |
| LQH43CN4R7M03□ | 4.7μH ±20% | 1MHz | 750mA | 0.15Ω | 35MHz | Kit |
| LQH43CN6R8M03□ | 6.8μH ±20% | 1MHz | 720mA | 0.20Ω | 30MHz | Kit |
| LQH43CN100K03□ | 10μH ±10% | 1MHz | 650mA | 0.24Ω | 23MHz | Kit |
| LQH43CN150K03□ | 15μH ±10% | 1MHz | 570mA | 0.32Ω | 20MHz | Kit |
| LQH43CN220K03□ | 22μH ±10% | 1MHz | 420mA | 0.6Ω | 15MHz | Kit |
| LQH43CN330K03□ | 33μH ±10% | 1MHz | 310mA | 1.0Ω | 12MHz | Kit |
| LQH43CN470K03□ | 47μH ±10% | 1MHz | 280mA | 1.1Ω | 10MHz | Kit |
| LQH43CN680K03□ | 68μH ±10% | 1MHz | 220mA | 1.7Ω | 8.4MHz | Kit |
| LQH43CN101K03□ | 100μH ±10% | 1MHz | 190mA | 2.2Ω | 6.8MHz | Kit |
| LQH43CN151K03□ | 150μH ±10% | 1MHz | 130mA | 3.5Ω | 5.5MHz | Kit |
| LQH43CN221K03□ | 220μH ±10% | 1MHz | 110mA | 4.0Ω | 4.5MHz | Kit |
| LQH43CN331K03□ | 330μH ±10% | 1MHz | 100mA | 6.8Ω | 3.6MHz | Kit |
| LQH43CN471K03□ | 470μH ±10% | 1kHz | 90mA | 8.5Ω | 3.0MHz | Kit |

Class of Magnetic Shield: No magnetic shield


Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

*1 When applied rated current to the products, self-temperature rise shall be limited to 20°C max. and inductance will be within ±10% of initial inductance value.

Impedance-Frequency Characteristics (Typ.)



Inductance-Current Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH43CN_33 Series 1812/4532 (inch/mm)

Low DC Resistance Type

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 500 |



Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current ^{*1} | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---------------------------|-----------------------------|---------------|---------------------------------|-----|
| LQH43CNR56M33□ | 0.56μH ±20% | 1MHz | 2950mA | 0.023Ω ±30% | 160MHz | Kit |
| LQH43CNR82M33□ | 0.82μH ±20% | 1MHz | 2800mA | 0.027Ω ±30% | 130MHz | Kit |
| LQH43CN1R0M33□ | 1.0μH ±20% | 1MHz | 2600mA | 0.032Ω ±30% | 110MHz | Kit |
| LQH43CN1R5M33□ | 1.5μH ±20% | 1MHz | 2450mA | 0.036Ω ±30% | 80MHz | Kit |
| LQH43CN1R8M33□ | 1.8μH ±20% | 1MHz | 2300mA | 0.042Ω ±30% | 70MHz | Kit |
| LQH43CN2R2M33□ | 2.2μH ±20% | 1MHz | 2100mA | 0.047Ω ±30% | 60MHz | Kit |
| LQH43CN2R7M33□ | 2.7μH ±20% | 1MHz | 1800mA | 0.053Ω ±30% | 50MHz | Kit |
| LQH43CN3R3M33□ | 3.3μH ±20% | 1MHz | 1650mA | 0.076Ω ±30% | 47MHz | Kit |
| LQH43CN3R9M33□ | 3.9μH ±20% | 1MHz | 1600mA | 0.082Ω ±30% | 40MHz | Kit |

Class of Magnetic Shield: No magnetic shield


Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

*1 When applied rated current to the products, self-temperature rise shall be limited to 40°C max. and inductance will be within ±20% of initial inductance value.

Impedance-Frequency Characteristics (Typ.)



Inductance-Current Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH55DN_03 Series 2220/5750 (inch/mm)

Large Current

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 350 |
| K | ø330mm Embossed Taping | 1500 |



Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current ^{*1} | DC Resistance | Self-Resonance Frequency (min.) |
|----------------|--------------|---------------------------|-----------------------------|---------------|---------------------------------|
| LQH55DNR12M03□ | 0.12μH ±20% | 1MHz | 6000mA | 0.007Ω ±40% | 450MHz |
| LQH55DNR27M03□ | 0.27μH ±20% | 1MHz | 5300mA | 0.010Ω ±40% | 300MHz |
| LQH55DNR47M03□ | 0.47μH ±20% | 1MHz | 4800mA | 0.013Ω ±40% | 200MHz |
| LQH55DN1R0M03□ | 1.0μH ±20% | 1MHz | 4000mA | 0.019Ω ±40% | 150MHz |
| LQH55DN1R5M03□ | 1.5μH ±20% | 1MHz | 3700mA | 0.022Ω ±40% | 110MHz |
| LQH55DN2R2M03□ | 2.2μH ±20% | 1MHz | 3200mA | 0.029Ω ±40% | 80MHz |
| LQH55DN3R3M03□ | 3.3μH ±20% | 1MHz | 2900mA | 0.036Ω ±40% | 40MHz |
| LQH55DN4R7M03□ | 4.7μH ±20% | 1MHz | 2700mA | 0.041Ω ±40% | 30MHz |
| LQH55DN6R8M03□ | 6.8μH ±20% | 1MHz | 2000mA | 0.074Ω ±40% | 25MHz |
| LQH55DN100M03□ | 10μH ±20% | 1MHz | 1700mA | 0.093Ω ±40% | 20MHz |
| LQH55DN150M03□ | 15μH ±20% | 1MHz | 1400mA | 0.15Ω ±40% | 17MHz |
| LQH55DN220M03□ | 22μH ±20% | 1MHz | 1200mA | 0.19Ω ±40% | 15MHz |
| LQH55DN330M03□ | 33μH ±20% | 1MHz | 900mA | 0.32Ω ±40% | 12MHz |
| LQH55DN470M03□ | 47μH ±20% | 1MHz | 800mA | 0.40Ω ±40% | 10MHz |
| LQH55DN680M03□ | 68μH ±20% | 1MHz | 640mA | 0.67Ω ±40% | 7.6MHz |
| LQH55DN101M03□ | 100μH ±20% | 100kHz | 560mA | 0.86Ω ±40% | 6.5MHz |
| LQH55DN151M03□ | 150μH ±20% | 100kHz | 420mA | 1.9Ω ±40% | 5.0MHz |
| LQH55DN221M03□ | 220μH ±20% | 100kHz | 320mA | 2.4Ω ±40% | 4.0MHz |
| LQH55DN331M03□ | 330μH ±20% | 100kHz | 270mA | 4.4Ω ±40% | 3.1MHz |
| LQH55DN471M03□ | 470μH ±20% | 100kHz | 240mA | 5.4Ω ±40% | 2.4MHz |
| LQH55DN681M03□ | 680μH ±20% | 100kHz | 190mA | 8.1Ω ±40% | 1.9MHz |
| LQH55DN102M03□ | 1000μH ±20% | 10kHz | 150mA | 10.3Ω ±40% | 1.7MHz |
| LQH55DN222M03□ | 2200μH ±20% | 10kHz | 100mA | 21.5Ω ±40% | 1.2MHz |
| LQH55DN472M03□ | 4700μH ±20% | 10kHz | 70mA | 43.6Ω ±40% | 0.8MHz |
| LQH55DN103M03□ | 10000μH ±20% | 10kHz | 50mA | 100Ω ±40% | 0.5MHz |

Class of Magnetic Shield: No magnetic shield


Operating Temperature Range (Self-temperature rise is not included): -40°C~+80°C

For reflow soldering only.


*1 When applied rated current to the products, self-temperature rise shall be limited to 40°C max. and inductance will be within ±40% of initial inductance value.

Continued on the following page.

■ Impedance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH66SN_03 Series 2525/6363 (inch/mm)

Closed Magnetic Circuit

Appearance/Dimensions



(in mm)

Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 350 |
| K | ø330mm Embossed Taping | 1500 |



Refer to pages 102 to 106 for mounting information.

Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current ^{*1} | DC Resistance | Self-Resonance Frequency (min.) |
|----------------|--------------|---------------------------|-----------------------------|---------------|---------------------------------|
| LQH66SNR27M03□ | 0.27μH ±20% | 1MHz | 6000mA | 0.007Ω ±40% | 300MHz |
| LQH66SNR68M03□ | 0.68μH ±20% | 1MHz | 5300mA | 0.010Ω ±40% | 180MHz |
| LQH66SN1R0M03□ | 1.0μH ±20% | 1MHz | 4700mA | 0.013Ω ±40% | 150MHz |
| LQH66SN1R5M03□ | 1.5μH ±20% | 1MHz | 3800mA | 0.016Ω ±40% | 110MHz |
| LQH66SN2R2M03□ | 2.2μH ±20% | 1MHz | 3300mA | 0.019Ω ±40% | 80MHz |
| LQH66SN3R3M03□ | 3.3μH ±20% | 1MHz | 2600mA | 0.022Ω ±40% | 40MHz |
| LQH66SN4R7M03□ | 4.7μH ±20% | 1MHz | 2200mA | 0.025Ω ±40% | 30MHz |
| LQH66SN6R8M03□ | 6.8μH ±20% | 1MHz | 1800mA | 0.029Ω ±40% | 25MHz |
| LQH66SN100M03□ | 10μH ±20% | 1MHz | 1600mA | 0.036Ω ±40% | 20MHz |
| LQH66SN150M03□ | 15μH ±20% | 1MHz | 1300mA | 0.069Ω ±40% | 17MHz |
| LQH66SN220M03□ | 22μH ±20% | 1MHz | 1100mA | 0.087Ω ±40% | 15MHz |
| LQH66SN330M03□ | 33μH ±20% | 1MHz | 860mA | 0.14Ω ±40% | 12MHz |
| LQH66SN470M03□ | 47μH ±20% | 1MHz | 760mA | 0.17Ω ±40% | 10MHz |
| LQH66SN680M03□ | 68μH ±20% | 1MHz | 600mA | 0.29Ω ±40% | 7.6MHz |
| LQH66SN101M03□ | 100μH ±20% | 100kHz | 520mA | 0.36Ω ±40% | 6.5MHz |
| LQH66SN151M03□ | 150μH ±20% | 100kHz | 420mA | 0.63Ω ±40% | 5.0MHz |
| LQH66SN221M03□ | 220μH ±20% | 100kHz | 350mA | 0.79Ω ±40% | 4.0MHz |
| LQH66SN331M03□ | 330μH ±20% | 100kHz | 280mA | 1.8Ω ±40% | 3.2MHz |
| LQH66SN471M03□ | 470μH ±20% | 100kHz | 240mA | 2.2Ω ±40% | 2.5MHz |
| LQH66SN681M03□ | 680μH ±20% | 100kHz | 200mA | 3.9Ω ±40% | 2.0MHz |
| LQH66SN102M03□ | 1000μH ±20% | 10kHz | 160mA | 4.9Ω ±40% | 1.7MHz |
| LQH66SN222M03□ | 2200μH ±20% | 10kHz | 100mA | 9.4Ω ±40% | 1.2MHz |
| LQH66SN472M03□ | 4700μH ±20% | 10kHz | 70mA | 19.5Ω ±40% | 0.8MHz |
| LQH66SN103M03□ | 10000μH ±20% | 10kHz | 50mA | 39.7Ω ±40% | 0.5MHz |

Class of Magnetic Shield: Magnetic shield of ferrite

Operating Temperature Range (Self-temperature rise is not included): -40°C~+80°C


For reflow soldering only.

*1 When applied rated current to the products, self-temperature rise shall be limited to 40°C max. and inductance will be within ±40% of initial inductance value.


Continued on the following page.

[△]Note • Please read rating and [△]CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Impedance-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)



Wire Wound Type (Ferrite Core)
Inductors for Power Lines

Inductors for General Use

RF Inductors

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Caution

● Rating

1. About the Rated Current

Do not use products beyond the rated current as this may create excessive heat and deteriorate the insulation resistance.

2. About Excessive Surge Current

Surge current (pulse current or rush current) greater than the specified rated current applied to the product may cause a critical failure, such as an open circuit, burnout caused by excessive temperature rise. Please contact us in advance in case of applying the surge current.

Notice

● Storage and Operating Condition

<Operating Environment>

Do not use products in chemical atmosphere such as chlorine gas, acid or sulfide gas.

<Storage Requirements>

1. Storage Period

LQM series should be used within 6 months; the other products should be used within 12 months. Check solderability if this period is exceeded.

2. Storage Conditions

(1) Store products in a warehouse in compliance with the following conditions:

Temperature: -10 to +40°C.

Humidity: 15 to 85% (relative humidity)

Do not subject products to rapid changes in temperature and humidity.

Do not store them in chemical atmosphere such as one containing sulfuric acid gas or alkaline gas.

This will prevent electrode oxidation, which causes poor solderability and possible corrosion of inductors.

(2) Do not store products in bulk packaging to prevent collision among inductors, which causes core chipping and wire breakage.

(3) Store products on pallets to protect from humidity, dust, etc.

(4) Avoid heat shock, vibration, direct sunlight, etc.

● Handling

This item is designed to have sufficient strength, but handle with care to avoid chipping or breaking its ceramic structure.

LQW_C series

- To prevent breaking the wire, avoid touching with sharp material, such as tweezers or other material such as bristles of cleaning brush, to the wire wound portion.
- To prevent breaking the core, avoid applying excessive mechanical shock to products mounted on the board.
- In some mounting machines, when picking up components, a support pin pushes the components up from the bottom of the base tape. In this case, please remove the support pin. The support pin may damage the components and break the wire.

- In rare cases, the laser recognition cannot recognize this component. Please contact us when you use laser recognition. (There is no problem with the permeation and reflection type.)
- The product temperature rises about 40°C maximum when the permissible current is applied to LQW15C/LQW18C. Please take care for the temperature of the substrate and air around the part.

LQH_C/D/H/M/N/P series

- To prevent breaking the wire, avoid touching with sharp material, such as tweezers or the bristles of a cleaning brush, to the wire wound portion of this product.
- To prevent breaking the core, avoid applying excessive mechanical shock to products mounted on the board.
- Temperature may rise up to max. 40°C when applying the rated current to Inductors for Power Lines. Be careful of the temperature rating of the circuit board and components around the chip Inductors.

LQM series


- There is the possibility that magnetism may change the inductance value. Do not use a magnet or tweezers with magnetism when handling chip inductors. (The tip of the tweezers should be molded with resin or pottery.)
- When the excessive current over rated current is applied, it may cause the inductance value to change due to magnetism.



<Handling>

1. Avoid applying excessive stress to products to prevent damage.
2. Do not touch wire wound with sharp objects such as tweezers to prevent wire breakage.
3. Do not apply excessive force to products mounted on boards to prevent core breakage.

<Transportation>

Do not apply excessive vibration or mechanical shock to products.

Continued on the following page. 

 Note • Please read rating and  CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

<Resin Coating>

When coating products with resin, the relatively high resin curing stress may change inductance values. For exterior coating, select resin carefully so that electrical and mechanical performance of the product is not affected. Prior to use, please evaluate reliability with the product mounted in your application set. (LQW, LQH series)

An open circuit issue may occur by mechanical stress caused by the resin, amount/cured shape of resin, or operating conditions, etc. Some resins containing impurities or chloride may possibly generate chlorine by hydrolysis under some operating conditions, causing corrosion of the inductor wire and leading to an open circuit.

<Rated Current>

(LQH2HP_G0·LQH2HP_J0 Series)

Inductance will be more than the value, which is 30% down from minimum rated Inductance value.

(Other LQH_P Series except for LQH2HP_G0 Series)

Inductance will be within ±30% of nominal Inductance value.

• Based on Temperature Rise


For LQH2MC series and LQH_P series, rated current is set to keep temperature rise caused by self heating 40°C or less.

For other Inductors for Power Lines, please refer to individual specifications.


<Handling of a Substrate>

After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting the substrate when cropping the substrate, inserting and removing a connector from the substrate, or tightening a screw to the substrate. Excessive mechanical stress may cause cracking in the Product.

Bending




Twisting



● Measuring Method

Measuring Method of Inductance/Q

1. Residual elements and stray elements of test fixtures can be described by F-parameter as shown in the following:



2. The impedance of chip inductors (chip coils) Z_x and measured value Z_m can be described by input/output current/voltage.

$$Z_m = \frac{V_1}{I_1}, \quad Z_x = \frac{V_2}{I_2}$$

3. Thus, the relation between Z_x and Z_m is shown in the following:

$$Z_x = \alpha \frac{Z_m - \beta}{1 - Z_m \Gamma} \quad \text{where, } \alpha = D / A = 1$$

$$\beta = B / D = Z_{sm} - (1 - Y_{om} Z_{sm}) Z_{ss}$$

$$\Gamma = C / A = Y_{om}$$

Z_{sm} : measured impedance of short chip
 Z_{ss} : residual impedance of short chip*
 Y_{om} : measured admittance when opening the fixture

*Residual impedance of short chip

| Residual Impedance | Series |
|--------------------|---------------|
| 0.556nH | LQW15C |
| 0.771nH | LQW18C |

4. L_x and Q_x should be calculated with the following equation.

$$L_x = \frac{\text{Im}(Z_x)}{2\pi f}, \quad Q_x = \frac{\text{Im}(Z_x)}{\text{Re}(Z_x)}$$

L_x : Inductance of chip Inductors (chip coils)
 Q_x : Q of chip Inductors (chip coils)
 f : Measuring frequency






⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Inductors for Power Lines Soldering and Mounting

1. Standard Land Pattern Dimensions

A high Q value is achieved when the PCB electrode land pattern is designed so that it does not project beyond the chip Inductors (chip coils) electrode.

Land Pattern + Solder Resist
 Land Pattern
 Solder Resist
 (in mm)

| Series | Standard Land Dimensions | | | | | | | | | | |
|---|---|---------------------------|---|-------------|-------------------|------|-----|-----|------------------------------------|------|------|
| LQM18F/18P LQM21D/21F/21P LQM2MP (Expect for LQM2MP_GH) LQM2HP (Except for LQM2HP_GH/JH) LQM31P LQM32P LQH2MC LQH31C LQH32P LQH44P LQH5BP LQH55D/66S LQW15C_00 LQW15C_10 LQW18C |  | Part Number | | a | b | c | | | | | |
| | | LQM18F/18P | Flow | 0.7 | 2.2-2.6 | | 0.7 | | | | |
| | | | Reflow | | 1.8-2.0 | | | | | | |
| | | LQM21D/21F/21P | | 1.2 | 3.0-4.0 | 1.0 | | | | | |
| | | LQM2MP | | 0.8 | 2.4 | 1.8 | | | | | |
| | | LQM2HP | | 1.6 | 3.0 | 1.5 | | | | | |
| | | LQM31P | | 2.0 | 4.2-5.2 | 1.2 | | | | | |
| | | LQM32P | | 1.9 | 3.6 | 2.7 | | | | | |
| | | LQH2MC | | 0.8 | 2.6 | 1.0 | | | | | |
| | | LQH31C | | 1.0 | 4.5 | 1.5 | | | | | |
| | | LQH32P | | 1.3 | 3.8 | 2.0 | | | | | |
| | | LQH44P | | 1.3 | 4.4 | 3.0 | | | | | |
| | | LQH5BP | | 1.8 | 5.5 | 4.1 | | | | | |
| | | LQH55D/66S | | 2.0 | 8.0 | 3.5 | | | | | |
| | | LQW15C_00 | | 0.4 | 1.4 | 0.6 | | | | | |
| | | LQW15C_10 | | 0.4 | 1.4 | 0.66 | | | | | |
| | | LQW18C | | 0.7 | 2.2 | 1.0 | | | | | |
| | | LQM2MP_GH LQM2HP_GH/JH |  | Part Number | Rated Current (A) | a | b | c | Land Pad Thickness and Dimension d | | |
| | | | | | | | | | 18µm | 35µm | 70µm |
| | | | | LQM2MP_GH | 0-1.5 | 0.8 | 2.4 | 1.8 | 1.8 | 1.8 | 1.8 |
| 1.5-2.5 | 2.4 | | | | 1.8 | | | | 1.8 | | |
| 2.5-5.0 | 5.0 | | | | 2.4 | | | | 1.8 | | |
| LQM2HP_GH | 0-1.5 | | | 1.6 | 3.0 | 1.5 | 1.5 | 1.5 | 1.5 | | |
| | 1.5-2.6 | | | | | | 2.4 | 1.5 | 1.5 | | |
| | 2.6-3.3 | | | | | | 3.6 | 2.4 | 1.5 | | |
| LQM2HP_JH | 0-1.6 | | | 1.6 | 3.0 | 1.5 | 1.5 | 1.5 | 1.5 | | |
| | 1.6-2.4 | | | | | | 2.4 | 1.5 | 1.5 | | |
| | 2.4-3.5 | 3.6 | 2.4 | | | | 1.5 | | | | |
| LQH2HP (Except for LQH2HP_GR) |  | | | | | | | | | | |
| LQH2HP_GR |  | | | | | | | | | | |
| LQH32C |  | | | | | | | | | | |

Attention should be paid to potential magnetic coupling effects when using the Inductors (coils) as a resonator.

Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Inductors for Power Lines
Soldering and Mounting
Inductors for General Use
RF Inductors

Land Pattern + Solder Resist
 Land Pattern
 Solder Resist
 (in mm)

| Series | Standard Land Dimensions |
|--------------------------|--------------------------|
| LQH3NP | |
| LQH43C LQH43P | |

2. Standard Soldering Conditions

(1) Soldering method

Chip Inductors (Chip coils) can be flow or reflow soldered. Please contact Murata regarding other soldering methods.

As for LQH2MC/2HP/3NP/32P/44P/5BP/55D/66S, LQM2MP_GH/2HP_GH/2HP_JH/32P, LQW15C/18C series, please use reflow soldering.

Solder: Use Sn-3.0Ag-0.5Cu solder.

Flux: Use rosin-based flux, but not strongly acidic flux (with chlorine content exceeding 0.2wt%).


Do not use water-soluble flux.

The flux used for LQW15C/18C series should use the rosin-based flux that includes middle activator equivalent to 0.06wt% to 0.1wt% chlorine.

For additional mounting methods, please contact Murata.

(2) Soldering profile

● Flow Soldering profile (Sn-3.0Ag-0.5Cu solder)




| Series | Pre-heating | | Standard Profile | | | Limit Profile | | |
|--|-------------|------------|------------------|------------|---------------|---------------|------------|---------------|
| | Temp. (T1) | Time. (t1) | Heating | | Cycle of flow | Heating | | Cycle of flow |
| | | | Temp. (T2) | Time. (t2) | | Temp. (T3) | Time. (t2) | |
| LQM18F/18P LQM21D/21F/21P/2MP/2HP (Except for LQM2HP_GH/JH) LQM31P LQH31C | 150°C | 60s min. | 250°C | 4 to 6s | 2 times max. | 265±3°C | 5s max. | 2 times max. |
| LQH32C LQH43C/43P | 150°C | 60s min. | 250°C | 4 to 6s | 2 times max. | 265±3°C | 5s max. | 1 times |

Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

● Reflow Soldering profile
(Sn-3.0Ag-0.5Cu solder)



| Series | Standard Profile | | | | Limit Profile | | | |
|--|------------------|------------|-----------------------|-----------------|---------------|------------|-----------------------|-----------------|
| | Heating | | Peak temperature (T2) | Cycle of reflow | Heating | | Peak temperature (T4) | Cycle of reflow |
| | Temp. (T1) | Time. (t1) | | | Temp. (T3) | Time. (t2) | | |
| LQM18F/18P LQM21D/21F/21P/2MP/2HP LQM31P/32P LQH2MC, LQH2HP LQH31C LQH3NP/32P/43P/44P/5BP LQW15C/18C | 220°C | 30 to 60s | 245±3°C | 2 times max. | 230°C | 60s max. | 260°C/10s | 2 times max. |
| LQH32C LQH43C LQH55D, LQH66S | 220°C | 30 to 60s | 245±3°C | 2 times max. | 230°C | 60s max. | 260°C/10s | 1 time |


(3) Reworking with Soldering Iron
Preheating at 150°C for 1 minute is required. Do not directly touch the ceramic element with the tip of the soldering iron. The reworking soldering conditions are as follows:

Soldering iron power output: 80W max.
Temperature of soldering iron tip: 350°C
Diameter of soldering iron end: 3.0mm max.
Soldering time: within 3 s

3. Mounting Instructions

(1) Land Pattern Dimensions

Large lands reduce Q of the mounted chip. Also, large protruding land areas (bordered by lines having dimensions 'c' and 'd' shown) cause floating and electrode leaching.




(2) Land Pattern Designing (LQH series, LQW series)

Please follow the recommended patterns. Otherwise, their performance, which includes electrical performance or solderability, may be affected, or result in "position shift" in the soldering process.

(3) Magnetic Coupling

Since some chip inductors (chip coils) are constructed like an open magnetic circuit, narrow spacing between inductors (coils) may cause magnetic coupling. LQM, LQH66S, and LQH_P series have a magnetically shielded structure. The structure makes their coupling coefficient smaller than that of conventional chip inductors (chip coils).





Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

(4) PCB Warping

PCB should be designed so that products are not subjected to the mechanical stress caused by warping the board.




(5) Amount of Solder Paste

Excessive solder causes electrode corrosion, while insufficient solder causes low electrode bonding strength. Adjust the amount of solder paste as shown on the right so that solder is applied.


● Guideline of solder paste thickness

- LQW15C: 50 to 100µm
- LQM, LQW18C, LQH2MC/2HP, LQH3NP/32P, LQH44P/5BP/55P: 100 to 150µm
- LQH31C/32C, LQH43C/43P, LQH55D, LQH66S: 200 to 300µm



(6) Amount of Adhesive

If too much adhesive is applied, then it may overflow into the land or termination areas and yield poor solderability. In contrast, if insufficient adhesive is applied, or if the adhesive is not sufficiently hardened, then the chip may become detached during flow soldering. Apply the adhesive in accordance with the conditions shown in the chart.



Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

4. Cleaning


The following conditions should be observed when cleaning chip inductors (chip coils):

- (1) Cleaning Temperature: 60°C max. (40°C max. for alcohol cleaning agents)
- (2) Ultrasonic
Output: 20W/l max.
Duration: 5 minutes max.
Frequency: 28 to 40kHz
Care should be taken not to cause resonance of the PCB and mounted products.
- (3) Cleaning agent
The following cleaning agents have been tested on individual components. Evaluation in complete assembly should be done prior to production.
 - (a) Alcohol cleaning agents
Isopropyl alcohol (IPA)
 - (b) Aqueous cleaning agents
Pine Alpha ST-100S
LQH66S series: Aqueous agents should not be used because they may cause quality deterioration or damage to appearance.

- (4) Ensure that flux residue is completely removed. Component should be thoroughly dried after aqueous agents have been removed with deionized water.

For additional cleaning methods, please contact Murata.

■ Minimum Quantity and 8mm Width Taping Dimensions



Paper Tape


| Part Number | Dimensions | | Total Thickness of Tape | Packaging Code (Minimum Qty. [pcs.]) | | |
|-------------|------------|------|-------------------------|--------------------------------------|-------------|-------------|
| | a | b | | c | ø180mm reel | ø330mm reel |
| LQW15C_00 | 0.64 | 1.18 | 0.8 max. | D [10000] | - | B [500] |
| LQW15C_10 | 0.69 | 1.18 | 0.8 max. | D [10000] | - | B [500] |

(in mm)

Continued on the following page.

Note • Please read rating and **CAUTION** (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Minimum Quantity and 8mm Width Taping Dimensions



Paper Tape

| Part Number | Dimensions | | Total Thickness of Tape | Packaging Code (Minimum Qty. [pcs.]) | | |
|------------------|------------|------|-------------------------|--------------------------------------|-------------|----------|
| | a | b | | ø180mm reel | ø330mm reel | Bulk |
| LQM21D (1-10µH) | 1.45 | 2.25 | 1.1 max. | D [4000] | J [10000] | B [1000] |
| LQM21F (1-2.2µH) | 1.45 | 2.25 | 1.1 max. | D [4000] | J [10000] | B [1000] |
| LQM21P_C0 | 1.45 | 2.25 | 0.8 max. | D [4000] | - | B [1000] |
| LQM21P_G | 1.45 | 2.25 | 1.1 max. | D [4000] | - | B [1000] |
| LQM18F | 1.05 | 1.85 | 1.1 max. | D [4000] | J [10000] | B [1000] |
| LQM18P_D0 | 1.05 | 1.85 | 0.85 max. | D [4000] | - | B [1000] |
| LQW18C | 1.0 | 1.8 | 1.1 max. | D [4000] | - | B [500] |

Embossed Tape


| Part Number | Dimensions | | Depth of Cavity | Packaging Code (Minimum Qty. [pcs.]) | | |
|-------------------|------------|------|-----------------|--------------------------------------|-------------|----------|
| | a | b | | ø180mm reel | ø330mm reel | Bulk |
| LQM18P_B0 | 1.0 | 1.8 | 0.50 | L [4000] | - | B [1000] |
| LQM18P_C0 | 1.0 | 1.8 | 0.60 | L [4000] | - | B [1000] |
| LQM18P_F0 | 1.0 | 1.8 | 1.0 | L [4000] | - | B [1000] |
| LQM21D (22-47µH) | 1.45 | 2.25 | 1.3 | L [3000] | K [10000] | B [1000] |
| LQM21F (4.7-47µH) | 1.45 | 2.25 | 1.3 | L [3000] | K [10000] | B [1000] |
| LQM2HP_J0/JC | 2.25 | 2.75 | 1.3 | L [3000] | - | B [1000] |
| LQM2HP_JH | 2.25 | 2.75 | 1.3 | L [3000] | - | - |
| LQM2HP_G | 2.3 | 2.8 | 1.1 | L [3000] | - | B [1000] |
| LQM2HP_GH | 2.3 | 2.8 | 1.1 | L [3000] | - | - |
| LQM2HP_E0 | 2.3 | 2.8 | 0.9 | L [3000] | - | B [1000] |
| LQM2MP_G0 | 1.85 | 2.25 | 1.1 | L [3000] | - | B [1000] |
| LQM2MP_GH | 1.9 | 2.4 | 1.1 | L [3000] | - | - |
| LQM31P_00 | 1.9 | 3.5 | 1.05 | L [3000] | - | B [1000] |
| LQM31P_C0 | 1.9 | 3.5 | 0.75 | L [4000] | - | B [1000] |
| LQM32P_G0 | 2.9 | 3.6 | 1.15 | L [3000] | - | B [1000] |
| LQH31C | 1.9 | 3.6 | 2.0 | L [2000] | K [7500] | - |
| LQH32C_33/23 | 2.9 | 3.6 | 2.1 | L [2000] | K [7500] | - |
| LQH32C_53 | 2.9 | 3.6 | 1.7 | L [2000] | K [7500] | - |
| LQH32P | 2.9 | 3.6 | 1.7 | L [2000] | K [7500] | - |
| LQH2MC_02 | 1.9 | 2.3 | 1.05 | L [3000] | - | B [100] |
| LQH2MC_52 | 1.9 | 2.3 | 0.8 | L [3000] | - | B [100] |

(in mm)

Continued on the following page. ↗

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


■ Minimum Quantity and 8mm Width Taping Dimensions



Dimension of the cavity of embossed tape is measured at the bottom side.

Embossed Tape

| Part Number | Dimensions | | Depth of Cavity | Packaging Code (Minimum Qty. [pcs.]) | | |
|--------------|------------|-----|-----------------|--------------------------------------|--------------------------|------|
| | a | b | | $\phi 180\text{mm}$ reel | $\phi 330\text{mm}$ reel | Bulk |
| LQH2HP_G0/GR | 2.3 | 2.8 | 1.1 | L [3000] | - | - |
| LQH2HP_J0 | 2.3 | 2.8 | 1.3 | L [2000] | - | - |
| LQH2HP_M0 | 2.3 | 2.8 | 1.6 | L [2000] | - | - |



Dimension of the cavity of embossed tape is measured at the bottom side.

Embossed Tape


| Part Number | Dimensions | | Depth of Cavity | Packaging Code (Minimum Qty. [pcs.]) | | |
|-------------|------------|-----|-----------------|--------------------------------------|--------------------------|------|
| | a | b | | $\phi 180\text{mm}$ reel | $\phi 330\text{mm}$ reel | Bulk |
| LQH3NP_MR | 3.3 | 3.3 | 1.6 | E [2000] | F [8000] | - |

(in mm)

Continued on the following page.

Note • Please read rating and **CAUTION** (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


■ Minimum Quantity and 12mm Width Embossed Taping Dimensions



Dimension of the cavity of embossed tape is measured at the bottom side.

Embossed Tape

| Part Number | Dimensions (*c: Depth of Cavity) | | | | Packaging Code (Minimum Qty. [pcs.]) | | |
|-------------|----------------------------------|-----|-----|------|--------------------------------------|-------------|------|
| | a | b | c | d | ø180mm reel | ø330mm reel | Bulk |
| LQH3NP_M0 | 3.3 | 3.3 | 1.6 | 0.25 | L [1000] | K [4000] | - |
| LQH3NP_J0 | 3.3 | 3.3 | 1.3 | 0.25 | L [1000] | K [5000] | - |
| LQH3NP_G0 | 3.3 | 3.3 | 1.1 | 0.25 | L [1500] | K [6000] | - |



Dimension of the cavity of embossed tape is measured at the bottom side.

Embossed Tape

| Part Number | Dimensions (*c: Depth of Cavity) | | | | Packaging Code (Minimum Qty. [pcs.]) | | |
|-------------|----------------------------------|-----|-----|-----|--------------------------------------|-------------|------|
| | a | b | c | d | ø180mm reel | ø330mm reel | Bulk |
| LQH43C | 3.6 | 4.9 | 2.7 | 0.3 | L [500] | - | - |
| LQH43P | 3.6 | 4.9 | 2.7 | 0.3 | L [500] | K [2500] | - |
| LQH44 P_J0 | 4.3 | 4.3 | 1.4 | 0.3 | L [1000] | K [3500] | - |
| LQH44P_P0 | 4.3 | 4.3 | 1.9 | 0.3 | L [1000] | K [3500] | - |
| LQH5BP | 5.3 | 5.3 | 2.4 | 0.3 | L [500] | K [3000] | - |
| LQH55D | 5.4 | 6.1 | 5.0 | 0.4 | L [350] | K [1500] | - |
| LQH66S | 6.7 | 6.7 | 5.6 | 0.4 | L [350] | K [1500] | - |

(in mm)

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Holder Type



● EKLMQM2PK-KIT (Inductors for Power Lines: Multilayer Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|-------------------|--------------------|
| | | | Nominal | Tolerance | | |
| 1 | LQM18PN1R5NB0 | 10 | 1.5μH | ±30% | 0.35±25% | 600 |
| 2 | LQM18PN1R8NC0 | 10 | 1.8μH | ±30% | 0.24±25% | 700 |
| 3 | LQM18PN2R5ND0 | 10 | 2.5μH | ±30% | 0.24±25% | 700 |
| 4 | LQM18PN1R0NF0 | 10 | 1.0μH | ±30% | 0.28±25% | 600 |
| 5 | LQM18PNR22NFR | 10 | 0.22μH | ±30% | 0.11±25% | 1250 |
| 6 | LQM18PNR47NFR | 10 | 0.47μH | ±30% | 0.15±25% | 1100 |
| 7 | LQM18PN1R0MFR | 10 | 1.0μH | ±20% | 0.20±25% | 950 |
| 8 | LQM18PN1R5MFR | 10 | 1.5μH | ±20% | 0.23±25% | 800 |
| 9 | LQM18PN2R2MFR | 10 | 2.2μH | ±20% | 0.30±25% | 750 |
| 10 | LQM18PN3R3MFR | 10 | 3.3μH | ±20% | 0.35±25% | 700 |
| 11 | LQM18PN4R7MFR | 10 | 4.7μH | ±20% | 0.44±25% | 620 |
| 12 | LQM21PNR47MC0 | 10 | 0.47μH | ±20% | 0.12±25% | 1100 |
| 13 | LQM21PN1R0MC0 | 10 | 1.0μH | ±20% | 0.19±25% | 800 |
| 14 | LQM21PN1R5MC0 | 10 | 1.5μH | ±20% | 0.26±25% | 700 |
| 15 | LQM21PN2R2MC0 | 10 | 2.2μH | ±20% | 0.34±25% | 600 |
| 16 | LQM21PNR47MG0 | 10 | 0.47μH | ±20% | 0.075±25% | 1300 |
| 17 | LQM21PNR54MG0 | 10 | 0.54μH | ±20% | 0.075±25% | 1300 |
| 18 | LQM21PN3R3MG0 | 10 | 3.3μH | ±20% | 0.165±25% | 800 |
| 19 | LQM21PN2R2MGS | 10 | 2.2μH | ±20% | 0.180±25% | 950 |
| 20 | LQM21PN4R7MGS | 10 | 4.7μH | ±20% | 0.290±25% | 750 |
| 21 | LQM21PN1R0NGC | 10 | 1.0μH | ±30% | 0.10±25% | 900 |
| 22 | LQM21PN2R2NGC | 10 | 2.2μH | ±30% | 0.23±25% | 800 |
| 23 | LQM21PN1R0NGR | 10 | 1.0μH | ±30% | 0.066±25% | 1300 |
| 24 | LQM21PN3R3MGR | 10 | 3.3μH | ±20% | 0.150±25% | 1000 |
| 25 | LQM21PN4R7MGR | 10 | 4.7μH | ±20% | 0.23±25% | 800 |
| 26 | LQM2MPNR47MG0 | 10 | 0.47μH | ±20% | 0.060±25% | 1600 |
| 27 | LQM2MPN1R0NG0 | 10 | 1.0μH | ±30% | 0.085±25% | 1400 |
| 28 | LQM2MPN1R5MG0 | 10 | 1.5μH | ±20% | 0.11±25% | 1200 |
| 29 | LQM2MPN2R2MG0 | 10 | 2.2μH | ±20% | 0.11±25% | 1200 |
| 30 | LQM2MPN3R3NG0 | 10 | 3.3μH | ±30% | 0.12±25% | 1200 |
| 31 | LQM2MPN4R7MG0 | 10 | 4.7μH | ±20% | 0.14±25% | 1100 |
| 32 | LQM2HPNR56ME0 | 10 | 0.56μH | ±20% | 0.06±25% | 1500 |
| 33 | LQM2HPNR47MG0 | 10 | 0.47μH | ±20% | 0.04±25% | 1800 |
| 34 | LQM2HPN1R0MG0 | 10 | 1.0μH | ±20% | 0.055±25% | 1600 |
| 35 | LQM2HPN1R5MG0 | 10 | 1.5μH | ±20% | 0.07±25% | 1500 |
| 36 | LQM2HPN2R2MG0 | 10 | 2.2μH | ±20% | 0.08±25% | 1300 |
| 37 | LQM2HPN3R3MG0 | 10 | 3.3μH | ±20% | 0.10±25% | 1200 |
| 38 | LQM2HPN4R7MG0 | 10 | 4.7μH | ±20% | 0.11±25% | 1100 |
| 39 | LQM2HPN1R0MGC | 10 | 1.0μH | ±20% | 0.08±25% | 1500 |
| 40 | LQM2HPN3R3MGC | 10 | 3.3μH | ±20% | 0.16±25% | 1000 |
| 41 | LQM2HPN4R7MGC | 10 | 4.7μH | ±20% | 0.18±25% | 800 |
| 42 | LQM2HPN2R2MGS | 10 | 2.2μH | ±20% | 0.18±25% | 1100 |
| 43 | LQM2HPN3R3MGS | 10 | 3.3μH | ±20% | 0.21±25% | 1050 |
| 44 | LQM2HPN4R7MGS | 10 | 4.7μH | ±20% | 0.25±25% | 1000 |
| 45 | LQM2HPN1R0MJ0 | 10 | 1.0μH | ±20% | 0.09±25% | 1500 |
| 46 | LQM2HPN2R2MJ0 | 10 | 2.2μH | ±20% | 0.12±25% | 1000 |
| 47 | LQM2HPN3R3MJ0 | 10 | 3.3μH | ±20% | 0.12±25% | 1000 |
| 48 | LQM2HPN1R0MJC | 10 | 1.0μH | ±20% | 0.086±25% | 1500 |
| 49 | LQM2HPN2R2NJC | 10 | 2.2μH | ±30% | 0.175±25% | 1000 |
| 50 | LQM31PNR47MC0 | 10 | 0.47μH | ±20% | 0.085±25% | 1300 |
| 51 | LQM31PN1R0MC0 | 10 | 1.0μH | ±20% | 0.14±25% | 1100 |
| 52 | LQM31PN1R5MC0 | 10 | 1.5μH | ±20% | 0.17±25% | 1000 |
| 53 | LQM31PN2R2MC0 | 10 | 2.2μH | ±20% | 0.25±25% | 900 |
| 54 | LQM31PNR47M00 | 10 | 0.47μH | ±20% | 0.07±25% | 1400 |
| 55 | LQM31PN1R0M00 | 10 | 1.0μH | ±20% | 0.12±25% | 1200 |

Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|-------------------|--------------------|
| | | | Nominal | Tolerance | | |
| 56 | LQM31PN1R5M00 | 10 | 1.5μH | ±20% | 0.14±25% | 1000 |
| 57 | LQM31PN2R2M00 | 10 | 2.2μH | ±20% | 0.19±25% | 900 |
| 58 | LQM31PN3R3M00 | 10 | 3.3μH | ±20% | 0.24±25% | 800 |
| 59 | LQM31PN4R7M00 | 10 | 4.7μH | ±20% | 0.30±25% | 700 |
| 60 | LQM32PN1R0MG0 | 10 | 1.0μH | ±20% | 0.048±25% | 1800 |

●EKLMM18FC-KIT (Inductors for Power Lines: Multilayer Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|-------------------|--------------------|
| | | | Nominal | Tolerance | | |
| 1 | LQM18FN1R0M00 | 10 | 1.0μH | ±20% | 0.20±30% | 150 |
| 2 | LQM18FN2R2M00 | 10 | 2.2μH | ±20% | 0.40±30% | 120 |
| 3 | LQM18FN4R7M00 | 10 | 4.7μH | ±20% | 0.60±30% | 80 |
| 4 | LQM18FN100M00 | 10 | 10μH | ±20% | 0.90±30% | 50 |
| 5 | LQM21FN1R0N00 | 10 | 1.0μH | ±30% | 0.20±30% | 220 |
| 6 | LQM21FN2R2N00 | 10 | 2.2μH | ±30% | 0.28±30% | 150 |
| 7 | LQM21FN220N00 | 10 | 22μH | ±30% | 0.35±30% | 13 |
| 8 | LQM21FN470N00 | 10 | 47μH | ±30% | 0.60±30% | 7 |
| 9 | LQM21FN4R7M70 | 10 | 4.7μH | ±20% | 0.35±30% | 120 |
| 10 | LQM21FN100M70 | 10 | 10μH | ±20% | 0.60±30% | 100 |
| 11 | LQM21FN4R7M80 | 10 | 4.7μH | ±20% | 0.18±30% | 120 |
| 12 | LQM21FN100M80 | 10 | 10μH | ±20% | 0.30±30% | 100 |

●EKLHM2MCK-KIT (Inductors for Power Lines: Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) | Rated Current (mA) | |
|-----|---------------|-----------------|------------|-----------|-------------------|----------------------------|---------------------------|
| | | | Nominal | Tolerance | | Based on Inductance Change | Based on Temperature Rise |
| 1 | LQH2MCN1R0M02 | 10 | 1.0μH | ±20% | 0.30±30% | - | 485 |
| 2 | LQH2MCN1R5M02 | 10 | 1.5μH | ±20% | 0.40±30% | - | 445 |
| 3 | LQH2MCN2R2M02 | 10 | 2.2μH | ±20% | 0.48±30% | - | 425 |
| 4 | LQH2MCN3R3M02 | 10 | 3.3μH | ±20% | 0.60±30% | - | 375 |
| 5 | LQH2MCN4R7M02 | 10 | 4.7μH | ±20% | 0.8±30% | - | 300 |
| 6 | LQH2MCN5R6M02 | 10 | 5.6μH | ±20% | 0.9±30% | - | 280 |
| 7 | LQH2MCN6R8M02 | 10 | 6.8μH | ±20% | 1.0±30% | - | 255 |
| 8 | LQH2MCN8R2M02 | 10 | 8.2μH | ±20% | 1.1±30% | - | 235 |
| 9 | LQH2MCN100K02 | 10 | 10μH | ±10% | 1.2±30% | - | 225 |
| 10 | LQH2MCN120K02 | 10 | 12μH | ±10% | 1.4±30% | - | 210 |
| 11 | LQH2MCN150K02 | 10 | 15μH | ±10% | 1.6±30% | - | 200 |
| 12 | LQH2MCN180K02 | 10 | 18μH | ±10% | 1.8±30% | - | 190 |
| 13 | LQH2MCN220K02 | 10 | 22μH | ±10% | 2.1±30% | - | 185 |
| 14 | LQH2MCN270K02 | 10 | 27μH | ±10% | 2.5±30% | - | 180 |
| 15 | LQH2MCN330K02 | 10 | 33μH | ±10% | 2.8±30% | - | 160 |
| 16 | LQH2MCN390K02 | 10 | 39μH | ±10% | 4.4±30% | - | 125 |
| 17 | LQH2MCN470K02 | 10 | 47μH | ±10% | 5.1±30% | - | 120 |
| 18 | LQH2MCN560K02 | 10 | 56μH | ±10% | 5.7±30% | - | 110 |
| 19 | LQH2MCN680K02 | 10 | 68μH | ±10% | 6.6±30% | - | 100 |
| 20 | LQH2MCN820K02 | 10 | 82μH | ±10% | 7.5±30% | - | 90 |
| 21 | LQH2MCN1R0M52 | 10 | 1.0μH | ±20% | 0.25±30% | - | 595 |
| 22 | LQH2MCN1R5M52 | 10 | 1.5μH | ±20% | 0.33±30% | - | 540 |
| 23 | LQH2MCN2R2M52 | 10 | 2.2μH | ±20% | 0.42±30% | - | 500 |
| 24 | LQH2MCN3R3M52 | 10 | 3.3μH | ±20% | 0.74±30% | - | 360 |
| 25 | LQH2MCN4R7M52 | 10 | 4.7μH | ±20% | 0.91±30% | - | 335 |
| 26 | LQH2MCN6R8M52 | 10 | 6.8μH | ±20% | 1.23±30% | - | 285 |
| 27 | LQH2MCN100M52 | 10 | 10μH | ±20% | 2.27±30% | - | 200 |
| 28 | LQH2MCN120M52 | 10 | 12μH | ±20% | 2.4±30% | - | 170 |
| 29 | LQH2MCN150M52 | 10 | 15μH | ±20% | 3.5±30% | - | 150 |
| 30 | LQH2MCN180M52 | 10 | 18μH | ±20% | 4±30% | - | 140 |
| 31 | LQH2MCN220M52 | 10 | 22μH | ±20% | 5.5±30% | - | 130 |
| 32 | LQH2HPN2R2MG0 | 10 | 2.2μH | ±20% | 0.17±20% | 1640 | 1000 |
| 33 | LQH2HPN3R3MG0 | 10 | 3.3μH | ±20% | 0.27±20% | 1290 | 810 |
| 34 | LQH2HPN4R7MG0 | 10 | 4.7μH | ±20% | 0.36±20% | 1000 | 700 |
| 35 | LQH2HPN6R8MG0 | 10 | 6.8μH | ±20% | 0.5±20% | 800 | 590 |
| 36 | LQH2HPN100MG0 | 10 | 10μH | ±20% | 0.73±20% | 700 | 490 |
| 37 | LQH2HPN220MG0 | 10 | 22μH | ±20% | 1.6±20% | 490 | 340 |
| 38 | LQH2HPN101MG0 | 10 | 100μH | ±20% | 10±20% | 210 | 130 |
| 39 | LQH2HPN1R0MGR | 10 | 1.0μH | ±20% | 0.068±20% | 2130 | 2100 |
| 40 | LQH2HPN2R2MGR | 10 | 2.2μH | ±20% | 0.134±20% | 1550 | 1470 |

Continued on the following page. ↗

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) | Rated Current (mA) | |
|-----|---------------|-----------------|------------|-----------|-------------------|----------------------------|---------------------------|
| | | | Nominal | Tolerance | | Based on Inductance Change | Based on Temperature Rise |
| 41 | LQH2HPN1R5NJ0 | 10 | 1.5μH | ±30% | 0.096±20% | 2400 | 1500 |
| 42 | LQH2HPN2R2MJ0 | 10 | 2.2μH | ±20% | 0.132±20% | 1800 | 1300 |
| 43 | LQH2HPN3R3MJ0 | 10 | 3.3μH | ±20% | 0.230±20% | 1500 | 950 |
| 44 | LQH2HPN4R7MJ0 | 10 | 4.7μH | ±20% | 0.330±20% | 1250 | 700 |
| 45 | LQH2HPN6R8MJ0 | 10 | 6.8μH | ±20% | 0.448±20% | 1100 | 600 |
| 46 | LQH2HPN100MJ0 | 10 | 10μH | ±20% | 0.641±20% | 820 | 550 |
| 47 | LQH2HPN2R2MM0 | 10 | 2.2μH | ±20% | 0.146±20% | 1700 | 1250 |
| 48 | LQH2HPN4R7NM0 | 10 | 4.7μH | ±30% | 0.342±20% | 1200 | 800 |

●EKLQMH3PE-KIT (Inductors for Power Lines: Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) | Rated Current (mA) | |
|-----|---------------|-----------------|------------|-----------|-------------------|----------------------------|---------------------------|
| | | | Nominal | Tolerance | | Based on Inductance Change | Based on Temperature Rise |
| 1 | LQH3NPN1R0NG0 | 10 | 1.0μH | ±30% | 0.08±20% | 1650 | 1525 |
| 2 | LQH3NPN1R5NG0 | 10 | 1.5μH | ±30% | 0.10±20% | 1300 | 1470 |
| 3 | LQH3NPN2R2NG0 | 10 | 2.2μH | ±30% | 0.14±20% | 1250 | 1270 |
| 4 | LQH3NPN3R3NG0 | 10 | 3.3μH | ±30% | 0.18±20% | 850 | 1130 |
| 5 | LQH3NPN4R7NG0 | 10 | 4.7μH | ±30% | 0.26±20% | 800 | 925 |
| 6 | LQH3NPN6R8NG0 | 10 | 6.8μH | ±30% | 0.45±20% | 650 | 710 |
| 7 | LQH3NPN100MG0 | 10 | 10μH | ±20% | 0.57±20% | 500 | 630 |
| 8 | LQH3NPN150NG0 | 10 | 15μH | ±30% | 0.91±20% | 370 | 475 |
| 9 | LQH3NPN220MG0 | 10 | 22μH | ±20% | 1.1±20% | 340 | 430 |
| 10 | LQH3NPN330MG0 | 10 | 33μH | ±20% | 2.1±20% | 250 | 345 |
| 11 | LQH3NPN470MG0 | 10 | 47μH | ±20% | 3.0±20% | 170 | 270 |
| 12 | LQH3NPN680MG0 | 10 | 68μH | ±20% | 4.2±20% | 150 | 235 |
| 13 | LQH3NPN101MG0 | 10 | 100μH | ±20% | 8.0±20% | 140 | 165 |
| 14 | LQH3NPN151MG0 | 10 | 150μH | ±20% | 11±20% | 110 | 145 |
| 15 | LQH3NPN221MG0 | 10 | 220μH | ±20% | 14±20% | 100 | 130 |
| 16 | LQH3NPN251MG0 | 10 | 250μH | ±20% | 15±20% | 80 | 130 |
| 17 | LQH3NPN1R0NJ0 | 10 | 1.0μH | ±30% | 0.040±20% | 1650 | 1620 |
| 18 | LQH3NPN1R5NJ0 | 10 | 1.5μH | ±30% | 0.055±20% | 1200 | 1500 |
| 19 | LQH3NPN2R2MJ0 | 10 | 2.2μH | ±20% | 0.069±20% | 1150 | 1460 |
| 20 | LQH3NPN3R3MJ0 | 10 | 3.3μH | ±20% | 0.105±20% | 950 | 1270 |
| 21 | LQH3NPN4R7MJ0 | 10 | 4.7μH | ±20% | 0.130±20% | 780 | 1120 |
| 22 | LQH3NPN6R8MJ0 | 10 | 6.8μH | ±20% | 0.210±20% | 700 | 850 |
| 23 | LQH3NPN100MJ0 | 10 | 10μH | ±20% | 0.300±20% | 560 | 710 |
| 24 | LQH3NPN150MJ0 | 10 | 15μH | ±20% | 0.440±20% | 440 | 590 |
| 25 | LQH3NPN220MJ0 | 10 | 22μH | ±20% | 0.600±20% | 350 | 510 |
| 26 | LQH3NPN330MJ0 | 10 | 33μH | ±20% | 0.900±20% | 280 | 410 |
| 27 | LQH3NPN470MJ0 | 10 | 47μH | ±20% | 1.30±20% | 200 | 350 |
| 28 | LQH3NPN1R0MM0 | 10 | 1.0μH | ±20% | 0.044±20% | 1400 | 2050 |
| 29 | LQH3NPN2R2MM0 | 10 | 2.2μH | ±20% | 0.073±20% | 1250 | 1600 |
| 30 | LQH3NPN3R3MM0 | 10 | 3.3μH | ±20% | 0.092±20% | 1000 | 1450 |
| 31 | LQH3NPN4R7MM0 | 10 | 4.7μH | ±20% | 0.13±20% | 880 | 1250 |
| 32 | LQH3NPN6R8MM0 | 10 | 6.8μH | ±20% | 0.20±20% | 820 | 1000 |
| 33 | LQH3NPN100MM0 | 10 | 10μH | ±20% | 0.26±20% | 550 | 870 |
| 34 | LQH3NPN150MM0 | 10 | 15μH | ±20% | 0.36±20% | 520 | 730 |
| 35 | LQH3NPN220MM0 | 10 | 22μH | ±20% | 0.51±20% | 410 | 650 |
| 36 | LQH3NPN330MM0 | 10 | 33μH | ±20% | 0.85±20% | 370 | 500 |
| 37 | LQH3NPN470MM0 | 10 | 47μH | ±20% | 1.25±20% | 310 | 410 |
| 38 | LQH3NPN101MM0 | 10 | 100μH | ±20% | 3.50±20% | 200 | 240 |
| 39 | LQH3NPN1R0MMR | 10 | 1.0μH | ±20% | 0.042±20% | 1600 | 2150 |
| 40 | LQH3NPN2R2MMR | 10 | 2.2μH | ±20% | 0.068±20% | 1380 | 1750 |
| 41 | LQH3NPN3R3MMR | 10 | 3.3μH | ±20% | 0.088±20% | 1200 | 1550 |
| 42 | LQH3NPN4R7MMR | 10 | 4.7μH | ±20% | 0.105±20% | 950 | 1400 |
| 43 | LQH3NPN6R8MMR | 10 | 6.8μH | ±20% | 0.155±20% | 830 | 1250 |
| 44 | LQH3NPN100MMR | 10 | 10μH | ±20% | 0.210±20% | 590 | 1150 |
| 45 | LQH3NPN220MMR | 10 | 22μH | ±20% | 0.480±20% | 430 | 750 |
| 46 | LQH3NPN330MMR | 10 | 33μH | ±20% | 0.790±20% | 380 | 600 |
| 47 | LQH3NPN470MMR | 10 | 47μH | ±20% | 1.140±20% | 320 | 460 |
| 48 | LQH32PNR47NN0 | 10 | 0.47μH | ±30% | 0.030±20% | 3400 | 2550 |
| 49 | LQH32PN1R0NN0 | 10 | 1.0μH | ±30% | 0.045±20% | 2300 | 2050 |
| 50 | LQH32PN1R5NN0 | 10 | 1.5μH | ±30% | 0.057±20% | 1750 | 1750 |
| 51 | LQH32PN2R2NN0 | 10 | 2.2μH | ±30% | 0.076±20% | 1550 | 1600 |
| 52 | LQH32PN3R3NN0 | 10 | 3.3μH | ±30% | 0.12±20% | 1250 | 1200 |
| 53 | LQH32PN4R7NN0 | 10 | 4.7μH | ±30% | 0.18±20% | 1000 | 1000 |

Continued on the following page. ↗

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) | Rated Current (mA) | |
|-----|---------------|-----------------|------------|-----------|-------------------|----------------------------|---------------------------|
| | | | Nominal | Tolerance | | Based on Inductance Change | Based on Temperature Rise |
| 54 | LQH32PN6R8NN0 | 10 | 6.8μH | ±30% | 0.24±20% | 850 | 850 |
| 55 | LQH32PN100MN0 | 10 | 10μH | ±20% | 0.38±20% | 750 | 700 |
| 56 | LQH32PN150MN0 | 10 | 15μH | ±20% | 0.57±20% | 600 | 520 |
| 57 | LQH32PN220MN0 | 10 | 22μH | ±20% | 0.81±20% | 500 | 450 |
| 58 | LQH32PN330MN0 | 10 | 33μH | ±20% | 1.15±20% | 380 | 390 |
| 59 | LQH32PN470MN0 | 10 | 47μH | ±20% | 1.78±20% | 330 | 310 |
| 60 | LQH32PN680MN0 | 10 | 68μH | ±20% | 2.28±20% | 280 | 275 |
| 61 | LQH32PN101MN0 | 10 | 100μH | ±20% | 2.70±20% | 180 | 250 |
| 62 | LQH32PN121MN0 | 10 | 120μH | ±20% | 4.38±20% | 170 | 200 |
| 63 | LQH32PNR47NNC | 10 | 0.47μH | ±30% | 0.024±20% | 4400 | 2900 |
| 64 | LQH32PN1R0NNC | 10 | 1.0μH | ±30% | 0.036±20% | 3000 | 2500 |
| 65 | LQH32PN1R5NNC | 10 | 1.5μH | ±30% | 0.053±20% | 2600 | 2100 |
| 66 | LQH32PN2R2NNC | 10 | 2.2μH | ±30% | 0.064±20% | 2000 | 1850 |
| 67 | LQH32PN3R3NNC | 10 | 3.3μH | ±30% | 0.100±20% | 1900 | 1550 |
| 68 | LQH32PN4R7NNC | 10 | 4.7μH | ±30% | 0.155±20% | 1600 | 1200 |
| 69 | LQH32PN6R8NNC | 10 | 6.8μH | ±30% | 0.220±20% | 1300 | 1100 |
| 70 | LQH32PN100MNC | 10 | 10μH | ±20% | 0.295±20% | 1000 | 900 |
| 71 | LQH32PN150MNC | 10 | 15μH | ±20% | 0.475±20% | 800 | 700 |
| 72 | LQH32PN220MNC | 10 | 22μH | ±20% | 0.685±20% | 650 | 550 |

●EKLMQH3BA-KIT (Inductors for Power Lines: Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) | Rated Current (mA) | | |
|-----|---------------|-----------------|------------|-----------|-------------------|----------------------------|---------------------------|------|
| | | | Nominal | Tolerance | | Based on Inductance Change | Based on Temperature Rise | |
| | | | | | | Ambient temperature 85°C | Ambient temperature 105°C | |
| 1 | LQH32PBR47NN0 | 10 | 0.47μH | ±30% | 0.030±20% | 3400 | 2550 | 1600 |
| 2 | LQH32PB1R0NN0 | 10 | 1.0μH | ±30% | 0.045±20% | 2300 | 2050 | 1320 |
| 3 | LQH32PB1R5NN0 | 10 | 1.5μH | ±30% | 0.057±20% | 1750 | 1750 | 1010 |
| 4 | LQH32PB2R2NN0 | 10 | 2.2μH | ±30% | 0.076±20% | 1550 | 1600 | 970 |
| 5 | LQH32PB3R3NN0 | 10 | 3.3μH | ±30% | 0.12±20% | 1250 | 1200 | 670 |
| 6 | LQH32PB4R7NN0 | 10 | 4.7μH | ±30% | 0.18±20% | 1000 | 1000 | 530 |
| 7 | LQH32PB6R8NN0 | 10 | 6.8μH | ±30% | 0.24±20% | 850 | 850 | 510 |
| 8 | LQH32PB100MN0 | 10 | 10μH | ±20% | 0.38±20% | 750 | 700 | 380 |
| 9 | LQH32PB150MN0 | 10 | 15μH | ±20% | 0.57±20% | 600 | 520 | 320 |
| 10 | LQH32PB220MN0 | 10 | 22μH | ±20% | 0.81±20% | 500 | 450 | 240 |
| 11 | LQH32PB330MN0 | 10 | 33μH | ±20% | 1.15±20% | 380 | 390 | 190 |
| 12 | LQH32PB470MN0 | 10 | 47μH | ±20% | 1.78±20% | 330 | 310 | 140 |
| 13 | LQH32PB680MN0 | 10 | 68μH | ±20% | 2.28±20% | 280 | 275 | 120 |
| 14 | LQH32PB101MN0 | 10 | 100μH | ±20% | 2.70±20% | 180 | 250 | 110 |
| 15 | LQH32PB121MN0 | 10 | 120μH | ±20% | 4.38±20% | 170 | 200 | 80 |
| 16 | LQH32PBR47NNC | 10 | 0.47μH | ±30% | 0.024±20% | 4400 | 2900 | 1490 |
| 17 | LQH32PB1R0NNC | 10 | 1.0μH | ±30% | 0.036±20% | 3000 | 2500 | 1380 |
| 18 | LQH32PB1R5NNC | 10 | 1.5μH | ±30% | 0.053±20% | 2600 | 2100 | 1110 |
| 19 | LQH32PB2R2NNC | 10 | 2.2μH | ±30% | 0.064±20% | 2000 | 1850 | 910 |
| 20 | LQH32PB3R3NNC | 10 | 3.3μH | ±30% | 0.100±20% | 1900 | 1550 | 800 |
| 21 | LQH32PB4R7NNC | 10 | 4.7μH | ±30% | 0.155±20% | 1600 | 1200 | 610 |
| 22 | LQH32PB6R8NNC | 10 | 6.8μH | ±30% | 0.220±20% | 1300 | 1100 | 550 |
| 23 | LQH32PB100MNC | 10 | 10μH | ±20% | 0.295±20% | 1000 | 900 | 450 |
| 24 | LQH32PB150MNC | 10 | 15μH | ±20% | 0.475±20% | 800 | 700 | 330 |
| 25 | LQH32PB220MNC | 10 | 22μH | ±20% | 0.685±20% | 650 | 550 | 270 |

●EKLMQH4PD-KIT (Inductors for Power Lines: Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) | Rated Current (mA) | |
|-----|---------------|-----------------|------------|-----------|-------------------|----------------------------|---------------------------|
| | | | Nominal | Tolerance | | Based on Inductance Change | Based on Temperature Rise |
| 1 | LQH44PN1R0NJ0 | 10 | 1.0μH | ±30% | 0.048±20% | 2000 | 1530 |
| 2 | LQH44PN1R5MJ0 | 10 | 1.5μH | ±20% | 0.061±20% | 1600 | 1380 |
| 3 | LQH44PN2R2MJ0 | 10 | 2.2μH | ±20% | 0.074±20% | 1320 | 1230 |
| 4 | LQH44PN3R3MJ0 | 10 | 3.3μH | ±20% | 0.088±20% | 900 | 1000 |
| 5 | LQH44PN4R7MJ0 | 10 | 4.7μH | ±20% | 0.117±20% | 840 | 980 |
| 6 | LQH44PN6R8MJ0 | 10 | 6.8μH | ±20% | 0.143±20% | 720 | 860 |
| 7 | LQH44PN100MJ0 | 10 | 10μH | ±20% | 0.207±20% | 560 | 790 |
| 8 | LQH44PN150MJ0 | 10 | 15μH | ±20% | 0.385±20% | 430 | 610 |
| 9 | LQH44PN220MJ0 | 10 | 22μH | ±20% | 0.480±20% | 400 | 550 |
| 10 | LQH44PN330MJ0 | 10 | 33μH | ±20% | 0.740±20% | 360 | 430 |
| 11 | LQH44PN470MJ0 | 10 | 47μH | ±20% | 1.014±20% | 300 | 380 |
| 12 | LQH44PN1R0NP0 | 10 | 1.0μH | ±30% | 0.030±20% | 2950 | 2450 |

Continued on the following page. ↗

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) | Rated Current (mA) | |
|-----|---------------|-----------------|------------|-----------|-------------------|----------------------------|---------------------------|
| | | | Nominal | Tolerance | | Based on Inductance Change | Based on Temperature Rise |
| 13 | LQH44PN2R2MP0 | 10 | 2.2μH | ±20% | 0.049±20% | 2500 | 1800 |
| 14 | LQH44PN3R3MP0 | 10 | 3.3μH | ±20% | 0.065±20% | 2100 | 1770 |
| 15 | LQH44PN4R7MP0 | 10 | 4.7μH | ±20% | 0.080±20% | 1700 | 1700 |
| 16 | LQH44PN6R8MP0 | 10 | 6.8μH | ±20% | 0.12±20% | 1400 | 1340 |
| 17 | LQH44PN100MP0 | 10 | 10μH | ±20% | 0.16±20% | 1150 | 1170 |
| 18 | LQH44PN220MP0 | 10 | 22μH | ±20% | 0.37±20% | 800 | 790 |
| 19 | LQH43PN1R0N26 | 10 | 1.0μH | ±30% | 0.026±20% | 3400 | 3300 |
| 20 | LQH43PN2R2M26 | 10 | 2.2μH | ±20% | 0.042±20% | 2300 | 2500 |
| 21 | LQH43PN3R3M26 | 10 | 3.3μH | ±20% | 0.052±20% | 1800 | 2100 |
| 22 | LQH43PN4R7M26 | 10 | 4.7μH | ±20% | 0.075±20% | 1400 | 1600 |
| 23 | LQH43PN6R8M26 | 10 | 6.8μH | ±20% | 0.098±20% | 1200 | 1400 |
| 24 | LQH43PN8R2M26 | 10 | 8.2μH | ±20% | 0.128±20% | 1100 | 1300 |
| 25 | LQH43PN100M26 | 10 | 10μH | ±20% | 0.147±20% | 1050 | 1170 |
| 26 | LQH43PN220M26 | 10 | 22μH | ±20% | 0.327±20% | 700 | 780 |
| 27 | LQH43PN470M26 | 10 | 47μH | ±20% | 0.718±20% | 470 | 520 |
| 28 | LQH43PN101M26 | 10 | 100μH | ±20% | 1.538±20% | 320 | 320 |
| 29 | LQH43PN151M26 | 10 | 150μH | ±20% | 2.362±20% | 280 | 260 |
| 30 | LQH43PN221M26 | 10 | 220μH | ±20% | 2.900±20% | 220 | 240 |

●EKLMQH5PC-KIT (Inductors for Power Lines: Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) | Rated Current (mA) | |
|-----|---------------|-----------------|------------|-----------|-------------------|----------------------------|---------------------------|
| | | | Nominal | Tolerance | | Based on Inductance Change | Based on Temperature Rise |
| 1 | LQH5BPNR47NT0 | 10 | 0.47μH | ±30% | 0.012±20% | 7700 | 4000 |
| 2 | LQH5BPN1R0NT0 | 10 | 1.0μH | ±30% | 0.019±20% | 5800 | 3100 |
| 3 | LQH5BPN1R2NT0 | 10 | 1.2μH | ±30% | 0.019±20% | 5400 | 3100 |
| 4 | LQH5BPN1R5NT0 | 10 | 1.5μH | ±30% | 0.024±20% | 5000 | 3000 |
| 5 | LQH5BPN2R2NT0 | 10 | 2.2μH | ±30% | 0.030±20% | 4000 | 2600 |
| 6 | LQH5BPN2R7NT0 | 10 | 2.7μH | ±30% | 0.035±20% | 3800 | 2500 |
| 7 | LQH5BPN3R3NT0 | 10 | 3.3μH | ±30% | 0.044±20% | 3500 | 2300 |
| 8 | LQH5BPN4R7NT0 | 10 | 4.7μH | ±30% | 0.058±20% | 3000 | 2000 |
| 9 | LQH5BPN6R8NT0 | 10 | 6.8μH | ±30% | 0.083±20% | 2500 | 1650 |
| 10 | LQH5BPN100MT0 | 10 | 10μH | ±20% | 0.106±20% | 2000 | 1600 |
| 11 | LQH5BPN150MT0 | 10 | 15μH | ±20% | 0.187±20% | 1600 | 1200 |
| 12 | LQH5BPN220MT0 | 10 | 22μH | ±20% | 0.259±20% | 1400 | 1050 |

●EKL32CC-KIT (Inductors for Power Lines: Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|-------------------|--------------------|
| | | | Nominal | Tolerance | | |
| 1 | LQH32CNR15M33 | 10 | 0.15μH | ±20% | 0.028±30% | 1450 |
| 2 | LQH32CNR27M33 | 10 | 0.27μH | ±20% | 0.034±30% | 1250 |
| 3 | LQH32CNR47M33 | 10 | 0.47μH | ±20% | 0.042±30% | 1100 |
| 4 | LQH32CN1R0M33 | 10 | 1.0μH | ±20% | 0.06±30% | 1000 |
| 5 | LQH32CN2R2M33 | 10 | 2.2μH | ±20% | 0.097±30% | 790 |
| 6 | LQH32CN4R7M33 | 10 | 4.7μH | ±20% | 0.15±30% | 650 |
| 7 | LQH32CN100K33 | 10 | 10μH | ±10% | 0.3±30% | 450 |
| 8 | LQH32CN1R0M23 | 10 | 1.0μH | ±20% | 0.09±30% | 800 |
| 9 | LQH32CN2R2M23 | 10 | 2.2μH | ±20% | 0.13±30% | 600 |
| 10 | LQH32CN4R7M23 | 10 | 4.7μH | ±20% | 0.2±30% | 450 |
| 11 | LQH32CN100K23 | 10 | 10μH | ±10% | 0.44±30% | 300 |
| 12 | LQH32CN220K23 | 10 | 22μH | ±10% | 0.71±30% | 250 |
| 13 | LQH32CN470K23 | 10 | 47μH | ±10% | 1.3±30% | 170 |
| 14 | LQH32CN101K23 | 10 | 100μH | ±10% | 3.5±30% | 100 |
| 15 | LQH32CN221K23 | 10 | 220μH | ±10% | 8.4±30% | 70 |
| 16 | LQH32CN331K23 | 10 | 330μH | ±10% | 10±30% | 60 |
| 17 | LQH32CN391K23 | 10 | 390μH | ±10% | 17±30% | 60 |
| 18 | LQH32CN471K23 | 10 | 470μH | ±10% | 19±30% | 60 |
| 19 | LQH32CN561K23 | 10 | 560μH | ±10% | 22±30% | 60 |
| 20 | LQH32CN1R0M53 | 10 | 1.0μH | ±20% | 0.06±30% | 1000 |
| 21 | LQH32CN2R2M53 | 10 | 2.2μH | ±20% | 0.097±30% | 790 |
| 22 | LQH32CN4R7M53 | 10 | 4.7μH | ±20% | 0.15±30% | 650 |
| 23 | LQH32CN100K53 | 10 | 10μH | ±10% | 0.3±30% | 450 |
| 24 | LQH32CN150K53 | 10 | 15μH | ±10% | 0.58±30% | 300 |
| 25 | LQH32CN220K53 | 10 | 22μH | ±10% | 0.71±30% | 250 |
| 26 | LQH32CN330K53 | 10 | 33μH | ±10% | 1.1±30% | 200 |
| 27 | LQH32CN470K53 | 10 | 47μH | ±10% | 1.3±30% | 170 |

Continued on the following page. ↗

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|-------------------|--------------------|
| | | | Nominal | Tolerance | | |
| 28 | LQH32CN680K53 | 10 | 68μH | ±10% | 2.2±30% | 130 |
| 29 | LQH32CN101K53 | 10 | 100μH | ±10% | 3.5±30% | 100 |

●EKL43CD-KIT (Inductors for Power Lines: Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | |
| 1 | LQH43CN1R0M03 | 10 | 1.0μH | ±20% | 0.08 | 1080 |
| 2 | LQH43CN1R5M03 | 10 | 1.5μH | ±20% | 0.09 | 1000 |
| 3 | LQH43CN2R2M03 | 10 | 2.2μH | ±20% | 0.11 | 900 |
| 4 | LQH43CN3R3M03 | 10 | 3.3μH | ±20% | 0.13 | 800 |
| 5 | LQH43CN4R7M03 | 10 | 4.7μH | ±20% | 0.15 | 750 |
| 6 | LQH43CN6R8M03 | 10 | 6.8μH | ±20% | 0.20 | 720 |
| 7 | LQH43CN100K03 | 10 | 10μH | ±10% | 0.24 | 650 |
| 8 | LQH43CN150K03 | 10 | 15μH | ±10% | 0.32 | 570 |
| 9 | LQH43CN220K03 | 10 | 22μH | ±10% | 0.60 | 420 |
| 10 | LQH43CN330K03 | 10 | 33μH | ±10% | 1.00 | 310 |
| 11 | LQH43CN470K03 | 10 | 47μH | ±10% | 1.10 | 280 |
| 12 | LQH43CN680K03 | 10 | 68μH | ±10% | 1.70 | 220 |
| 13 | LQH43CN101K03 | 10 | 100μH | ±10% | 2.20 | 190 |
| 14 | LQH43CN151K03 | 10 | 150μH | ±10% | 3.50 | 130 |
| 15 | LQH43CN221K03 | 10 | 220μH | ±10% | 4.00 | 110 |
| 16 | LQH43CN331K03 | 10 | 330μH | ±10% | 6.80 | 100 |
| 17 | LQH43CN471K03 | 10 | 470μH | ±10% | 8.50 | 90 |
| 18 | LQH43CNR56M33 | 10 | 0.56μH | ±20% | 0.030 | 2950 |
| 19 | LQH43CNR82M33 | 10 | 0.82μH | ±20% | 0.036 | 2800 |
| 20 | LQH43CN1R0M33 | 10 | 1.0μH | ±20% | 0.042 | 2600 |
| 21 | LQH43CN1R5M33 | 10 | 1.5μH | ±20% | 0.047 | 2450 |
| 22 | LQH43CN1R8M33 | 10 | 1.8μH | ±20% | 0.055 | 2300 |
| 23 | LQH43CN2R2M33 | 10 | 2.2μH | ±20% | 0.062 | 2100 |
| 24 | LQH43CN2R7M33 | 10 | 2.7μH | ±20% | 0.069 | 1800 |
| 25 | LQH43CN3R3M33 | 10 | 3.3μH | ±20% | 0.099 | 1650 |
| 26 | LQH43CN3R9M33 | 10 | 3.9μH | ±20% | 0.107 | 1600 |

●EKL18CC-KIT (Inductors for Power Lines: Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | |
| 1 | LQW15CN18NJ00 | 10 | 18nH | ±5% | 0.046 | 1400 |
| 2 | LQW15CN33NJ00 | 10 | 33nH | ±5% | 0.065 | 1300 |
| 3 | LQW15CN48NJ00 | 10 | 48nH | ±5% | 0.078 | 1100 |
| 4 | LQW15CN70NJ00 | 10 | 70nH | ±5% | 0.12 | 820 |
| 5 | LQW15CN96NJ00 | 10 | 96nH | ±5% | 0.16 | 730 |
| 6 | LQW15CNR13J00 | 10 | 130nH | ±5% | 0.23 | 640 |
| 7 | LQW15CNR16J00 | 10 | 160nH | ±5% | 0.33 | 480 |
| 8 | LQW15CNR20J00 | 10 | 200nH | ±5% | 0.47 | 390 |
| 9 | LQW15CNR39K10 | 10 | 390nH | ±10% | 0.62 | 370 |
| 10 | LQW15CNR56K10 | 10 | 560nH | ±10% | 0.71 | 300 |
| 11 | LQW18CN4N9D00 | 10 | 4.9nH | ±0.5nH | 0.015 | 2600 |
| 12 | LQW18CN15NJ00 | 10 | 15nH | ±5% | 0.025 | 2200 |
| 13 | LQW18CN33NJ00 | 10 | 33nH | ±5% | 0.035 | 1700 |
| 14 | LQW18CN55NJ00 | 10 | 55nH | ±5% | 0.045 | 1500 |
| 15 | LQW18CN85NJ00 | 10 | 85nH | ±5% | 0.060 | 1400 |
| 16 | LQW18CNR10K00 | 10 | 100nH | ±10% | 0.10 | 1000 |
| 17 | LQW18CNR12J00 | 10 | 120nH | ±5% | 0.085 | 1100 |
| 18 | LQW18CNR16J00 | 10 | 160nH | ±5% | 0.10 | 1000 |
| 19 | LQW18CNR21J00 | 10 | 210nH | ±5% | 0.15 | 800 |
| 20 | LQW18CNR27J00 | 10 | 270nH | ±5% | 0.16 | 750 |
| 21 | LQW18CNR33J00 | 10 | 330nH | ±5% | 0.25 | 630 |
| 22 | LQW18CNR39J00 | 10 | 390nH | ±5% | 0.28 | 620 |
| 23 | LQW18CNR47J00 | 10 | 470nH | ±5% | 0.45 | 500 |
| 24 | LQW18CNR56J00 | 10 | 560nH | ±5% | 0.48 | 450 |
| 25 | LQW18CNR65J00 | 10 | 650nH | ±5% | 0.52 | 430 |

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

● Inductors for General Use

| | |
|------------------------------|-----|
| Part Numbering | 118 |
| Product Detail | 119 |
| ⚠Caution/Notice | 136 |
| Soldering and Mounting | 137 |
| Packaging | 141 |
| Design Kits | 142 |

Inductors for General Use Part Numbering

(Part Number) **LQ M 18 N N 47N M 0 0 D**
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩

① Product ID

| Product ID | |
|------------|-----------------------------|
| LQ | Chip Inductors (Chip Coils) |

② Structure

| Code | Structure |
|------|--------------------------------|
| B | Multilayer Type (Ferrite Core) |
| H | Wire Wound Type (Ferrite Core) |
| M | Multilayer Type (Ferrite Core) |

③ Dimensions (L×W)

| Code | Dimensions (L×W) | Size Code (in inch) |
|------|------------------|---------------------|
| 15 | 1.0×0.5mm | 0402 |
| 18 | 1.6×0.8mm | 0603 |
| 21 | 2.0×1.25mm | 0805 |
| 31 | 3.2×1.6mm | 1206 |
| 32 | 3.2×2.5mm | 1210 |
| 43 | 4.5×3.2mm | 1812 |
| 44 | 4.0×4.0mm | 1515 |

④ Applications and Characteristics

| Code | Series | Applications and Characteristics |
|------|---------|-------------------------------------|
| N | LQB/LQM | for Resonant Circuit |
| N | LQH | for Resonant Circuit |
| M | | for Resonant Circuit (Coating Type) |

⑤ Category

| Code | Category |
|------|---------------|
| N | Standard Type |

⑩ Packaging

| Code | Packaging | Series |
|------|-------------------------------|-------------------|
| K | Embossed Taping (ø330mm Reel) | LQH/LQM21*1 |
| L | Embossed Taping (ø180mm Reel) | LQH/LQM21*1 |
| B | Bulk | LQB/LQM |
| J | Paper Taping (ø330mm Reel) | LQB/LQM18/LQM21*2 |
| D | Paper Taping (ø180mm Reel) | LQB/LQM18/LQM21*2 |

*1 LQM21N(2.7 - 4.7μH) only.

*2 LQM21N(0.1 - 2.2μH) only.

⑥ Inductance

Expressed by three-digit alphanumeric. The unit is micro-henry (μH). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two figures. If there is a decimal point, it is expressed by the capital letter "R". In this case, all figures are significant digits. If inductance is less than 0.1μH, the inductance code is expressed by a combination of two figures and the capital letter "N", and the unit of inductance is nano-henry (nH). The capital letter "N" indicates the unit of "nH", and also expresses a decimal point. In this case, all figures are significant digits.

⑦ Inductance Tolerance

| Code | Inductance Tolerance |
|------|----------------------|
| J | ±5% |
| K | ±10% |
| M | ±20% |
| N | ±30% |

⑧ Features

| Code | Features | Series |
|------|---------------|--------------|
| 0 | Standard Type | LQM*1 /LQH*2 |
| 1 | Standard Type | LQB/LQM21N |
| 2 | Standard Type | LQH32M |

*1 Except for LQM21N Series

*2 Except for LQH32 Series

⑨ Electrode

•Lead (Pb) Free


| Code | Electrode | Series |
|------|-----------|---------|
| 0 | Sn | LQB/LQM |
| 3 | LF Solder | LQH |

LQB15NN_10

Series 0402/1005 (inch/mm)

For Near Field Communication, Matching, Choke

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 10000 |
| J | ø330mm Paper Taping | 50000 |
| B | Packing in Bulk | 1000 |



Refer to pages 137 to 140 for mounting information.

Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current ^{*1} | DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|-----------------------------|---------------|----------|------------------|---------------------------------|-----|
| LQB15NNR22J10□ | 220nH ±5% | 25MHz | 380mA | 0.35Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR22K10□ | 220nH ±10% | 25MHz | 380mA | 0.35Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR22M10□ | 220nH ±20% | 25MHz | 380mA | 0.35Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR27J10□ | 270nH ±5% | 25MHz | 330mA | 0.41Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR27K10□ | 270nH ±10% | 25MHz | 330mA | 0.41Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR27M10□ | 270nH ±20% | 25MHz | 330mA | 0.41Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR33J10□ | 330nH ±5% | 25MHz | 300mA | 0.48Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR33K10□ | 330nH ±10% | 25MHz | 300mA | 0.48Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR33M10□ | 330nH ±20% | 25MHz | 300mA | 0.48Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR39J10□ | 390nH ±5% | 25MHz | 300mA | 0.54Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR39K10□ | 390nH ±10% | 25MHz | 300mA | 0.54Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR39M10□ | 390nH ±20% | 25MHz | 300mA | 0.54Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR47J10□ | 470nH ±5% | 25MHz | 300mA | 0.64Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR47K10□ | 470nH ±10% | 25MHz | 300mA | 0.64Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR47M10□ | 470nH ±20% | 25MHz | 300mA | 0.64Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR56J10□ | 560nH ±5% | 25MHz | 300mA | 0.73Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR56K10□ | 560nH ±10% | 25MHz | 300mA | 0.73Ω ±25% | 10 | 25MHz | 80MHz | New |
| LQB15NNR56M10□ | 560nH ±20% | 25MHz | 300mA | 0.73Ω ±25% | 10 | 25MHz | 80MHz | New |

Class of Magnetic Shield: Magnetic shield of ferrite


Operating Temperature Range: -55°C~+125°C

For reflow soldering only.


*1 When rated current is applied to the products, self-generation of heat will rise to 25°C or less.

Continued on the following page.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQB18NN_10 Series 0603/1608 (inch/mm)

For Near Field Communication, Matching, Choke

Appearance/Dimensions



(in mm)

Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| B | Packing in Bulk | 1000 |



Refer to pages 137 to 140 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQB18NNR22J10□ | 220nH ±5% | 25MHz | 450mA | 0.37Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR22K10□ | 220nH ±10% | 25MHz | 450mA | 0.37Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR22M10□ | 220nH ±20% | 25MHz | 450mA | 0.37Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR22N10□ | 220nH ±30% | 25MHz | 450mA | 0.37Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR27J10□ | 270nH ±5% | 25MHz | 450mA | 0.45Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR27K10□ | 270nH ±10% | 25MHz | 450mA | 0.45Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR27M10□ | 270nH ±20% | 25MHz | 450mA | 0.45Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR27N10□ | 270nH ±30% | 25MHz | 450mA | 0.45Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR33J10□ | 330nH ±5% | 25MHz | 450mA | 0.45Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR33K10□ | 330nH ±10% | 25MHz | 450mA | 0.45Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR33M10□ | 330nH ±20% | 25MHz | 450mA | 0.45Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR33N10□ | 330nH ±30% | 25MHz | 450mA | 0.45Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR39J10□ | 390nH ±5% | 25MHz | 450mA | 0.58Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR39K10□ | 390nH ±10% | 25MHz | 450mA | 0.58Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR39M10□ | 390nH ±20% | 25MHz | 450mA | 0.58Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR39N10□ | 390nH ±30% | 25MHz | 450mA | 0.58Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR47J10□ | 470nH ±5% | 25MHz | 400mA | 0.58Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR47K10□ | 470nH ±10% | 25MHz | 400mA | 0.58Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR47M10□ | 470nH ±20% | 25MHz | 400mA | 0.58Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR47N10□ | 470nH ±30% | 25MHz | 400mA | 0.58Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR56J10□ | 560nH ±5% | 25MHz | 300mA | 0.85Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR56K10□ | 560nH ±10% | 25MHz | 300mA | 0.85Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR56M10□ | 560nH ±20% | 25MHz | 300mA | 0.85Ω | 25 | 25MHz | 80MHz | New |
| LQB18NNR56N10□ | 560nH ±30% | 25MHz | 300mA | 0.85Ω | 25 | 25MHz | 80MHz | New |

Class of Magnetic Shield: Magnetic shield of ferrite
 Operating Temperature Range: -55°C~+125°C


Continued on the following page.

Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM18NN_00 Series 0603/1608 (inch/mm)

Size Code 0603 (1608) in inch (in mm)

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| J | ø330mm Paper Taping | 10000 |
| B | Packing in Bulk | 1000 |



Refer to pages 137 to 140 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|-------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQM18NN47NM00□ | 47nH ±20% | 50MHz | 50mA | 0.30Ω | 10 | 50MHz | 260MHz | Kit |
| LQM18NN68NM00□ | 68nH ±20% | 50MHz | 50mA | 0.30Ω | 10 | 50MHz | 250MHz | Kit |
| LQM18NN82NM00□ | 82nH ±20% | 50MHz | 50mA | 0.30Ω | 10 | 50MHz | 245MHz | Kit |
| LQM18NNR10K00□ | 100nH ±10% | 25MHz | 50mA | 0.50Ω | 15 | 25MHz | 240MHz | Kit |
| LQM18NNR12K00□ | 120nH ±10% | 25MHz | 50mA | 0.50Ω | 15 | 25MHz | 205MHz | Kit |
| LQM18NNR15K00□ | 150nH ±10% | 25MHz | 50mA | 0.60Ω | 15 | 25MHz | 180MHz | Kit |
| LQM18NNR18K00□ | 180nH ±10% | 25MHz | 50mA | 0.60Ω | 15 | 25MHz | 165MHz | Kit |
| LQM18NNR22K00□ | 220nH ±10% | 25MHz | 50mA | 0.80Ω | 15 | 25MHz | 150MHz | Kit |
| LQM18NNR27K00□ | 270nH ±10% | 25MHz | 50mA | 0.80Ω | 15 | 25MHz | 136MHz | Kit |
| LQM18NNR33K00□ | 330nH ±10% | 25MHz | 35mA | 0.85Ω | 15 | 25MHz | 125MHz | Kit |
| LQM18NNR39K00□ | 390nH ±10% | 25MHz | 35mA | 1.00Ω | 15 | 25MHz | 110MHz | Kit |
| LQM18NNR47K00□ | 470nH ±10% | 25MHz | 35mA | 1.35Ω | 15 | 25MHz | 105MHz | Kit |
| LQM18NNR56K00□ | 560nH ±10% | 25MHz | 35mA | 1.55Ω | 15 | 25MHz | 95MHz | Kit |
| LQM18NNR68K00□ | 680nH ±10% | 25MHz | 35mA | 1.70Ω | 15 | 25MHz | 90MHz | Kit |
| LQM18NNR82K00□ | 820nH ±10% | 25MHz | 35mA | 2.10Ω | 15 | 25MHz | 85MHz | Kit |
| LQM18NN1R0K00□ | 1000nH ±10% | 10MHz | 25mA | 0.60Ω | 35 | 10MHz | 75MHz | Kit |
| LQM18NN1R2K00□ | 1200nH ±10% | 10MHz | 25mA | 0.80Ω | 35 | 10MHz | 65MHz | Kit |
| LQM18NN1R5K00□ | 1500nH ±10% | 10MHz | 25mA | 0.80Ω | 35 | 10MHz | 60MHz | Kit |
| LQM18NN1R8K00□ | 1800nH ±10% | 10MHz | 25mA | 0.95Ω | 35 | 10MHz | 55MHz | Kit |
| LQM18NN2R2K00□ | 2200nH ±10% | 10MHz | 15mA | 1.15Ω | 35 | 10MHz | 50MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite
 Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


Continued on the following page. ↗

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQM21NN_10 Series 0805/2012 (inch/mm)

Size Code 0805 (2012) in inch (in mm)

Appearance/Dimensions



| | | |
|----------------|--------------------------|----------|
| Dimension of t | Inductance: 0.1 to 2.2μH | 0.85±0.2 |
| | Inductance: 2.7 to 4.7μH | 1.25±0.2 |

Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| L | ø180mm Embossed Taping | 3000 |
| J | ø330mm Paper Taping | 10000 |
| K | ø330mm Embossed Taping | 10000 |
| B | Packing in Bulk | 1000 |



Refer to pages 137 to 140 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|-------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQM21NNR10K10□ | 0.1μH ±10% | 25MHz | 250mA | 0.26Ω | 20 | 25MHz | 340MHz | Kit |
| LQM21NNR12K10□ | 0.12μH ±10% | 25MHz | 250mA | 0.29Ω | 20 | 25MHz | 310MHz | Kit |
| LQM21NNR15K10□ | 0.15μH ±10% | 25MHz | 250mA | 0.32Ω | 20 | 25MHz | 270MHz | Kit |
| LQM21NNR18K10□ | 0.18μH ±10% | 25MHz | 250mA | 0.35Ω | 20 | 25MHz | 250MHz | Kit |
| LQM21NNR22K10□ | 0.22μH ±10% | 25MHz | 250mA | 0.38Ω | 20 | 25MHz | 220MHz | Kit |
| LQM21NNR27K10□ | 0.27μH ±10% | 25MHz | 250mA | 0.42Ω | 20 | 25MHz | 200MHz | Kit |
| LQM21NNR33K10□ | 0.33μH ±10% | 25MHz | 250mA | 0.48Ω | 20 | 25MHz | 180MHz | Kit |
| LQM21NNR39K10□ | 0.39μH ±10% | 25MHz | 200mA | 0.53Ω | 25 | 25MHz | 165MHz | Kit |
| LQM21NNR47K10□ | 0.47μH ±10% | 25MHz | 200mA | 0.57Ω | 25 | 25MHz | 150MHz | Kit |
| LQM21NNR56K10□ | 0.56μH ±10% | 25MHz | 150mA | 0.63Ω | 25 | 25MHz | 140MHz | Kit |
| LQM21NNR68K10□ | 0.68μH ±10% | 25MHz | 150mA | 0.72Ω | 25 | 25MHz | 125MHz | Kit |
| LQM21NNR82K10□ | 0.82μH ±10% | 25MHz | 150mA | 0.81Ω | 25 | 25MHz | 115MHz | Kit |
| LQM21NN1R0K10□ | 1.0μH ±10% | 10MHz | 50mA | 0.40Ω | 45 | 10MHz | 107MHz | Kit |
| LQM21NN1R2K10□ | 1.2μH ±10% | 10MHz | 50mA | 0.47Ω | 45 | 10MHz | 97MHz | Kit |
| LQM21NN1R5K10□ | 1.5μH ±10% | 10MHz | 50mA | 0.50Ω | 45 | 10MHz | 87MHz | Kit |
| LQM21NN1R8K10□ | 1.8μH ±10% | 10MHz | 50mA | 0.57Ω | 45 | 10MHz | 80MHz | Kit |
| LQM21NN2R2K10□ | 2.2μH ±10% | 10MHz | 30mA | 0.63Ω | 45 | 10MHz | 71MHz | Kit |
| LQM21NN2R7K10□ | 2.7μH ±10% | 10MHz | 30mA | 0.69Ω | 45 | 10MHz | 66MHz | Kit |
| LQM21NN3R3K10□ | 3.3μH ±10% | 10MHz | 30mA | 0.80Ω | 45 | 10MHz | 59MHz | Kit |
| LQM21NN3R9K10□ | 3.9μH ±10% | 10MHz | 30mA | 0.89Ω | 45 | 10MHz | 53MHz | Kit |
| LQM21NN4R7K10□ | 4.7μH ±10% | 10MHz | 30mA | 1.00Ω | 45 | 10MHz | 47MHz | Kit |

Class of Magnetic Shield: Magnetic shield of ferrite
 Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


Continued on the following page. ↗

Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH31MN_03

Series 1206/3216 (inch/mm)

Size Code 1206 (3216) in inch (in mm)

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |
| K | ø330mm Embossed Taping | 7500 |



Refer to pages 137 to 140 for mounting information.

Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current ^{*1} | DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) |
|----------------|-------------|---------------------------|-----------------------------|---------------|----------|------------------|---------------------------------|
| LQH31MNR15K03□ | 0.15μH ±10% | 1MHz | 250mA | 0.39Ω ±40% | 20 | 25.2MHz | 250MHz |
| LQH31MNR22K03□ | 0.22μH ±10% | 1MHz | 240mA | 0.43Ω ±40% | 20 | 25.2MHz | 250MHz |
| LQH31MNR33K03□ | 0.33μH ±10% | 1MHz | 230mA | 0.45Ω ±40% | 30 | 25.2MHz | 250MHz |
| LQH31MNR47K03□ | 0.47μH ±10% | 1MHz | 215mA | 0.83Ω ±40% | 30 | 25.2MHz | 200MHz |
| LQH31MNR56K03□ | 0.56μH ±10% | 1MHz | 200mA | 0.61Ω ±40% | 30 | 25.2MHz | 180MHz |
| LQH31MNR68K03□ | 0.68μH ±10% | 1MHz | 190mA | 0.67Ω ±40% | 30 | 25.2MHz | 160MHz |
| LQH31MNR82K03□ | 0.82μH ±10% | 1MHz | 185mA | 0.73Ω ±40% | 30 | 25.2MHz | 120MHz |
| LQH31MN1R0K03□ | 1.0μH ±10% | 1MHz | 175mA | 0.49Ω ±30% | 35 | 10MHz | 100MHz |
| LQH31MN1R2J03□ | 1.2μH ±5% | 1MHz | 165mA | 0.37Ω ±30% | 35 | 10MHz | 90MHz |
| LQH31MN1R2K03□ | 1.2μH ±10% | 1MHz | 165mA | 0.9Ω ±30% | 35 | 10MHz | 90MHz |
| LQH31MN1R5J03□ | 1.5μH ±5% | 1MHz | 155mA | 1.0Ω ±30% | 35 | 10MHz | 75MHz |
| LQH31MN1R5K03□ | 1.5μH ±10% | 1MHz | 155mA | 1.0Ω ±30% | 35 | 10MHz | 75MHz |
| LQH31MN1R8J03□ | 1.8μH ±5% | 1MHz | 150mA | 1.6Ω ±30% | 35 | 10MHz | 60MHz |
| LQH31MN1R8K03□ | 1.8μH ±10% | 1MHz | 150mA | 1.6Ω ±30% | 35 | 10MHz | 60MHz |
| LQH31MN2R2J03□ | 2.2μH ±5% | 1MHz | 140mA | 0.7Ω ±30% | 35 | 10MHz | 50MHz |
| LQH31MN2R2K03□ | 2.2μH ±10% | 1MHz | 140mA | 0.7Ω ±30% | 35 | 10MHz | 50MHz |
| LQH31MN2R7J03□ | 2.7μH ±5% | 1MHz | 135mA | 0.55Ω ±30% | 35 | 10MHz | 43MHz |
| LQH31MN2R7K03□ | 2.7μH ±10% | 1MHz | 135mA | 0.55Ω ±30% | 35 | 10MHz | 43MHz |
| LQH31MN3R3J03□ | 3.3μH ±5% | 1MHz | 130mA | 0.61Ω ±30% | 35 | 8MHz | 38MHz |
| LQH31MN3R3K03□ | 3.3μH ±10% | 1MHz | 130mA | 0.61Ω ±30% | 35 | 8MHz | 38MHz |
| LQH31MN3R9J03□ | 3.9μH ±5% | 1MHz | 125mA | 1.5Ω ±30% | 35 | 8MHz | 35MHz |
| LQH31MN3R9K03□ | 3.9μH ±10% | 1MHz | 125mA | 1.5Ω ±30% | 35 | 8MHz | 35MHz |
| LQH31MN4R7J03□ | 4.7μH ±5% | 1MHz | 120mA | 1.7Ω ±30% | 35 | 8MHz | 31MHz |
| LQH31MN4R7K03□ | 4.7μH ±10% | 1MHz | 120mA | 1.7Ω ±30% | 35 | 8MHz | 31MHz |
| LQH31MN5R6J03□ | 5.6μH ±5% | 1MHz | 115mA | 1.8Ω ±30% | 35 | 8MHz | 28MHz |
| LQH31MN5R6K03□ | 5.6μH ±10% | 1MHz | 115mA | 1.8Ω ±30% | 35 | 8MHz | 28MHz |
| LQH31MN6R8J03□ | 6.8μH ±5% | 1MHz | 110mA | 2.0Ω ±30% | 35 | 8MHz | 25MHz |
| LQH31MN6R8K03□ | 6.8μH ±10% | 1MHz | 110mA | 2.0Ω ±30% | 35 | 8MHz | 25MHz |
| LQH31MN8R2J03□ | 8.2μH ±5% | 1MHz | 105mA | 2.2Ω ±30% | 35 | 8MHz | 23MHz |
| LQH31MN8R2K03□ | 8.2μH ±10% | 1MHz | 105mA | 2.2Ω ±30% | 35 | 8MHz | 23MHz |
| LQH31MN100J03□ | 10μH ±5% | 1MHz | 100mA | 2.5Ω ±30% | 35 | 5MHz | 20MHz |
| LQH31MN100K03□ | 10μH ±10% | 1MHz | 100mA | 2.5Ω ±30% | 35 | 5MHz | 20MHz |

Class of Magnetic Shield: No magnetic shield

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

*1 When applied rated current to the products, self-temperature rise shall be limited to 20°C max. and inductance will be within ±10% of initial inductance value.

Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current ^{*1} | DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) |
|----------------|------------|---------------------------|-----------------------------|---------------|----------|------------------|---------------------------------|
| LQH31MN120J03□ | 12μH ±5% | 1MHz | 95mA | 2.7Ω ±30% | 35 | 5MHz | 18MHz |
| LQH31MN120K03□ | 12μH ±10% | 1MHz | 95mA | 2.7Ω ±30% | 35 | 5MHz | 18MHz |
| LQH31MN150J03□ | 15μH ±5% | 1MHz | 90mA | 3.0Ω ±30% | 35 | 5MHz | 16MHz |
| LQH31MN150K03□ | 15μH ±10% | 1MHz | 90mA | 3.0Ω ±30% | 35 | 5MHz | 16MHz |
| LQH31MN180J03□ | 18μH ±5% | 1MHz | 85mA | 3.4Ω ±30% | 35 | 5MHz | 15MHz |
| LQH31MN180K03□ | 18μH ±10% | 1MHz | 85mA | 3.4Ω ±30% | 35 | 5MHz | 15MHz |
| LQH31MN220J03□ | 22μH ±5% | 1MHz | 85mA | 3.1Ω ±30% | 40 | 2.5MHz | 14MHz |
| LQH31MN220K03□ | 22μH ±10% | 1MHz | 85mA | 3.1Ω ±30% | 40 | 2.5MHz | 14MHz |
| LQH31MN270J03□ | 27μH ±5% | 1MHz | 85mA | 3.4Ω ±30% | 40 | 2.5MHz | 13MHz |
| LQH31MN270K03□ | 27μH ±10% | 1MHz | 85mA | 3.4Ω ±30% | 40 | 2.5MHz | 13MHz |
| LQH31MN330J03□ | 33μH ±5% | 1MHz | 80mA | 3.8Ω ±30% | 40 | 2.5MHz | 12MHz |
| LQH31MN330K03□ | 33μH ±10% | 1MHz | 80mA | 3.8Ω ±30% | 40 | 2.5MHz | 12MHz |
| LQH31MN390J03□ | 39μH ±5% | 1MHz | 55mA | 7.2Ω ±30% | 40 | 2.5MHz | 11MHz |
| LQH31MN390K03□ | 39μH ±10% | 1MHz | 55mA | 7.2Ω ±30% | 40 | 2.5MHz | 11MHz |
| LQH31MN470J03□ | 47μH ±5% | 1MHz | 55mA | 8.0Ω ±30% | 40 | 2.5MHz | 10MHz |
| LQH31MN470K03□ | 47μH ±10% | 1MHz | 55mA | 8.0Ω ±30% | 40 | 2.5MHz | 10MHz |
| LQH31MN560J03□ | 56μH ±5% | 1MHz | 50mA | 8.9Ω ±30% | 40 | 2.5MHz | 9MHz |
| LQH31MN560K03□ | 56μH ±10% | 1MHz | 50mA | 8.9Ω ±30% | 40 | 2.5MHz | 9MHz |
| LQH31MN680J03□ | 68μH ±5% | 1MHz | 50mA | 9.9Ω ±30% | 40 | 2.5MHz | 8.5MHz |
| LQH31MN680K03□ | 68μH ±10% | 1MHz | 50mA | 9.9Ω ±30% | 40 | 2.5MHz | 8.5MHz |
| LQH31MN820J03□ | 82μH ±5% | 1MHz | 45mA | 11.0Ω ±30% | 40 | 2.5MHz | 7.5MHz |
| LQH31MN820K03□ | 82μH ±10% | 1MHz | 45mA | 11.0Ω ±30% | 40 | 2.5MHz | 7.5MHz |
| LQH31MN101J03□ | 100μH ±5% | 1MHz | 45mA | 12.0Ω ±30% | 40 | 2.5MHz | 7MHz |
| LQH31MN101K03□ | 100μH ±10% | 1MHz | 45mA | 12.0Ω ±30% | 40 | 2.5MHz | 7MHz |

Class of Magnetic Shield: No magnetic shield


Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

*1 When applied rated current to the products, self-temperature rise shall be limited to 20°C max. and inductance will be within ±10% of initial inductance value.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Wire Wound Type (Ferrite Core)

LQH32MN_23 Series 1210/3225 (inch/mm)

Size Code 1210 (3225) in inch (in mm)

■ Appearance/
Dimensions

■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |
| K | ø330mm Embossed Taping | 7500 |



Refer to pages 137 to 140 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQH32MN1R0M23□ | 1.0μH ±20% | 1MHz | 445mA | 0.5Ω | 20 | 1MHz | 100MHz | Kit |
| LQH32MN1R2M23□ | 1.2μH ±20% | 1MHz | 425mA | 0.6Ω | 20 | 1MHz | 100MHz | Kit |
| LQH32MN1R5K23□ | 1.5μH ±10% | 1MHz | 400mA | 0.6Ω | 20 | 1MHz | 75MHz | Kit |
| LQH32MN1R8K23□ | 1.8μH ±10% | 1MHz | 390mA | 0.7Ω | 20 | 1MHz | 60MHz | Kit |
| LQH32MN2R2K23□ | 2.2μH ±10% | 1MHz | 370mA | 0.8Ω | 20 | 1MHz | 50MHz | Kit |
| LQH32MN2R7K23□ | 2.7μH ±10% | 1MHz | 320mA | 0.9Ω | 20 | 1MHz | 43MHz | Kit |
| LQH32MN3R3K23□ | 3.3μH ±10% | 1MHz | 300mA | 1.0Ω | 20 | 1MHz | 38MHz | Kit |
| LQH32MN3R9K23□ | 3.9μH ±10% | 1MHz | 290mA | 1.1Ω | 20 | 1MHz | 35MHz | Kit |
| LQH32MN4R7K23□ | 4.7μH ±10% | 1MHz | 270mA | 1.2Ω | 20 | 1MHz | 31MHz | Kit |
| LQH32MN5R6K23□ | 5.6μH ±10% | 1MHz | 250mA | 1.3Ω | 20 | 1MHz | 28MHz | Kit |
| LQH32MN6R8K23□ | 6.8μH ±10% | 1MHz | 240mA | 1.5Ω | 20 | 1MHz | 25MHz | Kit |
| LQH32MN8R2K23□ | 8.2μH ±10% | 1MHz | 225mA | 1.6Ω | 20 | 1MHz | 23MHz | Kit |
| LQH32MN100J23□ | 10μH ±5% | 1MHz | 190mA | 1.8Ω | 35 | 1MHz | 20MHz | |
| LQH32MN100K23□ | 10μH ±10% | 1MHz | 190mA | 1.8Ω | 35 | 1MHz | 20MHz | Kit |
| LQH32MN120J23□ | 12μH ±5% | 1MHz | 180mA | 2.0Ω | 35 | 1MHz | 18MHz | |
| LQH32MN120K23□ | 12μH ±10% | 1MHz | 180mA | 2.0Ω | 35 | 1MHz | 18MHz | Kit |
| LQH32MN150J23□ | 15μH ±5% | 1MHz | 170mA | 2.2Ω | 35 | 1MHz | 16MHz | |
| LQH32MN150K23□ | 15μH ±10% | 1MHz | 170mA | 2.2Ω | 35 | 1MHz | 16MHz | Kit |
| LQH32MN180J23□ | 18μH ±5% | 1MHz | 165mA | 2.5Ω | 35 | 1MHz | 15MHz | |
| LQH32MN180K23□ | 18μH ±10% | 1MHz | 165mA | 2.5Ω | 35 | 1MHz | 15MHz | Kit |
| LQH32MN220J23□ | 22μH ±5% | 1MHz | 150mA | 2.8Ω | 35 | 1MHz | 14MHz | |
| LQH32MN220K23□ | 22μH ±10% | 1MHz | 150mA | 2.8Ω | 35 | 1MHz | 14MHz | Kit |
| LQH32MN270J23□ | 27μH ±5% | 1MHz | 125mA | 3.1Ω | 35 | 1MHz | 13MHz | |
| LQH32MN270K23□ | 27μH ±10% | 1MHz | 125mA | 3.1Ω | 35 | 1MHz | 13MHz | Kit |
| LQH32MN330J23□ | 33μH ±5% | 1MHz | 115mA | 3.5Ω | 40 | 1MHz | 12MHz | |
| LQH32MN330K23□ | 33μH ±10% | 1MHz | 115mA | 3.5Ω | 40 | 1MHz | 12MHz | Kit |
| LQH32MN390J23□ | 39μH ±5% | 1MHz | 110mA | 3.9Ω | 40 | 1MHz | 11MHz | |
| LQH32MN390K23□ | 39μH ±10% | 1MHz | 110mA | 3.9Ω | 40 | 1MHz | 11MHz | Kit |
| LQH32MN470J23□ | 47μH ±5% | 1MHz | 100mA | 4.3Ω | 40 | 1MHz | 11MHz | |
| LQH32MN470K23□ | 47μH ±10% | 1MHz | 100mA | 4.3Ω | 40 | 1MHz | 11MHz | Kit |
| LQH32MN560J23□ | 56μH ±5% | 1MHz | 85mA | 4.9Ω | 40 | 1MHz | 10MHz | |
| LQH32MN560K23□ | 56μH ±10% | 1MHz | 85mA | 4.9Ω | 40 | 1MHz | 10MHz | Kit |

Class of Magnetic Shield: No magnetic shield

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

Continued on the following page.


△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQH32MN680J23□ | 68μH ±5% | 1MHz | 80mA | 5.5Ω | 40 | 1MHz | 9MHz | |
| LQH32MN680K23□ | 68μH ±10% | 1MHz | 80mA | 5.5Ω | 40 | 1MHz | 9MHz | Kit |
| LQH32MN820J23□ | 82μH ±5% | 1MHz | 70mA | 6.2Ω | 40 | 1MHz | 8.5MHz | |
| LQH32MN820K23□ | 82μH ±10% | 1MHz | 70mA | 6.2Ω | 40 | 1MHz | 8.5MHz | Kit |
| LQH32MN101J23□ | 100μH ±5% | 1MHz | 80mA | 7.0Ω | 40 | 796kHz | 8MHz | |
| LQH32MN101K23□ | 100μH ±10% | 1MHz | 80mA | 7.0Ω | 40 | 796kHz | 8MHz | Kit |
| LQH32MN121J23□ | 120μH ±5% | 1MHz | 75mA | 8.0Ω | 40 | 796kHz | 7.5MHz | |
| LQH32MN121K23□ | 120μH ±10% | 1MHz | 75mA | 8.0Ω | 40 | 796kHz | 7.5MHz | Kit |
| LQH32MN151J23□ | 150μH ±5% | 1MHz | 70mA | 9.3Ω | 40 | 796kHz | 7MHz | |
| LQH32MN151K23□ | 150μH ±10% | 1MHz | 70mA | 9.3Ω | 40 | 796kHz | 7MHz | Kit |
| LQH32MN181J23□ | 180μH ±5% | 1MHz | 65mA | 10.2Ω | 40 | 796kHz | 6MHz | |
| LQH32MN181K23□ | 180μH ±10% | 1MHz | 65mA | 10.2Ω | 40 | 796kHz | 6MHz | Kit |
| LQH32MN221J23□ | 220μH ±5% | 1MHz | 65mA | 11.8Ω | 40 | 796kHz | 5.5MHz | |
| LQH32MN221K23□ | 220μH ±10% | 1MHz | 65mA | 11.8Ω | 40 | 796kHz | 5.5MHz | Kit |
| LQH32MN271J23□ | 270μH ±5% | 1MHz | 65mA | 12.5Ω | 40 | 796kHz | 5MHz | |
| LQH32MN271K23□ | 270μH ±10% | 1MHz | 65mA | 12.5Ω | 40 | 796kHz | 5MHz | Kit |
| LQH32MN331J23□ | 330μH ±5% | 1MHz | 65mA | 13.0Ω | 40 | 796kHz | 5MHz | |
| LQH32MN331K23□ | 330μH ±10% | 1MHz | 65mA | 13.0Ω | 40 | 796kHz | 5MHz | Kit |
| LQH32MN391J23□ | 390μH ±5% | 1MHz | 50mA | 22.0Ω | 50 | 796kHz | 5MHz | |
| LQH32MN391K23□ | 390μH ±10% | 1MHz | 50mA | 22.0Ω | 50 | 796kHz | 5MHz | Kit |
| LQH32MN471J23□ | 470μH ±5% | 1kHz | 45mA | 25.0Ω | 50 | 796kHz | 5MHz | |
| LQH32MN471K23□ | 470μH ±10% | 1kHz | 45mA | 25.0Ω | 50 | 796kHz | 5MHz | Kit |
| LQH32MN561J23□ | 560μH ±5% | 1kHz | 40mA | 28.0Ω | 50 | 796kHz | 5MHz | |
| LQH32MN561K23□ | 560μH ±10% | 1kHz | 40mA | 28.0Ω | 50 | 796kHz | 5MHz | Kit |


Class of Magnetic Shield: No magnetic shield

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH43MN_03/LQH43NN_03 Series 1812/4532 (inch/mm)

Size Code 1812 (4532) in inch (in mm)

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 500 |
| K | ø330mm Embossed Taping | 2500 |



Refer to pages 137 to 140 for mounting information.

Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQH43MN1R0M03□ | 1.0μH ±20% | 1MHz | 500mA | 0.20Ω | 20 | 1MHz | 120MHz | Kit |
| LQH43MN1R2M03□ | 1.2μH ±20% | 1MHz | 500mA | 0.20Ω | 20 | 1MHz | 100MHz | Kit |
| LQH43MN1R5M03□ | 1.5μH ±20% | 1MHz | 500mA | 0.30Ω | 20 | 1MHz | 85MHz | Kit |
| LQH43MN1R8M03□ | 1.8μH ±20% | 1MHz | 500mA | 0.30Ω | 20 | 1MHz | 75MHz | Kit |
| LQH43MN2R2M03□ | 2.2μH ±20% | 1MHz | 500mA | 0.30Ω | 20 | 1MHz | 62MHz | Kit |
| LQH43MN2R7M03□ | 2.7μH ±20% | 1MHz | 500mA | 0.32Ω | 20 | 1MHz | 53MHz | Kit |
| LQH43MN3R3M03□ | 3.3μH ±20% | 1MHz | 500mA | 0.35Ω | 20 | 1MHz | 47MHz | Kit |
| LQH43MN3R9M03□ | 3.9μH ±20% | 1MHz | 500mA | 0.38Ω | 20 | 1MHz | 41MHz | Kit |
| LQH43MN4R7K03□ | 4.7μH ±10% | 1MHz | 500mA | 0.40Ω | 30 | 1MHz | 38MHz | Kit |
| LQH43MN5R6K03□ | 5.6μH ±10% | 1MHz | 500mA | 0.47Ω | 30 | 1MHz | 33MHz | Kit |
| LQH43MN6R8K03□ | 6.8μH ±10% | 1MHz | 450mA | 0.50Ω | 30 | 1MHz | 31MHz | Kit |
| LQH43MN8R2K03□ | 8.2μH ±10% | 1MHz | 450mA | 0.56Ω | 30 | 1MHz | 27MHz | Kit |
| LQH43MN100J03□ | 10μH ±5% | 1MHz | 400mA | 0.56Ω | 35 | 1MHz | 23MHz | |
| LQH43MN100K03□ | 10μH ±10% | 1MHz | 400mA | 0.56Ω | 35 | 1MHz | 23MHz | Kit |
| LQH43MN120J03□ | 12μH ±5% | 1MHz | 380mA | 0.62Ω | 35 | 1MHz | 21MHz | |
| LQH43MN120K03□ | 12μH ±10% | 1MHz | 380mA | 0.62Ω | 35 | 1MHz | 21MHz | Kit |
| LQH43MN150J03□ | 15μH ±5% | 1MHz | 360mA | 0.73Ω | 35 | 1MHz | 19MHz | |
| LQH43MN150K03□ | 15μH ±10% | 1MHz | 360mA | 0.73Ω | 35 | 1MHz | 19MHz | Kit |
| LQH43MN180J03□ | 18μH ±5% | 1MHz | 340mA | 0.82Ω | 35 | 1MHz | 17MHz | |
| LQH43MN180K03□ | 18μH ±10% | 1MHz | 340mA | 0.82Ω | 35 | 1MHz | 17MHz | Kit |
| LQH43MN220J03□ | 22μH ±5% | 1MHz | 320mA | 0.94Ω | 35 | 1MHz | 15MHz | |
| LQH43MN220K03□ | 22μH ±10% | 1MHz | 320mA | 0.94Ω | 35 | 1MHz | 15MHz | Kit |
| LQH43MN270J03□ | 27μH ±5% | 1MHz | 300mA | 1.1Ω | 35 | 1MHz | 14MHz | |
| LQH43MN270K03□ | 27μH ±10% | 1MHz | 300mA | 1.1Ω | 35 | 1MHz | 14MHz | Kit |
| LQH43MN330J03□ | 33μH ±5% | 1MHz | 270mA | 1.2Ω | 35 | 1MHz | 12MHz | |
| LQH43MN330K03□ | 33μH ±10% | 1MHz | 270mA | 1.2Ω | 35 | 1MHz | 12MHz | Kit |
| LQH43MN390J03□ | 39μH ±5% | 1MHz | 240mA | 1.4Ω | 35 | 1MHz | 11MHz | |
| LQH43MN390K03□ | 39μH ±10% | 1MHz | 240mA | 1.4Ω | 35 | 1MHz | 11MHz | Kit |
| LQH43MN470J03□ | 47μH ±5% | 1MHz | 220mA | 1.5Ω | 35 | 1MHz | 10MHz | |
| LQH43MN470K03□ | 47μH ±10% | 1MHz | 220mA | 1.5Ω | 35 | 1MHz | 10MHz | Kit |
| LQH43MN560J03□ | 56μH ±5% | 1MHz | 200mA | 1.7Ω | 35 | 1MHz | 9.3MHz | |
| LQH43MN560K03□ | 56μH ±10% | 1MHz | 200mA | 1.7Ω | 35 | 1MHz | 9.3MHz | Kit |

Class of Magnetic Shield: No magnetic shield

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|-------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQH43MN680J03□ | 68μH ±5% | 1MHz | 180mA | 1.9Ω | 35 | 1MHz | 8.4MHz | |
| LQH43MN680K03□ | 68μH ±10% | 1MHz | 180mA | 1.9Ω | 35 | 1MHz | 8.4MHz | Kit |
| LQH43MN820J03□ | 82μH ±5% | 1MHz | 170mA | 2.2Ω | 35 | 1MHz | 7.5MHz | |
| LQH43MN820K03□ | 82μH ±10% | 1MHz | 170mA | 2.2Ω | 35 | 1MHz | 7.5MHz | Kit |
| LQH43MN101J03□ | 100μH ±5% | 1MHz | 160mA | 2.5Ω | 40 | 796kHz | 6.8MHz | |
| LQH43MN101K03□ | 100μH ±10% | 1MHz | 160mA | 2.5Ω | 40 | 796kHz | 6.8MHz | Kit |
| LQH43MN121J03□ | 120μH ±5% | 1MHz | 150mA | 3.0Ω | 40 | 796kHz | 6.2MHz | |
| LQH43MN121K03□ | 120μH ±10% | 1MHz | 150mA | 3.0Ω | 40 | 796kHz | 6.2MHz | Kit |
| LQH43MN151J03□ | 150μH ±5% | 1MHz | 130mA | 3.7Ω | 40 | 796kHz | 5.5MHz | |
| LQH43MN151K03□ | 150μH ±10% | 1MHz | 130mA | 3.7Ω | 40 | 796kHz | 5.5MHz | Kit |
| LQH43MN181J03□ | 180μH ±5% | 1MHz | 120mA | 4.5Ω | 40 | 796kHz | 5.0MHz | |
| LQH43MN181K03□ | 180μH ±10% | 1MHz | 120mA | 4.5Ω | 40 | 796kHz | 5.0MHz | Kit |
| LQH43MN221J03□ | 220μH ±5% | 1MHz | 110mA | 5.4Ω | 40 | 796kHz | 4.5MHz | |
| LQH43MN221K03□ | 220μH ±10% | 1MHz | 110mA | 5.4Ω | 40 | 796kHz | 4.5MHz | Kit |
| LQH43MN271J03□ | 270μH ±5% | 1MHz | 100mA | 6.8Ω | 40 | 796kHz | 4.0MHz | |
| LQH43MN271K03□ | 270μH ±10% | 1MHz | 100mA | 6.8Ω | 40 | 796kHz | 4.0MHz | Kit |
| LQH43MN331J03□ | 330μH ±5% | 1MHz | 95mA | 8.2Ω | 40 | 796kHz | 3.6MHz | |
| LQH43MN331K03□ | 330μH ±10% | 1MHz | 95mA | 8.2Ω | 40 | 796kHz | 3.6MHz | Kit |
| LQH43MN391J03□ | 390μH ±5% | 1MHz | 90mA | 9.7Ω | 40 | 796kHz | 3.3MHz | |
| LQH43MN391K03□ | 390μH ±10% | 1MHz | 90mA | 9.7Ω | 40 | 796kHz | 3.3MHz | Kit |
| LQH43MN471J03□ | 470μH ±5% | 1kHz | 80mA | 11.8Ω | 40 | 796kHz | 3.0MHz | |
| LQH43MN471K03□ | 470μH ±10% | 1kHz | 80mA | 11.8Ω | 40 | 796kHz | 3.0MHz | Kit |
| LQH43MN561J03□ | 560μH ±5% | 1kHz | 70mA | 14.5Ω | 40 | 796kHz | 2.7MHz | |
| LQH43MN561K03□ | 560μH ±10% | 1kHz | 70mA | 14.5Ω | 40 | 796kHz | 2.7MHz | Kit |
| LQH43MN681J03□ | 680μH ±5% | 1kHz | 65mA | 17.0Ω | 40 | 796kHz | 2.5MHz | |
| LQH43MN681K03□ | 680μH ±10% | 1kHz | 65mA | 17.0Ω | 40 | 796kHz | 2.5MHz | Kit |
| LQH43MN821J03□ | 820μH ±5% | 1kHz | 60mA | 20.5Ω | 40 | 796kHz | 2.2MHz | |
| LQH43MN821K03□ | 820μH ±10% | 1kHz | 60mA | 20.5Ω | 40 | 796kHz | 2.2MHz | Kit |
| LQH43MN102J03□ | 1000μH ±5% | 1kHz | 50mA | 25.0Ω | 40 | 252kHz | 2.0MHz | |
| LQH43MN102K03□ | 1000μH ±10% | 1kHz | 50mA | 25.0Ω | 40 | 252kHz | 2.0MHz | Kit |
| LQH43MN122J03□ | 1200μH ±5% | 1kHz | 45mA | 30.0Ω | 40 | 252kHz | 1.8MHz | |
| LQH43MN122K03□ | 1200μH ±10% | 1kHz | 45mA | 30.0Ω | 40 | 252kHz | 1.8MHz | Kit |
| LQH43MN152J03□ | 1500μH ±5% | 1kHz | 40mA | 37.0Ω | 40 | 252kHz | 1.6MHz | |
| LQH43MN152K03□ | 1500μH ±10% | 1kHz | 40mA | 37.0Ω | 40 | 252kHz | 1.6MHz | Kit |
| LQH43NN182J03□ | 1800μH ±5% | 1kHz | 35mA | 45.0Ω | 40 | 252kHz | 1.5MHz | |
| LQH43NN182K03□ | 1800μH ±10% | 1kHz | 35mA | 45.0Ω | 40 | 252kHz | 1.5MHz | Kit |
| LQH43NN222J03□ | 2200μH ±5% | 1kHz | 30mA | 50.0Ω | 40 | 252kHz | 1.3MHz | |
| LQH43NN222K03□ | 2200μH ±10% | 1kHz | 30mA | 50.0Ω | 40 | 252kHz | 1.3MHz | Kit |


Class of Magnetic Shield: No magnetic shield

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


Continued on the following page. 

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Current Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH44NN_03 Series 1515/4040 (inch/mm)

Size Code 1515 (4040) in inch (in mm), General

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 250 |
| K | ø330mm Embossed Taping | 1500 |



Refer to pages 137 to 140 for mounting information.

Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current ^{*1} | DC Resistance | Self-Resonance Frequency (min.) | |
|----------------|-------------|---------------------------|-----------------------------|---------------|---------------------------------|-----|
| LQH44NNR51M03□ | 0.51μH ±20% | 1kHz | 4.5A | 0.0075Ω ±30% | 160MHz | New |
| LQH44NNR74M03□ | 0.74μH ±20% | 1kHz | 3.5A | 0.011Ω ±30% | 150MHz | New |
| LQH44NN1R0M03□ | 1.0μH ±20% | 1kHz | 3.3A | 0.012Ω ±30% | 90MHz | New |
| LQH44NN1R5M03□ | 1.5μH ±20% | 1kHz | 3.2A | 0.016Ω ±30% | 70MHz | New |
| LQH44NN2R2M03□ | 2.2μH ±20% | 1kHz | 2.5A | 0.019Ω ±20% | 55MHz | New |
| LQH44NN3R3M03□ | 3.3μH ±20% | 1kHz | 2.25A | 0.024Ω ±30% | 34.8MHz | New |
| LQH44NN4R7M03□ | 4.7μH ±20% | 1kHz | 1.95A | 0.040Ω ±30% | 23.4MHz | New |
| LQH44NN5R0K03□ | 5.0μH ±10% | 1kHz | 1.95A | 0.040Ω ±30% | 23.4MHz | New |
| LQH44NN6R8K03□ | 6.8μH ±10% | 1kHz | 1.6A | 0.051Ω ±30% | 19.8MHz | New |
| LQH44NN100K03□ | 10μH ±10% | 1kHz | 1.3A | 0.067Ω ±30% | 23.5MHz | New |
| LQH44NN150K03□ | 15μH ±10% | 1kHz | 1.1A | 0.100Ω ±30% | 11.5MHz | New |
| LQH44NN220K03□ | 22μH ±10% | 1kHz | 0.95A | 0.170Ω ±30% | 14MHz | New |
| LQH44NN330K03□ | 33μH ±10% | 1kHz | 0.76A | 0.210Ω ±30% | 12MHz | New |
| LQH44NN470K03□ | 47μH ±10% | 1kHz | 0.64A | 0.330Ω ±30% | 10MHz | New |
| LQH44NN680K03□ | 68μH ±10% | 1kHz | 0.53A | 0.410Ω ±30% | 8.0MHz | New |
| LQH44NN101K03□ | 100μH ±10% | 1kHz | 0.3A | 0.540Ω ±30% | 6.3MHz | New |
| LQH44NN151K03□ | 150μH ±10% | 1kHz | 0.26A | 0.920Ω ±30% | 5.2MHz | New |
| LQH44NN221K03□ | 220μH ±10% | 1kHz | 0.21A | 1.20Ω ±30% | 3.9MHz | New |
| LQH44NN331K03□ | 330μH ±10% | 1kHz | 0.18A | 1.76Ω ±30% | 3.0MHz | New |
| LQH44NN471K03□ | 470μH ±10% | 1kHz | 0.145A | 2.23Ω ±30% | 2.7MHz | New |

Class of Magnetic Shield: No magnetic shield

Operating Temperature Range (Self-temperature rise is included): -40°C~+125°C

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


For reflow soldering only.

*1 When applied rated current to the products, self-temperature rise shall be limited to 40°C max. and inductance will be within ±20% of initial inductance value.

Continued on the following page.

[△]Note • Please read rating and [△]CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Inductance-Current Characteristics (Typ.)



⚠ Caution

● Rating

1. About the Rated Current

Do not use products beyond the rated current as this may create excessive heat and deteriorate the insulation resistance.

2. About Excessive Surge Current

Surge current (pulse current or rush current) greater than the specified rated current applied to the product may cause a critical failure, such as an open circuit, burnout caused by excessive temperature rise. Please contact us in advance in case of applying the surge current.

Notice

● Storage and Operating Condition

<Operating Environment>

Do not use products in chemical atmosphere such as chlorine gas, acid or sulfide gas.

<Storage Requirements>

1. Storage Period

LQB series and LQM series should be used within 6 months; the other products should be used within 12 months.

Check solderability if this period is exceeded.

2. Storage Conditions

(1) Store products in a warehouse in compliance with the following conditions:

Temperature: -10 to +40 degrees C.

Humidity: 15 to 85% (relative humidity)

Do not subject products to rapid changes in temperature and humidity.

Do not store them in chemical atmosphere such as one containing sulfurous acid gas or alkaline gas.

This will prevent electrode oxidation, which causes poor solderability and possible corrosion of inductors.

(2) Do not store products in bulk packaging to prevent collision among inductors, which causes core chipping and wire breakage.

(3) Store products on pallets to protect from humidity, dust, etc.

(4) Avoid heat shock, vibration, direct sunlight, etc.

● Handling

This item is designed to have sufficient strength, but handle with care to avoid chipping or breaking its ceramic structure.

LQH_M/N series

- To prevent breaking the wire, avoid touching with sharp material, such as tweezers or the bristles of a cleaning brush, to the wire wound portion of this product.
- To prevent breaking the core, avoid applying excessive mechanical shock to products mounted on the board.

LQB series and LQM series

- There is the possibility that magnetism may change the inductance value. Do not use a magnet or

tweezers with magnetism when handling chip inductors. (The tip of the tweezers should be molded with resin or pottery.)

- When excessive current over the rated current is applied, it may cause the inductance value to change due to magnetism.

<Handling>

1. Avoid applying excessive stress to products to prevent damage.

2. Do not touch wire wound with sharp objects such as tweezers to prevent wire breakage.

3. Do not apply excessive force to products mounted on boards to prevent core breakage.

<Transportation>

Do not apply excessive vibration or mechanical shock to products.

<Resin Coating>

When coating products with resin, the relatively high resin curing stress may change inductance values.

For exterior coating, select resin carefully so that electrical and mechanical performance of the product is not affected. Prior to use, please evaluate reliability with the product mounted in your application set.


(LQH series)

An open circuit issue may occur by mechanical stress caused by the resin, amount/cured shape of resin, or operating conditions, etc. Some resins containing impurities or chloride may possibly generate chlorine by hydrolysis under some operating conditions, causing corrosion of the inductor wire and leading to an open circuit.


<Handling of a Substrate>

After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting the substrate when cropping the substrate, inserting and removing a connector from the substrate, or tightening a screw to the substrate. Excessive mechanical stress may cause cracking in the Product.

Bending




Twisting



1. Standard Land Pattern Dimensions

A high Q value is achieved when the PCB electrode land pattern is designed so that it does not project beyond the chip Inductors (chip coils) electrode.



| Series | Standard Land Dimensions | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|--|--------------------------|---|-------------|-----|---------|-----|---|---------|--------|-----|---------|-----|--------|------|-----|---------|-----|--------|--------|---------|--------|--|-----|---------|-----|--------|--|-----|-----|-----|--------|--|-----|-----|-----|
| LQB15N LQB18N LQM18N LQM21N LQH31M LQH44N | | <table border="1"> <thead> <tr> <th>Part Number</th> <th></th> <th>a</th> <th>b</th> <th>c</th> </tr> </thead> <tbody> <tr> <td>LQB15NN</td> <td>Reflow</td> <td>0.4</td> <td>1.2-1.4</td> <td>0.5</td> </tr> <tr> <td>LQB18N</td> <td>Flow</td> <td rowspan="2">0.7</td> <td>2.2-2.6</td> <td rowspan="2">0.7</td> </tr> <tr> <td>LQM18N</td> <td>Reflow</td> <td>1.8-2.0</td> </tr> <tr> <td>LQM21N</td> <td></td> <td>1.2</td> <td>3.0-4.0</td> <td>1.0</td> </tr> <tr> <td>LQH31M</td> <td></td> <td>1.0</td> <td>4.5</td> <td>1.5</td> </tr> <tr> <td>LQH44N</td> <td></td> <td>1.3</td> <td>4.4</td> <td>3.0</td> </tr> </tbody> </table> | Part Number | | a | b | c | LQB15NN | Reflow | 0.4 | 1.2-1.4 | 0.5 | LQB18N | Flow | 0.7 | 2.2-2.6 | 0.7 | LQM18N | Reflow | 1.8-2.0 | LQM21N | | 1.2 | 3.0-4.0 | 1.0 | LQH31M | | 1.0 | 4.5 | 1.5 | LQH44N | | 1.3 | 4.4 | 3.0 |
| | | Part Number | | a | b | c | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | LQB15NN | Reflow | 0.4 | 1.2-1.4 | 0.5 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | LQB18N | Flow | 0.7 | 2.2-2.6 | 0.7 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | LQM18N | Reflow | | 1.8-2.0 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | LQM21N | | 1.2 | 3.0-4.0 | 1.0 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| LQH31M | | 1.0 | 4.5 | 1.5 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| LQH44N | | 1.3 | 4.4 | 3.0 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| LQH32M | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| LQH43M LQH43N | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |

Attention should be paid to potential magnetic coupling effects when using the Inductors (coils) as a resonator.

2. Standard Soldering Conditions

(1) Soldering method

Chip Inductors (Chip coils) can be flow or reflow soldered.

Please contact Murata regarding other soldering methods.

Solder: Use Sn-3.0Ag-0.5Cu solder.

Flux: Use rosin-based flux, but not strongly acidic flux (with chlorine content exceeding 0.2wt%).

Do not use water-soluble flux.


For additional mounting methods, please contact Murata.

Continued on the following page.

Note • Please read rating and **CAUTION** (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


(2) Soldering profile

● Flow Soldering profile
(Sn-3.0Ag-0.5Cu solder)



| Series | Pre-heating | | Standard Profile | | | Limit Profile | | |
|--------------------------------------|-------------|------------|------------------|------------|---------------|---------------|------------|---------------|
| | Temp. (T1) | Time. (t1) | Heating | | Cycle of flow | Heating | | Cycle of flow |
| | | | Temp. (T2) | Time. (t2) | | Temp. (T3) | Time. (t2) | |
| LQB18N LQM18N LQM21N LQH31M | 150°C | 60s min. | 250°C | 4 to 6s | 2 times max. | 265±3°C | 5s max. | 2 times max. |
| LQH32M LQH43M(N) | 150°C | 60s min. | 250°C | 4 to 6s | 2 times max. | 265±3°C | 5s max. | 1 times |

● Reflow Soldering profile
(Sn-3.0Ag-0.5Cu solder)



| Series | Standard Profile | | | | Limit Profile | | | |
|--|------------------|------------|-----------------------|-----------------|---------------|------------|-----------------------|-----------------|
| | Heating | | Peak temperature (T2) | Cycle of reflow | Heating | | Peak temperature (T4) | Cycle of reflow |
| | Temp. (T1) | Time. (t1) | | | Temp. (T3) | Time. (t2) | | |
| LQB15N LQB18N LQM18N LQM21N LQH31M LQH44N | 220°C | 30 to 60s | 245±3°C | 2 times max. | 230°C | 60s max. | 260°C/10s | 2 times max. |
| LQH32M LQH43M(N) | 220°C | 30 to 60s | 245±3°C | 2 times max. | 230°C | 60s max. | 260°C/10s | 1 time |

(3) Reworking with Soldering Iron

Preheating at 150°C for 1 minute is required. Do not directly touch the ceramic element with the tip of the soldering iron. The reworking soldering conditions are as follows:

Soldering iron power output: 80W max.
Temperature of soldering iron tip: 350°C
Diameter of soldering iron end: 3.0mm max.
Soldering time: within 3 s


Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

3. Mounting Instructions

(1) Land Pattern Dimensions

Large lands reduce Q of the mounted chip. Also, large protruding land areas (bordered by lines having dimensions 'c' and 'd' shown) cause floating and electrode leaching.




(2) Land Pattern Designing (LQH series)

Please follow the recommended patterns. Otherwise, their performance, which includes electrical performance or solderability, may be affected, or result in "position shift" in the soldering process.



(3) Magnetic Coupling

Since some chip inductors (chip coils) are constructed like an open magnetic circuit, narrow spacing between inductors (coils) may cause magnetic coupling. LQB/LQM series have a magnetically shielded structure. The structure makes their coupling coefficient smaller than that of conventional chip inductors (chip coils).



(4) PCB Warping


PCB should be designed so that products are not subjected to the mechanical stress caused by warping the board.



(5) Amount of Solder Paste

Excessive solder causes electrode corrosion, while insufficient solder causes low electrode bonding strength. Adjust the amount of solder paste as shown on the right so that solder is applied.

- Guideline of solder paste thickness
 - LQB/LQM: 100 to 150μm
 - LQHs except for ones written above: 200 to 300μm




Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

(6) Amount of Adhesive

If too much adhesive is applied, then it may overflow into the land or termination areas and yield poor solderability. In contrast, if insufficient adhesive is applied, or if the adhesive is not sufficiently hardened, then the chip may become detached during flow soldering. Apply the adhesive in accordance with the conditions shown in the chart.



| Part Number | Typical Application Amount (in:mg) |
|---------------|------------------------------------|
| | IR-100 |
| LQB18N/LQM18N | 0.06-0.07 |
| LQM21N | 0.20-0.25 |
| LQH31M | 0.20-0.25 |
| LQH32M | 0.27-0.35 |
| LQH43M(N) | 0.60-0.80 |

4. Cleaning

The following conditions should be observed when cleaning chip inductors (chip coils):


- (1) Cleaning Temperature: 60°C max. (40°C max. for alcohol cleaning agents)
- (2) Ultrasonic
 - Output: 20W/l max.
 - Duration: 5 minutes max.
 - Frequency: 28 to 40kHz
 - Care should be taken not to cause resonance of the PCB and mounted products.
- (3) Cleaning agent
 - The following cleaning agents have been tested on individual components. Evaluation in complete assembly should be done prior to production.
 - (a) Alcohol cleaning agents
 - Isopropyl alcohol (IPA)
 - (b) Aqueous cleaning agents
 - Pine Alpha ST-100S

- (4) Ensure that flux residue is completely removed. Component should be thoroughly dried after aqueous agents have been removed with deionized water.

For additional cleaning methods, please contact Murata.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Minimum Quantity and 8mm Width Taping Dimensions



Dimension of the cavity of embossed tape is measured at the bottom side.

Paper Tape


| Part Number | Dimensions | | Total Thickness of Tape | Packaging Code (Minimum Qty. [pcs.]) | | |
|--------------------------|------------|------|-------------------------|--------------------------------------|--------------------|--------------------|
| | a | b | | c | $\phi 180$ mm reel | $\phi 330$ mm reel |
| LQB15N | 1.15 | 0.65 | 0.8 max. | D [10000] | J [50000] | B [1000] |
| LQB18N | 1.05 | 1.85 | 1.1 max. | D [4000] | - | B [1000] |
| LQM21N (0.1-2.2 μ H) | 1.45 | 2.25 | 1.1 max. | D [4000] | J [10000] | B [1000] |
| LQM18N | 1.05 | 1.85 | 1.1 max. | D [4000] | J [10000] | B [1000] |

Embossed Tape

| Part Number | Dimensions | | Depth of Cavity | Packaging Code (Minimum Qty. [pcs.]) | | |
|--------------------------|------------|------|-----------------|--------------------------------------|--------------------|--------------------|
| | a | b | | c | $\phi 180$ mm reel | $\phi 330$ mm reel |
| LQM21N (2.7-4.7 μ H) | 1.45 | 2.25 | 1.3 | L [3000] | K [10000] | B [1000] |
| LQH31M | 1.9 | 3.6 | 2.0 | L [2000] | K [7500] | - |
| LQH32M | 2.9 | 3.6 | 2.1 | L [2000] | K [7500] | - |

(in mm)

■ Minimum Quantity and 12mm Width Embossed Taping Dimensions



Dimension of the cavity of embossed tape is measured at the bottom side.

Embossed Tape

| Part Number | Dimensions (*c: Depth of Cavity) | | | | Packaging Code (Minimum Qty. [pcs.]) | | |
|-------------|----------------------------------|-----|-----|-----|--------------------------------------|--------------------|------|
| | a | b | c | d | $\phi 180$ mm reel | $\phi 330$ mm reel | Bulk |
| LQH43M(N) | 3.6 | 4.9 | 2.7 | 0.3 | L [500] | K [2500] | - |
| LQH44N | 4.3 | 4.3 | 4.7 | 0.4 | L [250] | K [1500] | - |

(in mm)

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Holder Type



● EKLMMQ18B-KIT (for General Use Multilayer Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQM18NN47NM00 | 10 | 47nH | ±20% | 10 | 0.30 | 50 |
| 2 | LQM18NN68NM00 | 10 | 68nH | ±20% | 10 | 0.30 | 50 |
| 3 | LQM18NN82NM00 | 10 | 82nH | ±20% | 10 | 0.30 | 50 |
| 4 | LQM18NNR10K00 | 10 | 100nH | ±10% | 15 | 0.50 | 50 |
| 5 | LQM18NNR12K00 | 10 | 120nH | ±10% | 15 | 0.50 | 50 |
| 6 | LQM18NNR15K00 | 10 | 150nH | ±10% | 15 | 0.60 | 50 |
| 7 | LQM18NNR18K00 | 10 | 180nH | ±10% | 15 | 0.60 | 50 |
| 8 | LQM18NNR22K00 | 10 | 220nH | ±10% | 15 | 0.80 | 50 |
| 9 | LQM18NNR27K00 | 10 | 270nH | ±10% | 15 | 0.80 | 50 |
| 10 | LQM18NNR33K00 | 10 | 330nH | ±10% | 15 | 0.85 | 35 |
| 11 | LQM18NNR39K00 | 10 | 390nH | ±10% | 15 | 1.00 | 35 |
| 12 | LQM18NNR47K00 | 10 | 470nH | ±10% | 15 | 1.35 | 35 |
| 13 | LQM18NNR56K00 | 10 | 560nH | ±10% | 15 | 1.55 | 35 |
| 14 | LQM18NNR68K00 | 10 | 680nH | ±10% | 15 | 1.70 | 35 |
| 15 | LQM18NNR82K00 | 10 | 820nH | ±10% | 15 | 2.10 | 35 |
| 16 | LQM18NN1R0K00 | 10 | 1000nH | ±10% | 35 | 0.60 | 25 |
| 17 | LQM18NN1R2K00 | 10 | 1200nH | ±10% | 35 | 0.80 | 25 |
| 18 | LQM18NN1R5K00 | 10 | 1500nH | ±10% | 35 | 0.80 | 25 |
| 19 | LQM18NN1R8K00 | 10 | 1800nH | ±10% | 35 | 0.95 | 25 |
| 20 | LQM18NN2R2K00 | 10 | 2200nH | ±10% | 35 | 1.15 | 15 |

● EKLMM21NB-KIT (for General Use Multilayer Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQM21NNR10K10 | 10 | 0.1μH | ±10% | 20 | 0.26 | 250 |
| 2 | LQM21NNR12K10 | 10 | 0.12μH | ±10% | 20 | 0.29 | 250 |
| 3 | LQM21NNR15K10 | 10 | 0.15μH | ±10% | 20 | 0.32 | 250 |
| 4 | LQM21NNR18K10 | 10 | 0.18μH | ±10% | 20 | 0.35 | 250 |
| 5 | LQM21NNR22K10 | 10 | 0.22μH | ±10% | 20 | 0.38 | 250 |
| 6 | LQM21NNR27K10 | 10 | 0.27μH | ±10% | 20 | 0.42 | 250 |
| 7 | LQM21NNR33K10 | 10 | 0.33μH | ±10% | 20 | 0.48 | 250 |
| 8 | LQM21NNR39K10 | 10 | 0.39μH | ±10% | 25 | 0.53 | 200 |
| 9 | LQM21NNR47K10 | 10 | 0.47μH | ±10% | 25 | 0.57 | 200 |
| 10 | LQM21NNR56K10 | 10 | 0.56μH | ±10% | 25 | 0.63 | 150 |
| 11 | LQM21NNR68K10 | 10 | 0.68μH | ±10% | 25 | 0.72 | 150 |
| 12 | LQM21NNR82K10 | 10 | 0.82μH | ±10% | 25 | 0.81 | 150 |
| 13 | LQM21NN1R0K10 | 10 | 1.0μH | ±10% | 45 | 0.40 | 50 |
| 14 | LQM21NN1R2K10 | 10 | 1.2μH | ±10% | 45 | 0.47 | 50 |
| 15 | LQM21NN1R5K10 | 10 | 1.5μH | ±10% | 45 | 0.50 | 50 |
| 16 | LQM21NN1R8K10 | 10 | 1.8μH | ±10% | 45 | 0.57 | 50 |
| 17 | LQM21NN2R2K10 | 10 | 2.2μH | ±10% | 45 | 0.63 | 30 |
| 18 | LQM21NN2R7K10 | 10 | 2.7μH | ±10% | 45 | 0.69 | 30 |
| 19 | LQM21NN3R3K10 | 10 | 3.3μH | ±10% | 45 | 0.80 | 30 |
| 20 | LQM21NN3R9K10 | 10 | 3.9μH | ±10% | 45 | 0.89 | 30 |
| 21 | LQM21NN4R7K10 | 10 | 4.7μH | ±10% | 45 | 1.00 | 30 |

● EKLMMH32MC-KIT (for General Use Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | |
| 1 | LQH32MN1R0M23 | 10 | 1.0μH | ±20% | 0.50 | 445 |
| 2 | LQH32MN1R2M23 | 10 | 1.2μH | ±20% | 0.60 | 425 |
| 3 | LQH32MN1R5K23 | 10 | 1.5μH | ±10% | 0.60 | 400 |
| 4 | LQH32MN1R8K23 | 10 | 1.8μH | ±10% | 0.70 | 390 |
| 5 | LQH32MN2R2K23 | 10 | 2.2μH | ±10% | 0.80 | 370 |
| 6 | LQH32MN2R7K23 | 10 | 2.7μH | ±10% | 0.90 | 320 |

Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



Continued from the preceding page.


| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|-------------|------------|---------------------------------|--------------------|
| | | | Nominal | Tolerance | | |
| 7 | LQH32MN3R3K23 | 10 | 3.3 μ H | $\pm 10\%$ | 1.00 | 300 |
| 8 | LQH32MN3R9K23 | 10 | 3.9 μ H | $\pm 10\%$ | 1.10 | 290 |
| 9 | LQH32MN4R7K23 | 10 | 4.7 μ H | $\pm 10\%$ | 1.20 | 270 |
| 10 | LQH32MN5R6K23 | 10 | 5.6 μ H | $\pm 10\%$ | 1.30 | 250 |
| 11 | LQH32MN6R8K23 | 10 | 6.8 μ H | $\pm 10\%$ | 1.50 | 240 |
| 12 | LQH32MN8R2K23 | 10 | 8.2 μ H | $\pm 10\%$ | 1.60 | 225 |
| 13 | LQH32MN100K23 | 10 | 10 μ H | $\pm 10\%$ | 1.8 | 190 |
| 14 | LQH32MN120K23 | 10 | 12 μ H | $\pm 10\%$ | 2.0 | 180 |
| 15 | LQH32MN150K23 | 10 | 15 μ H | $\pm 10\%$ | 2.2 | 170 |
| 16 | LQH32MN180K23 | 10 | 18 μ H | $\pm 10\%$ | 2.5 | 165 |
| 17 | LQH32MN220K23 | 10 | 22 μ H | $\pm 10\%$ | 2.8 | 150 |
| 18 | LQH32MN270K23 | 10 | 27 μ H | $\pm 10\%$ | 3.1 | 125 |
| 19 | LQH32MN330K23 | 10 | 33 μ H | $\pm 10\%$ | 3.5 | 115 |
| 20 | LQH32MN390K23 | 10 | 39 μ H | $\pm 10\%$ | 3.9 | 110 |
| 21 | LQH32MN470K23 | 10 | 47 μ H | $\pm 10\%$ | 4.3 | 100 |
| 22 | LQH32MN560K23 | 10 | 56 μ H | $\pm 10\%$ | 4.9 | 85 |
| 23 | LQH32MN680K23 | 10 | 68 μ H | $\pm 10\%$ | 5.5 | 80 |
| 24 | LQH32MN820K23 | 10 | 82 μ H | $\pm 10\%$ | 6.2 | 70 |
| 25 | LQH32MN101K23 | 10 | 100 μ H | $\pm 10\%$ | 7.0 | 80 |
| 26 | LQH32MN121K23 | 10 | 120 μ H | $\pm 10\%$ | 8.0 | 75 |
| 27 | LQH32MN151K23 | 10 | 150 μ H | $\pm 10\%$ | 9.3 | 70 |
| 28 | LQH32MN181K23 | 10 | 180 μ H | $\pm 10\%$ | 10.2 | 65 |
| 29 | LQH32MN221K23 | 10 | 220 μ H | $\pm 10\%$ | 11.8 | 65 |
| 30 | LQH32MN271K23 | 10 | 270 μ H | $\pm 10\%$ | 12.5 | 65 |
| 31 | LQH32MN331K23 | 10 | 330 μ H | $\pm 10\%$ | 13.0 | 65 |
| 32 | LQH32MN391K23 | 10 | 390 μ H | $\pm 10\%$ | 22.0 | 50 |
| 33 | LQH32MN471K23 | 10 | 470 μ H | $\pm 10\%$ | 25.0 | 45 |
| 34 | LQH32MN561K23 | 10 | 560 μ H | $\pm 10\%$ | 28.0 | 40 |

●EKL43MB-KIT (for General Use Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|-------------|------------|---------------------------------|--------------------|
| | | | Nominal | Tolerance | | |
| 1 | LQH43MN1R0M03 | 10 | 1.0 μ H | $\pm 20\%$ | 0.20 | 500 |
| 2 | LQH43MN1R2M03 | 10 | 1.2 μ H | $\pm 20\%$ | 0.20 | 500 |
| 3 | LQH43MN1R5M03 | 10 | 1.5 μ H | $\pm 20\%$ | 0.30 | 500 |
| 4 | LQH43MN1R8M03 | 10 | 1.8 μ H | $\pm 20\%$ | 0.30 | 500 |
| 5 | LQH43MN2R2M03 | 10 | 2.2 μ H | $\pm 20\%$ | 0.30 | 500 |
| 6 | LQH43MN2R7M03 | 10 | 2.7 μ H | $\pm 20\%$ | 0.32 | 500 |
| 7 | LQH43MN3R3M03 | 10 | 3.3 μ H | $\pm 20\%$ | 0.35 | 500 |
| 8 | LQH43MN3R9M03 | 10 | 3.9 μ H | $\pm 20\%$ | 0.38 | 500 |
| 9 | LQH43MN4R7K03 | 10 | 4.7 μ H | $\pm 10\%$ | 0.40 | 500 |
| 10 | LQH43MN5R6K03 | 10 | 5.6 μ H | $\pm 10\%$ | 0.47 | 500 |
| 11 | LQH43MN6R8K03 | 10 | 6.8 μ H | $\pm 10\%$ | 0.50 | 450 |
| 12 | LQH43MN8R2K03 | 10 | 8.2 μ H | $\pm 10\%$ | 0.56 | 450 |
| 13 | LQH43MN100K03 | 10 | 10 μ H | $\pm 10\%$ | 0.56 | 400 |
| 14 | LQH43MN120K03 | 10 | 12 μ H | $\pm 10\%$ | 0.62 | 380 |
| 15 | LQH43MN150K03 | 10 | 15 μ H | $\pm 10\%$ | 0.73 | 360 |
| 16 | LQH43MN180K03 | 10 | 18 μ H | $\pm 10\%$ | 0.82 | 340 |
| 17 | LQH43MN220K03 | 10 | 22 μ H | $\pm 10\%$ | 0.94 | 320 |
| 18 | LQH43MN270K03 | 10 | 27 μ H | $\pm 10\%$ | 1.10 | 300 |
| 19 | LQH43MN330K03 | 10 | 33 μ H | $\pm 10\%$ | 1.20 | 270 |
| 20 | LQH43MN390K03 | 10 | 39 μ H | $\pm 10\%$ | 1.40 | 240 |
| 21 | LQH43MN470K03 | 10 | 47 μ H | $\pm 10\%$ | 1.50 | 220 |
| 22 | LQH43MN560K03 | 10 | 56 μ H | $\pm 10\%$ | 1.7 | 200 |
| 23 | LQH43MN680K03 | 10 | 68 μ H | $\pm 10\%$ | 1.9 | 180 |
| 24 | LQH43MN820K03 | 10 | 82 μ H | $\pm 10\%$ | 2.2 | 170 |
| 25 | LQH43MN101K03 | 10 | 100 μ H | $\pm 10\%$ | 2.5 | 160 |
| 26 | LQH43MN121K03 | 10 | 120 μ H | $\pm 10\%$ | 3.0 | 150 |
| 27 | LQH43MN151K03 | 10 | 150 μ H | $\pm 10\%$ | 3.7 | 130 |
| 28 | LQH43MN181K03 | 10 | 180 μ H | $\pm 10\%$ | 4.5 | 120 |
| 29 | LQH43MN221K03 | 10 | 220 μ H | $\pm 10\%$ | 5.4 | 110 |
| 30 | LQH43MN271K03 | 10 | 270 μ H | $\pm 10\%$ | 6.8 | 100 |
| 31 | LQH43MN331K03 | 10 | 330 μ H | $\pm 10\%$ | 8.2 | 95 |
| 32 | LQH43MN391K03 | 10 | 390 μ H | $\pm 10\%$ | 9.7 | 90 |
| 33 | LQH43MN471K03 | 10 | 470 μ H | $\pm 10\%$ | 11.8 | 80 |

Continued on the following page. 

 Note • Please read rating and  CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

 Continued from the preceding page.

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|--------------------|--------------|------------|------------------------------------|-----------------------|
| | | | Nominal | Tolerance | | |
| 34 | LQH43MN561K03 | 10 | 560 μ H | $\pm 10\%$ | 14.5 | 70 |
| 35 | LQH43MN681K03 | 10 | 680 μ H | $\pm 10\%$ | 17.0 | 65 |
| 36 | LQH43MN821K03 | 10 | 820 μ H | $\pm 10\%$ | 20.5 | 60 |
| 37 | LQH43MN102K03 | 10 | 1000 μ H | $\pm 10\%$ | 25.0 | 50 |
| 38 | LQH43MN122K03 | 10 | 1200 μ H | $\pm 10\%$ | 30.0 | 45 |
| 39 | LQH43MN152K03 | 10 | 1500 μ H | $\pm 10\%$ | 37.0 | 40 |
| 40 | LQH43NN182K03 | 10 | 1800 μ H | $\pm 10\%$ | 45.0 | 35 |
| 41 | LQH43NN222K03 | 10 | 2200 μ H | $\pm 10\%$ | 50.0 | 30 |


● RF Inductors

| | |
|------------------------------|-----|
| Introduction | 146 |
| Part Numbering | 147 |
| Product Detail | 148 |
| ⚠Caution/Notice | 225 |
| Soldering and Mounting | 227 |
| Packaging | 231 |
| Design Kits | 232 |

Introduction of RF Inductors

Applications of RF Inductors

LNA



For Matching

High Q or tight inductance tolerance is required to improve signal quality. Especially, film type is suitable at receiver circuit because tight tolerance is required.


- Recommended
- | | |
|-------------------------------------|-----------------|
| Film Type | Wire Wound Type |
| LQP03T Series (for miniaturization) | LQW15A Series |
| LQP15M Series | LQW18A Series |
| Multilayer Type | LQW18A Series |
| LQG15H Series | |

For RF Choke

Low DC resistance is required because of large operation current. Wire wound type or multilayer type is suitable.

- Recommended
- | |
|-----------------|
| Wire Wound Type |
| LQW15A Series |
| LQW18A Series |
| Multilayer Type |
| LQG15H Series |

IF SAW Filter




For Matching

High Q is required to reduce signal loss. Wire wound type and film type are suitable when tight tolerance is essential.

- Recommended
- | | |
|-----------------|-----------------|
| Wire Wound Type | Multilayer Type |
| LQW15A Series | LQG15H Series |
| LQW18A Series | |
| LQW2BH Series | |
| Film Type | |
| LQP03T Series | |
| LQP15M Series | |

VCO



For Matching

For Oscillator

High Q or tight inductance tolerance is required to stabilize oscillation and signal quality. Wire wound type is suitable for high Q, film type is suitable for tight tolerance.


- Recommended
- | | |
|-------------------------------------|-----------------------------|
| Wire Wound Type | Film Type |
| LQW15A Series | LQP03T Series |
| LQW18A Series | (for miniaturization) |
| LQW18A_10 Series | LQP15M Series |
| (for output efficiency improvement) | (for frequency selectivity) |
| | Multilayer Type |
| | LQG15H Series |

For RF Choke

Low DC resistance is required because of large operation current. Wire wound type or multilayer type is suitable.

- Recommended
- | |
|------------------|
| Wire Wound Type |
| LQW15A Series |
| LQW18A Series |
| LQW18A_10 Series |
| Multilayer Type |
| LQG15H Series |

PA



For Matching

Small shape is required. Film type is suitable because of its tight inductance tolerance and fine inductance step.


- Recommended
- | | |
|---|-------------------------------------|
| Film Type | Wire Wound Type |
| LQP02T Series | LQW15A Series |
| LQP03T Series (for miniaturization) | LQW18A Series |
| LQP15M Series (for frequency selectivity) | LQW18A_10 Series |
| Multilayer Type | LQW2BH Series |
| LQG15H Series | (for output efficiency improvement) |

For RF Choke

Low DC resistance is required because of large operation current. Especially, wire wound type is suitable for GSM because over 1A of current is working.

- Recommended
- | | |
|-------------------------------------|-----------------|
| Wire Wound Type | Multilayer Type |
| LQW15A Series | LQG15H Series |
| LQW18A Series | |
| LQW18A_10 Series | |
| LQW2BH Series | |
| (for output efficiency improvement) | |

ANTENNA




For Matching

LQW series is suitable for attaining high antenna sensitivity because of its high Q and tight tolerance spec.

- Recommended
- | |
|-----------------|
| Wire Wound Type |
| LQW15A Series |
| LQW18A Series |

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

RF Inductors Part Numbering



① Product ID

| Product ID | |
|------------|-----------------------------|
| LQ | Chip Inductors (Chip Coils) |

② Structure

| Code | Structure |
|------|--|
| G | Multilayer Type (Air-core Inductors (Coils)) |
| H | Wire Wound Type (Ferrite Core) |
| P | Film Type |
| W | Wire Wound Type (Air-core Inductors (Coils)) |
| | Wire Wound Type (Ferrite Core) |

③ Dimensions (L×W)

| Code | Dimensions (L×W) | Size Code (in inch) |
|------|------------------|---------------------|
| 02 | 0.4×0.2mm | 01005 |
| 03 | 0.6×0.3mm | 0201 |
| 04 | 0.8×0.4mm | 03015 |
| 15 | 1.0×0.5mm | 0402 |
| 18 | 1.6×0.8mm | 0603 |
| 21 | 2.0×1.25mm | 0805 |
| 2B | 2.0×1.5mm | 0805 |
| 2U | 2.5×2.0mm | 1008 |
| 31 | 3.2×1.6mm | 1206 |

④ Applications and Characteristics

| Code | Series | Applications and Characteristics |
|------|--------|---------------------------------------|
| H | LQG | Multilayer Air-core Inductors (Coils) |
| M | LQP | Film Type |
| T | | Film Type (Low DC Resistance Type) |
| A | LQW | High Q Type (UHF-SHF) |
| H | | High Q Type (VHF-UHF) |
| H | LQH | for High-frequency Resonant Circuit |

⑤ Category

| Code | Category |
|------|----------------------|
| G/N | Standard Type |
| S | |
| Q | High Q Type |
| W | Specialty Dimensions |

⑩ Packaging

| Code | Packaging | Series |
|------|-------------------------------|--------------------------|
| K | Embossed Taping (ø330mm Reel) | LQH/LQW□□H*2 |
| L | Embossed Taping (ø180mm Reel) | LQH/LQW2BA/LQW2UA/LQW□□H |
| B | Bulk | LQW/LQG/LQP |
| J | Paper Taping (ø330mm Reel) | LQW18A/LQG/LQP*1 |
| D | Paper Taping (ø180mm Reel) | LQW□□A*3 /LQG/LQP |

*1 Except for LQP02T

*2 Except for LQW21H

*3 Except for LQW2BA/LQW2UA

⑥ Inductance

Expressed by three-digit alphanumeric. The unit is micro-henry (μH). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two figures. If there is a decimal point, it is expressed by the capital letter "R." In this case, all figures are significant digits. If inductance is less than 0.1μH, the inductance code is expressed by a combination of two figures and the capital letter "N," and the unit of inductance is nano-henry (nH).

The capital letter "N" indicates the unit of "nH," and also expresses a decimal point. In this case, all figures are significant digits.

⑦ Inductance Tolerance

| Code | Inductance Tolerance |
|------|----------------------|
| B | ±0.1nH |
| C | ±0.2nH |
| D | ±0.5nH |
| G | ±2% |
| H | ±3% |
| J | ±5% |
| K | ±10% |
| S | ±0.3nH |
| W | ±0.05nH |

⑧ Features

| Code | Features | Series |
|------|--|-------------------|
| 0 | Standard Type | LQG/LQP/LQW/LQH*1 |
| 1 | High-Q/Low DC Resistance | LQW15A/18A/2BH |
| 8 | Low DC Resistance, Large Rated Current | LQW15A/LQW18A |

*1 Except for LQH32 Series

⑨ Electrode


•Lead (Pb) Free

| Code | Electrode | Series |
|------|-----------|------------------------------------|
| 0 | Sn | LQG18H/LQW□□A/LQW□□C |
| 2 | | LQG15H/LQP02T/LQP03T/LQP15T/LQP□□M |
| 3 | LF Solder | LQW□□H/LQH |

LQG15HN_02 Series 0402/1005 (inch/mm)

Size Code 0402 (1005) in inch (in mm), Multilayer Type

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 10000 |
| J | ø330mm Paper Taping | 50000 |
| B | Packing in Bulk | 1000 |



Refer to pages 227 to 230 for mounting information.

Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|
| LQG15HN1N0S02□ | 1.0nH ±0.3nH | 100MHz | 300mA | 0.10 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN1N1S02□ | 1.1nH ±0.3nH | 100MHz | 300mA | 0.10 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN1N2S02□ | 1.2nH ±0.3nH | 100MHz | 300mA | 0.10 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN1N3S02□ | 1.3nH ±0.3nH | 100MHz | 300mA | 0.10 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN1N5S02□ | 1.5nH ±0.3nH | 100MHz | 300mA | 0.10 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN1N6S02□ | 1.6nH ±0.3nH | 100MHz | 300mA | 0.10 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN1N8S02□ | 1.8nH ±0.3nH | 100MHz | 300mA | 0.10 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN2N0S02□ | 2.0nH ±0.3nH | 100MHz | 300mA | 0.12 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN2N2S02□ | 2.2nH ±0.3nH | 100MHz | 300mA | 0.15 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN2N4S02□ | 2.4nH ±0.3nH | 100MHz | 300mA | 0.16 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN2N7S02□ | 2.7nH ±0.3nH | 100MHz | 300mA | 0.17 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN3N0S02□ | 3.0nH ±0.3nH | 100MHz | 300mA | 0.18 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN3N3S02□ | 3.3nH ±0.3nH | 100MHz | 300mA | 0.19 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN3N6S02□ | 3.6nH ±0.3nH | 100MHz | 300mA | 0.19 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN3N9S02□ | 3.9nH ±0.3nH | 100MHz | 300mA | 0.19 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN4N3S02□ | 4.3nH ±0.3nH | 100MHz | 300mA | 0.21 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN4N7S02□ | 4.7nH ±0.3nH | 100MHz | 300mA | 0.23 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN5N1S02□ | 5.1nH ±0.3nH | 100MHz | 300mA | 0.24 Ω | 8 | 100MHz | 6000MHz |
| LQG15HN5N6S02□ | 5.6nH ±0.3nH | 100MHz | 300mA | 0.26 Ω | 8 | 100MHz | 5300MHz |
| LQG15HN6N2S02□ | 6.2nH ±0.3nH | 100MHz | 300mA | 0.27 Ω | 8 | 100MHz | 4300MHz |
| LQG15HN6N8J02□ | 6.8nH ±5% | 100MHz | 300mA | 0.29 Ω | 8 | 100MHz | 4200MHz |
| LQG15HN7N5J02□ | 7.5nH ±5% | 100MHz | 300mA | 0.31 Ω | 8 | 100MHz | 3900MHz |
| LQG15HN8N2J02□ | 8.2nH ±5% | 100MHz | 300mA | 0.33 Ω | 8 | 100MHz | 3600MHz |
| LQG15HN9N1J02□ | 9.1nH ±5% | 100MHz | 300mA | 0.34 Ω | 8 | 100MHz | 3400MHz |
| LQG15HN10NJ02□ | 10nH ±5% | 100MHz | 300mA | 0.35 Ω | 8 | 100MHz | 3200MHz |
| LQG15HN12NJ02□ | 12nH ±5% | 100MHz | 300mA | 0.41 Ω | 8 | 100MHz | 2800MHz |
| LQG15HN15NJ02□ | 15nH ±5% | 100MHz | 300mA | 0.46 Ω | 8 | 100MHz | 2300MHz |
| LQG15HN18NJ02□ | 18nH ±5% | 100MHz | 300mA | 0.51 Ω | 8 | 100MHz | 2100MHz |
| LQG15HN22NJ02□ | 22nH ±5% | 100MHz | 300mA | 0.58 Ω | 8 | 100MHz | 1800MHz |
| LQG15HN27NJ02□ | 27nH ±5% | 100MHz | 300mA | 0.67 Ω | 8 | 100MHz | 1600MHz |
| LQG15HN33NJ02□ | 33nH ±5% | 100MHz | 200mA | 0.67 Ω | 8 | 100MHz | 1500MHz |
| LQG15HN39NJ02□ | 39nH ±5% | 100MHz | 200mA | 1.06 Ω | 8 | 100MHz | 1200MHz |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.


Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|
| LQG15HN47NJ02□ | 47nH ±5% | 100MHz | 200mA | 1.15 Ω | 8 | 100MHz | 1000MHz |
| LQG15HN56NJ02□ | 56nH ±5% | 100MHz | 200mA | 1.20 Ω | 8 | 100MHz | 800MHz |
| LQG15HN68NJ02□ | 68nH ±5% | 100MHz | 180mA | 1.25 Ω | 8 | 100MHz | 800MHz |
| LQG15HN82NJ02□ | 82nH ±5% | 100MHz | 150mA | 1.60 Ω | 8 | 100MHz | 600MHz |
| LQG15HNR10J02□ | 100nH ±5% | 100MHz | 150mA | 1.60 Ω | 8 | 100MHz | 600MHz |
| LQG15HNR12J02□ | 120nH ±5% | 100MHz | 150mA | 1.60 Ω | 8 | 100MHz | 600MHz |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
 For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQG15HS_02 Series 0402/1005 (inch/mm)

Designed under Industrial Global Standard

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 10000 |
| J | ø330mm Paper Taping | 50000 |
| B | Packing in Bulk | 1000 |



Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQG15HS1N0S02□ | 1.0nH ±0.3nH | 100MHz | 300mA | 0.07Ω | 8 | 100MHz | 10000MHz | Kit |
| LQG15HS1N1S02□ | 1.1nH ±0.3nH | 100MHz | 300mA | 0.09Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS1N2S02□ | 1.2nH ±0.3nH | 100MHz | 300mA | 0.09Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS1N3S02□ | 1.3nH ±0.3nH | 100MHz | 300mA | 0.09Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS1N5S02□ | 1.5nH ±0.3nH | 100MHz | 300mA | 0.10Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS1N6S02□ | 1.6nH ±0.3nH | 100MHz | 300mA | 0.10Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS1N8S02□ | 1.8nH ±0.3nH | 100MHz | 300mA | 0.10Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS2N0S02□ | 2.0nH ±0.3nH | 100MHz | 300mA | 0.10Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS2N2S02□ | 2.2nH ±0.3nH | 100MHz | 300mA | 0.12Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS2N4S02□ | 2.4nH ±0.3nH | 100MHz | 300mA | 0.15Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS2N7S02□ | 2.7nH ±0.3nH | 100MHz | 300mA | 0.15Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS3N0S02□ | 3.0nH ±0.3nH | 100MHz | 300mA | 0.17Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS3N3S02□ | 3.3nH ±0.3nH | 100MHz | 300mA | 0.17Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS3N6S02□ | 3.6nH ±0.3nH | 100MHz | 300mA | 0.18Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS3N9S02□ | 3.9nH ±0.3nH | 100MHz | 300mA | 0.18Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS4N3S02□ | 4.3nH ±0.3nH | 100MHz | 300mA | 0.18Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS4N7S02□ | 4.7nH ±0.3nH | 100MHz | 300mA | 0.18Ω | 8 | 100MHz | 6000MHz | Kit |
| LQG15HS5N1S02□ | 5.1nH ±0.3nH | 100MHz | 300mA | 0.20Ω | 8 | 100MHz | 5300MHz | Kit |
| LQG15HS5N6S02□ | 5.6nH ±0.3nH | 100MHz | 300mA | 0.20Ω | 8 | 100MHz | 4500MHz | Kit |
| LQG15HS6N2S02□ | 6.2nH ±0.3nH | 100MHz | 300mA | 0.22Ω | 8 | 100MHz | 4500MHz | Kit |
| LQG15HS6N8J02□ | 6.8nH ±5% | 100MHz | 300mA | 0.24Ω | 8 | 100MHz | 4500MHz | Kit |
| LQG15HS7N5J02□ | 7.5nH ±5% | 100MHz | 300mA | 0.24Ω | 8 | 100MHz | 4200MHz | Kit |
| LQG15HS8N2J02□ | 8.2nH ±5% | 100MHz | 300mA | 0.24Ω | 8 | 100MHz | 3700MHz | Kit |
| LQG15HS9N1J02□ | 9.1nH ±5% | 100MHz | 300mA | 0.26Ω | 8 | 100MHz | 3400MHz | Kit |
| LQG15HS10NJ02□ | 10nH ±5% | 100MHz | 300mA | 0.26Ω | 8 | 100MHz | 3400MHz | Kit |
| LQG15HS12NJ02□ | 12nH ±5% | 100MHz | 300mA | 0.28Ω | 8 | 100MHz | 3000MHz | Kit |
| LQG15HS15NJ02□ | 15nH ±5% | 100MHz | 300mA | 0.32Ω | 8 | 100MHz | 2500MHz | Kit |
| LQG15HS18NJ02□ | 18nH ±5% | 100MHz | 300mA | 0.36Ω | 8 | 100MHz | 2200MHz | Kit |
| LQG15HS22NJ02□ | 22nH ±5% | 100MHz | 300mA | 0.42Ω | 8 | 100MHz | 1900MHz | Kit |
| LQG15HS27NJ02□ | 27nH ±5% | 100MHz | 300mA | 0.46Ω | 8 | 100MHz | 1700MHz | Kit |
| LQG15HS33NJ02□ | 33nH ±5% | 100MHz | 200mA | 0.58Ω | 8 | 100MHz | 1600MHz | Kit |
| LQG15HS39NJ02□ | 39nH ±5% | 100MHz | 200mA | 0.65Ω | 8 | 100MHz | 1200MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.


Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQG15HS47NJ02□ | 47nH ±5% | 100MHz | 200mA | 0.72Ω | 8 | 100MHz | 1000MHz | Kit |
| LQG15HS56NJ02□ | 56nH ±5% | 100MHz | 200mA | 0.82Ω | 8 | 100MHz | 800MHz | Kit |
| LQG15HS68NJ02□ | 68nH ±5% | 100MHz | 180mA | 0.92Ω | 8 | 100MHz | 800MHz | Kit |
| LQG15HS82NJ02□ | 82nH ±5% | 100MHz | 150mA | 1.20Ω | 8 | 100MHz | 700MHz | Kit |
| LQG15HSR10J02□ | 100nH ±5% | 100MHz | 150mA | 1.25Ω | 8 | 100MHz | 600MHz | Kit |
| LQG15HSR12J02□ | 120nH ±5% | 100MHz | 150mA | 1.30Ω | 8 | 100MHz | 600MHz | Kit |
| LQG15HSR15J02□ | 150nH ±5% | 100MHz | 140mA | 2.99Ω | 8 | 100MHz | 550MHz | Kit |
| LQG15HSR18J02□ | 180nH ±5% | 100MHz | 130mA | 3.38Ω | 8 | 100MHz | 500MHz | Kit |
| LQG15HSR22J02□ | 220nH ±5% | 100MHz | 120mA | 3.77Ω | 8 | 100MHz | 450MHz | Kit |
| LQG15HSR27J02□ | 270nH ±5% | 100MHz | 110mA | 4.94Ω | 8 | 100MHz | 400MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Reference Data

4991A&16196D


| Part Number | Q (Typ.) | | | | |
|---------------|----------|--------|--------|--------|--------|
| | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQG15HS1N0□02 | 32 | 34 | 49 | 52 | 55 |
| LQG15HS1N1□02 | 24 | 26 | 41 | 43 | 47 |
| LQG15HS1N2□02 | 29 | 31 | 47 | 49 | 53 |
| LQG15HS1N3□02 | 35 | 37 | 51 | 53 | 54 |
| LQG15HS1N5□02 | 31 | 32 | 46 | 49 | 51 |
| LQG15HS1N6□02 | 31 | 33 | 48 | 50 | 52 |
| LQG15HS1N8□02 | 31 | 33 | 47 | 48 | 50 |
| LQG15HS2N0□02 | 33 | 35 | 47 | 48 | 49 |
| LQG15HS2N2□02 | 29 | 31 | 44 | 45 | 46 |
| LQG15HS2N4□02 | 28 | 29 | 42 | 44 | 47 |
| LQG15HS2N7□02 | 29 | 30 | 43 | 44 | 47 |
| LQG15HS3N0□02 | 28 | 30 | 42 | 44 | 47 |
| LQG15HS3N3□02 | 29 | 31 | 42 | 43 | 44 |
| LQG15HS3N6□02 | 28 | 29 | 42 | 43 | 46 |
| LQG15HS3N9□02 | 28 | 29 | 40 | 41 | 44 |
| LQG15HS4N3□02 | 27 | 29 | 39 | 40 | 42 |
| LQG15HS4N7□02 | 28 | 29 | 39 | 40 | 41 |
| LQG15HS5N1□02 | 28 | 30 | 39 | 40 | 41 |
| LQG15HS5N6□02 | 28 | 29 | 36 | 36 | 35 |
| LQG15HS6N2□02 | 26 | 28 | 36 | 36 | 36 |
| LQG15HS6N8□02 | 26 | 28 | 36 | 36 | 35 |
| LQG15HS7N5□02 | 27 | 28 | 35 | 35 | 33 |
| LQG15HS8N2□02 | 27 | 28 | 33 | 32 | 29 |
| LQG15HS9N1□02 | 26 | 27 | 33 | 32 | 29 |
| LQG15HS10N□02 | 26 | 28 | 33 | 32 | 29 |
| LQG15HS12N□02 | 25 | 26 | 26 | 24 | 17 |
| LQG15HS15N□02 | 24 | 25 | 22 | 19 | 11 |
| LQG15HS18N□02 | 24 | 25 | 21 | 18 | - |
| LQG15HS22N□02 | 23 | 24 | 17 | - | - |
| LQG15HS27N□02 | 21 | 21 | - | - | - |
| LQG15HS33N□02 | 20 | 20 | - | - | - |
| LQG15HS39N□02 | 19 | 19 | - | - | - |
| LQG15HS47N□02 | 17 | 16 | - | - | - |
| LQG15HS56N□02 | 15 | 13 | - | - | - |
| LQG15HS68N□02 | 12 | 10 | - | - | - |
| LQG15HS82N□02 | 9 | 6 | - | - | - |
| LQG15HSR10□02 | - | - | - | - | - |
| LQG15HSR12□02 | - | - | - | - | - |

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQG18HN_00 Series 0603/1608 (inch/mm)

Size Code 0603 (1608) in inch (in mm), Multilayer Type

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| J | ø330mm Paper Taping | 10000 |
| B | Packing in Bulk | 1000 |



Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQG18HN1N2S00□ | 1.2nH ±0.3nH | 100MHz | 500mA | 0.10Ω | 12 | 100MHz | 6000MHz | Kit |
| LQG18HN1N5S00□ | 1.5nH ±0.3nH | 100MHz | 500mA | 0.10Ω | 12 | 100MHz | 6000MHz | Kit |
| LQG18HN1N8S00□ | 1.8nH ±0.3nH | 100MHz | 500mA | 0.10Ω | 12 | 100MHz | 6000MHz | Kit |
| LQG18HN2N2S00□ | 2.2nH ±0.3nH | 100MHz | 500mA | 0.10Ω | 12 | 100MHz | 6000MHz | Kit |
| LQG18HN2N7S00□ | 2.7nH ±0.3nH | 100MHz | 500mA | 0.15Ω | 12 | 100MHz | 6000MHz | Kit |
| LQG18HN3N3S00□ | 3.3nH ±0.3nH | 100MHz | 500mA | 0.15Ω | 12 | 100MHz | 6000MHz | Kit |
| LQG18HN3N9S00□ | 3.9nH ±0.3nH | 100MHz | 450mA | 0.15Ω | 12 | 100MHz | 6000MHz | Kit |
| LQG18HN4N7S00□ | 4.7nH ±0.3nH | 100MHz | 450mA | 0.20Ω | 12 | 100MHz | 6000MHz | Kit |
| LQG18HN5N6S00□ | 5.6nH ±0.3nH | 100MHz | 430mA | 0.20Ω | 12 | 100MHz | 5000MHz | Kit |
| LQG18HN6N8J00□ | 6.8nH ±5% | 100MHz | 430mA | 0.25Ω | 12 | 100MHz | 5000MHz | Kit |
| LQG18HN8N2J00□ | 8.2nH ±5% | 100MHz | 400mA | 0.25Ω | 12 | 100MHz | 4000MHz | Kit |
| LQG18HN10NJ00□ | 10nH ±5% | 100MHz | 400mA | 0.30Ω | 12 | 100MHz | 3500MHz | Kit |
| LQG18HN12NJ00□ | 12nH ±5% | 100MHz | 400mA | 0.35Ω | 12 | 100MHz | 3000MHz | Kit |
| LQG18HN15NJ00□ | 15nH ±5% | 100MHz | 350mA | 0.40Ω | 12 | 100MHz | 2800MHz | Kit |
| LQG18HN18NJ00□ | 18nH ±5% | 100MHz | 350mA | 0.45Ω | 12 | 100MHz | 2600MHz | Kit |
| LQG18HN22NJ00□ | 22nH ±5% | 100MHz | 300mA | 0.50Ω | 12 | 100MHz | 2300MHz | Kit |
| LQG18HN27NJ00□ | 27nH ±5% | 100MHz | 300mA | 0.55Ω | 12 | 100MHz | 2000MHz | Kit |
| LQG18HN33NJ00□ | 33nH ±5% | 100MHz | 300mA | 0.60Ω | 12 | 100MHz | 1700MHz | Kit |
| LQG18HN39NJ00□ | 39nH ±5% | 100MHz | 300mA | 0.65Ω | 12 | 100MHz | 1500MHz | Kit |
| LQG18HN47NJ00□ | 47nH ±5% | 100MHz | 300mA | 0.70Ω | 12 | 100MHz | 1200MHz | Kit |
| LQG18HN56NJ00□ | 56nH ±5% | 100MHz | 300mA | 0.75Ω | 12 | 100MHz | 1100MHz | Kit |
| LQG18HN68NJ00□ | 68nH ±5% | 100MHz | 300mA | 0.80Ω | 12 | 100MHz | 1000MHz | Kit |
| LQG18HN82NJ00□ | 82nH ±5% | 100MHz | 300mA | 0.85Ω | 12 | 100MHz | 900MHz | Kit |
| LQG18HNR10J00□ | 100nH ±5% | 100MHz | 300mA | 0.90Ω | 12 | 100MHz | 800MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C
For reflow soldering only.


Continued on the following page. ↗

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQP02TN_02 Series 01005/0402 (inch/mm)

Size Code 01005 (0402) in inch (in mm)

■ Appearance/ Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 20000 |
| B | Packing in Bulk | 500 |



Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQP02TN0N2B02□ | 0.2nH ±0.1nH | 500MHz | 320mA | 0.50Ω | - | - | 20000MHz | Kit |
| LQP02TN0N2C02□ | 0.2nH ±0.2nH | 500MHz | 320mA | 0.50Ω | - | - | 20000MHz | |
| LQP02TN0N3B02□ | 0.3nH ±0.1nH | 500MHz | 320mA | 0.50Ω | - | - | 20000MHz | Kit |
| LQP02TN0N3C02□ | 0.3nH ±0.2nH | 500MHz | 320mA | 0.50Ω | - | - | 20000MHz | |
| LQP02TN0N4B02□ | 0.4nH ±0.1nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 18000MHz | Kit |
| LQP02TN0N4C02□ | 0.4nH ±0.2nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 18000MHz | |
| LQP02TN0N4S02□ | 0.4nH ±0.3nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 18000MHz | |
| LQP02TN0N5B02□ | 0.5nH ±0.1nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 18000MHz | Kit |
| LQP02TN0N5C02□ | 0.5nH ±0.2nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 18000MHz | |
| LQP02TN0N5S02□ | 0.5nH ±0.3nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 18000MHz | |
| LQP02TN0N6B02□ | 0.6nH ±0.1nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 17000MHz | Kit |
| LQP02TN0N6C02□ | 0.6nH ±0.2nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 17000MHz | |
| LQP02TN0N6S02□ | 0.6nH ±0.3nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 17000MHz | |
| LQP02TN0N7B02□ | 0.7nH ±0.1nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 16500MHz | Kit |
| LQP02TN0N7C02□ | 0.7nH ±0.2nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 16500MHz | |
| LQP02TN0N7S02□ | 0.7nH ±0.3nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 16500MHz | |
| LQP02TN0N8B02□ | 0.8nH ±0.1nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 16500MHz | Kit |
| LQP02TN0N8C02□ | 0.8nH ±0.2nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 16500MHz | |
| LQP02TN0N8S02□ | 0.8nH ±0.3nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 16500MHz | |
| LQP02TN0N9B02□ | 0.9nH ±0.1nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 13000MHz | Kit |
| LQP02TN0N9C02□ | 0.9nH ±0.2nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 13000MHz | |
| LQP02TN0N9S02□ | 0.9nH ±0.3nH | 500MHz | 320mA | 0.50Ω | 8 | 500MHz | 13000MHz | |
| LQP02TN1N0B02□ | 1.0nH ±0.1nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 13000MHz | Kit |
| LQP02TN1N0C02□ | 1.0nH ±0.2nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 13000MHz | |
| LQP02TN1N0S02□ | 1.0nH ±0.3nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 13000MHz | |
| LQP02TN1N1B02□ | 1.1nH ±0.1nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 12500MHz | Kit |
| LQP02TN1N1C02□ | 1.1nH ±0.2nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 12500MHz | |
| LQP02TN1N1S02□ | 1.1nH ±0.3nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 12500MHz | |
| LQP02TN1N2B02□ | 1.2nH ±0.1nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 12500MHz | Kit |
| LQP02TN1N2C02□ | 1.2nH ±0.2nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 12500MHz | |
| LQP02TN1N2S02□ | 1.2nH ±0.3nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 12500MHz | |
| LQP02TN1N3B02□ | 1.3nH ±0.1nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 11500MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQP02TN1N3C02□ | 1.3nH ±0.2nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 11500MHz | |
| LQP02TN1N3S02□ | 1.3nH ±0.3nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 11500MHz | |
| LQP02TN1N4B02□ | 1.4nH ±0.1nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 11500MHz | Kit |
| LQP02TN1N4C02□ | 1.4nH ±0.2nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 11500MHz | |
| LQP02TN1N4S02□ | 1.4nH ±0.3nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 11500MHz | |
| LQP02TN1N5B02□ | 1.5nH ±0.1nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 9500MHz | Kit |
| LQP02TN1N5C02□ | 1.5nH ±0.2nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 9500MHz | |
| LQP02TN1N5S02□ | 1.5nH ±0.3nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 9500MHz | |
| LQP02TN1N6B02□ | 1.6nH ±0.1nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 9500MHz | Kit |
| LQP02TN1N6C02□ | 1.6nH ±0.2nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 9500MHz | |
| LQP02TN1N6S02□ | 1.6nH ±0.3nH | 500MHz | 220mA | 0.60Ω | 8 | 500MHz | 9500MHz | |
| LQP02TN1N7B02□ | 1.7nH ±0.1nH | 500MHz | 200mA | 0.70Ω | 8 | 500MHz | 9500MHz | Kit |
| LQP02TN1N7C02□ | 1.7nH ±0.2nH | 500MHz | 200mA | 0.70Ω | 8 | 500MHz | 9500MHz | |
| LQP02TN1N7S02□ | 1.7nH ±0.3nH | 500MHz | 200mA | 0.70Ω | 8 | 500MHz | 9500MHz | |
| LQP02TN1N8B02□ | 1.8nH ±0.1nH | 500MHz | 200mA | 0.70Ω | 8 | 500MHz | 9000MHz | Kit |
| LQP02TN1N8C02□ | 1.8nH ±0.2nH | 500MHz | 200mA | 0.70Ω | 8 | 500MHz | 9000MHz | |
| LQP02TN1N8S02□ | 1.8nH ±0.3nH | 500MHz | 200mA | 0.70Ω | 8 | 500MHz | 9000MHz | |
| LQP02TN1N9B02□ | 1.9nH ±0.1nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 9000MHz | Kit |
| LQP02TN1N9C02□ | 1.9nH ±0.2nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 9000MHz | |
| LQP02TN1N9S02□ | 1.9nH ±0.3nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 9000MHz | |
| LQP02TN2N0B02□ | 2.0nH ±0.1nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 9000MHz | Kit |
| LQP02TN2N0C02□ | 2.0nH ±0.2nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 9000MHz | |
| LQP02TN2N0S02□ | 2.0nH ±0.3nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 9000MHz | |
| LQP02TN2N1B02□ | 2.1nH ±0.1nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 9000MHz | Kit |
| LQP02TN2N1C02□ | 2.1nH ±0.2nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 9000MHz | |
| LQP02TN2N1S02□ | 2.1nH ±0.3nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 9000MHz | |
| LQP02TN2N2B02□ | 2.2nH ±0.1nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN2N2C02□ | 2.2nH ±0.2nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN2N2S02□ | 2.2nH ±0.3nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN2N3B02□ | 2.3nH ±0.1nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN2N3C02□ | 2.3nH ±0.2nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN2N3S02□ | 2.3nH ±0.3nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN2N4B02□ | 2.4nH ±0.1nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN2N4C02□ | 2.4nH ±0.2nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN2N4S02□ | 2.4nH ±0.3nH | 500MHz | 200mA | 0.75Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN2N5B02□ | 2.5nH ±0.1nH | 500MHz | 200mA | 0.80Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN2N5C02□ | 2.5nH ±0.2nH | 500MHz | 200mA | 0.80Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN2N5S02□ | 2.5nH ±0.3nH | 500MHz | 200mA | 0.80Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN2N6B02□ | 2.6nH ±0.1nH | 500MHz | 200mA | 0.80Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN2N6C02□ | 2.6nH ±0.2nH | 500MHz | 200mA | 0.80Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN2N6S02□ | 2.6nH ±0.3nH | 500MHz | 200mA | 0.80Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN2N7B02□ | 2.7nH ±0.1nH | 500MHz | 200mA | 0.80Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN2N7C02□ | 2.7nH ±0.2nH | 500MHz | 200mA | 0.80Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN2N7S02□ | 2.7nH ±0.3nH | 500MHz | 200mA | 0.80Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN2N8B02□ | 2.8nH ±0.1nH | 500MHz | 200mA | 1.10Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN2N8C02□ | 2.8nH ±0.2nH | 500MHz | 200mA | 1.10Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN2N8S02□ | 2.8nH ±0.3nH | 500MHz | 200mA | 1.10Ω | 8 | 500MHz | 7500MHz | |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.


Continued on the following page. 

 Note • Please read rating and  CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

O05E.pdf
Nov.25,2013

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQP02TN2N9B02□ | 2.9nH ±0.1nH | 500MHz | 200mA | 1.10Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN2N9C02□ | 2.9nH ±0.2nH | 500MHz | 200mA | 1.10Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN2N9S02□ | 2.9nH ±0.3nH | 500MHz | 200mA | 1.10Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N0B02□ | 3.0nH ±0.1nH | 500MHz | 200mA | 1.10Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN3N0C02□ | 3.0nH ±0.2nH | 500MHz | 200mA | 1.10Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N0S02□ | 3.0nH ±0.3nH | 500MHz | 200mA | 1.10Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N1B02□ | 3.1nH ±0.1nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN3N1C02□ | 3.1nH ±0.2nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N1S02□ | 3.1nH ±0.3nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N2B02□ | 3.2nH ±0.1nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN3N2C02□ | 3.2nH ±0.2nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N2S02□ | 3.2nH ±0.3nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N3B02□ | 3.3nH ±0.1nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN3N3C02□ | 3.3nH ±0.2nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N3S02□ | 3.3nH ±0.3nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N4B02□ | 3.4nH ±0.1nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN3N4C02□ | 3.4nH ±0.2nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N4S02□ | 3.4nH ±0.3nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N5B02□ | 3.5nH ±0.1nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN3N5C02□ | 3.5nH ±0.2nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N5S02□ | 3.5nH ±0.3nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N6B02□ | 3.6nH ±0.1nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN3N6C02□ | 3.6nH ±0.2nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N6S02□ | 3.6nH ±0.3nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N7B02□ | 3.7nH ±0.1nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN3N7C02□ | 3.7nH ±0.2nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N7S02□ | 3.7nH ±0.3nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N8B02□ | 3.8nH ±0.1nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN3N8C02□ | 3.8nH ±0.2nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N8S02□ | 3.8nH ±0.3nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N9B02□ | 3.9nH ±0.1nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN3N9C02□ | 3.9nH ±0.2nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN3N9S02□ | 3.9nH ±0.3nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN4N0B02□ | 4.0nH ±0.1nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN4N0C02□ | 4.0nH ±0.2nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN4N0S02□ | 4.0nH ±0.3nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN4N1B02□ | 4.1nH ±0.1nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | Kit |
| LQP02TN4N1C02□ | 4.1nH ±0.2nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN4N1S02□ | 4.1nH ±0.3nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7500MHz | |
| LQP02TN4N2B02□ | 4.2nH ±0.1nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7000MHz | Kit |
| LQP02TN4N2C02□ | 4.2nH ±0.2nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7000MHz | |
| LQP02TN4N2S02□ | 4.2nH ±0.3nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7000MHz | |
| LQP02TN4N3H02□ | 4.3nH ±3% | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7000MHz | Kit |
| LQP02TN4N3J02□ | 4.3nH ±5% | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7000MHz | |
| LQP02TN4N3S02□ | 4.3nH ±0.3nH | 500MHz | 180mA | 1.30Ω | 8 | 500MHz | 7000MHz | |
| LQP02TN4N7H02□ | 4.7nH ±3% | 500MHz | 160mA | 1.50Ω | 8 | 500MHz | 6500MHz | Kit |
| LQP02TN4N7J02□ | 4.7nH ±5% | 500MHz | 160mA | 1.50Ω | 8 | 500MHz | 6500MHz | |


Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

Continued on the following page. 

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQP02TN4N7S02□ | 4.7nH ±0.3nH | 500MHz | 160mA | 1.50Ω | 8 | 500MHz | 6500MHz | |
| LQP02TN5N1H02□ | 5.1nH ±3% | 500MHz | 160mA | 1.50Ω | 8 | 500MHz | 6500MHz | Kit |
| LQP02TN5N1J02□ | 5.1nH ±5% | 500MHz | 160mA | 1.50Ω | 8 | 500MHz | 6500MHz | |
| LQP02TN5N1S02□ | 5.1nH ±0.3nH | 500MHz | 160mA | 1.50Ω | 8 | 500MHz | 6500MHz | |
| LQP02TN5N6H02□ | 5.6nH ±3% | 500MHz | 140mA | 1.80Ω | 8 | 500MHz | 6000MHz | Kit |
| LQP02TN5N6J02□ | 5.6nH ±5% | 500MHz | 140mA | 1.80Ω | 8 | 500MHz | 6000MHz | |
| LQP02TN5N6S02□ | 5.6nH ±0.3nH | 500MHz | 140mA | 1.80Ω | 8 | 500MHz | 6000MHz | |
| LQP02TN6N2H02□ | 6.2nH ±3% | 500MHz | 140mA | 1.80Ω | 8 | 500MHz | 5500MHz | Kit |
| LQP02TN6N2J02□ | 6.2nH ±5% | 500MHz | 140mA | 1.80Ω | 8 | 500MHz | 5500MHz | |
| LQP02TN6N8H02□ | 6.8nH ±3% | 500MHz | 140mA | 2.00Ω | 8 | 500MHz | 5500MHz | Kit |
| LQP02TN6N8J02□ | 6.8nH ±5% | 500MHz | 140mA | 2.00Ω | 8 | 500MHz | 5500MHz | |
| LQP02TN7N5H02□ | 7.5nH ±3% | 500MHz | 140mA | 2.00Ω | 8 | 500MHz | 4500MHz | Kit |
| LQP02TN7N5J02□ | 7.5nH ±5% | 500MHz | 140mA | 2.00Ω | 8 | 500MHz | 4500MHz | |
| LQP02TN8N2H02□ | 8.2nH ±3% | 500MHz | 140mA | 2.10Ω | 8 | 500MHz | 4500MHz | Kit |
| LQP02TN8N2J02□ | 8.2nH ±5% | 500MHz | 140mA | 2.10Ω | 8 | 500MHz | 4500MHz | |
| LQP02TN9N1H02□ | 9.1nH ±3% | 500MHz | 140mA | 2.10Ω | 8 | 500MHz | 4000MHz | Kit |
| LQP02TN9N1J02□ | 9.1nH ±5% | 500MHz | 140mA | 2.10Ω | 8 | 500MHz | 4000MHz | |
| LQP02TN10NH02□ | 10nH ±3% | 500MHz | 140mA | 2.50Ω | 8 | 500MHz | 4000MHz | Kit |
| LQP02TN10NJ02□ | 10nH ±5% | 500MHz | 140mA | 2.50Ω | 8 | 500MHz | 4000MHz | |
| LQP02TN11NH02□ | 11nH ±3% | 500MHz | 140mA | 2.80Ω | 7 | 500MHz | 3500MHz | Kit |
| LQP02TN11NJ02□ | 11nH ±5% | 500MHz | 140mA | 2.80Ω | 7 | 500MHz | 3500MHz | |
| LQP02TN12NH02□ | 12nH ±3% | 500MHz | 140mA | 2.80Ω | 7 | 500MHz | 3500MHz | Kit |
| LQP02TN12NJ02□ | 12nH ±5% | 500MHz | 140mA | 2.80Ω | 7 | 500MHz | 3500MHz | |
| LQP02TN13NH02□ | 13nH ±3% | 500MHz | 140mA | 3.20Ω | 7 | 500MHz | 3000MHz | Kit |
| LQP02TN13NJ02□ | 13nH ±5% | 500MHz | 140mA | 3.20Ω | 7 | 500MHz | 3000MHz | |
| LQP02TN15NH02□ | 15nH ±3% | 500MHz | 140mA | 3.20Ω | 7 | 500MHz | 3000MHz | Kit |
| LQP02TN15NJ02□ | 15nH ±5% | 500MHz | 140mA | 3.20Ω | 7 | 500MHz | 3000MHz | |
| LQP02TN16NH02□ | 16nH ±3% | 500MHz | 140mA | 3.50Ω | 7 | 500MHz | 2500MHz | Kit |
| LQP02TN16NJ02□ | 16nH ±5% | 500MHz | 140mA | 3.50Ω | 7 | 500MHz | 2500MHz | |
| LQP02TN18NH02□ | 18nH ±3% | 500MHz | 140mA | 3.50Ω | 7 | 500MHz | 2500MHz | Kit |
| LQP02TN18NJ02□ | 18nH ±5% | 500MHz | 140mA | 3.50Ω | 7 | 500MHz | 2500MHz | |
| LQP02TN20NH02□ | 20nH ±3% | 500MHz | 120mA | 5.00Ω | 6 | 500MHz | 2300MHz | Kit |
| LQP02TN20NJ02□ | 20nH ±5% | 500MHz | 120mA | 5.00Ω | 6 | 500MHz | 2300MHz | |
| LQP02TN22NH02□ | 22nH ±3% | 500MHz | 120mA | 5.00Ω | 6 | 500MHz | 2300MHz | New |
| LQP02TN22NJ02□ | 22nH ±5% | 500MHz | 120mA | 5.00Ω | 6 | 500MHz | 2300MHz | New |
| LQP02TN24NH02□ | 24nH ±3% | 500MHz | 120mA | 5.50Ω | 6 | 500MHz | 2000MHz | New |
| LQP02TN24NJ02□ | 24nH ±5% | 500MHz | 120mA | 5.50Ω | 6 | 500MHz | 2000MHz | New |
| LQP02TN27NH02□ | 27nH ±3% | 500MHz | 120mA | 5.50Ω | 6 | 500MHz | 2000MHz | New |
| LQP02TN27NJ02□ | 27nH ±5% | 500MHz | 120mA | 5.50Ω | 6 | 500MHz | 2000MHz | New |
| LQP02TN30NH02□ | 30nH ±3% | 500MHz | 90mA | 6.50Ω | 6 | 500MHz | 1800MHz | New |
| LQP02TN30NJ02□ | 30nH ±5% | 500MHz | 90mA | 6.50Ω | 6 | 500MHz | 1800MHz | New |
| LQP02TN33NH02□ | 33nH ±3% | 300MHz | 90mA | 6.50Ω | 4 | 300MHz | 1800MHz | New |
| LQP02TN33NJ02□ | 33nH ±5% | 300MHz | 90mA | 6.50Ω | 4 | 300MHz | 1800MHz | New |
| LQP02TN36NH02□ | 36nH ±3% | 300MHz | 90mA | 7.00Ω | 4 | 300MHz | 1600MHz | New |
| LQP02TN36NJ02□ | 36nH ±5% | 300MHz | 90mA | 7.00Ω | 4 | 300MHz | 1600MHz | New |
| LQP02TN39NH02□ | 39nH ±3% | 300MHz | 90mA | 7.00Ω | 4 | 300MHz | 1600MHz | New |
| LQP02TN39NJ02□ | 39nH ±5% | 300MHz | 90mA | 7.00Ω | 4 | 300MHz | 1600MHz | New |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.


Continued on the following page. 

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



■ Reference Data

4991A&16196D

| Part Number | Q (Typ.) | | | | |
|---------------|----------|--------|--------|--------|--------|
| | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQP02TN0N2□02 | 20 | 40 | 69 | 65 | 74 |
| LQP02TN0N3□02 | 21 | 24 | 37 | 38 | 43 |
| LQP02TN0N4□02 | 13 | 14 | 22 | 24 | 26 |
| LQP02TN0N5□02 | 13 | 14 | 23 | 24 | 27 |
| LQP02TN0N6□02 | 15 | 16 | 25 | 26 | 32 |
| LQP02TN0N7□02 | 14 | 15 | 23 | 24 | 27 |
| LQP02TN0N8□02 | 14 | 15 | 22 | 24 | 27 |
| LQP02TN0N9□02 | 15 | 16 | 23 | 25 | 29 |
| LQP02TN1N0□02 | 13 | 14 | 21 | 23 | 26 |
| LQP02TN1N1□02 | 14 | 15 | 23 | 25 | 28 |
| LQP02TN1N2□02 | 14 | 15 | 22 | 23 | 26 |
| LQP02TN1N3□02 | 14 | 15 | 23 | 24 | 27 |
| LQP02TN1N4□02 | 14 | 15 | 23 | 24 | 27 |
| LQP02TN1N5□02 | 13 | 14 | 21 | 23 | 25 |
| LQP02TN1N6□02 | 14 | 15 | 22 | 24 | 26 |
| LQP02TN1N7□02 | 13 | 14 | 21 | 23 | 25 |
| LQP02TN1N8□02 | 14 | 15 | 22 | 23 | 26 |
| LQP02TN1N9□02 | 14 | 15 | 22 | 23 | 26 |
| LQP02TN2N0□02 | 14 | 15 | 22 | 24 | 26 |
| LQP02TN2N1□02 | 14 | 15 | 22 | 23 | 25 |
| LQP02TN2N2□02 | 13 | 14 | 20 | 21 | 23 |
| LQP02TN2N3□02 | 13 | 14 | 21 | 22 | 24 |
| LQP02TN2N4□02 | 13 | 14 | 21 | 22 | 24 |
| LQP02TN2N5□02 | 14 | 14 | 21 | 22 | 23 |
| LQP02TN2N6□02 | 14 | 15 | 22 | 23 | 25 |
| LQP02TN2N7□02 | 14 | 14 | 22 | 23 | 25 |
| LQP02TN2N8□02 | 11 | 12 | 18 | 19 | 21 |
| LQP02TN2N9□02 | 13 | 14 | 20 | 21 | 23 |
| LQP02TN3N0□02 | 13 | 14 | 20 | 22 | 23 |
| LQP02TN3N1□02 | 12 | 13 | 20 | 21 | 23 |
| LQP02TN3N2□02 | 13 | 13 | 20 | 21 | 23 |
| LQP02TN3N3□02 | 14 | 14 | 21 | 22 | 24 |
| LQP02TN3N4□02 | 13 | 14 | 20 | 22 | 23 |

Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Q (Typ.) | | | | |
|---------------|----------|--------|--------|--------|--------|
| | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQP02TN3N5□02 | 13 | 14 | 20 | 22 | 23 |
| LQP02TN3N6□02 | 13 | 14 | 21 | 22 | 24 |
| LQP02TN3N7□02 | 13 | 14 | 21 | 22 | 23 |
| LQP02TN3N8□02 | 13 | 14 | 20 | 21 | 23 |
| LQP02TN3N9□02 | 13 | 14 | 20 | 22 | 23 |
| LQP02TN4N0□02 | 13 | 14 | 20 | 21 | 23 |
| LQP02TN4N1□02 | 13 | 14 | 20 | 21 | 23 |
| LQP02TN4N2□02 | 14 | 14 | 20 | 22 | 23 |
| LQP02TN4N3□02 | 13 | 14 | 21 | 22 | 24 |
| LQP02TN4N7□02 | 13 | 14 | 20 | 21 | 23 |
| LQP02TN5N1□02 | 14 | 15 | 21 | 22 | 24 |
| LQP02TN5N6□02 | 14 | 14 | 20 | 22 | 23 |
| LQP02TN6N2□02 | 13 | 14 | 20 | 21 | 22 |
| LQP02TN6N8□02 | 13 | 14 | 20 | 21 | 22 |
| LQP02TN7N5□02 | 14 | 15 | 21 | 22 | 23 |
| LQP02TN8N2□02 | 13 | 14 | 20 | 20 | 22 |
| LQP02TN9N1□02 | 13 | 14 | 18 | 19 | 19 |
| LQP02TN10N□02 | 14 | 14 | 19 | 20 | 20 |
| LQP02TN11N□02 | 14 | 14 | 18 | 18 | 17 |
| LQP02TN12N□02 | 14 | 15 | 18 | 18 | 18 |
| LQP02TN13N□02 | 14 | 15 | 19 | 19 | 18 |
| LQP02TN15N□02 | 15 | 15 | 18 | 18 | 16 |
| LQP02TN16N□02 | 13 | 13 | 15 | 14 | 12 |
| LQP02TN18N□02 | 12 | 13 | 14 | 13 | 11 |
| LQP02TN20N□02 | 10 | 11 | 11 | 10 | 7 |
| LQP02TN22N□02 | 10 | 10 | 10 | 9 | 7 |
| LQP02TN24N□02 | 10 | 10 | 10 | 9 | 6 |
| LQP02TN27N□02 | 10 | 10 | 8 | 7 | 3 |
| LQP02TN30N□02 | 9 | 9 | 7 | 6 | - |
| LQP02TN33N□02 | 10 | 10 | 7 | 5 | - |
| LQP02TN36N□02 | 8 | 9 | 6 | 4 | - |
| LQP02TN39N□02 | 8 | 9 | 4 | 2 | - |

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQP02TQ_02 Series 01005/0402 (inch/mm)

Size Code 01005 (0402) in inch (in mm), Largest Q

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 20000 |
| B | Packing in Bulk | 500 |



Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQP02TQ0N4B02□ | 0.4nH ±0.1nH | 500MHz | 990mA | 0.1Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ0N4C02□ | 0.4nH ±0.2nH | 500MHz | 990mA | 0.1Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ0N5B02□ | 0.5nH ±0.1nH | 500MHz | 730mA | 0.1Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ0N5C02□ | 0.5nH ±0.2nH | 500MHz | 730mA | 0.1Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ0N6B02□ | 0.6nH ±0.1nH | 500MHz | 730mA | 0.1Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ0N6C02□ | 0.6nH ±0.2nH | 500MHz | 730mA | 0.1Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ0N7B02□ | 0.7nH ±0.1nH | 500MHz | 630mA | 0.15Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ0N7C02□ | 0.7nH ±0.2nH | 500MHz | 630mA | 0.15Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ0N8B02□ | 0.8nH ±0.1nH | 500MHz | 630mA | 0.15Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ0N8C02□ | 0.8nH ±0.2nH | 500MHz | 630mA | 0.15Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ0N9B02□ | 0.9nH ±0.1nH | 500MHz | 580mA | 0.15Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ0N9C02□ | 0.9nH ±0.2nH | 500MHz | 580mA | 0.15Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ1N0B02□ | 1.0nH ±0.1nH | 500MHz | 580mA | 0.15Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ1N0C02□ | 1.0nH ±0.2nH | 500MHz | 580mA | 0.15Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ1N1B02□ | 1.1nH ±0.1nH | 500MHz | 570mA | 0.2Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ1N1C02□ | 1.1nH ±0.2nH | 500MHz | 570mA | 0.2Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ1N2B02□ | 1.2nH ±0.1nH | 500MHz | 550mA | 0.2Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ1N2C02□ | 1.2nH ±0.2nH | 500MHz | 550mA | 0.2Ω | 10 | 500MHz | 16600MHz | New |
| LQP02TQ1N3B02□ | 1.3nH ±0.1nH | 500MHz | 400mA | 0.2Ω | 10 | 500MHz | 15000MHz | New |
| LQP02TQ1N3C02□ | 1.3nH ±0.2nH | 500MHz | 400mA | 0.2Ω | 10 | 500MHz | 15000MHz | New |
| LQP02TQ1N5B02□ | 1.5nH ±0.1nH | 500MHz | 400mA | 0.2Ω | 10 | 500MHz | 15000MHz | New |
| LQP02TQ1N5C02□ | 1.5nH ±0.2nH | 500MHz | 400mA | 0.2Ω | 10 | 500MHz | 15000MHz | New |
| LQP02TQ1N6B02□ | 1.6nH ±0.1nH | 500MHz | 390mA | 0.3Ω | 10 | 500MHz | 15000MHz | New |
| LQP02TQ1N6C02□ | 1.6nH ±0.2nH | 500MHz | 390mA | 0.3Ω | 10 | 500MHz | 15000MHz | New |
| LQP02TQ1N8B02□ | 1.8nH ±0.1nH | 500MHz | 380mA | 0.3Ω | 10 | 500MHz | 15000MHz | New |
| LQP02TQ1N8C02□ | 1.8nH ±0.2nH | 500MHz | 380mA | 0.3Ω | 10 | 500MHz | 15000MHz | New |
| LQP02TQ2N0B02□ | 2.0nH ±0.1nH | 500MHz | 380mA | 0.3Ω | 10 | 500MHz | 13000MHz | New |
| LQP02TQ2N0C02□ | 2.0nH ±0.2nH | 500MHz | 380mA | 0.3Ω | 10 | 500MHz | 13000MHz | New |
| LQP02TQ2N2B02□ | 2.2nH ±0.1nH | 500MHz | 380mA | 0.3Ω | 10 | 500MHz | 13000MHz | New |
| LQP02TQ2N2C02□ | 2.2nH ±0.2nH | 500MHz | 380mA | 0.3Ω | 10 | 500MHz | 13000MHz | New |
| LQP02TQ2N4B02□ | 2.4nH ±0.1nH | 500MHz | 370mA | 0.4Ω | 10 | 500MHz | 13000MHz | New |
| LQP02TQ2N4C02□ | 2.4nH ±0.2nH | 500MHz | 370mA | 0.4Ω | 10 | 500MHz | 13000MHz | New |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.


Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQP02TQ2N7B02□ | 2.7nH ±0.1nH | 500MHz | 370mA | 0.4Ω | 10 | 500MHz | 11500MHz | New |
| LQP02TQ2N7C02□ | 2.7nH ±0.2nH | 500MHz | 370mA | 0.4Ω | 10 | 500MHz | 11500MHz | New |
| LQP02TQ3N0B02□ | 3.0nH ±0.1nH | 500MHz | 360mA | 0.45Ω | 10 | 500MHz | 10000MHz | New |
| LQP02TQ3N0C02□ | 3.0nH ±0.2nH | 500MHz | 360mA | 0.45Ω | 10 | 500MHz | 10000MHz | New |
| LQP02TQ3N3B02□ | 3.3nH ±0.1nH | 500MHz | 290mA | 0.9Ω | 10 | 500MHz | 10000MHz | New |
| LQP02TQ3N3C02□ | 3.3nH ±0.2nH | 500MHz | 290mA | 0.9Ω | 10 | 500MHz | 10000MHz | New |
| LQP02TQ3N6B02□ | 3.6nH ±0.1nH | 500MHz | 280mA | 1Ω | 10 | 500MHz | 9700MHz | New |
| LQP02TQ3N6C02□ | 3.6nH ±0.2nH | 500MHz | 280mA | 1Ω | 10 | 500MHz | 9700MHz | New |
| LQP02TQ3N9B02□ | 3.9nH ±0.1nH | 500MHz | 270mA | 1Ω | 10 | 500MHz | 9000MHz | New |
| LQP02TQ3N9C02□ | 3.9nH ±0.2nH | 500MHz | 270mA | 1Ω | 10 | 500MHz | 9000MHz | New |
| LQP02TQ4N3H02□ | 4.3nH ±3% | 500MHz | 270mA | 1Ω | 10 | 500MHz | 9000MHz | New |
| LQP02TQ4N3J02□ | 4.3nH ±5% | 500MHz | 270mA | 1Ω | 10 | 500MHz | 9000MHz | New |
| LQP02TQ4N7H02□ | 4.7nH ±3% | 500MHz | 270mA | 1Ω | 10 | 500MHz | 8500MHz | New |
| LQP02TQ4N7J02□ | 4.7nH ±5% | 500MHz | 270mA | 1Ω | 10 | 500MHz | 8500MHz | New |
| LQP02TQ5N1H02□ | 5.1nH ±3% | 500MHz | 250mA | 1.2Ω | 10 | 500MHz | 7800MHz | New |
| LQP02TQ5N1J02□ | 5.1nH ±5% | 500MHz | 250mA | 1.2Ω | 10 | 500MHz | 7800MHz | New |
| LQP02TQ5N6H02□ | 5.6nH ±3% | 500MHz | 230mA | 1.3Ω | 10 | 500MHz | 7800MHz | New |
| LQP02TQ5N6J02□ | 5.6nH ±5% | 500MHz | 230mA | 1.3Ω | 10 | 500MHz | 7800MHz | New |
| LQP02TQ6N2H02□ | 6.2nH ±3% | 500MHz | 220mA | 1.3Ω | 10 | 500MHz | 7200MHz | New |
| LQP02TQ6N2J02□ | 6.2nH ±5% | 500MHz | 220mA | 1.3Ω | 10 | 500MHz | 7200MHz | New |
| LQP02TQ6N8H02□ | 6.8nH ±3% | 500MHz | 210mA | 1.4Ω | 10 | 500MHz | 6600MHz | New |
| LQP02TQ6N8J02□ | 6.8nH ±5% | 500MHz | 210mA | 1.4Ω | 10 | 500MHz | 6600MHz | New |
| LQP02TQ7N5H02□ | 7.5nH ±3% | 500MHz | 200mA | 1.5Ω | 10 | 500MHz | 6600MHz | New |
| LQP02TQ7N5J02□ | 7.5nH ±5% | 500MHz | 200mA | 1.5Ω | 10 | 500MHz | 6600MHz | New |
| LQP02TQ8N2H02□ | 8.2nH ±3% | 500MHz | 190mA | 1.6Ω | 10 | 500MHz | 6600MHz | New |
| LQP02TQ8N2J02□ | 8.2nH ±5% | 500MHz | 190mA | 1.6Ω | 10 | 500MHz | 6600MHz | New |
| LQP02TQ9N1H02□ | 9.1nH ±3% | 500MHz | 170mA | 1.7Ω | 10 | 500MHz | 5900MHz | New |
| LQP02TQ9N1J02□ | 9.1nH ±5% | 500MHz | 170mA | 1.7Ω | 10 | 500MHz | 5900MHz | New |
| LQP02TQ10NH02□ | 10nH ±3% | 500MHz | 170mA | 1.7Ω | 10 | 500MHz | 5500MHz | New |
| LQP02TQ10NJ02□ | 10nH ±5% | 500MHz | 170mA | 1.7Ω | 10 | 500MHz | 5500MHz | New |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Reference Data

4991A+16196D

| Part Number | Q (Typ.) | | | | |
|-------------|----------|--------|--------|--------|--------|
| | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQP02TQ0N4 | 27 | 28 | 43 | 45 | 50 |
| LQP02TQ0N5 | 18 | 20 | 32 | 34 | 39 |
| LQP02TQ0N6 | 19 | 21 | 36 | 38 | 43 |
| LQP02TQ0N7 | 19 | 21 | 35 | 37 | 42 |
| LQP02TQ0N8 | 20 | 21 | 32 | 34 | 38 |
| LQP02TQ0N9 | 19 | 20 | 33 | 34 | 38 |
| LQP02TQ1N0 | 19 | 20 | 31 | 32 | 37 |
| LQP02TQ1N1 | 19 | 21 | 31 | 32 | 36 |
| LQP02TQ1N2 | 20 | 21 | 31 | 32 | 37 |
| LQP02TQ1N3 | 18 | 19 | 29 | 30 | 34 |
| LQP02TQ1N5 | 18 | 19 | 29 | 30 | 34 |
| LQP02TQ1N6 | 18 | 19 | 29 | 31 | 36 |
| LQP02TQ1N8 | 18 | 20 | 29 | 30 | 35 |
| LQP02TQ2N0 | 18 | 20 | 29 | 31 | 34 |
| LQP02TQ2N2 | 20 | 21 | 31 | 33 | 38 |
| LQP02TQ2N4 | 20 | 21 | 31 | 33 | 38 |
| LQP02TQ2N7 | 19 | 20 | 30 | 32 | 37 |
| LQP02TQ3N0 | 19 | 20 | 30 | 32 | 36 |
| LQP02TQ3N3 | 17 | 18 | 27 | 29 | 33 |
| LQP02TQ3N6 | 17 | 18 | 27 | 29 | 32 |
| LQP02TQ3N9 | 17 | 18 | 26 | 28 | 31 |
| LQP02TQ4N3 | 17 | 18 | 27 | 29 | 32 |
| LQP02TQ4N7 | 18 | 19 | 28 | 29 | 32 |
| LQP02TQ5N1 | 18 | 19 | 27 | 29 | 32 |
| LQP02TQ5N6 | 18 | 19 | 28 | 29 | 32 |
| LQP02TQ6N2 | 18 | 19 | 27 | 29 | 31 |
| LQP02TQ6N8 | 18 | 19 | 27 | 28 | 30 |
| LQP02TQ7N5 | 18 | 19 | 28 | 29 | 32 |
| LQP02TQ8N2 | 19 | 20 | 28 | 30 | 32 |
| LQP02TQ9N1 | 18 | 19 | 27 | 28 | 30 |
| LQP02TQ10N | 18 | 19 | 27 | 28 | 29 |

Inductors for Power Lines

Inductors for General Use


Film Type (Non-Magnetic Core)
RF Inductors

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQP03TG_02 Series 0201/0603 (inch/mm)

Size Code 0201 (0603) in inch (in mm), Standard Type

Appearance/Dimensions



(in mm)

Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 15000 |
| J | ø330mm Paper Taping | 50000 |
| B | Packing in Bulk | 500 |



Refer to pages 227 to 230 for mounting information.

Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQP03TG0N6B02□ | 0.6nH ±0.1nH | 500MHz | 850mA | 0.08Ω | 11 | 500MHz | 18000MHz | Kit |
| LQP03TG0N6C02□ | 0.6nH ±0.2nH | 500MHz | 850mA | 0.08Ω | 11 | 500MHz | 18000MHz | |
| LQP03TG0N7B02□ | 0.7nH ±0.1nH | 500MHz | 750mA | 0.10Ω | 12 | 500MHz | 18000MHz | Kit |
| LQP03TG0N7C02□ | 0.7nH ±0.2nH | 500MHz | 750mA | 0.10Ω | 12 | 500MHz | 18000MHz | |
| LQP03TG0N8B02□ | 0.8nH ±0.1nH | 500MHz | 750mA | 0.10Ω | 12 | 500MHz | 18000MHz | Kit |
| LQP03TG0N8C02□ | 0.8nH ±0.2nH | 500MHz | 750mA | 0.10Ω | 12 | 500MHz | 18000MHz | |
| LQP03TG0N9B02□ | 0.9nH ±0.1nH | 500MHz | 700mA | 0.12Ω | 12 | 500MHz | 18000MHz | Kit |
| LQP03TG0N9C02□ | 0.9nH ±0.2nH | 500MHz | 700mA | 0.12Ω | 12 | 500MHz | 18000MHz | |
| LQP03TG1N0B02□ | 1.0nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 12 | 500MHz | 17000MHz | Kit |
| LQP03TG1N0C02□ | 1.0nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 12 | 500MHz | 17000MHz | |
| LQP03TG1N1B02□ | 1.1nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 12 | 500MHz | 17000MHz | Kit |
| LQP03TG1N1C02□ | 1.1nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 12 | 500MHz | 17000MHz | |
| LQP03TG1N2B02□ | 1.2nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 13 | 500MHz | 15000MHz | Kit |
| LQP03TG1N2C02□ | 1.2nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 13 | 500MHz | 15000MHz | |
| LQP03TG1N3B02□ | 1.3nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 13 | 500MHz | 15000MHz | Kit |
| LQP03TG1N3C02□ | 1.3nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 13 | 500MHz | 15000MHz | |
| LQP03TG1N4B02□ | 1.4nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 13 | 500MHz | 14000MHz | Kit |
| LQP03TG1N4C02□ | 1.4nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 13 | 500MHz | 14000MHz | |
| LQP03TG1N5B02□ | 1.5nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 13 | 500MHz | 13500MHz | Kit |
| LQP03TG1N5C02□ | 1.5nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 13 | 500MHz | 13500MHz | |
| LQP03TG1N6B02□ | 1.6nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 13 | 500MHz | 13000MHz | Kit |
| LQP03TG1N6C02□ | 1.6nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 13 | 500MHz | 13000MHz | |
| LQP03TG1N7B02□ | 1.7nH ±0.1nH | 500MHz | 500mA | 0.20Ω | 13 | 500MHz | 12500MHz | Kit |
| LQP03TG1N7C02□ | 1.7nH ±0.2nH | 500MHz | 500mA | 0.20Ω | 13 | 500MHz | 12500MHz | |
| LQP03TG1N8B02□ | 1.8nH ±0.1nH | 500MHz | 500mA | 0.20Ω | 13 | 500MHz | 12500MHz | Kit |
| LQP03TG1N8C02□ | 1.8nH ±0.2nH | 500MHz | 500mA | 0.20Ω | 13 | 500MHz | 12500MHz | |
| LQP03TG1N9B02□ | 1.9nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 12500MHz | Kit |
| LQP03TG1N9C02□ | 1.9nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 12500MHz | |
| LQP03TG2N0B02□ | 2.0nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 12500MHz | Kit |
| LQP03TG2N0C02□ | 2.0nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 12500MHz | |
| LQP03TG2N1B02□ | 2.1nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 12000MHz | Kit |
| LQP03TG2N1C02□ | 2.1nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 12000MHz | |


Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQP03TG2N2B02□ | 2.2nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 12000MHz | Kit |
| LQP03TG2N2C02□ | 2.2nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 12000MHz | |
| LQP03TG2N3B02□ | 2.3nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 11500MHz | Kit |
| LQP03TG2N3C02□ | 2.3nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 11500MHz | |
| LQP03TG2N4B02□ | 2.4nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 11000MHz | Kit |
| LQP03TG2N4C02□ | 2.4nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 11000MHz | |
| LQP03TG2N5B02□ | 2.5nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 11000MHz | Kit |
| LQP03TG2N5C02□ | 2.5nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 11000MHz | |
| LQP03TG2N6B02□ | 2.6nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 11000MHz | Kit |
| LQP03TG2N6C02□ | 2.6nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 11000MHz | |
| LQP03TG2N7B02□ | 2.7nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 11000MHz | Kit |
| LQP03TG2N7C02□ | 2.7nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 11000MHz | |
| LQP03TG2N8B02□ | 2.8nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 9500MHz | Kit |
| LQP03TG2N8C02□ | 2.8nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 9500MHz | |
| LQP03TG2N9B02□ | 2.9nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 9500MHz | Kit |
| LQP03TG2N9C02□ | 2.9nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 9500MHz | |
| LQP03TG3N0B02□ | 3.0nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 9500MHz | Kit |
| LQP03TG3N0C02□ | 3.0nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 13 | 500MHz | 9500MHz | |
| LQP03TG3N1B02□ | 3.1nH ±0.1nH | 500MHz | 400mA | 0.32Ω | 13 | 500MHz | 9500MHz | Kit |
| LQP03TG3N1C02□ | 3.1nH ±0.2nH | 500MHz | 400mA | 0.32Ω | 13 | 500MHz | 9500MHz | |
| LQP03TG3N2B02□ | 3.2nH ±0.1nH | 500MHz | 400mA | 0.32Ω | 13 | 500MHz | 9500MHz | Kit |
| LQP03TG3N2C02□ | 3.2nH ±0.2nH | 500MHz | 400mA | 0.32Ω | 13 | 500MHz | 9500MHz | |
| LQP03TG3N3B02□ | 3.3nH ±0.1nH | 500MHz | 400mA | 0.32Ω | 13 | 500MHz | 9500MHz | Kit |
| LQP03TG3N3C02□ | 3.3nH ±0.2nH | 500MHz | 400mA | 0.32Ω | 13 | 500MHz | 9500MHz | |
| LQP03TG3N4B02□ | 3.4nH ±0.1nH | 500MHz | 350mA | 0.35Ω | 13 | 500MHz | 8000MHz | Kit |
| LQP03TG3N4C02□ | 3.4nH ±0.2nH | 500MHz | 350mA | 0.35Ω | 13 | 500MHz | 8000MHz | |
| LQP03TG3N5B02□ | 3.5nH ±0.1nH | 500MHz | 350mA | 0.35Ω | 13 | 500MHz | 8000MHz | Kit |
| LQP03TG3N5C02□ | 3.5nH ±0.2nH | 500MHz | 350mA | 0.35Ω | 13 | 500MHz | 8000MHz | |
| LQP03TG3N6B02□ | 3.6nH ±0.1nH | 500MHz | 350mA | 0.35Ω | 13 | 500MHz | 8000MHz | Kit |
| LQP03TG3N6C02□ | 3.6nH ±0.2nH | 500MHz | 350mA | 0.35Ω | 13 | 500MHz | 8000MHz | |
| LQP03TG3N7B02□ | 3.7nH ±0.1nH | 500MHz | 350mA | 0.35Ω | 13 | 500MHz | 7000MHz | Kit |
| LQP03TG3N7C02□ | 3.7nH ±0.2nH | 500MHz | 350mA | 0.35Ω | 13 | 500MHz | 7000MHz | |
| LQP03TG3N8B02□ | 3.8nH ±0.1nH | 500MHz | 350mA | 0.35Ω | 13 | 500MHz | 7000MHz | Kit |
| LQP03TG3N8C02□ | 3.8nH ±0.2nH | 500MHz | 350mA | 0.35Ω | 13 | 500MHz | 7000MHz | |
| LQP03TG3N9B02□ | 3.9nH ±0.1nH | 500MHz | 350mA | 0.35Ω | 13 | 500MHz | 6500MHz | Kit |
| LQP03TG3N9C02□ | 3.9nH ±0.2nH | 500MHz | 350mA | 0.35Ω | 13 | 500MHz | 6500MHz | |
| LQP03TG4N3H02□ | 4.3nH ±3% | 500MHz | 300mA | 0.58Ω | 13 | 500MHz | 6500MHz | Kit |
| LQP03TG4N3J02□ | 4.3nH ±5% | 500MHz | 300mA | 0.58Ω | 13 | 500MHz | 6500MHz | |
| LQP03TG4N7H02□ | 4.7nH ±3% | 500MHz | 250mA | 0.72Ω | 12 | 500MHz | 6500MHz | Kit |
| LQP03TG4N7J02□ | 4.7nH ±5% | 500MHz | 250mA | 0.72Ω | 12 | 500MHz | 6500MHz | |
| LQP03TG5N1H02□ | 5.1nH ±3% | 500MHz | 250mA | 0.72Ω | 12 | 500MHz | 6500MHz | Kit |
| LQP03TG5N1J02□ | 5.1nH ±5% | 500MHz | 250mA | 0.72Ω | 12 | 500MHz | 6500MHz | |
| LQP03TG5N6H02□ | 5.6nH ±3% | 500MHz | 250mA | 0.88Ω | 12 | 500MHz | 6000MHz | Kit |
| LQP03TG5N6J02□ | 5.6nH ±5% | 500MHz | 250mA | 0.88Ω | 12 | 500MHz | 6000MHz | |
| LQP03TG6N2H02□ | 6.2nH ±3% | 500MHz | 200mA | 1.15Ω | 12 | 500MHz | 6000MHz | Kit |
| LQP03TG6N2J02□ | 6.2nH ±5% | 500MHz | 200mA | 1.15Ω | 12 | 500MHz | 6000MHz | |
| LQP03TG6N8H02□ | 6.8nH ±3% | 500MHz | 200mA | 1.15Ω | 12 | 500MHz | 5400MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.


Continued on the following page. 

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQP03TG6N8J02□ | 6.8nH ±5% | 500MHz | 200mA | 1.15Ω | 12 | 500MHz | 5400MHz | |
| LQP03TG7N5H02□ | 7.5nH ±3% | 500MHz | 200mA | 1.22Ω | 12 | 500MHz | 4800MHz | Kit |
| LQP03TG7N5J02□ | 7.5nH ±5% | 500MHz | 200mA | 1.22Ω | 12 | 500MHz | 4800MHz | |
| LQP03TG8N2H02□ | 8.2nH ±3% | 500MHz | 200mA | 1.40Ω | 12 | 500MHz | 4800MHz | Kit |
| LQP03TG8N2J02□ | 8.2nH ±5% | 500MHz | 200mA | 1.40Ω | 12 | 500MHz | 4800MHz | |
| LQP03TG9N1H02□ | 9.1nH ±3% | 500MHz | 200mA | 1.40Ω | 11 | 500MHz | 4500MHz | Kit |
| LQP03TG9N1J02□ | 9.1nH ±5% | 500MHz | 200mA | 1.40Ω | 11 | 500MHz | 4500MHz | |
| LQP03TG10NH02□ | 10nH ±3% | 500MHz | 190mA | 1.52Ω | 11 | 500MHz | 4500MHz | Kit |
| LQP03TG10NJ02□ | 10nH ±5% | 500MHz | 190mA | 1.52Ω | 11 | 500MHz | 4500MHz | |
| LQP03TG12NH02□ | 12nH ±3% | 500MHz | 180mA | 1.78Ω | 11 | 500MHz | 3700MHz | Kit |
| LQP03TG12NJ02□ | 12nH ±5% | 500MHz | 180mA | 1.78Ω | 11 | 500MHz | 3700MHz | |
| LQP03TG15NH02□ | 15nH ±3% | 500MHz | 170mA | 1.90Ω | 11 | 500MHz | 3100MHz | Kit |
| LQP03TG15NJ02□ | 15nH ±5% | 500MHz | 170mA | 1.90Ω | 11 | 500MHz | 3100MHz | |
| LQP03TG18NH02□ | 18nH ±3% | 500MHz | 160mA | 2.28Ω | 11 | 500MHz | 2800MHz | Kit |
| LQP03TG18NJ02□ | 18nH ±5% | 500MHz | 160mA | 2.28Ω | 11 | 500MHz | 2800MHz | |
| LQP03TG22NH02□ | 22nH ±3% | 500MHz | 140mA | 2.85Ω | 9 | 500MHz | 2500MHz | Kit |
| LQP03TG22NJ02□ | 22nH ±5% | 500MHz | 140mA | 2.85Ω | 9 | 500MHz | 2500MHz | |
| LQP03TG27NH02□ | 27nH ±3% | 500MHz | 120mA | 3.65Ω | 7 | 500MHz | 1700MHz | New |
| LQP03TG27NJ02□ | 27nH ±5% | 500MHz | 120mA | 3.65Ω | 7 | 500MHz | 1700MHz | New |
| LQP03TG33NJ02□ | 33nH ±5% | 300MHz | 110mA | 4.25Ω | 7 | 300MHz | 1600MHz | New |
| LQP03TG39NJ02□ | 39nH ±5% | 300MHz | 110mA | 4.6Ω | 7 | 300MHz | 1500MHz | New |
| LQP03TG47NJ02□ | 47nH ±5% | 300MHz | 100mA | 5.2Ω | 7 | 300MHz | 1300MHz | New |
| LQP03TG56NJ02□ | 56nH ±5% | 300MHz | 100mA | 5.6Ω | 7 | 300MHz | 1200MHz | New |
| LQP03TG68NJ02□ | 68nH ±5% | 300MHz | 90mA | 6.25Ω | 6 | 300MHz | 1100MHz | New |
| LQP03TG82NJ02□ | 82nH ±5% | 300MHz | 90mA | 7.15Ω | 6 | 300MHz | 1000MHz | New |
| LQP03TGR10J02□ | 100nH ±5% | 300MHz | 80mA | 8.05Ω | 6 | 300MHz | 900MHz | New |
| LQP03TGR12J02□ | 120nH ±5% | 300MHz | 80mA | 8.75Ω | 6 | 300MHz | 800MHz | New |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



Continued on the following page.



△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Reference Data

4991A+16197A

| Part Number | Q (Typ.) | | | | |
|-------------|----------|--------|--------|--------|--------|
| | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQP03TG0N6 | 17 | 18 | 26 | 27 | 29 |
| LQP03TG0N7 | 18 | 20 | 29 | 30 | 33 |
| LQP03TG0N8 | 18 | 20 | 29 | 30 | 33 |
| LQP03TG0N9 | 19 | 20 | 30 | 31 | 34 |
| LQP03TG1N0 | 18 | 19 | 28 | 29 | 31 |
| LQP03TG1N1 | 18 | 20 | 28 | 29 | 32 |
| LQP03TG1N2 | 19 | 20 | 29 | 30 | 33 |
| LQP03TG1N3 | 18 | 19 | 28 | 29 | 32 |
| LQP03TG1N4 | 20 | 21 | 31 | 32 | 34 |
| LQP03TG1N5 | 21 | 22 | 32 | 33 | 35 |
| LQP03TG1N6 | 18 | 20 | 29 | 30 | 32 |
| LQP03TG1N7 | 19 | 20 | 29 | 30 | 33 |
| LQP03TG1N8 | 20 | 21 | 30 | 31 | 33 |
| LQP03TG1N9 | 19 | 20 | 29 | 31 | 33 |
| LQP03TG2N0 | 20 | 21 | 30 | 31 | 33 |
| LQP03TG2N1 | 19 | 20 | 28 | 29 | 31 |
| LQP03TG2N2 | 19 | 20 | 28 | 29 | 31 |
| LQP03TG2N3 | 19 | 20 | 28 | 29 | 32 |
| LQP03TG2N4 | 20 | 21 | 30 | 31 | 34 |
| LQP03TG2N5 | 19 | 20 | 29 | 30 | 32 |
| LQP03TG2N6 | 19 | 20 | 28 | 30 | 32 |
| LQP03TG2N7 | 19 | 20 | 29 | 30 | 31 |
| LQP03TG2N8 | 20 | 21 | 30 | 31 | 33 |
| LQP03TG2N9 | 20 | 21 | 30 | 31 | 34 |
| LQP03TG3N0 | 21 | 22 | 30 | 31 | 33 |
| LQP03TG3N1 | 20 | 21 | 30 | 31 | 34 |
| LQP03TG3N2 | 20 | 21 | 30 | 31 | 33 |
| LQP03TG3N3 | 21 | 22 | 31 | 31 | 34 |
| LQP03TG3N4 | 20 | 21 | 29 | 30 | 32 |
| LQP03TG3N5 | 19 | 20 | 28 | 29 | 31 |
| LQP03TG3N6 | 20 | 21 | 29 | 29 | 31 |
| LQP03TG3N7 | 18 | 20 | 28 | 29 | 30 |
| LQP03TG3N8 | 18 | 19 | 27 | 28 | 30 |
| LQP03TG3N9 | 20 | 21 | 29 | 30 | 31 |
| LQP03TG4N3 | 19 | 21 | 28 | 28 | 30 |
| LQP03TG4N7 | 19 | 20 | 27 | 28 | 29 |
| LQP03TG5N1 | 19 | 20 | 27 | 27 | 29 |
| LQP03TG5N6 | 18 | 19 | 25 | 26 | 27 |
| LQP03TG6N2 | 18 | 19 | 25 | 26 | 26 |
| LQP03TG6N8 | 18 | 19 | 25 | 25 | 25 |
| LQP03TG7N5 | 18 | 19 | 24 | 24 | 24 |
| LQP03TG8N2 | 18 | 19 | 24 | 24 | 24 |
| LQP03TG9N1 | 18 | 19 | 23 | 22 | 22 |
| LQP03TG10N | 18 | 19 | 23 | 23 | 22 |
| LQP03TG12N | 17 | 18 | 20 | 20 | 17 |
| LQP03TG15N | 17 | 18 | 18 | 17 | 13 |
| LQP03TG18N | 15 | 16 | 14 | 13 | 8 |
| LQP03TG22N | 13 | 14 | 11 | 9 | 4 |

Continued on the following page. 


 Note • Please read rating and  CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Q (Typ.) | | | | |
|-------------|----------|--------|--------|--------|--------|
| | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQP03TG27N | 13 | 13 | 5 | - | - |
| LQP03TG33N | 13 | 12 | - | - | - |
| LQP03TG39N | 13 | 12 | - | - | - |
| LQP03TG47N | 13 | 12 | - | - | - |
| LQP03TG56N | 11 | 10 | - | - | - |
| LQP03TG68N | 10 | 9 | - | - | - |
| LQP03TG82N | 9 | 8 | - | - | - |
| LQP03TGR10 | 7 | 6 | - | - | - |
| LQP03TGR12 | 7 | 5 | - | - | - |

LQP03TN_02 Series 0201/0603 (inch/mm)

Size Code 0201 (0603) in inch (in mm), High Q, Wide Variation

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 15000 |
| J | ø330mm Paper Taping | 50000 |
| B | Packing in Bulk | 500 |



Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQP03TN0N6B02□ | 0.6nH ±0.1nH | 500MHz | 850mA | 0.07Ω | 14 | 500MHz | 20000MHz | Kit |
| LQP03TN0N6C02□ | 0.6nH ±0.2nH | 500MHz | 850mA | 0.07Ω | 14 | 500MHz | 20000MHz | |
| LQP03TN0N7B02□ | 0.7nH ±0.1nH | 500MHz | 800mA | 0.08Ω | 14 | 500MHz | 20000MHz | Kit |
| LQP03TN0N7C02□ | 0.7nH ±0.2nH | 500MHz | 800mA | 0.08Ω | 14 | 500MHz | 20000MHz | |
| LQP03TN0N8B02□ | 0.8nH ±0.1nH | 500MHz | 800mA | 0.08Ω | 14 | 500MHz | 18000MHz | Kit |
| LQP03TN0N8C02□ | 0.8nH ±0.2nH | 500MHz | 800mA | 0.08Ω | 14 | 500MHz | 18000MHz | |
| LQP03TN0N9B02□ | 0.9nH ±0.1nH | 500MHz | 750mA | 0.10Ω | 14 | 500MHz | 18000MHz | Kit |
| LQP03TN0N9C02□ | 0.9nH ±0.2nH | 500MHz | 750mA | 0.10Ω | 14 | 500MHz | 18000MHz | |
| LQP03TN1N0B02□ | 1.0nH ±0.1nH | 500MHz | 750mA | 0.10Ω | 14 | 500MHz | 17000MHz | Kit |
| LQP03TN1N0C02□ | 1.0nH ±0.2nH | 500MHz | 750mA | 0.10Ω | 14 | 500MHz | 17000MHz | |
| LQP03TN1N1B02□ | 1.1nH ±0.1nH | 500MHz | 750mA | 0.10Ω | 14 | 500MHz | 17000MHz | Kit |
| LQP03TN1N1C02□ | 1.1nH ±0.2nH | 500MHz | 750mA | 0.10Ω | 14 | 500MHz | 17000MHz | |
| LQP03TN1N2B02□ | 1.2nH ±0.1nH | 500MHz | 750mA | 0.10Ω | 14 | 500MHz | 17000MHz | Kit |
| LQP03TN1N2C02□ | 1.2nH ±0.2nH | 500MHz | 750mA | 0.10Ω | 14 | 500MHz | 17000MHz | |
| LQP03TN1N3B02□ | 1.3nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 17000MHz | Kit |
| LQP03TN1N3C02□ | 1.3nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 17000MHz | |
| LQP03TN1N4B02□ | 1.4nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 16000MHz | Kit |
| LQP03TN1N4C02□ | 1.4nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 16000MHz | |
| LQP03TN1N5B02□ | 1.5nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 15000MHz | Kit |
| LQP03TN1N5C02□ | 1.5nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 15000MHz | |
| LQP03TN1N6B02□ | 1.6nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 15000MHz | Kit |
| LQP03TN1N6C02□ | 1.6nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 15000MHz | |
| LQP03TN1N7B02□ | 1.7nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 15000MHz | Kit |
| LQP03TN1N7C02□ | 1.7nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 15000MHz | |
| LQP03TN1N8B02□ | 1.8nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 15000MHz | Kit |
| LQP03TN1N8C02□ | 1.8nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 15000MHz | |
| LQP03TN1N9B02□ | 1.9nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 12500MHz | Kit |
| LQP03TN1N9C02□ | 1.9nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 12500MHz | |
| LQP03TN2N0B02□ | 2.0nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 12500MHz | Kit |
| LQP03TN2N0C02□ | 2.0nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 12500MHz | |
| LQP03TN2N1B02□ | 2.1nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 11000MHz | Kit |
| LQP03TN2N1C02□ | 2.1nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 11000MHz | |
| LQP03TN2N2B02□ | 2.2nH ±0.1nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 11000MHz | Kit |


Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQP03TN2N2C02□ | 2.2nH ±0.2nH | 500MHz | 600mA | 0.15Ω | 14 | 500MHz | 11000MHz | |
| LQP03TN2N3B02□ | 2.3nH ±0.1nH | 500MHz | 500mA | 0.20Ω | 14 | 500MHz | 10000MHz | Kit |
| LQP03TN2N3C02□ | 2.3nH ±0.2nH | 500MHz | 500mA | 0.20Ω | 14 | 500MHz | 10000MHz | |
| LQP03TN2N4B02□ | 2.4nH ±0.1nH | 500MHz | 500mA | 0.20Ω | 14 | 500MHz | 10000MHz | Kit |
| LQP03TN2N4C02□ | 2.4nH ±0.2nH | 500MHz | 500mA | 0.20Ω | 14 | 500MHz | 10000MHz | |
| LQP03TN2N5B02□ | 2.5nH ±0.1nH | 500MHz | 500mA | 0.20Ω | 14 | 500MHz | 10000MHz | Kit |
| LQP03TN2N5C02□ | 2.5nH ±0.2nH | 500MHz | 500mA | 0.20Ω | 14 | 500MHz | 10000MHz | |
| LQP03TN2N6B02□ | 2.6nH ±0.1nH | 500MHz | 500mA | 0.20Ω | 14 | 500MHz | 10000MHz | Kit |
| LQP03TN2N6C02□ | 2.6nH ±0.2nH | 500MHz | 500mA | 0.20Ω | 14 | 500MHz | 10000MHz | |
| LQP03TN2N7B02□ | 2.7nH ±0.1nH | 500MHz | 500mA | 0.20Ω | 14 | 500MHz | 10000MHz | Kit |
| LQP03TN2N7C02□ | 2.7nH ±0.2nH | 500MHz | 500mA | 0.20Ω | 14 | 500MHz | 10000MHz | |
| LQP03TN2N8B02□ | 2.8nH ±0.1nH | 500MHz | 500mA | 0.20Ω | 14 | 500MHz | 9500MHz | Kit |
| LQP03TN2N8C02□ | 2.8nH ±0.2nH | 500MHz | 500mA | 0.20Ω | 14 | 500MHz | 9500MHz | |
| LQP03TN2N9B02□ | 2.9nH ±0.1nH | 500MHz | 500mA | 0.20Ω | 14 | 500MHz | 9500MHz | Kit |
| LQP03TN2N9C02□ | 2.9nH ±0.2nH | 500MHz | 500mA | 0.20Ω | 14 | 500MHz | 9500MHz | |
| LQP03TN3N0B02□ | 3.0nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 14 | 500MHz | 9500MHz | Kit |
| LQP03TN3N0C02□ | 3.0nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 14 | 500MHz | 9500MHz | |
| LQP03TN3N1B02□ | 3.1nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 14 | 500MHz | 8000MHz | Kit |
| LQP03TN3N1C02□ | 3.1nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 14 | 500MHz | 8000MHz | |
| LQP03TN3N2B02□ | 3.2nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 14 | 500MHz | 8000MHz | Kit |
| LQP03TN3N2C02□ | 3.2nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 14 | 500MHz | 8000MHz | |
| LQP03TN3N3B02□ | 3.3nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 14 | 500MHz | 8000MHz | Kit |
| LQP03TN3N3C02□ | 3.3nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 14 | 500MHz | 8000MHz | |
| LQP03TN3N4B02□ | 3.4nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 14 | 500MHz | 7000MHz | Kit |
| LQP03TN3N4C02□ | 3.4nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 14 | 500MHz | 7000MHz | |
| LQP03TN3N5B02□ | 3.5nH ±0.1nH | 500MHz | 450mA | 0.25Ω | 14 | 500MHz | 7000MHz | Kit |
| LQP03TN3N5C02□ | 3.5nH ±0.2nH | 500MHz | 450mA | 0.25Ω | 14 | 500MHz | 7000MHz | |
| LQP03TN3N6B02□ | 3.6nH ±0.1nH | 500MHz | 400mA | 0.30Ω | 14 | 500MHz | 6000MHz | Kit |
| LQP03TN3N6C02□ | 3.6nH ±0.2nH | 500MHz | 400mA | 0.30Ω | 14 | 500MHz | 6000MHz | |
| LQP03TN3N7B02□ | 3.7nH ±0.1nH | 500MHz | 400mA | 0.30Ω | 14 | 500MHz | 6000MHz | Kit |
| LQP03TN3N7C02□ | 3.7nH ±0.2nH | 500MHz | 400mA | 0.30Ω | 14 | 500MHz | 6000MHz | |
| LQP03TN3N8B02□ | 3.8nH ±0.1nH | 500MHz | 400mA | 0.30Ω | 14 | 500MHz | 6000MHz | Kit |
| LQP03TN3N8C02□ | 3.8nH ±0.2nH | 500MHz | 400mA | 0.30Ω | 14 | 500MHz | 6000MHz | |
| LQP03TN3N9B02□ | 3.9nH ±0.1nH | 500MHz | 400mA | 0.30Ω | 14 | 500MHz | 5700MHz | Kit |
| LQP03TN3N9C02□ | 3.9nH ±0.2nH | 500MHz | 400mA | 0.30Ω | 14 | 500MHz | 5700MHz | |
| LQP03TN4N0B02□ | 4.0nH ±0.1nH | 500MHz | 350mA | 0.40Ω | 14 | 500MHz | 5300MHz | Kit |
| LQP03TN4N0C02□ | 4.0nH ±0.2nH | 500MHz | 350mA | 0.40Ω | 14 | 500MHz | 5300MHz | |
| LQP03TN4N1B02□ | 4.1nH ±0.1nH | 500MHz | 350mA | 0.40Ω | 14 | 500MHz | 5300MHz | Kit |
| LQP03TN4N1C02□ | 4.1nH ±0.2nH | 500MHz | 350mA | 0.40Ω | 14 | 500MHz | 5300MHz | |
| LQP03TN4N2B02□ | 4.2nH ±0.1nH | 500MHz | 350mA | 0.40Ω | 14 | 500MHz | 5300MHz | Kit |
| LQP03TN4N2C02□ | 4.2nH ±0.2nH | 500MHz | 350mA | 0.40Ω | 14 | 500MHz | 5300MHz | |
| LQP03TN4N3H02□ | 4.3nH ±3% | 500MHz | 350mA | 0.40Ω | 14 | 500MHz | 5300MHz | Kit |
| LQP03TN4N3J02□ | 4.3nH ±5% | 500MHz | 350mA | 0.40Ω | 14 | 500MHz | 5300MHz | |
| LQP03TN4N7H02□ | 4.7nH ±3% | 500MHz | 350mA | 0.40Ω | 14 | 500MHz | 4400MHz | Kit |
| LQP03TN4N7J02□ | 4.7nH ±5% | 500MHz | 350mA | 0.40Ω | 14 | 500MHz | 4400MHz | |
| LQP03TN5N1H02□ | 5.1nH ±3% | 500MHz | 350mA | 0.40Ω | 14 | 500MHz | 4200MHz | Kit |
| LQP03TN5N1J02□ | 5.1nH ±5% | 500MHz | 350mA | 0.40Ω | 14 | 500MHz | 4200MHz | |
| LQP03TN5N6H02□ | 5.6nH ±3% | 500MHz | 350mA | 0.40Ω | 14 | 500MHz | 4000MHz | Kit |


Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

Continued on the following page. 

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|---------|
| LQP03TN5N6J02□ | 5.6nH ±5% | 500MHz | 350mA | 0.40Ω | 14 | 500MHz | 4000MHz | |
| LQP03TN6N2H02□ | 6.2nH ±3% | 500MHz | 300mA | 0.60Ω | 14 | 500MHz | 4000MHz | Kit |
| LQP03TN6N2J02□ | 6.2nH ±5% | 500MHz | 300mA | 0.60Ω | 14 | 500MHz | 4000MHz | |
| LQP03TN6N8H02□ | 6.8nH ±3% | 500MHz | 300mA | 0.60Ω | 14 | 500MHz | 3900MHz | Kit |
| LQP03TN6N8J02□ | 6.8nH ±5% | 500MHz | 300mA | 0.60Ω | 14 | 500MHz | 3900MHz | |
| LQP03TN7N5H02□ | 7.5nH ±3% | 500MHz | 300mA | 0.60Ω | 14 | 500MHz | 3700MHz | Kit |
| LQP03TN7N5J02□ | 7.5nH ±5% | 500MHz | 300mA | 0.60Ω | 14 | 500MHz | 3700MHz | |
| LQP03TN8N2H02□ | 8.2nH ±3% | 500MHz | 250mA | 0.70Ω | 14 | 500MHz | 3600MHz | Kit |
| LQP03TN8N2J02□ | 8.2nH ±5% | 500MHz | 250mA | 0.70Ω | 14 | 500MHz | 3600MHz | |
| LQP03TN9N1H02□ | 9.1nH ±3% | 500MHz | 250mA | 0.70Ω | 14 | 500MHz | 3300MHz | Kit |
| LQP03TN9N1J02□ | 9.1nH ±5% | 500MHz | 250mA | 0.70Ω | 14 | 500MHz | 3300MHz | |
| LQP03TN10NH02□ | 10nH ±3% | 500MHz | 250mA | 0.70Ω | 14 | 500MHz | 3200MHz | Kit |
| LQP03TN10NJ02□ | 10nH ±5% | 500MHz | 250mA | 0.70Ω | 14 | 500MHz | 3200MHz | |
| LQP03TN11NH02□ | 11nH ±3% | 500MHz | 250mA | 0.80Ω | 14 | 500MHz | 2900MHz | Kit |
| LQP03TN11NJ02□ | 11nH ±5% | 500MHz | 250mA | 0.80Ω | 14 | 500MHz | 2900MHz | |
| LQP03TN12NH02□ | 12nH ±3% | 500MHz | 250mA | 0.70Ω | 12 | 500MHz | 2900MHz | Kit |
| LQP03TN12NJ02□ | 12nH ±5% | 500MHz | 250mA | 0.70Ω | 12 | 500MHz | 2900MHz | |
| LQP03TN13NH02□ | 13nH ±3% | 500MHz | 250mA | 0.80Ω | 12 | 500MHz | 2600MHz | Kit |
| LQP03TN13NJ02□ | 13nH ±5% | 500MHz | 250mA | 0.80Ω | 12 | 500MHz | 2600MHz | |
| LQP03TN15NH02□ | 15nH ±3% | 500MHz | 250mA | 0.70Ω | 12 | 500MHz | 2600MHz | Kit |
| LQP03TN15NJ02□ | 15nH ±5% | 500MHz | 250mA | 0.70Ω | 12 | 500MHz | 2600MHz | |
| LQP03TN16NH02□ | 16nH ±3% | 500MHz | 200mA | 0.95Ω | 12 | 500MHz | 2200MHz | Kit |
| LQP03TN16NJ02□ | 16nH ±5% | 500MHz | 200mA | 0.95Ω | 12 | 500MHz | 2200MHz | |
| LQP03TN18NH02□ | 18nH ±3% | 500MHz | 200mA | 0.80Ω | 12 | 500MHz | 2200MHz | Kit |
| LQP03TN18NJ02□ | 18nH ±5% | 500MHz | 200mA | 0.80Ω | 12 | 500MHz | 2200MHz | |
| LQP03TN20NH02□ | 20nH ±3% | 500MHz | 150mA | 2.30Ω | 12 | 500MHz | 2200MHz | Kit |
| LQP03TN20NJ02□ | 20nH ±5% | 500MHz | 150mA | 2.30Ω | 12 | 500MHz | 2200MHz | |
| LQP03TN22NH02□ | 22nH ±3% | 500MHz | 150mA | 1.90Ω | 12 | 500MHz | 2200MHz | Kit |
| LQP03TN22NJ02□ | 22nH ±5% | 500MHz | 150mA | 1.90Ω | 12 | 500MHz | 2200MHz | |
| LQP03TN24NH02□ | 24nH ±3% | 500MHz | 140mA | 2.30Ω | 12 | 500MHz | 2000MHz | Kit |
| LQP03TN24NJ02□ | 24nH ±5% | 500MHz | 140mA | 2.30Ω | 12 | 500MHz | 2000MHz | |
| LQP03TN27NH02□ | 27nH ±3% | 500MHz | 140mA | 2.30Ω | 12 | 500MHz | 2000MHz | Kit |
| LQP03TN27NJ02□ | 27nH ±5% | 500MHz | 140mA | 2.30Ω | 12 | 500MHz | 2000MHz | |
| LQP03TN30NH02□ | 30nH ±3% | 500MHz | 120mA | 2.95Ω | 9 | 500MHz | 1700MHz | Kit |
| LQP03TN30NJ02□ | 30nH ±5% | 500MHz | 120mA | 2.95Ω | 9 | 500MHz | 1700MHz | |
| LQP03TN33NJ02□ | 33nH ±5% | 300MHz | 120mA | 2.95Ω | 9 | 300MHz | 1700MHz | Kit |
| LQP03TN36NJ02□ | 36nH ±5% | 300MHz | 120mA | 3.00Ω | 9 | 300MHz | 1500MHz | Kit |
| LQP03TN39NJ02□ | 39nH ±5% | 300MHz | 120mA | 3.00Ω | 9 | 300MHz | 1500MHz | Kit |
| LQP03TN43NJ02□ | 43nH ±5% | 300MHz | 100mA | 3.60Ω | 9 | 300MHz | 1300MHz | Kit |
| LQP03TN47NJ02□ | 47nH ±5% | 300MHz | 100mA | 3.60Ω | 9 | 300MHz | 1300MHz | Kit |
| LQP03TN51NJ02□ | 51nH ±5% | 300MHz | 100mA | 3.90Ω | 9 | 300MHz | 1200MHz | Kit |
| LQP03TN56NJ02□ | 56nH ±5% | 300MHz | 100mA | 3.90Ω | 9 | 300MHz | 1200MHz | Kit |
| LQP03TN62NJ02□ | 62nH ±5% | 300MHz | 100mA | 8Ω | 8 | 300MHz | 1100MHz | Kit |
| LQP03TN68NJ02□ | 68nH ±5% | 300MHz | 100mA | 8Ω | 8 | 300MHz | 1100MHz | Kit |
| LQP03TN75NJ02□ | 75nH ±5% | 300MHz | 100mA | 10Ω | 8 | 300MHz | 1000MHz | New |
| LQP03TN82NJ02□ | 82nH ±5% | 300MHz | 100mA | 10Ω | 8 | 300MHz | 1000MHz | Kit |
| LQP03TN91NJ02□ | 91nH ±5% | 300MHz | 80mA | 10Ω | 8 | 300MHz | 900MHz | New Kit |
| LQP03TNR10J02□ | 100nH ±5% | 300MHz | 80mA | 10Ω | 8 | 300MHz | 900MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.


Continued on the following page. 

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|---------|
| LQP03TNR11J02□ | 110nH ±5% | 300MHz | 80mA | 12Ω | 8 | 300MHz | 800MHz | New Kit |
| LQP03TNR12J02□ | 120nH ±5% | 300MHz | 80mA | 12Ω | 8 | 300MHz | 800MHz | Kit |
| LQP03TNR13J02□ | 130nH ±5% | 100MHz | 80mA | 9Ω | 5 | 100MHz | 650MHz | New Kit |
| LQP03TNR15J02□ | 150nH ±5% | 100MHz | 80mA | 9Ω | 5 | 100MHz | 650MHz | Kit |
| LQP03TNR16J02□ | 160nH ±5% | 100MHz | 70mA | 11Ω | 5 | 100MHz | 600MHz | New Kit |
| LQP03TNR18J02□ | 180nH ±5% | 100MHz | 70mA | 11Ω | 5 | 100MHz | 600MHz | Kit |
| LQP03TNR20J02□ | 200nH ±5% | 100MHz | 60mA | 13Ω | 5 | 100MHz | 500MHz | New Kit |
| LQP03TNR22J02□ | 220nH ±5% | 100MHz | 60mA | 13Ω | 5 | 100MHz | 500MHz | Kit |
| LQP03TNR24J02□ | 240nH ±5% | 100MHz | 60mA | 15Ω | 5 | 100MHz | 450MHz | New Kit |
| LQP03TNR27J02□ | 270nH ±5% | 100MHz | 60mA | 15Ω | 5 | 100MHz | 450MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



■ Reference Data

4991A&16197A

| Part Number | Q (Typ.) | | | | |
|---------------|----------|---------|---------|---------|---------|
| | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQP03TN0N6□02 | 35 min. | 40 min. | 62 min. | 67 min. | 71 min. |
| LQP03TN0N7□02 | 35 min. | 40 min. | 62 min. | 67 min. | 71 min. |
| LQP03TN0N8□02 | 35 min. | 40 min. | 62 min. | 67 min. | 71 min. |
| LQP03TN0N9□02 | 35 min. | 40 min. | 62 min. | 67 min. | 71 min. |
| LQP03TN1N0□02 | 35 min. | 40 min. | 62 min. | 67 min. | 71 min. |
| LQP03TN1N1□02 | 35 min. | 40 min. | 62 min. | 67 min. | 71 min. |
| LQP03TN1N2□02 | 31 | 34 | 51 | 54 | 59 |
| LQP03TN1N3□02 | 34 | 36 | 55 | 58 | 64 |
| LQP03TN1N4□02 | 31 | 34 | 52 | 55 | 61 |
| LQP03TN1N5□02 | 29 | 31 | 47 | 49 | 54 |
| LQP03TN1N6□02 | 30 | 32 | 47 | 49 | 54 |
| LQP03TN1N7□02 | 30 | 31 | 47 | 49 | 53 |
| LQP03TN1N8□02 | 32 | 34 | 50 | 53 | 57 |
| LQP03TN1N9□02 | 29 | 31 | 45 | 48 | 52 |
| LQP03TN2N0□02 | 28 | 30 | 44 | 46 | 50 |
| LQP03TN2N1□02 | 30 | 31 | 46 | 48 | 52 |
| LQP03TN2N2□02 | 30 | 32 | 46 | 48 | 52 |
| LQP03TN2N3□02 | 29 | 30 | 44 | 46 | 50 |
| LQP03TN2N4□02 | 28 | 30 | 43 | 45 | 49 |
| LQP03TN2N5□02 | 27 | 29 | 41 | 43 | 47 |

Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Q (Typ.) | | | | |
|---------------|----------|--------|--------|--------|--------|
| | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQP03TN2N6□02 | 26 | 28 | 40 | 42 | 46 |
| LQP03TN2N7□02 | 28 | 29 | 42 | 44 | 47 |
| LQP03TN2N8□02 | 27 | 28 | 39 | 41 | 45 |
| LQP03TN2N9□02 | 27 | 28 | 41 | 42 | 45 |
| LQP03TN3N0□02 | 29 | 31 | 44 | 45 | 48 |
| LQP03TN3N1□02 | 28 | 29 | 40 | 42 | 46 |
| LQP03TN3N2□02 | 28 | 29 | 39 | 41 | 44 |
| LQP03TN3N3□02 | 25 | 26 | 37 | 39 | 42 |
| LQP03TN3N4□02 | 25 | 27 | 37 | 38 | 41 |
| LQP03TN3N5□02 | 27 | 28 | 40 | 41 | 43 |
| LQP03TN3N6□02 | 26 | 27 | 38 | 39 | 41 |
| LQP03TN3N7□02 | 26 | 27 | 38 | 39 | 41 |
| LQP03TN3N8□02 | 25 | 27 | 37 | 38 | 39 |
| LQP03TN3N9□02 | 24 | 26 | 36 | 37 | 39 |
| LQP03TN4N0□02 | 26 | 27 | 37 | 38 | 40 |
| LQP03TN4N1□02 | 25 | 26 | 36 | 37 | 39 |
| LQP03TN4N2□02 | 25 | 27 | 37 | 38 | 40 |
| LQP03TN4N3□02 | 24 | 26 | 36 | 37 | 39 |
| LQP03TN4N7□02 | 25 | 27 | 37 | 38 | 39 |
| LQP03TN5N1□02 | 26 | 28 | 35 | 36 | 37 |
| LQP03TN5N6□02 | 25 | 26 | 36 | 37 | 38 |
| LQP03TN6N2□02 | 23 | 25 | 33 | 34 | 35 |
| LQP03TN6N8□02 | 25 | 27 | 36 | 37 | 37 |
| LQP03TN7N5□02 | 25 | 26 | 34 | 35 | 35 |
| LQP03TN8N2□02 | 24 | 25 | 33 | 34 | 33 |
| LQP03TN9N1□02 | 25 | 26 | 32 | 32 | 31 |
| LQP03TN10N□02 | 24 | 26 | 32 | 32 | 32 |
| LQP03TN11N□02 | 24 | 25 | 29 | 29 | 27 |
| LQP03TN12N□02 | 23 | 24 | 27 | 26 | 23 |
| LQP03TN13N□02 | 23 | 24 | 27 | 26 | 22 |
| LQP03TN15N□02 | 23 | 24 | 25 | 24 | 19 |
| LQP03TN16N□02 | 23 | 24 | 24 | 23 | 18 |
| LQP03TN18N□02 | 23 | 24 | 23 | 20 | 14 |
| LQP03TN20N□02 | 21 | 22 | 22 | 20 | 15 |
| LQP03TN22N□02 | 22 | 22 | 21 | - | - |
| LQP03TN24N□02 | 21 | 21 | 19 | - | - |
| LQP03TN27N□02 | 21 | 22 | 21 | - | - |
| LQP03TN30N□02 | 19 | 20 | - | - | - |
| LQP03TN33N□02 | 20 | 20 | - | - | - |
| LQP03TN36N□02 | 18 | 18 | - | - | - |
| LQP03TN39N□02 | 18 | 18 | - | - | - |
| LQP03TN43N□02 | 17 | 16 | - | - | - |
| LQP03TN47N□02 | 17 | 16 | - | - | - |
| LQP03TN51N□02 | 17 | 17 | - | - | - |
| LQP03TN56N□02 | 16 | 16 | - | - | - |
| LQP03TN62N□02 | 15 | 14 | - | - | - |
| LQP03TN68N□02 | 11 | 10 | - | - | - |
| LQP03TN75N□02 | 10 | 9 | - | - | - |
| LQP03TN82N□02 | 11 | 10 | - | - | - |
| LQP03TN91N□02 | 9 | 8 | - | - | - |
| LQP03TNR10□02 | 8 | 6 | - | - | - |
| LQP03TNR11□02 | 7 | 5 | - | - | - |
| LQP03TNR12□02 | 7 | 4 | - | - | - |

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQP15MN_02 Series 0402/1005 (inch/mm)

Size Code 0402 (1005) in inch (in mm), Tight Inductance Tolerance, Film Type

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 10000 |
| J | ø330mm Paper Taping | 50000 |
| B | Packing in Bulk | 500 |



Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|---------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQP15MN1N0B02□ | 1.0nH ±0.1nH | 500MHz | 400mA | 0.1Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN1N0W02□ | 1.0nH ±0.05nH | 500MHz | 400mA | 0.1Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN1N1B02□ | 1.1nH ±0.1nH | 500MHz | 390mA | 0.1Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN1N1W02□ | 1.1nH ±0.05nH | 500MHz | 390mA | 0.1Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN1N2B02□ | 1.2nH ±0.1nH | 500MHz | 390mA | 0.1Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN1N2W02□ | 1.2nH ±0.05nH | 500MHz | 390mA | 0.1Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN1N3B02□ | 1.3nH ±0.1nH | 500MHz | 280mA | 0.2Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN1N3W02□ | 1.3nH ±0.05nH | 500MHz | 280mA | 0.2Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN1N4W02□ | 1.4nH ±0.05nH | 500MHz | 280mA | 0.2Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN1N5B02□ | 1.5nH ±0.1nH | 500MHz | 280mA | 0.2Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN1N5W02□ | 1.5nH ±0.05nH | 500MHz | 280mA | 0.2Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN1N6B02□ | 1.6nH ±0.1nH | 500MHz | 220mA | 0.3Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN1N6W02□ | 1.6nH ±0.05nH | 500MHz | 220mA | 0.3Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN1N7W02□ | 1.7nH ±0.05nH | 500MHz | 280mA | 0.2Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN1N8B02□ | 1.8nH ±0.1nH | 500MHz | 280mA | 0.2Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN1N8W02□ | 1.8nH ±0.05nH | 500MHz | 280mA | 0.2Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN1N9W02□ | 1.9nH ±0.05nH | 500MHz | 220mA | 0.3Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN2N0B02□ | 2.0nH ±0.1nH | 500MHz | 220mA | 0.3Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN2N0W02□ | 2.0nH ±0.05nH | 500MHz | 220mA | 0.3Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN2N1W02□ | 2.1nH ±0.05nH | 500MHz | 220mA | 0.3Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN2N2B02□ | 2.2nH ±0.1nH | 500MHz | 220mA | 0.3Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN2N2W02□ | 2.2nH ±0.05nH | 500MHz | 220mA | 0.3Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN2N3W02□ | 2.3nH ±0.05nH | 500MHz | 220mA | 0.3Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN2N4B02□ | 2.4nH ±0.1nH | 500MHz | 220mA | 0.3Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN2N4W02□ | 2.4nH ±0.05nH | 500MHz | 220mA | 0.3Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN2N5W02□ | 2.5nH ±0.05nH | 500MHz | 220mA | 0.3Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN2N6W02□ | 2.6nH ±0.05nH | 500MHz | 220mA | 0.3Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN2N7B02□ | 2.7nH ±0.1nH | 500MHz | 220mA | 0.3Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN2N7W02□ | 2.7nH ±0.05nH | 500MHz | 220mA | 0.3Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN2N8W02□ | 2.8nH ±0.05nH | 500MHz | 190mA | 0.4Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN2N9W02□ | 2.9nH ±0.05nH | 500MHz | 190mA | 0.4Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN3N0B02□ | 3.0nH ±0.1nH | 500MHz | 190mA | 0.4Ω | 13 | 500MHz | 6000MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C
For reflow soldering only.


Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|---------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQP15MN3N0W02□ | 3.0nH ±0.05nH | 500MHz | 190mA | 0.4Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN3N1W02□ | 3.1nH ±0.05nH | 500MHz | 190mA | 0.4Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN3N2W02□ | 3.2nH ±0.05nH | 500MHz | 190mA | 0.4Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN3N3B02□ | 3.3nH ±0.1nH | 500MHz | 190mA | 0.4Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN3N3W02□ | 3.3nH ±0.05nH | 500MHz | 190mA | 0.4Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN3N4W02□ | 3.4nH ±0.05nH | 500MHz | 170mA | 0.5Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN3N5W02□ | 3.5nH ±0.05nH | 500MHz | 170mA | 0.5Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN3N6B02□ | 3.6nH ±0.1nH | 500MHz | 170mA | 0.5Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN3N6W02□ | 3.6nH ±0.05nH | 500MHz | 170mA | 0.5Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN3N7W02□ | 3.7nH ±0.05nH | 500MHz | 170mA | 0.5Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN3N8W02□ | 3.8nH ±0.05nH | 500MHz | 170mA | 0.5Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN3N9B02□ | 3.9nH ±0.1nH | 500MHz | 170mA | 0.5Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN3N9W02□ | 3.9nH ±0.05nH | 500MHz | 170mA | 0.5Ω | 13 | 500MHz | 6000MHz | |
| LQP15MN4N3B02□ | 4.3nH ±0.1nH | 500MHz | 160mA | 0.6Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN4N7B02□ | 4.7nH ±0.1nH | 500MHz | 160mA | 0.6Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN5N1B02□ | 5.1nH ±0.1nH | 500MHz | 140mA | 0.7Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN5N6B02□ | 5.6nH ±0.1nH | 500MHz | 140mA | 0.7Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN6N2B02□ | 6.2nH ±0.1nH | 500MHz | 130mA | 0.9Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN6N8B02□ | 6.8nH ±0.1nH | 500MHz | 130mA | 0.9Ω | 13 | 500MHz | 6000MHz | Kit |
| LQP15MN7N5B02□ | 7.5nH ±0.1nH | 500MHz | 110mA | 1.1Ω | 13 | 500MHz | 5500MHz | Kit |
| LQP15MN8N2B02□ | 8.2nH ±0.1nH | 500MHz | 110mA | 1.1Ω | 13 | 500MHz | 5500MHz | Kit |
| LQP15MN9N1B02□ | 9.1nH ±0.1nH | 500MHz | 100mA | 1.3Ω | 13 | 500MHz | 4500MHz | Kit |
| LQP15MN10NG02□ | 10nH ±2% | 500MHz | 100mA | 1.3Ω | 13 | 500MHz | 4500MHz | Kit |
| LQP15MN12NG02□ | 12nH ±2% | 500MHz | 90mA | 1.6Ω | 13 | 500MHz | 3700MHz | Kit |
| LQP15MN15NG02□ | 15nH ±2% | 500MHz | 90mA | 1.8Ω | 13 | 500MHz | 3300MHz | Kit |
| LQP15MN18NG02□ | 18nH ±2% | 500MHz | 80mA | 2.0Ω | 13 | 500MHz | 3100MHz | Kit |
| LQP15MN22NG02□ | 22nH ±2% | 500MHz | 70mA | 2.6Ω | 13 | 500MHz | 2800MHz | Kit |
| LQP15MN27NG02□ | 27nH ±2% | 500MHz | 70mA | 3.1Ω | 13 | 500MHz | 2500MHz | Kit |
| LQP15MN33NG02□ | 33nH ±2% | 500MHz | 60mA | 3.8Ω | 13 | 500MHz | 2100MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C
 For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Reference Data

4991A&16197A


| Part Number | Q (Typ.) | | | | |
|---------------|----------|--------|--------|--------|--------|
| | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQP15MN1N0□02 | 80 | 88 | 157 | 172 | 188 |
| LQP15MN1N1□02 | 60 | 65 | 107 | 115 | 125 |
| LQP15MN1N2□02 | 56 | 61 | 100 | 104 | 114 |
| LQP15MN1N3□02 | 46 | 50 | 77 | 81 | 86 |
| LQP15MN1N4□02 | 40 | 44 | 65 | 68 | 73 |
| LQP15MN1N5□02 | 34 | 36 | 55 | 57 | 62 |
| LQP15MN1N6□02 | 25 | 27 | 40 | 42 | 46 |
| LQP15MN1N7□02 | 29 | 32 | 47 | 49 | 53 |
| LQP15MN1N8□02 | 32 | 35 | 51 | 53 | 57 |
| LQP15MN1N9□02 | 34 | 36 | 54 | 56 | 60 |
| LQP15MN2N0□02 | 32 | 34 | 51 | 53 | 57 |
| LQP15MN2N1□02 | 34 | 37 | 55 | 57 | 61 |
| LQP15MN2N2□02 | 31 | 33 | 49 | 51 | 55 |
| LQP15MN2N3□02 | 32 | 34 | 51 | 54 | 58 |
| LQP15MN2N4□02 | 32 | 34 | 51 | 53 | 57 |
| LQP15MN2N5□02 | 31 | 33 | 50 | 52 | 56 |
| LQP15MN2N6□02 | 29 | 32 | 47 | 49 | 53 |
| LQP15MN2N7□02 | 29 | 32 | 47 | 49 | 53 |
| LQP15MN2N8□02 | 28 | 30 | 45 | 46 | 50 |
| LQP15MN2N9□02 | 28 | 30 | 44 | 45 | 48 |
| LQP15MN3N0□02 | 27 | 29 | 43 | 44 | 48 |
| LQP15MN3N1□02 | 25 | 27 | 39 | 41 | 44 |
| LQP15MN3N2□02 | 24 | 26 | 36 | 37 | 40 |
| LQP15MN3N3□02 | 23 | 25 | 36 | 37 | 39 |
| LQP15MN3N4□02 | 24 | 25 | 36 | 37 | 39 |
| LQP15MN3N5□02 | 25 | 27 | 38 | 39 | 42 |
| LQP15MN3N6□02 | 24 | 26 | 38 | 39 | 42 |
| LQP15MN3N7□02 | 25 | 27 | 38 | 39 | 42 |
| LQP15MN3N8□02 | 25 | 26 | 37 | 38 | 41 |
| LQP15MN3N9□02 | 25 | 27 | 38 | 40 | 42 |
| LQP15MN4N3□02 | 25 | 26 | 38 | 39 | 42 |
| LQP15MN4N7□02 | 26 | 28 | 40 | 41 | 43 |
| LQP15MN5N1□02 | 26 | 27 | 39 | 40 | 42 |
| LQP15MN5N6□02 | 22 | 23 | 32 | 32 | 34 |
| LQP15MN6N2□02 | 22 | 23 | 33 | 33 | 35 |
| LQP15MN6N8□02 | 22 | 24 | 32 | 33 | 34 |
| LQP15MN7N5□02 | 23 | 24 | 32 | 33 | 34 |
| LQP15MN8N2□02 | 23 | 25 | 34 | 35 | 36 |
| LQP15MN9N1□02 | 23 | 24 | 33 | 33 | 34 |
| LQP15MN10N□02 | 23 | 24 | 31 | 31 | - |
| LQP15MN12N□02 | 24 | 26 | 32 | 32 | - |
| LQP15MN15N□02 | 23 | 24 | 28 | 28 | - |
| LQP15MN18N□02 | 22 | 23 | 25 | 24 | - |
| LQP15MN22N□02 | 23 | 24 | 24 | 22 | - |
| LQP15MN27N□02 | 23 | 24 | 22 | 20 | - |
| LQP15MN33N□02 | 22 | 23 | 20 | - | - |

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQP18MN_02 Series 0603/1608 (inch/mm)

Size Code 0603 (1608) in inch (in mm), Film Type

Appearance/Dimensions



(in mm)

Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| J | ø330mm Paper Taping | 10000 |
| B | Packing in Bulk | 500 |



Refer to pages 227 to 230 for mounting information.

Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|
| LQP18MN1N3C02□ | 1.3nH ±0.2nH | 500MHz | 300mA | 0.3Ω | 17 | 500MHz | 6000MHz |
| LQP18MN1N5C02□ | 1.5nH ±0.2nH | 500MHz | 300mA | 0.3Ω | 17 | 500MHz | 6000MHz |
| LQP18MN1N8C02□ | 1.8nH ±0.2nH | 500MHz | 250mA | 0.4Ω | 17 | 500MHz | 6000MHz |
| LQP18MN2N2C02□ | 2.2nH ±0.2nH | 500MHz | 250mA | 0.4Ω | 17 | 500MHz | 6000MHz |
| LQP18MN2N7C02□ | 2.7nH ±0.2nH | 500MHz | 250mA | 0.4Ω | 17 | 500MHz | 6000MHz |
| LQP18MN3N3C02□ | 3.3nH ±0.2nH | 500MHz | 250mA | 0.4Ω | 17 | 500MHz | 6000MHz |
| LQP18MN3N9C02□ | 3.9nH ±0.2nH | 500MHz | 200mA | 0.5Ω | 17 | 500MHz | 5900MHz |
| LQP18MN4N7C02□ | 4.7nH ±0.2nH | 500MHz | 200mA | 0.5Ω | 17 | 500MHz | 5200MHz |
| LQP18MN5N6C02□ | 5.6nH ±0.2nH | 500MHz | 200mA | 0.6Ω | 17 | 500MHz | 4700MHz |
| LQP18MN6N8C02□ | 6.8nH ±0.2nH | 500MHz | 200mA | 0.7Ω | 17 | 500MHz | 4300MHz |
| LQP18MN8N2C02□ | 8.2nH ±0.2nH | 500MHz | 150mA | 0.8Ω | 17 | 500MHz | 3600MHz |
| LQP18MN10NG02□ | 10nH ±2% | 500MHz | 150mA | 1.0Ω | 17 | 500MHz | 3400MHz |
| LQP18MN12NG02□ | 12nH ±2% | 500MHz | 150mA | 1.0Ω | 17 | 500MHz | 3000MHz |
| LQP18MN15NG02□ | 15nH ±2% | 500MHz | 150mA | 1.3Ω | 17 | 500MHz | 2700MHz |
| LQP18MN18NG02□ | 18nH ±2% | 500MHz | 100mA | 1.5Ω | 17 | 500MHz | 2300MHz |
| LQP18MN22NG02□ | 22nH ±2% | 500MHz | 100mA | 1.9Ω | 17 | 500MHz | 2100MHz |
| LQP18MN27NG02□ | 27nH ±2% | 500MHz | 100mA | 2.4Ω | 17 | 500MHz | 1900MHz |
| LQP18MN33NG02□ | 33nH ±2% | 500MHz | 100mA | 2.8Ω | 17 | 500MHz | 1700MHz |
| LQP18MN39NG02□ | 39nH ±2% | 500MHz | 100mA | 2.8Ω | 17 | 500MHz | 1400MHz |
| LQP18MN47NG02□ | 47nH ±2% | 300MHz | 100mA | 2.2Ω | 17 | 300MHz | 1200MHz |
| LQP18MN56NG02□ | 56nH ±2% | 300MHz | 50mA | 3.4Ω | 17 | 300MHz | 1000MHz |
| LQP18MN68NG02□ | 68nH ±2% | 300MHz | 50mA | 3.5Ω | 17 | 300MHz | 900MHz |
| LQP18MN82NG02□ | 82nH ±2% | 300MHz | 50mA | 4.6Ω | 17 | 300MHz | 800MHz |
| LQP18MNR10G02□ | 100nH ±2% | 300MHz | 50mA | 6.1Ω | 17 | 300MHz | 700MHz |

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C
For reflow soldering only.


Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQW03AW_00 Series

Suitable for Mounting in a Narrow Space in Antenna Matching Circuits

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 10000 |

Thickness 0.45mm max.
E-12 Step
E-24 Step
Reflow OK


Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|-----------|------------------|---------------------------------|---------|
| LQW03AW5N4C00□ | 5.4nH ±0.2nH | 100MHz | 420mA | 0.21Ω | 46 (Typ.) | 900MHz | 8.5GHz | New |
| LQW03AW5N4J00□ | 5.4nH ±5% | 100MHz | 420mA | 0.21Ω | 46 (Typ.) | 900MHz | 8.5GHz | New Kit |
| LQW03AW5N6C00□ | 5.6nH ±0.2nH | 100MHz | 330mA | 0.33Ω | 37 (Typ.) | 900MHz | 8.3GHz | New |
| LQW03AW5N6J00□ | 5.6nH ±5% | 100MHz | 330mA | 0.33Ω | 37 (Typ.) | 900MHz | 8.3GHz | New Kit |
| LQW03AW5N8C00□ | 5.8nH ±0.2nH | 100MHz | 460mA | 0.16Ω | 47 (Typ.) | 900MHz | 8.8GHz | New |
| LQW03AW5N8J00□ | 5.8nH ±5% | 100MHz | 460mA | 0.16Ω | 47 (Typ.) | 900MHz | 8.8GHz | New Kit |
| LQW03AW6N8C00□ | 6.8nH ±0.2nH | 100MHz | 460mA | 0.18Ω | 42 (Typ.) | 900MHz | 7.7GHz | New |
| LQW03AW6N8J00□ | 6.8nH ±5% | 100MHz | 460mA | 0.18Ω | 42 (Typ.) | 900MHz | 7.7GHz | New Kit |
| LQW03AW7N5C00□ | 7.5nH ±0.2nH | 100MHz | 400mA | 0.24Ω | 41 (Typ.) | 900MHz | 7.5GHz | New |
| LQW03AW7N5J00□ | 7.5nH ±5% | 100MHz | 400mA | 0.24Ω | 41 (Typ.) | 900MHz | 7.5GHz | New Kit |
| LQW03AW8N7C00□ | 8.7nH ±0.2nH | 100MHz | 290mA | 0.42Ω | 39 (Typ.) | 900MHz | 7.5GHz | New |
| LQW03AW8N7J00□ | 8.7nH ±5% | 100MHz | 290mA | 0.42Ω | 39 (Typ.) | 900MHz | 7.5GHz | New Kit |
| LQW03AW9N1C00□ | 9.1nH ±0.2nH | 100MHz | 460mA | 0.22Ω | 46 (Typ.) | 900MHz | 6.4GHz | New |
| LQW03AW9N1J00□ | 9.1nH ±5% | 100MHz | 460mA | 0.22Ω | 46 (Typ.) | 900MHz | 6.4GHz | New Kit |
| LQW03AW13NJ00□ | 13nH ±5% | 100MHz | 280mA | 0.54Ω | 39 (Typ.) | 900MHz | 5.9GHz | New Kit |

Operating Temperature Range (Self-temperature rise is included): -55°C~+125°C
For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Reference Data

4991A&16197A

| Part Number | Inductance (nH) | Q (Typ.) | | | | |
|-------------|-----------------|----------|--------|--------|--------|--------|
| | Nominal | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQW03AW5N4 | 5.4 | 43 | 46 | 64 | 66 | 69 |
| LQW03AW5N6 | 5.6 | 34 | 37 | 51 | 53 | 56 |
| LQW03AW5N8 | 5.8 | 44 | 48 | 67 | 68 | 71 |
| LQW03AW6N8 | 6.8 | 40 | 42 | 59 | 60 | 63 |
| LQW03AW7N5 | 7.5 | 38 | 41 | 57 | 58 | 61 |
| LQW03AW8N7 | 8.7 | 37 | 39 | 55 | 56 | 59 |
| LQW03AW9N1 | 9.1 | 42 | 46 | 63 | 63 | 65 |
| LQW03AW13N | 13.0 | 37 | 40 | 52 | 53 | 55 |


⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQW04AN_00

Series 03015/0804 (inch/mm)

Size Code 03015 (0804) in inch (in mm), Wound Type

Appearance/Dimensions



(in mm)

Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 10000 |
| B | Packing in Bulk | 500 |



Refer to pages 227 to 230 for mounting information.

Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW04AN1N1C00□ | 1.1nH ±0.2nH | 100MHz | 990mA | 0.03Ω | 15 | 250MHz | 20.0GHz | Kit |
| LQW04AN1N1D00□ | 1.1nH ±0.5nH | 100MHz | 990mA | 0.03Ω | 15 | 250MHz | 20.0GHz | |
| LQW04AN1N8C00□ | 1.8nH ±0.2nH | 100MHz | 700mA | 0.06Ω | 15 | 250MHz | 17.0GHz | Kit |
| LQW04AN1N8D00□ | 1.8nH ±0.5nH | 100MHz | 700mA | 0.06Ω | 15 | 250MHz | 17.0GHz | |
| LQW04AN2N7C00□ | 2.7nH ±0.2nH | 100MHz | 570mA | 0.07Ω | 15 | 250MHz | 15.0GHz | Kit |
| LQW04AN2N7D00□ | 2.7nH ±0.5nH | 100MHz | 570mA | 0.07Ω | 15 | 250MHz | 15.0GHz | |
| LQW04AN3N0C00□ | 3.0nH ±0.2nH | 100MHz | 620mA | 0.07Ω | 15 | 250MHz | 13.0GHz | Kit |
| LQW04AN3N0D00□ | 3.0nH ±0.5nH | 100MHz | 620mA | 0.07Ω | 15 | 250MHz | 13.0GHz | |
| LQW04AN3N3C00□ | 3.3nH ±0.2nH | 100MHz | 440mA | 0.14Ω | 10 | 250MHz | 10.0GHz | Kit |
| LQW04AN3N3D00□ | 3.3nH ±0.5nH | 100MHz | 440mA | 0.14Ω | 10 | 250MHz | 10.0GHz | |
| LQW04AN3N6C00□ | 3.6nH ±0.2nH | 100MHz | 530mA | 0.10Ω | 15 | 250MHz | 13.0GHz | Kit |
| LQW04AN3N6D00□ | 3.6nH ±0.5nH | 100MHz | 530mA | 0.10Ω | 15 | 250MHz | 13.0GHz | |
| LQW04AN3N9C00□ | 3.9nH ±0.2nH | 100MHz | 530mA | 0.10Ω | 15 | 250MHz | 12.0GHz | Kit |
| LQW04AN3N9D00□ | 3.9nH ±0.5nH | 100MHz | 530mA | 0.10Ω | 15 | 250MHz | 12.0GHz | |
| LQW04AN4N3C00□ | 4.3nH ±0.2nH | 100MHz | 530mA | 0.10Ω | 15 | 250MHz | 11.0GHz | Kit |
| LQW04AN4N3D00□ | 4.3nH ±0.5nH | 100MHz | 530mA | 0.10Ω | 15 | 250MHz | 11.0GHz | |
| LQW04AN4N7C00□ | 4.7nH ±0.2nH | 100MHz | 440mA | 0.14Ω | 20 | 250MHz | 10.0GHz | Kit |
| LQW04AN4N7D00□ | 4.7nH ±0.5nH | 100MHz | 440mA | 0.14Ω | 20 | 250MHz | 10.0GHz | |
| LQW04AN5N1C00□ | 5.1nH ±0.2nH | 100MHz | 470mA | 0.12Ω | 20 | 250MHz | 10.0GHz | Kit |
| LQW04AN5N1D00□ | 5.1nH ±0.5nH | 100MHz | 470mA | 0.12Ω | 20 | 250MHz | 10.0GHz | |
| LQW04AN5N6C00□ | 5.6nH ±0.2nH | 100MHz | 470mA | 0.12Ω | 20 | 250MHz | 9.0GHz | Kit |
| LQW04AN5N6D00□ | 5.6nH ±0.5nH | 100MHz | 470mA | 0.12Ω | 20 | 250MHz | 9.0GHz | |
| LQW04AN6N2C00□ | 6.2nH ±0.2nH | 100MHz | 390mA | 0.19Ω | 20 | 250MHz | 9.0GHz | Kit |
| LQW04AN6N2D00□ | 6.2nH ±0.5nH | 100MHz | 390mA | 0.19Ω | 20 | 250MHz | 9.0GHz | |
| LQW04AN6N8C00□ | 6.8nH ±0.2nH | 100MHz | 440mA | 0.14Ω | 20 | 250MHz | 9.0GHz | Kit |
| LQW04AN6N8D00□ | 6.8nH ±0.5nH | 100MHz | 440mA | 0.14Ω | 20 | 250MHz | 9.0GHz | |
| LQW04AN7N5C00□ | 7.5nH ±0.2nH | 100MHz | 440mA | 0.14Ω | 20 | 250MHz | 8.0GHz | Kit |
| LQW04AN7N5D00□ | 7.5nH ±0.5nH | 100MHz | 440mA | 0.14Ω | 20 | 250MHz | 8.0GHz | |
| LQW04AN8N2C00□ | 8.2nH ±0.2nH | 100MHz | 350mA | 0.23Ω | 20 | 250MHz | 8.0GHz | Kit |
| LQW04AN8N2D00□ | 8.2nH ±0.5nH | 100MHz | 350mA | 0.23Ω | 20 | 250MHz | 8.0GHz | |
| LQW04AN9N1C00□ | 9.1nH ±0.2nH | 100MHz | 400mA | 0.16Ω | 20 | 250MHz | 7.0GHz | Kit |
| LQW04AN9N1D00□ | 9.1nH ±0.5nH | 100MHz | 400mA | 0.16Ω | 20 | 250MHz | 7.0GHz | |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.


Continued on the following page.

[△]Note • Please read rating and [△]CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|---------------|---------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW04AN10NH00 | 10nH \pm 3% | 100MHz | 330mA | 0.26 Ω | 20 | 250MHz | 7.0GHz | Kit |
| LQW04AN10NJ00 | 10nH \pm 5% | 100MHz | 330mA | 0.26 Ω | 20 | 250MHz | 7.0GHz | |
| LQW04AN11NH00 | 11nH \pm 3% | 100MHz | 310mA | 0.28 Ω | 15 | 250MHz | 7.0GHz | Kit |
| LQW04AN11NJ00 | 11nH \pm 5% | 100MHz | 310mA | 0.28 Ω | 15 | 250MHz | 7.0GHz | |
| LQW04AN12NH00 | 12nH \pm 3% | 100MHz | 310mA | 0.28 Ω | 15 | 250MHz | 6.0GHz | Kit |
| LQW04AN12NJ00 | 12nH \pm 5% | 100MHz | 310mA | 0.28 Ω | 15 | 250MHz | 6.0GHz | |
| LQW04AN13NH00 | 13nH \pm 3% | 100MHz | 280mA | 0.34 Ω | 15 | 250MHz | 6.0GHz | Kit |
| LQW04AN13NJ00 | 13nH \pm 5% | 100MHz | 280mA | 0.34 Ω | 15 | 250MHz | 6.0GHz | |
| LQW04AN15NH00 | 15nH \pm 3% | 100MHz | 240mA | 0.48 Ω | 15 | 250MHz | 5.5GHz | Kit |
| LQW04AN15NJ00 | 15nH \pm 5% | 100MHz | 240mA | 0.48 Ω | 15 | 250MHz | 5.5GHz | |
| LQW04AN16NH00 | 16nH \pm 3% | 100MHz | 270mA | 0.38 Ω | 15 | 250MHz | 5.5GHz | Kit |
| LQW04AN16NJ00 | 16nH \pm 5% | 100MHz | 270mA | 0.38 Ω | 15 | 250MHz | 5.5GHz | |
| LQW04AN18NH00 | 18nH \pm 3% | 100MHz | 220mA | 0.54 Ω | 15 | 250MHz | 5.0GHz | Kit |
| LQW04AN18NJ00 | 18nH \pm 5% | 100MHz | 220mA | 0.54 Ω | 15 | 250MHz | 5.0GHz | |
| LQW04AN19NH00 | 19nH \pm 3% | 100MHz | 160mA | 0.73 Ω | 15 | 250MHz | 5.0GHz | Kit |
| LQW04AN19NJ00 | 19nH \pm 5% | 100MHz | 160mA | 0.73 Ω | 15 | 250MHz | 5.0GHz | |
| LQW04AN20NH00 | 20nH \pm 3% | 100MHz | 210mA | 0.56 Ω | 15 | 250MHz | 5.0GHz | Kit |
| LQW04AN20NJ00 | 20nH \pm 5% | 100MHz | 210mA | 0.56 Ω | 15 | 250MHz | 5.0GHz | |
| LQW04AN22NH00 | 22nH \pm 3% | 100MHz | 200mA | 0.63 Ω | 15 | 250MHz | 5.0GHz | Kit |
| LQW04AN22NJ00 | 22nH \pm 5% | 100MHz | 200mA | 0.63 Ω | 15 | 250MHz | 5.0GHz | |
| LQW04AN23NH00 | 23nH \pm 3% | 100MHz | 160mA | 0.95 Ω | 15 | 250MHz | 4.0GHz | Kit |
| LQW04AN23NJ00 | 23nH \pm 5% | 100MHz | 160mA | 0.95 Ω | 15 | 250MHz | 4.0GHz | |
| LQW04AN24NH00 | 24nH \pm 3% | 100MHz | 160mA | 0.95 Ω | 15 | 250MHz | 4.0GHz | Kit |
| LQW04AN24NJ00 | 24nH \pm 5% | 100MHz | 160mA | 0.95 Ω | 15 | 250MHz | 4.0GHz | |
| LQW04AN25NH00 | 25nH \pm 3% | 100MHz | 160mA | 0.95 Ω | 15 | 250MHz | 4.0GHz | Kit |
| LQW04AN25NJ00 | 25nH \pm 5% | 100MHz | 160mA | 0.95 Ω | 15 | 250MHz | 4.0GHz | |
| LQW04AN27NH00 | 27nH \pm 3% | 100MHz | 160mA | 0.95 Ω | 15 | 250MHz | 4.0GHz | Kit |
| LQW04AN27NJ00 | 27nH \pm 5% | 100MHz | 160mA | 0.95 Ω | 15 | 250MHz | 4.0GHz | |
| LQW04AN33NH00 | 33nH \pm 3% | 100MHz | 140mA | 1.11 Ω | 15 | 250MHz | 4.0GHz | Kit |
| LQW04AN33NJ00 | 33nH \pm 5% | 100MHz | 140mA | 1.11 Ω | 15 | 250MHz | 4.0GHz | |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Reference Data

4991A&16197A


| Part Number | Inductance (nH) | Q (Typ.) | | | | |
|-------------|-----------------|----------|--------|--------|--------|--------|
| | Nominal | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQW04AN1N1 | 1.1 | 61 | 65 | 79 | 85 | 92 |
| LQW04AN1N8 | 1.8 | 48 | 52 | 75 | 80 | 88 |
| LQW04AN2N7 | 2.7 | 46 | 50 | 70 | 75 | 85 |
| LQW04AN3N0 | 3.0 | 47 | 50 | 70 | 75 | 85 |
| LQW04AN3N3 | 3.3 | 40 | 43 | 62 | 64 | 69 |
| LQW04AN3N6 | 3.6 | 46 | 48 | 69 | 72 | 78 |
| LQW04AN3N9 | 3.9 | 46 | 48 | 69 | 72 | 79 |
| LQW04AN4N3 | 4.3 | 47 | 50 | 69 | 73 | 79 |
| LQW04AN4N7 | 4.7 | 43 | 45 | 63 | 67 | 72 |
| LQW04AN5N1 | 5.1 | 47 | 49 | 69 | 72 | 80 |
| LQW04AN5N6 | 5.6 | 47 | 49 | 69 | 72 | 79 |
| LQW04AN6N2 | 6.2 | 42 | 45 | 63 | 65 | 70 |
| LQW04AN6N8 | 6.8 | 45 | 48 | 66 | 68 | 74 |
| LQW04AN7N5 | 7.5 | 45 | 47 | 66 | 67 | 70 |
| LQW04AN8N2 | 8.2 | 43 | 45 | 61 | 63 | 67 |
| LQW04AN9N1 | 9.1 | 45 | 47 | 65 | 66 | 68 |
| LQW04AN10N | 10 | 43 | 46 | 61 | 63 | 65 |
| LQW04AN11N | 11 | 43 | 46 | 63 | 65 | 67 |
| LQW04AN12N | 12 | 44 | 47 | 63 | 64 | 66 |
| LQW04AN13N | 13 | 44 | 46 | 62 | 64 | 66 |
| LQW04AN15N | 15 | 43 | 45 | 59 | 60 | 61 |
| LQW04AN16N | 16 | 43 | 47 | 60 | 61 | 61 |
| LQW04AN18N | 18 | 42 | 45 | 57 | 58 | 57 |
| LQW04AN20N | 20 | 42 | 45 | 57 | 58 | 55 |
| LQW04AN22N | 22 | 42 | 46 | 56 | 57 | 55 |
| LQW04AN27N | 27 | 42 | 44 | 51 | 50 | 47 |
| LQW04AN33N | 33 | 43 | 45 | 52 | 50 | 47 |

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQW15AN_00 Series 0402/1005 (inch/mm)

Size Code 0402 (1005) in inch (in mm), Wound Type

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 10000 |
| B | Packing in Bulk | 500 |



Refer to pages 227 to 230 for mounting information.

Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW15AN1N5B00□ | 1.5nH ±0.1nH | 100MHz | 1000mA | 0.03Ω | 10 | 250MHz | 18.0GHz | Kit |
| LQW15AN1N5C00□ | 1.5nH ±0.2nH | 100MHz | 1000mA | 0.03Ω | 10 | 250MHz | 18.0GHz | |
| LQW15AN1N5D00□ | 1.5nH ±0.5nH | 100MHz | 1000mA | 0.03Ω | 10 | 250MHz | 18.0GHz | |
| LQW15AN2N4B00□ | 2.4nH ±0.1nH | 100MHz | 850mA | 0.05Ω | 20 | 250MHz | 15.0GHz | Kit |
| LQW15AN2N4C00□ | 2.4nH ±0.2nH | 100MHz | 850mA | 0.05Ω | 20 | 250MHz | 15.0GHz | |
| LQW15AN2N4D00□ | 2.4nH ±0.5nH | 100MHz | 850mA | 0.05Ω | 20 | 250MHz | 15.0GHz | |
| LQW15AN2N5B00□ | 2.5nH ±0.1nH | 100MHz | 850mA | 0.05Ω | 20 | 250MHz | 15.0GHz | Kit |
| LQW15AN2N5C00□ | 2.5nH ±0.2nH | 100MHz | 850mA | 0.05Ω | 20 | 250MHz | 15.0GHz | |
| LQW15AN2N5D00□ | 2.5nH ±0.5nH | 100MHz | 850mA | 0.05Ω | 20 | 250MHz | 15.0GHz | |
| LQW15AN2N7B00□ | 2.7nH ±0.1nH | 100MHz | 850mA | 0.05Ω | 20 | 250MHz | 15.0GHz | Kit |
| LQW15AN2N7C00□ | 2.7nH ±0.2nH | 100MHz | 850mA | 0.05Ω | 20 | 250MHz | 15.0GHz | |
| LQW15AN2N7D00□ | 2.7nH ±0.5nH | 100MHz | 850mA | 0.05Ω | 20 | 250MHz | 15.0GHz | |
| LQW15AN2N9B00□ | 2.9nH ±0.1nH | 100MHz | 750mA | 0.07Ω | 20 | 250MHz | 15.0GHz | Kit |
| LQW15AN2N9C00□ | 2.9nH ±0.2nH | 100MHz | 750mA | 0.07Ω | 20 | 250MHz | 15.0GHz | |
| LQW15AN2N9D00□ | 2.9nH ±0.5nH | 100MHz | 750mA | 0.07Ω | 20 | 250MHz | 15.0GHz | |
| LQW15AN3N9B00□ | 3.9nH ±0.1nH | 100MHz | 750mA | 0.07Ω | 25 | 250MHz | 10.0GHz | Kit |
| LQW15AN3N9C00□ | 3.9nH ±0.2nH | 100MHz | 750mA | 0.07Ω | 25 | 250MHz | 10.0GHz | |
| LQW15AN3N9D00□ | 3.9nH ±0.5nH | 100MHz | 750mA | 0.07Ω | 25 | 250MHz | 10.0GHz | |
| LQW15AN4N1B00□ | 4.1nH ±0.1nH | 100MHz | 750mA | 0.07Ω | 25 | 250MHz | 10.0GHz | Kit |
| LQW15AN4N1C00□ | 4.1nH ±0.2nH | 100MHz | 750mA | 0.07Ω | 25 | 250MHz | 10.0GHz | |
| LQW15AN4N1D00□ | 4.1nH ±0.5nH | 100MHz | 750mA | 0.07Ω | 25 | 250MHz | 10.0GHz | |
| LQW15AN4N3B00□ | 4.3nH ±0.1nH | 100MHz | 750mA | 0.07Ω | 25 | 250MHz | 10.0GHz | Kit |
| LQW15AN4N3C00□ | 4.3nH ±0.2nH | 100MHz | 750mA | 0.07Ω | 25 | 250MHz | 10.0GHz | |
| LQW15AN4N3D00□ | 4.3nH ±0.5nH | 100MHz | 750mA | 0.07Ω | 25 | 250MHz | 10.0GHz | |
| LQW15AN4N7B00□ | 4.7nH ±0.1nH | 100MHz | 750mA | 0.07Ω | 25 | 250MHz | 8.0GHz | Kit |
| LQW15AN4N7C00□ | 4.7nH ±0.2nH | 100MHz | 750mA | 0.07Ω | 25 | 250MHz | 8.0GHz | |
| LQW15AN4N7D00□ | 4.7nH ±0.5nH | 100MHz | 750mA | 0.07Ω | 25 | 250MHz | 8.0GHz | |
| LQW15AN5N1B00□ | 5.1nH ±0.1nH | 100MHz | 600mA | 0.12Ω | 25 | 250MHz | 8.0GHz | Kit |
| LQW15AN5N1C00□ | 5.1nH ±0.2nH | 100MHz | 600mA | 0.12Ω | 25 | 250MHz | 8.0GHz | |
| LQW15AN5N1D00□ | 5.1nH ±0.5nH | 100MHz | 600mA | 0.12Ω | 25 | 250MHz | 8.0GHz | |
| LQW15AN5N8B00□ | 5.8nH ±0.1nH | 100MHz | 700mA | 0.12Ω | 25 | 250MHz | 8.0GHz | Kit |
| LQW15AN5N8C00□ | 5.8nH ±0.2nH | 100MHz | 700mA | 0.12Ω | 25 | 250MHz | 8.0GHz | |


Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW15AN5N8D00□ | 5.8nH ±0.5nH | 100MHz | 700mA | 0.12Ω | 25 | 250MHz | 8.0GHz | |
| LQW15AN6N2B00□ | 6.2nH ±0.1nH | 100MHz | 700mA | 0.09Ω | 25 | 250MHz | 8.0GHz | Kit |
| LQW15AN6N2C00□ | 6.2nH ±0.2nH | 100MHz | 700mA | 0.09Ω | 25 | 250MHz | 8.0GHz | |
| LQW15AN6N2D00□ | 6.2nH ±0.5nH | 100MHz | 700mA | 0.09Ω | 25 | 250MHz | 8.0GHz | |
| LQW15AN6N8G00□ | 6.8nH ±2% | 100MHz | 700mA | 0.09Ω | 25 | 250MHz | 6.0GHz | Kit |
| LQW15AN6N8H00□ | 6.8nH ±3% | 100MHz | 700mA | 0.09Ω | 25 | 250MHz | 6.0GHz | |
| LQW15AN6N8J00□ | 6.8nH ±5% | 100MHz | 700mA | 0.09Ω | 25 | 250MHz | 6.0GHz | |
| LQW15AN7N3G00□ | 7.3nH ±2% | 100MHz | 570mA | 0.13Ω | 25 | 250MHz | 6.0GHz | Kit |
| LQW15AN7N3H00□ | 7.3nH ±3% | 100MHz | 570mA | 0.13Ω | 25 | 250MHz | 6.0GHz | |
| LQW15AN7N3J00□ | 7.3nH ±5% | 100MHz | 570mA | 0.13Ω | 25 | 250MHz | 6.0GHz | |
| LQW15AN7N5G00□ | 7.5nH ±2% | 100MHz | 570mA | 0.13Ω | 25 | 250MHz | 6.0GHz | Kit |
| LQW15AN7N5H00□ | 7.5nH ±3% | 100MHz | 570mA | 0.13Ω | 25 | 250MHz | 6.0GHz | |
| LQW15AN7N5J00□ | 7.5nH ±5% | 100MHz | 570mA | 0.13Ω | 25 | 250MHz | 6.0GHz | |
| LQW15AN8N2G00□ | 8.2nH ±2% | 100MHz | 540mA | 0.14Ω | 25 | 250MHz | 5.5GHz | Kit |
| LQW15AN8N2H00□ | 8.2nH ±3% | 100MHz | 540mA | 0.14Ω | 25 | 250MHz | 5.5GHz | |
| LQW15AN8N2J00□ | 8.2nH ±5% | 100MHz | 540mA | 0.14Ω | 25 | 250MHz | 5.5GHz | |
| LQW15AN8N7G00□ | 8.7nH ±2% | 100MHz | 540mA | 0.14Ω | 25 | 250MHz | 5.5GHz | Kit |
| LQW15AN8N7H00□ | 8.7nH ±3% | 100MHz | 540mA | 0.14Ω | 25 | 250MHz | 5.5GHz | |
| LQW15AN8N7J00□ | 8.7nH ±5% | 100MHz | 540mA | 0.14Ω | 25 | 250MHz | 5.5GHz | |
| LQW15AN9N1G00□ | 9.1nH ±2% | 100MHz | 540mA | 0.14Ω | 25 | 250MHz | 5.5GHz | Kit |
| LQW15AN9N1H00□ | 9.1nH ±3% | 100MHz | 540mA | 0.14Ω | 25 | 250MHz | 5.5GHz | |
| LQW15AN9N1J00□ | 9.1nH ±5% | 100MHz | 540mA | 0.14Ω | 25 | 250MHz | 5.5GHz | |
| LQW15AN9N5G00□ | 9.5nH ±2% | 100MHz | 540mA | 0.14Ω | 25 | 250MHz | 5.5GHz | Kit |
| LQW15AN9N5H00□ | 9.5nH ±3% | 100MHz | 540mA | 0.14Ω | 25 | 250MHz | 5.5GHz | |
| LQW15AN9N5J00□ | 9.5nH ±5% | 100MHz | 540mA | 0.14Ω | 25 | 250MHz | 5.5GHz | |
| LQW15AN10NG00□ | 10nH ±2% | 100MHz | 500mA | 0.17Ω | 25 | 250MHz | 5.5GHz | Kit |
| LQW15AN10NH00□ | 10nH ±3% | 100MHz | 500mA | 0.17Ω | 25 | 250MHz | 5.5GHz | |
| LQW15AN10NJ00□ | 10nH ±5% | 100MHz | 500mA | 0.17Ω | 25 | 250MHz | 5.5GHz | |
| LQW15AN11NG00□ | 11nH ±2% | 100MHz | 500mA | 0.14Ω | 30 | 250MHz | 5.5GHz | Kit |
| LQW15AN11NH00□ | 11nH ±3% | 100MHz | 500mA | 0.14Ω | 30 | 250MHz | 5.5GHz | |
| LQW15AN11NJ00□ | 11nH ±5% | 100MHz | 500mA | 0.14Ω | 30 | 250MHz | 5.5GHz | |
| LQW15AN12NG00□ | 12nH ±2% | 100MHz | 500mA | 0.14Ω | 30 | 250MHz | 5.5GHz | Kit |
| LQW15AN12NH00□ | 12nH ±3% | 100MHz | 500mA | 0.14Ω | 30 | 250MHz | 5.5GHz | |
| LQW15AN12NJ00□ | 12nH ±5% | 100MHz | 500mA | 0.14Ω | 30 | 250MHz | 5.5GHz | |
| LQW15AN13NG00□ | 13nH ±2% | 100MHz | 430mA | 0.21Ω | 25 | 250MHz | 5.0GHz | Kit |
| LQW15AN13NH00□ | 13nH ±3% | 100MHz | 430mA | 0.21Ω | 25 | 250MHz | 5.0GHz | |
| LQW15AN13NJ00□ | 13nH ±5% | 100MHz | 430mA | 0.21Ω | 25 | 250MHz | 5.0GHz | |
| LQW15AN15NG00□ | 15nH ±2% | 100MHz | 460mA | 0.16Ω | 30 | 250MHz | 5.0GHz | Kit |
| LQW15AN15NH00□ | 15nH ±3% | 100MHz | 460mA | 0.16Ω | 30 | 250MHz | 5.0GHz | |
| LQW15AN15NJ00□ | 15nH ±5% | 100MHz | 460mA | 0.16Ω | 30 | 250MHz | 5.0GHz | |
| LQW15AN16NG00□ | 16nH ±2% | 100MHz | 370mA | 0.24Ω | 25 | 250MHz | 4.5GHz | Kit |
| LQW15AN16NH00□ | 16nH ±3% | 100MHz | 370mA | 0.24Ω | 25 | 250MHz | 4.5GHz | |
| LQW15AN16NJ00□ | 16nH ±5% | 100MHz | 370mA | 0.24Ω | 25 | 250MHz | 4.5GHz | |
| LQW15AN18NG00□ | 18nH ±2% | 100MHz | 370mA | 0.27Ω | 25 | 250MHz | 4.5GHz | Kit |
| LQW15AN18NH00□ | 18nH ±3% | 100MHz | 370mA | 0.27Ω | 25 | 250MHz | 4.5GHz | |
| LQW15AN18NJ00□ | 18nH ±5% | 100MHz | 370mA | 0.27Ω | 25 | 250MHz | 4.5GHz | |
| LQW15AN19NG00□ | 19nH ±2% | 100MHz | 370mA | 0.27Ω | 25 | 250MHz | 4.5GHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.



Continued on the following page. 

 Note • Please read rating and  CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW15AN19NH00□ | 19nH ±3% | 100MHz | 370mA | 0.27Ω | 25 | 250MHz | 4.5GHz | |
| LQW15AN19NJ00□ | 19nH ±5% | 100MHz | 370mA | 0.27Ω | 25 | 250MHz | 4.5GHz | |
| LQW15AN20NG00□ | 20nH ±2% | 100MHz | 370mA | 0.27Ω | 25 | 250MHz | 4.0GHz | Kit |
| LQW15AN20NH00□ | 20nH ±3% | 100MHz | 370mA | 0.27Ω | 25 | 250MHz | 4.0GHz | |
| LQW15AN20NJ00□ | 20nH ±5% | 100MHz | 370mA | 0.27Ω | 25 | 250MHz | 4.0GHz | |
| LQW15AN22NG00□ | 22nH ±2% | 100MHz | 310mA | 0.30Ω | 25 | 250MHz | 4.0GHz | Kit |
| LQW15AN22NH00□ | 22nH ±3% | 100MHz | 310mA | 0.30Ω | 25 | 250MHz | 4.0GHz | |
| LQW15AN22NJ00□ | 22nH ±5% | 100MHz | 310mA | 0.30Ω | 25 | 250MHz | 4.0GHz | |
| LQW15AN23NG00□ | 23nH ±2% | 100MHz | 310mA | 0.30Ω | 25 | 250MHz | 3.8GHz | Kit |
| LQW15AN23NH00□ | 23nH ±3% | 100MHz | 310mA | 0.30Ω | 25 | 250MHz | 3.8GHz | |
| LQW15AN23NJ00□ | 23nH ±5% | 100MHz | 310mA | 0.30Ω | 25 | 250MHz | 3.8GHz | |
| LQW15AN24NG00□ | 24nH ±2% | 100MHz | 280mA | 0.52Ω | 25 | 250MHz | 3.5GHz | Kit |
| LQW15AN24NH00□ | 24nH ±3% | 100MHz | 280mA | 0.52Ω | 25 | 250MHz | 3.5GHz | |
| LQW15AN24NJ00□ | 24nH ±5% | 100MHz | 280mA | 0.52Ω | 25 | 250MHz | 3.5GHz | |
| LQW15AN27NG00□ | 27nH ±2% | 100MHz | 280mA | 0.52Ω | 25 | 250MHz | 3.5GHz | Kit |
| LQW15AN27NH00□ | 27nH ±3% | 100MHz | 280mA | 0.52Ω | 25 | 250MHz | 3.5GHz | |
| LQW15AN27NJ00□ | 27nH ±5% | 100MHz | 280mA | 0.52Ω | 25 | 250MHz | 3.5GHz | |
| LQW15AN30NG00□ | 30nH ±2% | 100MHz | 270mA | 0.58Ω | 25 | 250MHz | 3.3GHz | Kit |
| LQW15AN30NH00□ | 30nH ±3% | 100MHz | 270mA | 0.58Ω | 25 | 250MHz | 3.3GHz | |
| LQW15AN30NJ00□ | 30nH ±5% | 100MHz | 270mA | 0.58Ω | 25 | 250MHz | 3.3GHz | |
| LQW15AN33NG00□ | 33nH ±2% | 100MHz | 260mA | 0.63Ω | 25 | 250MHz | 3.2GHz | Kit |
| LQW15AN33NH00□ | 33nH ±3% | 100MHz | 260mA | 0.63Ω | 25 | 250MHz | 3.2GHz | |
| LQW15AN33NJ00□ | 33nH ±5% | 100MHz | 260mA | 0.63Ω | 25 | 250MHz | 3.2GHz | |
| LQW15AN36NG00□ | 36nH ±2% | 100MHz | 260mA | 0.63Ω | 25 | 250MHz | 3.1GHz | Kit |
| LQW15AN36NH00□ | 36nH ±3% | 100MHz | 260mA | 0.63Ω | 25 | 250MHz | 3.1GHz | |
| LQW15AN36NJ00□ | 36nH ±5% | 100MHz | 260mA | 0.63Ω | 25 | 250MHz | 3.1GHz | |
| LQW15AN39NG00□ | 39nH ±2% | 100MHz | 250mA | 0.70Ω | 25 | 250MHz | 3.0GHz | Kit |
| LQW15AN39NH00□ | 39nH ±3% | 100MHz | 250mA | 0.70Ω | 25 | 250MHz | 3.0GHz | |
| LQW15AN39NJ00□ | 39nH ±5% | 100MHz | 250mA | 0.70Ω | 25 | 250MHz | 3.0GHz | |
| LQW15AN40NG00□ | 40nH ±2% | 100MHz | 250mA | 0.70Ω | 25 | 250MHz | 3.0GHz | Kit |
| LQW15AN40NH00□ | 40nH ±3% | 100MHz | 250mA | 0.70Ω | 25 | 250MHz | 3.0GHz | |
| LQW15AN40NJ00□ | 40nH ±5% | 100MHz | 250mA | 0.70Ω | 25 | 250MHz | 3.0GHz | |
| LQW15AN43NG00□ | 43nH ±2% | 100MHz | 250mA | 0.70Ω | 25 | 250MHz | 3.0GHz | Kit |
| LQW15AN43NH00□ | 43nH ±3% | 100MHz | 250mA | 0.70Ω | 25 | 250MHz | 3.0GHz | |
| LQW15AN43NJ00□ | 43nH ±5% | 100MHz | 250mA | 0.70Ω | 25 | 250MHz | 3.0GHz | |
| LQW15AN47NG00□ | 47nH ±2% | 100MHz | 210mA | 1.08Ω | 25 | 200MHz | 2.9GHz | Kit |
| LQW15AN47NH00□ | 47nH ±3% | 100MHz | 210mA | 1.08Ω | 25 | 200MHz | 2.9GHz | |
| LQW15AN47NJ00□ | 47nH ±5% | 100MHz | 210mA | 1.08Ω | 25 | 200MHz | 2.9GHz | |
| LQW15AN51NG00□ | 51nH ±2% | 100MHz | 210mA | 1.08Ω | 25 | 200MHz | 2.85GHz | Kit |
| LQW15AN51NH00□ | 51nH ±3% | 100MHz | 210mA | 1.08Ω | 25 | 200MHz | 2.85GHz | |
| LQW15AN51NJ00□ | 51nH ±5% | 100MHz | 210mA | 1.08Ω | 25 | 200MHz | 2.85GHz | |
| LQW15AN56NG00□ | 56nH ±2% | 100MHz | 200mA | 1.17Ω | 25 | 200MHz | 2.8GHz | Kit |
| LQW15AN56NH00□ | 56nH ±3% | 100MHz | 200mA | 1.17Ω | 25 | 200MHz | 2.8GHz | |
| LQW15AN56NJ00□ | 56nH ±5% | 100MHz | 200mA | 1.17Ω | 25 | 200MHz | 2.8GHz | |
| LQW15AN62NG00□ | 62nH ±2% | 100MHz | 145mA | 1.82Ω | 20 | 200MHz | 2.6GHz | Kit |
| LQW15AN62NH00□ | 62nH ±3% | 100MHz | 145mA | 1.82Ω | 20 | 200MHz | 2.6GHz | |
| LQW15AN62NJ00□ | 62nH ±5% | 100MHz | 145mA | 1.82Ω | 20 | 200MHz | 2.6GHz | |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.


Continued on the following page. 

 Note • Please read rating and  CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW15AN68NG00□ | 68nH ±2% | 100MHz | 140mA | 1.96Ω | 20 | 200MHz | 2.5GHz | Kit |
| LQW15AN68NJ00□ | 68nH ±5% | 100MHz | 140mA | 1.96Ω | 20 | 200MHz | 2.5GHz | |
| LQW15AN72NG00□ | 72nH ±2% | 100MHz | 135mA | 2.10Ω | 20 | 150MHz | 2.5GHz | Kit |
| LQW15AN72NJ00□ | 72nH ±5% | 100MHz | 135mA | 2.10Ω | 20 | 150MHz | 2.5GHz | |
| LQW15AN75NG00□ | 75nH ±2% | 100MHz | 135mA | 2.10Ω | 20 | 150MHz | 2.4GHz | Kit |
| LQW15AN75NJ00□ | 75nH ±5% | 100MHz | 135mA | 2.10Ω | 20 | 150MHz | 2.4GHz | |
| LQW15AN82NG00□ | 82nH ±2% | 100MHz | 130mA | 2.24Ω | 20 | 150MHz | 2.3GHz | Kit |
| LQW15AN82NJ00□ | 82nH ±5% | 100MHz | 130mA | 2.24Ω | 20 | 150MHz | 2.3GHz | |
| LQW15AN91NG00□ | 91nH ±2% | 100MHz | 125mA | 2.38Ω | 20 | 150MHz | 2.1GHz | Kit |
| LQW15AN91NJ00□ | 91nH ±5% | 100MHz | 125mA | 2.38Ω | 20 | 150MHz | 2.1GHz | |
| LQW15ANR10J00□ | 100nH ±5% | 100MHz | 120mA | 2.52Ω | 20 | 150MHz | 1.5GHz | Kit |
| LQW15ANR12J00□ | 120nH ±5% | 100MHz | 110mA | 2.66Ω | 20 | 150MHz | 1.0GHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
 For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Reference Data

LQW15AN_00

4991A&16197A


| Part Number | Inductance (nH) | Q (Typ.) | | | | |
|-------------|-----------------|----------|--------|--------|--------|--------|
| | Nominal | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQW15AN1N5 | 1.5 | 55 | 60 | 90 | 100 | 115 |
| LQW15AN2N4 | 2.4 | 65 | 67 | 98 | 108 | 120 |
| LQW15AN2N5 | 2.5 | 65 | 67 | 90 | 100 | 110 |
| LQW15AN2N7 | 2.7 | 67 | 73 | 100 | 105 | 120 |
| LQW15AN2N9 | 2.9 | 53 | 58 | 80 | 85 | 92 |
| LQW15AN3N9 | 3.9 | 58 | 61 | 88 | 92 | 100 |
| LQW15AN4N1 | 4.1 | 58 | 61 | 88 | 92 | 100 |
| LQW15AN4N3 | 4.3 | 58 | 61 | 88 | 92 | 100 |
| LQW15AN4N7 | 4.7 | 65 | 67 | 88 | 92 | 95 |
| LQW15AN5N1 | 5.1 | 60 | 65 | 85 | 90 | 95 |
| LQW15AN5N8 | 5.8 | 63 | 67 | 88 | 92 | 105 |
| LQW15AN6N2 | 6.2 | 63 | 65 | 90 | 95 | 105 |
| LQW15AN6N8 | 6.8 | 70 | 72 | 96 | 100 | 103 |
| LQW15AN7N3 | 7.3 | 58 | 63 | 88 | 90 | 92 |
| LQW15AN7N5 | 7.5 | 58 | 63 | 88 | 90 | 92 |
| LQW15AN8N2 | 8.2 | 62 | 67 | 90 | 95 | 102 |
| LQW15AN8N7 | 8.7 | 60 | 62 | 85 | 90 | 92 |
| LQW15AN9N1 | 9.1 | 62 | 68 | 90 | 92 | 95 |
| LQW15AN9N5 | 9.5 | 62 | 68 | 90 | 92 | 95 |
| LQW15AN10N | 10 | 60 | 65 | 82 | 85 | 84 |
| LQW15AN11N | 11 | 65 | 70 | 105 | 110 | 120 |
| LQW15AN12N | 12 | 60 | 62 | 85 | 90 | 91 |
| LQW15AN13N | 13 | 60 | 62 | 72 | 71 | 67 |
| LQW15AN15N | 15 | 60 | 65 | 85 | 88 | 90 |
| LQW15AN16N | 16 | 60 | 63 | 90 | 100 | 110 |
| LQW15AN18N | 18 | 63 | 65 | 88 | 87 | 85 |
| LQW15AN19N | 19 | 57 | 62 | 80 | 82 | 83 |
| LQW15AN20N | 20 | 57 | 62 | 80 | 82 | 83 |
| LQW15AN22N | 22 | 55 | 58 | 75 | 78 | - |
| LQW15AN23N | 23 | 55 | 58 | 75 | 78 | - |
| LQW15AN24N | 24 | 50 | 50 | 42 | - | - |
| LQW15AN27N | 27 | 55 | 56 | 58 | - | - |
| LQW15AN30N | 30 | 55 | 58 | 68 | - | - |
| LQW15AN33N | 33 | 55 | 56 | 53 | - | - |
| LQW15AN36N | 36 | 52 | 52 | 42 | - | - |
| LQW15AN39N | 39 | 55 | 56 | - | - | - |
| LQW15AN40N | 40 | 55 | 56 | - | - | - |
| LQW15AN43N | 43 | 55 | 56 | - | - | - |
| LQW15AN47N | 47 | 52 | 54 | - | - | - |
| LQW15AN51N | 51 | 52 | 54 | - | - | - |
| LQW15AN56N | 56 | 53 | 55 | - | - | - |
| LQW15AN62N | 62 | 51 | 52 | - | - | - |
| LQW15AN68N | 68 | 49 | 52 | - | - | - |
| LQW15AN72N | 72 | 49 | 52 | - | - | - |
| LQW15AN75N | 75 | 49 | 52 | - | - | - |
| LQW15AN82N | 82 | 49 | 50 | - | - | - |
| LQW15AN91N | 91 | 52 | 53 | - | - | - |
| LQW15ANR10 | 100 | 43 | 43 | - | - | - |
| LQW15ANR12 | 120 | 30 | 23 | - | - | - |

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQW15AN_10 Series 0402/1005 (inch/mm)

Size Code 0402 (1005) in inch (in mm), High Q, Low DC Resistance Type

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 10000 |
| B | Packing in Bulk | 500 |

Thickness 0.6mm max.
 Low Rdc
 E-12 Step
 E-24 Step
 Hi Q
 Tight Tolerance
 Reflow OK


Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW15AN1N3C10□ | 1.3nH ±0.2nH | 100MHz | 1200mA | 0.017Ω | 20 | 250MHz | 16.0GHz | Kit |
| LQW15AN1N3D10□ | 1.3nH ±0.5nH | 100MHz | 1200mA | 0.017Ω | 20 | 250MHz | 16.0GHz | |
| LQW15AN2N2C10□ | 2.2nH ±0.2nH | 100MHz | 1000mA | 0.027Ω | 25 | 250MHz | 14.0GHz | Kit |
| LQW15AN2N2D10□ | 2.2nH ±0.5nH | 100MHz | 1000mA | 0.027Ω | 25 | 250MHz | 14.0GHz | |
| LQW15AN2N4D10□ | 2.4nH ±0.5nH | 100MHz | 1000mA | 0.027Ω | 25 | 250MHz | 14.0GHz | Kit |
| LQW15AN3N3D10□ | 3.3nH ±0.5nH | 100MHz | 900mA | 0.040Ω | 30 | 250MHz | 12.0GHz | Kit |
| LQW15AN3N4C10□ | 3.4nH ±0.2nH | 100MHz | 900mA | 0.040Ω | 30 | 250MHz | 12.0GHz | Kit |
| LQW15AN3N4D10□ | 3.4nH ±0.5nH | 100MHz | 900mA | 0.040Ω | 30 | 250MHz | 12.0GHz | |
| LQW15AN3N6C10□ | 3.6nH ±0.2nH | 100MHz | 900mA | 0.040Ω | 30 | 250MHz | 9.5GHz | Kit |
| LQW15AN3N6D10□ | 3.6nH ±0.5nH | 100MHz | 900mA | 0.040Ω | 30 | 250MHz | 9.5GHz | |
| LQW15AN3N9D10□ | 3.9nH ±0.5nH | 100MHz | 900mA | 0.040Ω | 30 | 250MHz | 7.0GHz | Kit |
| LQW15AN4N7D10□ | 4.7nH ±0.5nH | 100MHz | 800mA | 0.051Ω | 30 | 250MHz | 8.0GHz | Kit |
| LQW15AN5N1C10□ | 5.1nH ±0.2nH | 100MHz | 800mA | 0.051Ω | 30 | 250MHz | 8.0GHz | Kit |
| LQW15AN5N1D10□ | 5.1nH ±0.5nH | 100MHz | 800mA | 0.051Ω | 30 | 250MHz | 8.0GHz | |
| LQW15AN5N6C10□ | 5.6nH ±0.2nH | 100MHz | 800mA | 0.051Ω | 30 | 250MHz | 8.0GHz | Kit |
| LQW15AN5N6D10□ | 5.6nH ±0.5nH | 100MHz | 800mA | 0.051Ω | 30 | 250MHz | 8.0GHz | |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
 For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Reference Data

LQW15AN_10

4991A&16197A


| Part Number | Inductance (nH) | Q (Typ.) | | | | |
|-------------|-----------------|----------|--------|--------|--------|--------|
| | Nominal | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQW15AN1N3 | 1.3 | 90 | 95 | 145 | 160 | 180 |
| LQW15AN2N2 | 2.2 | 85 | 90 | 130 | 140 | 160 |
| LQW15AN2N4 | 2.4 | 80 | 85 | 130 | 140 | 160 |
| LQW15AN3N3 | 3.3 | 80 | 85 | 120 | 128 | 140 |
| LQW15AN3N4 | 3.4 | 80 | 85 | 120 | 128 | 140 |
| LQW15AN3N6 | 3.6 | 73 | 75 | 110 | 115 | 130 |
| LQW15AN3N9 | 3.9 | 75 | 80 | 110 | 115 | 120 |
| LQW15AN4N7 | 4.7 | 75 | 80 | 113 | 120 | 132 |
| LQW15AN5N1 | 5.1 | 75 | 80 | 110 | 115 | 128 |
| LQW15AN5N6 | 5.6 | 70 | 75 | 100 | 105 | 110 |

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQW15AN_80 Series 0402/1005 (inch/mm)

Size Code 0402 (1005) in inch (in mm), Wound Type

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 10000 |
| B | Packing in Bulk | 500 |



Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW15AN1N3C80□ | 1.3nH ±0.2nH | 100MHz | 3150mA | 0.012Ω | 20 | 250MHz | 18.0GHz | Kit |
| LQW15AN1N3D80□ | 1.3nH ±0.5nH | 100MHz | 3150mA | 0.012Ω | 20 | 250MHz | 18.0GHz | |
| LQW15AN1N5C80□ | 1.5nH ±0.2nH | 100MHz | 2100mA | 0.028Ω | 20 | 250MHz | 18.0GHz | New |
| LQW15AN1N5D80□ | 1.5nH ±0.5nH | 100MHz | 2100mA | 0.028Ω | 20 | 250MHz | 18.0GHz | New |
| LQW15AN1N6C80□ | 1.6nH ±0.2nH | 100MHz | 1450mA | 0.045Ω | 20 | 250MHz | 18.0GHz | New |
| LQW15AN1N6D80□ | 1.6nH ±0.5nH | 100MHz | 1450mA | 0.045Ω | 20 | 250MHz | 18.0GHz | New |
| LQW15AN1N7C80□ | 1.7nH ±0.2nH | 100MHz | 1150mA | 0.065Ω | 20 | 250MHz | 18.0GHz | New |
| LQW15AN1N7D80□ | 1.7nH ±0.5nH | 100MHz | 1150mA | 0.065Ω | 20 | 250MHz | 18.0GHz | New |
| LQW15AN2N2B80□ | 2.2nH ±0.1nH | 100MHz | 2530mA | 0.022Ω | 30 | 250MHz | 15.5GHz | New |
| LQW15AN2N2C80□ | 2.2nH ±0.2nH | 100MHz | 2530mA | 0.022Ω | 30 | 250MHz | 15.5GHz | New |
| LQW15AN2N2D80□ | 2.2nH ±0.5nH | 100MHz | 2530mA | 0.022Ω | 30 | 250MHz | 15.5GHz | New |
| LQW15AN2N3B80□ | 2.3nH ±0.1nH | 100MHz | 2530mA | 0.022Ω | 30 | 250MHz | 15.5GHz | Kit |
| LQW15AN2N3C80□ | 2.3nH ±0.2nH | 100MHz | 2530mA | 0.022Ω | 30 | 250MHz | 15.5GHz | |
| LQW15AN2N3D80□ | 2.3nH ±0.5nH | 100MHz | 2530mA | 0.022Ω | 30 | 250MHz | 15.5GHz | |
| LQW15AN2N4B80□ | 2.4nH ±0.1nH | 100MHz | 2530mA | 0.022Ω | 30 | 250MHz | 15.5GHz | Kit |
| LQW15AN2N4C80□ | 2.4nH ±0.2nH | 100MHz | 2530mA | 0.022Ω | 30 | 250MHz | 15.5GHz | |
| LQW15AN2N4D80□ | 2.4nH ±0.5nH | 100MHz | 2530mA | 0.022Ω | 30 | 250MHz | 15.5GHz | |
| LQW15AN2N5B80□ | 2.5nH ±0.1nH | 100MHz | 2100mA | 0.030Ω | 30 | 250MHz | 15.5GHz | New |
| LQW15AN2N5C80□ | 2.5nH ±0.2nH | 100MHz | 2100mA | 0.030Ω | 30 | 250MHz | 15.5GHz | New |
| LQW15AN2N5D80□ | 2.5nH ±0.5nH | 100MHz | 2100mA | 0.030Ω | 30 | 250MHz | 15.5GHz | New |
| LQW15AN2N6B80□ | 2.6nH ±0.1nH | 100MHz | 1950mA | 0.035Ω | 30 | 250MHz | 14.5GHz | New |
| LQW15AN2N6C80□ | 2.6nH ±0.2nH | 100MHz | 1950mA | 0.035Ω | 30 | 250MHz | 14.5GHz | New |
| LQW15AN2N6D80□ | 2.6nH ±0.5nH | 100MHz | 1950mA | 0.035Ω | 30 | 250MHz | 14.5GHz | New |
| LQW15AN2N7B80□ | 2.7nH ±0.1nH | 100MHz | 1500mA | 0.047Ω | 28 | 250MHz | 14.0GHz | New |
| LQW15AN2N7C80□ | 2.7nH ±0.2nH | 100MHz | 1500mA | 0.047Ω | 28 | 250MHz | 14.0GHz | New |
| LQW15AN2N7D80□ | 2.7nH ±0.5nH | 100MHz | 1500mA | 0.047Ω | 28 | 250MHz | 14.0GHz | New |
| LQW15AN2N8B80□ | 2.8nH ±0.1nH | 100MHz | 1500mA | 0.047Ω | 27 | 250MHz | 13.5GHz | New |
| LQW15AN2N8C80□ | 2.8nH ±0.2nH | 100MHz | 1500mA | 0.047Ω | 27 | 250MHz | 13.5GHz | New |
| LQW15AN2N8D80□ | 2.8nH ±0.5nH | 100MHz | 1500mA | 0.047Ω | 27 | 250MHz | 13.5GHz | New |
| LQW15AN2N9B80□ | 2.9nH ±0.1nH | 100MHz | 1500mA | 0.047Ω | 25 | 250MHz | 12.5GHz | New |
| LQW15AN2N9C80□ | 2.9nH ±0.2nH | 100MHz | 1500mA | 0.047Ω | 25 | 250MHz | 12.5GHz | New |
| LQW15AN2N9D80□ | 2.9nH ±0.5nH | 100MHz | 1500mA | 0.047Ω | 25 | 250MHz | 12.5GHz | New |
| LQW15AN3N0B80□ | 3nH ±0.1nH | 100MHz | 1350mA | 0.063Ω | 20 | 250MHz | 12.5GHz | New |


Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|---------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW15AN3N0C80 | 3nH ±0.2nH | 100MHz | 1350mA | 0.063Ω | 20 | 250MHz | 12.5GHz | New |
| LQW15AN3N0D80 | 3nH ±0.5nH | 100MHz | 1350mA | 0.063Ω | 20 | 250MHz | 12.5GHz | New |
| LQW15AN3N3B80 | 3.3nH ±0.1nH | 100MHz | 2000mA | 0.030Ω | 30 | 250MHz | 14.0GHz | New |
| LQW15AN3N3C80 | 3.3nH ±0.2nH | 100MHz | 2000mA | 0.030Ω | 30 | 250MHz | 14.0GHz | New |
| LQW15AN3N3D80 | 3.3nH ±0.5nH | 100MHz | 2000mA | 0.030Ω | 30 | 250MHz | 14.0GHz | New |
| LQW15AN3N4B80 | 3.4nH ±0.1nH | 100MHz | 1950mA | 0.030Ω | 30 | 250MHz | 10.0GHz | Kit |
| LQW15AN3N4C80 | 3.4nH ±0.2nH | 100MHz | 1950mA | 0.030Ω | 30 | 250MHz | 10.0GHz | |
| LQW15AN3N4D80 | 3.4nH ±0.5nH | 100MHz | 1950mA | 0.030Ω | 30 | 250MHz | 10.0GHz | |
| LQW15AN3N5B80 | 3.5nH ±0.1nH | 100MHz | 1950mA | 0.030Ω | 30 | 250MHz | 10.0GHz | New |
| LQW15AN3N5C80 | 3.5nH ±0.2nH | 100MHz | 1950mA | 0.030Ω | 30 | 250MHz | 10.0GHz | New |
| LQW15AN3N5D80 | 3.5nH ±0.5nH | 100MHz | 1950mA | 0.030Ω | 30 | 250MHz | 10.0GHz | New |
| LQW15AN3N6B80 | 3.6nH ±0.1nH | 100MHz | 1950mA | 0.030Ω | 30 | 250MHz | 10.0GHz | Kit |
| LQW15AN3N6C80 | 3.6nH ±0.2nH | 100MHz | 1950mA | 0.030Ω | 30 | 250MHz | 10.0GHz | |
| LQW15AN3N6D80 | 3.6nH ±0.5nH | 100MHz | 1950mA | 0.030Ω | 30 | 250MHz | 10.0GHz | |
| LQW15AN3N7B80 | 3.7nH ±0.1nH | 100MHz | 1950mA | 0.030Ω | 35 | 250MHz | 10.0GHz | New |
| LQW15AN3N7C80 | 3.7nH ±0.2nH | 100MHz | 1950mA | 0.030Ω | 35 | 250MHz | 10.0GHz | New |
| LQW15AN3N7D80 | 3.7nH ±0.5nH | 100MHz | 1950mA | 0.030Ω | 35 | 250MHz | 10.0GHz | New |
| LQW15AN3N8B80 | 3.8nH ±0.1nH | 100MHz | 1950mA | 0.030Ω | 35 | 250MHz | 10.0GHz | Kit |
| LQW15AN3N8C80 | 3.8nH ±0.2nH | 100MHz | 1950mA | 0.030Ω | 35 | 250MHz | 10.0GHz | |
| LQW15AN3N8D80 | 3.8nH ±0.5nH | 100MHz | 1950mA | 0.030Ω | 35 | 250MHz | 10.0GHz | |
| LQW15AN3N9B80 | 3.9nH ±0.1nH | 100MHz | 1950mA | 0.030Ω | 35 | 250MHz | 10.0GHz | Kit |
| LQW15AN3N9C80 | 3.9nH ±0.2nH | 100MHz | 1950mA | 0.030Ω | 35 | 250MHz | 10.0GHz | |
| LQW15AN3N9D80 | 3.9nH ±0.5nH | 100MHz | 1950mA | 0.030Ω | 35 | 250MHz | 10.0GHz | |
| LQW15AN4N0B80 | 4.0nH ±0.1nH | 100MHz | 1950mA | 0.030Ω | 30 | 250MHz | 10.0GHz | Kit |
| LQW15AN4N0C80 | 4.0nH ±0.2nH | 100MHz | 1950mA | 0.030Ω | 30 | 250MHz | 10.0GHz | |
| LQW15AN4N0D80 | 4.0nH ±0.5nH | 100MHz | 1950mA | 0.030Ω | 30 | 250MHz | 10.0GHz | |
| LQW15AN4N1B80 | 4.1nH ±0.1nH | 100MHz | 1800mA | 0.044Ω | 30 | 250MHz | 9.6GHz | New |
| LQW15AN4N1C80 | 4.1nH ±0.2nH | 100MHz | 1800mA | 0.044Ω | 30 | 250MHz | 9.6GHz | New |
| LQW15AN4N1D80 | 4.1nH ±0.5nH | 100MHz | 1800mA | 0.044Ω | 30 | 250MHz | 9.6GHz | New |
| LQW15AN4N2B80 | 4.2nH ±0.1nH | 100MHz | 1800mA | 0.044Ω | 30 | 250MHz | 9.6GHz | New |
| LQW15AN4N2C80 | 4.2nH ±0.2nH | 100MHz | 1800mA | 0.044Ω | 30 | 250MHz | 9.6GHz | New |
| LQW15AN4N2D80 | 4.2nH ±0.5nH | 100MHz | 1800mA | 0.044Ω | 30 | 250MHz | 9.6GHz | New |
| LQW15AN4N3B80 | 4.3nH ±0.1nH | 100MHz | 1800mA | 0.044Ω | 32 | 250MHz | 9.6GHz | New |
| LQW15AN4N3C80 | 4.3nH ±0.2nH | 100MHz | 1800mA | 0.044Ω | 32 | 250MHz | 9.6GHz | New |
| LQW15AN4N3D80 | 4.3nH ±0.5nH | 100MHz | 1800mA | 0.044Ω | 32 | 250MHz | 9.6GHz | New |
| LQW15AN4N4B80 | 4.4nH ±0.1nH | 100MHz | 1600mA | 0.052Ω | 34 | 250MHz | 9.6GHz | New |
| LQW15AN4N4C80 | 4.4nH ±0.2nH | 100MHz | 1600mA | 0.052Ω | 34 | 250MHz | 9.6GHz | New |
| LQW15AN4N4D80 | 4.4nH ±0.5nH | 100MHz | 1600mA | 0.052Ω | 34 | 250MHz | 9.6GHz | New |
| LQW15AN4N5B80 | 4.5nH ±0.1nH | 100MHz | 1450mA | 0.060Ω | 34 | 250MHz | 9.6GHz | New |
| LQW15AN4N5C80 | 4.5nH ±0.2nH | 100MHz | 1450mA | 0.060Ω | 34 | 250MHz | 9.6GHz | New |
| LQW15AN4N5D80 | 4.5nH ±0.5nH | 100MHz | 1450mA | 0.060Ω | 34 | 250MHz | 9.6GHz | New |
| LQW15AN4N6B80 | 4.6nH ±0.1nH | 100MHz | 1450mA | 0.060Ω | 32 | 250MHz | 9.6GHz | New |
| LQW15AN4N6C80 | 4.6nH ±0.2nH | 100MHz | 1450mA | 0.060Ω | 32 | 250MHz | 9.6GHz | New |
| LQW15AN4N6D80 | 4.6nH ±0.5nH | 100MHz | 1450mA | 0.060Ω | 32 | 250MHz | 9.6GHz | New |
| LQW15AN4N7B80 | 4.7nH ±0.1nH | 100MHz | 1200mA | 0.071Ω | 31 | 250MHz | 8.0GHz | New |
| LQW15AN4N7C80 | 4.7nH ±0.2nH | 100MHz | 1200mA | 0.071Ω | 31 | 250MHz | 8.0GHz | New |
| LQW15AN4N7D80 | 4.7nH ±0.5nH | 100MHz | 1200mA | 0.071Ω | 31 | 250MHz | 8.0GHz | New |
| LQW15AN4N8B80 | 4.8nH ±0.1nH | 100MHz | 1200mA | 0.071Ω | 30 | 250MHz | 8.0GHz | New |


Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.



Continued on the following page. 

 Note • Please read rating and  CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|---------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW15AN4N8C80 | 4.8nH ±0.2nH | 100MHz | 1200mA | 0.071 Ω | 30 | 250MHz | 8.0GHz | New |
| LQW15AN4N8D80 | 4.8nH ±0.5nH | 100MHz | 1200mA | 0.071 Ω | 30 | 250MHz | 8.0GHz | New |
| LQW15AN4N9B80 | 4.9nH ±0.1nH | 100MHz | 1200mA | 0.071 Ω | 27 | 250MHz | 8.0GHz | New |
| LQW15AN4N9C80 | 4.9nH ±0.2nH | 100MHz | 1200mA | 0.071 Ω | 27 | 250MHz | 8.0GHz | New |
| LQW15AN4N9D80 | 4.9nH ±0.5nH | 100MHz | 1200mA | 0.071 Ω | 27 | 250MHz | 8.0GHz | New |
| LQW15AN5N0B80 | 5.0nH ±0.1nH | 100MHz | 1770mA | 0.040 Ω | 32 | 250MHz | 10.0GHz | New |
| LQW15AN5N0C80 | 5.0nH ±0.2nH | 100MHz | 1770mA | 0.040 Ω | 32 | 250MHz | 10.0GHz | New |
| LQW15AN5N0D80 | 5.0nH ±0.5nH | 100MHz | 1770mA | 0.040 Ω | 32 | 250MHz | 10.0GHz | New |
| LQW15AN5N1B80 | 5.1nH ±0.1nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | Kit |
| LQW15AN5N1C80 | 5.1nH ±0.2nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | |
| LQW15AN5N1D80 | 5.1nH ±0.5nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | |
| LQW15AN5N2B80 | 5.2nH ±0.1nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | Kit |
| LQW15AN5N2C80 | 5.2nH ±0.2nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | |
| LQW15AN5N2D80 | 5.2nH ±0.5nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | |
| LQW15AN5N3B80 | 5.3nH ±0.1nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | New |
| LQW15AN5N3C80 | 5.3nH ±0.2nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | New |
| LQW15AN5N3D80 | 5.3nH ±0.5nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | New |
| LQW15AN5N4B80 | 5.4nH ±0.1nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | Kit |
| LQW15AN5N4C80 | 5.4nH ±0.2nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | |
| LQW15AN5N4D80 | 5.4nH ±0.5nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | |
| LQW15AN5N5B80 | 5.5nH ±0.1nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | New |
| LQW15AN5N5C80 | 5.5nH ±0.2nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | New |
| LQW15AN5N5D80 | 5.5nH ±0.5nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | New |
| LQW15AN5N6B80 | 5.6nH ±0.1nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | Kit |
| LQW15AN5N6C80 | 5.6nH ±0.2nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | |
| LQW15AN5N6D80 | 5.6nH ±0.5nH | 100MHz | 1770mA | 0.040 Ω | 35 | 250MHz | 8.0GHz | |
| LQW15AN5N7B80 | 5.7nH ±0.1nH | 100MHz | 1770mA | 0.040 Ω | 30 | 250MHz | 8.0GHz | Kit |
| LQW15AN5N7C80 | 5.7nH ±0.2nH | 100MHz | 1770mA | 0.040 Ω | 30 | 250MHz | 8.0GHz | |
| LQW15AN5N7D80 | 5.7nH ±0.5nH | 100MHz | 1770mA | 0.040 Ω | 30 | 250MHz | 8.0GHz | |
| LQW15AN5N8B80 | 5.8nH ±0.1nH | 100MHz | 1770mA | 0.040 Ω | 30 | 250MHz | 8.0GHz | Kit |
| LQW15AN5N8C80 | 5.8nH ±0.2nH | 100MHz | 1770mA | 0.040 Ω | 30 | 250MHz | 8.0GHz | |
| LQW15AN5N8D80 | 5.8nH ±0.5nH | 100MHz | 1770mA | 0.040 Ω | 30 | 250MHz | 8.0GHz | |
| LQW15AN5N9B80 | 5.9nH ±0.1nH | 100MHz | 1770mA | 0.040 Ω | 30 | 250MHz | 8.0GHz | New |
| LQW15AN5N9C80 | 5.9nH ±0.2nH | 100MHz | 1770mA | 0.040 Ω | 30 | 250MHz | 8.0GHz | New |
| LQW15AN5N9D80 | 5.9nH ±0.5nH | 100MHz | 1770mA | 0.040 Ω | 30 | 250MHz | 8.0GHz | New |
| LQW15AN6N0B80 | 6.0nH ±0.1nH | 100MHz | 1600mA | 0.056 Ω | 32 | 250MHz | 8.0GHz | New |
| LQW15AN6N0C80 | 6.0nH ±0.2nH | 100MHz | 1600mA | 0.056 Ω | 32 | 250MHz | 8.0GHz | New |
| LQW15AN6N0D80 | 6.0nH ±0.5nH | 100MHz | 1600mA | 0.056 Ω | 32 | 250MHz | 8.0GHz | New |
| LQW15AN6N1B80 | 6.1nH ±0.1nH | 100MHz | 1600mA | 0.056 Ω | 32 | 250MHz | 8.0GHz | New |
| LQW15AN6N1C80 | 6.1nH ±0.2nH | 100MHz | 1600mA | 0.056 Ω | 32 | 250MHz | 8.0GHz | New |
| LQW15AN6N1D80 | 6.1nH ±0.5nH | 100MHz | 1600mA | 0.056 Ω | 32 | 250MHz | 8.0GHz | New |
| LQW15AN6N2B80 | 6.2nH ±0.1nH | 100MHz | 1600mA | 0.056 Ω | 33 | 250MHz | 8.0GHz | New |
| LQW15AN6N2C80 | 6.2nH ±0.2nH | 100MHz | 1600mA | 0.056 Ω | 33 | 250MHz | 8.0GHz | New |
| LQW15AN6N2D80 | 6.2nH ±0.5nH | 100MHz | 1600mA | 0.056 Ω | 33 | 250MHz | 8.0GHz | New |
| LQW15AN6N3G80 | 6.3nH ±2% | 100MHz | 1600mA | 0.057 Ω | 32 | 250MHz | 7.8GHz | New |
| LQW15AN6N3J80 | 6.3nH ±5% | 100MHz | 1600mA | 0.057 Ω | 32 | 250MHz | 7.8GHz | New |
| LQW15AN6N4G80 | 6.4nH ±2% | 100MHz | 1380mA | 0.065 Ω | 33 | 250MHz | 7.0GHz | New |
| LQW15AN6N4J80 | 6.4nH ±5% | 100MHz | 1380mA | 0.065 Ω | 33 | 250MHz | 7.0GHz | New |


Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

Continued on the following page. 

 Note • Please read rating and  CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW15AN6N5G80□ | 6.5nH ±2% | 100MHz | 1380mA | 0.065Ω | 32 | 250MHz | 7.0GHz | New |
| LQW15AN6N5J80□ | 6.5nH ±5% | 100MHz | 1380mA | 0.065Ω | 32 | 250MHz | 7.0GHz | New |
| LQW15AN6N6G80□ | 6.6nH ±2% | 100MHz | 1280mA | 0.078Ω | 30 | 250MHz | 7.0GHz | New |
| LQW15AN6N6J80□ | 6.6nH ±5% | 100MHz | 1280mA | 0.078Ω | 30 | 250MHz | 7.0GHz | New |
| LQW15AN6N7G80□ | 6.7nH ±2% | 100MHz | 1280mA | 0.078Ω | 30 | 250MHz | 7.0GHz | New |
| LQW15AN6N7J80□ | 6.7nH ±5% | 100MHz | 1280mA | 0.078Ω | 30 | 250MHz | 7.0GHz | New |
| LQW15AN6N8G80□ | 6.8nH ±2% | 100MHz | 1450mA | 0.068Ω | 30 | 250MHz | 7.0GHz | New |
| LQW15AN6N8J80□ | 6.8nH ±5% | 100MHz | 1450mA | 0.068Ω | 30 | 250MHz | 7.0GHz | New |
| LQW15AN6N9G80□ | 6.9nH ±2% | 100MHz | 1420mA | 0.069Ω | 32 | 250MHz | 8.5GHz | New |
| LQW15AN6N9J80□ | 6.9nH ±5% | 100MHz | 1420mA | 0.069Ω | 32 | 250MHz | 8.5GHz | New |
| LQW15AN7N0G80□ | 7.0nH ±2% | 100MHz | 1420mA | 0.069Ω | 33 | 250MHz | 8.0GHz | New |
| LQW15AN7N0J80□ | 7.0nH ±5% | 100MHz | 1420mA | 0.069Ω | 33 | 250MHz | 8.0GHz | New |
| LQW15AN7N1G80□ | 7.1nH ±2% | 100MHz | 1420mA | 0.069Ω | 32 | 250MHz | 7.0GHz | New |
| LQW15AN7N1J80□ | 7.1nH ±5% | 100MHz | 1420mA | 0.069Ω | 32 | 250MHz | 7.0GHz | New |
| LQW15AN7N2G80□ | 7.2nH ±2% | 100MHz | 1700mA | 0.050Ω | 32 | 250MHz | 7.0GHz | New |
| LQW15AN7N2J80□ | 7.2nH ±5% | 100MHz | 1700mA | 0.050Ω | 32 | 250MHz | 7.0GHz | New |
| LQW15AN7N3G80□ | 7.3nH ±2% | 100MHz | 1700mA | 0.050Ω | 32 | 250MHz | 7.0GHz | New |
| LQW15AN7N3J80□ | 7.3nH ±5% | 100MHz | 1700mA | 0.050Ω | 32 | 250MHz | 7.0GHz | New |
| LQW15AN7N4G80□ | 7.4nH ±2% | 100MHz | 1700mA | 0.050Ω | 30 | 250MHz | 7.0GHz | Kit |
| LQW15AN7N4J80□ | 7.4nH ±5% | 100MHz | 1700mA | 0.050Ω | 30 | 250MHz | 7.0GHz | |
| LQW15AN7N5G80□ | 7.5nH ±2% | 100MHz | 1700mA | 0.050Ω | 35 | 250MHz | 7.0GHz | Kit |
| LQW15AN7N5J80□ | 7.5nH ±5% | 100MHz | 1700mA | 0.050Ω | 35 | 250MHz | 7.0GHz | |
| LQW15AN7N6G80□ | 7.6nH ±2% | 100MHz | 1700mA | 0.050Ω | 30 | 250MHz | 7.0GHz | Kit |
| LQW15AN7N6J80□ | 7.6nH ±5% | 100MHz | 1700mA | 0.050Ω | 30 | 250MHz | 7.0GHz | |
| LQW15AN7N7G80□ | 7.7nH ±2% | 100MHz | 1700mA | 0.050Ω | 30 | 250MHz | 7.0GHz | Kit |
| LQW15AN7N7J80□ | 7.7nH ±5% | 100MHz | 1700mA | 0.050Ω | 30 | 250MHz | 7.0GHz | |
| LQW15AN7N8G80□ | 7.8nH ±2% | 100MHz | 1700mA | 0.050Ω | 30 | 250MHz | 7.0GHz | Kit |
| LQW15AN7N8J80□ | 7.8nH ±5% | 100MHz | 1700mA | 0.050Ω | 30 | 250MHz | 7.0GHz | |
| LQW15AN7N9G80□ | 7.9nH ±2% | 100MHz | 1700mA | 0.050Ω | 30 | 250MHz | 7.0GHz | New |
| LQW15AN7N9J80□ | 7.9nH ±5% | 100MHz | 1700mA | 0.050Ω | 30 | 250MHz | 7.0GHz | New |
| LQW15AN8N0G80□ | 8.0nH ±2% | 100MHz | 1700mA | 0.050Ω | 30 | 250MHz | 7.0GHz | Kit |
| LQW15AN8N0J80□ | 8.0nH ±5% | 100MHz | 1700mA | 0.050Ω | 30 | 250MHz | 7.0GHz | |
| LQW15AN8N1G80□ | 8.1nH ±2% | 100MHz | 1500mA | 0.069Ω | 32 | 250MHz | 6.5GHz | New |
| LQW15AN8N1J80□ | 8.1nH ±5% | 100MHz | 1500mA | 0.069Ω | 32 | 250MHz | 6.5GHz | New |
| LQW15AN8N2G80□ | 8.2nH ±2% | 100MHz | 1500mA | 0.069Ω | 32 | 250MHz | 6.5GHz | New |
| LQW15AN8N2J80□ | 8.2nH ±5% | 100MHz | 1500mA | 0.069Ω | 32 | 250MHz | 6.5GHz | New |
| LQW15AN8N3G80□ | 8.3nH ±2% | 100MHz | 1500mA | 0.069Ω | 32 | 250MHz | 6.5GHz | New |
| LQW15AN8N3J80□ | 8.3nH ±5% | 100MHz | 1500mA | 0.069Ω | 32 | 250MHz | 6.5GHz | New |
| LQW15AN8N4G80□ | 8.4nH ±2% | 100MHz | 1500mA | 0.069Ω | 32 | 250MHz | 6.5GHz | New |
| LQW15AN8N4J80□ | 8.4nH ±5% | 100MHz | 1500mA | 0.069Ω | 32 | 250MHz | 6.5GHz | New |
| LQW15AN8N5G80□ | 8.5nH ±2% | 100MHz | 1500mA | 0.069Ω | 32 | 250MHz | 6.5GHz | New |
| LQW15AN8N5J80□ | 8.5nH ±5% | 100MHz | 1500mA | 0.069Ω | 32 | 250MHz | 6.5GHz | New |
| LQW15AN8N6G80□ | 8.6nH ±2% | 100MHz | 1420mA | 0.070Ω | 31 | 250MHz | 6.5GHz | New |
| LQW15AN8N6J80□ | 8.6nH ±5% | 100MHz | 1420mA | 0.070Ω | 31 | 250MHz | 6.5GHz | New |
| LQW15AN8N7G80□ | 8.7nH ±2% | 100MHz | 1420mA | 0.070Ω | 31 | 250MHz | 6.5GHz | New |
| LQW15AN8N7J80□ | 8.7nH ±5% | 100MHz | 1420mA | 0.070Ω | 31 | 250MHz | 6.5GHz | New |
| LQW15AN8N8G80□ | 8.8nH ±2% | 100MHz | 1420mA | 0.070Ω | 31 | 250MHz | 6.5GHz | New |
| LQW15AN8N8J80□ | 8.8nH ±5% | 100MHz | 1420mA | 0.070Ω | 31 | 250MHz | 6.5GHz | New |


Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

Continued on the following page. 

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW15AN8N9G80□ | 8.9nH ±2% | 100MHz | 1420mA | 0.070Ω | 31 | 250MHz | 6.5GHz | New |
| LQW15AN8N9J80□ | 8.9nH ±5% | 100MHz | 1420mA | 0.070Ω | 31 | 250MHz | 6.5GHz | New |
| LQW15AN9N0G80□ | 9nH ±2% | 100MHz | 1420mA | 0.070Ω | 30 | 250MHz | 6.5GHz | New |
| LQW15AN9N0J80□ | 9nH ±5% | 100MHz | 1420mA | 0.070Ω | 30 | 250MHz | 6.5GHz | New |
| LQW15AN9N1G80□ | 9.1nH ±2% | 100MHz | 1400mA | 0.080Ω | 32 | 250MHz | 6.5GHz | New |
| LQW15AN9N1J80□ | 9.1nH ±5% | 100MHz | 1400mA | 0.080Ω | 32 | 250MHz | 6.5GHz | New |
| LQW15AN9N2G80□ | 9.2nH ±2% | 100MHz | 1400mA | 0.081Ω | 32 | 250MHz | 6.0GHz | New |
| LQW15AN9N2J80□ | 9.2nH ±5% | 100MHz | 1400mA | 0.081Ω | 32 | 250MHz | 6.0GHz | New |
| LQW15AN9N3G80□ | 9.3nH ±2% | 100MHz | 1400mA | 0.081Ω | 34 | 250MHz | 6.0GHz | New |
| LQW15AN9N3J80□ | 9.3nH ±5% | 100MHz | 1400mA | 0.081Ω | 34 | 250MHz | 6.0GHz | New |
| LQW15AN9N4G80□ | 9.4nH ±2% | 100MHz | 1400mA | 0.081Ω | 33 | 250MHz | 6.0GHz | New |
| LQW15AN9N4J80□ | 9.4nH ±5% | 100MHz | 1400mA | 0.081Ω | 33 | 250MHz | 6.0GHz | New |
| LQW15AN9N5G80□ | 9.5nH ±2% | 100MHz | 1400mA | 0.081Ω | 32 | 250MHz | 6.0GHz | New |
| LQW15AN9N5J80□ | 9.5nH ±5% | 100MHz | 1400mA | 0.081Ω | 32 | 250MHz | 6.0GHz | New |
| LQW15AN9N6G80□ | 9.6nH ±2% | 100MHz | 1400mA | 0.081Ω | 33 | 250MHz | 6.0GHz | New |
| LQW15AN9N6J80□ | 9.6nH ±5% | 100MHz | 1400mA | 0.081Ω | 33 | 250MHz | 6.0GHz | New |
| LQW15AN9N7G80□ | 9.7nH ±2% | 100MHz | 1400mA | 0.081Ω | 33 | 250MHz | 6.0GHz | New |
| LQW15AN9N7J80□ | 9.7nH ±5% | 100MHz | 1400mA | 0.081Ω | 33 | 250MHz | 6.0GHz | New |
| LQW15AN9N8G80□ | 9.8nH ±2% | 100MHz | 1400mA | 0.081Ω | 34 | 250MHz | 6.0GHz | New |
| LQW15AN9N8J80□ | 9.8nH ±5% | 100MHz | 1400mA | 0.081Ω | 34 | 250MHz | 6.0GHz | New |
| LQW15AN9N9G80□ | 9.9nH ±2% | 100MHz | 1400mA | 0.081Ω | 32 | 250MHz | 6.0GHz | New |
| LQW15AN9N9J80□ | 9.9nH ±5% | 100MHz | 1400mA | 0.081Ω | 32 | 250MHz | 6.0GHz | New |
| LQW15AN10NG80□ | 10nH ±2% | 100MHz | 1400mA | 0.081Ω | 31 | 250MHz | 6.0GHz | New |
| LQW15AN10NJ80□ | 10nH ±5% | 100MHz | 1400mA | 0.081Ω | 31 | 250MHz | 6.0GHz | New |
| LQW15AN11NG80□ | 11nH ±2% | 100MHz | 1400mA | 0.083Ω | 32 | 250MHz | 6.2GHz | New |
| LQW15AN11NJ80□ | 11nH ±5% | 100MHz | 1400mA | 0.083Ω | 32 | 250MHz | 6.2GHz | New |
| LQW15AN12NG80□ | 12nH ±2% | 100MHz | 1240mA | 0.093Ω | 30 | 250MHz | 5.2GHz | New |
| LQW15AN12NJ80□ | 12nH ±5% | 100MHz | 1240mA | 0.093Ω | 30 | 250MHz | 5.2GHz | New |
| LQW15AN13NG80□ | 13nH ±2% | 100MHz | 1240mA | 0.093Ω | 30 | 250MHz | 5.2GHz | Kit |
| LQW15AN13NJ80□ | 13nH ±5% | 100MHz | 1240mA | 0.093Ω | 30 | 250MHz | 5.2GHz | |
| LQW15AN14NG80□ | 14nH ±2% | 100MHz | 1150mA | 0.111Ω | 31 | 250MHz | 5.2GHz | New |
| LQW15AN14NJ80□ | 14nH ±5% | 100MHz | 1150mA | 0.111Ω | 31 | 250MHz | 5.2GHz | New |
| LQW15AN15NG80□ | 15nH ±2% | 100MHz | 1150mA | 0.114Ω | 31 | 250MHz | 5.5GHz | New |
| LQW15AN15NJ80□ | 15nH ±5% | 100MHz | 1150mA | 0.114Ω | 31 | 250MHz | 5.5GHz | New |
| LQW15AN16NG80□ | 16nH ±2% | 100MHz | 1000mA | 0.126Ω | 31 | 250MHz | 5.0GHz | New |
| LQW15AN16NJ80□ | 16nH ±5% | 100MHz | 1000mA | 0.126Ω | 31 | 250MHz | 5.0GHz | New |
| LQW15AN17NG80□ | 17nH ±2% | 100MHz | 1000mA | 0.126Ω | 30 | 250MHz | 5.0GHz | New |
| LQW15AN17NJ80□ | 17nH ±5% | 100MHz | 1000mA | 0.126Ω | 30 | 250MHz | 5.0GHz | New |
| LQW15AN18NG80□ | 18nH ±2% | 100MHz | 1050mA | 0.130Ω | 30 | 250MHz | 5.2GHz | New |
| LQW15AN18NJ80□ | 18nH ±5% | 100MHz | 1050mA | 0.130Ω | 30 | 250MHz | 5.2GHz | New |
| LQW15AN19NG80□ | 19nH ±2% | 100MHz | 920mA | 0.156Ω | 30 | 250MHz | 5.0GHz | New |
| LQW15AN19NJ80□ | 19nH ±5% | 100MHz | 920mA | 0.156Ω | 30 | 250MHz | 5.0GHz | New |
| LQW15AN20NG80□ | 20nH ±2% | 100MHz | 800mA | 0.186Ω | 30 | 250MHz | 4.5GHz | New |
| LQW15AN20NJ80□ | 20nH ±5% | 100MHz | 800mA | 0.186Ω | 30 | 250MHz | 4.5GHz | New |
| LQW15AN21NG80□ | 21nH ±2% | 100MHz | 780mA | 0.202Ω | 30 | 250MHz | 4.5GHz | New |
| LQW15AN21NJ80□ | 21nH ±5% | 100MHz | 780mA | 0.202Ω | 30 | 250MHz | 4.5GHz | New |
| LQW15AN22NG80□ | 22nH ±2% | 100MHz | 780mA | 0.202Ω | 30 | 250MHz | 4.5GHz | New |
| LQW15AN22NJ80□ | 22nH ±5% | 100MHz | 780mA | 0.202Ω | 30 | 250MHz | 4.5GHz | New |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.


Continued on the following page. 

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|---------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW15AN23NG80 | 23nH ±2% | 100MHz | 760mA | 0.201Ω | 29 | 250MHz | 4.5GHz | New |
| LQW15AN23NJ80 | 23nH ±5% | 100MHz | 760mA | 0.201Ω | 29 | 250MHz | 4.5GHz | New |
| LQW15AN24NG80 | 24nH ±2% | 100MHz | 770mA | 0.212Ω | 31 | 250MHz | 4.0GHz | New |
| LQW15AN24NJ80 | 24nH ±5% | 100MHz | 770mA | 0.212Ω | 31 | 250MHz | 4.0GHz | New |
| LQW15AN25NG80 | 25nH ±2% | 100MHz | 750mA | 0.221Ω | 31 | 250MHz | 4.1GHz | New |
| LQW15AN25NJ80 | 25nH ±5% | 100MHz | 750mA | 0.221Ω | 31 | 250MHz | 4.1GHz | New |
| LQW15AN26NG80 | 26nH ±2% | 100MHz | 720mA | 0.282Ω | 29 | 250MHz | 4.1GHz | New |
| LQW15AN26NJ80 | 26nH ±5% | 100MHz | 720mA | 0.282Ω | 29 | 250MHz | 4.1GHz | New |
| LQW15AN27NG80 | 27nH ±2% | 100MHz | 680mA | 0.288Ω | 30 | 250MHz | 4.0GHz | Kit |
| LQW15AN27NJ80 | 27nH ±5% | 100MHz | 680mA | 0.288Ω | 30 | 250MHz | 4.0GHz | |
| LQW15AN30NG80 | 30nH ±2% | 100MHz | 660mA | 0.309Ω | 30 | 250MHz | 3.8GHz | New |
| LQW15AN30NJ80 | 30nH ±5% | 100MHz | 660mA | 0.309Ω | 30 | 250MHz | 3.8GHz | New |
| LQW15AN33NG80 | 33nH ±2% | 100MHz | 620mA | 0.336Ω | 30 | 250MHz | 3.6GHz | Kit |
| LQW15AN33NJ80 | 33nH ±5% | 100MHz | 620mA | 0.336Ω | 30 | 250MHz | 3.6GHz | |
| LQW15AN36NG80 | 36nH ±2% | 100MHz | 540mA | 0.431Ω | 30 | 250MHz | 3.5GHz | New |
| LQW15AN36NJ80 | 36nH ±5% | 100MHz | 540mA | 0.431Ω | 30 | 250MHz | 3.5GHz | New |
| LQW15AN39NG80 | 39nH ±2% | 100MHz | 530mA | 0.456Ω | 28 | 250MHz | 3.4GHz | New |
| LQW15AN39NJ80 | 39nH ±5% | 100MHz | 530mA | 0.456Ω | 28 | 250MHz | 3.4GHz | New |
| LQW15AN43NG80 | 43nH ±2% | 100MHz | 515mA | 0.516Ω | 30 | 250MHz | 3.4GHz | Kit |
| LQW15AN43NJ80 | 43nH ±5% | 100MHz | 515mA | 0.516Ω | 30 | 250MHz | 3.4GHz | |
| LQW15AN47NG80 | 47nH ±2% | 100MHz | 440mA | 0.648Ω | 25 | 200MHz | 3.2GHz | New |
| LQW15AN47NJ80 | 47nH ±5% | 100MHz | 440mA | 0.648Ω | 25 | 200MHz | 3.2GHz | New |
| LQW15AN51NG80 | 51nH ±2% | 100MHz | 415mA | 0.696Ω | 25 | 200MHz | 2.9GHz | New |
| LQW15AN51NJ80 | 51nH ±5% | 100MHz | 415mA | 0.696Ω | 25 | 200MHz | 2.9GHz | New |
| LQW15AN53NG80 | 53nH ±2% | 100MHz | 415mA | 0.696Ω | 25 | 200MHz | 2.9GHz | Kit |
| LQW15AN53NJ80 | 53nH ±5% | 100MHz | 415mA | 0.696Ω | 25 | 200MHz | 2.9GHz | |
| LQW15AN56NG80 | 56nH ±2% | 100MHz | 340mA | 0.996Ω | 25 | 200MHz | 2.9GHz | New |
| LQW15AN56NJ80 | 56nH ±5% | 100MHz | 340mA | 0.996Ω | 25 | 200MHz | 2.9GHz | New |
| LQW15AN68NG80 | 68nH ±2% | 100MHz | 320mA | 1.128Ω | 25 | 200MHz | 2.5GHz | New |
| LQW15AN68NJ80 | 68nH ±5% | 100MHz | 320mA | 1.128Ω | 25 | 200MHz | 2.5GHz | New |
| LQW15AN75NG80 | 75nH ±2% | 100MHz | 320mA | 1.224Ω | 25 | 200MHz | 2.4GHz | Kit |
| LQW15AN75NJ80 | 75nH ±5% | 100MHz | 320mA | 1.224Ω | 25 | 200MHz | 2.4GHz | |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)




Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Derating of Rated Current

In operating temperature exceeding +85°C, derating of current is necessary for LQW15AN_80 series. Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current



Reference Data

4991A&16197A

| Part Number | Inductance (nH) | Q (Typ.) | | | | |
|-------------|-----------------|----------|--------|--------|--------|--------|
| | Nominal | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQW15AN1N3 | 1.3 | 83 | 88 | 121 | 128 | 144 |
| LQW15AN1N6 | 1.6 | 53 | 57 | 87 | 93 | 101 |
| LQW15AN1N7 | 1.7 | 52 | 57 | 86 | 92 | 100 |
| LQW15AN2N3 | 2.3 | 70 | 74 | 104 | 108 | 119 |
| LQW15AN2N4 | 2.4 | 63 | 67 | 93 | 97 | 107 |
| LQW15AN2N5 | 2.5 | 64 | 68 | 102 | 109 | 119 |
| LQW15AN2N6 | 2.6 | 64 | 68 | 102 | 107 | 115 |
| LQW15AN2N7 | 2.7 | 60 | 64 | 95 | 102 | 111 |
| LQW15AN2N8 | 2.8 | 61 | 66 | 99 | 104 | 110 |
| LQW15AN2N9 | 2.9 | 61 | 65 | 97 | 102 | 108 |
| LQW15AN3N4 | 3.4 | 66 | 70 | 96 | 99 | 108 |
| LQW15AN3N5 | 3.5 | 74 | 77 | 107 | 110 | 119 |
| LQW15AN3N6 | 3.6 | 62 | 66 | 91 | 94 | 103 |
| LQW15AN3N7 | 3.7 | 74 | 78 | 104 | 108 | 117 |
| LQW15AN3N8 | 3.8 | 68 | 72 | 99 | 103 | 111 |
| LQW15AN3N9 | 3.9 | 75 | 80 | 110 | 114 | 121 |
| LQW15AN4N0 | 4.0 | 68 | 71 | 97 | 101 | 108 |
| LQW15AN4N2 | 4.2 | 70 | 75 | 107 | 112 | 120 |
| LQW15AN4N4 | 4.4 | 65 | 69 | 99 | 103 | 105 |
| LQW15AN4N5 | 4.5 | 66 | 70 | 99 | 103 | 105 |
| LQW15AN4N7 | 4.7 | 58 | 61 | 85 | 90 | 95 |
| LQW15AN4N8 | 4.8 | 58 | 61 | 83 | 87 | 93 |
| LQW15AN5N1 | 5.1 | 64 | 68 | 94 | 97 | 104 |
| LQW15AN5N2 | 5.2 | 66 | 70 | 96 | 100 | 107 |
| LQW15AN5N3 | 5.3 | 71 | 75 | 103 | 106 | 114 |
| LQW15AN5N4 | 5.4 | 62 | 66 | 88 | 92 | 95 |
| LQW15AN5N5 | 5.5 | 70 | 74 | 99 | 102 | 107 |
| LQW15AN5N6 | 5.6 | 64 | 68 | 93 | 96 | 100 |
| LQW15AN5N7 | 5.7 | 68 | 73 | 97 | 101 | 107 |
| LQW15AN5N8 | 5.8 | 65 | 69 | 92 | 94 | 97 |
| LQW15AN5N9 | 5.9 | 69 | 73 | 96 | 98 | 103 |
| LQW15AN6N0 | 6.0 | 63 | 67 | 94 | 96 | 96 |

Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance (nH) | Q (Typ.) | | | | |
|-------------|-----------------|----------|--------|--------|--------|--------|
| | Nominal | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQW15AN6N2 | 6.2 | 70 | 74 | 102 | 104 | 102 |
| LQW15AN6N4 | 6.4 | 59 | 64 | 89 | 91 | 90 |
| LQW15AN6N5 | 6.5 | 62 | 66 | 84 | 83 | 76 |
| LQW15AN6N6 | 6.6 | 64 | 68 | 92 | 94 | 93 |
| LQW15AN6N7 | 6.7 | 62 | 66 | 90 | 92 | 91 |
| LQW15AN6N9 | 6.9 | 65 | 70 | 96 | 97 | 93 |
| LQW15AN7N0 | 7.0 | 66 | 71 | 101 | 104 | 105 |
| LQW15AN7N4 | 7.4 | 63 | 67 | 91 | 93 | 97 |
| LQW15AN7N5 | 7.5 | 65 | 69 | 89 | 92 | 98 |
| LQW15AN7N6 | 7.6 | 64 | 68 | 90 | 92 | 93 |
| LQW15AN7N7 | 7.7 | 62 | 66 | 86 | 88 | 88 |
| LQW15AN7N8 | 7.8 | 66 | 71 | 89 | 90 | 87 |
| LQW15AN7N9 | 7.9 | 69 | 72 | 92 | 94 | 96 |
| LQW15AN8N0 | 8.0 | 64 | 67 | 84 | 84 | 81 |
| LQW15AN8N2 | 8.2 | 63 | 67 | 89 | 92 | 95 |
| LQW15AN8N4 | 8.4 | 68 | 72 | 96 | 96 | 91 |
| LQW15AN9N1 | 9.1 | 62 | 66 | 87 | 87 | 82 |
| LQW15AN9N2 | 9.2 | 61 | 65 | 89 | 90 | 87 |
| LQW15AN9N4 | 9.4 | 65 | 70 | 96 | 97 | 93 |
| LQW15AN9N5 | 9.5 | 63 | 67 | 89 | 90 | 85 |
| LQW15AN9N6 | 9.6 | 65 | 69 | 92 | 92 | 87 |
| LQW15AN9N8 | 9.8 | 63 | 67 | 92 | 93 | 89 |
| LQW15AN10N | 10 | 65 | 70 | 92 | 91 | 85 |
| LQW15AN12N | 12 | 60 | 64 | 82 | 85 | 86 |
| LQW15AN13N | 13 | 60 | 63 | 74 | 73 | 65 |
| LQW15AN16N | 16 | 61 | 64 | 80 | 78 | 68 |
| LQW15AN20N | 20 | 58 | 61 | 70 | 67 | 57 |
| LQW15AN21N | 21 | 59 | 63 | 72 | 69 | 57 |
| LQW15AN24N | 24 | 56 | 59 | 67 | 63 | 51 |
| LQW15AN25N | 25 | 57 | 60 | 70 | 66 | 54 |
| LQW15AN27N | 27 | 55 | 58 | 58 | 53 | 40 |
| LQW15AN33N | 33 | 54 | 56 | 50 | 45 | 32 |
| LQW15AN43N | 43 | 56 | 59 | 48 | 38 | 21 |
| LQW15AN51N | 51 | 55 | 59 | 37 | 30 | 32 |
| LQW15AN53N | 53 | 53 | 55 | 50 | 43 | 26 |
| LQW15AN68N | 68 | 49 | 50 | 37 | 31 | 16 |
| LQW15AN75N | 75 | 52 | 53 | 40 | 31 | 15 |

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQW18AN_00 Series 0603/1608 (inch/mm)

Size Code 0603 (1608) in inch (in mm), Wound Type

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| J | ø330mm Paper Taping | 10000 |
| B | Packing in Bulk | 500 |



Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW18AN2N2D00□ | 2.2nH ±0.5nH | 100MHz | 700mA | 0.049Ω | 16 | 250MHz | 6000MHz | |
| LQW18AN3N6C00□ | 3.6nH ±0.2nH | 100MHz | 850mA | 0.059Ω | 25 | 250MHz | 6000MHz | Kit |
| LQW18AN3N6D00□ | 3.6nH ±0.5nH | 100MHz | 850mA | 0.059Ω | 25 | 250MHz | 6000MHz | |
| LQW18AN3N9C00□ | 3.9nH ±0.2nH | 100MHz | 850mA | 0.059Ω | 35 | 250MHz | 6000MHz | Kit |
| LQW18AN3N9D00□ | 3.9nH ±0.5nH | 100MHz | 850mA | 0.059Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN4N3C00□ | 4.3nH ±0.2nH | 100MHz | 850mA | 0.059Ω | 35 | 250MHz | 6000MHz | Kit |
| LQW18AN4N3D00□ | 4.3nH ±0.5nH | 100MHz | 850mA | 0.059Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN4N7D00□ | 4.7nH ±0.5nH | 100MHz | 850mA | 0.059Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN5N6C00□ | 5.6nH ±0.2nH | 100MHz | 750mA | 0.082Ω | 35 | 250MHz | 6000MHz | Kit |
| LQW18AN5N6D00□ | 5.6nH ±0.5nH | 100MHz | 750mA | 0.082Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN6N2C00□ | 6.2nH ±0.2nH | 100MHz | 750mA | 0.082Ω | 35 | 250MHz | 6000MHz | Kit |
| LQW18AN6N2D00□ | 6.2nH ±0.5nH | 100MHz | 750mA | 0.082Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN6N8C00□ | 6.8nH ±0.2nH | 100MHz | 750mA | 0.082Ω | 35 | 250MHz | 6000MHz | Kit |
| LQW18AN6N8D00□ | 6.8nH ±0.5nH | 100MHz | 750mA | 0.082Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN7N5C00□ | 7.5nH ±0.2nH | 100MHz | 750mA | 0.082Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN7N5D00□ | 7.5nH ±0.5nH | 100MHz | 750mA | 0.082Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN8N2C00□ | 8.2nH ±0.2nH | 100MHz | 650mA | 0.11Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN8N2D00□ | 8.2nH ±0.5nH | 100MHz | 650mA | 0.11Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN8N7C00□ | 8.7nH ±0.2nH | 100MHz | 650mA | 0.11Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN8N7D00□ | 8.7nH ±0.5nH | 100MHz | 650mA | 0.11Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN9N1C00□ | 9.1nH ±0.2nH | 100MHz | 650mA | 0.11Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN9N1D00□ | 9.1nH ±0.5nH | 100MHz | 650mA | 0.11Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN9N5D00□ | 9.5nH ±0.5nH | 100MHz | 650mA | 0.11Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN10NG00□ | 10nH ±2% | 100MHz | 650mA | 0.11Ω | 35 | 250MHz | 6000MHz | Kit |
| LQW18AN10NJ00□ | 10nH ±5% | 100MHz | 650mA | 0.11Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN11NG00□ | 11nH ±2% | 100MHz | 650mA | 0.11Ω | 35 | 250MHz | 6000MHz | Kit |
| LQW18AN11NJ00□ | 11nH ±5% | 100MHz | 650mA | 0.11Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN12NG00□ | 12nH ±2% | 100MHz | 600mA | 0.13Ω | 35 | 250MHz | 6000MHz | Kit |
| LQW18AN12NJ00□ | 12nH ±5% | 100MHz | 600mA | 0.13Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN13NG00□ | 13nH ±2% | 100MHz | 600mA | 0.13Ω | 35 | 250MHz | 6000MHz | Kit |
| LQW18AN13NJ00□ | 13nH ±5% | 100MHz | 600mA | 0.13Ω | 35 | 250MHz | 6000MHz | |
| LQW18AN15NG00□ | 15nH ±2% | 100MHz | 600mA | 0.13Ω | 40 | 250MHz | 6000MHz | Kit |


Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW18AN15NJ00□ | 15nH ±5% | 100MHz | 600mA | 0.13Ω | 40 | 250MHz | 6000MHz | |
| LQW18AN16NG00□ | 16nH ±2% | 100MHz | 550mA | 0.16Ω | 40 | 250MHz | 5500MHz | Kit |
| LQW18AN16NJ00□ | 16nH ±5% | 100MHz | 550mA | 0.16Ω | 40 | 250MHz | 5500MHz | |
| LQW18AN18NG00□ | 18nH ±2% | 100MHz | 550mA | 0.16Ω | 40 | 250MHz | 5500MHz | Kit |
| LQW18AN18NJ00□ | 18nH ±5% | 100MHz | 550mA | 0.16Ω | 40 | 250MHz | 5500MHz | |
| LQW18AN20NG00□ | 20nH ±2% | 100MHz | 550mA | 0.16Ω | 40 | 250MHz | 4900MHz | Kit |
| LQW18AN20NJ00□ | 20nH ±5% | 100MHz | 550mA | 0.16Ω | 40 | 250MHz | 4900MHz | |
| LQW18AN22NG00□ | 22nH ±2% | 100MHz | 500mA | 0.17Ω | 40 | 250MHz | 4600MHz | Kit |
| LQW18AN22NJ00□ | 22nH ±5% | 100MHz | 500mA | 0.17Ω | 40 | 250MHz | 4600MHz | |
| LQW18AN24NG00□ | 24nH ±2% | 100MHz | 500mA | 0.21Ω | 40 | 250MHz | 3800MHz | Kit |
| LQW18AN24NJ00□ | 24nH ±5% | 100MHz | 500mA | 0.21Ω | 40 | 250MHz | 3800MHz | |
| LQW18AN27NG00□ | 27nH ±2% | 100MHz | 440mA | 0.21Ω | 40 | 250MHz | 3700MHz | Kit |
| LQW18AN27NJ00□ | 27nH ±5% | 100MHz | 440mA | 0.21Ω | 40 | 250MHz | 3700MHz | |
| LQW18AN30NG00□ | 30nH ±2% | 100MHz | 420mA | 0.23Ω | 40 | 250MHz | 3300MHz | Kit |
| LQW18AN30NJ00□ | 30nH ±5% | 100MHz | 420mA | 0.23Ω | 40 | 250MHz | 3300MHz | |
| LQW18AN33NG00□ | 33nH ±2% | 100MHz | 420mA | 0.23Ω | 40 | 250MHz | 3200MHz | Kit |
| LQW18AN33NJ00□ | 33nH ±5% | 100MHz | 420mA | 0.23Ω | 40 | 250MHz | 3200MHz | |
| LQW18AN36NG00□ | 36nH ±2% | 100MHz | 400mA | 0.26Ω | 40 | 250MHz | 2900MHz | Kit |
| LQW18AN36NJ00□ | 36nH ±5% | 100MHz | 400mA | 0.26Ω | 40 | 250MHz | 2900MHz | |
| LQW18AN39NG00□ | 39nH ±2% | 100MHz | 400mA | 0.26Ω | 40 | 250MHz | 2800MHz | Kit |
| LQW18AN39NJ00□ | 39nH ±5% | 100MHz | 400mA | 0.26Ω | 40 | 250MHz | 2800MHz | |
| LQW18AN43NG00□ | 43nH ±2% | 100MHz | 380mA | 0.29Ω | 40 | 200MHz | 2700MHz | Kit |
| LQW18AN43NJ00□ | 43nH ±5% | 100MHz | 380mA | 0.29Ω | 40 | 200MHz | 2700MHz | |
| LQW18AN47NG00□ | 47nH ±2% | 100MHz | 380mA | 0.29Ω | 38 | 200MHz | 2600MHz | Kit |
| LQW18AN47NJ00□ | 47nH ±5% | 100MHz | 380mA | 0.29Ω | 38 | 200MHz | 2600MHz | |
| LQW18AN51NG00□ | 51nH ±2% | 100MHz | 370mA | 0.33Ω | 38 | 200MHz | 2500MHz | Kit |
| LQW18AN51NJ00□ | 51nH ±5% | 100MHz | 370mA | 0.33Ω | 38 | 200MHz | 2500MHz | |
| LQW18AN56NG00□ | 56nH ±2% | 100MHz | 360mA | 0.35Ω | 38 | 200MHz | 2400MHz | Kit |
| LQW18AN56NJ00□ | 56nH ±5% | 100MHz | 360mA | 0.35Ω | 38 | 200MHz | 2400MHz | |
| LQW18AN62NG00□ | 62nH ±2% | 100MHz | 280mA | 0.51Ω | 38 | 200MHz | 2300MHz | Kit |
| LQW18AN62NJ00□ | 62nH ±5% | 100MHz | 280mA | 0.51Ω | 38 | 200MHz | 2300MHz | |
| LQW18AN68NG00□ | 68nH ±2% | 100MHz | 340mA | 0.38Ω | 38 | 200MHz | 2200MHz | Kit |
| LQW18AN68NJ00□ | 68nH ±5% | 100MHz | 340mA | 0.38Ω | 38 | 200MHz | 2200MHz | |
| LQW18AN72NG00□ | 72nH ±2% | 100MHz | 270mA | 0.56Ω | 34 | 150MHz | 2100MHz | Kit |
| LQW18AN72NJ00□ | 72nH ±5% | 100MHz | 270mA | 0.56Ω | 34 | 150MHz | 2100MHz | |
| LQW18AN75NG00□ | 75nH ±2% | 100MHz | 270mA | 0.56Ω | 34 | 150MHz | 2050MHz | Kit |
| LQW18AN75NJ00□ | 75nH ±5% | 100MHz | 270mA | 0.56Ω | 34 | 150MHz | 2050MHz | |
| LQW18AN82NG00□ | 82nH ±2% | 100MHz | 250mA | 0.60Ω | 34 | 150MHz | 2000MHz | Kit |
| LQW18AN82NJ00□ | 82nH ±5% | 100MHz | 250mA | 0.60Ω | 34 | 150MHz | 2000MHz | |
| LQW18AN91NG00□ | 91nH ±2% | 100MHz | 230mA | 0.64Ω | 34 | 150MHz | 1900MHz | Kit |
| LQW18AN91NJ00□ | 91nH ±5% | 100MHz | 230mA | 0.64Ω | 34 | 150MHz | 1900MHz | |
| LQW18ANR10G00□ | 100nH ±2% | 100MHz | 220mA | 0.68Ω | 34 | 150MHz | 1800MHz | Kit |
| LQW18ANR10J00□ | 100nH ±5% | 100MHz | 220mA | 0.68Ω | 34 | 150MHz | 1800MHz | |
| LQW18ANR11G00□ | 110nH ±2% | 100MHz | 200mA | 1.2Ω | 32 | 150MHz | 1700MHz | Kit |
| LQW18ANR11J00□ | 110nH ±5% | 100MHz | 200mA | 1.2Ω | 32 | 150MHz | 1700MHz | |
| LQW18ANR12G00□ | 120nH ±2% | 100MHz | 180mA | 1.3Ω | 32 | 150MHz | 1600MHz | Kit |
| LQW18ANR12J00□ | 120nH ±5% | 100MHz | 180mA | 1.3Ω | 32 | 150MHz | 1600MHz | |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.


Continued on the following page. 

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW18ANR13G00□ | 130nH ±2% | 100MHz | 170mA | 1.4Ω | 32 | 150MHz | 1450MHz | Kit |
| LQW18ANR13J00□ | 130nH ±5% | 100MHz | 170mA | 1.4Ω | 32 | 150MHz | 1450MHz | |
| LQW18ANR15G00□ | 150nH ±2% | 100MHz | 160mA | 1.5Ω | 32 | 150MHz | 1400MHz | Kit |
| LQW18ANR15J00□ | 150nH ±5% | 100MHz | 160mA | 1.5Ω | 32 | 150MHz | 1400MHz | |
| LQW18ANR16G00□ | 160nH ±2% | 100MHz | 150mA | 2.1Ω | 32 | 150MHz | 1350MHz | Kit |
| LQW18ANR16J00□ | 160nH ±5% | 100MHz | 150mA | 2.1Ω | 32 | 150MHz | 1350MHz | |
| LQW18ANR18G00□ | 180nH ±2% | 100MHz | 140mA | 2.2Ω | 25 | 100MHz | 1300MHz | Kit |
| LQW18ANR18J00□ | 180nH ±5% | 100MHz | 140mA | 2.2Ω | 25 | 100MHz | 1300MHz | |
| LQW18ANR20G00□ | 200nH ±2% | 100MHz | 120mA | 2.4Ω | 25 | 100MHz | 1250MHz | Kit |
| LQW18ANR20J00□ | 200nH ±5% | 100MHz | 120mA | 2.4Ω | 25 | 100MHz | 1250MHz | |
| LQW18ANR22G00□ | 220nH ±2% | 100MHz | 120mA | 2.5Ω | 25 | 100MHz | 1200MHz | Kit |
| LQW18ANR22J00□ | 220nH ±5% | 100MHz | 120mA | 2.5Ω | 25 | 100MHz | 1200MHz | |
| LQW18ANR27G00□ | 270nH ±2% | 100MHz | 110mA | 3.4Ω | 30 | 100MHz | 960MHz | Kit |
| LQW18ANR27J00□ | 270nH ±5% | 100MHz | 110mA | 3.4Ω | 30 | 100MHz | 960MHz | |
| LQW18ANR33G00□ | 330nH ±2% | 100MHz | 85mA | 5.5Ω | 30 | 100MHz | 800MHz | Kit |
| LQW18ANR33J00□ | 330nH ±5% | 100MHz | 85mA | 5.5Ω | 30 | 100MHz | 800MHz | |
| LQW18ANR39G00□ | 390nH ±2% | 100MHz | 80mA | 6.2Ω | 30 | 100MHz | 800MHz | Kit |
| LQW18ANR39J00□ | 390nH ±5% | 100MHz | 80mA | 6.2Ω | 30 | 100MHz | 800MHz | |
| LQW18ANR47G00□ | 470nH ±2% | 100MHz | 75mA | 7.0Ω | 30 | 100MHz | 700MHz | Kit |
| LQW18ANR47J00□ | 470nH ±5% | 100MHz | 75mA | 7.0Ω | 30 | 100MHz | 700MHz | |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
 For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Reference Data

LQW18AN_00

4991A&16197A

| Part Number | Inductance (nH) | Q (Typ.) | | | | |
|---------------|-----------------|----------|--------|--------|--------|--------|
| | Nominal | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQW18AN2N2□00 | 2.2 | 74 | 77 | 113 | 124 | 134 |
| LQW18AN3N6□00 | 3.6 | 60 | 63 | 92 | 94 | 103 |
| LQW18AN3N9□00 | 3.9 | 65 | 68 | 97 | 99 | 109 |
| LQW18AN4N3□00 | 4.3 | 71 | 74 | 105 | 107 | 118 |
| LQW18AN4N7□00 | 4.7 | 72 | 75 | 108 | 120 | 130 |
| LQW18AN5N6□00 | 5.6 | 67 | 70 | 100 | 103 | 113 |
| LQW18AN6N2□00 | 6.2 | 70 | 73 | 105 | 107 | 118 |
| LQW18AN6N8□00 | 6.8 | 78 | 82 | 115 | 117 | 127 |
| LQW18AN7N5□00 | 7.5 | 85 | 86 | 117 | 132 | 140 |
| LQW18AN8N2□00 | 8.2 | 73 | 78 | 112 | 116 | 130 |
| LQW18AN8N7□00 | 8.7 | 80 | 82 | 115 | 132 | 143 |
| LQW18AN9N1□00 | 9.1 | 86 | 88 | 124 | 142 | 155 |
| LQW18AN9N5□00 | 9.5 | 79 | 84 | 119 | 119 | 132 |
| LQW18AN10N□00 | 10 | 75 | 78 | 103 | 102 | 105 |
| LQW18AN11N□00 | 11 | 82 | 85 | 110 | 108 | 110 |
| LQW18AN12N□00 | 12 | 80 | 84 | 114 | 114 | 120 |
| LQW18AN13N□00 | 13 | 79 | 82 | 108 | 105 | 107 |
| LQW18AN15N□00 | 15 | 81 | 84 | 102 | 97 | 92 |
| LQW18AN16N□00 | 16 | 86 | 90 | 119 | 116 | 119 |
| LQW18AN18N□00 | 18 | 82 | 85 | 101 | 96 | 89 |
| LQW18AN20N□00 | 20 | 81 | 83 | 95 | 90 | 78 |
| LQW18AN22N□00 | 22 | 84 | 88 | 104 | 101 | 95 |
| LQW18AN24N□00 | 24 | 80 | 82 | 92 | 86 | 75 |
| LQW18AN27N□00 | 27 | 79 | 81 | 80 | 72 | 57 |
| LQW18AN30N□00 | 30 | 81 | 82 | 84 | 75 | 59 |
| LQW18AN33N□00 | 33 | 78 | 79 | 71 | 60 | 43 |
| LQW18AN36N□00 | 36 | 79 | 81 | 73 | 62 | 44 |
| LQW18AN39N□00 | 39 | 78 | 78 | 66 | 55 | 37 |
| LQW18AN43N□00 | 43 | 79 | 81 | 73 | 61 | 43 |
| LQW18AN47N□00 | 47 | 75 | 74 | 55 | 42 | 24 |
| LQW18AN51N□00 | 51 | 77 | 78 | 60 | 46 | 26 |
| LQW18AN56N□00 | 56 | 80 | 82 | 66 | 51 | 31 |
| LQW18AN62N□00 | 62 | 71 | 71 | 40 | 26 | 7 |
| LQW18AN68N□00 | 68 | 75 | 77 | 46 | 31 | 11 |
| LQW18AN72N□00 | 72 | 69 | 69 | 37 | 23 | 4 |
| LQW18AN75N□00 | 75 | 68 | 66 | 32 | 18 | - |
| LQW18AN82N□00 | 82 | 66 | 64 | 26 | 12 | - |
| LQW18AN91N□00 | 91 | 66 | 65 | 22 | 8 | - |
| LQW18ANR10□00 | 100 | 68 | 67 | 24 | 9 | - |
| LQW18ANR11□00 | 110 | 65 | 63 | 15 | 1 | - |
| LQW18ANR12□00 | 120 | 64 | 62 | 11 | - | - |
| LQW18ANR13□00 | 130 | 62 | 59 | 7 | - | - |
| LQW18ANR15□00 | 150 | 60 | 57 | 3 | - | - |
| LQW18ANR16□00 | 160 | 59 | 54 | - | - | - |
| LQW18ANR18□00 | 180 | 60 | 55 | - | - | - |
| LQW18ANR20□00 | 200 | 57 | 54 | - | - | - |
| LQW18ANR22□00 | 220 | 54 | 47 | - | - | - |
| LQW18ANR27□00 | 270 | 52 | 46 | - | - | - |
| LQW18ANR33□00 | 330 | 47 | 35 | - | - | - |
| LQW18ANR39□00 | 390 | 33 | 23 | - | - | - |
| LQW18ANR47□00 | 470 | 22 | 13 | - | - | - |


△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQW18AN_10

Series 0603/1608 (inch/mm)

Size Code 0603 (1608) in inch (in mm), High Q, Low DC Resistance Type

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| J | ø330mm Paper Taping | 10000 |
| B | Packing in Bulk | 500 |



Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW18AN2N2D10□ | 2.2nH ±0.5nH | 100MHz | 1400mA | 0.018Ω | 25 | 250MHz | 18000MHz | |
| LQW18AN3N9C10□ | 3.9nH ±0.2nH | 100MHz | 1000mA | 0.032Ω | 38 | 250MHz | 11000MHz | Kit |
| LQW18AN3N9D10□ | 3.9nH ±0.5nH | 100MHz | 1000mA | 0.032Ω | 38 | 250MHz | 11000MHz | |
| LQW18AN5N6D10□ | 5.6nH ±0.5nH | 100MHz | 900mA | 0.045Ω | 38 | 250MHz | 10000MHz | |
| LQW18AN6N8C10□ | 6.8nH ±0.2nH | 100MHz | 900mA | 0.045Ω | 38 | 250MHz | 7000MHz | Kit |
| LQW18AN6N8D10□ | 6.8nH ±0.5nH | 100MHz | 900mA | 0.045Ω | 38 | 250MHz | 7000MHz | |
| LQW18AN8N2D10□ | 8.2nH ±0.5nH | 100MHz | 800mA | 0.058Ω | 38 | 250MHz | 7000MHz | |
| LQW18AN10NG10□ | 10nH ±2% | 100MHz | 800mA | 0.058Ω | 38 | 250MHz | 5000MHz | Kit |
| LQW18AN10NJ10□ | 10nH ±5% | 100MHz | 800mA | 0.058Ω | 38 | 250MHz | 5000MHz | |
| LQW18AN12NG10□ | 12nH ±2% | 100MHz | 750mA | 0.071Ω | 38 | 250MHz | 5000MHz | Kit |
| LQW18AN12NJ10□ | 12nH ±5% | 100MHz | 750mA | 0.071Ω | 38 | 250MHz | 5000MHz | |
| LQW18AN15NJ10□ | 15nH ±5% | 100MHz | 700mA | 0.085Ω | 42 | 250MHz | 4500MHz | |
| LQW18AN18NG10□ | 18nH ±2% | 100MHz | 700mA | 0.085Ω | 42 | 250MHz | 3500MHz | Kit |
| LQW18AN18NJ10□ | 18nH ±5% | 100MHz | 700mA | 0.085Ω | 42 | 250MHz | 3500MHz | |
| LQW18AN22NG10□ | 22nH ±2% | 100MHz | 640mA | 0.099Ω | 42 | 250MHz | 3200MHz | Kit |
| LQW18AN22NJ10□ | 22nH ±5% | 100MHz | 640mA | 0.099Ω | 42 | 250MHz | 3200MHz | |
| LQW18AN27NG10□ | 27nH ±2% | 100MHz | 590mA | 0.116Ω | 42 | 250MHz | 2800MHz | Kit |
| LQW18AN27NJ10□ | 27nH ±5% | 100MHz | 590mA | 0.116Ω | 42 | 250MHz | 2800MHz | |
| LQW18AN33NJ10□ | 33nH ±5% | 100MHz | 550mA | 0.132Ω | 42 | 250MHz | 2500MHz | |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.


Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



■ Reference Data

LQW18AN_10

4991A&16197A


| Part Number | Inductance (nH) | Q (Typ.) | | | | |
|---------------|-----------------|----------|--------|--------|--------|--------|
| | Nominal | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQW18AN2N2□10 | 2.2 | 72 | 75 | 114 | 125 | 134 |
| LQW18AN3N9□10 | 3.9 | 75 | 81 | 117 | 120 | 130 |
| LQW18AN5N6□10 | 5.6 | 73 | 76 | 109 | 124 | 136 |
| LQW18AN6N8□10 | 6.8 | 85 | 91 | 124 | 124 | 131 |
| LQW18AN8N2□10 | 8.2 | 86 | 89 | 130 | 152 | 171 |
| LQW18AN10N□10 | 10 | 84 | 89 | 117 | 115 | 119 |
| LQW18AN12N□10 | 12 | 88 | 95 | 125 | 123 | 128 |
| LQW18AN15N□10 | 15 | 81 | 85 | 125 | 149 | 169 |
| LQW18AN18N□10 | 18 | 90 | 96 | 112 | 106 | 101 |
| LQW18AN22N□10 | 22 | 88 | 93 | 97 | 90 | 80 |
| LQW18AN27N□10 | 27 | 83 | 88 | 85 | 77 | 63 |
| LQW18AN33N□10 | 33 | 94 | 93 | 107 | 121 | 121 |

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQW18AN_80 Series 0603/1608 (inch/mm)

High Frequency Inductors with Low DC Resistance and High Current Capability

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|---------------------|------------------|
| D | ø180mm Paper Taping | 4000 |
| J | ø330mm Paper Taping | 10000 |
| B | Packing in Bulk | 500 |



Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|---------|
| LQW18AN2N2C80□ | 2.2nH ±0.2nH | 100MHz | 3200mA | 0.018Ω | 24 | 250MHz | 15000MHz | New |
| LQW18AN2N4C80□ | 2.4nH ±0.2nH | 100MHz | 2400mA | 0.026Ω | 18 | 250MHz | 15000MHz | New |
| LQW18AN3N0C80□ | 3.0nH ±0.2nH | 100MHz | 670mA | 0.17Ω | 13 | 250MHz | 15000MHz | New |
| LQW18AN3N9B80□ | 3.9nH ±0.1nH | 100MHz | 2200mA | 0.028Ω | 30 | 250MHz | 10000MHz | New |
| LQW18AN3N9C80□ | 3.9nH ±0.2nH | 100MHz | 2200mA | 0.028Ω | 30 | 250MHz | 10000MHz | New |
| LQW18AN4N1B80□ | 4.1nH ±0.1nH | 100MHz | 2200mA | 0.028Ω | 30 | 250MHz | 10000MHz | New |
| LQW18AN4N1C80□ | 4.1nH ±0.2nH | 100MHz | 2200mA | 0.028Ω | 30 | 250MHz | 10000MHz | New |
| LQW18AN4N2B80□ | 4.2nH ±0.1nH | 100MHz | 2200mA | 0.028Ω | 30 | 250MHz | 10000MHz | New |
| LQW18AN4N2C80□ | 4.2nH ±0.2nH | 100MHz | 2200mA | 0.028Ω | 30 | 250MHz | 10000MHz | New |
| LQW18AN4N3B80□ | 4.3nH ±0.1nH | 100MHz | 2100mA | 0.036Ω | 35 | 250MHz | 11600MHz | New Kit |
| LQW18AN4N3C80□ | 4.3nH ±0.2nH | 100MHz | 2100mA | 0.036Ω | 35 | 250MHz | 11600MHz | New |
| LQW18AN4N7B80□ | 4.7nH ±0.1nH | 100MHz | 1500mA | 0.054Ω | 25 | 250MHz | 10400MHz | New Kit |
| LQW18AN4N7C80□ | 4.7nH ±0.2nH | 100MHz | 1500mA | 0.054Ω | 25 | 250MHz | 10400MHz | New |
| LQW18AN4N9B80□ | 4.9nH ±0.1nH | 100MHz | 1200mA | 0.081Ω | 23 | 250MHz | 7300MHz | New Kit |
| LQW18AN4N9C80□ | 4.9nH ±0.2nH | 100MHz | 1200mA | 0.081Ω | 23 | 250MHz | 7300MHz | New |
| LQW18AN5N6C80□ | 5.6nH ±0.2nH | 100MHz | 1900mA | 0.04Ω | 38 | 250MHz | 6650MHz | New |
| LQW18AN6N0C80□ | 6.0nH ±0.2nH | 100MHz | 1900mA | 0.04Ω | 40 | 250MHz | 6650MHz | New |
| LQW18AN6N5C80□ | 6.5nH ±0.2nH | 100MHz | 1900mA | 0.04Ω | 40 | 250MHz | 6650MHz | New |
| LQW18AN6N8C80□ | 6.8nH ±0.2nH | 100MHz | 1900mA | 0.04Ω | 40 | 250MHz | 6650MHz | New |
| LQW18AN7N2C80□ | 7.2nH ±0.2nH | 100MHz | 1900mA | 0.04Ω | 38 | 250MHz | 6650MHz | New |
| LQW18AN7N5C80□ | 7.5nH ±0.2nH | 100MHz | 1500mA | 0.048Ω | 35 | 250MHz | 7000MHz | New |
| LQW18AN8N2C80□ | 8.2nH ±0.2nH | 100MHz | 1600mA | 0.052Ω | 38 | 250MHz | 4750MHz | New |
| LQW18AN8N4C80□ | 8.4nH ±0.2nH | 100MHz | 1600mA | 0.052Ω | 38 | 250MHz | 4750MHz | New |
| LQW18AN8N7C80□ | 8.7nH ±0.2nH | 100MHz | 1600mA | 0.052Ω | 38 | 250MHz | 4750MHz | New |
| LQW18AN9N1C80□ | 9.1nH ±0.2nH | 100MHz | 1600mA | 0.052Ω | 38 | 250MHz | 4750MHz | New |
| LQW18AN9N5C80□ | 9.5nH ±0.2nH | 100MHz | 1600mA | 0.052Ω | 38 | 250MHz | 4750MHz | New |
| LQW18AN9N9C80□ | 9.9nH ±0.2nH | 100MHz | 1600mA | 0.052Ω | 38 | 250MHz | 4750MHz | New |
| LQW18AN10NG80□ | 10nH ±2% | 100MHz | 1600mA | 0.052Ω | 38 | 250MHz | 4750MHz | New |
| LQW18AN10NJ80□ | 10nH ±5% | 100MHz | 1600mA | 0.052Ω | 38 | 250MHz | 4750MHz | New |
| LQW18AN11NG80□ | 11nH ±2% | 100MHz | 1600mA | 0.052Ω | 40 | 250MHz | 4750MHz | New |
| LQW18AN11NJ80□ | 11nH ±5% | 100MHz | 1600mA | 0.052Ω | 40 | 250MHz | 4750MHz | New |
| LQW18AN12NG80□ | 12nH ±2% | 100MHz | 1500mA | 0.064Ω | 37 | 250MHz | 5000MHz | New |


Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|---------|
| LQW18AN12NJ80□ | 12nH ±5% | 100MHz | 1500mA | 0.064Ω | 37 | 250MHz | 5000MHz | New |
| LQW18AN13NG80□ | 13nH ±2% | 100MHz | 1500mA | 0.064Ω | 37 | 250MHz | 5000MHz | New |
| LQW18AN13NJ80□ | 13nH ±5% | 100MHz | 1500mA | 0.064Ω | 37 | 250MHz | 5000MHz | New |
| LQW18AN15NG80□ | 15nH ±2% | 100MHz | 1400mA | 0.075Ω | 38 | 250MHz | 4600MHz | New |
| LQW18AN15NJ80□ | 15nH ±5% | 100MHz | 1400mA | 0.075Ω | 38 | 250MHz | 4600MHz | New |
| LQW18AN16NG80□ | 16nH ±2% | 100MHz | 1400mA | 0.075Ω | 40 | 250MHz | 4600MHz | New |
| LQW18AN16NJ80□ | 16nH ±5% | 100MHz | 1400mA | 0.075Ω | 40 | 250MHz | 4600MHz | New |
| LQW18AN17NG80□ | 17nH ±2% | 100MHz | 1400mA | 0.075Ω | 40 | 250MHz | 4600MHz | New |
| LQW18AN17NJ80□ | 17nH ±5% | 100MHz | 1400mA | 0.075Ω | 40 | 250MHz | 4600MHz | New |
| LQW18AN18NG80□ | 18nH ±2% | 100MHz | 1400mA | 0.075Ω | 40 | 250MHz | 4600MHz | New |
| LQW18AN18NJ80□ | 18nH ±5% | 100MHz | 1400mA | 0.075Ω | 40 | 250MHz | 4600MHz | New |
| LQW18AN19NG80□ | 19nH ±2% | 100MHz | 1400mA | 0.075Ω | 40 | 250MHz | 4600MHz | New |
| LQW18AN19NJ80□ | 19nH ±5% | 100MHz | 1400mA | 0.075Ω | 40 | 250MHz | 4600MHz | New |
| LQW18AN22NG80□ | 22nH ±2% | 100MHz | 1300mA | 0.086Ω | 40 | 250MHz | 3450MHz | New |
| LQW18AN22NJ80□ | 22nH ±5% | 100MHz | 1300mA | 0.086Ω | 40 | 250MHz | 3450MHz | New |
| LQW18AN23NG80□ | 23nH ±2% | 100MHz | 1300mA | 0.086Ω | 40 | 250MHz | 3450MHz | New |
| LQW18AN23NJ80□ | 23nH ±5% | 100MHz | 1300mA | 0.086Ω | 40 | 250MHz | 3450MHz | New |
| LQW18AN24NG80□ | 24nH ±2% | 100MHz | 1300mA | 0.086Ω | 40 | 250MHz | 3450MHz | New |
| LQW18AN24NJ80□ | 24nH ±5% | 100MHz | 1300mA | 0.086Ω | 40 | 250MHz | 3450MHz | New |
| LQW18AN25NG80□ | 25nH ±2% | 100MHz | 1200mA | 0.098Ω | 40 | 250MHz | 3600MHz | New |
| LQW18AN25NJ80□ | 25nH ±5% | 100MHz | 1200mA | 0.098Ω | 40 | 250MHz | 3600MHz | New |
| LQW18AN27NG80□ | 27nH ±2% | 100MHz | 1200mA | 0.098Ω | 40 | 250MHz | 3600MHz | New |
| LQW18AN27NJ80□ | 27nH ±5% | 100MHz | 1200mA | 0.098Ω | 40 | 250MHz | 3600MHz | New |
| LQW18AN28NG80□ | 28nH ±2% | 100MHz | 1200mA | 0.098Ω | 40 | 250MHz | 3600MHz | New |
| LQW18AN28NJ80□ | 28nH ±5% | 100MHz | 1200mA | 0.098Ω | 40 | 250MHz | 3600MHz | New |
| LQW18AN30NG80□ | 30nH ±2% | 100MHz | 1100mA | 0.12Ω | 40 | 250MHz | 2880MHz | New Kit |
| LQW18AN30NJ80□ | 30nH ±5% | 100MHz | 1100mA | 0.12Ω | 40 | 250MHz | 2880MHz | New |
| LQW18AN31NG80□ | 31nH ±2% | 100MHz | 1100mA | 0.11Ω | 40 | 250MHz | 3150MHz | New |
| LQW18AN31NJ80□ | 31nH ±5% | 100MHz | 1100mA | 0.11Ω | 40 | 250MHz | 3150MHz | New |
| LQW18AN33NG80□ | 33nH ±2% | 100MHz | 1100mA | 0.11Ω | 40 | 250MHz | 3150MHz | New |
| LQW18AN33NJ80□ | 33nH ±5% | 100MHz | 1100mA | 0.11Ω | 40 | 250MHz | 3150MHz | New |
| LQW18AN34NG80□ | 34nH ±2% | 100MHz | 1050mA | 0.15Ω | 40 | 250MHz | 3000MHz | New |
| LQW18AN34NJ80□ | 34nH ±5% | 100MHz | 1050mA | 0.15Ω | 40 | 250MHz | 3000MHz | New |
| LQW18AN36NG80□ | 36nH ±2% | 100MHz | 910mA | 0.20Ω | 37 | 250MHz | 3000MHz | New Kit |
| LQW18AN36NJ80□ | 36nH ±5% | 100MHz | 910mA | 0.20Ω | 37 | 250MHz | 3000MHz | New |
| LQW18AN37NG80□ | 37nH ±2% | 100MHz | 910mA | 0.20Ω | 37 | 250MHz | 3000MHz | New |
| LQW18AN37NJ80□ | 37nH ±5% | 100MHz | 910mA | 0.20Ω | 37 | 250MHz | 3000MHz | New |
| LQW18AN39NG80□ | 39nH ±2% | 100MHz | 1000mA | 0.16Ω | 40 | 250MHz | 3280MHz | New Kit |
| LQW18AN39NJ80□ | 39nH ±5% | 100MHz | 1000mA | 0.16Ω | 40 | 250MHz | 3280MHz | New |
| LQW18AN41NG80□ | 41nH ±2% | 100MHz | 1000mA | 0.16Ω | 40 | 250MHz | 3280MHz | New |
| LQW18AN41NJ80□ | 41nH ±5% | 100MHz | 1000mA | 0.16Ω | 40 | 250MHz | 3280MHz | New |
| LQW18AN43NG80□ | 43nH ±2% | 100MHz | 840mA | 0.21Ω | 40 | 250MHz | 2780MHz | New Kit |
| LQW18AN43NJ80□ | 43nH ±5% | 100MHz | 840mA | 0.21Ω | 40 | 250MHz | 2780MHz | New |
| LQW18AN44NG80□ | 44nH ±2% | 100MHz | 840mA | 0.21Ω | 40 | 250MHz | 2780MHz | New |
| LQW18AN44NJ80□ | 44nH ±5% | 100MHz | 840mA | 0.21Ω | 40 | 250MHz | 2780MHz | New |
| LQW18AN47NG80□ | 47nH ±2% | 100MHz | 830mA | 0.23Ω | 32 | 200MHz | 2700MHz | New Kit |
| LQW18AN47NJ80□ | 47nH ±5% | 100MHz | 830mA | 0.23Ω | 32 | 200MHz | 2700MHz | New |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

Continued on the following page. 

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|---------|
| LQW18AN48NG80□ | 48nH ±2% | 100MHz | 830mA | 0.23Ω | 32 | 200MHz | 2700MHz | New |
| LQW18AN48NJ80□ | 48nH ±5% | 100MHz | 830mA | 0.23Ω | 32 | 200MHz | 2700MHz | New |
| LQW18AN51NG80□ | 51nH ±2% | 100MHz | 830mA | 0.23Ω | 32 | 200MHz | 2700MHz | New Kit |
| LQW18AN51NJ80□ | 51nH ±5% | 100MHz | 830mA | 0.23Ω | 32 | 200MHz | 2700MHz | New |
| LQW18AN52NG80□ | 52nH ±2% | 100MHz | 750mA | 0.27Ω | 35 | 200MHz | 2750MHz | New |
| LQW18AN52NJ80□ | 52nH ±5% | 100MHz | 750mA | 0.27Ω | 35 | 200MHz | 2750MHz | New |
| LQW18AN56NG80□ | 56nH ±2% | 100MHz | 770mA | 0.26Ω | 38 | 200MHz | 2600MHz | New Kit |
| LQW18AN56NJ80□ | 56nH ±5% | 100MHz | 770mA | 0.26Ω | 38 | 200MHz | 2600MHz | New |
| LQW18AN58NG80□ | 58nH ±2% | 100MHz | 700mA | 0.30Ω | 35 | 200MHz | 2400MHz | New |
| LQW18AN58NJ80□ | 58nH ±5% | 100MHz | 700mA | 0.30Ω | 35 | 200MHz | 2400MHz | New |
| LQW18AN68NG80□ | 68nH ±2% | 100MHz | 630mA | 0.38Ω | 37 | 200MHz | 2380MHz | New Kit |
| LQW18AN68NJ80□ | 68nH ±5% | 100MHz | 630mA | 0.38Ω | 37 | 200MHz | 2380MHz | New |
| LQW18AN69NG80□ | 69nH ±2% | 100MHz | 630mA | 0.38Ω | 37 | 200MHz | 2380MHz | New |
| LQW18AN69NJ80□ | 69nH ±5% | 100MHz | 630mA | 0.38Ω | 37 | 200MHz | 2380MHz | New |
| LQW18AN72NG80□ | 72nH ±2% | 100MHz | 560mA | 0.47Ω | 34 | 150MHz | 2330MHz | New Kit |
| LQW18AN72NJ80□ | 72nH ±5% | 100MHz | 560mA | 0.47Ω | 34 | 150MHz | 2330MHz | New |
| LQW18AN73NG80□ | 73nH ±2% | 100MHz | 590mA | 0.41Ω | 28 | 150MHz | 2280MHz | New |
| LQW18AN73NJ80□ | 73nH ±5% | 100MHz | 590mA | 0.41Ω | 28 | 150MHz | 2280MHz | New |
| LQW18AN75NG80□ | 75nH ±2% | 100MHz | 590mA | 0.41Ω | 28 | 150MHz | 2280MHz | New Kit |
| LQW18AN75NJ80□ | 75nH ±5% | 100MHz | 590mA | 0.41Ω | 28 | 150MHz | 2280MHz | New |
| LQW18AN78NG80□ | 78nH ±2% | 100MHz | 590mA | 0.41Ω | 28 | 150MHz | 2280MHz | New |
| LQW18AN78NJ80□ | 78nH ±5% | 100MHz | 590mA | 0.41Ω | 28 | 150MHz | 2280MHz | New |
| LQW18AN82NG80□ | 82nH ±2% | 100MHz | 550mA | 0.5Ω | 34 | 150MHz | 2230MHz | New Kit |
| LQW18AN82NJ80□ | 82nH ±5% | 100MHz | 550mA | 0.5Ω | 34 | 150MHz | 2230MHz | New |
| LQW18AN83NG80□ | 83nH ±2% | 100MHz | 550mA | 0.5Ω | 34 | 150MHz | 2230MHz | New |
| LQW18AN83NJ80□ | 83nH ±5% | 100MHz | 550mA | 0.5Ω | 34 | 150MHz | 2230MHz | New |
| LQW18AN91NG80□ | 91nH ±2% | 100MHz | 520mA | 0.54Ω | 33 | 150MHz | 1900MHz | New Kit |
| LQW18AN91NJ80□ | 91nH ±5% | 100MHz | 520mA | 0.54Ω | 33 | 150MHz | 1900MHz | New |
| LQW18AN94NG80□ | 94nH ±2% | 100MHz | 490mA | 0.63Ω | 34 | 150MHz | 1750MHz | New |
| LQW18AN94NJ80□ | 94nH ±5% | 100MHz | 490mA | 0.63Ω | 34 | 150MHz | 1750MHz | New |
| LQW18ANR10G80□ | 100nH ±2% | 100MHz | 490mA | 0.63Ω | 34 | 150MHz | 1750MHz | New Kit |
| LQW18ANR10J80□ | 100nH ±5% | 100MHz | 490mA | 0.63Ω | 34 | 150MHz | 1750MHz | New |
| LQW18ANR11G80□ | 110nH ±2% | 100MHz | 450mA | 0.7Ω | 32 | 150MHz | 1730MHz | New Kit |
| LQW18ANR11J80□ | 110nH ±5% | 100MHz | 450mA | 0.7Ω | 32 | 150MHz | 1730MHz | New |
| LQW18ANR12G80□ | 120nH ±2% | 100MHz | 450mA | 0.72Ω | 32 | 150MHz | 1650MHz | New Kit |
| LQW18ANR12J80□ | 120nH ±5% | 100MHz | 450mA | 0.72Ω | 32 | 150MHz | 1650MHz | New |
| LQW18ANR15G80□ | 150nH ±2% | 100MHz | 420mA | 0.87Ω | 28 | 150MHz | 1580MHz | New Kit |
| LQW18ANR15J80□ | 150nH ±5% | 100MHz | 420mA | 0.87Ω | 28 | 150MHz | 1580MHz | New |
| LQW18ANR18G80□ | 180nH ±2% | 100MHz | 310mA | 1.65Ω | 25 | 100MHz | 1380MHz | New Kit |
| LQW18ANR18J80□ | 180nH ±5% | 100MHz | 310mA | 1.65Ω | 25 | 100MHz | 1380MHz | New |
| LQW18ANR20G80□ | 200nH ±2% | 100MHz | 290mA | 1.74Ω | 25 | 100MHz | 1350MHz | New Kit |
| LQW18ANR20J80□ | 200nH ±5% | 100MHz | 290mA | 1.74Ω | 25 | 100MHz | 1350MHz | New |
| LQW18ANR21G80□ | 210nH ±2% | 100MHz | 280mA | 1.98Ω | 27 | 100MHz | 1330MHz | New Kit |
| LQW18ANR21J80□ | 210nH ±5% | 100MHz | 280mA | 1.98Ω | 27 | 100MHz | 1330MHz | New |
| LQW18ANR22G80□ | 220nH ±2% | 100MHz | 280mA | 2.08Ω | 25 | 100MHz | 1330MHz | New Kit |
| LQW18ANR22J80□ | 220nH ±5% | 100MHz | 280mA | 2.08Ω | 25 | 100MHz | 1330MHz | New |
| LQW18ANR25G80□ | 250nH ±2% | 100MHz | 250mA | 2.28Ω | 24 | 100MHz | 1330MHz | New Kit |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.


Continued on the following page. 

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|---------|
| LQW18ANR25J80□ | 250nH ±5% | 100MHz | 250mA | 2.28Ω | 24 | 100MHz | 1330MHz | New |
| LQW18ANR27G80□ | 270nH ±2% | 100MHz | 260mA | 2.42Ω | 24 | 100MHz | 1250MHz | New Kit |
| LQW18ANR27J80□ | 270nH ±5% | 100MHz | 260mA | 2.42Ω | 24 | 100MHz | 1250MHz | New |
| LQW18ANR30G80□ | 300nH ±2% | 100MHz | 220mA | 3.12Ω | 25 | 100MHz | 1200MHz | New Kit |
| LQW18ANR30J80□ | 300nH ±5% | 100MHz | 220mA | 3.12Ω | 25 | 100MHz | 1200MHz | New |
| LQW18ANR33G80□ | 330nH ±2% | 100MHz | 190mA | 3.84Ω | 25 | 100MHz | 1100MHz | New Kit |
| LQW18ANR33J80□ | 330nH ±5% | 100MHz | 190mA | 3.84Ω | 25 | 100MHz | 1100MHz | New |
| LQW18ANR36G80□ | 360nH ±2% | 100MHz | 190mA | 3.98Ω | 25 | 100MHz | 1050MHz | New Kit |
| LQW18ANR36J80□ | 360nH ±5% | 100MHz | 190mA | 3.98Ω | 25 | 100MHz | 1050MHz | New |
| LQW18ANR39G80□ | 390nH ±2% | 100MHz | 190mA | 4.23Ω | 25 | 100MHz | 1100MHz | New Kit |
| LQW18ANR39J80□ | 390nH ±5% | 100MHz | 190mA | 4.23Ω | 25 | 100MHz | 1100MHz | New |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)




■ Inductance-Frequency Characteristics (Typ.)



■ Derating of Rated Current

In operating temperature exceeding +85°C, derating of current is necessary for LQW18AN_80 series. Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current



△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


Wire Wound Type (Non-Magnetic Core)

LQW2BHN_03

Series 0805/2015 (inch/mm)

Size Code 0805 (2015) in inch (in mm), Wound Type

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |
| K | ø330mm Embossed Taping | 7500 |



Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW2BHN3N3D03□ | 3.3nH ±0.5nH | 100MHz | 910mA | 0.05Ω | 10 | 250MHz | 6000MHz | |
| LQW2BHN6N8D03□ | 6.8nH ±0.5nH | 100MHz | 680mA | 0.11Ω | 20 | 250MHz | 5400MHz | |
| LQW2BHN8N2D03□ | 8.2nH ±0.5nH | 100MHz | 630mA | 0.12Ω | 20 | 250MHz | 3900MHz | |
| LQW2BHN10NJ03□ | 10nH ±5% | 100MHz | 1320mA | 0.03Ω | 30 | 250MHz | 3300MHz | |
| LQW2BHN12NJ03□ | 12nH ±5% | 100MHz | 680mA | 0.11Ω | 30 | 250MHz | 3200MHz | |
| LQW2BHN15NJ03□ | 15nH ±5% | 100MHz | 630mA | 0.12Ω | 30 | 250MHz | 2700MHz | |
| LQW2BHN18NJ03□ | 18nH ±5% | 100MHz | 690mA | 0.10Ω | 30 | 250MHz | 2600MHz | |
| LQW2BHN22NJ03□ | 22nH ±5% | 100MHz | 720mA | 0.09Ω | 30 | 250MHz | 2100MHz | |
| LQW2BHN27NJ03□ | 27nH ±5% | 100MHz | 540mA | 0.17Ω | 40 | 250MHz | 2300MHz | |
| LQW2BHN33NG03□ | 33nH ±2% | 100MHz | 570mA | 0.15Ω | 40 | 250MHz | 1900MHz | Kit |
| LQW2BHN33NJ03□ | 33nH ±5% | 100MHz | 570mA | 0.15Ω | 40 | 250MHz | 1900MHz | |
| LQW2BHN39NG03□ | 39nH ±2% | 100MHz | 730mA | 0.09Ω | 40 | 250MHz | 1700MHz | Kit |
| LQW2BHN39NJ03□ | 39nH ±5% | 100MHz | 730mA | 0.09Ω | 40 | 250MHz | 1700MHz | |
| LQW2BHN47NG03□ | 47nH ±2% | 100MHz | 450mA | 0.23Ω | 40 | 200MHz | 1600MHz | Kit |
| LQW2BHN47NJ03□ | 47nH ±5% | 100MHz | 450mA | 0.23Ω | 40 | 200MHz | 1600MHz | |
| LQW2BHN56NG03□ | 56nH ±2% | 100MHz | 430mA | 0.26Ω | 40 | 200MHz | 1500MHz | Kit |
| LQW2BHN56NJ03□ | 56nH ±5% | 100MHz | 430mA | 0.26Ω | 40 | 200MHz | 1500MHz | |
| LQW2BHN68NG03□ | 68nH ±2% | 100MHz | 460mA | 0.23Ω | 40 | 200MHz | 1200MHz | Kit |
| LQW2BHN68NJ03□ | 68nH ±5% | 100MHz | 460mA | 0.23Ω | 40 | 200MHz | 1200MHz | |
| LQW2BHN82NG03□ | 82nH ±2% | 100MHz | 320mA | 0.42Ω | 40 | 150MHz | 1100MHz | Kit |
| LQW2BHN82NJ03□ | 82nH ±5% | 100MHz | 320mA | 0.42Ω | 40 | 150MHz | 1100MHz | |
| LQW2BHNR10G03□ | 100nH ±2% | 100MHz | 270mA | 0.55Ω | 35 | 150MHz | 900MHz | Kit |
| LQW2BHNR10J03□ | 100nH ±5% | 100MHz | 350mA | 0.38Ω | 40 | 150MHz | 900MHz | |
| LQW2BHNR12G03□ | 120nH ±2% | 100MHz | 320mA | 0.40Ω | 40 | 150MHz | 750MHz | Kit |
| LQW2BHNR12J03□ | 120nH ±5% | 100MHz | 320mA | 0.40Ω | 40 | 150MHz | 750MHz | |
| LQW2BHNR15G03□ | 150nH ±2% | 100MHz | 260mA | 0.68Ω | 30 | 150MHz | 350MHz | Kit |
| LQW2BHNR15J03□ | 150nH ±5% | 100MHz | 390mA | 0.47Ω | 30 | 150MHz | 350MHz | |
| LQW2BHNR18G03□ | 180nH ±2% | 100MHz | 250mA | 0.71Ω | 35 | 100MHz | 700MHz | Kit |
| LQW2BHNR18J03□ | 180nH ±5% | 100MHz | 250mA | 0.71Ω | 35 | 100MHz | 700MHz | |
| LQW2BHNR22G03□ | 220nH ±2% | 100MHz | 240mA | 0.70Ω | 35 | 100MHz | 500MHz | Kit |
| LQW2BHNR22J03□ | 220nH ±5% | 100MHz | 240mA | 0.70Ω | 35 | 100MHz | 500MHz | |
| LQW2BHNR27J03□ | 270nH ±5% | 10MHz | 190mA | 2.00Ω | 15 | 25.2MHz | 550MHz | |
| LQW2BHNR27K03□ | 270nH ±10% | 10MHz | 190mA | 2.00Ω | 15 | 25.2MHz | 550MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW2BHNR33J03□ | 330nH ±5% | 10MHz | 180mA | 2.20Ω | 15 | 25.2MHz | 500MHz | |
| LQW2BHNR33K03□ | 330nH ±10% | 10MHz | 180mA | 2.20Ω | 15 | 25.2MHz | 500MHz | Kit |
| LQW2BHNR39J03□ | 390nH ±5% | 10MHz | 170mA | 2.50Ω | 15 | 25.2MHz | 400MHz | |
| LQW2BHNR39K03□ | 390nH ±10% | 10MHz | 170mA | 2.50Ω | 15 | 25.2MHz | 400MHz | Kit |
| LQW2BHNR47J03□ | 470nH ±5% | 10MHz | 160mA | 2.80Ω | 15 | 25.2MHz | 350MHz | |
| LQW2BHNR47K03□ | 470nH ±10% | 10MHz | 160mA | 2.80Ω | 15 | 25.2MHz | 350MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



■ Reference Data

LQW2BHN_03

4991A&16197A

| Part Number | Inductance (nH) | | Q (Typ.) | | | |
|---------------|-----------------|--------|----------|--------|--------|--------|
| | 100MHz | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQW2BHN3N3□03 | 3.3 | 55 | 58 | 85 | 88 | 98 |
| LQW2BHN6N8□03 | 6.8 | 51 | 55 | 77 | 78 | 80 |
| LQW2BHN8N2□03 | 8.2 | 60 | 64 | 88 | 88 | 88 |
| LQW2BHN10N□03 | 10 | 81 | 86 | 114 | 110 | 100 |
| LQW2BHN12N□03 | 12 | 77 | 81 | 88 | 83 | 77 |
| LQW2BHN15N□03 | 15 | 76 | 80 | 75 | 66 | 50 |
| LQW2BHN18N□03 | 18 | 81 | 83 | 70 | 58 | 39 |
| LQW2BHN22N□03 | 22 | 85 | 87 | 47 | 31 | 8 |
| LQW2BHN27N□03 | 27 | 77 | 79 | 43 | 28 | 6 |
| LQW2BHN33N□03 | 33 | 76 | 77 | 15 | 1 | - |
| LQW2BHN39N□03 | 39 | 83 | 76 | - | - | - |
| LQW2BHN47N□03 | 47 | 70 | 64 | - | - | - |
| LQW2BHN56N□03 | 56 | 73 | 67 | - | - | - |
| LQW2BHN68N□03 | 68 | 62 | 51 | - | - | - |
| LQW2BHN82N□03 | 82 | 64 | 56 | - | - | - |
| LQW2BHNR10□03 | 100 | 50 | 37 | - | - | - |
| LQW2BHNR12□03 | 120 | 31 | 15 | - | - | - |
| LQW2BHNR15□03 | 150 | 21 | 4 | - | - | - |
| LQW2BHNR18□03 | 180 | 1 | - | - | - | - |
| LQW2BHNR22□03 | 220 | - | - | - | - | - |
| LQW2BHNR27□03 | 270 | - | - | - | - | - |
| LQW2BHNR33□03 | 330 | - | - | - | - | - |
| LQW2BHNR39□03 | 390 | - | - | - | - | - |
| LQW2BHNR47□03 | 470 | - | - | - | - | - |

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


Wire Wound Type (Non-Magnetic Core)

LQW2BHN_13

Series 0805/2015 (inch/mm)

Size Code 0805 (2015) in inch (in mm), High Q Wound, Low DC Resistance Type

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |
| K | ø330mm Embossed Taping | 7500 |




Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|--------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW2BHN2N7D13□ | 2.7nH ±0.5nH | 100MHz | 1900mA | 0.02Ω | 20 | 250MHz | 6000MHz | Kit |
| LQW2BHN3N1D13□ | 3.1nH ±0.5nH | 100MHz | 1800mA | 0.02Ω | 20 | 250MHz | 6000MHz | Kit |
| LQW2BHN3N3D13□ | 3.3nH ±0.5nH | 100MHz | 1700mA | 0.02Ω | 20 | 250MHz | 6000MHz | Kit |
| LQW2BHN5N6D13□ | 5.6nH ±0.5nH | 100MHz | 1500mA | 0.02Ω | 35 | 250MHz | 6000MHz | Kit |
| LQW2BHN6N8D13□ | 6.8nH ±0.5nH | 100MHz | 1400mA | 0.02Ω | 35 | 250MHz | 5400MHz | Kit |
| LQW2BHN8N6D13□ | 8.6nH ±0.5nH | 100MHz | 1300mA | 0.03Ω | 35 | 250MHz | 3900MHz | Kit |
| LQW2BHN10NJ13□ | 10nH ±5% | 100MHz | 1320mA | 0.03Ω | 35 | 250MHz | 3300MHz | Kit |
| LQW2BHN12NK13□ | 12nH ±10% | 100MHz | 1100mA | 0.04Ω | 40 | 250MHz | 3200MHz | Kit |
| LQW2BHN15NK13□ | 15nH ±10% | 100MHz | 1000mA | 0.04Ω | 40 | 250MHz | 3100MHz | Kit |
| LQW2BHN18NK13□ | 18.8nH ±10% | 100MHz | 1000mA | 0.05Ω | 40 | 250MHz | 2600MHz | Kit |
| LQW2BHN21NK13□ | 21nH ±10% | 100MHz | 950mA | 0.05Ω | 40 | 250MHz | 2200MHz | Kit |
| LQW2BHN27NK13□ | 27nH ±10% | 100MHz | 900mA | 0.06Ω | 40 | 250MHz | 1800MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Reference Data

LQW2BHN_13

4991A&16197A


| Part Number | Inductance (nH) | Q (Typ.) | | | | |
|---------------|-----------------|----------|--------|--------|--------|--------|
| | 100MHz | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQW2BHN2N7□13 | 2.7 | 73 | 77 | 113 | 119 | 128 |
| LQW2BHN3N1□13 | 3.1 | 67 | 72 | 111 | 115 | 126 |
| LQW2BHN3N3□13 | 3.3 | 83 | 90 | 120 | 121 | 138 |
| LQW2BHN5N6□13 | 5.6 | 60 | 82 | 127 | 130 | 142 |
| LQW2BHN6N8□13 | 6.8 | 68 | 72 | 110 | 113 | 120 |
| LQW2BHN8N6□13 | 8.6 | 90 | 100 | 140 | 142 | 135 |
| LQW2BHN10N□13 | 10 | 90 | 95 | 124 | 118 | 106 |
| LQW2BHN12N□13 | 12 | 103 | 107 | 115 | 101 | 76 |
| LQW2BHN15N□13 | 15 | 91 | 94 | 91 | 75 | 49 |
| LQW2BHN18N□13 | 18.8 | 105 | 109 | 65 | 44 | 15 |
| LQW2BHN21N□13 | 21 | 98 | 98 | 52 | 31 | - |
| LQW2BHN27N□13 | 27 | 87 | 83 | 10 | - | - |

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQW2BAS_00 Series 0805/2015 (inch/mm)

Size Code 0805 (2015) in inch (in mm), Horizontal Wound Type

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |



Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW2BAS2N8J00□ | 2.8nH ±5% | 250MHz | 800mA | 0.06Ω | 80 | 1500MHz | 12200MHz | Kit |
| LQW2BAS3N0J00□ | 3.0nH ±5% | 250MHz | 800mA | 0.06Ω | 65 | 1500MHz | 12200MHz | Kit |
| LQW2BAS5N6J00□ | 5.6nH ±5% | 250MHz | 600mA | 0.08Ω | 65 | 1000MHz | 5900MHz | Kit |
| LQW2BAS6N8J00□ | 6.8nH ±5% | 250MHz | 600mA | 0.11Ω | 50 | 1000MHz | 5600MHz | Kit |
| LQW2BAS7N5J00□ | 7.5nH ±5% | 250MHz | 600mA | 0.14Ω | 50 | 1000MHz | 4800MHz | Kit |
| LQW2BAS8N2J00□ | 8.2nH ±5% | 250MHz | 600mA | 0.12Ω | 50 | 1000MHz | 4400MHz | Kit |
| LQW2BAS10NJ00□ | 10nH ±5% | 250MHz | 600mA | 0.10Ω | 60 | 500MHz | 4300MHz | Kit |
| LQW2BAS12NJ00□ | 12nH ±5% | 250MHz | 600mA | 0.15Ω | 50 | 500MHz | 4000MHz | Kit |
| LQW2BAS15NJ00□ | 15nH ±5% | 250MHz | 600mA | 0.17Ω | 50 | 500MHz | 3200MHz | Kit |
| LQW2BAS18NJ00□ | 18nH ±5% | 250MHz | 600mA | 0.20Ω | 50 | 500MHz | 3100MHz | Kit |
| LQW2BAS22NJ00□ | 22nH ±5% | 250MHz | 500mA | 0.22Ω | 55 | 500MHz | 2600MHz | Kit |
| LQW2BAS24NJ00□ | 24nH ±5% | 250MHz | 500mA | 0.22Ω | 50 | 500MHz | 2400MHz | Kit |
| LQW2BAS27NJ00□ | 27nH ±5% | 250MHz | 500mA | 0.25Ω | 55 | 500MHz | 2580MHz | Kit |
| LQW2BAS33NG00□ | 33nH ±2% | 250MHz | 500mA | 0.27Ω | 60 | 500MHz | 2150MHz | Kit |
| LQW2BAS33NJ00□ | 33nH ±5% | 250MHz | 500mA | 0.27Ω | 60 | 500MHz | 2150MHz | |
| LQW2BAS36NG00□ | 36nH ±2% | 250MHz | 500mA | 0.27Ω | 55 | 500MHz | 1900MHz | Kit |
| LQW2BAS36NJ00□ | 36nH ±5% | 250MHz | 500mA | 0.27Ω | 55 | 500MHz | 1900MHz | |
| LQW2BAS39NG00□ | 39nH ±2% | 250MHz | 500mA | 0.29Ω | 60 | 500MHz | 2000MHz | Kit |
| LQW2BAS39NJ00□ | 39nH ±5% | 250MHz | 500mA | 0.29Ω | 60 | 500MHz | 2000MHz | |
| LQW2BAS43NG00□ | 43nH ±2% | 200MHz | 500mA | 0.34Ω | 60 | 500MHz | 1800MHz | Kit |
| LQW2BAS43NJ00□ | 43nH ±5% | 200MHz | 500mA | 0.34Ω | 60 | 500MHz | 1800MHz | |
| LQW2BAS47NG00□ | 47nH ±2% | 200MHz | 500mA | 0.31Ω | 60 | 500MHz | 1700MHz | Kit |
| LQW2BAS47NJ00□ | 47nH ±5% | 200MHz | 500mA | 0.31Ω | 60 | 500MHz | 1700MHz | |
| LQW2BAS56NG00□ | 56nH ±2% | 200MHz | 500mA | 0.34Ω | 60 | 500MHz | 1600MHz | Kit |
| LQW2BAS56NJ00□ | 56nH ±5% | 200MHz | 500mA | 0.34Ω | 60 | 500MHz | 1600MHz | |
| LQW2BAS68NG00□ | 68nH ±2% | 200MHz | 500mA | 0.38Ω | 60 | 500MHz | 1500MHz | Kit |
| LQW2BAS68NJ00□ | 68nH ±5% | 200MHz | 500mA | 0.38Ω | 60 | 500MHz | 1500MHz | |
| LQW2BAS82NG00□ | 82nH ±2% | 150MHz | 400mA | 0.42Ω | 65 | 500MHz | 1330MHz | Kit |
| LQW2BAS82NJ00□ | 82nH ±5% | 150MHz | 400mA | 0.42Ω | 65 | 500MHz | 1330MHz | |
| LQW2BAS91NG00□ | 91nH ±2% | 150MHz | 400mA | 0.48Ω | 65 | 500MHz | 1330MHz | Kit |
| LQW2BAS91NJ00□ | 91nH ±5% | 150MHz | 400mA | 0.48Ω | 65 | 500MHz | 1330MHz | |
| LQW2BASR10G00□ | 100nH ±2% | 150MHz | 400mA | 0.46Ω | 65 | 500MHz | 1250MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.


Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW2BASR10J00□ | 100nH ±5% | 150MHz | 400mA | 0.46Ω | 65 | 500MHz | 1250MHz | |
| LQW2BASR11G00□ | 110nH ±2% | 150MHz | 400mA | 0.48Ω | 50 | 250MHz | 1100MHz | Kit |
| LQW2BASR11J00□ | 110nH ±5% | 150MHz | 400mA | 0.48Ω | 50 | 250MHz | 1100MHz | |
| LQW2BASR12G00□ | 120nH ±2% | 150MHz | 400mA | 0.51Ω | 50 | 250MHz | 1100MHz | Kit |
| LQW2BASR12J00□ | 120nH ±5% | 150MHz | 400mA | 0.51Ω | 50 | 250MHz | 1100MHz | |
| LQW2BASR15G00□ | 150nH ±2% | 100MHz | 400mA | 0.56Ω | 50 | 250MHz | 920MHz | Kit |
| LQW2BASR15J00□ | 150nH ±5% | 100MHz | 400mA | 0.56Ω | 50 | 250MHz | 920MHz | |
| LQW2BASR18G00□ | 180nH ±2% | 100MHz | 400mA | 0.64Ω | 50 | 250MHz | 920MHz | Kit |
| LQW2BASR18J00□ | 180nH ±5% | 100MHz | 400mA | 0.64Ω | 50 | 250MHz | 920MHz | |
| LQW2BASR22G00□ | 220nH ±2% | 100MHz | 400mA | 0.70Ω | 50 | 250MHz | 820MHz | Kit |
| LQW2BASR22J00□ | 220nH ±5% | 100MHz | 400mA | 0.70Ω | 50 | 250MHz | 820MHz | |
| LQW2BASR24G00□ | 240nH ±2% | 100MHz | 350mA | 1.00Ω | 44 | 250MHz | 770MHz | Kit |
| LQW2BASR24J00□ | 240nH ±5% | 100MHz | 350mA | 1.00Ω | 44 | 250MHz | 770MHz | |
| LQW2BASR27G00□ | 270nH ±2% | 100MHz | 350mA | 1.00Ω | 48 | 250MHz | 730MHz | Kit |
| LQW2BASR27J00□ | 270nH ±5% | 100MHz | 350mA | 1.00Ω | 48 | 250MHz | 730MHz | |
| LQW2BASR33G00□ | 330nH ±2% | 100MHz | 310mA | 1.40Ω | 48 | 250MHz | 650MHz | Kit |
| LQW2BASR33J00□ | 330nH ±5% | 100MHz | 310mA | 1.40Ω | 48 | 250MHz | 650MHz | |
| LQW2BASR39J00□ | 390nH ±5% | 100MHz | 290mA | 1.50Ω | 48 | 250MHz | 600MHz | Kit |
| LQW2BASR47J00□ | 470nH ±5% | 50MHz | 250mA | 1.76Ω | 33 | 100MHz | 300MHz | Kit |
| LQW2BASR56J00□ | 560nH ±5% | 25MHz | 230mA | 1.90Ω | 23 | 50MHz | 270MHz | Kit |
| LQW2BASR68J00□ | 680nH ±5% | 25MHz | 190mA | 2.20Ω | 23 | 50MHz | 250MHz | Kit |
| LQW2BASR82J00□ | 820nH ±5% | 25MHz | 180mA | 2.35Ω | 23 | 50MHz | 230MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Reference Data

LQW2BAS_00

4991A&16197A


| Part Number | Inductance (nH) | | | Q (Typ.) | | |
|---------------|-----------------|--------|--------|----------|--------|--------|
| | 100MHz | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQW2BAS2N8□00 | 2.8 | 100 | 95 | 170 | 175 | 190 |
| LQW2BAS3N0□00 | 3 | 63 | 67 | 100 | 104 | 110 |
| LQW2BAS5N6□00 | 5.6 | 96 | 100 | 150 | 153 | 160 |
| LQW2BAS6N8□00 | 6.8 | 77 | 70 | 97 | 100 | 106 |
| LQW2BAS7N5□00 | 7.5 | 66 | 70 | 91 | 90 | 94 |
| LQW2BAS8N2□00 | 8.2 | 64 | 70 | 94 | 94 | 96 |
| LQW2BAS10N□00 | 10 | 96 | 100 | 138 | 140 | 138 |
| LQW2BAS12N□00 | 12 | 73 | 77 | 120 | 103 | 101 |
| LQW2BAS15N□00 | 15 | 78 | 80 | 92 | 80 | 76 |
| LQW2BAS18N□00 | 18 | 84 | 89 | 104 | 100 | 86 |
| LQW2BAS22N□00 | 22 | 91 | 90 | 89 | 80 | 56 |
| LQW2BAS24N□00 | 24 | 87 | 87 | 63 | 51 | 36 |
| LQW2BAS27N□00 | 27 | 90 | 92 | 93 | 89 | 65 |
| LQW2BAS33N□00 | 33 | 92 | 93 | 60 | 45 | 13 |
| LQW2BAS36N□00 | 36 | 92 | 93 | 43 | 26 | 2 |
| LQW2BAS39N□00 | 39 | 96 | 95 | 61 | 41 | 15 |
| LQW2BAS43N□00 | 43 | 95 | 96 | 37 | 17 | - |
| LQW2BAS47N□00 | 47 | 91 | 88 | 24 | 5 | - |
| LQW2BAS56N□00 | 56 | 92 | 90 | 17 | - | - |
| LQW2BAS68N□00 | 68 | 91 | 87 | 4 | - | - |
| LQW2BAS82N□00 | 82 | 85 | 75 | - | - | - |
| LQW2BAS91N□00 | 91 | 83 | 74 | - | - | - |
| LQW2BASR10□00 | 100 | 78 | 64 | - | - | - |
| LQW2BASR11□00 | 110 | 68 | 50 | - | - | - |
| LQW2BASR12□00 | 120 | 48 | 28 | - | - | - |
| LQW2BASR15□00 | 150 | 48 | 32 | - | - | - |
| LQW2BASR18□00 | 180 | 34 | 20 | - | - | - |
| LQW2BASR22□00 | 220 | 29 | 11 | - | - | - |
| LQW2BASR24□00 | 240 | 22 | 5 | - | - | - |
| LQW2BASR27□00 | 270 | 11 | - | - | - | - |
| LQW2BASR33□00 | 330 | 4 | - | - | - | - |
| LQW2BASR39□00 | 390 | - | - | - | - | - |
| LQW2BASR47□00 | 470 | - | - | - | - | - |
| LQW2BASR56□00 | 560 | - | - | - | - | - |
| LQW2BASR68□00 | 680 | - | - | - | - | - |
| LQW2BASR82□00 | 820 | - | - | - | - | - |

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQW2UAS_00 Series 1008/2520 (inch/mm)

Size Code 1008 (2520) in inch (in mm), Wound Type

Appearance/Dimensions



Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |



Refer to pages 227 to 230 for mounting information.

Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW2UAS12NG00□ | 12nH ±2% | 50MHz | 1000mA | 0.09Ω | 50 | 500MHz | 3300MHz | Kit |
| LQW2UAS12NJ00□ | 12nH ±5% | 50MHz | 1000mA | 0.09Ω | 50 | 500MHz | 3300MHz | |
| LQW2UAS18NG00□ | 18nH ±2% | 50MHz | 1000mA | 0.11Ω | 50 | 350MHz | 2500MHz | Kit |
| LQW2UAS18NJ00□ | 18nH ±5% | 50MHz | 1000mA | 0.11Ω | 50 | 350MHz | 2500MHz | |
| LQW2UAS22NG00□ | 22nH ±2% | 50MHz | 1000mA | 0.12Ω | 55 | 350MHz | 2400MHz | Kit |
| LQW2UAS22NJ00□ | 22nH ±5% | 50MHz | 1000mA | 0.12Ω | 55 | 350MHz | 2400MHz | |
| LQW2UAS27NG00□ | 27nH ±2% | 50MHz | 1000mA | 0.13Ω | 55 | 350MHz | 1600MHz | Kit |
| LQW2UAS27NJ00□ | 27nH ±5% | 50MHz | 1000mA | 0.13Ω | 55 | 350MHz | 1600MHz | |
| LQW2UAS33NG00□ | 33nH ±2% | 50MHz | 1000mA | 0.14Ω | 60 | 350MHz | 1600MHz | Kit |
| LQW2UAS33NJ00□ | 33nH ±5% | 50MHz | 1000mA | 0.14Ω | 60 | 350MHz | 1600MHz | |
| LQW2UAS39NG00□ | 39nH ±2% | 50MHz | 1000mA | 0.15Ω | 60 | 350MHz | 1500MHz | Kit |
| LQW2UAS39NJ00□ | 39nH ±5% | 50MHz | 1000mA | 0.15Ω | 60 | 350MHz | 1500MHz | |
| LQW2UAS47NG00□ | 47nH ±2% | 50MHz | 1000mA | 0.16Ω | 65 | 350MHz | 1500MHz | Kit |
| LQW2UAS47NJ00□ | 47nH ±5% | 50MHz | 1000mA | 0.16Ω | 65 | 350MHz | 1500MHz | |
| LQW2UAS56NG00□ | 56nH ±2% | 50MHz | 1000mA | 0.18Ω | 65 | 350MHz | 1300MHz | Kit |
| LQW2UAS56NJ00□ | 56nH ±5% | 50MHz | 1000mA | 0.18Ω | 65 | 350MHz | 1300MHz | |
| LQW2UAS68NG00□ | 68nH ±2% | 50MHz | 1000mA | 0.2Ω | 65 | 350MHz | 1300MHz | Kit |
| LQW2UAS68NJ00□ | 68nH ±5% | 50MHz | 1000mA | 0.2Ω | 65 | 350MHz | 1300MHz | |
| LQW2UAS82NG00□ | 82nH ±2% | 50MHz | 1000mA | 0.22Ω | 60 | 350MHz | 1000MHz | Kit |
| LQW2UAS82NJ00□ | 82nH ±5% | 50MHz | 1000mA | 0.22Ω | 60 | 350MHz | 1000MHz | |
| LQW2UASR10G00□ | 100nH ±2% | 25MHz | 650mA | 0.56Ω | 60 | 350MHz | 1000MHz | Kit |
| LQW2UASR10J00□ | 100nH ±5% | 25MHz | 650mA | 0.56Ω | 60 | 350MHz | 1000MHz | |
| LQW2UASR12G00□ | 120nH ±2% | 25MHz | 650mA | 0.63Ω | 60 | 350MHz | 950MHz | Kit |
| LQW2UASR12J00□ | 120nH ±5% | 25MHz | 650mA | 0.63Ω | 60 | 350MHz | 950MHz | |
| LQW2UASR15G00□ | 150nH ±2% | 25MHz | 580mA | 0.7Ω | 45 | 100MHz | 850MHz | Kit |
| LQW2UASR15J00□ | 150nH ±5% | 25MHz | 580mA | 0.7Ω | 45 | 100MHz | 850MHz | |
| LQW2UASR18G00□ | 180nH ±2% | 25MHz | 620mA | 0.77Ω | 45 | 100MHz | 750MHz | Kit |
| LQW2UASR18J00□ | 180nH ±5% | 25MHz | 620mA | 0.77Ω | 45 | 100MHz | 750MHz | |
| LQW2UASR22G00□ | 220nH ±2% | 25MHz | 500mA | 0.84Ω | 45 | 100MHz | 700MHz | Kit |
| LQW2UASR22J00□ | 220nH ±5% | 25MHz | 500mA | 0.84Ω | 45 | 100MHz | 700MHz | |
| LQW2UASR27G00□ | 270nH ±2% | 25MHz | 500mA | 0.91Ω | 45 | 100MHz | 600MHz | Kit |
| LQW2UASR27J00□ | 270nH ±5% | 25MHz | 500mA | 0.91Ω | 45 | 100MHz | 600MHz | |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.


Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW2UASR33G00□ | 330nH ±2% | 25MHz | 450mA | 1.05Ω | 45 | 100MHz | 570MHz | Kit |
| LQW2UASR33J00□ | 330nH ±5% | 25MHz | 450mA | 1.05Ω | 45 | 100MHz | 570MHz | |
| LQW2UASR39G00□ | 390nH ±2% | 25MHz | 470mA | 1.12Ω | 45 | 100MHz | 500MHz | Kit |
| LQW2UASR39J00□ | 390nH ±5% | 25MHz | 470mA | 1.12Ω | 45 | 100MHz | 500MHz | |
| LQW2UASR47G00□ | 470nH ±2% | 25MHz | 470mA | 1.19Ω | 45 | 100MHz | 450MHz | Kit |
| LQW2UASR47J00□ | 470nH ±5% | 25MHz | 470mA | 1.19Ω | 45 | 100MHz | 450MHz | |
| LQW2UASR56G00□ | 560nH ±2% | 25MHz | 400mA | 1.33Ω | 45 | 100MHz | 415MHz | Kit |
| LQW2UASR56J00□ | 560nH ±5% | 25MHz | 400mA | 1.33Ω | 45 | 100MHz | 415MHz | |
| LQW2UASR62G00□ | 620nH ±2% | 25MHz | 300mA | 1.4Ω | 45 | 100MHz | 375MHz | Kit |
| LQW2UASR62J00□ | 620nH ±5% | 25MHz | 300mA | 1.4Ω | 45 | 100MHz | 375MHz | |
| LQW2UASR68G00□ | 680nH ±2% | 25MHz | 400mA | 1.47Ω | 45 | 100MHz | 375MHz | Kit |
| LQW2UASR68J00□ | 680nH ±5% | 25MHz | 400mA | 1.47Ω | 45 | 100MHz | 375MHz | |
| LQW2UASR75G00□ | 750nH ±2% | 25MHz | 360mA | 1.54Ω | 45 | 100MHz | 360MHz | Kit |
| LQW2UASR75J00□ | 750nH ±5% | 25MHz | 360mA | 1.54Ω | 45 | 100MHz | 360MHz | |
| LQW2UASR82G00□ | 820nH ±2% | 25MHz | 400mA | 1.61Ω | 45 | 100MHz | 350MHz | Kit |
| LQW2UASR82J00□ | 820nH ±5% | 25MHz | 400mA | 1.61Ω | 45 | 100MHz | 350MHz | |
| LQW2UASR91G00□ | 910nH ±2% | 25MHz | 380mA | 1.68Ω | 35 | 50MHz | 320MHz | Kit |
| LQW2UASR91J00□ | 910nH ±5% | 25MHz | 380mA | 1.68Ω | 35 | 50MHz | 320MHz | |
| LQW2UAS1R0G00□ | 1000nH ±2% | 25MHz | 370mA | 1.75Ω | 35 | 50MHz | 290MHz | Kit |
| LQW2UAS1R0J00□ | 1000nH ±5% | 25MHz | 370mA | 1.75Ω | 35 | 50MHz | 290MHz | |
| LQW2UAS1R2J00□ | 1200nH ±5% | 7.9MHz | 310mA | 2.0Ω | 35 | 50MHz | 210MHz | Kit |
| LQW2UAS1R5J00□ | 1500nH ±5% | 7.9MHz | 330mA | 2.3Ω | 28 | 50MHz | 120MHz | Kit |
| LQW2UAS1R8J00□ | 1800nH ±5% | 7.9MHz | 300mA | 2.6Ω | 28 | 50MHz | 140MHz | Kit |
| LQW2UAS2R2J00□ | 2200nH ±5% | 7.9MHz | 280mA | 2.8Ω | 28 | 50MHz | 130MHz | Kit |
| LQW2UAS2R7J00□ | 2700nH ±5% | 7.9MHz | 290mA | 3.2Ω | 22 | 25MHz | 110MHz | Kit |
| LQW2UAS3R3J00□ | 3300nH ±5% | 7.9MHz | 290mA | 3.4Ω | 22 | 25MHz | 90MHz | Kit |
| LQW2UAS3R9J00□ | 3900nH ±5% | 7.9MHz | 260mA | 3.6Ω | 20 | 25MHz | 70MHz | Kit |
| LQW2UAS4R7J00□ | 4700nH ±5% | 7.9MHz | 260mA | 4.0Ω | 20 | 25MHz | 60MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -55°C~+125°C
For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Reference Data

LQW2UAS_00

4991A&16197A


| Part Number | Inductance (nH) | | Q (Typ.) | | | |
|---------------|-----------------|--------|----------|--------|--------|--------|
| | 100MHz | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQW2UAS12N□00 | 12 | 108 | 114 | 125 | 120 | 110 |
| LQW2UAS18N□00 | 18 | 123 | 130 | 123 | 118 | 90 |
| LQW2UAS22N□00 | 22 | 120 | 122 | 94 | 73 | 43 |
| LQW2UAS27N□00 | 27 | 103 | 103 | 34 | 14 | - |
| LQW2UAS33N□00 | 33 | 122 | 125 | 67 | 41 | - |
| LQW2UAS39N□00 | 39 | 115 | 110 | 9 | - | - |
| LQW2UAS47N□00 | 47 | 120 | 125 | 19 | - | - |
| LQW2UAS56N□00 | 56 | 111 | 98 | - | - | - |
| LQW2UAS68N□00 | 68 | 110 | 100 | - | - | - |
| LQW2UAS82N□00 | 82 | 75 | 60 | - | - | - |
| LQW2UASR10□00 | 100 | 70 | 57 | - | - | - |
| LQW2UASR12□00 | 120 | 67 | 50 | - | - | - |
| LQW2UASR15□00 | 150 | 47 | 25 | - | - | - |
| LQW2UASR18□00 | 180 | 27 | 5 | - | - | - |
| LQW2UASR22□00 | 220 | 7 | - | - | - | - |
| LQW2UASR27□00 | 270 | - | - | - | - | - |
| LQW2UASR33□00 | 330 | - | - | - | - | - |
| LQW2UASR39□00 | 390 | - | - | - | - | - |
| LQW2UASR47□00 | 470 | - | - | - | - | - |
| LQW2UASR56□00 | 560 | - | - | - | - | - |
| LQW2UASR62□00 | 620 | - | - | - | - | - |
| LQW2UASR68□00 | 680 | - | - | - | - | - |
| LQW2UASR75□00 | 750 | - | - | - | - | - |
| LQW2UASR82□00 | 820 | - | - | - | - | - |
| LQW2UASR91□00 | 910 | - | - | - | - | - |
| LQW2UAS1R0□00 | 1000 | - | - | - | - | - |
| LQW2UAS1R2□00 | 1200 | - | - | - | - | - |
| LQW2UAS1R5□00 | 1500 | - | - | - | - | - |
| LQW2UAS1R8□00 | 1800 | - | - | - | - | - |
| LQW2UAS2R2□00 | 2200 | - | - | - | - | - |
| LQW2UAS2R7□00 | 2700 | - | - | - | - | - |
| LQW2UAS3R3□00 | 3300 | - | - | - | - | - |
| LQW2UAS3R9□00 | 3900 | - | - | - | - | - |
| LQW2UAS4R7□00 | 4700 | - | - | - | - | - |

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQW31HN_03 Series 1206/3216 (inch/mm)

Size Code 1206 (3216) in inch (in mm), Wound Type

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |
| K | ø330mm Embossed Taping | 7500 |



Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) |
|----------------|-------------|---------------------------|---------------|---------------|----------|------------------|---------------------------------|
| LQW31HN8N8J03□ | 8.8nH ±5% | 100MHz | 750mA | 0.029Ω ±40% | 50 | 436MHz | 1000MHz |
| LQW31HN8N8K03□ | 8.8nH ±10% | 100MHz | 750mA | 0.029Ω ±40% | 50 | 436MHz | 1000MHz |
| LQW31HN15NJ03□ | 14.7nH ±5% | 100MHz | 680mA | 0.035Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN15NK03□ | 14.7nH ±10% | 100MHz | 680mA | 0.035Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN17NJ03□ | 17nH ±5% | 100MHz | 650mA | 0.037Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN17NK03□ | 17nH ±10% | 100MHz | 650mA | 0.037Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN23NJ03□ | 23nH ±5% | 100MHz | 590mA | 0.046Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN23NK03□ | 23nH ±10% | 100MHz | 590mA | 0.046Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN27NJ03□ | 27nH ±5% | 100MHz | 560mA | 0.051Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN27NK03□ | 27nH ±10% | 100MHz | 560mA | 0.051Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN33NJ03□ | 33nH ±5% | 100MHz | 530mA | 0.057Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN33NK03□ | 33nH ±10% | 100MHz | 530mA | 0.057Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN39NJ03□ | 39nH ±5% | 100MHz | 490mA | 0.067Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN39NK03□ | 39nH ±10% | 100MHz | 490mA | 0.067Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN47NJ03□ | 47nH ±5% | 100MHz | 380mA | 0.11Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN47NK03□ | 47nH ±10% | 100MHz | 380mA | 0.11Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN56NJ03□ | 56nH ±5% | 100MHz | 330mA | 0.14Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN56NK03□ | 56nH ±10% | 100MHz | 330mA | 0.14Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN64NJ03□ | 64nH ±5% | 100MHz | 290mA | 0.18Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN64NK03□ | 64nH ±10% | 100MHz | 290mA | 0.18Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN84NJ03□ | 84nH ±5% | 100MHz | 240mA | 0.28Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HN84NK03□ | 84nH ±10% | 100MHz | 240mA | 0.28Ω ±40% | 60 | 436MHz | 1000MHz |
| LQW31HNR10J03□ | 100nH ±5% | 100MHz | 230mA | 0.3Ω ±40% | 60 | 436MHz | 900MHz |
| LQW31HNR10K03□ | 100nH ±10% | 100MHz | 230mA | 0.3Ω ±40% | 60 | 436MHz | 900MHz |

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C


Continued on the following page. ↗

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



■ Reference Data

LQW31HN_03

4991A&16197A


| Part Number | Inductance (nH) | | | Q (Typ.) | | |
|---------------|-----------------|--------|--------|----------|--------|--------|
| | 100MHz | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQW31HN8N8□03 | 8.8 | 101 | 107 | 146 | 146 | 157 |
| LQW31HN15N□03 | 14.7 | 105 | 108 | 92 | 75 | 50 |
| LQW31HN17N□03 | 17 | 106 | 108 | 66 | 47 | 22 |
| LQW31HN23N□03 | 23 | 109 | 109 | 53 | 32 | - |
| LQW31HN27N□03 | 27 | 106 | 109 | 37 | 14 | - |
| LQW31HN33N□03 | 33 | 98 | 96 | 5 | - | - |
| LQW31HN39N□03 | 39 | 90 | 88 | - | - | - |
| LQW31HN47N□03 | 47 | 80 | 72 | - | - | - |
| LQW31HN56N□03 | 56 | 77 | 67 | - | - | - |
| LQW31HN64N□03 | 64 | 73 | 61 | - | - | - |
| LQW31HN84N□03 | 84 | 59 | 47 | - | - | - |
| LQW31HNR10□03 | 100 | 40 | 25 | - | - | - |

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQW21HN_00 Series 0805/2012 (inch/mm)

Size Code 0805 (2012) in inch (in mm), Ferrite Core High Frequency Wound Type

■ Appearance/ Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 3000 |
| B | Packing in Bulk | 500 |




Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)


| Part Number | Inductance | Inductance Test Frequency | Rated Current | Max. of DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) | |
|----------------|------------|---------------------------|---------------|-----------------------|----------|------------------|---------------------------------|-----|
| LQW21HNR47J00□ | 0.47μH ±5% | 10MHz | 160mA | 1.30Ω | 35 | 100MHz | 620MHz | Kit |
| LQW21HNR56J00□ | 0.56μH ±5% | 10MHz | 150mA | 1.43Ω | 35 | 100MHz | 580MHz | Kit |
| LQW21HNR68J00□ | 0.68μH ±5% | 10MHz | 130mA | 2.21Ω | 35 | 100MHz | 520MHz | Kit |
| LQW21HNR82J00□ | 0.82μH ±5% | 10MHz | 125mA | 2.34Ω | 35 | 100MHz | 480MHz | Kit |
| LQW21HN1R0J00□ | 1.0μH ±5% | 10MHz | 115mA | 2.86Ω | 35 | 100MHz | 450MHz | Kit |
| LQW21HN1R2J00□ | 1.2μH ±5% | 10MHz | 100mA | 3.12Ω | 35 | 100MHz | 400MHz | Kit |
| LQW21HN1R5J00□ | 1.5μH ±5% | 10MHz | 85mA | 5.33Ω | 35 | 100MHz | 350MHz | Kit |
| LQW21HN1R8J00□ | 1.8μH ±5% | 10MHz | 80mA | 5.85Ω | 35 | 100MHz | 320MHz | Kit |
| LQW21HN2R2J00□ | 2.2μH ±5% | 10MHz | 75mA | 6.50Ω | 35 | 100MHz | 300MHz | Kit |

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C
For reflow soldering only.

■ Q-Frequency Characteristics (Typ.)



■ Inductance-Frequency Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Reference Data

LQW21HN_00

4991A&16197A


| Part Number | Inductance (μ H) | Q (Typ.) | | | | |
|---------------|-----------------------|----------|-------|-------|-------|--------|
| | | 30MHz | 70MHz | 80MHz | 90MHz | 100MHz |
| LQW21HNR47□00 | 0.47 | 40 | 54 | 55 | 56 | 55 |
| LQW21HNR56□00 | 0.56 | 46 | 63 | 64 | 64 | 60 |
| LQW21HNR68□00 | 0.68 | 41 | 56 | 56 | 57 | 54 |
| LQW21HNR82□00 | 0.82 | 41 | 57 | 58 | 59 | 57 |
| LQW21HN1R0□00 | 1.0 | 44 | 54 | 54 | 54 | 50 |
| LQW21HN1R2□00 | 1.2 | 44 | 57 | 58 | 58 | 52 |
| LQW21HN1R5□00 | 1.5 | 39 | 56 | 56 | 56 | 53 |
| LQW21HN1R8□00 | 1.8 | 41 | 56 | 55 | 54 | 50 |
| LQW21HN2R2□00 | 2.2 | 43 | 57 | 55 | 55 | 50 |

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

LQH31HN_03 Series 1206/3216 (inch/mm)

Size Code 1206 (3216) in inch (in mm), Ferrite Core High Frequency Wound Type

■ Appearance/Dimensions



■ Packaging

| Code | Packaging | Minimum Quantity |
|------|------------------------|------------------|
| L | ø180mm Embossed Taping | 2000 |
| K | ø330mm Embossed Taping | 7500 |




Refer to pages 227 to 230 for mounting information.

■ Rated Value (□: packaging code)

| Part Number | Inductance | Inductance Test Frequency | Rated Current | DC Resistance | Q (min.) | Q Test Frequency | Self-Resonance Frequency (min.) |
|----------------|------------|---------------------------|---------------|---------------|----------|------------------|---------------------------------|
| LQH31HN54NK03□ | 54nH ±10% | 1MHz | 920mA | 0.035Ω ±30% | 50 | 100MHz | 800MHz |
| LQH31HN95NK03□ | 95nH ±10% | 1MHz | 790mA | 0.047Ω ±30% | 60 | 100MHz | 650MHz |
| LQH31HNR14J03□ | 145nH ±5% | 1MHz | 700mA | 0.061Ω ±30% | 60 | 100MHz | 500MHz |
| LQH31HNR14K03□ | 145nH ±10% | 1MHz | 700mA | 0.061Ω ±30% | 60 | 100MHz | 500MHz |
| LQH31HNR21J03□ | 215nH ±5% | 1MHz | 520mA | 0.11Ω ±30% | 60 | 100MHz | 430MHz |
| LQH31HNR21K03□ | 215nH ±10% | 1MHz | 520mA | 0.11Ω ±30% | 60 | 100MHz | 430MHz |
| LQH31HNR29J03□ | 290nH ±5% | 1MHz | 420mA | 0.17Ω ±30% | 60 | 100MHz | 360MHz |
| LQH31HNR29K03□ | 290nH ±10% | 1MHz | 420mA | 0.17Ω ±30% | 60 | 100MHz | 360MHz |
| LQH31HNR39J03□ | 390nH ±5% | 1MHz | 330mA | 0.26Ω ±30% | 60 | 100MHz | 300MHz |
| LQH31HNR39K03□ | 390nH ±10% | 1MHz | 330mA | 0.26Ω ±30% | 60 | 100MHz | 300MHz |
| LQH31HNR50J03□ | 500nH ±5% | 1MHz | 260mA | 0.44Ω ±30% | 60 | 100MHz | 270MHz |
| LQH31HNR50K03□ | 500nH ±10% | 1MHz | 260mA | 0.44Ω ±30% | 60 | 100MHz | 270MHz |
| LQH31HNR61J03□ | 610nH ±5% | 1MHz | 250mA | 0.48Ω ±30% | 60 | 100MHz | 240MHz |
| LQH31HNR61K03□ | 610nH ±10% | 1MHz | 250mA | 0.48Ω ±30% | 60 | 100MHz | 240MHz |
| LQH31HNR75J03□ | 750nH ±5% | 1MHz | 190mA | 0.79Ω ±30% | 60 | 100MHz | 220MHz |
| LQH31HNR75K03□ | 750nH ±10% | 1MHz | 190mA | 0.79Ω ±30% | 60 | 100MHz | 220MHz |
| LQH31HNR88J03□ | 880nH ±5% | 1MHz | 180mA | 0.86Ω ±30% | 60 | 100MHz | 200MHz |
| LQH31HNR88K03□ | 880nH ±10% | 1MHz | 180mA | 0.86Ω ±30% | 60 | 100MHz | 200MHz |

Operating Temperature Range (Self-temperature rise is not included): -40°C~+85°C

■ Q-Frequency Characteristics (Typ.)



Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Reference Data

LQH31HN_03

4991A&16197A

| Part Number | Inductance (nH) | Q (Typ.) | | | | |
|---------------|-----------------|----------|--------|--------|--------|--------|
| | 100MHz | 800MHz | 900MHz | 1.8GHz | 2.0GHz | 2.4GHz |
| LQH31HN54N□03 | 54 | 2 | 1 | - | - | - |
| LQH31HN95N□03 | 95 | 1 | - | - | - | - |
| LQH31HNR14□03 | 145 | - | - | - | - | - |
| LQH31HNR21□03 | 215 | - | - | - | - | - |
| LQH31HNR29□03 | 290 | - | - | - | - | - |
| LQH31HNR39□03 | 390 | - | - | - | - | - |
| LQH31HNR50□03 | 500 | - | - | - | - | - |
| LQH31HNR61□03 | 610 | - | - | - | - | - |
| LQH31HNR75□03 | 750 | - | - | - | - | - |
| LQH31HNR88□03 | 880 | - | - | - | - | - |

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

⚠ Caution

● Rating

1. About the Rated Current

Do not use products beyond the rated current as this may create excessive heat and deteriorate the insulation resistance.

2. About Excessive Surge Current

Surge current (pulse current or rush current) greater than the specified rated current applied to the product may cause a critical failure, such as an open circuit, burnout caused by excessive temperature rise. Please contact us in advance in case of applying the surge current.

Notice

● Storage and Operating Condition

<Operating Environment>

Do not use products in chemical atmosphere such as chlorine gas, acid or sulfide gas.

<Storage Requirements>

1. Storage Period

LQG series should be used within 6 months; the other products should be used within 12 months. Check solderability if this period is exceeded.

2. Storage Conditions

(1) Store products in a warehouse in compliance with the following conditions:

Temperature: -10 to +40 degrees C.

Humidity: 15 to 85% (relative humidity)

Do not subject products to rapid changes in temperature and humidity.

Do not store them in chemical atmosphere such as one containing sulfurous acid gas or alkaline gas.

This will prevent electrode oxidation, which causes poor solderability and possible corrosion of inductors.

(2) Do not store products in bulk packaging to prevent collision among inductors, which causes core chipping and wire breakage.

(3) Store products on pallets to protect from humidity, dust, etc.

(4) Avoid heat shock, vibration, direct sunlight, etc.

● Handling

This item is designed to have sufficient strength, but handle with care to avoid chipping or breaking its ceramic structure.

LQW_A/LQW_H series

- To prevent breaking the wire, avoid touching with sharp material, such as tweezers or the bristles of a cleaning brush, to the wire wound portion.

- To prevent breaking the core, avoid applying excessive mechanical shock to products mounted on the board.

- In some mounting machines, when picking up components, a support pin pushes the components up from the bottom of the base tape. In this case, please remove the support pin. The support pin may damage the components and break the wire.

- In rare cases, the laser recognition cannot recognize this component. Please contact us when you use laser recognition. (There is no problem with the permeation and reflection type.)

LQH_H series

- To prevent breaking the wire, avoid touching with sharp material, such as tweezers or the bristles of a cleaning brush, to the wire wound portion of this product.

- To prevent breaking the core, avoid applying excessive mechanical shock to products mounted on the board.

LQG,LQP series (except LQP02T_02/LQP03T_02)

- The pattern of the chip Inductors is covered with protective film. Take care to avoid damaging the chip Inductors when handling it with pick-up nozzles, sharp instruments, etc.

<Handling>


1. Avoid applying excessive stress to products to prevent damage.



2. Do not touch wire wound with sharp objects such as tweezers to prevent wire breakage.

3. Do not apply excessive force to products mounted on boards to prevent core breakage.

<Transportation>

Do not apply excessive vibration or mechanical shock to products.

Continued on the following page. 

 Note • Please read rating and  CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

<Resin Coating>

When coating products with resin, the relatively high resin curing stress may change inductance values. For exterior coating, select resin carefully so that electrical and mechanical performance of the product is not affected. Prior to use, please evaluate reliability with the product mounted in your application set.

(LQW,LQH series)

An open circuit issue may occur by mechanical stress caused by the resin, amount/cured shape of resin, or operating conditions, etc. Some resins containing impurities or chloride may possibly generate chlorine by hydrolysis under some operating conditions, causing corrosion of the inductor wire and leading to an open circuit.

(LQP02T_02,LQP03T_02)


When products are coated with resin, please contact us in advance.

<Handling of a Substrate>


After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting the substrate when cropping the substrate, inserting and removing a connector from the substrate, or tightening a screw to the substrate.

Excessive mechanical stress may cause cracking in the Product.

Bending




Twisting



● Measuring Method

Measuring Method of Inductance/Q

1. Residual elements and stray elements of test fixtures can be described by F-parameter as shown in the following:



2. The impedance of chip Inductors (chip coils) Z_x and measured value Z_m can be described by input/output current/voltage.

$$Z_m = \frac{V_1}{I_1}, \quad Z_x = \frac{V_2}{I_2}$$

3. Thus, the relation between Z_x and Z_m is shown in the following:

$$Z_x = \alpha \frac{Z_m - \beta}{1 - Z_m \Gamma} \quad \text{where, } \alpha = D / A = 1$$

$$\beta = B / D = Z_{sm} - (1 - Y_{om} Z_{sm}) Z_{ss}$$

$$\Gamma = C / A = Y_{om}$$

Z_{sm} : measured impedance of short chip
 Z_{ss} : residual impedance of short chip*
 Y_{om} : measured admittance when opening the fixture)

*Residual impedance of short chip

| Residual Impedance | Series |
|--------------------|--------------------------------|
| 0nH | LQG15HS/LQP03TG |
| 0.110nH | LQP02TN/LQP02TQ |
| 0.480nH | LQP03TN_02 |
| 0.556nH | LQG15HN, LQW15A, LQP15M |
| 0.771nH | LQG18H, LQP18M, LQW18A, LQW21H |

4. L_x and Q_x should be calculated with the following equation.

$$L_x = \frac{\text{Im}(Z_x)}{2\pi f}, \quad Q_x = \frac{\text{Im}(Z_x)}{\text{Re}(Z_x)}$$

L_x : Inductance of chip Inductors (chip coils)


Q_x : Q of chip Inductors (chip coils)

f: Measuring frequency

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

1. Standard Land Pattern Dimensions

A high Q value is achieved when the PCB electrode land pattern is designed so that it does not project beyond the chip Inductors (chip coils) electrode.



| Series | Standard Land Dimensions | | | | |
|--|--------------------------|--------------|----------|----------|----------|
| LQG15H LQG18H LQP02TN LQP02TQ LQP03T LQP15M LQP18M LQW03A LQW04A LQW15A LQW18A LQW21H LQW2BH LQW2BA LQW2UA LQW31H LQH31H | | Part Number | a | b | c |
| | | LQG15H | 0.4 | 1.4-1.5 | 0.5-0.6 |
| | | LQG18H | 0.6-0.8 | 1.8-2.2 | 0.6-0.8 |
| | | LQP02TN | 0.16-0.2 | 0.4-0.56 | 0.2-0.23 |
| | | LQP02TQ | 0.2 | 0.56 | 0.2 |
| | | LQP03T | 0.2-0.3 | 0.8-0.9 | 0.2-0.3 |
| | | LQP15M | 0.4 | 1.4-1.5 | 0.5-0.6 |
| | | LQP18M | 0.7-0.9 | 1.8-2.2 | 0.6-0.8 |
| | | LQW03A | 0.23 | 0.65 | 0.4 |
| | | LQW04A | 0.4 | 1.0 | 0.4 |
| | | LQW15A_00/10 | 0.5 | 1.2 | 0.65 |
| | | LQW15A_80 | 0.6 | 1.42 | 0.66 |
| | | LQW18A_00/10 | 0.6-0.8 | 1.9-2.0 | 0.7-1.0 |
| | | LQW18A_80 | 0.86 | 2.0 | 1.15 |
| | | LQW21H | 1.0 | 2.6 | 1.2 |
| | | LQW2BH | 0.8 | 3.0 | 1.2 |
| | | LQW2BA | 0.76 | 2.8 | 1.78 |
| LQW2UA | 1.27 | 3.3 | 2.54 | | |
| LQH31H | 1.0 | 4.5 | 1.5 | | |
| LQW31H | | | | | |

Attention should be paid to potential magnetic coupling effects when using the Inductors (coils) as a resonator.

2. Standard Soldering Conditions

(1) Soldering method

Chip Inductors (Chip coils) can be flow or reflow soldered. Please contact Murata regarding other soldering methods.

As for LQG, LQP, LQW03A/04A/15A/18A/21H/2BA/2UA series, please use reflow soldering.

Solder: Use Sn-3.0Ag-0.5Cu solder.

Flux: Use rosin-based flux, but not strongly acidic flux (with chlorine content exceeding 0.2wt%).

Do not use water-soluble flux.

The flux used for LQW03/04/15/18/21/2BA/2UA series should use the rosin-based flux that includes middle activator equivalent to 0.06wt% to 0.1wt% chlorine.


For additional mounting methods, please contact Murata.

Continued on the following page. ↗

Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


(2) Soldering profile

- Flow Soldering profile (Sn-3.0Ag-0.5Cu solder)



| Series | Pre-heating | | Standard Profile | | | Limit Profile | | |
|----------------------|-------------|------------|------------------|------------|---------------|---------------|------------|---------------|
| | Temp. (T1) | Time. (t1) | Heating | | Cycle of flow | Heating | | Cycle of flow |
| | | | Temp. (T2) | Time. (t2) | | Temp. (T3) | Time. (t2) | |
| LQW2BH/31H LQH31H | 150°C | 60s min. | 250°C | 4 to 6s | 2 times max. | 265±3°C | 5s max. | 2 times max. |

- Reflow Soldering profile (Sn-3.0Ag-0.5Cu solder)



| Series | Standard Profile | | | | Limit Profile | | | |
|--|------------------|------------|-----------------------|-----------------|---------------|------------|-----------------------|-----------------|
| | Heating | | Peak temperature (T2) | Cycle of reflow | Heating | | Peak temperature (T4) | Cycle of reflow |
| | Temp. (T1) | Time. (t1) | | | Temp. (T3) | Time. (t2) | | |
| LQG15H/18H LQW03A/04A/15A/18A/21H LQW2BA/2UA LQP02T/03T/15M/18M LQW2BH/31H LQH31H | 220°C | 30 to 60s | 245±3°C | 2 times max. | 230°C | 60s max. | 260°C/10s | 2 times max. |

(3) Reworking with Soldering Iron

*Except for LQP02T Series

Preheating at 150°C for 1 minute is required. Do not directly touch the ceramic element with the tip of the soldering iron. The reworking soldering conditions are as follows:

Soldering iron power output: 80W max.

Temperature of soldering iron tip: 350°C

Diameter of soldering iron end: 3.0mm max.

Soldering time: within 3 s


Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

3. Mounting Instructions

(1) Land Pattern Dimensions

Large lands reduce Q of the mounted chip. Also, large protruding land areas (bordered by lines having dimensions 'c' and 'd' shown) cause floating and electrode leaching.





(2) Land Pattern Designing (LQW series)

Please follow the recommended patterns. Otherwise, their performance, which includes electrical performance or solderability, may be affected, or result in "position shift" in the soldering process.

(3) PCB Warping

PCB should be designed so that products are not subjected to the mechanical stress caused by warping the board.




Continued on the following page. ↗


⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

(4) Amount of Solder Paste
 Excessive solder causes electrode corrosion, while insufficient solder causes low electrode bonding strength. Adjust the amount of solder paste as shown on the right so that solder is applied.

- Guideline of solder paste thickness
 - LQP (Except for LQP02T), LQG, LQW15AN_00/LQW15AN_10/LQW18AN/LQW21H/LQW2BA/LQW2UA: 100 to 150µm
 - LQP02T: 50 to 80µm
 - LQW03A/LQW04A: 80 to 100µm
 - LQW15AN_80: 50 to 100µm
 - LQW_H: 200 to 300µm



LQW15A Series:
 Too much solder may cause slant or rotation of the chip at the time of solder melting. Please reduce the amount of solder by using a smaller solder area than the land pattern, as shown in the figure at right.



(5) Amount of Adhesive
 If too much adhesive is applied, then it may overflow into the land or termination areas and yield poor solderability. In contrast, if insufficient adhesive is applied, or if the adhesive is not sufficiently hardened, then the chip may become detached during flow soldering. Apply the adhesive in accordance with the conditions shown in the chart.

LQW_H

| Part Number | Typical Application Amount (in:mg) |
|------------------|------------------------------------|
| | IR-100 |
| LQW2BH | 0.15-0.20 |
| LQH31H LQW31H | 0.20-0.25 |

4. Cleaning

The following conditions should be observed when cleaning chip inductors (chip coils):


- (1) Cleaning Temperature: 60°C max. (40°C max. for alcohol cleaning agents)
- (2) Ultrasonic
 - Output: 20W/l max.
 - Duration: 5 minutes max.
 - Frequency: 28 to 40kHz
 - Care should be taken not to cause resonance of the PCB and mounted products.
- (3) Cleaning agent
 - The following cleaning agents have been tested on individual components. Evaluation in complete assembly should be done prior to production.

- (a) Alcohol cleaning agents
Isopropyl alcohol (IPA)
- (b) Aqueous cleaning agents
Pine Alpha ST-100S
- (4) Ensure that flux residue is completely removed. Component should be thoroughly dried after aqueous agents have been removed with deionized water.

For additional cleaning methods, please contact Murata.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Minimum Quantity and 8mm Width Taping Dimensions




Paper Tape

| Part Number | Dimensions | | Total Thickness of Tape | Packaging Code (Minimum Qty. [pcs.]) | | |
|--------------|----------------|-----------|-------------------------|--------------------------------------|-------------|-------------|
| | a | b | | c | ø180mm reel | ø330mm reel |
| LQG15H | 0.62 | 1.12 | 0.8 max. | D [10000] | J [50000] | B [1000] |
| LQP02TN | 0.24 | 0.47 | 0.39 max. | D [20000] | - | B [500] |
| LQP02TQ | 0.24 | 0.45 | 0.39 max. | D [20000] | - | B [500] |
| LQP03T *1 | 0.35 | 0.65/0.67 | 0.55 max. | D [15000] | J [50000] | B [500] |
| LQP15M | 0.70 | 1.20 | 0.8 max. | D [10000] | J [50000] | B [500] |
| LQP18M | 1.19 | 2.0 | 0.8 max. | D [4000] | J [10000] | B [500] |
| LQW03A | 0.52 | 0.65 | 0.75 max. | D [10000] | - | - |
| LQW04A | 0.50 | 0.905 | 0.75 max. | D [10000] | - | B [500] |
| LQW15A_00 *2 | 0.64/0.66/0.69 | 1.18 | 0.8 max. | D [10000] | - | B [500] |
| LQW15A_10 *3 | 0.66/0.69 | 1.18 | 0.8 max. | D [10000] | - | B [500] |
| LQW15A_80 | 0.75 | 1.18 | 0.8 max. | D [10000] | - | B [500] |

- *1 0.67 (LQP03TG · LQP03TN_02; 0.6-62nH, 130-270nH) *3 0.69 (1.3nH)
- 0.65 (LQP03TN_02; 68-120nH) 0.66 (2.2-5.6nH)
- *2 0.69 (1.5-2.7nH, 3.9-4.7nH, 5.8-6.8nH, 8.2-9.5nH, 11nH, 12nH, 15nH)
- 0.66 (2.9nH, 5.1nH, 7.3nH, 7.5nH, 10nH, 13nH, 16-23nH, 100nH, 120nH)
- 0.64 (24-91nH)

(in mm)

Minimum Quantity and 8mm Width Taping Dimensions



Dimension of the cavity of embossed tape is measured at the bottom side.

Paper Tape

| Part Number | Dimensions | | Total Thickness of Tape | Packaging Code (Minimum Qty. [pcs.]) | | |
|-------------|------------|------|-------------------------|--------------------------------------|-------------|-------------|
| | a | b | | c | ø180mm reel | ø330mm reel |
| LQG18H | 1.05 | 1.85 | 1.1 max. | D [4000] | J [10000] | B [1000] |
| LQW18A_00 | 1.0 | 1.8 | 1.1 max. | D [4000] | J [10000] | B [500] |
| LQW18A_10 | 1.1 | 1.9 | 1.1 max. | D [4000] | J [10000] | B [500] |
| LQW18A_80 | 1.15 | 1.9 | 1.1 max. | D [4000] | J [10000] | B [500] |

Embossed Tape


| Part Number | Dimensions | | Depth of Cavity | Packaging Code (Minimum Qty. [pcs.]) | | |
|----------------|------------|-----|-----------------|--------------------------------------|-------------|-------------|
| | a | b | | c | ø180mm reel | ø330mm reel |
| LQH31H, LQW31H | 1.9 | 3.6 | 2.0 | L [2000] | K [7500] | - |
| LQW21H | 1.55 | 2.3 | 1.1 | L [3000] | - | B [500] |
| LQW2BH | 1.75 | 2.3 | 2.0 | L [2000] | K [7500] | - |
| LQW2BA | 1.8 | 2.3 | 1.65 | L [2000] | - | - |
| LQW2UA | 2.7 | 2.8 | 2.15 | L [2000] | - | - |

(in mm)

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

RF Inductors **Design Kits**

■ Holder Type



●EKLMQ15SC-KIT (RF Inductors Multilayer Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQG15HS1N0S02 | 10 | 1.0nH | ±0.3nH | 8 | 0.07 | 300 |
| 2 | LQG15HS1N1S02 | 10 | 1.1nH | ±0.3nH | 8 | 0.09 | 300 |
| 3 | LQG15HS1N2S02 | 10 | 1.2nH | ±0.3nH | 8 | 0.09 | 300 |
| 4 | LQG15HS1N3S02 | 10 | 1.3nH | ±0.3nH | 8 | 0.09 | 300 |
| 5 | LQG15HS1N5S02 | 10 | 1.5nH | ±0.3nH | 8 | 0.10 | 300 |
| 6 | LQG15HS1N6S02 | 10 | 1.6nH | ±0.3nH | 8 | 0.10 | 300 |
| 7 | LQG15HS1N8S02 | 10 | 1.8nH | ±0.3nH | 8 | 0.10 | 300 |
| 8 | LQG15HS2N0S02 | 10 | 2.0nH | ±0.3nH | 8 | 0.10 | 300 |
| 9 | LQG15HS2N2S02 | 10 | 2.2nH | ±0.3nH | 8 | 0.12 | 300 |
| 10 | LQG15HS2N4S02 | 10 | 2.4nH | ±0.3nH | 8 | 0.15 | 300 |
| 11 | LQG15HS2N7S02 | 10 | 2.7nH | ±0.3nH | 8 | 0.15 | 300 |
| 12 | LQG15HS3N0S02 | 10 | 3.0nH | ±0.3nH | 8 | 0.17 | 300 |
| 13 | LQG15HS3N3S02 | 10 | 3.3nH | ±0.3nH | 8 | 0.17 | 300 |
| 14 | LQG15HS3N6S02 | 10 | 3.6nH | ±0.3nH | 8 | 0.18 | 300 |
| 15 | LQG15HS3N9S02 | 10 | 3.9nH | ±0.3nH | 8 | 0.18 | 300 |
| 16 | LQG15HS4N3S02 | 10 | 4.3nH | ±0.3nH | 8 | 0.18 | 300 |
| 17 | LQG15HS4N7S02 | 10 | 4.7nH | ±0.3nH | 8 | 0.18 | 300 |
| 18 | LQG15HS5N1S02 | 10 | 5.1nH | ±0.3nH | 8 | 0.20 | 300 |
| 19 | LQG15HS5N6S02 | 10 | 5.6nH | ±0.3nH | 8 | 0.20 | 300 |
| 20 | LQG15HS6N2S02 | 10 | 6.2nH | ±0.3nH | 8 | 0.22 | 300 |
| 21 | LQG15HS6N8J02 | 10 | 6.8nH | ±5% | 8 | 0.24 | 300 |
| 22 | LQG15HS7N5J02 | 10 | 7.5nH | ±5% | 8 | 0.24 | 300 |
| 23 | LQG15HS8N2J02 | 10 | 8.2nH | ±5% | 8 | 0.24 | 300 |
| 24 | LQG15HS9N1J02 | 10 | 9.1nH | ±5% | 8 | 0.26 | 300 |
| 25 | LQG15HS10NJ02 | 10 | 10nH | ±5% | 8 | 0.26 | 300 |
| 26 | LQG15HS12NJ02 | 10 | 12nH | ±5% | 8 | 0.28 | 300 |
| 27 | LQG15HS15NJ02 | 10 | 15nH | ±5% | 8 | 0.32 | 300 |
| 28 | LQG15HS18NJ02 | 10 | 18nH | ±5% | 8 | 0.36 | 300 |
| 29 | LQG15HS22NJ02 | 10 | 22nH | ±5% | 8 | 0.42 | 300 |
| 30 | LQG15HS27NJ02 | 10 | 27nH | ±5% | 8 | 0.46 | 300 |
| 31 | LQG15HS33NJ02 | 10 | 33nH | ±5% | 8 | 0.58 | 200 |
| 32 | LQG15HS39NJ02 | 10 | 39nH | ±5% | 8 | 0.65 | 200 |
| 33 | LQG15HS47NJ02 | 10 | 47nH | ±5% | 8 | 0.72 | 200 |
| 34 | LQG15HS56NJ02 | 10 | 56nH | ±5% | 8 | 0.82 | 200 |
| 35 | LQG15HS68NJ02 | 10 | 68nH | ±5% | 8 | 0.92 | 180 |
| 36 | LQG15HS82NJ02 | 10 | 82nH | ±5% | 8 | 1.20 | 150 |
| 37 | LQG15HSR10J02 | 10 | 100nH | ±5% | 8 | 1.25 | 150 |
| 38 | LQG15HSR12J02 | 10 | 120nH | ±5% | 8 | 1.30 | 150 |
| 39 | LQG15HSR15J02 | 10 | 150nH | ±5% | 8 | 2.99 | 140 |
| 40 | LQG15HSR18J02 | 10 | 180nH | ±5% | 8 | 3.38 | 130 |
| 41 | LQG15HSR22J02 | 10 | 220nH | ±5% | 8 | 3.77 | 120 |
| 42 | LQG15HSR27J02 | 10 | 270nH | ±5% | 8 | 4.94 | 110 |

●EKLMQG18B-KIT (RF Inductors Multilayer Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQG18HN1N2S00 | 10 | 1.2nH | ±0.3nH | 12 | 0.10 | 500 |
| 2 | LQG18HN1N5S00 | 10 | 1.5nH | ±0.3nH | 12 | 0.10 | 500 |
| 3 | LQG18HN1N8S00 | 10 | 1.8nH | ±0.3nH | 12 | 0.10 | 500 |
| 4 | LQG18HN2N2S00 | 10 | 2.2nH | ±0.3nH | 12 | 0.10 | 500 |
| 5 | LQG18HN2N7S00 | 10 | 2.7nH | ±0.3nH | 12 | 0.15 | 500 |
| 6 | LQG18HN3N3S00 | 10 | 3.3nH | ±0.3nH | 12 | 0.15 | 500 |
| 7 | LQG18HN3N9S00 | 10 | 3.9nH | ±0.3nH | 12 | 0.15 | 450 |
| 8 | LQG18HN4N7S00 | 10 | 4.7nH | ±0.3nH | 12 | 0.20 | 450 |
| 9 | LQG18HN5N6S00 | 10 | 5.6nH | ±0.3nH | 12 | 0.20 | 430 |

Continued on the following page.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 10 | LQG18HN6N8J00 | 10 | 6.8nH | ±5% | 12 | 0.25 | 430 |
| 11 | LQG18HN8N2J00 | 10 | 8.2nH | ±5% | 12 | 0.25 | 400 |
| 12 | LQG18HN10NJ00 | 10 | 10nH | ±5% | 12 | 0.30 | 400 |
| 13 | LQG18HN12NJ00 | 10 | 12nH | ±5% | 12 | 0.35 | 400 |
| 14 | LQG18HN15NJ00 | 10 | 15nH | ±5% | 12 | 0.40 | 350 |
| 15 | LQG18HN18NJ00 | 10 | 18nH | ±5% | 12 | 0.45 | 350 |
| 16 | LQG18HN22NJ00 | 10 | 22nH | ±5% | 12 | 0.50 | 300 |
| 17 | LQG18HN27NJ00 | 10 | 27nH | ±5% | 12 | 0.55 | 300 |
| 18 | LQG18HN33NJ00 | 10 | 33nH | ±5% | 12 | 0.60 | 300 |
| 19 | LQG18HN39NJ00 | 10 | 39nH | ±5% | 12 | 0.65 | 300 |
| 20 | LQG18HN47NJ00 | 10 | 47nH | ±5% | 12 | 0.70 | 300 |
| 21 | LQG18HN56NJ00 | 10 | 56nH | ±5% | 12 | 0.75 | 300 |
| 22 | LQG18HN68NJ00 | 10 | 68nH | ±5% | 12 | 0.80 | 300 |
| 23 | LQG18HN82NJ00 | 10 | 82nH | ±5% | 12 | 0.85 | 300 |
| 24 | LQG18HNR10J00 | 10 | 100nH | ±5% | 12 | 0.90 | 300 |

●EKLMP02F-KIT (RF Inductors Film Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQP02TN0N2B02 | 10 | 0.2nH | ±0.1nH | - | 0.50 | 320 |
| 2 | LQP02TN0N3B02 | 10 | 0.3nH | ±0.1nH | - | 0.50 | 320 |
| 3 | LQP02TN0N4B02 | 10 | 0.4nH | ±0.1nH | 8 | 0.50 | 320 |
| 4 | LQP02TN0N5B02 | 10 | 0.5nH | ±0.1nH | 8 | 0.50 | 320 |
| 5 | LQP02TN0N6B02 | 10 | 0.6nH | ±0.1nH | 8 | 0.50 | 320 |
| 6 | LQP02TN0N7B02 | 10 | 0.7nH | ±0.1nH | 8 | 0.50 | 320 |
| 7 | LQP02TN0N8B02 | 10 | 0.8nH | ±0.1nH | 8 | 0.50 | 320 |
| 8 | LQP02TN0N9B02 | 10 | 0.9nH | ±0.1nH | 8 | 0.50 | 320 |
| 9 | LQP02TN1N0B02 | 10 | 1.0nH | ±0.1nH | 8 | 0.60 | 220 |
| 10 | LQP02TN1N1B02 | 10 | 1.1nH | ±0.1nH | 8 | 0.60 | 220 |
| 11 | LQP02TN1N2B02 | 10 | 1.2nH | ±0.1nH | 8 | 0.60 | 220 |
| 12 | LQP02TN1N3B02 | 10 | 1.3nH | ±0.1nH | 8 | 0.60 | 220 |
| 13 | LQP02TN1N4B02 | 10 | 1.4nH | ±0.1nH | 8 | 0.60 | 220 |
| 14 | LQP02TN1N5B02 | 10 | 1.5nH | ±0.1nH | 8 | 0.60 | 220 |
| 15 | LQP02TN1N6B02 | 10 | 1.6nH | ±0.1nH | 8 | 0.60 | 220 |
| 16 | LQP02TN1N7B02 | 10 | 1.7nH | ±0.1nH | 8 | 0.70 | 200 |
| 17 | LQP02TN1N8B02 | 10 | 1.8nH | ±0.1nH | 8 | 0.70 | 200 |
| 18 | LQP02TN1N9B02 | 10 | 1.9nH | ±0.1nH | 8 | 0.75 | 200 |
| 19 | LQP02TN2N0B02 | 10 | 2.0nH | ±0.1nH | 8 | 0.75 | 200 |
| 20 | LQP02TN2N1B02 | 10 | 2.1nH | ±0.1nH | 8 | 0.75 | 200 |
| 21 | LQP02TN2N2B02 | 10 | 2.2nH | ±0.1nH | 8 | 0.75 | 200 |
| 22 | LQP02TN2N3B02 | 10 | 2.3nH | ±0.1nH | 8 | 0.75 | 200 |
| 23 | LQP02TN2N4B02 | 10 | 2.4nH | ±0.1nH | 8 | 0.75 | 200 |
| 24 | LQP02TN2N5B02 | 10 | 2.5nH | ±0.1nH | 8 | 0.80 | 200 |
| 25 | LQP02TN2N6B02 | 10 | 2.6nH | ±0.1nH | 8 | 0.80 | 200 |
| 26 | LQP02TN2N7B02 | 10 | 2.7nH | ±0.1nH | 8 | 0.80 | 200 |
| 27 | LQP02TN2N8B02 | 10 | 2.8nH | ±0.1nH | 8 | 1.10 | 200 |
| 28 | LQP02TN2N9B02 | 10 | 2.9nH | ±0.1nH | 8 | 1.10 | 200 |
| 29 | LQP02TN3N0B02 | 10 | 3.0nH | ±0.1nH | 8 | 1.10 | 200 |
| 30 | LQP02TN3N1B02 | 10 | 3.1nH | ±0.1nH | 8 | 1.30 | 180 |
| 31 | LQP02TN3N2B02 | 10 | 3.2nH | ±0.1nH | 8 | 1.30 | 180 |
| 32 | LQP02TN3N3B02 | 10 | 3.3nH | ±0.1nH | 8 | 1.30 | 180 |
| 33 | LQP02TN3N4B02 | 10 | 3.4nH | ±0.1nH | 8 | 1.30 | 180 |
| 34 | LQP02TN3N5B02 | 10 | 3.5nH | ±0.1nH | 8 | 1.30 | 180 |
| 35 | LQP02TN3N6B02 | 10 | 3.6nH | ±0.1nH | 8 | 1.30 | 180 |
| 36 | LQP02TN3N7B02 | 10 | 3.7nH | ±0.1nH | 8 | 1.30 | 180 |
| 37 | LQP02TN3N8B02 | 10 | 3.8nH | ±0.1nH | 8 | 1.30 | 180 |
| 38 | LQP02TN3N9B02 | 10 | 3.9nH | ±0.1nH | 8 | 1.30 | 180 |
| 39 | LQP02TN4N0B02 | 10 | 4.0nH | ±0.1nH | 8 | 1.30 | 180 |
| 40 | LQP02TN4N1B02 | 10 | 4.1nH | ±0.1nH | 8 | 1.30 | 180 |
| 41 | LQP02TN4N2B02 | 10 | 4.2nH | ±0.1nH | 8 | 1.30 | 180 |
| 42 | LQP02TN4N3H02 | 10 | 4.3nH | ±3% | 8 | 1.30 | 180 |
| 43 | LQP02TN4N7H02 | 10 | 4.7nH | ±3% | 8 | 1.50 | 160 |
| 44 | LQP02TN5N1H02 | 10 | 5.1nH | ±3% | 8 | 1.50 | 160 |
| 45 | LQP02TN5N6H02 | 10 | 5.6nH | ±3% | 8 | 1.80 | 140 |
| 46 | LQP02TN6N2H02 | 10 | 6.2nH | ±3% | 8 | 1.80 | 140 |

Continued on the following page. ↗

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 47 | LQP02TN6N8H02 | 10 | 6.8nH | ±3% | 8 | 2.00 | 140 |
| 48 | LQP02TN7N5H02 | 10 | 7.5nH | ±3% | 8 | 2.00 | 140 |
| 49 | LQP02TN8N2H02 | 10 | 8.2nH | ±3% | 8 | 2.10 | 140 |
| 50 | LQP02TN9N1H02 | 10 | 9.1nH | ±3% | 8 | 2.10 | 140 |
| 51 | LQP02TN10NH02 | 10 | 10nH | ±3% | 8 | 2.50 | 140 |
| 52 | LQP02TN11NH02 | 10 | 11nH | ±3% | 7 | 2.80 | 140 |
| 53 | LQP02TN12NH02 | 10 | 12nH | ±3% | 7 | 2.80 | 140 |
| 54 | LQP02TN13NH02 | 10 | 13nH | ±3% | 7 | 3.20 | 140 |
| 55 | LQP02TN15NH02 | 10 | 15nH | ±3% | 7 | 3.20 | 140 |
| 56 | LQP02TN16NH02 | 10 | 16nH | ±3% | 7 | 3.50 | 140 |
| 57 | LQP02TN18NH02 | 10 | 18nH | ±3% | 7 | 3.50 | 140 |
| 58 | LQP02TN20NH02 | 10 | 20nH | ±3% | 6 | 5.00 | 100 |

●EKLMP3GC-KIT (RF Inductors Film Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQP03TG0N6B02 | 10 | 0.6nH | ±0.1nH | 11 | 0.08 | 850 |
| 2 | LQP03TG0N7B02 | 10 | 0.7nH | ±0.1nH | 12 | 0.10 | 750 |
| 3 | LQP03TG0N8B02 | 10 | 0.8nH | ±0.1nH | 12 | 0.10 | 750 |
| 4 | LQP03TG0N9B02 | 10 | 0.9nH | ±0.1nH | 12 | 0.12 | 700 |
| 5 | LQP03TG1N0B02 | 10 | 1.0nH | ±0.1nH | 12 | 0.15 | 600 |
| 6 | LQP03TG1N1B02 | 10 | 1.1nH | ±0.1nH | 12 | 0.15 | 600 |
| 7 | LQP03TG1N2B02 | 10 | 1.2nH | ±0.1nH | 13 | 0.15 | 600 |
| 8 | LQP03TG1N3B02 | 10 | 1.3nH | ±0.1nH | 13 | 0.15 | 600 |
| 9 | LQP03TG1N4B02 | 10 | 1.4nH | ±0.1nH | 13 | 0.15 | 600 |
| 10 | LQP03TG1N5B02 | 10 | 1.5nH | ±0.1nH | 13 | 0.15 | 600 |
| 11 | LQP03TG1N6B02 | 10 | 1.6nH | ±0.1nH | 13 | 0.15 | 600 |
| 12 | LQP03TG1N7B02 | 10 | 1.7nH | ±0.1nH | 13 | 0.20 | 500 |
| 13 | LQP03TG1N8B02 | 10 | 1.8nH | ±0.1nH | 13 | 0.20 | 500 |
| 14 | LQP03TG1N9B02 | 10 | 1.9nH | ±0.1nH | 13 | 0.25 | 450 |
| 15 | LQP03TG2N0B02 | 10 | 2.0nH | ±0.1nH | 13 | 0.25 | 450 |
| 16 | LQP03TG2N1B02 | 10 | 2.1nH | ±0.1nH | 13 | 0.25 | 450 |
| 17 | LQP03TG2N2B02 | 10 | 2.2nH | ±0.1nH | 13 | 0.25 | 450 |
| 18 | LQP03TG2N3B02 | 10 | 2.3nH | ±0.1nH | 13 | 0.25 | 450 |
| 19 | LQP03TG2N4B02 | 10 | 2.4nH | ±0.1nH | 13 | 0.25 | 450 |
| 20 | LQP03TG2N5B02 | 10 | 2.5nH | ±0.1nH | 13 | 0.25 | 450 |
| 21 | LQP03TG2N6B02 | 10 | 2.6nH | ±0.1nH | 13 | 0.25 | 450 |
| 22 | LQP03TG2N7B02 | 10 | 2.7nH | ±0.1nH | 13 | 0.25 | 450 |
| 23 | LQP03TG2N8B02 | 10 | 2.8nH | ±0.1nH | 13 | 0.25 | 450 |
| 24 | LQP03TG2N9B02 | 10 | 2.9nH | ±0.1nH | 13 | 0.25 | 450 |
| 25 | LQP03TG3N0B02 | 10 | 3.0nH | ±0.1nH | 13 | 0.25 | 450 |
| 26 | LQP03TG3N1B02 | 10 | 3.1nH | ±0.1nH | 13 | 0.32 | 400 |
| 27 | LQP03TG3N2B02 | 10 | 3.2nH | ±0.1nH | 13 | 0.32 | 400 |
| 28 | LQP03TG3N3B02 | 10 | 3.3nH | ±0.1nH | 13 | 0.32 | 400 |
| 29 | LQP03TG3N4B02 | 10 | 3.4nH | ±0.1nH | 13 | 0.35 | 350 |
| 30 | LQP03TG3N5B02 | 10 | 3.5nH | ±0.1nH | 13 | 0.35 | 350 |
| 31 | LQP03TG3N6B02 | 10 | 3.6nH | ±0.1nH | 13 | 0.35 | 350 |
| 32 | LQP03TG3N7B02 | 10 | 3.7nH | ±0.1nH | 13 | 0.35 | 350 |
| 33 | LQP03TG3N8B02 | 10 | 3.8nH | ±0.1nH | 13 | 0.35 | 350 |
| 34 | LQP03TG3N9B02 | 10 | 3.9nH | ±0.1nH | 13 | 0.35 | 350 |
| 35 | LQP03TG4N3H02 | 10 | 4.3nH | ±3% | 13 | 0.58 | 300 |
| 36 | LQP03TG4N7H02 | 10 | 4.7nH | ±3% | 12 | 0.72 | 250 |
| 37 | LQP03TG5N1H02 | 10 | 5.1nH | ±3% | 12 | 0.72 | 250 |
| 38 | LQP03TG5N6H02 | 10 | 5.6nH | ±3% | 12 | 0.88 | 250 |
| 39 | LQP03TG6N2H02 | 10 | 6.2nH | ±3% | 12 | 1.15 | 200 |
| 40 | LQP03TG6N8H02 | 10 | 6.8nH | ±3% | 12 | 1.15 | 200 |
| 41 | LQP03TG7N5H02 | 10 | 7.5nH | ±3% | 12 | 1.22 | 200 |
| 42 | LQP03TG8N2H02 | 10 | 8.2nH | ±3% | 12 | 1.40 | 200 |
| 43 | LQP03TG9N1H02 | 10 | 9.1nH | ±3% | 11 | 1.40 | 200 |
| 44 | LQP03TG10NH02 | 10 | 10nH | ±3% | 11 | 1.52 | 190 |
| 45 | LQP03TG12NH02 | 10 | 12nH | ±3% | 11 | 1.78 | 180 |
| 46 | LQP03TG15NH02 | 10 | 15nH | ±3% | 11 | 1.90 | 170 |
| 47 | LQP03TG18NH02 | 10 | 18nH | ±3% | 11 | 2.28 | 160 |
| 48 | LQP03TG22NH02 | 10 | 22nH | ±3% | 9 | 2.85 | 140 |

Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

●EKLMP3AB-KIT (RF Inductors Film Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQP03TN0N6B02 | 10 | 0.6nH | ±0.1nH | 14 | 0.07 | 850 |
| 2 | LQP03TN0N7B02 | 10 | 0.7nH | ±0.1nH | 14 | 0.08 | 800 |
| 3 | LQP03TN0N8B02 | 10 | 0.8nH | ±0.1nH | 14 | 0.08 | 800 |
| 4 | LQP03TN0N9B02 | 10 | 0.9nH | ±0.1nH | 14 | 0.10 | 750 |
| 5 | LQP03TN1N0B02 | 10 | 1.0nH | ±0.1nH | 14 | 0.10 | 750 |
| 6 | LQP03TN1N1B02 | 10 | 1.1nH | ±0.1nH | 14 | 0.10 | 750 |
| 7 | LQP03TN1N2B02 | 10 | 1.2nH | ±0.1nH | 14 | 0.10 | 750 |
| 8 | LQP03TN1N3B02 | 10 | 1.3nH | ±0.1nH | 14 | 0.15 | 600 |
| 9 | LQP03TN1N4B02 | 10 | 1.4nH | ±0.1nH | 14 | 0.15 | 600 |
| 10 | LQP03TN1N5B02 | 10 | 1.5nH | ±0.1nH | 14 | 0.15 | 600 |
| 11 | LQP03TN1N6B02 | 10 | 1.6nH | ±0.1nH | 14 | 0.15 | 600 |
| 12 | LQP03TN1N7B02 | 10 | 1.7nH | ±0.1nH | 14 | 0.15 | 600 |
| 13 | LQP03TN1N8B02 | 10 | 1.8nH | ±0.1nH | 14 | 0.15 | 600 |
| 14 | LQP03TN1N9B02 | 10 | 1.9nH | ±0.1nH | 14 | 0.15 | 600 |
| 15 | LQP03TN2N0B02 | 10 | 2.0nH | ±0.1nH | 14 | 0.15 | 600 |
| 16 | LQP03TN2N1B02 | 10 | 2.1nH | ±0.1nH | 14 | 0.15 | 600 |
| 17 | LQP03TN2N2B02 | 10 | 2.2nH | ±0.1nH | 14 | 0.15 | 600 |
| 18 | LQP03TN2N3B02 | 10 | 2.3nH | ±0.1nH | 14 | 0.20 | 500 |
| 19 | LQP03TN2N4B02 | 10 | 2.4nH | ±0.1nH | 14 | 0.20 | 500 |
| 20 | LQP03TN2N5B02 | 10 | 2.5nH | ±0.1nH | 14 | 0.20 | 500 |
| 21 | LQP03TN2N6B02 | 10 | 2.6nH | ±0.1nH | 14 | 0.20 | 500 |
| 22 | LQP03TN2N7B02 | 10 | 2.7nH | ±0.1nH | 14 | 0.20 | 500 |
| 23 | LQP03TN2N8B02 | 10 | 2.8nH | ±0.1nH | 14 | 0.20 | 500 |
| 24 | LQP03TN2N9B02 | 10 | 2.9nH | ±0.1nH | 14 | 0.20 | 500 |
| 25 | LQP03TN3N0B02 | 10 | 3.0nH | ±0.1nH | 14 | 0.25 | 450 |
| 26 | LQP03TN3N1B02 | 10 | 3.1nH | ±0.1nH | 14 | 0.25 | 450 |
| 27 | LQP03TN3N2B02 | 10 | 3.2nH | ±0.1nH | 14 | 0.25 | 450 |
| 28 | LQP03TN3N3B02 | 10 | 3.3nH | ±0.1nH | 14 | 0.25 | 450 |
| 29 | LQP03TN3N4B02 | 10 | 3.4nH | ±0.1nH | 14 | 0.25 | 450 |
| 30 | LQP03TN3N5B02 | 10 | 3.5nH | ±0.1nH | 14 | 0.25 | 450 |
| 31 | LQP03TN3N6B02 | 10 | 3.6nH | ±0.1nH | 14 | 0.30 | 400 |
| 32 | LQP03TN3N7B02 | 10 | 3.7nH | ±0.1nH | 14 | 0.30 | 400 |
| 33 | LQP03TN3N8B02 | 10 | 3.8nH | ±0.1nH | 14 | 0.30 | 400 |
| 34 | LQP03TN3N9B02 | 10 | 3.9nH | ±0.1nH | 14 | 0.30 | 400 |
| 35 | LQP03TN4N0B02 | 10 | 4.0nH | ±0.1nH | 14 | 0.40 | 350 |
| 36 | LQP03TN4N1B02 | 10 | 4.1nH | ±0.1nH | 14 | 0.40 | 350 |
| 37 | LQP03TN4N2B02 | 10 | 4.2nH | ±0.1nH | 14 | 0.40 | 350 |
| 38 | LQP03TN4N3H02 | 10 | 4.3nH | ±3% | 14 | 0.40 | 350 |
| 39 | LQP03TN4N7H02 | 10 | 4.7nH | ±3% | 14 | 0.40 | 350 |
| 40 | LQP03TN5N1H02 | 10 | 5.1nH | ±3% | 14 | 0.40 | 350 |
| 41 | LQP03TN5N6H02 | 10 | 5.6nH | ±3% | 14 | 0.40 | 350 |
| 42 | LQP03TN6N2H02 | 10 | 6.2nH | ±3% | 14 | 0.60 | 300 |
| 43 | LQP03TN6N8H02 | 10 | 6.8nH | ±3% | 14 | 0.60 | 300 |
| 44 | LQP03TN7N5H02 | 10 | 7.5nH | ±3% | 14 | 0.60 | 300 |
| 45 | LQP03TN8N2H02 | 10 | 8.2nH | ±3% | 14 | 0.70 | 250 |
| 46 | LQP03TN9N1H02 | 10 | 9.1nH | ±3% | 14 | 0.70 | 250 |
| 47 | LQP03TN10NH02 | 10 | 10nH | ±3% | 14 | 0.70 | 250 |
| 48 | LQP03TN11NH02 | 10 | 11nH | ±3% | 14 | 0.80 | 250 |
| 49 | LQP03TN12NH02 | 10 | 12nH | ±3% | 12 | 0.70 | 250 |
| 50 | LQP03TN13NH02 | 10 | 13nH | ±3% | 12 | 0.80 | 250 |
| 51 | LQP03TN15NH02 | 10 | 15nH | ±3% | 12 | 0.70 | 250 |
| 52 | LQP03TN16NH02 | 10 | 16nH | ±3% | 12 | 0.95 | 200 |
| 53 | LQP03TN18NH02 | 10 | 18nH | ±3% | 12 | 0.80 | 200 |
| 54 | LQP03TN20NH02 | 10 | 20nH | ±3% | 12 | 2.30 | 150 |

●EKLMP3BB-KIT (RF Inductors Film Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQP03TN22NH02 | 10 | 22nH | ±3% | 12 | 1.90 | 150 |
| 2 | LQP03TN24NH02 | 10 | 24nH | ±3% | 12 | 2.30 | 140 |
| 3 | LQP03TN27NH02 | 10 | 27nH | ±3% | 12 | 2.30 | 140 |
| 4 | LQP03TN30NH02 | 10 | 30nH | ±3% | 9 | 2.95 | 120 |
| 5 | LQP03TN33NJ02 | 10 | 33nH | ±5% | 9 | 2.95 | 120 |

Continued on the following page. ↗

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 6 | LQP03TN36NJ02 | 10 | 36nH | ±5% | 9 | 3.00 | 120 |
| 7 | LQP03TN39NJ02 | 10 | 39nH | ±5% | 9 | 3.00 | 120 |
| 8 | LQP03TN43NJ02 | 10 | 43nH | ±5% | 9 | 3.60 | 100 |
| 9 | LQP03TN47NJ02 | 10 | 47nH | ±5% | 9 | 3.60 | 100 |
| 10 | LQP03TN51NJ02 | 10 | 51nH | ±5% | 9 | 3.90 | 100 |
| 11 | LQP03TN56NJ02 | 10 | 56nH | ±5% | 9 | 3.90 | 100 |
| 12 | LQP03TN62NJ02 | 10 | 62nH | ±5% | 8 | 8 | 100 |
| 13 | LQP03TN68NJ02 | 10 | 68nH | ±5% | 8 | 8 | 100 |
| 14 | LQP03TN75NJ02 | 10 | 75nH | ±5% | 8 | 10 | 100 |
| 15 | LQP03TN82NJ02 | 10 | 82nH | ±5% | 8 | 10 | 100 |
| 16 | LQP03TN91NJ02 | 10 | 91nH | ±5% | 8 | 10 | 80 |
| 17 | LQP03TNR10J02 | 10 | 100nH | ±5% | 8 | 10 | 80 |
| 18 | LQP03TNR11J02 | 10 | 110nH | ±5% | 8 | 12 | 80 |
| 19 | LQP03TNR12J02 | 10 | 120nH | ±5% | 8 | 12 | 80 |
| 20 | LQP03TNR13J02 | 10 | 130nH | ±5% | 5 | 9 | 80 |
| 21 | LQP03TNR15J02 | 10 | 150nH | ±5% | 5 | 9 | 80 |
| 22 | LQP03TNR16J02 | 10 | 160nH | ±5% | 5 | 11 | 70 |
| 23 | LQP03TNR18J02 | 10 | 180nH | ±5% | 5 | 11 | 70 |
| 24 | LQP03TNR20J02 | 10 | 200nH | ±5% | 5 | 13 | 60 |
| 25 | LQP03TNR22J02 | 10 | 220nH | ±5% | 5 | 13 | 60 |
| 26 | LQP03TNR24J02 | 10 | 240nH | ±5% | 5 | 15 | 60 |
| 27 | LQP03TNR27J02 | 10 | 270nH | ±5% | 5 | 15 | 60 |

●EKLMP15B-KIT (RF Inductors Film Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQP15MN1N0B02 | 10 | 1.0nH | ±0.1nH | 13 | 0.1 | 400 |
| 2 | LQP15MN1N1B02 | 10 | 1.1nH | ±0.1nH | 13 | 0.1 | 390 |
| 3 | LQP15MN1N2B02 | 10 | 1.2nH | ±0.1nH | 13 | 0.1 | 390 |
| 4 | LQP15MN1N3B02 | 10 | 1.3nH | ±0.1nH | 13 | 0.2 | 280 |
| 5 | LQP15MN1N5B02 | 10 | 1.5nH | ±0.1nH | 13 | 0.2 | 280 |
| 6 | LQP15MN1N6B02 | 10 | 1.6nH | ±0.1nH | 13 | 0.3 | 220 |
| 7 | LQP15MN1N8B02 | 10 | 1.8nH | ±0.1nH | 13 | 0.2 | 280 |
| 8 | LQP15MN2N0B02 | 10 | 2.0nH | ±0.1nH | 13 | 0.3 | 220 |
| 9 | LQP15MN2N2B02 | 10 | 2.2nH | ±0.1nH | 13 | 0.3 | 220 |
| 10 | LQP15MN2N4B02 | 10 | 2.4nH | ±0.1nH | 13 | 0.3 | 220 |
| 11 | LQP15MN2N7B02 | 10 | 2.7nH | ±0.1nH | 13 | 0.3 | 220 |
| 12 | LQP15MN3N0B02 | 10 | 3.0nH | ±0.1nH | 13 | 0.4 | 190 |
| 13 | LQP15MN3N3B02 | 10 | 3.3nH | ±0.1nH | 13 | 0.4 | 190 |
| 14 | LQP15MN3N6B02 | 10 | 3.6nH | ±0.1nH | 13 | 0.5 | 170 |
| 15 | LQP15MN3N9B02 | 10 | 3.9nH | ±0.1nH | 13 | 0.5 | 170 |
| 16 | LQP15MN4N3B02 | 10 | 4.3nH | ±0.1nH | 13 | 0.6 | 160 |
| 17 | LQP15MN4N7B02 | 10 | 4.7nH | ±0.1nH | 13 | 0.6 | 160 |
| 18 | LQP15MN5N1B02 | 10 | 5.1nH | ±0.1nH | 13 | 0.7 | 140 |
| 19 | LQP15MN5N6B02 | 10 | 5.6nH | ±0.1nH | 13 | 0.7 | 140 |
| 20 | LQP15MN6N2B02 | 10 | 6.2nH | ±0.1nH | 13 | 0.9 | 130 |
| 21 | LQP15MN6N8B02 | 10 | 6.8nH | ±0.1nH | 13 | 0.9 | 130 |
| 22 | LQP15MN7N5B02 | 10 | 7.5nH | ±0.1nH | 13 | 1.1 | 110 |
| 23 | LQP15MN8N2B02 | 10 | 8.2nH | ±0.1nH | 13 | 1.1 | 110 |
| 24 | LQP15MN9N1B02 | 10 | 9.1nH | ±0.1nH | 13 | 1.3 | 100 |
| 25 | LQP15MN10NG02 | 10 | 10nH | ±2% | 13 | 1.3 | 100 |
| 26 | LQP15MN12NG02 | 10 | 12nH | ±2% | 13 | 1.6 | 90 |
| 27 | LQP15MN15NG02 | 10 | 15nH | ±2% | 13 | 1.8 | 90 |
| 28 | LQP15MN18NG02 | 10 | 18nH | ±2% | 13 | 2.0 | 80 |
| 29 | LQP15MN22NG02 | 10 | 22nH | ±2% | 13 | 2.6 | 70 |
| 30 | LQP15MN27NG02 | 10 | 27nH | ±2% | 13 | 3.1 | 70 |
| 31 | LQP15MN33NG02 | 10 | 33nH | ±2% | 13 | 3.8 | 60 |

●EKLQW03A-KIT (RF Inductors Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | |
| 1 | LQW03AW5N4J00 | 10 | 5.4nH | ±5% | 0.21 | 420 |
| 2 | LQW03AW5N6J00 | 10 | 5.6nH | ±5% | 0.33 | 330 |
| 3 | LQW03AW5N8J00 | 10 | 5.8nH | ±5% | 0.16 | 460 |
| 4 | LQW03AW6N8J00 | 10 | 6.8nH | ±5% | 0.18 | 460 |

Continued on the following page. ↗

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

| No. | Part Number | Quantity (pcs.) | Inductance | | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | |
| 5 | LQW03AW7N5J00 | 10 | 7.5nH | ±5% | 0.24 | 400 |
| 6 | LQW03AW8N7J00 | 10 | 8.7nH | ±5% | 0.42 | 290 |
| 7 | LQW03AW9N1J00 | 10 | 9.1nH | ±5% | 0.22 | 460 |
| 8 | LQW03AW13NJ00 | 10 | 13nH | ±5% | 0.54 | 280 |

●EKLQW04D-KIT (RF Inductors Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQW04AN1N1C00 | 10 | 1.1nH | ±0.2nH | 15 | 0.03 | 990 |
| 2 | LQW04AN1N8C00 | 10 | 1.8nH | ±0.2nH | 15 | 0.06 | 700 |
| 3 | LQW04AN2N7C00 | 10 | 2.7nH | ±0.2nH | 15 | 0.07 | 570 |
| 4 | LQW04AN3N0C00 | 10 | 3.0nH | ±0.2nH | 15 | 0.07 | 620 |
| 5 | LQW04AN3N3C00 | 10 | 3.3nH | ±0.2nH | 10 | 0.14 | 440 |
| 6 | LQW04AN3N6C00 | 10 | 3.6nH | ±0.2nH | 15 | 0.10 | 530 |
| 7 | LQW04AN3N9C00 | 10 | 3.9nH | ±0.2nH | 15 | 0.10 | 530 |
| 8 | LQW04AN4N3C00 | 10 | 4.3nH | ±0.2nH | 15 | 0.10 | 530 |
| 9 | LQW04AN4N7C00 | 10 | 4.7nH | ±0.2nH | 20 | 0.14 | 440 |
| 10 | LQW04AN5N1C00 | 10 | 5.1nH | ±0.2nH | 20 | 0.12 | 470 |
| 11 | LQW04AN5N6C00 | 10 | 5.6nH | ±0.2nH | 20 | 0.12 | 470 |
| 12 | LQW04AN6N2C00 | 10 | 6.2nH | ±0.2nH | 20 | 0.19 | 390 |
| 13 | LQW04AN6N8C00 | 10 | 6.8nH | ±0.2nH | 20 | 0.14 | 440 |
| 14 | LQW04AN7N5C00 | 10 | 7.5nH | ±0.2nH | 20 | 0.14 | 440 |
| 15 | LQW04AN8N2C00 | 10 | 8.2nH | ±0.2nH | 20 | 0.23 | 350 |
| 16 | LQW04AN9N1C00 | 10 | 9.1nH | ±0.2nH | 20 | 0.16 | 400 |
| 17 | LQW04AN10NH00 | 10 | 10nH | ±3% | 20 | 0.26 | 330 |
| 18 | LQW04AN11NH00 | 10 | 11nH | ±3% | 15 | 0.28 | 310 |
| 19 | LQW04AN12NH00 | 10 | 12nH | ±3% | 15 | 0.28 | 310 |
| 20 | LQW04AN13NH00 | 10 | 13nH | ±3% | 15 | 0.34 | 280 |
| 21 | LQW04AN15NH00 | 10 | 15nH | ±3% | 15 | 0.48 | 240 |
| 22 | LQW04AN16NH00 | 10 | 16nH | ±3% | 15 | 0.38 | 270 |
| 23 | LQW04AN18NH00 | 10 | 18nH | ±3% | 15 | 0.54 | 220 |
| 24 | LQW04AN19NH00 | 10 | 19nH | ±3% | 15 | 0.73 | 160 |
| 25 | LQW04AN20NH00 | 10 | 20nH | ±3% | 15 | 0.56 | 210 |
| 26 | LQW04AN22NH00 | 10 | 22nH | ±3% | 15 | 0.63 | 200 |
| 27 | LQW04AN23NH00 | 10 | 23nH | ±3% | 15 | 0.95 | 160 |
| 28 | LQW04AN24NH00 | 10 | 24nH | ±3% | 15 | 0.95 | 160 |
| 29 | LQW04AN25NH00 | 10 | 25nH | ±3% | 15 | 0.95 | 160 |
| 30 | LQW04AN27NH00 | 10 | 27nH | ±3% | 15 | 0.95 | 160 |
| 31 | LQW04AN33NH00 | 10 | 33nH | ±3% | 15 | 1.11 | 140 |

●EKLQW15K-KIT (RF Inductors Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQW15AN1N5B00 | 10 | 1.5nH | ±0.1nH | 10 | 0.03 | 1000 |
| 2 | LQW15AN2N4B00 | 10 | 2.4nH | ±0.1nH | 20 | 0.05 | 850 |
| 3 | LQW15AN2N5B00 | 10 | 2.5nH | ±0.1nH | 20 | 0.05 | 850 |
| 4 | LQW15AN2N7B00 | 10 | 2.7nH | ±0.1nH | 20 | 0.05 | 850 |
| 5 | LQW15AN2N9B00 | 10 | 2.9nH | ±0.1nH | 20 | 0.07 | 750 |
| 6 | LQW15AN3N9B00 | 10 | 3.9nH | ±0.1nH | 25 | 0.07 | 750 |
| 7 | LQW15AN4N1B00 | 10 | 4.1nH | ±0.1nH | 25 | 0.07 | 750 |
| 8 | LQW15AN4N3B00 | 10 | 4.3nH | ±0.1nH | 25 | 0.07 | 750 |
| 9 | LQW15AN4N7B00 | 10 | 4.7nH | ±0.1nH | 25 | 0.07 | 750 |
| 10 | LQW15AN5N1B00 | 10 | 5.1nH | ±0.1nH | 25 | 0.12 | 600 |
| 11 | LQW15AN5N8B00 | 10 | 5.8nH | ±0.1nH | 25 | 0.12 | 700 |
| 12 | LQW15AN6N2B00 | 10 | 6.2nH | ±0.1nH | 25 | 0.09 | 700 |
| 13 | LQW15AN6N8G00 | 10 | 6.8nH | ±2% | 25 | 0.09 | 700 |
| 14 | LQW15AN7N3G00 | 10 | 7.3nH | ±2% | 25 | 0.13 | 570 |
| 15 | LQW15AN7N5G00 | 10 | 7.5nH | ±2% | 25 | 0.13 | 570 |
| 16 | LQW15AN8N2G00 | 10 | 8.2nH | ±2% | 25 | 0.14 | 540 |
| 17 | LQW15AN8N7G00 | 10 | 8.7nH | ±2% | 25 | 0.14 | 540 |
| 18 | LQW15AN9N1G00 | 10 | 9.1nH | ±2% | 25 | 0.14 | 540 |
| 19 | LQW15AN9N5G00 | 10 | 9.5nH | ±2% | 25 | 0.14 | 540 |
| 20 | LQW15AN10NG00 | 10 | 10nH | ±2% | 25 | 0.17 | 500 |
| 21 | LQW15AN11NG00 | 10 | 11nH | ±2% | 30 | 0.14 | 500 |
| 22 | LQW15AN12NG00 | 10 | 12nH | ±2% | 30 | 0.14 | 500 |

Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 23 | LQW15AN13NG00 | 10 | 13nH | ±2% | 25 | 0.21 | 430 |
| 24 | LQW15AN15NG00 | 10 | 15nH | ±2% | 30 | 0.16 | 460 |
| 25 | LQW15AN16NG00 | 10 | 16nH | ±2% | 25 | 0.24 | 370 |
| 26 | LQW15AN18NG00 | 10 | 18nH | ±2% | 25 | 0.27 | 370 |
| 27 | LQW15AN19NG00 | 10 | 19nH | ±2% | 25 | 0.27 | 370 |
| 28 | LQW15AN20NG00 | 10 | 20nH | ±2% | 25 | 0.27 | 370 |
| 29 | LQW15AN22NG00 | 10 | 22nH | ±2% | 25 | 0.30 | 310 |
| 30 | LQW15AN23NG00 | 10 | 23nH | ±2% | 25 | 0.30 | 310 |
| 31 | LQW15AN24NG00 | 10 | 24nH | ±2% | 25 | 0.52 | 280 |
| 32 | LQW15AN27NG00 | 10 | 27nH | ±2% | 25 | 0.52 | 280 |
| 33 | LQW15AN30NG00 | 10 | 30nH | ±2% | 25 | 0.58 | 270 |
| 34 | LQW15AN33NG00 | 10 | 33nH | ±2% | 25 | 0.63 | 260 |
| 35 | LQW15AN36NG00 | 10 | 36nH | ±2% | 25 | 0.63 | 260 |
| 36 | LQW15AN39NG00 | 10 | 39nH | ±2% | 25 | 0.70 | 250 |
| 37 | LQW15AN40NG00 | 10 | 40nH | ±2% | 25 | 0.70 | 250 |
| 38 | LQW15AN43NG00 | 10 | 43nH | ±2% | 25 | 0.70 | 250 |
| 39 | LQW15AN47NG00 | 10 | 47nH | ±2% | 25 | 1.08 | 210 |
| 40 | LQW15AN51NG00 | 10 | 51nH | ±2% | 25 | 1.08 | 210 |
| 41 | LQW15AN56NG00 | 10 | 56nH | ±2% | 25 | 1.17 | 200 |
| 42 | LQW15AN62NG00 | 10 | 62nH | ±2% | 20 | 1.82 | 145 |
| 43 | LQW15AN68NG00 | 10 | 68nH | ±2% | 20 | 1.96 | 140 |
| 44 | LQW15AN72NG00 | 10 | 72nH | ±2% | 20 | 2.10 | 135 |
| 45 | LQW15AN75NG00 | 10 | 75nH | ±2% | 20 | 2.10 | 135 |
| 46 | LQW15AN82NG00 | 10 | 82nH | ±2% | 20 | 2.24 | 130 |
| 47 | LQW15AN91NG00 | 10 | 91nH | ±2% | 20 | 2.38 | 125 |
| 48 | LQW15ANR10J00 | 10 | 100nH | ±5% | 20 | 2.52 | 120 |
| 49 | LQW15ANR12J00 | 10 | 120nH | ±5% | 20 | 2.66 | 110 |
| 50 | LQW15AN1N3C10 | 10 | 1.3nH | ±0.2nH | 20 | 0.017 | 1200 |
| 51 | LQW15AN2N2C10 | 10 | 2.2nH | ±0.2nH | 25 | 0.027 | 1000 |
| 52 | LQW15AN2N4D10 | 10 | 2.4nH | ±0.5nH | 25 | 0.027 | 1000 |
| 53 | LQW15AN3N3D10 | 10 | 3.3nH | ±0.5nH | 30 | 0.04 | 900 |
| 54 | LQW15AN3N4C10 | 10 | 3.4nH | ±0.2nH | 30 | 0.04 | 900 |
| 55 | LQW15AN3N6C10 | 10 | 3.6nH | ±0.2nH | 30 | 0.04 | 900 |
| 56 | LQW15AN3N9D10 | 10 | 3.9nH | ±0.5nH | 30 | 0.040 | 900 |
| 57 | LQW15AN4N7D10 | 10 | 4.7nH | ±0.5nH | 30 | 0.051 | 800 |
| 58 | LQW15AN5N1C10 | 10 | 5.1nH | ±0.2nH | 30 | 0.051 | 800 |
| 59 | LQW15AN5N6C10 | 10 | 5.6nH | ±0.2nH | 30 | 0.051 | 800 |

●EKLQW80A-KIT (RF Inductors Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQW15AN1N3C80 | 10 | 1.3nH | ±0.2nH | 20 | 0.012 | 3150 |
| 2 | LQW15AN2N3B80 | 10 | 2.3nH | ±0.1nH | 30 | 0.022 | 2530 |
| 3 | LQW15AN2N4B80 | 10 | 2.4nH | ±0.1nH | 30 | 0.022 | 2530 |
| 4 | LQW15AN3N4B80 | 10 | 3.4nH | ±0.1nH | 30 | 0.030 | 1950 |
| 5 | LQW15AN3N6B80 | 10 | 3.6nH | ±0.1nH | 30 | 0.030 | 1950 |
| 6 | LQW15AN3N8B80 | 10 | 3.8nH | ±0.1nH | 35 | 0.030 | 1950 |
| 7 | LQW15AN3N9B80 | 10 | 3.9nH | ±0.1nH | 35 | 0.030 | 1950 |
| 8 | LQW15AN4N0B80 | 10 | 4.0nH | ±0.1nH | 30 | 0.030 | 1950 |
| 9 | LQW15AN5N1B80 | 10 | 5.1nH | ±0.1nH | 35 | 0.040 | 1770 |
| 10 | LQW15AN5N2B80 | 10 | 5.2nH | ±0.1nH | 35 | 0.040 | 1770 |
| 11 | LQW15AN5N4B80 | 10 | 5.4nH | ±0.1nH | 35 | 0.040 | 1770 |
| 12 | LQW15AN5N6B80 | 10 | 5.6nH | ±0.1nH | 35 | 0.040 | 1770 |
| 13 | LQW15AN5N7B80 | 10 | 5.7nH | ±0.1nH | 30 | 0.040 | 1770 |
| 14 | LQW15AN5N8B80 | 10 | 5.8nH | ±0.1nH | 30 | 0.040 | 1770 |
| 15 | LQW15AN7N4G80 | 10 | 7.4nH | ±2% | 30 | 0.050 | 1700 |
| 16 | LQW15AN7N5G80 | 10 | 7.5nH | ±2% | 35 | 0.050 | 1700 |
| 17 | LQW15AN7N6G80 | 10 | 7.6nH | ±2% | 30 | 0.050 | 1700 |
| 18 | LQW15AN7N7G80 | 10 | 7.7nH | ±2% | 30 | 0.050 | 1700 |
| 19 | LQW15AN7N8G80 | 10 | 7.8nH | ±2% | 30 | 0.050 | 1700 |
| 20 | LQW15AN8N0G80 | 10 | 8.0nH | ±2% | 30 | 0.050 | 1700 |
| 21 | LQW15AN13NG80 | 10 | 13nH | ±2% | 30 | 0.093 | 1240 |
| 22 | LQW15AN27NG80 | 10 | 27nH | ±2% | 30 | 0.288 | 680 |
| 23 | LQW15AN33NG80 | 10 | 33nH | ±2% | 30 | 0.336 | 620 |
| 24 | LQW15AN43NG80 | 10 | 43nH | ±2% | 30 | 0.516 | 515 |

Continued on the following page.

Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 25 | LQW15AN53NG80 | 10 | 53nH | ±2% | 25 | 0.696 | 415 |
| 26 | LQW15AN75NG80 | 10 | 75nH | ±2% | 25 | 1.224 | 320 |

●EKLQW18A-KIT (RF Inductors Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQW18AN3N6C00 | 10 | 3.6nH | ±0.2nH | 25 | 0.059 | 850 |
| 2 | LQW18AN3N9C00 | 10 | 3.9nH | ±0.2nH | 35 | 0.059 | 850 |
| 3 | LQW18AN4N3C00 | 10 | 4.3nH | ±0.2nH | 35 | 0.059 | 850 |
| 4 | LQW18AN5N6C00 | 10 | 5.6nH | ±0.2nH | 35 | 0.082 | 750 |
| 5 | LQW18AN6N2C00 | 10 | 6.2nH | ±0.2nH | 35 | 0.082 | 750 |
| 6 | LQW18AN6N8C00 | 10 | 6.8nH | ±0.2nH | 35 | 0.082 | 750 |
| 7 | LQW18AN10NG00 | 10 | 10nH | ±2% | 35 | 0.11 | 650 |
| 8 | LQW18AN11NG00 | 10 | 11nH | ±2% | 35 | 0.11 | 650 |
| 9 | LQW18AN12NG00 | 10 | 12nH | ±2% | 35 | 0.13 | 600 |
| 10 | LQW18AN13NG00 | 10 | 13nH | ±2% | 35 | 0.13 | 600 |
| 11 | LQW18AN15NG00 | 10 | 15nH | ±2% | 40 | 0.13 | 600 |
| 12 | LQW18AN16NG00 | 10 | 16nH | ±2% | 40 | 0.16 | 550 |
| 13 | LQW18AN18NG00 | 10 | 18nH | ±2% | 40 | 0.16 | 550 |
| 14 | LQW18AN20NG00 | 10 | 20nH | ±2% | 40 | 0.16 | 550 |
| 15 | LQW18AN22NG00 | 10 | 22nH | ±2% | 40 | 0.17 | 500 |
| 16 | LQW18AN24NG00 | 10 | 24nH | ±2% | 40 | 0.21 | 500 |
| 17 | LQW18AN27NG00 | 10 | 27nH | ±2% | 40 | 0.21 | 440 |
| 18 | LQW18AN30NG00 | 10 | 30nH | ±2% | 40 | 0.23 | 420 |
| 19 | LQW18AN33NG00 | 10 | 33nH | ±2% | 40 | 0.23 | 420 |
| 20 | LQW18AN36NG00 | 10 | 36nH | ±2% | 40 | 0.26 | 400 |
| 21 | LQW18AN39NG00 | 10 | 39nH | ±2% | 40 | 0.26 | 400 |
| 22 | LQW18AN43NG00 | 10 | 43nH | ±2% | 40 | 0.29 | 380 |
| 23 | LQW18AN47NG00 | 10 | 47nH | ±2% | 38 | 0.29 | 380 |
| 24 | LQW18AN51NG00 | 10 | 51nH | ±2% | 38 | 0.33 | 370 |
| 25 | LQW18AN56NG00 | 10 | 56nH | ±2% | 38 | 0.35 | 360 |
| 26 | LQW18AN62NG00 | 10 | 62nH | ±2% | 38 | 0.51 | 280 |
| 27 | LQW18AN68NG00 | 10 | 68nH | ±2% | 38 | 0.38 | 340 |
| 28 | LQW18AN72NG00 | 10 | 72nH | ±2% | 34 | 0.56 | 270 |
| 29 | LQW18AN75NG00 | 10 | 75nH | ±2% | 34 | 0.56 | 270 |
| 30 | LQW18AN82NG00 | 10 | 82nH | ±2% | 34 | 0.60 | 250 |
| 31 | LQW18AN91NG00 | 10 | 91nH | ±2% | 34 | 0.64 | 230 |
| 32 | LQW18ANR10G00 | 10 | 100nH | ±2% | 34 | 0.68 | 220 |
| 33 | LQW18ANR11G00 | 10 | 110nH | ±2% | 32 | 1.2 | 200 |
| 34 | LQW18ANR12G00 | 10 | 120nH | ±2% | 32 | 1.3 | 180 |
| 35 | LQW18ANR13G00 | 10 | 130nH | ±2% | 32 | 1.4 | 170 |
| 36 | LQW18ANR15G00 | 10 | 150nH | ±2% | 32 | 1.5 | 160 |
| 37 | LQW18ANR16G00 | 10 | 160nH | ±2% | 32 | 2.1 | 150 |
| 38 | LQW18ANR18G00 | 10 | 180nH | ±2% | 25 | 2.2 | 140 |
| 39 | LQW18ANR20G00 | 10 | 200nH | ±2% | 25 | 2.4 | 120 |
| 40 | LQW18ANR22G00 | 10 | 220nH | ±2% | 25 | 2.5 | 120 |
| 41 | LQW18ANR27G00 | 10 | 270nH | ±2% | 30 | 3.4 | 110 |
| 42 | LQW18ANR33G00 | 10 | 330nH | ±2% | 30 | 5.5 | 85 |
| 43 | LQW18ANR39G00 | 10 | 390nH | ±2% | 30 | 6.2 | 80 |
| 44 | LQW18ANR47G00 | 10 | 470nH | ±2% | 30 | 7.0 | 75 |
| 45 | LQW18AN3N9C10 | 10 | 3.9nH | ±0.2nH | 38 | 0.032 | 1000 |
| 46 | LQW18AN6N8C10 | 10 | 6.8nH | ±0.2nH | 38 | 0.045 | 900 |
| 47 | LQW18AN10NG10 | 10 | 10nH | ±2% | 38 | 0.058 | 800 |
| 48 | LQW18AN12NG10 | 10 | 12nH | ±2% | 38 | 0.071 | 750 |
| 49 | LQW18AN18NG10 | 10 | 18nH | ±2% | 42 | 0.085 | 700 |
| 50 | LQW18AN22NG10 | 10 | 22nH | ±2% | 42 | 0.099 | 640 |
| 51 | LQW18AN27NG10 | 10 | 27nH | ±2% | 42 | 0.116 | 590 |

●EKLQ80GB-KIT (RF Inductors Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQW18AN4N3B80 | 10 | 4.3nH | ±0.1nH | 35 | 0.036 | 2100 |
| 2 | LQW18AN4N7B80 | 10 | 4.7nH | ±0.1nH | 25 | 0.054 | 1500 |
| 3 | LQW18AN4N9B80 | 10 | 4.9nH | ±0.1nH | 23 | 0.081 | 1200 |
| 4 | LQW18AN30NG80 | 10 | 30nH | ±2% | 40 | 0.12 | 1100 |

Continued on the following page.

Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 5 | LQW18AN36NG80 | 10 | 36nH | ±2% | 37 | 0.2 | 910 |
| 6 | LQW18AN39NG80 | 10 | 39nH | ±2% | 40 | 0.16 | 1000 |
| 7 | LQW18AN43NG80 | 10 | 43nH | ±2% | 40 | 0.21 | 840 |
| 8 | LQW18AN47NG80 | 10 | 47nH | ±2% | 32 | 0.23 | 830 |
| 9 | LQW18AN51NG80 | 10 | 51nH | ±2% | 32 | 0.23 | 830 |
| 10 | LQW18AN56NG80 | 10 | 56nH | ±2% | 38 | 0.26 | 770 |
| 11 | LQW18AN68NG80 | 10 | 68nH | ±2% | 37 | 0.38 | 630 |
| 12 | LQW18AN72NG80 | 10 | 72nH | ±2% | 34 | 0.47 | 560 |
| 13 | LQW18AN75NG80 | 10 | 75nH | ±2% | 28 | 0.41 | 590 |
| 14 | LQW18AN82NG80 | 10 | 82nH | ±2% | 34 | 0.5 | 550 |
| 15 | LQW18AN91NG80 | 10 | 91nH | ±2% | 33 | 0.54 | 520 |
| 16 | LQW18ANR10G80 | 10 | 100nH | ±2% | 34 | 0.63 | 490 |
| 17 | LQW18ANR11G80 | 10 | 110nH | ±2% | 32 | 0.7 | 450 |
| 18 | LQW18ANR12G80 | 10 | 120nH | ±2% | 32 | 0.72 | 450 |
| 19 | LQW18ANR15G80 | 10 | 150nH | ±2% | 28 | 0.87 | 420 |
| 20 | LQW18ANR18G80 | 10 | 180nH | ±2% | 25 | 1.65 | 310 |
| 21 | LQW18ANR20G80 | 10 | 200nH | ±2% | 25 | 1.74 | 290 |
| 22 | LQW18ANR21G80 | 10 | 210nH | ±2% | 27 | 1.98 | 280 |
| 23 | LQW18ANR22G80 | 10 | 220nH | ±2% | 25 | 2.08 | 280 |
| 24 | LQW18ANR25G80 | 10 | 250nH | ±2% | 24 | 2.28 | 250 |
| 25 | LQW18ANR27G80 | 10 | 270nH | ±2% | 24 | 2.42 | 260 |
| 26 | LQW18ANR30G80 | 10 | 300nH | ±2% | 25 | 3.12 | 220 |
| 27 | LQW18ANR33G80 | 10 | 330nH | ±2% | 25 | 3.84 | 190 |
| 28 | LQW18ANR36G80 | 10 | 360nH | ±2% | 25 | 3.98 | 190 |
| 29 | LQW18ANR39G80 | 10 | 390nH | ±2% | 25 | 4.23 | 190 |

●EKLQW21A-KIT (RF Inductors Wire Wound Ferrite Core Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQW21HNR47J00 | 10 | 0.47μH | ±5% | 35 | 1.30 | 160 |
| 2 | LQW21HNR56J00 | 10 | 0.56μH | ±5% | 35 | 1.43 | 150 |
| 3 | LQW21HNR68J00 | 10 | 0.68μH | ±5% | 35 | 2.21 | 130 |
| 4 | LQW21HNR82J00 | 10 | 0.82μH | ±5% | 35 | 2.34 | 125 |
| 5 | LQW21HN1R0J00 | 10 | 1.0μH | ±5% | 35 | 2.86 | 115 |
| 6 | LQW21HN1R2J00 | 10 | 1.2μH | ±5% | 35 | 3.12 | 100 |
| 7 | LQW21HN1R5J00 | 10 | 1.5μH | ±5% | 35 | 5.33 | 85 |
| 8 | LQW21HN1R8J00 | 10 | 1.8μH | ±5% | 35 | 5.85 | 80 |
| 9 | LQW21HN2R2J00 | 10 | 2.2μH | ±5% | 35 | 6.50 | 75 |

●EKLQW2BC-KIT (RF Inductors Wire Wound Air Core Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQW2BHN2N7D13 | 10 | 2.7nH | ±0.5nH | 20 | 0.02 | 1900 |
| 2 | LQW2BHN3N1D13 | 10 | 3.1nH | ±0.5nH | 20 | 0.02 | 1800 |
| 3 | LQW2BHN3N3D13 | 10 | 3.3nH | ±0.5nH | 20 | 0.02 | 1700 |
| 4 | LQW2BHN5N6D13 | 10 | 5.6nH | ±0.5nH | 35 | 0.02 | 1500 |
| 5 | LQW2BHN6N8D13 | 10 | 6.8nH | ±0.5nH | 35 | 0.02 | 1400 |
| 6 | LQW2BHN8N6D13 | 10 | 8.6nH | ±0.5nH | 35 | 0.03 | 1300 |
| 7 | LQW2BHN10NJ13 | 10 | 10nH | ±5% | 35 | 0.03 | 1320 |
| 8 | LQW2BHN12NK13 | 10 | 12nH | ±10% | 40 | 0.04 | 1100 |
| 9 | LQW2BHN15NK13 | 10 | 15nH | ±10% | 40 | 0.04 | 1000 |
| 10 | LQW2BHN18NK13 | 10 | 18.8nH | ±10% | 40 | 0.05 | 1000 |
| 11 | LQW2BHN21NK13 | 10 | 21nH | ±10% | 40 | 0.05 | 950 |
| 12 | LQW2BHN27NK13 | 10 | 27nH | ±10% | 40 | 0.06 | 900 |
| 13 | LQW2BHN33NG03 | 10 | 33nH | ±2% | 40 | 0.15 | 570 |
| 14 | LQW2BHN39NG03 | 10 | 39nH | ±2% | 40 | 0.09 | 730 |
| 15 | LQW2BHN47NG03 | 10 | 47nH | ±2% | 40 | 0.23 | 450 |
| 16 | LQW2BHN56NG03 | 10 | 56nH | ±2% | 40 | 0.26 | 430 |
| 17 | LQW2BHN68NG03 | 10 | 68nH | ±2% | 40 | 0.23 | 460 |
| 18 | LQW2BHN82NG03 | 10 | 82nH | ±2% | 40 | 0.42 | 320 |
| 19 | LQW2BHNR10G03 | 10 | 100nH | ±2% | 35 | 0.55 | 270 |
| 20 | LQW2BHNR12G03 | 10 | 120nH | ±2% | 40 | 0.40 | 320 |
| 21 | LQW2BHNR15G03 | 10 | 150nH | ±2% | 30 | 0.68 | 260 |
| 22 | LQW2BHNR18G03 | 10 | 180nH | ±2% | 35 | 0.71 | 250 |
| 23 | LQW2BHNR22G03 | 10 | 220nH | ±2% | 35 | 0.70 | 240 |

Continued on the following page. ↗

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 24 | LQW2BHNR27K03 | 10 | 270nH | ±10% | 15 | 2.00 | 190 |
| 25 | LQW2BHNR33K03 | 10 | 330nH | ±10% | 15 | 2.20 | 180 |
| 26 | LQW2BHNR39K03 | 10 | 390nH | ±10% | 15 | 2.50 | 170 |
| 27 | LQW2BHNR47K03 | 10 | 470nH | ±10% | 15 | 2.80 | 160 |

●EKLW2BUB-KIT (RF Inductors Wire Wound Type)

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 1 | LQW2BAS2N8J00 | 10 | 2.8nH | ±5% | 80 | 0.06 | 800 |
| 2 | LQW2BAS3N0J00 | 10 | 3nH | ±5% | 65 | 0.06 | 800 |
| 3 | LQW2BAS5N6J00 | 10 | 5.6nH | ±5% | 65 | 0.08 | 600 |
| 4 | LQW2BAS6N8J00 | 10 | 6.8nH | ±5% | 50 | 0.11 | 600 |
| 5 | LQW2BAS7N5J00 | 10 | 7.5nH | ±5% | 50 | 0.14 | 600 |
| 6 | LQW2BAS8N2J00 | 10 | 8.2nH | ±5% | 50 | 0.12 | 600 |
| 7 | LQW2BAS10NJ00 | 10 | 10nH | ±5% | 60 | 0.10 | 600 |
| 8 | LQW2BAS12NJ00 | 10 | 12nH | ±5% | 50 | 0.15 | 600 |
| 9 | LQW2BAS15NJ00 | 10 | 15nH | ±5% | 50 | 0.17 | 600 |
| 10 | LQW2BAS18NJ00 | 10 | 18nH | ±5% | 50 | 0.20 | 600 |
| 11 | LQW2BAS22NJ00 | 10 | 22nH | ±5% | 55 | 0.22 | 500 |
| 12 | LQW2BAS24NJ00 | 10 | 24nH | ±5% | 50 | 0.22 | 500 |
| 13 | LQW2BAS27NJ00 | 10 | 27nH | ±5% | 55 | 0.25 | 500 |
| 14 | LQW2BAS33NG00 | 10 | 33nH | ±2% | 60 | 0.27 | 500 |
| 15 | LQW2BAS36NG00 | 10 | 36nH | ±2% | 55 | 0.27 | 500 |
| 16 | LQW2BAS39NG00 | 10 | 39nH | ±2% | 60 | 0.29 | 500 |
| 17 | LQW2BAS43NG00 | 10 | 43nH | ±2% | 60 | 0.34 | 500 |
| 18 | LQW2BAS47NG00 | 10 | 47nH | ±2% | 60 | 0.31 | 500 |
| 19 | LQW2BAS56NG00 | 10 | 56nH | ±2% | 60 | 0.34 | 500 |
| 20 | LQW2BAS68NG00 | 10 | 68nH | ±2% | 60 | 0.38 | 500 |
| 21 | LQW2BAS82NG00 | 10 | 82nH | ±2% | 65 | 0.42 | 400 |
| 22 | LQW2BAS91NG00 | 10 | 91nH | ±2% | 65 | 0.48 | 400 |
| 23 | LQW2BASR10G00 | 10 | 100nH | ±2% | 65 | 0.46 | 400 |
| 24 | LQW2BASR11G00 | 10 | 110nH | ±2% | 50 | 0.48 | 400 |
| 25 | LQW2BASR12G00 | 10 | 120nH | ±2% | 50 | 0.51 | 400 |
| 26 | LQW2BASR15G00 | 10 | 150nH | ±2% | 50 | 0.56 | 400 |
| 27 | LQW2BASR18G00 | 10 | 180nH | ±2% | 50 | 0.64 | 400 |
| 28 | LQW2BASR22G00 | 10 | 220nH | ±2% | 50 | 0.70 | 400 |
| 29 | LQW2BASR24G00 | 10 | 240nH | ±2% | 44 | 1.00 | 350 |
| 30 | LQW2BASR27G00 | 10 | 270nH | ±2% | 48 | 1.00 | 350 |
| 31 | LQW2BASR33G00 | 10 | 330nH | ±2% | 48 | 1.40 | 310 |
| 32 | LQW2BASR39J00 | 10 | 390nH | ±5% | 48 | 1.50 | 290 |
| 33 | LQW2BASR47J00 | 10 | 470nH | ±5% | 33 | 1.76 | 250 |
| 34 | LQW2BASR56J00 | 10 | 560nH | ±5% | 23 | 1.90 | 230 |
| 35 | LQW2BASR68J00 | 10 | 680nH | ±5% | 23 | 2.20 | 190 |
| 36 | LQW2BASR82J00 | 10 | 820nH | ±5% | 23 | 2.35 | 180 |
| 37 | LQW2UAS12NG00 | 10 | 12nH | ±2% | 50 | 0.09 | 1000 |
| 38 | LQW2UAS18NG00 | 10 | 18nH | ±2% | 50 | 0.11 | 1000 |
| 39 | LQW2UAS22NG00 | 10 | 22nH | ±2% | 55 | 0.12 | 1000 |
| 40 | LQW2UAS27NG00 | 10 | 27nH | ±2% | 55 | 0.13 | 1000 |
| 41 | LQW2UAS33NG00 | 10 | 33nH | ±2% | 60 | 0.14 | 1000 |
| 42 | LQW2UAS39NG00 | 10 | 39nH | ±2% | 60 | 0.15 | 1000 |
| 43 | LQW2UAS47NG00 | 10 | 47nH | ±2% | 65 | 0.16 | 1000 |
| 44 | LQW2UAS56NG00 | 10 | 56nH | ±2% | 65 | 0.18 | 1000 |
| 45 | LQW2UAS68NG00 | 10 | 68nH | ±2% | 65 | 0.2 | 1000 |
| 46 | LQW2UAS82NG00 | 10 | 82nH | ±2% | 60 | 0.22 | 1000 |
| 47 | LQW2UASR10G00 | 10 | 100nH | ±2% | 60 | 0.56 | 650 |
| 48 | LQW2UASR12G00 | 10 | 120nH | ±2% | 60 | 0.63 | 650 |
| 49 | LQW2UASR15G00 | 10 | 150nH | ±2% | 45 | 0.7 | 580 |
| 50 | LQW2UASR18G00 | 10 | 180nH | ±2% | 45 | 0.77 | 620 |
| 51 | LQW2UASR22G00 | 10 | 220nH | ±2% | 45 | 0.84 | 500 |
| 52 | LQW2UASR27G00 | 10 | 270nH | ±2% | 45 | 0.91 | 500 |
| 53 | LQW2UASR33G00 | 10 | 330nH | ±2% | 45 | 1.05 | 450 |
| 54 | LQW2UASR39G00 | 10 | 390nH | ±2% | 45 | 1.12 | 470 |
| 55 | LQW2UASR47G00 | 10 | 470nH | ±2% | 45 | 1.19 | 470 |
| 56 | LQW2UASR56G00 | 10 | 560nH | ±2% | 45 | 1.33 | 400 |
| 57 | LQW2UASR62G00 | 10 | 620nH | ±2% | 45 | 1.4 | 300 |

Continued on the following page.

Note • Please read rating and CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

| No. | Part Number | Quantity (pcs.) | Inductance | | Q (min.) | DC Resistance (Ω) max. | Rated Current (mA) |
|-----|---------------|-----------------|------------|-----------|----------|---------------------------------|--------------------|
| | | | Nominal | Tolerance | | | |
| 58 | LQW2UASR68G00 | 10 | 680nH | $\pm 2\%$ | 45 | 1.47 | 400 |
| 59 | LQW2UASR75G00 | 10 | 750nH | $\pm 2\%$ | 45 | 1.54 | 360 |
| 60 | LQW2UASR82G00 | 10 | 820nH | $\pm 2\%$ | 45 | 1.61 | 400 |
| 61 | LQW2UASR91G00 | 10 | 910nH | $\pm 2\%$ | 35 | 1.68 | 380 |
| 62 | LQW2UAS1R0G00 | 10 | 1000nH | $\pm 2\%$ | 35 | 1.75 | 370 |
| 63 | LQW2UAS1R2J00 | 10 | 1200nH | $\pm 5\%$ | 35 | 2.0 | 310 |
| 64 | LQW2UAS1R5J00 | 10 | 1500nH | $\pm 5\%$ | 28 | 2.3 | 330 |
| 65 | LQW2UAS1R8J00 | 10 | 1800nH | $\pm 5\%$ | 28 | 2.6 | 300 |
| 66 | LQW2UAS2R2J00 | 10 | 2200nH | $\pm 5\%$ | 28 | 2.8 | 280 |
| 67 | LQW2UAS2R7J00 | 10 | 2700nH | $\pm 5\%$ | 22 | 3.2 | 290 |
| 68 | LQW2UAS3R3J00 | 10 | 3300nH | $\pm 5\%$ | 22 | 3.4 | 290 |
| 69 | LQW2UAS3R9J00 | 10 | 3900nH | $\pm 5\%$ | 20 | 3.6 | 260 |
| 70 | LQW2UAS4R7J00 | 10 | 4700nH | $\pm 5\%$ | 20 | 4.0 | 260 |

\triangle Note • Please read rating and \triangle CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



Inductors for Power Lines

| | | |
|---------|-------|------|
| LQH2HPN | | p.46 |
| LQH2MCN | | p.42 |
| LQH31CN | | p.90 |
| LQH32CN | | p.91 |
| LQH32PB | | p.65 |
| LQH32PN | | p.61 |
| LQH3NPN | | p.59 |
| LQH43CN | | p.94 |
| LQH43PB | | p.71 |
| LQH43PN | | p.69 |
| LQH44PN | | p.75 |
| LQH55DN | | p.96 |
| LQH5BPB | | p.79 |
| LQH5BPN | | p.77 |
| LQH66SN | | p.98 |
| LQM18FN | | p.81 |
| LQM18PN | | p.16 |
| LQM21DN | | p.82 |
| LQM21FN | | p.83 |
| LQM21PN | | p.22 |
| LQM2HPN | | p.38 |
| LQM2MPN | | p.27 |
| LQM31PN | | p.39 |
| LQM32PN | | p.41 |
| LQW15CN | | p.86 |
| LQW18CN | | p.89 |

Inductors for General Use

| | | |
|---------|-------|-------|
| LQB15NN | | p.119 |
| LQB18NN | | p.121 |
| LQH31MN | | p.127 |
| LQH32MN | | p.129 |
| LQH43MN | | p.131 |
| LQH43NN | | p.131 |
| LQH44NN | | p.134 |
| LQM18NN | | p.123 |
| LQM21NN | | p.125 |

RF Inductors

| | | |
|---------|-------|-------|
| LQG15HN | | p.148 |
| LQG15HS | | p.150 |
| LQG18HN | | p.153 |
| LQH31HN | | p.223 |
| LQP02TN | | p.155 |
| LQP02TQ | | p.161 |
| LQP03TG | | p.164 |
| LQP03TN | | p.169 |
| LQP15MN | | p.174 |
| LQP18MN | | p.177 |
| LQW03AW | | p.179 |
| LQW04AN | | p.181 |
| LQW15AN | | p.184 |
| LQW18AN | | p.199 |
| LQW21HN | | p.221 |
| LQW2BAS | | p.213 |
| LQW2BHN | | p.209 |
| LQW2UAS | | p.216 |
| LQW31HN | | p.219 |

Introduction of Chip Inductors Web Site



Please check out Murata's newsletter!
 Have fun while learning about electronic components.
http://www.murata.com/products/emicon_fun/

EMICON-FUN! is disseminated widely from basics (principles, characteristics, mounting, etc.) of capacitors, EMI suppression filters and inductors to information that can be used practically.
 Updated information is also distributed via the mail magazine.

Click here to register as reader → <https://fofa.jp/murata/a.p/107/>

You can register from Murata Manufacturing Web site page TOP.
<http://www.murata.com/products/>



← This banner is the entrance of register form

△Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Products Information

Chip Inductors product information page has been drastically updated.

inductor murata Search <http://www.murata.com/products/inductor/>

- ▶ **Point 1**
The product search engine has been replaced by powerful one!
- ▶ **Point 2**
New contents such as inductors selection guide, products recommendation for each application has been added.
- ▶ **Point 3**
Inductors are classified into high frequency inductors and power inductors.

Search for Inductors (for high frequency, power lines, general purpose)

- 1 Search in the lineups
Search product in product series lineup list.
- 2 Search by specifications
Search product with specifications such as inductance value, rated current or dimension.
- 3 Search by competitor's part number
Search Murata's alternative product specifying other vender's part numbers.
- 4 Search by part number
Search product specifying Murata's part numbers.

You can see product data from various viewpoint

The top page is divided.

- Explain about inductors from basic to practice
- Design assistance tools such as characteristics viewers and simulation libraries
- Frequently Asked Questions (FAQ)
- Shows selection guides of Murata inductors, recommended products to each application.

You can make inquiry or download catalogs from here.

△Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

△Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

⚠ Note:

1. Export Control

<For customers outside Japan>

No Murata products should be used or sold, through any channels, for use in the design, development, production, utilization, maintenance or operation of, or otherwise contribution to (1) any weapons (Weapons of Mass Destruction [nuclear, chemical or biological weapons or missiles] or conventional weapons) or (2) goods or systems specially designed or intended for military end-use or utilization by military end-users.

<For customers in Japan>

For products which are controlled items subject to the "Foreign Exchange and Foreign Trade Law" of Japan, the export license specified by the law is required for export.

2. Please contact our sales representatives or product engineers before using the products in this catalog for the applications listed below, which require especially high reliability for the prevention of defects which might directly damage a third party's life, body or property, or when one of our products is intended for use in applications other than those specified in this catalog.

- | | |
|-----------------------------|--|
| ① Aircraft equipment | ② Aerospace equipment |
| ③ Undersea equipment | ④ Power plant equipment |
| ⑤ Medical equipment | ⑥ Transportation equipment (vehicles, trains, ships, etc.) |
| ⑦ Traffic signal equipment | ⑧ Disaster prevention / crime prevention equipment |
| ⑨ Data-processing equipment | ⑩ Application of similar complexity and/or reliability requirements to the applications listed above |

3. Product specifications in this catalog are as of September 2013. They are subject to change or our products in it may be discontinued without advance notice.

Please check with our sales representatives or product engineers before ordering. If there are any questions, please contact our sales representatives or product engineers.

4. Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.

5. This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

6. Please note that unless otherwise specified, we shall assume no responsibility whatsoever for any conflict or dispute that may occur in connection with the effect of our and/or a third party's intellectual property rights and other related rights in consideration of your use of our products and/or information described or contained in our catalogs. In this connection, no representation shall be made to the effect that any third parties are authorized to use the rights mentioned above under licenses without our consent.

7. No ozone depleting substances (ODS) under the Montreal Protocol are used in our manufacturing process.



<http://www.murata.com/>

Head Office

1-10-1, Higashi Kotari, Nagaokakyo-shi, Kyoto 617-8555, Japan
Phone: 81-75-951-9111

International Division

3-29-12, Shibuya, Shibuya-ku, Tokyo 150-0002, Japan
Phone: 81-3-5469-6123 Fax: 81-3-5469-6155 E-mail: intl@murata.co.jp

Cat. No. O05E-25