

ACVATIX

Electromotive actuators for valves

SAY..P..



Actuators with 15 mm stroke and 200 N force

- SAY31P03 operating voltage AC 230 V, positioning signal 3-position
- SAY61P03 operating voltage AC/DC 24 V, positioning signal 0...10 V, 4...20 mA with position feedback, forced control, characteristic changeover
- SAY61P03/MO operating voltage AC/DC 24 V
RS-485 for Modbus RTU communication
- SAY81P03 Operating voltage AC/DC 24 V, positioning sign 3-position
- For direct mounting on valves; no adjustments required
- Manual adjuster, position and status indication (LED)
- Optional functional extension with auxiliary switch

Application

Electromotive actuators to operate Siemens combi valves for type series VPI46.40F9.5Q and VPI46.50F12Q with 15 mm stroke, as control valves on ventilation, air conditioning, district heating and refrigeration plants.

Features

Function	Description	Type
3-position control	A 3-position signal controls the actuator via connection terminals Y1 or Y2. The desired position is transmitted to the valve.	SAY31P03, SAY81P03
Modulating control	The positioning signal range (DC 0...10 V / DC 4...20 mA / 0...1000 Ω) corresponds to the positioning range (closed...open, or 0...100% stroke) in a linear manner.	SAY61P03
Positioning signal and characteristic changeover	Setting with DIL switch. Factory setting: <ul style="list-style-type: none">• Characteristic curve: log = Equal percentage (switch set to Off)• Positioning signal: DC 0...10 V (switch set to Off)	
Position feedback U	Signal returned to acquire the position via input.	
Forced control (Z-mode)	Forced control helps override automatic mode and is implemented via higher control.	SAY61P03, SAY61P03/MO
Calibration	Carry out during initial commissioning. The actuator drives to the top or bottom end position; the measured values are saved.	
Valve seat detection	The actuators have power-dependent seat detection. After calibration, the exact valve stroke is stored in the actuator's memory.	
Foreign body detection	After clogging is detected, three attempts are made to get past clogging. If unsuccessful, the actuator continues to follow the positioning signal only within a limited range, and the LED flashes red.	
Modbus RTU (RS-485), not galvanically isolated	Setpoint 0...100 % valve setting Actual value 0..100% for valve position Override control Open / Close / Min / Max / Stop Setpoint monitoring and backup mode	SAY61P03/MO

Type summary

Type	Item NO.	Stroke	Positioning force	Operating voltage	Positioning signal	Spring return time	Positioning time	LED	Manual adjustment	Comment
SAY31P03 ¹⁾	S55150-A132	15 mm	200 N	AC 230 V	3-pos.	-	30 s	-	Push and fix	3)
SAY61P03 ²⁾	S55150-A133			AC 24 V DC 24 V	DC ...10 V DC 4...20 mA 0...1000 Ω			yes		4)6)
SAY61P03/MO ²⁾	S55150-A145				Modbus RTU					5)
SAY81P03 ²⁾	S55150-A134				3-pos.			-		6)

¹⁾ Approbation: CE

²⁾ Approvals: CE, UL

³⁾ Optional accessories: Auxiliary switch

⁴⁾ Position feedback, forced control, characteristic changeover

⁵⁾ Position feedback, forced control

⁶⁾ Optional accessories: Auxiliary switch, sequence control, control action changeover

Scope of delivery

Actuators, valves and accessories are supplied in individual packs.

Accessories / spare parts

Electrical accessories

Type	Auxiliary switch ASC10.51	Function module AZX61.1
Item NO.	S55845-Z103	S55845-Z107
SAY31P..	Max. 2	Max. 1
SAY61P..		
SAY61P../MO		-
SAY81P..		Max. 1




Mechanical accessory

Type	Weather shield ASK39.1
Item NO.	S55845-Z109

Ordering (example)

Type	Order number	Designation	Number of pieces
SAY81P03	S55150-A134	Actuator	1
ASC10.51	S55845-Z103	Auxiliary switch	1

Spare parts

Product no. / SSN		
8000060843	Housing cover	Screw (valve stem coupling)
		
		U-bracket
		

Device combinations

Valve type		DN	H ₁₀₀ [mm]	$\dot{V}_{min.}$ [l/h]	\dot{V}_{m100} [l/h]	Δp_{min} [kPa]	Data sheet
VPI46.40F9.5Q	S55264-V129	40	15	1370	9500	25	N4855
VPI46.50F12Q	S55264-V130	50		1400	11500	36	

Product documentation

Title	Contents	Document ID
Actuators SAX..., SAY..., SAV..., SAL... for valves	Basic documentation: Detailed information on stroke actuators including Modbus types Stroke actuators for valves with 15/20/40 mm stroke and rotary actuators for butterfly valves	CE1P4040en
Electromotive actuators for valves SA..., Modbus RTU	Datasheet: Modbus communication profiles	A6V101037195
Mounting instructions G..161../MO and S..6/MO	Mounting instructions: Mounting and installation instructions for Modbus actuators	A5W00027551
Valve actuator DIL switch characteristic overview	Commissioning / configuration: Depictions, description of actuator and valve characteristics by DIL switch setting (English)	A6V12050595

Related documents such as the environmental declarations, declarations of conformity, etc., can be downloaded from the following Internet address:

www.siemens.com/bt/download

Safety**⚠ CAUTION****National safety regulations**

Failure to comply with national safety regulations may result in personal injury and property damage.

- Observe national provisions and comply with the appropriate safety regulations.

⚠ WARNING**Risk of burns from hot actuator brackets**

The actuator brackets on heating plants can also become hot from the contact with the hot valve during operation. The temperature of the actuator bracket can reach 100 °C.

When servicing the actuator:

- Switch off both pump and operating voltage.
- Close the main shutoff valve in the piping.
- Allow the piping to cool off.

Engineering**SAY31P03 / SAY81P03**

3-position actuators must be controlled by a controller, see Internal diagrams [► 14].

SAY61P03

Up to 10 actuators can drive in parallel on a controller output with a rating of 1 mA. Modulating actuators have an input impedance of 100 kΩ.


SAY61P03/MO

The Modbus converter is designed for analog control at 0...10 V.



Keep the analog signal setting on the actuator as is (switch 1 to OFF); adjustment not permitted.

Mounting positions






- 1) Requires weather shield ASK39.1 Housing protection class remains IP 54.
- 2) SAY61P../MO is not intended for outdoor use.

When used indoors, the cable must always be routed downwards for horizontal and suspended installation. Otherwise, IP protection is not guaranteed, as water flowing down the cable can penetrate the drive. In outdoor areas, only mount the actuators vertically and not horizontally or suspended.

Operation

Control action


On valves where the stem retracts to the close position, "direct acting" means that the value is fully closed at positioning signal $Y = 0\text{ V}$ or $Z = 0\text{ }\Omega$ (i.e. 100 %).

		Direct acting	
			
		Positioning signal Y	DC 0...10 V, 4...20 mA
		Positioning signal Z	0...1000 Ω
Y, Z	Positioning signal		
V	Volume flow		
	Control action: Direct acting		

Maintenance

Actuators are maintenance-free.

Disposal

	<p>This symbol or any other national label indicate that the product, its packaging, and, where applicable, any batteries may not be disposed of as domestic waste. Delete all personal data and dispose of the item(s) at separate collection and recycling facilities in accordance with local and national legislation.</p> <p>For additional details, refer to Siemens information on disposal.</p>
---	---

Warranty

The application-specific technical data is guaranteed only in combination with the Siemens products listed in the 'Device combinations' section. If third-party products are used, any guarantee provided by Siemens will be invalidated.

Technical data

Power supply		
Operating voltage	SAY31P03	AC 230 V \pm 15 %
	SAY61P03..	AC 24 V \pm 20 % / DC 24 V + 20 % / - 15 % (SELV / PELV)
	SAY81P03	
Frequency		45...65 Hz
External supply line fusing (EU)		<ul style="list-style-type: none"> • Non-renewable fuse 6...10 A slow • Circuit break max. 13 A, tripping characteristic B, C, D to EN 60898 • Power source with current limitation of max. 10 A
Typical switch-on current ¹⁾ (3-position actuators)	SAY31P03	2.3A
	SAY81P03	4.5A

Functional data		
Positioning times (with the specified nominal stroke)	The positioning time may vary depending on the type of valve (Type summary [► 3])	
	SAY31P03, SAY61P03, SAY81P03.	30 s
Positioning force		200 N
Nominal stroke		15 mm
Permissible media temperature (valve fitted)		1...120 °C

Signal Inputs		
Positioning signal "Y"	SAY31P03, SAY81P03	3-pos.
	SAY31P03 voltage	AC 230 V \pm 15 %
	SAY81P03 voltage	AC 24 V \pm 20% / DC 24 V + 20% / - 15%
	SAY61P03 (DC 0...10 V) current draw	\leq 0.1 mA
	Input impedance	\geq 100 k Ω
	SAY61P03 (DC 4...20 mA) current draw	DC 4...20 mA \pm 1%
	Input impedance	\leq 500 Ω

Power consumption at 50 Hz					
Type	Item NO.	Operating [W]	Operating [VA]	Standby [W]	Standby [VA]
SAY31P03	S55150-A132	2.2	4.0	1.3	2.2
SAY61P03	S55150-A133	2.7	6.5	1.7	4.5
SAY61P03/MO	S55150-A145	3.2	7.2	2.2	5.9
SAY81P03	S55150-A134	2.4	4.2	1.5	2.6

Communication		
Communication protocol	Modbus RTU	RS-485, not galvanically isolated
	Number of nodes	Max. 32
	Address range	1...245 / 255
	Factory setting	255
	Transmission formats	1-8-E-1 / 1-8-O-1 / 1-8-N-1 / 1-8-N-2
	Factory setting	1-8-E-1
	Baud rates (kbaud)	Auto / 9.6 / 19.2 / 38.4 / 57.6 / 76.8 / 115.2
	Factory setting	Auto
	Bus termination	120 Ω electronically switchable
	Factory setting	Off

Parallel connection	
SAY61P03	≤ 10 (depending on controller output)

Forced control		
Z positioning signal	SAY61P03	R = 0...1000 Ω , G, G0
	R = 0...1000 Ω	Stroke proportional to R
	Z connected to G	Max. stroke 100 % ²⁾
	Z connected to G0	Max. stroke 0 % ²⁾
	Voltage	Max. AC 24 V \pm 20 %
		Max. DC 24 V + 20 % / - 15 %
	Current draw	≤ 0.1 mA

Position feedback		
Position feedback U	SAY61P03	0...10 V DC
	Load impedance	> 10 k Ω resistive
	Load	Max. 1 mA

Connection cable		
Wire cross-sectional areas		0.75...1.5 mm ² , AWG 20. 16 ³⁾
Cable entries	SAY..P..	<ul style="list-style-type: none"> 2 entries Ø 20.5 mm (for M20) 1 entry Ø 25.5 mm (for M25)
	SAY61P../MO	Fixed connection cable 0.9m
		Number of cores 5 x 0.75 mm ²

Degree of protection and class		
Housing from vertical to horizontal		IP 54 as per EN 60529 ⁴⁾
Protection class as per EN 60730	SAY31P03 AC 230 V	II
	SAY61P03 AC / DC 24 V	III
	SAY81P03 AC / DC 24 V	

Environmental conditions		
Operation per IEC 60721-3-3	Climatic conditions	Class 3K5
	Mounting location	Indoors (weather-protected) ⁴⁾
	Temperature, general	-5...55 °C
	Humidity (non-condensing)	5...95 % r.h.
Transport per IEC 60721-3-2	Climatic conditions	Class 2K3
	Temperature	-25...70 °C
	Humidity	< 95 % r.h.
Storage per IEC 60721-3-1	Climatic conditions	Class 1K3
	Temperature	-15...55 °C
	Humidity	5...95 % r.h.
Max. media temperature when mounted on valve		120 °C

Directives and standards		
Product standard		EN 60730-x
Electromagnetic compatibility (field of use)		For residential, commercial, and industrial environments
EU conformity (CE)		See EU declaration of conformity A5W00000333 ⁵⁾
UK conformity (UKCA)		See UK declaration of conformity A5W00198022A-001 ⁵⁾
RCM compliance	AC 230 V	See RCM declaration of conformity A5W00000334 ⁵⁾
EAC compliance		Eurasian compliance for all SAY..P..
UL, cUL	AC 230 V	-
	AC / DC 24 V	UL 873 http://ul.com/database ; File number E35198

Environmental compatibility

Product environmental declarations 71 7331 0559 ⁵⁾ and A6V101083254 ⁵⁾ include data on environmentally friendly product design and testing (RoHS compliance, material composition, packaging, environmental benefits, disposal).

Dimensions

See Dimensions [► 16]

Accessories ⁶⁾

Auxiliary switch ASC10.51	Switching capacity	AC 24...230 V, 6 (2) A, potential free
External fusing of supply line		<ul style="list-style-type: none">• Non-renewable fuse 6...10 A slow• Circuit break max. 13 A, tripping characteristic B, C, D to EN 60898• Power source with current limitation of max. 10 A
US installation, UL & cUL		AC 24 V class 2, 5 A general purpose


¹⁾ Switching time for RMS value of the sine wave at nominal voltage




²⁾ Observe acting direction of DIL switches

³⁾ AWG = American wire gauge

⁴⁾ For outdoor operation, always use weather shield ASK39.1, housing protection class IP 54 remains as is. SAY61../MO is not intended for outdoor use.

⁵⁾ Documents can be downloaded at <http://www.siemens.com/bt/download>

⁶⁾ UL-approved components 



SAY31P03

	AC 230 V	3-pos.
N —	System neutral (SN)	
Y1 —	Positioning signal (actuator's stem retracts)	
Y2 —	Positioning signal (actuator's stem extends)	

SAY61P03

	AC / DC 24 V	DC 0...10 V 4...20 mA 0...1000 Ω
G0 —	System neutral (SN)	
G —	System potential (SP)	
Y —	Positioning signal for DC 0...10 V / 4...20 mA	
M —	Measuring neutral	
U —	Position feedback DC 0...10 V - (System neutral is measuring ground M)	
Z —	Control signal forced control	


SAY61P03/MO

	AC / DC 24 V	Modbus RTU connecting cable
G0 —	System neutral (SN)	black
G —	System potential (SP) AC 24 V / DC 24 V	red
REF —	Reference line (Modbus RTU)	purple
+ —	Bus + (Modbus RTU)	gray
- —	Bus - (Modbus RTU)	pink


SAY81P03

	AC / DC 24 V	3-pos.
G —	System potential (SP)	
Y1 —	Positioning signal (actuator's stem retracts)	
Y2 —	Positioning signal (actuator's stem extends)	


SAY31P03




SAY61P03




SAY61P03/MO




SAY81P03



Actuator




4040M01_02

Type	A	B	C	C1	C2	D	E	▶	▶▶	
	[mm]									[kg]
SAY..P..	242	124	150	68	82	80	100	100	200	1.780
SAY61P03/MO ¹⁾										1.930
With ASK39.1	267	154	300	200	100	-				2.010

¹⁾ Device has fixed connection cable – left cable entry occupied

External Modbus converter



Dimensions in mm

Type	X	kg
	[mm]	[kg]
SAY61P03/MO	250	0.15 ¹⁾

¹⁾ Included in total weight.

Revision numbers

Type	Valid from rev. no.
SAY31P03	..B
SAY61P03	..A
SAY61P03/MO	..A
SAY81P03	..A

Issued by
Siemens Switzerland Ltd
Smart Infrastructure
Global Headquarters
Theilerstrasse 1a
CH-6300 Zug
+41 58 724 2424
www.siemens.com/buildingtechnologies

© Siemens 2015
Technical specifications and availability subject to change without notice.

Document ID A6V10628469_en--_f
Edition 2024-08-27