LQ150X1LW72

TFT-LCD Module

Spec. Issue Date: April 13, 2006

No: LD-18322A

PREPARED BY: DATE SPEC No. LD-18322A FILE No. SHARP ISSUE: APR. 13.2006 APPROVED BY: PAGE: 21 pages DATE Mobile Liquid Crystal Display GROUP I APPLICABLE GROUP SHARP CORPORATION Mobile Liquid Crystal Display **SPECIFICATION** Group I **DEVICE SPECIFICATION**

TFT-LCD Module MODEL LQ150X1LW72

These parts have corresponded with the RoHS directive.

☐ CUSTOMER'S APPROVAL	
DATE	-
BY	

PRESENTED

BY T. Shaka

Division deputy general manager of

Mobile LCD design center

ENGINEERING DEPARTMENT IV

MOBILE LCD DESIGN CENTER

MOBILE LIQUID CRYSTAL DISPLAY GROUP I

SHARP CORPORATION

RECORDS OF REVISION

LQ150X1LW72

SPEC No.	DATE	REVISED	SUMMARY				
		No.	PAGE				
LD-18322A	APR. 13. 2006				1st Issue		
	1						
		-					
	I						

1. Application

This specification applies to the color 15.0 XGA TFT-LCD module LQ150X1LW72.

These specification sheets are the proprietary product of SHARP CORPORATION("SHARP) and include materials protected under copyright of SHARP. Do not reproduce or cause any third party to reproduce them in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP.

The device listed in this specification was designed and manufactured for use in general electronic equipment.

In case of using the device for applications such as control and safety equipment for transportation(aircraft, trains, automobiles, etc.), rescue and security equipment and various safety related equipment which require higher reliability and safety, take into consideration that appropriate measures such as fail-safe functions and redundant system design should be taken.

Do not use the device for equipment that requires an extreme level of reliability, such as aerospace applications, telecommunication equipment(trunk lines), nuclear power control equipment and medical or other equipment for life support.

SHARP assumes no responsibility for any damage resulting from the use of the device which does not comply with the instructions and the precautions specified in these specification sheets.

Contact and consult with a SHARP sales representative for any questions about this device.

2. Overview

This module is a color active matrix LCD module incorporating amorphous silicon TFT ($\underline{\text{Thin }}\underline{\text{Film }}\underline{\text{T}}$ ransistor). It is composed of a color TFT-LCD panel, driver ICs, control circuit, power supply circuit and a back light unit. Graphics and texts can be displayed on a $1024 \times \text{RGB} \times 768$ dots panel with about 16 million colors by using LVDS ($\underline{\text{Low }}\underline{\text{V}}$ oltage $\underline{\text{D}}$ ifferential $\underline{\text{S}}$ ignaling) and supplying +3.3V DC supply voltages for TFT-LCD panel driving and supply voltage for backlight.

It is a wide viewing-angle-module

(Vertical viewing angle:170 ° Horizontal viewing angle:170 ° ,CR 10).

Backlight-driving DC/AC inverter is not built in this module.

3. Mechanical Specifications

Parameter	Specifications	Unit
Display size	38 (Diagonal)	cm
	15.0 (Diagonal)	Inch
Active area	304.1 (H) × 228.1 (V)	mm
Pixel format	1024 (H) × 768 (V)	Pixel
	(1 pixel = R+G+B dots)	
Pixel pitch	0.297 (H) × 0.297 (V)	mm
Pixel configuration	R, G, B vertical stripe	
Display mode	Normally black	
Unit outline dimensions *1	331.6(W) × 254.76(H) × 12.5(D)	mm
Mass	1350(MAX)	g
Surface treatment	Anti-glare, LR-coating	
	and hard-coating 2H	
	(Haze value = 42)	

^{*1.}Note: excluding back light cables.

The thickness of module (D) doesn't contain the projection.

Outline dimensions are shown in Fig.1.

4. Input Terminals

4-1. TFT-LCD panel driving

CN1 (Interface signals and +3.3V DC power supply)

Using connectors : DF14H-20P-1.25H (Hirose Electric Co., Ltd.)

Corresponding connectors : DF14-20S-1.25C(Connector)

DF14-2628SCFA(Terminal)


Using LVDS Receiver : Contained in a control IC. [THC63LVDF84A(Thine) compatible]

Corresponding LVDS Transmitter : THC63LVDM83R(Thine) or compatible

Pin No.	Symbol	Function	Remark
1	Vcc	+3.3V Power supply	
2	Vcc	+3.3V Power supply	
3	GND	Ground	
4	GND	Ground	
5	Rx0-	LVDS CH0 data signal (-)	LVDS
6	Rx0+	LVDS CH0 data signal (+)	LVDS
7	GND	Ground	
8	Rx1-	LVDS CH1 data signal (-)	LVDS
9	Rx1+	LVDS CH1 data signal (+)	LVDS
10	GND	Ground	
11	Rx2-	LVDS CH2 data signal (-)	LVDS
12	Rx2+	LVDS CH2 data signal (+)	LVDS
13	GND	Ground	
14	CK-	LVDS CK- data signal (-)	LVDS
15	CK+	LVDS CK+ data signal (+)	LVDS
16	GND	Ground	
17	Rx3-	LVDS CH3 data signal (-)	LVDS
18	Rx3+	LVDS CH3 data signal (+)	LVDS
19	GND	Ground	
20	GND	Ground	

DATA Mapping

Tran	smitter	Innut Cional					
Pin No.	Data	Input Signal					
51	TA0	R0 (LSB)					
52	TA1	R1					
54	TA2	R2					
55	TA3	R3					
56	TA4	R4					
3	TA5	R5					
4	TA6	G0 (LSB)					
6	TB0	G1					
7	TB1	G2					
11	TB2	G3					
12	TB3	G4					
14	TB4	G5					
15	TB5	B0 (LSB)					
19	TB6	B1					
20	TC0	B2					
22	TC1	В3					
23	TC2	B4					
24	TC3	B5					
27	TC4	(NA)					
28	TC5	(NA)					
30	TC6	DE					
50	TD0	R6					
2	TD1	R7 (MSB)					
8	TD2	G6					
10	TD3	G7 (MSB)					
16	TD4	B6					
18	TD5	B7 (MSB)					
25	TD6	(NA)					




DE: Display Enable NA: Not Available

4-2 Interface block diagram

Using receiver: Contained in a control IC.

Corresponding Transmitter: THC63LVDM83A(THine electronics), DS90C383, DS90C383A(National semiconductor)




4-2. Backlight

CN 2, 3, 4, 5

The module-side connector: BHSR-02VS-1 (JST)

The user-side connector : SM02B-BHSS-1-TB (JST)

Pin no.	symbol	Funct	ion
1	V _H	Power supply for lamp	(High voltage side)
2	GND	Ground	



5. Absolute Maximum Ratings

Parameter	Symbol	Condition	Ratings	Unit	Remark
Supply voltage	Vcc	Ta=25	0 ~ +4.0	٧	
Storage temperature	T_{STG}	-	- 25 ~ +60		[Note1]
Operating temperature (Ambient)	T_{OPA}	-	0 ~ +50		

[Note1] Humidity: 95%RH Max. (Ta 40)

Maximum wet-bulb temperature at 39 or less. (Ta>40)

No condensation.

6. Electrical Characteristics

6-1. TFT-LCD panel driving

1. TFT-L	. TFT-LCD panel driving Ta = 25												
	Parameter	Symbol	Min.	Typ.	Max.	Unit	Remark						
Vcc	Supply voltage	Vcc	+3.0	+3.3	+3.6	V	[Note1]						
	Current dissipation	Icc	-	630	850	mA	[Note2]						
Perm	ssive input ripple voltage	V_{RF}	-	-	100	mVp-p	Vcc=+3.3V						
Term	inate Resister	R_{T}		100									

[Note1]


1) On-off sequences of Vcc and data

0 < t1 60ms

0 < t210ms

0 t3 1s

> 100ms t4




2) Dip conditions for supply voltage

1) V2 Vcc < V1 td 10ms

2) Vcc < V2

Vcc-dip conditions should also follow the on-off conditions.




[Note2] Typical current situation : 253-gray-bar pattern

Vcc=+3.3V, CK=65MHz

Gray scale: GS(n)

 $n=0 \sim 252$

The explanation of each gray scale, GS(n), is described below section 8.



6-2. Backlight

The back light system is an edge-lighting type with 4 CCFTs (Cold Cathode Fluorescent Tube).

The characteristics of the lamp are shown in the following table.

The value mentioned below is at the case of one CCFT.

CCFT Model Name: KTBE222MSTF-320MA262-Z (STANLEY ELECTRIC CO., LTD.)


Parameter	Symbol	Min.	Typ.	Max.	Unit	Remark
Lamp current range	I_L	3.5	6.5	7.5	mArms	[Note1]
Lamp voltage	$V_{\rm L}$	-	615	700	Vrms	Ta=25 ,IL=6.5mArms
Lamp power consumption	P_L	-	4.0	4.55	W	[Note2],IL=6.5mArms
Lamp frequency	FL	40	60	70	KHz	[Note3]
Kick-off voltage	Vs	-	-	1080	Vrms	Ta=25 【Note4】
		-	-	1480	Vrms	Ta=0 [Note4]
Lamp life time	$T_{\rm L}$	50,000	-	-	Hour	IL=6.5mArms [Note5]

[Note1] A lamp can be light in the range of lamp current shown above.

Maximum rating for current is measured by high frequency current measurement equipment connected to V_{LOW} at circuit showed below.

(Note: To keep enough kick-off voltage and necessary steady voltage for CCFT.)

Lamp frequency: $40 \sim 70 \text{kHz}$ Ambient temperature: $0 \sim 50$



[Note2] Referential data per one CCFT by calculation (IL \times VL).

The data does not include loss at inverter.

[Note3] Lamp frequency of inverter may produce interference with horizontal synchronous frequency, and this may cause horizontal beat on the display. Therefore, adjust lamp frequency, and keep inverter as far as from module or use electronic shielding between inverter and module to avoid interference.

[Note4] Kick-off voltage value is described as the index in the state of lamp only.

The kick-off voltage is estimated to be risen up as approx. +200V in the state of module only, and the further rise up can be seen according to the assembling status of user cabinet. Please set the kick-off voltage of inverter to avoid the lighting failures in the state of operation. Please design the inverter so that its open output voltage can be connected for more than 1 second to startup. Otherwise, the lamp may not be turned on. But, please set as 100ms when the ambient luminance around the lamp is more than 1lux.

[Note5] Lamp life time is defined as the time when either or occurs in the continuous operation under the condition of Ta=25 and the lamp current value indicated to the Remark.

Brightness becomes 50% of the original value under standard condition.

Kick-off voltage at Ta=0 exceeds maximum value,1480Vrms.

[Note6]

The performance of the backlight, for example lifetime or brightness, is much influenced by the characteristics of the DC-AC inverter for the lamp. When you design or order the inverter, please make sure that a poor lighting caused by the mismatch of the backlight and the inverter (miss-lighting, flicker, etc.) never occurs. When you confirm it, the module should be operated in the same condition as it is installed in your instrument.

Use the lamp inverter power source incorporating such safeguard as overvoltage / overcurrent protective circuit or lamp voltage waveform detection circuit, which should have individual control of each lamp.

In case one circuit without such individual control is connected to more than two lamps, excessive current may flow into one lamp when the other one is not in operation.


[Note7] Under the environment of 10lx or less, miss-lighting delay may occur.

7. Timing characteristics of input signals

7-1-1. Timing characteristics


Parameter	Symbol	Min.	Тур.	Max.	Unit	Remark
Frequency	1/Tc	60	65	85	MHz	
Horizontal period	TH	1056	1344	1720	clock	
		16.0	20.7	23.4	μs	
Horizontal period (High)	THd	1024		1024	clock	
Vertical period	TV	773	806	1008	line	[Note]
		13.3	16.7	18.1	ms	
Vertical period (High)	TVd	768		768	line	

[Note] In case of using the long vertical period, the deterioration of display quality, flicker etc. may occur.



7-2 Input Data Signals and Display Position on the screen

Graphics and texts can be displayed on a $1024 \times RGB \times 768$ dots panel with 16M colors by supplying 24 bit data signal (8bit/color [253 gray scales] $\times 3$).



Display Position of Data (V,H)

8. Input Signals, Basic Display Colors and Gray Scale of Each Color

Colors & Gray Gray Scale Gray Gray Scale Gray Gray Scale Scale Gray Scale Scale Gray Scale Scale Gray Scale Scale Gray Gray Scale Scale Gray Gray Scale Scale Gray Gray Scale Scale Gray Gray Scale Gray Gray Gray Scale Gray Gray Gray Gray Gray Gray Gray Gray				Data signal																							
Care Scale		Colors 8-	Grav											vata	. sigli	ıaı											
Black - 0 0 0 0 0 0 0 0 0			•	R0	R1	R2	R3	R4	R5	R6	R7	G0	G1	G2	G3	G4	G5	G6	G7	В0	B1	B2	В3	B4	B5	B6	В7
Figure F		_		0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Fig. Green - 0 0 0 0 0 0 0 0 0																											
Fig. Cyan - 0 0 0 0 0 0 0 0 0																											
Magental -	Basi																										
Magental -	ic C																										
Yellow -	olor																										
White -			-																								
Figure Green GS250 0 0 0 0 0 0 0 0 0			-																								
Gray Scale of Gr												X								X							
Calle of Red Case				0																							
Second S	Gr				0															0							
Second S	ay S	Darker		0	1	0			0	0	0	0	0	0			0	0	0	0	0	0			0	0	0
Second S	cale	仓	<u> </u>	. ↓										1	l				₩								
Second S	of l	Û	V				\	ν <u> </u>							1	<u>ا</u>								ν			
Red GS252 X X 1 1 1 1 1 1 1 1	Red	Brighter	GS250	0	1	0	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Black GS0 O O O O O O O O O		Û	GS251	1	1	0	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Gray Scale of Gr		Red	GS252	X	X	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Darker GS2 0 0 0 0 0 0 0 0 0		Black	GS0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Green GS252 0 0 0 0 0 0 0 0 0 0 0 0 0 1 1 0 1 1 1 1 1 1 0	Gr	Û	GS1	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Green GS252 0 0 0 0 0 0 0 0 0 0 0 0 0 1 1 0 1 1 1 1 1 1 0	ay S	Darker	GS2	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Green GS252 0 0 0 0 0 0 0 0 0 0 0 0 0 1 1 0 1 1 1 1 1 1 0	cale	仓	V				1	L				↓									`	V					
Green GS252 0 0 0 0 0 0 0 0 0 0 0 0 0 1 1 0 1 1 1 1 1 1 0	of (Û	\downarrow				\	l _							1	<u>ا</u>							`	ν			
Green GS252 0 0 0 0 0 0 0 0 0 0 0 0 0 1 1 0 1 1 1 1 1 1 0	Зree	Brighter	GS250	0	0	0	0	0	0	0	0	0	1	0	1	1	1	1	1	0	0	0	0	0	0	0	0
Black GSO O O O O O O O O O	n	Û	GS251	0	0	0	0	0	0	0	0	1	1	0	1	1	1	1	1	0	0	0	0	0	0	0	0
GRUP OF BEIGHT GS2 0		Green	GS252	0	0	0	0	0	0	0	0	X	X	1	1	1	1	1	1	0	0	0	0	0	0	0	0
Darker GS2 0 0 0 0 0 0 0 0 0		Black	GS0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
J GS251 0 <td></td> <td>仓</td> <td>GS1</td> <td>0</td> <td>1</td> <td>0</td> <td>0</td> <td>0</td> <td>0</td> <td>0</td> <td>0</td> <td>0</td>		仓	GS1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0
J GS251 0 <td>iray</td> <td>Darker</td> <td>GS2</td> <td>0</td> <td>1</td> <td>0</td> <td>0</td> <td>0</td> <td>0</td> <td>0</td> <td>0</td>	iray	Darker	GS2	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0
J GS251 0 <td>Sca</td> <td>仓</td> <td>\</td> <td></td> <td></td> <td></td> <td></td> <td>l</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td>1</td> <td>ı</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td>,</td> <td>V</td> <td></td> <td></td> <td></td>	Sca	仓	\					l							1	ı							,	V			
J GS251 0 <td>le of</td> <td>Û</td> <td>V</td> <td colspan="3"></td> <td colspan="6"></td> <td></td> <td></td> <td></td> <td></td> <td>,</td> <td>V</td> <td></td> <td></td> <td></td>	le of	Û	V														,	V									
J GS251 0 <td>: Blu</td> <td>Brighter</td> <td>GS250</td> <td>0</td> <td>1</td> <td>0</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td>	: Blu	Brighter	GS250	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0	1	1	1	1	1
	ie	_		0	0							0									1				1		
		Blue	GS252	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	X	X	1	1	1	1	1	1

^{0 :} Low level voltage,

Each basic color can be displayed in 253 gray scales from 8 bit data signals. According to the combination of total 24 bit data signals, the 16-million-color display can be achieved on the screen.

^{1 :} High level voltage.

X:Don't care.

9. Optical Characteristics

Ta=25 , Vcc = +3.3V

					1	1	10	t=23 , vec =13.3 v
Par	ameter	Symbol	Condition	Min.	Тур.	Max.	Unit	Remark
Viewing	Vertical	11	CR 10	70	85	-	Deg.	[Note1,4]
angle		12		70	85	-	Deg.	
range	Horizontal	21, 22		70	85	-	Deg.	
Cont	rast ratio	C R	=0 °	400	600	-		【 Note2,4 】
Respo	onse Time	Td+Tr		-	25	55	ms	【 Note3,4 】
Chron	naticity of	Wx		0.283	0.313	0.343	-	【Note4】
V	Vhite	Wy		0.299	0.329	0.359	-	
Chron	naticity of	Rx		0.608	0.638	0.668	-	
]	Red	Ry		0.309	0.339	0.369	-	
Chron	naticity of	Gx		0.250	0.280	0.310	-	
G	Green	Gy		0.570	0.600	0.630	-	
Chron	naticity of	Bx		0.114	0.144	0.174	-	
I	Blue	Ву		0.057	0.087	0.117	-	
Luminai	nce of white	YL		280	350	-	cd/m ²	IL=6.5mA FL= 60kHz rms [Note4]
White Uniformity		W		-	-	1.25	-	[Note5]

The measurement shall be executed 30 minutes after lighting at rating.

The optical characteristics shall be measured in a dark room or equivalent state with the method shown in Fig.2 below.





Fig2 Optical characteristics measurement method

[Note1] Definitions of viewing angle range:




[Note2] Definition of contrast ratio:

The contrast ratio is defined as the following.

[Note3] Definition of response time:


The response time is defined as the following figure and shall be measured by switching the input signal for "black" and "white".



[Note4] This shall be measured at center of the screen.

[Note5] Definition of white uniformity:

White uniformity is defined as the following with five measurements $(A \sim E)$.



10. Handling Precautions

- a) Be sure to turn off the power supply when inserting or disconnecting the cable.
- b) Be sure to design the cabinet so that the module can be installed without any extra stress such as warp or twist.
- c) Since the front polarize is easily damaged, pay attention not to scratch it.
- d) Since long contact with water may cause discoloration or spots, wipe off water drop immediately.
- e) When the panel surface is soiled, wipe it with absorbent cotton or other soft cloth.
- f) Since the panel is made of glass, it may break or crack if dropped or bumped on hard surface. Handle with care.
- g) Since CMOS LSI is used in this module, take care of static electricity and take the human earth into consideration when handling.
- h) Make sure the four mounting holes of the module are grounded sufficiently. Take electro-magnetic interference (EMI) into consideration.
- i) The module has some printed circuit boards (PCBs) on the back side. Take care to keep them form any stress or pressure when handling or installing the module; otherwise some of electronic parts on the PCBs may be damaged.
- j) Observe all other precautionary requirements in handling components.
- k) When some pressure is added onto the module from rear side constantly, it causes display non-uniformity issue, functional defect, etc. So, please avoid such design.
- When handling LCD modules and assembling them into cabinets, please be noted that long-term storage in the environment of oxidization or deoxidization gas and the use of such materials as reagent, solvent, adhesive, resin, etc. which generate these gasses, may cause corrosion and discoloration of the LCD modules.
- m) If a minute particle enters in the module and adheres to an optical material, it may cause display non-uniformity issue, etc. Therefore, fine-pitch filters have to be installed to cooling and inhalation hole if you intend to install a fan.

11. Packing form

a) Piling number of cartons: maximum 5 cartons

b) Packing quantity in one carton: 5 module

c) Carton size : 319mm(W) × 402mm(H) × 280mm(D)

d) Total mass of one carton filled with full modules: 8.5kg

e) Packing form is shown in Fig.3

12 . Reliability test items


No.	Test item	Conditions
1	High temperature storage test	Ta = 60 240h
2	Low temperature storage test	Ta = -25 240h
3	High temperature	Ta = 40 ; 95% RH 240h
	& high humidity operation test	(No condensation)
4	High temperature operation test	Ta = 50 240h
		(The panel temp. must be less than 60)
5	Low temperature operation test	Ta = 0 240H
6	Vibration test	Frequency: 10 ~ 57Hz/Vibration width (one side): 0.075mm
	(non- operating)	: $57 \sim 500$ Hz/Gravity : 9.8 m/s ²
		Wave form: sin wave
		Sweep time: 11minutes
		Test period: 3 hours
		(1 hour for each direction of X,Y,Z)
7	Shock test	Max. gravity: 490m/s ²
	(non- operating)	Pulse width: 11ms, half-sine wave
		Direction: $\pm X$, $\pm Y$, $\pm Z$,
		once for each direction.

【Result Evaluation Criteria】

Under the display quality test conditions with normal operation state, these shall be no change which may affect practical display function.

13. Others

1) Lot No. and indication Bar Code Label:



Production country

Japan	MADE IN JAPAN
Taiwan	MADE IN TAIWAN
China	MIDE IN CHINA

A production year (the last figures of the Christian Era)

Production month(1~9,X,Y,Z)

Sharp Control number

2) Packing Label

社内品番:(4 S) LQ150X1LW72				
Bar code ()				
LotNO. :(1T)2006.4.13				
Bar code ()				
Quantity:(Q) 5 pcs				
Bar code ()				
ユーザ品番:				
シャープ物流用ラベルです。				

Model No. (LQ150X1LW72)

Lot No. (Date)

Quantity

- 3) Adjusting volume have been set optimally before shipment, so do not change any adjusted value. If adjusted value is changed, the specification may not be satisfied.
- 4) Disassembling the module can cause permanent damage and should be strictly avoided.
- 5) Please be careful since image retention may occur when a fixed pattern is displayed for a long time.
- 6) The chemical compound which causes the destruction of ozone layer is not being used.
- 7) Material information of LPG (Light Pipe Guide) are labeled on the back of the module.

MATERIAL INFORMATION
>PLASTIC LIGHT GUIDE:PMMA<

8)Cold cathode fluorescent lamp in LCD PANEL contains a small amount of mercury, Please follow local ordinances or regulations for disposal. (put on the back of the module.)

COLD CATHOED FLUORESCENT LAMP IN LCD PANEL CONTAINS A SMALL AMOUNT OF MERCURY, PLEASE FOLLOW LOCAL ORDINANCES OR REGULATIONS FOR DISPOSAL 当該液晶ディスプレパ 礼は蛍光管が組込まれていますので、地方自治体の条例、または、規制に従って廃棄して下さい。

9) When any question or issue occurs, it shall be solved by mutual discussion.

Carton storage condition

Temperature 0 to 40

Humidity 95% RH or less

Reference condition: 20 to 35, 85%RH or less (summer)

5 to 15, 85%RH or less (winter)

• the total storage time (40 ,95%RH): 240H or less

Sunlight Be sure to shelter a product from the direct sunlight.

Atmosphere Harmful gas, such as acid and alkali which bites electronic components and/or

wires must not be detected.


Notes Be sure to put cartons on palette or base, don't put it on floor, and store them with

removing from wall

Please take care of ventilation in storehouse and around cartons, and control

changing temperature is within limits of natural environment

Storage period 1 year



- 1) TOLERANCE X-DIRECTION A:1.5±0.8
- 3) OBLIQUITY OF DISPLAY AREA |C-D|<0.8
- 2) TOLERANCE Y-DIRECTION B: 1.5±0.8

[CCFT CONNECTOR]

CN2/CN3/CN4/CN5 BHSR-02VS-1 (JST)

2 GND

- 1. UNSPECIFIED TOLERANCE TO BE ±0.5
- 2. WARP AND FLATING FOR PCB AND CHASSIS ARE EXCLUDED FROM THICKNESS AND DIMENSION OF THE UNIT.
- 3. THE THICKNESS IS EXCEPT FOR PORTION OF PROTECTION SHEET.
- 4. GAP BETWEEN BEZEL AND LCD PANEL ≦0.5

Fig. 1:LQ150X1LW72 OUTLINE DIMENSIONS

SECTION "C-C"




Fig. 3: PACKING FORM



NOTICE

This publication is the proprietary of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical for any purpose, in whole or in part, without the express written permission of SHARP Express written permission is also required before any use of this publication may be made by a third party.

The application circuit examples in this publication are provided to explain the representative applications of SHARP's devices and are not intended to guarantee any circuit design or permit any industrial property right or other rights to be executed. SHARP takes no responsibility for any problems related to any industrial property right or a third party resulting from the use of SHARP's devices, except for those resulting directly from device manufacturing processes.

In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that occur in equipment using any of SHARP's devices, shown in catalogs, data books, etc. Contact SHARP in order to obtain the latest device specification sheets before using any SHARP's device.

SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structures and other contents described herein at any time without notice in order to improve design or reliability. Contact SHARP in order to obtain the latest specification sheets before using any SHARP's device. Manufacturing locations are also subject to change without notice.

Observe the following points when using any device in this publication. SHARP takes no responsibility for damage caused by improper use *of the devices*.

The appropriate design measures should be taken to ensure reliability and safety when SHARP's devices are used for equipment such as:

- Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
- Traffic signals

- Gas leakage sensor breakers
- Alarm equipment
- Various safety devices etc.

SHARP's devices shall not be used for equipment that requires extremely high level of reliability, such as:

- Military and space applications
- Nuclear power control equipment
- Medical equipment for life support

Contact a SHARP representative, in advance, when intending to use SHARP's devices for any "specific" applications other than those recommended by SHARP.

Contact and consult with a SHARP representative if there are any questions about the contents of this publication.

SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Suggested applications (if any) are for standard use; See Important Restrictions for limitations on special applications. See Limited Warranty for SHARP's product warranty. The Limited Warranty is in lieu, and exclusive of, all other warranties, express or implied. ALL EXPRESS AND IMPLIED WARRANTIES, INCLUDING THE WARRANTIES OF MERCHANTABILITY, FITNESS FOR USE AND FITNESS FOR A PARTICULAR PURPOSE, ARE SPECIFICALLY EXCLUDED. In no event will SHARP be liable, or in any way responsible, for any incidental or consequential economic or property damage.



NORTH AMERICA

www.sharpsma.com

SHARP Microelectronics of the Americas 5700 NW Pacific Rim Blvd. Camas, WA 98607, U.S.A. Phone: (1) 360-834-2500 Fax: (1) 360-834-8903 Fast Info: (1) 800-833-9437

TAIWAN

SHARP Electronic Components (Taiwan) Corporation 8F-A, No. 16, Sec. 4, Nanking E. Rd. Taipei, Taiwan, Republic of China Phone: (886) 2-2577-7341 Fax: (886) 2-2577-7326/2-2577-7328

CHINA

SHARP Microelectronics of China (Shanghai) Co., Ltd. 28 Xin Jin Qiao Road King Tower 16F Pudong Shanghai, 201206 P.R. China Phone: (86) 21-5854-7710/21-5834-6056 Fax: (86) 21-5854-4340/21-5834-6057 **Head Office:**

No. 360, Bashen Road, Xin Development Bldg. 22 Waigaoqiao Free Trade Zone Shanghai 200131 P.R. China Email: smc@china.global.sharp.co.jp

EUROPE

SHARP Microelectronics Europe Division of Sharp Electronics (Europe) GmbH Sonninstrasse 3 20097 Hamburg, Germany Phone: (49) 40-2376-2286 Fax: (49) 40-2376-2232 www.sharpsme.com

SINGAPORE

SHARP Electronics (Singapore) PTE., Ltd. 438A, Alexandra Road, #05-01/02 Alexandra Technopark, Singapore 119967 Phone: (65) 271-3566 Fax: (65) 271-3855

HONG KONG

SHARP-ROXY (Hong Kong) Ltd.
3rd Business Division,
17/F, Admiralty Centre, Tower 1
18 Harcourt Road, Hong Kong
Phone: (852) 28229311
Fax: (852) 28660779
www.sharp.com.hk

Shenzhen Representative Office:

Room 13B1, Tower C, Electronics Science & Technology Building Shen Nan Zhong Road Shenzhen, P.R. China Phone: (86) 755-3273731

Phone: (86) 755-327373⁻¹ Fax: (86) 755-3273735

JAPAN

SHARP Corporation Electronic Components & Devices 22-22 Nagaike-cho, Abeno-Ku Osaka 545-8522, Japan Phone: (81) 6-6621-1221 Fax: (81) 6117-725300/6117-725301 www.sharp-world.com

KOREA

SHARP Electronic Components (Korea) Corporation RM 501 Geosung B/D, 541 Dohwa-dong, Mapo-ku Seoul 121-701, Korea Phone: (82) 2-711-5813 ~ 8 Fax: (82) 2-711-5819