

FPF1320 / FPF1321 IntelliMAX[™] Dual-Input Single-Output Advanced Power Switch with True Reverse-Current Blocking

Features

- DISO Load Switches
- Input Supply Operating Range: 1.5V ~ 5.5V
- R_{ON} 50mΩ at V_{IN}=3.3V Per Channel (Typical)
- True Reverse-Current Blocking (TRCB)
- Fixed Slew Rate Controlled 130µs for < 1µF C_{OUT}
- I_{SW}: 1.5A Per Channel (Maximum)
- Quick Discharge Feature on FPF1321
- Logic CMOS IO Meets JESD76 Standard for GPIO Interface and Related Power Supply Requirements
- ESD Protected:
 - Human Body Model: >6kV
 - Charged Device Model: >1.5kV
 - IEC 61000-4-2 Air Discharge: >15kV
 - IEC 61000-4-2 Contact Discharge: >8kV

Applications

- Smart phones / Tablet PCs
- Portable Devices
- Near Field Communication (NFC) Capable SIM Card Power Supply

Description

The FPF1320/21 is a Dual-Input Single-Output (DISO) load switch consisting of two sets of slew-rate controlled, low on-resistance, P-channel MOSFET switches and integrated analog features. The slew-rate-controlled turn-on characteristic prevents inrush current and the resulting excessive voltage droop on the power rails. The input voltage range operates from 1.5V to 5.5V to align with the requirements of low-voltage portable device power rails. FPF1320/21 performs seamless power-source transitions between two input power rails using the SEL pin with advanced break-before-make operation.


FPF1320/21 has a TRCB function to block unwanted reverse current from output to input during ON/OFF states. The switch is controlled by logic inputs of the SEL and EN pins, which are capable of interfacing directly with low-voltage control signals (GPIO).

FPF1321 has 65Ω on-chip load resistor for output quick discharge when EN is LOW.

FPF1320/21 is available in 1.0mm x 1.5mm WLCSP, 6-bump, with 0.5mm pitch.

Part Number	Top Mark	Channel	Switch Per Channel (Typ.) at 3.3V _{IN}	Reverse Current Blocking	Output Discharge	Rise Time (t _R)	Package
FPF1320UCX	QS	DISO	50mΩ	Yes	NA	130µs	1.0mmX1.5mm Wafer-
FPF1321UCX	QT	DISO	50mΩ	Yes	65Ω	130µs	Level Chip-Scale Package (WLCSP) 6- Bumps, 0.5mm Pitch

Ordering Information



Pin Description

Pin #	Name	Description
A1	EN	Enable input. Active HIGH. There is an internal pull-down resistor at the EN pin.
B1	SEL	Input power selection inputs. See Table 1. There are internal pull-down resistors at the SEL pins.
A2	V _{IN} A	Supply Input. Input to the power switch A.
B2	V _{OUT}	Switch output
C1	GND	Ground
C2	VINB	Supply Input. Input to power switch B.

Table 1. Truth Table

SEL	EN	Switch A	Switch B	V _{out}	Status
LOW	HIGH	ON	OFF	V _{IN} A	V _{IN} A Selected
HIGH	HIGH	OFF	ON	V _{IN} B	V _{IN} B Selected
х	LOW	OFF	OFF	Floating for FPF1320 GND for FPF1321	Both Switches are OFF

Absolute Maximum Ratings

Stresses exceeding the Absolute Maximum Ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Parameters			Max.	Unit	
V _{IN}	V _{IN} A, V _{IN} B, V _{SEL} , V _{EN} , V _{OUT} to GND			6	V	
I _{SW}	Maximum Continuous Switch Current per Channel			1.5	А	
PD	Total Power Dissipation at T	_A =25°C		1.2	W	
T _{STG}	Operating and Storage Junction Temperature			150	°C	
0	Thermal Resistance, Junction		85 ⁽¹⁾	°C/M		
Θ _{JA}	(1in. ² Pad of 2-oz. Copper)		110 ⁽²⁾	°C/W		
	Electrostatic Discharge Capability	Human Body Model, JESD22-A114	6.0			
		Charged Device Model, JESD22-C101	1.5		1	
ESD		Air Discharge (V _{IN} A, V _{IN} B to GND), IEC61000-4-2 System Level			kV	
		Contact Discharge (V _{IN} A, V _{IN} B to GND), IEC61000-4-2 System Level	8.0			

Notes:

- 1. Measured using 2S2P JEDEC std. PCB.
- 2. Measured using 2S2P JEDEC PCB cold-plate method.

Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to Absolute Maximum Ratings.

Symbol	Parameters	Min.	Max.	Unit
V _{IN}	Input Voltage on V _{IN} A, V _{IN} B	1.5	5.5	V
TA	Ambient Operating Temperature	-40	85	°C

ΰ
1
ω
Ö
PF1
ω
2
=
lte
Ľ
III M
2
<u>-</u>
╞
al-
5
ē
Ŧ
<u>S</u>
<u></u> 0
le-(
ò
Ĩ
p
1
Po
<u>ا ج</u>
n
Ce
ă
P
¥
ed Power S
Vit
t
2
1

Ш

Electrical Characteristics

 $V_{IN}A=V_{IN}B=1.5$ to 5.5V, $T_A=-40$ to 85°C unless otherwise noted. Typical values are at $V_{IN}A=V_{IN}B=3.3V$ and $T_A=25$ °C.

Symbol	Parameters	Condition	Min.	Тур.	Max.	Unit
Basic Operation	on					
$V_{IN}A, V_{IN}B$	Input Voltage		1.5		5.5	V
I _{SD}	Shutdown Current	SEL=HIGH or LOW, EN=GND, V _{OUT} =GND, V _{IN} A=V _{IN} B=5.5V			5	μA
Ι _Q	Quiescent Current	I _{OUT} =0mA, SEL=HIGH or LOW, EN=HIGH, VINA=VINB=5.5V		12	22	μA
		V _{IN} A=V _{IN} B=5.5V, I _{OUT} =200mA, T _A =25°C	42		60	
5		V _{IN} A=V _{IN} B=3.3V, I _{OUT} =200mA, T _A =25°C		50		mΩ
R _{on}	On-Resistance	V _{IN} A=V _{IN} B=1.8V, I _{OUT} =200mA, T _A =25°C to 85°C		80		
		V _{IN} A=V _{IN} B=1.5V, I _{OUT} =200mA, T _A =25°C			170	
VIH	SEL, EN Input Logic High Voltage	V _{IN} A, V _{IN} B=1.5V – 5.5V	1.15			V
V _{IL}	SEL, EN Input Logic Low Voltage	V _{IN} A, V _{IN} B=1.8V – 5.5V			0.65	V
	SEL, EN Input Logic Low Voltage	V _{IN} A, V _{IN} B=1.5V – 1.8V			0.60	
V _{DROOP_OUT}	Output Voltage Droop while Channel Switching from Higher Input Voltage Lower Input Voltage ⁽³⁾	$V_{IN}A=3.3V, V_{IN}B=5V$, Switching from $V_{IN}A \rightarrow V_{IN}B, R_L=150\Omega, C_{OUT}=1\mu F$			100	mV
I _{SEL} /I _{EN}	Input Leakage at SEL and EN Pin				1.2	μA
R _{SEL_PD} /R _{EN_PD}	Pull-Down Resistance at SEL or EN Pin			7		MΩ
R _{PD}	Output Pull-Down Resistance	SEL=HIGH or LOW, EN=GND, I_{FORCE} =20mA, T_A =25°C, FPF1321		65		Ω
True Reverse	Current Blocking				1	
V _{T_RCB}	RCB Protection Trip Point	V _{OUT} - V _{IN} A or V _{IN} B		45		mV
V _{R_RCB}	RCB Protection Release Trip Point	V _{IN} A or V _{IN} B -V _{OUT}		25		mV
I _{RCB}	V _{IN} A or V _{IN} B Current During RCB	V_{OUT} =5.5V, $V_{IN}A$ or $V_{IN}B$ =Short to GND		9	15	μA
t _{RCB_ON}	RCB Response Time when Device is ON ⁽³⁾	$V_{IN}A \text{ or } V_{IN}B=5V, V_{OUT}V_{INA,B}=100mV$		5		μs

Continued on the following page...

FPF1320 / FPF1321 — IntelliMAX[™] Dual-Input Single-Output Advanced Power Switch

Electrical Characteristics (Continued)

 $V_{IN}A=V_{IN}B=1.5$ to 5.5V, $T_A=-40$ to 85°C unless otherwise noted. Typical values are at $V_{IN}A=V_{IN}B=3.3V$ and $T_A=25°C$.

Symbol	Parameters	Condition	Min.	Тур.	Max.	Unit
Dynamic Cha	aracteristics					I
t _{DON}	Turn-On Delay ⁽⁴⁾	$V_{IN}A \text{ or } V_{IN}B=3.3V, R_L=150\Omega, C_L=1\mu F,$		120		μs
t _R	V _{OUT} Rise Time ⁽⁴⁾	T _A =25°C, SEL: HIGH,		130		μs
t _{on}	Turn-On Time ⁽⁶⁾	EN: LOW → HIGH		250		μs
t _{DOFF}	Turn-Off Delay ⁽⁴⁾	V _{IN} A or V _{IN} B=3.3V, R _I =150Ω, C _I =1µF,		15		μs
t _F	V _{OUT} Fall Time ⁽⁴⁾	T _A =25°C, SEL: HIGH,		320		μs
t _{OFF}	Turn-Off Time ⁽⁷⁾	EN: HIGH → LOW		335		μs
t _{DOFF}	Turn-Off Delay ^(4,5)	$V_{IN}A \text{ or } V_{IN}B = 3.3V, R_L = 150\Omega, C_L = 1\mu F,$		6		μs
t⊧	V _{OUT} Fall Time ^(4,5)	T _A =25°C, SEL: HIGH, EN: HIGH → LOW,		110		μs
t _{OFF}	Turn-Off Time ^(5,7)	Output Discharge Mode, FPF1321		116		μs
t _{tranr}	Transition Time LOW \rightarrow HIGH ⁽⁴⁾	$V_{IN}A=3.3V, V_{IN}B=5V,$ Switching from $V_{IN}A \rightarrow V_{IN}B$,		3		μs
t _{SLH}	Switch-Over Rising Delay ⁽⁴⁾	SEL: LOW → HIGH, EN: HIGH, R _L =150Ω, C _L =1μF, T _A =25°C		1		μs
t _{TRANF}	Transition Time HIGH → LOW ⁽⁴⁾	$V_{IN}A=3.3V, V_{IN}B=5V,$ Switching from VINB $\rightarrow V_{IN}A$,		45		μs
t _{SHL}	Switch-Over Falling Delay ⁽⁴⁾	SEL: HIGH → LOW, EN: HIGH, R _L =150Ω, C=1µF, T _A =25°C		5		μs

Notes:


3. This parameter is guaranteed by design and characterization; not production tested.

4. t_{DON}/t_{DOFF}/t_R/t_F/t_{TRANR}/t_{TRANF}/t_{SLH}/t_{SHL} are defined in Figure 5.

5. FPF1321 output discharge is enabled during off.


6. $t_{ON}=t_R + t_{DON}$.

7. $t_{OFF}=t_F + t_{DOFF}$.





Typical Characteristics








Figure 8. Shutdown Current vs. Temperature




Figure 10. R_{ON} vs. Temperature




Figure 7. Supply Current vs. Supply Voltage








Figure 9. Shutdown Current vs. Supply Voltage





Continued on the following page...









Figure 20. t_R and t_F with FPF1320 vs. Temperature






Figure 19. t_{DON} and t_{DOFF} vs. Temperature








Figure 21. t_R and t_F with FPF1321 vs. Temperature





Continued on the following page ...





Operation and Application Description

The FPF1320 and FPF1321 are dual-input single-output power multiplexer switches with controlled turn-on and seamless power source transition. The core is a 50m Ω P-channel MOSFET and controller capable of functioning over a wide input operating range of 1.5V to 5.5V per channel. The EN and SEL pins are active-HIGH, GPIO/CMOS-compatible input. They control the state of the switch and input power source selection, respectively. TRCB functionality blocks unwanted reverse current during both ON and OFF states when higher V_{OUT} than V_{IN}A or V_{IN}B is applied. FPF1321 has a 65 Ω output discharge path during off.

Input Capacitor

To limit the voltage drop on the input supply caused by transient inrush current when the switch turns on into a discharged load capacitor; a capacitor must be placed between the $V_{IN}A$ or $V_{IN}B$ pins to the GND pin. At least 1µF ceramic capacitor, C_{IN} , placed close to the pins, is usually sufficient. Higher-value C_{IN} can be used to reduce more the voltage drop.

Inrush Current

Inrush current occurs when the device is turned on. Inrush current is dependent on output capacitance and slew rate control capability, as expressed by:

$$I_{INRUSH} = C_{OUT} \times \frac{V_{IN} - V_{INITIAL}}{t_{R}} + I_{LOAD}$$
(1)

where:

- C_{OUT}: Output capacitance;
- t_R: Slew rate or rise time at V_{OUT};

V_{IN}: Input voltage, V_{IN}A or V_{IN}B;

VINITIAL: Initial voltage at COUT, usually GND; and

ILOAD: Load current.

Higher inrush current causes higher input voltage drop, depending on the distributed input resistance and input capacitance. High inrush current can cause problems.

FPF1320/1 has a 130 μs of slew rate capability under $3.3V_{IN}$ at $1\mu F$ of C_{OUT} and 150Ω of R_L so inrush current and input voltage drop can be minimized.

Power Source Selection

Input power source selection can be controlled by the SEL pin. When SEL is LOW, output is powered from $V_{IN}A$ while SEL is HIGH, $V_{IN}B$ is powering output. The SEL signal is ignored during device OFF.

Output Voltage Drop during Transition

Output voltage drop usually occurs during input power source transition period from low voltage to high voltage. The drop is highly dependent on output capacitance and load current.

FPF1320/1 adopts an advanced break-before-make control, which can result in minimized output voltage drop during the transition time.

Output Capacitor

Capacitor C_{OUT} of at least 1µF is highly recommended between the V_{OUT} and GND pins to achieve minimized output voltage drop during input power source transition. This capacitor also prevents parasitic board inductance.

True Reverse-Current Blocking

The true reverse-current blocking feature protects the input source against current flow from output to input regardless of whether the load switch is on or off.

Board Layout

For best performance, all traces should be as short as possible. To be most effective, the input and output capacitors should be placed close to the device to minimize the effect that parasitic trace inductance on normal and short-circuit operation. Wide traces or large copper planes for power pins (V_{IN}A, V_{IN}B, V_{OUT} and GND) minimize the parasitic electrical effects and the thermal impedance.




Figure 34. 6 Ball, 1.0 x 1.5mm, Wafer-Level Chip-Scale Package (WLCSP)

Product-Specific Dimensions

Product	D	E	X	Y
FPF1320UCX	1460µm+/-30µm	960µm+/-30µm	230µm	230µm
FPF1321UCX	1460µm+/-30µm	960µm+/-30µm	230µm	230µm

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings: http://www.fairchildsemi.com/packaging/.

FAIRCHILD SEMICONDUCTOR TRADEMARKS The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks. 2CoolTM E-PEST PowerTrench® The Power Franchise® FRFET® PowerXS^T AccuPower™ franchise Global Power ResourceSM AX-CAPTM* Programmable Active Droop™ BitSiC™ GreenBridge™ OFET TinyBoost™ Build it Now™ Green FPS™ QS™ TinyBuck™ Green FPS™ e-Series™ Quiet Series™ CorePLUS™ TinyCalc™ CorePOWER™ Gmax™ RapidConfigure™ TinyLogic® **GTO™ CROSSVOLT™ TINYOPTO™** IntelliMAXTh CTL™ Saving our world, 1mW/W/kW at a time™ TinyPower™ ISOPLANARTM Current Transfer Logic™ SignalWise™ TinyPWM™ DEUXPEED Making Small Speakers Sound Louder SmartMax™ TinyWire™ and Better Dual Cool™ SMART START™ TranSiC™ **EcoSPARK**® MegaBuck™ Solutions for Your Success™ TriFault Detect™ MICROCOUPLER™ EfficientMax™ SPM TRUECURRENT®* MicroFET ESBC^{TI} STEAL THT uSerDes™ R MicroPak™ SuperFET μ MicroPak2™ SuperSOT™-3 Fairchild® Miller Drive™ SuperSOT™-6 UHC Fairchild Semiconductor® MotionMax™ SuperSOT™-8 Ultra FRFET FACT Quiet Series™ Motion-SPM™ SupreMOS[®] FACT UniEET™ mWSaver™ FAST® SyncFET™ VCX™ OptoHiT™ Sync-Lock™ FastvCore™ VisualMax™ **OPTOLOGIC**[®] **FETBench™** VoltagePlus™ **OPTOPLANAR[®]** FlashWriter®* XS™ **FPS**Th æ * Trademarks of System General Corporation, used under license by Fairchild Semiconductor. DISCLAIMER FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS. LIFE SUPPORT POLICY FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein: Life support devices or systems are devices or systems which, (a) 2. A critical component in any component of a life support, device, or are intended for surgical implant into the body or (b) support or system whose failure to perform can be reasonably expected to sustain life, and (c) whose failure to perform when properly used in cause the failure of the life support device or system, or to affect its accordance with instructions for use provided in the labeling, can be safety or effectiveness. reasonably expected to result in a significant injury of the user ANTI-COUNTERFEITING POLICY Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com, under Sales Support Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors. PRODUCT STATUS DEFINITIONS **Definition of Terms Product Status Datasheet Identification** Definition Datasheet contains the design specifications for product development. Specifications may change Advance Information Formative / In Design in any manner without notice. Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild First Production Preliminary Semiconductor reserves the right to make changes at any time without notice to improve design Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make No Identification Needed **Full Production** changes at any time without notice to improve the design. Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. Obsolete Not In Production The datasheet is for reference information only

PF1320 / FPF1321 —

IntelliMAX[™] Dual-Input Single-Output Advanced Power Switch

