

150 mA μ Cap Ultra-Low Dropout Regulator

Features

- Ultra-Low Dropout Voltage: 60 mV @ 150 mA
- Input Voltage Range: 2.25 to 5.5V
- Stable with Ceramic Output Capacitors
- 150 mA output Current
- Low Output Noise: 20 μ V_{RMS}
- Low Quiescent Current of 90 μ A Total
- High PSRR: Up to 85 dB @1 kHz
- Less than 30 μ s Turn-On Time w/ $C_{BYP} = 0.01 \mu$ F
- High Output Accuracy:
 - $\pm 1.0\%$ Initial Accuracy
 - $\pm 2.0\%$ over Temperature
- Thermal Shutdown Protection
- Current Limit Protection
- Tiny 6-Lead 2 mm x 2 mm VDFN Package
- Ultra-Thin 6-Lead 2 mm x 2 mm UDFN Package
- Thin SOT 5-Lead Package

Applications

- Cellular Phones
- PDAs
- Fiber Optic Modules
- Portable Electronics
- Notebook PCs
- Audio Codec Power Supplies

General Description


The MIC5305 is a high-performance, 150 mA LDO regulator that offers extremely high PSRR and very low noise while consuming low ground current.

Ideal for battery-operated applications, the MIC5305 features 1% accuracy, extremely low dropout voltage (60 mV @ 150 mA), and low ground current at light load (typically 90 μ A). Equipped with a logic-compatible enable pin, the MIC5305 can be put into a zero off-mode current state that draws no current when disabled.

The MIC5305 is a μ Cap design that operates with very small ceramic output capacitors for stability, thereby reducing required board space and component cost.


The MIC5305 is available in fixed output voltages and adjustable output voltages in the compact 6-lead 2 mm x 2 mm VDFN leadless package, the ultra-thin 6-lead 2 mm x 2 mm UDFN, and 5-lead Thin SOT package.

Typical Application Circuit




MIC5305

Package Types



Functional Block Diagrams



1.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings †

Supply Voltage (V_{IN})	0V to +6V
Enable Input Voltage (V_{EN})	0V to +6V
Power Dissipation (P_D , Note 1)	Internally Limited
ESD Rating (Note 2)	2 kV

Operating Ratings ‡

Supply Voltage	+2.25V to +5.5V
Enable Input Voltage (V_{EN})	0V to V_{IN}

† **Notice:** Stresses above those listed under “Absolute Maximum Ratings” may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

‡ **Notice:** The device is not guaranteed to function outside its operating ratings.

Note 1: The maximum allowable power dissipation of any T_A (ambient temperature) is $P_{D(MAX)} = (T_{J(MAX)} - T_A)/\theta_{JA}$. Exceeding the maximum allowable power dissipation will result in excessive die temperature, and the regulator will go into thermal shutdown.

2: Devices are ESD sensitive. Handling precautions recommended. Human body model, 1.5 k Ω in series with 100 pF.

ELECTRICAL CHARACTERISTICS

Electrical Characteristics: $V_{IN} = V_{OUT} + 1V$; $C_{OUT} = 1.0 \mu F$; $I_{OUT} = 100 \mu A$; $T_A = +25^\circ C$. **Bold** values valid for $-40^\circ C$ to $+125^\circ C$; unless otherwise specified. [Note 1](#)

Parameter	Symbol	Min.	Typ.	Max.	Units	Conditions
Output Voltage Accuracy		-1.0	—	1.0	%	Variation from nominal V_{OUT}
		-2.0	—	2.0		Variation from nominal V_{OUT} , $I_{OUT} = 100 \text{ mA}$ to 150 mA
Output Voltage Temperature Coefficient		—	40	—	ppm/ $^\circ C$	—
Line Regulation	$\frac{\Delta V_{OUT}}{(V_{OUT} \times \Delta V_{IN})}$	—	0.02	0.3	%/V	$V_{IN} = V_{OUT} + 1V$ to $5.5V$
Load Regulation (Note 2)	$\frac{\Delta V_{OUT}}{V_{OUT}}$	—	0.1	0.5	%	$I_{OUT} = 100 \mu A$ to 150 mA
Dropout Voltage (Note 3)	V_{DO}	—	20	35	mV	$I_{OUT} = 50 \text{ mA}$, $V_{OUT} > 2.8V$
		—	60	85		$I_{OUT} = 150 \text{ mA}$, $V_{OUT} > 2.8V$
		—	27	45		$I_{OUT} = 50 \text{ mA}$, $V_{OUT} \leq 2.8V$
		—	85	110		$I_{OUT} = 150 \text{ mA}$, $V_{OUT} \leq 2.8V$
Ground Pin Current (Note 4)	I_{GND}	—	90	150	μA	$I_{OUT} = 0 \text{ mA}$ to 150 mA
Ground Pin Current in Shutdown	I_{SD}	—	0.5	—	μA	$V_{EN} \leq 0.2V$
Ripple Rejection	PSRR	—	85	—	dB	$f = \text{up to } 1 \text{ kHz}$; $C_{OUT} = 1.0 \mu F$ ceramic; $C_{BYP} = 0.1 \mu F$
		—	65	—		$f = 10 \text{ kHz}$; $C_{OUT} = 1.0 \mu F$ ceramic; $C_{BYP} = 0.1 \mu F$
Current Limit	I_{LIM}	300	600	900	mA	$V_{OUT} = 0V$

ELECTRICAL CHARACTERISTICS (CONTINUED)

Electrical Characteristics: $V_{IN} = V_{OUT} + 1V$; $C_{OUT} = 1.0 \mu F$; $I_{OUT} = 100 \mu A$; $T_A = +25^\circ C$. **Bold** values valid for $-40^\circ C$ to $+125^\circ C$; unless otherwise specified. [Note 1](#)

Parameter	Symbol	Min.	Typ.	Max.	Units	Conditions
Output Voltage Noise	e_n	—	20	—	μV_{RMS}	$C_{OUT} = 1 \mu F$, $C_{BYP} = 0.1 \mu F$, 10 Hz to 100 kHz
Turn-On Time	t_{ON}	—	30	100	μs	$C_{OUT} = 1 \mu F$; $C_{BYP} = 0.1 \mu F$; $I_{OUT} = 150 mA$
Enable Input						
Enable Input Voltage	V_{IL}	—	—	0.2	V	Logic Low (Regulator Shutdown)
	V_{IH}	1.0	—	—		Logic High (Regulator Enabled)
Enable Input Current	I_{IL}	—	0.01	1	μA	$V_{IL} \leq 0.2V$ (Regulator Shutdown)
	I_{IH}	—	0.01	1		$V_{IH} \geq 1.2V$ (Regulator Enabled)

Note 1: Specification for packaged product only.

- Regulation is measured at constant junction temperature using low duty cycle pulse testing; changes in output voltage due to heating effects are covered by the thermal regulation specification.
- Dropout voltage is defined as the input-to-output differential at which the output voltage drops 2% below its nominal V_{OUT} . For outputs below 2.25V, the dropout voltage is the input-to-output differential with the minimum input voltage 2.25V.
- Ground pin current is the regulator quiescent current. The total current drawn from the supply is the sum of the load current plus the ground pin current.

TEMPERATURE SPECIFICATIONS

Parameters	Sym.	Min.	Typ.	Max.	Units	Conditions
Temperature Ranges						
Junction Temperature Range	T_J	-40	—	+125	$^\circ C$	—
Storage Temperature	T_S	-65	—	+150	$^\circ C$	—
Lead Temperature	T_{LEAD}	—	—	+260	$^\circ C$	Soldering, 5 sec.
Package Thermal Resistances						
Thermal Resistance, UDFN 6-Ld	θ_{JA}	—	93	—	$^\circ C/W$	—
Thermal Resistance, VDFN 6-Ld	θ_{JA}	—	93	—	$^\circ C/W$	—
Thermal Resistance, TSOT 5-Ld	θ_{JA}	—	235	—	$^\circ C/W$	—

2.0 TYPICAL PERFORMANCE CURVES

Note: The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.




FIGURE 2-1: PSRR (Bypass Pin Cap = 0.01 μ F).




FIGURE 2-4: Ground Pin Current.




FIGURE 2-2: PSRR (Bypass Pin Cap = 0.1 μ F).




FIGURE 2-5: Ground Pin Current.




FIGURE 2-3: PSRR (Bypass Pin Cap = 1 μ F).




FIGURE 2-6: Ground Pin Current.




FIGURE 2-7: Ground Pin Current.




FIGURE 2-10: Dropout Voltage.




FIGURE 2-8: Ground Pin Current.




FIGURE 2-11: Dropout Voltage.




FIGURE 2-9: Dropout Characteristics.




FIGURE 2-12: Dropout Voltage.




FIGURE 2-13: Dropout Voltage.




FIGURE 2-16: Output Voltage vs. Temperature.




FIGURE 2-14: Dropout Voltage.




FIGURE 2-17: Enable Threshold vs. Temperature.




FIGURE 2-15: Short Circuit Current.




FIGURE 2-18: Output Noise Spectral Density.




FIGURE 2-19: Load Transient Response.




FIGURE 2-21: Enable Pin Delay.




FIGURE 2-20: Load Transient Response.




FIGURE 2-22: Shutdown Delay.

3.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in [Table 3-1](#).

TABLE 3-1: PIN FUNCTION TABLE

Pin Number VDFN-6 Fixed	Pin Number VDFN-6 Adjustable	Pin Number UDFN-6 Fixed	Pin Number TSOT-5 Fixed	Pin Name	Description
1	1	1	3	EN	Enable Input. Active High. High = on, Low = off. Do not leave floating.
2	2	2	2	GND	Ground.
3	3	3	1	VIN	Supply Input.
4	4	4	5	VOUT	Output Voltage.
—	5	—	—	ADJ	Adjust Input: Connect to external resistor voltage divider network.
5	—	5	—	NC	No connection for fixed-voltage parts.
6	6	6	4	BYP	Reference Bypass: Connect external 0.1 μ F to GND for reduced output noise. May be left open.
Heatsink Pad	Heatsink Pad	Heatsink Pad	—	EPAD	Exposed Heatsink Pad connected to ground internally.

4.0 APPLICATION INFORMATION

4.1 Enable/Shutdown

The MIC5305 comes with an active-high enable pin that allows the regulator to be disabled. Forcing the enable pin low disables the regulator and sends it into a “zero” off-mode current state. In this state, current consumed by the regulator goes nearly to zero. Forcing the enable pin high enables the output voltage. The active-high enable pin uses CMOS technology and the enable pin cannot be left floating; a floating enable pin may cause an indeterminate state on the output.

4.2 Input Capacitor

The MIC5305 is a high-performance, high bandwidth device. Therefore, it requires a well-bypassed input supply for optimal performance. A 1 μF capacitor is required from the input to ground to provide stability. Low-ESR ceramic capacitors provide optimal performance at a minimum of space. Additional high frequency capacitors, such as small-valued NPO dielectric-type capacitors, help filter out high-frequency noise and are good practice in any RF-based circuit.

4.3 Output Capacitor

The MIC5305 requires an output capacitor of 1 μF or greater to maintain stability. The design is optimized for use with low-ESR ceramic chip capacitors. High ESR capacitors may cause high frequency oscillation. The output capacitor can be increased, but performance has been optimized for a 1 μF ceramic output capacitor and does not improve significantly with larger capacitance.

X7R/X5R dielectric-type ceramic capacitors are recommended because of their temperature performance. X7R-type capacitors change capacitance by 15% over their operating temperature range and are the most stable type of ceramic capacitors. Z5U and Y5V dielectric capacitors change value by as much as 50% and 60%, respectively, over their operating temperature ranges. To use a ceramic chip capacitor with Y5V dielectric, the value must be much higher than an X7R ceramic capacitor to ensure the same minimum capacitance over the equivalent operating temperature range.

4.4 Bypass Capacitor

A capacitor can be placed from the noise bypass pin to ground to reduce output voltage noise. The capacitor bypasses the internal reference. A 0.1 μF capacitor is recommended for applications that require low-noise outputs. The bypass capacitor can be increased, further reducing noise and improving PSRR. Turn-on time increases slightly with respect to bypass capacitance. A unique, quick-start circuit allows the MIC5305 to drive a large capacitor on the bypass pin

without significantly slowing turn-on time. Refer to the [Typical Performance Curves](#) section for performance with different bypass capacitors.

4.5 No-Load Stability

Unlike many other voltage regulators, the MIC5305 will remain stable and in regulation with no load. This is especially important in CMOS RAM keep-alive applications.

4.6 Adjustable Regulator Application

Adjustable regulators use the ratio of two resistors to multiply the reference voltage to produce the desired output voltage. The MIC5305 can be adjusted from 1.25V to 5.5V by using two external resistors ([Figure 4-1](#)). The resistors set the output voltage based on the following equation:

EQUATION 4-1:

$$V_{OUT} = V_{REF} \times \left(1 + \frac{R1}{R2}\right)$$

Where:

$V_{REF} = 1.25\text{V}$




FIGURE 4-1: Adjustable Voltage Application.

4.7 Thermal Considerations

The MIC5305 is designed to provide 150 mA of continuous current in a very small package. Maximum ambient operating temperature can be calculated based on the output current and the voltage drop across the part. Given that the input voltage is 5.0V, the output voltage is 2.9V and the output current equals 150 mA.

The actual power dissipation of the regulator circuit can be determined using the following equation:

EQUATION 4-2:

$$P_D = (V_{IN} - V_{OUT}) \times I_{OUT} + V_{IN} \times I_{GND}$$

Because this device is CMOS and the ground current is typically <100 μA over the load range, the power dissipation contributed by the ground current is <1% and can be ignored for this calculation.

EQUATION 4-3:

$$P_D = (5.0V - 2.9V) \times 150\text{mA} = 0.32\text{W}$$

To determine the maximum ambient operating temperature of the package, use the junction-to-ambient thermal resistance of the device and the following basic equation:

EQUATION 4-4:

$$P_{D(MAX)} = \frac{T_{J(MAX)} - T_A}{\theta_{JA}}$$

Where:

$T_{J(MAX)} = 125^\circ\text{C}$, the max. junction temperature of the die.

$\theta_{JA} = 93^\circ\text{C/W}$, thermal resistance.

[Table 4-1](#) shows junction-to-ambient thermal resistance for the MIC5305 in the 6-lead 2 mm x 2 mm VDFN package.

TABLE 4-1: THERMAL RESISTANCE

Package	θ_{JA} Rec. Min. Footprint	θ_{JC}
VDFN 6-Ld	93°C/W	2°C/W

Substituting P_D for $P_{D(MAX)}$ and solving for the ambient operating temperature will give the maximum operating conditions for the regulator circuit. The junction-to-ambient thermal resistance for the minimum footprint (the minimum amount of copper that you can solder the part to) is 93°C/W , from [Table 4-1](#). The maximum power dissipation must not be exceeded for proper operation.

For example, when operating the MIC5305-2.9YML at an input voltage of 5.0V and 150 mA load with a minimum footprint layout, the maximum ambient operating temperature T_A can be determined as follows:

EQUATION 4-5:

$$0.32\text{W} = \frac{125^\circ\text{C} - T_A}{93^\circ\text{C/W}}$$

$$T_A = 95.2^\circ\text{C}$$

Therefore, a 2.9V application at 150 mA of output current can accept an ambient operating temperature of 95.2°C in a 6-lead 2 mm x 2 mm VDFN package. For a full discussion of heat sinking and thermal effects on voltage regulators, refer to the "Regulator Thermals" section of Microchip's [Designing with Low-Dropout Voltage Regulators](#) handbook.

5.0 PACKAGING INFORMATION

5.1 Package Marking Information

6-Lead UDFN*	Example	6-Lead VDFN*	Example
5-Lead TSOT* (Front)	Example	5-Lead TSOT* (Back)	Example

Note: A full list of marking codes for all available part numbers appears in the [Product Identification System](#) section.

Legend: XX...X Product code or customer-specific information
Y Year code (last digit of calendar year)
YY Year code (last 2 digits of calendar year)
WW Week code (week of January 1 is week '01')
NNN Alphanumeric traceability code
(e3) Pb-free JEDEC® designator for Matte Tin (Sn)
* This package is Pb-free. The Pb-free JEDEC designator ((e3)) can be found on the outer packaging for this package.

●, ▲, ▼ Pin one index is identified by a dot, delta up, or delta down (triangle mark).


Note: In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information. Package may or may not include the corporate logo.

Underbar (_) symbol may not be to scale.

Note: If the full seven-character YYWWNNN code cannot fit on the package, the following truncated codes are used based on the available marking space:
6 Characters = YWWNNN; 5 Characters = WWNNN; 4 Characters = WNNN; 3 Characters = NNN;
2 Characters = NN; 1 Character = N

6-Lead Very Thin Plastic Dual Flat, No Lead Package (JDA) - 2x2 mm Body [VDFN] Micrel Legacy Package

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>




Microchip Technology Drawing C04-1016A Sheet 1 of 2

MIC5305

6-Lead Very Thin Plastic Dual Flat, No Lead Package (JDA) - 2x2 mm Body [VDFN] Micrel Legacy Package

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Number of Terminals	N	6		
Pitch	e	0.65 BSC		
Overall Height	A	0.80	0.85	0.90
Standoff	A1	0.00	0.02	0.05
Terminal Thickness	A3	0.203 REF		
Overall Length	D	2.00 BSC		
Exposed Pad Length	D2	1.35	1.40	1.45
Overall Width	E	2.00 BSC		
Exposed Pad Width	E2	0.75	0.80	0.85
Terminal Width	b	0.20	0.25	0.30
Terminal Length	L	0.30	0.35	0.40
Terminal-to-Exposed-Pad	K	0.20	-	-


Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Package is saw singulated
- 3. Dimensioning and tolerancing per ASME Y14.5M
 - BSC: Basic Dimension. Theoretically exact value shown without tolerances.
 - REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-1016A Sheet 2 of 2

6-Lead Very Thin Plastic Dual Flat, No Lead Package (JDA) - 2x2 mm Body [VDFN] Micrel Legacy Package

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



RECOMMENDED LAND PATTERN

Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	E	0.65 BSC		
Optional Center Pad Width	X2			0.85
Optional Center Pad Length	Y2			1.45
Contact Pad Spacing	C1		2.00	
Contact Pad Width (X6)	X1			0.30
Contact Pad Length (X6)	Y1			0.75
Contact Pad to Center Pad (X6)	G1	0.20		
Thermal Via Diameter	V	0.27	0.30	0.33


Notes:

- Dimensioning and tolerancing per ASME Y14.5M
BSC: Basic Dimension. Theoretically exact value shown without tolerances.
- For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process

Microchip Technology Drawing C04-21016A

6-Lead Ultra Thin Plastic Dual Flat, No Lead Package (HSA) - 2x2x0.6 mm Body [UDFN] Micrel Legacy Package TDFN22-6LD-PL-1


Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



Microchip Technology Drawing C04-1156-HSA Rev A Sheet 1 of 2

6-Lead Ultra Thin Plastic Dual Flat, No Lead Package (HSA) - 2x2x0.6 mm Body [UDFN] Micrel Legacy Package TDFN22-6LD-PL-1

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Number of Terminals	N	6		
Pitch	e	0.65 BSC		
Overall Height	A	0.50	0.55	0.60
Standoff	A1	0.00	0.02	0.05
Terminal Thickness	A3	0.152 REF		
Overall Length	D	2.00 BSC		
Exposed Pad Length	D2	1.35	1.40	1.45
Overall Width	E	2.00 BSC		
Exposed Pad Width	E2	0.75	0.80	0.85
Terminal Width	b	0.20	0.25	0.30
Terminal Length	L	0.30	0.35	0.40
Terminal-to-Exposed-Pad	K	0.20	-	-


Notes:

- Pin 1 visual index feature may vary, but must be located within the hatched area.
- Package is saw singulated
- Dimensioning and tolerancing per ASME Y14.5M
BSC: Basic Dimension. Theoretically exact value shown without tolerances.
REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-1156-HSA Rev A Sheet 2 of 2

6-Lead Ultra Thin Plastic Dual Flat, No Lead Package (HSA) - 2x2x0.6 mm Body [UDFN] Micrel Legacy Package TDFN22-6LD-PL-1

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



RECOMMENDED LAND PATTERN

Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	E	0.65 BSC		
Center Pad Width	X2			1.32
Center Pad Length	Y2			0.82
Contact Pad Spacing	C		1.80	
Contact Pad Width (X6)	X1			0.20
Contact Pad Length (X6)	Y1			0.40
Contact Pad to Center Pad (X6)	G	0.29		
Thermal Via Diameter	V		0.33	



Notes:

- Dimensioning and tolerancing per ASME Y14.5M
BSC: Basic Dimension. Theoretically exact value shown without tolerances.
- For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process

Microchip Technology Drawing C04-3156-HSA Rev A


5-Lead Plastic Thin Small Outline Transistor (D5A) [TSOT] Micrel Legacy Package TSOT-5LD-PL-1

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



5-Lead Plastic Thin Small Outline Transistor (D5A) [TSOT] Micrel Legacy Package TSOT-5LD-PL-1

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Number of Leads	N	5		
Pitch	e	0.95 BSC		
Outside lead pitch	e1	1.90 BSC		
Overall Height	A	-	-	1.00
Molded Package Thickness	A2	0.84	0.87	0.90
Standoff	A1	0.00	-	0.10
Overall Width	E	2.80 BSC		
Molded Package Width	E1	1.60 BSC		
Overall Length	D	2.90 BSC		
Foot Length	L	0.30	0.40	0.50
Footprint	L1	0.60 REF		
Foot Angle	φ	0°	-	4°
Lead Thickness	c	0.127 REF		
Lead Width	b	0.30	-	0.50


Notes:

- Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.25mm per side.
- Dimensioning and tolerancing per ASME Y14.5M
BSC: Basic Dimension. Theoretically exact value shown without tolerances.
REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-1179 Rev A Sheet 1 of 2

5-Lead Plastic Thin Small Outline Transistor (D5A) [TSOT] Micrel Legacy Package TSOT-5LD-PL-1

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



RECOMMENDED LAND PATTERN

Units		MILLIMETERS		
Dimension	Limits	MIN	NOM	MAX
Contact Pitch	E	0.95 BSC		
Contact Pad Spacing	C		2.60	
Contact Pad Width (X5)	X1			0.60
Contact Pad Length (X5)	Y1			1.10
Contact Pad to Center Pad (X2)	G	0.20		

Notes:

- Dimensioning and tolerancing per ASME Y14.5M
BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-3179 Rev A

MIC5305

NOTES:

APPENDIX A: REVISION HISTORY

Revision A (May 2024)

- Converted Micrel document MIC5305 to Microchip data sheet DS20006746A.
- Minor text changes throughout.

MIC5305

NOTES:

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

Part Number	-X.X	X	XX	-XX	Examples:
Device	Output Voltage	Temp. Range	Package	Media Type	
Device:	MIC5305:	150 mA μ Cap Ultra-Low Dropout Regulator			a) MIC5305YML-TR: MIC5305, Adj. Output Voltage, -40°C to +125°C Temp. Range, 6-Lead VDFN, 5,000/Reel
	<blank>	= Adjustable (VDFN only)			b) MIC5305-2.5YD5-TX: MIC5305, 2.5V Output Voltage, -40°C to +125°C Temp. Range, 5-Lead TSOT, 3,000/Reel Reverse
	1.5	= 1.5V (TSOT and VDFN only)			c) MIC5305-2.8YMT-TR: MIC5305, 2.8V Output Voltage, -40°C to +125°C Temp. Range, 6-Lead UDFN, 5,000/Reel
	1.8	= 1.8V (TSOT and VDFN only)			d) MIC5305-3.0YD5-TR: MIC5305, 3.0V Output Voltage, -40°C to +125°C Temp. Range, 5-Lead TSOT, 3,000/Reel
	2.5	= 2.5V (TSOT and VDFN only)			e) MIC5305-2.9YML-TR: MIC5305, 2.9V Output Voltage, -40°C to +125°C Temp. Range, 6-Lead VDFN, 5,000/Reel
	2.6	= 2.6V (TSOT and VDFN only)			f) MIC5305-1.5YD5-TX: MIC5305, 1.5V Output Voltage, -40°C to +125°C Temp. Range, 5-Lead TSOT, 3,000/Reel Reverse
	2.7	= 2.7V (TSOT and VDFN only)			g) MIC5305-4.6YMT-TR: MIC5305, 4.6V Output Voltage, -40°C to +125°C Temp. Range, 6-Lead UDFN, 5,000/Reel
Output Voltage:	2.8	= 2.8V (All package options)			
	2.85	= 2.85V (TSOT and VDFN only)			
	2.9	= 2.9V (TSOT and VDFN only)			
	3.0	= 3.0V (TSOT and VDFN only)			
	3.3	= 3.3V (TSOT and VDFN only)			
	4.6	= 4.6V (VDFN or UDFN only)			
	4.75	= 4.75V (TSOT and VDFN only)			
Temperature Range:	Y	= -40°C to +125°C			
Package:	MT	= 6-Lead 2 mm x 2 mm UDFN			
	ML	= 6-Lead 2 mm x 2 mm VDFN			
	D5	= 5-Lead Thin SOT			
Media Type:	TR	= 3,000/Reel (TSOT only)			
	TR	= 5,000/Reel (UDFN and VDFN only)			
	TX	= 3,000/Reel, Rev. Tape & Reel (TSOT only)			

Note 1:	Tape and Reel identifier only appears in the catalog part number description. This identifier is used for ordering purposes and is not printed on the device package. Check with your Microchip Sales Office for package availability with the Tape and Reel option.
----------------	--

MARKING CODES

Part Number	Marking Code	Output Voltage	Package
MIC5305-1.5YML	815	1.5V	6-Lead 2 mm x 2 mm VDFN
MIC5305-1.8YML	818	1.8V	6-Lead 2 mm x 2 mm VDFN
MIC5305-2.5YML	825	2.5V	6-Lead 2 mm x 2 mm VDFN
MIC5305-2.6YML	826	2.6V	6-Lead 2 mm x 2 mm VDFN
MIC5305-2.7YML	827	2.7V	6-Lead 2 mm x 2 mm VDFN
MIC5305-2.8YML	828	2.8V	6-Lead 2 mm x 2 mm VDFN
MIC5305-2.85YML	82J	2.85V	6-Lead 2 mm x 2 mm VDFN
MIC5305-2.9YML	829	2.9V	6-Lead 2 mm x 2 mm VDFN
MIC5305-3.0YML	830	3.0V	6-Lead 2 mm x 2 mm VDFN
MIC5305-3.3YML	833	3.3V	6-Lead 2 mm x 2 mm VDFN
MIC5305-4.6YML	846	4.6V	6-Lead 2 mm x 2 mm VDFN
MIC5305-4.75YML	84H	4.75V	6-Lead 2 mm x 2 mm VDFN
MIC5305YML	8AA	Adjustable	6-Lead 2 mm x 2 mm VDFN
MIC5305-2.8YMT	828	2.8V	6-Lead 2 mm x 2 mm UDFN
MIC5305-4.6YMT	846	4.6V	6-Lead 2 mm x 2 mm UDFN
MIC5305-1.5YD5	N815	1.5V	5-Lead Thin SOT
MIC5305-1.8YD5	N818	1.8V	5-Lead Thin SOT

MIC5305

MARKING CODES

Part Number	Marking Code	Output Voltage	Package
MIC5305-2.5YD5	<u>N</u> 825	2.5V	5-Lead Thin SOT
MIC5305-2.6YD5	<u>N</u> 826	2.6V	5-Lead Thin SOT
MIC5305-2.7YD5	<u>N</u> 827	2.7V	5-Lead Thin SOT
MIC5305-2.8YD5	<u>N</u> 828	2.8V	5-Lead Thin SOT
MIC5305-2.85YD5	<u>N</u> 82J	2.85V	5-Lead Thin SOT
MIC5305-2.9YD5	<u>N</u> 829	2.9V	5-Lead Thin SOT
MIC5305-3.0YD5	<u>N</u> 830	3.0V	5-Lead Thin SOT
MIC5305-3.3YD5	<u>N</u> 833	3.3V	5-Lead Thin SOT
MIC5305-4.75YD5	<u>N</u> 84H	4.75V	5-Lead Thin SOT

Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
 - Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.
 - Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
 - Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that we are guaranteeing the product is "unbreakable" Code protection is constantly evolving. Microchip is committed to continuously improving the code protection features of our products.
-

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at <https://www.microchip.com/en-us/support/design-help/client-support-services>.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSEQUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, CryptoMemory, CryptoRF, dsPIC, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Klear, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricon, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, ClockWorks, The Embedded Control Solutions Company, EtherSynch, Flashtec, Hyper Speed Control, HyperLight Load, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, TimeCesium, TimeHub, TimePictra, TimeProvider, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, Clockstudio, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, EyeOpen, GridTime, IdealBridge, IGaT, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, IntelliMOS, Inter-Chip Connectivity, JitterBlocker, Knob-on-Display, MarginLink, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, mSiC, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICKit, PICtail, Power MOS IV, Power MOS 7, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SmartHLS, SMART-I.S., storClad, SQL, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, Trusted Time, TSHARC, Turing, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2024, Microchip Technology Incorporated and its subsidiaries.

All Rights Reserved.

ISBN: 978-1-6683-4498-9

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.

Worldwide Sales and Service

AMERICAS

Corporate Office
2355 West Chandler Blvd.
Chandler, AZ 85224-6199
Tel: 480-792-7200
Fax: 480-792-7277
Technical Support:
<http://www.microchip.com/support>
Web Address:
www.microchip.com

Atlanta
Duluth, GA
Tel: 678-957-9614
Fax: 678-957-1455

Austin, TX
Tel: 512-257-3370

Boston
Westborough, MA
Tel: 774-760-0087
Fax: 774-760-0088

Chicago
Itasca, IL
Tel: 630-285-0071
Fax: 630-285-0075

Dallas
Addison, TX
Tel: 972-818-7423
Fax: 972-818-2924

Detroit
Novi, MI
Tel: 248-848-4000

Houston, TX
Tel: 281-894-5983

Indianapolis
Noblesville, IN
Tel: 317-773-8323
Fax: 317-773-5453
Tel: 317-536-2380

Los Angeles
Mission Viejo, CA
Tel: 949-462-9523
Fax: 949-462-9608
Tel: 951-273-7800

Raleigh, NC
Tel: 919-844-7510

New York, NY
Tel: 631-435-6000

San Jose, CA
Tel: 408-735-9110
Tel: 408-436-4270

Canada - Toronto
Tel: 905-695-1980
Fax: 905-695-2078

ASIA/PACIFIC

Australia - Sydney
Tel: 61-2-9868-6733

China - Beijing
Tel: 86-10-8569-7000

China - Chengdu
Tel: 86-28-8665-5511

China - Chongqing
Tel: 86-23-8980-9588

China - Dongguan
Tel: 86-769-8702-9880

China - Guangzhou
Tel: 86-20-8755-8029

China - Hangzhou
Tel: 86-571-8792-8115

China - Hong Kong SAR
Tel: 852-2943-5100

China - Nanjing
Tel: 86-25-8473-2460

China - Qingdao
Tel: 86-532-8502-7355

China - Shanghai
Tel: 86-21-3326-8000

China - Shenyang
Tel: 86-24-2334-2829

China - Shenzhen
Tel: 86-755-8864-2200

China - Suzhou
Tel: 86-186-6233-1526

China - Wuhan
Tel: 86-27-5980-5300

China - Xian
Tel: 86-29-8833-7252

China - Xiamen
Tel: 86-592-2388138

China - Zhuhai
Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore
Tel: 91-80-3090-4444

India - New Delhi
Tel: 91-11-4160-8631

India - Pune
Tel: 91-20-4121-0141

Japan - Osaka
Tel: 81-6-6152-7160

Japan - Tokyo
Tel: 81-3-6880-3770

Korea - Daegu
Tel: 82-53-744-4301

Korea - Seoul
Tel: 82-2-554-7200

Malaysia - Kuala Lumpur
Tel: 60-3-7651-7906

Malaysia - Penang
Tel: 60-4-227-8870

Philippines - Manila
Tel: 63-2-634-9065

Singapore
Tel: 65-6334-8870

Taiwan - Hsin Chu
Tel: 886-3-577-8366

Taiwan - Kaohsiung
Tel: 886-7-213-7830

Taiwan - Taipei
Tel: 886-2-2508-8600

Thailand - Bangkok
Tel: 66-2-694-1351

Vietnam - Ho Chi Minh
Tel: 84-28-5448-2100

EUROPE

Austria - Wels
Tel: 43-7242-2244-39
Fax: 43-7242-2244-393

Denmark - Copenhagen
Tel: 45-4485-5910
Fax: 45-4485-2829

Finland - Espoo
Tel: 358-9-4520-820

France - Paris
Tel: 33-1-69-53-63-20
Fax: 33-1-69-30-90-79

Germany - Garching
Tel: 49-8931-9700

Germany - Haan
Tel: 49-2129-3766400

Germany - Heilbronn
Tel: 49-7131-72400

Germany - Karlsruhe
Tel: 49-721-625370

Germany - Munich
Tel: 49-89-627-144-0
Fax: 49-89-627-144-44

Germany - Rosenheim
Tel: 49-8031-354-560

Israel - Hod Hasharon
Tel: 972-9-775-5100

Italy - Milan
Tel: 39-0331-742611
Fax: 39-0331-466781

Italy - Padova
Tel: 39-049-7625286

Netherlands - Drunen
Tel: 31-416-690399
Fax: 31-416-690340

Norway - Trondheim
Tel: 47-7288-4388

Poland - Warsaw
Tel: 48-22-3325737

Romania - Bucharest
Tel: 40-21-407-87-50

Spain - Madrid
Tel: 34-91-708-08-90
Fax: 34-91-708-08-91

Sweden - Gothenberg
Tel: 46-31-704-60-40

Sweden - Stockholm
Tel: 46-8-5090-4654

UK - Wokingham
Tel: 44-118-921-5800
Fax: 44-118-921-5820