

Accessories

Cable clamps / Caps / Gaskets and seals / Housings for panel connectors / Screws and nuts / Ground kit / Couplings / Spare parts / Compound / Sleeves / End fittings / Threaded adaptors for connectors / Blanking plate kit / Cable glands / Union nuts / Contacts



Accessories



Cable clamp

Cable clamps are used to hold the cable in place and avoid traction on the wire / contacts connections.





Protective caps for panel-con. Protective caps for cable-con. Protective caps for cable-con.

Protective caps are designed to prevent foreign substances entering when the cable connector, coupler connector or panel connector are disconnected from each other.





Gaskets and seals

Seals are essential accessories to improve the tightness of our connectors.

Housings for panel connectors



Housing for panel connector Threaded adaptors

The housing is designed to protect the rear of the panel connector. It provides sealing and mechanical protection for the wires and contacts. Some housings provide 360° shielding continuity.



Screws and nuts

These screws and nuts are used to attach the panel connectors to the supporting walls.



Grounding kit for housing

For housings for the Standard, Rapid, Miniature, Industrial and Robotic Series.



Spare parts for circular panel connectors



Couplings for bare flexible hoses Couplings for covered flexible hoses

These couplings allow the attachment to one or more outlets of the housing of standardised flexible hoses (according to standards NF C68 100 and NF C68 161).



Sleeves

For B1 to B2 rectangular housings for the Standard, Rapid, Miniature, Industrial and Robotic Series.

Accessories

Connectors with non-removable contacts

Connectors with removable contacts

Accessories

End fittings



End fittings for soldering Pg and ISO threaded end fittings Crimp end fittings End fittings for pyrometer tubes

Threaded adaptors for connectors



Threaded adaptors for connectors

For panel connectors in the Standard, Rapid and Waterproof Series.

Blanking plate kit



Blanking plate kit

Blanking plate kit for the Standard, Rapid, Waterproof, Miniature, Industrial, Marine, Neptunox and Robotic Series.



Compound

Compound to coat the connections of all the Series.

Long cable gland



Long cable gland Short cable gland

Cable glands avoid traction on the wire / contact connections and improve the tightness of the connector.



Union nut

Couplings reduce traction on the wire / contact connections and improve the tightness of the connector.



Replacement contacts

Our contacts are designed to replace those in our connectors with removable contacts.

Dimensions and specifications may be changed without prior notice



Accessories – Cable clamps

Cable clamps for the Standard, Rapid, Miniature, Industrial and Industrial High-Performance Series

To support the cable, **cable connectors** and **coupler connectors** must be fitted with a connection accessory suitable for the diameter of the cable. Cable clamps support the cable and therefore avoid unnecessary and hazardous traction on the wire / contact connections. They are composed of a brass or light alloy barrel and two flanges assembled by two screws locked by toothed washers.

øΑ

These elements are protected by a nickel or olive-green cadmium coating. The cable clamps are held tightly together between the two shells of the cable connector or coupler connector housing or the housing of the panel connector for rectangular connectors, or are screwed at the rear of the body of the cable connector or coupler connector for circular connectors.





lype I							
Housing	Part Number	Ţ	Type 1 – Dimensions mm				
		ø A min.	ø B max.		C		
1	532 900 006	3	9		8,5		
1	532 894 006	7,5	9		11,5		
2	532 960 006	7	13		10,2		
3-4	532 940 006	12	18		13		
5	630 171 006	15	23		14,7		



Type 2							
Housing	Part Number	r Type 2 – Dimensions mm					
		ø A min.	ø B max.	ø C max.	D		
1	532 328 006	8,2	13	9	17,1		
2	532 329 006	11,8	18	13	20,1		
3-4	532 350 006	14,8	23	18	24		



Type 3					
Housing	Part Number	T	ype 3 – Din	nensions mi	n
		ø A min.	ø B max.		C
1	630 135 006	3	9		5
2	630 138 006	7	13		6
3-4	630 1 55 006	10	18		7
5	630 175 006	10	23		10



Type 1	High-Performance
--------	-------------------------

Housing	Part Number*	Ţ	Type 1 — Dimensions mm				
		ø A min.	ø B max.		C		
1	532 900 256	3	9		12,3		
2	532 960 256	7	13		13		

* olive-green cadmium coating, no RoHS





Pg end fitting with cable clamps

	Housing	Part Number		Dimensions mm					
			ø A max.	ø A min.	ø B	C	D	E (Pg)	
j	1	536 821 006	9	3	18	18,5	13	9	
	1	536 822 006	13	7	22	18,5	13	11	
j	3-4	536 823 006	18	10	26	22	17	16	

Type 2 High-Performance

Housing	Part Number*	Ŀ	Type 2 — Dimensions mm					
		ø A min.	D					
1	532 328 256	8,2	13	9	17,1			
2	532 329 256	11,8	18	13	20,1			



Type 3 High-Performance

	•					
Housing	Part Number*	Type 3 — Dimensions mm				
		ø A min.	ø B max.		C	
1	630 135 256	3	9		5	
2	630 138 256	7	13		6	

* olive-green cadmium coating, no RoHS



Accessories – Cable clamps

Cable clamps for the Waterproof Series

To support the cable, **cable connectors** and **coupler connectors** must be fitted with a connection accessory suitable for the diameter of the cable. Cable clamps support the cable and therefore avoid unnecessary and hazardous traction on the wire/contact connections. They are composed of a brass or light alloy barrel and two flanges assembled by two screws locked by toothed washers.

Housing	Nickel-	Part Number*	Capacity of the cable clamp		Dimensions mm		
	plated		ø A min.	ø A max.	ø B	C	Pg
1	633 421 006	633 421 256	7,5	12	23	16	11
2	633 422 006	633 422 256	10	17	30	19	16
3	633 423 006	633 423 256	15,5	23	39	28	21
4		633 424 256	15,8	24	48	28	29
5		633 425 256	19	32	56	34	36

* olive-green cadmium coating, no RoHS

These elements are protected by a nickel or olive-green cadmium coating. The cable clamps are screwed at the rear of the body of the cable connector or the coupler connector. Connectors with non-removable contacts

_



Accessories – Cable clamps

Cable clamps for the Miniature Push-Pull Series

To support the cable and ensure it is watertight, **cable connectors** and **coupler connectors** must be fitted with a connection accessory suitable for the diameter of the cable. Cable damps support the cable and therefore avoid unnecessary and hazardous traction on the wire / contact connections. They are composed of a brass or light alloy barrel and two flanges assembled by two screws locked by toothed





Housing	Part Number	Dimensions mm				
		ø A min.	ø A max.	ø B	C	
00	769 607 006	3,5	6	14,5	25	
0	769 619 006	6	9	17,5	31,5	
1	769 627 006	7	10	23,5	32,4	



Housing	Contacts	Part Number	Part Number	Dimensions mm			
		Standard	Cable Gland HP	ø A min.	ø A max.	ø B	C
00	3	530 331 006	530 692 006	4,5	6	14	15
00	4	530 841 006	530 844 006	4,5	6	14	15
0		530 371 006	530 693 006	5	8,5	18	16
1		769 627 006		7	10	23,5	32,4
1		769 628 006		5	8,5	23,5	32,4



Housing	Contacts	Part Number	Dimensions mm			
		Long Cable Gland	ø A min.	ø A max.	ø B	C
00	3	530 337 006	4,5	6	14	22
00	4	530 847 006	4,5	6	14	22
0		530 377 006	5	8,5	18	23

Dimensions and specifications may be changed without prior notice

Cable clamps for the Robotic Series

To support the cable, **cable connectors** and **coupler connectors** must be fitted with a connection accessory suitable for the diameter of the cable. Cable clamps support the cable and therefore avoid unnecessary and hazardous traction on the wire/contact connections. They are composed of a brass or light alloy barrel and two flanges assembled by two screws locked by toothed washers.

Dimension mm

ø B

11

14,5

18,5

A max.

8

11,5

15,4

øB

C

26,5

31,6

36,7

These elements are protected by a nickel coating. The cable clamps are held tightly together between the two shells of the cable connector or coupler connector housing or the housing of the panel connector.



Connectors with removable contacts

Accessories

echnical auides

JAEGER CONNECTEURS

Accessories – Cable clamps

Cable clamps for the Power Series Puissance

To support the cable, **cable connectors** and **coupler connectors** must be fitted with a connection accessory suitable for the diameter of the cable. Cable clamps support the cable and therefore avoid unnecessary and hazardous traction on the wire/contact connections. They are composed of a brass or light alloy barrel and two flanges assembled by two screws locked by toothed washers.

These elements are protected by a nickel coating or black anodising. The cable clamps are held tightly together between the two shells of the cable connector or coupler connector housing or the housing of the panel connector for rectangular connectors, or are screwed at the rear of the body of the cable connector or coupler connector for circular connectors.





Part Numbe

530 110 006

530 115 006

530 145 006

ø A min

2,3

7

10

Housing



Pg 36

Cable clamp for circular housing

Housing	Part Number	Dimensions mm								
		В	ø C	ø D min.	ø D max.					
5	809 605 006	73	56	20	32					
5	803 625 006	73	56	20	25					







Cable clamp for rectangular housing

Housing	Part Number	Dimensions mm								
		ø A	В	øC	ø D min.	ø D max.				
5	839 603 006	40	56	30	15	20				
5	839 604 006	40	56	30	15	23				
5	839 605 006	40	56	30	17	28				

RoHS

109



Accessories – **Protective caps**

Protective caps for the Standard, Rapid, Waterproof, Hermetic Series

Protective caps are designed to prevent foreign substances entering and to ensure the contacts in the Waterproof Series are sealed when the cable connector, coupler connector or panel connector are disconnected from each other.



Protective caps for male / female panel connector - metal

* olive-green cadmium coating, no RoHS

Housing	Standard	Rapid	Waterproof	Waterproof	Waterproof	Hermetic
	Series	Series	Series	HP * Series	Pg outlet Series	Series
1	536 910 006	536 910 006	536 910 006	536 910 256	536 910 006	536 910 006
2	536 911 006	536 911 006	536 911 006	536 911 256	536 911 006	536 911 006
3	536 912 006	536 846 006	536 912 006	536 912 256	536 912 006	536 912 006
4	536 913 006		536 913 006	536 913 256		536 913 006
5	536 914 006		536 914 006	539 914 256		536 914 006

Does not provide a watertight seal

Standard

Series

Housing

1

Protective caps for male / female panel connector - plastic

Rapid

Series

536 847 006 536 847 006 536 847 006

536 848 006 536 848 006 536 848 006

Series

RoHS

Hermetic

Protective caps for the Standard, Rapid, Waterproof, Hermetic Series

Protective caps are designed to prevent foreign substances entering and to ensure the contacts in the Waterproof Series are sealed when the cable connector, coupler connector or panel connector are disconnected from each other.





Standard – Rapid Series

Waterproof Series, HP (High-Performance), PG outlet

	ve caps					
			_		 	

Housing	Standard	Rapid	Waterproof	Waterproof	Waterproof	
	Series	Series	Series	HP * Series	Pg outlet Series	
1	532 260 006	532 260 006	532 270 006	532 270 256	532 270 006	
2	532 278 006	532 278 006	532 271 006	532 271 256	532 271 006	
3	532 262 006	532 218 006	532 262 206	532 262 256	532 262 206	
4	532 268 006		532 268 206	532 268 256	532 268 206	
5	532 269 006		532 269 206	532 269 256	532 269 206	







Waterproof Waterproof Waterproof

HP Series Pg outlet Series Series

536 847 006 536 847 006

536 848 006 536 848 006

Standard Series – Rapid

Waterproof Series, HP (High-Performance) , PG outlet

Protective caps for male cable connector - metal

Housing	Standard Rapid		Waterproof	Waterproof	Waterproof	
	Series	Series	Series	HP* Series	Pg outlet Series	
1	532 265 006	532 265 006	532 280 006	532 280 256	532 280 006	
2	532 279 006	532 279 006	532 281 006	532 281 256	532 281 006	
3	532 262 006	532 218 006	532 262 206	532 262 256	532 262 206	
4	532 268 006		532 268 206	532 268 256	532 268 206	
5	532 269 006		532 269 206	532 269 256	532 269 206	

* no RoHS

Accessories – **Protective caps**

Protective caps for the Standard, Rapid, Waterproof Series

Protective caps are designed to prevent foreign substances entering and to ensure the contacts in the Waterproof Series are sealed when the cable connector, coupler connector or panel connector are disconnected from each other.



Protective caps for male / female - metal coupler connector







RoHS

Protective caps for Miniature, Industrial, Waterproof Miniature, Industrial Waterproof and Industrial High-Performance Series

Protective caps are designed to prevent foreign substances entering and to ensure the contacts in the Waterproof Series are sealed when the cable connector, coupler connector or panel connector are disconnected from each other.



Connectors with removable contacts



Accessories – **Protective caps**

Protective caps for the Standard, Rapid, Waterproof Series

Protective caps are designed to prevent foreign substances entering and to ensure the contacts in the Waterproof Series are sealed when the cable connector, coupler connector or panel connector are disconnected from each other.



Protective caps for Atto and Natto Miniature Push-Pull Series

Protective caps are designed to prevent foreign substances entering and to ensure the contacts in the Waterproof Series are sealed when the cable connector, coupler connector or panel connector are disconnected from each other.



Protective caps — plastic Standard version









Protective caps – metal Standard version

Housing Part Number

00 533 610 006 0 533 650 006

761 907 006

Protective caps – nickel plated metal Standard version Housing Part Number





Protective caps – metal, black anodising High-Performance version



 0
 533 650 106

 1
 761 907 106



Protective caps - metal, black anodising High-Performance version Housing Part Number

00	536 620 106
0	536 660 106
1	536 610 106

RoHS

Dimensions and specifications may be changed without prior notice

Accessories – **Protective caps**

Protective caps for the Marine and Robotic Series

Protective caps are designed to prevent foreign substances entering and to ensure the contacts in the Marine Series are sealed when the cable connector, coupler connector or panel connector are disconnected from each other.



Protective caps – metal ARCAP (stainless steel)







1



RoHS

Connectors with non-removable contacts

Connectors with removable contacts

Accessories

echnical guides

Protective caps for the Neptunox Series

Protective caps are designed to prevent foreign substances entering and to ensure the contacts are sealed when the cable connector, coupler connector or panel connector are disconnected from each other.





Accessories – **Protective caps**

Protective caps for the Minex Series

Protective caps are designed to prevent foreign substances entering and to ensure the contacts are sealed when the cable connector, coupler connector or panel connector are disconnected from each other.









RoHS

Protective caps for the Power Series Puissance

Protective caps are designed to prevent foreign substances entering and to ensure the contacts are sealed when the cable connector, coupler connector or panel connector are disconnected from each other.





Accessories – Seals

Gaskets under panel connectors for the Standard, Rapid, Waterproof, Miniature, Industrial, Marine, Neptunox, Robotic Series

Seals are used to achieve an ingress protection rating of: IP 54/65 depending on the associated cable connector.





Housing	Pack of 10	Pack of 10	Dimensions in mm					
	neoprene gaskets under panel connector	Viton gaskets under panel connector for cable gland	А	ø B	øC	ø D	ø E	
1	536 945 006	536 945 026	27	21,1	3,2	28		
■ 2	536 946 006	536 946 026	32	27,2	3,5	34		
3	536 947 006		43	39,2	4,2	48		
• 4	536 126 006			45,2	4,2	54	63	
• 5	536 136 006			52,2	4,2	62	70	
■ 5	536 136 016		55	48	4,2	62		



Housing	Pack of 10 cable connector seals	Dimensio ø E	ns in mm ø F
1	532 510 006	19	2
2	532 511 006	25,5	1,8
3	532 512 006	36,5	2,5
4	532 514 006	41	2
5	532 516 006	46	2

Accessories

echnical guides

Gaskets under panel connector for Minex Series

Seals are used to achieve an ingress protection rating of: IP 54/65 depending on the associated cable connector.



Flat-Gasket for panel connector

Number	Pack of 10
of Cts	neoprene gaskets under panel connector
3	633 121 006
7	633 124 006

Seals for the Power Series Puissance



RoHS



Accessories - Housings for panel connector

Gaskets under panel connector for Atto and Natto Miniature Push-Pull Series

Seals are used to achieve an ingress protection rating of: IP 54/65 depending on the associated cable connector.



Housing	Pack of 10	Pack of 10					
	neoprene gaskets under panel connector	viton gaskets under panel connector for cable					
00	533 328 006	533 328 016					
0	533 368 006	533 368 016					
1	536 945 006	536 945 016					

RoHS

Housings for panel connectors in the Standard and Rapid Series





A														
Housing	Number of	Complet housing			Acces	sories			Housi	ng		Di	mensions n	nm
	Contacts	ISO screws		Cable clamp	10 gaskets under panel connector	pack of 100 ISO screws	En	d fittings for soldering		Α	B	C	ø D	
1	3-4-6	536 935 006		532 900 006	536 945 006	504 222 006		042 547 006	1	41	27	32,2	M 3	9
1	3-4-6	536 935 006	or	532 328 006	536 945 006	504 222 006	or	532 998 006	2	45,4	32	36,4	M 3	
1	3-4-6	536 935 006	or	630 135 006	536 945 006	504 222 006	or	042 937 006	3	52,6	43	47,6	M 4	1
2	4 (ø4)-8-12	536 937 006		532 960 006	536 946 006	504 222 006		532 955 006	4	58	47	53,8	M 4	1
2	4 (ø4)-8-12	536 937 006	or	532 329 006	536 946 006	504 222 006		532 955 006	5	65	54	61,5	M 4	1
2	4 (ø4)-8-12	536 937 006	or	630 138 006	536 946 006	504 222 006		532 955 006						
3	17	536 996 006		532 940 006	536 947 006	504 266 006		042 940 006						
3	17	536 996 006	or	532 350 006	536 947 006	504 266 006	or	042 943 006						
3	17	536 996 006	or	630 155 006	536 947 006	504 266 006								
4	25	536 880 006		532 940 006		504 266 006		042 940 006						
4	25	536 880 006	or	532 350 006		504 266 006	or	042 943 006						
4	25	536 880 006	or	630 155 006		504 266 006								
5	35-52	536 881 006		630 171 006	536 136 016	504 266 006		042 945 006						
5	35-52	536 881 006	or	630 175 006	536 136 016	504 266 006		042 945 006						

F

F

5

5

6

6

6

E 9

9

10

10

10

ø G

28

34

48 54

62

Accessories – Housings for panel connector



Threaded adaptors for connectors in the Atto and Natto Miniature Push-Pull Series

	Standard	Cable Gland	А	В	C	D
00	533 348 006	533 348 106	M11,5	18	7	15
0	533 349 006	533 349 106	M15	20	7	15
1	533 347 006	533 347 016	M 20	27	11	19
1	536 866 006	536 866 016	Pg 16	27	10,5	20,5

Housings for panel connectors in the Miniature and Industrial Series



:	(Barren		
	۲	۲	
	В		C

Housing	Housing for	Cable clamp		
	panel connector		page 106	
1	533 550 006		532 894 006	
1	533 550 006	or	532 328 006	
1	533 550 006	or	630 135 006	
2	533 558 006		532 960 006	
2	533 558 006	or	532 329 006	
2	533 558 006	or	630 138 006	
3	533 559 006		532 940 006	
3	533 559 006	or	532 350 006	
3	533 559 006	or	630 155 006	

Housing	Dimension mm				
	Α	В	C		
1	32,2	32,2	20,2		
2	36,4	36,4	23,5		
3	47.6	42.6	31.3		

RoHS













Accessories – **Couplings**

Couplings for bare flexible hoses in the Standard, Rapid, Miniature, Industrial and Robotic Series

For rectangular housings B1 to B5.

These couplings can be fitted to the cable connectors and coupler connectors with rectangular housing and housings for panel connectors. They allow the attachment to one or more outlets of the housing of standardised flexible hoses (according to standards NF C68 100 and NF C68 161). These metal hoses with no sheaths may be simple interlock or semi-waterproof.

Type 1, couplings without cable clamp



Type 1

532 967 006

532 968 006

532 969 006

1

3-4

ø

Bare Cable

9

12

17

Type 2

couplings with

532 962 006

532 963 006

532 964 006

532 965 006



min

7

9

12,5

12,5

Clamping ø

max

9

12

17

17



Flexible Hoses

ø mm

9,5 x 12,3

12 x 15

17,5 x 20,5

17,5 x 20,5

Designation

MSB 7-7

MSB 7-9

MSB 7-13

MSB 7-13

They may also be covered with shielding braid. These couplings consist of a barrel held tightly between the two shells of the cable connector, the coupler connector or the housing for panel connector and a ring with a left-hand thread. The hose is held between the two parts.

A cable clamp is incorporated into the barrel of type two couplings in order to reduce the force exerted on the cable. Barrel and nut are made of nickel-plated brass.

ø (øΕ

Туре	Housing		Dimension	ns in mm		Clampi	ing ø E	Weight
		Α	В	øC	ø D	min.	max.	in g
1	1	16,5	14,5	19	9			15
1	2	18	16	21	12			18
1	3-4-5	22,5	19,5	27	17			34
2	1	22,5	20,5	19		7	9	18
2	2	27	24	21		9	12	28
2	3-4-5	31,5	28,5	27		12,5	17	45

the coupler connector or the housing for panel connector and a ring with a left-hand thread.

The hose is held tightly between the two parts and the plastic sheath is gripped between the two

tapered seatings of the ring. A cable clamp is incorporated into the barrel of type 2 couplings

Couplings for covered flexible hoses in the Standard, Rapid, Miniature, Industrial and Robotic Series

For rectangular housings B1 to B5.

These couplings can be fitted to the cable connectors and coupler connectors with rectangular housing and housings for panel connectors. They allow the attachment to one or more outlets of the housing of standardised flexible hoses (according to standards NF C68 100 and NF C68 161). These couplings consist of a barrel held tightly between the two shells of the cable connector,

Type 2

530 133 006

530 134 006

530 135 006

ptings with ble clare

Type 1, couplings without cable clamp

Type 1

ouplings withou cable clamp

530 130 006

530 131 006

530 132 006

1

2

3-4

- 5

ø

Bare Cable

9

11

15

23





Clamping ø

max

9

11

15

23

min

7

9

12,5

15



Type 2, couplings with cable clamp

Flexible Hoses

ø mm

9 x 12.3

11 x 15

15 x 20,4

23 x 28,2

Designation

MSB 7-7

MSB 7-9

MSB 7-13

MSB 7-21



in order to reduce the force exerted on the cable.

Barrel and nut are made of nickel-plated brass.



Туре	Housing		Dimensions in mm			Clampi	ng ø E	Weight
		Α	В	ø C	ø D	min.	max.	in g
1	1	16,5	14,5	19	9			15
1	2	18	16	21	11			18
1	3-4	22,5	19,5	27	15			32
1	5	28	24	36	23			60
2	1	22,5	20,5	19		7	9	13
2	2	27	24	21		9	11	25
2	3-4	31,5	28,5	27		12,5	17	45
2	5	44	40	36		15	23	90

RoHS



Spare parts for circular panel connectors



Housing	Number of Contacts	Pack of 10 gaskets	Nut	Locknut
1	3-4-6	536 440 006	536 446 006	536 443 006
2	4 (ø 4)-8-12	536 441 006	536 447 006	536 444 006
3	17	536 442 006	536 448 006	
4	25	536 451 006	536 450 006	
5	35-52	536 454 006	536 453 006	

RoHS

Sealing accessory: Compound for all series

Compound to coat the connections.

Compound tube 100g 532 080 006



Type: Silicone elastomer, cold self-curing by contact with water or atmospheric humidity without the addition of a catalyst.

Aim: This product provides protection and waterproofing for the connections in the connectors, particularly in certain harsh operating conditions:

- very high ambient humidity, splashes of liquid or immersion;
- high ambient temperature;
- severe vibrations

The use of this product is not restricted to electrical connections.

Characteristics after curing:

Mechanical data:

- -Tensile force: 35 daN / cm²
- Shore A hardness: 45
- Density at 20 °C: 1,2
- Operating temperature: -70 °C to +200 °C

Electrical data:

Characteristics	Dry sample	Sample after 24 hours immersed in water
Volume resistivity	10º MΩ. cm	2 x 108 MΩ. cm
Losses (tangent of the angle) for frequency = 1MHz	3 x 10 ⁻³	5 x 10 ⁻³
Electric constant	3 ± 0,2	$3 \pm 0,2$
Dielectric strength	20000 V/mm	18000 V/mm

Resistance to chemical agents:

- (after 8 days of immersion at 25 °C)
- Hot water (85 °C): good resistance
- Boiling water: significant degradation after one month
- of immersion.
- Ethyl alcohol: no swelling

Solvents:

- Acetone: no swelling
- Mineral spirits: significant swelling
- Trichlorethylene: significant swelling
- Fuel: significant swelling
- Kerosene JP4: significant swelling

Oils:

- Oil ASTM N° 1: no swelling
- Oil ASTM N° 3: no swelling

Acids:

- Sulphuric acid 66 °B: no swelling
- Nitric acid 40 °B: no swelling
- Hydrochloric acid 22 °B: no swelling

Bases:

- Sodium hydroxide 36 °B: no swelling
- Ammonia: no swelling

Application:

- Easy and immediate application without prior mixing.
- Curing in the air (7 to 10 hours).
- See instructions with the packaging each tub.

Precautions:

- After use, carefully squeeze out any air remaining
- in the neck of the tube and replace the cap.
- Avoid storing the tube at temperatures
- higher than 40 °C.



Connectors with non-removable contacts

Connectors with removable contacts

Accessories

echnical guides

Accessories for sealable connectors for the Standard, Rapid, Miniature, Industrial and Robotic Series For rectangular housings B1 to B2. Drilling for screws Housing Pack of screws for Pack of screws for Drilling ø for the Material panel connector* cable connector* head of screw 536 810 006 1 536 812 006 1,2 mm Stainless steel 536 810 006 536 813 006 1,2 mm Stainless steel * The sealing of a Cable connector / Panel connector assembly requires the use of: 1 pack for panel connector 1 screw + 1 pack for cable connector 2 screws

RoHS

Sleeves for the Standard, Rapid, Miniature, Industrial and Robotic Series

For rectangular housings B1 to B2. Used as a grommet, it protects the connection soldering against the bending forces exerted on the electric cable.

The moulded synthetic rubber sleeve is held between the two shells of the cable connectors, coupler connectors or panel connector housings. It is suitable for cables with insulating sheaths (plastic or rubber). Operating temperature: -25 °C to +100 °C



Housing	Sleeve	Connection cable (mm)		
		ø min.	ø max.	
1	532 970 006	5*	5,5	
2	532 975 006	9*	10	

* N.B. for cables having a diameter less than the minimum value, use an intermediate sleeve (approximately 60 mm in length), e.g. a heat-shrinkable sheath.



Accessories – End fittings

Weld-on end fittings for the Standard, Rapid, Miniature, Industrial and Robotic Series

For rectangular housings B1 to B5.



Housing	Part Number	Dimension and		D	imensions m	m		Weight in
		No. of the sheath	ø A	ø B	C	D	ø E	grams
1	042 937 006	7,5 x 10,5 mm - No. 5	7,5	10,8	15	9,9	6,4	7
1	042 547 006	10,5 x 14 mm - No. 7	10,4	14,9	15	11,3	9,2	7
1	532 998 006*	9,5 x 12,5 mm - MSB 7	9	12,9	15,5	10,4	8	4
2	532 955 006*	12 x 15,2 mm - MSB 9	12	16,5	15	9,7	10,8	5
3-4	042 940 006	15 x 19 mm - No. 11	15	20,1	21,5	17	13,9	11
3-4	042 943 006	19 x 23 mm - No. 16	18,8	24,1	19,5	15	17	18
5	042 945 006*	19 x 23 mm - No. 16	18,7	24,2	19,4	14,9	17	

*These end fittings are designed to be connected to AFNOR standardised flexible metal hose according to standards NFC 68 100 and NFC 68 161. These end fittings allow the attachment to one or more of the housing outlets of a flexible protective sheath or a braided metal sheath for shielded cables or a grounding braid. The end fitting is held tightly between the two shells of the cable connector, the coupler connector or the housing of the panel connector.

RoHS

End fittings with Pg and ISO thread* for the Standard, Rapid, Miniature, Industrial, Robotic Series

For rectangular housings B1 to B5.



Promer-Pma, Rudolph, SE Sterling, Sonolia, S.T.B, Textilver, T.F.T. These end fittings are brass protected by nickel-plating.







Blanking plate kit for the Standard, Rapid, Waterproof, Miniature, Industrial, Marine, Neptunox and Robotic Series

This blanking plate kit is designed to seal the hole made in the wall to attach the panel connector when it is no longer needed. After removing the panel connector, fit the seal and then the blanking plate. Then screw in place using 4 screws, nuts and washers.

This blanking plate kit contains: a flat-gasket for panel connector, 4 screws, 4 washers, 4 nuts and a square blanking plate.

Material: nickel-plated brass





RoHS

1

Replacement ground terminal ø 1 mm for the Robotic Series

Cable connector	Pack of 10
Coupler Connector	
Male / Female	638 004 016

Cable cross-section: 0,6 mm² to 1,9 mm²

Accessories - Cable gland

Long cable gland (with claw and/or 360° shield connection) for the Atto and Natto Miniature Push-Pull Series



øA	h
ø B	- (

Housing	Standard	360° Shielding	Dimensions mm			
	Part Number	Part Number	ø A	ø B min.	ø B max.	C
00	769 807 006	769 907 006	14	3,6	6,8	25,8
0	769 819 006	769 919 006	17,5	4,6	8,5	31,2
1		769 927 006	22,5	10	13	39,5

RoHS

Short cable gland (without claw) for Atto and Natto Miniature Push-Pull Series



Housing	Standard	360° Shielding		Dimensions mm		
	Part Number	Part Number	ø A	ø B min.	ø B max.	C
00	530 332 006	530 694 006	14	3,6	6,7	18,2
0	530 372 006	530 695 006	17,5	6,3	9	23,8

Union nut for the Natto Miniature Push-Pull Series



Housing	Contacts	Part Number	Dimensions mm		
			ø A	ø B	C
00	3	530 330 006	14	11,3	6
00	4	530 840 006	14	11,3	6
0		530 370 006	17,5	12	7,8

To ensure the cable is watertight and to guarantee the mechanical resistance, cable connectors and coupler connectors must be fitted with a connection accessory to be selected from the following items, according to the diameter of the cable.

Connectors with non-removable contacts

RoHS



Accessories - Replacement contacts



Replacement contacts ø 1 mm for the Miniature, Natto Miniature Push-Pull, Marine, Neptunox and Robotic Series

										socket
Contacts	Pack of	Pack of	Pack of	Pack of	Pack of	Pack of	Pack of	Pack of	Pack of	
	3 contacts*	4 contacts*	7 contacts*	12 contacts**	19 contacts**	27 contacts**	37 contacts**	55 contacts**	100 contacts*	
Pins	530 303 006	533 877 006	530 307 006	530 311 006	530 313 006	530 315 006	530 317 006	530 319 006	530 211 506	pin
Sockets	530 302 006	533 876 006	530 306 006	530 310 006	530 312 006	530 314 006	530 316 006	530 318 006	530 213 506	

* For connectors with 3, 4 and 7 contacts: contact length 14,5 mm

** For connectors with 12, 19, 27, 37 and 55 contacts: contact length 17,5 mm

Replacement contacts ø 1,6 mm for the Natto Miniature Push-Pull, Industrial, Marine, Neptunox and Robotic Series

Contacts	Pack of					
	3 contacts	7 contacts	12 contacts	19 contacts	27 contacts	100 contacts
Pins	630 643 006	630 643 006	630 642 006	630 649 006	630 677 006	630 800 006
Sockets	630 633 006	630 637 006	630 632 006	630 639 006	630 667 006	630 700 006

Replacement contacts ø 2,4 mm for the Natto Miniature Push-Pull, Industrial, Marine, Neptunox and Robotic Series

Contacts	Pack of	Pack of Pack of		Pack of	
	3 contacts	4 contacts	7 contacts	12 contacts	
Pins	630 843 006	630 844 006	630 847 006	630 842 006	
Sockets	630 833 006	630 834 006	630 837 006	630 832 006	



socket

-

RoHS

RoHS

socket

Accessories – Replacement contacts

Replacement contacts: 17 mixed contacts ø 1 mm and ø 2,4 mm for the Industrial and Robotic Series



13 contacts ø 1 mm and 3 contacts de ø 2,4 mm



Connectors with non-removable contacts

Replacement contacts for the Power Series Puissance

Cross-section	Con	tacts	Part Number		
of the cable	ø (mm)	No. of contacts per pack	Pins pack	Sockets pack	
	1,6	2	630 643 006	630 633 006	
25 mm ²	8	3	807 103 006	807 203 006	
25 mm ²	8	4	807 104 006	807 204 006	
35 mm²	8	3	807 103 356	807 203 356	
95 mm²	12	2	897 101 106	897 201 006	

Replacement contacts for the Minex Series

Contacts	Pack of	Pack of
	3 contacts	7 contacts
Pins	530 303 006	530 307 006
Sockets	530 302 506	530 306 506



RoHS

Accessories

Accessories - Contacts for Thermocouples

Thermocouple data

In 1821, Seebeck discovered that an electric current flows in a closed loop with two wires made of different metals if the temperature of one of the two junctions is higher than that of the other. This bimetallic combination was called a **thermocouple**.

If one of the junctions is open whilst keeping its two ends at the same temperature, the electromotive force measured between the two ends depends on the difference in temperature between the two junctions more precisely, the electromotive force depends on the temperature of a single junction if the other is maintained at constant temperature.

Different combinations of metals and alloys were tested to form a thermocouple or thermoelectric couple. The main types of pairs selected are:

- Type S: a platinum rhodium 10% component and a platinum component
- Type J: an iron component and a constantan component
- Type T: a copper component and a constantan component
- Type K: a chromel component and an alumel component
- Type E: a chromel component and a constantan component

There are other thermocouples but they are less commonly used. The thermoelectric properties thus discovered gave rise to temperature measurement in industry. Some examples of use: pyrometer tubes, freeze-driers, medical, engine bearing temperature control, etc.

The choice of thermocouple is governed by:

- The temperature range to be measured
- its resistance to pollution and corrosion
- the resistance of the thermocouple for a given gas atmosphere

Туре	Colour Code	Conductor	Conductor	Temperature	Application recommended in atmospheres				
	Norme: IEC 584.3	+	-		vacuum	oxidizing	reducing	inert	gaseous
К	Green	Chromel	Alumel	-270 °C +1370 °C		х		х	Air argon
T	Brown	Copper	Constantan	-270 °C +400 °C		х	х		Air argon nitrogen
J	Black	Iron	Constantan	-210 °C +1200 °C	х	х	х	х	Air argon nitrogen
S	Yellow	Platine Rhodium 10 % Rh	Platinum	-50 °C +1760 °C		х			Air
E	Purple	Chromel	Constantan	-270 °C +1000 °C		х		х	Air argon

Part Numbers for thermocouple contacts for our Series of connectors with removable contacts

Natto Miniature Push-Pull Series, Miniature Series, Industrial Series, Marine Series, Robotic Series, Minex Series

- These thermocouple contacts, male or female, are interchangeable with the "Standard" contacts for the series listed above.

- The following are sold in packs under each part number: either two pins or two sockets, each pair of contacts making up a couple.
- In each pack, the positive + contact is the shortest pin or socket.

For	Couple — Type K		Couple — Type J		Couple — Type T		Couple — Type S		Couple — Type E	
connector	Chromel +	Alumel -	Iron +	Constantan -	Copper +	Constantan -	Platinum Rodium 10% +	Platinum -	Chromel +	Constantan -
	Pack of 2	Pack of 2	Pack of 2	Pack of 2	Pack of 2	Pack of 2	Pack of 2	Pack of 2	Pack of 2	Pack of 2
	pins	sockets	pins	sockets	pins	sockets	pins	sockets	pins	sockets
ø 1 mm-B0-B00	530 350 006	530 351 006	530 352 006	530 353 006	530 354 006	530 355 006	530 366 006	530 367 006	503 364 006	530 365 006
3-4-7 cts										
ø 1 mm 12-19-27	530 356 006	530 357 006	530 358 006	530 359 006	530 360 006	530 361 006	530 368 006	530 369 006	530 308 006	530 309 006
37-55 contacts										
ø 1,6 mm 3-4-7	630 650 006	630 651 006	630 652 006	630 653 006	630 654 006	630 655 006	630 655 006	630 657 006		
12-19-27 contacts										