# **MIC2287**

## 1.2 MHz PWM White LED Driver with OVP

### **Features**

- · 2.5V to 10V Input Voltage
- · Output Voltage Up to 34V
- · Over 500 mA Switch Current
- · 1.2 MHz PWM Operation
- · 95 mV Feedback Voltage
- · Output Overvoltage Protection (OVP)
- Options for 15V, 24V, and 34V OVP
- <1% Line and Load Regulation</li>
- <1 µA Shutdown Current</li>
- · Overtemperature Protection
- UVLO
- · Low Profile Thin SOT-23-5 Package Option
- 8-Lead 2 mm x 2 mm VDFN Package Option
- -40°C to +125°C Junction Temperature Range

### **Applications**

- · White LED Driver for Backlighting:
  - Cell Phones
  - PDAs
  - GPS Systems
  - Digital Cameras
  - MP3 Players
  - IP Phones
- Photo Flash LED Driver
- · LED Flashlights
- · Constant Current Power Supplies

### **General Description**

The MIC2287 is a 1.2 MHz pulse width modulated (PWM), boost-switching regulator that is optimized for constant current, white LED driver applications. With a maximum output voltage of 34V and a switch current of over 500 mA, the MIC2287 easily drives a string of up to 8 white LEDs in series, ensuring uniform brightness and eliminating several ballast resistors.

The MIC2287 implements a constant frequency, 1.2 MHz PWM control scheme. The high frequency PWM operation saves board space by reducing external component sizes. The added benefit of the constant frequency PWM scheme as opposed to variable frequency topologies is much lower noise and input ripple injected back to the battery source.

To optimize efficiency, the feedback voltage is set to only 95 mV. This reduces the power dissipation in the current set resistor and allows the lowest total output voltage, hence minimal current draw from the battery.


The MIC2287 is available with three levels of overvoltage protection: 15V, 24V, and 34V. This allows designers to choose the smallest possible external components with the appropriate voltage ratings for their applications.

The MIC2287 is available in low profile 5-lead Thin SOT-23 and an 8-lead 2 mm x 2 mm VDFN package options. The MIC2287 has a junction temperature range of  $-40^{\circ}$ C to  $+125^{\circ}$ C.


### **Package Types**



## **Typical Application Circuits**



## **Functional Block Diagram**



### 1.0 ELECTRICAL CHARACTERISTICS

### **Absolute Maximum Ratings †**

| Supply Voltage (V <sub>IN</sub> )     | +12\ |
|---------------------------------------|------|
| Switch Voltage (V <sub>SW</sub> )     |      |
| Enable Pin Voltage (V <sub>EN</sub> ) |      |
| Feedback Voltage (V <sub>FB</sub> )   |      |
| Switch Current (I <sub>SW</sub> )     |      |
| ESD Rating (Note 1)                   |      |

### **Operating Ratings ‡**

Supply Voltage (V<sub>IN</sub>) ......+2.5V to +10V

**† Notice:** Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

**‡ Notice:** The device is not guaranteed to function outside its operating ratings.

Note 1: Device is ESD sensitive. Handling precautions are recommended. Human body model.

### **ELECTRICAL CHARACTERISTICS**

 $T_A$  = +25°C,  $V_{IN}$  =  $V_{EN}$  = 3.6V,  $V_{OUT}$  = 10V,  $I_{OUT}$  = 10 mA, unless otherwise noted. **Bold** values valid for –40°C ≤  $T_J$  ≤ +125°C; unless noted. Note 1

| Parameter                 | Symbol            | Min. | Тур.             | Max. | Units | Conditions                                  |
|---------------------------|-------------------|------|------------------|------|-------|---|
| Supply Voltage Range      | V <sub>IN</sub>   | 2.5  | _                | 10   | V     | _   |
| Undervoltage Lockout      | V <sub>UVLO</sub> | 1.8  | 2.1              | 2.4  | V     | _   |
| Quiescent Current         | I <sub>VIN</sub>  | _    | 2.5              | 5    | mA    | V <sub>FB</sub> > 200 mV, (not switching)   |
| Shutdown Current          | I <sub>SD</sub>   | _    | 0.1              | 1    | μA    | V <sub>EN</sub> = 0V, Note 2                |
| Feedback Voltage          | V <sub>FB</sub>   | 90   | 95               | 100  | mV    | ±5%   |
| Feedback Input Current    | I <sub>FB</sub>   | _    | <del>-4</del> 50 | _    | nA    | V <sub>FB</sub> = 95 mV                     |
| Line Regulation (Note 3)  | _                 | _    | 0.5              | 1    | %     | 3V ≤ V <sub>IN</sub> ≤ 5V                   |
| Load Regulation (Note 3)  | _                 | _    | 0.5              | 2    | %     | 5 mA ≤ I <sub>OUT</sub> ≤ 20 mA             |
| Maximum Duty Cycle        | D <sub>MAX</sub>  | 85   | 90               | _    | %     | _   |
| Switch Current Limit      | I <sub>SW</sub>   | _    | 750              | _    | mA    | _   |
| Switch Saturation Voltage | V <sub>SW</sub>   | _    | 450              | _    | mV    | I <sub>SW</sub> = 0.5A                      |
| Switch Leakage Current    | I <sub>SW</sub>   | _    | 0.01             | 5    | μA    | V <sub>EN</sub> = 0V, V <sub>SW</sub> = 10V |
| Enable Threshold          | V                 | 1.5  | _                | _    | V     | Turn on                                     |
| Ellable Tillesliold       | V <sub>EN</sub>   | _    | _                | 0.4  | V     | Turn off                                    |
| Enable Pin Current        | I <sub>EN</sub>   | _    | 20               | 40   | μA    | V <sub>EN</sub> = 10V                       |
| Oscillator Frequency      | f <sub>SW</sub>   | 1.05 | 1.2              | 1.35 | MHz   | _   |
|                           |                   | 13   | 14               | 16   |       | MIC2287YML-15                               |
| Overvoltage Protection    | V <sub>OVP</sub>  | 21   | 22.5             | 24   | V     | MIC2287YML-24                               |
|                           |                   | 30   | 32               | 34   |       | MIC2287YML-34                               |
| Overtemperature Threshold | _                 | _    | 150              | _    | °C    | _   |
| Shutdown                  | T <sub>J</sub>    | _    | 10               | _    |       | Hysteresis                                  |

**Note 1:** Specifications for packaged product only.

- **2:**  $I_{SD} = I_{VIN}$ .
- 3: Ensured by design.

## **MIC2287**


## **TEMPERATURE SPECIFICATIONS**

| Parameters                       | Sym.           | Min. | Тур. | Max. | Units | Conditions |
|----------------------------------|----------------|------|------|------|-------|------------|
| Temperature Ranges               |                |      |      |      |       |            |
| Junction Temperature Range       | TJ             | -40  | _    | +125 | °C    | _          |
| Storage Temperature Range        | T <sub>S</sub> | -65  | _    | +150 | °C    | _          |
| Package Thermal Resistances      |                |      |      |      | •     |            |
| Thermal Resistance, VDFN 8-Ld    | $\theta_{JA}$  | _    | 93   | _    | °C/W  | _          |
| Thermal Resistance, TSOT-23 5-Ld | $\theta_{JA}$  | _    | 256  | _    | °C/W  | _          |

### 2.0 TYPICAL PERFORMANCE CURVES

Note:

The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.



**FIGURE 2-1:** Feedback Voltage vs. Input Voltage.




FIGURE 2-4: 3-Series LED Efficiency.




FIGURE 2-2: Shutdown Current vs. Input Voltage.






FIGURE 2-5: 6-Series LED Efficiency.



**FIGURE 2-3:** Quiescent Current vs. Input Voltage.



**FIGURE 2-6:** Switch Frequency vs. Temperature.




FIGURE 2-7: Temperature.

EN Pin Bias Current vs.




FIGURE 2-8: Temperature.

Saturation Voltage vs.






FIGURE 2-9: Temperature.

Current Limit vs.




**FIGURE 2-10:** vs. Current.

Switch Saturation Voltage



**FIGURE 2-11:** 6-Series LED Circuit without External Soft-Start.



**FIGURE 2-12:** 6-Series LED Circuit with External Soft-Start.

## 3.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in Table 3-1.

TABLE 3-1: PIN FUNCTION TABLE

| Pin Number<br>TSOT-23 | Pin Number<br>VDFN | Pin<br>Name | Description   |
|-----------------------|--------------------|-------------|---|
| 1                     | 7                  | SW          | Switch Node (Input): Internal power bipolar collector.  |
| 2                     | _                  | GND         | Ground (Return): Ground.  |
| 3                     | 6                  | FB          | Feedback (Input): Output voltage sense node. Connect the cathode of the LED to this pin. A resistor from this pin to Ground sets the LED current. |
| 4                     | 3                  | EN          | Enable (Input): Logic high enables the regulator. Logic low shuts down the regulator.   |
| 5                     | 2                  | VIN         | Supply (Input): 2.5V to 10V for internal circuitry.   |
| _                     | 1                  | OVP         | Overvoltage Protection (Input): Connect to the output.  |
| _                     | 4                  | AGND        | Analog ground.  |
| _                     | 8                  | PGND        | Power ground.   |
| _                     | 5                  | NC          | No connect (no internal connection to die).   |
| _                     | EP                 | GND         | Ground (Return): Exposed backside pad.  |

### 4.0 FUNCTIONAL DESCRIPTION

The MIC2287 is a constant frequency, PWM current mode boost regulator (see the Functional Block Diagram). The MIC2287 is composed of an oscillator, slope compensation ramp generator, current amplifier, g<sub>m</sub> error amplifier, PWM generator, and a 500 mA bipolar output transistor. The oscillator generates a 1.2 MHz clock. The clock's two functions are to trigger the PWM generator that turns on the output transistor and to reset the slope compensation ramp generator. The current amplifier is used to measure the switch current by amplifying the voltage signal from the internal sense resistor. The output of the current amplifier is summed with the output of the slope compensation ramp generator. This summed current-loop signal is fed to one of the inputs of the PWM generator.

The  $g_m$  error amplifier measures the LED current through the external sense resistor and amplifies the error between the detected signal and the 95 mV reference voltage. The output of the  $g_m$  error amplifier provides the voltage-loop signal that is fed to the other input of the PWM generator. When the current-loop signal exceeds the voltage-loop signal, the PWM generator turns off the bipolar output transistor. The next clock period initiates the next switching cycle, maintaining the constant frequency current-mode PWM control. The LED is set by the feedback resistor:

### **EQUATION 4-1:**

$$I_{LED} = \frac{95mV}{R_{FB}}$$

The Enable pin shuts down the output switching and disables control circuitry to reduce input current-to-leakage levels. Enable pin input current is zero at zero volts.

## 5.0 EXTERNAL COMPONENT SELECTION

The MIC2287 can be used across a wide rage of applications. Table 5-1 shows recommended inductor and output capacitor values for various series-LED applications.

TABLE 5-1: RECOMMENDED INDUCTOR & OUTPUT CAPACITOR VALUES

| Series<br>LEDs | L  | Manufacturer                                    | Min.<br>C <sub>OUT</sub> | Manufacturer                                  |
|----------------|--|---|--------------------------|---|
|                | 22 µH  | LQH32CN220K21 (Murata)<br>NLC453232T-220K (TDK) | 2.2 µF                   | 0805ZD225KAT (AVX)<br>GRM40X5R225K10 (Murata) |
|                | 15 µH  | LQH32CN150K21 (Murata)<br>NLC453232T-150K (TDK) | 1 µF                     | 0805ZD105KAT (AVX)<br>GRM40X5R105K10 (Murata) |
| 2              | 10 µH  | LQH32CN100K21 (Murata)<br>NLC453232T-100K (TDK) | 0.22 μF                  | 0805ZD224KAT (AVX)<br>GRM40X5R224K10 (Murata) |
|                | 6.8 µH   | LQH32CN6R8K21 (Murata)<br>NLC453232T-6R8K (TDK) | 0.22 µF                  | 0805ZD225KAT (AVX)<br>GRM40X5R225K10 (Murata) |
|                | 4.7 µH   | LQH32CN4R7K21 (Murata)<br>NLC453232T-4R7K (TDK) | 0.22 μF                  | 0805ZD224KAT (AVX)<br>GRM40X5R224K10 (Murata) |
|                | 22 µH  | LOH/3MN220K21 (Murata)                          |                          | 0805YD225MAT (AVX)<br>GRM40X5R225K16 (Murata) |
|                | 15 µH  | LOH43MN150K21 (Murata)                          |                          | 0805YD105MAT (AVX)<br>GRM40X5R105K16 (Murata) |
| 3              | 10 μH LQH43MN100K21 (Murata)<br>NLC453232T-100K (TDK)                      |   | 0.22 μF                  | 0805YD224MAT (AVX)<br>GRM40X5R224K16 (Murata) |
|                | 6.8 μH LQH43MN6R8K21 (Murata) NLC453232T-6R8K (TDK) LQH43MN4R7K21 (Murata) |   | 0.22 μF                  | 0805YD224MAT (AVX)<br>GRM40X5R224K16 (Murata) |
|                | 4.7 µH   | LQH43MN4R7K21 (Murata)<br>NLC453232T-4R7K (TDK) | 0.27 μF                  | 0805YD274MAT (AVX)<br>GRM40X5R224K16 (Murata) |
|                | 22 µH  | LQH43MN220K21 (Murata)<br>NLC453232T-220K (TDK) | 1 µF                     | 0805YD105MAT (AVX)<br>GRM40X5R105K25 (Murata) |
|                | 15 µH  | LQH43MN150K21 (Murata)<br>NLC453232T-150K (TDK) | 1 µF                     | 0805YD105MAT (AVX)<br>GRM40X5R105K25 (Murata) |
| 4              | 10 µH  | LQH43MN100K21 (Murata)<br>NLC453232T-100K (TDK) | 0.27 μF                  | 0805YD274MAT (AVX)<br>GRM40X5R274K25 (Murata) |
|                | 6.8 µH   | LQH43MN6R8K21 (Murata)<br>NLC453232T-6R8K (TDK) | 0.27 μF                  | 0805YD274MAT (AVX)<br>GRM40X5R274K25 (Murata) |
|                | 4.7 µH   | LQH43MN4R7K21 (Murata)<br>NLC453232T-4R7K (TDK) | 0.27 μF                  | 0805YD274MAT (AVX)<br>GRM40X5R274K25 (Murata) |
|                | 22 µH  | LQH43MN220K21 (Murata)<br>NLC453232T-220K (TDK) | 0.22 µF                  | 08053D224MAT (AVX)<br>GRM40X5R224K25 (Murata) |
|                | 15 µH  | LQH43MN150K21 (Murata)<br>NLC453232T-150K (TDK) | 0.22 µF                  | 08053D224MAT (AVX)<br>GRM40X5R224K25 (Murata) |
| 5, 6           | 10 µH  | LQH43MN100K21 (Murata)<br>NLC453232T-100K (TDK) | 0.27 µF                  | 08053D274MAT (AVX)<br>GRM40X5R274K25 (Murata) |
|                | 6.8 µH   | LQH43MN6R8K21 (Murata)<br>NLC453232T-6R8K (TDK) | 0.27 µF                  | 08053D274MAT (AVX)<br>GRM40X5R274K25 (Murata) |
|                | 4.7 µH   | LQH43MN4R7K21 (Murata)<br>NLC453232T-4R7K (TDK) | 0.27 µF                  | 08053D274MAT (AVX)<br>GRM40X5R274K25 (Murata) |

|                |        |   |                          | (   |
|----------------|--------|---|--------------------------|---|
| Series<br>LEDs | L      | Manufacturer                                    | Min.<br>C <sub>OUT</sub> | Manufacturer                                  |
|                | 22 µH  | LQH43MN220K21 (Murata)<br>NLC453232T-220K (TDK) | 0.22 μF                  | 08053D224MAT (AVX)<br>GRM40X5R224K25 (Murata) |
|                | 15 µH  | LQH43MN150K21 (Murata)<br>NLC453232T-150K (TDK) | 0.22 µF                  | 08053D224MAT (AVX)<br>GRM40X5R224K25 (Murata) |
| 7, 8           | 10 µH  | LQH43MN100K21 (Murata)<br>NLC453232T-100K (TDK) | 0.27 µF                  | 08053D274MAT (AVX)<br>GRM40X5R274K25 (Murata) |
|                | 6.8 µH | LQH43MN6R8K21 (Murata)<br>NLC453232T-6R8K (TDK) | 0.27 µF                  | 08053D274MAT (AVX)<br>GRM40X5R274K25 (Murata) |
|                | 4.7 µH | LQH43MN4R7K21 (Murata)<br>NLC453232T-4R7K (TDK) | 0.27 µF                  | 08053D274MAT (AVX)<br>GRM40X5R274K25 (Murata) |

TABLE 5-1: RECOMMENDED INDUCTOR & OUTPUT CAPACITOR VALUES (CONTINUED)

### 5.1 Dimming Control

There are two techniques for dimming control. One is PWM dimming and the other is continuous dimming.

PWM dimming control is implemented by applying a PWM signal on EN pin as shown in Figure 5-1. The MIC2287 is turned on and off by the PWM signal. With this method, the LEDs operate with either zero or full current. The average LED current is increased proportionally to the duty cycle of the PWM signal. This technique has high efficiency because the IC and the LEDs consume no current during the off cycle of the PWM signal. Typical PWM frequency should be between 100 Hz and 10 kHz.




FIGURE 5-1: PWM Dimming Method

2. Continuous dimming control is implemented by applying a DC control voltage to the FB pin of the MIC2287 through a series resistor as shown in Figure 5-2. The LED intensity (current) can be dynamically varied applying a DC voltage to the FB pin. The DC voltage can come from a DAC signal or a filtered PWM signal. The advantage of this approach is a high frequency PWM signal (>10 kHz) that can be used to control LED intensity.




FIGURE 5-2: Continuous Dimming.

### 5.2 Open-Circuit Protection

If the LEDs are disconnected from the circuit, or in case an LED fails open, the sense resistor will pull the FB pin to Ground. This will cause the MIC2287 to switch with a high duty cycle, resulting in output overvoltage. This may cause the SW pin voltage to exceed its maximum voltage rating, possibly damaging the IC and the external components. To ensure the highest level of protection, the MIC2287 has three product options in the 8-lead 2 mm x 2 mm VDFN with overvoltage protection (OVP). The extra pins of the VDFN package allow a dedicated OVP monitor with options for 15V, 24V, or 34V (see Figure 5-3). The reason for the three OVP levels is to let users choose the suitable level of OVP for their application. For example, a 3-LED application would typically see an output voltage of no more than 12V, so a 15V OVP option would offer a suitable level of protection. This allows the user to select the output diode and capacitor with the lowest voltage ratings, as well as smallest size and lowest cost. The OVP will clamp the output voltage to within the specified limits. For the Thin SOT-23-5 package, an OVP pin is not available. An external zener diode can be connected from the output of the converter to FB pin as shown in Figure 5-4. to implement similar protection.




FIGURE 5-3: VDFN Package OVP Circuit.




FIGURE 5-4: Thin SOT-23 Package OVP Circuit.

## 5.3 Start-Up and Inrush Current

During start-up, inrush current of approximately double the nominal current flows to set up the inductor current and the voltage on the output capacitor. If the inrush current needs to be limited, a soft-start circuit similar to Figure 5-5 could be implemented. The soft-start capacitor,  $C_{SS}$ , provides overdrive to the FB pin at start-up, resulting in gradual increase of switch duty cycle and limited inrush current.





FIGURE 5-5: Soft-Start Circuit.

## 6.0 PACKAGING INFORMATION

## 6.1 Package Marking Information



Legend:XX...XProduct code or customer-specific informationYYear code (last digit of calendar year)YYYear code (last 2 digits of calendar year)

YY Year code (last 2 digits of calendar year)
WW Week code (week of January 1 is week '01')

NNN Alphanumeric traceability code

Pb-free JEDEC<sup>®</sup> designator for Matte Tin (Sn)

\* This package is Pb-free. The Pb-free JEDEC designator (e3)
can be found on the outer packaging for this package.

•, ▲, ▼ Pin one index is identified by a dot, delta up, or delta down (triangle mark).

**Note**: In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information. Package may or may not include the corporate logo.

Underbar ( ) and/or Overbar ( ) symbol may not be to scale.


**Note:** If the full seven-character YYWWNNN code cannot fit on the package, the following truncated codes are used based on the available marking space:

6 Characters = YWWNNN; 5 Characters = WWNNN; 4 Characters = WNNN; 3 Characters = NNN;

2 Characters = NN; 1 Character = N

## 8-Lead Very Thin Plastic Dual Flat, No Lead Package (H2A) - 2x2x0.9 mm Body [VDFN] With 1.20x0.6 mm Exposed Pad


**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing C04-1247 Rev B Sheet 1 of 2

# 8-Lead Very Thin Plastic Dual Flat, No Lead Package (H2A) - 2x2x.9 mm Body [VDFN] With 1.20x0.6 mm Exposed Pad

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



|                         | Units  | N    | IILLIMETER: | S    |
|-------------------------|--------|------|-------------|------|
| Dimension               | Limits | MIN  | NOM         | MAX  |
| Number of Terminals     | Ν      |      | 8           |      |
| Pitch                   | е      |      | 0.50 BSC    |      |
| Overall Height          | Α      | 0.80 | 0.85        | 0.90 |
| Standoff                | A1     | 0.00 | 0.02        | 0.05 |
| Terminal Thickness      | A3     |      | 0.203 REF   |      |
| Overall Length          | D      |      | 2.00 BSC    |      |
| Exposed Pad Length      | D2     | 1.10 | 1.20        | 1.30 |
| Overall Width           | Е      |      | 2.00 BSC    |      |
| Exposed Pad Width       | E2     | 0.50 | 0.60        | 0.70 |
| Terminal Width          | b      | 0.20 | 0.25        | 0.30 |
| Terminal Length         | L      | 0.30 | 0.35        | 0.40 |
| Terminal-to-Exposed-Pad | K      |      | 0.35 REF    |      |


### Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Package is saw singulated
- 3. Dimensioning and tolerancing per ASME Y14.5M
  - BSC: Basic Dimension. Theoretically exact value shown without tolerances.
  - REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-1247 Rev B Sheet 2 of 2

# 8-Lead Very Thin Plastic Dual Flat, No Lead Package (H2A) - 2x2 mm Body [VDFN] Micrel Legacy Package

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

|                                | Units  | N    | ILLIMETER | S    |
|--------------------------------|--------|------|-----------|------|
| Dimension                      | Limits | MIN  | NOM       | MAX  |
| Contact Pitch                  | Е      |      | 0.50 BSC  |      |
| Optional Center Pad Width      | X2     |      |           | 1.30 |
| Optional Center Pad Length     | Y2     |      |           | 0.70 |
| Contact Pad Spacing            | С      |      | 1.90      |      |
| Contact Pad Width (X8)         | X1     |      |           | 0.30 |
| Contact Pad Length (X8)        | Y1     |      |           | 0.80 |
| Contact Pad to Center Pad (X8) | G1     | 0.20 |           |      |
| Thermal Via Diameter           | V      | 0.27 | 0.30      | 0.33 |


#### Notes:


- Dimensioning and tolerancing per ASME Y14.5M
   BSC: Basic Dimension. Theoretically exact value shown without tolerances.
- 2. For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process

Microchip Technology Drawing C04-3247 Rev. B

# 5-Lead Plastic Thin Small Outline Transistor (D5A) [TSOT] Micrel Legacy Package TSOT-5LD-PL-1

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging






Microchip Technology Drawing C04-1179 Rev A Sheet 1 of 2

## 5-Lead Plastic Thin Small Outline Transistor (D5A) [TSOT] Micrel Legacy Package TSOT-5LD-PL-1

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



|                          | Units  | N    | IILLIMETER: | S    |
|--------------------------|--------|------|-------------|------|
| Dimension                | Limits | MIN  | NOM         | MAX  |
| Number of Leads          | Ν      |      | 5           |      |
| Pitch                    | е      |      | 0.95 BSC    |      |
| Outside lead pitch       | e1     |      | 1.90 BSC    |      |
| Overall Height           | Α      | -    | -           | 1.00 |
| Molded Package Thickness | A2     | 0.84 | 0.87        | 0.90 |
| Standoff                 | A1     | 0.00 | -           | 0.10 |
| Overall Width            | Е      |      | 2.80 BSC    |      |
| Molded Package Width     | E1     |      | 1.60 BSC    |      |
| Overall Length           | D      |      | 2.90 BSC    |      |
| Foot Length              | Г      | 0.30 | 0.40        | 0.50 |
| Footprint                | L1     |      | 0.60 REF    |      |
| Foot Angle               | ф      | 0°   | -           | 4°   |
| Lead Thickness           | С      |      | 0.127 REF   | ·    |
| Lead Width               | b      | 0.30 | -           | 0.50 |

### Notes:

- 1. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.25mm per side.


Dimensioning and tolerancing per ASME Y14.5M
 BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-1179 Rev A Sheet 1 of 2

# 5-Lead Plastic Thin Small Outline Transistor (D5A) [TSOT] Micrel Legacy Package TSOT-5LD-PL-1

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



### RECOMMENDED LAND PATTERN

|                                | Units  | N    | <b>IILLIMETER</b> | S    |
|--------------------------------|--------|------|-------------------|------|
| Dimension                      | Limits | MIN  | NOM               | MAX  |
| Contact Pitch                  | Е      |      | 0.95 BSC          |      |
| Contact Pad Spacing            | С      |      | 2.60              |      |
| Contact Pad Width (X5)         | X1     |      |                   | 0.60 |
| Contact Pad Length (X5)        | Y1     |      |                   | 1.10 |
| Contact Pad to Center Pad (X2) | G      | 0.20 |                   |      |

### Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-3179 Rev A

## **APPENDIX A: REVISION HISTORY**

## **Revision A (October 2024)**

- Converted Micrel document MIC2287 to Microchip data sheet DS20006946A.
- Minor text changes throughout.



NOTES:

## PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

| Part Number           | [-XX]                     |     | <u>X</u>     | <u>xx</u>      | - <u>XX</u>    |
|-----------------------|---------------------------|-----|--------------|----------------|----------------|
| Device                | Overvoltage<br>Protection | Tem | np. Range    | Package        | Media Type     |
| Device:               | MIC2287:                  |     | 1.2 MHz PW   | M White LED D  | river with OVP |
|                       | <blank></blank>           |     | None         |                |                |
| Overvoltage           | -15                       | = ' | 15V          |                |                |
| Protection:           | -24                       | = : | 24V          |                |                |
|                       | -34                       | = ; | 34V          |                |                |
| Temperature<br>Range: | Y                         | = - | –40°C to +12 | 25°C           |                |
| B I                   | D5                        | = : | 5-Lead Thin  | SOT-23         |                |
| Package:              | ML                        | = 8 | 8-Lead 2 mn  | n x 2 mm VDFN  |                |
|                       | TR                        | = ; | 3,000/Reel ( | D5 only)       |                |
| Media Type:           | TR                        |     | 5,000/Reel ( |                |                |
|                       | TX                        | = ; | 3,000/Rev. F | Reel (D5 only) |                |

#### amples:

MIC2287YD5-TR:

MIC2287, No Overvoltage Protection, –40°C to +125°C Temp. Range, 5-Lead TSOT-23, 3,000/Reel

MIC2287-15YML-TR:

MIC2287, 15V Overvoltage Protection, -40°C to +125°C Temp. Range, 8-Lead VDFN, 5,000/Reel

MIC2287-24YML-TR:

MIC2287, 24V Overvoltage Protection, -40°C to +125°C Temp. Range, 8-Lead VDFN, 5,000/Reel

MIC2287-34YML-TR:

MIC2287, 34V Overvoltage Protection, –40°C to +125°C Temp. Range, 8-Lead

VDFN, 5,000/Reel

Tape and Reel identifier only appears in the lote: catalog part number description. This identifier is used for ordering purposes and is not printed on the device package. Check with your Microchip Sales Office for package availability with the Tape and Reel option.



NOTES:

#### Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.
- Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not
  mean that we are guaranteeing the product is "unbreakable" Code protection is constantly evolving. Microchip is committed to
  continuously improving the code protection features of our products.

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at <a href="https://www.microchip.com/en-us/support/design-help/client-support-services">https://www.microchip.com/en-us/support/design-help/client-support-services</a>.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSEQUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

#### **Trademarks**

The Microchip name and logo, the Microchip logo, Adaptec, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, CryptoMemory, CryptoRF, dsPlC, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, ClockWorks, The Embedded Control Solutions Company, EtherSynch, Flashtec, Hyper Speed Control, HyperLight Load, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, TimeCesium, TimeHub, TimePictra, TimeProvider, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, Clockstudio, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, EyeOpen, GridTime, IdealBridge, IGaT, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, IntelliMOS, Inter-Chip Connectivity, JitterBlocker, Knob-on-Display, MarginLink, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, mSiC, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, Power MOS IV, Power MOS 7, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SmartHLS, SMART-I.S., storClad, SQI, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, Trusted Time, TSHARC, Turing, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2024, Microchip Technology Incorporated and its subsidiaries.

All Rights Reserved.

ISBN: 978-1-6683-0465-5

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.



## Worldwide Sales and Service

#### **AMERICAS**

**Corporate Office** 2355 West Chandler Blvd. Chandler, AZ 85224-6199

Tel: 480-792-7200 Fax: 480-792-7277 **Technical Support:** 

http://www.microchip.com/ support

Web Address:

www.microchip.com

Atlanta Duluth, GA

Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

**Boston** 

Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL

Tel: 630-285-0071 Fax: 630-285-0075

**Dallas** 

Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Novi. MI

Tel: 248-848-4000

Houston, TX

Tel: 281-894-5983 Indianapolis

Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles

Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

Raleigh, NC Tel: 919-844-7510

New York, NY Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110 Tel: 408-436-4270

Canada - Toronto Tel: 905-695-1980 Fax: 905-695-2078

### ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

China - Beijing Tel: 86-10-8569-7000

China - Chengdu Tel: 86-28-8665-5511

China - Chongqing Tel: 86-23-8980-9588

China - Dongguan Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

China - Nanjing Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

China - Shanghai Tel: 86-21-3326-8000

China - Shenyang Tel: 86-24-2334-2829

China - Shenzhen Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

China - Wuhan

Tel: 86-27-5980-5300 China - Xian Tel: 86-29-8833-7252

China - Xiamen Tel: 86-592-2388138

China - Zhuhai Tel: 86-756-3210040

#### ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631

India - Pune Tel: 91-20-4121-0141

Japan - Osaka Tel: 81-6-6152-7160

Japan - Tokyo

Tel: 81-3-6880- 3770 Korea - Daegu

Tel: 82-53-744-4301 Korea - Seoul Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

Singapore Tel: 65-6334-8870

Taiwan - Hsin Chu Tel: 886-3-577-8366

Taiwan - Kaohsiung Tel: 886-7-213-7830

Taiwan - Taipei Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100

#### **EUROPE**

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

Denmark - Copenhagen Tel: 45-4485-5910 Fax: 45-4485-2829

Finland - Espoo Tel: 358-9-4520-820

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

Germany - Garching Tel: 49-8931-9700

Germany - Haan Tel: 49-2129-3766400

Germany - Heilbronn Tel: 49-7131-72400

Germany - Karlsruhe Tel: 49-721-625370

Germany - Munich Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Rosenheim Tel: 49-8031-354-560

Israel - Hod Hasharon Tel: 972-9-775-5100

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Padova Tel: 39-049-7625286

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

Norway - Trondheim Tel: 47-7288-4388

Poland - Warsaw Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91 Sweden - Gothenberg

Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820