
SCCS071 - OCTOBER 2001

- Function, Pinout, and Drive Compatible With FCT and F Logic
- Reduced V_{OH} (Typically = 3.3 V) Versions of Equivalent FCT Functions
- Edge-Rate Control Circuitry for Significantly Improved Noise Characteristics
- I_{off} Supports Partial-Power-Down Mode Operation
- ESD Protection Exceeds JESD 22
 - 2000-V Human-Body Model (A114-A)
 - 200-V Machine Model (A115-A)
 - 1000-V Charged-Device Model (C101)
- Matched Rise and Fall Times
- Fully Compatible With TTL Input and Output Logic Levels
- CY54FCT244T
 - 48-mA Output Sink Current
 12-mA Output Source Current
- CY74FCT244T
 - 64-mA Output Sink Current
 32-mA Output Source Current
- 3-State Outputs

CY54FCT244T...D PACKAGE CY74FCT244T . . . P, Q, OR SO PACKAGE (TOP VIEW) OE_A [19 TOEB $DA_0 \prod 2$ ОВ₀ 🛛 з 18**∏** OA₀ DA₁ [] 4 ħ DBΩ 17 OB₁ **[**] 5 16 OA₁ $DA_2 \begin{bmatrix} 1 \\ 6 \end{bmatrix}$ 15 DB₁ OB₂ [] 7 14 DA₃ [] 8 DB₂ 13 12 OA₃ OB₃ [] 9 11 DB₃ GND [] 10



description

The 'FCT244T devices are octal buffers and line drivers designed to be employed as memory address drivers, clock drivers, and bus-oriented transmitters/receivers. These devices provide speed and drive capabilities equivalent to their fastest bipolar logic counterparts, while reducing power consumption. The input and output voltage levels allow direct interface with TTL, NMOS, and CMOS devices without external components.

These devices are fully specified for partial-power-down applications using I_{off}. The I_{off} circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



CY54FCT244T, CY74FCT244T 8-BIT BUFFERS/LINE DRIVERS WITH 3-STATE OUTPUTS SCCS071 - OCTOBER 2001

ORDERING INFORMATION

TA	PACI	KAGEŤ	SPEED (ns)	ORDERABLE PART NUMBER	TOP-SIDE MARKING
	QSOP – Q	Tape and reel	3.6	CY74FCT244DTQCT	FCT244D
0°C to 70°C	SOIC - SO	Tube	3.6	CY74FCT244DTSOC	FCT244D
	30IC - 30	Tape and reel	3.6	CY74FCT244DTSOCT	FC1244D
	SOIC - SO	Tube	4.1	CY74FCT244CTSOC	FCT244C
	3010 - 30	Tape and reel	4.1	CY74FCT244CTSOCT	FC1244C
	QSOP - Q	Tape and reel	4.1	CY74FCT244CTQCT	FCT244C
	DIP – P	Tube	4.6	CY74FCT244ATPC	CY74FCT244ATPC
-40°C to 85°C	SOIC - SO	Tube		CY74FCT244ATSOC	FCT244A
-40°C 10 65°C	30IC - 30	Tape and reel	4.6	CY74FCT244ATSOCT	FC1244A
	QSOP - Q	Tape and reel	4.6	CY74FCT244ATQCT	FCT244A
	SOIC - SO	Tube		CY74FCT244TSOC	FCT244
	3010 - 30	Tape and reel	6.5	CY74FCT244TSOCT	FC1244
	QSOP - Q	Tape and reel	6.5	CY74FCT244TQCT	FCT244
	CDIP – D	Tube	4.6	CY54FCT244CTDMB	
	LCC – L	Tube	4.6	CY54FCT244CTLMB	
-55°C to 125°C	CDIP – D	Tube	5.1	CY54FCT244ATDMB	
-55-6 10 125-6	LCC – L	Tube	5.1	CY54FCT244ATLMB	
	CDIP – D	Tube	7	CY54FCT244TDMB	
	LCC – L	Tube	7	CY54FCT244TLMB	

[†] Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.

FUNCTION TABLE


	INPUTS	OUTPUT	
OEA	OE _B	D	0
L	L	L	L
L	L	Н	Н
Н	Н	Χ	Z

H = High logic level, L = Low logic level, X = Don't care, Z = High-impedance state



SCCS071 - OCTOBER 2001

logic diagram (positive logic)



absolute maximum rating over operating free-air temperature range (unless otherwise noted)[†]

Supply voltage range to ground potential		–0.5 V to 7 V
DC input voltage range		–0.5 V to 7 V
DC output voltage range		–0.5 V to 7 V
DC output current (maximum sink current/pin) .		120 mA
Package thermal impedance, θ_{JA} (see Note 1):	P package	69°C/W
•	Q package	68°C/W
	SO package	58°C/W
Ambient temperature range with power applied,	, T _A	–65°C to 135°C
Storage temperature range, T _{stq}	· · · · · · · · · · · · · · · · · · ·	–65°C to 150°C

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTE 1: The package thermal impedance is calculated in accordance with JESD 51-7.



CY54FCT244T, CY74FCT244T 8-BIT BUFFERS/LINE DRIVERS WITH 3-STATE OUTPUTS SCCS071 - OCTOBER 2001

recommended operating conditions (see Note 2)

		CY54FCT244T			CY7	4FCT24	1DT	CY	UNIT		
		MIN	NOM	MAX	MIN	NOM	MAX	MIN	NOM	MAX	UNIT
Vcc	Supply voltage	4.5	5	5.5	4.75	5	5.25	4.75	5	5.25	V
VIH	High-level input voltage	2			2			2			V
V_{IL}	Low-level input voltage			8.0			8.0			0.8	V
IOH	High-level output current			-12			-32			-32	mA
lOL	Low-level output current			48			64			64	mA
TA	Operating free-air temperature	-55		125	0		70	-40		85	°C

NOTE 2: All unused inputs of the device must be held at $V_{\hbox{CC}}$ or GND to ensure proper device operation.



SCCS071 - OCTOBER 2001

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

	TEGT COMPLTIONS		CY	54FCT24	4T	CY	74FCT24	I4T	UNIT
PARAMETER	TEST CONDITIONS	Ī	MIN	TYP [†]	MAX	MIN	TYP [†]	MAX	UNIT
V., ,	$V_{CC} = 4.5 \text{ V}, \qquad I_{IN} = -18 \text{ mA}$			-0.7	-1.2				V
VIK	$V_{CC} = 4.75 \text{ V}, \qquad I_{IN} = -18 \text{ mA}$						-0.7	-1.2	V
	$V_{CC} = 4.5 \text{ V}, \qquad I_{OH} = -12 \text{ mA}$		2.4	3.3					
Voн	V _{CC} = 4.75 V					2			V
	$I_{OH} = -15 \text{ mA}$					2.4	3.3		
Va	$V_{CC} = 4.5 \text{ V}, \qquad I_{OL} = 48 \text{ mA}$			0.3	0.55				V
VOL	$V_{CC} = 4.75 \text{ V}, \qquad I_{OL} = 64 \text{ mA}$						0.3	0.55	V
V_{hys}	All inputs			0.2			0.2		V
1.	$V_{CC} = 5.5 \text{ V}, \qquad V_{IN} = V_{CC}$				5				μΑ
lį	$V_{CC} = 5.25 \text{ V}, \qquad V_{IN} = V_{CC}$							5	μΑ
1	$V_{CC} = 5.5 \text{ V}, \qquad V_{IN} = 2.7 \text{ V}$				±1				μА
lН	$V_{CC} = 5.25 \text{ V}, \qquad V_{IN} = 2.7 \text{ V}$							±1	μΑ
1	$V_{CC} = 5.5 \text{ V}, \qquad V_{IN} = 0.5 \text{ V}$				±1				μΑ
۱۱L	$V_{CC} = 5.25 \text{ V}, \qquad V_{IN} = 0.5 \text{ V}$							±1	μΑ
10711	$V_{CC} = 5.5 \text{ V}, \qquad V_{OUT} = 2.7 \text{ V}$				10				μΑ
lozh	$V_{CC} = 5.25 \text{ V}, \qquad V_{OUT} = 2.7 \text{ V}$							10	μΑ
lo=:	$V_{CC} = 5.5 \text{ V}, \qquad V_{OUT} = 0.5 \text{ V}$				-10				μΑ
lozl	$V_{CC} = 5.25 \text{ V}, \qquad V_{OUT} = 0.5 \text{ V}$							-10	μΑ
los‡	$V_{CC} = 5.5 \text{ V}, \qquad V_{OUT} = 0 \text{ V}$		-60	-120	-225				mA
iOS+	$V_{CC} = 5.25 \text{ V}, \qquad V_{OUT} = 0 \text{ V}$					-60	-120	-225	ША
l _{off}	$V_{CC} = 0 \text{ V}, \qquad V_{OUT} = 4.5 \text{ V}$				±1			±1	μΑ
laa	$V_{CC} = 5.5 \text{ V}, \qquad V_{IN} \le 0.2 \text{ V}, \qquad V_{IN} \ge 0.2 \text{ V}$	√CC - 0.2 V		0.1	0.2				A
Icc	$V_{CC} = 5.25 \text{ V}, \qquad V_{IN} \le 0.2 \text{ V}, \qquad V_{IN} \ge 0.2 \text{ V}$	√CC - 0.2 V					0.1	0.2	mA
Alaa	$V_{CC} = 5.5 \text{ V}, V_{IN} = 3.4 \text{ V}$, $f_1 = 0$, Outputs oper	1		0.5	2				mA
∆ICC	$V_{CC} = 5.25 \text{ V}, V_{IN} = 3.4 \text{ V}, f_1 = 0, \text{ Outputs operator}$	en					0.5	2	MA
	V _{CC} = 5.5 V, One input switching at 50% duty c	ycle,			0.45				
	Outputs open, $\overline{OE}_A = \overline{OE}_B = GND$, $V_{IN} \le 0.2 \text{ V or } V_{IN} \ge V_{CC} - 0.2 \text{ V}$			0.06	0.12				mA/
ICCD¶	V _{CC} = 5.25 V, One input switching at 50% duty	cycle							MHz
	Outputs open, $\overline{OE}_A = \overline{OE}_B = GND$,	, 5,5,5					0.06	0.12	
	$V_{IN} \le 0.2 \text{ V or } V_{IN} \ge V_{CC} - 0.2 \text{ V}$								

[†] Typical values are at $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$.



Not more than one output should be shorted at a time. Duration of short should not exceed one second. The use of high-speed test apparatus and/or sample-and-hold techniques are preferable to minimize internal chip heating and more accurately reflect operational values. Otherwise, prolonged shorting of a high output can raise the chip temperature well above normal and cause invalid readings in other parametric tests. In any sequence of parameter tests, Ios tests should be performed last.

[§] Per TTL-driven input ($V_{IN} = 3.4 \text{ V}$); all other inputs at V_{CC} or GND

This parameter is derived for use in total power-supply calculations.

CY54FCT244T, CY74FCT244T 8-BIT BUFFERS/LINE DRIVERS WITH 3-STATE OUTPUTS

SCCS071 - OCTOBER 2001

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted) (continued)

DADAMETED		FEST CONDITIONS	,	CY	54FCT24	4T	CY	74FCT24	4T	UNIT
PARAMETER		TEST CONDITIONS		MIN	TYP [†]	MAX	MIN	TYP [†]	MAX	UNIT
		One bit switching at f ₁ = 10 MHz	$V_{IN} \le 0.2 \text{ V or}$ $V_{IN} \ge V_{CC} - 0.2 \text{ V}$		0.7	1.4				
	V _{CC} = 5.5 V,	at 50% duty cycle	$V_{IN} = 3.4 \text{ V or GND}$		1	2.4				
	Outputs open, OE _A = OE _B = GND	Eight bits switching at f ₁ = 2.5 MHz	$V_{IN} = 0.2 \text{ V or}$ $V_{IN} \ge V_{CC} - 0.2 \text{ V}$		1.3	2.6				
IC#		at 50% duty cycle	$V_{IN} = 3.4 \text{ V or GND}$		3.3	10.6				mA
ıC"		One bit switching at f ₁ = 10 MHz	$V_{IN} \le 0.2 \text{ V or}$ $V_{IN} \ge V_{CC} - 0.2 \text{ V}$					0.7	1.4	IIIA
	$V_{CC} = 5.25 \text{ V},$	at 50% duty cycle	$V_{IN} = 3.4 \text{ V or GND}$					1	2.4	
	Outputs open, OE _A = OE _B = GND	Eight bits switching at f ₁ = 2.5 MHz	$V_{IN} = 0.2 \text{ V or}$ $V_{IN} \ge V_{CC} - 0.2 \text{ V}$					1.3	2.6	
		at 50% duty cycle	$V_{IN} = 3.4 \text{ V or GND}$					3.3	10.6	
C _i					5	10		5	10	pF
Co				·	9	12		9	12	pF

[†] Typical values are at $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$.

 $^{\#}$ IC = ICC + Δ ICC \times DH \times NT + ICCD (f₀/2 + f₁ \times N₁)

Where:

IC = Total supply current

ICC = Power-supply current with CMOS input levels

 ΔI_{CC} = Power-supply current for a TTL high input (V_{IN} = 3.4 V)

 $\begin{array}{ll} D_H &= \text{Duty cycle for TTL inputs high} \\ N_T &= \text{Number of TTL inputs at } D_H \end{array}$

I_{CCD} = Dynamic current caused by an input transition pair (HLH or LHL)

f₀ = Clock frequency for registered devices, otherwise zero

f₁ = Input signal frequency

N₁ = Number of inputs changing at f₁

All currents are in milliamperes and all frequencies are in megahertz.

|| Values for these conditions are examples of the I_{CC} formula.



CY54FCT244T, CY74FCT244T 8-BIT BUFFERS/LINE DRIVERS WITH 3-STATE OUTPUTS SCCS071 - OCTOBER 2001

switching characteristics over operating free-air temperature range (see Figure 1)


PARAMETER	FROM	то	CY54FC	CY54FCT244T		CY54FCT244AT		CY54FCT244CT		
PARAIVIETER	(INPUT)	(OUTPUT)	MIN	MAX	MIN	MAX	MIN	MAX	UNIT	
t _{PLH}	D	0	1.5	7	1.5	5.1	1.5	4.6	ne	
t _{PHL}	D	O	1.5	7	1.5	5.1	1.5	4.6	ns	
^t PZH	ŌĒ	0	1.5	8.5	1.5	6.5	1.5	6.5	20	
t _{PZL}	OE	O	1.5	8.5	1.5	6.5	1.5	6.5	ns	
^t PHZ	ŌĒ	0	1.5	7.5	1.5	5.9	1.5	5.7	20	
^t PLZ	OE .		1.5	7.5	1.5	5.9	1.5	5.7	ns	

switching characteristics over operating free-air temperature range (see Figure 1)

DADAMETED	FROM	то	CY74FCT244T		CY74FCT244AT		CY74FCT244CT		CY74FCT	UNIT	
PARAMETER	(INPUT)	(OUTPUT)	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	UNIT
t _{PLH}	D	0	1.5	6.5	1.5	4.6	1.5	4.1	1.5	3.6	
tPHL	U	O	1.5	6.5	1.5	4.6	1.5	4.1	1.5	3.6	ns
t _{PZH}	ŌĒ	0	1.5	8	1.5	6.2	1.5	5.8	1.5	4.8	ns
t _{PZL}	OL	O	1.5	8	1.5	6.2	1.5	5.8	1.5	4.8	
^t PHZ	ŌĒ	0	1.5	7	1.5	5.6	1.5	5.2	1.5	4	ns
^t PLZ	OE .	0	1.5	7	1.5	5.6	1.5	5.2	1.5	4	115

SCCS071 - OCTOBER 2001

PARAMETER MEASUREMENT INFORMATION



NOTES: A. C_L includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. The outputs are measured one at a time with one input transition per measurement.

Figure 1. Load Circuit and Voltage Waveforms







6-Feb-2020

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
5962-9220301M2A	ACTIVE	LCCC	FK	20	1	TBD	POST-PLATE	N / A for Pkg Type	-55 to 125	5962- 9220301M2A CY54FCT 244TLMB	Samples
5962-9220301MRA	ACTIVE	CDIP	J	20	1	TBD	Call TI	N / A for Pkg Type	-55 to 125	5962-9220301MR A CY54FCT244TDMB	Samples
5962-9220301MSA	ACTIVE	CFP	W	20	1	TBD	Call TI	N / A for Pkg Type	-55 to 125	5962-9220301MS A CY54FCT244TW	Samples
5962-9220302M2A	ACTIVE	LCCC	FK	20	1	TBD	POST-PLATE	N / A for Pkg Type	-55 to 125	5962- 9220302M2A CY54FCT 244ATLMB	Samples
5962-9220302MRA	ACTIVE	CDIP	J	20	1	TBD	Call TI	N / A for Pkg Type	-55 to 125	5962-9220302MR A CY54FCT244ATDM B	Samples
5962-9220302MSA	ACTIVE	CFP	W	20	1	TBD	Call TI	N / A for Pkg Type	-55 to 125	5962-9220302MS A CY54FCT244ATW	Samples
5962-9220303M2A	ACTIVE	LCCC	FK	20	1	TBD	POST-PLATE	N / A for Pkg Type	-55 to 125	5962- 9220303M2A	Sample
5962-9220303MRA	ACTIVE	CDIP	J	20	1	TBD	Call TI	N / A for Pkg Type	-55 to 125	5962-9220303MR A CY54FCT244CTDM B	Samples
CY54FCT244ATDMB	ACTIVE	CDIP	J	20	1	TBD	Call TI	N / A for Pkg Type	-55 to 125	5962-9220302MR A CY54FCT244ATDM B	Samples
CY54FCT244ATLMB	ACTIVE	LCCC	FK	20	1	TBD	POST-PLATE	N / A for Pkg Type	-55 to 125	5962- 9220302M2A CY54FCT 244ATLMB	Samples
CY54FCT244ATW	ACTIVE	CFP	W	20	1	TBD	Call TI	N / A for Pkg Type	-55 to 125	5962-9220302MS A	Samples



6-Feb-2020

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Sample
										CY54FCT244ATW	
CY54FCT244CTDMB	ACTIVE	CDIP	J	20	1	TBD	Call TI	N / A for Pkg Type	-55 to 125	5962-9220303MR A CY54FCT244CTDM B	Sample
CY54FCT244TDMB	ACTIVE	CDIP	J	20	1	TBD	Call TI	N / A for Pkg Type	-55 to 125	5962-9220301MR A CY54FCT244TDMB	Sample
CY54FCT244TLMB	ACTIVE	LCCC	FK	20	1	TBD	POST-PLATE	N / A for Pkg Type	-55 to 125	5962- 9220301M2A CY54FCT 244TLMB	Sample
CY54FCT244TW	ACTIVE	CFP	W	20	1	TBD	Call TI	N / A for Pkg Type	-55 to 125	5962-9220301MS A CY54FCT244TW	Sample
CY74FCT244ATPC	ACTIVE	PDIP	N	20	20	Pb-Free (RoHS)	NIPDAU	N / A for Pkg Type	-40 to 85	CY74FCT244ATPC	Sample
CY74FCT244ATQCT	ACTIVE	SSOP	DBQ	20	2500	Green (RoHS & no Sb/Br)	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	FCT244A	Sample
CY74FCT244ATQCTE4	ACTIVE	SSOP	DBQ	20	2500	Green (RoHS & no Sb/Br)	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	FCT244A	Sample
CY74FCT244ATSOC	ACTIVE	SOIC	DW	20	25	Green (RoHS & no Sb/Br)	NIPDAU	Level-1-260C-UNLIM	-40 to 85	FCT244A	Sample
CY74FCT244ATSOCT	ACTIVE	SOIC	DW	20	2000	Green (RoHS & no Sb/Br)	NIPDAU	Level-1-260C-UNLIM	-40 to 85	FCT244A	Sample
CY74FCT244CTQCT	ACTIVE	SSOP	DBQ	20	2500	Green (RoHS & no Sb/Br)	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	FCT244C	Sample
CY74FCT244CTSOC	ACTIVE	SOIC	DW	20	25	Green (RoHS & no Sb/Br)	NIPDAU	Level-1-260C-UNLIM	-40 to 85	FCT244C	Sample
CY74FCT244DTSOC	ACTIVE	SOIC	DW	20	25	Green (RoHS & no Sb/Br)	NIPDAU	Level-1-260C-UNLIM	-40 to 85	FCT244D	Sample
CY74FCT244DTSOCT	ACTIVE	SOIC	DW	20	2000	Green (RoHS & no Sb/Br)	NIPDAU	Level-1-260C-UNLIM	-40 to 85	FCT244D	Sample
CY74FCT244DTSOCTE4	ACTIVE	SOIC	DW	20	2000	Green (RoHS & no Sb/Br)	NIPDAU	Level-1-260C-UNLIM	-40 to 85	FCT244D	Sample
CY74FCT244TQCT	ACTIVE	SSOP	DBQ	20	2500	Green (RoHS & no Sb/Br)	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	FCT244	Sample



PACKAGE OPTION ADDENDUM

6-Feb-2020

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
CY74FCT244TSOC	ACTIVE	SOIC	DW	20	25	Green (RoHS & no Sb/Br)	NIPDAU	Level-1-260C-UNLIM	-40 to 85	FCT244	Samples
CY74FCT244TSOCT	ACTIVE	SOIC	DW	20	2000	Green (RoHS & no Sb/Br)	NIPDAU	Level-1-260C-UNLIM	-40 to 85	FCT244	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 2-Sep-2015

TAPE AND REEL INFORMATION





	Dimension designed to accommodate the component width
	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CY74FCT244ATQCT	SSOP	DBQ	20	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
CY74FCT244ATSOCT	SOIC	DW	20	2000	330.0	24.4	10.8	13.3	2.7	12.0	24.0	Q1
CY74FCT244CTQCT	SSOP	DBQ	20	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
CY74FCT244DTSOCT	SOIC	DW	20	2000	330.0	24.4	10.8	13.3	2.7	12.0	24.0	Q1
CY74FCT244TQCT	SSOP	DBQ	20	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
CY74FCT244TSOCT	SOIC	DW	20	2000	330.0	24.4	10.8	13.3	2.7	12.0	24.0	Q1

www.ti.com 2-Sep-2015



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
CY74FCT244ATQCT	SSOP	DBQ	20	2500	367.0	367.0	38.0
CY74FCT244ATSOCT	SOIC	DW	20	2000	367.0	367.0	45.0
CY74FCT244CTQCT	SSOP	DBQ	20	2500	367.0	367.0	38.0
CY74FCT244DTSOCT	SOIC	DW	20	2000	367.0	367.0	45.0
CY74FCT244TQCT	SSOP	DBQ	20	2500	367.0	367.0	38.0
CY74FCT244TSOCT	SOIC	DW	20	2000	367.0	367.0	45.0

14 LEADS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package is hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
- E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

N (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.





SOIC



- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm per side.
- 5. Reference JEDEC registration MS-013.



SOIC



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOIC



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



W (R-GDFP-F20)

CERAMIC DUAL FLATPACK



- A. All linear dimensions are in inches (millimeters).
- This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a ceramic lid using glass frit.

 D. Index point is provided on cap for terminal identification only.

 E. Falls within Mil—Std 1835 GDFP2—F20



FK (S-CQCC-N**)

LEADLESS CERAMIC CHIP CARRIER

28 TERMINAL SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a metal lid.
- D. Falls within JEDEC MS-004



DBQ (R-PDSO-G20)

PLASTIC SMALL-OUTLINE PACKAGE




- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15) per side.
- D. Falls within JEDEC MO-137 variation AD.



DBQ (R-PDSO-G20)

PLASTIC SMALL OUTLINE PACKAGE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Example stencil design based on a 50% volumetric metal load solder paste. Refer to IPC-7525 for other stencil recommendations.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

Tl's products are provided subject to Tl's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such Tl products. Tl's provision of these resources does not expand or otherwise alter Tl's applicable warranties or warranty disclaimers for Tl products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2020, Texas Instruments Incorporated