

DEWALT[®]

CATALOG

HIGH PERFORMANCE
INDUSTRIAL TOOLS &
ACCESSORIES
2022



58.5158° N, -6.2585° W.

GUARANTEED TOUGH.[®]

DEWALT



COMPLETE SOLUTIONS

DEWALT® is a market-leading manufacturer of premium power tools, accessories and anchors and fixings that provides a fully integrated system solution for various applications.

DEWALT® tools offer unparalleled performance, with durable construction for a professional finish. Rely on DEWALT® to get the job done, with a 3 year guarantee on most tools.

XR FLEXVOLT

Taking cordless drilling to the next level, the newest DEWALT® 60V MAX* XR FLEXVOLT® range provides true corded performance without the restrictions of the cord. With Brushless motors and Perform & Protect™ low vibration levels, these tools set the new standard on the jobsite.

With over 100 tools in the range the 20V MAX* XR® Lithium-Ion battery platform is the biggest and fastest growing in our range. All 20V MAX* XR® products are compatible with XR FLEXVOLT® batteries, giving you longer runtime and even greater flexibility meaning the CORDLESS JOBSITE has arrived.

**PERFORM
PROTECT™**

DeWALT® is constantly pushing the boundaries to create the most innovative tools for the construction professional.

Power tools which carry the Perform & Protect shield have passed rigorous testing to ensure they exceed the highest demands of the toughest environments, while maintaining a fundamental emphasis on safety. All of these products have to meet strict criteria in one or more of the following core areas: Control; Vibration; Dust.

**CONTROL**

Bind-up situations can occur when drilling, cutting, or grinding. These sudden torque reactions, when the tool body rotates, can potentially damage the tool or injure the user.

The Perform & Protect shield for **CONTROL** shows which products have additional features to help in those critical bind-up situations.

The two main different systems are:

- Anti rotation System for Rotary hammers
- Electronic Clutch for drills and grinders





CONTROL

Unique and innovative torque control features



VIBRATION

Up to 50% lower vibration*



DUST

Industry leading dust extraction solutions



VIBRATION

Vibration exposure can cause a range of conditions collectively known as hand-arm vibration syndrome (HAVS). Other conditions include carpal tunnel syndrome and vibration white finger.

When the Perform & Protect shield is awarded for **VIBRATION**, it is guaranteed that Tri-Axial vibration levels have been reduced, increasing usage time without reducing performance.

Three different anti-vibration systems are:

- Active Vibration Control
- Floating back handle
- Counter Balance System



DUST

Airborne dust inhalation can lead to a number of long-term health conditions such as silicosis and chronic obstructive pulmonary disease (COPD).

When the Perform & Protect shield is awarded for **DUST**, it is guaranteed the potential of inhaling dust is reduced to give a cleaner and safer working environment.

*When compared to hammers without this feature

DEWALT



XR FLEXVOLT
POWER OF CORDED | FREEDOM OF CORDLESS™



18V 54V WHAT IS XR FLEXVOLT?

XR FLEXVOLT® is a range of 60V MAX* power tools that offer runtime and performance which has never been seen before – for the first time, professional users can reliably undertake heavy-duty construction applications without the need for mains power.

This innovation means that for the first time, you can have 60V MAX* power across a whole range of tools without the inconvenience of a cable. DeWALT® XR FLEXVOLT® is the only battery on the market that can switch from 60V MAX* to 20V MAX*, making it backward-compatible with your existing XR® power tools.



CONVERTIBLE BATTERY PACK



BACKWARDS COMPATIBLE

XR FLEXVOLT®



DeWALT® is committed to offering real-world practicality and convenience. The XR FLEXVOLT® battery pack is not only interchangeable across the complete 60V MAX* range but is also backwards compatible with all existing 20V MAX* XR® tools. Circular saws, Drills, Table Saws, Nail Guns, Alligator Saws, Impact Drivers – professional users can now operate every power tool they need on a single cordless system.


HOW XR FLEXVOLT® WORKS

INTELLIGENT DESIGN

XR FLEXVOLT® batteries are 20V MAX* batteries that switch up to 60V MAX* when placed on a XR FLEXVOLT® tool. They are fully compatible with the entire 20V MAX* XR range, including chargers.



Parallel connection



Series connection



ADVANCED TECHNOLOGY

Standard XR® batteries have 5 x 3.6V (20V) cells connecting in a series and either one or two strings in parallel, giving either an 20V 2Ah or an 20V 5Ah battery.

FLEXVOLT® batteries are flexible. They connect in parallel for 20V MAX* tools and in a series for 60V MAX* tools. The result? The right power for the tool - with increased runtime and consistent performance.

60V MAX* - WITH NO CORDS
All the tool power you need - where you need it

AUTO SWITCHING
The only battery on the market that can switch from 20V MAX* to 60V MAX*



XR® COMPATIBLE
Use with your existing XR® Powertools

HEAVY DUTY POWER
Helping to build the cordless jobsite

DEWALT SERVICE

CONVENIENCE: At the heart of the DeWALT® 5 star service promise are 5 star service agents which are conveniently located throughout the country, with specialists always available to answer any questions whether you are on or off the jobsite.

SPEED: Having your tools back in action in the fastest time possible is our prime objective. Subject to parts availability, most repairs should not take more than 48 hours in the workshop and for those smaller urgent repairs we provide a “while-u-wait” service.

QUALITY: Highest Quality is assured with DeWALT® factory trained technicians carrying out all repairs with all work being backed by our 90 day warranty. Each DeWALT® repair comes with our personal “satisfaction tag” listing all the work done and a DeWALT® contact telephone number should you be less than 100% happy with the repair.

GENUINE PARTS: All parts used in repairs are original, ensuring both the highest quality and a perfect fit every time.

ONLINE SERVICE: www.2helpU.com provides information on the DeWALT® After Sales Services, including DeWALT® authorised repair agent locations, some frequently asked questions, technical information, spare part details, warranty policy and recycling of used tools.

Not all DeWALT® service agents are 5 star rated. Those that are not may not be able to provide all services available above but will display in-store a detailed list of their selected services.





DEWALT **3YR WARRANTY**

We believe a solid warranty package ensures the safety, reliability and service our products are meant to deliver - from the beginning to the end of every job.

The DeWALT® 3 year warranty covers manufacturing defects and labour for all products.

WARRANTY TERMS AND CONDITIONS

DeWALT® will repair, without charge, any defects due to defective materials or workmanship, within 3 years from date of purchase.

- The Warranty does not cover part failure due to excessive wear and tear or tool misuse

Wear & Tear refers to the number of hours and/or the environment that a product has been used in; this can affect: Armature Commutators, Bearings, Switches, Beat Pieces, Clutches, Gear & Pinion, Gearcase, Brushes, Chucks, Clamshells, Cord sets, Rubber parts and Attachments (Battery, Charger, Guard, Flanges ... etc.)

- The warranty does not apply where repairs have been attempted by unauthorised persons
- Issues not covered by the warranty include:
 - Extreme impacts or drops
 - Ingestion of foreign objects (i.e. Nails, screws ... etc)
 - Using tool for non-intended application
 - Any modification to the tool
 - Prolonged exposure to the extreme weather conditions
 - Wrong voltage
 - Using incorrect accessories or attachments
 - Lack of recommended service (especially hammers)
 - Use of incorrect grease
 - Not repaired with DeWALT® genuine parts



CUSTOMER EXPERIENCE CENTRE

Stanley Black & Decker currently operates state of art customer experience centers in four locations across Asia in Seoul - South Korea, Bangkok - Thailand, Pune – India & Shuzho – China. These centers not only enables us to showcase leading innovations in the world of powers tools, hand tools & power tool accessories it also provided a great platform for our customers to get an hands-on experience on using these products and make the right selection for some of their most demanding applications.

In addition these centers are used for safety & application trainings for industrial applications, new employee induction & advance employee modules, customer & channel partner team training, top to top

interactions and last but not the least Corporate Social Responsibility initiatives centered around makers of tomorrow – tradesmen, contractors and students in true spirit of our corporate mission. For the builders and protectors, for the makers and explorers, for those shaping and reshaping our world through hard work and inspiration, Stanley Black & Decker provides the tools and innovative solutions you can trust to get the job done—and we have since 1843.





**SALES AND
AFTER SALES
SUPPORT**



**ORIGINAL
PARTS**



WARRANTY



**GREAT SERVICE
NETWORK**



INFORMATION



**OMNICHANNEL
SUPPORT**

TOTAL CARE

**WE ARE COMMITTED TO EXCELLENCE IN OUR
TOOLS AND OUR SUPPORT**

Total Care establishes more direct and effective engagement with customers and channel partners. Our goal is to give you an added value experience, and to increase your customers' satisfaction with Stanley Black & Decker by providing more engaged support.

DEWALT

DEWALT®

GUARANTEED TOUGH.®



CONTENTS

FLEXVOLT	5
BRUSHLESS	7
CORDLESS	11
DRILL & FASTENING	13
METAL WORKING	15
CONCRETE WORKING	19
WOOD WORKING	25
OTHERS	31
FLAP DISCS	36
DIAMOND BLADE	37
CIRCULAR SAW BLADE	38
EXTREME 2 SDS-PLUS DRILL BITS	39
SDS-PLUS DRILL BITS	40
EXTREME SDS-MAX DRILL BITS	41
DEMOLITION CHISEL BITS	42
EXTREME SDS-MAX DRILL BITS	43
HSS-CO EXTREME COBALT DRILL BITS	44
HSS EXTREME 2 METAL PILOT POINT DRILL BITS	47
HSS-G JOBBER METAL DRILL BITS (BLACK OXIDE)	48
AUTHORIZED SERVICE CENTER	52





FLEXVOLT® 54V MAX* 3 MODE ROTARY HAMMER

DCH333X2

Voltage (V)	54V max
No Load Speed (RPM)	0-1,000
Impact Rate (BPM)	0-4,480
Impact Energy (J)	3.5J
Bit Holder	SDS-Plus
Chipping	Yes
Battery Chemistry	XR Li-Ion
Battery Capacity	2 pcs x 9.0 Ah
Weight (Kg)	4.6



FLEXVOLT® 60V MAX* 5" ANGLE GRINDER BARE UNIT

DCG418N-KR

Voltage (V)	60V max
Max. Disc Diameter (mm)	125
No Load Speed (RPM)	9,000
Spindle Thread	M10
Spindle Lock	Yes
Battery Chemistry	XR Li-Ion
Weight (Kg)	4.6
Bare Tools	



NEW



60V MAX* BRUSHLESS 7-1/4" CIRCULAR SAW KIT POWERED BY FLEXVOLT®

DCS578X2

Voltage	60V max
No Load Speed (RPM)	5,800
Max. Depth of Cut at 90° / 45° (mm)	65/41
Bevel Angle Adjustment	57°
Battery Chemistry	XR Li-Ion
Battery Capacity	2 pcs x 6.0 Ah
Weight (Kg)	3.7



**60V BATTERY XR FLEXVOLT
6.0AH / 9.0AH**

DCB606 / DCB609

54V CHARGER XR FLEXVOLT

DCB118

FLEXVOLT



**XR FLEX
VOLT™**

POWER OF CORDED | FREEDOM OF CORDLESS



**OUR
MOST
ADVANCED
SYSTEM**

**THE WORLD'S FIRST BATTERY
THAT AUTOMATICALLY
CHANGES VOLTAGE WHEN
YOU CHANGE TOOLS**

20V MAX* COMPACT BRUSHLESS 1/2" (13MM) DRILL DRIVER

DCD7771D2-B1

Chuck Size	1/2" (13 mm)
No Load Speed	0-500 / 0-1750 RPM
Power	340 UWO
Torque	65 Nm
Led Light	YES
Capacity	Wood 1" (25 mm) Metal 1/2" (13 mm)

NEW

**20V MAX*
BRUSHLESS**



More powerful, compact and lightweight, the 20V MAX* DEWALT Cordless Drill/Driver features Brushless Technology, and gives the tool greater efficiency, which translates into more power and more runtime.

20V MAX* COMPACT BRUSHLESS 1/2" (13 MM) HAMMER DRILL/DRIVER

DCD7781D2-B1

Chuck Size	1/2" (13 mm)
No Load Speed	0-500 / 0-1750 RPM
Power	340 UWO
Torque	65 Nm
Led Light	YES
Impact Per Minute	0-8500 / 0-29750 IPM
Capacity	Wood 1" (25 mm) Metal 1/2" (13 mm) Concrete 1/4" (6,5 mm)

NEW

**20V MAX*
BRUSHLESS**



More powerful, compact and lightweight, the 20V MAX* DEWALT Cordless Drill/Driver features Brushless Technology, and gives the tool greater efficiency, which translates into longer use time and requires less maintenance.

20V MAX* COMPACT BRUSHLESS 1/4" (6,35 MM) IMPACT DRIVER

DCF7871D2-B1

Chuck Size	1/4" (6,35 mm)
No Load Speed	0-2800 RPM
Power	280 UWO
Torque	170 Nm
Led Light	YES
Impact Per Minute	0-3200 IPM

NEW

**20V MAX*
BRUSHLESS**



Compact and lightweight design, the 20V MAX* DEWALT Cordless Driver features Brushless Technology, which gives the tool greater efficiency, which translates into longer use time and requires less maintenance.

MORE POWER MORE RUNTIME

55% HIGHER TORQUE
AND 13% MORE POWER*

DCD7771

20V MAX* COMPACT BRUSHLESS
1/2" (13MM) DRILL DRIVER



BRUSHLESS

DCD7781

20V MAX* COMPACT BRUSHLESS
1/2" (13 MM) AHAMMER DRILL/DRIVER



DCF7871D2-B1

20V MAX* COMPACT BRUSHLESS
1/4" (6,35 MM) IMPACT DRIVER



20V MAX*
BRUSHLESS

18V / 20V XR BRUSHLESS DRILL DRIVER
DCD791D2

Voltage (V)	18 / 20
Chuck Capacity (mm)	13
No Load Speed (RPM)	0-550 / 0-2,000
Max. Torque [Hard / Soft] (Nm)	70 / 27
Battery Chemistry	XR Li-Ion
Battery Capacity	2 pcs x 2.0 Ah
Weight (Kg)	1.1


18V / 20V XR BRUSHLESS IMPACT DRIVER
DCF887D2A

Voltage (V)	18 / 20
Chuck Capacity (inch)	1/4
No Load Speed (RPM)	0-1,000 / 0-2,800 / 0-3,250
Max. Torque (Nm)	205
Impact Rate (BPM)	0-3,200
Battery Chemistry	XR Li-Ion
Battery Capacity	2 pcs x 2.0 Ah
Weight (Kg)	0.9


18V / 20V XR BRUSHLESS HAMMER DRILL
DCD796D2

Voltage (V)	18 / 20
Chuck Capacity (mm)	13
No Load Speed (RPM)	0-550 / 0-2,000
Max. Torque [Hard / Soft] (Nm)	70 / 27
Impact Rate (BPM)	0-9,350 / 0-34,000
Battery Chemistry	XR Li-Ion
Battery Capacity	2 pcs x 2.0 Ah
Weight (Kg)	1.2



18V / 20V XR BRUSHLESS HIGH TORQUE IMPACT WRENCH WITH HOG RING

DCF899HP2

Voltage (V)	18 / 20
Bit Holder Size (inch)	1/2
No Load Speed (RPM)	0-400 / 0-1,200 / 0-1,900
Max. Torque (Nm)	950
Impact Rate (IPM)	0-2,400
Battery Chemistry	XR Li-Ion
Battery Capacity	2 pcs x 5.0 Ah
Weight (Kg)	2.6



18V / 20V XR BRUSHLESS MULTI TOOL

DCS355D2

Voltage (V)	18 / 20
Oscillations per Minute (OPM)	0-20,000
Switch Type	Variable Dual Grip
Tool Free Accessory	Yes
Battery Chemistry	XR Li-Ion
Battery Capacity	2 pcs x 2.0 Ah
Weight (Kg)	1.5



18V / 20V XR COMPACT DRILL DRIVER

DCD716G2K

Voltage	10.8 / 12
Chuck capacity (mm)	10
No Load Speed (RPM)	0-400/1,500
Impact Rate (BPM)	0-22,500
Max. Torque (Nm)	30
Battery Capacity	2 pcs x 1.3 Ah
Weight (kg)	1.1



10.8V / 12V XR COMPACT DRILL DRIVER

DCD700G2

Voltage (V)	10.8 / 12
Chuck Capacity (mm)	10
# of Speed Settings	2
No Load Speed (RPM)	0-400 / 0-1,500
Max. Torque [Hard / Soft] (Nm)	24 / 15
Battery Chemistry	XR Li-Ion
Battery Capacity	2 pcs x 1.3 Ah



18V / 20V XR COMPACT IMPACT WRENCH

DCF880M2

Voltage (V)	18 / 20
Bit Holder Size (inch)	1/2
No Load Speed (RPM)	0-2,300
Max. Torque (Nm)	203
Impact Rate (IPM)	0-2,700
Anvil Type	Detent Pin
Battery Chemistry	XR Li-Ion
Battery Capacity	2 pcs x 4.0 Ah
Weight (Kg)	1.5





12V MAX 2.0AH XR LI-ION BATTERY ACCESSOR

DCB127-KR



BATTERY 20V XR 2.0AH

DCB183



BATTERY 18V / 20V XR 4.0AH

DCB182



CHARGER 10.8V, 12V, 18V, 20V

DCB115



10MM 550W ROTARY DRILL

DWD014

Power Input (W)	550
Chuck Capacity (mm)	10
No Load Speed (RPM)	0-2,800
Max. Drilling Capacity in Wood (mm)	25
Max. Drilling Capacity in Steel (mm)	10
Length (mm)	207
Height	181
Include Chuck Key	Yes
Weight (Kg)	1.3



13MM 650W PERCUSSION DRILL

DWD024

Power Input (W)	650
Chuck Capacity (mm)	13
No Load Speed (RPM)	0-2,800
Max. Drilling Capacity in Wood (mm)	25
Max. Drilling Capacity in Steel (mm)	13
Max. Drilling Capacity in Concrete (mm)	16
Impact Rate (BPM)	0-47,600
Weight (Kg)	1.4



2 INCH 2-SPEED MAGNETIC DRILL PRESS

DWE1622K

Power Input (W)	1,200
No Load Speed (RPM)	350 / 450
Drill Point Pressure (Kg)	336
Annular Cutter Capacity	2
Cutter Accepted	3/4" Weldon
Length of Travel (inch)	4-3/8
Twist Bit Capacity [Diameter] (inch)	1/2
Overload Protection	Yes
Clamping Force (N)	3,800
Weight (Kg)	14.55



HEAVY-DUTY 1/2" IMPACT WRENCH WITH HOG RING RETAINER

DW293

Power Input (W)	710
Bit Holder Size (inch)	1/2
No Load Speed (RPM)	2,100
Max. Torque (Nm)	440
Impact Rate (IPM)	2,700
Weight (Kg)	3.2



100MM 680W TOGGLE SWITCH SAG

DW810B

Power Input (W)	710
Max. Disc Diameter (mm)	100
No Load Speed (RPM)	11,000
Spindle Thread	M10
Spindle Lock	Yes
Length with Disc (mm)	300
Height (mm)	65
Switch Type	Toggle
Weight (Kg)	1.8



100MM 720W SLIDE SWITCH SAG

DWE8100S

Power Input (W)	720
Max. Disc Diameter (mm)	100
No Load Speed (RPM)	12,000
Spindle Thread	M10
Spindle Lock	Yes
Length with Disc (mm)	300
Height (mm)	57
Switch Type	Slide
Weight (Kg)	1.58



100MM 850W PADDLE SWITCH SAG

DWE8200PL

Power Input (W)	850
Max. Disc Diameter (mm)	100
No Load Speed (RPM)	12,000
Spindle Thread	M10
Spindle Lock	Yes
Length with Disc (mm)	296
Height (mm)	57
Switch Type	Paddle
Weight (Kg)	1.75



125MM 720W SLIDE SWITCH SAG**DWE8110S**

Power Input (W)	720
Max. Disc Diameter (mm)	125
No Load Speed (RPM)	12,000
Spindle Thread	M14
Spindle Lock	Yes
Length with Disc (mm)	300
Height (mm)	60.5
Switch Type	Slide
Weight (Kg)	1.79



N175105

125MM 850W PADDLE SWITCH SAG**DWE8210PL**

Power Input (W)	850
Max. Disc Diameter (mm)	125
No Load Speed (RPM)	12,000
Spindle Thread	M14
Spindle Lock	Yes
Length with Disc (mm)	308
Height (mm)	60
Switch Type	Paddle
Weight (Kg)	1.95



N257699

125MM 850W SLIDE SWITCH SAG**DWE8210S**

Power Input (W)	850
Max. Disc Diameter (mm)	125
No Load Speed (RPM)	12,000
Spindle Thread	M14
Spindle Lock	Yes
Length with Disc (mm)	308
Height (mm)	60
Switch Type	Slide
Weight (Kg)	1.95



N257699

125MM 1010W SLIDE SWITCH SMALL ANGLE GRINDER (SAG)

DWE8310S

Power Input (W)	1,010
Max. Disc Diameter (mm)	125
No Load Speed (RPM)	11,500
Spindle Thread	M14
Spindle Lock	Yes
Length with Disc (mm)	-
Height (mm)	-
Switch Type	Slide
Weight (Kg)	1.85



125MM 1400W TRIGGER SWITCH SMALL ANGLE GRINDER (SAG)

DW830

Power Input (W)	1,400
Max. Disc Diameter (mm)	125
No Load Speed (RPM)	10,000
Spindle Thread	M14
Spindle Lock	Yes
Length with Disc (mm)	385
Height (mm)	115
Switch Type	Trigger
Weight (Kg)	3.1



180MM 2000W LARGE ANGLE GRINDER (LAG)

DWE493-B1

Power Input (W)	2,200
Max. Disc Diameter (mm)	180
No Load Speed (RPM)	8,500
Spindle Thread	M14
Spindle Lock	Yes
Length (mm)	484
Height (mm)	151
Switch Type	Trigger
Weight (Kg)	5.1

COMING SOON



230MM 2200W LARGE ANGLE GRINDER (LAG)

DWE492-B1

Power Input (W)	2,200
Max. Disc Diameter (mm)	230
No Load Speed (RPM)	6,500
Spindle Thread	M14
Spindle Lock	Yes
Length (mm)	490
Height (mm)	151
Switch Type	Trigger
Weight (Kg)	5.1

**COMING
SOON**



N495294

355MM 2300W CHOP SAW

D28730

Power Input (W)	2,300
Max. Disc Diameter (mm)	355
No Load Speed (RPM)	3,800
Cable Length (m)	90
Length (mm)	-
Switch Type	-
Weight (Kg)	17.5



N505712

25MM 400W DIE GRINDER

DWE886P


Power Input (W)	400
Max. Disc Diameter (mm)	25
No Load Speed (RPM)	25,000
Cable Length (m)	2.5
Length (mm)	356
Switch Type	Paddle
Weight (Kg)	1.65



N175105

22MM 3 MODE SDS-PLUS HAMMER**D25033K**

Power Input (W)	710
No Load Speed (RPM)	0-1,550
Impact Rate (BPM)	0-5,680
Impact Energy (J)	2.1
Bit Holder	SDS-Plus
Max. Drilling Capacity [Wood/Steel/Concrete](mm)	30 / 13 / 22
Active Vibration Control	No
Weight (Kg)	2.5

**N418049**

26MM 3 MODE SDS-PLUS HAMMER

D25133K

Power Input (W)	800
No Load Speed (RPM)	0-1,500
Impact Rate (BPM)	0-5,500
Impact Energy (J)	2.9
Bit Holder	SDS-Plus
Max. Drilling Capacity [Wood/Steel/Concrete](mm)	30 / 13 / 26
Active Vibration Control	No
Weight (Kg)	2.6



28MM 3 MODE SDS-PLUS HAMMER

D25143K

Power Input (W)	900
No Load Speed (RPM)	0-1,450
Impact Rate (BPM)	0-5,350
Impact Energy (J)	3.2
Bit Holder	SDS-Plus
Max. Drilling Capacity [Wood/Steel/Concrete](mm)	30 / 13 / 28
Active Vibration Control	No
Weight (Kg)	3.1



28MM 3 MODE SDS-PLUS HAMMER WITH QCC

D25144K

Power Input (W)	900
No Load Speed (RPM)	0-1,450
Impact Rate (BPM)	0-5,350
Impact Energy (J)	3.2
Bit Holder	SDS-Plus
Max. Drilling Capacity [Wood/Steel/Concrete](mm)	30 / 13 / 28
Active Vibration Control	No
Weight (Kg)	3.1



32MM 3 MODE SDS-PLUS COMBINATION HAMMER

D25413K

Power Input (W)	1000
No Load Speed (RPM)	0-820
Impact Rate (BPM)	0-4,700
Impact Energy (J)	4.2
Bit Holder	SDS-Plus
Max. Drilling Capacity [Wood/Steel/Concrete/Core Bit] (mm)	32/13/6- 32/100
Active Vibration Control	Yes
Weight (Kg)	4.2



48MM 7KG SDS-MAX COMBINATION HAMMER

D25733K

Power Input (W)	1,600
No Load Speed (RPM)	177-355
Impact Rate (BPM)	1,350-2,705
Impact Energy (J)	13.3
Bit Holder	SDS-Max
Max. Drilling Capacity [Concrete / Core Bit](mm)	48 / 125
Active Vibration Control	Yes
Weight (Kg)	7



48MM 7KG SDS-MAX COMBINATION HAMMER

D25721K

Power Input (W)	2,300
Max. Disc Diameter (mm)	355
No Load Speed (RPM)	3,800
Cable Length (m)	90
Length (mm)	-
Switch Type	-
Weight (Kg)	17.5



52MM 9KG SDS-MAX COMBINATION HAMMER

D25773K

Power Input (W)	1,700
No Load Speed (RPM)	145-290
Impact Rate (BPM)	1,105-2,210
Impact Energy (J)	19,4
Bit Holder	SDS-Max
Max. Drilling Capacity [Steel/ Wood](mm)	52 / 80
Active Vibration Control	Yes
Weight (Kg)	10.5



N630264



40MM SDS-MAX COMBINATION HAMMER

D25481K

Power Input (W)	1,050
No Load Speed (RPM)	0-540
Impact Rate (BPM)	3,150
Impact Energy (J)	6.1
Bit Holder	SDS-Max
Max. Drilling Capacity [Metal / Wood / Concrete] (mm)	16 / 35 / 40
Active Vibration Control	Yes
Weight (Kg)	5.9



N492849



7KG SDS MAX DEMOLITION HAMMER

D25872K

Power Input (W)	1,600
Impact Rate (BPM)	1,350-2,705
Impact Energy (J)	13.3
Bit Holder	SDS-Max
Length (mm)	544
Height (mm)	592
Active Vibration Control	Yes
Weight (Kg)	8.8



N581443



10KG SDS-MAX DEMOLITION HAMMER

D25901K

Power Input (W)	1,550
Impact Rate (BPM)	1,050-2,100
Impact Energy (J)	19
Bit Holder	SDS-Max
Length (mm)	690
Height (mm)	250
Active Vibration Control	Yes
Weight (Kg)	10.9



1005550-02



16KG HEX DEMOLITION HAMMER

D25961K

Power Input (W)	1,600
Impact Rate (BPM)	1,450
Impact Energy (J)	35
Bit Holder	30mm HEX
Length (mm)	544
Height (mm)	592
Active Vibration Control	Yes
Weight (Kg)	16.9



1005550-02



30KG HEX DEMOLITION HAMMER WITH TROLLEY

D25981K

Power Input (W)	2,100
Impact Rate (BPM)	960
Impact Energy (J)	62
Bit Holder	28mm HEX
Switch Type	Trigger
Variable Speed Switch	Yes
Lock-On	No
Active Vibration Control	Yes
Weight (Kg)	31



254MM MITER SAW

DW714

Power Input (W)	1,650
No Load Speed (RPM)	4,600
Blade Diameter (mm)	254
Bevel Capacity	45°
Miter Capacity (right/left)	57°/52°
Max. Cutting Capacity (WxH)At 900/900	95x68
Max. Cutting Capacity (WxH)At 450/900	67x68
Max. Cutting Capacity (WxH)At 900/450	95x40
Max. Cutting Capacity (WxH)At 450/450	70x40
Max. Depth of Cut (Saws)	89 mm
Weight (Kg)	13.1
Depth x Length x Height (mm)	470x286x82



305MM DUAL BEVEL SLIDING MITRE SAW

DWS780

Power Input (W)	1675
No Load Speed (RPM)	1,600-3,600
Mitre Capacity	60 / 50°
Bevel Capacity	49 / 49°
Max. Cutting Capacity Width x Height	303 x 110 mm
Blade Diameter	305 x 30 mm



HIGH PERFORMANCE JIGSAW

DWE349

Power Input (W)	500
No Load Stroke Rate (SPM)	660-3,200
Stroke Length (mm)	20
Bevel Capacity	+/- 45°
Max. Cutting Capacity in Wood (mm)	75
Max. Cutting Capacity in Steel (mm)	5
Max. Cutting Capacity in Non Ferrous Metal (mm)	15



90554571

JIGSAW BLADE

SKU	Length (mm)	Working Length (mm)	Tooth Pitch (mm)	Suitable for
DT2161-QZ	76	50	2	Metal
DT2166-QZ	100	68	4	Wood



184MM COMPACT CIRCULAR SAW

DWE561

Power Input (W)	1,200
Blade Diameter (mm)	184
No Load Speed (RPM)	5,500
Max. Depth of Cut at 90o / 45o (mm)	65 / 42
Bevel Angle Adjustment	48°
Weight (Kg)	3.6



254MM TABLE SAW

DWE7470

Power Input (W)	1,800
No Load Speed (RPM)	5,000
Miter Angle	450 L and R
Bevel Angle	00 to 450 L
Blade Size	254 mm
Max. Cut Depth 900 Bevel	76.2 mm
Max. Cut Depth 450 Bevel	63.5 mm
Max. Dado Cut Width	12.7 mm
Max. Dado Blade Diameter	152.4 mm
Weight (Kg)	21



5140133-73

SAW BLADE

SKU	Length (Inch)	Material Application	Tooth Count
DW3114	10	General Purpose	40
DW3106	10	Fine Crosscuts	60



13" THREE KNIFE, TWO SPEED THICKNESS PLANER

DW735

Power Input (W)	2,000-2,200
Max. Depth of Cut (mm)	3
Depth Capacity (mm)	150
Width Capacity (mm)	330
No Load Speed (RPM)	10,000
Cuts Per Inch	96 or 179
Tool Weight (Kg)	41



13" THICKNESS PLANER KNIVES FOR DW735

DW7352

Products Dimensions (mm)	Weight (Kg)	Torque (Nm)	Qty
411 x 101 x 10	0.15	158.2	3



1/4" SHEET PALM GRIP SANDER

DWE6411

Power Input (W)	230
Orbits/Stroke per Minute	14,000
Orbit Size (mm)	1.6
Pad Size (mm)	108 x 115
Height (mm)	135
Weight (Kg)	1.3



125MM RANDOM ORBITAL SANDER

DWE6423

Power Input (W)	230
Orbits/Strokes per Minute	8,000-12,000
Orbits (mm)	2.6
Pad Size (mm)	125
Weight (Kg)	1.28



1.5MM PORTABLE PLANER

D26676

Power Input (W)	550
Maximum Depth of Cut (mm)	1.5
Rebating Depth (mm)	9
Planer Width (mm)	82
Shoe Length (mm)	96



CORDED OSCILLATING MULTI TOOL

DWE315K

Power Input (W)	2,000-2,200
Max. Depth of Cut (mm)	3
Depth Capacity (mm)	150
Width Capacity (mm)	330
No Load Speed (RPM)	10,000
Cuts Per Inch	96 or 179
Tool Weight (Kg)	41



180MM 1250W POLISHER

DWP849X

Power Input (W)	1,250
Max. Disc Diameter (mm)	180
No Load Speed (RPM)	0-600 / 0-3,500
Spindle Thread	M14
Length with Disc (mm)	530
Height (mm)	14.5
Switch Type	Trigger
Weight (Kg)	3.0



TILE CUTTER

DW862

Power Input (W)	1,270
Wheel Diameter (mm)	110
No Load Speed (RPM)	13,500
Max. Depth of Cut (mm)	34
Weight (Kg)	3.1
Cord Length (m)	2.5



1800W COMPACT HEATGUN

D26411

Power Input (W)	1,800
Temperature (oC)	50-600
Weight (Kg)	0.65



2000W DIGITAL LED HEATGUN

D26414

Power Input (W)	2,000
Temperature (oC)	50-600
Air Flow (L/min)	650
Nozzle Diameter (mm)	22
Overheating Protection	Yes
Length (mm)	265
Height (mm)	210
Weight (Kg)	0.85



DEWALT 55 FT. LASER DISTANCE MEASURER

DW055PL-XJ

Range	55 ft/ 16m
Accuracy	1/4" / 6mm
Battery	Built-in Li-ion
Memory	0
Measurement Units	In/Ft/M
Continuous Measurement	Yes
Ingress Protection	IP54
Dimension (mm)	64.5x38x20.6

NEW



ELECTRICIAN POUCH M+

DWST83483-1



NEW

Dimensions	290mm x 150mm x 95mm
Durable	1680D
Pockets	19

DRILL HOLSTER

DWST83486-1



NEW

Dimensions	235 mm x 200mm x 60 mm
Durable	1680D
Pockets	6

45PC SCREWDRIVING DRILL BIT SET

DT71518-QZ

The DEWALT professional drilling/driving bit set offers a variety of industrial screwdriving/fastening bits including the most common fitments and drill bit sizes. The included magnetic drive guide helps reduce slipping and wobble, allowing users to work more efficiently and effectively. The kit comes with a professional case that keep things organized and provide maximum durability for all of the accessories.

- Combination set of both drill and screwdriver bits
- Suitable for drilling in metal, wood, plastic
- Comes with all the most common screwdriver sizes
- Supplied in a plastic case
- Assembly, drilling holes in metal, wood or plastic.

NEW



19PC METAL DRILL BIT HSS-G SET

DT5923-QZ

With 118° tip grinding, DEWALT Black Oxide Drill Bits deliver accurate holes. Produced in high quality high speed steel for extended durability.

- Precision ground spiral groove for maximum drilling progress and tool life as well as excellent concentricity
- Made of high-speed steel (HSS) according to DIN 338 Right-hand cutting spiral groove type N, 118 ° point angle, Tapered section.
- Surface bare metallic, dry
- Metal | Wood | Plastic

NEW



CONSTRUCTION TRIPOD

DW0737

The DW0737 Construction Tripod has a lightweight, durable aluminum construction and is easy to transport. Features flat head design, and pointed steel feet are stable on any terrain.

- Industry standard 5/8"x11 mounting threads with flat head design
- Quick-release legs for fast and easy set-up
- Height 60" opened, 38" closed
- Lightweight, durable, aluminum construction
- Pointed steel feet are stable on any terrain
- Built-in strap for easy transport

NEW





NEW! BONDED ABRASIVE

Sharp abrasives

Superior Grinding

High grain concentration

Aggressive grinding action - Rapid removal rate

Proprietary material mix

Ensures durable long life wheel

3 Sheets of fiberglass

Increases strength & provides wheel safety

Adheres to EN & ANSI standards

Certified for safety & consistent performance

Well balanced wheel

Reduces tool vibration



IA Type
HP HIGH Performance™

- High performance industrial
- Consistent quality



FCIA Type
SPEED™

FAST GRINDING

13-34% faster
than competitor

HOW WE WIN

Longer Wheel Life

Assured by DEWALT bond formulation

Rapid Removal Rate & Smooth Grinding

Ensured by Premium aggressive grains


Consistent Product Quality & Performance

Achieved by advanced manufacturing processes

PERFORMANCE CHART*

2-3x LIFE AGAINST CONVENTIONAL GRINDING WHEEL WITH BETTER CUT RATE

DEWALT 4 inch metal grinding wheel Grind Ratio Comparison with Competitors



Grinding Ratio: Grams of steel removed, per gram of wheel used

* Performance of grinding wheels was evaluated with an automated test rig on standard steel and grinding conditions.

GRINDING WHEELS

SKU #	TYPE	DIAMETER	THICKNESS	BORE	SPECIFICATION	APPLICATION	RPM
DWA4500IA-B1	27	100	6.0	16	A24RBF	Metal	15,300
DWA4500FCIA-B1	27	100	6.0	16	A24QBF	Metal Fast Grinding	15,300
DWA4500SIA-B1	27	100	6.0	16	WA24RBF	Inox	15,300
DW4543AIA-B1	27	125	6.0	22	A24RBF	Metal	12,250
DW4543AFCIA-B1	27	125	6.0	22	A24QBF	Metal Fast Grinding	12,250
DW4543SIA-AE	27	125	6.0	22	WA24RBF	INOX	12,250
DW4545AIA-B1	27	150	6.0	22	A24RBF	Metal	10,200
DW4545SIA-B1	27	150	6.0	22	WA24RBF	INOX	10,200
DW4547AIA-AE	27	180	6.0	22	A24RBF	Metal	8,500
DW4547SIA-AE	27	180	6.0	22	WA24RBF	INOX	8,500
DW4547AFCIA-AE	27	180	6.0	22	A24QBF	Metal Fast Grinding	8,500
DW4549AIA-AE	27	230	6.0	22	A24RBF	Metal	6,650

CUTTING WHEELS

SKU #	TYPE	DIAMETER	THICKNESS	BORE	SPECIFICATION	APPLICATION	RPM
DWA4520FAIA-B1	1	100	2.5	16	A30SBF	Metal	15,300
DWA4520FASIA-B1	1	100	2.5	16	WA30RBF	INOX	15,300
DWA8060SIA-AE	1	105	1.0	16	WA60TBF	INOX	15,300
DWA8050SIA-B1	1	105	1.6	16	WA46TBF	INOX	15,300
DWA8063SIA-B1	1	125	1.0	22	WA60TBF	INOX	12,250
DWA8052SIA-B1	1	125	1.6	22	WA46TBF	INOX	12,250
DWA4522FAIA-B1	1	125	2.5	22	A30SBF	Metal	12,250
DWA4522FASIA-B1	1	125	2.5	22	WA30RBF	INOX	12,250
DWA4523FAIA-B1	1	150	2.5	22	A30SBF	Metal	10,200
DWA4523FASIA-B1	1	150	2.5	22	WA30RBF	INOX	10,200
DWA4524FAIA-B1	1	180	2.5	22	A30SBF	Metal	8,500
DWA4524FASIA-B1	1	180	2.5	22	WA30RBF	INOX	8,500
DWA4525FAIA-B1	1	230	2.5	22	A30SBF	Metal	6,650
DWA4525FASIA-B1	1	230	2.5	22	WA30RBF	INOX	6,650

CUTTING & LIGHT GRINDING WHEELS

SKU #	TYPE	DIAMETER	THICKNESS	BORE	SPECIFICATION	APPLICATION	RPM
DWA4520IA-B1	27	100	3.0	16	A30SBF	Metal	15,300
DWA4520SIA-AE	27	100	3.0	16	WA30RBF	INOX	15,300
DWA4522IA-AE	27	125	3.0	22	A30SBF	Metal	12,250
DWA4522SIA-AE	27	125	3.0	22	WA30RBF	INOX	12,250
DWA4523IA-B1	27	150	3.0	22	A30SBF	Metal	10,200
DWA4523SIA-B1	27	150	3.0	22	WA30RBF	INOX	10,200
DWA4524IA-AE	27	180	3.0	22	A30SBF	Metal	8,500
DWA4524SIA-AE	27	180	3.0	22	WA30RBF	INOX	8,500
DWA4525IA-AE	27	230	3.0	22	A30SBF	Metal	6,650

CHOP SAW CUTTING WHEELS

SKU #	TYPE	DIAMETER	THICKNESS	BORE	SPECIFICATION	APPLICATION	RPM
DWA8011R-B1	1	355	3.0	25.4	A30RBF	Metal	3,875
DWA8012R-B1	1	405	3.0	32	A30RBF	Metal	3,440

EN12413




* THE ABOVE ABRASIVE WHEELS COMPLIES TO EN & ANSI STANDARDS

- Weld blending, removing weld slag
- Deburring
- Surface finishing and preparation
- Edge blending and chamfering
- Free of iron, sulphur and chlorine for contaminant-free grinding

FERROUS METAL STAINLESS STEEL

FLAP DISCS



HOW WE WIN



- Zirconia grit enables 3x faster material removal than fiber resin discs
- Premium abrasive cloth provides up to 15x longer life than fiber resin discs
- Free of iron, sulfur, and chlorine for contaminant free grinding
- Type 27 backing provides grinding angle of 0-15 degrees
- Type 29 backing provides grinding angle of 15-25 degrees



DEWALT HIGH PERFORMANCE FLAP DISCS

Cat No.	Diameter [mm]	Bore Size [mm]	Specification	Grit	PKS
DW8300	100	16	ZIRC	36	10
DW8302	100	16	ZIRC	60	10
DW8303	100	16	ZIRC	80	10
DW8304	100	16	ZIRC	120	10
DW8338	125	22.2	ZIRC	24	10
DW8315	125	22.2	ZIRC	36	10
DW8317	125	22.2	ZIRC	60	10
DW8318	125	22.2	ZIRC	80	10
DW8319	125	22.2	ZIRC	120	10
DW8340	180	22.2	ZIRC	24	10
DW8321	180	22.2	ZIRC	36	10
DW8323	180	22.2	ZIRC	60	10
DW8324	180	22.2	ZIRC	80	10
DW8325	180	22.2	ZIRC	120	10

Examples of Compatible DEWALT Power Tools



DWE8100S




DWE8210PL



DWE8310S

FEATURES & BENEFIT

- 01** Unique Manufacturing process increases durability of product
- 02** High diamond concentration increases speed and life of products
- 03** Superior Bond Matrix ensure consistent and long lasting high cutting speed



- 04** Optimum bond hardness reduces heat generation and subsequently ensure superb finishes
- 05** Evenly distributed diamond provides a consistent and effortless cut
- 06** High quality steel core reduces vibration during cutting



Also Available in
*high performance
Continuous
DW4790

HOW WE WIN

- Consistent cutting speed
- Well distributed diamond concentration quality
- High quality steel core reduces vibration during cuts
- Optimum bond hardness to meet general user CTQ

APPLICATION

Concrete



Marble



Brick



Tile



DEWALT HIGH PERFORMANCE DIAMOND BLADE

SKU	Description	Diameter	Box Quantity	Segment height	Arbor in blade	Installed adapter
DW4781-B1	105 x 2mm x 16mm HP segmented diamond blade (kering)	105	10	1.7	20	16
DW4790-B1	105 x 2mm x 16mm HP Continuous rim diamond blade (basah)	105	10	1.7	20	16



Application :

- Suitable for wood and aluminium cutting

Features :

- Super smooth cuts, little binding and burning generate best cutting result.

Examples of Compatible DEWALT Power Tools



DWE561



DW714



DWE7470

Cat No.	Description	Diameter [mm]	Bore Size	Teeth	Application
DWA03210-B1	TCT Al Saw Blade 255x30x80T	255	30	80	Aluminium
DWA03220-B1	TCT Al Saw Blade 255x30x100T	255	30	100	Aluminium
DWA03230-B1	TCT Al Saw Blade 305x30x80T	305	30	80	Aluminium
DWA03240-B1	TCT Al Saw Blade 305x30x100T	305	30	100	Aluminium
DWA03250-B1	TCT Al Saw Blade 305x30x120T	305	30	120	Aluminium
DWA03260-B1	TCT Al Saw Blade 255x30x120T	255	30	120	Aluminium
DWA03410-B1	TCT Saw Blade 105x16x40T	105	16	40	Wood
DWA03724-B1	TCT Saw Blade 185x25.4x24T	185	25.4	24	Wood
DWA03740-B1	TCT Saw Blade 185x25.4x40T	185	25.4	40	Wood
DWA03760-B1	TCT Saw Blade 185x25.4x60T	185	25.4	60	Wood
DWA03940-B1	TCT Saw Blade 235x30x40T	235	30	40	Wood
DWA03960-B1	TCT Saw Blade 235x30x60T	235	30	60	Wood
DWA03980-B1	TCT Saw Blade 235x30x80T	235	30	80	Wood
DWA31040-B1	TCT Saw Blade 255x30x40T	255	30	40	Wood
DWA31060-B1	TCT Saw Blade 255x30x60T	255	30	60	Wood



Applications

- Suitable for fast drilling of plug, anchor or clearance holes in masonry, stone, concrete and brick/block work

Features

- The innovative EXTREME DEWALT 2 SDS-Plus drill bit is amongst the very best in terms of durability, drilling life and speed



DEWALT EXTREME 2 SDS-PLUS DRILL BITS

Cat No.	Diameter [mm]	Length [mm]	Working Length [mm]	Cat No.	Diameter [mm]	Length [mm]	Working Length [mm]
DT9625	3	135	75	DT9558-QZ	12	600	550
DT9500-QZ	3.5	110	50	DT9559-QZ	12	1,000	950
DT9502-QZ	4	110	50	DT9560-QZ	13	160	100
DT9503-QZ	4	160	100	DT9561-QZ	13	200	150
DT9504-QZ	5	110	50	DT9562-QZ	13	260	200
DT9505-QZ	5	160	100	DT9563-QZ	13	300	250
DT9506-QZ	5	210	150	DT9565-QZ	13	450	400
DT9507-QZ	5	310	250	DT9566-QZ	14	160	100
DT9620-QZ	5	460	400	DT9567-QZ	14	200	150
DT9508-QZ	5.5	110	50	DT9568-QZ	14	260	200
DT9509-QZ	5.5	160	100	DT9569-QZ	14	300	250
DT9510-QZ	5.5	210	150	DT9570-QZ	14	450	400
DT9511-QZ	5.5	200	200	DT9571-QZ	14	600	550
DT9512-QZ	5.5	310	250	DT9572-QZ	14	1,000	950
DT9513-QZ	5.5	460	400	DT9573-QZ	15	160	100
DT9514-QZ	6	110	50	DT9574-QZ	15	200	150
DT9515-QZ	6	160	100	DT9575-QZ	15	260	200
DT9516-QZ	6	210	150	DT9576-QZ	15	300	250
DT9517-QZ	6	260	200	DT9577-QZ	15	450	400
DT9621-QZ	6	310	250	DT9578-QZ	16	160	100
DT9518-QZ	6	460	400	DT9579-QZ	16	200	150
DT9519-QZ	6.5	110	50	DT9580-QZ	16	260	200
DT9520-QZ	6.5	160	100	DT9581-QZ	16	300	250
DT9521-QZ	6.5	210	150	DT9582-QZ	16	450	400
DT9522-QZ	6.5	260	200	DT9583-QZ	16	600	550
DT9523-QZ	6.5	310	250	DT9584-QZ	16	800	750
DT9524-QZ	7	110	50	DT9585-QZ	16	1,000	950
DT9525-QZ	7	160	100	DT9586-QZ	17	200	150
DT9526-QZ	7	210	150	DT9587-QZ	18	200	150
DT9527-QZ	7	260	200	DT9588-QZ	18	250	200
DT9528-QZ	8	110	50	DT9589-QZ	18	300	250
DT9529-QZ	8	160	100	DT9590-QZ	18	450	400
DT9530-QZ	8	210	150	DT9591-QZ	18	600	550
DT9531-QZ	8	260	200	DT9592-QZ	18	800	750
DT9532-QZ	8	310	250	DT9593-QZ	18	1,000	950
DT9533-QZ	8	410	350	DT9596-QZ	19	450	400
DT9534-QZ	8	460	400	DT9597-QZ	20	200	150
DT9535-QZ	8	600	540	DT9598-QZ	20	300	250
DT9536-QZ	9	160	100	DT9599-QZ	20	450	400
DT9537-QZ	9	210	150	DT9600-QZ	20	600	550
DT9539-QZ	10	110	50	DT9601-QZ	20	1,000	950
DT9540-QZ	10	160	100	DT9602-QZ	22	250	200
DT9541-QZ	10	210	150	DT9603-QZ	22	300	250
DT9542-QZ	10	260	200	DT9604-QZ	22	450	400
DT9543-QZ	10	310	250	DT9605-QZ	22	600	550
DT9544-QZ	10	350	300	DT9606-QZ	22	800	750
DT9545-QZ	10	460	400	DT9607-QZ	22	1,000	950
DT9546-QZ	10	600	550	DT9609-QZ	24	250	200
DT9547-QZ	10	1,000	950	DT9610-QZ	24	450	400
DT9548-QZ	11	160	100	DT9611-QZ	25	250	200
DT9549-QZ	11	210	150	DT9612-QZ	25	300	250
DT9550-QZ	11	260	200	DT9613-QZ	25	450	400
DT9551-QZ	11	310	250	DT9614-QZ	25	1,000	950
DT9552-QZ	12	160	100	DT9615-QZ	26	250	200
DT9553-QZ	12	200	150	DT9616-QZ	26	450	400
DT9554-QZ	12	260	200	DT9617-QZ	26	800	750
DT9555-QZ	12	300	250	DT9618-QZ	30	250	200
DT9556-QZ	12	350	300	DT9619-QZ	30	450	400
DT9557-QZ	12	450	400				



Applications

- Suitable for drilling of plug, anchor or clearance holes in masonry, stone, concrete and brick/block work.

Features

- Maximized flute design, removes dust effectively and improves heat dissipation

DEWALT SDS-PLUS DRILL BITS							
Cat No.	Diameter [mm]	Length [mm]	Working Length [mm]	Cat No.	Diameter [mm]	Length [mm]	Working Length [mm]
DW00700	4	110	50	DW00715	13	300	250
DW00701	5	110	45	DW00716	14	160	100
DW00702	6	110	50	DW00717	16	160	100
DW00703	6	160	95	DW00718	16	200	150
DW00704	6.5	160	100	DW00719	16	300	250
DW00705	8	110	50	DW00720	16	460	410
DW00706	8	160	95	DW00721	18	200	150
DW00707	8	210	150	DW00725	20	200	150
DW00708	10	110	50	DW00726	20	300	250
DW00709	10	160	95	DW00727	20	460	410
DW00710	10	210	150	DW00728	22	200	150
DW00711	10	350	210	DW00730	22	450	400
DW00712	12	160	95	DW00731	25	250	200
DW00713	12	460	410	DW00732	25	450	400
DW00714	13	160	100				

Examples of Compatible DEWALT Power Tools



D25133K



D25143K



D25144K



DCH253M2



Applications

- For use with SDS-Max drive hammer drills for anchor, fixing or clearance holes in masonry concrete, brick or block work


Features

- 4 flute spiral with maximum flute entry enables faster debris removal.




DEWALT EXTREME SDS-MAX DRILL BITS

Cat No.	Diameter [mm]	Length [mm]	Working Length [mm]	Cat No.	Diameter [mm]	Length [mm]	Working Length [mm]
DT9400-QZ	12	340	200	DT9426-QZ	25	920	800
DT9401-QZ	12	540	400	DT9427-QZ	26	340	200
DT9402-QZ	12	670	550	DT9428-QZ	26	540	400
DT9403-QZ	13	340	200	DT9429-QZ	28	380	250
DT9404-QZ	13	540	400	DT9430-QZ	28	570	450
DT9405-QZ	14	340	200	DT9431-QZ	28	670	550
DT9406-QZ	14	540	400	DT9432-QZ	30	380	250
DT9407-QZ	15	340	200	DT9433-QZ	30	570	450
DT9408-QZ	15	540	400	DT9434-QZ	32	380	250
DT9409-QZ	16	340	200	DT9435-QZ	32	570	450
DT9410-QZ	16	540	400	DT9436-QZ	32	920	800
DT9411-QZ	18	340	200	DT9437-QZ	35	380	250
DT9412-QZ	18	540	400	DT9438-QZ	35	570	450
DT9413-QZ	19	340	200	DT9439-QZ	35	670	550
DT9414-QZ	19	540	400	DT9440-QZ	36	570	450
DT9415-QZ	19	670	550	DT9441-QZ	38	380	250
DT9416-QZ	20	340	200	DT9442-QZ	38	570	450
DT9417-QZ	20	540	400	DT9443-QZ	38	670	550
DT9418-QZ	20	920	800	DT9444-QZ	40	380	250
DT9419-QZ	22	340	200	DT9445-QZ	40	570	450
DT9420-QZ	22	540	400	DT9446-QZ	40	920	800
DT9421-QZ	22	920	800	DT9447-QZ	42	570	450
DT9422-QZ	24	340	200	DT9448-QZ	45	570	450
DT9423-QZ	24	540	400	DT9449-QZ	50	570	450
DT9424-QZ	25	340	200	DT9450-QZ	52	570	450
DT9425-QZ	25	540	400				



- Heavy duty chiseling and demolition task in concrete, stone (medium hardness), floor and wall tiles and general masonry
- Wide range of chisels
- Specially toughened steel and micro-processor controlled heat treatment ensures consistent tough chisels with longer life
- Available in pointed & flat tip shape

Shank Filment



DEWALT DEMOLITION CHISEL BITS			
Cat No.	Fitment	Tip Shape	Description
DWA0819	17mm Hex	Pointed	280mm pointed chisel 17mm Hex
DWA0814	17mm Hex	Flat	280mm x 22mm flat chisel 17mm Hex
DWA0818	17mm Hex	Pointed	450mm pointed chisel 17mm Hex
DWA0815	17mm Hex	Flat	450mm x 22mm flat chisel 17mm Hex
DWA0809	19mm Hex	Pointed	400mm pointed chisel 19mm Hex
DWA0811	19mm Hex	Flat	400mm x 25mm flat chisel 19mm Hex
DWA0810	19mm Hex	Pointed	600mm pointed chisel 19mm Hex
DWA0812	19mm Hex	Flat	600mm x 25mm flat chisel 19mm Hex
DWA0801	SDS Plus	Pointed	250mm pointed chisel SDS +
DWA0802	SDS Plus	Flat	250mm x 20mm flat chisel SDS +
DWA0804	SDS MAX	Pointed	300mm pointed chisel SDS-Max
DWA0805	SDS MAX	Pointed	400mm pointed chisel SDS-Max
DWA0806	SDS MAX	Flat	300mm x 25mm flat chisel SDS-Max
DWA0807	SDS MAX	Flat	400mm x 25mm flat chisel SDS-Max

Examples of Compatible DEWALT Power Tools



D25580



D25811K



D25871K



D25901



Applications

- Typically used for drilling anchor, plastic plug, fixing or pipework clearance holes
- Suitable for masonry, brick/blockwork, stone

Features

- Rotary/percussion masonry drill bit 130° Douglas form carbide tip
- Shank diameter of drill bits 10-13 mm is reduced to 9.5 mm
- Shank diameter of drill bits larger than 13 mm is reduced to 12.7 mm



DWD024

DEWALT MASONRY DRILL BITS					
Cat No.	Diameter [mm]	Length [mm]	Cat No.	Diameter [mm]	Length [mm]
DW530300C-B1	3.0	60.0	DW531600C-B1	16.0	150.0
DW530400C-B1	4.0	75.0	DW531800C-B1	18.0	160.0
DW530500C-B1	5.0	85.0	DW532000C-B1	20.0	160.0
DW530600C-B1	6.0	100.0	DW540500C-B1	5.0	150.0
DW530650C-B1	6.5	100.0	DW540600C-B1	6.0	150.0
DW530700C-B1	7.0	100.0	DW540800C-B1	8.0	150.0
DW530800C-B1	8.0	120.0	DW540950C-B1	10.0	150.0
DW530900C-B1	9.0	120.0	DW560800C-B1	8.0	300.0
DW531000C-B1	10.0	120.0	DW560950C-B1	10.0	300.0
DW531100C-B1	11.0	150.0	DW561250C-B1	13.0	300.0
DW531200C-B1	12.0	150.0	DW561600C-B1	16.0	300.0
DW531300C-B1	13.0	150.0	DW561900C-B1	20.0	300.0
DW531400C-B1	14.0	150.0			



Applications

- Suitable for portable or stationary drilling of high alloy content steels and metals with a tensile strength of up to 1100N/mm² e.g. heat and acid proof steel, cast iron, bronze, welded seams, stainless and chrome nickel steels

Features


- Faster drilling - up to 4x faster than standard HSS-R drill bits.
- Increased durability - up to 50% stronger than standard HSS-R drill bits.
- Cleaner, more accurate, burr-free holes due to recessed cutting wings
- Innovative tapered web greatly reduces breakage
- No-Slip shank with 3 flats eliminates slipping in the chuck [diameters 5.0mm and above only]
- Gold Ferrous Oxide coating prevents overheating for longer bit life
- 5% cobalt alloyed High Speed Steel for stability at high temperatures when drilling tough materials.

DEWALT HSS-CO EXTREME COBALT DRILL BITS

Cat No.	Diameter [mm]	Length [mm]	Working Length [mm]	Pcs in pack.
DT5408-QZ	3.5MM	70	39	2
DT5415-QZ	5.5MM	93	57	1
DT5416-QZ	6.0MM	93	57	1
DT5417-QZ	6.5MM	101	63	1
DT5421-QZ	9.0MM	125	81	1
DT5424-QZ	11.0MM	142	94	1
DT5426-QZ	12.0MM	151	101	1
DT5427-QZ	13.0MM	151	101	1
DT5636-QZ	4.2MM	75	43	1
DT5641-QZ	7.5MM	109	117	1
DT5644-QZ	8.5MM	117	75	1
DT5645-QZ	9.5MM	125	81	1
DT5647-QZ	10.5MM	133	87	1
DT5648-QZ	11.5MM	142	94	1
DT5650-QZ	12.5MM	151	101	1



LIFE



*In Drill Press vs. Other Uncoated Cobalt Drills

LIFE - Drill Press
4140 Tools Steel, .006" Feed Rate, 750 RPM



Applications

- Suitable for portable drilling of steel, alloyed and non-alloyed up to 900 N/mm²
- For drilling sheet or thin materials [suitable for use in wood and plastics]

Features

- Faster drilling with up to 4x faster than standard HSS-R drill bits
- Increased durability with up to 50% stronger than standard HSS-R drill bits
- Cleaner, more accurate, burr-free holes due to recessed cutting wings
- Innovative tapered web greatly reduces breakage
- No-Slip shank with 3 flats eliminates slipping in the chuck [diameters 5.0mm and above only]
- Gold Ferrous Oxide coating prevents overheating for longer bit life


FEATURES AND BENEFITS

PATENTED PILOT POINT TIP

- For clean, accurate & burr-free round holes
- Eliminates bit walking




DEWALT




COMPETITOR

PATENTED THICKER CORE DESIGN

- Strengthens bit and reduces breakage




DEWALT



COMPETITOR

NO SPIN SHANK

- Eliminates bit slippage



DEWALT HSS EXTREME 2 METAL PILOT POINT DRILL BITS

Cat No.	Diameter [mm]	Length [mm]	Working Length [mm]	Pack Qty.
DT5538-QZ	2.5	57	30	10
DT5539-QZ	3	61	33	10
DT5541-QZ	3.3	65	36	10
DT5542-QZ	3.5	70	39	10
DT5543-QZ	4	75	43	10
DT5544-QZ	4.2	75	43	10
DT5545-QZ	4.5	80	46	10
DT5546-QZ	4.8	86	46	10
DT5547-QZ	5	86	46	10
DT5548-QZ	5.5	93	57	10
DT5549-QZ	6	93	57	10
DT5550-QZ	6.5	101	58	10
DT5551-QZ	7	109	66	10
DT5552-QZ	7.5	109	66	10
DT5553-QZ	8	117	72	10
DT5554-QZ	8.5	117	72	10
DT5555-QZ	9	125	78	10
DT5556-QZ	9.5	125	78	10
DT5557-QZ	10	133	84	10
DT5558-QZ	10.5	133	84	10
DT5559-QZ	11	142	91	10
DT5560-QZ	11.5	142	91	10
DT5561-QZ	12	151	98	10
DT5562-QZ	12.5	151	98	10
DT5563-QZ	13	151	98	10



BEST SELLER

4x
Lebih
Cepat

50%
Lebih
Kuat

3x
Lebih
Bersih

2x
Lebih
Akurat

Applications

- Suitable for portable or stationary drilling in steel cast steel, alloyed and non-alloyed material, grey cast-iron, spherical-graphite cast iron, sintered iron, nickel, brass, etc up to 900N/mm²

Features

- Precision ground twist drill bit for rapid drilling, long life and excellent concentricity
- Ground from solid stock right hand cutting, type 'N' flute, precision ground at 135° point angle
- Diameter tolerance to h8
- Drills above 13mm [1/2"] have a shank reduced to 12.7mm

Examples of Compatible DEWALT Power Tools



DCD716C2K



DCD791D2



DWD024

DEWALT HSS-G JOBBER METAL DRILL BITS (BLACK OXIDE)

Cat No.	Description	Diameter [mm]	Length [mm]	Pack Qty
DT50465-XJ	PACK of 10 HSS-G Drill Bit 1.0MM	1	34	10pcs
DT50466-XJ	PACK of 10 HSS-G Drill Bit 1.5MM	1.5	40	10pcs
DT50467-XJ	PACK of 10 HSS-G Drill Bit 1.6MM	1.6	43	10pcs
DT50468-XJ	PACK of 10 HSS-G Drill Bit 2.0MM	2	49	10pcs
DT50469-XJ	PACK of 10 HSS-G Drill Bit 2.5MM	2.5	57	10pcs
DT50470-XJ	PACK of 10 HSS-G Drill Bit 3.0MM	3	61	10pcs
DT50471-XJ	PACK of 10 HSS-G Drill Bit 3.2MM	3.2	65	10pcs
DT50473-XJ	PACK of 10 HSS-G Drill Bit 4.0MM	4	75	10pcs
DT50474-XJ	PACK of 10 HSS-G Drill Bit 4.5MM	4.5	80	10pcs
DT50475-XJ	PACK of 10 HSS-G Drill Bit 4.8MM	4.8	86	10pcs
DT50476-XJ	PACK of 10 HSS-G Drill Bit 5.0MM	5	86	10pcs
DT50477-XJ	PACK of 10 HSS-G Drill Bit 5.5MM	5.5	93	10pcs
DT50478-XJ	PACK of 10 HSS-G Drill Bit 6.0MM	6	93	10pcs
DT50479-XJ	PACK of 10 HSS-G Drill Bit 6.35MM	6.35	101	10pcs
DT50480-XJ	PACK of 10 HSS-G Drill Bit 6.5MM	6.5	101	10pcs
DT50481-XJ	PACK of 10 HSS-G Drill Bit 7.0MM	7	109	10pcs
DT50484-XJ	PACK of 5 HSS-G Drill Bit 8.0MM	8	117	5pcs
DT50485-XJ	PACK of 5 HSS-G Drill Bit 8.5MM	8.5	117	5pcs
DT50486-XJ	PACK of 5 HSS-G Drill Bit 9.0MM	9	125	5pcs
DT50487-XJ	PACK of 5 HSS-G Drill Bit 9.5MM	9.5	125	5pcs
DT50488-XJ	PACK of 5 HSS-G Drill Bit 10.0MM	10	133	5pcs
DT50489-XJ	PACK of 5 HSS-G Drill Bit 10.5MM	10.5	133	5pcs
DT50490-XJ	PACK of 5 HSS-G Drill Bit 11.0MM	11	142	5pcs
DT50491-XJ	PACK of 5 HSS-G Drill Bit 11.5MM	11.5	142	5pcs
DT50492-XJ	PACK of 5 HSS-G Drill Bit 12.0MM	12	151	5pcs
DT50493-XJ	PACK of 5 HSS-G Drill Bit 12.5MM	12.5	151	5pcs
DT50494-XJ	PACK of 5 HSS-G Drill Bit 13.0MM	13	151	5pcs

LAYANAN PURNA JUAL Garansi DEWALT



3 TAHUN



1. Garansi terbatas DEWALT

Garansi terbatas selama 3 tahun semenjak tanggal pembelian :

- Gratis penggantian suku cadang sebanyak 3 kali selama 3 tahun.

Catatan : Masa garansi akan habis setelah penggantian suku cadang atau periode garansi yang diberikan (yang tercapai terlebih dahulu).

2. Syarat – syarat pengajuan klaim

Berikut dokumen yang harus dilengkapi pada saat pengajuan klaim ke Authorized Service Center:

- Kartu garansi
- Nota pembelian
- Unit produk beserta aksesoris dan kelengkapan

3. Pengecualian

Ketentuan garansi tidak berlaku pada:

- Kerusakan yang disebabkan oleh penggunaan suku cadang yang tidak asli.
- Suku cadang yang diganti secara rutin seperti: Carbon brush, Cord, Plug, Chuck, dll.
- Aksesoris dan Attachment.
- Unit produk yang sudah dimodifikasi
- Unit produk yang pernah diperbaiki oleh teknisi tidak resmi
- Kerusakan yang disebabkan oleh benda asing, zat asing, kecelakaan, penggunaan unit produk yang tidak

sesuai petunjuk, kelalaian, dll.

- * Untuk poin-poin yang tidak dijelaskan di atas, mohon untuk berkoordinasi dengan pihak Authorized Service Center.

Untuk memanfaatkan garansi Anda, bukti pembelian dan pengisian kartu garansi yang benar harus disertakan.

AUTHORIZED SERVICE CENTER

Ambon

CV. Bob Motor Ambon
Jl. Cendrawasih, Gang Merpati No.3,
Kelurahan Rijali, Sirimau, Kota Ambon,
Maluku 97123
Tel.: (+62) 911 – 349164
Hp.: 0821 9791 5549

Balikpapan

PT. Bumi Bangun Perkasa
Jl. Mulawarman Batakan No.17 RT.33
Balikpapan, Kalimantan Timur
Tel.: (+62) 542 – 7571079 / 7571080
Fax.: (+62) 542 – 7571081
Email.: angga@bumibangun.com
Web.: www.bumibangun.com

Bandung

PT. Haskar Inter Global / Toko Hong Kie
Jl. Station Timur No. 36 kelurahan Braga,
kecamatan sumur Bandung, kota Bandung
40111
Tel.: (+62) 22 – 4263402 / 4263489
Fax.: (+62) 22 – 4237161
Email.: haskarig@yahoo.co.id

PT. Perkakasku Multi Cemerlang
Jl. Jend. Ahmad Yani 350
Bandung, Jawa barat 40271
Tel.: (+62) 22 – 7271396 / 7271332
Fax.: (+62) 22 – 7214547

Batam

PT. Great Dynamic Indonesia
Komplek Srijaya Abadi Blok F No.7-10,
Nagoya, Batam Island - Indonesia 29432
Tel.: (+62) 778 – 455514 / 456881
Fax.: (+62) 778 – 457154
Email.: gdi@greatdynamic.com
handoko@greatdynamic.com
Website : www.greatdynamic.com

Bau Bau

PT. Sinar Mitra Bangunan /
Izzie Home
Jl. Sultan Hassanudin No 5 Bau-Bau
Pulau Buton, Sulawesi Tenggara
Tel.: (+62) 402 – 2821413 / 2821851
Fax.: (+62) 402 – 2822035
Email.: smb@izziehome.com

Bekasi

Toko Multi Mulya Teknik
Jl. Raya Cibarusah no 15/16 Desa
sukaesmi, lippo Cikarang, Bekasi
Tel.: (+62) 21 – 8971822 / 8971823

Bogor

PT. Dyas Marto Perkasa
Ruko Cikema Pabuaran
Jl. Raya Jakarta Bogor KM. 41 RT 001/005
Pabuaran Cibinong – Bogor 16916
Tel.: (+62) 21 – 8760999 / 8745810
Fax.: (+62) 21 – 8371 3366

Denpasar

Toko Mulia Teknik
Jl. Gatot Subroto No. 388,
Kec. Denpasar Utara - Bali, 80111
Hp.: 0851 0281 6699
Email.: muliateknikgatsu345@gmail.com

Depok

CV. Hanna Teknik
Jl. Akses UI No. 94, Kelapa Dua,
Cimanggis, Depok, Jawa Barat 16451
Tel.: (+62) 21 – 870 1111
Fax.: (+62) 21 – 870 2222
Email.: hannateknik@gmail.com

Jakarta

PT. Semesta Jaya Kimia
Jl. Gajah Mada No. 50, Kel. Krukut,
Kec. Taman Sari, Jakarta Barat 11140
Tel.: (+62) 21 – 6333355 / 6326895
Wa.: 0877 8679 6502

PT. Mitra Teknik Elektrindo
Komplek Ruko Glodok Plaza Blok A No.15
Taman Sari Glodok
Jakarta Barat 11140
Tel.: (+62) 21 – 6250606 / 6250609
Hp.: 0815 1357 1915
Email.: mitrateknikeletrindo@gmail.com
ssdmte@gmail.com
adefirman27@yahoo.com

PT. Yuan Wira Perdana
LTC Glodok Lt. GF1 Blok A26 No. 8-9
Jl. Hayam Wuruk Kel. Mangga Besar -
Jakarta Barat
Tel.: (+62) 21 – 22686872 / 811486909
Email.: service.powertools@yuanwira.com

Lampung

Toko Prima Keramik
Jl teuku umar no 5, Kedaton Bandar
Lampung
Tel.: (+62) 721 – 788672

Kendari

Toko Pelita Indah
Jl. MT Haryono no.95D-E Kendari Sulawesi
tenggara
Tel.: (+62) 401 – 3196605
Email.: pelitaindah.kendari@gmail.com

Makassar

CV. Zidan Al Fatih
Jl. Aroepala Perum Taman Yasmin E2/6,
Kota Makassar, Sulawesi Selatan
Tel.: (+62) 411 – 4675585
Hp.: 0812 4279 0627 / 0811 4101 1979
Email.: zidanalfatih@yahoo.com

CV. Zidan Al Fatih
Jl. Racing Centre / Prof. Abdurahman
Basalamah. No.2, Kec. Panakukang, kel.
Karampuang, kota Makassar. K.Pos 90231
Tel.: (+62) 411 – 4675585
Hp.: 0812 4279 0627 / 0811 4101 1979
Email.: zidanalfatih@yahoo.com

Medan

PT. Faedah Teknik
Jl. Tjong Yong Hian (d/h Jl. Bogor No.40),
Medan
Tel.: (+62) 61 – 4568886
Hp.: 0822 2108 668
Fax.: (+62) 61 – 4569174
Email.: faedah.medan@gmail.com

Padang

JD Teknik
Jl. Pagang Raya - Siteba, No. 41-41A RT.01
/ RW.01 Kurao Pagang, Nanggalo, Padang
- Sumatera Barat 25176
Hp.: 0821 6907 0055
Email.: ngs_pdg@yahoo.com

Palopo

Toko Setia Bangunan
Jl. K.H.A Razak No.97 KEL.Pajalesang Kec.
Wara Kota Palopo, Sulawesi Selatan
Hp.: 0812 4301 1143
Email.: rudylai@gmail.com

Pangkep

UD. Sentral Bangunan
Jl.Kemakmuran KM51 Kab.Pangkajene &
Kepulauan,Sulawesi Selatan.
Hp.: 0813 8929 1212

Pekanbaru

CV. Teknik Steel
Jl. Angkasa No. 34, Air Hitam, Payung
Sekaki, Pekanbaru, Riau.
Tel.: (+62) 761 – 7865150
Email.: Marketing.tekniksteel@gmail.com

Samarinda

PT. Subur Makmur Bangunan
Jl. Gatot Subroto No.62-68, Bandara,
Kec. Sungai Pinang, Kota Samarinda,
Kalimantan Timur 75123
Tel.: (+62) 541 – 201384

Surabaya

PT. Semesta Jaya Kimia
Ruko MM 41 Blok 41A Jl. Margomulyo No-
mor 41, Asemrowo, Surabaya, Jawa Timur
Tel.: (+62) 31-99343006

PT. RTT Power Indonesia
Jln Rungkut Industri Raya 1 Ruko Section
One Blok B7, Surabaya – Jawa Timur
Tel.: (+62) 31-99851059
Hp.: 0812 5983 1033
Email.: toolsteknik92@gmail.com

Tangerang

PT. TRIT Indonesia
Ruko The Prominence 38E No.41,
Jalan Jalur Sutera Boulevard, East
Panunggangan, Pinang, Tangerang City,
Hp.: 0812 1105 5022
Email.: service@trit.co.id
Web.: www.trit.co.id

Yogyakarta

Qhome Service Center
Jl. Raya Janti Ring Road Timur No. 96
Kanoman, RT. 006 / RW. 020
Banguntapan - Yogyakarta
Hp.: 0822 9929 9297

DEWALT®

GUARANTEED TOUGH.®



+62 855 7467 9105
(bebas pulsa, hanya aktif pada jam kerja)



support@dewalt.co.id



+1 209 409 3173
(Bahasa Indonesia)



<https://id.dewalt.global/>



DEWALT ID



@dewalt_id



DEWALT ID