




TORSION+



INSERTI 1/4" RESISTENTI A COPPIE ELEVATE EXTRA HARD
 1/4" extra-hard bits torques resistant



Applicazioni
 applications



Perfetto rapporto durezza/tenacità, TORSION+ raggiunge elevatissimi valori di resistenza alla torsione.

Perfect hardness/toughness ratio, TORSION+ reaches very high values of torsional stiffness.




Ottima resistenza all'usura: la geometria dell'impronta rimane costante anche dopo moltissimi cicli di avvitatura.

Excellent wear resistance: the geometry of the tip remains constant even after numerous screwing cycles.



Ideali per applicazioni intensive, anche nel settore industriale, dove l'efficienza dell'utensile deve rimanere costante per lungo tempo.

Ideal for heavy-duty applications, even in the industrial sector where tool efficiency must remain constant over a long time.

**61250****PH TORSION+****INSERTI 1/4" C PHILLIPS® - EXTRA DURI, RESISTENTI A COPPIE ELEVATE**
1/4" C PHILLIPS® BITS - EXTRA HARD, RESISTANT TO HIGH TORQUES**60/62 HRC****EASYPACK** | sacchetto PVC con Euro-hole • PVC bags with Euro-hole


	L mm	PCS.	COD.
PH1	25	10	61250005
PH2	25	10	61250010
PH3	25	10	61250015

**SELFPACK**
2 pcs.

	L mm	COD.
PH1	25	61250005002
PH2	25	61250010002
PH3	25	61250015002

**MINIBOX**
10 pcs.

	L mm	COD.
PH1	25	61250005010
PH2	25	61250010010
PH3	25	61250015010

61251**PH TORSION+****LAME 1/4" E PHILLIPS® - EXTRA DURI, RESISTENTI A COPPIE ELEVATE**
1/4" E PHILLIPS® POWER BITS - EXTRA HARD, RESISTANT TO HIGH TORQUES**60/62 HRC****EASYPACK** | sacchetto PVC con Euro-hole • PVC bags with Euro-hole

	L mm	PCS.	COD.
PH1	50	5	61251005
PH2	50	5	61251010
PH3	50	5	61251015

**SELFPACK**
2 pcs.


	L mm	COD.
PH1	50	61251005002
PH2	50	61251010002
PH3	50	61251015002

**MINIBOX**
5 pcs.

	L mm	COD.
PH1	50	61251005005
PH2	50	61251010005
PH3	50	61251015005


61260
PZ TORSION+
INSERTI 1/4" C POZIDRIV® - EXTRA DURI, RESISTENTI A COPPIE ELEVATE
1/4" C POZIDRIV® BITS - EXTRA HARD, RESISTANT TO HIGH TORQUES
60/62 HRC
EASYPACK | sacchetto PVC con Euro-hole • PVC bags with Euro-hole


	L mm	PCS.	COD.
PZ1	25	10	61260005
PZ2	25	10	61260010
PZ3	25	10	61260015



	L mm	COD.
PZ1	25	61260005002
PZ2	25	61260010002
PZ3	25	61260015002


SELPACK
2 pcs.


	L mm	COD.
PZ1	25	61260005010
PZ2	25	61260010010
PZ3	25	61260015010

MINIBOX
10 pcs.

61261
PZ TORSION+
LAME 1/4" E POZIDRIV® - EXTRA DURI, RESISTENTI A COPPIE ELEVATE
1/4" E POZIDRIV® POWER BITS - EXTRA HARD, RESISTANT TO HIGH TORQUES
60/62 HRC
EASYPACK | sacchetto PVC con Euro-hole • PVC bags with Euro-hole


	L mm	PCS.	COD.
PZ1	50	5	61261005
PZ2	50	5	61261010
PZ3	50	5	61261015




	L mm	COD.
PZ1	50	61261005002
PZ2	50	61261010002
PZ3	50	61261015002

SELPACK
2 pcs.


	L mm	COD.
PZ1	50	61261005005
PZ2	50	61261010005
PZ3	50	61261015005

MINIBOX
5 pcs.


**61270****TX TORSION+****INSERTI 1/4" C PER VITI TORX® - EXTRA DURI, RESISTENTI A COPPIE ELEVATE**
1/4" C BITS FOR TORX® SCREWS - EXTRA HARD, RESISTANT TO HIGH TORQUES**60/62 HRC****EASYPACK** | sacchetto PVC con Euro-hole • PVC bags with Euro-hole

	L mm	PCS.	COD.
TX10	25	10	61270005
TX15	25	10	61270010
TX20	25	10	61270015
TX25	25	10	61270020
TX27	25	10	61270025
TX30	25	10	61270030
TX40	25	10	61270035

	L mm	COD.
TX10	25	61270005002
TX15	25	61270010002
TX20	25	61270015002
TX25	25	61270020002
TX27	25	61270025002
TX30	25	61270030002
TX40	25	61270035002

**SELFPACK**
2 pcs.**MINIBOX**
10 pcs.

	L mm	COD.
TX10	25	61270005010
TX15	25	61270010010
TX20	25	61270015010
TX25	25	61270020010
TX27	25	61270025010
TX30	25	61270030010
TX40	25	61270035010

61271**TX TORSION+****LAME 1/4" E PER VITI TORX® - EXTRA DURI, RESISTENTI A COPPIE ELEVATE**
1/4" E POWER BITS FOR TORX® SCREWS - EXTRA HARD, RESISTANT TO HIGH TORQUES**60/62 HRC****EASYPACK** | sacchetto PVC con Euro-hole • PVC bags with Euro-hole

	L mm	PCS.	COD.
TX10	50	5	61271005
TX15	50	5	61271010
TX20	50	5	61271015
TX25	50	5	61271020
TX27	50	5	61271025
TX30	50	5	61271030
TX40	50	5	61271035

	L mm	COD.
TX10	50	61271005002
TX15	50	61271010002
TX20	50	61271015002
TX25	50	61271020002
TX27	50	61271025002
TX30	50	61271030002
TX40	50	61271035002

**SELFPACK**
2 pcs.**MINIBOX**
5 pcs.

	L mm	COD.
TX10	50	61271005005
TX15	50	61271010005
TX20	50	61271015005
TX25	50	61271020005
TX27	50	61271025005
TX30	50	61271030005
TX40	50	61271035005



66002

MYBIT 7 ASSORTIMENTI TORSION+

ASSORTIMENTO 7 PCS. - INSERTI + PORTAINSERTI
7 PCS. SET - BITS + BIT-HOLDER



7
pcs.

COD. **66002350**



PH1 1pc. | PH2 1pc. | PH3 1pc.



PZ1 1pc. | PZ2 1pc. | PZ3 1pc.

COD. **66002355**



TX10 1pc. | TX15 1pc. | TX20 1pc.

TX25 1pc. | TX30 1pc. | TX40 1pc.

COD. **66002360**



PH1 1pc. | PH2 1pc.



PZ1 1pc. | PZ2 1pc.



TX20 1pc. | TX25 1pc.

INCLUSO
INCLUDED
COD. 62013005



100 X 120 mm

66002

DISPLAY MYBIT 7 TORSION+

ESPOSITORE DA BANCO PER 12 BIT-SETS
12 PCS. BIT-SET DISPLAY



12
pcs.

COD. **66002354**



12 pcs.
COD. 66002350

COD. **66002359**



12 pcs.
COD. 66002355

COD. **66002364**



12 pcs.
COD. 66002360

150 X 40 X 195 mm



66007

MYBIT 7 POWER ASSORTIMENTI TORSION+

ASSORTIMENTO 7 PCS. - INSERTI
7 PCS. SET - BITS



7
pcs.

COD. **66007350**

61251 L=50mm		61261 L=50mm		61271 L=50mm		
PH1 1pc.	PH2 1pc.	PZ1 1pc.	PZ2 1pc.	TX25 1pc.	TX30 1pc.	TX40 1pc.

COD. **66007355**

61251 L=50mm			61261 L=50mm		
PH1 1pc.	PH2 2pcs.	PH3 1pc.	PZ1 1pc.	PZ2 1pc.	PZ3 1pc.



100 X 120 mm





66005

MYBIT 10 ASSORTIMENTI TORSION+

ASSORTIMENTO 10 PCS. - INSERTI + PORTAINSERITI
 10 PCS. SET - BITS + BIT-HOLDER



10
pcs.

COD. **66005350**

61250			61260			61270		
PH1	PH2	PH3	PZ1	PZ2	PZ3	TX20	TX25	TX30
1pc.	1pc.	1pc.	1pc.	1pc.	1pc.	1pc.	1pc.	1pc.



100 X 120 mm



INCLUSO
INCLUDED
COD. 62013005



66005

DISPLAY MYBIT 10 TORSION+

ESPOSITORE DA BANCO PER 12 BIT-SETS
 12 PCS. BIT-SET DISPLAY



12
pcs.

COD. **66005354**



12 pcs.
COD. 66005350

150 X 40 X 195 mm



66006

MYBIT 15 ASSORTIMENTI TORSION+

ASSORTIMENTO 15 PCS. - INSERTI + PORTAINSERI
15 PCS. SET - BITS + BIT-HOLDER



15
pcs.

COD. **66006310**

61250			61260		
PH1 1pc.	PH2 1pc.	PH3 1pc.	PZ1 1pc.	PZ2 1pc.	PZ3 1pc.
61270					
TX10 1pc.	TX15 1pc.	TX20 1pc.	TX25 1pc.	TX30 1pc.	TX40 1pc.
61251			61261		
PH2 1pc.			PZ2 1pc.		



100 X 167 mm



INCLUSO
INCLUDED
COD. 62013005



66006

DISPLAY MYBIT 15 TORSION+

ESPOSITORE DA BANCO PER 12 BIT-SETS
12 PCS. BIT-SET DISPLAY



12
pcs.

COD. **66006314**

	12 pcs. COD. 66006310
--	--------------------------

185 X 40 X 195 mm



66006

MYBIT 14 TORSION+ CON CRICCHETTO

ASSORTIMENTO 14 PCS. TORSION+ / CRICCHETTO
14 PCS. SET - BITS + BIT HOLDER AND RATCHET

COD. **66006510**

14
pcs.



100 X 170 mm



61250			61260		
PH1 1pc.	PH2 1pc.	PH3 1pc.	PZ1 1pc.	PZ2 1pc.	PZ3 1pc.

61270					
TX10 1pc.	TX15 1pc.	TX20 1pc.	TX25 1pc.	TX30 1pc.	TX40 1pc.

INCLUSO
INCLUDED

COD. 62013005

COD. 64221030



66010

ASSORTIMENTI TORSION+

ASSORTIMENTO 31 PCS. - INSERTI + PORTAINSERITI
31 PCS. SET - BITS + BIT-HOLDER

COD. **66010035**

31
pcs.



80 X 115 X 30 mm

61250			61260		
PH1 2pcs.	PH2 4pcs.	PH3 3pcs.	PZ1 2pcs.	PZ2 4pcs.	PZ3 3pcs.

61270			
TX20 3pcs.	TX25 3pcs.	TX30 3pcs.	TX40 3pcs.

INCLUSO
INCLUDED
COD. 62013005





66001

STORE 9 ASSORTIMENTI TORSION+

CASSETTIERA CON 9 SCOMPARTI PER ESPOSITORE MULTISTORE
DRAWERS WITH 9 COMPARTMENTS FOR MULTISTORE DISPLAY

COD. **66001065**

165
pcs.



600 X 90 X 65 mm

61250			61260			61270		
PH1	PH2	PH3	PZ1	PZ2	PZ3	TX20	TX25	TX30
10pcs.	30pcs.	20pcs.	10pcs.	30pcs.	20pcs.	15pcs.	15pcs.	15pcs.



MULTI STORE

COD. 66001005VC



66001

MULTI BIT ESPOSITORE INSERTI TORSION+

ESPOSITORE DA BANCO CON 25 SCOMPARTI
DISPLAY WITH 25 COMPARTMENTS

310
pcs.



COD. **66001315**

<p>61250 </p> <p>PH1 10pcs. PH2 30pcs. PH3 10pcs.</p>			<p>61260 </p> <p>PZ1 10pcs. PZ2 20pcs. PZ3 10pcs.</p>		
<p>61270 </p> <p>TX10 10pcs. TX15 10pcs. TX20 20pcs. TX25 20pcs. TX30 20pcs. TX40 10pcs.</p>					
<p>61251 </p> <p>PH1 10pcs. PH2 10pcs. PH3 10pcs.</p>			<p>61261 </p> <p>PZ1 10pcs. PZ2 10pcs. PZ3 10pcs.</p>		
<p>61271 </p> <p>TX10 10pcs. TX15 10pcs. TX20 10pcs. TX25 10pcs. TX30 10pcs. TX40 10pcs.</p>					
<p>62015010 </p> <p> 10pcs.</p>					

445 X 465 X 210 mm

STRUTTURA IN POLIPROPILENE ALVEOLARE AUTOPORTANTE, 25 SCOMPARTI.
SELF-SUPPORTING POLYPROPYLENE HONEYCOMB STRUCTURE, 25 COMPARTMENTS.

**66001****MULTI BOX ESPOSITORE MINIBOX TORSION+****ESPOSITORE DA BANCO PER MINIBOX
DISPLAY STAND FOR MINIBOX****270
pcs.**COD. **66001515**

370 X 545 X 220 mm

STRUTTURA IN FILO METALLICO DA BANCO ED APPENDIBILE ADATTA AD ACCOGLIERE
20 MISURE DIVERSE DI INSERTI CONFEZIONATI IN MINIBOX E DUE ARTICOLI ACCESSORI.
COUNTERTOP OR WALL-MOUNTED METAL WIRE STRUCTURE, SUITABLE FOR HOLDING BITS
IN 20 DIFFERENT SIZES, MINIBOX PACKED AND TWO ACCESSORIES.

			L mm	COD.	box
10 pcs.		PH1	25	61250005010	2
10 pcs.		PH2	25	61250010010	3
10 pcs.		PH3	25	61250015010	2
5 pcs.		PH2	50	61251010005	2
10 pcs.		PZ1	25	61260005010	2
10 pcs.		PZ2	25	61260010010	3
10 pcs.		PZ3	25	61260015010	2
5 pcs.		PZ2	50	61261010005	2
10 pcs.		TX15	25	61270010010	2
10 pcs.		TX20	25	61270015010	2
10 pcs.		TX25	25	61270020010	3
10 pcs.		TX30	25	61270030010	3
1 pc.		MYBIT 7		66002350	2
1 pc.		MYBIT 10		66005350	2
1 pc.				62016005001	3
1 pc.				62012010	3

SCHEDE TECNICHE TECHNICAL DATASHEETS

PHILLIPS®

A REGISTERED TRADEMARK OF PHILLIPS SCREW COMPANY





IN ACCORDO A NORME INTERNAZIONALI
IN ACCORDANCE WITH INTERNATIONAL STANDARDS

COPPIA DI TORSIONE SECONDO NORME
TIGHTENING TORQUE IN ACCORDANCE WITH THE STANDARDS

**DIN 5260
ISO 8764**

**DIN 5261*
ISO 8764***



+	A	Ø	Nm	Nm	Autofilettanti per metallo Self-tapping for metal			Autofilettanti per legno Self-tapping for wood			Metriche Metrics			
					ISO 7049 = DIN 7981	ISO 7050 = DIN 7982	ISO 7051 = DIN 7983	DIN 7996	DIN 7997	DIN 7995	ISO 7045 = DIN 7985	ISO 7046 = DIN 965	ISO 7047 = DIN 966	
PH0	0,84	3	1,0	1,0	2,2	2,2	2,2	2,0	2,0	2,0	2,0	2,0	2,0	2,0
PH1	1,30	4,5	3,5	3,8	2,2 2,9	2,2 2,9	2,2 2,9	2,5 3,0	2,5 3,0	2,5 3,0	2,5 3,0	2,5 3,0	2,5 3,0	2,5 3,0
PH2	2,31	6	8,2	10,3	3,5 4,8	3,5 4,8	3,5 4,8	3,5 5,0	3,5 5,0	3,5 5,0	4,0 5,0	4,0 5,0	4,0 5,0	4,0 5,0
PH3	3,84	8	19,5	32,0	5,5 6,3	5,5 6,3	5,5 6,3	5,5 7,0	5,5 7,0	5,5 7,0	6,0	6,0	6,0	6,0
PH4	5,11	10	38,0	88,7	8,0 9,5	8,0 9,5	8,0 9,5	8,0	8,0	8,0	8,0 10,0	8,0 10,0	8,0 10,0	8,0 10,0

* LE NORME PREVEDONO CHE SOTTO IL VALORE DI COPPIA INDICATA IL PROFILO DELL'UTENSILE NON PRESENTI ALCUNA DEFORMAZIONE

* THE STANDARDS REQUIRE THAT THE TOOL PROFILE DOES NOT DEFORM UNDER THE INDICATED TORQUE VALUES

SCHEDE TECNICHE TECHNICAL DATASHEETS

POZIDRIV®

A REGISTERED TRADEMARK OF PHILLIPS SCREW COMPANY




IN ACCORDO A NORME INTERNAZIONALI
IN ACCORDANCE WITH INTERNATIONAL STANDARDS

COPPIA DI TORSIONE SECONDO NORME
TIGHTENING TORQUE IN ACCORDANCE WITH THE STANDARDS

**DIN 5260
ISO 8764**

**DIN 5261*
ISO 8764***



+	A	Ø	Nm	Nm	Autofilettanti per metallo Self-tapping for metal			Autofilettanti per legno Self-tapping for wood			Metriche Metrics		
					ISO 7049 = DIN 7981	ISO 7050 = DIN 7982	ISO 7051 = DIN 7983	DIN 7996	DIN 7997	DIN 7995	ISO 7045 = DIN 7985	ISO 7046 = DIN 965	ISO 7047 = DIN 966
PZ0	0,45	3	1,0	1,0	2,2	2,2	2,2	2,0	2,0	2,0	2,0	2,0	2,0
PZ1	0,71	4,5	3,5	3,8	2,2 2,9	2,2 2,9	2,2 2,9	2,5 3,0	2,5 3,0	2,5 3,0	2,5 3,0	2,5 3,0	2,5 3,0
PZ2	1,00	6	8,2	10,3	3,5 4,8	3,5 4,8	3,5 4,8	3,5 5,0	3,5 5,0	3,5 5,0	4,0 5,0	4,0 5,0	4,0 5,0
PZ3	1,38	8	19,5	32,0	5,5 6,3	5,5 6,3	5,5 6,3	5,5 7,0	5,5 7,0	5,5 7,0	6,0	6,0	6,0
PZ4	2,10	10	38,0	88,7	8,0 9,5	8,0 9,5	8,0 9,5	8,0	8,0	8,0	8,0 10,0	8,0 10,0	8,0 10,0

* LE NORME PREVEDONO CHE SOTTO IL VALORE DI COPPIA INDICATA IL PROFILO DELL'UTENSILE NON PRESENTI ALCUNA DEFORMAZIONE

* THE STANDARDS REQUIRE THAT THE TOOL PROFILE DOES NOT DEFORM UNDER THE INDICATED TORQUE VALUES

SCHEDE TECNICHE TECHNICAL DATASHEETS

TORX®

A REGISTERED TRADEMARK OF ACCUMENT GLOBAL TECHNOLOGIES




IN ACCORDO A NORME INTERNAZIONALI
IN ACCORDANCE WITH INTERNATIONAL STANDARDS

COPPIA DI TORSIONE SECONDO NORME
TIGHTENING TORQUE IN ACCORDANCE WITH THE STANDARDS

TMD-702

TMD-702*



Torx Profile	A	J	Hand	Torque (Nm)	Torque (Nm)	Autofilettanti per metallo Self-tapping for metal			Autofilettanti per legno Self-tapping for wood			Metriche Metrics					
						ISO 7049 = DIN 7981	ISO 7050 = DIN 7982	ISO 7051 = DIN 7983	DIN 7996	DIN 7997	DIN 7995	ISO 7045 = DIN 7985	ISO 7046 = DIN 965	ISO 7047 = DIN 966	DIN 912 = 7984 = 6912	ISO 4762 = DIN 912	ISO 10642 = DIN 7991
TX03	1,12			0,25								1,2	1,4	1,4	1,2		
TX04	1,30			0,37													
TX05	1,37		0,43	0,51								1,4 1,6	1,8		1,4 1,6		
TX06	1,65		0,75	0,91		2,2	2,2					1,3 2,0	2,0		1,3 2,0		
TX07	1,97		1,4	1,7													
TX08	2,30	0,74	2,2	2,6	2,2	2,9	2,9	2,9				2,5	2,5	2,5		2,5	
TX09	2,48	0,81	2,8	3,4	2,9	2,9											
TX10	2,27	0,94	3,7	4,5	3,8	3,5	3,5	3,5	3,0	3,0		3,0	3,0	3,0	3,0	3,0	3,0
TX15	3,26	1,19	6,4	7,7	6,5	3,9	3,9	3,9	3,5	3,5		3,5	3,5	3,5	3,5		
TX20	3,84	1,57	10,5	12,7	10,8	4,2	4,2	4,2	4,0 4,5	4,0 4,5	4,5	4,0	4,0	4,0	4,0	4,0	4,0
TX25	4,40	1,96	15,9	19,0	16,1	4,8 5,5	4,8 5,5	4,8 5,5	4,5 6,0	4,5 5,0	4,5	5,0	5,0	5,0	4,0 5,0	5,0	5,0
TX27	4,96	2,21	22,5	26,9	22,9										4,3 5,0		
TX30	5,49	2,72	31,1	37,4	31,8	6,3	6,3	6,3	6,0	6,0		6,0	6,0	6,0	6,0	6,0	6,0
TX40	6,60	3,15	54,1	65,1	55,3	8,0				8,0 10,0		8,0	8,0	8,0	8,0		8,0
TX45	7,77	3,40	86,0	104,0	88,0											8,0	
TX50	8,79	3,73	132,0	159,0	135,0	10,0						10,0	10,0	10,0	10,0	10,0	10,0
TX55	11,17	4,75		257,0	218,0	12,0									12,0	12,0	
TX60	13,20	5,56		445,0	379,0										14,0	14,0	
TX70	15,49	6,73		701,0	596,0												

* PER QUESTO PROFILO I VALORI DI COPPIA INDICATI CORRISPONDONO AL VALORE MINIMO DI ROTTURA
* THE TORQUE VALUES INDICATED FOR THIS PROFILE CORRESPOND TO THE MINIMUM BREAKING VALUE

SCHEDE TECNICHE TECHNICAL DATASHEETS

TORX-PLUS®

TORX-PLUS® TAMPER RESISTANT

A REGISTERED TRADEMARK OF ACCUMENT GLOBAL TECHNOLOGIES




IN ACCORDO A NORME INTERNAZIONALI
IN ACCORDANCE WITH INTERNATIONAL STANDARDS

COPPIA DI TORSIONE SECONDO NORME
TIGHTENING TORQUE IN ACCORDANCE WITH THE STANDARDS

NMD-702
NMD-602

NMD-702*
NMD-602*



** DIAMETRO CIRCOSCRITTO · ** CIRCUMSCRIBED DIAMETER ·

		Autofilettanti per metallo Self-tapping for metal			Metriche Metrics												
	A		Nm		A	J		Nm	ISO 7049 = DIN 7981	ISO 7050 = DIN 7982	ISO 7051 = DIN 7983	ISO 7045 = DIN 7985	ISO 7046 = DIN 965	ISO 7047 = DIN 966	DIN 912 = 7984 = 6912	ISO 4762 = DIN 912	ISO 10642 = DIN 7991
10IP	2,72	5,42		10IPR	2,72	0,91	4,3		3,5	3,5	2,9 3,5	3,0	3,0	3,0	3,0	3,0	5,0
15IP	3,25	9,62		15IPR	3,25	1,17	7,3		3,9	3,9	3,5 3,9	3,5	3,5 4,0	3,5			6,0
20IP	3,84	16,15		20IPR	3,84	1,55	11,9		4,2	4,2	4,2	4,0	4,0 5,0	4,0	4,0	4,0	6,0
25IP	4,39	23,50		25IPR	4,39	1,93	17,4		4,8 5,5	4,8 5,5	4,8 5,5	5,0	5,0 6,0	5,0	5,0	5,0	7,0 8,0
27IP	4,95	34,62		27IPR	4,95	2,18	25,1										8,0
30IP	5,49	47,18		30IPR	5,49	2,57	33,5		6,3	6,3	6,3	6,0	6,0	6,0	8,0	6,0	
40IP	6,60	82,08		40IPR	6,60	2,92	59,4				8,0		8,0	8,0	8,0	8,0	10,0

* PER QUESTO PROFILO I VALORI DI COPPIA INDICATI CORRISPONDONO AL VALORE MINIMO DI ROTTURA

* THE TORQUE VALUES INDICATED FOR THIS PROFILE CORRESPOND TO THE MINIMUM BREAKING VALUE

SCHEDE TECNICHE TECHNICAL DATASHEETS

ESAGONO




IN ACCORDO A NORME INTERNAZIONALI
IN ACCORDANCE WITH INTERNATIONAL STANDARDS

COPPIA DI TORSIONE SECONDO NORME
TIGHTENING TORQUE IN ACCORDANCE WITH THE STANDARDS

DIN 911
DIN 7426

DIN 7426*
ISO 2936*



Metrie
Metrics

⊙	A	B _{MIN}	✋ Nm	🔧 Nm	Metrie Metrics				
					DIN 7984	ISO 4762 = DIN 7984	ISO 10642 = DIN 7991	DIN 908	DIN 913 914 DIN 915 916
0,7	0,7	1,6	0,08						1,4 1,8
0,9	0,9	1,8	0,18						2,0
1,3	1,3	2,0	0,53			1,4			2,5
1,5	1,5	2,3	0,82	0,95		1,6 2,0			3,0
2,0	2,0	3,0	1,9	2,3	3,0	2,5	3,0		4,0
2,5	2,5	3,8	3,4	4,4	4,0	3,0	4,0		5,0
3,0	3,0	4,5	6,6	7,6	5,0	4,0	5,0		6,0
4,0	4,0	6,0	16,0	18,0	6,0	5,0	6,0		8,0
5,0	5,0	7,5	30,0	35,0	8,0	6,0	8,0	10,0	10,0
6,0	6,0	9,0	52,0	61,0		8,0	10,0	12,0 14,0	12,0 14,0
7,0	7,0	10,5	78,0	97,0	10,0				
8,0	8,0	12,0	120,0	140,0	12,0	10,0	12,0	16,0 18,0	16,0 18,0
10,0	10,0	16,0	220,0	280,0	14,0	12,0	14,0 16,0	20,0 22,0	20,0 22,0
12,0	12,0	18,0	370,0	480,0	16,0 18,0	14,0	18,0 20,0	24,0 26,0	24,0 26,0
14,0	14,0	25,0	590,0		20,0 22,0	16,0 18,0	22,0 24,0		

* LE NORME PREVEDONO CHE SOTTO IL VALORE DI COPPIA INDICATA IL PROFILO DELL'UTENSILE NON PRESENTI ALCUNA DEFORMAZIONE

* THE STANDARDS REQUIRE THAT THE TOOL PROFILE DOES NOT DEFORM UNDER THE INDICATED TORQUE VALUES

SCHEDE TECNICHE TECHNICAL DATASHEETS

TAGLIO




IN ACCORDO A NORME INTERNAZIONALI
IN ACCORDANCE WITH INTERNATIONAL STANDARDS

COPPIA DI TORSIONE SECONDO NORME
TIGHTENING TORQUE IN ACCORDANCE WITH THE STANDARDS

DIN-ISO 2380

DIN-ISO 2380*



Ø	A	T	Nm	Nm	Autofilettanti per metallo Self-tapping for metal			Autofilettanti per legno Self-tapping for wood			Metriche Metrics							
					ISO 1481 = DIN 7971	ISO 1482 = DIN 7972	ISO 1483 = DIN 7973	DIN 96	DIN 97	DIN 95	ISO 1207 = DIN 84	ISO 1580 = DIN 85	ISO 2009 = DIN 963	ISO 2010 = DIN 964	ISO 4766 7435 = DIN 417-427			
1,5	0,30	0,50		0,15														
1,8	0,37	0,50		0,28								1,2 1,4						
2,0	0,40	0,70	0,3	0,35				1,6	1,6					1,6			2,5 3,0	
2,5	0,40	0,70	0,4	0,45				2,0		1,6		1,6 1,8			1,6		3,5	
3,0	0,50	0,90	0,7	0,8		2,2	2,2		2,0	2,0	2,0	2,0		2,0	2,0		4,0	
3,5	0,60	1,10	1,3	1,4	2,2			2,5	2,5	2,5	2,5			2,5	2,5			
4,0	0,50	0,90		1,1				2,0										
4,0	0,80	1,40	2,6	2,9	2,9	2,9	2,9	3,0 3,5	3,0 3,5	3,0 3,5	3,0	3,0	3,0 3,5	3,0 3,5	3,0 3,5		5,0 6,0	
4,5	0,60	1,10		1,8	2,2			2,5				2,5						
5,0	0,80	1,40	3,2	3,6														
5,5	0,80	1,40	3,5	3,9				3,5		3,5	3,0	3,5	3,5	3,5	3,5			
5,5	1,00	1,80	5,5	6,2	3,5 3,9	3,5 3,9	3,5 3,9	4,0 4,5	4,0 4,5	4,0 4,5	3,5	3,5	4,0	4,0				
6,0	1,00	1,80		6,7														
6,5	1,20	2,20	9,4	10,5		4,2 4,8	4,2	5,0 5,5	5,0	5,0	4,0		5,0	5,0		8,0		
7,0	1,20	2,20	10,0	11,3														
8,0	1,20	2,20	11,5	12,9	4,2		4,8		5,5	5,5	5,0	4,0						
8,0	1,60	2,90	20,5	22,9	4,8	5,5 6,3	5,5	6,0	6,0	6,0		5,0	6,0	6,0		10,0 12,0		
10,0	1,60	2,90	25,6	28,7	5,5 6,3		6,3		7,0 8,0	7,0	6,0					14,0		
13,0	2,00	3,60	52,0	58,0				8,0	10,0		8,0	8,0	8,0	8,0		16,0		

* LE NORME PREVEDONO CHE SOTTO IL VALORE DI COPPIA INDICATA IL PROFILO DELL'UTENSILE NON PRESENTI ALCUNA DEFORMAZIONE

* THE STANDARDS REQUIRE THAT THE TOOL PROFILE DOES NOT DEFORM UNDER THE INDICATED TORQUE VALUES


SCHEDE TECNICHE TECHNICAL DATASHEETS

TORX®

A REGISTERED TRADEMARK OF ACCUMENT GLOBAL TECHNOLOGIES



IN ACCORDO A SPECIFICA ACCUMENT GLOBAL TECHNOLOGIES
IN ACCORDANCE WITH THE SPECIFICATIONS OF ACCUMENT GLOBAL TECHNOLOGIES



Metriche
Metrics



	A	Metriche Metrics	
		ISO 4014 - 4017 = DIN 931 - 933	ISO 8100 = DIN 6921
	A		
E5	4,72	4,0	
E6	5,69	5,0	4,0
E7	6,17		
E8	7,47	6,0 7,0	5,0
E10	9,37	8,0	6,0
E11	10,03		
E12	11,12	10,0 11,0	8,0
E14	12,85	12,0	10,0
E16	14,71		
E18	16,64	14,0	12,0
E20	18,41	16,0	14,0
E22	20,24		
E24	22,09	18,0 20,0	

SCHEDE TECNICHE TECHNICAL DATASHEETS

ESAGONO




IN ACCORDO A NORME INTERNAZIONALI
IN ACCORDANCE WITH INTERNATIONAL STANDARDS

COPPIA DI TORSIONE SECONDO NORME
TIGHTENING TORQUE IN ACCORDANCE WITH THE STANDARDS

DIN 3129

DIN-ISO 1711*



			Autofilettanti per metallo <i>Self-tapping for metal</i>	Autofilettanti per legno <i>Self-tapping for wood</i>	Metriche <i>Metrics</i>		
	 Nm	 Nm	ISO 1479 = DIN 7976	DIN 571	ISO 4014 4016 4017	ISO 4035 4036 = DIN 439	ISO 4032 4033 = DIN 934
4		10,4			2,0	2,0	2,0
4,5		12,6			2,3		
5	11,5	15,1	2,9		2,5	2,5	2,5
5,5	14,4	17,8	3,5		3,0	3,0	3,0
6	17,6	23,2			3,5	3,5	3,5
7	25,2	33,2	3,9 4,2	4,0	4,0	4,0	4,0
8*	34,5	94,1	4,8 5,5	5,0	5,0	5,0	5,0
9*	45,4	119,2					
10*	58,1	147,0	6,3	6,0	6,0	6,0	6,0
11*	72,7	178,0			7,0		7,0
12*	89,1	212,0		7,0			
13*	107,0	249,0	8,0	8,0	8,0	8,0	8,0
14*	128,0	288,0					

* VALUTARE ANCHE RESISTENZA ATTACCO


* ALSO EVALUATE ATTACHMENT RESISTANCE

SCHEDE TECNICHE

TECHNICAL DATASHEETS

ATTACCHI MASCHIO STANDARD, APPLICAZIONI, RESISTENZE

STANDARD MALE ATTACHMENTS, APPLICATIONS, RESISTANCES


	 A  B		APPLICAZIONE APPLICATION	STANDARDS	Nm
	A=3mm			DIN 3126 Form A3	7,6
	A=4mm - 5/32"			DIN 3126 Form C4	18,0
	A=5,5mm			DIN 3126 Form A5,5	47,0
	B=VARIE			LTI	N.A.
	B=7mm			LTI	N.A.
	A=6,35mm - 1/4"			DIN 3126 Form C6,3	71,0
	A=6,35mm - 1/4"			DIN 3126 Form E6,3	71,0
	A=7,93mm - 5/16"			DIN 3126 Form C8	144,0
	A=7,93mm - 5/16"			FIAM-DESOUTTER	144,0
	A=9,52mm - 3/8"			AUTOMOTIVE	280,0
	A=11,2mm - 7/16"			DIN 3126 Form E11,2	396,0
	B=M4x0,7			ISO 724 - DIN 13.1	7,0
	B=M5x0,8			ISO 724 - DIN 13.1	18,0
	B=M6x1			ISO 724 - DIN 13.1	25,0
	B=10x32 UNF			ISO 724 - DIN 13.1	18,0
	B=BSF 3/16x32 Whitworth			ISO 724 - DIN 13.1	18,0

SCHEDE TECNICHE TECHNICAL DATASHEETS

ATTACCHI QUADRO STANDARD, APPLICAZIONI, RESISTENZE

STANDARD SQUARE ATTACHMENTS, APPLICATIONS, RESISTANCES

			APPLICAZIONE APPLICATION	STANDARDS	Nm
	A=6,35mm - 1/4"			DIN 3121 Form G6,3	68,6
	A=9,52mm - 3/8"			DIN 3121 Form G10	225,0
	A=12,70mm - 1/2"			DIN 3121 Form G12,5	569,0
	A=19,05mm - 3/4"			DIN 3121 Form H20	1569,0
	A=25,40mm - 1"			DIN 3121 Form H25	2795,0
	A=38,10mm - 1-1/2"			DIN 3121 Form H40	

			APPLICAZIONE APPLICATION	STANDARDS	Nm
	A=6,35mm - 1/4"			DIN 3121 Form G6,3	62,0
	A=9,52mm - 3/8"			DIN 3121 Form G10	202,0
	A=12,70mm - 1/2"			DIN 3121 Form G12,5	512,0
	A=19,05mm - 3/4"			DIN 3121 Form D20	1412,0