NEC NEC LCD Technologies, Ltd.

TFT COLOR LCD MODULE

NL8060BC26-30C

26cm (10.4 Type) SVGA LVDS Interface (1port)



This DATA SHEET is updated document from DOD-PP-0642 (1).

All information is subject to change without notice. Please confirm the sales representative before starting to design your system.

INTRODUCTION

The Copyright to this document belongs to NEC LCD Technologies, Ltd. (hereinafter called "NEC"). No part of this document will be used, reproduced or copied without prior written consent of NEC.

NEC does and will not assume any liability for infringement of patents, copyrights or other intellectual property rights of any third party arising out of or in connection with application of the products described herein except for that directly attributable to mechanisms and workmanship thereof. No license, express or implied, is granted under any patent, copyright or other intellectual property right of NEC.

Some electronic parts/components would fail or malfunction at a certain rate. In spite of every effort to enhance reliability of products by NEC, the possibility of failures and malfunction might not be avoided entirely. To prevent the risks of damage to death, human bodily injury or other property arising out thereof or in connection therewith, each customer is required to take sufficient measures in its safety designs and plans including, but not limited to, redundant system, fire-containment and anti-failure.

The products are classified into three quality grades: "**Standard**", "**Special**", and "**Specific**" of the highest grade of a quality assurance program at the choice of a customer. Each quality grade is designed for applications described below. Any customer who intends to use a product for application other than that of Standard quality grade is required to contact an NEC sales representative in advance.

The **Standard** quality grade applies to the products developed, designed and manufactured in accordance with the NEC standard quality assurance program, which are designed for such application as any failure or malfunction of the products (sets) or parts/components incorporated therein a customer uses are, directly or indirectly, free of any damage to death, human bodily injury or other property, like general electronic devices.

Examples: Computers, office automation equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment, industrial robots, etc.

The **Special** quality grade applies to the products developed, designed and manufactured in accordance with an NEC quality assurance program stricter than the standard one, which are designed for such application as any failure or malfunction of the products (sets) or parts/components incorporated therein a customer uses might directly cause any damage to death, human bodily injury or other property, or such application under more severe condition than that defined in the Standard quality grade without such direct damage.

Examples: Control systems for transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, medical equipment not specifically designed for life support, safety equipment, etc.

The **Specific** quality grade applies to the products developed, designed and manufactured in accordance with the standards or quality assurance program designated by a customer who requires an extremely higher level of reliability and quality for such products.

Examples: Military systems, aircraft control equipment, aerospace equipment, nuclear reactor control systems, medical equipment/devices/systems for life support, etc.

The quality grade of this product is the "Standard" unless otherwise specified in this document.

CONTENTS

INTRODUCTION	2
1. OUTLINE	
1.1 STRUCTURE AND PRINCIPLE	
1.2 APPLICATIONS	
1.3 FEATURES	
2. GENERAL SPECIFICATIONS	
3. BLOCK DIAGRAM	
4. DETAILED SPECIFICATIONS	
4.1 MECHANICAL SPECIFICATIONS	
4.2 ABSOLUTE MAXIMUM RATINGS	
4.3 ELECTRICAL CHARACTERISTICS	
4.3.2 Backlight lamp4.3.3 Power supply voltage ripple	
4.3.4 Fuse	
4.4 POWER SUPPLY VOLTAGE SEQUENCE	
4.4.1 LCD panel signal processing board	
4.4.1 LCD panel signal processing board	
4.5 CONNECTIONS AND FUNCTIONS FOR INTERFACE PINS	12
4.5.1 LCD panel signal processing board	
4.5.1 BCD panel signal processing board	
4.5.2 Dacklight famp. 4.5.3 Position of plug and socket	
4.5.4 Connection between receiver and transmitter for LVDS	14
4.5.5 Input data mapping	
4.6 DISPLAY COLORS AND INPUT DATA SIGNALS	
4.6.1 Combinations between input data signals, FRC signal and MSL signal	
4.6.2 16,777,216 colors	19
4.6.3 262,144 colors	
4.7 DISPLAY POSITIONS	
4.8 SCANNING DIRECTIONS	
4.9 INPUT SIGNAL TIMINGS	
4.9.1 Outline of input signal timings	
4.9.2 Timing characteristics	
4.9.3 Input signal timing chart	
4.10 OPTICS	
4.10.1 Optical characteristics	25
4.10.2 Definition of contrast ratio	26
4.10.3 Definition of luminance uniformity	26
4.10.4 Definition of response times	
4.10.5 Definition of viewing angles	
5. ESTIMATED LUMINANCE LIFETIME	
6. RELIABILITY TESTS	28
7. PRECAUTIONS	
7.1 MEANING OF CAUTION SIGNS	29
7.2 CAUTIONS	29
7.3 ATTENTIONS	
7.3.1 Handling of the product	
7.3.2 Environment	
7.3.3 Characteristics	
7.3.4 Other	
8. OUTLINE DRAWINGS	
8.1 FRONT VIEW	
8.2 REAR VIEW	33

1. OUTLINE

1.1 STRUCTURE AND PRINCIPLE

Color LCD module NL8060BC26-30C is composed of the amorphous silicon thin film transistor liquid crystal display (a-Si TFT LCD) panel structure with driver LSIs for driving the TFT (Thin Film Transistor) array and a backlight.

The a-Si TFT LCD panel structure is injected liquid crystal material into a narrow gap between the TFT array glass substrate and a color-filter glass substrate.

Color (Red, Green, Blue) data signals from a host system (e.g. signal generator, etc.) are modulated into best form for active matrix system by a signal processing circuit, and sent to the driver LSIs which drive the individual TFT arrays.

The TFT array as an electro-optical switch regulates the amount of transmitted light from the backlight assembly, when it is controlled by data signals. Color images are created by regulating the amount of transmitted light through the TFT array of red, green and blue dots.

1.2 APPLICATIONS

• For industrial use


1.3 FEATURES

- Adoption of ST-NLT (Super-Transmissive Natural Light TFT)
- High luminance
- High contrast
- Wide viewing angle
- Wide temperature range
- Low reflection
- LVDS interface
- Reversible-scan direction
- Selectable 8bit or 6bit digital signals for data of RGB
- Edge light type (without inverter)
- Replaceable lamp for backlight
- Acquisition product for UL60950-1/CSA C22.2 No.60950-1-03 (File number: E170632)
- Compliance with the European RoHS directive (2002/95/EC)

2. GENERAL SPECIFICATIONS

Display area	211.2 (H) × 158.4 (V) mm
Diagonal size of display	26cm (10.4 inches)
Drive system	a-Si TFT active matrix
Display color	16,777,216 colors (At 8-bit input, FRC terminal= High) 262,144 colors (At 6-bit input, FRC terminal= Low or Open)
Pixel	800 (H) × 600 (V)pixels
Pixel arrangement	RGB (Red dot, Green dot, Blue dot) vertical stripe
Dot pitch	$0.088 (H) \times 0.264 (V) mm$
Pixel pitch	$0.264 (H) \times 0.264 (V) mm$
Module size	243.0 (W) × 185.1 (H) × 10.5 (D) mm (typ.)
Weight	485g (typ.)
Contrast ratio	900: 1 (typ.)
Viewing angle	 At the contrast ratio ≥ 10:1 Horizontal: Right side 80° (typ.), Left side 80° (typ.) Vertical: Up side 80° (typ.), Down side 80° (typ.)
Designed viewing direction	 At DPS terminal= Low or Open: Normal scan Viewing direction without image reversal: up side (12 o'clock) Viewing direction with contrast peak: down side (6 o'clock) Viewing angle with optimum grayscale (γ≒ 2.2): normal axis (perpendicular)
Polarizer surface	Clear + Antireflection (AR)
Polarizer pencil-hardness	2H (min.) [by JIS K5400]
Color gamut	At LCD panel center 40% (typ.) [against NTSC color space]
Response time	$\begin{array}{c} Ton+Toff (10\% \longleftrightarrow 90\%) \\ 18ms (typ.) \end{array}$
Luminance	At IBL=5.0mArms / lamp 550cd/m ² (typ.)
Signal system	LVDS 1port (Receiver: Equivalent of THC63LVDF84B, THine Electronics Inc.) [8-bit digital signals for data of RGB colors, Dot clock (CLK), Data enable (DE)]
Signal system Power supply voltage	(Receiver: Equivalent of THC63LVDF84B, THine Electronics Inc.) [8-bit digital signals for data of RGB colors, Dot clock (CLK),
	(Receiver: Equivalent of THC63LVDF84B, THine Electronics Inc.) [8-bit digital signals for data of RGB colors, Dot clock (CLK), Data enable (DE)]

3. BLOCK DIAGRAM



4. DETAILED SPECIFICATIONS

4.1 MECHANICAL SPECIFICATIONS

Parameter	Specification		Unit
Module size	243.0 \pm 0.5 (W) \times 185.1 \pm 0.5 (H) \times 10.5 \pm 0.5 (D)	Note1	mm
Display area	211.2 (H) × 158.4 (V)	Note1	mm
Weight	485 (typ.), 510 (max.)		g

Note1: See "8. OUTLINE DRAWINGS".

4.2 ABSOLUTE MAXIMUM RATINGS

	Paramet	Symbol	Rating	Unit	Remarks	
Power supply	LCD panel signal processing board		VCC	-0.3 to +4.0	V	
voltage	L	amp voltage	VBLH	2,000	Vrms	
Input voltage	D	isplay signals Note1	VD	-0.3 to VCC+0.3	V	-
for signals	Fu	nction signals Note2	VF	-0.3 to VCC+0.3	v	
	Incident light	II	150,000	lx	Note3	
	Storage temperature			-30 to +80	°C	-
Operating t		Front surface	TopF	-20 to +70	°C	Note4
Operating t	emperature	Rear surface	TopR	-20 to +70	°C	Note5
				≤ 95	%	$Ta \le 40^{\circ}C$
	Relative hu	midity	RH	≤ 85	%	$40 < Ta \le 50^{\circ}C$
	Note6			≤ 55	%	$50 < Ta \le 60^{\circ}C$
				≤ 36	%	$60 < Ta \le 70^{\circ}C$
	Absolute hu Note6	АН	≤ 70 Note7	g/m ³	Ta > 70°C	

Note1: D0+/-, D1+/-, D2+/-, D3+/-, CLK+/-

Note2: DPS, FRC, MSL

- Note3: If the product surface (polarizer) is exposed to an ultraviolet ray, the polarizer may discolor (Surface treatment may be damaged.). Use a filter to protect the polarizer from the ultraviolet ray.
- Note4: Measured at center of LCD panel surface (including self-heat)
- Note5: Measured at center of LCD module's rear shield surface (including self-heat)
- Note6: No condensation
- Note7: Water amount at $Ta = 70^{\circ}C$ and RH = 36%

4.3 ELECTRICAL CHARACTERISTICS

4.3.1 LCD panel signal processing board

		, our a					(Ta= 25°C)
Parameter		Symbol	min.	typ.	max.	Unit	Remarks
Power supply voltage		VCC	3.0	3.3	3.6	V	-
Power supply current		ICC	-	400 Note1	660 Note2	mA	at VCC= 3.3V
Permissible ripple voltag	ge	VRP	-	-	100	mVp-p	for VCC
Differential input threshold	High	VTH	-	-	+100	mV	at VCM= 1.2V
voltage	Low	VTL	-100	-	-	mV	Note3
Terminating resistance		RT	-	100	-	Ω	-
Input voltage for DPS, FRC	High	VFH	0.7VCC	-	VCC	V	CMOS level
and MSL signals	Low	VFL	0	-	0.3VCC	V	CIVIOS level
Input current for FRC and	High	IFH	-	-	300	μΑ	
MSL signals	Low	IFL	-300	-	-	μΑ	-

Note1: Checkered flag pattern [by EIAJ ED-2522]

Note2: Pattern for maximum current


Note3: Common mode voltage for LVDS receiver

4.3.2 Backlight lamp

						(Ta=25°C, Note1)
Parameter	Symbol	min.	typ.	max.	Unit	Remarks
Lamp current Note3, Note4	IBL	2.0	5.0	5.5	mArms	at IBL= 5.0mArms: L= 550cd/m ² (typ.)
Lamp voltage Note2, Note3	VBLH	-	520	-	Vrms	-
Lamp starting voltage	VS	850	-	-	Vrms	Ta= 25°C
Note2, Note3, Note5, Note8	vS	1,150	-	-	Vrms	Ta= -20°C
Lamp oscillation frequency Note6	FO	50	-	72	kHz	-

Note1: This product consists of 2 backlight lamps, and these specifications are for each lamp.

- Note2: The lamp voltage cycle between lamps should be kept on a same phase. "VS" and "VBLH" are the voltage value between low voltage side (Cold) and high voltage side (Hot).
- Note3: The asymmetric ratio of working waveform for lamps (Lamp voltage peak ratio, Lamp current peak ratio and waveform space ratio) should be less than 5 % (See the following figure.). If the waveform is asymmetric, DC (Direct current) element apply into the lamp. In this case, a lamp lifetime may be shortened, because a distribution of a lamp enclosure substance inclines toward one side between low voltage terminal (Cold terminal) and high voltage terminal (Hot terminal). When designing the inverter, evaluate asymmetric of lamp working waveform sufficiently.



Pa: Supply voltage/current peak for positive, Pb: Supply voltage/current peak for negative Sa: Waveform space for positive part, Sb: Waveform space for negative part

- Note4: This product consists of 2 lamps. 2 lamps are contained in the 1 lamp holder, and both lamps are connected to 1 low voltage cable. Recommended lamp current is 5.0mArms typical for each lamp, and sum of 2 lamps is 10mArms typical. The lamp current should be measured by high-frequency current meter at the low voltage terminal.
- Note5: The inverter should be designed so that the lamp starting voltage can be maintained for more than 1 second. Otherwise the lamp may not be turned on.
- Note6: In case "FO" is not the recommended value, beat noise may display on the screen, because of interference between "FO" and "1/th". Recommended value of "FO" is as following.


$$FO = \frac{1}{4} \times \frac{1}{th} \times (2n-1)$$

- th: Horizontal signal period (See "**4.9.2 Timing characteristics**".) n: Natural number (1, 2, 3)
- Note7: Method of lamp cable installation may invite fluctuation of lamp current and voltage or asymmetric of lamp working waveform. When designing method of lamp cable installation, evaluate the fluctuation of lamp current, voltage and working waveform sufficiently.

NEC NEC LCD Technologies, Ltd.

Note8: In case of Inverter with Ballast condenser, "VS" is the voltage level between Ballast condenser and Connector (Refer to the below "Example of measurement"). "VS" should be designed to be more than minimum "VS". Otherwise the lamp may not be turned on because the lamp starting voltage is less than minimum "VS".

Example of measurement Probe capacity: 3pF (Tektronix, inc.: P6015A)



4.3.3 Power supply voltage ripple

This product works, even if the ripple voltage levels are beyond the permissible values as following the table, but there might be noise on the display image.

Power sup	ply voltage	Ripple voltage Note1 (Measure at input terminal of power supply)	Unit
VCC	3.3V	≤ 100	mVp-p

Note1: The permissible ripple voltage includes spike noise.


4.3.4	Fuse
-------	------

Parameter	Fı	ise	Rating	Fusing current	Remarks	
Farameter	Туре	Supplier	Kaung	Fushig current	Kemarks	
VCC	FCC16162AB	KAMAYA	1.6A	3.2A	Note1	
vee	VCC FCC16162AB ELECTRIC Co., Ltd.		32V	3.2A	Note1	

Note1: The power supply capacity should be more than the fusing current. If it is less than the fusing current, the fuse may not blow in a short time, and then nasty smell, smoke and so on may occur.

4.4 POWER SUPPLY VOLTAGE SEQUENCE


4.4.1 LCD panel signal processing board



- * These signals should be measured at the terminal of 100Ω resistance.
- Note1: In terms of voltage variation (voltage drop) while VCC rising edge is below 3.0V, a protection circuit may work, and then this product may not work.
- Note2: Display signals (D0+/-, D1+/-, D2+/-, D3+/-, CLK+/-) and function signals (DPS, FRC, MSL) must be Low or High impedance, exclude the VALID period (See above sequence diagram), in order to avoid that internal circuit is damaged.
 If some of display and function signals of this product are cut while this product is working, even if the signal input to it once again, it might not work normally. VCC should be cut

when the display and function signals are stopped.

4.4.2 Inverter (Option)



- Note1: These are the display and function signals for LCD panel signal processing board.
- Note2: The backlight should be turned on within the valid period of display and function signals, in order to avoid unstable data display.

4.5 CONNECTIONS AND FUNCTIONS FOR INTERFACE PINS

4.5.1 LCD panel signal processing board

CN1 socket (LCD module side):	FI-SE20P-HFE (Japan Aviation Electronics Industry Limited (JAE))
Adaptable plug:	FI-S20S (Japan Aviation Electronics Industry Limited (JAE))

	apta	ble plug.	11	-5205 (Japan Avianc			
Pin No. Symbol		Symbol	Signal	Input data	Input data	Remarks	
		5,11001	Signar	MAP A	MAP B	signal: 6bit	
1	А	D3+	Pixel data	R0-R1,G0-G1,B0-B1	R6-R7,G6-G7,B6-B7	-	Note1, Note2
Ī	В	GND	Ground		Ground		
2	А	D3-	D3- Pixel data R0-R1,G0-G1,B0-B1 R6-R7,G6-G7,B6-B7 -			-	Note1, Note2
Ī	В	GND	Ground		Ground		
3	3	DPS	Selection of scan direction	e	Reverse scan Normal scan		Note4
4	Ļ	FRC	Selection of the number of colors	Hi	gh	Low or Open	Note1 Note5
5	5	GND	Ground		Ground		Note3
6	5	CLK+	Pixel clock				
7	7	CLK-	Pixel clock	Pixel clock		Note2	
8	3	GND	Ground	Ground			Note3
9)	D2+	Pixel data			Note2	
10	0	D2-	I IXEI Uata	D4-D7,DE	B4-B7,DE B2-B5,DE		Note2
1	1	GND	Ground		Ground		Note3
12	2	D1+	Pixel data	G3-G7,B2-B3	G1-G5,B0	-B1	Note2
1.	3	D1-	T IXCI data	05-07,02-05	01-05,00	-01	Note2
14	4	GND	Ground		Ground		Note3
1:	5	D0+	Pixel data	R2-R7.G2	PO-P5 0		Note2
1	6	D0-		N2-N7,02	G2 R0-R5,G0		110162
1′	7	GND	Ground	Ground			Note3
1	8	MSL	Selection of LVDS input map	Low	High	Low	Note5
19	9	VCC	Power supply	Denne engels			Note3
20	0	VCC	r ower suppry	Power supply			

Note1: See "4.6 DISPLAY COLORS AND INPUT DATA SIGNALS".

Note2: Twist pair wires with 100Ω (Characteristic impedance) should be used between LCD panel signal processing board and LVDS transmitter.

Note3: All GND and VCC terminals should be used without any non-connected lines.

Note4: See "4.8 SCANNING DIRECTIONS".


Note5: See "4.5.4 Connection between receiver and transmitter for LVDS".

4.5.2 Backlight lamp

Attention: VBLH and VBLC must be connected correctly. Wrong connections will cause electric shock and also break down of the product.

CN2 plug (Adaptable s	LCD module side): socket:	BHR-04VS-1 (J.S.T Mfg. Co., Ltd.) SM03 (7-D1) B-BHS-1-TB(LF)(SN), SM03 (7-D1) B-BHS-1-TB	(J.S.T Mfg. Co., Ltd.)
Pin No.	Symbol	Signal	Remarks
1	VBLH	High voltage terminal (Hot)	Cable color: Sky blue
2	VBLH	High voltage terminal (Hot)	Cable color: Sky blue
3	N.C.	-	Keep this pin Open.
4	VBLC	Low voltage terminal (Cold)	Cable color: Black


4.5.3 Position of plug and socket



Rear side

Insert direction-

NEC NEC LCD Technologies, Ltd.





4.5.4 Connection between receiver and transmitter for LVDS

- Note2: LSB (Least Significant Bit) R0, G0, B0 MSB (Most Significant Bit) R7, G7, B7
- Note3: Twist pair wires with 100Ω (Characteristic impedance) should be used between LCD panel signal processing board and LVDS transmitter.
- Note4: Input signals to TC4, TC5 and TD6 are not used inside the product, but do not keep TC4, TC5 and TD6 open to avoid noise problem.

NL8060BC26-30C

NEC NEC LCD Technologies, Ltd.






- Note1: Recommended transmitter: THC63LVDM83R (THine Electronics Inc.) or equivalent
- Note2: LSB (Least Significant Bit) R0, G0, B0 MSB (Most Significant Bit) R7, G7, B7
- Note3: Twist pair wires with 100Ω (Characteristic impedance) should be used between LCD panel signal processing board and LVDS transmitter.
- Note4: Input signals to TC4, TC5 and TD6 are not used inside the product, but do not keep TC4, TC5 and TD6 open to avoid noise problem.


NL8060BC26-30C

(3) Input data signal: 6bit




- Note1: Recommended transmitter THC63LVDM83R (THine Electronics Inc.) or equivalent
- Note2: LSB (Least Significant Bit) R0, G0, B0 MSB (Most Significant Bit) R5, G5, B5
- Note3: Twist pair wires with 100Ω (Characteristic impedance) should be used between LCD panel signal processing board and LVDS transmitter.
- Note4: Input signals to TC4 and TC5 are not used inside the product, but do not keep TC4 and TC5 open to avoid noise problem.

- 4.5.5 Input data mapping
- (1) Input data signal: 8bit, MAP A




(2) Input data signal: 8bit, MAP B



NEC NEC LCD Technologies, Ltd.

(3) Input data signal: 6bit



4.6 DISPLAY COLORS AND INPUT DATA SIGNALS

4.6.1 Combinations between input data signals, FRC signal and MSL signal

This product can display in equivalent to 16,777,216 colors in 256 gray scales and 262,144 colors in 64 gray scales by combination between input data signals, FRC signal and MSL signal. See following table.

Combination	Input data signals	Input Data mapping	CN1- Pin No.1 and 2	FRC terminal	MSL terminal	Display colors	Remarks
1	8 bit	MAP A	D3+/-	High	Low	16,777,216	Note1
2	8 bit	MAP B	D3+/-	High	High	16,777,216	Note1
3	6 bit	-	GND	Low or open	Low	262,144	Note2

Note1: See "4.6.2 16,777,216 colors".

Note2: See "4.6.3 262,144 colors".

4.6.2 16,777,216 colors

This product can display equivalent of 16,777,216 colors in 256 gray scales by combination ① and ②. (See "**4.6.1 Combinations between input data signals, FRC signal and MSL signal**".) Also the relation between display colors and input data signals is as the following table.

Diapla	y colors								Data	a sig	nal	(0: I	Low	leve	el, 1	: Hi	gh le	evel))						
Displa	ty colors	R7	' R6	R5	R4	R3	R2	R1	R0	G7	7 G6	6 G5	G4	G3	G2	G1	G0	B7	' B6	B5	B4	B3	B2	B1	B0
	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	Blue	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	1
Basic Colors	Red	1	1	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Co]	Magenta	1	1	1	1	1	1	1	1	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	1
SIC	Green	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	1	0	0	0	0	0	0	0	0
\mathbf{Ba}	Cyan	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	Yellow	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	0	0	0	0	0	0	0	0
	White	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
e		0	0	0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
scal	dark	0	0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Red gray scale	↑				:									:								:			
d gi	\downarrow				:									•								:			
Re	bright	1	1	1	1	1	1	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	D 1	1	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	Red	1	1	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
ale		0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0	0
y sc	dark	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0	0	0
gra.	\uparrow																					:			
Green gray scale	↓ ↓ ↓ ↓ ↓	0	0	0	0	:	0	0	0	1	1	1	1	:	1	0	1	0	0	0	0	:	0	0	0
Gre	bright	0 0	1	1	1	1	1	1	0 1	1 0	0	0 0													
	Green	0	0	0	0	0	0	0	0	1 1	1	1	1	1	1	1	1	0 0	0	0	0	0	0	0	0
		0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1
ale	- اب ا	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0
/ sc	dark ↑	0	0	0	0	. 0	0	0	0	0	0	0	0	. 0	0	0	0	0	0	0	0	. 0	0	1	0
Blue gray scale														•											
ne f	↓ bright	0	0	0	0	0	0	0	0	0	0	0	0	. 0	0	0	0	1	1	1	1	1	1	0	1
Bl	origin	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	0
	Blue	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	1

4.6.3 262,144 colors

This product can display equivalent of 262,144 colors in 64 gray scales by combination ③. (See "**4.6.1 Combinations between input data signals, FRC signal and MSL signal**".) Also the relation between display colors and input data signals is as the following table.

Displa	y colors						Data	a sign	al (0:	Low	level	, 1: F	ligh le	evel)					
Dispia	ly colors	R 5	R4	R 3	R 2	R 1	R 0	G5	G4	G3	G2	G1	G0	B5	B4	B 3	B 2	B 1	B 0
	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	Blue	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1
ors	Red	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0
Basic colors	Magenta	1	1	1	1	1	1	0	0	0	0	0	0	1	1	1	1	1	1
isic	Green	0	0	0	0	0	0	1	1	1	1	1	1	0	0	0	0	0	0
\mathbf{B}^{a}	Cyan	0	0	0	0	0	0	1	1	1	1	1	1	1	1	1	1	1	1
	Yellow	1	1	1	1	1	1	1	1	1	1	1	1	0	0	0	0	0	0
	White	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
e		0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0
scal	dark	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0
Red gray scale	\uparrow			:	:						:						:		
l gr	\downarrow			:	:						:						:		
Rec	bright	1	1	1	1	0	1	0	0	0	0	0	0	0	0	0	0	0	0
		1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0
	Red	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0
	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
ale		0	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0
sci	dark	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0
gray	↑ ,			:	:						:						:		
Green gray scale	\downarrow			:	:						:						:		
Jree	bright	0	0	0	0	0	0	1	1	1	1	0	1	0	0	0	0	0	0
Ŭ	~	0	0	0	0	0	0	1	1	1	1	1	0	0	0	0	0	0	0
	Green	0	0	0	0	0	0	1	1	1	1	1	1	0	0	0	0	0	0
	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
le		0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1
sca	dark	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0
Blue gray scale	↑ 			:	:						:						:		
e B	\downarrow		0		:	~	0	0	0	0	:	~	0	1	1		:	~	
Blu	bright	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	0	1
	Dlus	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	0
	Blue	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1

4.7 DISPLAY POSITIONS

The following table is the coordinates per pixel (See "4.8 SCANNING DIRECTIONS".).

C (0, 0)						
R G	В					
1						
$\begin{array}{cc} C(&0,&0) \end{array}$	C(1, 0)	• •	C(X, 0)	• •	C(798, 0)	C(799, 0)
C(0, 1)	C(1, 1)	• •	C(X, 1)	• •	C(798, 1)	C(799, 1)
•	•	•	•	•	•	•
•	•	• • •	•	• • •	•	•••
•	•	•	•	•	•	•
C(0, Y)	C(1, Y)	• •	C(X, Y)	• •	C(798, Y)	C(799, Y)
•	•	•	•	•	•	•
•	•	• • •	•	• • •	•	•
•	•	•	•	•	•	•
C(0, 598)	C(1, 598)	• • •	C(X, 598)	• • •	C(798, 598)	C(799, 598)
C(0, 599)	C(1, 599)	• • •	C(X, 599)	• • •	C(798, 599)	C(799, 599)

4.8 SCANNING DIRECTIONS

The following figures are seen from a front view. Also the arrow shows the direction of scan.




Figure1. Normal scan (DPS: Low or Open)





Figure2. Reverse scan (DPS: High)


Note1: Meaning of C (X, Y) and D (X, Y)

C (X, Y): The coordinates of the display position (See "**4.7 DISPLAY POSITIONS**".) D (X, Y): The data number of input signal for LCD panel signal processing board

4.9 INPUT SIGNAL TIMINGS



• Horizontal signal



Note1: This diagram indicates virtual signal for set up to timing. Note2: See "**4.9.3 Input signal timing chart**" for numeration of pulse.

4.9.2 Timing characteristics

	enaraeteristici						(N	ote1, Note2, Note3)		
	Parameter		Symbol	min.	typ.	max.	Unit	Remarks		
	Frequency		1/tc	34.0	38.362	40.0	MHz	26.067ns (typ.)		
CLK	E	outy	-				-			
	Rise time	e, Fall time	-		-		ns	-		
	CLK-DATA	Setup time	-				ns			
DATA	CLK-DATA	Hold time	-		-		ns	-		
	Rise time, Fall time		-				ns			
		Cycle	th	24.0	26.693	30.1	μs	37.463kHz (typ.)		
	Horizontal	Cycle	tii	-	1,024	-	CLK	57.405KHZ (typ.)		
		Display period	thd		800		CLK	-		
	T7 (* 1	Cycle	tv	16.1	16.683	17.2	ms			
DE	Vertical (One frame)	Cycle	ťv	-	625	-	Н	59.94Hz (typ.)		
	· · ·	Display period	tvd		600		Н			
	CLK-DE	Setup time	-				ns			
	CEN-DE	Hold time	-				ns	-		
	Rise time	e, Fall time	-				ns			

Note1: Definition of parameters is as follows.


tc=1CLK, th=1H

Note2: See the data sheet of LVDS transmitter.

Note3: Vertical cycle (tv) should be specified in integral multiple of Horizontal cycle (th).

4.9.3 Input signal timing chart

Horizontal timing



4.10 OPTICS

4.10.1 Optical characteristics

								(Note1	, Note2)
Parameter		Condition		min.	typ.	max.	Unit	Measuring instrument	Remarks
Luminanc	ce	White at center $\theta R = 0^\circ, \ \theta L = 0^\circ, \ \theta U = 0^\circ, \ \theta D = 0^\circ$	L	400	550	-	cd/m ²	BM-5A	-
Contrast ra	tio	White/Black at center $\theta R= 0^\circ, \ \theta L= 0^\circ, \ \theta U= 0^\circ, \ \theta D= 0^\circ$	CR	600	900	-	-	BM-5A	Note3
Luminance unit	formity	White $\theta R = 0^\circ, \ \theta L = 0^\circ, \ \theta U = 0^\circ, \ \theta D = 0^\circ$	LU	-	1.25	1.4	I	BM-5A	Note4
	White	x coordinate	Wx	0.283	0.313	0.343	-		
	white	y coordinate	Wy	0.299	0.329	0.359	-		
	Red	x coordinate	Rx	-	0.57	-	-		
Chromaticity	Reu	y coordinate	Ry	-	0.341	-	-		
Chromatienty	Green	x coordinate	Gx	-	0.325	-	-	SR-3	Note5
	Gitteli	y coordinate	Gy	-	0.528	-	-	SIC 5	110105
	Blue	x coordinate	Bx	-	0.159	-	-		
	Diue	y coordinate	By	-	0.157	-	-		
Color gam	ut	$\theta R = 0^\circ, \ \theta L = 0^\circ, \ \theta U = 0^\circ, \ \theta D = 0^\circ$ at center, against NTSC color space	С	35	40	-	%		
Response ti	ma	White to Black	Ton	-	3	5	ms	BM-5A	Note6
Response u		Black to White	Toff	-	15	21	ms	DM-JA	Note7
	Right	$\theta U=0^{\circ}, \ \theta D=0^{\circ}, \ CR\geq 10$	θR	70	80	-	0		
Viewing angle	Left	$\theta U=0^{\circ}, \ \theta D=0^{\circ}, \ CR\geq 10$	θL	70	80	-	0	EZ	Note8
viewing angle	Up	$\theta R = 0^\circ, \ \theta L = 0^\circ, \ CR \ge 10$	θU	70	80	-	0	Contrast	110100
	Down	$\theta R = 0^{\circ}, \ \theta L = 0^{\circ}, \ CR \ge 10$	θD	70	80	-	0		


Note1: These are initial characteristics.

Note2: Measurement conditions are as follows.

Ta= 25°C, VCC= 3.3V, IBL= 5.0mArms/lamp, Display mode: SVGA,

Horizontal cycle=1/37.463kHz, Vertical cycle=1/59.94Hz, DPS=Low or Open: Normal scan

Optical characteristics are measured at luminance saturation after 20minutes from working the product, in the dark room. Also measurement methods are as follows.



- Note3: See "4.10.2 Definition of contrast ratio".
- Note4: See "4.10.3 Definition of luminance uniformity".
- Note5: These coordinates are found on CIE 1931 chromaticity diagram.
- Note6: Product surface temperature: TopF= 28°C
- Note7: See "4.10.4 Definition of response times".
- Note8: See "4.10.5 Definition of viewing angles".

4.10.2 Definition of contrast ratio


The contrast ratio is calculated by using the following formula.

Contrast ratio (CR) = Luminance of white screen Luminance of black screen

4.10.3 Definition of luminance uniformity


The luminance uniformity is calculated by using following formula.

The luminance is measured at near the 5 points shown below.




4.10.4 Definition of response times

Response time is measured, the luminance changes from "white" to "black", or "black" to "white" on the same screen point, by photo-detector. Ton is the time it takes the luminance change from 90% down to 10%. Also Toff is the time it takes the luminance change from 10% up to 90% (See the following diagram.).



4.10.5 Definition of viewing angles



5. ESTIMATED LUMINANCE LIFETIME

The luminance lifetime is the time from initial luminance to half-luminance.

This lifetime is the estimated value, and is not guarantee value.

	Condition	Luminance lifetime (MTTF) Note1, Note2	Unit
Modulo	25°C (Ambient temperature of the product) Continuous operation and IBL= 5.0mArms/lamp	43,000	h
Module	70°C (Surface temperature at screen center) Continuous operation and IBL= 5.0mArms/lamp	10,000	h
Cold cathode fluorescent lamp	25°C (Ambient temperature of the lamp) Continuous operation and IBL= 5.0mArms	50,000	h

Note1: MTTF is mean time to half-luminance.


Note2: In case the product works under low temperature environment, the lifetime becomes short.

6. RELIABILITY TESTS

Test item	Condition	Judgment Note1
High temperature and humidity (Operation)	 60 ± 2°C, RH= 90%, 240hours Display data is black. 	
High temperature (Operation)	 70 ± 3°C, 240hours Display data is black. 	
Heat cycle (Operation)	 -20 ± 3°C1hour 70 ± 3°C1hour 50cycles, 4 hours/cycle Display data is black. 	
Thermal shock (Non operation)	 -30 ± 3°C30minutes 80 ± 3°C30minutes 100cycles, 1hour/cycle Temperature transition time is within 5 minutes. 	No display malfunctions
ESD (Operation)	 150pF, 150Ω, ±10kV 9 places on a panel surface Note2 10 times each places at 1 sec interval 	
Dust (Operation)	 Sample dust: No. 15 (by JIS-Z8901) 15 seconds stir 8 times repeat at 1 hour interval 	
Vibration (Non operation)	 5 to 100Hz, 19.6m/s² 1 minute/cycle X, Y, Z directions 120 times each directions 	No display malfunctions No physical damages
Mechanical shock (Non operation)	 539m/s², 11ms ±X, ±Y, ±Z directions 5 times each directions 	

Note1: Display and appearance are checked under environmental conditions equivalent to the inspection conditions of defect criteria.


Note2: See the following figure for discharge points.



7. PRECAUTIONS

7.1 MEANING OF CAUTION SIGNS

The following caution signs have very important meaning. **Be sure to read "7.2 CAUTIONS" and "7.3 ATTENTIONS", after understanding these contents!**



7.2 CAUTIONS

- * Do not touch lamp cables while turn on. There is a danger of an electric shock.
- - * Do not touch the working backlight and IC. There is a danger of burn injury.
 - Do not shock and press the LCD panel and the backlight! There is a danger of breaking, because they are made of glass. (Shock: To be not greater 539m/s² and to be not greater 11ms, Pressure: To be not greater 19.6 N (\$\phi16mm jig))

7.3 ATTENTIONS \bigwedge

7.3.1 Handling of the product

- ① Take hold of both ends without touching the circuit board when the product (LCD module) is picked up from inner packing box to avoid broken down or misadjustment, because of stress to mounting parts on the circuit board.
- ② Do not hook nor pull cables such as lamp cable, and so on, in order to avoid any damage.
- ③ When the product is put on the table temporarily, display surface must be placed downward.
- ④ When handling the product, take the measures of electrostatic discharge with such as earth band, ionic shower and so on, because the product may be damaged by electrostatic.
- ⑤ The torque for product mounting screws must never exceed 0.294N⋅m. Higher torque might result in distortion of the bezel.
- (6) The product must be installed using mounting holes without undue stress such as bends or twist (See outline drawings). And do not add undue stress to any portion (such as bezel flat area). Bends or twist described above and undue stress to any portion may cause display mura.
- ⑦ Do not press or rub on the sensitive product surface. When cleaning the product surface, use of the cloth with ethanolic liquid such as screen cleaner for LCD is recommended.
- ③ Do not push nor pull the interface connectors while the product is working.
- Do not bend or unbend the lamp cable at the near part of the lamp holding rubber, to avoid the damage for high voltage side of the lamp.

- Properly connect the plug (backlight side) to adaptable socket (inverter side) without incomplete connection. After connecting, be careful not to hook the lamp cables because incomplete connection may occur by hooking the lamp cables. This incomplete connection may cause abnormal operation of high voltage circuit.
- If the lamp cable is attached on the metal part of the product directly, high frequency leak current to the metal part may occur, then the brightness may decrease or the lamp may not be turned on.
- When handling the product, use of an original protection sheet on the product surface (polarizer) is recommended for protection of product surface. Adhesive type protection sheet may change color or characteristics of the polarizer.
- ③ Usually liquid crystals don't leak through the breakage of glasses because of the surface tension of thin layer and the construction of LCD panel. But, if you contact with liquid crystal for the worst, please wash it out with soap.

7.3.2 Environment

- ① Do not operate or store in high temperature, high humidity, dewdrop atmosphere or corrosive gases. Keep the product in packing box with antistatic pouch in room temperature to avoid dusts and sunlight, when storing the product.
- ② In order to prevent dew condensation occurring by temperature difference, the product packing box should be opened after enough time being left under the environment of an unpacking room. Evaluate the leaving time sufficiently because a situation of dew condensation occurring is changed by the environmental temperature and humidity. (Recommended leaving time: 6 hours or more with packing state)
- ③ Do not operate in high magnetic field. Circuit boards may be broken down by it.
- ④ This product is not designed as radiation hardened.

7.3.3 Characteristics

The following items are neither defects nor failures.

- ① Characteristics of the LCD (such as response time, luminance, color uniformity and so on) may be changed depending on ambient temperature. If the product is stored under condition of low temperature for a long time, it may cause display mura. In this case, the product should be operated after enough time being left under condition of operating temperature.
- ② Display mura, flicker, vertical seam or small spot may be observed depending on display patterns.
- ③ Optical characteristics (e.g. luminance, display uniformity, etc.) gradually is going to change depending on operating time, and especially low temperature, because the LCD has cold cathode fluorescent lamps.
- ④ Do not display the fixed pattern for a long time because it may cause image sticking. Use a screen saver, if the fixed pattern is displayed on the screen.
- ⑤ The display color may be changed depending on viewing angle because of the use of condenser sheet in the backlight.
- [©] Optical characteristics may be changed depending on input signal timings.
- ⑦ The interference noise between input signal frequency for this product's signal processing board and luminance control frequency of the inverter may appear on a display. Set up luminance control frequency of the inverter so that the interference noise does not appear.
- ③ The product gives AR (antireflection) coating of the polarizer surface. Though AR (antireflection) coating actualizes the low reflection with the multilayer structure, the color of reflection may differ between products and the color change of reflection may occur in the same product by fluctuation of AR (antireflection) coating.
- After the product is stored under condition of low temperature or dark place for a long time, the cold cathode fluorescent lamp may not be turned on under the same condition because of the general characteristic of cold cathode fluorescent lamp. In addition, when Luminance control ratio is low in pulse width modulation method inverter, the lamp may not be turned on. In this case, power should be supplied again.

7.3.4 Other

- ① All GND and VCC terminals should be used without any non-connected lines.
- ② Do not disassemble a product or adjust variable resistors.
- ③ See "REPLACEMENT MANUAL FOR LAMP HOLDER SET", when replacing backlight lamps.
- ④ Pay attention not to insert foreign materials inside of the product, when using tapping screws.
- ⑤ Pack the product with original shipping package, in order to avoid any damages during transportation, when returning the product to NEC for repair and so on.
- The information of China RoHS directive six hazardous substances or elements in this product is as follows

	China RoHS directive six hazardous substances or elements											
Lead (Pb)	Mercury (Hg)	Cadmium (Cd)	Hexavalent Chromium (Cr VI)	Polybrominated Biphenys (PBB)	Polybrominated Biphenyl Ethers (PBDE)							
×	×	0	0	0	0							


Note1: O: This indicates that the poisonous or harmful material in all the homogeneous materials for this part is equal or below the limitation level of SJ/T11363-2006 standard regulation.

 \times : This indicates that the poisonous or harmful material in all the homogeneous materials for this part is above the limitation level of SJ/T11363-2006 standard regulation.

NEC NEC LCD Technologies, Ltd.

8. OUTLINE DRAWINGS

8.1 FRONT VIEW




Note3: Mounting hole portions (4 pieces)

Unit: mm

NEC NEC LCD Technologies, Ltd.

8.2 REAR VIEW



Note1: The values in parentheses are for reference.

Note2: The torque for product mounting screws must never exceed 0.294N·m.

Note3: Mounting hole portions (4 pieces)

Unit: mm