650V Enhancement mode GaN HEMT

GNP2025TD-Z

EcoGaN

Features

- 650V E-mode GaN HEMT
- 25mΩ Resistance
- 13.2nC Gate Charge

Package Information

W (Typ) × D (Typ) × H (Max)

11.68 mm × 9.9 mm × 2.4 mm

TOLL-8N

Application

- High Switching Frequency Converter
- High Density Converter



Key Performance Parameters

Symbol	Values	Unit
$V_{DS,max}$	650	V
I_D	59.8	A
$I_{D,pulse}$	119.7	A
$R_{DS(on),typ}$	25	mΩ
Q_g	13.2	nC
Q_{oss} @400V	138	nC
Q_{rr}	0	nC

Gate	8
Kelvin Source	7
Drain	Drain Contact
Source	1,2,3,4,5,6



Ordering Information

Ordering Code	Package	Ordering Unit (pcs)	Marking
GNP2025TD-ZTR	TOLL-8N	2,000	GNP2025

© 2025 ROHM Co., Ltd. All rights reserved.

Maximum Ratings

Parameter	Symbol	Ratings	Unit	Conditions
Drain to Source Voltage, continuous	V_{DSS}	650	V	-
Transient Drain to Source Voltage *1	$V_{DS(transient)}$	800	V	-
Gate to Source Voltage	V_{GSS}	-10 to +6.5	V	-
Transient Gate to Source Voltage *2	$V_{GS(transient)}$	8.5	V	-
Continuous Drain Current *3	I_D	59.8	A	T_c = 25°C
		26.8		T_c = 125°C
Pulse Drain Current *3*4	$I_{D,pulse}$	119.7	A	T_c = 25°C
		53.5		T_c = 125°C
Power Dissipation	P_{tot}	291	W	T_c = 25°C
Operation Temperature	T_j	-55 to +150	°C	-
Range of Storage Temperature	T_{stg}	-55 to +150	°C	-

*1 t_{pulse}=1μs, <10 hrs of total time.

*2 t_{pulse}<20ns, <0.5 hrs of total time.

*3 Limited and calculated by maximum temperature allowed.

*4 V_{GS}=6V,Duty=0.1, t_{pulse}=1μs.

Please note especially when using driver source
that V_{GSS}_surge must be in the range of absolute maximum rating.

Thermal Resistance

Parameter	Symbol	Values			Unit	Conditions
		Min	Typ	Max		
Thermal Resistance, Junction to Ambient	R_{thJA}	-	-	34.2	°C/W	Device on JEDEC Standard Board for Thermal Resistance
Thermal Resistance, Junction to Case	R_{thJC}	-	0.31	0.43	°C/W	-
Reflow Soldering Temperature	T_{solder}	-	-	260	°C	MSL 3

© 2025 ROHM Co., Ltd. All rights reserved.

Static Characteristic (T_j = 25°C)

Parameter	Symbol	Values			Unit	Conditions
		Min	Typ	Max		
Gate Threshold Voltage	$V_{GS(th)}$	1.0	1.5	2.5	V	V_{DS} = 30mV, I_D = 46mA
Drain to Source Breakdown Voltage	$V_{(BR)DSS}$	650	-	-	V	V_{GS} = 0V, T_j = 25°C
Zero Gate Voltage Drain Current	I_{DSS}	-	0.47	47	μA	V_{GS} = 0V V_{DS} = 650V T_j = 25°C
		-	13	-		V_{GS} = 0V V_{DS} = 650V T_j = 150°C
Gate to Source Leakage Current	I_{GSS}	-	0.2	5.0	mA	V_{GS} = 6.5V, V_{DS} = 0V
Static Drain to Source On State Resistance	$R_{DS(on)}$	-	26	36	mΩ	V_{GS} = 5.0V I_D = 12A T_j = 25°C
		-	60	-		V_{GS} = 5.0V I_D = 12A T_j = 150°C
		-	25	35		V_{GS} = 6.0V I_D = 12A T_j = 25°C
		-	58	-		V_{GS} = 6.0V I_D = 12A T_j = 150°C
Gate Input Resistance	R_G	-	0.8	-	Ω	f = 100MHz, open drain

© 2025 ROHM Co., Ltd. All rights reserved.

Dynamic Characteristics (T$_j$ = 25°C)

Parameter	Symbol	Values			Unit	Conditions
		Min	Typ	Max		
Input Capacitance	C_{iss}	-	413	-	pF	V_{GS} = 0V
Output Capacitance	C_{oss}	-	140	-		V_{DS} = 400V
Reverse Transfer Capacitance	C_{rss}	-	1.08	-		f = 1MHz
Effective Output Capacitance, Energy Related	$C_{o(er)}$	-	229	-	pF	V_{GS} = 0V, V_{DS} = 0V to 400V
Effective Output Capacitance, Time Related	$C_{o(tr)}$	-	346	-		V_{GS} = 0V, V_{DS} = 0V to 400V
Output Charge	Q_{oss}	-	138	-	nC	V_{GS} = 0V, V_{DS} = 0V to 400V
Turn - On Delay Time	$t_{d(on)}$	-	13.5	-	ns	V_{DS} = 400V
Rise Time	t_r	-	8.2	-		I_D = 8A
Turn - Off Delay Time	$t_{d(off)}$	-	40.1	-		V_{GS} = 6V / 0V
Fall Time	t_f	-	26.2	-		R_{on} = 10Ω R_{off} = 10Ω
Total Gate Charge	Q_g	-	13.2	-	nC	V_{DS} = 400V
Gate to Source Charge	Q_{gs}	-	0.9	-		I_D = 8A
Gate to Drain Charge	Q_{gd}		1.5			V_{GS} = 6V / 0V
Gate Plateau Voltage	V_{plat}	-	1.8	-	V	

Reverse Conduction Electrical Characteristics (T$_j$ = 25°C)

Parameter	Symbol	Values			Unit	Conditions
		Min	Typ	Max		
Source to Drain Reverse Voltage	V_{SD}	-	2.5	-	V	V_{GS} = 0V, I_{SD} = 12A
Reverse Recovery Time	t_{rr}	-	0	-	ns	
Reverse Recovery Charge	Q_{rr}	-	0	-	nC	
Peak Reverse Recovery Current	I_{rrm}	-	0	-	A	

© 2025 ROHM Co., Ltd. All rights reserved.

Electrical Characteristic Curves

Fig.1 Power Dissipation Derating Curve



$P_D = f(T_c)$

Fig.2 Normalized Transient Thermal Resistance vs. Pulse Width



$r(t) = f(P_W, D); T_c = 25°C$

Fig.3 Max. Safe Operating Area



$I_D = f(V_{DS}, P_W); T_c = 25°C$

Fig.4 Max. Safe Operating Area



$I_D = f(V_{DS}, P_W); T_c = 125°C$

© 2025 ROHM Co., Ltd. All rights reserved.

Electrical Characteristic Curves

Fig.5 Typ. Output Characteristics



$I_D = f(V_{DS}, V_{GS})$; $T_j = 25°C$

Fig.6 Typ. Output Characteristics



$I_D = f(V_{DS}, V_{GS})$; $T_j = 125°C$

Fig.7 Static Drain to Source On State Resistance vs. Drain to Source Current



$R_{DS(on)} = f(I_D, V_{GS})$; $T_j = 25°C$

Fig.8 Typ. Transfer Characteristics



$I_D = f(V_{GS}, T_j)$; V_{DS} = 10 V; T_j = 25°C, 125°C

© 2025 ROHM Co., Ltd. All rights reserved.

Electrical Characteristic Curves

Fig.9 Gate to Source Leakage



$I_{GSS} = f(V_{GS})$; T_j = 25°C

Fig.10 Drain to Source Leakage Characteristics



$I_{DSS} = f(V_{DS})$; V_{GS} = 0 V; T_j = 25°C, 125°C

Fig.11 Channel Reverse Characteristics



$I_D = f(V_{DS}, V_{GS})$; T_j = 25°C

Fig.12 Channel Reverse Characteristics



$I_D = f(V_{DS}, V_{GS})$; T_j = 125°C

© 2025 ROHM Co., Ltd. All rights reserved.

Electrical Characteristic Curves

Fig.13 Channel Reverse Characteristics



$I_S = f(V_{SD}, V_{GS})$; T_j = 25°C

Fig.14 Channel Reverse Characteristics



$I_S = f(V_{SD}, V_{GS})$; T_j = 125°C

Fig.15 Typ. Capacitance



$C_{XSS} = f(V_{DS})$; V_{GS} = 0V; f = 1MHz; T_j = 25°C

Fig.16 Typ. Coss Stored Energy



$E_{oss} = f(V_{DS})$; T_j = 25°C

© 2025 ROHM Co., Ltd. All rights reserved.

Electrical Characteristic Curves

Fig.17 Typ. Gate Charge	※ Gate Charge Waveform
	
V_{GS} = f(Q_G); V_{DCLINK} = 400V; I_D = 8A T_j = 25°C	

© 2025 ROHM Co., Ltd. All rights reserved.

Measurement Circuits and Waveforms

Fig.18 Gate Charge Measurement Circuit



Fig.19 Switching Characteristics Measurement Circuit



Fig.20 Waveforms for Switching Time



Fig.21 Waveforms for Switching Energy Loss



© 2025 ROHM Co., Ltd. All rights reserved.

Physical Dimension

(mm)



(mm)



© 2025 ROHM Co., Ltd. All rights reserved.

Revision History

Date	Revision	Changes
9.October.2025	001	New Release

© 2025 ROHM Co., Ltd. All rights reserved.

Package Information : TOLL-8N

1. Package Information

Package Name	TOLL-8N
Type	TO
Pin Count	8
Package Weight [g]	0.74
Lead Finish	Pure Tin
MSL	Level3

2. Package Structure



©2024 ROHM Co., Ltd. All rights reserved

3. Packing Specification

3.1 Packing form, Quantity, PIN1 Orientation

Packing Form		Tape&Reel
Packing Quantity	[pcs]	2000
PIN 1 Orientation		TR



Fig.1 Quadrant Assignments for PIN 1 Orientation in Tape

E2 : PIN1 is placed to the top left corner. TR : PIN1 is placed to the top right corner.

TL : PIN1 is placed to the lower left. E1 : PIN1 is placed to the lower right.

3.2 Use material

Item	Material
Embossed carrier tape	PS
Cover tape	PET+PE
Reel	PS
Desiccant	Clay
Envelope	Aluminum-laminated
Air cap	PE
Unit box	Cardboard
Shipping box	Cardboard

3.3 Leader specification

No component pockets are 420 mm or more.

3.4 Trailer specification

No component pockets are 180 mm or more. Tape is free from reel.

3.5 Peelback strength

Cover tape peelback strength is 0.2 N to 0.7 N.



Fig. 2 Test method

3.6 Missing Ics

(1) No consecutive dropouts.

(2) A maximun 0.1 % of specified number of products in each packing may be missing.

©2024 ROHM Co., Ltd. All rights reserved

3.7 Tape and Reel Specification

3.7.1 Tape Dimension



(unit:mm)

	Tape Dimension	Tape Tolerance
A1	10.30	±0.1
B1	12.10	±0.1
D0	φ1.5	+0.1/-0
D1	φ1.5	+0.1/-0
E	1.75	±0.1
F	11.50	±0.1
K'	2.70	±0.1
P0	4.00	±0.1
P1	12.0	±0.1
P2	2.00	±0.1
T	0.30	±0.1
W	24.0	±0.3

©2024 ROHM Co., Ltd. All rights reserved

3.7.2 Reel Dimension



(unit:mm)

	Reel Dimension	Reel Tolerance
A	330	±2.0
B	100	±1.0
C	13.2	±0.3
D		
E	2	±0.3
W1	24.4	
W2	31.4	

©2024 ROHM Co., Ltd. All rights reserved

3.8 Packing Method

1 reel(s) or less per unit box



3.9 Packing Style

5 unit boxes or less per shipping box



(unit:mm)

Shipping Box Dimension	
X	372
Y	368
Z	305

3.10 Label Specification



©2024 ROHM Co., Ltd. All rights reserved

3.11 Caution card specification



Remark) Standard item 1. calculated shelf life in caution card is not applied for MSL1 product.

3.12 Indicator card specification



©2024 ROHM Co., Ltd. All rights reserved

4. Footprint dimensions



(unit:mm)

In actual design, please optimize in accordance with the situation of your board design and soldering condition.

©2024 ROHM Co., Ltd. All rights reserved

5. Marking Specification



6. Storage conditions

6.1 Storage environment

Recommended storage conditions

	Min.	Max.	Unit
Temperature	5	30	°C
Humidity	-	70	% RH

6.2 Storage period (Start to count since delivery date)

	Min.	Max.	Unit
Storage period	-	1	year

6.3 Specified storage period until soldering

	Min.	Max.	Unit
Acceptable time	-	168	h

The above value is a time from opening the moisture-proof packaging until the soldering. Cases where it is necessary to perform the drying process is the following.

Case 1 : in excess of the above-mentioned "Acceptable time"

Case 2 : it has passed more than 6 years not open

Recommended the dry process conditions

	Temperature [°C]	Time [h]
Reel*(Note1)*	60	48
Other Heat-proof container		

(Note1) When carrying out the dry process in a "Reel" state, the peelback strength will change. Please refer to the following values:

	Min.	Max.	Unit
Peelback strength	0.2	0.9	N

The drying process is the impact on the solderability because the oxidation of the terminal portion will occur. Therefore, specify the maximum times of the dry processing as follows:

Recommended execution count of the dry process

		Unit
Reel	1	times
Other Heat-proof container		times

©2024 ROHM Co., Ltd. All rights reserved

7. Soldering conditions

7.1 Recommended temperature profile for reflow



7.2 Recommended condition for wave soldering

Preheating temperature	:	120 °C to 150	°C
Preheating time	:	60 s MAX	
Soldering temperature	:	260 °C ± 3	°C
Soldering time	:	12 s MAX	

Notes for wave soldering
(1)Soldering time is provided for total soldering time in case of dual wave soldering.
(2) Do not use other soldering methods with wave soldering.
(3) Recommend to clean the board to eliminate flux, solder waste,
and other impurities for reliability, after soldering.
(4) Optimize soldering condition to prevent solder bridging.
(5) The heatsink may not be connected using wave soldering methods.

7.3 Recommended condition for solder iron

Solder iron temperature	:	380 °C or less	
Mounting time	:	4 s or less	

Notes for solder iron
(1)The heatsink may not be connected using solder iron.
(2)Solder mounting time is the time per 1 lead

©2024 ROHM Co., Ltd. All rights reserved

Notice

Precaution on using ROHM Products

1. Our Products are designed and manufactured for application in ordinary electronic equipment (such as AV equipment, OA equipment, telecommunication equipment, home electronic appliances, amusement equipment, etc.). If you intend to use our Products in devices requiring extremely high reliability (such as medical equipment (Note 1), transport equipment, traffic equipment, aircraft/spacecraft, nuclear power controllers, fuel controllers, car equipment including car accessories, safety devices, etc.) and whose malfunction or failure may cause loss of human life, bodily injury or serious damage to property ("Specific Applications"), please consult with the ROHM sales representative in advance. Unless otherwise agreed in writing by ROHM in advance, ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of any ROHM's Products for Specific Applications.

(Note1) Medical Equipment Classification of the Specific Applications

JAPAN	USA	EU	CHINA
CLASSⅢ	CLASSⅢ	CLASSⅡb	CLASSⅢ
CLASSⅣ		CLASSⅢ	

2. ROHM designs and manufactures its Products subject to strict quality control system. However, semiconductor products can fail or malfunction at a certain rate. Please be sure to implement, at your own responsibilities, adequate safety measures including but not limited to fail-safe design against the physical injury, damage to any property, which a failure or malfunction of our Products may cause. The following are examples of safety measures:
   [a] Installation of protection circuits or other protective devices to improve system safety
   [b] Installation of redundant circuits to reduce the impact of single or multiple circuit failure

3. Our Products are designed and manufactured for use under standard conditions and not under any special or extraordinary environments or conditions, as exemplified below. Accordingly, ROHM shall not be in any way responsible or liable for any damages, expenses or losses arising from the use of any ROHM's Products under any special or extraordinary environments or conditions. If you intend to use our Products under any special or extraordinary environments or conditions (as exemplified below), your independent verification and confirmation of product performance, reliability, etc, prior to use, must be necessary:
   [a] Use of our Products in any types of liquid, including water, oils, chemicals, and organic solvents
   [b] Use of our Products outdoors or in places where the Products are exposed to direct sunlight or dust
   [c] Use of our Products in places where the Products are exposed to sea wind or corrosive gases, including Cl_2, H_2S, NH_3, SO_2, and NO_2
   [d] Use of our Products in places where the Products are exposed to static electricity or electromagnetic waves
   [e] Use of our Products in proximity to heat-producing components, plastic cords, or other flammable items
   [f] Sealing or coating our Products with resin or other coating materials
   [g] Use of our Products without cleaning residue of flux (Exclude cases where no-clean type fluxes is used. However, recommend sufficiently about the residue.) ; or Washing our Products by using water or water-soluble cleaning agents for cleaning residue after soldering
   [h] Use of the Products in places subject to dew condensation

4. The Products are not subject to radiation-proof design.

5. Please verify and confirm characteristics of the final or mounted products in using the Products.

6. In particular, if a transient load (a large amount of load applied in a short period of time, such as pulse, is applied, confirmation of performance characteristics after on-board mounting is strongly recommended. Avoid applying power exceeding normal rated power; exceeding the power rating under steady-state loading condition may negatively affect product performance and reliability.

7. De-rate Power Dissipation depending on ambient temperature. When used in sealed area, confirm that it is the use in the range that does not exceed the maximum junction temperature.

8. Confirm that operation temperature is within the specified range described in the product specification.

9. ROHM shall not be in any way responsible or liable for failure induced under deviant condition from what is defined in this document.

Precaution for Mounting / Circuit board design

1. When a highly active halogenous (chlorine, bromine, etc.) flux is used, the residue of flux may negatively affect product performance and reliability.

2. In principle, the reflow soldering method must be used on a surface-mount products, the flow soldering method must be used on a through hole mount products. If the flow soldering method is preferred on a surface-mount products, please consult with the ROHM representative in advance.

For details, please refer to ROHM Mounting specification

© 2015 ROHM Co., Ltd. All rights reserved.

Precautions Regarding Application Examples and External Circuits

1. If change is made to the constant of an external circuit, please allow a sufficient margin considering variations of the characteristics of the Products and external components, including transient characteristics, as well as static characteristics.

2. You agree that application notes, reference designs, and associated data and information contained in this document are presented only as guidance for Products use. Therefore, in case you use such information, you are solely responsible for it and you must exercise your own independent verification and judgment in the use of such information contained in this document. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of such information.

Precaution for Electrostatic

This Product is electrostatic sensitive product, which may be damaged due to electrostatic discharge. Please take proper caution in your manufacturing process and storage so that voltage exceeding the Products maximum rating will not be applied to Products. Please take special care under dry condition (e.g. Grounding of human body / equipment / solder iron, isolation from charged objects, setting of Ionizer, friction prevention and temperature / humidity control).

Precaution for Storage / Transportation

1. Product performance and soldered connections may deteriorate if the Products are stored in the places where:
   [a] the Products are exposed to sea winds or corrosive gases, including Cl_2, H_2S, NH_3, SO_2, and NO_2
   [b] the temperature or humidity exceeds those recommended by ROHM
   [c] the Products are exposed to direct sunshine or condensation
   [d] the Products are exposed to high Electrostatic

2. Even under ROHM recommended storage condition, solderability of products out of recommended storage time period may be degraded. It is strongly recommended to confirm solderability before using Products of which storage time is exceeding the recommended storage time period.

3. Store / transport cartons in the correct direction, which is indicated on a carton with a symbol. Otherwise bent leads may occur due to excessive stress applied when dropping of a carton.

4. Use Products within the specified time after opening a humidity barrier bag. Baking is required before using Products of which storage time is exceeding the recommended storage time period.

Precaution for Product Label

A two-dimensional barcode printed on ROHM Products label is for ROHM's internal use only.

Precaution for Disposition

When disposing Products please dispose them properly using an authorized industry waste company.

Precaution for Foreign Exchange and Foreign Trade act

Since concerned goods might be fallen under listed items of export control prescribed by Foreign exchange and Foreign trade act, please consult with ROHM in case of export.

Precaution Regarding Intellectual Property Rights

1. All information and data including but not limited to application example contained in this document is for reference only. ROHM does not warrant that foregoing information or data will not infringe any intellectual property rights or any other rights of any third party regarding such information or data.

2. ROHM shall not have any obligations where the claims, actions or demands arising from the combination of the Products with other articles such as components, circuits, systems or external equipment (including software).

3. No license, expressly or implied, is granted hereby under any intellectual property rights or other rights of ROHM or any third parties with respect to the Products or the information contained in this document. Provided, however, that ROHM will not assert its intellectual property rights or other rights against you or your customers to the extent necessary to manufacture or sell products containing the Products, subject to the terms and conditions herein.

Other Precaution

1. This document may not be reprinted or reproduced, in whole or in part, without prior written consent of ROHM.

2. The Products may not be disassembled, converted, modified, reproduced or otherwise changed without prior written consent of ROHM.

3. In no event shall you use in any way whatsoever the Products and the related technical information contained in the Products or this document for any military purposes, including but not limited to, the development of mass-destruction weapons.

4. The proper names of companies or products described in this document are trademarks or registered trademarks of ROHM, its affiliated companies or third parties.

© 2015 ROHM Co., Ltd. All rights reserved.

General Precaution

1. Before you use our Products, you are requested to carefully read this document and fully understand its contents. ROHM shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any ROHM's Products against warning, caution or note contained in this document.

2. All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sales representative.

3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate and/or error-free. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.

© 2015 ROHM Co., Ltd. All rights reserved.