1.5 A Low Dropout Linear Regulator


The NCP565/NCV565 low dropout linear regulator will provide 1.5 A at a fixed output voltage or an adjustable voltage down to 0.9 V. The fast loop response and low dropout voltage make this regulator ideal for applications where low voltage and good load transient response are important. Device protection includes current limit, short circuit protection, and thermal shutdown.

Features

- Ultra Fast Transient Response (<1.0 µs)
- Low Ground Current (1.5 mA at Iload = 1.5 A)
- Low Dropout Voltage (0.9 V at Iload = 1.5 A)
- Low Noise (28 µVrms)
- 0.9 V Reference Voltage
- Adjustable Output Voltage from 7.7 V down to 0.9 V
- 1.2 V, 1.5 V, 2.8 V, 3.0 V, 3.3 V Fixed Output Versions. Other Fixed Voltages Available on Request
- Current Limit Protection (3.3 A Typ)
- Thermal Shutdown Protection (160°C)
- NCV Prefix for Automotive and Other Applications Requiring Site and Change Controls
- Pb-Free Packages are Available

Typical Applications

- Servers
- ASIC Power Supplies
- Post Regulation for Power Supplies
- Constant Current Source




уу	=	Voltage Rating 12 = 1.2 V	Tab = V _{out} Pin 1. Grou
А	=	Assembly Location	2. V _{out}
Y	=	Year	3. V _{in}
W	=	Work Week	
•	=	Pb-Free Package	

(Note: Microdot may be in either location)

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 13 of this data sheet.

Ground








Figure 2. Typical Application Schematic, Adjustable Output

PIN DESCRIPTION

D ² PAK 5	D ² PAK 3	DF	N6	SOT-223		
Pin No. Adj. Version	Pin No. Fixed Version	Pin No. Adj. Version	Pin No. Fixed Version	Pin No. Fixed Version	Symbol	Description
1	-	1, 2	1, 2, 5	-	N.C.	-
2	1	3	3	3	V _{in}	Positive Power Supply Input Voltage
3, Tab	2, Tab	6	6	1	Ground	Power Supply Ground
4	3	4	4	2, Tab	V _{out}	Regulated Output Voltage
5	-	5	-	-	Adj	This pin is to be connected to the sense resistors on the output. The linear regulator will attempt to maintain 0.9 V between this pin and ground. Refer to the Application Information section for output voltage setting.






Figure 4. Block Diagram, Adjustable Output

ABSOLUTE MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Input Voltage (Note 1)	V _{in}	18	V
Output Pin Voltage	V _{out}	–0.3 to V _{in} + 0.3	V
Adjust Pin Voltage	V _{adj}	–0.3 to V _{in} + 0.3	V

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

NOTE: This device series contains ESD protection and exceeds the following tests:

Human Body Model JESD 22-A114-B Machine Model JESD 22-A115-A

THERMAL CHARACTERISTICS

Rating	Symbol	Value	Unit
Thermal Characteristics SOT-223 (Notes 1, 2) Thermal Resistance, Junction-to-Ambient Thermal Resistance, Junction-to-Pin	${f R}_{ heta JA} \ {f R}_{ heta JP}$	107 12	°C/W
Thermal Characteristics DFN6 (Notes 1, 2) Thermal Resistance, Junction-to-Ambient Thermal Resistance, Junction-to-Pin	$R_{ heta JA} \ R_{ heta JP}$	176 37	°C/W
Thermal Characteristics D ² PAK (5ld) (Notes 1, 2) Thermal Resistance, Junction-to-Case Thermal Resistance, Junction-to-Ambient Thermal Resistance, Junction-to-Pin	R _{θJC} R _{θJA} R _{θJP}	3 105 4	°C/W

OPERATING RANGES


Rating	Symbol	Value	Unit
Operating Input Voltage (Note 1)	V _{in}	V _{out} + V _{DO} , 2.5 (Note 3) to 9	V
Operating Junction Temperature Range	TJ	-40 to 150	°C
Operating Ambient Temperature Range	T _A	-40 to 125	°C
Storage Temperature Range	T _{stg}	–55 to 150	°C

1. Refer to Electrical Characteristics and Application Information for Safe Operating Area.2. As measured using a copper heat spreading area of 50 mm², 1 oz copper thickness.3. Minimum $V_{in} = (V_{out} + V_{DO})$ or 2.5 V, whichever is higher.


Characteristic	Symbol	Min	Тур	Max	Unit
ADJUSTABLE OUTPUT VERSION			-	-	
Reference Voltage (10 mA < I_{out} < 1.5 A; V_{out} + 1.6 V < V_{in} < 9.0 V; T_A = -10 to 105°C)	V _{ref}	0.882 (-2%)	0.9	0.918 (+2%)	V
Reference Voltage (10 mA < I_{out} < 1.5 A; V_{out} + 1.6 V < V_{in} < 9.0 V; T_A = -40 to 125°C)	V _{ref}	0.873 (-3%)	0.9	0.927 (+3%)	V
ADJ Pin Current (Note 5)	l _{Adj}	-	30	-	nA
Line Regulation (I _{out} = 10 mA) (Note 5)	Reg _{line}	-	0.03	-	%
Load Regulation (10 mA < I _{out} < 1.5 A) (Note 5)	Reg _{load}	-	0.03	-	%
Dropout Voltage (I _{out} = 1.5 A, V _{out} = 2.5 V) (Note 6)	Vdo	_	0.9	1.3	V
Current Limit	I _{lim}	1.6	3.3	-	Α
Ripple Rejection (120 Hz; I _{out} = 1.5 A) (Note 5)	RR	-	85	-	dB
Ripple Rejection (1 kHz; I _{out} = 1.5 A) (Note 5)	RR	-	75	-	dB
Ground Current (I _{out} = 1.5 A)	I _{GND}	-	1.5	3.0	mA
Output Noise Voltage (f = 100 Hz to 100 kHz, I _{out} = 1.5 A) (Note 5)	V _n	-	28	-	μVrms
Thermal Shutdown Protection (Note 5)	T _{SHD}	-	160	-	°C
FIXED OUTPUT VOLTAGE ($V_{in} = V_{out} + 1.6 \text{ V}$, $T_A = 25^{\circ}\text{C}$, $C_{in} = C_{out} = 150 \mu\text{F}$, unless other the second	nerwise note	ed, Note 4.)		
Output Voltage (10 mA < I _{out} < 1.5 A; 2.8 V < V _{in} < 9.0 V; T _A = -10 to 105°C) 1.2 V version	V _{out}	1.176 (–2%)	1.2	1.224 (+2%)	V
Output Voltage (10 mA < I _{out} < 1.5 A; 2.8 V < V _{in} < 9.0 V; T _A = -40 to 125°C) 1.2 V version	V _{out}	1.164 (-3%)	1.2	1.236 (+3%)	V
Output Voltage (10 mA < I _{out} < 1.5 A; 3.1 V < V _{in} < 9.0 V; T _A = -10 to 105°C) 1.5 V version	V _{out}	1.470 (-2%)	1.5	1.530 (+2%)	V
Output Voltage (10 mA < I _{out} < 1.5 A; 3.1 V < V _{in} < 9.0 V; T _A = -40 to 125°C) 1.5 V version	V _{out}	1.455 (–3%)	1.5	1.545 (+3%)	V
Output Voltage (10 mA < I _{out} < 1.5 A; 4.4 V < V _{in} < 9.0 V; T _A = -10 to 105°C) 2.8 V version	V _{out}	2.744 (-2%)	2.8	2.856 (+2%)	V
Output Voltage (10 mA < I _{out} < 1.5 A; 4.4 V < V _{in} < 9.0 V; T _A = -40 to 125°C) 2.8 V version	V _{out}	2.716 (-3%)	2.8	2.884 (+3%)	V
Output Voltage (10 mA < I _{out} < 1.5 A; 4.6 V < V _{in} < 9.0 V; T _A = -10 to 105°C) 3.0 V version	V _{out}	2.940 (-2%)	3.0	3.060 (+2%)	V
Output Voltage (10 mA < I_{out} < 1.5 A; 4.6 V < V_{in} < 9.0 V; T_A = –40 to 125°C) 3.0 V version	V _{out}	2.910 (-3%)	3.0	3.090 (+3%)	V
Output Voltage (10 mA < I _{out} < 1.5 A; 4.9 V < V _{in} < 9.0 V; T _A = -10 to 105°C) 3.3 V version	V _{out}	3.234 (-2%)	3.3	3.366 (+2%)	V
Output Voltage (10 mA < I _{out} < 1.5 A; 4.9 V < V _{in} < 9.0 V; T _A = -40 to 125°C) 3.3 V version	V _{out}	3.201 (-3%)	3.3	3.399 (+3%)	V
Line Regulation (I _{out} = 10 mA) (Note 5)	Reg _{line}	-	0.03	-	%
Load Regulation (10 mA < I _{out} < 1.5 A) (Note 5)	Reg _{load}	-	0.03	-	%
Dropout Voltage (I _{out} = 1.5 A, V _{out} = 2.5 V) (Note 6)	Vdo	-	0.9	1.3	V
Current Limit	l _{lim}	1.6	3.3	-	Α
Ripple Rejection (120 Hz; I _{out} = 1.5 A) (Note 5)	RR	-	85	-	dB
Ripple Rejection (1 kHz; I _{out} = 1.5 A) (Note 5)	RR	-	75	-	dB
Ground Current (I _{out} = 1.5 A)	I _{GND}	-	1.5	3.0	mA
Output Noise Voltage (f = 100 Hz to 100 kHz, V _{out} = 1.2 V, I _{out} = 1.5 A) (Note 5)	Vn	-	38	-	μVrms
Thermal Shutdown Protection (Note 5)	T _{SHD}	_	160	_	°C

Performance guaranteed over specified operating conditions by design, guard banded test limits, and/or characterization, production tested at T_J = T_A = 25°C. Low duty cycle pulse techniques are used during testing to maintain the junction temperature as close to ambient as possible.
 Typical values are based on design and/or characterization.
 Dropout voltage is a measurement of the minimum input/output differential at full load.


TYPICAL CHARACTERISTICS







TYPICAL CHARACTERISTICS



NOTE: Typical characteristics were measured with the same conditions as electrical characteristics.

APPLICATION INFORMATION

The NCP565 low dropout linear regulator provides adjustable voltages at currents up to 1.5 A. It features ultra fast transient response and low dropout voltage. These devices contain output current limiting, short circuit protection and thermal shutdown protection.

Input, Output Capacitor and Stability

An input bypass capacitor is recommended to improve transient response or if the regulator is located more than a few inches from the power source. This will reduce the circuit's sensitivity to the input line impedance at high frequencies and significantly enhance the output transient response. Different types and different sizes of input capacitors can be chosen dependent on the quality of power supply. A 150 μ F OSCON 16SA150M type from Sanyo should be adequate for most applications. The bypass capacitor should be mounted with shortest possible lead or track length directly across the regulator's input terminals.

The output capacitor is required for stability. The NCP565 remains stable with ceramic, tantalum, and aluminumelectrolytic capacitors with a minimum value of 1.0 μ F with ESR between 50 m Ω and 2.5 Ω . The NCP565 is optimized for use with a 150 μ F OSCON 16SA150M type in parallel with a 10 μ F OSCON 10SL10M type from Sanyo. The 10 μ F capacitor is used for best AC stability while 150 μ F capacitor is used for achieving excellent output transient response. The output capacitors should be placed as close as possible to the output pin of the device. If not, the excellent load transient response of NCP565 will be degraded.

Adjustable Operation

The typical application circuit for the adjustable output regulators is shown in Figure 2. The adjustable device develops and maintains the nominal 0.9 V reference voltage between Adj and ground pins. A resistor divider network R1 and R2 causes a fixed current to flow to ground. This current creates a voltage across R1 that adds to the 0.9 V across R2 and sets the overall output voltage.

The output voltage is set according to the formula:

$$V_{out} = V_{ref} \times \left(\frac{\text{R1} + \text{R2}}{\text{R2}} \right) - I_{Adj} \times \text{R2}$$

The adjust pin current, I_{Adj} , is typically 30 nA and normally much lower than the current flowing through R1 and R2, thus it generates a small output voltage error that can usually be ignored.

Load Transient Measurement

Large load current changes are always presented in microprocessor applications. Therefore good load transient performance is required for the power stage. NCP565 has the feature of ultra fast transient response. Its load transient responses in Figures 13 through 16 are tested on evaluation board shown in Figure 19. On the evaluation board, it consists of NCP565 regulator circuit with decoupling and filter capacitors and the pulse controlled current sink to obtain load current transitions. The load current transitions are measured by current probe. Because the signal from current probe has some time delay, it causes un–synchronization between the load current transition and output voltage response, which is shown in Figures 13 through 16.




Figure 19. Schematic for Transient Response Measurement

PCB Layout Considerations

Good PCB layout plays an important role in achieving good load transient performance. Because it is very sensitive to its PCB layout, particular care has to be taken when tackling Printed Circuit Board (PCB) layout. The figures below give an example of a layout where parasitic elements are minimized. For microprocessor applications it is customary to use an output capacitor network consisting of several capacitors in parallel. This reduces the overall ESR and reduces the instantaneous output voltage drop under transient load conditions. The output capacitor network should be as close as possible to the load for the best results. The schematic of NCP565 typical application circuit, which this PCB layout is base on, is shown in Figure 20. The output voltage is set to 3.3 V for this demonstration board according to the feedback resistors in the Table 1.




Figure 20. Schematic of NCP565 Typical Application Circuit




Figure 21. Top Layer




Figure 22. Bottom Layer




Figure 23. Silkscreen Layer

ltem	Used #	Component	Designators	Suppliers	Part Number
1	4	Radial Lead Aluminum Capacitor 150 μF/16 V	C1, C2, C3, C5	Sanyo Oscon	16SA150M
2	1	Radial Lead Aluminum Capacitor 10 μF/10 V	C4	Sanyo Oscon	10SL10M
3	1	SMT Chip Resistor (0805) 15.8 K 1%	R2	Vishay	CRCW08051582F
4	1	SMT Chip Resistor (0805) 42.2 K 1%	R1	Vishay	CRCW08054222F
5	1	SMT Ceramic Capacitor (0603) 5.6 pF 10%	C6	Vishay	VJ0603A5R6KXAA
6	1	NCP565 Low Dropout Linear Regulator	U1	ON Semiconductor	NCP565D2TR4

Table 1. Bill of Materials for NCP565 Adj Demonstration Board

Protection Diodes

When large external capacitors are used with a linear regulator it is sometimes necessary to add protection diodes. If the input voltage of the regulator gets shorted, the output capacitor will discharge into the output of the regulator. The discharge current depends on the value of the capacitor, the output voltage and the rate at which V_{in} drops. In the NCP565 linear regulator, the discharge path is through a large junction and protection diodes are not usually needed. If the regulator is used with large values of output capacitance and the input voltage is instantaneously shorted to ground, damage can occur. In this case, a diode connected as shown in Figure 24 is recommended.





Figure 24. Protection Diode for Large Output Capacitors

Thermal Considerations

This series contains an internal thermal limiting circuit that is designed to protect the regulator in the event that the maximum junction temperature is exceeded. This feature provides protection from a catastrophic device failure due to accidental overheating. It is not intended to be used as a substitute for proper heat sinking. The maximum device power dissipation can be calculated by:

$$P_{D} = \frac{T_{J}(max) - T_{A}}{R_{\theta}JA}$$




ORDERING INFORMATION


Device	Nominal Output Voltage**	Package	Shipping [†]
NCP565D2T		D ² PAK 5	
NCP565D2TG		D ² PAK 5 (Pb-Free)	50 Units / Tube
NCP565D2TR4	Adj	D ² PAK 5	
NCP565D2TR4G		D ² PAK 5 (Pb-Free)	800 / Tape & Reel
NCP565MNADJT2G		DFN6 (Pb-Free)	3000 / Tape & Reel
NCP565D2T12		D ² PAK 3	
NCP565D2T12G		D ² PAK 3 (Pb–Free)	50 Units / Tube
NCP565D2T12R4		D ² PAK 3	
NCP565D2T12R4G	Fixed (1.2 V)	D ² PAK 3 (Pb–Free)	800 / Tape & Reel
NCP565MN12T2G		DFN6 (Pb-Free)	3000 / Tape & Reel
NCP565ST12T3G		SOT-223 (Pb-Free)	4000 / Tape & Reel
NCP565MN15T2G	Fixed (1.5 V)	DFN6 (Pb-Free)	3000 / Tape & Reel
NCP565MN28T2G	Fixed (2.8 V)	DFN6 (Pb-Free)	3000 / Tape & Reel
NCP565MN30T2G	Fixed (3.0 V)	DFN6 (Pb-Free)	3000 / Tape & Reel
NCP565D2T33G		D ² PAK 3 (Pb–Free)	50 Units / Tube
NCP565D2T33R4G	Fixed (3.3 V)	D ² PAK 3 (Pb–Free)	800 / Tape & Reel
NCP565MN33T2G		DFN6 (Pb-Free)	3000 / Tape & Reel
NCV565D2TG*	6 -di	D ² PAK 5	50 Units / Tube
NCV565D2TR4G*	Adj	(Pb-Free)	800 / Tape & Reel
NCV565D2T12R4G*	5	D ² PAK 3 (Pb–Free)	800 / Tape & Reel
NCV565ST12T3G*		SOT–223 (Pb–Free)	4000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.
*NCV prefix is for automotive and other applications requiring site and change controls.
**For other fixed output versions, please contact the factory. The max Vout available for SOT-223 is 1.2 V.


PACKAGE DIMENSIONS

D²PAK 3 **D2T SUFFIX** CASE 936-03 **ISSUE C**





SOLDERING FOOTPRINT*




- NOTES: 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. 2. CONTROLLING DIMENSION: INCH. 3. TAB CONTOUR OPTIONAL WITHIN DIMENSIONS A AND K. 4. DIMENSIONS U AND V ESTABLISH A MINIMUM MOUNTING SURFACE FOR TERMINAL 4. 5. DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH OR GATE PROTRUSIONS. MOLD FLASH AND GATE PROTRUSIONS NOT TO EXCEED 0.025 (0.635) MAXIMUM.

	INCHES		MILLIMETER	
DIM	MIN	MAX	MIN	MAX
Α	0.386	0.403	9.804	10.236
В	0.356	0.368	9.042	9.347
С	0.170	0.180	4.318	4.572
D	0.026	0.036	0.660	0.914
Е	0.045	0.055	1.143	1.397
F	0.051	REF	1.295	5 REF
G	0.100	BSC	2.540) BSC
Н	0.539	0.579	13.691	14.707
ſ	0.125	MAX	3.175	MAX
Κ	0.050	REF	1.270) REF
L	0.000	0.010	0.000	0.254
М	0.088	0.102	2.235	2.591
Ν	0.018	0.026	0.457	0.660
Ρ	0.058	0.078	1.473	1.981
R	5°F	REF	5°	REF
S	0.116	REF	2.946	6 REF
U	0.200	MIN	5.08) MIN
٧	0.250) MIN	6.35	D MIN

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PACKAGE DIMENSIONS

D²PAK 5 CASE 936A-02 **ISSUE C**




*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

NOTES:
 DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 CONTROLLING DIMENSION: INCH.
 TAB CONTOUR OPTIONAL WITHIN DIMENSIONS A AND K.
 DIMENSIONS U AND V ESTABLISH A MINIMUM MOUNTING SURFACE FOR TERMINAL 6.
 DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH OR GATE PROTRUSIONS. MOLD FLASH AND GATE PROTRUSIONS NOT TO EXCEED 0.025 (0.635) MAXIMUM.

	INC	HES	MILLIN	IETERS	
DIM	MIN	MAX	MIN	MAX	
Α	0.386	0.403	9.804	10.236	
в	0.356	0.368	9.042	9.347	
С	0.170	0.180	4.318	4.572	
D	0.026	0.036	0.660	0.914	
E	0.045	0.055	1.143	1.397	
G	0.067	BSC	1.702	BSC	
Н	0.539	0.579	13.691	14.707	
к	0.050	REF	1.270 REF		
L	0.000	0.010	0.000	0.254	
М	0.088	0.102	2.235	2.591	
Ν	0.018	0.026	0.457	0.660	
Р	0.058	0.078	1.473	1.981	
R	5°F	REF	5° REF		
S	0.116	REF	2.946 REF		
U	0.200 MIN		5.080 MIN		
v	0.250	MIN	6.350) MIN	
U1	0.297	0.305	7.544	7.747	
V1	0.038	0.046	0.965	1.168	

PACKAGE DIMENSIONS

SOT-223 (TO-261) CASE 318E-04 ISSUE N



 DIM
 MIII

 A
 1.50

 A1
 0.02

 b
 0.60

 b1
 2.90


 c
 0.24

 D
 6.30

 E
 3.30

 e
 2.20


 e1
 2.90



NOTES: 6. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994. 7. CONTROLLING DIMENSION: INCH.

	MILLIMETERS			MILLIMETERS INCHES		
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	1.50	1.63	1.75	0.060	0.064	0.068
A1	0.02	0.06	0.10	0.001	0.002	0.004
b	0.60	0.75	0.89	0.024	0.030	0.035
b1	2.90	3.06	3.20	0.115	0.121	0.126
С	0.24	0.29	0.35	0.009	0.012	0.014
D	6.30	6.50	6.70	0.249	0.256	0.263
E	3.30	3.50	3.70	0.130	0.138	0.145
е	2.20	2.30	2.40	0.087	0.091	0.094
e1	0.85	0.94	1.05	0.033	0.037	0.041
L	0.20			0.008		
L1	1.50	1.75	2.00	0.060	0.069	0.078
ΗE	6.70	7.00	7.30	0.264	0.276	0.287
θ	0°	-	10°	0°	-	10°


SOLDERING FOOTPRINT



PACKAGE DIMENSIONS

DFN6, 3x3.3, 0.95 PITCH CASE 506AX-01

ISSUE O




NOTES:

- . DIMENSIONS AND TOLERANCING PER ASME Y14.5M, 1994.
- Y14.5M, 1994.
 2. CONTROLLING DIMENSION: MILLIMETERS.
 3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.25 AND 0.30 mm
- FROM TERMINAL.
- 4. COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.

	MILLIMETERS				
DIM	MIN	NOM	MAX		
Α	0.80		0.90		
A1	0.00		0.05		
A3	0	.20 REF			
b	0.30		0.40		
D	3.00 BSC				
D2	1.90		2.10		
Е	3	.30 BSC	;		
E2	1.10		1.30		
е	0	.95 BSC	;		
к	0.20				
L	0.40		0.60		
L1	0.00		0.15		

SOLDERING FOOTPRINT*



*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

The product described herein (NCP565), may be covered by one or more of the following U.S. patents: 5,920,184; 5,834,926. There may be other patents pending.

ON Semiconductor and are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use performance is and sole provided in an equation of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5773-3850 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative