Applicable Cylinder Series

Applicable Cylinder Series 1

	Cylinder series	روادي	21000	CDJ2	JCDM	CDM2	CDM3	1500	500	5003	300	JMDB	MDB	MDB-X1184	MDB1	CDA2	CDA2-X1184	CDS1	CDS2	CDOJ	CDU	Social	9	JCDQ			CDQ2			CDQ2-XB14	COR	3	CDOM	
	Bore size	٥4	ø6, ø10, ø16	ø6, ø10, ø16 CDJ2	ø20 to ø40 JCDM	ø20 to ø40 CDM2	ø20 to ø40 CDM3	∞20 to ∞63	ø80, ø100		∞80, ∞100	ø32 to ø100 JMDB	ø32 to ø125 MDB	ø40 to ø100 MDB-X1184	ø32 to ø125 MDB1	ø40 to ø100 CDA2	ø40 to ø100 CDA2-X1184	ø125 to ø200 CDS1	ø125 to ø160 CDS2			to ø20		-	ø12 to ø20	ø25	ø32 to ø100 CDQ2	ø125 to ø160	ø180 to ø200	ø16 to ø63 CDQ2-XB14		ø32 to ø50	ø12 to ø25	ø32 to ø100
\Box	D-H7 D-H7C																																\supset	
	D-H7C				ш							_			\Box						_												Ш	
	D-H7BA		Ш		ш					Ш		_	_		_	_		_	Ш		_	_		_								\perp	\vdash	
-	D-H7NF				ш							_	_		\dashv	_		_			_	_	_	_							\Box	\vdash	\rightarrow	
-	D-H7□W D-G5/K5	_	Н		Н		_			\vdash		\dashv	\dashv	_	\dashv	_		\dashv	Н	_	\dashv	\dashv	_	\dashv	Н	_	_			_	\vdash	\dashv	\dashv	_
ŀ	D-G5BA		Н		Н	-	Н		=	\dashv		\dashv	\dashv		\dashv			\dashv	-		\dashv	\dashv	-	\dashv							\dashv	\dashv	\rightarrow	_
ŀ	D-G59F				Н				=	\dashv		\dashv	\dashv		\neg			\neg			\dashv	\neg	_	\dashv							\dashv	\exists	\rightarrow	
ı	D-G5NT				П							\neg	\neg		\neg						\neg	\neg		\neg								T	\neg	Г
Ī	D-G5 W/K59W																																	Π
	D-G39/K39																																\Box	Ξ
-	D-G39A/K39A				ш							_	_		\Box	_		_			_	_		_		_							_	
-	D-F7/J7 D-J79C				ш							_	_		\dashv	_		_			_	_	_	_							\Box		_	
ŀ	D-579C D-F79F	_	Н		Н	-	Н			\vdash	_	\dashv	\dashv	_	\dashv	\dashv		\dashv	Н	_	\dashv	\dashv	_	\dashv						-	\dashv		-	
-	D-F7BA		\vdash		Н	\vdash				\vdash		\dashv	\dashv		\dashv	\dashv		\dashv	\vdash	\dashv	\dashv	\dashv	-	\dashv					\vdash	\vdash	\dashv		\dashv	
1	D-F7BAV		H		Н	\vdash	Н	Н	Н	\vdash	\dashv	\dashv	\dashv	\dashv	\dashv			\dashv	\vdash	_	\dashv	\dashv	+	\dashv					\vdash	\vdash	\dashv		\dashv	í
1	D-F7BAV D-F7□V		Н		Н	Н						\dashv			\dashv			\dashv	\vdash		\dashv	\dashv	+	\exists					Н	\vdash	\dashv		\dashv	
ı	D-F7NT D-F7□W(V)				П							\neg									\neg													
Sa	D-F7□W(V)											\Box																						
5	D-F5/J5				ш					Ш	_	_			_		_				_	_	_	_									_	
switches	D-F5BA				ш						_	\dashv			\dashv		_				\rightarrow	\dashv	_	\dashv		_					-	\dashv	\rightarrow	_
2	D-F5□W/J59W D-F59F	_	-		Н	-	Н			\vdash	_	\dashv		_	\dashv		\dashv			_	\dashv	\dashv	-	\dashv	_	_	_		-	-	\vdash	\dashv	\dashv	_
anto	D-F5NT				Н		Н			\vdash		\dashv			\dashv				=		\dashv	\dashv	-	\dashv							\dashv	\dashv	\rightarrow	_
a	D-F5NT D-G39C/K39C				Н		Н			\vdash		\dashv			\dashv				_		\dashv	\dashv	_	\dashv							\dashv	\dashv	\dashv	
state	D-M9																													\neg				
	D-M9□V																			╗														
S S	D-M9□W D-M9□WV																																	
თ [D-M9□WV																																	
ŀ	D-M9LE (Normally closed)										_	_		_							_		_											
ŀ	D-M9 EV (Normally closed)										\dashv	_		\dashv			_			_	-	_	_							-				
ŀ	D-M9□A D-M9□AV						=				\dashv	-		\dashv			-		=	-	-	-	-		=	=		=		-				
ŀ	D-Y5/Y6/Y7 -/Y7 -V				т		_				\dashv	_		\dashv			\dashv		=	_	_	_			_			_	_	\dashv			_	_
ŀ	D-Y7BA				Н							\neg							=		\dashv	\neg										\exists	\neg	
ı	D-Y7 W/Y7 WV		П		П	П	П					\neg									\exists	\neg	\neg	\neg							\Box	T	\neg	Г
- [D-Y7□W/Y7□WV D-M5																																	Ξ
	D-M5 W																				\Box												\Box	
-	D-M5□T				ш							_	_		_	_		_			_	_	_	_		_							\vdash	
ŀ	D-P3DWA D-P4DW				\vdash					-	_	\dashv		_	\dashv		_	\dashv			\rightarrow	-	_	\dashv	_						\vdash	\dashv	\rightarrow	_
ŀ	D-F9G/H (Normally closed)				Н		_		_		-	\dashv		_	\dashv		-			_	_	_		\dashv						-			_	
ŀ	D-Y7G/H (Normally closed)			_	Н							\dashv			\dashv				=	_	_	_	_	\dashv	_			_	_	-			_	_
ŀ	D-G5NB				П							_									\dashv	\neg		\neg								\neg	\neg	
ı	D-M9□J		П				П	П		\neg		\neg	\neg		T	\neg		\neg			\exists	\neg	T	\neg								П	T	Г
	D-F7NJ																																	
ļ	D-F6□				Ш							_	_		\perp	_					4	_												
4	D-F8□				ш		_				_	\dashv	_	_	\dashv	_		_	Ш		_			\dashv		_					\Box	\dashv	\dashv	_
ŀ	D-C7/C8 D-C73C/C80C		Н		Н		=				-	\dashv	\dashv	_	\dashv	\dashv	_	\dashv	Н		\dashv	\dashv	-	\dashv	-	_				_	\vdash	\dashv	\rightarrow	_
ŀ	D-B5/B6	_	Н		Н	=	=					\dashv	\dashv		\dashv			\dashv	Н		\dashv	\dashv	\rightarrow	\dashv		_	_				\dashv	\dashv	\rightarrow	_
ŀ	D-B59W				Н		=					\neg	\dashv								\dashv	\neg	\neg									\neg	\neg	
ı	D-A3/A4		П				П			\neg		\neg			\neg						\neg	\neg	T	\neg								T	\neg	Т
္တ	D-A3□A/A44A D-A3□C/A44C																																	
tches	D-A3 C/A44C																				\Box	\Box												
۲ı	D-A7/A8 D-A7□H/A80H	_	Ш		\vdash	Ш	\vdash	\vdash		\square	_	_	_	_	_	_		_	Ш	_	_	_	_	_					\vdash	\sqcup	\Box		\dashv	
S	D-A72C/A80H		Н		Н	Н	Н	\vdash		\vdash	\dashv	\dashv	-	\dashv	\dashv	-		\dashv	\vdash	-	\dashv	-	\dashv	\dashv					\vdash	\vdash	\vdash		\dashv	
auto swi	D-A73C/A80C D-A79W		Н		Н	Н	Н			\vdash	\dashv	\dashv	\dashv	\dashv	\dashv	\dashv	-	\dashv	\vdash	-	\dashv	\dashv	\dashv	\dashv					Н	\vdash	\vdash		\dashv	
B	D-A5/A6	-	H		Н	H	Н	Н	Н	\vdash		\dashv			\dashv					_	\dashv	\dashv	\dashv	\dashv					H	H	\vdash		\dashv	
8	D-A5/A6 D-A59W				Г																	_	_†	_								コ		
r	D-A9											\Box																						
	D-A9□V				┙							_]																						
-	D-E7□A/E80A D-Z7/Z8 D-P7	_	Ш		\vdash	Ш	\vdash	\vdash	Ш	\square	_	_		_			_			_	_	_	_	_	\square	_	_			\sqcup	\square	\rightarrow	_	_
-	D-Z//Z8		Н		Н	Н	Н	\vdash	H	\vdash	\dashv	-		\dashv			-			-	\dashv	-	\dashv	\dashv	\vdash	_				\vdash	\vdash	\dashv	\dashv	
1	D-P7 D-B3	-	H	Н	Н	H	Н	Н	Н	\vdash		-	\dashv		\dashv	\dashv		\dashv	\vdash		\dashv	\dashv	\dashv	\dashv	\vdash	-	-	Н	H	H	\vdash	\dashv	+	_
	5 50		Н	Н			6			_	,						4	$\overline{}$			6	_		_	Н				Н		_	_		_
_							,		-		٠ I	1-1	1.2		/	7/	۷.	1.7	ا ۲۲	~	~	- 0	- 1										ĕ	•
۸۵	tuator naga reference	ĕ	, I	4	5	16	8	8	ĭ	,	5	8	8	5	&	81	55	2	120	55	9	8	3	13			92			92	8	३ ।		5
Ac	tuator page reference Best Pneumatics No.)	Š	6 -1 P.21	@ -1 P.41	@ -1 P.153	@ -1 P.167	@ -1 P.269	4 0 007	7.	1 0 262	5	@ -1 P.377	@ -1 P.387	@ -1 P.433	@ -1 P.435	@ -1 P.465	@ -1 P.524	@ -1 P.527	@ -1 P.565	@ -1 P.593	@ -1 P.619	0.1 D 687	5	@ -1 P.753			@ -1 P.763			Ø -1 P.763	0.1 D 081	6	@ -1 P.1005	

				S	ņ																–	Ņ																	
	Cylinder series	CDQU	MDU	CDJ5-S	CDG5-S	2	9	HYDQ	HYDC	HYDG	MY1B	MY1H		MY1B		7	INI T INI	7) -	МҮ1Н	MY1HT	MV4		MY2	MY3	CY3R		CY1S	ᇄ	СУ1Н	CY1F	СУР	MXH	MXS	MXQ	MXQ	MXF	MXW	ΣX
	Bore size	∞20 to ∞40	o25 to o63 MDU	ø10, ø16	∞20 to ∞100	∞20 to ∞63	ø80, ø100	ø20 to ø63 HYDQ	ø32 to ø63 HYDC	o32 to o63 HYDG	ø25 to ø40	ø25 to ø40	ø10 to ø20	ø20	ø63 to ø100	ø16, ø20	ø25 to ø63	ø16, ø20	ø25 to ø63	o10 to o20 MY1H	ø50, ø63	o16, o20	ø25 to ø63	ø16, ø25, ø40 MY2	ø16 to ø63 MY3	∞6 to ∞20	∞25 to ∞63	∞e to ∞40	∞6 to ∞40	ø10 to ø32	ø10, ø15, ø25	o15, ø32	∞6 to ∞20	ø6 to ø25	∞6 to ∞25	∞6 to ∞25	o8 to ∞20	ø8 to ø25	94, 96, 98
	D-H7 D-H7C D-H7BA																										1	_											
-	D-H7C D-H7RA		-	-	H		H												Н		\dashv	_		\dashv	\vdash	\dashv	4	\dashv	_				_	_			\vdash	Н	\vdash
ł	D-H7NF			т			\vdash												Н		\dashv	_		\dashv		_	\forall	\forall		_							\Box	Н	Г
	D-H7□W																										1	\Box											
-	D-G5/K5 D-G5BA		-	_						_									Н		\dashv	_		\dashv	\vdash	_	-	\dashv	_	_					_		Н	Н	\vdash
ł	D-G59F			\vdash						Н									Н		\dashv	-		\dashv		_	\pm	\dashv	_	_					Н		\vdash	Н	Н
	D-G5NT																																						
-	D-G5□W/K59W D-G39/K39		_	⊢	-		_		_	_	_	_							-		_	_		_	\vdash	-	+	\dashv	_	_			_		_		\vdash	Н	\vdash
1	D-G39A/K39A		\vdash	\vdash	\vdash		\vdash		_	Н		_	Н						Н		\dashv	\exists		\dashv	\dashv	_	\pm	+					_		Н		\vdash	Н	\vdash
l	D-F7/J7																																						
	D-J79C		_	_	_																_	_		_	\Box	_	4	4									Ш	Ш	\vdash
	D-F79F D-F7BA	\vdash	\vdash	+	+		\vdash	\vdash	-	\vdash	-	-	Н	\vdash	-	Н	\vdash	Н	Н		\dashv	\dashv	\vdash	\dashv	\dashv	\dashv	+	\dashv		-	\vdash	H	-	Н	\vdash	\vdash	Н	Н	
	D-F7BA D-F7BAV																										#												
	D-F7□V D-F7NT	H	H	\perp	H		L	\vdash	_	L	_		H	H		H	H		\sqcup	-	4	4	H	_	\dashv		4	4					_		H	\vdash	H	Ц	\vdash
S	D-F7\\\\\(\V)		\vdash	+	\vdash		\vdash			Н	_		Н	_		Н	_		\vdash		\dashv	-		\dashv	\vdash	\dashv	+	\pm					_	_	Н		\vdash	Н	\vdash
흥	D-F7□W(V) D-F5/J5																											\equiv											
switches	D-F5BA D-F5□W/J59W		_	⊢	-		_		_		_	_							Н		_	_		_	\vdash	_	+	+	_	_			_				Н	Н	\vdash
OS	D-F59F		\vdash	+	\vdash		\vdash			Н	_		Н	_		Н	_		\vdash		\dashv	-		\dashv	\vdash	\dashv	+	+					_	_	Н		\vdash	Н	\vdash
Solid state auto	D-F5NT																										I	I											
욡	D-G39C/K39C		_	⊢	_		_			_											_	_				_	_	_							_			\Box	_
st	D-M9 D-M9□V			Н	-					Н			=		=	=			=		\dashv	_				-	-		-	-	=			=	=				
릙	D-M9□W																																						
ŭ	D-M9□WV																										_												
1	D-M9 E (Normally closed)			Н	-					Н			=		=	=			=		\dashv	_				_	-		\dashv	-	=			=	=				
ı	D-M9□EV (Normally closed) D-M9□A																																						
	D-M9∟AV				_		_			_											_					_	_	-	_										
1	D-Y5/Y6/Y7□/Y7□V D-Y7BA	H	-	\vdash	-				_	Н	_	_								-		-		\dashv	\vdash	-	-	+	\dashv	_			_		Н		\vdash	Н	\vdash
ı	D-Y7BA D-Y7□W/Y7□WV																											⇉											
	D-M5 D-M5□W		_	_	┞		_			_									Ш	_	_	_		_	\Box	_	_	\dashv	_						_		Н	Ш	\vdash
1	D-M5 T		 	\vdash	\vdash		\vdash		_	Н	_	_	Н	_	_	Н	_		Н		\dashv	\dashv		\dashv	\vdash	-	+	+	\dashv	-			_		Н		\vdash	Н	\vdash
ı	D-P3DWA																										⇉	⇉											
	D-P4DW			⊢	⊢		L			L			_	_	_	_			_		_	_					_	4	_	_				_	_				L
ł	D-F9G/H (Normally closed) D-Y7G/H (Normally closed)			Н	\vdash		\vdash		_	Н					=	П			=			=				-	-	-	\dashv			_			_				г
	D-G5NB																									_		_											
-	D-M9□J		-	⊢	-		_		_		_	_		_	_		_		Н		_	-		_	\vdash	-	+	+	-	_			_	_	H		Н	Н	\vdash
ł	D-F7NJ D-F6□		\vdash	$^{+}$	\vdash		\vdash						Н	_		Н	_		Н		\dashv			\dashv	\dashv	_	\pm	\forall							Н		\Box	Н	
	D-F8□																									\Box	\Box	\Box											Г
-	D-C7/C8 D-C73C/C80C		\vdash	⊢	⊢		\vdash		_	H	_	_	Н	_	_		_		Н	_	\dashv	-		\dashv	\vdash	\dashv	+	+	\dashv	_			_	_	H		\vdash	Н	\vdash
ł	D-B5/B6	H	\vdash	\vdash	\vdash					Н											\neg			\neg		_	\forall	\dashv	\exists						Н			Н	Г
	D-B59W																									\Box	4	\Box											⊏
	D-A3/A4 D-A3 \(\D\A/A/A		-	⊢	┢		\vdash		_	H	_	_	Н	_	_	Н	_		Н		\dashv	-		\dashv	\vdash	-	+	+	\dashv	_			_	_	H		\vdash	Н	\vdash
ě	D-A3 A/A44A D-A3 C/A44C		\vdash	T	T					Н									П		\neg	\neg		\neg	\Box	_	\top	\forall							Т			П	Г
auto switches	D-A7/A8																				\Box	\Box				\exists	7										П	П	Ē
S	D-A73C/A80C	\vdash	\vdash	\vdash	\vdash		\vdash	H	-	\vdash	-	-	Н		_	Н	\vdash	H	Н	-	\dashv	-	\vdash	\dashv	\vdash	\dashv	+	+		-	-	H	-	\vdash	\vdash	H	Н	H	-
ğ	D-A73C/A80C D-A79W			İ																							╛	J											
g	D-A5/A6	F	Г	F	Г		Г	П										П	П		\Box			\Box		7	Ţ	7	\Box							П	Д	Д	É
Beed	D-A59W D-A9			\vdash	\vdash	-	\vdash	\vdash	-	\vdash				H	_		\vdash		Н		\dashv						1	J	-			H							
	D-A9□V																										J												
	D-E7 A/E80A	F	Г	Γ	Г															4		4		4		_	J	4	4								Д	П	É
	D-Z7/Z8 D-P7	\vdash	\vdash	+	\vdash	\vdash	\vdash	Н	-	\vdash	_	-	Н			Н		Н		\dashv		\dashv		\dashv	\vdash	\dashv	-	+	\dashv		Н		-	Н		Н	Н	Н	\vdash
	D-B3																										1	╛											
		12	333		93	3	8	88	197	8	83	10:					52					0	2	367	ន	29		8	ᆵ	23	14	199		_	_	2	ıχ	<u>_</u>	2
A	ctuator page reference	Ø-1 P.1021	@-1 P.1033		2 -1 P.1063	}	F-1 P.1084	@ -1 P.1088	@ -1 P.1097	Ø-1 P.1103	@ -1 P.1183	Ø -1 P.1201					@ -1 P.1225					1 0 1330	į l	@ -1 P.1367	@ -1 P.1403	9 -1 P.1459		Ø-1 P.1485	Ø-1 P.1511	@ -1 P.1523	@ -1 P.1541	@ -1 P.1561	@ -2 P.15	@ -2 P.33	@ -2 P.73	@ -2 P.215	@ -2 P.265	@ -2 P.281	230
(: Best Pneumatics No.)	1	ī		Ţ	}	_	<u> </u>	Ξ	를	Ξ	Ξ					፲					5		<u></u>	뒭	<u> </u>		اتم	亰	Ξ	፲	፲	-5	-2	-5	-5	-2	2	@ -2 P.305
		0	0	4 (3		3	0	0	0	0	0					©					G	9	3	0	0) [⊠	©	3	0	3	0	©	0	3	0	0	6

 $\textbf{D-}\square$

Applicable Cylinder Series

Applicable Cylinder Series 2

	Cylinder series	MXP	ΜXΥ	MTS	MGJ	JMGP		MGP-Z			MGP		MGPW	MGO		5 5 M	MGC	MGF	MGZ	MGT	CXZ	CDBXW	CDPXW	TX	5	CXS	CXS	CDLUZ	COLMA COLMA	CDLG		CDL1		MLGC	CDNG	MDWB	MDNB	CDNA2
	Bore size	ø6 to ø16	06,010,012,016 MXY	o8 to ∞40		အ	ø12 to ø20	ø25	ø32 to ø100	020	ø25	932 to 9100	020, 025 032 to 063	a12 to a100 MGO	∞20 to ∞63	∞80 to ∞100	∞20 to ∞50 MGC	040, 063, 0100 MGF	o20 to o80 MGZ	∞63 to ∞100 MGT	ø10, ø15, ø25 CX2	ø10 ø16 to ø32	o10 to o32 CDPXW□	ø12 to ø25		- 1	0 032	010		040 to 040		00100	ø125 to ø160	o20 to o40 MLGC	o20 to o40 CDNG	32 to ø100 MDWB	32 to ø100 MDNB	o40 to o100 CDNA2
I	D-H7 D-H7C D-H7BA D-H7						Ť	_			_	_			Ĩ	Ď		_		Ĭ	_		Ť											Ì			Ĩ	
L	D-H7C		┝	L		┡	\vdash		Н	+	_	+	+	+		Н			_	+	+	+	⊢		\dashv	\dashv	-	+	+		+	+	╀					╄
H	D-H7NF		\vdash	\vdash		\vdash	\vdash	Н	Н	+	+	+	+	+	+	Н			\dashv	+	\pm	+	\vdash	H	\dashv	\dashv	-	+	+		+	+	+			Н	\vdash	+
П	D-H/∐W		\vdash	\vdash					Н	\top	_	+	+	+		Н			\dashv	\top	_	\top	\vdash		\dashv	\dashv	-	+	-		+	$^{+}$	+			Н	\vdash	$^{+}$
Г	D-G5/K5				П	Т	Т		П	T	T	T	\top	T					\neg	T	T		Т	П	\neg	\neg	Т	т	т	т					П		П	
Г	D-G5BA D-G59F									\Box		\Box								\Box									\perp									
L	D-G59F		╙	╙	_	_	_		Ш	4	_	4	\perp	\perp		ш			_	4	4	_	_		_	_	_	4	_	_		╄	╙			Ш		ш
L	D-G5NT		\vdash		_	\vdash	_		Н	+	_	+	+	+		ш			\dashv	+	_	_	\vdash		\dashv	\dashv	-	-	-	4	+	+	Н				_	-
H	D-G30/K30	_	\vdash	\vdash	-	\vdash	\vdash	\vdash	\vdash	+	+	+	+	+	-	Н		-	\dashv	+	-	+	\vdash		\dashv	\dashv	+	+	+	-	+	+	Н	_	Н		-	Н
H	D-G39A/K39A		\vdash			\vdash	\vdash		Н	+	+	+	+	+	+	\vdash	\dashv		\dashv	\pm	+	+	\vdash		\dashv	\dashv	+			+	_	-	_			П	_	f
r	D-G5□W/K59W D-G39/K39 D-G39A/K39A D-F7/J7				Т	Т	Т		П	\top	T	\top	\top	\top	т	П	T		\neg					П		\neg	T	T	_	\top	Т	†	T	П				t
L	D-J/9C									\Box		\Box								_									\perp									Γ
L	D-F79F		┡		_	⊢	_			_	_	4	+	+	_	Ш	_		\dashv	_		_	μ.	Ш		_	_	+	4	+	_	+	╄					L
H	D-F/BA	_	\vdash		\vdash	\vdash	\vdash		Н	+	+	+	+	+	+	Н	-		\dashv	-	-		Н	Н		\dashv	+	+	+	+	+	+	+	Н		Н	_	⊬
H	D-F7DAV	_	\vdash	\vdash	_	\vdash	\vdash	Н	\vdash	+	+	+	+	+	+	\vdash	_	\vdash	\dashv	-	-	-	Н	Н		\dashv	+	+	+	+	+	+	+	Н		Н	\vdash	t
ı	D-F7NT						т		П	\top	_	\top	\top	$^{+}$	\top	П	_		\dashv	-	•		т	Н		\dashv	_	$^{+}$	$^{+}$	$^{+}$	T	$^{+}$	$^{+}$	т				t
	D-F7□W(V)									\Box																			I									Ι
L	D-F79F D-F7BA D-F7BAV D-F7□V D-F7NT D-F7□W(V) D-F5/J5		_			⊢	_			_	_	4	+	+	_	Ш	_		\dashv	_	_	_	\vdash		_	_	_	+	4	-		╄	μ.					4
H	D-F5BA		\vdash		-	\vdash	\vdash		Н	+	-	+	+	+	+	Н	-		\dashv	+	-	_	\vdash		\dashv	\dashv	+	+	+	-	+	+	Н	Н				۰
H	D-F5BA D-F5□W/J59W D-F59F	_	\vdash			\vdash	\vdash		\vdash	+	+	+	+	+	+	Н	-		\dashv	+	+	+	\vdash		\dashv	\dashv	+	+	+	-	+	+	Н	Н				н
H	D-F5NT		\vdash			\vdash	\vdash		Н	\top	+	$^{+}$	+	+	+	Н	_		\dashv	\top	_	\top	\vdash		\neg	\dashv	+	$^{+}$	$^{+}$	-	т	т	Н					т
	D-G39C/K39C																			\Box									I									I
	D-M9											4				Ш					_	\perp					_	1	1			ш						1
L	D-M9□V D-M9□W		Н				Н			-	-	+	+	+	_	Н	_		_		-	_	\vdash		-		-	+	+	+	+	╄	Н					H
H	D-M9□WV		Н		Н		Н			-	-	-	+	+	Н	Н	-		-		+	+	\vdash		-		-	+	+	+	+	+	Н					н
Г	D-M9 F (Normally closed)									_		-	-	т		Н			_		_	\top	\vdash					+	н		т	т	Н					т
r	D-M9□EV (Normally closed) D-M9□A											_			г	П	╗				7	\top	Т				7				Т							П
L	D-M9□A															Ш					_						_	4	4									1
H	D-M9□AV D-Y5/Y6/Y7□/Y7□V				_					-	-	-	+	+	Н	Н	-		-		-	+	⊢		-	-	-	-	+	+	+	+	Н					H
H	D-13/10/17/17V	_	\vdash	\vdash		\vdash	\vdash		Н	-	-		+	-	-	Н	-		-		+	+	\vdash		\dashv	\dashv	-	+	+	-	+	+	Н	Н				н
H	D-Y7BA D-Y7□W/Y7□WV		\vdash			\vdash	\vdash		Н	_			+			Н	_		_		_	\top	\vdash		\neg	\neg		$^{+}$	$^{+}$	-	т	т						т
ı	D-M5					Т	Т		П	T	т	┱	\top	т	Т	П	T	П	╛	┱	7	\top	Т		\neg	╛	7	\top	†	т	т	т	т			П	Т	Т
	D-M5□W									\Box		\perp	\perp	\perp					\Box	\Box						\Box		\perp	I	I								Γ
L	D-M5□T		-			_	_			4	_	_	_	\perp	\perp	Ш	_		\dashv	_	-	_	\vdash		_	\rightarrow	_	+	+	+	_	+	\vdash				_	L
H	D-P3DWA D-P4DW	_	\vdash	\vdash	\vdash	\vdash	\vdash			-	-	-	+	+	+	Н	-		\dashv	-	+	+	\vdash		\dashv	\dashv	+	+	+	+	-	۰	Н	Н				н
H	D-F9G/H (Normally closed)					\vdash					-		+			Н					+	+	\vdash						÷		+	Н						Ħ
r	D-Y7G/H (Normally closed)		П			Т	Т	П	П				\top	т	г	П					7	\top	T	П	\neg	\neg		\top	т	_	Т			г	П			T
	D-Y7G/H (Normally closed) D-G5NB									\Box		\perp	\perp	I					\Box	\Box	\Box				\Box	\Box	\Box					\blacksquare						Γ
	D-M9□J		⊢	L	_	┡	_		Н	-	_	+	+	+	+	Н	_		_	-	-	_	⊢		-	\dashv	_	+	+	+	+	╀	╄	\vdash			L	Ł
H	D-F7NJ D-F6□	_	\vdash			Н	\vdash	Н	Н	+	+	+	+	+	+	Н	\dashv		\dashv	+	+	+	\vdash		\dashv	\dashv	+	+	+	+	+	+	+	Н	Н	Н	\vdash	H
H	D-F6□ D-F8□		\vdash				\vdash		Н	\top	_	$^{+}$	+	+	+	Н	_		\neg	\top	_	\top	\vdash		\neg	\dashv	_	$^{+}$	$^{+}$	+	+	+	+	Н			Н	t
	D-C7/C8 D-C73C/C80C									I		I	T	T						I																		İ
L	D-C73C/C80C									_	_	_	\perp	\perp		Ц			\Box	_	_					\Box	_		4		_	\perp						L
L	D-B5/B6	_	\vdash	⊢		⊢	\vdash		\vdash	+	-	+	+	+		Н			\dashv	+	+	_	\vdash		\dashv	\dashv	-	+	+	+	+	+	Н			Н	H	H
-	D-B59W D-A3/A4	_	\vdash	\vdash	\vdash	\vdash	\vdash	Н	Н	+	+	+	+	+	-	Н			\dashv	+	+	+	\vdash		\dashv	\dashv	+	+	+	+	+	+	Н	_			-	h
H	D-A3 \(\text{A44A} \)		\vdash	\vdash		\vdash	\vdash	Н	Н	\pm	$^{+}$	$^{+}$	+	+	+	Н	_		\dashv	\pm	+		\vdash	Н	\dashv	\dashv	$^{+}$	1	۰	_	_	т	т			П	Т	f
	D-A3 C/A44C																																					I
	D-A7/A8 D-A7□H/A80H					L				_	_	4	\perp	\perp	\perp	П	_			_				Ш		\neg	_	1	1	_	\perp	\perp	\vdash					I
H	D-A7_H/A80H	_	⊢		-	⊢	⊢		Н	+	+	+	+	+	+	Н	-		\dashv	-	-	-	Н	Н		\dashv	+	+	+	+	+	+	⊬	\vdash		H	_	╀
H	D-A/3C/A80C		\vdash	\vdash		⊢	\vdash	Н	\vdash	+	+	+	+	+	+	Н	\dashv		\dashv	-	-	_	_	Н	_	\dashv	+	+	+	+	+	+	+	\vdash		Н	Н	t
f	D-A73C/A80C D-A79W D-A5/A6 D-A59W	Т	T	T	T	T	T	Н	\vdash	+	+	†	\top	t	$^{+}$	\vdash	7		\dashv	$^{+}$	T	\top	T	Н	\dashv	\dashv	1	†	†		t	t		П	П			t
	D-A59W									\Box	1	I	I	Ι		П				\supset	I	\top				╛	\Box	1	I		Г							ſ
ı	D-A9				H	\vdash						1		H		Н		\dashv			+	+	\vdash				-	4										H
H	D-A9□V D-E7□A/E80A				H	\vdash								F		Н		\dashv					+				+	+	-									f
H	D-Z7/Z8			\vdash					Н				+			Н					_		\vdash		\neg			$^{+}$	$^{+}$									t
	D-E7□A/E80A D-Z7/Z8 D-P7											1	\perp	Г							1					⇉	1	1	1	Т	Γ	Г	Г					ľ
Ĺ	D-B3		F	F	L	F	H		Ц	\perp		4		+	+	Ц	4	H	4	4	4	\perp	L	\sqcup	4		+	+	+	+	L		L	H		"	L	H
	tuator page reference Best Pneumatics No.)	@ -2 P.327	@-2 P.355	@ -2 P.375	@ -2 P.401	@ -2 P.409		@ -2 P.423			Ø -2 P.423		@ -2 P.495	Q -2 P.519		Z P.535	@ -2 P.577	@ -2 P.595	@ -2 P.607	Ø-2 P.635	9 -2 P.647	@ -2 P.658		0-2 P.709	3	6-2 P.723	1010	CO. 1 7-100	00.7	6- 2 P.010		@ -2 P.830		@ -2 P.853	@ -2 P.863	CAT.ES20-246	@ -2 P.887	O.0 0 017

	Cylinder series	CDLS		CDLQ		RDLQ	MDLU		MLGP		ML1C	BEAB		REAS	REAL	REAH	DEBD	ב ס ט ע	REBH	REC	CDJ2Y	Vaccio	- 600	CDG1Y			CDA2Y		CDQ2Y	CDS2Y	CDM2Y	CDJ2X	CDM2X	X	× 22	CDQ2X	CDUX	RHC	
	Bore size	ø125 to ø200	ø20	ø25	ø32 to ø100	ø32 to ø63	ø25 to ø50				ø25 to ø40		ø25 to ø40	ø10 to ø40	ø10 to ø40 REAL	ø10 to ø32		ø25, ø32	ø15 to ø32	ø20 to ø40 REC		to ø20	-		200, ø100	001 0 01 700		o ø100	o32 to o100	ø125 to ø160 CDS2Y	o20 to o40 CDM2Y	o10 to o16 CDJ2X	o20 to o40 CDM2X	to ø20	ø 25	ø32 to ø100 CDQ2X			∞80 to ∞100
	D-H7 D-H7C D-H7BA																																						
	D-H7C	_			L			Ш	_		_	_	_									_	_		_	+	\perp		L	╙				_	_	_	_		_
	D-H/BA							Н	_	_	_	\dashv	_					_				\dashv	_	_	+	+	+	\vdash		⊢				\dashv	\dashv	_	_		-1
H	D-H7NF D-H7□W	_		\vdash	\vdash	₩	\vdash	Н	-	-	-	\dashv	\dashv	_	_	_	\vdash	\vdash				\dashv	\dashv		+	+	+	\vdash	┢	\vdash				\dashv	\dashv	\dashv	-		\dashv
H	D-G5/K5	\vdash		\vdash	\vdash	\vdash		Н	-	_	-	\dashv	\dashv	_		_	\vdash	\vdash	-			\dashv	\dashv		-	+				\vdash		_		\dashv	\dashv	\dashv	-		_
	D-G5BA							П	\neg			\neg					П				Н	\neg	╛	_	_	т	т	т		T				\neg	\neg		_	_	
	D-G59F																																						
	D-G5NT																																						
	D-G5\(\subseteq \W/K59\W)							Ш				_	_									_			_	_	4								_				
	D-G39/K39		_					Н	_		_	\dashv	_					_			Ш	\dashv	_	_	_	-	-				ш			_	\dashv	_	_		
	D-G39A/K39A	_		_	_			Н	-	_	_	\dashv	\dashv	_	_	_	-	-				\dashv	-	-	+	+	+	\vdash	_	\vdash				\dashv	\dashv	_	-	\dashv	-
ŀ	D-G39A/K39A D-F7/J7 D-J79C	\vdash		\vdash				Н	-	_	-	\dashv	\dashv		=	_	\vdash	\vdash				\dashv	\dashv	-	+	+	+	\vdash		Н	Н			\dashv	\dashv		-	\dashv	\dashv
	D-F79F		\vdash					Н	\dashv		-	\dashv	\dashv				Н			Н		\dashv	7	\dashv	+	+	+	t	۲		Н				\dashv		H	\dashv	\dashv
	D-F7BA D-F7BAV D-F7□V																						J	⇉			I		Г								J		J
	D-F7BAV			Г					\exists				\Box									\Box		\exists	T	T	F								\Box	J		\Box	Д
	D-F7⊔V	_	_					Н	_		_	\dashv	_					_				\dashv	_	_	+	+	+			_				_	_		_	\rightarrow	_
١ ,,	D-F7NI D-E7 W/V		\vdash					Н	\dashv	_	-	\dashv	\dashv			-		Н				\dashv	-	-	+	+	+	\vdash		Н				\dashv	\dashv		-	+	\dashv
ĕ	D-F5/J5		Н			-	_	Н	\dashv		-	\dashv	\dashv	_	_			Н				\dashv	\dashv	+		٠			т	-	Н	_		\dashv	\dashv	_	_	\dashv	\dashv
	D-F5BA		т					П	\neg			\neg	\neg								П	\neg	\dashv	\neg	-	т	т	т			Н			\neg	\neg	\neg	7	\dashv	\exists
switches	D-F7□V D-F7NT D-F7□W(V) D-F5/J5 D-F5BA D-F5□W/J59W																																						
윤	D-F39F																							\Box														\Box	\Box
ᄛ	D-F5NT		_					Н	_		_	\dashv	_					_				_	_	_	_	4	4	L						_	\dashv	_	_	_	_
읥	D-G39C/K39C D-M9	_	_	_				Н	_		-	_	_	_		_		_				_	_	-	-	-	+	Н	_	-				_	_	_	_	_	\dashv
Solid state auto	D-M9□V			Н				Н	-		-	_		_				_		=		-	-	-	-	+	+	Н		Н		=		-	-	-	-		\dashv
掔	D-M9□W								_														_													_	_		\exists
တိ	D-M9 WV																																						
	D-M9 E (Normally closed)																																						\Box
	D-M9 E (Normally closed) D-M9 EV (Normally closed) D-M9 A										_	_	_					_				_	_	_	-	+	+	H		H				_	_	_	_		-1
H	D-M9□AV			Н				Н			-			_		_		_		=		-	-	-	-	+	+	Н	Н	Н		=		-	-	-	-		\dashv
lŀ	D-Y5/Y6/Y7□/Y7□V		т						=		-	\dashv		_			\vdash					_	_	_	-	-			т		П			_	_	_	_	_	\dashv
	D-Y7BA		Т									╛	\neg			\equiv		$\overline{}$			П	\neg	\dashv	_	-	т	т	т			П				\neg	\neg	_	\dashv	\exists
	D-Y7BA D-Y7□W/Y7□WV																																						
	D-M5	_						Ш	_	_		_	_					_			Ш	_	_	4	4	+	+	_		╙				_	_	_	_	4	_
	D-M5□W							Н	_	_	_	\dashv	\dashv					_			Н	\dashv	-	-	_	+	+	\vdash		⊢				\dashv	\dashv	_	_	\rightarrow	-
ŀ	D-M5□T D-P3DWA	\vdash	\vdash				\vdash	Н		_	=	\dashv	\dashv	_				\vdash			Н	\dashv		-	-	٠	٠	-			Н			\dashv			-	\dashv	\dashv
1	D-P4DW	\vdash				Н		Н	_		\neg	\dashv	\dashv				\vdash	Н			Н	_	_	_	-	+		Н	т	_	Н			\dashv	\neg		_	\dashv	\dashv
	D-F9G/H (Normally closed)																								т			П		г									\neg
	D-Y / G/H (Normally closed)											\Box										\Box	\Box	\equiv	_		\perp							\Box	\Box			\Box	\Box
	D-G5NB		L	L	L	L	L	Ш	4	_	_	\dashv	_	_			Ц	L			Ш	_	_			+	+	1	L	1			\Box	_	\dashv	4	_		
	D-M9□J	_	_	_		H	-	Н	-	_	-	\dashv	\dashv	_		_	-	-			Н	\dashv	\dashv	-	+	+	+	\vdash	H	⊢				\dashv	\dashv	\dashv	-	+	\dashv
1	D-F7NJ D-F6□			\vdash	\vdash	H		Н	\dashv		\dashv	\dashv	\dashv	-		-	\vdash	\vdash		Н	Н	\dashv	\dashv	+	+	+	+	+	\vdash	+	\vdash			\dashv	\dashv	\dashv	-	+	\dashv
1	D-F8□							Н	_			\neg	\neg					-			Н	\neg	\neg	_	\top	+	+	\vdash	Н	\vdash				\neg	\neg	_	_	\dashv	\neg
	D-C7/C8 D-C73C/C80C																								1														╛
	D-C73C/C80C	Ĺ	Ĺ	Ĺ	Ĺ	Ľ	Ĺ	П			_		_				П	Ĺ	Щ			_	_		J	1	\perp		Ĺ					\Box	_		_		J
	D-B5/B6 D-B59W	_	_	-		₩		Н	-	_	-	\dashv	\dashv	_		_	-	-			Н	\dashv	\dashv	-	-	+	+	\vdash	-	⊢				\dashv	\dashv	\dashv	-	-	_
			\vdash	\vdash	\vdash	H		Н	\dashv		\dashv	\dashv	\dashv	-		-	\vdash	\vdash			Н	\dashv	+	7					Н					\dashv	\dashv	\dashv	-		
S	D-A3/A4 D-A3/A/A44A D-A3/A/A44C D-A7/A8 D-A7/A80H D-A730/A/A80C			Т		T		Н	\dashv				\dashv				Н				Н	\dashv	\dashv	\dashv	-				Т							\dashv	7	T	٦
Reed auto switches	D-A3□C/A44C																							⇉													⇉		╛
Įį.	D-A7/A8							П		\Box			_]										\Box	\supset	T	T	F	Г							\Box		_[П
S	D-A7□H/A80H	\vdash	\vdash	\vdash				\vdash	\dashv	-	_	\dashv	\dashv			_	Н	\vdash	\vdash	Н		\dashv	\dashv	+	+	+	+	\vdash		-	\vdash		\vdash	\dashv	\dashv		\dashv	\dashv	\dashv
울	D-A73C/A8UC	\vdash	\vdash	\vdash				Н	\dashv	\dashv	\dashv	\dashv	\dashv			-	\vdash	\vdash		Н		\dashv	\dashv	+	+	+	+	+		-	\vdash		\vdash	\dashv	\dashv		\dashv	+	-
a	D-A79W D-A5/A6			\vdash				H	_	_	\exists	\dashv	\dashv	٦	\vdash		\vdash	\vdash	Н	Н		\dashv	\dashv	+					Г		Н		\vdash	\dashv	-		_	\dashv	\dashv
8	D-A59W					L											П							_†										_		_†	_†	_†	7
۳ ا	D-A9																																						_
	D-A9□V D-E7□A/E80A						_					_	_				\square																						4
	D-E/□A/E80A		\vdash	\vdash	\vdash	\vdash	\vdash					\dashv		۲	Н		Н			Н	Н	\dashv	\dashv	+					\vdash		\vdash	\vdash	\vdash	\dashv	\dashv	\dashv	-	+	\dashv
	D-Z7/Z8 D-P7		\vdash	\vdash	\vdash	H	\vdash				\dashv	\dashv		٦	Н		Н			Н	Н	\dashv	\dashv	+	-				Н		Н	\vdash	\vdash	\dashv	\dashv	\dashv	+	+	\dashv
	D-B3		\vdash	Н		T		H	\dashv			\neg	\dashv				Н		Н	П	Н	\dashv	\dashv	\dashv	+	+	+	\vdash		t	Н	Н			\dashv	\dashv	1	\dashv	\dashv
	•	7		32	_	33	22	Г,	22		ള						_			2	Ξ		Į,	2	9	2		į	0					٥			T	ريا	
Ac	tuator page reference	P.977		@-2 P.1005		@ -2 P.1033	@ -2 P.1057		@ -2 P.1075		Q-2 P.1105			@ -3 P.15				@ -3 P.85		@ -3 P.115	@ -3 P.141		8-3 P.135	í		3		5	-3 P.135					9 -3 P 250	í			9 -3 P.345	:
	: Best Pneumatics No.)	2 P		2 P		2 P	2 P		2 P		2 P			3				3		3 P	片		е. П	5	5	5			,					е В	,			е.	
		0 -5		٥		0	ø		Ġ		0			٥				٥		0	0		Ġ	•	3	9		(Ď					Ġ	•			Ġ)

1579

Applicable Cylinder Series

Applicable Cylinder Series 3

		RZQ		MK		MK2T	CKQG	CLKQG	CKOP	CLKQP	CKG1	CKP1	CLK2G	CLK2P		RSDQ						2	CE1	CE2	ML2B		CVQM	CDVJ5		CDVM5	CDVM5k	CDVM3	CDVM3K	CDV3	CDV3K	CDVS1	Alexan
	Bore size	ø32 to ø63	ø12, ø16	ø20, ø25	ø32 to ø63	∞20 to ∞63	ø50	ø50	∞20	ø 50	ø40 to ø63	ø40 to ø63	ø40 to ø63	∞40 to ∞63	o12	ø16, ø20	ø32, ø40, ø50	ø40, ø50	∞50 to ∞80	ø20, ø32	08, 012, 020, 025, 032	012, 020 012, 020	ø32 to ø63	ø40 to ø100	ø25 to ø40 ML2B	ø32 to ø63	ø32 to ø63	ø10, ø16	ø10, ø16	∞20 to ∞40	ø20 to ø40 CDVM5K	∞20 to ∞40	∞20 to ∞40	ø40 to ø100 CDV3	ø40 to ø63	840 to 8100 CDVS1	ø40 to ø63
٦	D-H7 D-H7C D-H7BA	-		-	-		-			-		-	-	-		-	-		-		-		-	-	-			-			-						-
ı	D-H7C			П						П		\neg	\neg	T	╅	\neg	_		\neg	\neg	╅	\top		T										\neg	T	\top	\top
ı	D-H7BA														\neg		1		\neg	T	\neg												\neg			\neg	\top
ı	D-H7NF												\neg		\neg	\neg	1																			\neg	\top
ı	D-H7□W												\neg		\neg	\neg	_		\neg		\neg	\top	\top	T												\top	\top
ı	D-H7□W D-G5/K5												\neg		\neg	\neg	7	\neg	\neg		\neg	\top	\top								\neg	\neg	\neg				
ı	D-G5BA												\neg		\neg	\neg	T	\neg	\neg		\neg	\top	\top											\neg		\top	\neg
ı	D-G59F														\neg			\neg	\neg	T	\neg												\neg				
ı	D-G5NT												\neg		\neg	\neg	T	\neg	\neg		\neg	\top	\top														
ı	D-G5 W/K59W												\neg		\neg	\neg	T	\neg	\neg		\neg	\top	\top								\neg	\neg	\neg				
ı	D-G5□W/K59W D-G39/K39 D-G39A/K39A														\neg			\neg	\neg		\neg												\neg				
ı	D-G39A/K39A														\neg	\neg		\neg	\neg		\neg			П									\neg	\neg		\top	Т
ı	D-F7/J7 D-J79C																	\neg	\neg		\neg												\neg			\neg	\top
ı	D-J79C																				Т															Т	Т
ı	D-F79F																				Т															Т	Т
ı	D-F7BA																				Т															Т	Т
- [D-F7BAV																				Т															Т	Т
ı	D-F7BAV D-F7□V												\neg		П			\neg			T												\neg			\top	Т
	D-F7NT																				Т															Т	Т
R	D-F7□W(V)																																			\perp	\Box
į	D-F5/J5																																				
es liciliza	D-F5/J5 D-F5BA																																			\perp	
ð	D-F5∟W/J59W												_		_	_		_	_		_												_				
3	D-F59F												_		_	_		_	_		_	_											_			4	4
3	D-F5NT												_		_	_		_	_		_	_											_			4	4
2	D-G39C/K39C		_		_	_	_						_		_	_	_	_	_	_	_	_		╙									_			4	4
3	D-M9														_	_	4	_			4															4	4
š	D-M9□V											_	_	_	_	_	4	_		_	4			L									_		_	-	4
Solla state auto	D-M9□W D-M9□WV											\rightarrow		_	_	_	4	_	_	_	_	_	_		\vdash								_		_	-	4
7	D-M9UWV											_	_	_	_	_	-	_	_	_	4	-	-	H	-								_		_	-	4
-	D-M9 E (Normally closed)											_		_	_	-	-	_	_	_	-	-			-								-		_	-	-
-	D-M9 EV (Normally closed) D-M9 A D-M9 AV D-Y5/Y6/Y7 Y7 V											\rightarrow	\dashv	-	-	-	-	-	_	-	-	-	-	Н	\vdash			_					_		_	-	4
1	D-WI9 AV						-			-		\rightarrow	\dashv	-	-	-	-	-	-		-	-	-		-						_		-		-	-	-
ł	D-W9LAV						\vdash			Н	_	\rightarrow	\dashv	-	-	-	-	-	-		-	_	_		_								-		-	-	-
ł	D-Y7BA			Н	-					Н	_	\rightarrow	\dashv	-	\dashv	+	+	\dashv	\dashv		+	+	+		_			-	_		\vdash	\dashv	-		-	-	-
ł	D-Y7 \BA			Н	-					Н	_	\rightarrow	\dashv	-	\dashv	+	+	\dashv	\dashv		+	+	+		_			-	_	-	\vdash	\dashv	\dashv		_	_	+
ł	D-M5											\rightarrow	\dashv	_	\dashv	\rightarrow	+	\rightarrow	\dashv	_	+	+	+	_		\vdash					\vdash		_		_	-	-
ł	D-M5□W	_	_	Н	_	_	\vdash	\vdash		Н		\rightarrow	\dashv	_	\dashv	+	+	\dashv	\dashv	\rightarrow	+	+	+	+	\vdash								\dashv	\dashv	_	+	+
ł	D-M5□T			Н						Н			\dashv	_	\dashv	$^{+}$	_	\dashv	\dashv	\dashv	$^{+}$	\pm	+	\vdash									\dashv			+	\pm
ł	D-P3DWA									Н					\neg	-		\neg		\rightarrow	$^{+}$	$^{-}$	+	-		\vdash							\neg	\neg		\pm	\pm
Ì	D-P4DW		Т	П										T	\neg		\neg	┪	\neg	\neg	\top	\top		T									\neg			\top	\top
Ì	D-F9G/H (Normally closed)												\neg																								
Ì	D-Y7G/H (Normally closed)				П		П								\neg	\neg	Т	\neg	\neg														\neg				
I	D-G5NB												П			\neg	П	П			Т	Т		П												Т	Т
ĺ	D-M9□J																																			\perp	\exists
I	D-F7NJ																				\perp															\perp	\perp
	D-F6□												_		_	_	_	_	_		4	_		╙									_			\perp	_
l	D-F8□												_		_	_	4	_	_		_	_		_								_	_			\rightarrow	_
ļ	D-C7/C8												_		_	_	_		_		_	_		_												\rightarrow	_
ļ	D-C73C/C80C											_	_		_	_	4		_	_	_	_		╙										_	_	_	_
ļ	D-B5/B6													_	_	-	4	4	_	_	4	_			-										_	-	4
ŀ	D-B59W D-A3/A4				_		_					_	-	_	-	-	4	-	-	_	+	+	+		-								_		_	-	4
ŀ	D-A3/A4				_		_					_	-	_	-	-	4	-	-	_	+	+	+		_							_	_			-	4
ŀ	D-A3 A/A44A D-A3 C/A44C		_	Н	_	_	-			Н		\rightarrow	\dashv	-	\rightarrow	+	\rightarrow	\dashv	\dashv	\rightarrow	+	+	+	-	-					-		\dashv	\rightarrow	_	_	_	4
ŀ	D-A3_C/A44C	_	_	_	_	_	\vdash			Н		\rightarrow	\dashv	_	-	-	-	\rightarrow	\dashv	\rightarrow	+	-		-	-		-				-	\dashv	-		_	-	-
ŀ	D-A7/A8 D-A7□H/A80H		\vdash				\vdash			Н		\rightarrow	\dashv	-	-	-		\dashv	\dashv	\rightarrow	+	-	-	Н	\vdash			=	=	-		\dashv	\dashv	\dashv	-	+	+
ł	D-A73C/A80C	-	\vdash				\vdash			Н		\rightarrow	\dashv	\dashv	-	-	-	\dashv	\dashv	\rightarrow	+	-	-	Н	\vdash					-	\vdash	\dashv	\dashv	\dashv	-	+	+
ł	D-A79W	-	\vdash				\vdash			Н		\rightarrow	\dashv	\dashv	-	-	-	\dashv	\dashv	\rightarrow	+	-	-	Н	\vdash					-	\vdash	\dashv	\dashv	\dashv	-	+	+
ł	D-A75VA		\vdash	П			\vdash			Н		\rightarrow	\dashv	_	-	_	_	\dashv	\dashv	\rightarrow	+	_	_	-				_					\neg				
ŀ	D-A5/A6 D-A59W			Н				\vdash				\dashv	\dashv	-	+	+	$^{+}$	+	\dashv	\dashv	+	+	+			Н		Н		\vdash		\dashv	-				
п	D-40									Н		\dashv								\dashv	-				т												
ŀ	D-A9□V											_		_						7	-1																
ŀ	D-E7 A/E80A							П	П	П		\dashv	\dashv	7	\neg		7	7		\dashv	T	1			Т			П		\Box	П	\neg	7			\top	T
İ	D-Z7/Z8							П				\neg	\neg		\neg	\dashv	7	\neg	\neg		\dashv	\top	\top														
İ	D-A9 V D-E7 A/E80A D-Z7/Z8 D-P7				L										_†	_†	_†				_†		I	Γ												T	\top
J	D-B3												J		ゴ		╛	J				╧	I										J		J	丁	丁
		7		n		9		1			0	6	LC	,		6	Т	D.	6	ū	~	-	9	6	Ξ	2	6		-				\neg	_		•	\top
į	ctuator page reference	@ -3 P.367		@ -3 P.383		@ -3 P.403		2 0 407	"		0 - 2 D 410	Ŧ	0-3 P 445			0 -3 P.559		@ -3 P.575	@ -3 P.589	@ -3 P.605	Ø-3 P.617	2 -3 P.641	@ -3 P.656	@ -3 P.679	@ -3 P.701	@ -3 P.725	@ -3 P.739	0.2 0 750	4		8-3 P 771	:		9-3 D 812	5	@ -3 P.832	
		O.	1	ΔĹ		ıΔ	1		Ľ			Ľ I	Ω			O.		O. I	U.	0.	o li	n. I	0.	١٠.	l n i	n 1	n 1						- 1	-		٠.	- 17
)	: Best Pneumatics No.)	=		_		_			_		_	_				=	- 1	Ξ.	= 1	= 1	≖ι.		=	-	-	=	=	-	- 1		Δ	-		-	- 1	_	- 11

Auto Switch Variations

Auto Switch Variations 1 Auto switch Function Type Electrical entry Auto switch model Page mounting type D-M9N/M9P/M9B* 1591 D-M9NV/M9PV/M9BV* D-F8N/F8P/F8B 1592 D-M9NE/M9PE/M9BE (Normally closed)* 1592-1 D-M9NEV/M9PEV/M9BEV (Normally closed)* Direct Grommet D-F9G/F9H (Normally closed)* 1593 D-Y59A/Y59B/Y7P* 1594 D-Y69A/Y69B/Y7PV** state D-Y7G/Y7H (Normally closed)* 1595 D-M5N/M5P/M5B 1596 Solid a D-H7A1/H7A2/H7B 1597 Grommet D-G59/G5P/K59 1598 Band Connector D-H7C 1599 D-G39/K39 1600 General purpose auto switches Terminal conduit D-G39A/K39A 1601 D-F79/F7P/J79 1602 Grommet Rail D-F7NV/F7PV/F7BV 1603 1604 Connector D-J79C Grommet D-F59/F5P/J59 1605 Tie-rod Terminal conduit D-G39C/K39C 1606 D-A90/A93/A96* 1652 D-A90V/A93V/A96V* Direct Grommet D-Z73/Z76/Z80** 1663 1664 D-E73A/E76A/E80A D-C73/C76/C80 1653 Grommet D-B53/B54/B64 1654 D-C73C/C80C Connector 1655 D-A33/A34 Band 1656 Terminal conduit D-A33A/A34A 1657 **D-A44** 1656 DIN terminal D-A44A 1657 D-A72/A73/A80 1658 Grommet D-A72H/A73H/A76H/A80H 1659 Rail Connector D-A73C/A80C 1660 Grommet D-A53/A54/A56/A64/A67 1661 Terminal conduit D-A33C/A34C Tie-rod

D-A44C

^{**} These auto switches can be mounted with a tie-rod when auto switch mounting brackets are used. Refer to page 1691 for details.



DIN termina


D-

1662

^{*} These auto switches can be mounted with a band, a rail, a tie-rod or a square groove when auto switch mounting brackets are used. Refer to pages 1680, 1684, 1688 and 1696 to 1698 for details.


Auto Switch Variations

Auto Switch Variations 2




^{*} These auto switches can be mounted with a band, a rail, a tie-rod or a square groove when auto switch mounting brackets are used. Refer to pages 1680, 1684, 1688 and 1696 to 1698 for details.

^{**} These auto switches can be mounted with a tie-rod when auto switch mounting brackets are used. Refer to page 1691 for details.









D-□



D-MAX BE BE CE .

Prior to UseAuto Switches Common Specifications 1

Refer to the Auto Switch Precautions on pages 8 to 12 before using auto switches.

Auto Switches Common Specifications

Туре	Reed auto switch	Solid state auto switch
Leakage current	None	3-wire: 100 µA or less, 2-wire: 0.8 mA or less
Operating time	1.2 ms	1ms or less *3)
Impact resistance	300 m/s ²	1000 m/s ^{2 *4)}
Insulation resistance	50 $\mbox{M}\Omega$ or more (500 VDC measured via measured via	egohmmeter) (Between lead wire and case)
Withstand voltage	1500 VAC for 1 minute *1) (Between lead wire and case)	1000 VAC for 1 minute (Between lead wire and case)
Ambient temperature	-10 to	o 60°C
Enclosure	IEC60529 Sta	andard IP67 *2)

- * 1) Electrical entry: Connector type (A73C/A80C/C73C/C80C): 1000 VAC/min. (Between lead wire and the case)
- * 2) The terminal conduit type (D-A3/A3□A/A3□C/G39/G39A/G39C/K39/K39A/K39C), DIN terminal type (D-A44/A44A/A44C) and heat resistant auto switch (D-F7NJ) conform to IEC60529 Standard IP63.

The trimmer type amplifier section (D-R□K) conforms to IP40.

- * 3) Excluding the solid state auto switches with a timer (D-M5□T/G5NT/F7NT/F5NT types) and magnetic field resistant 2-color indicator solid state auto switch (D-P3DW□/P4DW). The operating time for D-J51 is 2 ms or less and for D-P3DW□/P4DW are 40 ms or less.
- * 4) 980 m/s2 for the trimmer type sensor section, 98 m/s2 for the amplifier section.

Lead Wire

Lead wire length indication

(Example)

D-M9BW L

Auto switch model

Lead wire length

Symbol	Length	Tolerance	Connector specifications	Solid state	Reed
Nil	0.5 m	±15 mm		•	•
M	1 m	±30 mm		• *2)	• *2)
L	3 m	±90 mm		•	•
Z	5 m	±150 mm		•	• *3)
N *1)	None	-		•	•
SAPC	0.5 m	±15 mm	M8-3 pin	0	_
MAPC	1 m	±30 mm	Plug connector	0	-
SBPC	0.5 m	±15 mm	M8-4 pin	0	-
MBPC	1 m	±30 mm	Plug connector	0	-
SDPC	0.5 m	±15 mm		0	_
MDPC	1 m	±30 mm	M12-4 pin A code (Normal key) Plug connector	0	-
LDPC	3 m	±90 mm	Plug connector	0	-

- ●: Standard ○: Produced upon receipt of order (Standard)
- * 1) Applicable to the connector type (D-□□C) only.
- * 2) Applicable to the D-M9 \Box (V), D-M9 \Box W (V), D-M9 \Box A (V), and D-A93 only
- 3) Applicable to the D-B53/B54, D-C73(C)/C80C, D-A93(V), D-A73(C)/A80C, D-A53/A54, D-Z73, and D-90/97/90A/93A only.
- * 4) For reed auto switches M8 and M12 type with connector, please contact SMC.
- * 5) The standard lead wire length of the trimmer auto switch is 3 m.
- * 6) The standard lead wire length of the solid state auto switch with the timer except for the D-P3DW and D-M9□A (V)□, water-resistant 2-color display solid state auto switch, wide range detection auto switch, heat resistant 2-color display solid state auto switch, and strong magnetic field resistant 2-color display solid state auto switch is 3 m or 5 m. (Product with a lead wire length of 0.5 m is not available.)

Lead wires with a connector indication

Part No. of Lead Wires with Connectors

(Applicable of ity	ioi conficctor type)
Model	Lead wire length
D-LC05	0.5 m
D-LC30	3 m
D-LC50	5 m

Prior to UseAuto Switches Common Specifications 2

Refer to the Auto Switch Precautions on pages 8 to 12 before using auto switches.

Term	Meaning
Hysteresis	A deviation amount between the ON position and OFF position caused by auto switch characteristics (difference in sensitivity between ON and OFF). When the switch is turned ON once and the switch (or piston) is moved in the opposite direction, a symptom occurs that the position where the switch operating position. This deviation amount is called "hysteresis". Note) Hysteresis may fluctuate due to the operating environment. Please contact SMC if hysteresis causes an operational problem.
Most sensitive position	A position (sensor layout position) where the sensitivity is highest on the detection surface of the auto switch enclosure. When the center of the magnet is aligned with this position, this becomes almost the center of the operating range and stable operation can be obtained.
Programmable Logic Controller (PLC)	One of elements making up the sequence control. The PLC is so designed that it receives signals, such as auto switch output and outputs them to other devices so as to perform the electrical control according to the preset program.
Operating temperature range	A temperature range, in which the auto switch can be used. If significant temperature change or freezing occurs even in this temperature range, this may cause the auto switch to malfunction.
Operating voltage	A voltage, at which the auto switch can be used. The operating voltage is indicated using generally used voltage (24 VDC or 100 VAC, etc.). For 2-wire type, the operating voltage has the same meaning as the power supply voltage or load voltage.
Operating current range	A range of the current value that can be flowed to the output of the auto switch. If the operating current is lower than this range, the auto switch does not operate correctly. Conversely, if the operating current is higher than this range, this may cause the auto switch to break.
Current consumption	This current value is necessary for the 3-wire type auto switch to operate the circuit through the power cable. For 2-wire type, as the current consumption is a part of the load current, it is not defined.
Insulation resistance	A resistance between the electric circuit and enclosure. Unless otherwise described particularly, 50 M Ω (Min) is used for auto switch.
Magnetic field resistant auto switch	An auto switch, for which measures against effects arising from external (welding) magnetic field generated in the spot welding process, etc. are taken. The solid state auto switch functions as it detects the frequency of the applied magnetic field. If the external magnetic field (AC) is applied, the last signal is retained not to be affected by the external magnetic field. This system can be used by the cylinder with normal magnetic force. The reed auto switch built-in a magnetic field shielded sensor with a low sensitivity to make the effect of the external magnetic field (DC or AC magnetic field) insusceptible. Therefore, a dedicated cylinder built-in the strong magnet needs to be selected and there is also an operable range (conditions).
Impact resistance value	A minimum acceleration that may cause the auto switch to malfunction or break when the standard impact is applied.
Water-resistant type auto switch	A model, long-term water resistance of which is improved by taking structural measures for the general (general purpose) product.
Withstand voltage	A tolerance dose when the voltage is applied to the portion between the electrical circuit and enclosure. The withstand voltage shows a strength level of the product against the voltage. If a voltage exceeding the withstand voltage is applied, this may cause the product to break. (The voltage described here is different from the power supply voltage necessary to operate the product.)
Proper mounting position	A dimension that shows the mounting position when the position is detected at the stroke end of the cylinder. As this position is set, the maximum sensitivity position is aligned with the center of the magnet. However, make the adjustment with the actual machine by considering the characteristic difference during actual setting. When an adjustment allowance is needed for the detection before the stroke, set a value with an adjustment allowance added to the proper mounting position.
Applicable load	A device that is assumed as a target load of the auto switch.
Operating time	A period of time until the auto switch output becomes stable after the magnetic force to operate the auto switch has been received.
Operating range	An auto switch operating range in response to the cylinder piston movement (ON length in response to the stroke). The operating range is determined by the magnetic force of the magnet (range, in which the magnetic force acts) and switch sensitivity. So, the operating range may vary as these conditions are changed by the ambient environment, etc. The operating range in the standard status (normal temperature, single cylinder, magnetic force, and sensitivity, etc.) is described in the catalog.





Prior to Use Auto Switches Common Specifications 3

Refer to the Auto Switch Precautions on pages 8 to 12 before using auto switches.

Term	Meaning
Minimum Stroke for Auto Switch Mounting	A minimum stroke value of the auto switch that can be mounted on the cylinder. The minimum stroke is determined by the specification limit (auto switch operation or position setting ability, etc.) and physical limit (mechanical interference associated with the auto switch mounting). Note that the catalog shows the value assuming that the position detection is performed at the stroke end and this value does not consider the adjustment allowance. When an adjustment allowance is needed, such as detection before the stroke, a value is set that this adjustment allowance is added to the minimum stroke.
Internal voltage drop	A voltage that is applied to the portion between the COM and signal line when the auto switch is ON. As only a value that the internal voltage drop is subtracted from the power supply voltage is applied to the input side of the PLC, the detection fault (incorrect input) may occur if this value is lower than the minimum operating voltage. So, take great care when selecting a device.
2-Color Indicator	As the end part of the auto switch operating range (boundary between ON and OFF) is an area where is susceptible to the external disturbance or stroke change during cylinder operation, this function is intended to quickly and properly make the setting at the center of the operating range where the stable operation can be obtained by changing the operation indication color of the auto switch.
Load	A device that is connected to the output of the auto switch so as to do any work is called "load". For example, the load is a relay or PLC, etc. To check the operation of the auto switch, a device equivalent to the load (such as resistor, etc.) is connected.
Load current	A current that flows to the load when the ON-OFF output is ON.
Enclosure	A class of protection against solid or water entry of the electrical machinery and apparatus specified in IEC60529. IP— Second characteristic numeral First Characteristics: Degrees of protection against solid foreign objects Non-protected Protected against solid foreign objects of 50 mm ø and greater Protected against solid foreign objects of 12 mm ø and greater Protected against solid foreign objects of 2.5 mm ø and greater Protected against solid foreign objects of 1.0 mm ø and greater Dust-protected Dusttight Second Characteristics: Degrees of protection against water Non-protected Protected against vertically falling water drops Protected against vertically falling water drops Protected against vertically falling water drops when enclosure tilted up to 15° Protected against rainfall when enclosure tilted up to 60° Protected against water jets Protected against water jets Protected against water jets Protected against the effects of temporary immersion in water Protected against the effects of continuous immersion in water Example) In the case of stipulated as IP65, we can know the degrees of protection is dustright and water jet-proof on the grounds that the first characteristic numeral is 5 respectively, that gives it will not be adversely affected by direct water jets from any direction.
Solid state auto switch	A switch that detects the magnetic field by the MR element and incorporates the judgement circuit to turn ON or OFF the output regardless of the contact or non-contact of the mechanical contact like transistor (non-contact part).
Leak current	A current that flows to operate the internal circuit when the ON-OFF output is OFF. In particular, if this leak current exceeds the detection current in the 2-wire type auto switch or PLC, this may cause reset fault. So, take great care when selecting a device.
Reed auto switch	A switch that uses the reed switch to detect the magnetic field and turn ON or OFF the output by the contact or non-contact of the mechanical contact (contact part is provided like relay or limit switch).
Induction load	A load that has the coil. The connection target of the auto switch is a relay.
Recommended lead wire bending radius	A minimum bending radius (reference value) of the lead wire when the lead wire is secured and constructed (oscillation or rotation is not considered). (As the temperature or current value conforms to the auto switch specifications, this lead wire bending radius differs from the value disclosed by the electric wire manufacturer.)
Electrical entry	A structure, in which the lead wire of the auto switch is taken out in the horizontal direction when the cylinder is laid out horizontally (cylinder rod is horizontal), is called "in-line entry". A structure, in which the lead wire is taken out in a direction perpendicular to the cylinder axis center, is called "perpendicular entry".

Prior to Use Auto Switches/Internal Circuit

Solid State Auto Switches

Solid state 3-wire, NPN



Solid state 3-wire, PNP



2-wire (Solid state)




(Power supply for switch and load are separate)



Brown

Reed Auto Switches



No.	(5)	6	7
Circuit diagram	3-wire (Reed switch, NPN) Brown Indicator Best Load Blue	2-wire (Reed switch) Brown 2-Color Control C	2-wire (Reed switch) Brown 2-Color Contact Co

Contact Protection Box/CD-P11, CD-P12

<Applicable switch models>

D-A7/A8, D-A7 H/A80H, D-A73C, A80C, D-C7/C8, D-C73C/C80C, D-E7 A. E80A. D-Z7/Z8. D-9/9 A. D-A9/A9 V. D-A79W

The auto switches above do not have a built-in contact protection circuit. A contact protection box is not required for solid state auto switches due to their construction

- 1. Where the operation load is an inductive load.
- 2. Where the wiring length to load is greater than 5 m.
- 3. Where the load voltage is 100/200 VAC.

Therefore, use a contact protection box with the switch for any of the above cases:

The contact life may be shortened (due to permanent energizing conditions.) D-A72(H) must be used with the contact protection box regardless of load types and lead wire length since it is greatly affected by loads. (Where the load voltage is 110 VAC)

When the load voltage is increased by more than 10% to the rating of applicable auto switches (except D-A73C/A80C/C73C/C80C/90/97/A79W) above, use a contact protection box (CD-P11) to reduce the upper limit of the load current by 10% so that it can be set within the range of the load current range, 110 VAC.


Even for the built-in contact protection circuit type (D-A34[A][C], DA44[A][C], D-A54/A64, D-A59W, D-B59W), use the contact protection box when the wiring length to load is very long (over 30 m) and PLC (Programmable Logic Controller) with a large inrush current is used.

Contact Protection Box Specifications


Part no.	CD-	P11	CD-P12
Load voltage	100 VAC or less	200 VAC	24 VDC
Max. load current	25 mA	12.5 mA	50 mA

*Lead wire length — Auto switch connection side 0.5 m. Load connection side

Contact Protection Box Internal Circuit



Contact Protection Box/Dimensions



Contact Protection Box Connection

To connect a switch unit to a contact protection box, connect the lead wire from the side of the contact protection box marked SWITCH to the lead wire coming out of the switch unit. Keep the switch as close as possible to the contact protection box, with a lead wire length of no more than 1 meter.




Prior to Use Auto Switch Connection and Example


Sink Input Specifications

3-wire, NPN Brown Input Auto switch (PLC internal circuit)

2-wire Brown Input; Auto switch (PLC internal circuit)

Source Input Specifications






Connect according to the applicable PLC input specifications, as the connection method will vary depending on the PLC input specifications.


Example of AND (Series) and OR (Parallel) Connection

When using solid state auto switches, ensure the application is set up so the signals for the first 50 ms are invalid. Depending on the operating environment, the product may not operate properly


3-wire AND connection for NPN output (Using relays)




(Performed with auto switches only)




3-wire OR connection for NPN output




3-wire AND connection for PNP output (Using relays)



(Performed with auto switches only)




3-wire OR connection for PNP output



(Reed)

2-wire AND connection




When two auto switches are connected in series, a load may malfunction because the load voltage will decline when in the ON state. The indicator lights will light up when both of the auto switches are in the ON state. Auto switches with load voltage less than 20V cannot be used.

Load voltage at ON = Power supply voltage Residual voltage x 2 pcs. = 24 V - 4 V x 2 pcs.

Example: Power supply is 24 VDC Internal voltage drop in auto switch is 4 V.

2-wire OR connection



(Solid state) When two auto switches are connected in parallel. malfunction may occur because the load voltage will increase when in the OFF state.

Load voltage at OFF = Leakage current x 2 pcs. x Load impedance = 1 mA x 2 pcs. x 3 kΩ

Example: Load impedance is 3 kΩ Leakage current from auto switch is 1 mA.

SMC

Because there is no current leakage, the load voltage will not increase when turned OFF However, depending on the number of auto switches in the ON state, the indicator lights may sometimes grow dim or not light up, due to the dispersion and reduction of the current flowing to


the auto switches.



Solid State Auto Switches

General Purpose Type, 2-color Indicator, 2-color Indicator with Diagnostic Output, Water Resistant 2-color Indicator, Hygienic Type, Timer Equipped Type, Magnetic Field Resistant Type, Heat Resistant Type, Wide Range Detection Type, Trimmer Auto Switch





Solid State Auto Switch Direct Mounting Type D-M9N(V)/D-M9P(V)/D-M9B(V) **(** € RoHS

Grommet 2-wire load current is reduced (2.5 to 40 mA).

Using flexible cable as standard



∆Caution

Precautions

Fix the auto switch with the existing screw installed on the auto switch body. The auto switch may be damaged if a screw other than the one supplied is used.

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-M9□, D-M9□V (With indicator light)						
Auto switch model	D-M9N	D-M9NV	D-M9P	D-M9PV	D-M9B	D-M9BV
Electrical entry direction	In-line	Perpendicular	In-line	Perpendicular	In-line	Perpendicular
Wiring type		3-w	rire		2-v	vire
Output type	N	PN	PI	NP	-	_
Applicable load		IC circuit, Relay, PLC			24 VDC r	elay, PLC
Power supply voltage	5, 12, 24 VDC (4.5 to 28 V)			_		
Current consumption		10 mA	or less		-	_
Load voltage	28 VDC	or less	-	_	24 VDC (10	to 28 VDC)
Load current		40 mA	or less		2.5 to	40 mA
Internal voltage drop	0.8 V or less at 10 mA (2 V or less at 40 mA) 4 V or less			r less		
Leakage current	100 μA or less at 24 VDC 0.8 mA or less			or less		
Indicator light	Red LED illuminates when turned ON.					
Standard			CE marki	ng, RoHS		

Oilproof Heavy-duty Lead Wire Specifications

Auto swi	tch model			D-M9B(V)		
Sheath	Outside diameter [mm]	2.6		2.6		
	Number of cores	3 cores (Brown/Blue/Black) 2 cores (Brown/B		2 cores (Brown/Blue)		
Insulator	Outside diameter [mm]	0.88				
0	Effective area [mm²]	0.15				
Conductor	Strand diameter [mm]	0.05				
Minimum bending radius	[mm] (Reference values)		17			

Note 1) Refer to page 1584 for solid state auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.

Weight


(g)


(mm)

Auto switch model		D-M9N(V)	D-M9P(V)	D-M9B(V)
	0.5 m (Nil)	8		7
Lead wire length	1 m (M)	14		13
Lead wife leftgill	3 m (L)	4	1	38
	5 m (Z)	68		63

Dimensions

D-M9□





Solid State Auto Switch Direct Mounting Type D-F8N/D-F8P/D-F8B



Refer to SMC website for the details of the products conforming to the international standards.

Grommet



Precautions

Fix the auto switch with the existing screw installed on the auto switch body. The auto switch may be damaged if a screw other than the one supplied is used.

Auto Switch Specifications

	PLC: Programmable Logic Controller			
D-F8□ (With i	ndicator light)			
Auto switch model	D-F8N D-F8P		D-F8B	
Electrical entry direction	Perpendicular	Perpendicular	Perpendicular	
Wiring type	3-w	rire	2-wire	
Output type	NPN	PNP	_	
Applicable load	IC circuit, 24 VI	IC circuit, 24 VDC Relay, PLC		
Power supply voltage	5, 12, 24 VDC (5, 12, 24 VDC (4.5 to 28 VDC)		
Current consumption	10 mA	or less	_	
Load voltage	28 VDC or less		24 VDC (10 to 28 VDC)	
Load current	40 mA or less	80 mA or less	2.5 to 40 mA	
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA load current) 0.8 V or less		4 V or less	
Leakage current	100 μA or less at 24 VDC 0.8 mA or less at 24			
Indicator light	Red LED illuminates when turned ON.			
Standard		CE marking, RoHS		

Oilproof Heavy-duty Lead Wire Specifications

Auto swi	tch model	D-F8N D-F8P		D-F8B
Sheath	Outside diameter [mm]	ø2.7		
Insulator	Number of cores	3 cores (Brown/Blue/Black) 2 cores (Br		2 cores (Brown/Blue)
insulator	Outside diameter [mm]	ø0.91		ø0.96
Conductor	Effective area [mm²]	0.15		0.18
Conductor	Strand diameter [mm]	mm] ø0.08		
Minimum bending radius [mm] (Reference values)		17		

Note 1) Refer to page 1584 for solid state auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.

Weight


(g)

Auto swit	tch model	D-F8N	D-F8P	D-F8B
	0.5 m (Nil)	7		
Lead wire length	3 m (L)		32	
	5 m (Z)		52	

Dimensions

(mm)

D-F8N/D-F8P/D-F8B



Normally Closed Solid State Auto Switch Direct Mounting Type D_MONE(\/\/\D_MODE(\/\/\D_MODE(\/\/\)

D-M9NE(V)/D-M9PE(V)/D-M9BE(V) \in



Grommet

- Output signal turns on when no magnetic force is detected.
- Can be used for the actuator adopted by the solid state auto switch D-M9 series (excluding special order products)





∧Caution

Precautions

Fix the auto switch with the existing screw installed on the auto switch body. The auto switch may be damaged if a screw other than the one supplied is used.

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-M9□E, D-M9□EV (With indicator light)						
Auto switch model	D-M9NE	D-M9NEV	D-M9PE	D-M9PEV	D-M9BE	D-M9BEV
Electrical entry direction	In-line	Perpendicular	In-line	Perpendicular	In-line	Perpendicular
Wiring type		3-w	/ire		2-v	vire
Output type	N	PN	PI	NP	-	-
Applicable load		IC circuit, Relay, PLC			24 VDC r	elay, PLC
Power supply voltage		5, 12, 24 VDC (4.5 to 28 V)				_
Current consumption		10 mA	or less		-	-
Load voltage	28 VDC	or less	-	_	24 VDC (10	to 28 VDC)
Load current		40 mA	or less		2.5 to	40 mA
Internal voltage drop	0.8 V or le	0.8 V or less at 10 mA (2 V or less at 40 mA)			4 V o	r less
Leakage current	100 μA or less at 24 VDC 0.8			0.8 mA	or less	
Indicator light	Red LED illuminates when turned ON.					
Standard			CE marki	ng, RoHS		

Oilproof Heavy-duty Lead Wire Specifications

Auto sw	itch model	D-M9NE(V) D-M9PE(V) D-M9BE		D-M9BE(V)
Sheath	Outside diameter [mm]	2.6		
	Number of cores	3 cores (Brown/Blue/Black) 2 cores (Brown/Bl		2 cores (Brown/Blue)
Insulator	Outside diameter [mm]	0.88		
0	Effective area [mm²]	0.15		
Conductor	Strand diameter [mm] 0.05			
Minimum bending radiu	s [mm] (Reference values)	17		

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight

(g)


(mm)


Auto switch model		D-M9NE(V)	D-M9PE(V)	D-M9BE(V)
7 tato own	0.5 m (Nil)	8		7
	1 m (M)*	14		13
Lead wire length 3 m (L)		41		38
	5 m (Z)*	68		63

^{*} The 1 m and 5 m options are produced upon receipt of order.

Dimensions

D-M9□E









Normally Closed Solid State Auto Switch Direct Mounting Type

D-F9G/D-F9H



Refer to SMC website for the details of the products conforming to the international standards.

Grommet

Output signal turns on when no magnetic force is detected.



∆Caution

Precautions

Fix the auto switch with the existing screw installed on the auto switch body. The auto switch may be damaged if a screw other than the one supplied is used.

Auto Switch Specifications

PLC: Programmable Logic Controller

D-F9G, D-F9H (With indicator light)				
Auto switch model	D-F9G D-F9H			
Wiring type	3-w	rire		
Output type	NPN	PNP		
Applicable load	IC circuit, F	Relay, PLC		
Power supply voltage	5, 12, 24 VDC (4.5 to 28 VDC)		
Current consumption	10 mA	or less		
Load voltage	28 VDC or less	_		
Load current	40 mA or less	80 mA or less		
Internal voltage drop	1.5 V or less	0.8 V or less		
internal voltage drop	(0.8 V or less at 10 mA load current)	0.0 V 01 less		
Leakage current	100 μA or less at 24 VDC			
Indicator light	Red LED illuminates when detecting nothing.			
Standard	CE markir	ng, RoHS		

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-F9G	D-F9H
Sheath	Outside diameter [mm]	ø2.7	
la sudata a	Number of cores	3 cores (Brown/Blue/Black)	
Insulator	Outside diameter [mm] Ø0.91		91
Conductor	Effective area [mm²]	0.15	
Conductor	Strand diameter [mm]	ø0.08	
Minimum bending radius	s [mm] (Reference values)	17	

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.


Weight

(g)

Auto switch model		D-F9G	D-F9H
	0.5 m (Nil)	7	
Lead wire length	3 m (L)	37	
	5 m (Z)	6	1

Dimensions

(mm)





1593



Solid State Auto Switch Direct Mounting Type

D-Y59⁸/D-Y69⁸/D-Y7P(V) **(** €



Grommet

Using flexible cable as standard spec.



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-Y5□, D-Y6□, D-Y7P, D-Y7PV (With indicator light)						
Auto switch model	D-Y59A	D-Y69A	D-Y7P	D-Y7PV	D-Y59B	D-Y69B
Electrical entry direction	In-line	Perpendicular	In-line	Perpendicular	In-line	Perpendicular
Wiring type		3-w	/ire		2-\	vire
Output type	NI	PN	PI	NΡ	-	_
Applicable load		IC circuit, F	Relay, PLC		24 VDC r	elay, PLC
Power supply voltage	5,	5, 12, 24 VDC (4.5 to 28 VDC)			-	_
Current consumption		10 mA or less			_	
Load voltage	28 VDC	28 VDC or less —			24 VDC (10) to 28 VDC)
Load current	40 mA	or less	80 mA	or less	2.5 to 40 mA	
Internal voltage drop	(0.8 V	1.5 V or less (0.8 V or less at 10 mA load current) 0.8 V or less			4 V c	or less
Leakage current	100 μA or less at 24 VDC			0.8 mA or le	ss at 24 VDC	
Indicator light		Red LED illuminates when turned ON.				
Standard			CE marki	ng, RoHS		

Oilproof Flexible Heavy-duty Lead Wire Specifications

Auto switch model D-Y□9A D-Y7P□		D-Y□9B			
Sheath	Outside diameter [mm]	ø3.4			
Inculator	Number of cores	3 cores (Brow	n/Blue/Black)	2 cores (Brown/Blue)	
Insulator	Outside diameter [mm]	ø1.0			
Conductor	Effective area [mm²]		0.15		
Conductor Strand diameter [mm]		ø0.05			
Minimum bending radius	s [mm] (Reference values)		21		

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight


(g)


Auto swit	Auto switch model		D-Y69A	D-Y7P(V)	D-Y59B	D-Y69B
	0.5 m (Nil)	10		9	9		
Lead wire length	3 m (L)	53		5	0		
	5 m (Z)		87		8	3	

Dimensions

D-Y59A/D-Y7P/D-Y59B

(mm)





D-Y69A/D-Y7PV/D-Y69B



Normally Closed Solid State Auto Switch Direct Mounting Type

D-Y7G/D-Y7H



Refer to SMC website for the details of the products conforming to the international standards.

Grommet

- Output signal turns on when no magnetic force is detected.
- Using flexible cable as standard spec.



Auto Switch Specifications

PLC: Programmable Logic Controller D-Y7G, D-Y7H (With indicator light) Auto switch model D-Y7G D-Y7H Wiring type 3-wire Output type NPN PNP Applicable load IC circuit, Relay, PLC 5, 12, 24 VDC (4.5 to 28 VDC) Power supply voltage Current consumption 10 mA or less Load voltage 28 VDC or less Load current 40 mA or less 80 mA or less 1.5 V or less Internal voltage drop 0.8 V or less (0.8 V or less at 10 mA load current) Leakage current 100 μA or less at 24 VDC Indicator light Red LED illuminates when detecting nothing. Standard CE marking, RoHS

Oilproof Flexible Heavy-duty Lead Wire Specifications

Auto swi	tch model	D-Y7G D-Y7H		D-Y7H
Sheath	Outside diameter [mm]	ø3.4		.4
Inculator	Number of cores	3 cores (Brown/Blue/Black)		n/Blue/Black)
Insulator	Outside diameter [mm]	ø1.0		
Conductor	Effective area [mm²]	0.15		15
Conductor	Strand diameter [mm]	ø0.05		05
Minimum bending radius	s [mm] (Reference values)		2	1

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.


Weight

(g)

Auto swit	tch model	D-Y7G	D-Y7H	
	0.5 m (Nil)	10		
Lead wire length	3 m (L)	53		
	5 m (Z)	87		

Dimensions

(mm)







Solid State Auto Switch Direct Mounting Type D-M5N/D-M5P/D-M5B

 $C \in \mathcal{C}$



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.





		PLC: Progra	ammable Logic Controller		
D-M5□ (With indic	cator light)				
Auto switch model	D-M5N	D-M5P	D-M5B		
Wiring type	3-v	vire	2-wire		
Output type	NPN	PNP	_		
Applicable load	IC circuit, F	Relay, PLC	24 VDC Relay, PLC		
Power supply voltage	5, 12, 24 VDC	(4.5 to 28 VDC)	_		
Current consumption	10 mA	or less	_		
Load voltage	28 VDC or less		24 VDC (10 to 28 VDC)		
Load current	40 mA or less	80 mA or less	5 to 40 mA		
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA load current) 0.8 V or less		4 V or less		
Leakage current	100 μA or les	0.8 mA or less at 24 VDC			
Indicator light	Red LED illuminates when turned ON.				
Standard		CE marking, RoHS			

Oilproof Heavy-duty Lead Wire Specifications

Auto swi	tch model	D-M5N D-M5P D-M5E		D-M5B
Sheath	Outside diameter [mm]	ø3.4		
la sulata a	Number of cores	3 cores (Brown/Blue/Black) 2 core		2 cores (Brown/Blue)
Insulator	Outside diameter [mm]	ø1.1		
Conductor	Effective area [mm²]			
Conductor	Strand diameter [mm]			
Minimum bending radius	s [mm] (Reference values)		21	


Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight

(g)

Auto switch model		D-M5N	D-M5P	D-M5B
	0.5 m (Nil)	16		14
Lead wire length	Lead wire length 3 m (L)		60	
	5 m (Z)	9	5	84

Dimensions



Solid State Auto Switch Band Mounting Type

D-H7A1/D-H7A2/D-H7B (€ ROHS



Grommet



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-H7□ (With indicator light)					
Auto switch model	D-H7A1	D-H7A2	D-H7B		
Wiring type	3-v	vire	2-wire		
Output type	NPN	PNP	_		
Applicable load	IC circuit, F	Relay, PLC	24 VDC Relay, PLC		
Power supply voltage	5, 12, 24 VDC	_			
Current consumption	10 mA	_			
Load voltage	28 VDC or less	-	24 VDC (10 to 28 VDC)		
Load current	40 mA or less	80 mA or less	5 to 40 mA		
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA load current)	(0.8 V or less 0.8 V or less			
Leakage current	100 μA or les	0.8 mA or less at 24 VDC			
Indicator light	Red LED illuminates when turned ON.				
Standard		CE marking, RoHS			

Oilproof Heavy-duty Lead Wire Specifications

Auto swi	tch model	D-H7A1 D-H7A2 D-H7B		D-H7B
Sheath	Outside diameter [mm]	ø3.4		
la sudata a	Number of cores	3 cores (Brown/Blue/Black) 2 co		2 cores (Brown/Blue)
Insulator	Outside diameter [mm]	ø1.1		
Conductor	Effective area [mm²]	0.2		
Strand diameter [mm]			ø0.08	
Minimum bending radiu	s [mm] (Reference values)		21	

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.


Weight

(g)

Auto swit	Auto switch model		D-H7A1 D-H7A2	
	0.5 m (Nil)	13		11
Lead wire length	3 m (L)	57		50
	5 m (Z)	9	2	81

Dimensions

(mm)





Solid State Auto Switch Band Mounting Type D-G59/D-G5P/D-K59



Refer to SMC website for the details of the products conforming to the international standards.

Grommet



Auto Switch Specifications

PLC: Programmable Logic Controller

D-G5□, D-K59 (With indicator light)					
Auto switch model	D-G59	D-G5P	D-K59		
Wiring type	3-v	vire	2-wire		
Output type	NPN	PNP	_		
Applicable load	IC circuit, F	Relay, PLC	24 VDC Relay, PLC		
Power supply voltage	5, 12, 24 VDC	_			
Current consumption	10 mA	or less	_		
Load voltage	28 VDC or less	_	24 VDC (10 to 28 VDC)		
Load current	40 mA or less	80 mA or less	5 to 40 mA		
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA load current)	(0.8 V or less 0.8 V or less			
Leakage current	100 μA or less at 24 VDC		0.8 mA or less at 24 VDC		
Indicator light	Red LED illuminates when turned ON.				
Standard		CE marking, RoHS			

Oilproof Heavy-duty Lead Wire Specifications

- processing and even the operation				
Auto swi	tch model	D-G59 D-G5P D-K59		D-K59
Sheath	Outside diameter [mm]	ø4		
la sudata a	Number of cores	Number of cores 3 cores (Brown/Blue/Black) 2 co		2 cores (Brown/Blue)
Insulator	Outside diameter [mm]	ø1.22		
Conductor	Effective area [mm²]	2] 0.3		
Conductor	Strand diameter [mm]	ø0.08		
Minimum bending radius [mm] (Reference values)			24	


Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight

(g)

Auto swit	Auto switch model		D-G5P	D-K59
	0.5 m (Nil) 20		18	
Lead wire length	3 m (L)	7	8	68
	5 m (Z)	124		108

Dimensions



Solid State Auto Switch Band Mounting Type D-H7C



Refer to SMC website for the details of the products conforming to the international standards.

CE marking, RoHS

Connector



Precautions

- 1. Confirm that the connector is appropriately tightened. If tightened insufficiently, the waterproof performance will deteriorate.
- 2. Refer to page 1679 for the details.

Lead wires with a connector indication Part No. of Lead Wires with Connectors

(Applicable only for confidence type)					
Model	Lead wire length				
D-LC05	0.5 m				
D-LC30	3 m				
D-LC50	5 m				

Auto Switch Specifications

PLC: Programmable Logic Controller D-H7C (With indicator light) Auto switch model D-H7C Wiring type 2-wire Output type Applicable load 24 VDC Relay, PLC Power supply voltage Current consumption Load voltage 24 VDC (10 to 28 VDC) Load current 5 to 40 mA Internal voltage drop 4 V or less Leakage current 0.8 mA or less at 24 VDC Indicator light Red LED illuminates when turned ON. Standard

Note 1) Refer to page 1584 for solid state auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.


Note 3) Lead wires with a connector may be shipped with switches.

Weight

(g)

Auto swit	ch model	D-H7C
	0.5 m (Nil)	15
Lead wire length	3 m (L)	54
	5 m (Z)	85

Dimensions







Solid State Auto Switch Band Mounting Type D-G39/D-K39



Refer to SMC website for the details of the products conforming to the international standards.

Terminal conduit



∆Caution

Precautions

- Use cable whose O.D. is within the size in the figure to maintain water resistant performance.
- 2. After wiring, confirm that tightening gland and all screws are tightened.

Auto Switch Specifications

PLC: Programmable Logic Controller

D-G39, D-K39 (With indicator light)						
Auto switch model	D-G39	D-K39				
Wiring type	3-wire	2-wire				
Output type	NPN	_				
Applicable load	IC circuit, Relay, PLC	24 VDC Relay, PLC				
Power supply voltage	5, 12, 24 VDC (4.5 to 28 VDC)	_				
Current consumption	10 mA or less	_				
Load voltage	28 VDC or less	24 VDC (10 to 28 VDC)				
Load current	40 mA or less	5 to 40 mA				
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA of load current)	4 V or less				
Leakage current	100 μA or less at 24 VDC	0.8 mA or less at 24 VDC				
Indicator light	Red LED illuminates when turned ON.					
Standard	CE marking, RoHS					


Note) Refer to page 1584 for solid state auto switch common specifications.

Weight

(g)

Auto switch model		D-G39	D-K39
Lead wire	None	116	

Dimensions



Solid State Auto Switch Band Mounting Type D-G39A/D-K39A



Refer to SMC website for the details of the products conforming to the international standards.

Terminal conduit





Precautions

- 1. Use cable whose O.D. is within the size in the figure to maintain water resistant performance.
- 2. After wiring, confirm that tightening gland and all screws are tightened.

Auto Switch Specifications

PLC: Programmable Logic Controller

D-G39A, D-K39A (With indicator light)						
Auto switch model	D-G39A	D-K39A				
Wiring type	3-wire	2-wire				
Output type	NPN	_				
Applicable load	IC circuit, Relay, PLC	24 VDC Relay, PLC				
Power supply voltage	5, 12, 24 VDC (4.5 to 28 VDC)	_				
Current consumption	10 mA or less	_				
Load voltage	28 VDC or less	24 VDC (10 to 28 VDC)				
Load current	40 mA or less	5 to 40 mA				
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA of load current)	4 V or less				
Leakage current	100 μA or less at 24 VDC	0.8 mA or less at 24 VDC				
Indicator light	Red LED illuminates when turned ON.					
Standard	CE marking, RoHS					


Note) Refer to page 1584 for solid state auto switch common specifications.

Weight

(g)

Auto switch model		D-G39A	D-K39A
Lead wire	None	110	

Dimensions







Solid State Auto Switch Rail Mounting Type D-F79/D-J79



Refer to SMC website for the details of the products conforming to the international standards.

Grommet



Auto Switch Specifications

PLC: Programmable Logic Controller

D-F7□, D-J79 (With indicator light)							
Auto switch model	D-F79	D-F79 D-F7P					
Wiring type	3-w	vire	2-wire				
Output type	NPN	PNP	_				
Applicable load	IC circuit, F	Relay, PLC	24 VDC Relay, PLC				
Power supply voltage	5, 12, 24 VDC ((4.5 to 28 VDC)	_				
Current consumption	10 mA	or less	_				
Load voltage	28 VDC or less	_	24 VDC (10 to 28 VDC)				
Load current	40 mA or less	80 mA or less	5 to 40 mA				
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA load current)	4 V or less					
Leakage current	100 μA or les	0.8 mA or less at 24 VDC					
Indicator light	Red LED illuminates when turned ON.						
Standard	CE marking, RoHS						

Oilproof Heavy-duty Lead Wire Specifications

the contract of the contract o						
Auto swi	tch model	D-F79 D-F7P D-J79		D-J79		
Sheath	Outside diameter [mm]	ø3.4		ø3.4		
Number of cores 3 cores (Brown/Blue/Black)		n/Blue/Black)	2 cores (Brown/Blue)			
Insulator	Outside diameter [mm]	ø1.1				
Conductor	Effective area [mm²]	a [mm²] 0.2				
Conductor	Strand diameter [mm]	ø0.08				
Minimum bending radius [mm] (Reference values)			21			


Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight

(g)

Auto swit	Auto switch model		D-F7P	D-J79
	0.5 m (Nil)	13		11
Lead wire length	3 m (L)	5	7	50
	5 m (Z)	92		81

Dimensions



Solid State Auto Switch Rail Mounting Type

D-F7NV/D-F7PV/D-F7BV (€ ROHS



Grommet Electrical entry: Perpendicular



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards. PLC: Programmable Logic Controller

		FLO. Flogia	ammable Logic Controller			
D-F7□V (With indicator light)						
Auto switch model	D-F7NV	D-F7PV	D-F7BV			
Wiring type	3-w	vire	2-wire			
Output type	NPN	PNP	_			
Applicable load	IC circuit, F	Relay, PLC	24 VDC Relay, PLC			
Power supply voltage	5, 12, 24 VDC (_				
Current consumption	10 mA	or less	_			
Load voltage	28 VDC or less —		24 VDC (10 to 28 VDC)			
Load current	40 mA or less	80 mA or less	5 to 40 mA			
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA load current)	4 V or less				
Leakage current	100 μA or les	0.8 mA or less at 24 VDC				
Indicator light	Red LED illuminates when turned ON.					
Standard	CE marking, RoHS					

Oilproof Heavy-duty Lead Wire Specifications

and the state of t							
Auto swi	tch model	D-F7NV	D-F7NV D-F7PV				
Sheath	Outside diameter [mm]	ø3.4					
la sudata a	Number of cores	3 cores (Brow	2 cores (Brown/Blue)				
Insulator	Outside diameter [mm]						
Conductor	Effective area [mm²]	0.2					
Conductor	Strand diameter [mm]						
Minimum bending radius [mm] (Reference values)		21					

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.


Weight

(g)

Auto switch model		D-F7NV	D-F7PV	D-F7BV
	0.5 m (Nil)	13 57		11
Lead wire length	3 m (L)			57
	5 m (Z)	92 81		81

Dimensions

(mm)





Solid State Auto Switch Rail Mounting Type **D-J79C**



Refer to SMC website for the details of the products conforming to the international standards.

Connector



∆Caution

Precautions

- Confirm that the connector is appropriately tightened. If tightened insufficiently, the waterproof performance will deteriorate.
- 2. Refer to page 1679 for the details.

Lead wires with a connector indication

Part No. of Lead Wires with Connectors
(Applicable only for connector type)

(ripplicable drilly for definitional type)					
Model	Lead wire length				
D-LC05	0.5 m				
D-LC30	3 m				
D-LC50	5 m				

Auto Switch Specifications

PLC: Programmable Logic Controller

D-J79C (With indicator	D-J79C (With indicator light)					
Auto switch model	D-J79C					
Wiring type	2-wire					
Output type	_					
Applicable load	24 VDC Relay, PLC					
Power supply voltage	_					
Current consumption	_					
Load voltage	24 VDC (10 to 28 VDC)					
Load current	5 to 40 mA					
Internal voltage drop	4 V or less					
Leakage current	0.8 mA or less at 24 VDC					
Indicator light	Red LED illuminates when turned ON.					
Standard	CE marking, RoHS					

Note 1) Refer to page 1584 for solid state auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.


Note 3) Lead wires with a connector may be shipped with auto switches.

Weight

(g)

Auto switch model		D-J79C
	0.5 m (Nil)	13
Lead wire length	3 m (L)	52
	5 m (Z)	83

Dimensions



Solid State Auto Switch Tie-rod Mounting Type D-F59/D-F5P/D-J59



Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

Auto Switch Specifications



Grommet

D-F5□, D-J59 (With indicator light)							
Auto switch model	D-F59	D-F5P	D-J59				
Wiring type	3-v	vire	2-wire				
Output type	NPN	PNP	_				
Applicable load	IC circuit, F	Relay, PLC	24 VDC Relay, PLC				
Power supply voltage	5, 12, 24 VDC (4.5 to 28 VDC)		_				
Current consumption	10 mA or less		_				
Load voltage	28 VDC or less	_	24 VDC (10 to 28 VDC)				
Load current	40 mA or less	80 mA or less	5 to 40 mA				
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA load current)	0.8 V or less	4 V or less				
Leakage current	100 μA or les	0.8 mA or less at 24 VDC					
Indicator light	Red LED illuminates when turned ON.						
Standard		CE marking, RoHS					

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-F59	D-F5P D-F5P		
Sheath	Outside diameter [mm]	ø4			
Insulator	Number of cores	3 cores (Brow	2 cores (Brown/Blue)		
insulator	Outside diameter [mm]				
Effective area [mn		0.3			
Conductor	Strand diameter [mm]				
Minimum bending radius [mm] (Reference values)		24			

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight


(g)

Auto switch model		D-F59	D-F59 D-F5P		
	0.5 m (Nil)	23 81		21	
Lead wire length	3 m (L)			71	
	5 m (Z)	127		111	

Dimensions

(mm)

D-F59/D-F5P/D-J59





Solid State Auto Switch Tie-rod Mounting Type D-G39C/D-K39C



Refer to SMC website for the details of the products conforming to the international standards.

Terminal conduit



△Caution

Precautions

- Use cable whose O.D. is within the size in the figure to maintain water resistant performance.
- 2. After wiring, confirm that tightening gland and all screws are tightened.

Auto Switch Specifications

PLC: Programmable Logic Controller D-G39C, D-K39C (With indicator light) Auto switch model **D-G39C D-K39C** Wiring type 3-wire 2-wire Output type NPN Applicable load IC circuit, Relay, PLC 24 VDC Relay, PLC Power voltage 5, 12, 24 VDC (4.5 to 28 VDC) Current consumption 10 mA or less 28 VDC or less 24 VDC (10 to 28 VDC) Load voltage Load current 40 mA or less 5 to 40 mA 1.5 V or less (0.8 V or less Internal voltage drop 4 V or less at 10 mA of load current) Current leakage 100 μA or less at 24 VDC 0.8 mA or less at 24 VDC

Red LED illuminates when turned ON.

CE marking, RoHS

Note) Refer to page 1584 for solid state auto switch common specifications.

Weight

Standard

Indicator light


(g)

Auto switch model	Applicable bore size (mm)	Weight
D-G39C-4, K39C-4	40	162
D-G39C-5, K39C-5	50	166
D-G39C-6, K39C-6	63	184
D-G39C-8, K39C-8	80	210
D-G39C-10, K39C-10	100	232

2 x M5 x 0.8 x 12

Dimensions

(mm)



Dimensions

Auto switch model	Applicable bore size (mm)	С	HW	Н	Η´	Т	T	Z
D-G39C-4, D-K39C-4	40	44	69	57	49.5	7.5	6.5	M5 x 0.8 x 16
D-G39C-5, D-K39C-5	50	52	77	58	50.5	8.5	6.5	IVIS X U.8 X 16
D-G39C-6, D-K39C-6	63	64	91	60.5	52	10.5	7.5	M5 x 0.8 x 20
D-G39C-8, D-K39C-8	80	78	107	64	53.5	12.5	9.5	M5 x 0.8 x 25
D-G39C-10, D-K39C-10	100	92	121	67	56.5	15.5	9.5	IVI5 X U.8 X 25



2-Color Indicator Solid State Auto Switch Direct Mounting Type D_MQNW(\/\D_MQDW(\/\)D_MQDW(\/\)

D-M9NW(V)/D-M9PW(V)/D-M9BW(V) **(**



Grommet

- 2-wire load current is reduced (2.5 to 40 mA).
- Using flexible cable as standard spec.
- The proper operating range can be determined by the color of the light. (Red → Green ← Red)



△Caution

Precautions

Fix the auto switch with the existing screw installed on the auto switch body. The auto switch may be damaged if a screw other than the one supplied is used.

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-M9□W, D-M	D-M9□W, D-M9□WV (With indicator light)								
Auto switch model	D-M9NW	D-M9NWV	D-M9PW D-M9PWV		D-M9BW	D-M9BWV			
Electrical entry direction	In-line	Perpendicular	In-line	Perpendicular	In-line	Perpendicular			
Wiring type		3-v	/ire		2-v	vire			
Output type	N	PN	PI	NΡ		_			
Applicable load		IC circuit, F	Relay, PLC		24 VDC r	elay, PLC			
Power supply voltage	5, 12, 24 VDC (4.5 to 28 V) —				_				
Current consumption	10 mA or less				_				
Load voltage	28 VDC or less — 24 VDC (10 to 2			to 28 VDC)					
Load current		40 mA	or less		2.5 to 40 mA				
Internal voltage drop	0.8 V or le	ess at 10 mA	(2 V or less	at 40 mA)	4 V c	r less			
Leakage current	100 μA or less at 24 VDC 0.8 m.				0.8 mA	or less			
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.					s.			
Standard		CE marking, RoHS							

Oilproof Flexible Heavy-duty Lead Wire Specifications

Auto switch model		D-M9NW(V)	D-M9PW(V)	D-M9BW(V)			
Sheath	Outside diameter [mm]	2.6					
la sudata a	Number of cores	3 cores (Brow	2 cores (Brown/Blue)				
Insulator	Outside diameter [mm]						
0	Effective area [mm²]		0.15				
Conductor	Strand diameter [mm]						
Minimum bending radius [mm] (Reference values)			17				


Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.


Weight

(g)

Auto switch model		D-M9NW(V)	D-M9PW(V)	D-M9BW(V)
Lead wire length	0.5 m (Nil)	8		7
	1 m (M)	14		13
	3 m (L)	41		38
	5 m (Z)	68		63

Dimensions (mm)





2-Color Indicator Solid State Auto Switch Direct Mounting Type D-Y7NW(V)/D-Y7PW(V)/D-Y7BW(V) €



Grommet

- The proper operating range can be determined by the color of the light.
 (Red → Green ← Red)
- Using flexible cable as standard spec.



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-Y7□W, D-Y7□WV (With indicator light)						
Auto switch model	D-Y7NW	D-Y7NWV	D-Y7PW	D-Y7PWV	D-Y7BW	D-Y7BWV
Electrical entry direction	In-line	Perpendicular	In-line	Perpendicular	In-line	Perpendicular
Wiring type		3-w	/ire		2-wire	
Output type	NPN PNP		_			
Applicable load	IC circuit, Relay, PLC			24 VDC relay, PLC		
Power supply voltage	5, 12, 24 VDC (4.5 to 28 VDC)			_		
Current consumption	10 mA or less			_		
Load voltage	28 VDC or less —		24 VDC (10 to 28 VDC)			
Load current	40 mA or less 80 mA or less		2.5 to 40 mA			
Internal voltage drop	(0.8 V	1.5 V or less (0.8 V or less at 10 mA load current) 0.8 V or less		4 V or less		
Leakage current	100 μA or less at 24 VDC			0.8 mA or less at 24 VDC		
Indicator light	Operating range ········· Red LED illuminates. Proper operating range ········ Green LED illuminates.					
Standard	CE marking, RoHS					

Oilproof Flexible Heavy-duty Lead Wire Specifications

Auto switch model		D-Y7NW□	D-Y7PW□	D-Y7BW□
Sheath	Outside diameter [mm]	ø3.4		
la sulata a	Number of cores	3 cores (Brown/Blue/Black)		2 cores (Brown/Blue)
Insulator	Outside diameter [mm]	ø1.0		
Conductor	Effective area [mm²]	0.15		
Conductor	Strand diameter [mm]	ø0.05		
Minimum bending radius [mm] (Reference values)		21		

Note 1) Refer to page 1584 for solid state auto switch common specifications.


Weight


(g)

Auto switch model		D-Y7NW(V)	D-Y7PW(V)	D-Y7BW(V)
	0.5 m (Nil)		11	
Lead wire length	3 m (L)		54	
	5 m (Z)		88	

<u>Dimensions</u> (mm)

ØSMC





Note 2) Refer to page 1584 for lead wire lengths.

2-Color Indicator Solid State Auto Switch **Direct Mounting Type**

D-M5NW/D-M5PW/D-M5BW (



Grommet

The proper operating range can be determined by the color of the light.

 $(Red \rightarrow Green \leftarrow Red)$



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards. PLC: Programmable Logic Controller

1 EG. 1 Togrammable Logic Controller						
D-M5□W (With indicator light)						
Auto switch model	D-M5NW D-M5PW		D-M5BW			
Wiring type	3-wire		2-wire			
Output type	NPN	PNP	_			
Applicable load	IC circuit, Relay, PLC		24 VDC Relay, PLC			
Power supply voltage	5, 12, 24 VDC	_				
Current consumption	10 mA or less		_			
Load voltage	28 VDC or less —		24 VDC (10 to 28 VDC)			
Load current	40 mA or less 80 mA or less		5 to 40 mA			
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA load current) 0.8 V or less		4 V or less			
Leakage current	100 μA or les	0.8 mA or less at 24 VDC				
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.					
Standard	CE marking, RoHS					

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-M5NW	D-M5PW	D-M5BW
Sheath	Outside diameter [mm]	ø3.4		
Inculator	Number of cores	3 cores (Brown/Blue/Black)		2 cores (Brown/Blue)
Insulator	Outside diameter [mm]	ø1.1		
Conductor	Effective area [mm²]	0.2		
Conductor	Strand diameter [mm]	ø0.08		
Minimum bending radius [mm] (Reference values)		21		

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.


Weight

(g)

Auto switch model		D-M5NW	D-M5PW	D-M5BW
	0.5 m (Nil)	16		14
Lead wire length	3 m (L)	60		53
	5 m (Z)	95		84

Dimensions

(mm)





2-Color Indicator Solid State Auto Switch Band Mounting Type

D-H7NW/D-H7PW/D-H7BW (



Grommet

The proper operating range can be determined by the color of the light.

 $(Red \rightarrow Green \leftarrow Red)$



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

	PLC: Programmable Logic Controlle				
D-H7 W (With	D-H7□W (With indicator light)				
Auto switch model	D-H7NW	D-H7PW	D-H7BW		
Wiring type	3-v	vire	2-wire		
Output type	NPN	PNP	_		
Applicable load	IC circuit,	Relay, PLC	24 VDC relay, PLC		
Power supply voltage	5, 12, 24 VDC (4.5 to 28 VDC)		_		
Current consumption	10 mA	10 mA or less			
Load voltage	28 VDC or less	28 VDC or less —			
Load current	40 mA or less	80 mA or less	5 to 40 mA		
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA load current) 0.8 V or less		4 V or less		
Leakage current	100 μA or less at 24 VDC 0.8 mA or less at				
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.				
Standard	CE marking, RoHS				

Oilproof Heavy-duty Lead Wire Specifications

	- protections, and, even the operation					
Auto switch model		D-H7NW	D-H7PW	D-H7BW		
Sheath	Outside diameter [mm]	ø3.4		ø3.4		
Insulator	Number of cores	3 cores (Brown/Blue/Black) 2 cores (Brown/Blu		2 cores (Brown/Blue)		
insulator	Outside diameter [mm]	ø1.1				
Conductor	Effective area [mm²]	0.2				
Strand diameter [mr		ø0.08				
Minimum bending radius [mm] (Reference values)		21				


Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight

(g)

Auto swit	tch model	D-H7NW	D-H7PW	D-H7BW
	0.5 m (Nil)	1	3	11
Lead wire length	3 m (L)	5	7	50
	5 m (Z)	9	2	81

Dimensions



2-Color Indicator Solid State Auto Switch Band Mounting Type

D-G59W/D-G5PW/D-K59W



Refer to SMC website for the details of the products conforming to the

Grommet

The proper operating range can be determined by the color of the light.

 $(Red \rightarrow Green \leftarrow Red)$



Auto Switch Specifications

international standards.

PLC: Programmable Logic Controller

D-G5□W, D-K	D-G5□W, D-K59W (With indicator light)				
Auto switch model	D-G59W	D-G59W D-G5PW			
Wiring type	3-w	vire	2-wire		
Output type	NPN	PNP	_		
Applicable load	IC circuit, F	Relay, PLC	24 VDC Relay, PLC		
Power supply voltage	5, 12, 24 VDC (4.5 to 28 VDC)		_		
Current consumption	10 mA or less		_		
Load voltage	28 VDC or less	28 VDC or less —			
Load current	40 mA or less	40 mA or less 80 mA or less			
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA load current) 0.8 V or less		4 V or less		
Leakage current	100 μA or less	0.8 mA or less at 24 VDC			
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.				
Standard	CE marking, RoHS				

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-G59W	D-G5PW	D-K59W
Sheath	Outside diameter [mm]	ø4		
Inculator	Number of cores	3 cores (Brown/Blue/Black) 2 cores (Brown/Blue		2 cores (Brown/Blue)
Insulator Outside diameter [mn		ø1.22		
Conductor	Effective area [mm²]	0.3		
Strand diameter [mm]		ø0.08		
Minimum bending radius [mm] (Reference values)		24		

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.


Weight

(g)

Auto swit	tch model	D-G59W	D-G5PW	D-K59W
	0.5 m (Nil)	2	0	18
Lead wire length	3 m (L)	7	8	68
	5 m (Z)	12	24	108

Dimensions

(mm)



D-□



2-Color Indicator Solid State Auto Switch **Rail Mounting Type**

D-F79W/D-F7PW/D-J79W



Grommet

The proper operating range can be determined by the color of the light.

 $(Red \rightarrow Green \leftarrow Red)$



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards. PLC: Programmable Logic Controller

D-F7□W, D-J7	D-F7□W, D-J79W (With indicator light)				
Auto switch model	D-F79W	D-F79W D-F7PW			
Wiring type	3-v	vire	2-wire		
Output type	NPN	PNP	_		
Applicable load	IC circuit,	Relay, PLC	24 VDC Relay, PLC		
Power supply voltage	5, 12, 24 VDC (4.5 to 28 VDC)		_		
Current consumption	10 mA or less		_		
Load voltage	28 VDC or less	28 VDC or less —			
Load current	40 mA or less	40 mA or less 80 mA or less			
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA load current) 0.8 V or less		4 V or less		
Leakage current	100 μA or less at 24 VDC		0.8 mA or less at 24 VDC		
Indicator light	Operating range Red LED illuminates.				

Proper operating range Green LED illuminates.

CE marking, RoHS

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-F79W	D-F7PW	D-J79W		
Sheath	Outside diameter [mm]	ø3.4		ø3.4		
Insulator	Number of cores	3 cores (Brown/Blue/Black) 2 cores (Brown/Blue		2 cores (Brown/Blue)		
insulator	Outside diameter [mm]	ø1.1				
Conductor	Effective area [mm²]	0.2				
Conductor	Strand diameter [mm]	ø0.08				
Minimum bending radius [mm] (Reference values)		21				

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight


Indicator light

Standard

(g)

Auto swit	ch model	D-F79W	D-F7PW	D-J79W
	0.5 m (Nil)	1	3	11
Lead wire length	3 m (L)	5	7	50
	5 m (Z)	9	2	81

Dimensions



2-Color Indicator Solid State Auto Switch Rail Mounting Type

D-F7NWV/D-F7BWV

 $C \in$



Grommet Electrical entry: Perpendicular

The proper operating range can be determined by the color of the light.

 $(Red \rightarrow Green \leftarrow Red)$



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-F7 WV (Wit	D-F7□WV (With indicator light)					
Auto switch model	D-F7NWV	D-F7BWV				
Wiring type	3-wire	2-wire				
Output type	NPN	_				
Applicable load	IC circuit, Relay, PLC	24 VDC Relay, PLC				
Power supply voltage	Power supply voltage 5, 12, 24 VDC (4.5 to 28 VDC) —					
Current consumption	10 mA or less	_				
Load voltage	28 VDC or less	24 VDC (10 to 28 VDC)				
Load current 40 mA or less		5 to 40 mA				
Internal voltage drop 1.5 V or less (0.8 V or less at 10 mA load current)		4 V or less				
Leakage current	100 μA or less at 24 VDC 0.8 mA or less at 24 VI					
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.					
Standard	CE mark	ing, RoHS				

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-F7NWV	D-F7BWV
Sheath	Outside diameter [mm]	ø3.4	
Insulator	Number of cores	3 cores (Brown/Blue/Black)	2 cores (Brown/Blue)
insulator	Outside diameter [mm]	[mm] Ø1.1	
Conductor	Effective area [mm²]	0.2	
Strand diameter [mm]		ø0.08	
Minimum bending radius [mm] (Reference values)		2	1

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.


Weight

(g)

Auto swit	ch model	D-F7NWV	D-F7BWV
	0.5 m (Nil)	13	11
Lead wire length	3 m (L)	57	50
	5 m (Z)	92	81

Dimensions

(mm)



D-□



2-Color Indicator Solid State Auto Switch Tie-rod Mounting Type D. EFOWID FEDWID 150W (C. C.)

D-F59W/D-F5PW/D-J59W (



Grommet

The proper operating range can be determined by the color of the light.

 $(Red \rightarrow Green \leftarrow Red)$



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

	1 EO. 1 Togrammable Eogle Controller				
D-F5□W, D-J5	D-F5□W, D-J59W (With indicator light)				
Auto switch model	D-F59W	D-J59W			
Wiring type	3-v	vire	2-wire		
Output type	NPN	PNP	_		
Applicable load	IC circuit, F	Relay, PLC	24 VDC Relay, PLC		
Power supply voltage	5, 12, 24 VDC ((4.5 to 28 VDC)	_		
Current consumption	10 mA	or less	_		
Load voltage	28 VDC or less	_	24 VDC (10 to 28 VDC)		
Load current	40 mA or less 80 mA or less		5 to 40 mA		
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA load current) 0.8 V or less		4 V or less		
Leakage current	100 μA or less at 24 VDC 0.8 mA or less at 24 VD				
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.				
Standard	CE marking, RoHS				

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-F59W	D-F59W D-F5PW		
Sheath	Outside diameter [mm]	ø4			
Insulator	Number of cores	3 cores (Brow	n/Blue/Black)	2 cores (Brown/Blue)	
insulator	Outside diameter [mm]				
Conductor	Effective area [mm²]	0.3			
Conductor	Strand diameter [mm]				
Minimum bending radius [mm] (Reference values)		24			


Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight

(g)

Auto swi	Auto switch model		D-F59W D-F5PW	
	0.5 m (Nil)	2	3	21
Lead wire length	3 m (L)	81		71
	5 m (Z)	12	27	111

Dimensions



2-Color Indicator with Diagnostic Output Solid State Auto Switch: Band Mounting Type

D-H7NF

Refer to SMC website for the details of

Grommet

Since the diagnostic output signal can be detected in the red display area, the difference of detecting position can be confirmed by the side of PLC (Programmable Logic Controller).



Auto Switch Specifications

PLC: Programmable Logic Controller

the products conforming to the

international standards.

D-H7NF (With indicator light)			
Auto switch model	D-H7NF		
Wiring type	4-wire		
Output type	NPN		
Diagnostic output	Normal operation		
Applicable load	IC circuit, Relay, PLC		
Power voltage	5, 12, 24 VDC (4.5 to 28 VDC)		
Current consumption	10 mA or less		
Load voltage	28 VDC or less		
Load current	50 mA or less at the total amount of normal output and diagnostic output		
Internal voltage drop	1.5 V or less (0.8 V or less at each output 5 mA)		
Current leakage	100 μA or less at 24 VDC		
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.		
Standard	CE marking, RoHS		

Oilproof Heavy-duty Lead Wire Specifications

onpresentation, and personnelled			
Auto switch model		D-H7NF	
Sheath	Outside diameter [mm]	ø3.4	
Inculator	Number of cores	4 cores (Brown/Blue/Black/Orange)	
Insulator	Outside diameter [mm]	ø0.98	
Conductor	Effective area [mm²]	0.2	
Conductor	Strand diameter [mm]	ø0.08	
Minimum bending radius [mm] (Reference values)		21	

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight

(g)

Auto swi	tch model	D-H7NF
	0.5 m (Nil)	13
Lead wire length	3 m (L)	56
	5 m (Z)	90


Diagnostic Output Operation


The diagnostic output signal is output within the red display area (where indicator light is Red), and the diagnostic output becomes OFF when the detecting position remains within the proper operating range (where indicator is Green). When the detecting position is not adjusted, the diagnostic output becomes

ØSMC

			ON			
Indicator light	OFF	Red	Green	Red	OFF	Red
OUT		ON	ON	ON		ON
OUT (Normal output) Lead wire (Black)	OFF				OFF	
Diagnosis OUT (Diagnostic output) Lead wire (Orange		ON	OFF	ON	OFF	ON

Dimensions







2-Color Indicator with Diagnostic Output Solid State Auto Switch: Band Mounting Type

D-G59F

Refer to SMC website for the details of

Grommet

Since the diagnostic output signal can be detected in the red display area, the difference of detecting position can be confirmed by the side of PLC (Programmable Logic Controller).



Auto Switch Specifications

PLC: Programmable Logic Controller

the products conforming to the

international standards.

D-G59F (With indicator light)			
Auto switch model	D-G59F		
Wiring type	4-wire		
Output type	NPN		
Diagnostic output	Normal operation		
Applicable load	IC circuit, Relay, PLC		
Power voltage	5, 12, 24 VDC (4.5 to 28 VDC)		
Current consumption	10 mA or less		
Load voltage	28 VDC or less		
Load current	50 mA or less at the total amount of normal output and diagnostic output		
Internal voltage drop	1.5 V or less (0.8 V or less at 5 mA)		
Current leakage	100 μA or less at 24 VDC		
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.		
Standard	CE marking, RoHS		

Oilproof Heavy-duty Lead Wire Specifications

supress really duty found the operations		
Auto switch model		D-G59F
Sheath Outside diameter [mm]		ø4
Inculator	Number of cores	4 cores (Brown/Blue/Black/Orange)
Insulator	Outside diameter [mm]	ø1.29
Effective area [mm²]	0.3	
Conductor Strand diameter [mm]		ø0.08
Minimum bending radius [mm] (Reference values)		24

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight

(g)


Auto switch model		D-G59F
	0.5 m (Nil)	20
Lead wire length	3 m (L)	74
	5 m (Z)	117


Diagnostic Output Operation

The diagnostic output signal is output within the red display area (where indicator light is Red), and the diagnostic output becomes OFF when the detecting position remains within the proper operating range (where indicator is Green). When the detecting position is not adjusted, the (Diagnosis output position is not adjusted, the (Diagnosis output) OFF diagnositic output becomes

ON OFF Red Green Red OFF Red ON ON ON ON OFF ON ON ON OFF OFF

Dimensions





2-Color Indicator with Diagnostic Output Solid State Auto Switch: Rail Mounting Type

D-F79F

Refer to SMC website for the details of

Grommet

Since the diagnostic output signal can be detected in the red display area, the difference of detecting position can be confirmed by the side of PLC (Programmable Logic Controller).



Auto Switch Specifications

PLC: Programmable Logic Controller

the products conforming to the

international standards.

D-F79F (With indicator light)			
Auto switch model	D-F79F		
Wiring type	4-wire		
Output type	NPN		
Diagnostic output	Normal operation		
Applicable load	IC circuit, Relay, PLC		
Power supply voltage	5, 12, 24 VDC (4.5 to 28 VDC)		
Current consumption	10 mA or less		
Load voltage	28 VDC or less		
Load current	50 mA or less at the total amount of normal output and diagnostic output		
Internal voltage drop	1.5 V or less (0.8 V or less at 5 mA)		
Leakage current	100 μA or less at 24 VDC		
Indicator light	Operating range ········ Red LED illuminates. Proper operating range ······· Green LED illuminates.		
Standard	CE marking, RoHS		

Oilproof Heavy-duty Lead Wire Specifications

empressi ricary daty zeda vine opecinicatione		
Auto sw	itch model	D-F79F
Sheath Outside diameter [mm]		ø3.4
Insulator	Number of cores	4 cores (Brown/Blue/Black/Orange)
insulator	Outside diameter [mm]	ø0.98
Conductor	Effective area [mm²]	0.2
Conductor	Strand diameter [mm]	ø0.08
Minimum bending radius [mm] (Reference values)		21

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight

(g)


Auto switch model		D-F79F
	0.5 m (Nil)	13
Lead wire length	3 m (L)	56
	5 m (Z)	90


Diagnostic Output Operation

The diagnostic output signal is output within the red display area (where indicator light is Red), and it is not output within the proper operating range (where indicator light is Green). When the auto switch detecting position is not adjusted, the diagnostic output becomes activated.

		ON			
Indicator OFF	Red	Green	Red	OFF	Red
•	ON	ON	ON		ON
OUT (Normal output) OFF Lead wire (Black)				OFF	ON
Diagnosis OUT (Diagnostic output) Lead wire (Orange)	ON	OFF	ON	OFF	ON

Dimensions









2-Color Indicator with Diagnostic Output Solid State Auto Switch: Tie-rod Mounting Type

D-F59F

Refer to SMC website for the details of

Grommet

Since the diagnostic output signal can be detected in the red display area, the difference of detecting position can be confirmed by the side of PLC (Programmable Logic Controller).



Auto Switch Specifications

PLC: Programmable Logic Controller

the products conforming to the

international standards.

D-F59F (With indicator light)						
Auto switch model	D-F59F					
Wiring type	4-wire					
Output type	NPN					
Diagnostic output	Normal operation					
Applicable load	IC circuit, Relay, PLC					
Power supply voltage 5, 12, 24 VDC (4.5 to 28 VDC)						
Current consumption	10 mA or less					
Load voltage	28 VDC or less					
Load current	50 mA or less at the total amount of normal output and diagnostic output					
Internal voltage drop	1.5 V or less (0.8 V or less at 5 mA)					
Leakage current	100 μA or less at 28 VDC					
Indicator light	Operating range ········· Red LED illuminates. Proper operating range ······· Green LED illuminates.					
Standard	CE marking, RoHS					

Oilproof Heavy-duty Lead Wire Specifications

Chiproci ficary daty zead wite openineations				
Auto sw	itch model	D-F59F		
Sheath Outside diameter [mm]		ø4		
Inculator	Number of cores	4 cores (Brown/Blue/Black/Orange)		
Insulator	Outside diameter [mm]	ø1.29		
Conductor	Effective area [mm²]	0.3		
Conductor	Strand diameter [mm]	ø0.08		
Minimum bending radiu	s [mm] (Reference values)	24		

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight

(g)


Auto switch model		D-F59F
	0.5 m (Nil)	22
Lead wire length	3 m (L)	77
	5 m (Z)	121


Diagnostic Output Operation

The diagnostic output signal is output within the red display area (where indicator light is Red), and it is not output within the proper operating range (where indicator light is Green). When the auto switch detecting position is not adjusted, the diagnostic output becomes activated.

			ON				
Indicator C	DFF	Red	Green	Red	OFF	F	Red
·		ON	ON	ON			ON
(Normal output) C Lead wire (Black)	OFF			L	OFF		
Diagnosis OUT (Diagnostic output) Lead wire (Orange)	OFF_	ON	OFF	ON	OFF		ON

Dimensions







Water Resistant 2-Color Indicator Solid State Auto Switch: Direct Mounting Type D-M9NA(V)/D-M9PA(V)/D-M9BA(V) (ROHS)

Grommet

- Water (coolant) resistant type
- 2-wire load current is reduced (2.5 to 40 mA).
- The proper operating range can be determined by the color of the light. (Red → Green ← Red)
- Using flexible cable as standard spec.



∆Caution

Precautions

Fix the auto switch with the existing screw installed on the auto switch body. The auto switch may be damaged if a screw other than the one supplied is used.

Please consult with SMC if using coolant

liquid other than water based solution.

Weight

(g)

Auto s	witch model	D-M9NA(V) D-M9PA(V)	D-M9BA(V)
	0.5 m (Nil)	8	7
Lead wire length	1 m (M)	14	13
	3 m (L)	41	38
	5 m (Z)	68	63

Auto Switch Specifications

PLC: Programmable Logic Controller

D-M9□A, D-M9□AV (With indicator light)						
Auto switch model	D-M9NA	D-M9NAV	D-M9PA D-M9PAV		D-M9BA	D-M9BAV
Electrical entry direction	In-line	Perpendicular	In-line	Perpendicular	In-line	Perpendicular
Wiring type		3-v	vire		2-v	vire
Output type	N	PN	PI	NΡ		_
Applicable load	IC circuit, Relay, PLC 24 VDC relay, PL				elay, PLC	
Power supply voltage	5, 12, 24 VDC (4.5 to 28 V) —				_	
Current consumption	10 mA or less —				_	
Load voltage	28 VDC or less 24 VDC (10 to 28 V				to 28 VDC)	
Load current	40 mA or less 2.5 to 40 mA				40 mA	
Internal voltage drop	0.8 V or less at 10 mA (2 V or less at 40 mA) 4 V or less				r less	
Leakage current	100 μA or less at 24 VDC 0.8 mA or less			or less		
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.					
Standard			CE marki	ng, RoHS		


Oilproof Flexible Heavy-duty Lead Wire Specifications


Auto switch model		D-M9NA□	D-M9NAV□	D-M9PA□	D-M9PAV□	D-M9BA□	D-M9BAV□
Sheath	Outside diameter [mm]		2.6 2.7 x 3.2 (ellips			2	.6
la sudata a	Number of cores	3 0	3 cores (Brown/Blue/Black) 2 cores (rown/Blue)
Insulator	Outside diameter [mm]	0.88		0.9	0.	88	
0	Effective area [mm²]	12]		0.	15		
Conductor	Strand diameter [mm]	0.05					
Minimum bending radius	[mm] (Reference values)		17		20	1	7

Note 1) Refer to page 1584 for solid state auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.

Dimensions (mm)





SMC

D-□

Water Resistant 2-Color Indicator Solid State Auto Switch: Direct Mounting Type

D-Y7BA

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-Y7BA (With indicator light)					
Auto switch model	D-Y7BA				
Wiring type	2-wire				
Applicable load	24 VDC Relay, PLC				
Load voltage	24 VDC (10 to 28 VDC)				
Load current	2.5 to 40 mA				
Internal voltage drop	4 V or less				
Leakage current	0.8 mA or less at 24 VDC				
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.				
Standard	CE marking, RoHS				

Oilproof Flexible Heavy-duty Lead Wire Specifications

Auto switch model		D-Y7BA
Sheath Outside diameter [mm]		ø3.4
Insulator	Number of cores	2 cores (Brown/Blue)
insulator	Outside diameter [mm]	ø1
Conductor	Effective area [mm²]	0.15
Conductor	Strand diameter [mm]	ø0.05
Minimum bending radius [mm] (Reference values)		21

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Grommet

- Water (coolant) resistant type Using flexible cable as
- standard spec.

 The proper operating range can be determined by the color of the light. $(Red \rightarrow Green \leftarrow Red)$



.↑Caution

Precautions


Please consult with SMC if using coolant liquid other than water based solution. Detection characteristics (operating range) are the same as D-Y5 and D-Y7 W, but the detection area length is different.


Weight

(g)

Auto switch model		D-Y7BA
Lead wire length	3 m (L)	54
Lead wife leftgill	5 m (Z)	88

Dimensions





Water Resistant 2-Color Indicator Solid State Auto Switch: Band Mounting Type

D-H7BA

Refer to SMC website for the details of

the products conforming to the

international standards.

Grommet

- Water (coolant) resistant type The proper operating range can be determined by the
 - color of the light. $(Red \rightarrow Green \leftarrow Red)$



∕\Caution

Precautions

Please consult with SMC if using coolant liquid other than water based solution.

Auto Switch Specifications

PLC: Programmable Logic Controller D-H7BA (With indicator light) Auto switch model D-H7BA Wiring type 2-wire Output type Applicable load 24 VDC Relay, PLC Power supply voltage Current consumption Load voltage 24 VDC (10 to 28 VDC) Load current 5 to 40 mA Internal voltage drop 4 V or less Leakage current 0.8 mA or less at 24 VDC Operating range Red LED illuminates. Indicator light Proper operating range Green LED illuminates. Standard CE marking, RoHS

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-H7BA
Sheath	Outside diameter [mm]	ø3.4
la sudada u	Number of cores	2 cores (Brown/Blue)
Insulator	Outside diameter [mm]	ø1.1
0	Effective area [mm²]	0.2
Conductor	Strand diameter [mm]	ø0.08
Minimum bending radius [mm] (Reference values)		21

Note 1) Refer to page 1584 for solid state auto switch common specifications.


Note 2) Refer to page 1584 for lead wire lengths.

Weight

(q)

Auto switch model		D-H7BA
Lead wire length	3 m (L)	50
Lead wire length	5 m (Z)	81

Dimensions





Water Resistant 2-Color Indicator Solid State Auto Switch: Band Mounting Type

D-G5BA

Refer to SMC website for the details of

Grommet

 Water (coolant) resistant type
 The proper operating range can be determined by the color of the light.
 (Red → Green ← Red)



∆Caution

Precautions

Please consult with SMC if using coolant liquid other than water based solution.

Auto Switch Specifications

PLC: Programmable Logic Controller

the products conforming to the

international standards.

1 20.1 Togrammable 20gle Control			
D-G5BA (With indicator light)			
Auto switch model	D-G5BA		
Wiring type	2-wire		
Output type	_		
Applicable load	24 VDC Relay, PLC		
Power supply voltage	_		
Current consumption	_		
Load voltage	24 VDC (10 to 28 VDC)		
Load current	5 to 40 mA		
Internal voltage drop	4 V or less		
Leakage current	0.8 mA or less at 24 VDC		
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.		
Standard CE marking, RoHS			

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-G5BA
Sheath	Outside diameter [mm]	ø4
la sulata a	Number of cores	2 cores (Brown/Blue)
Insulator	Outside diameter [mm]	ø1.22
0	Effective area [mm²]	0.3
Conductor	Strand diameter [mm]	ø0.08
Minimum bending radius [mm] (Reference values)		24

Note 1) Refer to page 1584 for solid state auto switch common specifications.


Note 2) Refer to page 1584 for lead wire lengths.


Weight

(g)

	Auto switch model		D-G5BA
	Lead wire length	3 m (L)	68
		5 m (Z)	108

Dimensions





Water Resistant 2-Color Indicator **Solid State Auto Switch: Rail Mounting Type**

D-F7BA(V)

Refer to SMC website for the details of the products conforming to the

international standards.

0.8 mA or less at 24 VDC Red LED illuminates.

Proper operating range Green LED illuminates.

CE marking, RoHS

Grommet

 Water (coolant) resistant type The proper operating range can be determined by the color of the light. $(Red \rightarrow Green \leftarrow Red)$



.↑Caution

Precautions

Please consult with SMC if using coolant liquid other than water based solution.

Auto Switch Specifications

PLC: Programmable Logic Controller D-F7BA(V) (With indicator light) Auto switch model D-F7BA D-F7BAV In-line **Electrical entry direction** Perpendicular Wiring type Output type Applicable load 24 VDC Relay, PLC Power supply voltage Current consumption Load voltage 24 VDC (10 to 28 VDC) Load current 5 to 40 mA Internal voltage drop 4 V or less

Oilproof Heavy-duty Lead Wire Specifications

onproor floary daty zoda wife opcomoditorio			
Auto switch model Sheath Outside diameter [mm]		D-F7BA	
		ø3.4	
Insulator	Number of cores	cores 2 cores (Brown/Blue)	
insulator	Outside diameter [mm]	ø1.1	
Conductor	Effective area [mm²]	0.2	
Conductor	Strand diameter [mm]	ø0.08	
Minimum bending radius [mm] (Reference values)		21	

Note 1) Refer to page 1584 for solid state auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.

Weight

Leakage current

Indicator light


Standard

(g)


Auto switch model		D-F7BA	D-F7BAV
Lead wire length	3 m (L)	5	0
Lead wire length	5 m (Z)	8	1


Dimensions (mm)

D-F7BA











Water Resistant 2-Color Indicator Solid State Auto Switch: Tie-rod Mounting Type

D-F5BA

Refer to SMC website for the details of the products conforming to the

Grommet

Water (coolant) resistant type
 The proper operating range can be determined by the color of the light.
 (Red → Green ← Red)



∆Caution

Precautions

Please consult with SMC if using coolant liquid other than water based solution.

Auto Switch Specifications

PLC: Programmable Logic Controller

international standards.

D-F5BA (With indicator light)			
Auto switch model D-F5BA			
Wiring type	2-wire		
Output type			
Applicable load	24 VDC Relay, PLC		
Power supply voltage	_		
Current consumption	_		
Load voltage	24 VDC (10 to 28 VDC)		
Load current	5 to 40 mA		
Internal voltage drop	4 V or less		
Leakage current	0.8 mA or less at 24 VDC		
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.		
Standard CE marking, RoHS			

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-F5BA	
Sheath Outside diameter [ø4	
la sudata a	Number of cores	2 cores (Brown/Blue)	
Insulator	Outside diameter [mm]	ø1.22	
Conductor	Effective area [mm²]	0.3	
Conductor	Strand diameter [mm]	ø0.08	
Minimum bending radius [mm] (Reference values)		24	


Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight

(g)

	Auto switch model		D-F5BA
	Lead wire length	3 m (L)	71
		5 m (Z)	111

Dimensions



For Hygienic Design Cylinders Solid State Auto Switch: Direct Mounting Type D-F6N/D-F6P/D-F6B (RoHS)

Grommet

- 2-wire load current is reduced (2.5 to 40 mA)
- Using flexible cable as standard spec.



∆Caution

Precautions

Fix the auto switch with the existing screw installed on the auto switch body. The auto switch may be damaged if a screw other than the one supplied is used.

Auto Switch Specifications

PLC: Programmable Logic Controller

D-F6□ (With indicator light)					
Auto switch part no.	D-F6N D-F6P		D-F6B		
Electrical entry direction		In-line			
Wiring type	3-1	wire	2-wire		
Output type	NPN	PNP	_		
Applicable load	IC circuit, re	24 VDC relay, PLC			
Power supply voltage	5, 12, 24 VDC (4.5 to 28 V)		_		
Current consumption	10 mA or less		_		
Load voltage	28 VDC or less —		24 VDC (10 to 28 VDC)		
Load current	40 mA or less		2.5 to 40 mA		
Internal voltage drop	0.8 V or less at 10 m/	4 V or less			
Leakage current	100 μA or les	0.8 mA or less			
Indicator light	Red LED illuminates when turned ON.				
Standard	CE marking, RoHS				

Oilproof Flexible Heavy-duty Lead Wire Specifications

Auto switch model		D-F6N□	D-F6P□	D-F6B□
Sheath Outside diameter [mm]		ø2.6		
	Number of cores	3 cores (Brown/Blue/Black) 2 cores (Brown/B		2 cores (Brown/Blue)
Insulator	Outside diameter [mm]	ø0.88		
	Effective area [mm²]	0.15		
Conductor	Strand diameter [mm]	ø0.05		
Minimum bending radius [mm] (Reference values)		17		

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.


Weight

(g)


Auto switch model		D-F6N	D-F6P	D-F6B
	0.5 m (Nil)	2	0	19
Lead wire length	3 m (L)	5	3	50
	5 m (Z)	8	0	75

Dimensions (mm)


D-F6□



D-F6B



D-F6N/F6P





D-□



Solid State Auto Switch with Timer Band Mounting Type

D-G5NT





Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

Grommet

- With built-in OFF-delay timer (approx. 200 ms)
- Easy intermediate detection



D-G5NT (With indicator light)		
Auto switch model	D-G5NT	
Wiring type	3-wire	
Output type	NPN	
Output operation	Off-delay	
Operating time	1 ms or less	
Off-delay time	200 ± 50 ms	
Applicable load IC circuit, Relay, PLC		
Power supply voltage	ipply voltage 5, 12, 24 VDC (4.5 to 28 VDC)	
Current consumption	10 mA or less	
Load voltage	28 VDC or less	
Load current	40 mA or less	
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA)	
Leakage current	100 μA or less at 24 VDC	
Indicator light Red LED illuminates when turned ON.		
Standard	CE marking, RoHS	

Oilproof Heavy-duty Lead Wire Specifications

onproversions, and pound the opposition		
Auto switch model		D-G5NT
Sheath Outside diameter [mm]		ø4
leculates	Number of cores	3 cores (Brown/Blue/Black)
Insulator	Outside diameter [mm]	ø1.22
Conductor	Effective area [mm²]	0.3
	Strand diameter [mm]	ø0.08
Minimum bending radius [mm] (Reference values)		24

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight

(g)

Auto switch model		D-G5NT
Lead wire length	3 m (L)	78
Lead wife leftgill	5 m (Z)	124

Timer Operation

Detection of intermediate positioning for high-speed cylinder


Detecting point dispersion occurs due to response time of PLC (sequencer); e.g. scanning.

Ex.) Cylinder speed - 1000 mm/sec. PLC response time — 0.1 sec. Detecting point dispersion — Within 100 mm (= 1000 mm/sec. x 0.1 sec.)

Take PLC response time into consideration when using.

Auto switch operating range (mm) Auto switch Cylinder speed (mm/s) detecting time ON (200 ms) Auto switch output ON time PLC response time

Dimensions (mm)



1626

Solid State Auto Switch with Timer Rail Mounting Type

D-F7NT

 $C \in$



Grommet

- With built-in OFF-delay timer (approx. 200 ms)
- Easy intermediate detection



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-F7NT (With indicator light)		
Auto switch model	D-F7NT	
Wiring type	3-wire	
Output type	NPN	
Output operation	Off-delay	
Operating time	1 ms or less	
Off-delay time 200 ± 50 ms		
Applicable load	IC circuit, Relay, PLC	
Power supply voltage	5, 12, 24 VDC (4.5 to 28 VDC)	
Current consumption 10 mA or less		
Load voltage 28 VDC or less		
Load current	40 mA or less	
Internal voltage drop 1.5 V or less (0.8 V or less at 10 mA)		
Leakage current 100 μA or less at 24 VDC		
Indicator light Red LED illuminates when turned ON.		
Standard CE marking, RoHS		

Oilproof Heavy-duty Lead Wire Specifications

Olipidol fleavy-duty Lead Wife Specifications		
Auto switch model		D-F7NT
Sheath Outside diameter [mm]		ø3.4
laculates	Number of cores	3 cores (Brown/Blue/Black)
Insulator	Outside diameter [mm]	ø1.1
Conductor	Effective area [mm²]	0.2
	Strand diameter [mm]	ø0.08
Minimum bending radius [mm] (Reference values)		21

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Weight

(g)

Auto switch model		D-F7NT
I and wise length	3 m (L)	57
Lead wire length	5 m (Z)	92

Timer Operation

Detection of intermediate positioning for high-speed cylinder

Detecting point dispersion occurs due to response time of PLC (sequencer); e.g. scanning.


Switch detecting time OFF ON Switch operating range (mm) ON (200 ms)


Switch output ON time OFF ON (200 ms)

Ex.) Cylinder speed — 1000 mm/sec. PLC response time — 0.1 sec. Detecting point dispersion — Within 100 mm (= 1000 mm/sec. x 0.1 sec.)

Take PLC response time into consider- PLC response time ation when using.

Dimensions







Solid State Auto Switch with Timer Tie-rod Mounting Type

D-F5NT





Grommet

- With built-in OFF-delay timer (approx. 200 ms)
- Easy intermediate detection



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

i zo. i rogianimazio zogio controllo		
D-F5NT (With indicator light)		
Auto switch model	D-F5NT	
Wiring type	3-wire	
Output type	NPN	
Output operation	Off-delay	
Operating time	1 ms or less	
Off-delay time	200 ± 50 ms	
Applicable load	IC circuit, Relay, PLC	
Power supply voltage	5, 12, 24 VDC (4.5 to 28 VDC)	
Current consumption	10 mA or less	
Load voltage	28 VDC or less	
Load current	40 mA or less	
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA)	
Leakage current	100 μA or less at 24 VDC	
Indicator light Red LED illuminates when turned ON.		
Standard CE marking, RoHS		

Oilproof Heavy-duty Lead Wire Specifications

onproversions, and pound the opposition		
Auto switch model		D-F5NT
Sheath Outside diameter [mm]		ø4
Insulator	Number of cores	3 cores (Brown/Blue/Black)
insulator	Outside diameter [mm]	ø1.22
Conductor	Effective area [mm²]	0.3
	Strand diameter [mm]	ø0.08
Minimum bending radius [mm] (Reference values)		24


Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Timer Operation

Detection of intermediate positioning for high-speed cylinder

Detecting point dispersion occurs due to response time of PLC (sequencer); e.g. scanning.

Ex.) Cylinder speed — 1000 mm/sec. PLC response time — 0.1 sec. Detecting point dispersion — Within 100 mm (= 1000 mm/sec. x 0.1 sec.) Table PLC response time into consideration when using.



Weight


D FENT

	Auto switch model		D-F5NT
	Lead wire length	3 m (L)	81
		5 m (Z)	127

Dimensions

(mm)

(g)



Solid State Auto Switch with Timer Direct Mounting Type

D-M5NT/D-M5PT



Refer to SMC website for the details of the products conforming to the international standards.

Grommet

- With built-in OFF-delay timer (approx. 200 ms)
- Easy intermediate detection



Auto Switch Specifications

PLC: Programmable Logic Controller D-M5
T (With indicator light) Auto switch model D-M5NT D-M5PT Wiring type 3-wire Output type NPN PNP **Output operation** Off-delay Operating time 1 ms or less Off-delay time $200 \pm 50 \text{ ms}$ Applicable load IC circuit, Relay, PLC 5, 12, 24 VDC (4.5 to 28 VDC) Power supply voltage 10 mA or less 12 mA or less **Current consumption** 28 VDC or less Load voltage Load current 80 mA or less 2 V or less Internal voltage drop 0.8 V or less (0.8 V or less at 10 mA load current) Leakage current 100 μA or less at 24 VDC Indicator light Red LED illuminates when turned ON. Standard CE marking, RoHS

Oilproof Heavy-duty Lead Wire Specifications

<u>- </u>			
Auto switch model		D-M5NT	D-M5PT
Sheath Outside diameter [mm]		ø3.4	
Inculator	Number of cores	3 cores (Brown/Blue/Black)	
Insulator	Outside diameter [mm]	ø1.1	
Conductor	Effective area [mm²]	0.	2
	Strand diameter [mm]	ø0.08	
Minimum bending radius [mm] (Reference values)		2	1

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Timer Operation

Detection of intermediate positioning for high-speed cylinder

Detecting point dispersion occurs due to response time of PLC (sequencer); e.g. scanning.

Ex.) Cylinder speed - 1000 mm/sec. PLC response time - 0.1 sec. Detecting point dispersion - Within 100 mm (= 1000 mm/sec. x 0.1 sec.) Take PLC response time into consideration when using.

Auto switch detecting time	ON Auto switch operating range (mm) OFF Cylinder speed (mm/s)
Auto switch output ON time	ON (200 ms)
PLC response time	

Weight

Auto switch model		D-M5NT	D-M5PT
Lood wire length	3 m (L)	6	0


95


Dimensions

5 m (Z)

(mm)

(g)









Magnetic Field Resistant 2-Color Indicator Solid State Auto Switch

D-P3DWASC/D-P3DWASE (€ c PN us

(Electrical Entry: Pre-wired connector)

- It is possible to use in an environment which generates a magnetic field disturbance (AC magnetic field).
- The proper operating range can be determined by the color of the light. (Red → Green ← Red)



∆Caution

Precautions

For single-phase AC welding machines. If it is used for current inverter welders (including rectifying type) and condenser type welders, the magnetic field resistance is reduced. Please contact SMC regarding the performance.

Magnetic Field Resistance

If the current of the AC welding machine is 16000 A or lower, the auto switch can be used, even if the distance between the welding conductor (gun cable) and the cylinder/actuator or auto switch is 0 mm.

Please contact SMC when the AC welding current exceeds 16000 A.

Weight

(g)

Auto switch model		D-P3DWASC	D-P3DWASE
Lead wire length (m)	0.3	2	5



Connector pin

Model	Connector pin and wiring			
iviodei	1	2	3	4
D-P3DWASC	_	_	OUT(∓)	OUT(±)
D-P3DWASE	OUT(±)	-	-	OUT(∓)

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-P3DWASC/E (With indicator light)			
Auto switch model	D-P3DWASC D-P3DWASE		
Applicable load 24 VDC relay, PLC		elay, PLC	
Load voltage	24 \	/DC	
Load current 6 to 40 mA Internal voltage drop 5 V or less		0 mA	
		r less	
Leakage current	1 mA or less at 24 VDC		
Operating time	40 ms	or less	
Indicator light Operating range Red LED illuminates. Proper operating range Green LED illum			
Standard	CE marking, UL (CSA), RoHS		

Oilproof Heavy-duty Lead Wire Specifications


Auto sw	itch model	D-P3DWASC	D-P3DWASE
Sheath	Outside diameter [mm]	ø4.8	
Insulator	Number of cores	2 00	res
insulator	Outside diameter [mm]	ø1.	52
Conductor	Effective area [mm²]	0.	5
Conductor	Strand diameter [mm]	ø0.	08
Minimum bending radius [mm] (Reference values)		2	9


- Impact resistance Switch: 1000 m/s², Connector: 300 m/s²
- ullet Insulation resistance 50 M Ω or more at 500 VDC Mega (between lead wire and case)
- Withstand voltage 1000 VAC for 1 minute (between lead wire and case)
- Ambient temperature −10 to 60°C
- Enclosure IEC60529 standard IP67

Polarity: Non-polar

Dimensions

(mm)





Note) A white color heat shrink tube is attached to the D-P3DWASE type only.



Magnetic Field Resistant 2-Color Indicator Solid State Auto Switch

D-P3DWA (Electrical Entry: Grommet)

Refer to SMC website for the details of

Auto Switch Specifications

the products conforming to the international standards. PLC: Programmable Logic Controller

	PLC: Programmable Logic Controller		
D-P3DWA (With indicator light)			
Auto switch model	D-P3DWA		
Applicable load	24 VDC relay, PLC		
Load voltage	24 VDC		
Load current	6 to 40 mA		
Internal voltage drop	5 V or less		
Leakage current	1 mA or less at 24 VDC		
Operating time	40 ms or less		
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.		
Standard	CE marking LIL (CSA) BoHS		

Oilproof Heavy-duty Lead Wire Specifications

.Auto switch model		D-P3DWA
Sheath Outside diameter [mm]		ø4.8
Insulator	Number of cores	2 cores (Brown/Blue)
insulator	Outside diameter [mm]	ø1.52
Conductor	Effective area [mm²]	0.5
Conductor	Strand diameter [mm]	ø0.08
Minimum bending radius [mm] (Reference values)		29

- Impact resistance Switch: 1000 m/s²
- Insulation resistance 50 M Ω or more at 500 VDC Mega (between lead wire and case)
- Withstand voltage 1000 VAC for 1 minute (between lead wire and case)
- ◆ Ambient temperature -10 to 60°C
- Enclosure IEC60529 standard IP67
- · Polarity: Non-polar

• It is possible to use in an environment which generates

a magnetic field disturbance (AC magnetic field). The proper operating range

can be determined by the color of the light. $(Red \rightarrow Green \leftarrow Red)$



Precautions

For single-phase AC welding machines. If it is used for current inverter welders (including rectifying type) and condenser type welders, the magnetic field resistance is reduced. Please contact SMC regarding the performance.

Magnetic Field Resistance

If the current of the AC welding machine is 16000 A or lower, the auto switch can be used, even if the distance between the welding conductor (gun cable) and the cylinder/actuator or auto switch is 0 mm. Please contact SMC when the AC welding current exceeds 16000 A.

Weight

length

D-P3DWA Auto switch model 0.5 m (NiI) 22 Lead wire 3 m (L)

5 m (Z)

Dimensions


(mm)

Body

(g)

104

170







Magnetic Field Resistant 2-Color Indicator Solid State Auto Switch C & C Thus D-P3DWSC/D-P3DWSE

(Electrical Entry: Pre-wired connector)



• It is possible to use in an environment which generates a magnetic field disturbance

(AC magnetic field). The proper operating range

can be determined by the color of the light. $(Red \rightarrow Green \leftarrow Red)$



∆Caution

Precautions

For single-phase AC welding machines. If it is used for current inverter welders (including rectifying type) and condenser type welders, the magnetic field resistance is reduced. Please contact SMC regarding the performance.

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-P3DWSC/E (With indicator light)				
Auto switch model	D-P3DWSC	D-P3DWSE		
Applicable load	24 VDC relay, PLC			
Load voltage	24 \	/DC		
Load current	6 to 40 mA or less			
Internal voltage drop	5 V or less			
Leakage current	1 mA or less at 24 VDC			
Operating time	40 ms or less			
Indicator light Operating range Red LED illuminates. Proper operating range Green LED illuminate				
Standard	CE marking, UL (CSA), RoHS			

Oilproof Heavy-duty Lead Wire Specifications

Auto sw	itch model	D-P3DWSC	D-P3DWSE
Sheath	Outside diameter [mm]	ø4.8	
Insulator	Number of cores	2 00	ores
insulator	Outside diameter [mm]	ø1.52	
Conductor	Effective area [mm²]	0.	5
Conductor	Strand diameter [mm]	ø0.	.08
Minimum bending radius [mm] (Reference values)		2	9

- Impact resistance Switch: 1000 m/s², Connector: 300 m/s²
- Insulation resistance 50 MΩ or more (500 VDC measured via megohmmeter) (between lead wire and case)
- Withstand voltage 1000 VAC for 1 minute (between lead wire and case)
- ◆ Ambient temperature -10 to 60°C
- Enclosure IEC60529 standard IP67
- Polarity: Non-polar

Magnetic Field Resistance

If the current of the AC welding machine is 16000 A or lower, the auto switch can be used, even if the distance between the welding conductor (gun cable) and the cylinder/actuator or auto switch is 0 mm

Please contact SMC when the AC welding current exceeds 16000 A.

Weight

(g)


Auto switch model		D-P3DWSC	D-P3DWSE
Lead wire length (m)	0.3	2	3




Connector pin

Model	Connector pin/Wiring			
iviodei	1	2	3	4
D-P3DWSC	_	_	OUT(∓)	OUT(±)
D-P3DWSE	OUT(±)	_	_	OUT(∓)

Dimensions





* When the auto switch is ordered on its own, the auto switch mounting bracket is not enclosed. In that case, please order it separately.



Magnetic Field Resistant 2-Color Indicator Solid State Auto Switch C C Sus

D-P3DW (Electrical Entry: Grommet)

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-P3DW (With indicator light)				
Auto switch model	D-P3DW			
Applicable load	24 VDC relay, PLC			
Load voltage	24 VDC			
Load current	6 to 40 mA or less			
Internal voltage drop	5 V or less			
Leakage current	1 mA or less at 24 VDC			
Operating time	40 ms or less			
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.			
Standard	CE marking UL (CSA) BoHS			

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-P3DW
Sheath Outside diameter [mm]		ø4.8
Inculator	Number of cores	2 cores (Brown/Blue)
Insulator	Outside diameter [mm]	ø1.52
Conductor	Effective area [mm²]	0.5
	Strand diameter [mm]	ø0.08
Minimum bending radius [mm] (Reference values)		29

- Impact resistance Switch: 1000 m/s²
- ullet Insulation resistance 50 M Ω or more (500 VDC measured via megohmmeter) (between lead wire and case)
- Withstand voltage 1000 VAC for 1 minute (between lead wire and case)
- ◆ Ambient temperature -10 to 60°C
- Enclosure IEC60529 standard IP67
- Polarity: Non-polar

• It is possible to use in an environment which generates a magnetic field disturbance (AC magnetic field).

 The proper operating range can be determined by the color of the light. $(Red \rightarrow Green \leftarrow Red)$



∧Caution

Precautions

For single-phase AC welding machines. If it is used for current inverter welders (including rectifying type) and condenser type welders, the magnetic field resistance is reduced. Please contact SMC regarding the performance.

Magnetic Field Resistance

If the current of the AC welding machine is 16000 A or lower, the auto switch can be used, even if the distance between the welding conductor (gun cable) and the cylinder/actuator or auto switch is 0 mm.

Please contact SMC when the AC welding current exceeds 16000 A.


Weight


(g)


Auto switch model		D-P3DW
	0.5 m (Nil)	20
Lead wire length	3 m (L)	102
	5 m (Z)	168


Dimensions


(mm)











* When the auto switch is ordered on its own, the auto switch mounting bracket is not enclosed. In that case, please order it separately.



1633

Magnetic Field Resistant 2-Color Indicator Solid State Auto Switch D-P4DWSC/D-P4DWSE

(Electrical Entry: Pre-wired connector)

Grommet

- It is possible to use in an environment which generates a magnetic field disturbance (AC magnetic field).
- The proper operating range can be determined by the color of the light. $(Red \rightarrow Green \leftarrow Red)$



∆Caution

Precautions

For single-phase AC welding machines. Not applicable for DC inverter welding machines (including rectifying type) and or condenser type welding.



Connector pin

Model	Connector pin/Wiring			
iviouei	1	2	3	4
D-P4DWSC	_	_	OUT(∓)	OUT(±)
D-P4DWSE	OUT(±)	_	_	OUT(∓)

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-P4DWS□ (With indicator light)		
Auto switch model	D-P4DWSC	D-P4DWSE
Applicable load	24 VDC r	elay, PLC
Load voltage	24 VDC (20	to 28 VDC)
Load current	ad current 6 to 40 mA or less	
Internal voltage drop	5 V or less	
Leakage current 1 mA or less at 24 VDC		s at 24 VDC
Operating time	40 ms or less	
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.	
Standard	CE marking, RoHS	

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-P4DWSC	D-P4DWSE
Sheath Outside diameter [mm] Ø6		6	
Inculator	Number of cores	2 00	ores
Insulator	Outside diameter [mm]	ø2.3	
Conductor	Effective area [mm²]	0.	5
	Strand diameter [mm]	ø0.08	
Minimum bending radius [mm] (Reference values)		4	8

 ■ Impact resistance — Switch: 1000 m/s², Connector: 300 m/s² Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Magnetic Field Resistance

Indicator light


If the current of the AC welding machine is 16000 A or lower, the auto switch can be used, even if the distance between the welding conductor (gun cable) and the cylinder or switch is 0 mm. Please contact SMC when the AC welding current exceeds 16000 A.

Weight (g)

Auto switch model	D-P4DWSC	D-P4DWSE	
	Auto switch model	3	5

Dimensions

(mm)



Note) Only for D-P4DWSE Printed contents: SE 1-4



Magnetic Field Resistant 2-Color Indicator Solid State Auto Switch

D-P4DW



Grommet

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-P4DW (With indicator light)		
Auto switch model	D-P4DW	
Applicable load	24 VDC relay, PLC	
Load voltage	24 VDC (20 to 28 VDC)	
Load current	6 to 40 mA or less 5 V or less	
Internal voltage drop		
Leakage current	1 mA or less at 24 VDC	
Operating time	40 ms or less	
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.	
Standard	CE marking BoHS	

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-P4DW
Sheath Outside diameter [mm]		ø6
Insulator	Number of cores	2 cores (Brown/Blue)
	Outside diameter [mm]	ø1.92
Conductor	Effective area [mm²]	0.5
	Strand diameter [mm]	ø0.08
Minimum bending radius [mm] (Reference values)		36

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Auto Switch Specifications

• It is possible to use in an environment which generates a magnetic field disturbance (AC magnetic field).

 The proper operating range can be determined by the color of the light.

 $(Red \rightarrow Green \leftarrow Red)$



Precautions

For single-phase AC welding machines. Not applicable for DC inverter welding machines (including rectifying type) and or condenser type welding.

Magnetic Field Resistance


If the current of the AC welding machine is 16000 A or lower, the auto switch can be used, even if the distance between the welding conductor (gun cable) and the cylinder or switch is 0 mm. Please contact SMC when the AC welding current exceeds 16000 A.


Weight

(g)

Auto switch model		D-P4DW
Lood wire length	3 m (L)	150
Lead wire length	5 m (7)	244

Dimensions







Heat Resistant 2-Color Indicator Solid State Auto Switch: Direct Mounting Type

D-M9NJ/D-M9PJ

Refer to SMC website for the details of the products conforming to the

international standards.

Grommet

 Improved heat resistant type The proper operating range can be determined by the color of the light. $(Red \rightarrow Green \leftarrow Red)$





∧Caution

Precautions

This auto switch can be mounted on the cylinder with heat resistant auto switch (-XB14) and is not applicable to the heat resistant cylinder (-XB6) since a magnet is not built in it.

Do not disconnect the cable between the sensor and amplifier by the customer.

Even when the sensor and amplifier are connected again, a contact resistance is produced, causing the auto switch to malfunction. Additionally, the sensor and amplifier are paired and they do not operate correctly in different combinations.

Auto Switch Specifications

PLC: Programmable Logic Controller D-M9NJ/D-M9PJ (With indicator light) Auto switch model D-M9NJ D-M9PJ Output type NPN PNP Power supply voltage 20 to 26 VDC 25 mA or less Current consumption Load voltage 28 VDC or less Load current 40 mA or less Internal voltage drop 0.8 V or less Leakage current 100 μA at 24 VDC Operating range Red LED illuminates. Indicator light Proper operating range Green LED illuminates. Sensor section: 0 to 150°C Ambient temperature Amplifier section: 0 to 60°C Sensor section: 1000 m/s2 Impact resistance Amplifier section: 300 m/s2 Standard CE marking, RoHS

Oilproof Heavy-duty Lead Wire Specifications (Grommet)


Auto switch model		D-M9NJ	D-M9PJ
Sheath	Outside diameter [mm]	n] ø3.4	
Insulator	Number of cores	3 cores (Brow	n/Blue/Black)
	Outside diameter [mm]	ø1.1	
0	Effective area [mm²]	0.	2
Conductor	Strand diameter [mm]	ø0.	08
Minimum bending radius [mm] (Reference values)		2	1


Weight

(g)

Auto swit	tch model	D-M9NJ	D-M9PJ
Lood wire length	3 m (L)	16	60
Lead wire length	5 m (Z)	20	00

Dimensions







Heat Resistant 2-Color Indicator Solid State Auto Switch: Rail Mounting Type D-F7NJ

Grommet

 Improved heat resistant type The proper operating range can be determined by the color of the light. $(Red \rightarrow Green \leftarrow Red)$



∆Caution

Precautions

Auto switch which can be mounted on heat resistant, compact cylinder, CDQ2-XB14. For using for other cylinders, please confirm

D-F7NJ is not applicable for the heat resistant type (-XB6) since a magnet is not built in it.

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

	PLC: Programmable Logic Controller	
D-F7NJ (With indicator light)		
Auto switch model	D-F7NJ	
Wiring type	3-wire	
Output type	NPN	
Applicable load	Relay, PLC	
Power supply voltage	24 VDC (20 to 26 VDC)	
Current consumption	25 mA or less	
Load voltage	28 VDC or less	
Load current	40 mA or less	
Internal voltage drop	0.8 V or less	
Leakage current	100 μA at 24 VDC	
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.	
Ambient temperature	Sensor section: 0 to 150°C Amplifier section: 0 to 60°C	
Impact resistance	Sensor section: 1000 m/s ² Amplifier section: 300 m/s ²	
Standard	Standard CE marking, RoHS	

Oilproof Heavy-duty Lead Wire Specifications (Grommet)

Auto switch model		D-F7NJ
Sheath Outside diameter [mm]		ø3.4
Inculator	Number of cores	3 cores (Brown/Blue/Black)
Insulator	Outside diameter [mm]	ø1.1
Conductor	Effective area [mm²]	0.2
Conductor	Strand diameter [mm]	ø0.08
Minimum bending radius [mm] (Reference values)		21


Weight

	Auto switch model		D-F7NJ
	Lead wire length	3 m (L)	170
		5 m (Z)	210

Dimensions

(mm)

(g)



D-□



Wide Range Detection Type Solid State Auto Switch: Band Mounting Type

D-G5NB



Grommet

- Wide range detection type
- Easy intermediate detection



∆Caution

Precautions

The operating range is common for all cylinder series, but it may vary depending on bore sizes.

Weight

(g)

Auto swi	D-G5NB	
Lead wire length	3 m (L)	79
	5 m (Z)	125

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

	i Eo. i rogrammable Eogic Comioliei				
D-G5NB (With indicator light)					
Auto switch model	D-G5NB				
Wiring type	3-wire				
Output type NPN					
Applicable load	Relay, PLC				
Power supply voltage	12, 24 VDC (10 to 28 VDC)				
Current consumption	12 mA or less				
Load voltage	10 to 28 VDC or less				
Load current	40 mA or less				
Internal voltage drop	0.4 V or less				
Leakage current	100 μA at 24 VDC				
Indicator light	Red LED illuminates when turned ON.				
Standard	CE marking, RoHS				

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-G5NB
Sheath Outside diameter [mm]		ø4
Inquilates	Number of cores	3 cores (Brown/Blue/Black)
Insulator	Outside diameter [mm]	ø1.22
Conductor	Effective area [mm²]	0.3
Conductor	Strand diameter [mm]	ø0.08
Minimum bending radius [mm] (Reference values)		24

Note 1) Refer to page 1584 for solid state auto switch common specifications. Note 2) Refer to page 1584 for lead wire lengths.

Applicable Cylinders


Cylinder series	Bore size (mm)
CDM2-Z, CDM2, CDBM2, CDVM3, CDVM5, CDLM2, CDLG1, MLGC	20, 25, 32, 40
CDG1-Z, CDG1	20, 25, 32, 40, 50, 63, 80, 100
CDA2-Z, CDA2, CDBA2, CDV3, CDVS1, CDL1	40, 50, 63, 80, 100
MGC, MGG	20, 25, 32, 40, 50

Operating Range

Cylinder series				Bore siz	ze (mm)			
Cylinder series	20	25	32	40	50	63	80	100
Mountable models	35	40	40	45	45	45	45	50

Note) The operating range above indicates average values at room temperature including hysteresis (assuming approximately ±30% dispersion).

Dimensions



^{*} Refer to page 520 for CDA2 and CDBA2.



Made to Order Specifications: **Solid State Auto Switch**

Refer to SMC website for the details of the products conforming to the international standards.

1 With Pre-wired Connector


• Eliminates the harnessing work by cable with connector specifications

Adopts global standardized connector (IEC947-5-2)

• IP67 construction



How to Order



L 3.0 m Note) L is available Note) Type D is

for the D-P4DW type only.

available for the D-P4DW type

Connector Specifications

Connector model	M8-3 pin	M8-4 pin	M12-4 pin
Pin arrangement	1 4	3 4	② ① ③ ④

Applicable Auto Switch


Manuatian	F	Electrical	A li l- l l - l	Lead v	vire len	gth (m)
Mounting	Function	entry	Applicable model	0.5	1.0	3.0
		Grommet (In-line)	F79, F7P, J79	•	•	_
	_	Grommet (Perpendicular)	F7NV, F7PV, F7BV	•	•	_
	2-color	Grommet (In-line)	F79W, F7PW, J79W	•	•	_
Rail	indicator	Grommet (Perpendicular)	F7NWV, F7BWV	•	•	_
mounting	With diagnostic output	Grommet (In-line)	F79F	•	•	_
type	Water resistant	Gronnine (in-line)	F7BA	•	•	_
	water resistant	Grommet (Perpendicular)	F7BAV	•	•	_
	With timer		F7NT	•	•	_
	Magnetic field resistant]	P4DW	•	•	•
			H7A1, H7A2, H7B	•	•	_
	_		G59, G5P, K59	•	•	_
	2-color]	H7NW, H7PW, H7BW	•	•	_
Band	indicator		G59W, G5PW, K59W	•	•	_
mounting type	Diagnostic output	Grommet (In-line)	H7NF, G59F	•	•	_
уро	Water resistant	1	H7BA, G5BA	•	•	_
	With timer]	G5NT	•	•	_
	Wide detection	1	G5NB	•	•	_
	_		F59, F5P, J59	•	•	_
Tie-rod	2-color indicator	1	F59W, F5PW, J59W	•	•	_
mounting	Diagnostic output	1	F59F	•	•	_
type	Water resistant	1	F5BA	•	•	_
	With timer	1	F5NT	•	•	_

Mounting	Function	Electrical	Applicable model	Lead wire length (m)		
I diletion		entry	Applicable model	0.5	1.0	3.0
		Grommet (In-line)	Y59A, Y7P, Y59B	•	•	_
		Grommet (Perpendicular)	Y69A, Y7PV, Y69B	•	•	
		Grommet (In-line)	M9N, M9P, M9B	•	•	_
	_	Grommet	M9NV, M9PV, M9BV	•	•	_
		(Perpendicular)	F8N, F8P, F8B	•	•	_
		Grommet (In-line)	F6N, F6P, F6B	•	•	_
Direct	Normally closed	Grommet (In-line)	Y7G, Y7H	•	•	_
mounting			F9G, F9H	•	•	
type	2-color indicator	Grommet (In-line)	Y7NW, Y7PW, Y7BW	•	•	_
		Grommet (Perpendicular)	Y7NWV, Y7PWV, Y7BWV	•	•	_
		Grommet (In-line)	M9NW, M9PW, M9BW	•	•	_
		Grommet (Perpendicular)	M9NWV, M9PWV, M9BWV	•	•	_
		Grommet (In-line)	Y7BA	•	•	_
	Water resistant	` ′	M9NA, M9PA, M9BA	•	•	
		Grommet (Perpendicular)	M9NAV, M9PAV, M9BAV	•	•	_
Poton/		Grommet (In-line)	S791/2, S7P1/2, T791/2	•	•	_
Rotary	_	` ′	S991/2, S9P1/2, T991/2	•	•	_
		Grommet (Perpendicular)	S99V1/2, T99V1/2	•	•	_

With Pre-wired Connector

Connector Pin Arrangement






Connector Specifications

Connector model	M8-3 pin	M8-4 pin	M12-4 pin		
Pin arrangement	1 4	3 4	② ① ③ ④		
Conformed standard	JIS C 4524, JIS C 4525, IEC 947-5-2, NECA 0402				
Impact resistance	300 m/s ²				
Enclosure	IP67 (IEC60529 standard)				
Insulation resistance	100 $M\Omega$ or more at 500 VDC measured via megohmmeter				
Withstand voltage	1500 VAC 1 minute (between contacts), Leak current 1 mA or less				



M8-4 pin

Dimensions





M12-4 pin

Weight for Connector Type

Part no.	Connector type	Weight
D-□□□APC	M8-3 pin	4 g
D-□□□BPC	M8-4 pin	4 g
D-□□□DPC	M12-4 pin	About 11 g

Connection (Female side) Connector Cable

As the parts are not supplied from SMC, refer to the application examples listed in the below. (For detail such as catalog availability, etc., please contact each manufacturer.)

Connector size	Number of pins	Manufacturer	Applicable series example	
	3	Phoenix Contact	SAC-3P	
M8	3	Corrence Corporation	M8-3D	
WIO		Corrence Corporation	M8-4D	
		OMROM Corporation	XS3	
	4	Phoenix Contact	SAC-4P	
		Corrence Corporation	VA-4D	
M12		OMROM Corporation	XS2	
		Azbil Corp.	PA5-4I	
		HIROSE ELECTRIC CO., LTD.	HR24	
		DDK Ltd.	CM01-8DP4S	




Made to Order Specifications: Solid State Auto Switch -50: Without Indicator Light (Dark room) Specifications -61: Oilproof Flexible Heavy-duty Cord Specifications

2 Without Indicator Light (for dark room specifications)

-50

Possible to use under the environment which hates a light.




Dimensions and specifications are common as standard products with the exception of no indicator light.

3 Oilproof Flexible Heavy-duty Cord Specifications

Symbol -61

This is the product which uses a heavy-duty cord having flexible characteristics 5 times (SMC comparison) as strong as oilproof heavy-duty cord used in the standard products.




Dimensions are identical with D-F5 type, G5 type, J59 type, K59 type. Lead wire diameter is changed from ø4 to ø3.4. In other series products, it is common as standard product's specifications.



Reed Auto Switches

General Purpose Type, 2-Color Indicator

Reed Switch Variations



^{*} Auto switches with an asterisk (*) can be mounted on a band (excluding D-A9□V), rail, tie-rod or square groove with an auto switch mounting bracket. Refer to pages 1680, 1684, 1688 and 1696 to 1698 for details.





^{**} This auto switch can be mounted by tie-rod with using auto switch mounting bracket. For details, refer to page 1691.

Reed Auto Switch Direct Mounting Type D-A90(V)/D-A93(V)/D-A96(V) (€

Grommet D-A93 D-A90 (V) D-A93V D-A96 (V)

Precautions

Fix the auto switch with the existing screw installed on the auto switch body. The auto switch may be damaged if a screw other than the one supplied is used.

Auto Switch Specifications

the products conforming to the international standards.

(g)

	PLC: Programmable Logic Controller					
D-A90, D-A90V (Without indicator light)						
Auto switch model	D-A90, D-A90V					
Applicable load		IC circuit, Relay, PLC				
Load voltage	24 V AC or less	48 V AC or less	100 V DC or less			
Maximum load current	50 mA	40 mA	20 mA			
Circuit diagram*		4				
Contact protection circuit	None					
Internal resistance	1 Ω or less (Including lead wire length of 3 m)					
Standard	CE marking					
D-A93, D-A93V, D-A96, D-A96V (With indicator light)						
Auto switch model	D-A93,	D-A96, D-A96V				
Applicable load	Relay	, PLC	IC circuit			
Load voltage	24 VDC ⁽⁴⁾	100 VAC	4 to 8 VDC			
Load current range and Maximum load current (3)	5 to 40 mA 5 to 20 mA		20 mA			
Circuit diagram*	3 5					
Contact protection circuit	None					
Internal voltage drop	D-A93: 2.4 V or less (up to 20 mA)/3 V or less (up to 40 mA) D-A93V: 2.7 V or less		0.8 V or less			
Indicator light	Red LED illuminates when turned ON.					
Standard	CE marking					

Oilproof Heavy-duty Lead Wire Specifications

	Auto switch model		D-A90(V)	D-A93(V)	D-A96(V)		
	Sheath	Outside diameter [mm]	ø2.7				
	Inquilates	Number of cores	2 cores (Brown/Blue)		3 cores (Brown/Blue/Black)		
	Insulator	Outside diameter [mm]	ø0.96		ø0.91		
	Conductor	Effective area [mm²]	0.18		0.15		
	Conductor	Strand diameter [mm]	ø0.08				
Lead	Lead wire minimum bending radius [mm] (Reference values)		17				

* Refer to the circuit diagram no. on page 1587.

Note 1) Refer to page 1584 for reed auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.

Note 3) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator

light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or more.

Note 4) The auto switches can operate at 12 VDC, but consider the internal voltage drop of the auto

switch described in Reed Auto Switch Precautions on page 12.


Weight


Model		D-A90	D-A90V	D-A93	D-A93V	D-A96	D-A96V
	0.5 m (NiI)	6	6	6	6	8	8
Lead wire length	1 m (M)	_	_	11	_	_	_
	3 m (L)	30	30	30	30	41	41

Dimensions (mm)

3 m (L)

5 m (Z)





Reed Auto Switch Band Mounting Type D-C73/D-C76/D-C80

((

Grommet



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-C7 (With indicator light)						
Auto switch model	D-0	D-C76				
Applicable load	Relay, PLC		IC circuit			
Load voltage	24 VDC ⁽⁴⁾	100 VAC	4 to 8 VDC			
Max. load current and range (3)	5 to 40 mA 5 to 20 mA		20 mA			
Circuit diagram*	(3	3)	(5)			
Contact protection circuit		None				
Internal voltage drop	2.4	V or less	0.8 V or less			
Indicator light	ator light Red LED illuminates when turned ON.					
Standard	CE marking					
D-C8 (Without indicator light)						
Auto switch model D-C80						
Applicable load	Relay, PLC, IC circuit					
Load voltage	24 V AC or less 48 V AC 100 V AC DC					
Max. load current	50 mA 40 mA 20 mA		20 mA			
Circuit diagram*	(4)					
Contact protection circuit	None					
Internal resistance	1 Ω or less (Including lead wire length of 3 m)					
Standard	CE marking					

Oilproof Heavy-duty Lead Wire Specifications

Chiprocally daily add that operations						
Auto switch model		D-C73	D-C76	D-C80		
Sheath	Outside diameter [mm]	ø3.4				
Inculator	Number of cores	2 cores (Brown/Blue)	3 cores (Brown/Blue/Black)	2 cores (Brown/Blue)		
Insulator	Outside diameter [mm]	ø1.1				
Conductor	Effective area [mm²]	0.2				
Conductor	Strand diameter [mm]	ø0.08				
Lead wire minimum bending radius [mm] (Reference values)		21				

^{*} Refer to the circuit diagram no. on page 1587.

Note 3) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or more.

Note 4) The auto switches can operate at 12 VDC, but consider the internal voltage drop of the auto switch described in Reed Auto Switch Precautions on page 12.


Weight

(g)

Auto switch model		D-C73	D-C76	D-C80	
	0.5 m (Nil)	9	10	9	
Lead wire length	3 m (L)	46	50	46	
	5 m (Z)	76	_	_	

Dimensions

(mm)



D-□



Note 1) Refer to page 1584 for reed auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.

Reed Auto Switch Band Mounting Type D-B53/D-B54/D-B64

 ϵ

Grommet



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-B5 (With indicator light)						
Auto switch model	D-B53		D-B54			
Applicable load	PLC		Relay, PLC			
Load voltage	24 VDC(4)	24 VDC ⁽⁴⁾	100 VAC	200 VAC		
Load current range (3)	5 to 50 mA	5 to 50 mA	5 to 25 mA	5 to 12.5 mA		
Circuit diagram*	3		1			
Contact protection circuit	None		Built-in			
Internal voltage drop	2.4 V or less	2.4 V or less (Up	to 20 mA)/3.5 V or	less (Up to 50 mA)		
Indicator light	Red	LED illuminates	when turned O	N.		
Standard		CE marking				
D-B6 (Without indica	tor light)					
Auto switch model		D-B	64			
Applicable load		Relay,	PLC			
Load voltage	24 V AC or less	100 V	AC	200 VAC		
Max. load current	Max. 50 mA Max. 25 mA Max. 12.5 mA					
Circuit diagram*	2					
Contact protection circuit	Built-in					
Internal resistance	25 Ω or less					
Standard	CE marking					

Oilproof Heavy-duty Lead Wire Specifications

onprocessions, and bound opposition				
Auto swi	tch model	D-B53/B54/B64		
Sheath	Outside diameter [mm]	ø4		
Insulator	Number of cores	2 cores (Brown/Blue)		
insulator	Outside diameter [mm]	ø1.22		
Conductor	Effective area [mm2]	0.3		
Conductor	Strand diameter [mm]	ø0.08		
Lead wire minimum bending	radius [mm] (Reference values)	24		

^{*} Refer to the circuit diagram no. on page 1587.

Note 3) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or more.

Note 4) The auto switches can operate at 12 VDC, but consider the internal voltage drop of the auto switch described in Reed Auto Switch Precautions on page 12.


Weight


Auto swit	ch model	D-B53	D-B54	D-B64
	0.5 m (Nil)	22	22	22
Lead wire length	3 m (L)	78	78	78
	E (7)	100	100	

Dimensions

(mm)

(g)







Note 1) Refer to page 1584 for reed auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.

Reed Auto Switch Band Mounting Type D-C73C/D-C80C

Connector



^Caution

Precautions

- 1. Confirm that the connector is appropriately tightened. If tightened insufficiently, the waterproof performance will deteriorate.
- 2. For details, refer to page 1679.

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

	PLC: Programmable Logic Controller
D-C73C (With indicator	light)
Auto switch model	D-C73C
Applicable load	Relay, PLC
Load voltage	24 VDC ⁽⁵⁾
Load current range (4)	5 to 40 mA
Circuit diagram*	3
Contact protection circuit	None
Internal voltage drop	2.4 V or less
Indicator light	Red LED illuminates when turned ON.
Standard	CE marking
D-C80C (Without indica	tor light)
Auto switch model	D-C80C
Applicable load	Relay, PLC
Load voltage	24 V _{DC} or less
Maximum load current	50 mA
Circuit diagram*	4
Contact protection circuit	None
Internal resistance	1 Ω or less (Including lead wire length of 3 m)
Standard	CE marking

* Refer to the circuit diagram no. on page 1587.

Note 1) Refer to page 1584 for reed auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.

Note 3) Lead wire with connector may be shipped with switch.

Note 4) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or more.

Note 5) The auto switches can operate at 12 VDC, but consider the internal voltage drop of the auto switch described in Reed Auto Switch Precautions on page 12.

Weight

(g)

Auto swit	tch model	D-C73C	D-C80C
	0.5 m (Nil)	14	14
Lead wire length	3 m (L)	53	53
	5 m (Z)	83	83


Lead wires with a connector indication

Part No. of Lead Wires with Connectors (Applicable only for connector type)

Model	Lead wire length
D-LC05	0.5 m
D-LC30	3 m
D-LC50	5 m

Dimensions

(mm)



Reed Auto Switch Band Mounting Type D-A33/D-A34/D-A44

((

Terminal conduit: D-A3 DIN terminal: D-A4



△Caution

Precautions

- Use cable whose O.D. is within the size in the figure to maintain water resistant performance.
- After wiring, confirm that tightening gland and all screws are tightened.

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC:	Programmable	Logic	Controlle	16

D-A3 (With indicator light) Terminal conduit						
Auto switch model	D-A33			D-A34		
Applicable load	PLC			Relay, PLC		
Load voltage	24 VDC (3)	24	VDC (3)	100 VAC	200 VAC	
Load current range (2)	5 to 50 mA	5 to	50 mA	5 to 25 mA	5 to 12.5 mA	
Circuit diagram*	3			1		
Contact protection circuit	None			Built-in		
Internal voltage drop	2.4 V or less	2.4 V	or less (Up t	to 20 mA)/3.5 V o	r less (Up to 50 mA)	
Indicator light	ı	Red LE	D illuminate	s when turned (N.	
Standard			CE m	arking		
D-A44 (With indic	ator light) DI	N teri	minal			
Auto switch model			D-A	\44		
Applicable load			Relay	, PLC		
Load voltage	24 VDC (3)		100	VAC	200 VAC	
Load current range	5 to 50 mA		5 to 2	5 mA	5 to 12.5 mA	
Circuit diagram*			(D		
Contact protection circuit	Built-in					
Internal voltage drop	2.4 V or less (Up to 20 mA)/3.5 V or less (Up to 50 mA)					
Indicator light	Red LED illuminates when turned ON.					
Standard	•		CE m	arking		

^{*} Refer to the circuit diagram no. on page 1587.

Note 1) Refer to page 1584 for reed auto switch common specifications.

Note 2) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or more.


Note 3) The auto switches can operate at 12 VDC, but consider the internal voltage drop of the auto switch described in Reed Auto Switch Precautions on page 12.

Weight

(g)

Auto switch mode	el	D-A33	D-A34	D-A44
Lead wire	None	116	116	114

D-A3 D-A4 Tightening gland Tightening gland





Reed Auto Switch Band Mounting Type D-A33A/D-A34A/D-A44A

 ϵ

Terminal conduit: D-A3□A DIN terminal: D-A44A





∆Caution

Precautions

- Use cable whose O.D. is within the size in the figure to maintain water resistant performance
- 2. After wiring, confirm that tightening gland and all screws are tightened.

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

	PLC: Programmable Logic Controller					
D-A3□A (With indicate	ator light) Te	ermin	al cond	uit		
Auto switch model	D-A33A			D-A34	4	
Applicable load	PLC			Relay, PL	.C	
Load voltage	24 VDC (3)	24	VDC (3)	100 VA	0	200 VAC
Load current range (2)	5 to 50 mA	5 to	50 mA	5 to 25 m	ıΑ	5 to 12.5 mA
Circuit diagram*	3			1)		
Contact protection circuit	None			Built-in		
Internal voltage drop	2.4 V or less	2.4 V	or less (Up t	o 20 mA)/3.5	V or I	ess (Up to 50 mA)
Indicator light	В	ed LED) illuminate	s when turn	ed Ol	N.
Standard		CE marking				
D-A44A (With indica	tor light) DII	N terr	minal			
Auto switch part model			D-A4	4 A		
Applicable load			Relay,	PLC		
Load voltage	24 VDC (3	3)	100 V	'AC		200 VAC
Load current range	5 to 50 m/	A	5 to 25	i mA	5	to 12.5 mA
Circuit diagram*			1			
Contact protection circuit	Built-in					
Internal voltage drop	2.4 V or less	s (Up to	o 20 mA)/3	3.5 V or less	(Up	to 50 mA)
Indicator light	Red LED illuminates when turned ON.					
Standard			CE ma	rking		

^{*} Refer to the circuit diagram no. on page 1587.

D-A44

Note 1) Refer to page 1584 for reed auto switch common specifications.

Note 2) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or more.

Note 3) The auto switches can operate at 12 VDC, but consider the internal voltage drop of the auto switch described in Reed Auto Switch Precautions on page 12.

Weight


(g)


Auto switch mode	el	D-A33A	D-A34A	D-A44A
Lead wire	None	112	112	110


Dimensions

(mm)

D-A3□A









Reed Auto Switch Rail Mounting Type D-A72/D-A73/D-A80

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards. PLC: Programmable Logic Controller



Grommet

Electrical entry: Perpendicular

D-A7 (With indicator light)						
Auto switch model	D-A72	D-A72 D-A73				
Applicable load	Relay, PLC	Relay	, PLC			
Load voltage	200 VAC	24 VDC (4)	100 VAC			
Load current range (3)	5 to 10 mA	5 to 40 mA	5 to 20 mA			
Circuit diagram*		3				
Contact protection circuit		None				
Internal voltage drop	2.4 V or less					
Indicator light	Red LED illuminates when turned ON.					
Standard	CE marking					
D-A8 (Without indicator	r light)					
Auto switch model		D-A80				
Applicable load		Relay, IC circuit, PLC	;			
Load voltage	24 V DC or less	48 V AC	100 V AC			
Maximum load current	50 mA	40 mA	20 mA			
Circuit diagram*	4					
Contact protection circuit	None					
Internal resistance	1 Ω or less	(Including lead wire le	ngth of 3 m)			
Standard		CE marking				

Oilproof Heavy-duty Lead Wire Specifications

- production y and y contract operations						
Auto switch model		D-A72	D-A72 D-A73			
Sheath	Outside diameter [mm]		ø3.4			
Insulator	Number of cores	2 cores (Brown/Blue)				
insulator	Outside diameter [mm]	ø1.1				
Conductor	Effective area [mm²]		0.2			
Conductor	Strand diameter [mm]	ø0.08				
Lead wire minimum bendin	ng radius [mm] (Reference values)		21			

[•] Lead wire Oilproof vinyl cabtire cord: ø3.4, 0.2 mm2, 2 cores (Brown, Blue), 0.5 m

* Refer to the circuit diagram no. on page 1587.

Note 1) Refer to page 1584 for reed auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.

Note 3) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or


Note 4) The auto switches can operate at 12 VDC, but consider the internal voltage drop of the auto switch described in Reed Auto Switch Precautions on page 12.

Weight

(g)

Auto swi	Auto switch model		D-A73	D-A80
	0.5 m (NiI)	10	10	10
Lead wire length	3 m (L)	47	47	47
	5 m (Z)	_	77	_

Dimensions





Reed Auto Switch Rail Mounting Type D-A7 H/D-A80H

Grommet Electrical entry: In-line



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

1 20: 1 Togrammable 20gle Controller					
D-A7□H (With indicator light)					
Auto switch model	D-A72H	D-A73H		D-A76H	
Applicable load	Relay, PLC	Relay, PLC		IC circuit	
Load voltage	200 VAC	24 VDC (4)	100 VAC	4 to 8 VDC	
Max. load current/Load current range(3)	5 to 10 mA	5 to 40 mA	5 to 20 mA	20 mA	
Circuit diagram*		3		(5)	
Contact protection circuit	None				
Internal voltage drop	2.4 V or less 0.8 V or le			0.8 V or less	
Indicator light	Red LED illuminates when turned ON.				
Standard		CE r	narking		
D-A80H (Without indica	tor light)				
Auto switch model		D-	A80H		
Applicable load		Relay, IC	circuit, PLC		
Load voltage	24 V AC or le	ss 48	V AC	100 V AC	
Maximum load current	50 mA	4) mA	20mA	
Circuit diagram*			4		
Contact protection circuit	None				
Internal resistance	1 Ω οι	r less (Including	lead wire leng	th of 3 m)	
OtII		05	and description		

Oilproof Heavy-duty Lead Wire Specifications

onproversions, and, even the operations						
Auto switch model		D-A72H/A73H	D-A80H			
Sheath	Outside diameter [mm]	ø3.4				
Insulator	Number of cores	2 cores (Brown/Blue)	2 cores (Brown/Blue)			
irisulator	Outside diameter [mm]	ø1.1				
Conductor	Effective area [mm²]	0.2				
Conductor	Strand diameter [mm]	ø0.08				
Lead wire minimum bending ra	re minimum bending radius (mm) (Reference values) 21					

* Refer to the circuit diagram no. on page 1587.

Note 1) Refer to page 1584 for reed auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.

Note 3) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or

Note 4) The auto switches can operate at 12 VDC, but consider the internal voltage drop of the auto switch described in Reed Auto Switch Precautions on page 12.

Weight


Auto swit	Auto switch model		D-A73H	D-A76H	D-A80H
	0.5 m (NiI)	10	10	11	10
Lead wire length	3 m (L)	47	47	52	47
	5 m (7)	_	77		_

Dimensions


(mm)

(g)

D-A7 H. D-A80H









Reed Auto Switch Rail Mounting Type D-A73C/D-A80C

 ϵ

Connector



∆Caution

Precautions

- Confirm that the connector is appropriately tightened. If tightened insufficiently, the waterproof performance will deteriorate.
- 2. Refer to page 1679 for the details.

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

	PLC: Programmable Logic Controller
D-A73C (With indicator	light)
Auto switch model	D-A73C
Applicable load	Relay, PLC
Load voltage	24 VDC (5)
Load current range (4)	5 to 40 mA
Circuit diagram*	3
Contact protection circuit	None
Internal voltage drop	2.4 V or less
Indicator light	Red LED illuminates when turned ON.
Standard	CE marking
D-A80C (Without indica	ator light)
Auto switch model	D-A80C
Applicable load	Relay, IC circuit, PLC
Load voltage	24 V AC
Maximum load current	50 mA
Circuit diagram*	4
Contact protection circuit	None
Internal resistance	1 Ω or less (Including lead wire length of 3 m)
Standard	CE marking

* Refer to the circuit diagram no. on page 1587.

Note 1) Refer to page 1584 for reed auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.

Note 3) Lead wire with connector may be shipped with the auto switch.

Note 4) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or more.

Note 5) The auto switches can operate at 12 VDC, but consider the internal voltage drop of the auto switch described in Reed Auto Switch Precautions on page 12.

Lead wires with a connector indication Part No. of Lead Wires with Connectors

(Applicable only for connector typ				
	Model	Lead wire length		
	D-LC05	0.5 m		
	D-LC30	3 m		
	D-LC50	5 m		


Weight

Auto switch model		D-A73C	D-A80C
	0.5 m (Nil)	12	12
Lead wire length	3 m (L)	54	54
	5 m (7)	84	84

Dimensions

(mm)

(g)



Reed Auto Switch Tie-rod Mounting Type D-A5□/**D-A6**[

Grommet



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-A5 (With indicator light)							
Auto switch model	D-A53	D-A54 [
Applicable load	PLC		Relay, PLC				
Load voltage	24 VDC (4)	24 VDC (4)	4 to 8 VDC				
Maximum load (3) current and range	5 to 50 mA	5 to 50 mA	5 to 25 mA	5 to 12.5 mA	20 mA		
Circuit diagram*	3		1)		(5)		
Contact protection circuit	None		None				
Internal voltage drop	2.4 V or less	2.4 V or less (Up to 20 mA)/3.5 V or less (Up to 50 mA) 0.8 V					
Indicator light		Red LED il	luminates whe	n turned ON.			

Standard	CE marking						
D-A6 (Without indicator light)							
Auto switch model	D-A64 D-A67						
Applicable load		Relay, PLC					
Load voltage	24 V AC or less	24 V AC or less 100 VAC 200 VAC					
Maximum load current	50 mA	50 mA 25 mA 12.5 mA					
Circuit diagram*		2		4			
Contact protection circuit		Built-in		None			
Internal resistance		1 Ω or less (Including lead wire length of 3 m)					
Standard	CE marking						

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-A53/A54 D-A56		D-A64/A67	
Sheath	Outside diameter [mm]	ø4			
In a colored	Number of cores	2 cores (Brown/Blue)	3 cores (Brown/Blue/Black)	2 cores (Brown/Blue)	
msulator	Outside diameter [mm]				
Conductor	Effective area [mm ²]	0.3	0.2	0.3	
Conductor	Strand diameter [mm]	ø0.08			
Lead wire minimum bending radius [mm] (Reference values)		24			


Weight

(g)


Auto swit	tch model	D-A53	D-A54	D-A56	D-A64	D-A67
	0.5 m (NiI)	-	24	24	24	
Lead wire length	3 m (L)		30	80	80)
Load Wile length	5 m (Z)	13	25	_	_	

Dimensions

(mm)









<sup>Refer to the circuit diagram no. on page 1587.

Note 1) Refer to page 1584 for reed auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.

Note 3) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will</sup> not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of

not be possible where the output stylian less than 20 miles to the less than 20 miles to be problem in terms or contact output, when an output signal exceeds 1 mile or more.

Note 4) The auto switches can operate at 12 VDC, but consider the internal voltage drop of the auto switch described in Reed Auto Switch Prescautions on page 12.

Reed Auto Switch Tie-rod Mounting Type D-A33C/D-A34C/D-A44C

Terminal conduit:D-A3□C **DIN terminal: D-A44C**



∧Caution

Precautions

- 1. Use cable whose O.D. is within the size in the figure to maintain water resistant performance.
- 2. After wiring, confirm that tightening gland and all screws are tightened.

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards

		PI	_C: Programr	mable	e Logic Controller
D-A3 C (With indicate	ator light) Te	rminal cond	uit		
Auto switch model	D-A33C		D-A340)	
Applicable load	PLC	Relay, PLC			
Load voltage	24 VDC (3)	24 VDC (3)	100 VAC		200 VAC
Load current range (2)	5 to 50 mA	5 to 50 mA	5 to 25 m	ıΑ	5 to 12.5 mA
Circuit diagram*	3	3 1			
Contact protection circuit	None	None Built-in			
Internal voltage drop	2.4 V or less	2.4 V or less (Up t	o 20 mA)/3.5 \	V or le	ess (Up to 50 mA)
Indicator light	Red LED illuminates when turned ON.			١.	
Standard	CE marking				
D-A44C (With indica	tor light) DI	N terminal			
Auto switch model		D-A4	4C		
Applicable load		Relay	, PLC		
Load voltage	24 VDC (3	100	VAC		200 VAC
Load current range (2)	5 to 50 m/	5 to 2	5 mA	5	to 12.5 mA
Circuit diagram*	0				
Contact protection circuit	t Built-in				
Internal voltage drop	2.4 V or less (Up to 20 mA)/3.5 V or less (Up to 50 mA)				
Indicator light	R	ed LED illuminate	s when turne	10 be	٧.
Standard		CE m	arking		

^{*} Refer to the circuit diagram no. on page 1587.

Note 1) Refer to page 1584 for reed auto switch common specifications.

Note 2) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no

inglit will be possible where the chupbut sight at less than 2- inc. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or more. Note 3) The auto switches can operate at 12 VDC, but consider the internal voltage drop of the auto switch described in Reed Auto Switch Precautions on page 15.

Weight

Auto switch model	Applicable bore size(mm)	Weight	Auto switch model	Applicable bore size(mm)	Weight
D-A33C-4, A34C-4	40	162	D-A44C-4	40	160
D-A33C-5, A34C-5	50	166	D-A44C-5	50	164
D-A33C-6, A34C-6	63	184	D-A44C-6	63	182
D-A33C-8, A34C-8	80	210	D-A44C-8	80	208
D-A33C-10, A34C-10	100	232	D-A44C-10	100	230

Dimensions

(mm)


(g)


Auto switch model	Applicable bore size (mm)	С	HW	Н	H'	T	T'	z
D-A3 C-4, D-A44C-4	40	44	69	58 (67.5)	50.5 (60)	7.5	6.5	M5 x 0.8 x 16
D-A3 C-5, D-A44C-5	50	52	77	59 (68.5)	51.5 (61)	8.5	6.5	IVIS X U.O X 10
D-A3□C-6, D-A44C-6	63	64	91	61.5 (71)	53 (62.5)	10.5	7.5	M5 x 0.8 x 20
D-A3 C-8, D-A44C-8	80	78	107	65 (74.5)	54.5 (64)	12.5	9.5	M5 x 0.8 x 25
D-A3 C-10. D-A44C-10	100	92	121	68 (77 5)	57.5 (67)	15.5	9.5	IVID X U.8 X 25

Dimensions

* (): Denotes the values of D-A44C

(mm)





1662



Reed Auto Switch Direct Mounting Type D-Z73/D-Z76/D-Z80

Grommet



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-Z7 (With indicator light)				
Auto switch model	D-2	Z 73	D-Z76	
Applicable load	Relay	, PLC	IC circuit	
Load voltage	24 VDC (4)	100 VAC	4 to 8 VDC	
Max. load current and load current range(3)	5 to 40 mA	5 to 20 mA	20 mA	
Circuit diagram*	(3)	(5)	
Contact protection circuit	None			
Internal voltage drop	2.4 V or less (Up to 20 mA)/3 V or less (Up to 40 mA) 0.8 V or less			
Indicator light	Red LED illuminates when turned ON.			
Standard	CE marking			
D-Z8 (Without indicator	light)			
Auto switch model		D-Z80		
Applicable load		Relay, PLC, IC circuit		
Load voltage	24 V DC or less	48 V _{DC}	100 V _{DC}	
Maximum load current	50 mA	40 mA	20 mA	
Circuit diagram*	4			
Contact protection circuit		None		
Internal resistance	1 Ω or less (Including 3 m lead wire)			
Standard		CE marking		

Oilproof Heavy-duty Lead Wire Specifications

Auto si	witch model	D-Z73	D-Z76	D-Z80
Sheath	Outside diameter [mm]	ø2.7	ø3.4	ø2.7
Insulator	Number of cores	2 cores (Brown/Blue)	3 cores (Brown/Blue/Black)	2 cores (Brown/Blue)
insulator	Outside diameter [mm]		ø1.1	
Conductor	Effective area [mm²]	0.18	0.2	0.18
Conductor	Strand diameter [mm]		ø0.08	
Lead wire minimum bendi	ng radius [mm] (Reference values)	17	21	17

^{*} Refer to the circuit diagram no. on page 1587.

Note 1) Refer to page 1584 for reed auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.

Note 3) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or

Note 4) The auto switches can operate at 12 VDC, but consider the internal voltage drop of the auto switch described in Reed Auto Switch Precautions on page 12.


Weight

(g)

(mm)

Auto swit	ch model	D-Z73	D-Z76	D-Z80
	0.5 m (NiI)	7	10	7
Lead wire length	3 m (L)	31	55	31
	5 m (Z)	50	Ī	J

Dimensions D-Z73, Z80 **D-Z76**







Reed Auto Switch Direct Mounting Type D-E73A/D-E76A/D-E80A

Grommet



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards. PLC: Programmable Logic Controller

D-E7□A (With indicator light)				
Auto switch model	D-E73A D-E76A			
Applicable load	Relay	Relay, PLC		
Load voltage	24 VDC (4)	100 VAC	4 to 8 VDC	
Max. load current and load current range(3)	5 to 40 mA 5 to 20 mA		20 mA	
Circuit diagram*	3		(5)	
Contact protection circuit	None			
Internal voltage drop	24V	or less	0.8 V or less	

Indicator light Red LED illuminates when turned ON. CE marking

Standard D-E80A (Without indicator light) D-E80A Auto switch model Applicable load Relay, PLC, IC circuit 24 V AC or less 48 V AC 100 V_{DC} Load voltage Maximum load current 50 mA 40 mA 20 mA Circuit diagram (4) Contact protection circuit None Internal resistance 1 Ω or less (Including lead wire length of 3 m)

CE marking

Oilproof Heavy-duty Lead Wire Specifications

Auto s	witch model	D-E73A D-E76A D-E80		D-E80A
Sheath	Outside diameter [mm]		ø3.4	
Insulator	Number of cores	2 cores (Brown/Blue)	3 cores (Brown/Blue/Black)	2 cores (Brown/Blue)
irisulator	Outside diameter [mm]		ø1.1	
Conductor	Effective area [mm²]		0.2	
Conductor	Strand diameter [mm]		ø0.08	
Lead wire minimum bendi	ng radius [mm] (Reference values)		21	

* Refer to the circuit diagram no. on page 1587.

Note 1) Refer to page 1584 for reed auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.

Note 3) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or

Note 4) The auto switches can operate at 12 VDC, but consider the internal voltage drop of the auto switch described in Reed Auto Switch Precautions on page 12.


Weight


Standard

(g)

Auto swit	tch model	D-E73A	D-E76A	D-E80A
Lead wire length	0.5 m (NiI)	10	11	10
Lead wire length	3 m (L)	47	55	47

Dimensions







2-Color Indicator Reed Auto Switch **Band Mounting Type D-B59W**

Grommet

The proper operating range can be determined by the color of the light.

 $(Red \rightarrow Green \leftarrow Red)$



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

	PLC: Programmable Logic Controller
D-B59W (With indicator	light)
Auto switch model	D-B59W
Applicable load	Relay, PLC
Load voltage	24 VDC
Load current range ⁽³⁾	5 to 40 mA
Circuit diagram*	6
Contact protection circuit	Built-in
Internal voltage drop	4 V or less
Indicator light	Operating range ········· Red LED illuminates. Proper operating range ······· Green LED illuminates.
Standard	CE marking

Oilproof Heavy-duty Lead Wire Specifications


Auto switch model		D-B59W
Sheath	Outside diameter [mm]	ø4
Insulator	Number of cores	2 cores (Brown/Blue)
insulator	Outside diameter [mm]	ø1.22
Conductor	Effective area [mm²]	0.3
Conductor	Strand diameter [mm]	ø0.08
Lead wire minimum bendin	g radius [mm] (Reference values)	24

Weight


(g)

Auto switch model		D-B59W
	0.5 m (Nil)	20
Lead wire length	3 m (L)	76

Dimensions











^{*} Refer to the circuit diagram no. on page 1587.
Note 1) Refer to page 1584 for reed auto switch common specifications.
Note 2) Refer to page 1584 for lead wire lengths.
Note 3) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or more.

2-Color Indicator Reed Auto Switch **Rail Mounting Type D-A79W**

Grommet

The proper operating range can be determined by the color of the light.

 $(Red \rightarrow Green \leftarrow Red)$



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

	PLC: Programmable Logic Controller	
D-A79W (With indicator light)		
Auto switch model D-A79W		
Applicable load	Relay, PLC	
Load voltage	24 VDC	
Load current range (3) 5 to 40 mA		
Circuit diagram*	7	
Contact protection circuit	None	
Internal voltage drop	4 V or less	
Indicator light	Operating range ········· Red LED illuminates. Proper operating range ······· Green LED illuminates.	
Standard	CE marking	

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-A79W
Sheath Outside diameter [mm]		ø3.4
Number of cores		2 cores (Brown/Blue)
Insulator	Outside diameter [mm]	ø1.1
Conductor Effective area [mm²]		0.2
Conductor	Strand diameter [mm]	ø0.08
Lead wire minimum bendin	g radius [mm] (Reference values)	21


Weight

Auto swit	tch model	D-A79W
Landonio Investo	0.5 m (NiI)	11
Lead wire length	3 m (L)	53

Dimensions

(mm)

(g)





<sup>Refer to the circuit diagram no. on page 1587.
Note 1) Refer to page 1584 for reed auto switch common specifications.
Note 2) Refer to page 1584 for lead wire lengths.
Note 3) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the</sup> indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or more.

2-Color Indicator Reed Auto Switch Tie-rod Mounting Type

D-A59W

Grommet

The proper operating range can be determined by the color of the light.

 $(Red \rightarrow Green \leftarrow Red)$



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Cor		
D-A59W (With indicator light)		
Auto switch model D-A59W		
Applicable load	Relay, PLC	
Load voltage	24 VDC	
Load current range(3)	5 to 40 mA	
Circuit diagram* 6		
Contact protection circuit Built-in		
Internal voltage drop	4 V or less	
Indicator light	Operating range ········· Red LED illuminates. Proper operating range ······· Green LED illuminates.	
Standard	CE marking	

Oilproof Heavy-duty Lead Wire Specifications


Auto switch model		D-A59W
Sheath Outside diameter [mm]		ø4
Number of cores		2 cores (Brown/Blue)
Insulator	Outside diameter [mm]	ø1.22
Conductor Effective area [mm²]		0.3
Conductor	Strand diameter [mm]	ø0.08
Lead wire minimum bending radius [mm] (Reference values)		24

Weight

(g)

Auto swit	ch model	D-A59W
I and order I are the	0.5 m (NiI)	25
Lead wire length	3 m (L)	80

Dimensions







^{*} Refer to the circuit diagram no. on page 1587.
Note 1) Refer to page 1584 for reed auto switch common specifications.
Note 2) Refer to page 1584 for lead wire lengths.
Note 3) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or more.

Magnetic Field Resistant 2-Color Indicator Reed Auto Switch

D-P79WSE

(Electrical Entry: Pre-wired connector)

Refer to SMC website for the details of the products conforming to the international standards.

Grommet

The proper operating range can be determined by the color of the light.

 $(Red \rightarrow Green \leftarrow Red)$



∆Caution

Precautions

Cylinder with a strong integrated magnet must be used.

Auto Switch Specifications

PLC: Programmable Logic Controller

Auto switch model	D-P79WSE	
Applicable load	PLC	
Load voltage	24 VDC	
Load current range	8 to 20 mA	
Circuit diagram*	6	
Contact protection circuit	Built-in	
Internal voltage drop	6 V or less	
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.	
Standard	CE marking	

Oilproof Heavy-duty Lead Wire Specifications

Au	to switch model	D-P79WSE
Sheath	Outside diameter [mm]	ø6
Insulator	Number of cores	2 cores
insulator	Outside diameter [mm]	ø2.3
Conductor Effective area [mm²]		0.5
Strand diameter [mm]		ø0.08
Lead wire minimum bending radius [mm] (Reference values)		48

^{*} Refer to the circuit diagram no. on page 1587.

Note 1) Refer to page 1584 for reed auto switch common specifications.


Weight


(g)

Auto switch model	D-P79WSE
	100

<u>Dimensions</u>

(mm)





Note) D-P79WSE = "SE 1 4-"

∧ Caution

Please be careful of the mounting direction.

The soft resin mold surface must be directed to the switch mounting bracket side.



Magnetic Field Resistant Reed Auto Switch D-P74

Grommet



∆Caution

Precautions

Cylinder with a strong integrated magnet must be used.

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-P74L/Z (With indicator light)		
Auto switch model	D-I	P74
Electrical entry	Gror	nmet
Application	Relay	, PLC
Load voltage	24 VDC 100 VAC	
Max. load voltage/Load current range	pad voltage/Load current range 5 to 40 mA 5 to 20	
Circuit diagram*	0	
Contact protection circuit	Built-in	
Internal voltage drop (internal resistance)	2.4 V or less	
Leakage current	0	
Indicator light	Red LED illuminates when turned ON.	
Standard	CE marking	

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-P74
Sheath	Outside diameter [mm]	ø6.8
Insulator	Number of cores	2 cores (White/Black)
insulator	Outside diameter [mm]	ø1.1
Conductor	Effective area [mm²]	0.75
Strand diameter [mm]		ø0.18
Lead wire minimum bending radius [mm] (Reference values)		48

Note 1) Refer to page 1584 for lead wire lengths.

Note 3) Refer to page 1584 for lead wire lengths.

Note 3) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or


Weight

	Auto switch model		D-P74		
		0.5 m (Nil)	48		
	Lead wire length	3 m (L)	189		
		5 m (Z)	320		

Dimensions

(mm)

(g)



^{*} Refer to the circuit diagram no. on page 1587. Note 1) Refer to page 1584 for reed auto switch common specifications.

Magnetic Field Resistant Reed Auto Switch D-P74-376

Grommet



∆Caution

Precautions

Cylinder with a strong integrated magnet must be used.

Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

PLC: Programmable Logic Controller

D-P74-376 (With indicator light)					
Auto switch model	D-P74-376				
Electrical entry	Grommet				
Application	Relay, PLC				
Load voltage	24 VDC				
Max. load current/Load current range	5 to 20 mA				
Circuit diagram*	①				
Contact protection circuit	Built-in				
Internal voltage drop (internal resistance)	2 V or less				
Leakage current	0				
Operating time	1.2 ms				
Indicator light	Red LED illuminates when turned ON.				
Standard	CE marking				

Oilproof Heavy-duty Lead Wire Specifications

Au	to switch model	D-P74
Sheath Outside diameter [mm]		ø6
Insulator	Number of cores	2 cores
insulator	Outside diameter [mm]	ø1.1
Conductor	Effective area [mm²]	0.75
Conductor	Strand diameter [mm]	ø0.18
Lead wire minimum I	pending radius [mm] (Reference values)	48

^{*} Refer to the circuit diagram no. on page 1587.

Note 1) Refer to page 1584 for reed auto switch common specifications.


Note 2) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or more.

Weight

(g)

Auto switch model	D-P74-376		
Auto switch model	60		

Dimensions



Heat Resistant Reed Auto Switch D-B30(J)/31(J)/35(J)

Can be used outdoors or under high temperature (Max. 120°C). Wide operating range (double that of other SMC products) enables stable position detection.



High temperature environment such as places around ignited gas outlet or furnace

Outdoor plants and environment with high temperature and humidity

Environment for steam cleaning or high temperature sterilization


Applications requiring wide operating range such as clamping of elastic work pieces

Use of metal case and heat resistant materials

The construction prevents influence of external environment by sealing the auto switch internal parts to improve heat resistance.

The wide operating range allows easy position setting and reduces influence of the work piece position changes

Auto Switch Internal Circuit



Auto Switch Specifications

Refer to SMC website for the details of the products conforming to the international standards.

	PLC: Programmable Logic Controlle					gic Controller	
Auto switch model	D-B30	D-B30J	D-B31	D-B31J	D-B35	D-B35J	
	Terminal		Terminal	Grommet	Terminal	Grommet	
Electrical entry	conduit	Grommet	conduit		conduit		
Operating voltage	24 VDC /	100 VAC	100 VAC		24 VDC		
Operating current range	5 to 30 mADC / 5 to 20 mAAC		5 to 20 mAAC		5 to 30 mADC		
Internal voltage drop	2.5 V or less		2.5 V or less		2.0 V or less		
Indicator light	Without indicator light Neon bulb lights up when OFF			s up when OFF	Red LED lights up when OFF		
Applicable load	PLC (Programmable Logic Controller)						
Shock resistance	300 m/s ²						
Leakage current	eakage current 0.1 mA or less			or less	1 mA or less		
Lead wire — 0.5 m		_	0.5 m	l	0.5 m		
Enclosure	Terminal conduit : IEC60529 IP64						
Liiciosure	Grommet : IEC60529 IP67						
Withstand voltage 1500 VAC for 1 minute (between case and terminals or lea			d wires)				
Insulation resistance	on resistance 50 MΩ or larger between case (ground) and lead wires (terminals)			rminals)			
Operating temperature range	g temperature range —10°C to 120°C						
Standard CE marking							

Oilproof Heavy-duty Lead Wire Specifications

Olipiool fleavy-duty Lead Wife Specifications							
Auto switch model		D-B30J D-B31J D-B35J					
Sheath	Outside diameter [mm]	ø6					
Insulator	Number of cores	2 cores (Brown/Blue)					
Insulator	Outside diameter [mm]	ø2.3					
Conductor	Effective area [mm²]	0.5					
Conductor	Strand diameter [mm]	Ø0.08					
Lead wire minimum bending radius [mm] (Reference values)		48 (Room temperature)					

Weight

(g)

Auto s	Auto switch model		D-B30J	D-B31	D-B31J	D-B35	D-B35J
	None	190	_	190	_	190	_
Lead wire	0.5 m (NiI)	_	250	_	250	_	250
length	3 m (L)	_	268	_	268	_	268
	5 m (Z)	_	462	_	462	_	462

Lead wire length

In case of the grommet type (J type), the lead wire length is 0.5 m.


(No lead wire is attached to the terminal conduit type.)

Manufacture of 3 m and 5 m types is also possible. Please consult SMC for these types.




Dimensions (mm)

Terminal conduit type D-B3□




Terminal conduit type D-B3□J




* Recommended minimum bending radius for lead wire RT $\,\,$: 25 mm or more $\,\,$ 120°C : 50 mm or more

Dimensions for Cylinder Mounting



Hs dimensions (mi						
D	Cylinder model					
Bore size	CDA2	MDB				
40 mm	58.5	57.5				
50 mm	64	63				
63 mm	71	69.5				
80 mm	79.5	78.5				
100 mm	90	89				

Mounting cylinder part no.



^{*} Please consult SMC in case the switch is to be mounted on models other than applicable cylinders.





D-B3 Series Specific Product Precautions

Be sure to read this before handling the products.

Refer to back page 50 for Safety Instructions and pages 8 to 12 for Auto Switch Precautions.

∧ Caution

1. Use the reed switch within the operating range.

Take precautions about the ambient temperature because using the reed switch beyond the operating range may affect its internal electronic parts and sealing construction, causing abnormalities to the service life of the contact, as well as operation and waterproof performance of the switch.

Also, the maximum temperature of the environment where the switch is used must be fully understood before operation is started because the temperature of the environment where the auto switch is installed may experience some changes after operation is started due to factors other than air temperature such as influence of radiation heat from the heat source, air circulation or heat conduction.

2. Take precautions about the environment where the auto switch is installed.

If conditions (water splashes, time, temperature) beyond the normal ranges can be applied to the auto switch, use the auto switch in an environment where it will not be directly exposed to water splashes at a high temperature by installing a cover to protect the entire auto switch, as long as it is possible. The grommet type auto switch has a construction that will protect its internal parts against water splashes at the normal temperature. However, if the conditions (water splashes, time, temperature) exceed the normal ranges, they may adversely affect the auto switch internal insulation performance.

Also, confirm the applicability of the auto switch in the environment because extreme heat cycles or a long-term high humidity may cause functional deterioration of the auto switch protection construction.

In principle, the terminal conduit type must be used in an environment with no exposure to humidity or water because at high temperatures, it may become impossible to achieve sufficient waterproof effect due to deformation of lead wire sealant depending on the heat resistance of the lead wire and cable clamp.

3. Visibility of an indicator light

Because the auto switch uses light emitting diodes and neon bulbs for display, continuous operation at a high temperature may cause changes in characteristics of the entire display circuit. Also, the transparency of the display window on the body may change depending on the characteristics of the resin.

Because of the above factors, lighting under high temperature may become dark, causing decline of visibility.

However, there could be no problem in output of the signal itself and its safety owing to adoption of the OFF-state lighting system.

4. Take precautions about leakage current.

According to the heat resistant characteristics of its parts, the auto switch adopts the OFF-state lighting system (the indicator light lights up when the reed switch contact is open and goes off when the reed switch contact is closed).

Since the current for indicator lighting is running when the auto switch is off, confirm the allowable leakage current of PLC etc. before selecting the model.

If the leakage current of the indicator light becomes a problem for the PLC operation, select a model without an indicator light.

5. Keep the lead wire length as short as possi-

If a long lead wire is used because of the conditions of the plant or equipment where the switch is installed, malfunction in the reed switch reset operation may occur due to premature damage to the contact surface caused by the inrush current resulting from the line flotation capacity and influence of the electric field created by the power line near the wiring.

Therefore, the maximum wiring length should be kept at 100 m or less

Avoid wiring in proximity with the power line. Also, if the length of wiring in use is extremely long (30 m or longer), schedule replacement in periodical maintenance.

The basic guidelines for replacement are a total wiring length of 100 m between the load and the auto switch and 1 million cycles of operation (at $120^{\circ}C$, 100 VAC PLC load).

Install the auto switch at the center of the operating range.

The operation range of the auto switch is set at approximately double that of the standard type in consideration of the mounting error when the detection position is set. However, this range is subject to change with the temperature. Although the variation in the operating range differs with the cylinder on which the auto switch is mounted, a temperature change of 100°C will roughly result in the maximum of 20% reduction in the overall operation range.

(Approximately 2 mm variation at the position where the auto switch usually turns on)

Therefore, install the auto switch at the center of the operating range (stable range), while understanding the possible change in the operating range and considering the stability of the auto switch operation.

(Avoid installation of the auto switch at the boundary where the auto switch turns on or off.)

7. Selection of applicable cylinders

The auto switch should be mounted on special cylinders (-X1184 series) because it is operated by magnets using heat resistant material.

Consult SMC in advance for special applications in which current cylinder cannot be used because, depending on the operating environment, it is possible that special measures should be taken or even the cylinder cannot be adapted.

8. Maintenance

After the auto switch is installed under high temperature, apply additional tightening peiodically to the auto switch mounting band. The rubber lining of the auto switch mounting band may need some time to adapt to the environment because of temperature chages in the installation environment. Perform additional tightening at a tightening torque of 2 to 3 N·m while carefully applying equal torque to both lifting screws.

9. Product upgrades

The product is subject to change without prior notice due to upgrades.

