



## 419D Acrylic Conformal Coating

MG Chemicals UK Limited

Version No: A-1.02

Safety Data Sheet (Conforms to Regulation (EU) No 2015/830)

Issue Date: 22/04/2019

Revision Date: 16/03/2020

L.REACH.GBR.EN

### SECTION 1 IDENTIFICATION OF THE SUBSTANCE / MIXTURE AND OF THE COMPANY / UNDERTAKING

#### 1.1. Product Identifier

Product name	419D
Synonyms	SDS Code: 419D-Liquid, 419D-55ML, 419D-1L, 419D-4L, 419D-20L, 419D-200L
Other means of identification	Acrylic Conformal Coating

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses	conformal coating
Uses advised against	Not Applicable

#### 1.3. Details of the supplier of the safety data sheet

Registered company name	MG Chemicals UK Limited	MG Chemicals (Head office)
Address	Heame House, 23 Bilston Street, Sedgely Dudley DY3 1JA United Kingdom	9347 - 193 Street Surrey V4N 4E7 British Columbia Canada
Telephone	+(44) 1663 362888	+(1) 800-201-8822
Fax	Not Available	+(1) 800-708-9888
Website	Not Available	www.mgchemicals.com
Email	sales@mgchemicals.com	Info@mgchemicals.com

#### 1.4. Emergency telephone number

Association / Organisation	Verisk 3E (Access code: 335388)	Not Available
Emergency telephone numbers	+(44) 20 35147487	Not Available
Other emergency telephone numbers	+(0) 800 680 0425	Not Available

### SECTION 2 HAZARDS IDENTIFICATION

#### 2.1. Classification of the substance or mixture

Classification according to regulation (EC) No 1272/2008 [CLP] [1]	H225 - Flammable Liquid Category 2, H319 - Eye Irritation Category 2, H317 - Skin Sensitizer Category 1B, H336 - Specific target organ toxicity - single exposure Category 3 (narcotic effects)
Legend:	1. Classified by Chemwatch; 2. Classification drawn from EC Directive 67/548/EEC - Annex I ; 3. Classification drawn from EC Directive 1272/2008 - Annex VI

#### 2.2. Label elements

Hazard pictogram(s)	
SIGNAL WORD	DANGER

#### Hazard statement(s)

H225	Highly flammable liquid and vapour.
H319	Causes serious eye irritation.
H317	May cause an allergic skin reaction.
H336	May cause drowsiness or dizziness.

#### Supplementary statement(s)

EUH066	Repeated exposure may cause skin dryness or cracking.
--------	---

Continued...

## 419D Acrylic Conformal Coating

## Precautionary statement(s) Prevention

P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P271	Use only outdoors or in a well-ventilated area.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P240	Ground/bond container and receiving equipment.
P241	Use explosion-proof electrical/ventilating/lighting/intrinsically safe equipment.
P242	Use only non-sparking tools.
P243	Take precautionary measures against static discharge.
P261	Avoid breathing mist/vapours/spray.
P272	Contaminated work clothing should not be allowed out of the workplace.

## Precautionary statement(s) Response

P370+P378	In case of fire: Use alcohol resistant foam or normal protein foam to extinguish.
P302+P352	IF ON SKIN: Wash with plenty of water and soap.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P312	Call a POISON CENTER/doctor/physician/first aider/if you feel unwell.
P333+P313	If skin irritation or rash occurs: Get medical advice/attention.
P337+P313	If eye irritation persists: Get medical advice/attention.
P362+P364	Take off contaminated clothing and wash it before reuse.
P303+P361+P353	IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.

## Precautionary statement(s) Storage

P403+P235	Store in a well-ventilated place. Keep cool.
P405	Store locked up.

## Precautionary statement(s) Disposal

P501	Dispose of contents/container in accordance with local regulations.
------	---

## 2.3. Other hazards

May produce discomfort of the eyes\*.

REACH - Art.57-59: The mixture does not contain Substances of Very High Concern (SVHC) at the SDS print date.

## SECTION 3 COMPOSITION / INFORMATION ON INGREDIENTS

## 3.1. Substances

See 'Composition on ingredients' in Section 3.2

## 3.2. Mixtures

1.CAS No 2.EC No 3.Index No 4.REACH No	%[weight]	Name	Classification according to regulation (EC) No 1272/2008 [CLP]
1.123-86-4 2.204-658-1 3.607-025-00-1 4.01-2119485493-29-XXXX 01-2120063204-67-XXXX	55	<u>n-butyl acetate</u>	Flammable Liquid Category 3, Specific target organ toxicity - single exposure Category 3 (narcotic effects); H226, H336, EUH066 [3]
1.78-93-3 2.201-159-0 3.606-002-00-3 4.01-2119457290-43-XXXX 01-2119943742-35-XXXX	15	<u>methyl ethyl ketone</u>	Flammable Liquid Category 2, Eye Irritation Category 2, Specific target organ toxicity - single exposure Category 3 (narcotic effects); H225, H319, H336, EUH066 [3]
1.80-62-6 2.201-297-1 3.607-035-00-6 4.01-2119452498-28-XXXX	0.1-0.2	<u>methyl methacrylate</u>	Flammable Liquid Category 2, Specific target organ toxicity - single exposure Category 3 (respiratory tract irritation), Skin Corrosion/Irritation Category 2, Skin Sensitizer Category 1; H225, H335, H315, H317 [3]
1.97-88-1 2.202-615-1 3.607-033-00-5 4.01-2119486394-28-XXXX	0.1-0.2	<u>n-butyl methacrylate</u>	Flammable Liquid Category 3, Eye Irritation Category 2, Specific target organ toxicity - single exposure Category 3 (respiratory tract irritation), Skin Corrosion/Irritation Category 2, Skin Sensitizer Category 1; H226, H319, H335, H315, H317 [3]
<b>Legend:</b>	1. Classified by Chemwatch; 2. Classification drawn from EC Directive 67/548/EEC - Annex I ; 3. Classification drawn from EC Directive 1272/2008 - Annex VI 4. Classification drawn from C&L		

## SECTION 4 FIRST AID MEASURES

## 419D Acrylic Conformal Coating

## 4.1. Description of first aid measures

<b>Eye Contact</b>	<p>If this product comes in contact with the eyes:</p> <ul style="list-style-type: none"> <li>▶ Wash out immediately with fresh running water.</li> <li>▶ Ensure complete irrigation of the eye by keeping eyelids apart and away from eye and moving the eyelids by occasionally lifting the upper and lower lids.</li> <li>▶ Seek medical attention without delay; if pain persists or recurs seek medical attention.</li> <li>▶ Removal of contact lenses after an eye injury should only be undertaken by skilled personnel.</li> </ul>
<b>Skin Contact</b>	<p>If skin contact occurs:</p> <ul style="list-style-type: none"> <li>▶ Immediately remove all contaminated clothing, including footwear.</li> <li>▶ Flush skin and hair with running water (and soap if available).</li> <li>▶ Seek medical attention in event of irritation.</li> </ul>
<b>Inhalation</b>	<ul style="list-style-type: none"> <li>▶ If fumes, aerosols or combustion products are inhaled remove from contaminated area.</li> <li>▶ Other measures are usually unnecessary.</li> </ul>
<b>Ingestion</b>	<ul style="list-style-type: none"> <li>▶ Immediately give a glass of water.</li> <li>▶ First aid is not generally required. If in doubt, contact a Poisons Information Centre or a doctor.</li> </ul>

## 4.2 Most important symptoms and effects, both acute and delayed

See Section 11

## 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.  
for simple esters:

## BASIC TREATMENT

- ▶ Establish a patent airway with suction where necessary.
- ▶ Watch for signs of respiratory insufficiency and assist ventilation as necessary.
- ▶ Administer oxygen by non-rebreather mask at 10 to 15 l/min.
- ▶ Monitor and treat, where necessary, for pulmonary oedema .
- ▶ Monitor and treat, where necessary, for shock.
- ▶ **DO NOT use emetics.** Where ingestion is suspected rinse mouth and give up to 200 ml water (5 ml/kg recommended) for dilution where patient is able to swallow, has a strong gag reflex and does not drool.
- ▶ Give activated charcoal.

## ADVANCED TREATMENT

- ▶ Consider orotracheal or nasotracheal intubation for airway control in unconscious patient or where respiratory arrest has occurred.
- ▶ Positive-pressure ventilation using a bag-valve mask might be of use.
- ▶ Monitor and treat, where necessary, for arrhythmias.
- ▶ Start an IV D5W TKO. If signs of hypovolaemia are present use lactated Ringers solution. Fluid overload might create complications.
- ▶ Drug therapy should be considered for pulmonary oedema.
- ▶ Hypotension with signs of hypovolaemia requires the cautious administration of fluids. Fluid overload might create complications.
- ▶ Treat seizures with diazepam.
- ▶ Proparacaine hydrochloride should be used to assist eye irrigation.

## EMERGENCY DEPARTMENT

- ▶ Laboratory analysis of complete blood count, serum electrolytes, BUN, creatinine, glucose, urinalysis, baseline for serum aminotransferases (ALT and AST), calcium, phosphorus and magnesium, may assist in establishing a treatment regime. Other useful analyses include anion and osmolar gaps, arterial blood gases (ABGs), chest radiographs and electrocardiograph.
- ▶ Positive end-expiratory pressure (PEEP)-assisted ventilation may be required for acute parenchymal injury or adult respiratory distress syndrome.
- ▶ Consult a toxicologist as necessary.

BRONSTEIN, A.C. and CURRANCE, P.L. EMERGENCY CARE FOR HAZARDOUS MATERIALS EXPOSURE: 2nd Ed. 1994

## SECTION 5 FIREFIGHTING MEASURES

## 5.1. Extinguishing media

- ▶ Alcohol stable foam.
- ▶ Dry chemical powder.
- ▶ BCF (where regulations permit).
- ▶ Carbon dioxide.
- ▶ Water spray or fog - Large fires only.

## 5.2. Special hazards arising from the substrate or mixture

<b>Fire Incompatibility</b>	▶ Avoid contamination with oxidising agents i.e. nitrates, oxidising acids, chlorine bleaches, pool chlorine etc. as ignition may result
-----------------------------	--

## 5.3. Advice for firefighters

<b>Fire Fighting</b>	<ul style="list-style-type: none"> <li>▶ Alert Fire Brigade and tell them location and nature of hazard.</li> <li>▶ May be violently or explosively reactive.</li> <li>▶ Wear breathing apparatus plus protective gloves in the event of a fire.</li> <li>▶ Prevent, by any means available, spillage from entering drains or water course.</li> <li>▶ Consider evacuation (or protect in place).</li> <li>▶ Fight fire from a safe distance, with adequate cover.</li> <li>▶ If safe, switch off electrical equipment until vapour fire hazard removed.</li> <li>▶ Use water delivered as a fine spray to control the fire and cool adjacent area.</li> <li>▶ Avoid spraying water onto liquid pools.</li> <li>▶ <b>Do not approach containers suspected to be hot.</b></li> <li>▶ Cool fire exposed containers with water spray from a protected location.</li> <li>▶ If safe to do so, remove containers from path of fire.</li> </ul>
----------------------	---

## 419D Acrylic Conformal Coating

## Fire/Explosion Hazard

- ▶ Liquid and vapour are highly flammable.
  - ▶ Severe fire hazard when exposed to heat, flame and/or oxidisers.
  - ▶ Vapour may travel a considerable distance to source of ignition.
  - ▶ Heating may cause expansion or decomposition leading to violent rupture of containers.
  - ▶ On combustion, may emit toxic fumes of carbon monoxide (CO).
- Combustion products include:  
carbon dioxide (CO<sub>2</sub>)  
other pyrolysis products typical of burning organic material.

## SECTION 6 ACCIDENTAL RELEASE MEASURES

## 6.1. Personal precautions, protective equipment and emergency procedures

See section 8

## 6.2. Environmental precautions

See section 12

## 6.3. Methods and material for containment and cleaning up

## Minor Spills

- ▶ Remove all ignition sources.
- ▶ Clean up all spills immediately.
- ▶ Avoid breathing vapours and contact with skin and eyes.
- ▶ Control personal contact with the substance, by using protective equipment.
- ▶ Contain and absorb small quantities with vermiculite or other absorbent material.
- ▶ Wipe up.
- ▶ Collect residues in a flammable waste container.

## Major Spills

Chemical Class: ester and ethers  
For release onto land: recommended sorbents listed in order of priority.

SORBENT TYPE	RANK	APPLICATION	COLLECTION	LIMITATIONS
--------------	------	-------------	------------	-------------

## LAND SPILL - SMALL

cross-linked polymer - particulate	1	shovel	shovel	R, W, SS
cross-linked polymer - pillow	1	throw	pitchfork	R, DGC, RT
sorbent clay - particulate	2	shovel	shovel	R, I, P
wood fiber - particulate	3	shovel	shovel	R, W, P, DGC
wood fiber - pillow	3	throw	pitchfork	R, P, DGC, RT
treated wood fiber - pillow	3	throw	pitchfork	DGC, RT

## LAND SPILL - MEDIUM

cross-linked polymer - particulate	1	blower	skiploader	R, W, SS
cross-linked polymer - pillow	2	throw	skiploader	R, DGC, RT
sorbent clay - particulate	3	blower	skiploader	R, I, P
polypropylene - particulate	3	blower	skiploader	W, SS, DGC
expanded mineral - particulate	4	blower	skiploader	R, I, W, P, DGC
wood fiber - particulate	4	blower	skiploader	R, W, P, DGC

## Legend

DGC: Not effective where ground cover is dense

R: Not reusable

I: Not incinerable

P: Effectiveness reduced when rainy

RT: Not effective where terrain is rugged

SS: Not for use within environmentally sensitive sites

W: Effectiveness reduced when windy

Reference: Sorbents for Liquid Hazardous Substance Cleanup and Control;

R.W Melvold et al: Pollution Technology Review No. 150: Noyes Data Corporation 1988

- ▶ Clear area of personnel and move upwind.
- ▶ Alert Fire Brigade and tell them location and nature of hazard.
- ▶ May be violently or explosively reactive.
- ▶ Wear breathing apparatus plus protective gloves.
- ▶ Prevent, by any means available, spillage from entering drains or water course.
- ▶ Consider evacuation (or protect in place).
- ▶ No smoking, naked lights or ignition sources.
- ▶ Increase ventilation.
- ▶ Stop leak if safe to do so.
- ▶ Water spray or fog may be used to disperse /absorb vapour.
- ▶ Contain spill with sand, earth or vermiculite.
- ▶ Use only spark-free shovels and explosion proof equipment.
- ▶ Collect recoverable product into labelled containers for recycling.
- ▶ Absorb remaining product with sand, earth or vermiculite.
- ▶ Collect solid residues and seal in labelled drums for disposal.
- ▶ Wash area and prevent runoff into drains.
- ▶ If contamination of drains or waterways occurs, advise emergency services.

## 6.4. Reference to other sections

Continued...

## 419D Acrylic Conformal Coating

Personal Protective Equipment advice is contained in Section 8 of the SDS.

## SECTION 7 HANDLING AND STORAGE

## 7.1. Precautions for safe handling

<b>Safe handling</b>	<ul style="list-style-type: none"> <li>▶ Containers, even those that have been emptied, may contain explosive vapours.</li> <li>▶ Do NOT cut, drill, grind, weld or perform similar operations on or near containers.</li> <li>▶ Avoid all personal contact, including inhalation.</li> <li>▶ Wear protective clothing when risk of exposure occurs.</li> <li>▶ Use in a well-ventilated area.</li> <li>▶ Prevent concentration in hollows and sumps.</li> <li>▶ <b>DO NOT enter confined spaces until atmosphere has been checked.</b></li> <li>▶ Avoid smoking, naked lights, heat or ignition sources.</li> <li>▶ When handling, <b>DO NOT eat, drink or smoke.</b></li> <li>▶ Vapour may ignite on pumping or pouring due to static electricity.</li> <li>▶ <b>DO NOT use plastic buckets.</b></li> <li>▶ Earth and secure metal containers when dispensing or pouring product.</li> <li>▶ Use spark-free tools when handling.</li> <li>▶ Avoid contact with incompatible materials.</li> <li>▶ Keep containers securely sealed.</li> <li>▶ Avoid physical damage to containers.</li> <li>▶ Always wash hands with soap and water after handling.</li> <li>▶ Work clothes should be laundered separately.</li> <li>▶ Use good occupational work practice.</li> <li>▶ Observe manufacturer's storage and handling recommendations contained within this SDS.</li> <li>▶ Atmosphere should be regularly checked against established exposure standards to ensure safe working conditions.</li> <li>▶ <b>DO NOT allow clothing wet with material to stay in contact with skin</b></li> </ul>
<b>Fire and explosion protection</b>	See section 5
<b>Other information</b>	<ul style="list-style-type: none"> <li>▶ Store in original containers in approved flame-proof area.</li> <li>▶ No smoking, naked lights, heat or ignition sources.</li> <li>▶ <b>DO NOT store in pits, depressions, basements or areas where vapours may be trapped.</b></li> <li>▶ Keep containers securely sealed.</li> <li>▶ Store away from incompatible materials in a cool, dry well ventilated area.</li> <li>▶ Protect containers against physical damage and check regularly for leaks.</li> <li>▶ Observe manufacturer's storage and handling recommendations contained within this SDS.</li> </ul>

## 7.2. Conditions for safe storage, including any incompatibilities

<b>Suitable container</b>	<ul style="list-style-type: none"> <li>▶ Packing as supplied by manufacturer.</li> <li>▶ Plastic containers may only be used if approved for flammable liquid.</li> <li>▶ Check that containers are clearly labelled and free from leaks.</li> <li>▶ For low viscosity materials (i) : Drums and jerry cans must be of the non-removable head type. (ii) : Where a can is to be used as an inner package, the can must have a screwed enclosure.</li> <li>▶ For materials with a viscosity of at least 2680 cSt. (23 deg. C)</li> <li>▶ For manufactured product having a viscosity of at least 250 cSt. (23 deg. C)</li> <li>▶ Manufactured product that requires stirring before use and having a viscosity of at least 20 cSt (25 deg. C): (i) Removable head packaging; (ii) Cans with friction closures and (iii) low pressure tubes and cartridges may be used.</li> <li>▶ Where combination packages are used, and the inner packages are of glass, there must be sufficient inert cushioning material in contact with inner and outer packages</li> <li>▶ In addition, where inner packagings are glass and contain liquids of packing group I there must be sufficient inert absorbent to absorb any spillage, unless the outer packaging is a close fitting moulded plastic box and the substances are not incompatible with the plastic.</li> </ul>
<b>Storage incompatibility</b>	<p>n-Butyl acetate:</p> <ul style="list-style-type: none"> <li>▶ reacts with water on standing to form acetic acid and n-butyl alcohol</li> <li>▶ reacts violently with strong oxidisers and potassium tert-butoxide</li> <li>▶ is incompatible with caustics, strong acids and nitrates</li> <li>▶ dissolves rubber, many plastics, resins and some coatings</li> </ul> <p>Methyl ethyl ketone:</p> <ul style="list-style-type: none"> <li>▶ reacts violently with strong oxidisers, aldehydes, nitric acid, perchloric acid, potassium tert-butoxide, oleum</li> <li>▶ is incompatible with inorganic acids, aliphatic amines, ammonia, caustics, isocyanates, pyridines, chlorosulfonic acid</li> <li>▶ forms unstable peroxides in storage, or on contact with propanol or hydrogen peroxide</li> <li>▶ attacks some plastics</li> <li>▶ may generate electrostatic charges, due to low conductivity, on flow or agitation</li> <li>▶ Esters react with acids to liberate heat along with alcohols and acids.</li> <li>▶ Strong oxidising acids may cause a vigorous reaction with esters that is sufficiently exothermic to ignite the reaction products.</li> <li>▶ Heat is also generated by the interaction of esters with caustic solutions.</li> <li>▶ Flammable hydrogen is generated by mixing esters with alkali metals and hydrides.</li> <li>▶ Esters may be incompatible with aliphatic amines and nitrates.</li> <li>▶ Avoid strong acids, bases.</li> </ul>

## 7.3. Specific end use(s)

See section 1.2

## SECTION 8 EXPOSURE CONTROLS / PERSONAL PROTECTION

## 8.1. Control parameters

## DERIVED NO EFFECT LEVEL (DNEL)

Not Available

## PREDICTED NO EFFECT LEVEL (PNEC)

Continued...

## 419D Acrylic Conformal Coating

Not Available

**OCCUPATIONAL EXPOSURE LIMITS (OEL)****INGREDIENT DATA**

Source	Ingredient	Material name	TWA	STEL	Peak	Notes
UK Workplace Exposure Limits (WELs)	n-butyl acetate	Butyl acetate	724 mg/m <sup>3</sup> / 150 ppm	966 mg/m <sup>3</sup> / 200 ppm	Not Available	Not Available
European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (English)	methyl ethyl ketone	Butanone	600 mg/m <sup>3</sup> / 200 ppm	900 mg/m <sup>3</sup> / 300 ppm	Not Available	Not Available
UK Workplace Exposure Limits (WELs)	methyl ethyl ketone	Butan-2-one (methyl ethyl ketone)	600 mg/m <sup>3</sup> / 200 ppm	899 mg/m <sup>3</sup> / 300 ppm	Not Available	Sk, BMGV
EU Consolidated List of Indicative Occupational Exposure Limit Values (IOELVs)	methyl ethyl ketone	Butanone	600 mg/m <sup>3</sup> / 200 ppm	900 mg/m <sup>3</sup> / 300 ppm	Not Available	Not Available
UK Workplace Exposure Limits (WELs)	methyl methacrylate	Methyl methacrylate	208 mg/m <sup>3</sup> / 50 ppm	416 mg/m <sup>3</sup> / 100 ppm	Not Available	Not Available
European Union (EU) Third List of Indicative Occupational Exposure Limit Values (IOELVs) (English)	methyl methacrylate	Methyl methacrylate	50 ppm	100 ppm	Not Available	Not Available

**EMERGENCY LIMITS**

Ingredient	Material name	TEEL-1	TEEL-2	TEEL-3
n-butyl acetate	Butyl acetate, n-	Not Available	Not Available	Not Available
methyl ethyl ketone	Butanone, 2-; (Methyl ethyl ketone; MEK)	Not Available	Not Available	Not Available
methyl methacrylate	Methyl methacrylate	Not Available	Not Available	Not Available
n-butyl methacrylate	Methyl butylacrylate, 2-; (Butyl methacrylate)	19 mg/m <sup>3</sup>	210 mg/m <sup>3</sup>	1,300 mg/m <sup>3</sup>

Ingredient	Original IDLH	Revised IDLH
n-butyl acetate	1,700 [LEL] ppm	Not Available
methyl ethyl ketone	3000 ppm	Not Available
methyl methacrylate	1000 ppm	Not Available
n-butyl methacrylate	Not Available	Not Available

**MATERIAL DATA****IFRA Prohibited Fragrance Substance**

The International Fragrance Association (IFRA) Standards form the basis for the globally accepted and recognized risk management system for the safe use of fragrance ingredients and are part of the IFRA Code of Practice. This is the self-regulating system of the industry, based on risk assessments carried out by an independent Expert Panel

For n-butyl acetate

Odour Threshold Value: 0.0063 ppm (detection), 0.038-12 ppm (recognition)

Exposure at or below the recommended TLV-TWA is thought to prevent significant irritation of the eyes and respiratory passages as well as narcotic effects. In light of the lack of substantive evidence regarding teratogenicity and a review of acute oral data a STEL is considered inappropriate.

Odour Safety Factor(OSF)

OSF=3.8E2 (n-BUTYL ACETATE)

For methyl ethyl ketone:

Odour Threshold Value: Variously reported as 2 ppm and 4.8 ppm

Odour threshold: 2 ppm (detection); 5 ppm (recognition) 25 ppm (easy recognition); 300 ppm IRRITATING

Exposures at or below the recommended TLV-TWA are thought to prevent injurious systemic effects and to minimise objections to odour and irritation. Where synergism or potentiation may occur stringent control of the primary toxin (e.g. n-hexane or methyl butyl ketone) is desirable and additional consideration should be given to lowering MEK exposures.

Odour Safety Factor(OSF)

OSF=28 (METHYL ETHYL KETONE)

Odour Threshold Value (methyl methacrylate): 0.049 ppm (detection), 0.34 ppm (recognition)

NOTE: Detector tubes measuring in excess of 50 ppm, are available.

Concentrations as low as 125 ppm methyl methacrylate have produced irritation of the mucous membranes of exposed workers. The recommended TLV-TWA is thought to be sufficiently low to protect against discomfort from irritation and acute systemic intoxication.

NOTE D: Certain substances which are susceptible to spontaneous polymerisation or decomposition are generally placed on the market in a stabilised form. It is in this form that they are listed on Annex I

When they are placed on the market in a non-stabilised form, the label must state the name of the substance followed by the words 'non-stabilised'

European Union (EU) List of harmonised classification and labelling hazardous substances, Table 3.1, Annex VI, Regulation (EC) No 1272/2008 (CLP) - up to the latest ATP

**8.2. Exposure controls**

<b>8.2.1. Appropriate engineering controls</b>	<p>Engineering controls are used to remove a hazard or place a barrier between the worker and the hazard. Well-designed engineering controls can be highly effective in protecting workers and will typically be independent of worker interactions to provide this high level of protection.</p> <p>The basic types of engineering controls are:</p> <p>Process controls which involve changing the way a job activity or process is done to reduce the risk.</p> <p>Enclosure and/or isolation of emission source which keeps a selected hazard 'physically' away from the worker and ventilation that strategically 'adds' and 'removes' air in the work environment. Ventilation can remove or dilute an air contaminant if designed properly. The design of a ventilation system must match the particular process and chemical or contaminant in use.</p> <p>Employers may need to use multiple types of controls to prevent employee overexposure.</p> <p>For flammable liquids and flammable gases, local exhaust ventilation or a process enclosure ventilation system may be required. Ventilation equipment should be explosion-resistant.</p> <p>Air contaminants generated in the workplace possess varying 'escape' velocities which, in turn, determine the 'capture velocities' of fresh circulating air required to effectively remove the contaminant.</p>
--	--

Continued...

## 419D Acrylic Conformal Coating

	<table border="1" data-bbox="391 192 1487 461"> <tr> <td>Type of Contaminant:</td> <td>Air Speed:</td> </tr> <tr> <td>solvent, vapours, degreasing etc., evaporating from tank (in still air).</td> <td>0.25-0.5 m/s (50-100 f/min.)</td> </tr> <tr> <td>aerosols, fumes from pouring operations, intermittent container filling, low speed conveyer transfers, welding, spray drift, plating acid fumes, pickling (released at low velocity into zone of active generation)</td> <td>0.5-1 m/s (100-200 f/min.)</td> </tr> <tr> <td>direct spray, spray painting in shallow booths, drum filling, conveyer loading, crusher dusts, gas discharge (active generation into zone of rapid air motion)</td> <td>1-2.5 m/s (200-500 f/min.)</td> </tr> </table> <p>Within each range the appropriate value depends on:</p> <table border="1" data-bbox="391 517 1487 685"> <thead> <tr> <th>Lower end of the range</th> <th>Upper end of the range</th> </tr> </thead> <tbody> <tr> <td>1: Room air currents minimal or favourable to capture</td> <td>1: Disturbing room air currents</td> </tr> <tr> <td>2: Contaminants of low toxicity or of nuisance value only.</td> <td>2: Contaminants of high toxicity</td> </tr> <tr> <td>3: Intermittent, low production.</td> <td>3: High production, heavy use</td> </tr> <tr> <td>4: Large hood or large air mass in motion</td> <td>4: Small hood-local control only</td> </tr> </tbody> </table> <p>Simple theory shows that air velocity falls rapidly with distance away from the opening of a simple extraction pipe. Velocity generally decreases with the square of distance from the extraction point (in simple cases). Therefore the air speed at the extraction point should be adjusted, accordingly, after reference to distance from the contaminating source. The air velocity at the extraction fan, for example, should be a minimum of 1-2 m/s (200-400 f/min.) for extraction of solvents generated in a tank 2 meters distant from the extraction point. Other mechanical considerations, producing performance deficits within the extraction apparatus, make it essential that theoretical air velocities are multiplied by factors of 10 or more when extraction systems are installed or used.</p>	Type of Contaminant:	Air Speed:	solvent, vapours, degreasing etc., evaporating from tank (in still air).	0.25-0.5 m/s (50-100 f/min.)	aerosols, fumes from pouring operations, intermittent container filling, low speed conveyer transfers, welding, spray drift, plating acid fumes, pickling (released at low velocity into zone of active generation)	0.5-1 m/s (100-200 f/min.)	direct spray, spray painting in shallow booths, drum filling, conveyer loading, crusher dusts, gas discharge (active generation into zone of rapid air motion)	1-2.5 m/s (200-500 f/min.)	Lower end of the range	Upper end of the range	1: Room air currents minimal or favourable to capture	1: Disturbing room air currents	2: Contaminants of low toxicity or of nuisance value only.	2: Contaminants of high toxicity	3: Intermittent, low production.	3: High production, heavy use	4: Large hood or large air mass in motion	4: Small hood-local control only
Type of Contaminant:	Air Speed:																		
solvent, vapours, degreasing etc., evaporating from tank (in still air).	0.25-0.5 m/s (50-100 f/min.)																		
aerosols, fumes from pouring operations, intermittent container filling, low speed conveyer transfers, welding, spray drift, plating acid fumes, pickling (released at low velocity into zone of active generation)	0.5-1 m/s (100-200 f/min.)																		
direct spray, spray painting in shallow booths, drum filling, conveyer loading, crusher dusts, gas discharge (active generation into zone of rapid air motion)	1-2.5 m/s (200-500 f/min.)																		
Lower end of the range	Upper end of the range																		
1: Room air currents minimal or favourable to capture	1: Disturbing room air currents																		
2: Contaminants of low toxicity or of nuisance value only.	2: Contaminants of high toxicity																		
3: Intermittent, low production.	3: High production, heavy use																		
4: Large hood or large air mass in motion	4: Small hood-local control only																		
8.2.2. Personal protection																			
Eye and face protection	<ul style="list-style-type: none"> <li>▶ Safety glasses with side shields.</li> <li>▶ Chemical goggles.</li> <li>▶ Contact lenses may pose a special hazard; soft contact lenses may absorb and concentrate irritants. A written policy document, describing the wearing of lenses or restrictions on use, should be created for each workplace or task. This should include a review of lens absorption and adsorption for the class of chemicals in use and an account of injury experience. Medical and first-aid personnel should be trained in their removal and suitable equipment should be readily available. In the event of chemical exposure, begin eye irrigation immediately and remove contact lens as soon as practicable. Lens should be removed at the first signs of eye redness or irritation - lens should be removed in a clean environment only after workers have washed hands thoroughly. [CDC NIOSH Current Intelligence Bulletin 59], [AS/NZS 1336 or national equivalent]</li> </ul>																		
Skin protection	See Hand protection below																		
Hands/feet protection	<ul style="list-style-type: none"> <li>▶ Wear chemical protective gloves, e.g. PVC.</li> <li>▶ Wear safety footwear or safety gumboots, e.g. Rubber</li> </ul> <p><b>NOTE:</b></p> <ul style="list-style-type: none"> <li>▶ The material may produce skin sensitisation in predisposed individuals. Care must be taken, when removing gloves and other protective equipment, to avoid all possible skin contact.</li> <li>▶ Contaminated leather items, such as shoes, belts and watch-bands should be removed and destroyed.</li> </ul> <p>The selection of suitable gloves does not only depend on the material, but also on further marks of quality which vary from manufacturer to manufacturer. Where the chemical is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.</p> <p>The exact break through time for substances has to be obtained from the manufacturer of the protective gloves and has to be observed when making a final choice.</p> <p>Personal hygiene is a key element of effective hand care. Gloves must only be worn on clean hands. After using gloves, hands should be washed and dried thoroughly. Application of a non-perfumed moisturizer is recommended.</p> <p>Suitability and durability of glove type is dependent on usage. Important factors in the selection of gloves include:</p> <ul style="list-style-type: none"> <li>- frequency and duration of contact,</li> <li>- chemical resistance of glove material,</li> <li>- glove thickness and</li> <li>- dexterity</li> </ul> <p>Select gloves tested to a relevant standard (e.g. Europe EN 374, US F739, AS/NZS 2161.1 or national equivalent).</p> <ul style="list-style-type: none"> <li>- When prolonged or frequently repeated contact may occur, a glove with a protection class of 5 or higher (breakthrough time greater than 240 minutes according to EN 374, AS/NZS 2161.10.1 or national equivalent) is recommended.</li> <li>- When only brief contact is expected, a glove with a protection class of 3 or higher (breakthrough time greater than 60 minutes according to EN 374, AS/NZS 2161.10.1 or national equivalent) is recommended.</li> <li>- Some glove polymer types are less affected by movement and this should be taken into account when considering gloves for long-term use.</li> <li>- Contaminated gloves should be replaced.</li> </ul> <p>For general applications, gloves with a thickness typically greater than 0.35 mm, are recommended.</p> <p>It should be emphasised that glove thickness is not necessarily a good predictor of glove resistance to a specific chemical, as the permeation efficiency of the glove will be dependent on the exact composition of the glove material. Therefore, glove selection should also be based on consideration of the task requirements and knowledge of breakthrough times.</p> <p>Glove thickness may also vary depending on the glove manufacturer, the glove type and the glove model. Therefore, the manufacturers' technical data should always be taken into account to ensure selection of the most appropriate glove for the task.</p> <p>Note: Depending on the activity being conducted, gloves of varying thickness may be required for specific tasks. For example:</p> <ul style="list-style-type: none"> <li>- Thinner gloves (down to 0.1 mm or less) may be required where a high degree of manual dexterity is needed. However, these gloves are only likely to give short duration protection and would normally be just for single use applications, then disposed of.</li> <li>- Thicker gloves (up to 3 mm or more) may be required where there is a mechanical (as well as a chemical) risk i.e. where there is abrasion or puncture potential</li> </ul> <p>Gloves must only be worn on clean hands. After using gloves, hands should be washed and dried thoroughly. Application of a non-perfumed moisturiser is recommended.</p>																		
Body protection	See Other protection below																		

## 419D Acrylic Conformal Coating

<b>Other protection</b>	<ul style="list-style-type: none"> <li>▶ Overalls.</li> <li>▶ PVC Apron.</li> <li>▶ PVC protective suit may be required if exposure severe.</li> <li>▶ Eyewash unit.</li> <li>▶ Ensure there is ready access to a safety shower. <ul style="list-style-type: none"> <li>- Some plastic personal protective equipment (PPE) (e.g. gloves, aprons, overshoes) are not recommended as they may produce static electricity.</li> <li>- For large scale or continuous use wear tight-weave non-static clothing (no metallic fasteners, cuffs or pockets).</li> <li>- Non sparking safety or conductive footwear should be considered. Conductive footwear describes a boot or shoe with a sole made from a conductive compound chemically bound to the bottom components, for permanent control to electrically ground the foot an shall dissipate static electricity from the body to reduce the possibility of ignition of volatile compounds. Electrical resistance must range between 0 to 500,000 ohms. Conductive shoes should be stored in lockers close to the room in which they are worn. Personnel who have been issued conductive footwear should not wear them from their place of work to their homes and return.</li> </ul> </li> </ul>
<b>Thermal hazards</b>	Not Available

## Recommended material(s)

## GLOVE SELECTION INDEX

Glove selection is based on a modified presentation of the: **'Forsberg Clothing Performance Index'**.

The effect(s) of the following substance(s) are taken into account in the **computer-generated** selection:

419D Premium Acrylic Conformal Coating

Material	CPI
PE/EVAL/PE	A
TEFLON	A
PVA	B
BUTYL	C
BUTYL/NEOPRENE	C
HYPALON	C
NATURAL RUBBER	C
NATURAL+NEOPRENE	C
NEOPRENE	C
NEOPRENE/NATURAL	C
NITRILE	C
NITRILE+PVC	C
PE	C
PVC	C
SARANEX-23	C
VITON/BUTYL	C
VITON/NEOPRENE	C

\* CPI - Chemwatch Performance Index

A: Best Selection

B: Satisfactory; may degrade after 4 hours continuous immersion

C: Poor to Dangerous Choice for other than short term immersion

**NOTE:** As a series of factors will influence the actual performance of the glove, a final selection must be based on detailed observation. -

\* Where the glove is to be used on a short term, casual or infrequent basis, factors such as 'feel' or convenience (e.g. disposability), may dictate a choice of gloves which might otherwise be unsuitable following long-term or frequent use. A qualified practitioner should be consulted.

## Respiratory protection

**Cartridge respirators should never be used for emergency ingress or in areas of unknown vapour concentrations or oxygen content. The wearer must be warned to leave the contaminated area immediately on detecting any odours through the respirator. The odour may indicate that the mask is not functioning properly, that the vapour concentration is too high, or that the mask is not properly fitted. Because of these limitations, only restricted use of cartridge respirators is considered appropriate.**

Selection of the Class and Type of respirator will depend upon the level of breathing zone contaminant and the chemical nature of the contaminant. Protection Factors (defined as the ratio of contaminant outside and inside the mask) may also be important.

Required minimum protection factor	Maximum gas/vapour concentration present in air p.p.m. (by volume)	Half-face Respirator	Full-Face Respirator
up to 10	1000	A-AUS / Class 1	-
up to 50	1000	-	A-AUS / Class 1
up to 50	5000	Airline *	-
up to 100	5000	-	A-2
up to 100	10000	-	A-3
100+		-	Airline**

\* - Continuous Flow

\*\* - Continuous-flow or positive pressure demand.

A(All classes) = Organic vapours, B AUS or B1 = Acid gases, B2 = Acid gas or hydrogen cyanide(HCN), B3 = Acid gas or hydrogen cyanide(HCN), E = Sulfur dioxide(SO<sub>2</sub>), G = Agricultural chemicals, K = Ammonia(NH<sub>3</sub>), Hg = Mercury, NO = Oxides of nitrogen, MB = Methyl bromide, AX = Low boiling point organic compounds(below 65 deg C)

## 8.2.3. Environmental exposure controls

See section 12

## SECTION 9 PHYSICAL AND CHEMICAL PROPERTIES

## 9.1. Information on basic physical and chemical properties

Appearance	Clear		
Physical state	Liquid	Relative density (Water = 1)	0.93
Odour	Not Available	Partition coefficient n-octanol / water	Not Available
Odour threshold	Not Available	Auto-ignition temperature (°C)	>294
pH (as supplied)	Not Available	Decomposition temperature	Not Available
Melting point / freezing point (°C)	Not Available	Viscosity (cSt)	110.00
Initial boiling point and boiling range (°C)	>80	Molecular weight (g/mol)	Not Available
Flash point (°C)	9	Taste	Not Available

Continued...

## 419D Acrylic Conformal Coating

Evaporation rate	<1 BuAC = 1	Explosive properties	Not Available
Flammability	HIGHLY FLAMMABLE.	Oxidising properties	Not Available
Upper Explosive Limit (%)	9.1	Surface Tension (dyn/cm or mN/m)	Not Available
Lower Explosive Limit (%)	1.7	Volatile Component (%vol)	Not Available
Vapour pressure (kPa)	4.30	Gas group	Not Available
Solubility in water (g/L)	Partly miscible	pH as a solution (1%)	Not Available
Vapour density (Air = 1)	>2.5	VOC g/L	Not Available

## 9.2. Other information

Not Available

## SECTION 10 STABILITY AND REACTIVITY

10.1. Reactivity	See section 7.2
10.2. Chemical stability	<ul style="list-style-type: none"> <li>▶ Unstable in the presence of incompatible materials.</li> <li>▶ Product is considered stable.</li> <li>▶ Hazardous polymerisation will not occur.</li> </ul>
10.3. Possibility of hazardous reactions	See section 7.2
10.4. Conditions to avoid	See section 7.2
10.5. Incompatible materials	See section 7.2
10.6. Hazardous decomposition products	See section 5.3

## SECTION 11 TOXICOLOGICAL INFORMATION

## 11.1. Information on toxicological effects

Inhaled	<p>The material is not thought to produce adverse health effects or irritation of the respiratory tract (as classified by EC Directives using animal models). Nevertheless, good hygiene practice requires that exposure be kept to a minimum and that suitable control measures be used in an occupational setting. Inhalation of vapours may cause drowsiness and dizziness. This may be accompanied by narcosis, reduced alertness, loss of reflexes, lack of coordination and vertigo.</p> <p>Acute exposure of humans to high concentrations of methyl ethyl ketone produces irritation to the eyes, nose, and throat. Other effects reported from acute inhalation exposure in humans include central nervous system depression, headache, and nausea.</p> <p>Easy odour recognition and irritant properties of methyl ethyl ketone means that high vapour levels are readily detected and should be avoided by application of control measures; however odour fatigue may occur with loss of warning of exposure.</p>
Ingestion	<p>The material has <b>NOT</b> been classified by EC Directives or other classification systems as 'harmful by ingestion'. This is because of the lack of corroborating animal or human evidence. The material may still be damaging to the health of the individual, following ingestion, especially where pre-existing organ (e.g liver, kidney) damage is evident. Present definitions of harmful or toxic substances are generally based on doses producing mortality rather than those producing morbidity (disease, ill-health). Gastrointestinal tract discomfort may produce nausea and vomiting. In an occupational setting however, ingestion of insignificant quantities is not thought to be cause for concern.</p>
Skin Contact	<p>The material is not thought to produce adverse health effects or skin irritation following contact (as classified by EC Directives using animal models). Nevertheless, good hygiene practice requires that exposure be kept to a minimum and that suitable gloves be used in an occupational setting. Repeated exposure may cause skin cracking, flaking or drying following normal handling and use.</p> <p>Dermatitis has been reported in humans following dermal exposure to methyl ethyl ketone. Tests involving acute exposure of rabbits has shown methyl ethyl ketone to have high acute toxicity from dermal exposure.</p> <p>Open cuts, abraded or irritated skin should not be exposed to this material</p> <p>Entry into the blood-stream through, for example, cuts, abrasions, puncture wounds or lesions, may produce systemic injury with harmful effects. Examine the skin prior to the use of the material and ensure that any external damage is suitably protected.</p>
Eye	<p>Evidence exists, or practical experience predicts, that the material may cause eye irritation in a substantial number of individuals and/or may produce significant ocular lesions which are present twenty-four hours or more after instillation into the eye(s) of experimental animals.</p> <p>Repeated or prolonged eye contact may cause inflammation characterised by temporary redness (similar to windburn) of the conjunctiva (conjunctivitis); temporary impairment of vision and/or other transient eye damage/ulceration may occur.</p>
Chronic	<p>Practical experience shows that skin contact with the material is capable either of inducing a sensitisation reaction in a substantial number of individuals, and/or of producing a positive response in experimental animals.</p> <p>Prolonged or repeated skin contact may cause drying with cracking, irritation and possible dermatitis following.</p> <p>Limited information is available on the chronic (long-term) effects of methyl ethyl ketone in humans. Chronic inhalation studies in animals have reported slight neurological, liver, kidney, and respiratory effects. No information is available on the developmental, reproductive, or carcinogenic effects of methyl ethyl ketone in humans. Developmental effects, including decreased foetal weight and foetal malformations, have been reported in mice and rats exposed to methyl ethyl ketone via inhalation and ingestion.</p> <p>Methyl ethyl ketone is considered to have a low order of toxicity; however methyl ethyl ketone is often used in combination with other solvents and the toxic effects of the mix may be greater than either solvent alone. Combinations of n-hexane with methyl ethyl ketone and also methyl n-butyl ketone with methyl ethyl ketone show increase in peripheral neuropathy, a progressive disorder of nerves of extremities.</p> <p>Combinations with chloroform also show increase in toxicity</p>

419D Acrylic Conformal Coating	TOXICITY	IRRITATION
	Not Available	Not Available
n-butyl acetate	TOXICITY	IRRITATION
	Dermal (rabbit) LD50: 3200 mg/kg <sup>[2]</sup>	Eye (human): 300 mg
	Inhalation (rat) LC50: 1.802 mg/l4 h <sup>[1]</sup>	Eye (rabbit): 20 mg (open)-SEVERE

Continued...

## 419D Acrylic Conformal Coating

	Oral (rat) LD50: 10768 mg/kg <sup>[2]</sup>	Eye (rabbit): 20 mg/24h - moderate Skin (rabbit): 500 mg/24h-moderate
methyl ethyl ketone	<b>TOXICITY</b>	<b>IRRITATION</b>
	Dermal (rabbit) LD50: 6480 mg/kg <sup>[2]</sup>	Eye (human): 350 ppm -irritant
	Inhalation (rat) LC50: 47 mg/l/8H <sup>[2]</sup>	Eye (rabbit): 80 mg - irritant
	Oral (rat) LD50: 2054 mg/kg <sup>[1]</sup>	Skin (rabbit): 402 mg/24 hr - mild Skin (rabbit):13.78mg/24 hr open
methyl methacrylate	<b>TOXICITY</b>	<b>IRRITATION</b>
	Dermal (rabbit) LD50: >5000 mg/kg <sup>[2]</sup>	Eye (rabbit): 150 mg
	Inhalation (rat) LC50: 78 mg/l/4H <sup>[2]</sup>	Skin (rabbit): 10000 mg/kg (open)
n-butyl methacrylate	<b>TOXICITY</b>	<b>IRRITATION</b>
	Dermal (rabbit) LD50: 11300 mg/kg <sup>[2]</sup>	Skin (rabbit): 10000 mg/kg (open)
	Inhalation (rat) LC50: 4904.39769 mg/l/4h <sup>[2]</sup>	
	<b>Legend:</b>	1. Value obtained from Europe ECHA Registered Substances - Acute toxicity 2. * Value obtained from manufacturer's SDS. Unless otherwise specified data extracted from RTECS - Register of Toxic Effect of chemical Substances

419D Acrylic Conformal Coating	Methyl ethyl ketone is considered to have a low order of toxicity; however methyl ethyl ketone is often used in combination with other solvents and the toxic effects of the mix may be greater than either solvent alone. Combinations of n-hexane with methyl ethyl ketone and also methyl n-butyl ketone with methyl ethyl ketone show increase in peripheral neuropathy, a progressive disorder of nerves of extremities. Combinations with chloroform also show increase in toxicity
N-BUTYL ACETATE	The material may produce severe irritation to the eye causing pronounced inflammation. Repeated or prolonged exposure to irritants may produce conjunctivitis. The material may cause skin irritation after prolonged or repeated exposure and may produce a contact dermatitis (nonallergic). This form of dermatitis is often characterised by skin redness (erythema) and swelling the epidermis. Histologically there may be intercellular oedema of the spongy layer (spongiosis) and intracellular oedema of the epidermis.
METHYL METHACRYLATE	<b>For methyl methacrylate:</b> Acute toxicity: MMA is rapidly absorbed after oral or inhalatory administration. <i>In vitro</i> skin absorption studies in human skin indicate that MMA can be absorbed through human skin. After inhalation to rats 10 to 20% of the substance is deposited in the upper respiratory tract where it is metabolised by local tissue esterases. Acute toxicity of MMA by the oral, dermal, and inhalative routes is low as judged by tests with different species: The oral LD50 for rats, mice, and rabbits is found to exceed 5000 mg/kg bw. Acute inhalation toxicity for rats and mice is described by LC50 values of > 25 mg/l/4 hours. Acute dermal toxicity is reported for rabbits to exceed 5000 mg/kg bw. Skin and respiratory irritation are reported for subjects exposed to monomeric MMA. The substance has been shown to produce severe skin irritation when tested undiluted on rabbit skin. There are indications from studies in animals that MMA can be irritating to the respiratory system. In contact with eyes MMA has shown only weak irritation of the conjunctivae. MMA has a moderate to strong sensitising potential in experimental animals. Cases of contact dermatitis have been reported for workers exposed to the monomeric chemical. There is no convincing evidence that MMA is a respiratory sensitiser in humans. The lead effect caused by MMA is a degeneration of the olfactory region of the nose being the most sensitive target tissue. For this effect a NOAEC of 25 ppm (104 mg/m <sup>3</sup> ) in a two-year inhalation study in rats was identified but only slight effects on the olfactory tissues have been observed at 100 ppm. Concerning systemic effects, two different valid studies have been considered for identifying a N(L)OEL. Due to different dose selections, different values for N(L)OELs are available. The LOELs and the NOELs for female rats ranges between 400 and 500 ppm and from 100 to 250 ppm respectively. In subchronic inhalation studies systemic toxic effects were seen in rats >1000 ppm, respectively in mice >500 ppm, including degenerative and necrotic lesions in liver, kidney, brain, and atrophic changes in spleen and bone marrow. These effects were not seen in chronic studies up to 1000 ppm. Oral administration to rats resulted in a NOAEL of 200 mg/kg bw/d. MMA has <i>in vitro</i> the potential for induction of mutagenic effects, especially clastogenicity. However, this potential is limited to high doses with strong toxic effects. Furthermore, the negative <i>in vivo</i> micronucleus test and the negative dominant lethal assay indicate that this potential is not expressed <i>in vivo</i> . There is no relevant concern on carcinogenicity of MMA in humans and animals. Epidemiology data on increased tumour rates in exposed cohorts are of limited reliability and cannot be related to MMA as the solely causal agent. MMA did not reveal an effect on male fertility when animals had been exposed to up to 9000 ppm. From the available developmental toxicity investigations, including an inhalation study according to OECD Guideline 414, no teratogenicity, embryotoxicity or foetotoxicity has been observed at exposure levels up to and including 2028 ppm (8425 mg/m <sup>3</sup> ). The available human data on sexual disorders in male and female workers cannot be considered to conclude on reproductive toxicity effects of MMA due to the uncertain validity of the studies The substance is classified by IARC as Group 3: <b>NOT</b> classifiable as to its carcinogenicity to humans. Evidence of carcinogenicity may be inadequate or limited in animal testing. Inhalation (human) TCLo: 60 mg/m <sup>3</sup> (15 ppm) [* Manuf. Rohm & Haas]
N-BUTYL METHACRYLATE	For iso-butyl methacrylate (i-BMA) and n-butyl methacrylate (n-BMA): <b>Acute toxicity:</b> It is anticipated that BMA is absorbed after oral or inhalation exposure. <i>In vitro</i> studies using isolated rat liver microsomes or porcine liver esterase showed rapid hydrolysis of n-BMA yielding methacrylic acid and n-butanol. No <i>in vivo</i> metabolism data is available on n-BMA/ i-BMA, but from the <i>in vitro</i> data rapid hydrolysis to methacrylic acid and the corresponding alcohol can be anticipated. n-BMA did not bind to glutathione (GSH) <i>in vitro</i> . It is expected that after hydrolysis the respective cleavage products, methacrylic acid and n-butanol or isobutanol are further metabolised to CO <sub>2</sub> . In mammals n-BMA/ i-BMA is of low oral toxicity by the oral, dermal or inhalation route. They have local irritating properties to rabbit skin and eyes. Respiratory tract irritation was observed after inhalation exposure to rats of n-BMA. Whilst n-BMA is a weak skin sensitiser in guinea pigs there is no such evidence for i-BMA. From available human clinical data it can be concluded that the sensitisation potential to humans of n-BMA is low.

## 419D Acrylic Conformal Coating

	<p><b>Repeat dose toxicity:</b> A repeat dose oral study of limited reliability, indicates that n-BMA is of low oral toxicity. A reliable 28-day exposure inhalation study in rats, for n-BMA demonstrated the formation of nasal lesions indicative of a local irritant effect of the nose without indication of systemic toxicity.</p> <p><b>Genotoxicity:</b> Neither n-BMA nor i-BMA was mutagenic in a number of gene mutation assays with Salmonella typhimurium. i-BMA was not clastogenic in a mouse micronucleus assay. There appears to be little concern for genotoxicity despite limited data.</p> <p><b>Carcinogenicity:</b> Given the lack of carcinogenicity observed with methyl methacrylic (the metabolite) and the lack of genotoxic potential there appears to be little concern for possible carcinogenicity of BMA. Neither isobutanol or n-butanol exhibit carcinogenic potential.</p> <p><b>Developmental toxicity:</b> Available data for methyl methacrylate and n-butanol isobutanol suggests that there is little concern for possible developmental effects arising out of inhalation exposure to non-maternally toxic concentrations of n-BMA/ i-BMA.</p> <p><b>Repeat dose toxicity:</b> Limited data from repeated dose studies with n-BMA, methyl methacrylate, methacrylic acid and a fertility study with n-butanol did not reveal any indications for possible toxicity on the reproductive organ</p>
419D Acrylic Conformal Coating & METHYL METHACRYLATE & N-BUTYL METHACRYLATE	<p>The following information refers to contact allergens as a group and may not be specific to this product.</p> <p>Contact allergies quickly manifest themselves as contact eczema, more rarely as urticaria or Quincke's oedema. The pathogenesis of contact eczema involves a cell-mediated (T lymphocytes) immune reaction of the delayed type. Other allergic skin reactions, e.g. contact urticaria, involve antibody-mediated immune reactions. The significance of the contact allergen is not simply determined by its sensitisation potential: the distribution of the substance and the opportunities for contact with it are equally important. A weakly sensitising substance which is widely distributed can be a more important allergen than one with stronger sensitising potential with which few individuals come into contact. From a clinical point of view, substances are noteworthy if they produce an allergic test reaction in more than 1% of the persons tested.</p>
METHYL METHACRYLATE & N-BUTYL METHACRYLATE	<p>Asthma-like symptoms may continue for months or even years after exposure to the material ceases. This may be due to a non-allergenic condition known as reactive airways dysfunction syndrome (RADS) which can occur following exposure to high levels of highly irritating compound. Key criteria for the diagnosis of RADS include the absence of preceding respiratory disease, in a non-atopic individual, with abrupt onset of persistent asthma-like symptoms within minutes to hours of a documented exposure to the irritant. A reversible airflow pattern, on spirometry, with the presence of moderate to severe bronchial hyperreactivity on methacholine challenge testing and the lack of minimal lymphocytic inflammation, without eosinophilia, have also been included in the criteria for diagnosis of RADS. RADS (or asthma) following an irritating inhalation is an infrequent disorder with rates related to the concentration of and duration of exposure to the irritating substance. Industrial bronchitis, on the other hand, is a disorder that occurs as result of exposure due to high concentrations of irritating substance (often particulate in nature) and is completely reversible after exposure ceases. The disorder is characterised by dyspnea, cough and mucus production.</p>
METHYL METHACRYLATE & N-BUTYL METHACRYLATE	<p>Where no 'official' classification for acrylates and methacrylates exists, there has been cautious attempts to create classifications in the absence of contrary evidence. For example</p> <p>Monalkyl or monoarylestere of acrylic acids should be classified as R36/37/38 and R51/53</p> <p>Monoalkyl or monoaryl esters of methacrylic acid should be classified as R36/37/38</p>
METHYL METHACRYLATE & N-BUTYL METHACRYLATE	<p>Based on the available oncogenicity data and without a better understanding of the carcinogenic mechanism the Health and Environmental Review Division (HERD), Office of Toxic Substances (OTS), of the US EPA previously concluded that all chemicals that contain the acrylate or methacrylate moiety (CH<sub>2</sub>=CHCOO or CH<sub>2</sub>=C(CH<sub>3</sub>)COO) should be considered to be a carcinogenic hazard unless shown otherwise by adequate testing. This position has now been revised and acrylates and methacrylates are no longer <i>de facto</i> carcinogens.</p>

Acute Toxicity	☹	Carcinogenicity	☹
Skin Irritation/Corrosion	☹	Reproductivity	☹
Serious Eye Damage/Irritation	✓	STOT - Single Exposure	✓
Respiratory or Skin sensitisation	✓	STOT - Repeated Exposure	☹
Mutagenicity	☹	Aspiration Hazard	☹

Legend: ✗ – Data available but does not fill the criteria for classification  
✓ – Data available to make classification  
☹ – Data Not Available to make classification

## SECTION 12 ECOLOGICAL INFORMATION

## 12.1. Toxicity

419D Acrylic Conformal Coating	ENDPOINT	TEST DURATION (HR)	SPECIES	VALUE	SOURCE
	Not Available	Not Available	Not Available	Not Available	Not Available

  

n-butyl acetate	ENDPOINT	TEST DURATION (HR)	SPECIES	VALUE	SOURCE
	LC50	96	Fish	18mg/L	4
	EC50	48	Crustacea	=32mg/L	1
	EC50	72	Algae or other aquatic plants	=674.7mg/L	1
	EC0	192	Algae or other aquatic plants	=21mg/L	1

  

methyl ethyl ketone	ENDPOINT	TEST DURATION (HR)	SPECIES	VALUE	SOURCE
	LC50	96	Fish	>400mg/L	4
	EC50	48	Crustacea	308mg/L	2
	EC50	96	Algae or other aquatic plants	>500mg/L	4
	NOEC	48	Crustacea	68mg/L	2

  

methyl methacrylate	ENDPOINT	TEST DURATION (HR)	SPECIES	VALUE	SOURCE
	LC50	96	Fish	>79mg/L	2
	EC50	48	Crustacea	=69mg/L	1
	EC50	72	Algae or other aquatic plants	>110mg/L	2
	NOEC	504	Crustacea	37mg/L	2

Continued...

## 419D Acrylic Conformal Coating

<b>Legend:</b>	Extracted from 1. IUCLID Toxicity Data 2. Europe ECHA Registered Substances - Ecotoxicological Information - Aquatic Toxicity 3. EPIWIN Suite V3.12 (QSAR) - Aquatic Toxicity Data (Estimated) 4. US EPA, Ecotox database - Aquatic Toxicity Data 5. ECETOC Aquatic Hazard Assessment Data 6. NITE (Japan) - Bioconcentration Data 7. METI (Japan) - Bioconcentration Data 8. Vendor Data
----------------	---

Harmful to aquatic organisms.

For methyl ethyl ketone:

log Kow : 0.26-0.69

log Koc : 0.69

Koc : 34

Half-life (hr) air : 2.3

Half-life (hr) H<sub>2</sub>O surface water : 72-288

Henry's atm m<sup>3</sup>/mol: 1.05E-05

BOD 5 : 1.5-2.24, 46%

COD : 2.2-2.31, 100%

ThOD : 2.44

BCF : 1

**Environmental fate:**

**TERRESTRIAL FATE:** Measured Koc values of 29 and 34 were obtained for methyl ethyl ketone in silt loams. Methyl ethyl ketone is expected to have very high mobility in soil. Volatilisation of methyl ethyl ketone from dry soil surfaces is expected based upon an experimental vapor pressure of 91 mm Hg at 25 deg C. Volatilization from moist soil surfaces is also expected given the measured Henry's Law constant of 4.7x10<sup>-5</sup> atm-cu m/mole. The volatilisation half-life of methyl ethyl ketone from silt and sandy loams was measured as 4.9 days. Methyl ethyl ketone is expected to biodegrade under both aerobic and anaerobic conditions as indicated by numerous screening tests.

**AQUATIC FATE:** Based on Koc values, methyl ethyl ketone is not expected to adsorb to suspended solids and sediment in water. Methyl ethyl ketone is expected to volatilise from water surfaces based on the measured Henry's Law constant. Estimated half-lives for a model river and model lake are 19 and 197, hours respectively. Biodegradation of this compound is expected based upon numerous screening tests. An estimated BCF value of 1 based on an experimental log Kow of 0.29, suggests that bioconcentration in aquatic organisms is low.

**ATMOSPHERIC FATE:** According to a model of gas/particle partitioning of semivolatile organic compounds in the atmosphere, methyl ethyl ketone, which has an experimental vapor pressure of 91 mm Hg at 25 deg C, will exist solely as a vapor in the ambient atmosphere. Vapour-phase methyl ethyl ketone is degraded in the atmosphere by reaction with photochemically-produced hydroxyl radicals; the half-life for this reaction in air is estimated to be about 14 days. Methyl ethyl ketone is also expected to undergo photodecomposition in the atmosphere by natural sunlight.

Photochemical degradation of methyl ethyl ketone by natural sunlight is expected to occur at approximately 1/5 the rate of degradation by photochemically produced hydroxyl radicals.

**Ecotoxicity:**

Fish LC50 (24 h): bluegill sunfish (*Lepomis macrochirus*) 1690-5640 mg/l; guppy (*Lebistes reticulatus*) 5700 mg/l; goldfish (*Carassius auratus*) >5000 mg/l

Fish LC50 (96 h): fathead minnow (*Pimephales promelas*) 3200 mg/l; bluegill sunfish (*Lepomis macrochirus*) 4467 mg/l; mosquito fish (*Gambusia affinis*) 5600 mg/l

Daphnia magna LC50 (48 h): <520-1382 mg/l

Daphnia magna LC50 (24 h): 8890 mg/l

Brine shrimp (*Artemia salina*) LC50 (24 h): 1950 mg/l

For n-butyl acetate:

Half-life (hr) air : 144

Half-life (hr) H<sub>2</sub>O surface water : 178-27156

Henry's atm m<sup>3</sup>/mol: 3.20E-04

BOD 5 if unstated: 0.15-1.02,7%

COD : 78%

ThOD : 2.207

BCF : 4-14

**Environmental Fate:**

**TERRESTRIAL FATE:** An estimated Koc value of 200 determined from a measured log Kow of 1.78 indicates that n-butyl acetate is expected to have moderate mobility in soil. Volatilisation of n-butyl acetate is expected from moist soil surfaces given its Henry's Law constant of 2.8x10<sup>-4</sup> atm-cu m/mole. Volatilisation from dry soil surfaces is expected based on a measured vapor pressure of 11.5 mm Hg. Using a standard BOD dilution technique and a sewage inoculum, theoretical BODs of 56 % to 86 % were observed during 5-20 day incubation periods, which suggests that n-butyl acetate may biodegrade in soil.

**AQUATIC FATE:** An estimated Koc value indicates that n-butyl acetate is not expected to adsorb to suspended solids and sediment in water. Butyl acetate is expected to volatilise from water surfaces based on a Henry's Law constant of 2.8x10<sup>-4</sup> atm-cu m/mole. Estimated half-lives for a model river and model lake are 7 and 127, hours respectively. An estimated BCF value of 10 based on the log Kow, suggests that bioconcentration in aquatic organisms is low. Using a filtered sewage seed, 5-day and 20-day theoretical BODs of 58 % and 83 % were measured in freshwater dilution tests; 5-day and 20-day theoretical BODs of 40 % and 61 % were measured in salt water. A 5-day theoretical BOD of 56.8 % and 51.8 % were measured for n-butyl acetate in distilled water and seawater, respectively. Hydrolysis may be an important environmental fate for this compound based upon experimentally determined hydrolysis half-lives of 114 and 11 days at pH 8 and 9 respectively.

**ATMOSPHERIC FATE:** According to a model of gas/particle partitioning of semivolatile organic compounds in the atmosphere, n-butyl acetate, which has a vapour pressure of 11.5 mm Hg at 25 deg C, is expected to exist solely as a vapor in the ambient atmosphere. Vapour-phase n-butyl acetate is degraded in the atmosphere by reaction with photochemically-produced hydroxyl radicals; the half-life for this reaction in air is estimated to be about 4 days

**Environmental fate:**

Fish LC50 (96 h, 23 C): island silverside (*Menidia beryllina*) 185 ppm (static bioassay in synthetic seawater, mild aeration applied after 24 h); bluegill sunfish (*Lepomis macrochirus*) 100 ppm

(static bioassay in fresh water, mild aeration applied after 24 h)

Fish EC50 (96 h): fathead minnow (*Pimephales promelas*) 18 mg/l (affected fish lost equilibrium prior to death)

Daphnia LC50 (48 h): 44 ppm

Algal LC50 (96 h): *Scenedesmus* 320 ppm

**DO NOT discharge into sewer or waterways.**

## 12.2. Persistence and degradability

Ingredient	Persistence: Water/Soil	Persistence: Air
n-butyl acetate	LOW	LOW
methyl ethyl ketone	LOW (Half-life = 14 days)	LOW (Half-life = 26.75 days)
methyl methacrylate	LOW	LOW
n-butyl methacrylate	LOW	LOW

## 12.3. Bioaccumulative potential

Ingredient	Bioaccumulation
n-butyl acetate	LOW (BCF = 14)
methyl ethyl ketone	LOW (LogKOW = 0.29)
methyl methacrylate	LOW (BCF = 6.6)
n-butyl methacrylate	LOW (BCF = 114)

## 12.4. Mobility in soil

Ingredient	Mobility
------------	----------

## 419D Acrylic Conformal Coating

n-butyl acetate	LOW (KOC = 20.86)
methyl ethyl ketone	MEDIUM (KOC = 3.827)
methyl methacrylate	LOW (KOC = 10.14)
n-butyl methacrylate	LOW (KOC = 63.6)

## 12.5. Results of PBT and vPvB assessment

	P	B	T
Relevant available data	Not Available	Not Available	Not Available
PBT Criteria fulfilled?	Not Available	Not Available	Not Available

## 12.6. Other adverse effects

No data available

## SECTION 13 DISPOSAL CONSIDERATIONS

## 13.1. Waste treatment methods

Product / Packaging disposal	<ul style="list-style-type: none"> <li>▶ Containers may still present a chemical hazard/ danger when empty.</li> <li>▶ Return to supplier for reuse/ recycling if possible.</li> </ul> <p>Otherwise:</p> <ul style="list-style-type: none"> <li>▶ If container can not be cleaned sufficiently well to ensure that residuals do not remain or if the container cannot be used to store the same product, then puncture containers, to prevent re-use, and bury at an authorised landfill.</li> <li>▶ Where possible retain label warnings and SDS and observe all notices pertaining to the product.</li> </ul> <p>Legislation addressing waste disposal requirements may differ by country, state and/ or territory. Each user must refer to laws operating in their area. In some areas, certain wastes must be tracked.</p> <p>A Hierarchy of Controls seems to be common - the user should investigate:</p> <ul style="list-style-type: none"> <li>▶ Reduction</li> <li>▶ Reuse</li> <li>▶ Recycling</li> <li>▶ Disposal (if all else fails)</li> </ul> <p>This material may be recycled if unused, or if it has not been contaminated so as to make it unsuitable for its intended use. If it has been contaminated, it may be possible to reclaim the product by filtration, distillation or some other means. Shelf life considerations should also be applied in making decisions of this type. Note that properties of a material may change in use, and recycling or reuse may not always be appropriate.</p> <ul style="list-style-type: none"> <li>▶ <b>DO NOT allow wash water from cleaning or process equipment to enter drains.</b></li> <li>▶ It may be necessary to collect all wash water for treatment before disposal.</li> <li>▶ In all cases disposal to sewer may be subject to local laws and regulations and these should be considered first.</li> <li>▶ Where in doubt contact the responsible authority.</li> <li>▶ Recycle wherever possible.</li> <li>▶ Consult manufacturer for recycling options or consult local or regional waste management authority for disposal if no suitable treatment or disposal facility can be identified.</li> <li>▶ Dispose of by: burial in a land-fill specifically licensed to accept chemical and / or pharmaceutical wastes or Incineration in a licensed apparatus (after admixture with suitable combustible material).</li> <li>▶ Decontaminate empty containers. Observe all label safeguards until containers are cleaned and destroyed.</li> </ul>	
	Waste treatment options	Not Available
	Sewage disposal options	Not Available

## SECTION 14 TRANSPORT INFORMATION

## Labels Required

		Limited Quantity: 419D-55ML, 419D-1L, 419D-4L
--	---	---

## Land transport (ADR)

14.1.UN number	1263										
14.2.UN proper shipping name	PAINT										
14.3. Transport hazard class(es)	<table border="1"> <tr> <td>Class</td> <td>3</td> </tr> <tr> <td>Subrisk</td> <td>Not Applicable</td> </tr> </table>	Class	3	Subrisk	Not Applicable						
Class	3										
Subrisk	Not Applicable										
14.4.Packing group	II										
14.5.Environmental hazard	Not Applicable										
14.6. Special precautions for user	<table border="1"> <tr> <td>Hazard identification (Kemler)</td> <td>33</td> </tr> <tr> <td>Classification code</td> <td>F1</td> </tr> <tr> <td>Hazard Label</td> <td>3</td> </tr> <tr> <td>Special provisions</td> <td>163 367 640C 640D 650</td> </tr> <tr> <td>Limited quantity</td> <td>5 L</td> </tr> </table>	Hazard identification (Kemler)	33	Classification code	F1	Hazard Label	3	Special provisions	163 367 640C 640D 650	Limited quantity	5 L
Hazard identification (Kemler)	33										
Classification code	F1										
Hazard Label	3										
Special provisions	163 367 640C 640D 650										
Limited quantity	5 L										

## 419D Acrylic Conformal Coating

## Air transport (ICAO-IATA / DGR)

14.1. UN number	1263	
14.2. UN proper shipping name	PAINT	
14.3. Transport hazard class(es)	ICAO/IATA Class	3
	ICAO / IATA Subrisk	Not Applicable
	ERG Code	3L
14.4. Packing group	II	
14.5. Environmental hazard	Not Applicable	
14.6. Special precautions for user	Special provisions	A3 A72 A192
	Cargo Only Packing Instructions	364
	Cargo Only Maximum Qty / Pack	60 L
	Passenger and Cargo Packing Instructions	353
	Passenger and Cargo Maximum Qty / Pack	5 L
	Passenger and Cargo Limited Quantity Packing Instructions	Y341
	Passenger and Cargo Limited Maximum Qty / Pack	1 L

## Sea transport (IMDG-Code / GGVSee)

14.1. UN number	1263	
14.2. UN proper shipping name	PAINT	
14.3. Transport hazard class(es)	IMDG Class	3
	IMDG Subrisk	Not Applicable
14.4. Packing group	II	
14.5. Environmental hazard	Not Applicable	
14.6. Special precautions for user	EMS Number	F-E , S-E
	Special provisions	163 367
	Limited Quantities	5 L

## Inland waterways transport (ADN)

14.1. UN number	1263	
14.2. UN proper shipping name	PAINT	
14.3. Transport hazard class(es)	3 Not Applicable	
14.4. Packing group	II	
14.5. Environmental hazard	Not Applicable	
14.6. Special precautions for user	Classification code	F1
	Special provisions	163; 367; 640C; 650; 640D
	Limited quantity	5 L
	Equipment required	PP, EX, A
	Fire cones number	1

## 14.7. Transport in bulk according to Annex II of MARPOL and the IBC code

Not Applicable

## SECTION 15 REGULATORY INFORMATION

## 15.1. Safety, health and environmental regulations / legislation specific for the substance or mixture

## N-BUTYL ACETATE(123-86-4) IS FOUND ON THE FOLLOWING REGULATORY LISTS

European Customs Inventory of Chemical Substances ECICS (English)

European Union - European Inventory of Existing Commercial Chemical Substances (EINECS) (English)

European Union (EU) Annex I to Directive 67/548/EEC on Classification and Labelling of Dangerous Substances - updated by ATP: 31

European Union (EU) Regulation (EC) No 1272/2008 on Classification, Labelling and Packaging of Substances and Mixtures - Annex VI

UK Workplace Exposure Limits (WELs)

## METHYL ETHYL KETONE(78-93-3) IS FOUND ON THE FOLLOWING REGULATORY LISTS

Continued...

## 419D Acrylic Conformal Coating

EU Consolidated List of Indicative Occupational Exposure Limit Values (IOELVs)	European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Greek)
EU European Chemicals Agency (ECHA) Community Rolling Action Plan (CoRAP) List of Substances	European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Hungarian)
European Customs Inventory of Chemical Substances ECICS (English)	European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Italian)
European Trade Union Confederation (ETUC) Priority List for REACH Authorisation	European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Latvian)
European Union - European Inventory of Existing Commercial Chemical Substances (EINECS) (English)	European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Lithuanian)
European Union (EU) Annex I to Directive 67/548/EEC on Classification and Labelling of Dangerous Substances - updated by ATP: 31	European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Maltese)
European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Bulgarian)	European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Polish)
European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Czech)	European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Portuguese)
European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Danish)	European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Romanian)
European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Dutch)	European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Slovak)
European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (English)	European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Slovenian)
European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Estonian)	European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Spanish)
European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Finnish)	European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (Swedish)
European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (French)	European Union (EU) Regulation (EC) No 1272/2008 on Classification, Labelling and Packaging of Substances and Mixtures - Annex VI
European Union (EU) First List of Indicative Occupational Exposure Limit Values (IOELVs) (German)	UK Workplace Exposure Limits (WELs)
<b>METHYL METHACRYLATE(80-62-6) IS FOUND ON THE FOLLOWING REGULATORY LISTS</b>	
EU European Chemicals Agency (ECHA) Community Rolling Action Plan (CoRAP) List of Substances	European Union (EU) Regulation (EC) No 1272/2008 on Classification, Labelling and Packaging of Substances and Mixtures - Annex VI
European Customs Inventory of Chemical Substances ECICS (English)	European Union (EU) Third List of Indicative Occupational Exposure Limit Values (IOELVs) (English)
European Union - European Inventory of Existing Commercial Chemical Substances (EINECS) (English)	International Agency for Research on Cancer (IARC) - Agents Classified by the IARC Monographs
European Union (EU) Annex I to Directive 67/548/EEC on Classification and Labelling of Dangerous Substances - updated by ATP: 31	International Air Transport Association (IATA) Dangerous Goods Regulations - Prohibited List Passenger and Cargo Aircraft
	UK Workplace Exposure Limits (WELs)

**N-BUTYL METHACRYLATE(97-88-1) IS FOUND ON THE FOLLOWING REGULATORY LISTS**

European Customs Inventory of Chemical Substances ECICS (English)	European Union (EU) Annex I to Directive 67/548/EEC on Classification and Labelling of Dangerous Substances - updated by ATP: 31
European Union - European Inventory of Existing Commercial Chemical Substances (EINECS)(English)	European Union (EU) Regulation (EC) No 1272/2008 on Classification, Labelling and Packaging of Substances and Mixtures - Annex VI

This safety data sheet is in compliance with the following EU legislation and its adaptations - as far as applicable - : 98/24/EC, 92/85/EC, 94/33/EC, 91/689/EEC, 1999/13/EC, Commission Regulation (EU) 2015/830, Regulation (EC) No 1272/2008 and their amendments

**15.2. Chemical safety assessment**

For further information please look at the Chemical Safety Assessment and Exposure Scenarios prepared by your Supply Chain if available.

National Inventory	Status
Australia - AICS	Y
Canada - DSL	Y
Canada - NDSL	N (methyl methacrylate; n-butyl acetate; n-butyl methacrylate; methyl ethyl ketone)
China - IECSC	Y
Europe - EINEC / ELINCS / NLP	Y
Japan - ENCS	N (n-butyl methacrylate)
Korea - KECI	Y
New Zealand - NZIoC	Y
Philippines - PICCS	Y
USA - TSCA	Y
<b>Legend:</b>	Y = All ingredients are on the inventory N = Not determined or one or more ingredients are not on the inventory and are not exempt from listing(see specific ingredients in brackets)

**SECTION 16 OTHER INFORMATION****Full text Risk and Hazard codes**

<b>H226</b>	Flammable liquid and vapour.
<b>H315</b>	Causes skin irritation.
<b>H335</b>	May cause respiratory irritation.

## 419D Acrylic Conformal Coating

### Other information

Classification of the preparation and its individual components has drawn on official and authoritative sources as well as independent review by the Chemwatch Classification committee using available literature references.

The SDS is a Hazard Communication tool and should be used to assist in the Risk Assessment. Many factors determine whether the reported Hazards are Risks in the workplace or other settings. Risks may be determined by reference to Exposures Scenarios. Scale of use, frequency of use and current or available engineering controls must be considered.

For detailed advice on Personal Protective Equipment, refer to the following EU CEN Standards:

EN 166 Personal eye-protection

EN 340 Protective clothing

EN 374 Protective gloves against chemicals and micro-organisms

EN 13832 Footwear protecting against chemicals

EN 133 Respiratory protective devices

### Definitions and abbreviations

PC—TWA: Permissible Concentration-Time Weighted Average

PC—STEL: Permissible Concentration-Short Term Exposure Limit

IARC: International Agency for Research on Cancer

ACGIH: American Conference of Governmental Industrial Hygienists

STEL: Short Term Exposure Limit

TEEL: Temporary Emergency Exposure Limit.

IDLH: Immediately Dangerous to Life or Health Concentrations

OSF: Odour Safety Factor

NOAEL :No Observed Adverse Effect Level

LOAEL: Lowest Observed Adverse Effect Level

TLV: Threshold Limit Value

LOD: Limit Of Detection

OTV: Odour Threshold Value

BCF: BioConcentration Factors

BEI: Biological Exposure Index

### Reason for Change

A-1.02 - Update to the emergency phone number information.