

5-V Low Drop Fixed Voltage Regulator

TLE 4268





Features

- Output voltage tolerance ≤ ±2%
- Very low current consumption
- Low-drop voltage
- Watchdog
- Settable reset threshold
- Overtemperature protection
- Reverse polarity protection
- Short-circuit proof
- Suitable for use in automotive electronics
- Wide temperature range
- Green Product (RoHS compliant)
- AEC Qualified




This device is a 5-V low-drop fixed-voltage regulator. The maximum input voltage is 45 V. It can deliver an output current of at least 180 mA. The IC is short-circuit proof and features temperature protection that disables the


circuit in the event of impermissibly high temperatures. The watchdog function is disabled as a function of the load, so that a controller is not interrupted during sleep mode by a watchdog reset.



The IC regulates an input voltage $V_{\rm I}$ in the range 5.5 V < $V_{\rm I}$ < 45 V to $V_{\rm Q,nom}$ = 5.0 V. In the event of an output voltage $V_{\rm Q}$ < $V_{\rm RT}$, a reset signal is generated. The wiring of the reset switching threshold input enables the value of $V_{\rm RT}$ to be reduced. The reset delay time can be adjusted using an external capacitor. The integrated watchdog monitors the connected active controller. If there is no rising edge at the watchdog input, the reset

Туре	Package
TLE 4268 GS	PG-DSO-8-16
TLE 4268 G	PG-DSO-20-35







output is set to low. The reset delay capacitor provides a wide adjustment range for the pulse repetition time. The watchdog function is only activated if the load exceeds 8 mA. This ensures that a microcontroller is not activated during power-down and the current drain is not increased. The IC is protected against overload and overtemperature.




Figure 1 Pin Configuration (top view)

Table 1 Pin Definitions and Functions

Pin	Symbol	Function
1	I	Input voltage
2	N.C.	Not connected
3	RO	Reset output
4	GND	Ground
5	D	Reset delay
6	RADJI	Reset switching threshold
7	W	Watchdog input
8	Q	5 V output voltage

Data Sheet 2 Rev. 1.5, 2007-03-20






Figure 2 Pin Configuration (top view)

Table 2 Pin Definitions and Functions

Pin	Symbol	Function
1, 2, 8, 13, 19, 20	N.C.	Not connected.
3	RO	Reset output ; the open collector output is connected to the 5-V output via an integrated resistor of 30 k Ω .
4 7, 14 17	GND	Ground
9	D	Reset delay; connect a capacitor to ground for delay time adjustment.
10	RADJ	Reset switching threshold; for setting the switching threshold, output to ground with voltage divider. If this input is connected to ground, the reset is triggered at an output voltage of 4.5 V.
11	W	Watchdog input ; positive-edge-triggered input for monitoring a microcontroller.
12	Q	5-V output voltage; block to ground with 22 μ F capacitor, ESR < 3 Ω .
18	I	Input voltage; block to ground directly on the IC with ceramic capacitor.

Data Sheet 3 Rev. 1.5, 2007-03-20



Circuit Description

The control amplifier compares a reference voltage, which is kept highly accurate by resistance adjustment, to a voltage that is proportional to the output voltage and drives the base of the series transistor via a buffer. Saturation control as a function of the load current prevents any over-saturation of the power element. If the externally scaled down output voltage at the reset threshold input drops below 1.35 V, the external reset delay capacitor is discharged by the reset generator. If the voltage on the capacitor reaches the lower threshold $V_{\rm DRL}$, a reset signal is generated on the reset output and not cancelled again until the upper threshold voltage is exceeded. If the reset threshold input is connected to GND, reset is triggered at an output voltage of 4.5 V. A connected microcontroller is monitored by the watchdog logic. If pulses are missing, the rest output is set to low. The pulse sequence time can be set within a wide range with the reset delay capacitor. The IC also incorporates internal circuits for protection against:

- Overload
- Overtemperature
- Reverse polarity




Figure 3 Block Diagram TLE 4268 G (PG-DSO-20-35)

Data Sheet 4 Rev. 1.5, 2007-03-20



Table 3 Absolute Maximum Ratings

Parameter	Symbol	Limit Values		Unit	Notes	
		Min.	Max.			
Input I		1	1	1		
Input voltage Input current	$egin{array}{c} V_{l} \ I_{l} \end{array}$	-30 -	45 -	V -	– Internally limited	
Reset Output RO		-1		I		
Voltage Current	$V_{R} \ I_{R}$	-0.3 -	7 –	V -	– Internally limited	
Reset Delay D						
Voltage Current	$egin{array}{c} V_{D} \ I_{D} \end{array}$	-0.3 -	7 –	V -	- Internally limited	
Watchdog W	<u> </u>				•	
Watchdog input	V_{W}	-0.3	7	V	_	
Reset Switching Threshold RADJ						
Reset threshold	V_{RADJ}	-0.3	7	V	_	
Output Q	<u> </u>				•	
Output voltage Output current	$V_{Q} = I_{Q}$	-0.3 -	7	V -	- Internally limited	
Ground GND			·			
Current	I_{GND}	-100	50	mA	_	
Temperatures			•	<u>.</u>		
Junction temperature Storage temperature	$T_{ m S}$	-40 -50	150 150	°C		



Table 4 Operating Range

Parameter	Symbol	Limit Values		Unit	Notes
		Min.	Max.		
Input voltage	V_{I}	_	45	V	_
Junction temperature	$T_{\rm j}$	-40	150	°C	_
Thermal Resistance			•	•	
Junction ambient (soldered)	$R_{ ext{thj-a}} \ R_{ ext{thj-a}}$	_ _	185 100	K/W K/W	PG-DSO-8-16 ¹⁾ PG-DSO-20-35 ¹⁾
Junction pin	$R_{ ext{thj-pin}} \ R_{ ext{thi-pin}}$		72 23	K/W K/W	PG-DSO-8-16 ²⁾ PG-DSO-20-35 ³⁾

¹⁾ Package mounted on PCB $80 \times 80 \times 1.5 \text{ mm}^3$; 35μ Cu; 5μ Sn; Footprint only; zero airflow.

Optimum reliability and life time are guaranteed if the junction temperature does not exceed 125 °C in operating mode. Operation at up to the maximum junction temperature of 150 °C is possible in principle. Note, however, operation at the maximum permitted ratings could affect the reliability of the device.

Data Sheet 6 Rev. 1.5, 2007-03-20

²⁾ Measured to pin 2.

³⁾ Measured to pin 5.



Table 5 Characteristics

 $V_{\rm I}$ = 13.5 V; -40 °C ≤ $T_{\rm j}$ ≤ 125 °C (unless otherwise specified)

Parameter	Symbol	Limit Values		Unit	Test Condition	
		Min.	Тур.	Max.	1	
Output voltage	V_{Q}	4.90	5.00	5.10	V	5 mA $\leq I_{\rm Q} \leq$ 150 mA; 6 V $\leq V_{\rm I} \leq$ 28 V
Output current limiting	I_{Q}	180	250	_	mA	_
Current consumption $I_q = I_l - I_Q$	I_{q}	_	300	450	μΑ	$I_{Q} = 0 \text{ mA}$
Current consumption $I_q = I_l - I_Q$	I_{q}	_	13	20	mA	$I_{\rm Q}$ = 150 mA
Drop voltage	V_{DR}	_	0.25	0.50	V	$I_{\rm Q}$ = 150 mA ¹⁾
Load regulation	$\Delta V_{Q,Lo}$	_	10	30	mV	$I_{\rm Q}$ = 5 to 150 mA
Line regulation	$\Delta V_{Q,Li}$	_	10	30	mV	$V_{\rm I}$ = 6 to 28 V $I_{\rm Q}$ = 150 mA
Reset Generator			•	•		
Reset threshold	$V_{Q,rt}$	4.2	4.5	4.8	V	_
Reset adjust threshold	V_{RADJ}	1.28	1.35	1.45	V	_
Reset low voltage	$V_{RO,I}$	_	0.2	0.5	V	1 mA external
Saturation voltage	V_{D}	_	30	100	mV	$V_{\rm Q} < V_{\rm RT}$
Charging current	$I_{D,c}$	5	12	18	μΑ	$V_{\rm D}$ = 1.0 V
Upper reset timing threshold	V_{DU}	1.4	1.8	2.2	V	_
Reset delay time	$t_{\rm rd}$	10	15	25	ms	$C_{\rm D}$ = 100 nF
Reset reaction time	t_{rr}	_	2	_	μs	$C_{\rm D}$ = 100 nF
Pull-up	R_{RO}	18	30	46	kΩ	with resp. to V_{Q}
Lower reset timing threshold	V_{DRL}	0.2	0.4	0.55	V	_



Table 5Characteristics (cont'd)

 $V_{\rm I}$ = 13.5 V; -40 °C ≤ $T_{\rm j}$ ≤ 125 °C (unless otherwise specified)

Parameter	Symbol	Limit Values			Unit	Test Condition	
		Min.	Тур.	Max.			
Watchdog							
Discharge current	$I_{D,d}$	1.5	3.5	5.2	μΑ	$V_{\rm D}$ = 1.0 V	
Charging current	$I_{D,c}$	5	12	18	μА	$V_{\rm D}$ = 1.0 V	
Upper timing threshold	V_{DU}	1.4	1.8	2.2	V	_	
Lower timing threshold	V_{DWL}	0.2	0.4	0.55	V	_	
Watchdog period	T_{WP}	30	55	75	ms	$C_{\rm D}$ = 100 nF	
Watchdog trigger time	T_{WT}	25	40	60	ms	$C_{\rm D}$ = 100 nF	
Activating current	I_{Q}	2	8	15	mA	Activates watchdog	
Slew rate	$\mathrm{d}V_{\mathrm{W}}/\mathrm{dt}$	5	_	_	V/μs	from 20% up to 80% $V_{\rm Q}^{\ 2)}$	

¹⁾ Drop voltage = $V_{\rm I}$ - $V_{\rm Q}$ (measured when the output voltage has dropped 100 mV from the nominal value obtained at 13.5 V input)

Note: The reset output is low in range from $V_{\rm Q}$ = 1 V to $V_{\rm Q,rt}$

Data Sheet 8 Rev. 1.5, 2007-03-20

²⁾ Watchdog pulse recognition tested with 10 kHz max. pulse frequency






Figure 4 Test Circuit



Reset Timing

The power-on reset delay time is defined by the charging time of an external capacitor $C_{\rm D}$ which can be calculated as follows:

$$C_{\rm D} = (\Delta t_{\rm rd} \times I_{\rm D.c})/\Delta V \tag{1}$$

Definitions:

- C_D = delay capacitor
- $\Delta t_{\rm rd}$ = delay time
- $I_{D,c}$ = charge current, typical 12 μ A
- $\Delta \dot{V} = V_{DU}$, typical 1.8 V
- V_{DU} = upper delay switching threshold at C_{D} for reset delay time

The reset reaction time $t_{\rm rr}$ is the time it takes the voltage regulator to set the reset out LOW after the output voltage has dropped below the reset threshold. It is typically 1 μ s for delay capacitor of 47 nF. For other values for $C_{\rm D}$ the reaction time can be estimated using the following equation:

$$t_{\rm rr} \approx 20 \text{ s/F} \times C_{\rm D}$$
 (2)




Figure 5 Timing (Watchdog disabled)

Data Sheet 10 Rev. 1.5, 2007-03-20







Figure 6 Timing of the Watchdog Function


Data Sheet 11 Rev. 1.5, 2007-03-20




Drop Voltage V_{DR} versus Output Current I_{Q}




Current Consumption $I_{\rm q}$ versus Output Current $I_{\rm Q}$



Current Consumption I_{q} versus Input Voltage V_{l}




Output Voltage versus Input Voltage $V_{\rm I}$







Charge Current $I_{D,c}$ and Discharge Current $I_{D,d}$ versus Temperature T_i




Timing Threshold $V_{\mathrm{DU}},\,V_{\mathrm{DWL}},\,V_{\mathrm{DRL}}$ versus Temperature T_{i}



Output Voltage $V_{\rm Q}$ versus Temperature $T_{\rm i}$



Output Current $I_{\mathbf{Q}}$ versus Input Voltage $V_{\mathbf{I}}$





Package Outlines




Figure 7 PG-DSO-8-16 (Plastic Dual Small Outline)

Green Product (RoHS compliant)

To meet the world-wide customer requirements for environmentally friendly products and to be compliant with government regulations the device is available as a green product. Green products are RoHS-Compliant (i.e Pb-free finish on leads and suitable for Pb-free soldering according to IPC/JEDEC J-STD-020).

You can find all of our packages, sorts of packing and others in our Infineon Internet Page "Products": http://www.infineon.com/products.

SMD = Surface Mounted Device

Dimensions in mm






Figure 8 PG-DSO-20-35 (Plastic Dual Small Outline)

Green Product (RoHS compliant)

To meet the world-wide customer requirements for environmentally friendly products and to be compliant with government regulations the device is available as a green product. Green products are RoHS-Compliant (i.e Pb-free finish on leads and suitable for Pb-free soldering according to IPC/JEDEC J-STD-020).

You can find all of our packages, sorts of packing and others in our Infineon Internet Page "Products": http://www.infineon.com/products.

SMD = Surface Mounted Device

Dimensions in mm



Version	Date	Changes
Rev. 1.5	2007-03-20	Initial version of RoHS-compliant derivate of TLE 4268 Page 1: AEC certified statement added Page 1 and Page 14 ff: RoHS compliance statement and Green product feature added Page 1 and Page 14 ff: Package changed to RoHS compliant version Legal Disclaimer updated

Data Sheet 16 Rev. 1.5, 2007-03-20

Edition 2007-03-20
Published by
Infineon Technologies AG
81726 Munich, Germany
© 2007 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.