PSoC® 6 MCU: PSoC 63 with BLE Datasheet



Programmable System-on-Chip (PSoC®)

General Description

PSoC[®] 6 MCU is a high-performance, ultra-low-power and secure MCU platform, purpose-built for IoT applications. The PSoC 63 with BLE product family, based on the PSoC 6 MCU platform, is a combination of a dual core microcontroller with low-power flash technology, digital programmable logic, high-performance analog-to-digital and standard communication and timing peripherals. The PSoC 63 family provides wireless connectivity with BLE 5.0 compliance.

Features

32-bit Dual-Core CPU Subsystem

- 150-MHz Arm[®] Cortex[®]-M4F CPU with single-cycle multiply (Floating Point and Memory Protection Unit)
- 100-MHz Cortex-M0+ CPU with single-cycle multiply and MPU
- User-selectable core logic operation at either 1.1 V or 0.9 V
- 8-KB Instruction Caches for both CPU cores
- Active CPU current slope with 1.1-V core operation
 - □ Cortex-M4: 40 μA/MHz
 - □ Cortex-M0+: 20 µA/MHz
- Active CPU current slope with 0.9-V core operation
 - □ Cortex-M4: 22 µA/MHz□ Cortex-M0+: 15 µA/MHz
- Two DMA controllers with 16 channels each

Flash Memory Subsystem

- 1-MB Application Flash, 32-KB emulated EEPROM area, and 32-KB Supervisory Flash
- 288-KB SRAM with power and data retention control
- One-Time-Programmable (OTP) 1-Kb eFuse memory for validation and security

Bluetooth Low Energy (Bluetooth Smart) BT 5.0 Subsystem

- 2.4-GHz RF transceiver with 50-W antenna drive
- Digital PHY
- Link Layer engine supporting master and slave modes
- Programmable output power: up to 4 dBm
- RX sensitivity: -95 dBm
- RSSI: 4-dB resolution
- 5.7 mA TX (0 dBm) and 6.7 mA RX (2 Mbps) current with 3.3-V battery and internal SIMO Buck converter
- Link Layer engine supports four connections simultaneously
- Supports 2 Mbps LE data rate

Low-Power 1.7-V to 3.6-V Operation

- Six power modes for fine-grained power management
- Deep Sleep mode current of 7 µA with 64-KB SRAM retention
- On-chip Single-In Multiple Out (SIMO) DC-DC Buck converter, <1 µA quiescent current
- Backup domain with 64 bytes of memory and Real-Time Clock

Flexible Clocking Options

- On-chip crystal oscillators (4 to 35 MHz, and 32 kHz)
- Phase-locked Loop (PLL) for multiplying clock frequencies
- 8 MHz Internal Main Oscillator (IMO) with ±2% accuracy
- Ultra-low-power 32-kHz Internal Low-speed Oscillator (ILO)
- Frequency Locked Loop (FLL) for multiplying IMO frequency

QSPI Interface (QSPI)/Serial Memory Interface (SMIF)

- Execute-In-Place (XIP) from external Quad SPI Flash
- On-the-fly encryption and decryption
- 4-KB cache for greater XIP performance with lower power
- Supports single, dual, quad, dual-quad, and octal interfaces w/ throughput up to 640 Mbps

Serial Communication

- Nine run-time configurable serial communication blocks (SCBs)
 - ☐ Eight SCBs: configurable as SPI, I²C, or UARTs☐ One Deep Sleep SCB: configurable as SPI or I²C
- USB Full-Speed Dual-role Host and Device interface

Audio Subsystem

■ Two PDM channels and one I²S channel with TDM mode

Programmable Analog

- 12-bit 1-Msps SAR ADC with differential and single-ended modes and 16-channel sequencer with result averaging
- Two low-power comparators available in Deep Sleep and Hibernate modes
- Built-in temp sensor connected to ADC
- One 12-bit voltage mode DAC with < 5-µs settling time
- Two opamps with low-power operation modes

Up to 78 Programmable GPIOs

- Two Smart I/O ports (16 I/Os) enable Boolean operations on GPIO pins; available during Deep Sleep
- Programmable drive modes, strengths, and slew rates
- Six overvoltage-tolerant (OVT) pins

Cypress Semiconductor Corporation • 198
Document Number: 002-18787 Rev. *H



Capacitive Sensing

- Cypress CapSense Sigma-Delta (CSD) provides best-in-class SNR, liquid tolerance, and proximity sensing
- Enables dynamic usage of both self and mutual sensing
- Automatic hardware tuning (SmartSenseTM)

Security Built into Platform Architecture

- ROM-based root of trust via uninterruptible Secure Boot
- Step-wise authentication of execution images
- Secure execution of code in execute-only mode for protected routines
- All Debug and Test ingress paths can be disabled
- Up to eight Protection Contexts

Cryptography Accelerators

- Hardware acceleration for symmetric and asymmetric cryptographic methods and hash functions
- True Random Number Generator (TRNG) function

Programmable Digital

- 12 programmable logic blocks, each with 8 Macrocells and an 8-bit data path (called universal digital blocks or UDBs)
- Usable as drag-and-drop Boolean primitives (gates, registers), or as Verilog programmable blocks
- Cypress-provided peripheral component library using UDBs to implement functions such as Communication peripherals (for example, LIN, UART, SPI, I²C, S/PDIF and other protocols), Waveform Generators, Pseudo-Random Sequence (PRS) generation, and many other functions.)

Energy Profiler

- Block that provides history of time spent in different power modes
- Allows software energy profiling to observe and optimize energy consumption

Packages

- 116-BGA and 104-MCSP packages with PSoC 6 and BLE Radio
- 104-MCSP package with BLE Radio and USB
- 124-BGA package in the process of qualification
- 68-QFN package

PSoC® 6 MCU: PSoC 63 with BLE Datasheet



Contents

Development Ecosystem	4
PSoC 6 MCU Resources	4
PSoC Creator	5
ModusToolbox™ IDE and the PSoC 6 SDK	5
Blocks and Functionality	7
Functional Description	
CPU and Memory Subsystem	8
System Resources 1	0
BLE Radio and Subsystem 1	2
Programmable Analog Subsystem 1	3
Programmable Digital 1	
Fixed-Function Digital 1	
GPIO 1	5
Special-Function Peripherals 1	6
Pinouts 2	0
Power Supply Considerations 3	6
Electrical Specifications 3	8
Absolute Maximum Ratings	8

Device-Level Specifications	38
Analog Peripherals	45
Digital Peripherals	54
Memory	56
System Resources	57
Packaging	71
Acronyms	76
Document Conventions	78
Unit of Measure	78
Errata	79
Revision History	81
Sales, Solutions, and Legal Information	82
Worldwide Sales and Design Support	82
Products	82
PSoC® Solutions	82
Cypress Developer Community	82
Technical Support	



Development Ecosystem

PSoC 6 MCU Resources

Cypress provides a wealth of data at www.cypress.com to help you select the right PSoC device and quickly and effectively integrate it into your design. The following is an abbreviated, hyperlinked list of resources for PSoC 6 MCU:

- Overview: PSoC Portfolio, PSoC Roadmap
- Product Selectors: PSoC 6 MCU
- Application Notes cover a broad range of topics, from basic to advanced level, and include the following:
 - □ AN221774: Getting Started with PSoC 6 MCU
 - □ AN210781: Getting Started with PSoC 6 MCU BLE
 - □ AN218241: PSoC 6 MCU Hardware Design Guide
 - □ AN213924: PSoC 6 MCU Device Firmware Update Guide
 - □ AN215656: PSoC 6 MCU Dual-CPU System Design
- □ AN219528: PSoC 6 MCU Power Reduction Techniques
- □ AN221111: PSoC 6 MCU Creating a Secure System
- □ AN85951: PSoC 4, PSoC 6 MCU CapSense Design Guide
- Code Examples demonstrate product features and usage, and are also available on Cypress GitHub repositories.
- Technical Reference Manuals (TRMs) provide detailed descriptions of PSoC 6 MCU architecture and registers.

- PSoC 6 MCU Programming Specification provides the information necessary to program PSoC 6 MCU nonvolatile memory
- Development Tools
 - ¬ ModusToolbox™ enables cross platform code development with a robust suite of tools and software libraries
 - □ PSoC 6 BLE: CY8CKIT-062-BLE supports the PSoC 63 series MCU with Bluetooth Low-Energy (BLE) connectivity.
 - □ PSoC 62: CY8CKIT-062-Wi-Fi-/BT supports the PSoC 62 series MCU with WiFi and Bluetooth connectivity.
 - PSoC 6 CAD libraries provide footprint and schematic support for common tools
- Training Videos are available on a wide range of topics including the PSoC 6 MCU 101 series
- Cypress Developer Community enables connection with fellow PSoC developers around the world, 24 hours a day, 7 days a week, and hosts a dedicated PSoC 6 MCU Community

Document Number: 002-18787 Rev. *H Page 4 of 82




PSoC Creator

PSoC Creator is a free Windows-based Integrated Design Environment (IDE). It enables you to design hardware and firmware systems concurrently, based on PSoC 6 MCU. As shown below, with PSoC Creator, you can:

- 1. Explore the library of 200+ Components in PSoC Creator
- Drag and drop Component icons to complete your hardware system design in the main design workspace
- Configure Components using the Component Configuration Tools and the Component datasheets
- Co-design your application firmware and hardware in the PSoC Creator IDE or build project for 3rd party IDE
- Prototype your solution with the PSoC 6 Pioneer Kits.If a design change is needed, PSoC Creator and Components enable you to make changes on the fly without the need for hardware revisions.

Figure 1. PSoC Creator Schematic Entry and Components



ModusToolbox™ IDE and the PSoC 6 SDK

ModusToolbox is an Eclipse-based development environment on Windows, macOS, and Linux platforms that includes the ModusToolbox IDE and the PSoC 6 SDK. The ModusToolbox IDE brings together several device resources, middleware, and firmware to build an application. Using ModusToolbox, you can enable and configure device resources and middleware libraries, write C/assembly source code, and program and debug the device.

The PSoC 6 SDK is the software development kit for the PSoC 6 MCU. The SDK makes it easier to develop firmware for supported devices without the need to understand the intricacies of the device resources.

For additional detail on using the Cypress tools, refer to AN221774: Getting Started with PSoC 6 MCU and the documentation and help integrated into ModusToolbox. As Figure 1 shows, with the ModusToolbox IDE, you can:

- 1. Create a new application based on a list of starter applications, filtered by kit or device, or browse the collection of code examples online.
- 2. Configure device resources in design.modus to build your hardware system design in the workspace.
- 3. Add software components or middleware.
- 4. Develop your application firmware.






Figure 2. ModusToolbox IDE Resources and Middleware



Blocks and Functionality

Figure 3 shows the block diagram.

There are five major subsystems: CPU subsystem, BLE subsystem, system resources, peripheral blocks, and I/O subsystem.




Figure 3. Block Diagram

Figure 3 shows the subsystems of the chip and gives a very simplified view of their inter-connections (Multi-layer AHB is used in practice). The color-coding shows the lowest power mode where the particular block is still functional (for example, LP Comparator is functional in Deep Sleep mode).

The PSoC 6 devices include extensive support for programming, testing, debugging, and tracing both hardware and firmware.

Complete debug-on-chip functionality enables full device debugging in the final system using the standard production device. It does not require special interfaces, debugging pods, simulators, or emulators. Only the standard programming connections are required to fully support debug.

The ModusToolbox Integrated Development Environment (IDE) provides fully integrated programming and debug support for these devices. The SWJ (SWD and JTAG) interface is fully compatible with industry-standard third party probes. With the ability to disable debug features, with very robust flash protection, and by allowing customer-proprietary functionality to be implemented in on-chip programmable blocks, PSoC 6 provides a very high level of security.

There are three debug access ports, one each for CM4 and CM0+, and a system port. They are enabled by default. Each can be disabled and enabled independently.

Additionally, all device interfaces can be permanently disabled (device security) for applications concerned about attacks due to a maliciously reprogrammed device or attempts to defeat security by starting and interrupting flash programming sequences. All programming, debug, and test interfaces are disabled when maximum device security is enabled. The security level is a trade-off the customer can make.

The PSoC Creator Integrated Development Environment (IDE) provides fully integrated programming and debug support for PSoC 6 devices. The SWJ (SWD and JTAG) interface is fully compatible with industry-standard third party probes. With the ability to disable debug features, with very robust flash protection, and by allowing customer-proprietary functionality to be implemented in on-chip programmable blocks, the PSoC 6 family provides a very high level of security.

Document Number: 002-18787 Rev. *H Page 7 of 82



Functional Description

The following sections provide an overview of the features, capabilities and operation of each functional block identified in the block diagram in Figure 3. For more detailed information, refer to the following three references.

Peripheral Driver Library (PDL) Application Programming Interface (API) Reference Manual.

PDL provides low-level drivers for each resource in the device, and supports the entire PSoC 6 MCU portfolio. PDL is an element of the PSoC 6 SDK, which is installed as part of ModusToolbox. With ModusToolbox installed, you can access the PDL API reference manual either from the Documentation tab of the Quick Panel, or you can navigate directly to it at $<install_directory>|ModusToolbox_<ver-sion>|libraries||psoc6sw-<version>|docs.|$ Using PDL should be the primary means of interacting with the PSoC 6 MCU hardware.

■ Architecture Technical Reference Manual (TRM)

The architecture TRM provides the detailed description of each resource in the device. This is the next reference to use if it is necessary to understand the operation of the hardware below the software provided by PDL. It describes the architecture and functionality of each resource and explains the operation of each resource in all modes. It provides specific guidance regarding the use of associated registers.

■ Register Technical Reference Manual

The register TRM provides the complete list of all registers in the device. It includes the breakdown of all register fields, their possible settings, read/write accessibility, and default states. All registers that have a reasonable use in typical applications have functions to access them from within PDL. Note that ModusToolbox and PDL may provide software default conditions for some registers that are different from and override the hardware defaults.

CPU and Memory Subsystem

PSoC 63 has multiple bus masters, as Figure 3 shows. They are: two CPUs, two DMA controllers, and a Crypto block. Generally, in , all memory and peripherals can be accessed and shared by all bus masters through multi-layer Arm AMBA high-performance bus (AHB) arbitration. Accesses between Cores can be synchronized using an inter-processor communication (IPC) block.

CPU

There are two Arm Cortex CPUs:

The Cortex-M4 (CM4) CPU has single-cycle multiply, a floating-point unit (FPU), and a memory protection unit (MPU). It can run at up to 150 MHz. This is the main CPU, designed for a short interrupt response time, high code density, and high throughput.

CM4 implements a version of the Thumb instruction set based on Thumb-2 technology (defined in the *Armv7-M Architecture Reference Manual*).

The Cortex-M0+ (CM0+) CPU has single-cycle multiply, and an MPU. It can run at up to 100 MHz; however, for CM4 speeds above 100 MHz, CM0+ and bus peripherals are limited to half

the speed of CM4. Thus, for CM4 running at 150 MHz, CM0+ and peripherals are limited to 75 MHz.

CM0+ is the secondary CPU; it is used to implement system calls and device-level security, safety, and protection features. CM0+ provides a secure, uninterruptible boot function. This guarantees that post boot, system integrity is checked and memory and peripheral access privileges are enforced.

CM0+ implements the Armv6-M Thumb instruction set (defined in the *Armv6-M Architecture Reference Manual*).

These CPUs have the following power draw, at V_{DD} = 3.3 V and using the internal buck regulator:

Table 1. Active Current Slope at V_{DD} = 3.3 V Using the Internal Buck Regulator

		System Power Mode	
		ULP	LP
СРИ	Cortex-M0+	15 μA/MHz	20 μA/MHz
	Cortex-M4	22 μA/MHz	40 μA/MHz

These CPUs can be selectively placed in their Sleep and Deep Sleep power modes as defined by Arm.

Each CPU has an 8-KB instruction cache with 4-way set associativity. Both CPUs have nested vectored interrupt controllers (NVIC) for rapid and deterministic interrupt response, and wakeup interrupt controllers (WIC) for CPU wakeup from Deep Sleep power mode.

These CPUs have extensive debug support. has a debug access port (DAP) that acts as the interface for device programming and debug. An external programmer or debugger (the "host") communicates with the DAP through the device serial wire debug (SWD) or Joint Test Action Group (JTAG) interface pins. Through the DAP (and subject to device security restrictions), the host can access the device memory and peripherals as well as the registers in both CPUs.

Each CPU offers debug and trace features as follows:

- CM4 supports six hardware breakpoints and four watchpoints, 4-bit embedded trace macrocell (ETM), serial wire viewer (SWV), and printf()-style debugging through the single wire output (SWO) pin.
- CM0+ supports four hardware breakpoints and two watchpoints, and a micro trace buffer (MTB) with 4 KB dedicated RAM.

PSoC 63 also has an Embedded Cross Trigger for synchronized debugging and tracing of both CPUs.

Interrupts

PSoC 63 with BLE has 147 system and peripheral interrupt sources and supports interrupts and system exception on both CPUs. CM4 has 147 interrupt request lines (IRQ), with the interrupt source 'n' directly connected to IRQn. CM0+ has 32 interrupts IRQ[31:0] with configurable mapping of one system interrupt source to any of the IRQ[31:0].

Each interrupt supports configurable priority levels (eight levels for CM4 and four levels for CM0+). One system interrupt can be mapped to each of the CPU's non-maskable interrupt (NMI). Up to 41 interrupt sources are capable of waking the device from Deep Sleep power mode using the WIC. Refer to the technical reference manual for details.



DMA Controllers

There are two DMA controllers with 16 channels each. They support independent accesses to peripherals using the AHB Multi-layer bus. The descriptors for DMA channels can be in SRAM or flash. Therefore, the number of descriptors are limited only by the size of the memory. Each descriptor can transfer data in two nested loops with configurable address increments to the source and destination. The size of data transfer per descriptor varies based on the type of DMA channel. Refer to the technical reference manual for detail.

Cryptography Accelerator (Crypto)

This subsystem consists of hardware implementation and acceleration of cryptographic functions and random number generators.

The Crypto subsystem supports the following:

- Encryption/Decryption Functions
 - □ Data Encryption Standard (DES)
 - □ Triple DES (3DES)
 - □ Advanced Encryption Standard (AES) (128-, 192-, 256-bit)
 - ☐ Elliptic Curve Cryptography (ECC)
 - □ RSA cryptography functions
- Hashing functions
 - □ Secure Hash Algorithm (SHA)
 - □ SHA1
 - □ SHA224/256/384/512
- Message authentication functions (MAC)
 - ☐ Hashed message authentication code (HMAC)
 - □ Cipher-based message authentication code (CMAC)
- 32-bit cyclic redundancy code (CRC) generator
- Random number generators
 - □ Pseudo random number generator (PRNG)
 - ☐ True random number generator (TRNG)

Protection Units

PSoC 63 with BLE has multiple types of protection units to control erroneous or unauthorized access to memory and peripheral registers. CM4 and CM0+ have Arm MPUs for protection at the bus master level. Other bus masters use additional MPUs. Shared memory protection units (SMPUs) help implement memory protection for memory/ resources that are shared among multiple bus masters. Peripheral protection units (PPU) are similar to SMPUs but are designed for protecting the peripheral register space.

Protection units support memory and peripheral access attributes including address range, read/write, code/data, privilege level, secure/non-secure, and protection context.

Protection units are configured at secure boot to control access privileges and rights for bus masters and peripherals.

Up to eight protection contexts (secure boot is in protection context 0) allow access privileges for memory and system resources to be set by the secure boot process per protection context by bus master and code privilege level. Multiple protection contexts are supported on a single CPU.

Memory

PSoC 63 with BLE contains flash, SRAM, ROM, and eFuse memory blocks.

■ Flash

Up to 1 MB of application flash is provided, with two additional 32-KB flash sectors. The application flash is organized into 256-KB sectors. The first 32-KB flash sector is typically used for EEPROM emulation, or equivalent data storage. The second 32-KB region is the supervisory flash (SFlash). Data stored in SFlash includes device trim values, Flash Boot executable code, and encryption keys. After the device transitions into secure mode, SFlash can no longer be changed.

The flash has 128-bit-wide accesses to reduce power. Write operations can be performed at the row level. A row, also referred to as a page, is 512 bytes. Read operations are supported in both System Low Power and Ultra-Low Power modes, however write operations may not be performed in System Ultra-Low Power mode.

■ SRAM

There is 288 KB of SRAM memory, which can be fully retained or retained in increments of user-designated 32 KB blocks.

ROM

The 128-KB ROM, also referred to as the supervisory ROM (SROM), provides code (ROM Boot) for several system functions. The PSoC 6 MCU ROM contains device initialization, flash write, security, eFuse programming, and other system-level routines. ROM code is executed only by the CM0+ CPU, in protection context 0. A system function can be initiated by either CPU, or through the DAP. This causes an NMI interrupt in CM0+, which causes CM0+ to execute the system function.

■ eFuse

One-time-programmable eFuse consists of 1024 bits, of which 512 are reserved for system use. The remaining bits are available for storing security key information, hash values, unique IDs or other similar user-defined content. Each fuse is individually programmed; once programmed (or "blown"), its state cannot be changed. Blowing a fuse transitions it from the default state of 0 to 1. To program an eFuse, $V_{\rm DDIOO}$ must be at 2.5 V ±5%, with a current draw of 14 mA (max).

Boot Code

Two blocks of code, ROM Boot and Flash Boot, are pre-programmed into the device and work together to provide device startup and configuration, basic security features, life-cycle stage management and other system functions.

■ ROM Boot

On a device reset, the boot code in ROM is the first code to execute. This code performs the following:

- Integrity checks of flash boot code
- □ Device trim setting (calibration)
- ☐ Setting the device protection units
- □ Setting device access restrictions for secure life-cycle states ROM cannot be changed and acts as the Root of Trust in a secure system. ROM code will guarantee secure boot if authentication of application flash is required.



■ Flash Boot

Flash boot is firmware stored in SFlash that ensures that only a validated application may run on the device. It also ensures that the firmware image has not been modified, such as by a malicious third party.

Flash boot:

- ☐ Is validated by ROM Boot
- □ Runs after ROM Boot and before the user application
- □ Verifies the integrity of the user application
- □ Enables system calls
- □ Configures the Debug Access Port
- □ Launches the user application in the CM4

If the user application cannot be validated, then flash boot ensures that the device is transitioned into a safe state.

Memory Map

Both CPUs have a fixed address map, with shared access to memory and peripherals. The 32-bit (4 GB) address space is divided into the regions shown in Table 2. Note that code can be executed from the code and SRAM regions.

Table 2. Address Map for CM4 and CM0+

Address Bangs	Name	Use
Address Range	Name	Use
0x0000 0000 – 0x1FFF FFFF	Code	Program code region. Data can also be placed here. It includes the exception vector table, which starts at address 0.
0x2000 0000 – 0x3FFF FFFF	SRAM	Data region. Code can also be executed from this region. Note that CM4 bit-band in this region is not supported.
0x4000 0000 – 0x5FFF FFFF	Peripheral	All peripheral registers. Code cannot be executed from this region. Note that CM4 bit-band in this region is not supported.
0x6000 0000 – 0x9FFF FFFF	External RAM	Code can be executed from this region.
0xA000 0000 – 0xDFFF FFFF	External device	Not used.
0xE000 0000 – 0xE00F FFFF	Private peripheral Bus	Provides access to peripheral registers within the CPU core.
0xE010 0A000 – 0xFFFF FFFF	Device	Device-specific system registers.

The device memory map shown in Table 3 applies to both CPUs. That is, the CPUs share access to all PSoC 6 MCU memory and peripheral registers. Note that code can be executed from the Code, SRAM, and external RAM regions.

Table 3. Internal Memory Address Map for CM4 and CM0+

Address Range	Memory Type	Size
0x0000 0000 – 0x0001 FFFF	ROM	128 KB
0x0800 0000 – 0x0804 7FFF	SRAM	Up to 288 KB
0x1000 0000 – 0x100F FFFF	Application flash	Up to 1 MB
0x1400 0000 - 0x1400 7FFF	EEPROM emulation flash	32 KB
0x1600 0000 - 0x1600 7FFF	Supervisory flash	32 KB
0x1800 0000 - 0x1FFF FFFF	External memory execute in place region	Up to 128 MB

Note that the SRAM is located in the Code region for both CPUs (see Table 2). There is no physical memory located in the CPUs' SRAM region.

System Resources

Power System

The power system provides assurance that voltage levels are as required for each respective mode and will either delay mode entry (on power-on reset (POR), for example) until voltage levels are as required for proper function or generate resets (brown-out detect (BOD)) when the power supply drops below specified levels. The design guarantees safe chip operation between power supply voltage dropping below specified levels (for example, below 1.7 V) and the reset occurring. There are no voltage sequencing requirements.

The V_{DD} supply (1.7 to 3.6 V) powers an on-chip buck regulator or an LDO, selectable by the user. In addition, both the buck and the LDO offer a selectable (0.9 or 1.1 V) core operating voltage (V_{CCD}). The selection lets users choose between two system power modes:

- System Low Power (LP) operates V_{CCD} at 1.1 V and offers high performance, with no restrictions on any of the device configurations
- System Ultra Low Power (ULP) operates V_{CCD} at 0.9 V for exceptional low power results, but imposes limitations on maximum clock speeds.

An additional backup domain adds an "always on" functionality using a separate power domain supplied by a backup supply (V_{BACKUP}) such as a battery or supercapacitor. It includes a real-time clock (RTC) with alarm feature, supported by a 32.768-kHz watch crystal oscillator (WCO), and power-management IC (PMIC) control. Pin 5 of Port 0 (P0.5) can be assigned as an enable signal for an external PMIC. RTC alarms can be used as a trigger for the PMIC enable signal.

Power Modes

PSoC 6 MCU can operate in four system and three CPU power modes. These modes are intended to minimize the average power consumption in an application. For more details on power modes and other power-saving configuration options, see the application note, AN219528: PSoC 6 MCU Low-Power Modes and Power Reduction Techniques and the Architecture TRM, Power Modes chapter.



Power modes supported by PSoC 6 MCUs, in the order of decreasing power consumption, are:

- System Low Power (LP) All peripherals and CPU power modes are available at maximum speed
- System Ultra Low Power (ULP) All peripherals and CPU power modes are available, but with limited speed
- CPU Active CPU is executing code in system LP or ULP mode
- CPU Sleep CPU code execution is halted in system LP or **ULP** mode
- CPU Deep Sleep CPU code execution is halted and system Deep Sleep is requested in system LP or ULP mode
- System Deep Sleep Only low-frequency peripherals are available after both CPUs enter CPU Deep Sleep mode
- System Hibernate Device and I/O states are frozen and the device resets on wakeup

CPU Active, Sleep, and Deep Sleep are standard Arm-defined power modes supported by the Arm CPU instruction set architecture (ISA). LP, ULP, Deep Sleep and Hibernate modes are additional low-power modes supported by PSoC 6 MCU. Hibernate mode is the lowest power mode in the PSoC 6 MCU and on wakeup, the CPU and all peripherals go through a reset.

Clock System

The PSoC 63 with BLE clock system consists of the following (see Figure 3):

- IMO
- ILO/PILO
- Watch crystal oscillator (WCO)
- External MHz crystal oscillator (ECO)
- External clock input
- One PLL
- One FLL

Clocks may be buffered and brought out to a pin on a smart I/O port.

IMO Clock Source

The IMO is the primary source of internal clocking. It is trimmed during testing to achieve the specified accuracy. The IMO default frequency is 8 MHz. IMO tolerance is ±2% and its current consumption is less than 10 µA.

ILO Clock Source

The ILO is a very low power oscillator, nominally 32 kHz, which operates in all power modes. The ILO can be calibrated against a higher accuracy clock for better accuracy.

Precision ILO (PILO)

PILO is an additional source that can provide a more accurate 32.768-kHz clock than ILO when periodically calibrated using a high-accuracy clock such as the ECO. The PILO works in Deep Sleep and higher modes. It does not work in Hibernate mode.




Figure 4. Clocking Diagram

PII O



Watchdog Timer

A watchdog timer is implemented in the clock block running from the ILO; this allows watchdog operation during Deep Sleep and Hibernate modes, and generates a watchdog reset if not serviced before the timeout occurs. The watchdog reset is recorded in the Reset Cause register.

Clock Dividers

Integer and fractional clock dividers are provided for peripheral use and timing purposes. There are:

- Eight 8-bit clock dividers
- Sixteen 16-bit integer clock dividers
- Four 16.5-bit fractional clock dividers
- One 24.5-bit fractional clock divider

Trigger Routing

PSoC 6 MCU contains a trigger multiplexer block. This is a collection of digital multiplexers and switches that are used for routing trigger signals between peripheral blocks and between GPIOs and peripheral blocks.

Reset

PSoC 6 MCU can be reset from a variety of sources:

- Power-on reset (POR) to hold the device in reset while the power supply ramps up to the level required for the device to function properly. POR activates automatically at power-up.
- Brown-out detect (BOD) reset to monitor the digital voltage supply V_{DDD} and generate a reset if V_{DDD} falls below the minimum required logic operating voltage.
- External reset (XRES) to reset the device using an external input. The XRES pin is active LOW a logic '1' on the pin has no effect and a logic '0' causes reset. The pin is pulled to logic '1' inside the device. XRES is available as a dedicated pin.
- Watchdog timer (WDT) reset to reset the device if the firmware execution fails to service the watchdog timer within a specified timeout period.
- Software-initiated reset to reset the device on demand using firmware.
- Logic-protection fault can trigger an interrupt to a fault handler or reset the device if unauthorized operating conditions occur; for example, reaching a debug breakpoint while executing privileged code.
- Hibernate wakeup reset to bring the device out of the Hibernate low-power mode.

Reset events are asynchronous and guarantee reversion to a known state. Some of the reset sources are recorded in a register, which is retained through reset and allows software to determine the cause of the reset.

BLE Radio and Subsystem

PSoC 63 with BLE incorporates a Bluetooth Smart subsystem that contains the Physical Layer (PHY) and Link Layer (LL) engines with an embedded security engine. The physical layer consists of the digital PHY and the RF transceiver that transmits and receives GFSK packets at 2 Mbps over a 2.4-GHz ISM band, which is compliant with Bluetooth Smart Bluetooth Specification 5.0. The baseband controller is a composite hardware and firmware implementation that supports both master and slave modes. Key protocol elements, such as HCl and link control, are implemented in firmware. Time-critical functional blocks, such as encryption, CRC, data whitening, and access code correlation, are implemented in hardware (in the LL engine).

The RF transceiver contains an integrated balun, which provides a single-ended RF port pin to drive a 50- Ω antenna via a matching/filtering network. In the receive direction, this block converts the RF signal from the antenna to a digital bit stream after performing GFSK demodulation. In the transmit direction, this block performs GFSK modulation and then converts a digital baseband signal to a radio frequency before transmitting it to air through the antenna.

Key features of BLESS are as follows:

- Master and slave single-mode protocol stack with logical link control and adaptation protocol (L2CAP), attribute (ATT), and security manager (SM) protocols
- API access to generic attribute profile (GATT), generic access profile (GAP), and L2CAP
- L2CAP connection-oriented channel (Bluetooth 4.1 feature)
- GAP features
 - ☐ Broadcaster, Observer, Peripheral, and Central roles
- ☐ Security mode 1: Level 1, 2, and 3
- User-defined advertising data
- Multiple bond support
- GATT features
 - □ GATT client and server
 - Supports GATT sub-procedures
 - 32-bit universally unique identifier (UUID) (Bluetooth 4.1 feature)
- Security Manager (SM)
 - Pairing methods: Just works, Passkey Entry, and Out of Band
 - □ LE Secure Connection Pairing model
 - Authenticated man-in-the-middle (MITM) protection and data signing
- Link Layer (LL)
 - ☐ Master and Slave roles
 - □ 128-bit AES engine
 - $\ensuremath{\square}$ Low-duty cycle advertising
 - □ LE Ping
- Supports all SIG-adopted BLE profiles
- Power levels for Adv (1.28s, 31 bytes, 0 dBm) and Con (300 ms, 0 byte, 0 dBm) are 42 µW and 70 µW respectively



Programmable Analog Subsystem

12-bit SAR ADC

The 12-bit, 1-Msps SAR ADC can operate at a maximum clock rate of 18 MHz and requires a minimum of 18 clocks at that frequency to do a 12-bit conversion. One of three internal reference voltages may be used for the ADC reference voltage. The references are, $V_{\rm DD},\,V_{\rm DD}/2,\,{\rm and}\,V_{\rm REF}$ (nominally 1.2 V and trimmed to $\pm 1\%$). An external reference may also be used, by either driving the VREF pin or routing an external reference to GPIO pin P9.7. These reference options allow ratio-metric readings or absolute readings at the accuracy of the reference used. The input range of the ADC is the full supply voltage between $V_{\rm SS}$ and $V_{\rm DDIOA}/V_{\rm DDIOA}$. The SAR ADC may be configured with a mix of single ended and differential signals in the same configuration.

The SAR ADC's sample-and-hold (S/H) aperture is programmable to allow sufficient time for signals with a high impedance to settle sufficiently, if required. System performance will be 65 dB for true 12-bit precision provided appropriate references are used and system noise levels permit it. To improve performance in noisy conditions, an external bypass capacitor for the internal reference amplifier (through the fixed "VREF" pin), may be added.

The SAR is connected to a fixed set of pins through an input sequencer. The sequencer cycles through the selected channels autonomously (sequencer scan) and does so with zero switching overhead (that is, the aggregate sampling bandwidth is equal to 1 Msps whether it is for a single channel or distributed over several channels). The result of each channel is buffered, so that an interrupt may be triggered only when a full scan of all channels is complete. Also, a pair of range registers can be set to detect and cause an interrupt if an input exceeds a minimum and/or maximum value. This allows fast detection of out-of-range values without having to wait for a sequencer scan to be completed and the CPU to read the values and check for out-of-range values in software. The SAR can also be connected, under firmware control, to most other GPIO pins via the Analog Multiplexer Bus (AMUXBUS). The SAR is not available in Deep Sleep and Hibernate modes as it requires a high -speed clock (up to 18 MHz). The SAR operating range is 1.71 to 3.6 V.

Temperature Sensor

An on-chip temperature sensor is part of the SAR sequencer block and may be scanned by the SAR ADC. It consists of a diode, which is biased by a current source that can be disabled to save power. The temperature sensor may be connected directly to the SAR ADC as one of the measurement channels. The ADC digitizes the temperature sensor's output and a Cypress-supplied software function may be used to convert the reading to temperature which includes calibration and linearization.

12-bit Digital-Analog Converter

There is a 12-bit voltage mode DAC on the chip, which can settle in less than 5 μ s. The DAC may be driven by the DMA controllers to generate user-defined waveforms. The DAC output from the chip can either be the resistive ladder output (highly linear near ground) or a buffered output.

Continuous Time Block (CTBm) with Two Opamps

This block consists of two opamps, which have their inputs and outputs connected to fixed pins and have three power modes and a comparator mode. The outputs of these opamps can be used as buffers for the SAR inputs. The non-inverting inputs of these opamps can be connected to either of two pins, thus allowing independent sensors to be used at different times. The pin selection can be made via firmware. The opamps can be set to one of the four power levels; the lowest level allowing operation in Deep Sleep mode in order to preserve lower performance Continuous-Time functionality in Deep Sleep mode. The DAC output can be buffered through an opamp.

Low-Power Comparators

Two low-power comparators are provided, which can operate in all power modes. This allows other analog system resources to be disabled while retaining the ability to monitor external voltage levels during Deep Sleep and Hibernate modes. The comparator outputs are normally synchronized to avoid metastability unless operating in an asynchronous power mode (Hibernate) where the system wake-up circuit is activated by a comparator-switch event.






Figure 5. Analog Subsystem

Programmable Digital

Smart I/O

Smart I/O™ is a programmable logic fabric that enables Boolean operations on signals traveling from device internal resources to the GPIO pins or on signals traveling into the device from external sources. The Smart I/O block sits between the GPIO pins and the high-speed I/O matrix (HSIOM) and is dedicated to a single port.

There are two Smart I/O blocks: one on Port 8 and one on Port 9. When the Smart I/O is not enabled, all signals on Port 8 and Port 9 bypass the Smart I/O hardware.

Smart I/O supports:

- Deep Sleep operation
- Boolean operations without CPU intervention
- Asynchronous or synchronous (clocked) operation

Each Smart I/O block contains a data unit (DU) and eight look up tables (LUTs).

The DU:

- Performs unique functions based on a selectable opcode.
- Can source input signals from internal resources, the GPIO port, or a value in the DU register.

Each LUT:

- Has three selectable input sources. The input signals may be sourced from another LUT, an internal resource, an external signal from a GPIO pin, or from the DU.
- Acts as a programmable Boolean logic table.
- Can be synchronous or asynchronous.

Universal Digital Blocks (UDBs) and Port Interfaces

PSoC 63 has 12 UDBs; the UDB array also provides a switched Digital System Interconnect (DSI) fabric that allows signals from peripherals and ports to be routed to and through the UDBs for communication and control.

Fixed-Function Digital

Timer/Counter/PWM Block

- The TCPWM supports the following operational modes:
 - ☐ Timer-counter with compare
 - □ Timer-counter with capture
 - □ Quadrature decoding
 - □ Pulse width modulation (PWM)
 - □ Pseudo-random PWM
 - □ PWM with dead time
- Up, down, and up/down counting modes.
- Clock prescaling (division by 1, 2, 4, ... 64, 128)

Document Number: 002-18787 Rev. *H



- Double buffering of compare/capture and period values
- Underflow, overflow, and capture/compare output signals
- Supports interrupt on:
 - ☐ Terminal count Depends on the mode; typically occurs on overflow or underflow
 - ☐ Capture/compare The count is captured to the capture register or the counter value equals the value in the compare
- Complementary output for PWMs
- Selectable start, reload, stop, count, and capture event signals for each TCPWM with rising edge, falling edge, both edges, and level trigger options. The TCPWM has a Kill input to force outputs to a predetermined state; for example, this is used in motor-drive systems when an overcurrent state is indicated and the PWMs driving the FETs need to be shut off immediately with no time for software intervention.

In this device there are:

- Eight 32-bit TCPWMS
- Twenty-four 16-bit TCPWMs

Serial Communication Blocks (SCB)

PSoC 63 with BLE has 9 SCBs:

- Eight can implement either I²C, UART, or SPI.
- One SCB can operate in Deep Sleep with an external clock, this SCB can be either SPI slave or I²C slave.

I²C Mode: The SCB can implement a full multi-master and slave interface (it is capable of multimaster arbitration). This block can operate at speeds of up to 1 Mbps (Fast Mode Plus). It also supports Ezi2C that creates a mailbox address range in the memory of PSoC 63 and effectively reduces the I2C communication to reading from and writing to an array in the memory. The SCB supports a 256-byte FIFO for receive and transmit.

The I²C peripheral is compatible with I²C standard-mode, Fast Mode, and Fast Mode Plus devices as defined in the NXP I²C-bus specification and user manual (UM10204). The I²C bus I/O is implemented with GPIO in open-drain modes.

UART Mode: This is a full-feature UART operating at up to 8 Mbps. It supports automotive single-wire interface (LIN), infrared interface (IrDA), and SmartCard (ISO7816) protocols, all of which are minor variants of the basic UART protocol. In addition, it supports the 9-bit multiprocessor mode that allows the addressing of peripherals connected over common RX and TX lines. Common UART functions such as parity error, break detect, and frame error are supported. A 256-byte FIFO allows much greater CPU service latencies to be tolerated.

SPI Mode: The SPI mode supports full Motorola SPI, TI Secure Simple Pairing (SSP) (essentially adds a start pulse that is used to synchronize SPI Codecs), and National Microwire (half-duplex form of SPI). The SPI block supports an EzSPI mode in which the data interchange is reduced to reading and writing an array in memory. The SPI interface will operate with a 25-MHz SPI Clock.

USB Full-Speed Dual Role Host and Device Interface

PSoC 63 with BLE incorporates a dual-role USB Host and Device interface. The device can have up to eight endpoints. A 512 byte SRAM buffer is provided and DMA is supported.

Datasheet

QSPI InterfaceSerial Memory Interface (SMIF)

A serial memory interface is provided, running at up to 80 MHz. It supports single, dual, quad, dual-quad and octal SPI configurations, and supports up to four external memory devices. It supports two modes of operation:

- Memory-mapped I/O (MMIO), a command mode interface that provides data access via the SMIF registers and FIFOs
- Execute in Place (XIP), in which AHB reads and writes are directly translated to SPI read and write transfers.

In XIP mode, the external memory is mapped into the PSoC 6 MCU internal address space, enabling code execution directly from the external memory. To improve performance, a 4-KB cache is included. XIP mode also supports AES-128 on-the-fly encryption and decryption, enabling secure storage and access of code and data in the external memory.

PSoC 63 with BLE has up to 78 GPIOs. The GPIO block implements the following:

- Eight drive strength modes:
 - Analog input mode (input and output buffers disabled)
 - □ Input only
 - □ Weak pull-up with strong pull-down
 - ☐ Strong pull-up with weak pull-down
 - ☐ Open drain with strong pull-down
 - Open drain with strong pull-up
 - ☐ Strong pull-up with strong pull-down
 - Weak pull-up with weak pull-down
- Input threshold select (CMOS or LVTTL)
- Hold mode for latching previous state (used for retaining the I/O state in Deep Sleep and Hibernate modes)
- Selectable slew rates for dV/dt-related noise control to improve **EMI**

The pins are organized in logical entities called ports, which are up to 8-pin in width. During power-on and reset, the pins are forced to the disable state so as not to crowbar any inputs and/or cause excess turn-on current. A multiplexing network known as the high-speed I/O matrix (HSIOM) is used to multiplex between various peripheral and analog signals that may connect to an I/O pin. Data output and pin state registers store, respectively, the values to be driven on the pins and the states of the pins

Every I/O pin can generate an interrupt if so enabled; each I/O port has an interrupt request (IRQ) and interrupt service routine (ISR) vector associated with it. Six GPIO pins are capable of overvoltage-tolerant (OVT) operation where the input voltage may be higher than VDD. (These OVT pins are commonly used for the I²C functionality to allow powering the chip OFF while maintaining a physical connection to an operating I²C bus without affecting its functionality).



PSoC[®] 6 MCU: PSoC 63 with BLE Datasheet

GPIO pins can be ganged to source or sink higher values of current. GPIO pins, including OVT pins, may not be pulled up higher than 3.6 V.

Special-Function Peripherals

Audio Subsystem

This subsystem consists of the following hardware blocks:

- One Inter-IC Sound (I²S) interfaces
- Two pulse-density modulation to pulse-code modulation decoder channels

The I²S interface implements two independent hardware FIFO buffers – TX and RX, which can operate in master or slave mode. The following features are supported:

- Multiple data formats I²S, left-justified, Time Division Multiplexed (TDM) mode A, and TDM mode B
- Programmable channel/word lengths 8/16/18/20/24/32 bits
- Internal/external clock operation. Up to 192 ksps
- Interrupt mask events trigger, not empty, full, overflow, underflow, watchdog
- Configurable FIFO trigger level with DMA support

The I²S interface is commonly used to connect with audio codecs, simple DACs, and digital microphones.

The PDM-to-PCM decoder implements a single hardware RX FIFO that decodes a stereo or mono 1-bit PDM input stream to PCM data output. The following features are supported:

■ Programmable data output word length – 16/18/20/24 bits

- Programmable gain amplifier (PGA) for volume control from -12 dB to +10.5 dB in 1.5 dB steps
- Configurable PDM clock generation. Range from 384 kHz to 3.072 MHz
- Droop correction and configurable decimation rate for sampling; up to 48 ksps
- Programmable high-pass filter gain
- Interrupt mask events not empty, overflow, trigger, underflow
- Configurable FIFO trigger level with DMA support

The PDM-to-PCM decoder is commonly used to connect to digital PDM microphones. Up to two microphones can be connected to the same PDM Data line.

CapSense Subsystem

CapSense is supported in PSoC 6 MCU through a CapSense sigma-delta (CSD) hardware block. It is designed for high-sensitivity self-capacitance and mutual-capacitance measurements, and is specifically built for user interface solutions.

In addition to CapSense, the CSD hardware block supports three general-purpose functions. These are available when CapSense is not being used. Alternatively, two or more functions can be time-multiplexed in an application under firmware control. The four functions supported by the CSD hardware block are:

- CapSense
- 10-bit ADC
- Programmable current sources (IDAC)
- Comparator

Document Number: 002-18787 Rev. *H Page 16 of 82



CapSense

Capacitive touch sensors are designed for user interfaces that rely on human body capacitance to detect the presence of a finger on or near a sensor. Cypress CapSense solutions bring elegant, reliable, and simple capacitive touch sensing functions to applications including IoT, industrial, automotive, and home appliances.

The Cypress-proprietary CapSense technology offers the following features:

- Best-in-class signal-to-noise ratio (SNR) and robust sensing under harsh and noisy conditions
- Self-capacitance (CSD) and mutual-capacitance (CSX) sensing methods
- Support for various widgets, including buttons, matrix buttons, sliders, touchpads, and proximity sensors
- High-performance sensing across a variety of materials
- Best-in-class liquid tolerance
- SmartSense[™] auto-tuning technology that helps avoid complex manual tuning processes
- Superior immunity against external noise
- Spread-spectrum clocks for low radiated emissions
- Gesture and built-in self-test libraries
- Ultra-low power consumption
- An integrated graphical CapSense tuner for real-time tuning, testing, and debugging

ADC

The CapSense subsystem slope ADC offers the following features:

- Selectable 8- or 10-bit resolution
- Selectable input range: GND to V_{REF} and GND to V_{DDA} on any GPIO input
- Measurement of V_{DDA} against an internal reference without the use of GPIO or external components

IDAC

The CSD block has two programmable current sources, which offer the following features:

- 7-bit resolution
- Sink and source current modes
- A current source programmable from 37.5 nA to 609 µA
- Two IDACs that can be used in parallel to form one 8-bit IDAC

Comparator

The CapSense subsystem comparator operates in the System Low Power and Ultra-Low Power modes. The inverting input is connected to an internal programmable reference voltage and the non-inverting input can be connected to any GPIO via the AMUXBUS.

CapSense Hardware Subsystem

Figure 6 shows the high-level hardware overview of the CapSense subsystem, which includes a delta sigma converter, internal clock dividers, a shield driver, and two programmable current sources.

The inputs are managed through analog multiplexed buses (AMUXBUS A/B). The input and output of all functions offered by the CSD block can be provided on any GPIO or on a group of GPIOs under software control, with the exception of the comparator output and external capacitors that use dedicated GPIOs.

Self-capacitance is supported by the CSD block using AMUXBUS A, an external modulator capacitor, and a GPIO for each sensor. There is a shield electrode (optional) for self-capacitance sensing. This is supported using AMUXBUS B and an optional external shield tank capacitor (to increase the drive capability of the shield driver) should this be required. Mutual-capacitance is supported by the CSD block using AMUXBUS A, two external integrated capacitors, and a GPIO for transmit and receive electrodes.

The ADC does not require an external component. Any GPIO that can be connected to AMUXBUS A can be an input to the ADC under software control. The ADC can accept V_{DDA} as an input without needing GPIOs (for applications such as battery voltage measurement).

The two programmable current sources (IDACs) in general-purpose mode can be connected to AMUXBUS A or B. They can therefore connect to any GPIO pin. The comparator resides in the delta-sigma converter. The inverting input is connected to VREF, with output on dedicated GPIO. The non-inverting input and output is accessible on any GPIO using AMUXBUS.

The CSD block can operate in active and sleep CPU power modes, and seamlessly transition between LP and ULP system modes. It can be powered down in Deep Sleep and Hibernate modes. Upon wakeup from Hibernate mode, the CSD block requires re-initialization. However, operation can be resumed without re-initialization upon exit from Deep Sleep mode, under firmware control.






Figure 6. CapSense Hardware Subsystem

Figure 7 shows the high-level software overview. Cypress provides a middleware library for each function to enable quick integration. User applications interact only with middleware to implement functions of the CSD block. The middleware interacts with underlying drivers to access hardware as necessary. The CSD driver facilitates time-multiplexing of the CSD hardware if more than one piece of CSD-related middleware is present in a project. It prevents access conflicts in this case.

CapSense middleware has configurator software to enable fast configuration and incorporating it into middleware. It also has a tuner for performance evaluation and real-time tuning of the system. Both can be launched from the ModusToolbox IDE or in standalone mode. The tuner requires the EZ12C communication interface in the application to enable real-time tuning capability. The tuner can update configuration parameters directly in the device as well as in the configurator.



CapSense and ADC middleware use the CSD interrupt to implement non-blocking sensing and A-to-D conversion. Therefore, interrupt service routines are a defined part of the middleware, which must be initialized by the application. For dual-CPU devices, middleware and drivers can operate on either CPU. Cypress recommends using the middleware only in one

CPU. If both CPUs must access the CSD driver, memory access should be managed in the application.

Refer to AN85951: PSoC 4 and PSoC 6 MCU CapSense Design Guide for more details on CSX sensing, CSD sensing, shield electrode usage and its benefits, and capacitive system design guidelines. Refer to the middleware API reference guide available in the PSoC 6 SDK for more detail on middleware.




Figure 7. CapSense Software/Firmware Subsystem

Document Number: 002-18787 Rev. *H



Pinouts

Table 4. Pinouts for 104-MCSP and 116-BGA Packages

104-MC	SP-BLE	116-BG	A-BLE
Pin	Name	Pin	Name
C7	VCCD	A2	VCCD
C6	VDDD	B1	VDDD
C9	VBACKUP	C1	VBACKUP
D8	P0.0	C2	P0.0
E6	P0.1	D3	P0.1
D9	P0.2	E4	P0.2
E7	P0.3	E3	P0.3
E8	P0.4	F3	P0.4
E9	P0.5	D2	P0.5
E5	XRES	E2	XRES
F5	P1.0	G3	P1.0
F6	P1.1	F2	P1.1
		J5	P1.2
F9	P1.3	J4	P1.3
F8	P1.4	J3	P1.4
F7	P1.5	J2	P1.5
G9	VDD_NS	H3	VDD_NS
G8	VIND1	F1	VIND1
H8	VIND2	G1	VIND2
J8	VBUCK1	G2	VBUCK1
H9	VRF	H1	VRF
L9	VDDR1	L2	VDDR1
N9	VSSR	J1, K2, K3, K4, K5, L1, L3, L4, L5, M3, M8	VSSR
M9	ANT	K1	ANT
M9	ANT	K1	ANT
K2	P6.1	J8	P6.1
M2	P6.2	L9	P6.2
L1	P6.3	K9	P6.3

104-MCSP-BLE		116-BGA-BLE		
Pin	Name	Pin	Name	
N9	VSSR	J1, K2, K3, K4, K5, L1, L3, L4, L5, M3, M8	VSSR	
P9	VDDR2	M1	VDDR2	
P6,P7	VSSR	J1, K2, K3, K4, K5, L1, L3, L4, L5, M3, M8	VSSR	
P8	VDDR3	M2	VDDR3	
P1	VSS	J1, K2, K3, K4, K5, L1, L3, L4, L5, M3, M8	VSSR	
M5	XI	M4	ΧI	
P5	XO	M5	XO	
M3	VSSR	J1, K2, K3, K4, K5, L1, L3, L4, L5, M3, M8	VSSR	
M4	DVDD	M6	DVDD	
P1	VSS	J1, K2, K3, K4, K5, L1, L3, L4, L5, M3, M8	VSSR	
P4	VDCDC	M7	VDCDC	
P2	NC			
P3	VSSR	J1, K2, K3, K4, K5, L1, L3, L4, L5, M3, M8	VSSR	
L2	VDDR_HVL	L7	VDDR_HVL	
J7	P5.0	L6	P5.0	
J5	P5.1	K6	P5.1	
J6	P5.2	J6	P5.2	
H7	P5.3	K7	P5.3	
H6	P5.4	J7	P5.4	
J4	P5.5	L8	P5.5	
K3	P5.6	M9	P5.6	
K4	P5.7			
L2	VDDR_HVL	L7	VDDR_HVL	
L2	VDDR_HVL	L7	VDDR_HVL	
J3	P6.0	K8	P6.0	
B2	P10.1	A8	P10.1	
C3	P10.2	F6	P10.2	
E4	P10.3	E6	P10.3	

Document Number: 002-18787 Rev. *H Page 20 of 82



Table 4. Pinouts for 104-MCSP and 116-BGA Packages (continued)

104-M	CSP-BLE	116-B	GA-BLE	104-MCS	P-BLE
Pin	Name	Pin	Name	Pin	Name
J2	P6.4	J9	P6.4	A2	P10.4
K1	P6.5	M10	P6.5	A3	P10.
N2	P6.6	L10	P6.6	D5	P10.6
M1	P6.7	K10	P6.7	В3	P10.7
N1	P7.0	J10	P7.0	C4	P11.0
G6	P7.1	H10	P7.1	C5	P11.
H4	P7.2	H8	P7.2	D6	P11.2
G5	P7.3	H7	P7.3		
Н3	P7.4	H6	P7.4	A1	VDD/
H2	P7.5	G9	P7.5	A1	VDD/
G3	P7.6	G8	P7.6	C2	P10.0
G2	P7.7	G7	P7.7	B4	P11.3
D1	VDDIO1	G10	VDDIO1	A4	P11.4
G4	P8.0	F10	P8.0	B5	P11.
G1	P8.1	F9	P8.1	A5	P11.6
F3	P8.2	F8	P8.2	A6	P11.7
F2	P8.3	F7	P8.3	B6	VDDIC
F1	P8.4	G6	P8.4	D7, D4, F4, G7	VSS
E3	P8.5	E9	P8.5	B7	P12.0
E1	P8.6	E8	P8.6	A7	P12.
E2	P8.7	E7	P8.7	B8	P12.2
A1	VDDA	A9	VDDA	A8	P12.3
D2	P9.0	D10	P9.0	C8	P12.4
C1	P9.1	D9	P9.1		
D3	P9.2	D8	P9.2		
B1	P9.3	D7	P9.3		
		C10	P9.4	A9	P13.0
		C9	P9.5	B9	P13.
		C8	P9.6		
		C7	P9.7		

104-MCSP-BLE		116-BGA-BLE		
Pin	Name	Pin	Name	
A2	P10.4	D6	P10.4	
A3	P10.5	B7	P10.5	
D5	P10.6	A7	P10.6	
В3	P10.7			
C4	P11.0	F5	P11.0	
C5	P11.1	E5	P11.1	
D6	P11.2	D5	P11.2	
		B10	VREF	
A1	VDDA	A9	VDDA	
A1	VDDA	A9	VDDA	
C2	P10.0	B8	P10.0	
B4	P11.3	C6	P11.3	
A4	P11.4	B6	P11.4	
B5	P11.5	A6	P11.5	
A5	P11.6	B5	P11.6	
A6	P11.7	A5	P11.7	
В6	VDDIO0	B3	VDDIO0	
D7, D4, F4, G7	VSS	B2, B9, H2, H9, D1	VSS	
В7	P12.0	A4	P12.0	
A7	P12.1	B4	P12.1	
B8	P12.2	C4	P12.2	
A8	P12.3	A3	P12.3	
C8	P12.4	C5	P12.4	
		D4	P12.5	
		G5	P12.6	
		H5	P12.7	
A9	P13.0	H4	P13.0	
В9	P13.1	G4	P13.1	
		F4	P13.6	
		C3	P13.7	

Note: Balls H5 and J9 are No-Connects (NC) in the 104-MCSP package.

Document Number: 002-18787 Rev. *H Page 21 of 82



Table 5. Pinouts for 104-MCSP with USB

104-M-CSP-BLE-USB		
Pin	Name	
C7	VCCD	
C6	VDDD	
C9	VBACKUP	
D8	P0.0	
E6	P0.1	
D9	P0.2	
E7	P0.3	
E8	P0.4	
E9	P0.5	
E5	XRES	
F5	P1.0	
F6	P1.1	
F8	P1.4	
F7	P1.5	
G9	VDD_NS	
G8	VIND1	
H8	VIND2	
F9	VBUCK1	
H9	VRF	
H7	VDDUSB	
J9	USBDM	
J8	USBDP	
N9	VSSR	
L9	VDDR1	
M9	ANT	
P9	VDDR2	
P6, P7	VSSR	
P8	VDDR3	
P1	VSS	
M5	XI	
P5	XO	
M4	DVDD	
M3	VSSR	
P1	VSS	
P4	VDCDC	
P3	VSSR	
L2	VDDR_HVL	

104-M-CSP-BLE-USB		
Pin	Name	
J5	P5.1	
J6	P5.2	
H6	P5.3	
H5	P5.4	
J4	P5.5	
K3	P5.6	
K4	P5.7	
L2	VDDR_HVL	
J3	P6.0	
K2	P6.1	
M2	P6.2	
L1	P6.3	
J2	P6.4	
K1	P6.5	
N2	P6.6	
M1	P6.7	
N1	P7.0	
G6	P7.1	
H4	P7.2	
G5	P7.3	
H3	P7.4	
H2	P7.5	
G3	P7.6	
G2	P7.7	
D1	VDDIO1	
G4	P8.0	
G1	P8.1	
F3	P8.2	
F2	P8.3	
F1	P8.4	
E3	P8.5	
E1	P8.6	
E2	P8.7	
A1	VDDA	
D2	P9.0	
C1	P9.1	
D3	P9.2	

Document Number: 002-18787 Rev. *H Page 22 of 82



Table 5. Pinouts for 104-MCSP with USB (continued)

104-M-CSP-BLE-USB		
Pin	Name	
J7	P5.0	
A1	VDDA	
C2	P10.0	
B2	P10.1	
C3	P10.2	
E4	P10.3	
A2	P10.4	
A3	P10.5	
D5	P10.6	
B3	P10.7	
C4	P11.0	
C5	P11.1	
D6	P11.2	
B4	P11.3	
A4	P11.4	

104-M-CSF	P-BLE-USB
Pin	Name
B1	P9.3
B5	P11.5
A5	P11.6
A6	P11.7
B6	VDDIO0
D7, D4, F4, G7	VSS
B7	P12.0
A7	P12.1
B8	P12.2
A8	P12.3
C8	P12.4
A9	P13.0
В9	P13.1
P2	NC

Table 6. Pinouts for 124-BGA-SIP Package

	124	I-BGA-SIP
Pin	Name	
B13	VCCD	
A13	VDDD	
D10, C11, D4, K4, K10, M12	VSS	
A10	VBACKUP	
C9	P0.0	
B9	P0.1	
A9	P0.2	
C8	P0.3	
B8	P0.4	
C7	P0.5	
C7	P0.5	
A8	XRES	
B7	P1.0	
A7	P1.1	
C6	P1.2	

-317	
Pin	Name
E2	VDDR2
D2	VDDR3
F1	XI
E1	XO
F2	DVDD
F3	VDCDC
G3	VDDR_HVL
G1	P5.0
H3	P5.1
H2	P5.2
H1	P5.3
J3	P5.4
J2	P5.5
J1	P5.6
K1	P5.7
-	

Document Number: 002-18787 Rev. *H Page 23 of 82



Table 6. Pinouts for 124-BGA-SIP Package (continued)

	124-	BGA-SIP	
Pin	Name	Pin	Name
B6	P1.3	G3	VDDR_HVL
A6	P1.4	K2	P6.0
C5	P1.5	К3	P6.1
A5	VDD_NS	L3	P6.2
B5	VIND1	L2	P6.3
B4	VIND2	L1	P6.4
C4	VBUCK1	M2	P6.5
A4	VRF	M1	P6.6
A2	VDDUSB	N2	P6.7
A3	USBDM	N3	P7.0
B3	USBDP	M3	P7.1
C2	VDDR1	N4	P7.2
B1,B2,C3,D1,E3,G2,A1	VSSR	N1	P7.3
C1	ANT	L4	P7.4
N5	P7.5	J13	P10.7
M5	P7.6	J12	P11.0
L5	P7.7	J11	P11.1
M4	VDDIO1	H13	P11.2
N6	P8.0	H12	P11.3
M6	P8.1	H11	P11.4
L6	P8.2	G13	P11.5
N7	P8.3	G12	P11.6
M7	P8.4	G11	P11.7
L7	P8.5	D11	VDDIO0
N8	P8.6	F13	P12.0
M8	P8.7	F12	P12.1
L9	P9.0	F11	P12.2
M9	P9.1	E13	P12.3
N9	P9.2	E12	P12.4
L8	P9.3	E11	P12.5

Document Number: 002-18787 Rev. *H Page 24 of 82



Table 6. Pinouts for 124-BGA-SIP Package (continued)

	124-
Pin	Name
N10	P9.4
M10	P9.5
L10	P9.6
N11	P9.7
N12	VREF
N13	VDDIOA
M13	VDDA
M11	P10.0
L13	P10.1
L12	P10.2
L11	P10.3
K13	P10.4
K12	P10.5
K11	P10.6
1	

Pin	Name
D13	P12.6
D12	P12.7
A12	P13.0
C13	P13.1
C12	P13.2
B12	P13.3
B11	P13.4
A11	P13.5
C10	P13.6
B10	P13.7
D3	NC
	Pin D13 D12 A12 C13 C12 B12 B11 A11 C10 B10

Table 7. Pinouts for 68-QFN Package

68-QF	N-BLE
Pin	Name
67	VCCD
68	VDDD
1	VBACKUP
2	P0.0
3	P0.1
4	P0.2
5	P0.3
6	P0.4
7	P0.5
8	XRES
9	VDD_NS
10	VIND1

68-QF	N-BLE
Pin	Name
12	VCCBUCK1
13	VCCBUCK2
14	NC
15	VDDR1
16	GANT1
17	ANT
18	GANT2
19	VDDR2
20	VDDR3
21	XI
22	ХО
23	DVDD

Document Number: 002-18787 Rev. *H Page 25 of 82



Table 7. Pinouts for 68-QFN Package (continued)

68-QFN-BLE									
Pin	Name								
11	VIND2								
25	VDDR_HVL								
26	P6.0								
27	NC								
28	P6.1								
29	P6.2								
30	P6.3								
31	P6.4								
32	P6.5								
33	P6.6								
34	P6.7								
35	P7.0								
36	P7.1								
37	P7.2								
38	P7.3								
39	P7.4								
40	P7.5								
41	P7.6								
42	P7.7								
43	VDDIO_1								
44	P8.0								
45	P8.1								
46	P8.2								

68-QFN-BLE									
Pin	Name								
24	VDCDC								
47	VDDA								
48	P9.0								
49	P9.1								
50	P9.2								
51	P9.3								
52	VREF								
53	VDDIO_A								
54	P10.0								
55	P10.1								
56	P11.0								
57	P11.1								
58	P11.2								
59	P11.3								
60	P11.4								
61	P11.5								
62	P11.6								
63	P11.7								
64	VDDIO_0								
65	P12.6								
66	P12.7								
14	NC								
27	NC								

The correspondence of power supplies to ports by package type is as follows:

■ P0: VBACKUP ■ P9, P10: VDDA

■ P1: VDDD. Port 1 Pins are Over-Voltage Tolerant (OVT). ■ P11, P12, P13: VDDIO0

■ P5, P6, P7, P8: VDDIO1

Document Number: 002-18787 Rev. *H Page 26 of 82



Each Port Pin has multiple alternate functions. These are defined in Table 8.

Table 8. Multiple Alternate Functions^[1]

Port/ Pin	ACT #0	ACT #1	DS #2	ACT #4	ACT #5	ACT #6	ACT #7	ACT #8	ACT #9	ACT #10	ACT #12	ACT #13	ACT #14	ACT #15	DS #4	DS #5	DS #6
P0.0	tcpwm[0].l ine[0]:0	tcpwm[1].line [0]:0		srss.ext _clk:0				scb[0].spi _select1:0			peri.tr_io_i nput[0]:0						
P0.1	tcpwm[0].l ine_comp l[0]:0	tcpwm[1].line _compl[0]:0						scb[0].spi _select2:0			peri.tr_io_i nput[1]:0					cpuss.swj_ trstn	
P0.2	tcpwm[0].l ine[1]:0	tcpwm[1].line [1]:0				scb[0].ua rt_rx:0	scb[0].i2 c_scl:0	scb[0].spi _mosi:0									
P0.3	tcpwm[0].l ine_comp l[1]:0	tcpwm[1].line _compl[1]:0				scb[0].ua rt_tx:0	scb[0].i2 c_sda:0	scb[0].spi _miso:0									
P0.4	tcpwm[0].l ine[2]:0	tcpwm[1].line [2]:0				scb[0].ua rt_rts:0		scb[0].spi _clk:0				peri.tr_io_ output[0]:2					
P0.5	tcpwm[0].l ine_comp l[2]:0	tcpwm[1].line _compl[2]:0		srss.ext _clk:1		scb[0].ua rt_cts:0		scb[0].spi _select0:0				peri.tr_io_ output[1]:2					
P1.0	tcpwm[0].l ine[3]:0	tcpwm[1].line [3]:0				scb[7].ua rt_rx:0	scb[7].i2 c_scl:0	scb[7].spi _mosi:0			peri.tr_io_i nput[2]:0						
P1.1	tcpwm[0].l ine_comp l[3]:0	tcpwm[1].line _compl[3]:0				scb[7].ua rt_tx:0	scb[7].i2 c_sda:0	scb[7].spi _miso:0			peri.tr_io_i nput[3]:0						
P1.2	tcpwm[0].l ine[4]:4	tcpwm[1].line [12]:1				scb[7].ua rt_rts:0		scb[7].spi _clk:0									
P1.3	tcpwm[0].l ine_comp l[4]:4	tcpwm[1].line _compl[12]:1				scb[7].ua rt_cts:0		scb[7].spi _select0:0									
P1.4	tcpwm[0].l ine[5]:4	tcpwm[1].line [13]:1						scb[7].spi _select1:0									
P1.5	tcpwm[0].l ine_comp l[5]:4	tcpwm[1].line _compl[14]:1						scb[7].spi _select2:0									
P5.0	tcpwm[0].l ine[4]:0	tcpwm[1].line [4]:0				scb[5].ua rt_rx:0	scb[5].i2 c_scl:0	scb[5].spi _mosi:0		audioss.clk _i2s_if	peri.tr_io_i nput[10]:0						
P5.1	tcpwm[0].l ine_comp l[4]:0	tcpwm[1].line _compl[4]:0				scb[5].ua rt_tx:0	scb[5].i2 c_sda:0	scb[5].spi _miso:0		audioss.tx _sck	peri.tr_io_i nput[11]:0						
P5.2	tcpwm[0].l ine[5]:0	tcpwm[1].line [5]:0				scb[5].ua rt_rts:0		scb[5].spi _clk:0		audioss.tx _ws							

Note

For example, the name tcpwm[0].line_compl[3]:4 indicates that this is instance 0 of a tcpwm block, the signal is line_compl # 3 (complement of the line output) and this is the fourth occurrence (copy) of the signal. Signal copies are provided to allow flexibility in routing and to maximise utilisation of on-chip resources.

Document Number: 002-18787 Rev. *H

^{1.} The notation for a signal is of the form IPName[x].signal_name[u]:y.

IPName = Name of the block (such as tcpwm), x = Unique instance of the IP, Signal_name = Name of the signal, u = Signal number where there are more than one signals for a particular signal name, y = Designates copies of the signal name.



Table 8. Multiple Alternate Functions^[1] (continued)

Port/ Pin	ACT #0	ACT #1	DS #2	ACT #4	ACT #5	ACT #6	ACT #7	ACT #8	ACT #9	ACT #10	ACT #12	ACT #13	ACT #14	ACT #15	DS #4	DS #5	DS #6
P5.3	tcpwm[0].l ine_comp l[5]:0	tcpwm[1].line _compl[5]:0				scb[5].ua rt_cts:0		scb[5].spi _select0:0		audioss.tx _sdo							
P5.4	tcpwm[0].l ine[6]:0	tcpwm[1].line [6]:0						scb[5].spi _select1:0		audioss.rx _sck							
P5.5	tcpwm[0].l ine_comp l[6]:0	tcpwm[1].line _compl[6]:0						scb[5].spi _select2:0		audioss.rx _ws							
P5.6	tcpwm[0].l ine[7]:0	tcpwm[1].line [7]:0						scb[5].spi _select3:0		audioss.rx _sdi							
P5.7	tcpwm[0].l ine_comp I[7]:0	tcpwm[1].line _compl[7]:0						scb[3].spi _select3:0									
P6.0	tcpwm[0].l ine[0]:1	tcpwm[1].line [8]:0	scb[8].i2 c_scl:0			scb[3].ua rt_rx:0	scb[3].i2 c_scl:0	scb[3].spi _mosi:0				cpuss.fault _out[0]					scb[8].spi _mosi:0
P6.1	tcpwm[0].l ine_comp l[0]:1	tcpwm[1].line _compl[8]:0	scb[8].i2 c_sda:0			scb[3].ua rt_tx:0	scb[3].i2 c_sda:0	scb[3].spi _miso:0				cpuss.fault _out[1]					scb[8].spi _miso:0
P6.2	tcpwm[0].l ine[1]:1	tcpwm[1].line [9]:0				scb[3].ua rt_rts:0		scb[3].spi _clk:0									scb[8].spi _clk:0
P6.3	tcpwm[0].l ine_comp l[1]:1	tcpwm[1].line _compl[9]:0				scb[3].ua rt_cts:0		scb[3].spi _select0:0									scb[8].spi _select0:0
P6.4	tcpwm[0].l ine[2]:1	tcpwm[1].line [10]:0	scb[8].i2 c_scl:1			scb[6].ua rt_rx:2	scb[6].i2 c_scl:2	scb[6].spi _mosi:2			peri.tr_io_i nput[12]:0	peri.tr_io_ output[0]:1				cpuss.swj_ swo_tdo	scb[8].spi _mosi:1
P6.5	tcpwm[0].l ine_comp l[2]:1	tcpwm[1].line _compl[10]:0	scb[8].i2 c_sda:1			scb[6].ua rt_tx:2	scb[6].i2 c_sda:2	scb[6].spi _miso:2			peri.tr_io_i nput[13]:0	peri.tr_io_ output[1]:1				cpuss.swj_ swdoe_tdi	scb[8].spi _miso:1
P6.6	tcpwm[0].l ine[3]:1	tcpwm[1].line [11]:0				scb[6].ua rt_rts:2		scb[6].spi _clk:2								cpuss.swj_ swdio_tms	scb[8].spi _clk:1
P6.7	tcpwm[0].l ine_comp l[3]:1	tcpwm[1].line _compl[11]:0				scb[6].ua rt_cts:2		scb[6].spi _select0:2								cpuss.swj_ swclk_tclk	scb[8].spi _select0:1
P7.0	tcpwm[0].l ine[4]:1	tcpwm[1].line [12]:0				scb[4].ua rt_rx:1	scb[4].i2 c_scl:1	scb[4].spi _mosi:1			peri.tr_io_i nput[14]:0		cpuss.trace clock				
P7.1	tcpwm[0].l ine_comp l[4]:1	tcpwm[1].line _compl[12]:0				scb[4].ua rt_tx:1	scb[4].i2 c_sda:1	scb[4].spi _miso:1			peri.tr_io_i nput[15]:0						

Document Number: 002-18787 Rev. *H Page 28 of 82

^{1.} The notation for a signal is of the form IPName[x].signal_name[u]:y.

IPName = Name of the block (such as tcpwm), x = Unique instance of the IP, Signal_name = Name of the signal, u = Signal number where there are more than one signals for a particular signal name, y = Designates

For example, the name tcpwm[0].line_compl[3]:4 indicates that this is instance 0 of a tcpwm block, the signal is line_compl # 3 (complement of the line output) and this is the fourth occurrence (copy) of the signal. Signal copies are provided to allow flexibility in routing and to maximise utilisation of on-chip resources.



Table 8. Multiple Alternate Functions^[1] (continued)

Port/ Pin	ACT #0	ACT #1	DS #2	ACT #4	ACT #5	ACT #6	ACT #7	ACT #8	ACT #9	ACT #10	ACT #12	ACT #13	ACT #14	ACT #15	DS #4	DS #5	DS #6
P7.2	tcpwm[0].l ine[5]:1	tcpwm[1].line [13]:0				scb[4].ua rt_rts:1		scb[4].spi _clk:1									
P7.3	tcpwm[0].l ine_comp l[5]:1	tcpwm[1].line _compl[13]:0				scb[4].ua rt_cts:1		scb[4].spi _select0:1									
P7.4	tcpwm[0].l ine[6]:1	tcpwm[1].line [14]:0						scb[4].spi _select1:1					bless.ext_l- na_rx_ctl_out	cpuss.trac e_data[3]:2			
P7.5	tcpwm[0].l ine_comp l[6]:1	tcpwm[1].line _compl[14]:0						scb[4].spi _select2:1					bless.ext_pa_t x_ctl_out	cpuss.trac e_data[2]:2			
P7.6	tcpwm[0].l ine[7]:1	tcpwm[1].line [15]:0						scb[4].spi _select3:1					bless.ext_pa_l- na_chip_en_ou t	cpuss.trac e_data[1]:2			
P7.7	tcpwm[0].l ine_comp I[7]:1	tcpwm[1].line _compl[15]:0						scb[3].spi _select1:0	cpuss.clk_ fm_pump					cpuss.trac e_data[0]:2			
P8.0	tcpwm[0].l ine[0]:2	tcpwm[1].line [16]:0				scb[4].ua rt_rx:0	scb[4].i2 c_scl:0	scb[4].spi _mosi:0			peri.tr_io_i nput[16]:0						
P8.1	tcpwm[0].l ine_comp l[0]:2	tcpwm[1].line _compl[16]:0				scb[4].ua rt_tx:0	scb[4].i2 c_sda:0	scb[4].spi _miso:0			peri.tr_io_i nput[17]:0						
P8.2	tcpwm[0].l ine[1]:2	tcpwm[1].line [17]:0				scb[4].ua rt_rts:0		scb[4].spi _clk:0									
P8.3	tcpwm[0].l ine_comp l[1]:2	tcpwm[1].line _compl[17]:0				scb[4].ua rt_cts:0		scb[4].spi _select0:0									
P8.4	tcpwm[0].l ine[2]:2	tcpwm[1].line [18]:0						scb[4].spi _select1:0									
P8.5	tcpwm[0].l ine_comp l[2]:2	tcpwm[1].line _compl[18]:0						scb[4].spi _select2:0									
P8.6	tcpwm[0].l ine[3]:2	tcpwm[1].line [19]:0						scb[4].spi _select3:0									
P8.7	tcpwm[0].l ine_comp l[3]:2	tcpwm[1].line _compl[19]:0						scb[3].spi _select2:0									
P9.0	tcpwm[0].l ine[4]:2	tcpwm[1].line [20]:0				scb[2].ua rt_rx:0	scb[2].i2 c_scl:0	scb[2].spi _mosi:0			peri.tr_io_i nput[18]:0			cpuss.trac e_data[3]:0			

Document Number: 002-18787 Rev. *H Page 29 of 82

^{1.} The notation for a signal is of the form IPName[x].signal_name[u]:y.

IPName = Name of the block (such as tcpwm), x = Unique instance of the IP, Signal_name = Name of the signal, u = Signal number where there are more than one signals for a particular signal name, y = Designates

For example, the name tcpwm[0].line_compl[3]:4 indicates that this is instance 0 of a tcpwm block, the signal is line_compl # 3 (complement of the line output) and this is the fourth occurrence (copy) of the signal. Signal copies are provided to allow flexibility in routing and to maximise utilisation of on-chip resources.



Table 8. Multiple Alternate Functions^[1] (continued)

Port/ Pin	ACT #0	ACT #1	DS #2	ACT #4	ACT #5	ACT #6	ACT #7	ACT #8	ACT #9	ACT #10	ACT #12	ACT #13	ACT #14	ACT #15	DS #4	DS #5	DS #6
P9.1	tcpwm[0].l ine_comp l[4]:2	tcpwm[1].line _compl[20]:0				scb[2].ua rt_tx:0	scb[2].i2 c_sda:0	scb[2].spi _miso:0			peri.tr_io_i nput[19]:0			cpuss.trac e_data[2]:0			
P9.2	tcpwm[0].l ine[5]:2	tcpwm[1].line [21]:0				scb[2].ua rt_rts:0		scb[2].spi _clk:0		pass.dsi_ct b_cmp0:1				cpuss.trac e_data[1]:0			
P9.3	tcpwm[0].l ine_comp l[5]:2	tcpwm[1].line _compl[21]:0				scb[2].ua rt_cts:0		scb[2].spi _select0:0		pass.dsi_ct b_cmp1:1				cpuss.trac e_data[0]:0			
P9.4	tcpwm[0].l ine[7]:5	tcpwm[1].line [0]:2						scb[2].spi _select1:0									
P9.5	tcpwm[0].l ine_comp I[7]:5	tcpwm[1].line _compl[0]:2						scb[2].spi _select2:0									
P9.6	tcpwm[0].l ine[0]:6	tcpwm[1].line [1]:2						scb[2].spi _select3:0									
P9.7	tcpwm[0].l ine_comp l[0]:6	tcpwm[1].line _compl[1]:2															
P10.0	tcpwm[0].l ine[6]:2	tcpwm[1].line [22]:0				scb[1].ua rt_rx:1	scb[1].i2 c_scl:1	scb[1].spi _mosi:1			peri.tr_io_i nput[20]:0			cpuss.trac e_data[3]:1			
P10.1	tcpwm[0].l ine_comp l[6]:2	tcpwm[1].line _compl[22]:0				scb[1].ua rt_tx:1	scb[1].i2 c_sda:1	scb[1].spi _miso:1			peri.tr_io_i nput[21]:0			cpuss.trac e_data[2]:1			
P10.2	tcpwm[0].l ine[7]:2	tcpwm[1].line [23]:0				scb[1].ua rt_rts:1		scb[1].spi _clk:1						cpuss.trac e_data[1]:1			
P10.3	tcpwm[0].l ine_comp I[7]:2	tcpwm[1].line _compl[23]:0				scb[1].ua rt_cts:1		scb[1].spi _select0:1						cpuss.trac e_data[0]:1			
P10.4	tcpwm[0].I ine[0]:3	tcpwm[1].line [0]:1						scb[1].spi _select1:1	audioss.p dm_clk								
P10.5	tcpwm[0].I ine_comp I[0]:3	tcpwm[1].line _compl[0]:1						scb[1].spi _select2:1	audioss.p dm_data								
P10.6	tcpwm[0].I ine[1]:6	tcpwm[1].line [2]:2						scb[1].spi _select3:1									
P10.7	tcpwm[0].l ine_comp I[1]:6	tcpwm[1].line _compl[2]:2															

Document Number: 002-18787 Rev. *H Page 30 of 82

^{1.} The notation for a signal is of the form IPName[x].signal_name[u]:y.

IPName = Name of the block (such as tcpwm), x = Unique instance of the IP, Signal_name = Name of the signal, u = Signal number where there are more than one signals for a particular signal name, y = Designates

For example, the name tcpwm[0].line_compl[3]:4 indicates that this is instance 0 of a tcpwm block, the signal is line_compl # 3 (complement of the line output) and this is the fourth occurrence (copy) of the signal. Signal copies are provided to allow flexibility in routing and to maximise utilisation of on-chip resources.



Table 8. Multiple Alternate Functions^[1] (continued)

Port/ Pin	ACT #0	ACT #1	DS #2	ACT #4	ACT #5	ACT #6	ACT #7	ACT #8	ACT #9	ACT #10	ACT #12	ACT #13	ACT #14	ACT #15	DS #4	DS #5	DS #6
P11.0	tcpwm[0].l ine[1]:3	tcpwm[1].line [1]:1			smif.spi_ select2	scb[5].ua rt_rx:1	scb[5].i2 c_scl:1	scb[5].spi _mosi:1			peri.tr_io_i nput[22]:0						
P11.1	tcpwm[0].l ine_comp l[1]:3	tcpwm[1].line _compl[1]:1			smif.spi_ select1	scb[5].ua rt_tx:1	scb[5].i2 c_sda:1	scb[5].spi _miso:1			peri.tr_io_i nput[23]:0						
P11.2	tcpwm[0].l ine[2]:3	tcpwm[1].line [2]:1			smif.spi_ select0	scb[5].ua rt_rts:1		scb[5].spi _clk:1									
P11.3	tcpwm[0].l ine_comp l[2]:3	tcpwm[1].line _compl[2]:1			smif.spi_ data3	scb[5].ua rt_cts:1		scb[5].spi _select0:1				peri.tr_io_ output[0]:0					
P11.4	tcpwm[0].l ine[3]:3	tcpwm[1].line [3]:1			smif.spi_ data2			scb[5].spi _select1:1				peri.tr_io_ output[1]:0					
P11.5	tcpwm[0].l ine_comp l[3]:3	tcpwm[1].line _compl[3]:1			smif.spi_ data1			scb[5].spi _select2:1									
P11.6					smif.spi_ data0			scb[5].spi _select3:1									
P11.7					smif.spi_ clk												
P12.0	tcpwm[0].l ine[4]:3	tcpwm[1].line [4]:1			smif.spi_ data4	scb[6].ua rt_rx:0	scb[6].i2 c_scl:0	scb[6].spi _mosi:0			peri.tr_io_i nput[24]:0						
P12.1	tcpwm[0].l ine_comp l[4]:3	tcpwm[1].line _compl[4]:1			smif.spi_ data5	scb[6].ua rt_tx:0	scb[6].i2 c_sda:0	scb[6].spi _miso:0			peri.tr_io_i nput[25]:0						
P12.2	tcpwm[0].l ine[5]:3	tcpwm[1].line [5]:1			smif.spi_ data6	scb[6].ua rt_rts:0		scb[6].spi _clk:0									
P12.3	tcpwm[0].l ine_comp l[5]:3	tcpwm[1].line _compl[5]:1			smif.spi_ data7	scb[6].ua rt_cts:0		scb[6].spi _select0:0									
P12.4	tcpwm[0].l ine[6]:3	tcpwm[1].line [6]:1			smif.spi_ select3			scb[6].spi _select1:0	audioss.p dm_clk								
P12.5	tcpwm[0].l ine_comp l[6]:3	tcpwm[1].line _compl[6]:1						scb[6].spi _select2:0	audioss.p dm_data								
P12.6	tcpwm[0].l ine[7]:3	tcpwm[1].line [7]:1						scb[6].spi _select3:0									
P12.7	tcpwm[0].l ine_comp I[7]:3	tcpwm[1].line _compl[7]:1			_	_											

Note

For example, the name tcpwm[0].line_compl[3]:4 indicates that this is instance 0 of a tcpwm block, the signal is line_compl # 3 (complement of the line output) and this is the fourth occurrence (copy) of the signal. Signal copies are provided to allow flexibility in routing and to maximise utilisation of on-chip resources.

Document Number: 002-18787 Rev. *H

^{1.} The notation for a signal is of the form IPName[x].signal_name[u]:y.
IPName = Name of the block (such as tcpwm), x = Unique instance of the IP, Signal_name = Name of the signal number where there are more than one signals for a particular signal name, y = Designates copies of the signal name.



Table 8. Multiple Alternate Functions^[1] (continued)

Port/ Pin	ACT #0	ACT #1	DS #2	ACT #4	ACT #5	ACT #6	ACT #7	ACT #8	ACT #9	ACT #10	ACT #12	ACT #13	ACT #14	ACT #15	DS #4	DS #5	DS #6
P13.0	tcpwm[0].l ine[0]:4	tcpwm[1].line [8]:1				scb[6].ua rt_rx:1	scb[6].i2 c_scl:1	scb[6].spi _mosi:1			peri.tr_io_i nput[26]:0						
P13.1	tcpwm[0].l ine_comp l[0]:4	tcpwm[1].line _compl[8]:1				scb[6].ua rt_tx:1	scb[6].i2 c_sda:1	scb[6].spi _miso:1			peri.tr_io_i nput[27]:0						
P13.2	tcpwm[0].l ine[1]:4	tcpwm[1].line [9]:1				scb[6].ua rt_rts:1		scb[6].spi _clk:1									
P13.3	tcpwm[0].l ine_comp l[1]:4	tcpwm[1].line _compl[9]:1				scb[6].ua rt_cts:1		scb[6].spi _select0:1									
P13.4	tcpwm[0].l ine[2]:4	tcpwm[1].line [10]:1						scb[6].spi _select1:1									
P13.5	tcpwm[0].l ine_comp l[2]:4	tcpwm[1].line _compl[10]:1						scb[6].spi _select2:1									
P13.6	tcpwm[0].l ine[3]:4	tcpwm[1].line [11]:1						scb[6].spi _select3:1									
P13.7	tcpwm[0].l ine_comp l[3]:4	tcpwm[1].line _compl[11]:1															

Note

Document Number: 002-18787 Rev. *H Page 32 of 82

^{1.} The notation for a signal is of the form IPName[x].signal_name[u]:y.

IPName = Name of the block (such as tcpwm), x = Unique instance of the IP, Signal_name = Name of the signal, u = Signal number where there are more than one signals for a particular signal name, y = Designates

copies of the signal name.

For example, the name tcpwm[0].line_compl[3]:4 indicates that this is instance 0 of a tcpwm block, the signal is line_compl # 3 (complement of the line output) and this is the fourth occurrence (copy) of the signal. Signal copies are provided to allow flexibility in routing and to maximise utilisation of on-chip resources.



Analog, Smart I/O, and DSI alternate Port Pin functionality is provided in Table 9.

Table 9. Port Pin Analog, Smart I/O, and DSI Functions

Port/Pin	Name	Analog	Digital HV	DSI	SMARTIO
P0.0	P0.0	wco_in		dsi[0].port_if[0]	
P0.1	P0.1	wco_out		dsi[0].port_if[1]	
P0.2	P0.2			dsi[0].port_if[2]	
P0.3	P0.3			dsi[0].port_if[3]	
P0.4	P0.4		pmic_wakeup_in hibernate_wakeup[1]	dsi[0].port_if[4]	
P0.5	P0.5		pmic_wakeup_out	dsi[0].port_if[5]	
P1.0	P1.0			dsi[1].port_if[0]	
P1.1	P1.1			dsi[1].port_if[1]	
P1.2	P1.2			dsi[1].port_if[2]	
P1.3	P1.3			dsi[1].port_if[3]	
P1.4	P1.4		hibernate_wakeup[0]	dsi[1].port_if[4]	
P1.5	P1.5			dsi[1].port_if[5]	
P2.0	P2.0			dsi[2].port_if[0]	
P2.1	P2.1			dsi[2].port_if[1]	
P2.2	P2.2			dsi[2].port_if[2]	
P2.3	P2.3			dsi[2].port_if[3]	
P2.4	P2.4			dsi[2].port_if[4]	
P2.5	P2.5			dsi[2].port_if[5]	
P2.6	P2.6			dsi[2].port_if[6]	
P2.7	P2.7			dsi[2].port_if[7]	
P3.0	P3.0				
P3.1	P3.1				
P3.2	P3.2				
P3.3	P3.3				
P3.4	P3.4				
P3.5	P3.5				
P4.0	P4.0			dsi[0].port_if[6]	
P4.1	P4.1			dsi[0].port_if[7]	
P4.2	P4.2			dsi[1].port_if[6]	
P4.3	P4.3			dsi[1].port_if[7]	
P5.0	P5.0			dsi[3].port_if[0]	
P5.1	P5.1			dsi[3].port_if[1]	
P5.2	P5.2			dsi[3].port_if[2]	
P5.3	P5.3			dsi[3].port_if[3]	
P5.4	P5.4			dsi[3].port_if[4]	
P5.5	P5.5			dsi[3].port_if[5]	
P5.6	P5.6	lpcomp.inp_comp0		dsi[3].port_if[6]	
P5.7	P5.7	lpcomp.inn_comp0		dsi[3].port_if[7]	

Document Number: 002-18787 Rev. *H Page 33 of 82



Table 9. Port Pin Analog, Smart I/O, and DSI Functions (continued)

Port/Pin	Name	Analog	Digital HV	DSI	SMARTIO
P6.0	P6.0			dsi[4].port_if[0]	
P6.1	P6.1			dsi[4].port_if[1]	
P6.2	P6.2	lpcomp.inp_comp1		dsi[4].port_if[2]	
P6.3	P6.3	lpcomp.inn_comp1		dsi[4].port_if[3]	
P6.4	P6.4			dsi[4].port_if[4]	
P6.5	P6.5			dsi[4].port_if[5]	
P6.6	P6.6		swd_data	dsi[4].port_if[6]	
P6.7	P6.7		swd_clk	dsi[4].port_if[7]	
P7.0	P7.0			dsi[5].port_if[0]	
P7.1	P7.1	csd.cmodpadd csd.cmodpads		dsi[5].port_if[1]	
P7.2	P7.2	csd.csh_tankpadd csd.csh_tankpads		dsi[5].port_if[2]	
P7.3	P7.3	csd.vref_ext		dsi[5].port_if[3]	
P7.4	P7.4			dsi[5].port_if[4]	
P7.5	P7.5			dsi[5].port_if[5]	
P7.6	P7.6			dsi[5].port_if[6]	
P7.7	P7.7	csd.cshieldpads		dsi[5].port_if[7]	
P8.0	P8.0			dsi[11].port_if[0]	smartio[8].io[0]
P8.1	P8.1			dsi[11].port_if[1]	smartio[8].io[1]
P8.2	P8.2			dsi[11].port_if[2]	smartio[8].io[2]
P8.3	P8.3			dsi[11].port_if[3]	smartio[8].io[3]
P8.4	P8.4			dsi[11].port_if[4]	smartio[8].io[4]
P8.5	P8.5			dsi[11].port_if[5]	smartio[8].io[5]
P8.6	P8.6			dsi[11].port_if[6]	smartio[8].io[6]
P8.7	P8.7			dsi[11].port_if[7]	smartio[8].io[7]
P9.0	P9.0	ctb_oa0+		dsi[10].port_if[0]	smartio[9].io[0]
P9.1	P9.1	ctb_oa0-		dsi[10].port_if[1]	smartio[9].io[1]
P9.2	P9.2	ctb_oa0_out		dsi[10].port_if[2]	smartio[9].io[2]
P9.3	P9.3	ctb_oa1_out		dsi[10].port_if[3]	smartio[9].io[3
P9.4	P9.4	ctb_oa1-		dsi[10].port_if[4]	smartio[9].io[4
P9.5	P9.5	ctb_oa1+		dsi[10].port_if[5]	smartio[9].io[5]
P9.6	P9.6	ctb_oa0+		dsi[10].port_if[6]	smartio[9].io[6]
P9.7	P9.7	ctb_oa1+ or ext_vref		dsi[10].port_if[7]	smartio[9].io[7]
P10.0	P10.0	sarmux[0]		dsi[9].port_if[0]	
P10.1	P10.1	sarmux[1]		dsi[9].port_if[1]	
P10.2	P10.2	sarmux[2]		dsi[9].port_if[2]	
P10.3	P10.3	sarmux[3]		dsi[9].port_if[3]	

Document Number: 002-18787 Rev. *H Page 34 of 82



Table 9. Port Pin Analog, Smart I/O, and DSI Functions (continued)

Port/Pin	Name	Analog	Digital HV	DSI	SMARTIO
P10.4	P10.4	sarmux[4]		dsi[9].port_if[4]	
P10.5	P10.5	sarmux[5]		dsi[9].port_if[5]	
P10.6	P10.6	sarmux[6]		dsi[9].port_if[6]	
P10.7	P10.7	sarmux[7]		dsi[9].port_if[7]	
P11.0	P11.0			dsi[8].port_if[0]	
P11.1	P11.1			dsi[8].port_if[1]	
P11.2	P11.2			dsi[8].port_if[2]	
P11.3	P11.3			dsi[8].port_if[3]	
P11.4	P11.4			dsi[8].port_if[4]	
P11.5	P11.5			dsi[8].port_if[5]	
P11.6	P11.6			dsi[8].port_if[6]	
P11.7	P11.7			dsi[8].port_if[7]	
P12.0	P12.0			dsi[7].port_if[0]	
P12.1	P12.1			dsi[7].port_if[1]	
P12.2	P12.2			dsi[7].port_if[2]	
P12.3	P12.3			dsi[7].port_if[3]	
P12.4	P12.4			dsi[7].port_if[4]	
P12.5	P12.5			dsi[7].port_if[5]	
P12.6	P12.6	srss.eco_in		dsi[7].port_if[6]	
P12.7	P12.7	srss.eco_out		dsi[7].port_if[7]	
P13.0	P13.0			dsi[6].port_if[0]	
P13.1	P13.1			dsi[6].port_if[1]	
P13.2	P13.2			dsi[6].port_if[2]	
P13.3	P13.3			dsi[6].port_if[3]	
P13.4	P13.4			dsi[6].port_if[4]	
P13.5	P13.5			dsi[6].port_if[5]	
P13.6	P13.6			dsi[6].port_if[6]	
P13.7	P13.7			dsi[6].port_if[7]	

Document Number: 002-18787 Rev. *H Page 35 of 82




Power Supply Considerations

The power system diagram (see Figure 8) shows the general requirements for power pins. The diagram also shows the radio pins that need to be decoupled. The power scheme allows different VDDIO and VDDA connections. Because no sequencing requirements need to be analyzed and specified, customers may bring up the power supplies in any order and the power system is responsible for ensuring power is good in all domains before allowing operation. VDDD, VDDA, and VDDIO may be separate nets, which are not ohmically connected on

chip. Depending on different package requirements, these may be required to be connected off chip.

The power system will have a buck regulator in addition to an LDO. A Single Input Multiple Output (SIMO) Buck regulator with multiple outputs allows saving an inductor and also providing a high-efficiency supply to the radio (see Figure 8).

Figure 8. Power Connections



Note

Applicable for PSoC 6 devices with BLE only.

PSoC® 6 MCU: PSoC 63 with BLE Datasheet



Figure 8 shows the power supply pins to the PSoC and the connections between the PSoC and the radio. It also shows which pins need bypass capacitors. Refer to AN218241 - PSoC 6 MCU Hardware Design Considerations for details on the required connections for any given design.

Description of power pins is as follows:

- VBACKUP is the supply to the backup domain. The backup domain includes the 32-kHz WCO, RTC, and backup registers. It can generate a wake-up interrupt to the chip via the RTC timers or an external input. It can also generate an output to wakeup external circuitry. It is connected to VDDD when not used as a separate battery backup domain. VBACKUP provides the supply for Port 0.
- VDDD is the main digital supply input (1.7 to 3.6 V). It provides the inputs for the internal Regulators and for Port 1.
- VDDA is the supply for analog peripherals (1.7 to 3.6 V). It must be connected to VDDIOA on the PCB.
- VDDIOA is the supply to for Ports 9 and 10. It must be connected to VDDA on the PCB when present. Ports 9 and 10 are supplied by VDDA when VDDIOA is not present.
- VDD_NS is the supply input to the Buck and should be at the same potential as VDDD. The bypass capacitor between VDD_NS and ground should be 10 µF.
- VDDIO0 is the Supply for Ports 11 to 13 when present. When not present, these ports are supplied by VDDD.
- VDDIO1 is the Supply for Ports 5 to 8 when present. When not present, these ports are supplied by VDDA.
- VDDIOR is the Supply for Ports 2 to 4 on the 124 BGA only.
- VDDUSB is the USB supply and is required to be 2.85 V to 3.6 V for USB operation. In addition, the pin powers Port 14. When USB is not used, this pin can be 1.7 V to 3.6 V for using Port 14 pins as GPIOs

All the pins above may be shorted to VDDD as shown in Figure 8.

- VBUCK1 is the output 1 of on-chip SIMO regulator and requires a bypass capacitor connection for proper operation. This output can power VCCD when internal regulators are powered down.
- VCCD is the internal core regulators' (LDO) output and requires a bypass capacitor connection for proper operation. Used as core supply input when internal regulators are OFF.
- VRF is the output 2 of the on-chip SIMO regulator and requires bypass capacitor connection for proper operation. This output can power the VDCDC input.
- VDCDC is the BLE radio digital supply input and is typically connected to VRF externally.
- The VDDR1, VDDR2, and VDDR3 pins are for the BLE radio analog supply input and are connected to VDCDC externally.
- VDDR_HVL is the PSoC 6 MCU to BLE radio interface supply output and requires a bypass capacitor connection for proper operation.
- DVDD is the BLE subsystem regulators' (LDO) output and requires a bypass capacitor connection for proper operation.

The supply voltage range is 1.71 to 3.6 V with all functions and circuits operating over that range. All grounds must be shorted together on the PCB. Bypass capacitors must be used from VDDD and VDDA to ground and wherever indicated in the diagram. Typical practice for systems in this frequency range is to use a capacitor in the 10-µF range in parallel with a smaller capacitor (0.1 µF, for example). Note that these are simply rules of thumb and that, for critical applications, the PCB layout, lead inductance, and the bypass capacitor parasitic should be simulated to design and obtain optimal bypassing. Recommended Buck output capacitor values are 10 µF for Vrf and 4.7 µF for VBUCK1. The capacitor connected to Vind2 should be 100 nF. All capacitors should be $\pm 20\%$ or better; the recommended inductor value is 2.2 µH $\pm 20\%$ (for example, TDK MLP2012H2R2MT0S1).

Document Number: 002-18787 Rev. *H Page 37 of 82



Electrical Specifications

Absolute Maximum Ratings

Table 10. Absolute Maximum Ratings^[3]

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID1	V _{DD_ABS}	Analog or digital supply relative to V_{SS} ($V_{SSD} = V_{SSA}$)	-0.5	_	4	V	Absolute Maximum
SID2	V _{CCD_ABS}	Direct digital core voltage input relative to V _{SSD}	-0.5	_	1.2	٧	Absolute Maximum
SID3	V _{GPIO_ABS}	GPIO voltage; V _{DDD} or V _{DDA}	-0.5	_	V _{DD} + 0.5	V	Absolute Maximum
SID4	I _{GPIO_ABS}	Current per GPIO	-25	-	25	mA	Absolute Maximum
SID5	I _{GPIO_injection}	GPIO injection current per pin	-0.5	_	0.5	mA	Absolute Maximum
SID3A	ESD_HBM	Electrostatic discharge Human Body Model	2200	_	_	V	Absolute Maximum
SID3B	ESD_HBM_ ANT	Electrostatic discharge Human Body Model; Antenna Pin	500	_	_	V	Absolute Maximum; RF pin
SID4A	ESD_CDM	Electrostatic discharge Charged Device Model	500	_	_	V	Absolute Maximum
SID4B	ESD_CDM_ANT	Electrostatic discharge Charged Device Model; Antenna Pin	200	_	_	V	Absolute Maximum; RF pin
SID4C	ESD_CDM_X	Electrostatic discharge Charged Device Model; XI, XO pins	200	_	_	V	Absolute Maximum; XI, XO Pins
SID5A	LU	Pin current for latchup-free operation	-100	_	100	mA	Absolute Maximum

Note: All specifications are valid for −40 °C ≤ TA ≤ 85 °C and for 1.71 V to 3.6 V except where noted.

Device-Level Specifications

Table 11. Power Supply Range, CPU Current, and Transition Time Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions				
DC Specifications											
SID6	V_{DDD}	Internal Regulator and Port 1 GPIO Supply	1.7	_	3.6	V	-				
SID7	V _{DDA}	Analog Power Supply Voltage. Shorted to V _{DDIOA} on PCB.	1.7	-	3.6	V	Internally unregulated supply				
SID7A	V _{DDIO1}	GPIO Supply for Ports 5 to 8 when present	1.7	_	3.6	V	V _{DDIO_1} must be ≥ V _{DDA} .				
SID7B	V_{DDIO0}	GPIO Supply for Ports 11 to 13 when present	1.7	_	3.6	V	-				
SID7E	$V_{\rm DDIO0}$	Supply for E-Fuse Programming	2.38	2.5	2.62	V	E-Fuse Programming Voltage				
SID7C	V _{DDIO2}	GPIO Supply for Ports 2 to 4 on BGA 124 only	1.7	_	3.6	V	_				
SID7D	$V_{\rm DDIOA}$	GPIO Supply for Ports 9 to 10. Shorted to V _{DDA} on PCB.	1.7	-	3.6	V	_				
SID7F	V _{DDUSB}	Supply for Port 14 (USB or GPIO) when present	1.7	_	3.6	V	Min. supply is 2.85 V for USB				
SID6B	V _{BACKUP}	Backup Power and GPIO Port 0 supply when present	1.7	_	3.6	V	Min. is 1.4 V in Backup mode				
							<u> </u>				

Note

Document Number: 002-18787 Rev. *H Page 38 of 82

^{3.} Usage above the absolute maximum conditions listed in Table 10 may cause permanent damage to the device. Exposure to absolute maximum conditions for extended periods of time may affect device reliability. The maximum storage temperature is 150 °C in compliance with JEDEC Standard JESD22-A103, High Temperature Storage Life. When used below absolute maximum conditions but above normal operating conditions, the device may not operate to specification.



Table 11. Power Supply Range, CPU Current, and Transition Time Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID8	V _{CCD1}	Output voltage (for core logic bypass)	_	1.1	_	V	High-speed mode
SID9	V _{CCD2}	Output voltage (for core logic bypass)	_	0.9	_	V	ULP mode. Valid for –20 to 85 °C.
SID10	C _{EFC}	External regulator voltage (V _{CCD}) bypass	3.8	4.7	5.6	μF	X5R ceramic or better; Value for 0.8 to 1.2 V.
SID11	C _{EXC}	Power supply decoupling capacitor	-	10	_	μF	X5R ceramic or better
LP RANGE	POWER SPEC	CIFICATIONS (for V _{CCD} = 1.1 V with Buck ar	nd LDO)				
Cortex M4.	Active Mode						
Execute wi	th Cache Disal	bled (Flash)		ı			
SIDF1	I _{DD1}	Execute from Flash; CM4 Active 50 MHz, CM0+ Sleep 25 MHz.	-	2.3	3.2	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
		With IMO & FLL. While(1).	-	3.1	3.6	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			_	5.7	6.5	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
SIDE3		Execute from Flash; CM4 Active 8 MHz.	-	0.9	1.5	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDF2	I _{DD2}	CM0+ Sleep 8 MHz. With IMO. While(1).	_	1.2	1.6	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			_	2.8	3.5	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
Execute wi	th Cache Enab	oled					
		Execute from Cache; CM4 Active 150 MHz,	-	6.3	7	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDC1	I _{DD3}	CM0+ Sleep 75 MHz. IMO & FLL. Dhrystone.	-	9.7	11.2	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
		·	_	14.4	15.1	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
		Execute from Cache;	-	4.8	5.8	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDC2	I_{DD4}	CM4 Active 100 MHz, CM0+ Sleep 100 MHz. IMO & FLL. Dhrystone.	-	7.4	8.4	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
		ŕ	-	11.3	12	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
		Execute from Cache; CM4 Active 50 MHz,	_	2.4	3.4	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDC3	I _{DD5}	CM0+ Sleep 25 MHz. IMO & FLL. Dhrystone	-	3.7	4.1	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			-	6.3	7.2	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
		Encode from Oarley OMA Asting OMILE	-	0.9	1.5	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDC4	I _{DD6}	Execute from Cache; CM4 Active 8 MHz, CM0+ Sleep 8 MHz. IMO. Dhrystone.	_	1.3	1.8	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			-	3	3.8	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
Cortex M0+	+. Active Mode						
Execute wi	th Cache Disal	bled (Flash)		ı	1		
SIDF3	looz	Execute from Flash; CM4 Off, CM0+ Active 50 MHz.	-	2.4	3.3	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
CIDIO	I _{DD7}	With IMO & FLL. While (1).	-	3.2	3.7	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			_	5.6	6.3	mA	V_{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
SIDF4	Inne	Execute from Flash; CM4 Off, CM0+ Active 8 MHz.	-	0.8	1.5	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
CIDI 4	I _{DD8}	With IMO. While (1).	-	1.1	1.6	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			_	2.60	3.4	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C

Document Number: 002-18787 Rev. *H Page 39 of 82



Table 11. Power Supply Range, CPU Current, and Transition Time Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
----------	-----------	-------------	-----	-----	-----	------	----------------------

	th Cache En	abled					
SIDC5	I _{DD9}	Execute from Cache; CM4 Off, CM0+ Active 100 MHz.	ı	3.8	4.5	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
	-DD9	With IMO & FLL. Dhrystone.	ı	5.9	6.5	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			ı	9	9.7	mA	V_{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
NDCC I	Execute from Cache; CM4 Off, CM0+ Active 8 MHz.	_	0.8	1.3	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C	
SIDC6	I _{DD10}	With IMO. Dhrystone.	-	1.20	1.7	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			-	2.60	3.4	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
Cortex M4.	Sleep Mode						
		CM4 Sleep 100 MHz;	-	1.5	2.2	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDS1	I _{DD11}	CM0+ Sleep 100 MHz. With IMO & FLL.	-	2.2	2.7	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			-	4	4.6	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
		CM4 Sloop FO MI IT	-	1.2	1.9	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDS2	I _{DD12}	CM4 Sleep 50 MHz; CM0+ Sleep 25 MHz. With IMO & FLL.	-	1.7	2.2	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			1	3.4	4.3	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
	I _{DD13}	CM4 Sleep 8 MHz, CM0+ Sleep 8 MHz. With IMO.	_	0.7	1.3	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDS3			-	1	1.5	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			1	2.4	3.3	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
Cortex M0+	Sleep Mod	е					
		CM4 Off, CM0+ Sleep 50 MHz.	_	1.3	2	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDS4	I _{DD14}	With IMO & FLL.	-	1.9	2.4	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			-	3.80	4.6	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
			-	0.7	1.3	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDS5	I _{DD15}	CM4 Off, CM0+ Sleep 8 MHz. With IMO.	-	1	1.5	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			ı	2.4	3.3	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
Cortex M4.	Minimum Re	egulator Current Mode		_			
		Execute from Elech: CMAIDA 8 MHz, CMO+	_	0.9	1.5	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDLPA1	I _{DD16}	Execute from Flash; CM4 LPA 8 MHz, CM0+ Sleep 8 MHz. With IMO. While (1).	ı	1.2	1.7	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			ı	2.8	3.5	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
		Execute from Cache; CM4 LPA 8 MHz.	-	0.9	1.5	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDLPA2	I _{DD17}	CM0+ Sleep 8 MHz. With IMO. Dhrystone.	-	1.3	1.8	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
<u> </u>			ı	2.9	3.7	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
Cortex M0+	+. Minimum F	Regulator Current Mode					

Document Number: 002-18787 Rev. *H Page 40 of 82



Table 11. Power Supply Range, CPU Current, and Transition Time Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
		Execute from Flash;	_	0.8	1.4	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDLPA3	I _{DD18}	CM4 Off, CM0+ Active 8 MHz. With IMO. While (1).	_	1.1	1.6	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
		With hid. Wille (1).	_	2.7	3.6	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
			_	0.8	1.4	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDLPA4	I _{DD19}	Execute from Cache; CM4 Off, CM0+ Active 8 MHz. With IMO. Dhrystone.	_	1.2	1.7	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
		·	_	2.7	3.6	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
Cortex M4.	Minimum Reg	ulator Current Mode					
			_	0.7	1.1	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDLPS1	I _{DD20}	CM4 Sleep 8 MHz, CM0+ Sleep 8 MHz. With IMO.	_	1	1.5	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			_	2.4	3.3	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
Cortex M0+	. Minimum Re	gulator Current Mode	Į.	Į.	Į.	•	
			_	0.6	1.1	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDLPS3	I _{DD22}	CM4 Off, CM0+ Sleep 8 MHz. With IMO.	_	0.9	1.5	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
			_	2.4	3.3	mA	V _{DDD} = 1.8 to 3.3 V, LDO, Max at 85 °C
ULP RANG	E POWER SPE	ECIFICATIONS (for $V_{CCD} = 0.9 V$ using the I	Buck). U	LP mod	e is valid	from –2	0 to +85 °C.
Cortex M4.	Active Mode						
Execute wi	th Cache Disal	bled (Flash)					
SIDF5	I _{DD3}	Execute from Flash; CM4 Active 50 MHz, CM0+ Sleep 25 MHz.	-	1.7	2.2	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
		With IMO & FLL. While(1).	_	2.1	2.4	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
SIDF6	I _{DD4}	Execute from Flash; CM4 Active 8 MHz,	_	0.56	0.8	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
	1004	CM0+ Sleep 8 MHz. With IMO. While (1)	_	0.75	1	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
Execute wi	th Cache Enab	oled					
SIDC8	I _{DD10}	Execute from Cache; CM4 Active 50 MHz, CM0+ Sleep 25 MHz. With IMO & FLL. Dhrystone.	_	1.6	2.2	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
		With two & LE. Dillystone.	_	2.4	2.7	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
SIDC9	I _{DD11}	Execute from Cache; CM4 Active 8 MHz, CM0+ Sleep 8 MHz.	_	0.65	0.8	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
	DDTT	With IMO. Dhrystone.	_	0.8	1.1	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
Cortex M0+	Active Mode						
Execute wi	th Cache Disal	bled (Flash)					
SIDF7	I _{DD16}	Execute from Flash; CM4 Off, CM0+ Active	_	1	1.4	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
	DD 10	25 MHz. With IMO & FLL. Write(1).	_	1.34	1.6	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
SIDF8	I _{DD17}	Execute from Flash; CM4 Off, CM0+ Active	_	0.54	0.75	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
		8 MHz. With IMO. While(1).	_	0.73	1	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
Execute wi	th Cache Enab	oled					
SIDC10	I _{DD18}	Execute from Cache; CM4 Off, CM0+ Active 25 MHz. With IMO & FLL. Dhrystone.	_	0.91	1.25	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
		23 IVII IZ. VVIIII IIVIO α FLL. DIII yStorie.	_	1.34	1.6	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C

Document Number: 002-18787 Rev. *H Page 41 of 82



Table 11. Power Supply Range, CPU Current, and Transition Time Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SIDC11		Execute from Cache; CM4 Off, CM0+ Active 8 MHz. With IMO. Dhrystone.	_	0.51	0.72	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
	22.10	8 MHZ. With IMO. Drifystone.	_	0.73	0.95	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C

Cortex M4.	Sleep Mode						
01007		CM4 Sleep 50 MHz, CM0+ Sleep 25 MHz.	_	0.76	1.1	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDS7	I _{DD21}	With IMO & FLL.	_	1.1	1.4	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
CIDCO	1	CM4 Sleep 8 MHz, CM0+ Sleep 8 MHz.	1	0.42	0.65	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
SIDS8	I _{DD22}	With IMO.	_	0.59	0.8	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
Cortex M0+	+. Sleep Mode					·	
SIDS9	I _{DD23}	CM4 Off, CM0+ Sleep 25 MHz.	_	0.62	0.9	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
CIDOS	23טטי	With IMO & FLL.	_	0.88	1.1	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
SIDS10	l	CM4 Off, CM0+ Sleep 8 MHz.	ı	0.41	0.6	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
	I _{DD24}	With IMO.	-	0.58	0.8	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
Cortex M4.	Minimum Reg	ulator Current Mode		1			
SIDLPA5	I _{DD25}	Execute from Flash. CM4 Active 8 MHz,	-	0.52	0.75	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
	DD23	CM0+ Sleep 8 MHz. With IMO. While(1).	_	0.76	1	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
SIDLPA6	I _{DD26}	Execute from Cache. CM4 Active 8 MHz,	-	0.54	0.76	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
	DD20	CM0+ Sleep 8 MHz. With IMO. Dhrystone.	-	0.78	1	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
Cortex M0+	⊦. Minimum Re	gulator Current Mode					
SIDLPA7	I _{DD27}	Execute from Flash. CM4 Off, CM0+ Active	-	0.51	0.75	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
	DD21	8 MHz. With IMO. While (1).	-	0.75	1	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
SIDLPA8	I _{DD28}	Execute from Cache. CM4 Off, CM0+ Active	-	0.48	0.7	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
	5520	8 MHz. With IMO. Dhrystone.	-	0.7	0.95	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
Cortex M4.	Minimum Reg	ulator Current Mode					
SIDLPS5	I _{DD29}	CM4 Sleep 8 MHz, CM0 Sleep 8 MHz.	-	0.4	0.6	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
	5525	With IMO.	_	0.57	0.8	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
Cortex M0+	⊦. Minimum Re	gulator Current Mode					
SIDLPS7	I _{DD31}	CM4 Off, CM0+ Sleep 8 MHz. With IMO.	-	0.39	0.6	mA	V _{DDD} = 3.3 V, Buck ON, Max at 60 °C
	ונטטי		_	0.56	8.0	mA	V _{DDD} = 1.8 V, Buck ON, Max at 60 °C
Deep Sleep	Mode						
SIDDS1	I _{DD33A}	With internal Buck enabled and 64K SRAM retention	-	7	-	μA	Max value is at 85 °C
SIDDS1_B	I _{DD33A_B}	With internal Buck enabled and 64K SRAM retention	-	7	_	μA	Max value is at 60 °C
SIDDS2	I _{DD33B}	With internal Buck enabled and 256K SRAM retention	-	9	_	μΑ	Max value is at 85 °C
SIDDS2_B	I _{DD33B_B}	With internal Buck enabled and 256K SRAM retention	-	9	_	μΑ	Max value is at 60 °C

Document Number: 002-18787 Rev. *H Page 42 of 82



Table 11. Power Supply Range, CPU Current, and Transition Time Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
Hibernate Mode							
SIDHIB1	I _{DD34}	V _{DDD} = 1.8 V	_	300	1	nA	No clocks running
SIDHIB2	I _{DD34A}	V _{DDD} = 3.3 V	_	800	1	nA	No clocks running

Power Mo	de Transition T	ïmes					
SID12	T _{LPACT_ACT}	Low Power Active to Active transition time	_	_	35	μs	Including PLL lock time
SID13	T _{DS_LPACT}	Deep Sleep to LP Active transition time. Guaranteed by Design	-	-	25	μs	Cypress supplied software wakeup routines take approximately 100 CPU clock cycles after hardware wakeup (the 25 µs) before transition to Application code. With an 8 MHz CPU clock (LP Active), the time before user code executes is 25 + 12.5 = 37.5 µs.
SID13A	T _{DS_ACT}	Deep Sleep to Active transition time. Guaranteed by Design.	_	_	25	μs	Cypress supplied software wakeup routines take approximately 100 CPU clock cycles after hardware wakeup (the 25 µs) before transition to Application code. With a 25 MHz CPU clock (FLL), the time before user code executes is 25 + 4 = 29 µs. With a 100 MHz CPU clock, the time is 25 + 1.0 = 26 µs.
SID14	T _{HIB_ACT}	Hibernate to Active transition time	_	500	_	μs	Including PLL lock time

XRES

Table 12. XRES

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions			
KRES (Active Low) Specifications										
XRES AC Specifications										
SID15	T _{XRES_ACT}	POR or XRES release to Active transition time	_	750	_	μs	Normal mode, 50 MHz M0+.			
SID16	T _{XRES_PW}	XRES Pulse width	5	_	-	μs	_			
XRES DC S	pecifications									
SID17	T _{XRES_IDD}	IDD when XRES asserted	_	300	_	nA	V _{DDD} = 1.8 V			
SID17A	T _{XRES_IDD_1}	IDD when XRES asserted	_	800	_	nA	V _{DDD} = 3.3 V			
SID77	V _{IH}	Input Voltage high threshold	0.7 * V _{DD}	-	-	V	CMOS Input			
SID78	V _{IL}	Input Voltage low threshold	_	_	0.3 * V _{DD}	V	CMOS Input			
SID80	C _{IN}	Input Capacitance	_	3	_	pF	-			
SID81	V _{HYSXRES}	Input voltage hysteresis	_	100	-	mV	-			
SID82	I _{DIODE}	Current through protection diode to V _{DD} /V _{SS}	_	_	100	μA	_			

Notes

- Cypress-supplied software wakeup routines take approximately 100 CPU clock cycles after hardware wakeup (the 25 μs) before transition to Application code. With an 8-MHz CPU clock (LP Active), the time before user code executes is 25 + 12.5 = 37.5 μs.
 Cypress-supplied software wakeup routines take approximately 100 CPU clock cycles after hardware wakeup (the 25 μs) before transition to Application code. With a 25-MHz CPU clock (FLL), the time before user code executes is 25 + 4 = 29 μs. With a 100-MHz CPU clock, the time is 25 + 1 = 26 μs.

Document Number: 002-18787 Rev. *H Page 43 of 82



GPIO

Table 13. GPIO Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
GPIO DC Spe	ecifications						1
SID57	V _{IH}	Input voltage high threshold	0.7 * V _{DD}	_	_	V	CMOS Input
SID57A	I _{IHS}	Input current when Pad > VDDIO for OVT inputs	-	-	10	μΑ	Per I ² C Spec
SID58	V _{IL}	Input voltage low threshold	_	-	0.3 * V _{DD}	V	CMOS Input
SID241	V _{IH}	LVTTL input, V _{DD} < 2.7 V	0.7 * V _{DD}	-	_	V	_
SID242	V _{IL}	LVTTL input, V _{DD} < 2.7 V	_	-	0.3*V _{DD}	V	_
SID243	V _{IH}	LVTTL input, V _{DD} ≥ 2.7 V	2.0	-	-	V	_
SID244	V _{IL}	LVTTL input, V _{DD} ≥ 2.7 V	_	-	0.8	V	_
SID59	V _{OH}	Output voltage high level	V _{DD} – 0.5	-	_	V	I _{OH} = 8 mA
SID62A	V _{OL}	Output voltage low level	_	-	0.4	V	I _{OL} = 8 mA
SID63	R _{PULLUP}	Pull-up resistor	3.5	5.6	8.5	kΩ	_
SID64	R _{PULLDOWN}	Pull-down resistor	3.5	5.6	8.5	kΩ	_
SID65	I _{IL}	Input leakage current (absolute value)	-	-	2	nA	25 °C, V _{DD} = 3.0 V
SID65A	I _{IL_CTBM}	Input leakage on CTBm input pins	_	-	4	nA	_
SID66	C _{IN}	Input Capacitance	_	_	5	pF	_
SID67	V _{HYSTTL}	Input hysteresis LVTTL V _{DD} > 2.7 V	100	0	-	mV	-
SID68	V _{HYSCMOS}	Input hysteresis CMOS	0.05 * V _{DD}	_	_	mV	_
SID69	I _{DIODE}	Current through protection diode to V _{DD} /V _{SS}	-	-	100	μΑ	_
SID69A	I _{TOT_GPIO}	Maximum Total Source or Sink Chip Current	-	-	200	mA	-
GPIO AC Spe	ecifications						
SID70	T _{RISEF}	Rise time in Fast Strong Mode. 10% to 90% of V _{DD}	-	-	2.5	ns	Cload = 15 pF, 8 mA drive strength
SID71	T _{FALLF}	Fall time in Fast Strong Mode. 10% to 90% of V _{DD}	-	-	2.5	ns	Cload = 15 pF, 8 mA drive strength
SID72	T _{RISES_1}	Rise time in Slow Strong Mode. 10% to 90% of V _{DD}	52	-	142	ns	Cload = 15 pF, 8 mA drive strength, V _{DD} ≤ 2.7 V
SID72A	T _{RISES_2}	Rise time in Slow Strong Mode. 10% to 90% of V _{DD}	48	_	102	ns	Cload = 15 pF, 8 mA drive strength, 2.7 V < $V_{DD} \le 3.6 \text{ V}$
SID73	T _{FALLS_1}	Fall time in Slow Strong Mode. 10% to 90% of V _{DD}	44	_	211	ns	Cload = 15 pF, 8 mA drive strength, V _{DD} ≤ 2.7 V
SID73A	T _{FALLS_2}	Fall time in Slow Strong Mode. 10% to 90% of V _{DD}	42	_	93	ns	Cload = 15 pF, 8 mA drive strength, 2.7 V < V _{DD} ≤ 3.6 V
SID73G	T _{FALL_I2C}	Fall time (30% to 70% of V _{DD}) in Slow Strong mode	20 * V _{DDIO} / 5.5	-	250	ns	Cload = 10 pF to 400 pF, 8-mA drive strength

Document Number: 002-18787 Rev. *H Page 44 of 82



Table 13. GPIO Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID74	F _{GPIOUT1}	GPIO Fout. Fast Strong mode.	-	-	100	MHz	90/10%, 15-pF load, 60/40 duty cycle
SID75	F _{GPIOUT2}	GPIO Fout; Slow Strong mode.	-	-	16.7		90/10%, 15-pF load, 60/40 duty cycle
SID76	F _{GPIOUT3}	GPIO Fout; Fast Strong mode.	-	-	7	MHz	90/10%, 25-pF load, 60/40 duty cycle
SID245	F _{GPIOUT4}	GPIO Fout; Slow Strong mode.	-	-	3.5	MHz	90/10%, 25-pF load, 60/40 duty cycle
SID246	F _{GPIOIN}	GPIO input operating frequency;1.71 V \leq V _{DD} \leq 3.6 V	-	-	100	MHz	90/10% V _{IO}

Analog Peripherals

Opamp

Table 14. Opamp Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
	I _{DD}	Opamp Block current. No load.	-	_	-		_
SID269	I _{DD_HI}	Power = Hi	-	1300	1500	μA	_
SID270	I _{DD_MED}	Power = Med	-	450	600	μA	_
SID271	I _{DD_LOW}	Power = Lo	-	250	350	μA	_
	GBW	Load = 20 pF, 0.1 mA. V _{DDA} = 2.7 V	_	-	_		-
SID272	G _{BW_HI}	Power = Hi	6	_	-	MHz	-
SID273	G _{BW_MED}	Power = Med	4	_	-	MHz	-
SID274	G _{BW_LO}	Power = Lo	-	1	-	MHz	-
	I _{OUT_MAX}	V _{DDA} ≥ 2.7 V, 500 mV from rail	-	_	-		-
SID275	I _{OUT_MAX_HI}	Power = Hi	10	_	-	mA	-
SID276	I _{OUT_MAX_MID}	Power = Mid	10	_	-	mA	-
SID277	I _{OUT_MAX_LO}	Power = Lo	-	5	-	mA	-
	I _{OUT}	V _{DDA} = 1.71 V, 500 mV from rail	-	_	-		-
SID278	I _{OUT_MAX_HI}	Power = Hi	4	_	-	mA	-
SID279	I _{OUT_MAX_MID}	Power = Mid	4	_	-	mA	-
SID280	I _{OUT_MAX_LO}	Power = Lo	-	2	-	mA	-
SID281	V _{IN}	Input voltage range	0	_	V _{DDA} – 0.2	V	-
SID282	V_{CM}	Input common mode voltage	0	_	V _{DDA} – 0.2	V	-
	V _{OUT}	V _{DDA} ≥ 2.7 V	-	_	-		-
SID283	V _{OUT_1}	Power = hi, Iload = 10 mA	0.5	_	V _{DDA} – 0.5	V	-
SID284	V _{OUT_2}	Power = hi, Iload = 1 mA	0.2	_	V _{DDA} – 0.2	V	-
SID285	V _{OUT_3}	Power = med, Iload = 1 mA	0.2	_	V _{DDA} – 0.2	V	-
SID286	V _{OUT_4}	Power = Io, Iload = 0.1 mA	0.2	-	V _{DDA} – 0.2	V	_
SID287	V _{OS_UNTR}	Offset voltage, untrimmed	-	-	_	mV	_
SID288	V _{OS_TR}	Offset voltage, trimmed	-1	±0.5	1	mV	High mode, 0.2 to V _{DDA} – 0.2

Document Number: 002-18787 Rev. *H Page 45 of 82



Table 14. Opamp Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID288A	V _{OS_TR}	Offset voltage, trimmed	_	±1	-	mV	Medium mode
SID288B	V _{OS_TR}	Offset voltage, trimmed	_	±2	_	mV	Low mode
SID289	V _{OS_DR_UNTR}	Offset voltage drift, untrimmed	_	_	_	μV/°C	-
SID290	V _{OS_DR_TR}	Offset voltage drift, trimmed	-10	±3	10	μV/°C	High mode, 0.2 to V _{DDA} – 0.2
SID290A	V _{OS_DR_TR}	Offset voltage drift, trimmed	_	±10		μV/°C	Medium mode
SID290B	V _{OS_DR_TR}	Offset voltage drift, trimmed	-	±10	_	μV/°C	Low mode
SID291	CMRR	DC Common mode rejection ratio	67	80	_	dB	V _{DDD} = 3.3 V
SID292	PSRR	Power supply rejection ratio at 1 kHz, 10-mV ripple	70	85	_	dB	V _{DDD} = 3.3 V
Noise			_	_	_		-
SID293	VN1	Input-referred, 1 Hz–1 GHz, power = Hi	_	100	_	μVrms	_
SID294	VN2	Input-referred, 1 kHz, power = Hi	_	180	_	nV/rtHz	_
SID295	VN3	Input-referred, 10 kHz, power = Hi	_	70	-	nV/rtHz	_
SID296	VN4	Input-referred, 100 kHz, power = Hi	_	38	-	nV/rtHz	_
SID297	CLOAD	Stable up to max. load. Performance specs at 50 pF.	_	-	125	pF	_
SID298	SLEW_RATE	Output slew rate	6	ı	ı	V/µs	Cload = 50 pF, Power = High, $V_{DDA} \ge 2.7 \text{ V}$
SID299	T_OP_WAKE	From disable to enable, no external RC dominating	_	25	-	μs	_
	COMP_MODE	Comparator mode; 50-mV overdrive, Trise = Tfall (approx.)	_		-		_
SID300	T _{PD1}	Response time; power = hi	-	150	-	ns	-
SID301	T _{PD2}	Response time; power = med	-	400	-	ns	_
SID302	T _{PD3}	Response time; power = lo	_	2000	_	ns	-
SID303	V _{HYST_OP}	Hysteresis	_	10	_	mV	-
Deep Sleep		Mode 2 is lowest current range. Mode 1 has higher GBW.					Deep Sleep mode operation: V _{DDA} ≥ 2.7 V. V _{IN} is 0.2 to V _{DDA} – 1.5 V
SID_DS_1	I _{DD_HI_M1}	Mode 1, High current	_	1300	1500	μA	Typ at 25 °C
SID_DS_2	I _{DD_MED_M1}	Mode 1, Medium current	_	460	600	μΑ	Typ at 25 °C
SID_DS_3	I _{DD_LOW_M1}	Mode 1, Low current	_	230	350	μΑ	Typ at 25 °C
SID_DS_4	I _{DD_HI_M2}	Mode 2, High current	_	120	_	μΑ	25 °C
SID_DS_5	I _{DD_MED_M2}	Mode 2, Medium current	_	60	_	μA	25 °C
SID_DS_6	I _{DD_LOW_M2}	Mode 2, Low current	_	15	_	μA	25 °C
SID_DS_7	GBW_HI_M1	Mode 1, High current	_	4	-	MHz	25 °C
SID DS 8	GBW MED M1	Mode 1, Medium current	_	2	_	MHz	25 °C

Document Number: 002-18787 Rev. *H Page 46 of 82



Table 14. Opamp Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID_DS_9	GBW_LOW_M1	Mode 1, Low current	-	0.5	-	MHz	25 °C
SID_DS_10	GBW_HI_M2	Mode 2, High current	I	0.5	-	MHz	20-pF load, no DC load 0.2 V to V _{DDA} – 1.5 V
SID_DS_11	GBW_MED_M2	Mode 2, Medium current	1	0.2	ı	MHz	20-pF load, no DC load 0.2 V to V _{DDA} – 1.5 V
SID_DS_12	GBW_LOW_M2	Mode 2, Low current	-	0.1	_	MHz	20-pF load, no DC load 0.2 V to V _{DDA} – 1.5 V
SID_DS_13	V _{OS_HI_M1}	Mode 1, High current	-	5	_	mV	With trim 25 °C, 0.2 V to V _{DDA} – 1.5 V
SID_DS_14	V _{OS_MED_M1}	Mode 1, Medium current	1	5	-	mV	With trim 25 °C, 0.2 V to V _{DDA} – 1.5 V
SID_DS_15	V _{OS_LOW_M1}	Mode 1, Low current	ı	5	-	mV	With trim 25 °C, 0.2 V to V _{DDA} – 1.5 V
SID_DS_16	V _{OS_HI_M2}	Mode 2, High current	1	5	ı	mV	With trim 25 °C, 0.2 V to V _{DDA} – 1.5 V
SID_DS_17	V _{OS_MED_M2}	Mode 2, Medium current	1	5	1	mV	With trim 25 °C, 0.2 V to V _{DDA} – 1.5 V
SID_DS_18	V _{OS_LOW_M2}	Mode 2, Low current	ı	5	-	mV	With trim 25 °C, 0.2 V to V _{DDA} – 1.5 V
SID_DS_19	I _{OUT_HI_M1}	Mode 1, High current	ı	10	1	mA	Output is 0.5 V to V _{DDA} – 0.5 V
SID_DS_20	I _{OUT_MED_M1}	Mode 1, Medium current	1	10	1	mA	Output is 0.5 V to V _{DDA} – 0.5 V
SID_DS_21	I _{OUT_LOW_M1}	Mode 1, Low current	ı	4	-	mA	Output is 0.5 V to V _{DDA} – 0.5 V
SID_DS_22	I _{OUT_HI_M2}	Mode 2, High current	-	1	_	mA	Output is 0.5 V to V _{DDA} – 0.5 V
SID_DS_23	I _{OUT_MED_M2}	Mode 2, Medium current	-	1	_	mA	Output is 0.5 V to V _{DDA} – 0.5 V
SID_DS_24	I _{OUT_LOW_M2}	Mode 2, Low current	-	0.5	_	mA	Output is 0.5 V to V _{DDA} – 0.5 V

Document Number: 002-18787 Rev. *H Page 47 of 82



Table 15. Low-Power (LP) Comparator Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
LP Compar	ator DC Specific	ations					
SID84	V _{OFFSET1}	Input offset voltage for COMP1. Normal power mode.	-10	_	10	mV	COMP0 offset is ±25 mV
SID85A	V _{OFFSET2}	Input offset voltage. Low-power mode.	-25	±12	25	mV	_
SID85B	V _{OFFSET3}	Input offset voltage. Ultra low-power mode.	-25	±12	25	mV	_
SID86	V _{HYST1}	Hysteresis when enabled in Normal mode	_	-	60	mV	_
SID86A	V _{HYST2}	Hysteresis when enabled in Low-power mode	_	-	80	mV	_
SID87	V _{ICM1}	Input common mode voltage in Normal mode	0	_	V _{DDIO1} – 0.1	V	_
SID247	V _{ICM2}	Input common mode voltage in Low power mode	0	-	V _{DDIO1} – 0.1	V	-
SID247A	V _{ICM3}	Input common mode voltage in Ultra low power mode	0	_	V _{DDIO1} – 0.1	V	_
SID88	CMRR	Common mode rejection ratio in Normal power mode	50	_	-	dB	_
SID89	I _{CMP1}	Block Current, Normal mode	_	_	150	μΑ	-
SID248	I _{CMP2}	Block Current, Low power mode	-	-	10	μA	_
SID259	I _{CMP3}	Block Current in Ultra low-power mode	_	0.3	0.85	μΑ	-
SID90	ZCMP	DC Input impedance of comparator	35	-	_	МΩ	_
LP Compar	ator AC Specific	ations					
SID91	T _{RESP1}	Response time, Normal mode, 100 mV overdrive	_	_	100	ns	_
SID258	T _{RESP2}	Response time, Low power mode, 100 mV overdrive	_	_	1000	ns	_
SID92	T _{RESP3}	Response time, Ultra-low power mode, 100 mV overdrive	-	_	20	μs	_
SID92E	T_CMP_EN1	Time from Enabling to operation	-	_	10	μs	Normal and Low-power modes
SID92F	T_CMP_EN2	Time from Enabling to operation	-	_	50	μs	Ultra low-power mode
	•	·		•			•

Table 16. Temperature Sensor Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID93	T _{SENSACC}	Temperature sensor accuracy	– 5	±1	5	ပ္	–40 to +85 °C

Table 17. Internal Reference Specification

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID93R	V_{REFBG}	-	1.188	1.2	1.212	V	_

Document Number: 002-18787 Rev. *H Page 48 of 82



SAR ADC

Table 18. 12-bit SAR ADC DC Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID94	A_RES	SAR ADC Resolution	_	_	12	bits	_
SID95	A_CHNLS_S	Number of channels - single ended	_	_	16	-	8 full speed.
SID96	A-CHNKS_D	Number of channels - differential	_	_	8	_	Diff inputs use neighboring I/O
SID97	A-MONO	Monotonicity	_	_	_	_	Yes
SID98	A_GAINERR	Gain error	_	_	±0.2	%	With external reference.
SID99	A_OFFSET	Input offset voltage	_	_	2	mV	Measured with 1-V reference
SID100	A_ISAR_1	Current consumption at 1 Msps	_	_	1	mA	At 1 Msps. External Bypass Cap.
SID100A	A_ISAR_2	Current consumption at 1 Msps. Reference = V _{DD}	_	_	1.25	mA	At 1 Msps. External Bypass Cap.
SID101	A_VINS	Input voltage range - single-ended	V _{SS}	_	V_{DDA}	V	_
SID102	A_VIND	Input voltage range - differential	V _{SS}	_	V_{DDA}	V	_
SID103	A_INRES	Input resistance	_	_	2.2	kΩ	_
SID104	A_INCAP	Input capacitance	_	_	10	pF	_

Table 19. 12-bit SAR ADC AC Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
12-bit SAR	ADC AC Specif	fications					
SID106	A_PSRR	Power supply rejection ratio	70	_	_	dB	_
SID107	A_CMRR	Common mode rejection ratio	66	_	_	dB	Measured at 1 V.
One Megas	sample per seco	ond mode:					
SID108	A_SAMP_1	Sample rate with external reference bypass cap.	-	_	1	Msps	_
SID108A	A_SAMP_2	Sample rate with no bypass cap; Reference = V _{DD}	-	_	250	ksps	_
SID108B	A_SAMP_3	Sample rate with no bypass cap. Internal reference.	-	_	100	ksps	_
SID109	A_SINAD	Signal-to-noise and Distortion ratio (SINAD). V _{DDA} = 2.7 to 3.6 V, 1 Msps.	64	_	_	dB	Fin = 10 kHz
SID111A	A_INL	Integral Non Linearity. V _{DDA} = 2.7 to 3.6 V, 1 Msps	-2	_	2	LSB	Measured with internal V _{REF} = 1.2 V and bypass cap.
SID111B	A_INL	Integral Non Linearity. V _{DDA} = 2.7 to 3.6 V, 1 Msps	-4	_	4	LSB	Measured with external V _{REF} ≥ 1 V and V _{IN} common mode < 2 * Vref.
SID112A	A_DNL	Differential Non Linearity. V _{DDA} = 2.7 to 3.6 V, 1 Msps	-1	_	1.4	LSB	Measured with internal V _{REF} = 1.2 V and bypass cap.
SID112B	A_DNL	Differential Non Linearity. V _{DDA} = 2.7 to 3.6 V, 1 Msps	–1	-	1.7	LSB	Measured with external V _{REF} ≥ 1 V and V _{IN} common mode < 2 * Vref.
SID113	A_THD	Total harmonic distortion. V _{DDA} = 2.7 to 3.6 V, 1 Msps.	-	-	- 65	dB	Fin = 10 kHz

Document Number: 002-18787 Rev. *H Page 49 of 82



Table 20. 12-bit DAC Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions				
12-bit DA	12-bit DAC DC Specifications										
SID108D	DAC_RES	DAC resolution	_	_	12	bits	-				
SID111D	DAC_INL	Integral Non-Linearity	-4	_	4	LSB	-				
SID112D	DAC_DNL	Differential Non Linearity	-2	_	2	LSB	Monotonic to 11 bits.				
SID99D	DAC_OFFSET	Output Voltage zero offset error	-10	-	10	mV	For 000 (hex)				
SID103D	DAC_OUT_RE S	DAC Output Resistance	-	15	_	kΩ	_				
SID100D	DAC_IDD	DAC Current	-	-	125	μA	-				
SID101D	DAC_QIDD	DAC Current when DAC stopped	_	-	1	μA	-				
12-bit DA	C AC Specification	ons									
SID109D	DAC_CONV	DAC Settling time	-	-	2	μs	Driving through CTBm buffer; 25-pF load				
SID110D	DAC_Wakeup	Time from Enabling to ready for conversion	-	-	10	μs	_				

CSD

Table 21. CapSense Sigma-Delta (CSD) Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
CSD V2 Speci	fications						
SYS.PER#3	V _{DD_RIPPLE}	Max allowed ripple on power supply, DC to 10 MHz	-	-	±50	mV	V _{DDA} > 2 V (with ripple), 25 °C T _A , Sensitivity = 0.1 pF
SYS.PER#16	V _{DD_RIPPLE_1.8}	Max allowed ripple on power supply, DC to 10 MHz	-	_	±25	mV	V_{DDA} > 1.75 V (with ripple), 25 ° C T _A , Parasitic Capacitance (C _P) < 20 pF, Sensitivity \geq 0.4 pF
SID.CSD.BLK	I _{CSD}	Maximum block current			4500	μA	-
SID.CSD#15	V_{REF}	Voltage reference for CSD and Comparator	0.6	1.2	V _{DDA} – 0.6	V	V _{DDA} – V _{REF} ≥ 0.6 V
SID.CSD#15A	V _{REF_EXT}	External Voltage reference for CSD and Comparator	0.6		V _{DDA} – 0.6	V	V _{DDA} – V _{REF} ≥ 0.6 V
SID.CSD#16	I _{DAC1IDD}	IDAC1 (7-bits) block current	-	_	1900	μA	_
SID.CSD#17	I _{DAC2IDD}	IDAC2 (7-bits) block current	-	_	1900	μA	_
SID308	V _{CSD}	Voltage range of operation	1.7	_	3.6	V	1.71 to 3.6 V
SID308A	V _{COMPIDAC}	Voltage compliance range of IDAC	0.6	_	V _{DDA} – 0.6	V	V _{DDA} – V _{REF} ≥ 0.6 V
SID309	I _{DAC1DNL}	DNL	-1	_	1	LSB	_
SID310	I _{DAC1INL}	INL	-3	_	3	LSB	If V _{DDA} < 2 V then for LSB of 2.4 μA or less
SID311	I _{DAC2DNL}	DNL	-1	-	1	LSB	_
SID312	I _{DAC2INL}	INL	-3	-	3	LSB	If V _{DDA} < 2 V then for LSB of 2.4 μA or less
SNRC of the fo	ollowing is Ratio	o of counts of finger to noise. Gu	aranteed	by cha	racterizat	ion	

Document Number: 002-18787 Rev. *H Page 50 of 82



Table 21. CapSense Sigma-Delta (CSD) Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID313_1A	SNRC_1	SRSS Reference. IMO + FLL Clock Source. 0.1-pF sensitivity	5	-	_	Ratio	9.5-pF max. capacitance
SID313_1B	SNRC_2	SRSS Reference. IMO + FLL Clock Source. 0.3-pF sensitivity	5	_	_	Ratio	31-pF max. capacitance
SID313_1C	SNRC_3	SRSS Reference. IMO + FLL Clock Source. 0.6-pF sensitivity	5	_	_	Ratio	61-pF max. capacitance
SID313_2A	SNRC_4	PASS Reference. IMO + FLL Clock Source. 0.1-pF sensitivity	5	_	_	Ratio	12-pF max. capacitance
SID313_2B	SNRC_5	PASS Reference. IMO + FLL Clock Source. 0.3-pF sensitivity	5	_	_	Ratio	47-pF max. capacitance
SID313_2C	SNRC_6	PASS Reference. IMO + FLL Clock Source. 0.6-pF sensitivity	5	_	_	Ratio	86-pF max. capacitance
SID313_3A	SNRC_7	PASS Reference. IMO + PLL Clock Source. 0.1-pF sensitivity	5	_	_	Ratio	27-pF max. capacitance
SID313_3B	SNRC_8	PASS Reference. IMO + PLL Clock Source. 0.3-pF sensitivity	5	_	_	Ratio	86-pF max. capacitance
SID313_3C	SNRC_9	PASS Reference. IMO + PLL Clock Source. 0.6-pF sensitivity	5	_	-	Ratio	168-pF max. capacitance
SID314	I _{DAC1CRT1}	Output current of IDAC1 (7 bits) in low range	4.2		5.7	μA	LSB = 37.5-nA typ
SID314A	I _{DAC1CRT2}	Output current of IDAC1(7 bits) in medium range	33.7		45.6	μA	LSB = 300-nA typ.
SID314B	I _{DAC1CRT3}	Output current of IDAC1(7 bits) in high range	270		365	μA	LSB = 2.4-µA typ.
SID314C	I _{DAC1CRT12}	Output current of IDAC1 (7 bits) in low range, 2X mode	8		11.4	μA	LSB = 37.5-nA typ. 2X output stage
SID314D	I _{DAC1CRT22}	Output current of IDAC1(7 bits) in medium range, 2X mode	67		91	μΑ	LSB = 300-nA typ. 2X output stage
SID314E	I _{DAC1CRT32}	Output current of IDAC1(7 bits) in high range, 2X mode. V _{DDA} > 2 V	540		730	μΑ	LSB = 2.4-µA typ. 2X output stage
SID315	I _{DAC2CRT1}	Output current of IDAC2 (7 bits) in low range	4.2		5.7	μA	LSB = 37.5-nA typ.
SID315A	I _{DAC2CRT2}	Output current of IDAC2 (7 bits) in medium range	33.7		45.6	μΑ	LSB = 300-nA typ.
SID315B	I _{DAC2CRT3}	Output current of IDAC2 (7 bits) in high range	270		365	μA	LSB = 2.4-µA typ.
SID315C	I _{DAC2CRT12}	Output current of IDAC2 (7 bits) in low range, 2X mode	8		11.4	μA	LSB = 37.5-nA typ. 2X output stage
SID315D	I _{DAC2CRT22}	Output current of IDAC2(7 bits) in medium range, 2X mode	67		91	μA	LSB = 300-nA typ. 2X output stage
SID315E	I _{DAC2CRT32}	Output current of IDAC2(7 bits) in high range, 2X mode. V _{DDA} > 2V	540		730	μA	LSB = 2.4-µA typ. 2X output stage
SID315F	I _{DAC3CRT13}	Output current of IDAC in 8-bit mode in low range	8		11.4	μA	LSB = 37.5-nA typ.
SID315G	I _{DAC3CRT23}	Output current of IDAC in 8-bit mode in medium range	67		91	μA	LSB = 300-nA typ.
SID315H	I _{DAC3CRT33}	Output current of IDAC in 8-bit mode in high range. V _{DDA} > 2V	540		730	μA	LSB = 2.4-µA typ.

Document Number: 002-18787 Rev. *H



Table 21. CapSense Sigma-Delta (CSD) Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID320	I _{DACOFFSET}	All zeroes input	-	-	1	LSB	Polarity set by Source or Sink
SID321	I _{DACGAIN}	Full-scale error less offset	_	_	±15	%	LSB = 2.4-µA typ.
SID322	I _{DACMISMATCH1}	Mismatch between IDAC1 and IDAC2 in Low mode	_	-	9.2	LSB	LSB = 37.5-nA typ.
SID322A	I _{DACMISMATCH2}	Mismatch between IDAC1 and IDAC2 in Medium mode	-	_	6	LSB	LSB = 300-nA typ.
SID322B	I _{DACMISMATCH3}	Mismatch between IDAC1 and IDAC2 in High mode	-	_	5.8	LSB	LSB = 2.4-µA typ.
SID323	I _{DACSET8}	Settling time to 0.5 LSB for 8-bit IDAC	_	_	10	μs	Full-scale transition. No external load.
SID324	I _{DACSET7}	Settling time to 0.5 LSB for 7-bit IDAC	-	_	10	μs	Full-scale transition. No external load.
SID325	CMOD	External modulator capacitor.	_	2.2	-	nF	5-V rating, X7R or NP0 cap.

Table 22. CSD ADC Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
CSDv2 AD	C Specifications					•	
SIDA94	A_RES	Resolution	_	_	10	bits	Auto-zeroing is required every milli- second
SID95	A_CHNLS_S	Number of channels - single ended	-	-	-	16	-
SIDA97	A-MONO	Monotonicity	_	_	Yes	_	V _{REF} mode
SIDA98	A_GAINERR_VREF	Gain error	-	0.6	-	%	Reference Source: SRSS $(V_{REF} = 1.20 \text{ V}, V_{DDA} < 2.2 \text{ V}), (V_{REF} = 1.6 \text{ V}, 2.2 \text{ V} < V_{DDA} < 2.7 \text{ V}), (V_{REF} = 2.13 \text{ V}, V_{DDA} > 2.7 \text{ V})$
SIDA98A	A_GAINERR_VDDA	Gain error	_	0.2	1	%	Reference Source: SRSS ($V_{REF} = 1.20 \text{ V}, V_{DDA} < 2.2 \text{ V}$), ($V_{REF} = 1.6 \text{ V}, 2.2 \text{ V} < V_{DDA} < 2.7 \text{ V}$), ($V_{REF} = 2.13 \text{ V}, V_{DDA} > 2.7 \text{ V}$)
SIDA99	A_OFFSET_VREF	Input offset voltage	-	0.5	-	LSb	After ADC calibration, Ref. Src = SRSS, $(V_{REF} = 1.20 \text{ V}, V_{DDA} < 2.2 \text{ V}), \\ (V_{REF} = 1.6 \text{ V}, 2.2 \text{ V} < V_{DDA} < 2.7 \text{ V}), \\ (V_{REF} = 2.13 \text{ V}, V_{DDA} > 2.7 \text{ V})$
SIDA99A	A_OFFSET_VDDA	Input offset voltage	-	0.5	-	LSb	After ADC calibration, Ref. Src = SRSS, $(V_{REF} = 1.20 \text{ V}, V_{DDA} < 2.2 \text{ V}), \\ (V_{REF} = 1.6 \text{ V}, 2.2 \text{ V} < V_{DDA} < 2.7 \text{ V}), \\ (V_{REF} = 2.13 \text{ V}, V_{DDA} > 2.7 \text{ V})$
SIDA100	A_ISAR_VREF	Current consumption	_	0.3	_	mA	CSD ADC Block current
SIDA100A	A_ISAR_VDDA	Current consumption	_	0.3	-	mA	CSD ADC Block current
SIDA101	A_VINS_VREF	Input voltage range - single ended	V _{SSA}	_	V _{REF}	V	(V _{REF} = 1.20 V, V _{DDA} < 2.2 V), (V _{REF} =1.6 V, 2.2 V <v<sub>DDA < 2.7 V), (V_{REF} = 2.13 V, V_{DDA} > 2.7 V)</v<sub>

Document Number: 002-18787 Rev. *H Page 52 of 82



Table 22. CSD ADC Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SIDA101A	A_VINS_VDDA	Input voltage range - single ended	V _{SSA}	-	V_{DDA}	V	(V _{REF} = 1.20 V, V _{DDA} < 2.2 V), (V _{REF} = 1.6 V, 2.2 V <v<sub>DDA < 2.7 V), (V_{REF} = 2.13 V, V_{DDA} > 2.7 V)</v<sub>
SIDA103	A_INRES	Input charging resistance	_	15	_	kΩ	_
SIDA104	A_INCAP	Input capacitance	_	41	_	pF	_
SIDA106	A_PSRR	Power supply rejection ratio (DC)	_	60	-	dB	-
SIDA107	A_TACQ	Sample acquisition time	_	10	-	μs	Measured with 50 -Ω source impedance. 10 μs is default software driver acquisition time setting. Settling to within 0.05%.
SIDA108	A_CONV8	Conversion time for 8-bit resolution at conversion rate = Fhclk/(2"(N+2)). Clock frequency = 50 MHz.	_	25	Ι	μs	Does not include acquisition time.
SIDA108A	A_CONV10	Conversion time for 10-bit resolution at conversion rate = Fhclk/(2"(N+2)). Clock frequency = 50 MHz.	_	60	ı	μs	Does not include acquisition time.
SIDA109	A_SND_VRE	Signal-to-noise and Distortion ratio (SINAD)	_	57	-	dB	Measured with 50-Ω source impedance
SIDA109A	A_SND_VDDA	Signal-to-noise and Distortion ratio (SINAD)	_	52	-	dB	Measured with 50-Ω source impedance
SIDA111	A_INL_VREF	Integral Non Linearity. 11.6 ksps	_	_	2	LSB	Measured with 50-Ω source impedance
SIDA111A	A_INL_VDDA	Integral Non Linearity. 11.6 ksps	-	_	2	LSB	Measured with 50-Ω source impedance
SIDA112	A_DNL_VREF	Differential Non Linearity. 11.6 ksps	-	_	1	LSB	Measured with 50-Ω source impedance
SIDA112A	A_DNL_VDDA	Differential Non Linearity. 11.6 ksps	_	_	1	LSB	Measured with 50-Ω source impedance

Document Number: 002-18787 Rev. *H Page 53 of 82



Digital Peripherals

Table 23. Timer/Counter/PWM (TCPWM) Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID.TCPWM.1	I _{TCPWM1}	Block current consumption at 8 MHz	-	_	70	μA	All modes (TCPWM)
SID.TCPWM.2	I _{TCPWM2}	Block current consumption at 24 MHz	-	_	180	μA	All modes (TCPWM)
SID.TCPWM.2A	I _{TCPWM3}	Block current consumption at 50 MHz	-	_	270	μA	All modes (TCPWM)
SID.TCPWM.2B	I _{TCPWM4}	Block current consumption at 100 MHz	-	_	540	μA	All modes (TCPWM)
SID.TCPWM.3	TCPWM _{FREQ}	Operating frequency	-	_	100	MHz	Fc max = Fcpu Maximum = 100 MHz
SID.TCPWM.4	TPWM _{ENEXT}	Input Trigger Pulse Width for all Trigger Events	2 / Fc	-	-	ns	Trigger Events can be Stop, Start, Reload, Count, Capture, or Kill depending on which mode of operation is selected. Fc is counter operating frequency.
SID.TCPWM.5	TPWM _{EXT}	Output Trigger Pulse widths	1.5 / Fc	-	-	ns	Minimum possible width of Overflow, Underflow, and CC (Counter equals Compare value) trigger outputs
SID.TCPWM.5A	TC _{RES}	Resolution of Counter	1 / Fc	-	-	ns	Minimum time between successive counts
SID.TCPWM.5B	PWM _{RES}	PWM Resolution	1 / Fc	_	-	ns	Minimum pulse width of PWM Output
SID.TCPWM.5C	Q _{RES}	Quadrature inputs resolution	2 / Fc	-	_	ns	Minimum pulse width between Quadrature phase inputs. Delays from pins should be similar.

Table 24. Serial Communication Block (SCB) Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions			
Fixed I ² C	DC Specifica	tions				•				
SID149	I _{I2C1}	Block current consumption at 100 kHz	_	-	30	μA	-			
SID150	I _{I2C2}	Block current consumption at 400 kHz	_	-	80	μA	-			
SID151	I _{I2C3}	Block current consumption at 1 Mbps	_	_	180	μΑ	-			
SID152	I _{I2C4}	I2C enabled in Deep Sleep mode	_	_	1.7	μΑ	At 60 °C			
Fixed I ² C	AC Specifica	tions				•				
SID153	F _{I2C1}	Bit Rate	_	_	1	Mbps	-			
Fixed UAI	RT DC Specifi	cations								
SID160	I _{UART1}	Block current consumption at 100 kbps	_	-	30	μA	-			
SID161	I _{UART2}	Block current consumption at 1000 kbps	_	_	180	μA	-			
Fixed UAI	RT AC Specifi	cations								
SID162A	F _{UART1}	Bit Rate	_	-	3	Mbps	ULP Mode			
	F _{UART2}		_	-	8		LP Mode			
	Fixed SPI DC Specifications									
SID163	I _{SPI1}	Block current consumption at 1Mbps	_	_	220	μΑ	_			

Document Number: 002-18787 Rev. *H Page 54 of 82



Table 24. Serial Communication Block (SCB) Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID164	I _{SPI2}	Block current consumption at 4 Mbps	_	_	340	μA	_
SID165	I _{SPI3}	Block current consumption at 8 Mbps	_	_	360	μΑ	_
SID165A	I _{SP14}	Block current consumption at 25 Mbps	_	_	800	μΑ	_
Fixed SPI	AC Specifica	tions for LP Mode (1.1 V) unless noted	other	wise.			
SID166	F _{SPI}	SPI Operating Frequency Master and Externally Clocked Slave	_	_	25	MHz	14-MHz max for ULP (0.9 V) mode
SID166A	F _{SPI_IC}	SPI Slave Internally Clocked	_	_	15	MHz	5-MHz max for ULP (0.9 V) mode
SID166B	F _{SPI_EXT}	SPI Operating Frequency Master (F _{SCB} is SPI Clock)	_	_	F _{SCB} /4	MHz	F _{SCB} max is 100 MHz in LP mode, 25 MHz max in ULP mode
Fixed SPI	Master mode	AC Specifications for LP Mode (1.1 V)	unles	s note	ed otherwi	se.	
SID167	T_{DMO}	MOSI Valid after SClock driving edge	_	_	12	ns	20-ns max for ULP (0.9 V) mode
SID168	T _{DSI}	MISO Valid before SClock capturing edge	5	_	_	ns	Full clock, late MISO sampling
SID169	T _{HMO}	MOSI data hold time	0	_	_	ns	Referred to Slave capturing edge
SID169A	T _{SSELMSCK1}	SSEL Valid to first SCK Valid edge	18	_	_	ns	Referred to Master clock edge
SID169B	T _{SSELMSCK2}	SSEL Hold after last SCK Valid edge	18	_	_	ns	Referred to Master clock edge
Fixed SPI	Slave mode /	AC Specifications for LP Mode (1.1 V) ι	ınless	noted	dotherwise	Э.	
SID170	T_{DMI}	MOSI Valid before Sclock Capturing edge	5	_	_	ns	_
SID171A	T _{DSO_EXT}	MISO Valid after Sclock driving edge in Ext. Clk. mode	-	-	20	ns	35-ns max. for ULP (0.9 V) mode
SID171	T _{DSO}	MISO Valid after Sclock driving edge in Internally Clk. Mode	-	-	T _{DSO_EXT} + 3 * Tscb	ns	Tscb is Serial Comm. Block clock period.
SID171B	T _{DSO}	MISO Valid after Sclock driving edge in Internally Clk. Mode with Median filter enabled.	_	-	T _{DSO_EXT} + 4 * Tscb	ns	Tscb is Serial Comm. Block clock period.
SID172	T _{HSO}	Previous MISO data hold time	5	_	_	ns	_
SID172A	TSSEL _{SCK1}	SSEL Valid to first SCK Valid edge	65		_	ns	_
SID172B	TSSEL _{SCK2}	SSEL Hold after Last SCK Valid edge	65		_	ns	

Document Number: 002-18787 Rev. *H Page 55 of 82



LCD Specifications

Table 25. LCD Direct Drive DC Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID154	I _{LCDLOW}	Operating current in low-power mode	1	5	-	μΑ	16 × 4 small segment display at 50 Hz
SID155	C _{LCDCAP}	LCD capacitance per segment/common driver	ı	500	5000	pF	_
SID156	LCD _{OFFSET}	Long-term segment offset	_	20	_	mV	_
SID157	I _{LCDOP1}	PWM Mode current. 3.3-V bias. 8-MHz IMO. 25 °C.	_	0.6	_	mA	32 × 4 segments 50 Hz
SID158	I _{LCDOP2}	PWM Mode current. 3.3-V bias. 8-MHz IMO. 25 °C.	_	0.5	_	mA	32 × 4 segments 50 Hz

Table 26. LCD Direct Drive AC Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID159	F _{LCD}	LCD frame rate	10	50	150	Hz	_

Memory

Table 27. Flash Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions					
Flash DC	Specifications											
SID173	VPE	Erase and program voltage	1.71	_	3.6	V	_					
Flash AC	Flash AC Specifications											
SID174	T _{ROWWRITE}	Row (Block) write time (erase & program)	_	-	16	ms	Row (Block) = 512 bytes					
SID175	T _{ROWERASE}	Row erase time	_	_	11	ms	_					
SID176	T _{ROWPROGRAM}	Row program time after erase	_	_	5	ms	_					
SID178	T _{BULKERASE}	Bulk erase time (1024 KB)	_	_	11	ms	_					
SID179	T _{SECTORERASE}	Sector erase time (256 KB)	_	_	11	ms	512 rows per sector					
SID178S	T _{SSERIAE}	Sub-sector erase time	_	_	11	ms	8 rows per sub-sector					
SID179S	T _{SSWRITE}	Sub-sector write time; 1 erase plus 8 program times	_	-	51	ms	_					
SID180S	T _{SWRITE}	Sector write time; 1 erase plus 512 program times	_	-	2.6	seconds	_					
SID180	T _{DEVPROG}	Total device program time	_	_	15	seconds	_					
SID181	F _{END}	Flash Endurance	100 k	_	_	cycles	_					
SID182	F _{RET1}	Flash Retention. Ta ≤ 25 °C, 100 k P/E cycles	10	_	_	years	_					
SID182A	F _{RET2}	Flash Retention. Ta ≤ 85 °C, 10 k P/E cycles	10	_	_	years	_					
SID182B	F _{RET3}	Flash Retention. Ta ≤ 55 °C, 20 k P/E cycles	20	-	_	years	_					

Note

Document Number: 002-18787 Rev. *H Page 56 of 82

^{6.} It can take as much as 16 milliseconds to write to flash. During this time, the device should not be reset, or flash operations will be interrupted and cannot be relied on to have completed. Reset sources include the XRES pin, software resets, CPU lockup states and privilege violations, improper power supply levels, and watchdogs. Make certain that these are not inadvertently activated.



Table 27. Flash Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID256	T _{WS100}	Number of Wait states at 100 MHz	3	_	1		_
SID257	T _{WS50}	Number of Wait states at 50 MHz	2	_	-		_

System Resources

Table 28. PSoC 6 System Resources

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
Power-Or	-Reset with Bı	own-out DC Specifications					
Precise P	OR(PPOR)						
SID190	V _{FALLPPOR}	BOD trip voltage in Active and Sleep modes. V _{DDD} .	1.54	-	_	V	BOD Reset guaranteed for levels below 1.54 V
SID192	V _{FALLDPSLP}	BOD trip voltage in Deep Sleep. V _{DDD}	1.54	-	_	V	_
SID192A	V _{DDRAMP}	Maximum power supply ramp rate (any supply)	_	_	100	mV/μs	Active mode
POR with	Brown-out AC	Specification					
SID194A	V _{DDRAMP_DS}	Maximum power supply ramp rate (any supply) in Deep Sleep	-	_	10	mV/μs	BOD operation guaranteed
Voltage M	onitors DC Sp	ecifications					
SID195R	V _{HVD0}		1.18	1.23	1.27	V	_
SID195	V _{HVDI1}		1.38	1.43	1.47	V	_
SID196	V _{HVDI2}		1.57	1.63	1.68	V	_
SID197	V _{HVDI3}		1.76	1.83	1.89	V	_
SID198	V_{HVDI4}		1.95	2.03	2.1	V	_
SID199	V_{HVDI5}		2.05	2.13	2.2	V	_
SID200	V _{HVDI6}		2.15	2.23	2.3	V	_
SID201	V _{HVDI7}		2.24	2.33	2.41	V	_
SID202	V_{HVDI8}		2.34	2.43	2.51	V	_
SID203	V_{HVDI9}		2.44	2.53	2.61	V	_
SID204	V _{HVDI10}		2.53	2.63	2.72	V	_
SID205	V _{HVDI11}		2.63	2.73	2.82	V	_
SID206	V _{HVDI12}		2.73	2.83	2.92	V	_
SID207	V _{HVDI13}		2.82	2.93	3.03	V	_
SID208	V _{HVDI14}		2.92	3.03	3.13	V	_
SID209	V _{HVDI15}		3.02	3.13	3.23	V	_
SID211	LVI_IDD	Block current	_	5	15	μΑ	_
Voltage M	lonitors AC Sp	ecification					
SID212	T _{MONTRIP}	Voltage monitor trip time	_	_	170	ns	

Document Number: 002-18787 Rev. *H Page 57 of 82



SWD Interface

Table 29. SWD and Trace Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions					
SWD and	SWD and Trace Interface											
SID214	F_SWDCLK2	$1.7~V \le V_{DDD} \le 3.6~V$	-	1	25	MHz	LP mode. V _{CCD} = 1.1 V					
SID214L	F_SWDCLK2L	$1.7~V \le V_{DDD} \le 3.6~V$	-	-	12	MHz	ULP mode. V _{CCD} = 0.9 V.					
SID215	T_SWDI_SETUP	T = 1/f SWDCLK	0.25 * T	_	_	ns	_					
SID216	T_SWDI_HOLD	T = 1/f SWDCLK	0.25 * T	1	-	ns	_					
SID217	T_SWDO_VALID	T = 1/f SWDCLK	-	1	0.5 * T	ns	_					
SID217A	T_SWDO_HOLD	T = 1/f SWDCLK	1	1	-	ns	_					
SID214T	F_TRCLK_LP1	With Trace Data setup/hold times of 2/1 ns respectively	-	-	75	MHz	LP Mode. V _{DD} = 1.1 V					
SID215T	F_TRCLK_LP2	With Trace Data setup/hold times of 3/2 ns respectively	-	1	70	MHz	LP Mode. V _{DD} = 1.1 V					
SID216T	F_TRCLK_ULP	With Trace Data setup/hold times of 3/2 ns respectively	_	_	25	MHz	ULP Mode. V _{DD} = 0.9 V					

Internal Main Oscillator

Table 30. IMO DC Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID218	I _{IMO1}	IMO operating current at 8 MHz	_	9	15	μΑ	_

Table 31. IMO AC Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID223	F _{IMOTOL1}	Frequency variation centered on 8 MHz	-	-	±2	%	_
SID227	T _{JITR}	Cycle-to-Cycle and Period jitter	-	±250	_	ps	_

Internal Low-Speed Oscillator

Table 32. ILO DC Specification

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID231	I _{ILO2}	ILO operating current at 32 kHz	_	0.3	0.7	μΑ	_

Table 33. ILO AC Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID234	T _{STARTILO1}	ILO startup time	-	-	7	μs	Startup time to 95% of final frequency
SID236	T _{LIODUTY}	ILO Duty cycle	45	50	55	%	_
SID237	F _{ILOTRIM1}	32-kHz trimmed frequency	28.8	32	36.1	kHz	

Document Number: 002-18787 Rev. *H Page 58 of 82



Crystal Oscillator Specifications

Table 34. ECO Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions				
MHz ECO	MHz ECO DC Specifications										
SID316	I _{DD_MHz}	Block operating current with Cload up to 18 pF	-	800	1600	μΑ	Max = 33 MHz, Type = 16 MHz				
MHz ECO	MHz ECO AC Specifications										
SID317	F_MHz	Crystal frequency range	4	-	35	MHz	_				
kHz ECO	DC Specification										
SID318	I _{DD_kHz}	Block operating current with 32-kHz crystal	_	0.38	1	μA	_				
SID321E	ESR32K	Equivalent Series Resistance	-	80	_	kΩ	_				
SID322E	PD32K	Drive level	-	_	1	μW	_				
kHz ECO	AC Specification										
SID319	F_kHz	32-kHz trimmed frequency	_	32.768	_	kHz	_				
SID320	Ton_kHz	Startup time	-	-	500	ms	_				
SID320E	F _{TOL32K}	Frequency tolerance	-	50	250	ppm	_				

External Clock Specifications

Table 35. External Clock Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID305	EXTCLK _{FREQ}	External Clock input Frequency	0	1	100	MHz	_
SID306	EXTCLK _{DUTY}	Duty cycle; Measured at V _{DD/2}	45	_	55	%	_

Table 36. PLL Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID305P	PLL_LOCK	Time to achieve PLL Lock	-	16	35	μs	_
SID306P	PLL_OUT	Output frequency from PLL Block	-	1	150	MHz	_
SID307P	PLL_IDD	PLL Current	-	0.55	1.1	mA	Typ at 100 MHz out.
SID308P	PLL_JTR	Period Jitter	_	_	150	ps	100-MHz output frequency

Table 37. Clock Source Switching Time

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID262	TCLK _{SWITCH}	Clock switching from clk1 to clk2 in clock periods	1	ı	4 clk1 + 3 clk2	periods	_

Document Number: 002-18787 Rev. *H Page 59 of 82



Table 38. Frequency Locked Loop (FLL) Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions				
Frequency	Frequency Locked Loop (FLL) Specifications										
SID450	FLL_RANGE	Input frequency range.	0.001	1	100	MHz	Lower limit allows lock to USB SOF signal (1 kHz). Upper limit is for External input.				
SID451	FLL_OUT_DIV2	Output frequency range. V _{CCD} = 1.1 V	24.00	-	100.00	MHz	Output range of FLL divided-by-2 output				
SID451A	FLL_OUT_DIV2	Output frequency range. V _{CCD} = 0.9 V	24.00	-	50.00	MHz	Output range of FLL divided-by-2 output				
SID452	FLL_DUTY_DIV2	Divided-by-2 output; High or Low	47.00	-	53.00	%	_				
SID454	FLL_WAKEUP	Time from stable input clock to 1% of final value on deep sleep wakeup	_	-	7.50	μs	With IMO input, less than 10 °C change in temperature while in Deep Sleep, and Fout ≥ 50 MHz.				
SID455	FLL_JITTER	Period jitter (1 sigma at 100 MHz)	-	_	35.00	ps	50 ps at 48 MHz, 35 ps at 100 MHz				
SID456	FLL_CURRENT	CCO + Logic current	_	_	5.50	μΑ/MHz	_				

Table 39. UDB AC Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions				
Data Path I	Data Path Performance										
SID249	F _{MAX-TIMER}	Max frequency of 16-bit timer in a UDB pair	-	_	100	MHz	_				
SID250	F _{MAX-ADDER}	Max frequency of 16-bit adder in a UDB pair	_	-	100	MHz	_				
SID251	F _{MAX_CRC}	Max frequency of 16-bit CRC/PRS in a UDB pair	_	-	100	MHz	_				
PLD Perfor	rmance in UDB										
SID252	F _{MAX_PLD}	Max frequency of 2-pass PLD function in a UDB pair	-	_	100	MHz	_				
Clock to O	utput Performano	е									
SID253	T _{CLK_OUT_UDB1}	Prop. delay for clock in to data out	_	5	_	ns	_				
UDB Port A	Adaptor Specifica	tions									
Conditions:	10-pF load, 3-V V	_{DDIO} and V _{DDD}									
SID263	T _{LCLKDO}	LCLK to Output delay	-	-	11	ns	_				
SID264	T _{DINLCLK}	Input setup time to LCLCK rising edge	_	_	7	ns	_				
SID265	T _{DINLCLKHLD}	Input hold time from LCLK rising edge	5	_	_	ns	_				
SID266	T _{LCLKHIZ}	LCLK to Output tristated	_	-	28	ns	_				

Note

Document Number: 002-18787 Rev. *H Page 60 of 82

^{7.} The undivided output of the FLL must be a minimum of 2.5X the input frequency.



Table 39. UDB AC Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID267	T _{FLCLK}	LCLK frequency	-	_	33	MHz	_
SID268	T _{LCLKDUTY}	LCLK duty cycle (percentage high)	40%	_	60%	%	_

Table 40. USB Specifications (USB requires LP Mode 1.1-V Internal Supply)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions				
USB Block	USB Block Specifications										
SID322U	Vusb_3.3	Device supply for USB operation	3.15	-	3.6	V	USB Configured, USB Reg. bypassed				
SID323U	Vusb_3.3	Device supply for USB operation (functional operation only)	2.85	-	3.6	V	USB Configured, USB Reg. bypassed				
SID325U	lusb_config	Device supply current in Active mode	_	8	_	mA	V _{DDD} = 3.3 V				
SID328	lsub_suspend	Device supply current in Sleep mode	-	0.5	-	mA	V _{DDD} = 3.3 V, PICU wakeup				
SID329	lsub_suspend	Device supply current in Sleep mode	-	0.3	-	mA	V _{DDD} = 3.3 V, Device disconnected				
SID330U	USB_Drive_Res	USB driver impedance	28	-	44	Ω	Series resistors are on chip				
SID331U	USB_Pulldown	USB pull-down resistors in Host mode	14.25	-	24.8	kΩ	_				
SID332U	USB_Pullup_Idle	Idle mode range	900	_	1575	Ω	Bus idle				
SID333U	USB_Pullup	Active mode	1425	-	3090	Ω	Upstream device transmitting				

Table 41. QSPI Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SMIF QSPI Spe	ecifications. All	specs with 15-pF load.					
SID390Q	Fsmifclock	SMIF QSPI output clock frequency	_	_	80	MHz	LP mode (1.1 V)
SID390QU	Fsmifclocku	SMIF QSPI output clock frequency	-	-	50	MHz	ULP mode (0.9 V). Guaranteed by Char.
SID397Q	ldd_qspi	Block current in LP mode (1.1 V)	-	-	1900	μA	LP mode (1.1 V)
SID398Q	ldd_qspi_u	Block current in ULP mode (0.9 V)	-	-	590	μA	ULP mode (0.9 V)
SID391Q	Tsetup	Input data set-up time with respect to clock capturing edge	4.5	_	_	ns	_
SID392Q	Tdatahold	Input data hold time with respect to clock capturing edge	0	_	_	ns	_
SID393Q	Tdataoutvalid	Output data valid time with respect to clock falling edge	_	_	3.7	ns	7.5-ns max for ULP mode (0.9 V)
SID394Q	Tholdtime	Output data hold time with respect to clock rising edge	3	-	_	ns	_
SID395Q	Tseloutvalid	Output Select valid time with respect to clock rising edge	_	-	7.5	ns	15-ns max for ULP mode (0.9 V)
SID396Q	Tselouthold	Output Select hold time with respect to clock rising edge	0.5*Tsc lk	-	_	ns	Tsclk = Fsmifclk cycle time

Document Number: 002-18787 Rev. *H Page 61 of 82



Table 42. Audio Subsystem Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
Audio Su	osystem specific	ations		1		<u>I</u>	
PDM Spec	cifications						
SID400P	PDM_IDD1	PDM Active current, Stereo operation, 1-MHz clock	-	175	ı	μΑ	16-bit audio at 16 ksps
SID401	PDM_IDD2	PDM Active current, Stereo operation, 3-MHz clock	_	600	_	μA	24-bit audio at 48 ksps
SID402	PDM_JITTER	RMS Jitter in PDM clock	-200	-	200	ps	-
SID403	PDM_CLK	PDM Clock speed	0.384	_	3.072	MHz	-
SID403A	PDM_BLK_CLK	PDM Block input clock	1.024	_	49.152	MHz	-
SID403B	PDM_SETUP	Data input set-up time to PDM_CLK edge	10	_	_	ns	_
SID403C	PDM_HOLD	Data input hold time to PDM_CLK edge	10	-	_	ns	_
SID404	PDM_OUT	Audio sample rate	8	_	48	ksps	-
SID405	PDM_WL	Word Length	16	_	24	bits	-
SID406	PDM_SNR	Signal-to-Noise Ratio (A-weighted)	_	100	_	dB	PDM input, 20 Hz to 20 kHz BW
SID407	PDM_DR	Dynamic Range (A-weighted)	_	100	_	dB	20 Hz to 20 kHz BW, – 60 dB FS
SID408	PDM_FR	Frequency Response	-0.2	-	0.2	dB	DC to 0.45. DC Blocking filter off.
SID409	PDM_SB	Stop Band	_	0.56 6	_	f	_
SID410	PDM_SBA	Stop Band Attenuation	_	60	-	dB	-
SID411	PDM_GAIN	Adjustable Gain	-12	-	10.5	dB	PDM to PCM, 1.5 dB/step
SID412	PDM_ST	Startup time	_	48	_		WS (Word Select) cycles
I2S Speci	fications. The sa	me for LP and ULP modes unle	ss stated otherw	ise.			
SID413	I2S_WORD	Length of I2S Word	8	_	32	bits	_
SID414	12S_WS	Word Clock frequency in LP mode	-	_	192	kHz	12.288-MHz bit clock with 32-bit word
SID414M	12S_WS_U	Word Clock frequency in ULP mode	-	_	48	kHz	3.072-MHz bit clock with 32-bit word
SID414A	I2S_WS_TDM	Word Clock frequency in TDM mode for LP	_	-	48	kHz	Eight 32-bit channels
SID414X	I2S_WS_TDM_ U	Word Clock frequency in TDM mode for ULP	_	_	12	kHz	Eight 32-bit channels
I2S Slave	Mode			•			
SID430	TS_WS	WS Setup Time to the Following Rising Edge of SCK for LP Mode	5	_	-	ns	-
SID430U	TS_WS	WS Setup Time to the Following Rising Edge of SCK for ULP Mode	11	_	-	ns	-

Document Number: 002-18787 Rev. *H Page 62 of 82



Table 42. Audio Subsystem Specifications (continued)

Spec ID#	Parameter	Description Min		Тур	Max	Unit	Details / Conditions	
SID430A	TH_WS	WS Hold Time to the Following Edge of SCK	TMCLK_SOC + 5	_	_	ns	-	
SID432	TD_SDO	Delay Time of TX_SDO Transition from Edge of TX_SCK for LP mode	- (TMCLK_SOC + 25)	_	TMCLK_ SOC + 2 5	ns	Associated clock edge depends on selected polarity	
SID432U	TD_SDO	Delay Time of TX_SDO Transition from Edge of TX_SCK for ULP mode	- (TMCLK_SOC + 70)	-	TMCLK_ SOC + 7	ns	Associated clock edge depends on selected polarity	
SID433	TS_SDI	RX_SDI Setup Time to the Following Edge of RX_SCK in Lp Mode	5	-	-	ns	-	
SID433U	TS_SDI	RX_SDI Setup Time to the Following Edge of RX_SCK in ULP mode	11	_	_	ns	-	
SID434	TH_SDI	RX_SDI Hold Time to the Rising Edge of RX_SCK	TMCLK_SOC + 5	_	_	ns	-	
SID435	TSCKCY	TX/RX_SCK Bit Clock Duty Cycle	45	_	55	%	_	
I2S Maste	r Mode							
SID437	TD_WS	WS Transition Delay from Falling Edge of SCK in LP mode	-10	_	20	ns	-	
SID437U	TD_WS_U	WS Transition Delay from Falling Edge of SCK in ULP mode	-10	_	40	ns	-	
SID438	TD_SDO	SDO Transition Delay from Falling Edge of SCK in LP mode	-10	-	20	ns	-	
SID438U	TD_SDO	SDO Transition Delay from Falling Edge of SCK in ULP mode	-10	_	40	ns	-	
SID439	TS_SDI	SDI Setup Time to the Associated Edge of SCK	5	-	-	ns	Associated clock edge depends on selected polarity	
SID440	TH_SDI	SDI Hold Time to the Associated Edge of SCK	TMCLK_SOC +			ns	T is TX/RX_SCK Bit Clock period. Associated clock edge depends on selected polarity.	
SID443	TSCKCY	SCK Bit Clock Duty Cycle	45	- 55 %		_		
SID445	FMCLK_SOC	MCLK_SOC Frequency in LP mode	1.024	_	98.304	MHz	FMCLK_SOC = 8 * Bit-clock	
SID445U	FMCLK_SOC_U	MCLK_SOC Frequency in ULP mode	1.024	-	24.576	MHz	FMCLK_SOC_U = 8 * Bit-clock	
SID446	TMCLKCY	MCLK_SOC Duty Cycle	45 – 55 %		%	_		
SID447	TJITTER	MCLK_SOC Input Jitter	-100	_	100	ps	_	

Document Number: 002-18787 Rev. *H Page 63 of 82



Table 43. Smart I/O Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID420	SMIO_BYP	Smart I/O Bypass delay	_	-	2	ns	-
SID421	SMIO_LUT	Smart I/O LUT prop delay	_	TBD	_	ns	-

Table 44. BLE Subsystem Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions		
BLE Subs	ystem Specificat	tions							
RF Receiv	er Specifications	s (1 Mbps)							
SID317R	RXS,IDLE	RX Sensitivity with Ideal Transmitter	-	-95	_	dBm	Across RF Operating Frequency Range		
SID317RR	RXS,IDLE	RX Sensitivity with Ideal Trans- mitter	-	-93	_	dBm	255-byte packet length, across Frequency Range		
SID318R	RXS,DIRTY	RX Sensitivity with Dirty Transmitter	-	-92	_	dBm	RF-PHY Specification (RCV-LE/CA/01/C)		
SID319R	PRXMAX	Maximum received signal strength at < 0.1% PER	-	0	_	dBm	RF-PHY Specification (RCV-LE/CA/06/C)		
SID320R	CI1	Co-channel interference, Wanted Signal at –67 dBm and Interferer at FRX	Co-channel interference, Wanted Signal at –67 dBm and – 9 21						
SID321R	CI2	Adjacent channel interference Wanted Signal at –67 dBm and Interferer at FRX ± 1 MHz	15	dB	RF-PHY Specification (RCV-LE/CA/03/C)				
SID322R	CI3	Adjacent channel interference Wanted Signal at –67 dBm and Interferer at FRX ± 2 MHz	_	-26	-17	dB	RF-PHY Specification (RCV-LE/CA/03/C)		
SID323R	CI4	Adjacent channel interference Wanted Signal at –67 dBm and Interferer at ≥ FRX ± 3 MHz	-	-33	-27	dB	RF-PHY Specification (RCV-LE/CA/03/C)		
SID324R	CI5	Adjacent channel interference Wanted Signal at –67 dBm and Interferer at Image frequency (FIMAGE)	-	-20	– 9	dB	RF-PHY Specification (RCV-LE/CA/03/C)		
SID325R	CI6	Adjacent channel interference Wanted Signal at –67 dBm and Interferer at Image frequency (FIMAGE ± 1 MHz)	-	-28	-15	dB	RF-PHY Specification (RCV-LE/CA/03/C)		
RF Receiv	er Specifications	s (2 Mbps)							
SID326	RXS,IDLE	RX Sensitivity with Ideal Transmitter	-	-92	_	dBm	Across RF Operating Frequency Range		
SID326R	RXS,IDLE	RX Sensitivity with Ideal Transmitter	– –90 – dВm		255-byte packet length, across Frequency Range				
SID327	RXS,DIRTY	RX Sensitivity with Dirty Transmitter	-				RF-PHY Specification (RCV-LE/CA/01/C)		
SID328R	PRXMAX	Maximum received signal strength at < 0.1% PER	-	0	_	dBm	RF-PHY Specification (RCV-LE/CA/06/C)		

Document Number: 002-18787 Rev. *H Page 64 of 82



Table 44. BLE Subsystem Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID329R	CI1	Co-channel interference, Wanted Signal at –67 dBm and Interferer at FRX	_	9	21	dB	RF-PHY Specification (RCV-LE/CA/03/C)
SID330	CI2	Adjacent channel interference Wanted Signal at –67 dBm and Interferer at FRX ± 2 MHz	-	3	15	dB	RF-PHY Specification (RCV-LE/CA/03/C)
SID331	CI3	Adjacent channel interference Wanted Signal at –67 dBm and Interferer at FRX ± 4 MHz	-	-26	-17	dB	RF-PHY Specification (RCV-LE/CA/03/C)
SID332	CI4	Adjacent channel interference Wanted Signal at –67 dBm and Interferer at ≥ FRX ± 6 MHz	-	-33	-27	dB	RF-PHY Specification (RCV-LE/CA/03/C)
SID333	CI5	Adjacent channel interference Wanted Signal at –67 dBm and Interferer at Image frequency (FIMAGE)	_	-20	-9	dB	RF-PHY Specification (RCV-LE/CA/03/C)
SID334	CI6	Adjacent channel interference Wanted Signal at –67 dBm and Interferer at Image frequency (FIMAGE ± 2MHz)	_	-28	-15	dB	RF-PHY Specification (RCV-LE/CA/03/C)
RF Receiv	er Specification ((1 & 2 Mbps)					
SID338	OBB1	Out of Band Blocking Wanted Signal at –67 dBm and Interferer at F = 30–2000 MHz	-30	-27	_	dBm	RF-PHY Specification (RCV-LE/CA/04/C)
SID339	OBB2	Out of Band Blocking Wanted Signal at –67 dBm and Interferer at F = 2003–2399 MHz	-35	-27	-	dBm	RF-PHY Specification (RCV-LE/CA/04/C)
SID340	OBB3	Out of Band Blocking, Wanted Signal at –67 dBm and Interferer at F= 2484–2997MHz	-35	-27	_	dBm	RF-PHY Specification (RCV-LE/CA/04/C)
SID341	OBB4	Out of Band Blocking Wanted Signal at –67 dBm and Interferer at F= 3000–12750 MHz	-30	-27	-	dBm	RF-PHY Specification (RCV-LE/CA/04/C)
SID342	IMD	Intermodulation Performance Wanted Signal at –64 dBm and 1 Mbps BLE, 3rd, 4th and 5th offset channel	-50	_	-	dBm	RF-PHY Specification (RCV-LE/CA/05/C)
SID343	RXSE1	Receiver Spurious emission 30 MHz to 1.0 GHz	sion – – –57		dBm	100-kHz measurement bandwidth ETSI EN300 328 V2.1.1	
SID344	RXSE2	Receiver Spurious emission 1.0 GHz to 12.75 GHz	_	_	-53	dBm	1-MHz measurement bandwidth ETSI EN300 328 V2.1.1
RF Transm	itter Specifications	<u> </u>	-	_	_	_	
SID345	TXP,ACC	RF Power Accuracy	-1	_	1	dB	_
SID346	TXP,RANGE	Frequency Accuracy	-	24	_	dB	-20 dBm to +4 dBm
SID347	TXP,0dBm	Output Power, 0 dB Gain setting	_	0	_	dBm	_
SID348	TXP,MAX	Output Power, Maximum Power Setting	_	4	_	dBm	_

Document Number: 002-18787 Rev. *H Page 65 of 82



Table 44. BLE Subsystem Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions		
SID349	TXP,MIN	Output Power, Minimum Power Setting	_	-20	_	dBm	-		
SID350	F2AVG	Average Frequency deviation for 10101010 pattern	185	-	_	kHz	RF-PHY Specification (TRM-LE/CA/05/C)		
SID350R	F2AVG_2M	Average Frequency deviation for 10101010 pattern for 2 Mbps	370	_	-	kHz	RF-PHY Specification (TRM-LE/CA/05/C)		
SID351	F1AVG	Average Frequency deviation for 11110000 pattern	225	250	275	kHz	RF-PHY Specification (TRM-LE/CA/05/C)		
SID351R	F1AVG_2M	Average Frequency deviation for 11110000 pattern for 2 Mbps	450	500	550	kHz	RF-PHY Specification (TRM-LE/CA/05/C)		
SID352	EO	Eye opening = ΔF2AVG/ΔF1AVG	0.8	-	_	_	RF-PHY Specification (TRM-LE/CA/05/C)		
SID353	FTX,ACC	Frequency Accuracy	-150	-	150	kHz	RF-PHY Specification (TRM-LE/CA/06/C)		
SID354	FTX,MAXDR	Maximum Frequency Drift	-50	-	50	kHz	RF-PHY Specification (TRM-LE/CA/06/C)		
SID355	FTX,INITDR	Initial Frequency drift	-20	-	20	kHz	RF-PHY Specification (TRM-LE/CA/06/C)		
SID356	FTX,DR	Maximum Drift Rate	-20	-	20	kHz/ 50 μs	RF-PHY Specification (TRM-LE/CA/06/C)		
SID357	IBSE1	In Band Spurious Emission at 2 MHz offset (1 Mbps) In Band Spurious Emission at 4 MHz offset (2 Mbps)	_	-	-20	dBm	RF-PHY Specification (TRM-LE/CA/03/C)		
SID358	IBSE2	In Band Spurious Emission at ≥ 3 MHz offset (1 Mbps) In Band Spurious Emission at ≥ 6 MHz offset (2 Mbps)	_	-	-30	dBm	RF-PHY Specification (TRM-LE/CA/03/C)		
SID359	TXSE1	Transmitter Spurious Emissions (Averaging), < 1.0 GHz	_	-	-55.5	dBm	FCC-15.247		
SID360	TXSE2	Transmitter Spurious Emissions (Averaging), > 1.0 GHz			-41.5	dBm	FCC-15.247		
RF Curren	t Specification								
SID361	IRX1_wb	Receive Current (1 Mbps)	_	6.7	_	mA	VDD_NS = V _{DDD} = 3.3 V current with buck		
SID362	ITX1_wb_0dBm	TX Current at 0 dBm setting (1 Mbps)	_	5.7	-	mA	VDD_NS = V _{DDD} = 3.3 V current with buck		
SID363	IRX1_nb	Receive Current (1 Mbps)	-	11	-	mA	V _{DDD} current without buck		
SID364	ITX1_nb_0dBm	TX Current at 0-dBm setting (1 Mbps)	_	10	-	mA	V _{DDD} current without buck		
SID365	ITX1_nb_4dBm	TX Current at 4-dBm setting (1 Mbps)	_	13	_	mA	V _{DDD} current without buck		
SID365R	ITX1_wb_4dBm	TX Current at 4-dBm setting (1 Mbps)	_	8.5	_	mA	VDD_NS = V _{DDD} = 3.3 V current with buck		
SID366	ITX1_nb_20dBm	TX Current at –20-dBm setting (1 Mbps)	_	7	_	mA	V _{DDD} current without buck		
SID367	IRX2_wb	Receive Current (2 Mbps)	_	7	_	mA	VDD_NS = V _{DDD} = 3.3 V current with buck		

Document Number: 002-18787 Rev. *H Page 66 of 82



Table 44. BLE Subsystem Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID368	ITX2_wb_0dBm	TX Current at 0-dBm setting (2 Mbps)	_	5.7	_	mA	VDD_NS = V _{DDD} = 3.3 V current with buck
SID369	IRX2_nb	Receive Current (2 Mbps)	_	11.3	_	mA	V _{DDD} current without buck
SID370	ITX2_nb_0dBm	TX Current at 0-dBm setting (2 Mbps)	-	10	-	mA	V _{DDD} current without buck
SID371	ITX2_nb_4dBm	TX Current at 4-dBm setting (2 Mbps)	-	13	-	mA	V _{DDD} current without buck
SID371R	ITX2_wb_4dBm	TX Current at 4-dBm setting (2 Mbps)	_	8.5	_	mA	VDD_NS = V _{DDD} = 3.3 V current with buck
SID372	ITX2_nb_20dBm	TX Current at –20-dBm setting (2 Mbps)	_	7	_	mA	V _{DDD} current without buck
General Ri	F Specification						
SID373	FREQ	RF operating frequency	2400	-	2482	MHz	_
SID374	CHBW	Channel spacing	_	2	-	MHz	_
SID375	DR1	On-air Data Rate (1 Mbps)	_	1000	-	kbps	_
SID376	DR2	On-air Data Rate (2 Mbps)	_	2000	_	kbps	_
SID377	TXSUP	Transmitter Startup time	_	80	82	μs	_
SID378	RXSUP	Receiver Startup time	_	80	82	μs	_
RSSI Spec	ification						
SID379	RSSI,ACC	RSSI Accuracy	-4	_	4	dB	−95 dBm to −20 dBm measurement range
SID380	RSSI,RES	RSSI Resolution	_	1	_	dB	_
SID381	RSSI,PER	RSSI Sample Period	_	6	_	μs	_
System-Le	vel BLE Specific	ations					
SID433R	Adv_Pwr	1.28s, 32 bytes, 0 dBm	_	42	_	μW	3.3 V, Buck, w/o Deep Sleep current
SID434R	Conn_Pwr_300	300 ms, 0 byte, 0 dBm	-	70	_	μW	3.3 V, Buck, w/o Deep Sleep current
SID435R	Conn_Pwr_1S	1000 ms, 0 byte, 0 dBm	_	30	_	μW	3.3 V, Buck, w/o Deep Sleep current
SID436R	Conn_Pwr_4S	4000 ms, 0 byte, 0 dBm	-	4	_	μW	3.3 V, Buck, w/o Deep Sleep current

Table 45. ECO Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions		
16-MHz Crystal Oscillator									
SID382	FXO1	Crystal frequency	_	16	_	MHz	_		
SID383	ESR1	Equivalent series resistance	_	100	250	Ω	_		
SID384	Txostart1	Startup time	-	400	_	μs	Frequency Stable (16 MHz ±50 ppm)		
SID385	IXO1	Operating current	-	300	_	μA	Includes crystal current, LDO and BG		
32-MHz Crystal Oscillator									

Document Number: 002-18787 Rev. *H Page 67 of 82



Table 45. ECO Specifications (continued)

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID386	FXO2	Crystal frequency	_	32	1	MHz	-
SID387	ESR2	Equivalent series resistance	-	50	100	Ω	_
SID388	Txostart2	Startup time	-	400	1	μs	Frequency Stable (32 MHz ±50 ppm)
SID389	IXO2	Operating current	-	350	-	μΑ	Includes crystal current, LDO and BG
16-MHz ar	nd 32-MHz Crystal (Oscillator					
SID390	FTOL	Frequency tolerance	-20	_	20	ppm	After trimming, including aging and temp drift
SID391	PD	Drive level	_	_	100	μW	_

Table 46. Precision ILO (PILO) Specifications

Spec ID#	Parameter	Description	Min	Тур	Max	Unit	Details / Conditions
SID 430R	I _{PILO}	Operating current	1	1.2	4	μΑ	_
SID431	F_PILO	PILO nominal frequency	-	32768	1	Hz	T = 25 °C with 20-ppm crystal
SID432R	ACC_PILO	PILO accuracy with periodic calibration	-500	_	500	ppm	_

Document Number: 002-18787 Rev. *H Page 68 of 82



Ordering Information

Table 1 lists the PSoC 63 with BLE part numbers and features. The table shows Marketing Part Numbers (MPNs) for products including the BLE Radio. The packages are 104-MCSP, 68-QFN, and 116-BGA. The 124-BGA Package is in the process of qualification.

Table 47. BLE Series Part Numbers

Family	MPN	CPU Speed (M4)	CPU Speed (M0+)	Single core/Dual core	ULP/LP	Flash	SRAM	No. of CTBMs	No. of UDBs	CapSense	СКУРТО	Secure Boot	USB	GPIOs	Package
63	CY8C6336LQI-BLF02	150	-	Single	LP	512	128	0	0	No	No	No	No	41	68-QFN
	CY8C6336LQI-BLF42	150	ı	Single	LP	512	128	0	0	Yes	Yes	No	No	41	68-QFN
	CY8C6347LQI-BLD52	150/50	100/25	Double	FLEX	1024	288	1	12	Yes	Yes	Yes	No	41	68-QFN
	CY8C6336BZI-BLF03	150	ı	Single	LP	512	128	0	0	No	No	No	No	78	116-BGA
	CY8C6316BZI-BLF03	50	ı	Single	ULP	512	128	0	0	No	No	No	No	78	116-BGA
	CY8C6316BZI-BLF53	50	ı	Single	ULP	512	128	1	12	Yes	Yes	No	No	78	116-BGA
	CY8C6337BZI-BLF13	150	ı	Single	LP	1024	288	0	0	Yes	No	No	No	78	116-BGA
	CY8C6336BZI-BLD13	150	100	Double	LP	512	128	0	0	Yes	No	No	No	78	116-BGA
	CY8C6347BZI-BLD43	150/50	100/25	Double	FLEX	1024	288	0	0	Yes	Yes	Yes	No	78	116-BGA
	CY8C6347BZI-BLD33	150/50	100/25	Double	FLEX	1024	288	1	12	Yes	No	No	No	78	116-BGA
	CY8C6347BZI-BLD53	150/50	100/25	Double	FLEX	1024	288	1	12	Yes	Yes	Yes	No	78	116-BGA
	CY8C6336BZI-BLF04	150	_	Single	LP	512	128	0	0	No	No	No	Yes	84	124-BGA-BLE
	CY8C6316BZI-BLF04	50	-	Single	ULP	512	128	0	0	No	No	No	Yes	84	124-BGA-BLE
	CY8C6316BZI-BLF54	50	-	Single	ULP	512	128	1	12	Yes	Yes	No	Yes	84	124-BGA-BLE
	CY8C6337BZI-BLF14	150	1	Single	LP	1024	288	0	0	Yes	No	No	Yes	84	124-BGA-BLE
	CY8C6336BZI-BLD14	150	100	Double	LP	512	128	0	0	Yes	No	No	Yes	84	124-BGA-BLE
	CY8C6347BZI-BLD44	150/50	100/25	Double	FLEX	1024	288	0	0	Yes	Yes	Yes	Yes	84	124-BGA-BLE
	CY8C6347BZI-BLD34	150/50	100/25	Double	FLEX	1024	288	1	12	Yes	No	No	Yes	84	124-BGA-BLE
	CY8C6347BZI-BLD54	150/50	100/25	Double	FLEX	1024	288	1	12	Yes	Yes	Yes	Yes	84	124-BGA-BLE
	CY8C6347FMI-BLD13	150/50	100/25	Double	FLEX	1024	288	0	0	Yes	No	No	No	70	104-MCSP
	CY8C6347FMI-BLD43	150/50	100/25	Double	FLEX	1024	288	0	0	Yes	Yes	Yes	No	70	104-MCSP
	CY8C6347FMI-BLD33	150/50	100/25	Double	FLEX	1024	288	1	12	Yes	No	No	No	70	104-MCSP
	CY8C6347FMI-BLD53	150/50	100/25	Double	FLEX	1024	288	1	12	Yes	Yes	Yes	No	70	104-MCSP
	CY8C6347FMI-BUD13	150/50	100/25	Double	FLEX	1024	288	0	0	Yes	No	No	Yes	69	104-MCSP-USB
	CY8C6347FMI-BUD43	150/50	100/25	Double	FLEX	1024	288	0	0	Yes	Yes	Yes	Yes	69	104-MCSP-USB
	CY8C6347FMI-BUD33	150/50	100/25	Double	FLEX	1024	288	1	12	Yes	No	No	Yes	69	104-MCSP-USB
	CY8C6347FMI-BUD53	150/50	100/25	Double	FLEX	1024	288	1	12	Yes	Yes	Yes	Yes	69	104-MCSP-USB

Table 48 lists the field values.

Table 48. MPN Nomenclature

Field	Description	Values	Meaning
CY8C	Cypress Prefix		

Document Number: 002-18787 Rev. *H Page 69 of 82



Table 48. MPN Nomenclature

Field	Description	Values	Meaning
6	Architecture	6	PSoC 6
		0	Value
Α	Family	1	Programmable
A	raililly	2	Performance
		3	Connectivity
		1	50 MHz
В	Speed	2	100 MHz
Б	Speed	3	150 MHz
		4	150/50 MHz
		4	128 KB
С	Floob Consoity	5	256 KB
C	Flash Capacity	6	512 KB
		7	1024 KB
		AX	TQFP I (0.8 mm pitch)
		AZ	TQFP II (0.5 mm pitch)
D	Package Code	LQ	QFN
		BZ	BGA
		FM	M-CSP
		С	Consumer
Е	Temperature Range	I	Industrial
		Q	Extended Industrial (105 °C)
		N/A	PSoC 6A
		S	PSoC 6A-S (Example)
F	Silicon Family	М	PSoC 6A-M (Example)
		L	PSoC 6A-L (Example)
		BL	PSoC 6A-BLE
		Z	M0+
G	Core	F	M4
		D	Dual-Core M4/M0+
XY	Attributes Code	00–99	Code of feature set in the specific family
ES	Engineering sample	ES	Engineering samples or not
Т	Tape/Reel Shipment	Т	Tape and Reel shipment or not

Document Number: 002-18787 Rev. *H Page 70 of 82



Packaging

PSoC 63 with BLE will be offered in four packages: 116-BGA, 124-BGA, 68-QFN, and 104-MCSP. The 124-BGA package is in the process of qualification.

Table 49. Package Dimensions

Spec ID#	Package	Description	Package Drawing Number
PKG_1	124-BGA	124-BGA, $9 \times 9 \times 1$ mm height with 0.65-mm pitch	001-97718
PKG_2	104-MCSP	104-MCSP, $3.8 \times 5 \times 0.65$ mm height with 0.35-mm pitch	002-16508
PKG_4	116-BGA	116-BGA, $5.2 \times 6.4 \times 0.70$ mm height with 0.5-mm pitch	002-16574
PKG_5	68-QFN	68-QFN, $8 \times 8 \times 1$ mm height with 0.4-mm pitch	001-96836

Table 50. Package Characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
T _A	Operating ambient temperature	-	-40	25.00	85	°C
TJ	Operating junction temperature	-	-40	_	100	°C
T_{JA}	Package θ _{JA} (116-BGA)	-	_	36	_	°C/watt
T_JC	Package θ _{JC} (116-BGA)	-	_	12	_	°C/watt
T_{JA}	Package θ _{JA} (124-BGA)	-	_	36	_	°C/watt
T_JC	Package θ _{JC} (124-BGA)	-	_	15	_	°C/watt
T_{JA}	Package θ _{JA} (104-CSP)	-	_	34	_	°C/watt
T_{JA}	Package θ _{JA} (68-QFN)	-	_	26.2	_	°C/watt
T_{JC}	Package θ _{JC} (68-QFN)	_	_	7.2	_	°C/watt

Table 51. Solder Reflow Peak Temperature

Package	Maximum Peak Temperature	Maximum Time at Peak Temperature
124-BGA, 116-BGA, and 68-QFN	260 °C	30 seconds
104-MCSP	260 °C	30 seconds


Table 52. Package Moisture Sensitivity Level (MSL), IPC/JEDEC J-STD-2


Package	MSL
124-BGA, 116-BGA, and 68-QFN	MSL 3
104-MCSP	MSL 1

Document Number: 002-18787 Rev. *H Page 71 of 82



Figure 9. 104-WLCSP $3.8 \times 5.0 \times 0.65$ mm





SIDE VIEW

0.225+0.03	9 8 7 6 5 4 3 2 1	%b [104X]
	-00000000	A
j '	000000000	В
	000000000	С
<u>6</u>	00000000	D
	00000000	Ε
	00000000	F
	<u>— 0000ф0000 </u>	G -
	—•••••••• • •	н
	0000φ000+	J
됩	+ + + + + 0000	к
	0 + + + + + + + + + + + + + + + + + + +	L
	O + + + 00000	M N
	0 + + + + + + 00	P
F		
03		
0.225+0.03	0.521 ^{+0.03}	0.521+0.03
0.2	D1	
	BOTTOM VIEW	
	BOTTOW VIEW	

		DIMENSIONS	
SYMBOL	MIN.	NOM.	MAX.
Α	-	-	0.650
A1	0.167	0.185	0.203
D	3.791	3.841	3.891
E.	4.95	5.00	5.05
D1	2.80 BSC		
E1	4.55 BSC		
MD	9		
ME		14	
N		104	
Øь	0.215	0.245	0.275
eD	0.335	0.350	0.365
еE	0.335	0.350	0.365
SD	0.35 BSC		
SF	0.175 BSC		

NOTES

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SOLDER BALL POSITION DESIGNATION PER JEP95, SECTION 3, SPP-020.
- 3. "e" REPRESENTS THE SOLDER BALL GRID PITCH.
- SYMBOL "MD" IS THE BALL MATRIX SIZE IN THE "D" DIRECTION.
 SYMBOL "ME" IS THE BALL MATRIX SIZE IN THE "E" DIRECTION.
 N IS THE NUMBER OF POPULATED SOLDER BALL POSITIONS FOR MATRIX
 SIZE MD X ME.

⚠ DIMENSION "b" IS MEASURED AT THE MAXIMUM BALL DIAMETER IN A PLANE PARALLEL TO DATUM C.

SD" AND "SE" ARE MEASURED WITH RESPECT TO DATUMS A AND B AND DEFINE THE POSITION OF THE CENTER SOLDER BALL IN THE OUTER ROW.

WHEN THERE IS AN ODD NUMBER OF SOLDER BALLS IN THE OUTER ROW,

"SD" OR "SE" = 0.

WHEN THERE IS AN EVEN NUMBER OF SOLDER BALLS IN THE OUTER ROW, "SD" = eD/2 AND "SE" = eE/2.

A1 CORNER TO BE IDENTIFIED BY CHAMFER, LASER OR INK MARK METALIZED MARK, INDENTATION OR OTHER MEANS.

- 8. "+" INDICATES THE THEORETICAL CENTER OF DEPOPULATED SOLDER

 BALLS
- 9. JEDEC SPECIFICATION NO. REF. : N/A.

002-16508 *E

Document Number: 002-18787 Rev. *H Page 72 of 82





2X 0.10 C
A1 CORNER


D
A B
A1 CORNER

E
O.10 C 2X

TOP VIEW







	DIMENSIONS			
SYMBOL	MIN.	NOM.	MAX.	
А	-	-	0.70	
A1	0.16	0.21	0.26	
D		5.20 BSC		
E		6.40 BSC		
D1	4.50 BSC			
E1	5.50 BSC			
MD	10			
ME	12			
N		116		
Ø b	0.25	0.30	0.35	
eD	0.50 BSC			
eE	0.50 BSC			
SD	0.25 BSC			
SE	0.25 BSC			

NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SOLDER BALL POSITION DESIGNATION PER JEP95, SECTION 3, SPP-020.
- 3. "e" REPRESENTS THE SOLDER BALL GRID PITCH.
- 4. SYMBOL "MD" IS THE BALL MATRIX SIZE IN THE "D" DIRECTION.

 SYMBOL "ME" IS THE BALL MATRIX SIZE IN THE "E" DIRECTION.

 N IS THE NUMBER OF POPULATED SOLDER BALL POSITIONS FOR MATRIX SIZE MD X ME.
- (\$\timesion "b" is measured at the maximum ball diameter in a plane parallel to datum c.
- - WHEN THERE IS AN EVEN NUMBER OF SOLDER BALLS IN THE OUTER ROW, "SD" = eD/2 AND "SE" = eE/2.
- 1 CORNER TO BE IDENTIFIED BY CHAMFER, LASER OR INK MARK METALIZED MARK, INDENTATION OR OTHER MEANS.
- 8. "+" INDICATES THE THEORETICAL CENTER OF DEPOPULATED SOLDER BALLS.
- 9. JEDEC SPECIFICATION NO. REF: N/A

002-16574 *B

Document Number: 002-18787 Rev. *H Page 73 of 82



□0.08|C| В – (datum B) Α A1 BALL 1 2 3 4 5 6 7 8 9 10 11 12 13 CORNER ဓဝဝဝ်ဝဝ PIN A1 CORNER В 000000000000 С 0000000000000 D Ε SD G D1 Н J (datum A) Κ 0000++ ++0000 K L 000000000000 L М 0000000000000 000000000000 N еE SIDE VIEW **TOP VIEW BOTTOM VIEW**

Figure 11. 124-BGA 9.0 × 9.0 × 1.0 mm

CVMPOL		DIMENSIONS		
SYMBOL	MIN.	NOM.	MAX.	
Α	-	-	1.00	
A1	0.16	0.21	0.26	
D	8.90	9.00	9.10	
E	8.90	9.00	9.10	
D1	7.80 BSC			
E1		7.80 BSC		
MD	13			
ME		13		
N		124		
Øb	0.25	0.30	0.35	
eD	0.65 BSC			
eE	0.65 BSC			
SD	0			
SE	0			

NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SOLDER BALL POSITION DESIGNATION PER JEP95, SECTION 3, SPP-020.
- 3. "e" REPRESENTS THE SOLDER BALL GRID PITCH.
- 4. SYMBOL "MD" IS THE BALL MATRIX SIZE IN THE "D" DIRECTION.

 SYMBOL "ME" IS THE BALL MATRIX SIZE IN THE "E" DIRECTION.

 N IS THE NUMBER OF POPULATED SOLDER BALL POSITIONS FOR MATRIX SIZE MD X MF.
- DIMENSION "b" IS MEASURED AT THE MAXIMUM BALL DIAMETER IN A PLANE PARALLEL TO DATUM C.
- "SD" AND "SE" ARE MEASURED WITH RESPECT TO DATUMS A AND B AND DEFINE THE POSITION OF THE CENTER SOLDER BALL IN THE OUTER ROW.

 WHEN THERE IS AN ODD NUMBER OF SOLDER BALLS IN THE OUTER ROW
 "SD" OR "SE" = 0.

WHEN THERE IS AN EVEN NUMBER OF SOLDER BALLS IN THE OUTER ROW, "SD" = eD/2 AND "SE" = eE/2.


- A1 CORNER TO BE IDENTIFIED BY CHAMFER, LASER OR INK MARK METALIZED MARK, INDENTATION OR OTHER MEANS.
- 8. "+" INDICATES THE THEORETICAL CENTER OF DEPOPULATED SOLDER BALLS.
- 9. JEDEC SPECIFICATION NO. REF.: MO-280.

001-97718 *B

Document Number: 002-18787 Rev. *H Page 74 of 82



Figure 12. 68 QFN 8 × 8 × 1 mm



NOTES:

- 1. MATCH AREA IS SOLDERABLE EXPOSED METAL.
- 2. REFERENCE JEDEC#: MO-220
- 3. ALL DIMENSIONS ARE IN MILLIMETERS

001-96836 *A



Acronyms

Acronym	Description
3DES	triple DES (data encryption standard)
ADC	analog-to-digital converter
AES	advanced encryption standard
АНВ	AMBA (advanced microcontroller bus architecture) high-performance bus, an Arm data transfer bus
AMUX	analog multiplexer
AMUXBUS	analog multiplexer bus
API	application programming interface
Arm [®]	advanced RISC machine, a CPU architecture
BGA	ball grid array
BOD	brown-out detect
CAD	computer aided design
cco	current controlled oscillator
CM0+	Cortex-M0+, an Arm CPU
CM4	Cortex-M4, an Arm CPU
CMAC	cipher-based message authentication code
CMOS	complementary metal-oxide-semiconductor, a process technology for IC fabrication
CMRR	common-mode rejection ratio
CPU	central processing unit
CRC	cyclic redundancy check, an error-checking protocol
CSD	CapSense Sigma-Delta
csx	Cypress mutual capacitance sensing method. See also CSD
DAC	digital-to-analog converter, see also IDAC, VDAC
DAP	debug access port
DES	data encryption standard
DMA	direct memory access, see also TD
DNL	differential nonlinearity, see also INL
DSI	digital system interconnect
DU	data unit
ECC	elliptic curve cryptography
ECO	external crystal oscillator
EEPROM	electrically erasable programmable read-only memory
EMI	electromagnetic interference
ESD	electrostatic discharge
ETM	embedded trace macrocell
FIFO	first-in, first-out
FLL	frequency locked loop
FPU	floating-point unit

Acronym	Description
FS	full-speed
GND	Ground
GPIO	general-purpose input/output, applies to a PSoC pin
HMAC	Hash-based message authentication code
HSIOM	high-speed I/O matrix
I/O	input/output, see also GPIO, DIO, SIO, USBIO
I ² C, or IIC	Inter-Integrated Circuit, a communications protocol
l ² S	inter-IC sound
IC	integrated circuit
IDAC	current DAC, see also DAC, VDAC
IDE	integrated development environment
ILO	internal low-speed oscillator, see also IMO
IMO	internal main oscillator, see also ILO
INL	integral nonlinearity, see also DNL
IoT	internet of things
IPC	inter-processor communication
IRQ	interrupt request
ISR	interrupt service routine
JTAG	Joint Test Action Group
LCD	liquid crystal display
LIN	Local Interconnect Network, a communications protocol
LP	low power
LS	low-speed
LUT	lookup table
LVD	low-voltage detect, see also LVI
LVTTL	low-voltage transistor-transistor logic
MAC	multiply-accumulate
MCU	microcontroller unit
MISO	master-in slave-out
MMIO	memory-mapped input output
MOSI	master-out slave-in
MPU	memory protection unit
MSL	moisture sensitivity level
Msps	million samples per second
MTB	micro trace buffer
MUL	multiplier
NC	no connect
NMI	nonmaskable interrupt
NVIC	nested vectored interrupt controller
OTP	one-time programmable
OVT	overvoltage tolerant

Document Number: 002-18787 Rev. *H Page 76 of 82



Acronym	Description		
PASS	programmable analog subsystem		
PCB	printed circuit board		
PCM	pulse code modulation		
PDM	pulse density modulation		
PHY	physical layer		
PICU	port interrupt control unit		
PLL	phase-locked loop		
PMIC	power management integrated circuit		
POR	power-on reset		
PPU	peripheral protection unit		
PRNG	pseudo random number generator		
PSoC [®]	Programmable System-on-Chip™		
PSRR	power supply rejection ratio		
PWM	pulse-width modulator		
QD	quadrature decoder		
QSPI	quad serial peripheral interface		
RAM	random-access memory		
RISC	reduced-instruction-set computing		
RMS	root-mean-square		
ROM	read-only memory		
RSA	Rivest–Shamir–Adleman, a public-key cryptography algorithm		
RTC	real-time clock		
RX	receive		
S/H	sample and hold		
SAR	successive approximation register		
SARMUX	SAR ADC multiplexer bus		
SCB	serial communication block		
Sflash	supervisory flash		
SHA	secure hash algorithm		
SINAD	signal to noise and distortion ratio		
SNR	signal-to-noise ration		
SOF	start of frame		
SPI	Serial Peripheral Interface, a communications protocol		
SRAM	static random access memory		
SROM	supervisory read-only memory		
SRSS	system resources subsystem		
SWD	serial wire debug, a test protocol		
SWJ	serial wire JTAG		
swo	single wire output		
SWV	serial-wire viewer		
TCPWM	timer, counter, pulse-width modulator		
TDM	time division multiplexed		

Acronym	Description			
TQFP	thin quad flat package			
TRM	technical reference manual			
TRNG	true random number generator			
TX	transmit			
UART Universal Asynchronous Transmitter Receive communications protocol				
ULP	ultra-low power			
USB	Universal Serial Bus			
WCO	watch crystal oscillator			
WDT	watchdog timer			
WIC	wakeup interrupt controller			
WLCSP	wafer level chip scale package			
XIP	execute-in-place			
XRES	external reset input pin			

Document Number: 002-18787 Rev. *H Page 77 of 82



Document Conventions

Unit of Measure

Table 53. Unit of Measure

Symbol	Unit of Measure		
°C	degrees Celsius		
dB	decibel		
fF	femto farad		
Hz	hertz		
KB	1024 bytes		
kbps	kilobits per second		
khr	kilohour		
kHz	kilohertz		
kΩ	kilo ohm		
ksps	kilosamples per second		
LSB	least significant bit		
Mbps	megabits per second		
MHz	megahertz		
ΜΩ	mega-ohm		
Msps	megasamples per second		
μA	microampere		
μF	microfarad		

Table 53. Unit of Measure (continued)

Symbol	Unit of Measure		
μΗ	microhenry		
μs	microsecond		
μV	microvolt		
μW	microwatt		
mA	milliampere		
ms	millisecond		
mV	millivolt		
nA	nanoampere		
ns	nanosecond		
nV	nanovolt		
Ω	ohm		
pF	picofarad		
ppm	parts per million		
ps	picosecond		
s	second		
sps	samples per second		
sqrtHz	square root of hertz		
V	volt		

Document Number: 002-18787 Rev. *H Page 78 of 82



Errata

This section describes the errata for the PSoC 6 63 Product Family. Details include errata trigger conditions, scope of impact, available workarounds, and silicon revision applicability. Compare this document to the device's data sheet for a complete functional description. Contact your local Cypress Sales Representative if you have questions.

Part Numbers Affected

Part Number	Device Characteristics
CY8C6XX	PSoC 6 63 Product Family

PSoC 6 63 Qualification Status

Production

PSoC 6 63 Errata Summary

Noise is caused in supply and ground traces when multiple outputs switch. The amount of noise is dependent on the number of outputs, the drive strength of the output drivers, the frequency of the switching, and the impact on specific ports. The noise is worse at higher voltages ($V_{DD} = 2.7 \text{ V}$ and higher) and should not be an issue with 1.8 V externally regulated (that is, $V_{DD} = 1.8 \text{ V} \pm 5\%$) designs.

For cases where there are large numbers of GPIOs switching simultaneously, the following errata conditions are applicable. Note that the exact number cannot be specified as there are too many system-dependent conditions.

This table defines the errata applicability to available PSoC 63 family devices.

Items	CY8C6XX 63	Silicon Revision	Fix Status
[1] Drive mode strength must be limited.	All	*C silicon	Investigation underway. Fix planned by Q2'19
[2] CapSense use is restricted to Ports 6 and 7 with switching restrictions on other ports.	All	*C silicon	Investigation underway. Fix planned by Q2'19
[3] Switching noise can cause ADC errors due to voltage reference noise.	All	*C silicon	Investigation underway. Fix planned by Q2'19
[4] Port Usage restrictions must be applied.	All	*C silicon	Investigation underway. Fix planned by Q2'19

1. Drive mode strength must be limited.			
	There are four Drive mode strengths: DM0, DM1, DM2, and DM3, DM0 being the strongest and DM3 the weakest in order. Usage of DM0 can cause noise in supply and ground lines for simultaneous outputs switching. Drive mode strength must be limited to DM2 for all GPIOs except for the 80 MHz QSPI clock which may use DM1.		
Problem Definition	The V_{OL} and V_{OH} specs are affected as follows (also applies to V_{DDIO} , V_{DDIOA} , and V_{DDA} pins): $V_{DD} < 2.7 \text{ V}$:		
	$V_{OL} = 0.5 \text{ V} @ I_{OL} = 6 \text{ mA}. V_{OH} = V_{DD} - 0.5 \text{ V}, I_{OH} = 6 \text{ mA}.$		
	$V_{DD} \ge 2.7 \text{ V}$:		
	$V_{OL} = 0.4 @ I_{OL} = 6 \text{ mA. } V_{OH} = V_{DD} - 0.5 \text{ V}, I_{OH} = 6 \text{ mA.}$		
Parameters Affected	Drive mode settings.		
Trigger Condition(s)	Simultaneous outputs switching with high drive strength		
Scope of Impact	Causes supply and ground noise, which can affect ADC and CapSense operation		
Workaround Follow drive mode strength restrictions. Drive Mode 2 (DM2) should be used for all ports except for the QSPI clock, which should be DM1			
Fix Status	x Status Investigation underway. Fix planned by Q2'19.		

Document Number: 002-18787 Rev. *H Page 79 of 82



2. CapSense use is restricted to Ports 6 and 7 with switching restrictions on other ports.			
Problem Definition	GPIO simultaneous switching creates noise which can affect CapSense accuracy in unrestricted use		
Parameters Affected	CapSense sensitivity and accuracy		
Trigger Condition(s)	Noise caused by GPIO simultaneous output switching during CapSense operation		
Scope of Impact CapSense may produce erroneous results due to noise coupling from switching GPIOs.			
Workaround	For CapSense usage, the following restrictions apply: a. Limit switching on Port 1 to 1 MHz (no more than 2 outputs) with slow slew rate. b. CapSense pins are restricted to Ports 6 and 7. No other GPIO output activity is allowed on Ports 6 and 7. c. Switching in Ports 5 and 8 is restricted to 1 MHz (no more than 2 outputs) with slow slew rate setting. CapSense must use the SRSS reference.		
Fix Status	Investigation underway. Fix planned by Q2'19.		

3. Switching noise can cause ADC errors due to voltage reference noise.			
Problem Definition	Definition 12-bit SAR ADC Counts are affected by switching noise		
Parameters Affected	meters Affected ADC accuracy		
Trigger Condition(s) Switching noise caused by GPIO simultaneous switching			
Scope of Impact	ADC accuracy will be impacted		
Workaround	Restrict switching on Ports 9 and 10 (analog input ports). The Programmable Analog Sub-System (PASS), including the SAR ADC, is connected to Ports 9 and 10. With no switching on Ports 9 and 10, the ADC error may be up to 4 LSB counts. Switching in Ports 9 and 10 is restricted to 1 MHz (no more than 2 outputs) with slow slew rate setting and, in this case, the ADC error may be up to 12 counts.		
Fix Status	Investigation underway; Fix planned by Q2 19.		

4. Port Usage restrictions must be applied.			
Problem Definition	GPIO simultaneous switching causes supply and ground noise that adversely affects other on-chip subsystems).		
Parameters Affected	CapSense and ADC results		
Trigger Condition(s)	GPIO simultaneous switching with unrestricted strengths and frequency.		
Scope of Impact Incorrect results may cause false sensing or failure to sense for CapSense and inaccurate results may not deliver 12-bit accuracy).			
	Follow Port Usage restrictions:		
	a. Switching on Port 0 must be restricted to less than 8 MHz.		
Workaround	b. Switching on Port 1 must be restricted to less than 1 MHz with slow rate and no more than 2 outputs.		
	c. Ports 9 and 10 must be restricted to 8 MHz when not using the ADC and the restrictions stated earlier used when the ADC is used.		
	d. Use VREF from System Resource Subsystem (SRSS) for CapSense		
Fix Status	Investigation underway. Fix planned by Q2'19.		

Document Number: 002-18787 Rev. *H Page 80 of 82



Revision History

Description Title: PSoC [®] 6 MCU: PSoC 63 with BLE Datasheet Programmable System-on-Chip (PSoC [®]) Document Number: 002-18787					
Revision	ECN	Orig. of Change	Submission Date	Description of Change	
*F	6164322	WKA	05/03/2018	Release of production datasheet.	
*G	6250376	WKA	07/17/2018	Corrected document number in the revision history table.	
*H	6522270	WKA	04/01/2019	Updated Functional Description. Added "Pinouts for 104-MCSP with USB" table in Pinouts. Added package diagram (spec 001-97718 *B). Added a note in Table 4. Updated Table 11, Table 24, and Table 34 in Electrical Specifications.	

Document Number: 002-18787 Rev. *H Page 81 of 82

PSoC® 6 MCU: PSoC 63 with BLE Datasheet

Sales, Solutions, and Legal Information

Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at Cypress Locations.

Products

Arm® Cortex® Microcontrollers cypress.com/arm Automotive cypress.com/automotive Clocks & Buffers cypress.com/clocks Interface cypress.com/interface Internet of Things cypress.com/iot Memory cypress.com/memory Microcontrollers cypress.com/mcu **PSoC** cypress.com/psoc

Power Management ICs cypress.com/pmic Touch Sensing cypress.com/touch cypress.com/usb **USB Controllers** Wireless Connectivity cypress.com/wireless

PSoC® Solutions

PSoC 1 | PSoC 3 | PSoC 4 | PSoC 5LP | PSoC 6 MCU

Cypress Developer Community

Community | Projects | Video | Blogs | Training | Components

Technical Support

cypress.com/support

© Cypress Semiconductor Corporation, 2018-2019. This document is the property of Cypress Semiconductor Corporation and its subsidiaries ("Cypress"). This document, including any software or firmware included or referenced in this document ("Software"), is owned by Cypress under the intellectual property laws and treaties of the United States and other countries worldwide. Cypress reserves all rights under such laws and treaties and does not, except as specifically stated in this paragraph, grant any license under its patents, copyrights, trademarks, or other intellectual property rights. If the Software is not accompanied by a license agreement and you do not otherwise have a written agreement with Cypress governing the use of the Software, then Cypress hereby grants you a personal, non-exclusive, nontransferable license (without the right to sublicense) (1) under its copyright rights in the Software (a) for Software provided in source code form, to modify and reproduce the Software solely for use with Cypress hardware products, only internally within your organization, and (b) to distribute the Software in binary code form externally to end users (either directly or indirectly through resellers and distributors), solely for use on Cypress hardware product units, and (2) under those claims of Cypress's patents that are infringed by the Software (as provided by Cypress, unmodified) to make, use, distribute, and import the Software solely for use with Cypress hardware products. Any other use, reproduction, modification, translation, or compilation of the Software is prohibited.

TO THE EXTENT PERMITTED BY APPLICABLE LAW, CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS DOCUMENT OR ANY SOFTWARE OR ACCOMPANYING HARDWARE, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. No computing device can be absolutely secure. Therefore, despite security measures implemented in Cypress hardware or software products, Cypress shall have no liability arising out of any security breach, such as unauthorized access to or use of a Cypress product. CYPRESS DOES NOT REPRESENT, WARRANT, OR GUARANTEE THAT CYPRESS PRODUCTS, OR SYSTEMS CREATED USING CYPRESS PRODUCTS, WILL BE FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATALOSS OR THEFT, OR OTHER SECURITY INTRUSION (collectively, "Security Breach"). Cypress disclaims any liability relating to any Security Breach, and you shall and hereby do release Cypress from any claim, damage, or other liability arising from any Security Breach. In addition, the products described in these materials may contain design defects or errors known as errata which may cause the product to deviate from published specifications. To the extent permitted by applicable law, Cypress reserves the right to make changes to this document without further notice. Cypress does not assume any liability arising out of the application or use of any product or circuit described in this document. Any information provided in this document, including any sample design information or programming code, is provided only for reference purposes. It is the responsibility of the user of this document to properly design, program, and test the functionality and safety of any application made of this information and any resulting product. "High-Risk Device" means any device or system whose failure could cause personal injury, death, or property damage. Examples of High-Risk Devices are weapons, nuclear installations, surgical implants, and other medical devices. "Critical Component" means any component of a High-Risk Device whose failure to perform can be reasonably expected to cause, directly or indirectly, the failure of the High-Risk Device, or to affect its safety or effectiveness. Cypress is not liable, in whole or in part, and you shall and hereby do release Cypress from any claim, damage, or other liability arising from any use of a Cypress product as a Critical Component in a High-Risk Device. You shall indemnify and hold Cypress, its directors, officers, employees, agents, affiliates, distributors, and assigns harmless from and against all claims, costs, damages, and expenses, arising out of any claim, including claims for product liability, personal injury or death, or property damage arising from any use of a Cypress product as a Critical Component in a High-Risk Device. Cypress products are not intended or authorized for use as a Critical Component in any High-Risk Device except to the limited extent that (i) Cypress's published data sheet for the product explicitly states Cypress has qualified the product for use in a specific High-Risk Device, or (ii) Cypress has given you advance written authorization to use the product as a Critical Component in the specific High-Risk Device and you have signed a separate indemnification agreement.

Cypress, the Cypress logo, Spansion, the Spansion logo, and combinations thereof, WICED, PSoC, CapSense, EZ-USB, F-RAM, and Traveo are trademarks or registered trademarks of Cypress in the United States and other countries. For a more complete list of Cypress trademarks, visit cypress.com. Other names and brands may be claimed as property of their respective owners.

Document Number: 002-18787 Rev. *H Revised April 1, 2019 Page 82 of 82