

ESSENTIAL-X



UHS-I microSD Card

Product Datasheet

Revision History

Revision	Description	Date
001	First released	Feb, 2024
002	Removed 4GB	Dec, 2024

NOTE: INFORMATION IN THIS PRODUCT SPECIFICATION IS SUBJECT TO CHANGE AT ANYTIME WITHOUT NOTICE, ALL PRODUCT SPECIFICATIONS ARE PROVIDED FOR REFERENCE ONLY.

Overview

- Capacity

- 8GB-512GB

- Flash Type

- MLC/TLC/QLC

- Speed Class

- C10, U1-U3

- Controller and Flash

- ASolid/SMI/Yeestor
- Hynix/Micron/Samsung/SanDisk/YMTC

- Power Consumption

- Power Up Current < 250uA
- Standby Current < 1000uA
- Read Current < 400mA
- Write Current < 400mA

- Supply Voltage

- 2.7~3.6V

- Temperature Range

- Operation: 0°C ~ 70°C
- Storage: -25°C ~ 85°C

- P/E Cycle

- 1000-3000

- Advanced Flash Management

- Static and Dynamic Wear Leveling
- Bad Block Management

- Automatic Power Down

- Automatic Wake Up

- Smart Power Management

- Damage Free Powered Card

Insertion and Removal

- Write Protect with Mechanical

Switch

- CE Compliant

- FCC Compliant

- RoHS Compliant

Content

1. Introduction	- 1 -
1.1 Error Correction Code (ECC)	- 1 -
1.2 Wear Leveling	- 1 -
1.3 Bad Block Management	- 1 -
2. Product List	- 2 -
3. Product Specifications	- 3 -
4. Environmental Specification	- 4 -
5. Memory Cards Comparison	- 8 -
6. Electrical Characteristics	- 9 -
6.1 General DC Characteristics	- 9 -
6.2 Flash Interface AC Characteristics	- 10 -
6.3 Power Consumption	- 11 -
7. Interface	- 12 -
8. Physical Dimension	13

1. Introduction

Essential-X Series microSD are highly integrated flash memories with serial and random-access capability. It is accessible via a dedicated serial interface optimized for fast and reliable data transmission. This interface allows several cards to be staked by through connection their peripheral contacts. Essential-X Series microSD are fully compatible to a new consumer standard, called SD cards system standard define in the microSD cards system specification.

The microSD cards system is a new mass –storage system based on innovations in semiconductor technology. It has been developed to provide an inexpensive mechanically robust storage medium in card form for multimedia consumer applications. Essential-X Series microSD allow the design of inexpensive players and drivers without moving parts. A low power consumption and a wide supply voltage range favors mobile, battery – powered application such as audio players, organizers, palmtops, electronic books, encyclopedia and dictionaries. Using very effective data compression schemes such as MPEG, Essential-X Series microSD will deliver enough capacity for all kinds of multimedia data.

1.1 Error Correction Code (ECC)

Flash memory cells will deteriorate with use, which might generate random bit errors in the stored data. Thus, Essential-X Series microSD apply the BCH ECC Algorithm, which can detect and correct errors occur during Read process, ensure data been read correctly, as well as protect data from corruption.

1.2 Wear Leveling

NAND Flash devices can only undergo a limited number of program/erase cycles, and in most cases, the flash media are not used evenly. If some area get updated more frequently than others, the lifetime of the device would be reduced significantly. Thus, Wear Leveling technique is applied to extend the lifespan of NAND Flash by evenly distributing write and erase cycles across the media.

Wear Leveling algorithm can efficiently spread out the flash usage through the whole flash media area. Moreover, by implementing both dynamic and static Wear Leveling algorithms, the life expectancy of the NAND Flash is greatly improved.

1.3 Bad Block Management

Bad blocks are blocks that include one or more invalid bits, and their reliability is not guaranteed. Blocks that are identified and marked as bad by the manufacturer are referred to as “Initial Bad Blocks”. Bad blocks that are developed during the lifespan of the flash are named “Later Bad Blocks”. Efficient bad block management algorithm has been implemented to detect the factory-produced bad blocks and manages any bad blocks that appear with use. This practice further prevents data being stored into bad blocks and improves the data reliability.

2. Product List

Part Number	Capacity	Actual Size (Min)	Speed Class	Write Speed (Min)	UHS-I	Type
ES008GTFC1MP/NB	8GB	7.3GB	⑩ U1	10 MB/S	SDR104	SDHC
ES016GTFC1MP/NB	16GB	14.7GB	⑩ U1	10 MB/S	SDR104	SDHC
ES032GTFC1MP/NB	32GB	29.1GB	⑩ U1	10 MB/S	SDR104	SDHC
ES032GTFU3MP/NB	32GB	29.1GB	⑩ U3	30 MB/S	SDR104	SDHC
ES064GTFC1MP/NB	64GB	58.2GB	⑩ U1	10 MB/S	SDR104	SDXC
ES064GTFU3MP/NB	64GB	58.2GB	⑩ U3	30 MB/S	SDR104	SDXC
ES128GTFC1MP/NB	128GB	116.4GB	⑩ U1	10 MB/S	SDR104	SDXC
ES128GTFU3MP/NB	128GB	116.4GB	⑩ U3	30 MB/S	SDR104	SDXC
ES256GTFU3MP/NB	256GB	230.4GB	⑩ U3	30 MB/S	SDR104	SDXC
ES512GTFU3MP/NB	512GB	460.8GB	⑩ U3	30 MB/S	SDR104	SDXC

3. Product Specifications

- Card capacity of non-secure area and secure area support Specifications
- Support SD and SPI mode
- Designed for read-only and read/write cards
- Bus Speed Mode (use 4 parallel data lines)
 - . Non-UHS Mode
 - » Default speed mode: 3.3V signaling, frequency up to 25MHz, up to 12.5 MB/sec
 - » High speed mode: 3.3V signaling, frequency up to 50MHz, up to 25 MB/sec
 - . UHS Mode
 - » SDR12: SDR up to 25MHz, 1.8V signaling
 - » SDR25: SDR up to 50MHz, 1.8V signaling
 - » SDR50: 1.8V signaling, frequency up to 100MHz, up to 50 MB/sec
 - » SDR104: 1.8V signaling, frequency up to 208MHz, up to 104MB/sec
 - » DDR50: 1.8V signaling, frequency up to 50MHz, sampled on both clock edges, up to 50 MB/sec

Note:1. Timing in 1.8V signaling is different from that of 3.3V signaling.

2. To properly run the UHS mode, please ensure the device supports UHS-I mode.

- The command list supports [Part 1 Physical Layer Specification Ver3.1 Final] definitions
- Copyrights Protection Mechanism
 - . Compliant with the highest security of CPRM standard
- Support CPRM (Content Protection for Recordable Media) of SD Card
- Card removal during read operation will never harm the content
- Password Protection of cards (optional)
- Write Protect feature using mechanical switch
- Built-in write protection features (permanent and temporary)
- +4KV/-4KV ESD protection in contact pads
- Operation voltage range: 2.7 ~ 3.6V
- Support Dynamic and Static Wear Leveling
- Dimension: 15mm (L) x 11mm (W) x 1mm (H)

4. Environmental Specification

Temperature and Humidity

- Temperature Range
 - . Operational: 0°C ~ 70°C
 - . Storage: -25°C ~ 85°C
- Humidity
 - . Operational: RH = 95% under 25°C
 - . Diamond grade: RH = 93% under 40°C

Table 4-1 High Temperature Test Condition

	Temperature	Humidity	Test Time	Result
Operation	70°C	0% RH	96 hours	No any abnormality is detected
Storage	85°C	0% RH	500 hours	

Table 4-2 Low Temperature Test Condition

	Temperature	Humidity	Test Time	Result
Operation	0°C	0% RH	96 hours	No any abnormality is detected
Storage	-25°C	0% RH	168 hours	

Table 4-3 High Humidity Test Condition

	Temperature	Humidity	Test Time	Result
Operation	25°C	95% RH	1 hour	No any abnormality is detected
Storage	40°C	93% RH	500 hours	

Table 4-4 Temperature Cycle Test

	Temperature	Test Time	Cycle	Result
Operation	0°C	30 min	10 Cycles	No any abnormality is detected
	70°C	30 min		
Storage	-25°C	30 min	10 Cycles	No any abnormality is detected
	85°C	30 min		

Shock

Table 4-5 Shock Specification

	Acceleration Force	Half Sin Pulse Duration	Result
Essential-X Series	1500G	0.5ms	No any abnormality is detected when power on

Vibration

Table 4-6 Vibration Specification

	Condition		Vibration Orientation	Result
	Frequency/Displacement	Frequency/Acceleration		
Essential-X Series	20Hz~80Hz/ 1.52mm	80Hz~2000Hz/20G	X, Y, Z axis/30 min for each	No any abnormality is detected when power on

Drop

Table 4-7 Vibration Specification

	Height of Drop	Number of Drop	Result
Essential-X Series	150cm free fall	6 face of each unit	No any abnormality is detected when power on

Bending

Table 4-8 Bending Specification

	Force	Action	Result
Essential-X Series	≥ 10N	Hold 1min/5 times	No any abnormality is detected when power on

Torque

Table 4-9 Torque Specification

	Force	Action	Result
Essential-X Series	0. 1N-m or +/-2.5 deg	Hold 30 seconds/5 times	No any abnormality is detected when power on

Electrostatic Discharge(ESD)

Table 4-10 ESD Specification



	Condition	Result
Essential-X Series	Contact: +/- 4KV each item 10 times/Pin Air: +/- 8KV 10 times/ Pin	PASS

EMI Compliance

- FCC:CISPR22
- CE:EN55022
- BSMI:13438

5. Memory Cards Comparison

Table 5-1 Comparing UHS Speed Grade Symbols

	U1(UHS Speed Grade 1)	U3(UHS Speed Grade 3)
Operable Under	UHS-I Bus I/F, UHS-II Bus I/F	
microSD Memory Card	microSDHC UHS-I and UHS-II, microSDXC UHS-I and UHS-II	
Mark		
Performance	10 MB/s minimum write speed	30 MB/s minimum write speed
Applications	Full higher potential of recording real-time broadcasts and capturing large-size HD videos.	Capable of recording 4K/2K video.

Note: UHS (Ultra High Speed), the fastest performance category available today, defines bus-interface speeds up to 312 Megabytes per second for greater device performance. It is available on SDXC and SDHC memory cards and devices.

6. Electrical Characteristics

6.1 General DC Characteristics

Table 6-1 General DC Characteristics

Parameter	Symbol	Min	Typical	Max	Unit
Power Supply Voltage	V_{CCA}	2.7	3.3	3.6	V
Operating Temperature	—	0	—	70	°C
Storage Temperature	—	-25	—	85	°C
All Input Leakage Current	—	-10	—	10	uA
All Out Leakage Current	—	-10	—	10	uA

Table 6-2 Bus Operating Conditions –Signal Line's Load

Parameter	Symbol	Min	Typical	Max	Unit	Remark
Pull-up Resistance for CMD signal	R_{CMD}	4.7	—	100	K Ω	To prevent bus floating
Pull –Up Resistance for DAT{3:0} Signals	R_{DAT}	10	—	100	K Ω	To prevent bus floating
Card Capacitance for Eash Signal Pin	C_{CARD}	—	—	10	Pf	—
Pull –Up Resistance Inside Card {DAT(3)}	R_{DAT3}	10	—	150	K Ω	May be used for card detection

Table 6-3 Open –Drain Mode Bus Signal Level

Parameter	Symbol	Min	Max	Unit	Condition
Output High Voltage	V_{OH}	—	—	V	$I_{OH} = -100\mu A$
Output Low Voltage	V_{OL}	—	0.3	V	$I_{OL} = 2\text{ mA}$

Table 6-4 Push –Pull Mode Bus Signal Level – High Voltage 3.3V Signaling Mode

Parameter	Symbol	Min	Max	Unit	Condition
Output High Voltage	V_{OH}	2.4	—	V	$V_{CC} \text{ I/O} = 3.3V$
Output Low Voltage	V_{OL}	—	0.4	V	$V_{CC} \text{ I/O} = 3.3V$
Input High Voltage	V_{IH}	2.0	3.6	V	$V_{CC} \text{ I/O} = 3.3V$
Input Low Voltage	V_{IL}	-0.3	0.8	V	$V_{CC} \text{ I/O} = 3.3V$

The input levels are identical with the push –pull mode bus signal levels.

Note: $V_{CC} \text{ I/O} = I/O$ buffer power.

Table 6-5 Push –Pull Mode Bus Signal Level – High Voltage 1.8V Signaling Mode

Parameter	Symbol	Min	Max	Unit	Condition
Output High Voltage	V_{OH}	1.4	—	V	$V_{CC} \text{ I/O} = 1.8V$
Output Low Voltage	V_{OL}	—	0.4	V	$V_{CC} \text{ I/O} = 1.8V$
Input High Voltage	V_{IH}	1.2	2.1	V	$V_{CC} \text{ I/O} = 1.8V$
Input Low Voltage	V_{IL}	-0.3	0.6	V	$V_{CC} \text{ I/O} = 1.8V$

6.2 Flash Interface AC Characteristics

Table 6-6 Flash Interface AC Timings

Parameter	Symbol	Min	Max	Unit
CLE Setup Time	t_{CLS}	27.5	—	ns
CLE Hold Time	t_{CLH}	12.5	—	ns
ALE Setup Time	t_{ALS}	25.0	—	ns

ALE Hold Time	t_{ALH}	10.0	—	ns
ALE Cycle Time	t_{WC}	37.5	—	ns
WE Pulse Width	t_{WP}	15.0	—	ns
WE High Hold Time	t_{WH}	20.0	—	ns
Write Data Output Setup Time	t_{DS}	25.0	—	ns
Write Data Output Hold Time	t_{DH}	12.5	—	ns
Read Cycle Time	t_{RC}	37.5	—	ns
RE Pulse Width	t_{RP}	17.5	—	ns
RE High Hold Time	t_{REH}	20.0	—	ns

6.3 Power Consumption

Table 6-7 Power Consumption

Bus Speed Mode		Max. Power Up Current(uA)	Max.Standby Currnet(uA)	Max.Read Currnet(uA)	Max.Write Currnet(uA)
Default Speed Mode		250	1000	150@3.6V	150@3.6V
High Speed Mode		250	1000	200@3.6V	200@3.6V
UHS-I Mode	UHS50/DDR 50	250	1000	400@3.6V	400@3.6V
	UHS104	250	1000	400@3.6V	400@3.6V

Note: 1.Power consumption are measured at room temperature.

2. Power consumption of Max. Standby Current is for Essential-X Series cards under and including 64GB only. For 128GB and over, the power consumption is to be determined.

3. The table above is the power consumption of Essential-X Series cards with different bus speed modes. Power consumption may differ according to flash type, OS platform and capacity.

7. Interface

Pad Assignment and Descriptions




Table 7-1 Essential-X Series Memory Card Pad Addignment

Pin	SD Mode			SPI Mode		
	Name	Type	Description	Name	Type	Description
1	DAT2	I/O/PP	Data Line [bit2]	RSV	—	—
2	CD/DAT3	I/O/PP	Card Detect/Data Line [bit3]	CS	I	Chip Select (net true)
3	CMD	PP	Command/Response	DI	I	Data In
4	VDD	S	Supply voltage	VDD	S	Supply voltage
5	CLK	I	Clock	SCLK	I	Clock
6	VSS	S	Supply voltage ground	VSS	S	Supply voltage ground
7	DAT0	I/O/PP	Data Line [bit0]	DO	O/PP	Data Out
8	DAT1	I/O/PP	Data Line [bit1]	RSV	—	—

Note: S: power supply, I: input; O: output using push-pull drivers; PP: I/O using push-pull drivers.

8. Physical Dimension



Dimension: 15mm(L) x 11mm(W) x 1mm(H)

COMMON DIMENSIONS				
SYMBOL	MIN	NOM	MAX	REF.SHEET
A	10.90	11.00	11.10	1
A1	9.60	9.70	9.80	1
A2	0.90	1.00	1.10	2
A2"	0.425	0.550	0.675	2
A3	7.60	7.70	7.80	2
A4	1.05	1.10	1.15	2
A5	0.85	0.90	0.95	2
A6	8.10	8.30	8.50	2
A7	-	-	1.88	2
A8	0.50	0.60	0.70	2
A9	0.80	-	-	2
A10	-	-	1.50	2
B	14.90	15.00	15.10	1
B1	6.30	6.40	6.50	1
B2	1.74	1.84	1.94	1
B3	1.40	4.50	1.60	1
B4	0.42	0.52	0.62	1
B5	3.50	3.60	3.70	2
B6	5.50	-	-	2
B7	0.20	0.30	0.40	2
B8	1.00	1.10	1.10	2
B9	8.60	8.80	9.00	2
B10	7.80	7.90	8.00	2
B11	1.10	1.20	1.30	2
B12	-	-	0.89	2
C	0.90	1.00	1.10	1
C1	0.60	0.70	0.80	1
C2	0.20	0.30	0.40	1
C3	0.00	0.10	0.20	1

COMMON DIMENSIONS				
SYMBOL	MIN	NOM	MAX	REF.SHEET
R1	0.10	0.20	0.30	1
R2	0.10	0.20	0.30	1
R3	0.70	0.80	0.90	1
R4	0.70	0.80	0.90	1
R5	0.70	0.80	0.90	1
R6	0.70	0.80	0.90	1
R7	29.90	30.00	30.10	1
R10	0.10	0.20	0.30	1
R11	0.10	0.20	0.30	1
R12	0.10	0.20	0.40	1
R13	0.10	0.20	0.40	1
R14	0.10	0.20	0.40	1
R15	0.10	0.20	0.40	1
R16	0.10	0.20	0.40	1
R17	0.10	0.20	0.30	1
R18	0.10	0.20	0.30	1
Note:				
1. Dimensions are in millimeter.				
Pin NO.	PIN NAME (SD MODE)		Critical Dimensions to be monitored in Production Before Label Attach: A, A2", B, B8, B10 After Label Attach: A10, A7, B12, C3	
1	DAT2			
2	CE/DAT3			
3	CMD			
4	VDD			
5	CLK			
6	VSS2			
7	DATA0			
8	DATA1			

Above technical information is based on industry standard data and attested to be reliable. However, no warranty made either expressed or implied as to its accuracy and assumes no liability in connection with the use of these products. Changes may be made in specifications at any time without prior notice.