

PCA9634

8-bit Fm+ I²C-bus LED driver Rev. 05 — 28 February 2008

Product data sheet

General description 1.

The PCA9634 is an I²C-bus controlled 8-bit LED driver optimized for Red/Green/Blue/Amber (RGBA) color mixing applications. Each LED output has its own 8-bit resolution (256 steps) fixed frequency Individual PWM controller that operates at 97 kHz with a duty cycle that is adjustable from 0 % to 99.6 % to allow the LED to be set to a specific brightness value. An additional 8-bit resolution (256 steps) Group PWM controller has both a fixed frequency of 190 Hz and an adjustable frequency between 24 Hz to once every 10.73 seconds with a duty cycle that is adjustable from 0 % to 99.6 % that is used to either dim or blink all LEDs with the same value.

Each LED output can be off, on (no PWM control), set at its Individual PWM controller value or at both Individual and Group PWM controller values. The LED output driver is programmed to be either open-drain with a 25 mA current sink capability at 5 V or totem-pole with a 25 mA sink, 10 mA source capability at 5 V. The PCA9634 operates with a supply voltage range of 2.3 V to 5.5 V and the outputs are 5.5 V tolerant. LEDs can be directly connected to the LED output (up to 25 mA, 5.5 V) or controlled with external drivers and a minimum amount of discrete components for larger current or higher voltage LEDs.

The PCA9634 is one of the first LED controller devices in a new Fast-mode Plus (Fm+) family. Fm+ devices offer higher frequency (up to 1 MHz) and more densely populated bus operation (up to 4000 pF).

The active LOW Output Enable input pin (OE) allows asynchronous control of the LED outputs and can be used to set all the outputs to a defined I²C-bus programmable logic state. The \overline{OE} can also be used to externally PWM the outputs, which is useful when multiple devices need to be dimmed or blinked together using software control.

Software programmable LED Group and three Sub Call I²C-bus addresses allow all or defined groups of PCA9634 devices to respond to a common I²C-bus address, allowing for example, all red LEDs to be turned on or off at the same time or marquee chasing effect, thus minimizing I²C-bus commands. Seven hardware address pins allow up to 126 devices on the same bus.

The Software Reset (SWRST) Call allows the master to perform a reset of the PCA9634 through the I²C-bus, identical to the Power-On Reset (POR) that initializes the registers to their default state causing the outputs to be set HIGH (LED off). This allows an easy and quick way to reconfigure all device registers to the same condition.



8-bit Fm+ I2C-bus LED driver

2. Features

- 8 LED drivers. Each output programmable at:
 - Off
 - On
 - Programmable LED brightness
 - Programmable group dimming/blinking mixed with individual LED brightness
- 1 MHz Fast-mode Plus compatible I²C-bus interface with 30 mA high drive capability on SDA output for driving high capacitive buses
- 256-step (8-bit) linear programmable brightness per LED output varying from fully off (default) to maximum brightness using a 97 kHz PWM signal
- 256-step group brightness control allows general dimming (using a 190 Hz PWM signal) from fully off to maximum brightness (default)
- 256-step group blinking with frequency programmable from 24 Hz to 10.73 s and duty cycle from 0 % to 99.6 %
- Eight totem-pole outputs (sink 25 mA and source 10 mA at 5 V) with software programmable open-drain LED outputs selection (default at totem-pole). No input function.
- Output state change programmable on the Acknowledge or the STOP Command to update outputs byte-by-byte or all at the same time (default to 'Change on STOP').
- Active LOW Output Enable (\overline{OE}) input pin. LED outputs programmable to 1, 0 or 'high-impedance' (default at power-up) when \overline{OE} is HIGH, thus allowing hardware blinking and dimming of the LEDs.
- 7 hardware address pins allow 126 devices to be connected to the same I²C-bus
- 4 software programmable I²C-bus addresses (one LED Group Call address and three LED Sub Call addresses) allow groups of devices to be addressed at the same time in any combination (for example, one register used for 'All Call' so that all the PCA9634s on the I²C-bus can be addressed at the same time and the second register used for three different addresses so that ¹/₃ of all devices on the bus can be addressed at the same time in a group). Software enable and disable for I²C-bus address.
- Software Reset feature (SWRST Call) allows the device to be reset through the I²C-bus
- Up to 126 possible hardware adjustable individual I²C-bus addresses per device so that each device can be programmed individually.
- 25 MHz internal oscillator requires no external components
- Internal power-on reset
- Noise filter on SDA/SCL inputs
- Edge rate control on outputs
- No glitch on power-up
- Supports hot insertion
- Low standby current
- Operating power supply voltage range of 2.3 V to 5.5 V
- 5.5 V tolerant inputs
- -40 °C to +85 °C operation
- ESD protection exceeds 2000 V HBM per JESD22-A114, 200 V MM per JESD22-A115, and 1000 V CDM per JESD22-C101
- Latch-up testing is done to JEDEC Standard JESD78 which exceeds 100 mA

8-bit Fm+ I²C-bus LED driver

■ Packages offered: SO20, TSSOP20, HVQFN20

3. Applications

- RGB or RGBA LED drivers
- LED status information
- LED displays
- LCD backlights
- Keypad backlights for cellular phones or handheld devices


4. Ordering information

Table 1. Ordering information

Type number	Topside	Package				
	mark	Name	Description	Version		
PCA9634D	PCA9634D	SO20	plastic small outline package; 20 leads; body width 7.5 mm	SOT163-1		
PCA9634PW	PCA9634	TSSOP20	plastic thin shrink small outline package; 20 leads; body width 4.4 mm	SOT360-1		
PCA9634BS	9634	HVQFN20	plastic thermal enhanced very thin quad flat package; no leads; 20 terminals; body $5\times5\times0.85~\text{mm}$	SOT662-1		

8-bit Fm+ I²C-bus LED driver


5. Block diagram



8-bit Fm+ I²C-bus LED driver

6. Pinning information

6.1 Pinning



6.2 Pin description

Table 2. Pin description for SO20 and TSSOP20

Symbol	Pin	Туре	Description
A0	1	I	address input 0
A1	2	I	address input 1
A2	3	I	address input 2
A3	4	I	address input 3
A4	5	I	address input 4
LED0	6	0	LED driver 0
LED1	7	0	LED driver 1
LED2	8	0	LED driver 2
LED3	9	0	LED driver 3

PCA9634_5 © NXP B.V. 2008. All rights reserved.

8-bit Fm+ I²C-bus LED driver

 Table 2.
 Pin description for SO20 and TSSOP20 ...continued

Symbol	Pin	Туре	Description
V_{SS}	10	power supply	supply ground
LED4	11	0	LED driver 4
LED5	12	0	LED driver 5
LED6	13	0	LED driver 6
LED7	14	0	LED driver 7
ŌĒ	15	1	active LOW Output Enable
A5	16	I	address input 5
A6	17	I	address input 6
SCL	18	I	serial clock line
SDA	19	I/O	serial data line
V_{DD}	20	power supply	supply voltage

Table 3. Pin description for HVQFN20

Symbol	Pin	Туре	Description
A2	1	I	address input 2
A3	2	I	address input 3
A4	3	I	address input 4
LED0	4	0	LED driver 0
LED1	5	0	LED driver 1
LED2	6	0	LED driver 2
LED3	7	0	LED driver 3
V _{SS} [1]	8	power supply	supply ground
LED4	9	0	LED driver 4
LED5	10	0	LED driver 5
LED6	11	0	LED driver 6
LED7	12	0	LED driver 7
ŌĒ	13	I	active LOW Output Enable
A5	14	I	address input 5
A6	15	I	address input 6
SCL	16	I	serial clock line
SDA	17	I/O	serial data line
V_{DD}	18	power supply	supply voltage
A0	19	I	address input 0
A1	20	I	address input 1

^[1] HVQFN20 package die supply ground is connected to both the V_{SS} pin and the exposed center pad. The V_{SS} pin must be connected to supply ground for proper device operation. For enhanced thermal, electrical, and board-level performance, the exposed pad needs to be soldered to the board using a corresponding thermal pad on the board, and for proper heat conduction through the board thermal vias need to be incorporated in the PCB in the thermal pad region.

8-bit Fm+ I2C-bus LED driver

7. Functional description

Refer to Figure 1 "Block diagram of PCA9634".

7.1 Device addresses

Following a START condition, the bus master must output the address of the slave it is accessing.


There are a maximum of 128 possible programmable addresses using the 7 hardware address pins. Two of these addresses, Software Reset and LED All Call, cannot be used because their default power-up state is ON, leaving a maximum of 126 addresses. Using other reserved addresses, as well as any other subcall address, will reduce the total number of possible addresses even further.

7.1.1 Regular I²C-bus slave address

The I²C-bus slave address of the PCA9634 is shown in <u>Figure 5</u>. To conserve power, no internal pull-up resistors are incorporated on the hardware selectable address pins and they must be pulled HIGH or LOW.

Remark: Reserved I²C-bus addresses must be used with caution since they can interfere with:

- 'reserved for future use' I²C-bus addresses (0000 011, 1111 1XX)
- slave devices that use the 10-bit addressing scheme (1111 0XX)
- slave devices that are designed to respond to the General Call address (0000 000)
- High-speed mode (Hs-mode) master code (0000 1XX).



The last bit of the address byte defines the operation to be performed. When set to logic 1 a read is selected, while a logic 0 selects a write operation.

7.1.2 LED All Call I²C-bus address

- Default power-up value (ALLCALLADR register): E0h or 1110 000
- Programmable through I²C-bus (volatile programming)
- At power-up, LED All Call I²C-bus address is enabled. PCA9634 sends an ACK when E0h ($R/\overline{W} = 0$) or E1h ($R/\overline{W} = 1$) is sent by the master.

See Section 7.3.8 "ALLCALLADR: LED All Call I2C-bus address" for more detail.

Remark: The default LED All Call I^2C -bus address (E0h or 1110 000) must not be used as a regular I^2C -bus slave address since this address is enabled at power-up. All the PCA9634s on the I^2C -bus will acknowledge the address if sent by the I^2C -bus master.

8-bit Fm+ I2C-bus LED driver

7.1.3 LED Sub Call I²C-bus addresses


- 3 different I²C-bus addresses can be used
- Default power-up values:
 - SUBADR1 register: E2h or 1110 001SUBADR2 register: E4h or 1110 010SUBADR3 register: E8h or 1110 100
- Programmable through I²C-bus (volatile programming)
- At power-up, Sub Call I²C-bus addresses are disabled. PCA9634 does not send an ACK when E2h (R/W = 0) or E3h (R/W = 1), E4h (R/W = 0) or E5h (R/W = 1), or E8h (R/W = 0) or E9h (R/W = 1) is sent by the master.

See Section 7.3.7 "SUBADR1 to SUBADR3: I2C-bus subaddress 1 to 3" for more detail.

Remark: The default LED Sub Call I²C-bus addresses may be used as regular I²C-bus slave addresses as long as they are disabled.

7.1.4 Software Reset I²C-bus address

The address shown in Figure 6 is used when a reset of the PCA9634 needs to be performed by the master. The Software Reset address (SWRST Call) must be used with $R/\overline{W} = 0$. If $R/\overline{W} = 1$, the PCA9634 does not acknowledge the SWRST. See Section 7.6 "Software Reset" for more detail.




Remark: The Software Reset I²C-bus address is a reserved address and cannot be used as a regular I²C-bus slave address or as an LED All Call or LED Sub Call address.

7.2 Control register

Following the successful acknowledgement of the slave address, LED All Call address or LED Sub Call address, the bus master will send a byte to the PCA9634, which will be stored in the Control register.

The lowest 5 bits are used as a pointer to determine which register will be accessed (D[4:0]). The highest 3 bits are used as Auto-Increment flag and Auto-Increment options (AI[2:0]).

8-bit Fm+ I2C-bus LED driver



When the Auto-Increment flag is set (AI2 = 1), the five low order bits of the Control register are automatically incremented after a read or write. This allows the user to program the registers sequentially. Four different types of Auto-Increment are possible, depending on AI1 and AI0 values.

Table 4. Auto-Increment options

Al2	Al1	AI0	Function
0	0	0	no Auto-Increment
1	0	0	Auto-Increment for all registers. D[4:0] roll over to '0 0000' after the last register (1 0001) is accessed.
1	0	1	Auto-Increment for individual brightness registers only. D[4:0] roll over to '0 0010' after the last register (0 1001) is accessed.
1	1	0	Auto-Increment for global control registers only. D[4:0] roll over to '0 1010' after the last register (0 1011) is accessed.
1	1	1	Auto-Increment for individual and global control registers only. D[4:0] roll over to '0 0010' after the last register (0 1011) is accessed.

Remark: Other combinations not shown in $\underline{\text{Table 4}}$ (AI[2:0] = 001, 010, and 011) are reserved and must not be used for proper device operation.

AI[2:0] = 000 is used when the same register must be accessed several times during a single I^2C -bus communication, for example, changes the brightness of a single LED. Data is overwritten each time the register is accessed during a write operation.

AI[2:0] = 100 is used when all the registers must be sequentially accessed, for example, power-up programming.

AI[2:0] = 101 is used when the four LED drivers must be individually programmed with different values during the same I^2C -bus communication, for example, changing color setting to another color setting.

Al[2:0] = 110 is used when the LED drivers must be globally programmed with different settings during the same I²C-bus communication, for example, global brightness or blinking change.

Al[2:0] = 111 is used when individual and global changes must be performed during the same l²C-bus communication, for example, changing a color and global brightness at the same time.

Only the 5 least significant bits D[4:0] are affected by the Al[2:0] bits.

8-bit Fm+ I²C-bus LED driver

When the Control register is written, the register entry point determined by D[4:0] is the first register that will be addressed (read or write operation), and can be anywhere between 0 0000 and 1 0001 (as defined in Table 5). When AI[2] = 1, the Auto-Increment flag is set and the rollover value at which the register increment stops and goes to the next one is determined by AI[2:0]. See Table 4 for rollover values. For example, if the Control register = 1110 1100 (ECh), then the register addressing sequence will be (in hex): $0C \rightarrow ... \rightarrow 11 \rightarrow 00 \rightarrow ... \rightarrow 0B \rightarrow 02 \rightarrow ... \rightarrow 0B \rightarrow 02 \rightarrow ... \rightarrow 0B \rightarrow 02 \rightarrow ...$ as long as the master keeps sending or reading data.

7.3 Register definitions

Table 5. Register summary[1]

Register number (hex)	D4	D3	D2	D1	D0	Name	Туре	Function
-								
00	0	0	0	0	0	MODE1	read/write	Mode register 1
01	0	0	0	0	1	MODE2	read/write	Mode register 2
02	0	0	0	1	0	PWM0	read/write	brightness control LED0
03	0	0	0	1	1	PWM1	read/write	brightness control LED1
04	0	0	1	0	0	PWM2	read/write	brightness control LED2
05	0	0	1	0	1	PWM3	read/write	brightness control LED3
06	0	0	1	1	0	PWM4	read/write	brightness control LED4
07	0	0	1	1	1	PWM5	read/write	brightness control LED5
08	0	1	0	0	0	PWM6	read/write	brightness control LED6
09	0	1	0	0	1	PWM7	read/write	brightness control LED7
0A	0	1	0	1	0	GRPPWM	read/write	group duty cycle control
0B	0	1	0	1	1	GRPFREQ	read/write	group frequency
0C	0	1	1	0	0	LEDOUT0	read/write	LED output state 0
0D	0	1	1	0	1	LEDOUT1	read/write	LED output state 1
0E	0	1	1	1	0	SUBADR1	read/write	I ² C-bus subaddress 1
0F	0	1	1	1	1	SUBADR2	read/write	I ² C-bus subaddress 2
10	1	0	0	0	0	SUBADR3	read/write	I ² C-bus subaddress 3
11	1	0	0	0	1	ALLCALLADR	read/write	LED All Call I ² C-bus address

^[1] Only D[4:0] = 0 0000 to 1 0001 are allowed and will be acknowledged. D[4:0] = 1 0010 to 1 1111 are reserved and will not be acknowledged.

7.3.1 Mode register 1, MODE1

Table 6. MODE1 - Mode register 1 (address 00h) bit description Legend: * default value.

Bit	Symbol	Access	Value	Description
7	Al2	read only	0	register Auto-Increment disabled
			1*	register Auto-Increment enabled
6	Al1	read only	0*	Auto-Increment bit 1 = 0
			1	Auto-Increment bit 1 = 1
5	AI0	read only	0*	Auto-Increment bit 0 = 0
			1	Auto-Increment bit 0 = 1

PCA9634_5 © NXP B.V. 2008. All rights reserved.

8-bit Fm+ I²C-bus LED driver

Table 6. MODE1 - Mode register 1 (address 00h) bit description ...continued Legend: * default value.

•				
Bit	Symbol	Access	Value	Description
4	SLEEP	R/W	0	Normal mode[1]
			1*	Low power mode; oscillator off[2]
3	SUB1	R/W	0*	PCA9634 does not respond to I ² C-bus subaddress 1
			1	PCA9634 responds to I ² C-bus subaddress 1
2	2 SUB2 R/W		0*	PCA9634 does not respond to I ² C-bus subaddress 2
			1	PCA9634 responds to I ² C-bus subaddress 2
1	SUB3	R/W	0*	PCA9634 does not respond to I ² C-bus subaddress 3
			1	PCA9634 responds to I ² C-bus subaddress 3
0	ALLCALL	R/W	0	PCA9634 does not respond to LED All Call I ² C-bus address
			1*	PCA9634 responds to LED All Call I ² C-bus address

^[1] It takes 500 μs max. for the oscillator to be up and running once SLEEP bit has been set to logic 0. Timings on LEDn outputs are not guaranteed if PWMx, GRPPWM or GRPFREQ registers are accessed within the 500 μs window.

7.3.2 Mode register 2, MODE2

Table 7. MODE2 - Mode register 2 (address 01h) bit description Legend: * default value.

Bit	Symbol	Access	Value	Description
7	-	read only	0*	reserved
6	-	read only	0*	reserved
5	DMBLNK	R/W	0*	Group control = dimming
			1	Group control = blinking
4	INVRT[1]	R/W	0*	output logic state not inverted; value to use when no external driver used; applicable when $\overline{\text{OE}} = 0$
			1	output logic state inverted; value to use when external driver used; applicable when $\overline{\text{OE}} = 0$
3	OCH R/W		0*	outputs change on STOP command[2]
			1	outputs change on ACK
2	OUTDRV[1]	R/W	0	the 8 LED outputs are configured with an open-drain structure
			1*	the 8 LED outputs are configured with a totem-pole structure
1 to 0	OUTNE[1:0][3] R/W		00	when $\overline{OE} = 1$ (output drivers not enabled), LEDn = 0
			01*	when $\overline{OE} = 1$ (output drivers not enabled):
				LEDn = 1 when OUTDRV = 1
				LEDn = high-impedance when OUTDRV = 0 (same as OUTNE[1:0] = 10)
			10	when \overline{OE} = 1 (output drivers not enabled), LEDn = high-impedance
			11	reserved

^[1] See Section 7.7 "Using the PCA9634 with and without external drivers" for more details. Normal LEDs can be driven directly in either mode. Some newer LEDs include integrated zener diodes to limit voltage transients, reduce EMI and protect the LEDs, and these must be driven only in the open-drain mode to prevent overheating the IC.

PCA9634_5 © NXP B.V. 2008. All rights reserved.

^[2] When the oscillator is off (Sleep mode) the LED outputs cannot be turned on, off or dimmed/blinked.

^[2] Change of the outputs at the STOP command allows synchronizing outputs of more than one PCA9634. Applicable to registers from 02h (PWM0) to 08h (LEDOUT) only.

^[3] See Section 7.4 "Active LOW output enable input" for more details.

8-bit Fm+ I2C-bus LED driver

7.3.3 PWM0 to PWM7: Individual brightness control

Table 8. PWM0 to PWM7 - PWM registers 0 to 7 (address 02h to 09h) bit description Legend: * default value.

Address	Register	Bit	Symbol	Access	Value	Description
02h	PWM0	7:0	IDC0[7:0]	R/W	0000 0000*	PWM0 Individual Duty Cycle
03h	PWM1	7:0	IDC1[7:0]	R/W	0000 0000*	PWM1 Individual Duty Cycle
04h	PWM2	7:0	IDC2[7:0]	R/W	0000 0000*	PWM2 Individual Duty Cycle
05h	PWM3	7:0	IDC3[7:0]	R/W	0000 0000*	PWM3 Individual Duty Cycle
06h	PWM4	7:0	IDC4[7:0]	R/W	0000 0000*	PWM4 Individual Duty Cycle
07h	PWM5	7:0	IDC5[7:0]	R/W	0000 0000*	PWM5 Individual Duty Cycle
08h	PWM6	7:0	IDC6[7:0]	R/W	0000 0000*	PWM6 Individual Duty Cycle
09h	PWM7	7:0	IDC7[7:0]	R/W	0000 0000*	PWM7 Individual Duty Cycle

A 97 kHz fixed frequency signal is used for each output. Duty cycle is controlled through 256 linear steps from 00h (0 % duty cycle = LED output off) to FFh (99.6 % duty cycle = LED output at maximum brightness). Applicable to LED outputs programmed with LDRx = 10 or 11 (LEDOUT0 and LEDOUT1 registers).

$$duty\ cycle = \frac{IDC[7:0]}{256} \tag{1}$$

7.3.4 GRPPWM: Group duty cycle control

Table 9. GRPPWM - Group duty cycle control register (address 0Ah) bit description Legend: * default value.

Address	Register	Bit	Symbol	Access	Value	Description
0Ah	GRPPWM	7:0	GDC[7:0]	R/W	1111 1111	GRPPWM register

When DMBLNK bit (MODE2 register) is programmed with 0, a 190 Hz fixed frequency signal is superimposed with the 97 kHz individual brightness control signal. GRPPWM is then used as a global brightness control allowing the LED outputs to be dimmed with the same value. The value in GRPFREQ is then a 'Don't care'.

General brightness for the 8 outputs is controlled through 256 linear steps from 00h (0 % duty cycle = LED output off) to FFh (99.6 % duty cycle = maximum brightness). Applicable to LED outputs programmed with LDRx = 11 (LEDOUT0 and LEDOUT1 registers).

When DMBLNK bit is programmed with logic 1, GRPPWM and GRPFREQ registers define a global blinking pattern, where GRPFREQ contains the blinking period (from 24 Hz to 10.73 s) and GRPPWM the duty cycle (ON/OFF ratio in %).

$$duty\ cycle = \frac{GDC[7:0]}{256} \tag{2}$$

8-bit Fm+ I2C-bus LED driver

7.3.5 GRPFREQ: Group frequency

Table 10. GRPFREQ - Group Frequency register (address 0Bh) bit description Legend: * default value.

Address	Register	Bit	Symbol	Access	Value	Description
0Bh	GRPFREQ	7:0	GFRQ[7:0]	R/W	0000 0000*	GRPFREQ register

GRPFREQ is used to program the global blinking period when DMBLNK bit (MODE2 register) is equal to 1. Value in this register is a 'Don't care' when DMBLNK = 0. Applicable to LED outputs programmed with LDRx = 11 (LEDOUT0 and LEDOUT1 registers).

Blinking period is controlled through 256 linear steps from 00h (41 ms, frequency 24 Hz) to FFh (10.73 s).

global blinking period =
$$\frac{GFRQ[7:0]+1}{24}$$
 (in seconds) (3)

7.3.6 LEDOUT0 and LEDOUT1: LED driver output state

Table 11. LEDOUT0 and LEDOUT1- LED driver output state registers (address 0Ch and 0Dh) bit description

Legend: * default value.

Address	Register	Bit	Symbol	Access	Value	Description
0Ch	LEDOUT0	7:6	LDR3	R/W	00*	LED3 output state control
		5:4	LDR2	R/W	00*	LED2 output state control
		3:2	LDR1	R/W	00*	LED1 output state control
		1:0	LDR0	R/W	00*	LED0 output state control
0Dh	LEDOUT1	7:6	LDR7	R/W	00*	LED7 output state control
		5:4	LDR6	R/W	00*	LED6 output state control
		3:2	LDR5	R/W	00*	LED5 output state control
		1:0	LDR4	R/W	00*	LED4 output state control

LDRx = 00 — LED driver x is off (default power-up state).

LDRx = 01 — LED driver x is fully on (individual brightness and group dimming/blinking not controlled).

LDRx = 10 — LED driver x individual brightness can be controlled through its PWMx register.

LDRx = 11 — LED driver x individual brightness and group dimming/blinking can be controlled through its PWMx register and the GRPPWM registers.

8-bit Fm+ I2C-bus LED driver

7.3.7 SUBADR1 to SUBADR3: I2C-bus subaddress 1 to 3

Table 12. SUBADR1 to SUBADR3 - I²C-bus subaddress registers 1 to 3 (address 0Eh to 10h) bit description

Legend: * default value.

Address	Register	Bit	Symbol	Access	Value	Description
0Eh	SUBADR1	7:1	A1[7:1]	R/W	1110 001*	I ² C-bus subaddress 1
		0	A1[0]	R only	0*	reserved
0Fh	SUBADR2	7:1	A2[7:1]	R/W	1110 010*	I ² C-bus subaddress 2
		0	A2[0]	R only	0*	reserved
10h	SUBADR3	7:1	A3[7:1]	R/W	1110 100*	I ² C-bus subaddress 3
		0	A3[0]	R only	0*	reserved

Subaddresses are programmable through the I²C-bus. Default power-up values are E2h, E4h, E8h, and the device(s) will not acknowledge these addresses right after power-up (the corresponding SUBx bit in MODE1 register is equal to 0).

Once subaddresses have been programmed to their right values, SUBx bits need to be set to 1 in order to have the device acknowledging these addresses (MODE1 register).

Only the 7 MSBs representing the I^2 C-bus subaddress are valid. The LSB in SUBADRx register is a read-only bit (0).

When SUBx is set to 1, the corresponding I^2C -bus subaddress can be used during either an I^2C -bus read or write sequence.

7.3.8 ALLCALLADR: LED All Call I²C-bus address

Table 13. ALLCALLADR - LED All Call I²C-bus address register (address 11h) bit description

Legend: * default value.

Address	Register	Bit	Symbol	Access	Value	Description
11h	ALLCALLADR	7:1	AC[7:1]	R/W	1110 000*	ALLCALL I ² C-bus address register
		0	AC[0]	R only	0*	reserved

The LED All Call I²C-bus address allows all the PCA9634s on the bus to be programmed at the same time (ALLCALL bit in register MODE1 must be equal to 1—power-up default state). This address is programmable through the I²C-bus and can be used during either an I²C-bus read or write sequence. The register address can also be programmed as a Sub Call.

Only the 7 MSBs representing the All Call I²C-bus address are valid. The LSB in ALLCALLADR register is a read-only bit (0).

If ALLCALL bit = 0, the device does not acknowledge the address programmed in register ALLCALLADR.

8-bit Fm+ I2C-bus LED driver

7.4 Active LOW output enable input

The active LOW output enable (\overline{OE}) pin, allows to enable or disable all the LED outputs at the same time.

- When a LOW level is applied to OE pin, all the LED outputs are enabled and follow the output state defined in the LEDOUT register with the polarity defined by INVRT bit (MODE2 register).
- When a HIGH level is applied to \overline{OE} pin, all the LED outputs are programmed to the value that is defined by OUTNE[1:0] in the MODE2 register.

Table 14. LED outputs when $\overline{OE} = 1$

OUTNE1	OUTNE0	LED outputs
0	0	0
0	1	1 if OUTDRV = 1, high-impedance if OUTDRV = 0
1	0	high-impedance
1	1	reserved

The $\overline{\text{OE}}$ pin can be used as a synchronization signal to switch on/off several PCA9634 devices at the same time. This requires an external clock reference that provides blinking period and the duty cycle.

The $\overline{\text{OE}}$ pin can also be used as an external dimming control signal. The frequency of the external clock must be high enough not to be seen by the human eye, and the duty cycle value determines the brightness of the LEDs.

Remark: Do not use \overline{OE} as an external blinking control signal when internal global blinking is selected (DMBLNK = 1, MODE2 register) since it will result in an undefined blinking pattern. Do not use \overline{OE} as an external dimming control signal when internal global dimming is selected (DMBLNK = 0, MODE2 register) since it will result in an undefined dimming pattern.

7.5 Power-on reset

When power is applied to V_{DD} , an internal power-on reset holds the PCA9634 in a reset condition until V_{DD} has reached V_{POR} . At this point, the reset condition is released and the PCA9634 registers and I²C-bus state machine are initialized to their default states (all zeroes) causing all the channels to be deselected. Thereafter, V_{DD} must be lowered below 0.2 V to reset the device.

8-bit Fm+ I2C-bus LED driver

7.6 Software Reset

The Software Reset Call (SWRST Call) allows all the devices in the I²C-bus to be reset to the power-up state value through a specific formatted I²C-bus command. To be performed correctly, it implies that the I²C-bus is functional and that there is no device hanging the bus.

The SWRST Call function is defined as the following:

- 1. A START command is sent by the I²C-bus master.
- 2. The reserved SWRST I²C-bus address '0000 011' with the R/W bit set to '0' (write) is sent by the I²C-bus master.
- 3. The PCA9634 device(s) acknowledge(s) after seeing the SWRST Call address '0000 0110' (06h) only. If the R/W bit is set to '1' (read), no acknowledge is returned to the I²C-bus master.
- 4. Once the SWRST Call address has been sent and acknowledged, the master sends 2 bytes with 2 specific values (SWRST data byte 1 and byte 2):
 - a. Byte 1 = A5h: the PCA9634 acknowledges this value only. If byte 1 is not equal to A5h, the PCA9634 does not acknowledge it.
 - b. Byte 2 = 5Ah: the PCA9634 acknowledges this value only. If byte 2 is not equal to 5Ah, then the PCA9634 does not acknowledge it.
 - If more than 2 bytes of data are sent, the PCA9634 does not acknowledge any more.
- 5. Once the right 2 bytes (SWRST data byte 1 and byte 2 only) have been sent and correctly acknowledged, the master sends a STOP command to end the SWRST Call: the PCA9634 then resets to the default value (power-up value) and is ready to be addressed again within the specified bus free time (t_{BUF}).

The I²C-bus master must interpret a non-acknowledge from the PCA9634 (at any time) as a 'SWRST Call Abort'. The PCA9634 does not initiate a reset of its registers. This happens only when the format of the SWRST Call sequence is not correct.

8-bit Fm+ I2C-bus LED driver

17 of 38

7.7 Using the PCA9634 with and without external drivers

The PCA9634 LED output drivers are 5.5 V only tolerant and can sink up to 25 mA at 5 V.

If the device needs to drive LEDs to a higher voltage and/or higher current, use of an external driver is required.

- INVRT bit (MODE2 register) can be used to keep the LED PWM control firmware the same (PWMx and GRPPWM values directly calculated from their respective formulas and the LED output state determined by LEDOUT register value) independently of the type of external driver. This bit allows LED output polarity inversion/non-inversion only when OE = 0.
- OUTDRV bit (MODE2 register) allows minimizing the amount of external components required to control the external driver (N-type or P-type device).

Table 15. Use of INVRT and OUTDRV based on connection to the LEDn outputs when $\overline{OE} = 0$ [1]

INVRT	OUTDRV	Direct connection to	LEDn	External N-type d	river	External P-type dr	iver
		Firmware	External pull-up resistor	Firmware	External pull-up resistor	Firmware	External pull-up resistor
0	0	formulas and LED output state values apply[2]	LED current limiting R[2]	formulas and LED output state values inverted	required	formulas and LED output state values apply	required
0	1	formulas and LED output state values apply[2]	LED current limiting R[2]	formulas and LED output state values inverted	not required	formulas and LED output state values apply[4]	not required[4]
1	0	formulas and LED output state values inverted	LED current limiting R	formulas and LED output state values apply	required	formulas and LED output state values inverted	required
1	1	formulas and LED output state values inverted	LED current limiting R	formulas and LED output state values apply[3]	not required ^[3]	formulas and LED output state values inverted	not required

^[1] When \overline{OE} = 1, LED output state is controlled only by OUTNE[1:0] bits (MODE2 register).

^[2] Correct configuration when LEDs directly connected to the LEDn outputs (connection to V_{DD} through current limiting resistor).

^[3] Optimum configuration when external N-type (NPN, NMOS) driver used.

^[4] Optimum configuration when external P-type (PNP, PMOS) driver used.

8-bit Fm+ I²C-bus LED driver

Table 16. Output transistors based on LEDOUT registers, INVRT and OUTDRV bits when $\overline{OE} = 0$

LEDOUT	INVRT	OUTDRV	Upper transistor (V _{DD} to LEDn)	Lower transistor (LEDn to V _{SS})	LEDn state
00	0	0	off	off	high-Z ^[2]
LED driver off	0	1	on	off	V_{DD}
	1	0	off	on	V _{SS}
	1	1	off	on	V _{SS}
01	0	0	off	on	V _{SS}
LED driver on	0	1	off	on	V _{SS}
	1	0	off	off	high-Z ^[2]
	1	1	on	off	V_{DD}
10 Individual	0	0	off	Individual PWM (non-inverted)	V_{SS} or high- $Z^{[2]}$ = PWMx value
brightness control	0	1	Individual PWM (non-inverted)	Individual PWM (non-inverted)	V_{SS} or V_{DD} = PWMx value
	1	0	off	Individual PWM (inverted)	high- $Z^{[2]}$ or $V_{SS} = 1 - PWMx$ value
	1	1	Individual PWM (inverted)	Individual PWM (inverted)	V_{DD} or $V_{SS} = 1 - PWMx$ value
11 Individual + Group	0	0	off	Individual + Group PWM (non-inverted)	V _{SS} or high-Z ^[2] = PWMx or GRPPWM values
dimming/blinking	0	1	Individual PWM (non-inverted)	Individual PWM (non-inverted)	V_{SS} or V_{DD} = PWMx or GRPPWM values
	1	0	off	Individual + Group PWM (inverted)	high- $Z^{[2]}$ or $V_{SS} = (1 - PWMx)$ or $(1 - GRPPWM)$ values
	1	1	Individual PWM (inverted)	Individual PWM (inverted)	V_{DD} or $V_{SS} = (1 - PWMx)$ or $(1 - GRPPWM)$ values

^[1] When $\overline{OE} = 1$, LED output state is controlled only by OUTNE[1:0] bits (MODE2 register).

^[2] External pull-up or LED current limiting resistor connects LEDn to V_{DD} .

8-bit Fm+ I2C-bus LED driver


19 of 38

7.8 Individual brightness control with group dimming/blinking

A 97 kHz fixed frequency signal with programmable duty cycle (8 bits, 256 steps) is used to control individually the brightness for each LED.

On top of this signal, one of the following signals can be superimposed (this signal can be applied to the 4 LED outputs):

- A lower 190 Hz fixed frequency signal with programmable duty cycle (8 bits, 256 steps) is used to provide a global brightness control.
- A programmable frequency signal from 24 Hz to ¹/_{10.73} Hz (8 bits, 256 steps) with programmable duty cycle (8 bits, 256 steps) is used to provide a global blinking control.




8-bit Fm+ I2C-bus LED driver

8. Characteristics of the I²C-bus

The I²C-bus is for 2-way, 2-line communication between different ICs or modules. The two lines are a serial data line (SDA) and a serial clock line (SCL). Both lines must be connected to a positive supply via a pull-up resistor when connected to the output stages of a device. Data transfer may be initiated only when the bus is not busy.


8.1 Bit transfer

One data bit is transferred during each clock pulse. The data on the SDA line must remain stable during the HIGH period of the clock pulse as changes in the data line at this time will be interpreted as control signals (see Figure 9).



8.1.1 START and STOP conditions


Both data and clock lines remain HIGH when the bus is not busy. A HIGH-to-LOW transition of the data line while the clock is HIGH is defined as the START condition (S). A LOW-to-HIGH transition of the data line while the clock is HIGH is defined as the STOP condition (P) (see Figure 10.)



8.2 System configuration

A device generating a message is a 'transmitter'; a device receiving is the 'receiver'. The device that controls the message is the 'master' and the devices which are controlled by the master are the 'slaves' (see Figure 11).

8-bit Fm+ I2C-bus LED driver




8.3 Acknowledge

The number of data bytes transferred between the START and the STOP conditions from transmitter to receiver is not limited. Each byte of eight bits is followed by one acknowledge bit. The acknowledge bit is a HIGH level put on the bus by the transmitter, whereas the master generates an extra acknowledge related clock pulse.


A slave receiver which is addressed must generate an acknowledge after the reception of each byte. Also a master must generate an acknowledge after the reception of each byte that has been clocked out of the slave transmitter. The device that acknowledges has to pull down the SDA line during the acknowledge clock pulse, so that the SDA line is stable LOW during the HIGH period of the acknowledge related clock pulse; set-up time and hold time must be taken into account.


A master receiver must signal an end of data to the transmitter by not generating an acknowledge on the last byte that has been clocked out of the slave. In this event, the transmitter must leave the data line HIGH to enable the master to generate a STOP condition.




8-bit Fm+ I2C-bus LED driver


9. Bus transactions









8-bit Fm+ I2C-bus LED driver





8-bit Fm+ I2C-bus LED driver

10. Application design-in information



Question 1: What kind of edge rate control is there on the outputs?

• The typical edge rates depend on the output configuration, supply voltage, and the applied load. The outputs can be configured as either open-drain NMOS or totem-pole outputs. If the customer is using the part to directly drive LEDs, they should be using it in an open-drain NMOS, if they are concerned about the maximum ISS and ground bounce. The edge rate control was designed primarily to slow down the turn-on of the output device; it turns off rather quickly (~1.5 ns). In simulation, the typical turn-on time for the open-drain NMOS was ~14 ns (V_{DD} = 3.6 V; C_L = 50 pF; R_{PU} = 500 Ω).

Question 2: Is ground bounce possible?

 Ground bounce is a possibility, especially if all 16 outputs are transitioned at full current (25 mA each). There is a fair amount of decoupling capacitance on chip (~50 pF), which is intended to suppress some of the ground bounce. The customer will need to determine if additional decoupling capacitance externally placed as close as physically possible to the device is required.

8-bit Fm+ I2C-bus LED driver

25 of 38

Question 3: Can I really sink 400 mA through the single ground pin on the package and will this cause any ground bounce problem due to the PWM of the LEDs?

Yes, you can sink 400 mA through a single ground pin on the package. Although the
package only has one ground pin, there are two ground pads on the die itself
connected to this one pin. Although some ground bounce is likely, it will not disrupt the
operation of the part and would be reduced by the external decoupling capacitance.

Question 4: I can't turn the LEDs on or off, but their registers are set properly. Why?

 Check the Mode Register 1 bit 4 SLEEP setting. The value needs to be 0 so that the OSC is turn on. If the OSC is turned off, the LEDs cannot be turned on or off and also can't be dimmed or blinked.

Question 5: I'm using LEDs with integrated zener diodes and the IC is getting very hot. Why?

• The IC outputs can be set to either open-drain or push-pull and default to push-pull outputs. In this application with the zener diodes, they need to be set to open-drain since in the push-pull architecture there is a low resistance path to GND through the zener and this is causing the IC to overheat. The PCA9632/33/34/35 ICs all power-up in the push-pull output mode and with the logic state HIGH, so one of the first things that need to be done is to set the outputs to open-drain.

11. Limiting values

Table 17. Limiting values
In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions	Min	Max	Unit
V_{DD}	supply voltage		-0.5	+6.0	V
V _{I/O}	voltage on an input/output pin		$V_{SS}-0.5$	5.5	V
I _{O(LEDn)}	output current on pin LEDn		-	25	mA
I _{SS}	ground supply current		-	200	mA
P _{tot}	total power dissipation		-	400	mW
T _{stg}	storage temperature		- 65	+150	°C
T _{amb}	ambient temperature	operating	-40	+85	°C

8-bit Fm+ I²C-bus LED driver

12. Static characteristics

Table 18. Static characteristics

 V_{DD} = 2.3 V to 5.5 V; V_{SS} = 0 V; T_{amb} = -40 °C to +85 °C; unless otherwise specified.

Symbol	Parameter	Conditions	N	Min	Тур	Max	Unit
Supply							
V_{DD}	supply voltage		2	2.3	-	5.5	V
I _{DD}	supply current	Operating mode; $V_{DD} = 2.3 \text{ V}$; no load; $f_{SCL} = 1 \text{ MHz}$	-		2.5	10	mA
		Operating mode; $V_{DD} = 3.3 \text{ V}$; no load; $f_{SCL} = 1 \text{ MHz}$	-		2.5	10	mA
		Operating mode; $V_{DD} = 5.5 \text{ V}$; no load; $f_{SCL} = 1 \text{ MHz}$	-		2.5	10	mA
I _{stb}	standby current	V_{DD} = 2.3 V; no load; f_{SCL} = 0 Hz; I/O = inputs; V_{I} = V_{DD}	-		2.3	11	μΑ
		V_{DD} = 3.3 V; no load; f_{SCL} = 0 Hz; I/O = inputs; V_{I} = V_{DD}	-		2.9	12	μΑ
		V_{DD} = 5.5 V; no load; f_{SCL} = 0 Hz; I/O = inputs; V_{I} = V_{DD}	-		3.8	15.5	μΑ
V_{POR}	power-on reset voltage	no load; $V_I = V_{DD}$ or V_{SS}	<u>[1]</u> _		1.5	2.0	V
Input SCI	L; input/output SDA						
V _{IL}	LOW-level input voltage		_	-0.5	-	+0.3V _{DD}	V
V _{IH}	HIGH-level input voltage		C).7V _{DD}	-	5.5	V
I _{OL}	LOW-level output current	$V_{OL} = 0.4 \text{ V}; V_{DD} = 2.3 \text{ V}$	2	20	-	-	mΑ
		$V_{OL} = 0.4 \text{ V}; V_{DD} = 5.0 \text{ V}$	3	30	-	-	mΑ
IL	leakage current	$V_I = V_{DD}$ or V_{SS}	_	-1	-	+1	μΑ
C _i	input capacitance	$V_I = V_{SS}$	-		6	10	pF
LED drive	er outputs						
I _{OL}	LOW-level output current	$V_{OL} = 0.5 \text{ V}; V_{DD} = 2.3 \text{ V}$	<u>[2]</u> 1	12	-	-	mΑ
		$V_{OL} = 0.5 \text{ V}; V_{DD} = 3.0 \text{ V}$	<u>[2]</u> 1	17	-	-	mΑ
		$V_{OL} = 0.5 \text{ V}; V_{DD} = 4.5 \text{ V}$	[2] 2	25	-	-	mΑ
I _{OL(tot)}	total LOW-level output current	$V_{OL} = 0.5 \text{ V}; V_{DD} = 4.5 \text{ V}$	[2] _		-	200	mΑ
I _{OH}	HIGH-level output current	open-drain; V _{OH} = V _{DD}	_	-50	-	+50	μΑ
V _{OH}	HIGH-level output voltage	$I_{OH} = -10 \text{ mA}; V_{DD} = 2.3 \text{ V}$	1	1.6	-	-	V
		$I_{OH} = -10 \text{ mA}; V_{DD} = 3.0 \text{ V}$	2	2.3	-	-	V
		$I_{OH} = -10 \text{ mA}; V_{DD} = 4.5 \text{ V}$	4	1.0	-	-	V
Co	output capacitance		-		2.5	5	pF
OE input							
V _{IL}	LOW-level input voltage		_	-0.5	-	+0.8	V
V _{IH}	HIGH-level input voltage		2	2	-	5.5	V
I _{LI}	input leakage current		_	-1	-	+1	μΑ
C _i	input capacitance		-		3.7	5	pF

8-bit Fm+ I²C-bus LED driver

Table 18. Static characteristics ... continued

 V_{DD} = 2.3 V to 5.5 V; V_{SS} = 0 V; T_{amb} = -40 °C to +85 °C; unless otherwise specified.

, co , amb					
Parameter	Conditions	Min	Тур	Max	Unit
inputs					
LOW-level input voltage		-0.5	-	+0.3V _{DD}	V
HIGH-level input voltage		$0.7V_{DD}$	-	5.5	V
input leakage current		-1	-	+1	μΑ
input capacitance		-	3.7	5	pF
	LOW-level input voltage HIGH-level input voltage input leakage current	LOW-level input voltage HIGH-level input voltage input leakage current	LOW-level input voltage -0.5 HIGH-level input voltage 0.7V _{DD} input leakage current -1	LOW-level input voltage LOW-level input voltage HIGH-level input voltage input leakage current -1 -	inputs LOW-level input voltage HIGH-level input voltage $0.7V_{DD}$ - 5.5 input leakage current -1 - $+1$

^[1] V_{DD} must be lowered to 0.2 V in order to reset part.

13. Dynamic characteristics

Table 19. Dynamic characteristics

Symbol	Parameter	Conditions	itions Standard-mode I ² C-bus		Fast-mod I ² C-bus		Fast-mo	Unit		
				Min	Max	Min	Max	Min	Max	
f_{SCL}	SCL clock frequency	<u>[1</u>	1]	0	100	0	400	0	1000	kHz
t _{BUF}	bus free time between a STOP and START condition			4.7	-	1.3	-	0.5	-	μs
t _{HD;STA}	hold time (repeated) START condition			4.0	-	0.6	-	0.26	-	μs
t _{SU;STA}	set-up time for a repeated START condition			4.7	-	0.6	-	0.26	-	μs
t _{SU;STO}	set-up time for STOP condition			4.0	-	0.6	-	0.26	-	μs
$t_{\text{HD;DAT}}$	data hold time			0	-	0	-	0	-	ns
$t_{\text{VD;ACK}}$	data valid acknowledge time	[2	2]	0.3	3.45	0.1	0.9	0.05	0.45	μs
$t_{\text{VD;DAT}}$	data valid time	[3	3]	0.3	3.45	0.1	0.9	0.05	0.45	μs
t _{SU;DAT}	data set-up time			250	-	100	-	50	-	ns
t_{LOW}	LOW period of the SCL clock			4.7	-	1.3	-	0.5	-	μs
t _{HIGH}	HIGH period of the SCL clock			4.0	-	0.6	-	0.26	-	μs
t _f	fall time of both SDA and SCL signals	<u>[5][</u> 6	<u>6]</u>	-	300	20 + 0.1C _b [4]	300	-	120	ns
t _r	rise time of both SDA and SCL signals			-	1000	$20 + 0.1C_b$ ^[4]	300	-	120	ns
t _{SP}	pulse width of spikes that must be suppressed by the input filter	[7	<u>7]</u>	-	50	-	50	-	50	ns

^[1] Minimum SCL clock frequency is limited by the bus time-out feature, which resets the serial bus interface if either SDA or SCL is held LOW for a minimum of 25 ms. Disable bus time-out feature for DC operation.

^[2] Each bit must be limited to a maximum of 25 mA and the total package limited to 200 mA due to internal busing limits.


^[2] $t_{VD;ACK}$ = time for Acknowledgement signal from SCL LOW to SDA (out) LOW.


^[3] $t_{VD;DAT}$ = minimum time for SDA data out to be valid following SCL LOW.

^[4] C_b = total capacitance of one bus line in pF.

8-bit Fm+ I²C-bus LED driver


- [5] A master device must internally provide a hold time of at least 300 ns for the SDA signal (refer to the V_{IL} of the SCL signal) in order to bridge the undefined region of SCL's falling edge.
- [6] The maximum t_f for the SDA and SCL bus lines is specified at 300 ns. The maximum fall time (t_f) for the SDA output stage is specified at 250 ns. This allows series protection resistors to be connected between the SDA and the SCL pins and the SDA/SCL bus lines without exceeding the maximum specified t_f.
- [7] Input filters on the SDA and SCL inputs suppress noise spikes less than 50 ns.





8-bit Fm+ I²C-bus LED driver

14. Test information




PCA9634 NXP Semiconductors

8-bit Fm+ I²C-bus LED driver

15. Package outline

SO20: plastic small outline package; 20 leads; body width 7.5 mm

SOT163-1



UNIT	A max.	A ₁	A ₂	A ₃	bp	С	D ⁽¹⁾	E ⁽¹⁾	е	HE	L	Lp	ρ	٧	w	у	z ⁽¹⁾	θ
mm	2.65	0.3 0.1	2.45 2.25	0.25	0.49 0.36	0.32 0.23	13.0 12.6	7.6 7.4	1.27	10.65 10.00	1.4	1.1 0.4	1.1 1.0	0.25	0.25	0.1	0.9 0.4	8°
inches	0.1	0.012 0.004	0.096 0.089	0.01	0.019 0.014	0.013 0.009	0.51 0.49	0.30 0.29	0.05	0.419 0.394	0.055	0.043 0.016	0.043 0.039	0.01	0.01	0.004	0.035 0.016	0°

Note

1. Plastic or metal protrusions of 0.15 mm (0.006 inch) maximum per side are not included.

OUTLINE		REFER	EUROPEAN	ISSUE DATE		
VERSION	IEC	JEDEC	EDEC JEITA		PROJECTION	ISSUE DATE
SOT163-1	075E04	MS-013				99-12-27 03-02-19


Fig 22. Package outline SOT163-1 (SO20)

PCA9634_5 © NXP B.V. 2008. All rights reserved.

PCA9634 NXP Semiconductors

TSSOP20: plastic thin shrink small outline package; 20 leads; body width 4.4 mm

SOT360-1



- Notes 1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.
- 2. Plastic interlead protrusions of 0.25 mm maximum per side are not included.

OUTLINE VERSION	REFERENCES			EUROPEAN	ISSUE DATE	
	IEC	JEDEC	JEITA		PROJECTION	ISSUE DATE
SOT360-1		MO-153				99-12-27 03-02-19
	1	L		1		I

Fig 23. Package outline SOT360-1 (TSSOP20)

PCA9634_5 © NXP B.V. 2008. All rights reserved.

8-bit Fm+ I²C-bus LED driver

HVQFN20: plastic thermal enhanced very thin quad flat package; no leads; 20 terminals; body $5 \times 5 \times 0.85$ mm

SOT662-1




Fig 24. Package outline SOT662-1 (HVQFN20)

PCA9634_5 © NXP B.V. 2008. All rights reserved.

8-bit Fm+ I2C-bus LED driver

16. Handling information

Inputs and outputs are protected against electrostatic discharge in normal handling. However, to be completely safe you must take normal precautions appropriate to handling integrated circuits.

17. Soldering of SMD packages

This text provides a very brief insight into a complex technology. A more in-depth account of soldering ICs can be found in Application Note *AN10365 "Surface mount reflow soldering description"*.

17.1 Introduction to soldering

Soldering is one of the most common methods through which packages are attached to Printed Circuit Boards (PCBs), to form electrical circuits. The soldered joint provides both the mechanical and the electrical connection. There is no single soldering method that is ideal for all IC packages. Wave soldering is often preferred when through-hole and Surface Mount Devices (SMDs) are mixed on one printed wiring board; however, it is not suitable for fine pitch SMDs. Reflow soldering is ideal for the small pitches and high densities that come with increased miniaturization.

17.2 Wave and reflow soldering

Wave soldering is a joining technology in which the joints are made by solder coming from a standing wave of liquid solder. The wave soldering process is suitable for the following:

- Through-hole components
- Leaded or leadless SMDs, which are glued to the surface of the printed circuit board

Not all SMDs can be wave soldered. Packages with solder balls, and some leadless packages which have solder lands underneath the body, cannot be wave soldered. Also, leaded SMDs with leads having a pitch smaller than ~0.6 mm cannot be wave soldered, due to an increased probability of bridging.

The reflow soldering process involves applying solder paste to a board, followed by component placement and exposure to a temperature profile. Leaded packages, packages with solder balls, and leadless packages are all reflow solderable.

Key characteristics in both wave and reflow soldering are:

- Board specifications, including the board finish, solder masks and vias
- · Package footprints, including solder thieves and orientation
- The moisture sensitivity level of the packages
- Package placement
- Inspection and repair
- Lead-free soldering versus SnPb soldering

17.3 Wave soldering

Key characteristics in wave soldering are:

8-bit Fm+ I2C-bus LED driver

- Process issues, such as application of adhesive and flux, clinching of leads, board transport, the solder wave parameters, and the time during which components are exposed to the wave
- Solder bath specifications, including temperature and impurities

17.4 Reflow soldering

Key characteristics in reflow soldering are:

- Lead-free versus SnPb soldering; note that a lead-free reflow process usually leads to higher minimum peak temperatures (see <u>Figure 25</u>) than a SnPb process, thus reducing the process window
- Solder paste printing issues including smearing, release, and adjusting the process window for a mix of large and small components on one board
- Reflow temperature profile; this profile includes preheat, reflow (in which the board is heated to the peak temperature) and cooling down. It is imperative that the peak temperature is high enough for the solder to make reliable solder joints (a solder paste characteristic). In addition, the peak temperature must be low enough that the packages and/or boards are not damaged. The peak temperature of the package depends on package thickness and volume and is classified in accordance with Table 20 and 21

Table 20. SnPb eutectic process (from J-STD-020C)

Package thickness (mm)	Package reflow temperature (°C)		
	Volume (mm³)		
	< 350	≥ 350	
< 2.5	235	220	
≥ 2.5	220	220	


Table 21. Lead-free process (from J-STD-020C)

Package reflow temperature (°C)				
Volume (mm³)				
< 350	350 to 2000	> 2000		
260	260	260		
260	250	245		
250	245	245		
	Volume (mm³) < 350 260	Volume (mm³) < 350		

Moisture sensitivity precautions, as indicated on the packing, must be respected at all times.

Studies have shown that small packages reach higher temperatures during reflow soldering, see Figure 25.

8-bit Fm+ I²C-bus LED driver



For further information on temperature profiles, refer to Application Note *AN10365* "Surface mount reflow soldering description".

18. Abbreviations

Table 22. Abbreviations

Acronym	Description
CDM	Charged Device Model
DUT	Device Under Test
EMI	ElectroMagnetic Interference
ESD	ElectroStatic Discharge
HBM	Human Body Model
I ² C-bus	Inter-Integrated Circuit bus
IC	Integrated Circuit
LCD	Liquid Crystal Display
LED	Light Emitting Diode
LSB	Least Significant Bit
MM	Machine Model
MSB	Most Significant Bit
PCB	Printed-Circuit Board
PWM	Pulse Width Modulation
RGB	Red/Green/Blue
RGBA	Red/Green/Blue/Amber
SMBus	System Management Bus

8-bit Fm+ I²C-bus LED driver

19. Revision history

Table 23. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes	
PCA9634_5	20080228	Product data sheet	-	PCA9634_4	
Modifications:	 Table 6 "MODE1 - Mode register 1 (address 00h) bit description": Table note [1]: changed from " set to logic 1." to " set to logic 0." Table note [2]: re-written. Table 7 "MODE2 - Mode register 2 (address 01h) bit description", Table note [1]: added 2nd and 3rd sentences. Section 10 "Application design-in information": Figure 18 "Typical application": added note "All of the 8 LEDn outputs configurable as either open-drain or totem pole. Mixing of configurations is not possible." 				
		luestions and answers .imiting values": changed I _{SS(ma}	ax) from "100 mA" to "200 m	A"	
PCA9634_4	20070105	Product data sheet	-	PCA9634_3	
PCA9634_3	20061113	Product data sheet	-	PCA9634_2	
	00000740	Objective data sheet	_	DCA0004 4	
PCA9634_2	20060713	Objective data sheet	-	PCA9634_1	

8-bit Fm+ I2C-bus LED driver

20. Legal information

20.1 Data sheet status

Document status[1][2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions"
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

20.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

20.3 Disclaimers

General — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected

to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

20.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

I²C-bus — logo is a trademark of NXP B.V.

21. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

PCA9634 NXP Semiconductors

> 16 17 17.1

21 22

8-bit Fm+ I²C-bus LED driver

22. Contents

1	General description
2	Features
3	Applications
4	Ordering information
5	Block diagram 4
6	Pinning information 5
6.1	Pinning
6.2	Pin description 5
7	Functional description 7
7.1	Device addresses
7.1.1	Regular I ² C-bus slave address
7.1.2	LED All Call I ² C-bus address
7.1.3 7.1.4	LED Sub Call I ² C-bus addresses 8
7.1. 4 7.2	Software Reset I ² C-bus address
7.3	Register definitions
7.3.1	Mode register 1, MODE1
7.3.2	Mode register 2, MODE2
7.3.3	PWM0 to PWM7: Individual brightness control 12
7.3.4	GRPPWM: Group duty cycle control 12
7.3.5	GRPFREQ: Group frequency 13
7.3.6	LEDOUT0 and LEDOUT1: LED driver
	output state
7.3.7	SUBADR1 to SUBADR3: I ² C-bus
	subaddress 1 to 3
7.3.8	ALLCALLADR: LED All Call I ² C-bus address. 14
7.4 7.5	Active LOW output enable input
7.5 7.6	Power-on reset
7.0 7.7	Using the PCA9634 with and without external
	drivers
7.8	Individual brightness control with group
	dimming/blinking
8	Characteristics of the I ² C-bus
8.1	Bit transfer
8.1.1	START and STOP conditions 20
8.2	System configuration 20
8.3	Acknowledge 21
9	Bus transactions
10	Application design-in information 24
11	Limiting values
12	Static characteristics
13	Dynamic characteristics 27
14	Test information
15	Package outline

16	Handling information 33	3
17	Soldering of SMD packages	3
17.1	Introduction to soldering	3
17.2	Wave and reflow soldering	3
17.3	Wave soldering	3
17.4	Reflow soldering	4
18	Abbreviations 3	5
19	Revision history 3	6
20	Legal information 3	7
20.1	Data sheet status	7
20.2	Definitions 3	7
20.3	Disclaimers	7
20.4	Trademarks 3	7
21	Contact information 3	7
22	Contents	8

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.



© NXP B.V. 2008.

All rights reserved.

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 28 February 2008 Document identifier: PCA9634_5