



SCREWDRIVER

catalogue



BAHCO

Index



ERGO™

2

ERGO™ Screwdrivers.....	2
ERGO™ With interchangeable blades.....	20
ERGO™ Impact driver	22
ERGO™ Insulated with Slim blade.....	32
ERGO™ Insulated.....	36
ERGO™ Stainless Steel.....	40
ERGO™ Non sparking.....	46
ERGO™ Tools @ Height.....	50



BAHCOFIT

54



600 SERIES

68



RATCHETING

74



PRECISION

82



T-HANDLE

88



HEX KEYS

94



OTHERS

106







ERGO™ Screwdrivers

The Bahco ERGO™ Process

If hand tools are to be ergonomic, they must be suitable to the task, the user and the environment. That is why all three of these factors are crucial when creating an ERGO™ product.

Ergonomic tools are designed to fit the human hand, minimising grip-strength demands and allowing muscles to relax periodically, reducing the risk of static muscle fatigue.

Whenever an ERGO™ tool is being developed, sustainable efficiency and effectiveness are considered, as well as reliability and durability in challenging environments.

We work hard to deliver the best possible tools to every user, and over the years we have continuously developed, improved and fine-tuned the way we do this, which resulted in the **Bahco ERGO™ Process**. This is a comprehensive three-phase process (each phase including several steps), which ensures the validity of ERGO™ tools.

The **Bahco ERGO™ Process** is unique for Bahco and scientifically performed with the help of Industrial Designers and Ergonomists.

The **Bahco ERGO™ Process** is in accordance with ISO 9241.

BAHCO ERGO™ PRODUCTS ARE CONTINUALLY AWARDED WITH THE MOST PRESTIGIOUS DESIGN AWARDS

Bahco ERGO™ products have been included in research papers and business cases. We also actively work with universities and research centers all over to create our products:

- **Comfort Effects of Participatory Design of Screwdrivers**
TU Delft The Netherlands
- **Success Via Design - Business case**
by Triad Design & Harvard University*
- **Business case: AB SANDVIK SAWS & TOOLS:**
THE ERGO STRATEGY University of Western Ontario
- **Mastership in Design research at UFSC**
Federal University of Santa Catarina - Brazil
- **Ergonomía** - Universidad de Navarra, Spain
- **Lectures** at university of Politecnico of Milan
- **Scandinavian Design** - Taschen



Excellent Swedish Design Awards: The Svensk Form/Swedish Society of Crafts and Design verifies and spreads knowledge about good, self-assured Swedish design.



Reddot Award: With a history spanning more than 50 years, the "Reddot Award: product design" is one of the most important international product competitions.




Japanese Good Design Award: Since 1957, the Good Design Award has been given to outstanding designs for more than 50 years.




The Handle

The handle diameter is optimized to transmit the maximum torque and increase productivity. Double handle for very high forces, when both hands are required.



We don't believe in average people, that is why we analyze anthropometrical databases to define the handle sizes in the assortment.



USER

SAFETY
PLEASURE
COOL TOOL
FEELING
USER PRIDE



INSPIRED BY
PROFESSIONALS



TASK

PRODUCTIVITY
& PROFITABILITY
QUALITY PERFORMANCE



ENVIRONMENT

DURABILITY
INNOVATION

The Colour Coding

The colour coding supports the cognitive processes related to the identification of the right screwdriver. Instead of having to check every tip, you can quickly see which one is what just by the colour of the first injection.

The Blade


The blade is made of high performance alloy steel for maximum durability.
Nickel chrome plated for maximum corrosion resistance.




The ERGO™ Screwdriver has been developed through our three phase Bahco ERGO™ Process. This program takes account of facts and experiences from users, ergonomists, industrial designers, and R&D departments, as well as extensive testing and trials.

It is easier to use, more comfortable to hold and significantly more functional. It reduces muscle tension and risk of accidents and injuries, while increasing job satisfaction, productivity and profitability.

ERGO™ TOOLS START THEIR LIVES AS A SERIES OF QUESTIONNAIRES TO END USERS ABOUT THEIR EXPERIENCES WITH PARTICULAR TOOLS AND HOW THEY WOULD LIKE TO SEE THEM IMPROVED.



THIS INFORMATION IS THEN COUPLED WITH DOCUMENTATION SHOWING HOW THE TOOL IS USED IN THE NORMAL WORK SITUATIONS.




● NEW SERIES OF PROTOTYPES

We tried very different handle diameters with different end users to understand what fits best the human hand.



**WE OBSERVE PROFESSIONALS
IN THEIR WORKING SITE TO
UNDERSTAND HOW THEY USE
THE TOOLS**

In Bahco, we are forerunners in hand tool design and ergonomics. We have been designing hand tools since 1856 and researching in ergonomics since 1978.



▲ SPECIFICATIONS

Bahco ERGO™ tools are made with the most advanced technologies. As manufacturers, we comply with the highest quality standards.

★ TEST AND BE CONVINCED

In Bahco we are completely confident about the superiority of ERGO™ tools. That is why we always develop a test unit for an ERGO™ tool so that professional users can feel the difference.



▲ FINAL DESIGN PROPOSAL



Choosing the right tip


THE BEST PERFORMING SCREWDRIVER IN THE WORLD

Tip Precision: The tip precision increases the lifetime of the screwdriver and avoids damage on a workpiece.

Torque Transmission: The screwdriver transmits the torque the and less force is needed to do the job.

Oxidation test: Less oxidation improves the lifetime and performance of the screwdriver.

Tip Strength: A strong tip will secure the tip precision throughout its lifetime.



More than just aesthetically pleasing



NO DOUBT, THE BEST SCREWDRIVER IN THE WORLD


Choosing the right colour code

CONTINUOUSLY UPDATING THE RANGE ACCORDING TO THE LATEST MARKET DEMANDS

Bahco continuously works with end users and experts in the market. Being close to the most demanding end users, Bahco anticipates on changes in applications used in all industries. To keep delivering the best solutions, Bahco is continuously developing the screwdriver assortment to fit the latest request and market applications.



EASY TO FIND THE RIGHT TIP IN YOUR TOOL CASE WITH THE DOUBLE COLOUR CODE WHICH DOESN'T WEAR OUT



Info handle sizes



**TORQUE & CONTROL
IN PERFECT BALANCE**



It's shape, it's dimensions and it's touch are all designed, extensively tested and developed, following a scientific process, to give the ERGO™ screwdrivers an optimal balance between torque (twisting force) and control. Because every situation demands another approach the ERGO™ screwdriver

range offers a set of five handle sizes and a stubby to improve productivity at all times. E.g. The double shape handles for tasks where you need to use both hands to get the extra torque or the new extra small handle size when control and precision is a must.

Slotted

Straight



						
BE-8002	0.3	2.0	60	17x103	5	30
BE-8010	0.4	2.5	60	17x103	5	31
BE-8210	0.4	2.5	75	17x103	5	33
BE-8020	0.5	3.0	60	17x103	5	30
BE-8020L	0.5	3.0	75	17x103	5	33
BE-8022	0.5	3.0	100	17x103	5	34
BE-8220	0.5	3.0	125	17x103	5	36
BE-8225	0.5	3.0	200	17x103	5	45
BE-8030	0.6	3.5	75	17x103	5	34
BE-8235	0.6	3.5	200	17x103	5	45
BE-8230	0.6	3.5	125	17x103	5	37
BE-8040	0.8	4.0	100	20x122	5	39
BE-8240	0.8	4.0	175	20x122	5	47
BE-8242	1.0	5.5	150	27x122	5	47
BE-8250L	1.0	5.5	200	27x122	5	90
BE-8241	1.0	5.5	125	27x122	5	47
BE-8251	1.0	6.0	150	36x122	5	44
BE-8252	1.2	6.5	150	36x122	5	47

Flat




						
BE-8150	1.0	5.5	100	27x122	5	66
BE-8250	1.0	5.5	150	27x122	5	112
BE-8155	1.2	6.5	125	36x122	5	73
BE-8255	1.2	6.5	150	36x122	5	116
BE-8256	1.6	8.0	150	36x122	5	135
BE-8257	1.6	8.0	175	36x122	5	140
BE-8258	1.6	10.0	200	36x165	5	195

Stubby




						
BE-8330	0.6	3.5	25	36x58	5	37
BE-8340	0.8	4.0	25	36x58	5	38
BE-8350	1.0	5.5	25	36x58	5	40
BE-8450	1.0	5.5	45	36x58	5	44
BE-8355	1.2	6.5	25	36x58	5	43
BE-8455	1.2	6.5	45	36x58	5	48
BE-8360	1.2	8.0	25	36x58	5	44


WHAT IS THE DIFFERENCE BETWEEN FLAT AND STRAIGHT?



						
BE-8158	1.0	5.5	125	27x122	9	5
BE-8159	1.2	6.5	150	36x122	11	5
BE-8160	1.6	8	125	36x122	14	5
BE-8260	1.6	8	175	36x122	14	5



						
BE-8865	1.6	8	175	36x165	14	5
BE-8870	1.6	10	175	36x165	18	5
BE-8880	2.0	12	200	36x165	18	5
BE-8890	2.5	14	200	36x165	18	5



DOUBLE HANDLE

Double shape handle, for use with both hands (in large sizes). Its larger surface of elastomer together with its advanced ergonomic design allows an optimum comfortable grip and maximum torque power.





BE-8600	PH 0	60	17x103	5	30
BE-8605	PH 0	100	17x103	5	80
BE-8608	PH 0	200	17x103	5	180
BE-8610	PH 1	75	27x122	5	156
BE-8611	PH 1	75	20x122	5	62
BE-8610L	PH 1	200	27x122	5	62
BE-8620	PH 2	100	36x122	5	81
BE-8621	PH 2	100	27x122	5	106
BE-8622	PH 2	150	36x122	5	106
BE-8620L	PH 2	200	36x122	5	127
BE-8623	PH 3	150	36x122	5	150

Double handle



BE-8624	PH 4	200	36x165	5	225
---------	------	-----	--------	---	-----

Hexagonal blade



BE-8628	PH 1	100	27x122	9	5	72
BE-8629	PH 2	125	36x122	11	5	122
BE-8630	PH 3	150	36x122	14	5	173

Hexagonal blade double handle




BE-8640	PH 4	200	36x165	18	5	292
---------	------	-----	--------	----	---	-----

Stubby



BE-8601	PH 1	25	36x58	5	40
BE-8602	PH 2	25	36x58	5	43

BOLSTER



Hexagonal profile shank with Hexagonal nut allows the use of a wrench open end spanner for demanding jobs which require extremely high torque power.



Pozidriv



BE-8800	PZ 0	60	17x103	5	30
BE-8810	PZ 1	75	27x122	5	62
BE-8811	PZ 1	75	20x122	5	62
BE-8810L	PZ 1	200	27x122	5	81
BE-8820	PZ 2	100	36x122	5	106
BE-8821	PZ 2	100	27x122	5	106
BE-8820L	PZ 2	200	36x122	5	127
BE-8823	PZ 3	150	36x122	5	150

Double handle



BE-8824	PZ 4	200	36x165	5	224

Hexagonal blade



BE-8828	PZ 1	100	27x122	9	72
BE-8829	PZ 2	125	36x122	11	122
BE-8830	PZ 3	150	36x122	14	173

Hexagonal blade double handle



BE-8840	PZ 4	200	36x165	18	292

Stubby




BE-8801	PZ 1	25	36x58	5	40
BE-8802	PZ 2	25	36x58	5	43

USING THE CORRECT COMBINATION

Three main consequences of using the wrong tip:

- 1 Needed torque is not applied
- 2 Increase the risk of breakage of the screwdriver tip
- 3 Working piece can be damaged



BLACK TIP = MORE ACCURACY

The black finish tip.

It's an oxidation process that is not adding any layer, therefore the tip is more precise. Use black finish tip for higher accuracy.





BE-8904	T 4	1.30	75	17x103	5	30
BE-8905	T 5	1.37	75	17x103	5	30
BE-8906	T 6	1.65	75	17x103	5	30
BE-8907	T 7	1.97	75	17x103	5	30
BE-8908	T 8	2.30	75	17x103	5	32
BE-8909	T 9	2.48	75	17x103	5	33
BE-8910	T 10	2.72	75	20x122	5	31
BE-8915	T 15	3.26	100	27x122	5	57
BE-8920	T 20	3.84	100	27x122	5	57
BE-8925	T 25	4.40	125	27x122	5	70
BE-8927	T 27	4.96	125	27x122	5	70
BE-8930	T 30	5.49	150	36x122	5	119

Double handle



BE-8940	T 40	6.60	150	36x165	5	130
BE-8945	T 45	7.70	150	36x165	5	178

TORX® TAMPER



BE-7907	TR 7	1.97	75	17x103	5	31
BE-7908	TR 8	2.30	75	17x103	5	31
BE-7909	TR 9	2.48	75	17x103	5	31
BE-7910	TR 10	2.72	75	20x122	5	31
BE-7915	TR 15	3.26	100	27x122	5	57
BE-7920	TR 20	3.84	100	27x122	5	57
BE-7925	TR 25	4.40	125	27x122	5	70
BE-7927	TR 27	4.96	125	27x122	5	70
BE-7930	TR 30	5.49	150	36x122	5	119

TORX® TAMPER double handle



BE-7940	TR 40	6.60	150	36x165	5	130

TORX® TAMPER

TORX®, Tamper-Resistant contains a post or pin in the center of the head that prevents a "standard" TORX® driver from being inserted which means safety screws cannot be unscrewed.



TORX® Ball



BE-7515	T 15	3.26	100	27x122	5	57
BE-7520	T 20	3.84	100	27x100	5	57
BE-7525	T 25	4.40	125	27x122	5	70
BE-7527	T 27	4.96	125	27x122	5	70
BE-7530	T 30	5.49	150	36x122	5	119
BE-7540	T 40	6.60	150	36x122	5	119

TORX® BALL

The spherical drive profile allows work at an angle of up to 30° with total effectiveness. TORX® BALL end tips are necessary when screwdriving in tight spots or at an angle.




TORX PLUS®



BE-7715	T 15	3,26	100	27x122	5	57
BE-7720	T 20	3,84	100	27x100	5	57
BE-7725	T 25	4,40	125	27x122	5	70
BE-7727	T 27	4,96	125	27x122	5	70
BE-7730	T 30	5,49	150	36x122	5	119
BE-7740	T 40	6,60	150	36x122	5	119

TORX PLUS®

TORX PLUS® is designed to allow greater torque, to minimize wear and to increase productivity by reducing down-time. With a larger contact area than the standard TORX®, the amount of transmission increases, as well as the life time of the tools.



TORX® vs. TORX PLUS®



Hexagonal



BE-6902	2	100	17x103	5	32
BE-6925	2.5	100	17x103	5	32
BE-6903	3	100	20x122	5	35

Ball



BE-8715	1.5	60	17x103	5	30
BE-8702	2	100	17x103	5	32
BE-8725	2.5	100	17x103	5	32
BE-8703	3	100	20x122	5	35
BE-8704	4	100	27x122	5	66
BE-8705	5	100	36x122	5	105
BE-8706	6	125	36x122	5	125
BE-8708	8	150	36x122	5	197

Ball Double handle



BE-8710	10	150	36x165	5	250

Ball inches



BE-8700-7/64	7/64"	100	20x122	5	35
BE-8700-5/32	5/32"	100	27x122	5	66
BE-8700-3/16	3/16"	100	27x122	5	105
BE-8700-7/32	7/32"	100	36x122	5	110
BE-8700-1/4	1/4"	125	36x122	5	126
BE-8700-5/16	5/16"	150	36x122	5	197

Ball Double handle



BE-8700-3/8	3/8"	150	36x165	5	250

HEX BALL

Screwdriver for Hexagonal head screws, ball ended, easy to insert in the screw head from a range of angles, up to 30°, giving better access than the standard hex.



Robertson



BE-9001	# 1	80	27x122	1	62
BE-9002	# 2	80	27x122	5	62
BE-9003	# 3	100	27x122	5	105



Torq-Set



BE-8080-1	1	75	27x122	5	58
BE-8080-2	2	75	27x122	5	58
BE-8080-3	3	75	27x122	5	58
BE-8080-4	4	75	27x122	5	58
BE-8080-5	5	75	27x122	5	58
BE-8080-6	6	75	27x122	5	58
BE-8080-8	8	100	27x122	5	75
BE-8080-10	10	100	27x122	5	75



Triwing



BE-9100	0	80	20x122	5	34
BE-9101	1	80	20x122	5	34
BE-9102	2	80	27x122	5	62
BE-9103	3	80	27x202	5	62
BE-9104	4	100	27x122	5	75
BE-9105	5	100	27x122	5	75



Awl

Round tip



BE-8985	6.0	100	27x122	5	67

Stubby



BE-8986	6	25	36x58	5	40

Reamer

Square tip



BE-8980	6.0	100	27x122	5	5.5

Nut Driver

Slim bore



BE-6400M-4	4	23x5.9	100	20x122	5	36
BE-6400M-5	5	23x6.95	100	20x122	5	38
BE-6400M-5,5	5.5	23x7.65	100	20x122	5	38
BE-6400M-7	7	23x9.8	100	20x122	5	42

Long bore



BE-7803	3	50x6	125	20x122	5	52
BE-7835	3.5	50x6	125	20x122	5	54
BE-7804	4	60x7	125	20x122	5	57
BE-7845	4.5	60x7	125	20x122	5	58
BE-7805	5	60x8	125	20x122	5	60
BE-7855	5.5	60x8.7	125	20x122	5	62
BE-7806	6	60x9.5	125	20x122	5	64
BE-7807	7	60x11	125	27x122	5	100
BE-7808	8	60x12	125	27x122	5	104
BE-7809	9	60x14	125	36x122	5	136
BE-7810	10	60x10	125	36x122	5	140
BE-7811	11	60x16	125	36x122	5	169
BE-7812	12	60x17	125	36x122	5	184

Long bore double handle



BE-7813	13	60x18	125	36x165	5	215
BE-7814	14	60x20	125	36x165	5	230

Flexible blade



BE-7606	6	11x27	150	27x122	5	126
BE-7607	7	11x27	150	27x122	5	126
BE-7608	8	11x27	150	27x122	5	126


slim bore



long bore



flexible blade



PERMANENT MAGNET



The ERGO™ bit holder with strong permanent magnet holds perfectly the bit.

Bit Holder



BE-8577	1/4"	9.5x24	118	36x122	5	5.5



ERGO™ Screwdriver Sets



Set **5** pcs



BE-9885

1

355

BE-8910, BE-8915,
BE-8920, BE-8925
T10x75, T15x100, T20x100,
T25x125, T30x150



Set **6** pcs



BE-9871

1

450

BE-8220S
0.5x3x100, insulated



BE-8611, BE-8621
PH1x75, PH2x100



BE-8820
PZ2x100



BE-8920, BE-8925
T20x100, T25x125



Set **6** pcs



BE-9881

1

450

BE-8020, BE-8040
0.5x3x60, 0.8x4x100



BE-8150, BE-8155
1.0x5.5x100, 1.2x6.5x125



BE-8610, BE-8620
PH1x75, PH2x100



Set **6** pcs



BE-9882

1

400

BE-8020, BE-8040
0.5x3x60, 0.8x4x100



BE-8150, BE-8155
1.0x5.5x100, 1.2x6.5x125



BE-8810, BE-8820
PZ1x75, PZ2x100



Set **6** pcs



BE-9884

1

450

BE-8040, BE-8241
0.8x4x100, 1.0x5.5x125



BE-8611, BE-8621
PH1x75, PH2x100



BE-8811, BE-8821
PZ1x75, PZ2x100



Set **6** pcs



BE-9886

1

430

BE-8030
0.6x3.5x75



BE-8150
1x5.5x100



BE-8611, BE-8621
PH1x75, PH2x100



BE-8811, BE-8821
PZ1x75, PZ2x100







Set **8** pcs

			
BE-9872		1	595
BE-8030 0.6x3.5x75			
BE-8611, BE-8621 PH1x75, PH2x100			
BE-8811, BE-8821 PZ1x75, PZ2x100			
BE-8915, BE-8920, BE-8925 T15x100, T20x100, T25x125			



Set **13** pcs

					
BE-9875		1		975	
BE-8040 0.8x4x100					
BE-8150, BE-8155 1.0x5.5x100, 1.2x6.5x125					
BE-8621 PH2x100					
BE-8811, BE-8821 PZ1x75, PZ2x100					
BE-8910, BE-8915, BE-8920, BE-8925 T10x75, T15x100, T20x100, T25x125					
BE-8010S, BE-8230S 0.4x2.5x75, 0.6x3.5x100 insulated					
BE-8810S PZ1x80, insulated					



Set **13** pcs

			
BE-9879		1	975
BE-8010, BE-8040, BE-8150 0.4x2.5x60, 0.8x4x100, 1x5.5x100			
BE-8611, BE-8621 PH1x75, PH2x100			
BE-8811, BE-8821 PZ1x75, PZ2x100			
BE-8910, BE-8915, BE-8920, BE-8925 T10x75, T15x100, T20x100, T25x125			
BE-8220SL 0.5x3x100, slim insulated			
BE-8620SL PH1x80, slim insulated			



Set **15** pcs

				
BE-9877		1	1100	
BE-8030 0.6x3.5x75				
BE-8150 1x5.5x100				
BE-8611, BE-8621 PH1x75, PH2x100				
BE-8811, BE-8821 PZ1x75, PZ2x100				
BE-8910, BE-8915, BE-8920, BE-8925 T10x75, T15x100, T20x100, T25x125				
BE-8220S, BE-8040S, BE-8050S 0.5x3x100, 0.8x4x100, 1x5.5x125, insulated				
BE-8610S, BE-8620S PH1x80, PH2x100, insulated				



ERGO™ Handle with Interchangeable Blades

NOT ONLY THE MOST COMFORTABLE SCREWDRIVER BUT THE MOST UNIVERSAL TOO!

New to the ERGO™ assortment is the screwdriver with interchangeable blades, an ERGO™ handle combined with a quick release bit holder.

The ERGO™ handle with interchangeable blades combines the comfort of an ERGO™ screwdriver with the flexibility of easy changing blades.

ERGO™ handle with quick release



BE-8575	ERGO™ HANDLE WITH QUICK RELEASE	1	100	

Spare blades 100 mm



8020-2P	(x2) 1/4" 0.5x3.0	100	1	55
8030-2P	(x2) 1/4" 0.6x3.5	100	1	55
8040-2P	(x2) 1/4" 0.8x4.0	100	1	55
8242-2P	(x2) 1/4" 1x5.5	100	1	55
8252-2P	(x2) 1/4" 1.2x6.5	100	1	55

8600-2P	(x2) 1/4" PH0	100	1	55
8610-2P	(x2) 1/4" PH1	100	1	55
8620-2P	(x2) 1/4" PH2	100	1	55
8630-2P	(x2) 1/4" PH3	100	1	55

8800-2P	(x2) 1/4" PZ0	100	1	55
8810-2P	(x2) 1/4" PZ1	100	1	55
8820-2P	(x2) 1/4" PZ2	100	1	55
8830-2P	(x2) 1/4" PZ3	100	1	55

8910-2P	(x2) 1/4" TORX10	100	1	55
8915-2P	(x2) 1/4" TORX15	100	1	55
8920-2P	(x2) 1/4" TORX20	100	1	55
8925-2P	(x2) 1/4" TORX25	100	1	55
8927-2P	(x2) 1/4" TORX27	100	1	55
8930-2P	(x2) 1/4" TORX30	100	1	55
8940-2P	(x2) 1/4" TORX40	100	1	55

8703-2P	(x2) 1/4" HEX BALL 3	100	1	55
8704-2P	(x2) 1/4" HEX BALL 4	100	1	55
8705-2P	(x2) 1/4" HEX BALL 5	100	1	55
8706-2P	(x2) 1/4" HEX BALL 6	100	1	55



Spare blades 300 mm



8040L-2P	(x2) 1/4" 0.8x4	300	1	170
8242L-2P	(x2) 1/4" 1.0x5.5	300	1	170
8252L-2P	(x2) 1/4" 1.2x6.5	300	1	170

8610L-2P	(x2) 1/4" PH1	300	1	170
8620L-2P	(x2) 1/4" PH2	300	1	170

8810L-2P	(x2) 1/4" PZ1	300	1	170
8820L-2P	(x2) 1/4" PZ2	300	1	170

8915L-2P	(x2) 1/4" TORX15	300	1	170
8920L-2P	(x2) 1/4" TORX20	300	1	170
8925L-2P	(x2) 1/4" TORX25	300	1	170
8927L-2P	(x2) 1/4" TORX27	300	1	170
8930L-2P	(x2) 1/4" TORX30	300	1	170


Spare blades 400 mm



8252XL-1P	(x1) 1/4" 1.2x6.5	400	1	120

8620XL-1P	(x1) 1/4" PH2	400	1	120
8630XL-1P	(x1) 1/4" PH3	400	1	120

8820XL-1P	(x1) 1/4" PZ2	400	1	120
8830XL-1P	(x1) 1/4" PZ3	400	1	120





ERGO™ handle with interchangeable blades

BE-8571	7 pcs set, ERGO™ handle with interchangeable blades: PH1, PH2, PZ1, PZ2, 1x5.5, 1.2x6.5	1	425
BE-8572	9 pcs set, ERGO™ handle with interchangeable blades: PH1, PH2, PZ1, PZ2, T10, T15, 1x5.5, 1.2x6.5	1	485
BE-8573	8 pcs set, ERGO™ handle with interchangeable blades: T10, T15, T20, T25, T27, T30, T40	1	450
BE-8576	22 pcs set, ERGO™ handle with interchangeable blades (16 pcs): PH1, PH2, PH3, PZ1, PZ2, PZ3, T10, T15, T20, T25, T30, T40, 0.6x3.5, 0.8x4.0, 1.0x5.5, 1.2x6.5 Bits (6 pcs): H2,5, H3, H4, H5, H6, H8	1	600
BE-8574	8 pcs set, ERGO™ handle with interchangeable blades: PH1, PH2, PZ2, 0.8x40, T20, T25, T30	1	450



ERGO™ handle with Interchangeable Blades

- 100 mm Hexagonal blades
- In a Nylon pouch or Foam inlay
- Available in 4 sets or as spare parts








ERGO™ Impact driver



Designed for **chiseling, fastening and loosening heavily rusted, corroded and seized screws**, this screwdriver transfers impact force directly to the work surface.

The **striking metal cap** at the top of the handle gives additional protection for jobs requiring high impact and maximum force.





For strength and capability in your toughest jobs, the **ERGO™ Impact Driver** can do it all.

— Slotted

Straight



BE-8135TB	0.6	3.5	75	27x122	—	10	65
BE-8145TB	0.8	4.5	100	27x122	5	10	65
BE-8150TB	1.0	5.5	100	27x122	5	10	75
BE-8155TB	1.2	6.5	125	36x122	6	10	125
BE-8256TB	1.6	8.0	150	36x122	8	10	162
BE-8258TB	1.6	10	175	36x122	8	10	210
BE-8262TB	2.0	12	200	36x122	8	10	291

+ Phillips



						
BE-8610TB	PH 1	100	27x122	5	10	72
BE-8620TB	PH 2	125	36x122	6	10	122
BE-8623TB	PH 3	150	36x122	8	10	173
BE-8624TB	PH 4	175	36x122	8	10	292

+ Pozidriv



						
BE-8810TB	PZ 1	100	27x122	5	10	72
BE-8820TB	PZ 2	125	36x122	6	10	122
BE-8823TB	PZ 3	150	36x122	8	10	173
BE-8824TB	PZ 4	175	36x122	8	10	292

+ Torx®



BE-8910TB	T 10	2.72	75	27x122	—	5	65
BE-8915TB	T 15	3.26	100	27x122	5	5	98
BE-8920TB	T 20	3.84	100	27x122	5	5	100
BE-8925TB	T 25	4.40	100	27x122	5	5	102
BE-8927TB	T 27	4.96	125	27x122	5	5	125
BE-8930TB	T 30	5.49	150	36x122	6	5	175
BE-8940TB	T 40	6.60	150	36x122	8	5	232



ERGO™ Impact Driver Screwdriver Sets



 		Set 5 pcs	
			
BE-9885TB	1	600	
BE-8915TB, BE-8920TB, BE-8925TB, BE-8930TB, BE-8940TB T15x100, T20x100, T25x100, T30x150, T40x150			

  		Set 6 pcs	
			
BE-9881TB	1	750	
BE-8135TB, BE-8145TB, BE-8150TB, BE-8155TB 0.6x3.5x75, 0.8x4.5x100, 1x5.5x100, 1.2x6.5x125			
BE-8610TB, BE-8620TB PH1x100, PH2x125			

  		Set 6 pcs	
			
BE-9882TB	1	750	
BE-8135TB, BE-8145TB, BE-8150TB, BE-8155TB 0.6x3.5x75, 0.8x4.5x100, 1x5.5x100, 1.2x6.5x125			
BE-8810TB, BE-8820TB PZ1x100, PZ2x125			








ERGO™ Insulated

Insulated Screwdrivers

For work on live equipment up to 1000 volts, Bahco offers a wide range of insulated safety tools. All Bahco insulated tools are manufactured according to the **International Standard IEC60900** for working with **live systems up to 1000 V AC and 1500 V DC**.



Dielectric test

The tools are immersed in water for 24 hours. A voltage of 10kV is then continuously applied for 3 minutes. The test is considered successful if no electrical puncture, spark over, or flashover occurs during the test period. Leakage limits must not be exceeded.



Impact test

The tools are cooled to -25 °C for 2 hours. Then, a special hammer is used with some force on the insulating layer. The test is considered successful if the insulating material shows no breaks and passes the dielectric test.



Insulation adhesion test

The tools are stored at a temperature of 70 °C for 168 hours. Then, a force of 490 N is applied in the direction of the line dividing the insulating material from the conductive part for 3 minutes. During this test the insulation material must stay firmly attached to the tools.



Flame test

When placed over a fire, where the height of the flames on the tools does not exceed 120 mm, if the insulation material does not melt or leak, then the test is passed.




Permanent marking durability

The markings are rubbed for 15 seconds with a rag soaked in water, and then for 15 seconds with a rag soaked in isopropanol. The test is passed if, after this process, the markings are still legible.



They follow strict quality controls and all tools are subjected to the most stringent, individual tests. We recommend following the safety instructions very closely when working with any live systems.

**Penetration test**

The insulated surfaces of the tools are pressed with a special device. A voltage of 5000 V is then applied to the tool for 3 minutes. The test is considered successful if no electrical puncture, spark-over, or flash-over occurs during the test period.

**Visual and dimensional**

The tools, and in particular the insulation, are visually controlled and have to be free from external defects. The markings have to be perfectly legible and the dimensions have to be in accordance with the standard.

**SCREWDRIVERS FOR
ELECTRICIANS
FOR WORK ON LIVE EQUIPMENT,
UP TO 1000 V**

**ALL INSULATED
SCREWDRIVERS ARE TESTED
100% FOLLOWING A STRICT
QUALITY CONTROL.
BAHCO SCREWDRIVERS ARE
A GUARANTEE OF QUALITY
AND SAFETY.**

**ROUTINE TESTS IN
ACCORDANCE TO
IEC60900 SPECIFICATION**



ERGO™ Slim Insulated Screwdrivers


The Bahco ERGO™ insulated assortment includes the “Slim” line range.

The normal blades are limited in confined spaces. The new “slim” blades are **30% slimmer than regular insulated blades** for better accessibility and let users access deeply inset screws and operate spring tension clamp terminal blocks.

All Bahco insulated tools are manufactured according to the International Standard IEC60900 for working with **live systems up to 1000 V AC and 1500 V DC**. All insulated screwdrivers are tested 100% following a strict quality control to guarantee quality and user safety.



SLIM BLADES




THE BLADES ARE 30% SLIMMER THAN REGULAR INSULATED BLADES FOR BETTER ACCESSIBILITY (E.G. SUNKEN SCREWS AND SPRING ELEMENTS)



Insulated ERGO™ Screwdrivers

- Screwdriver developed according to the scientific ERGO™ process
- **For work on live equipment, up to 1000 V**
- Handle: 3-component handle, for maximum user comfort and force transmission
- Easy to choose the right tip, with the colour-coded handle and the symbol on the domed end
- High performance alloy steel, insulation moulded directly into the blade
- Black finish tip for higher accuracy
- Individually inspected and manufactured according to IEC 60900



Slim Insulated Blades

— Slotted



	mm	mm	mm	mm	mm	g
BE-8220SL	0.5	3	100	17x103	5	33
BE-8230SL	0.6	3.5	100	17x103	5	33
BE-8040SL	0.8	4	100	20x122	5	33
BE-8050SL	1.0	5.5	125	27x122	5	62
BE-8255SL	1.2	6.5	150	36x122	5	105

✚ Pozidriv




		mm	mm	mm	g
BE-8810SL	PZ 1	80	20x122	5	64
BE-8820SL	PZ 2	100	27x122	5	110

✚ Phillips



		mm	mm	mm	g
BE-8610SL	PH 1	80	20x122	5	64
BE-8620SL	PH 2	100	27x122	5	108

✚ Torx®



						
BE-8910SL	T 10	2.72	100	20x122	5	33
BE-8915SL	T 15	3.26	100	20x122	5	62
BE-8920SL	T 20	3.84	100	20x122	5	62
BE-8925SL	T 25	4.40	125	27x122	5	77
BE-8930SL	T 30	5.49	150	36x122	5	129

✚ Combi tip SL/PH




		mm	mm	mm	g
BE-8510SL	5 / PH1	80	20x122	5	60
BE-8520SL	6 / PH2	100	27x122	5	100

✚ Combi tip SL/PZ



		mm	mm	mm	g
BE-8710SL	5 / PZ1	80	20x122	5	60
BE-8720SL	6 / PZ2	100	27x122	5	100

THE BLADES ARE 30% SLIMMER THAN REGULAR INSULATED BLADES FOR BETTER ACCESSIBILITY (E.G. SUNKEN SCREWS AND SPRING ELEMENTS)



Slim Insulated Sets

Hanging twinpack with 2 screwdrivers



Set 2 pcs



BE-9891SL

1

132

BE-8610SL, BE-8620SL
PH1x80, PH2x100



Set 2 pcs



BE-9890SL

1

175

BE-8710SL, BE-8720SL
5/PZ1, 6/PZ2, combi tip



Set 2 pcs



BE-9894SL

1

132

BE-8810SL, BE-8820SL
PZ1x80, PZ2x100



XXL



Set 4 pcs



BE-9880SL

1

320

BE-8910SL, BE-8915SL,
BE-8920SL, BE-8925SL
T10x100, T15x100, T20x100,
T25x125



Set 5 pcs



BE-9882SL

1

440

BE-8220SL, BE-8040SL,
BE-8050SL
0.5x3.0x75, 0.8x4.0x100,
1.0x5.5x125



BE-8810SL, BE-8820SL
PZ1x80, PZ2x100



Set 5 pcs



BE-9881SL

1

440

BE-8220SL, BE-8040SL,
BE-8050SL
0.5x3.0x75, 0.8x4.0x100,
1.0x5.5x125



BE-8610SL, BE-8620SL
PH1x80, PH2x100



Set 12 pcs



BE-9878SL

1

900

BE-8010S
0.4x2.5x75 standard



BE-8220SL, BE-8230SL,
BE-8040SL, BE-8050SL
0.5x3.0x75, 0.5x3.5x100,
0.8x4.0x100, 1.0x5.5x125



BE-8610SL / BE-8620SL
PH1x80, PH2x100




BE-8810SL, BE-8820SL
PZ1x80, PZ2x100



BE-8910SL
T10x100



BE-8510SL, BE-8520SL
5/PH1, 6/PH2, combi tip



Standard insulated screwdrivers

Slotted



	mm	mm	mm	mm		
BE-8010S	0.4	2.5	75	17x103	5	30
BE-8220S	0.5	3	100	17x103	5	33
BE-8230S	0.6	3.5	100	17x103	5	33
BE-8040S	0.8	4	100	20x122	5	33
BE-8050S	1.0	5.5	125	27x122	5	62
BE-8255S	1.2	6.5	150	36x122	5	105
BE-8065S	1.2	8	175	36x122	5	127
BE-8258S	1.6	10	200	36x165	5	270
BE-8259S	2.0	12	200	36x165	5	280

Phillips



		mm	mm		
BE-8600S	PH 0	75	17x103	5	31
BE-8610S	PH 1	80	27x122	5	64
BE-8611S	PH 1	80	20x122	5	33
BE-8612S	PH 1	150	27x122	5	155
BE-8620S	PH 2	100	36x122	5	108
BE-8621S	PH 2	100	27x122	5	75
BE-8622S	PH 2	175	36x122	5	175
BE-8630S	PH 3	150	36x122	5	159
BE-8640S	PH 4	200	36x165	5	268

Pozidriv



		mm	mm		
BE-8800S	PZ 0	75	17x103	5	31
BE-8810S	PZ 1	80	27x122	5	64
BE-8811S	PZ 1	80	20x122	5	33
BE-8812S	PZ 1	150	27x122	5	155
BE-8820S	PZ 2	100	36x122	5	110
BE-8821S	PZ 2	100	27x122	5	75
BE-8822S	PZ 2	175	36x122	5	175
BE-8830S	PZ 3	150	36x122	5	159
BE-8840S	PZ 4	200	36x161	5	268

Torx®




							
BE-8905S	T 5	1.42	75	17x103	5	200	
BE-8906S	T 6	1.70	75	17x103	5	200	
BE-8907S	T 7	1.99	75	20x122	5	200	
BE-8908S	T 8	2.31	75	20x122	5	200	
BE-8909S	T 9	2.50	75	20x122	5	200	
BE-8910S	T 10	2.72	100	20x122	5	33	
BE-8915S	T 15	3.26	125	27x122	5	62	
BE-8920S	T 20	3.84	125	27x122	5	62	
BE-8925S	T 25	4.40	150	27x122	5	77	
BE-8930S	T 30	5.49	175	36x122	5	129	

Hexagonal



	mm	mm	mm		
BE-8725S	2.5	100	17x103	5	33
BE-8703S	3	125	20x122	5	62
BE-8704S	4	150	20x122	5	78
BE-8705S	5	175	27x122	5	128
BE-8706S	6	150	27x122	5	159
BE-8708S	8	200	36x122	5	235

Nut Driver



	 mm	 mm	 mm	 mm		
BE-7855S	5.5	27x122	125	20x122	5	62
BE-7806S	6	27x122	125	20x122	5	64
BE-7807S	7	27x122	125	27x122	5	100
BE-7808S	8	27x122	125	27x122	5	104
BE-7809S	9	36x122	125	36x122	5	136
BE-7810S	10	36x122	125	36x122	5	140

Insulated Combi Screwdrivers

IEC 60900  1000V  

Some tasks demand speciality tools.

That is why we have specially made combi screwdrivers for use in terminal blocks, control cabinets, switches, relays, or similar.



Insulated combi for Slotted and Phillips head screws



Combi tip SL/PH

 IEC60900  1000V  

     					
BE-8510S	5 / PH1	80	27x122	5	60
BE-8520S	6 / PH2	100	36x122	5	100



Insulated combi for Slotted and Pozidriv head screws



Combi tip SL/PZ

 IEC60900  1000V  

     					
BE-8710S	5 / PZ1	80	27x122	5	60
BE-8720S	6 / PZ2	100	36x122	5	100



ERGO™ Insulated Screwdriver Sets

Hanging twinpack with 2 screwdrivers



IEC60900 1000V

Set 2 pcs

		1	450
BE-9890S			
BE-8710S, BE-8720S 5/PZ1, 6/PZ2, combi tip			



IEC60900 1000V

Set 5 pcs

		1	450
BE-9881S			
BE-8220S, BE-8040S, BE-8050S 0.5x3x100, 0.8x4x100, 1x5.5x125			
BE-8610S, BE-8620S PH1x80, PH2x100			

IEC60900 1000V

Set 5 pcs

		1	450
BE-9882S			
BE-8220S, BE-8040S, BE-8050S 0.5x3x100, 0.8x4x100, 1x5.5x125			
BE-8810S, BE-8820S PZ1x80, PZ2x100			

IEC60900 1000V

Set 6 pcs

		1	450
BE-9884S			
BE-8220S, BE-8040S 0.5x3x100, 0.8x4x100			
BE-8810S, BE-8820S PZ1x80, PZ2x100			
BE-8710S, BE-8720S 5/PZ1, 6/PZ2, combi tip			

IEC60900 1000V

Set 5 pcs

		1	455
BE-9885S			
806-11 0.6x3x65			
BE-8510S, BE-8520S 5/PH1, 6/PH2, combi tip			
BE-8710S, BE-8720S 5/PZ1, 6/PZ2, combi tip			


Set 5 pcs

BE-9871SL			1	450
BE-8040SL 0.8x4.0x100	ⓘ			
BE-8220SL 0.5x3x100	ⓘ			
BE-8610SL, BE-8620SL PH1x80, PH2x100	⊕			
BE-8910SL T10x100	⊛			


Set 5 pcs

BE-9872 SL			1	450
BE-8040SL 0.8x4.0x100	ⓘ			
BE-8220SL 0.5x3x100	ⓘ			
BE-8810SL PZ1x80	⊕			
BE-8910SL, BE-8920SL T10x100, T20x100	⊛			


Set 7 pcs

BE-9887S			1	460
806-1-1 0.6x3x65	ⓘ			
BE-8010S, BE-8230S, BE-8040S, BE-8050S 0.4x2.5x75, 0.6x3.5x100, 0.8x4.0x100, 1.0x5.5x125	ⓘ			
BE-8610S, BE-8621S PH1x80, PH2x100	⊕			


Set 7 pcs

BE-9889S			1	450
806-1-1 0.6x3x65	ⓘ			
BE-8010S, BE-8230S, BE-8040S, BE-8050S 0.4x2.5x75, 0.6x3.5x100, 0.8x4.0x100, 1.0x5.5x125	ⓘ			
BE-8810S, BE-8821S PZ1x80, PZ2x100	⊕			


Set 7 pcs

BE-9888S			1	530
BE-8010S, BE-8220S, BE-8040S, BE-8050S 0.4x2.5x75, 0.5x3.0x100, 0.8x4.0x100, 1.0x5.5x125	ⓘ			
BE-8800S, BE-8820S, BE-8830S PZ0x75, PZ2x100, PZ3x150	⊕			


Set 14 pcs

BE-9876S			1	1076
BE-8010S, BE-8220S, BE-8230S, BE-8040S, BE-8050S 0.4x2.5x75, 0.5x3x100, 0.6x3.5x100, 0.8x4.0x100, 1.0x5.5x125	ⓘ			
BE-8610S, BE-8620S PH1x80, PH2x100	⊕			
BE-8810S, BE-8820S PZ1x80, PZ2x100	⊕			
BE-8910S, BE-8915S, BE-8920S T10x100, T15x125, T20x125	⊛			
BE-8710S, BE-8720S 5/PZ1, 6/PZ2, combi tip	⊕			







ERGO™ Stainless Steel

Stainless Steel Screwdrivers

Stainless steel is a leading material for maximum quality requirements in both the interior design and building construction sectors. **Stainless steel** is corrosion and antacid-resistant, weather-resistant, hygienic and easy to clean. Non-rusting stainless steel plays an important role in sectors such as the food industry, medical industry, offshore applications and automotive engineering.

However, rust can also be created even on non-rusting stainless steel through contact with a contaminated tool. This leaves foreign particles upon the stainless steel surface that then rust. This “extraneous rust” is not only a aesthetic problem but a safety threat.




That's why non-rusting stainless steel needs non-rusting stainless steel tools.

The stainless steel protects against the formation of rust that can occur when screwdriving jobs on stainless steel are performed with non-stainless steel tools.

STAINLESS STEEL TOOLS CAN BE USED WITH NON STAINLESS STEEL SCREWS

However stainless steel screws need stainless steel tools. The reason is that the contact with conventional tool creates «foreign» particles upon the stainless steel surface and start rusting when exposed to oxygen.



Slotted

Straight



						
BE-8020i	0.5	3.0	60	17x103	5	30
Be-8030i	0.6	3.5	75	17x103	5	34
BE-8040i	0.8	4.0	100	20x122	5	39
BE-8241i	1.0	5.5	125	27x122	5	44
BE-8252i	1.2	6.5	150	36x122	5	47

Phillips



						
BE-8600i	PH 0	60	17x103	5	30	
BE-8610i	PH 1	75	27x122	5	62	
BE-8620i	PH 2	100	36x122	5	106	
BE-8623i	PH 3	150	36x122	5	150	

Pozidriv



						
BE-8800i	PZ 0	60	17x103	5	30	
BE-8810i	PZ 1	75	27x122	5	62	
BE-8820i	PZ 2	100	36x122	5	106	
BE-8823i	PZ 3	150	36x122	5	150	

Torx®



						
BE-8910i	T 10	2.72	75	20x122	5	30
BE-8915i	T 15	3.26	100	27x122	5	55
BE-8920i	T 20	3.84	100	27x122	5	60
BE-8925i	T 25	4.40	125	27x122	5	70



Screwdriver Sets



Set 6 pcs

BE-9881i

1

450

Set 6 pcs

BE-9882i

1

450



Non Sparking Tools

Bahco has a non sparking tool range which fits the stringent safety demands of different segments such as Oil & Gas, Mining and other industries where there is a risk of fire or explosion due to sparks, the so called ATEX zone ("Atmosphères Explosibles") dust. The risk of explosion is related to combustible or easily ignitable vapors.

Using non sparking tools helps to protect the user and the workplace and provides a higher safety.

As regulations develop, more and more companies, in various industries, see a demand for non sparking tools in order to assure a higher safety.



**NON SPARKING TOOLS
ARE COMMONLY USED IN
PETROCHEMICALS/CHEMICALS,
OIL AND GAS GENERATION, GAS
TRANSPORTATION AND REFINERIES.
CERTIFIED BY THE BAM INSTITUTE**

Slotted

Flat



NSB300-4.5-100	0.5	4.5	100	20x122	1	50
NSB300-6-100	0.8	6	100	27x122	1	75
NSB300-8-150	1.2	8	150	36x122	1	130
NSB300-10-300	1.8	10	200	36x122	1	245
NSB300-11-350	2	11	350	36x122	1	320
NSB300-12-400	2.4	12	400	36x122	1	415
NSB300-13-450	2.4	13	450	36x122	1	460



NS301-3-50	0.5	3	50	20x122	1	35
NS301-4-100	0.8	4	100	20x122	1	50
NS301-4-150	0.8	4	150	20x122	1	130
NS301-5-100	1	5	100	20x122	1	50
NS301-5-200	1	5	200	27x122	1	180
NS301-6-100	1	6	100	27x122	1	50
NS301-8-150	1.2	8	150	36x122	1	130
NS301-10-200	1.6	10	200	36x122	1	180
NS301-10-300	1.6	10	300	36x122	1	230



NSB301-3-50	0.5	3	50	20x122	1	35
NSB301-4-100	0.8	4	100	20x122	1	50
NSB301-4-150	0.8	4	150	20x122	1	130
NSB301-5-100	1	5	100	20x122	1	50
NSB301-5-200	1	5	200	27x122	1	180
NSB301-6-100	1	6	100	27x122	1	50
NSB301-8-150	1.2	8	150	36x122	1	130
NSB301-10-200	1.6	10	200	36x122	1	180
NSB301-10-300	1.6	10	300	36x122	1	230



Slotted



						
NS300-3-50	0.4	3	50	20x122	1	35
NS300-3-75	0.4	3	75	20x122	1	35
NS300-4-75	0.5	4	75	20x122	1	45
NS300-4.5-50	0.5	4.5	50	20x122	1	43
NS300-4.5-100	0.5	4.5	100	20x122	1	50
NS300-5-75	0.6	5	75	20x122	1	70
NS300-5-100	0.6	5	100	20x122	1	75
NS300-6-100	0.8	6	100	27x122	1	75
NS300-6-125	0.8	6	125	27x122	1	100
NS300-6-150	0.8	6	150	27x122	1	110
NS300-7-150	1	7	150	27x122	1	125
NS300-8-150	1.2	8	150	36x122	1	130
NS300-8-200	1.2	8	200	36x122	1	165
NS300-9-250	1.4	9	250	36x122	1	185
NS300-10-200	1.8	10	200	36x122	1	165
NS300-10-300	1.8	10	300	36x122	1	245
NS300-11-250	2	11	250	36x122	1	260
NS300-11-300	2	11	300	36x122	1	320
NS300-11-350	2	11	350	36x122	1	320
NS300-12-400	2.4	12	400	36x122	1	415
NS300-13-450	2.4	13	450	36x122	1	460



						
NSB300-3-50	0.4	3	50	20x122	1	35
NSB300-3-75	0.4	3	75	20x122	1	35
NSB300-4-75	0.5	4	75	20x122	1	45
NSB300-4.5-50	0.5	4.5	50	20x122	1	43
NSB300-4.5-100	0.5	4.5	100	20x122	1	50
NSB300-5-75	0.6	5	75	20x122	1	70
NSB300-5-100	0.6	5	100	20x122	1	75
NSB300-6-100	1.0	6	100	27x122	1	75
NSB300-6-125	0.8	6	125	27x122	1	100
NSB300-6-150	0.8	6	150	27x122	1	110
NSB300-7-150	1	7	150	27x122	1	125
NSB300-8-150	1.2	8	150	36x122	1	130
NSB300-8-200	1.2	8	200	36x122	1	165
NSB300-9-250	1.4	9	250	36x122	1	185
NSB300-10-200	1.8	10	200	36x122	1	165
NSB300-10-300	1.8	10	200	36x122	1	245
NSB300-11-250	2	11	250	36x122	1	260
NSB300-11-300	2	11	300	36x122	1	320
NSB300-11-350	2	11	350	36x122	1	320
NSB300-12-400	2.4	12	400	36x122	1	415
NSB300-13-450	2.4	13	450	36x122	1	460

Phillips



					
NSB302-0-50	PH 0	50	20x122	1	35
NSB302-1-100	PH 1	100	20x122	1	50
NSB302-2-125	PH 2	125	27x122	1	80
NSB302-3-150	PH 3	150	36x122	1	130
NSB302-4-300	PH 4	300	36x122	1	230



					
NS302-0-50	PH 0	50	20x122	1	35
NS302-1-100	PH 1	100	20x122	1	50
NS302-2-125	PH 2	125	27x122	1	80
NS302-3-150	PH 3	150	36x122	1	130
NS302-4-300	PH 4	300	36x122	1	230

Pozidriv



					
NSB304-0-50	PZ 0	50	20x122	1	35
NSB304-1-100	PZ 1	100	20x122	1	50
NSB304-2-125	PZ 2	125	27x122	1	80
NSB304-3-150	PZ 3	150	36x122	1	130
NSB304-4-300	PZ 4	300	36x122	1	230



					
NS304-0-50	PZ 0	50	20x122	1	35
NS304-1-100	PZ 1	100	20x122	1	50
NS304-2-125	PZ 2	125	27x122	1	80
NS304-3-150	PZ 3	150	36x122	1	130
NS304-4-300	PZ 4	300	36x122	1	230



TOOLS @ HEIGHT

Bahco is member of Drops (dropped objects prevention scheme) an industry-wide initiative focused on preventing dropped objects, with the ultimate goal of delivering a second nature dropped objects prevention strategy

across our industry. All our tool solutions are approved according to DROPS practices. For each tool, Bahco has developed the best solution to work at height. Each solution is certified and they cannot be unassembled.

DROPS BASIC REMIT IS TO CONSIDER ALL AVENUES AVAILABLE FOR IMPROVING THE INDUSTRY'S DROPPED OBJECT PREVENTION PERFORMANCE



They distil and identify the key learnings and deliver these back into the industry in the form of awareness, best practice, recommendations, lessons, tools and techniques. DROPS is a Global Work Group, represented by 200 operators, contractors, service companies and industry bodies, all sharing commitment and enthusiasm for the common goal of dropped object prevention.

ALL SOLUTIONS DEVELOPED BY BAHCO

1 Safety chuck

Designed for screwdrivers to allow free rotation of tool



2 Kevlar string

Very strong and fire resistant textile used for insulated screwdriver with special glue to avoid dismantling



3 Dyneema string

Extremely strong textile. Soft but very resistant with an aluminum closure to avoid dismantling



— Slotted



	mm	mm	mm	mm		g
TAHBE-8020L	0.5	3	75	20x122	1	33
TAHBE-8030	0.6	3.5	75	20x122	1	34
TAHBE-8040	0.8	4	100	20x122	1	39
TAHBE-8241	1	5.5	150	27x122	1	47
TAHBE-8252	1.2	6.5	150	36x122	1	47



	mm	mm	mm	mm		g
TAHBE-8155	1.2	6.5	125	36x122	1	112
TAHBE-8257	1.6	8	175	36x122	1	140
TAHBE-8258	1.6	10	200	36x161	1	195



	mm	mm	mm	mm		g
TAHBE-8260	1.6	8	175	36x122	1	112



	mm	mm	mm	mm		g
TAHBE-8350	1	5.5	25	36x58	1	40

Pin releaser



	mm	mm	mm		g
TAHPINRELEASER	6	50	36x58	1	64

+ Phillips



		mm	mm		g
TAHBE-8610	PH 1	75	27x122	1	62
TAHBE-8611	PH 1	75	20x122	1	62
TAHBE-8620	PH 2	100	36x122	1	106
TAHBE-8620L	PH 2	200	36x122	1	127
TAHBE-8623	PH 3	150	36x122	1	150
TAHBE-8624	PH 4	200	36x165	1	225



		mm	mm		g
TAHBE-8630	PH 3	150	36x122	14	173



		mm	mm		g
TAHBE-8602	PH 2	25	36x58	1	43

+ Pozidriv



		mm	mm		g
TAHBE-8810	PZ 1	75	27x122	1	62
TAHBE-8820	PZ 2	100	36x122	1	106



		mm	mm		g
TAHBE-8830	PZ 3	150	36x122	14	173





TAHBE-8910	T 10	2.72	75	20x122	1	31
TAHBE-8915	T 15	3.26	100	27x122	1	57
TAHBE-8920	T 20	3.84	100	27x122	1	57
TAHBE-8925	T 25	4.40	125	27x122	1	70
TAHBE-8930	T 30	5.49	150	36x122	1	119

Insulated



TAHBE-8040S	0.8	4	100	20x122	1	33
TAHBE-8050S	1.0	5.5	125	27x122	1	62
TAHBE-8220S	0.5	3	100	20x122	1	33
TAHBE-8255S	1.2	6.5	150	36x122	1	105



TAHBE-8610S	PH 1	80	27x122	1	64	
TAHBE-8620S	PH 2	100	36x122	1	108	
TAHBE-8630S	PH 3	150	36x122	1	159	
TAHBE-8640S	PH 4	200	36x165	1	268	



TAHBE-8910S	T 10	2.72	75	20x122	1	40
TAHBE-8915S	T 15	3.26	75	27x122	1	62
TAHBE-8920S	T 20	3.84	75	27x122	1	62
TAHBE-8925S	T 25	4.4	75	27x122	1	77
TAHBE-8930S	T 30	5.49	75	36x122	1	129



Slim



TAHBE-8820SL	PZ 2	100	36x122	1	100	







BAHCOFit

“For everyone, for everything”

When the Premium was presented in 1993 even we could not imagine that it would become the undisputed leader in every professional's toolbox. The challenge we faced after 22 years was how to develop and launch the next generation screwdriver, a challenge we rose to and we are confident will become another milestone in our history. A product that has been inspired by our own R+D+i and made in our screwdriver manufacturing plant.

100 % made in Spain.

BahcoFit has a new patented handle design, from which 75 % is rubber, and with vertical grooves which makes for the perfect grip. Combined with performance alloy steel blades and more than 50 years manufacturing millions of screwdrivers resulting in the highest quality finished product. **BahcoFit** now arrives to be the right screwdriver for professionals:

- **Adapted to the hand**, and not vice versa
- **Adapted to all types of uses and demands**
- **Developed for modern needs**



Rounded end allows you to apply force without hurting the palm of your hand

1

2-component handle with more than 75% of rubber material

2

Can be hung

7

Vertical grooves for comfortable grip and maximum friction; anti-slip

8

Indelible symbol tip. Easy to choose the right tip

3

Size laser marking

9

Small finger marks on both sides of the neck for precision application

4

Soft, high-friction material with ridged surface for comfortable grip and maximum friction even when the hand is oily

10

High performance alloy steel

5

Code laser marked on the blade

11

Black tip: provides precise tip

6



— Slotted

Flat



B190.040.075	0.8	4.0	75	24.5x95	10	44
B190.040.100	0.8	4.0	100	24.5x95	10	44
B190.055.100	1.0	5.5	100	30x105	10	66
B190.055.125	1.0	5.5	125	30x105	10	70
B190.065.125	1.2	6.5	125	34x117	10	102
B190.065.150	1.2	6.5	150	34x117	10	102
B190.080.150	1.6	8.0	150	34x117	10	110
B190.080.175	1.6	8.0	175	34x117	10	120
B190.100.200	1.6	10.0	200	34x117	10	170
B190.120.250	2.0	12.0	250	34x117	10	220
B190.140.250	2.5	14.0	250	34x117	10	220

Straight



B191.025.075	0.4	2.5	75	24.5x95	10	20
B191.030.075	0.5	3.0	75	24.5x95	10	27
B191.030.100	0.5	3.0	100	24.5x95	10	28
B191.030.200	0.5	3.0	200	24.5x95	10	30
B191.035.100	0.6	3.5	100	24.5x95	10	30
B191.040.100	0.8	4.0	100	24.5x95	10	44
B191.040.125	0.8	4.0	125	24.5x95	10	47
B191.040.250	0.8	4.0	250	24.5x95	10	60
B191.055.125	1.0	5.5	125	30x105	10	70
B191.055.150	1.0	5.5	150	30x105	10	79
B191.055.300	1.0	5.5	300	30x105	10	105
B191.065.150	1.2	6.5	150	34x117	10	100
B191.065.300	1.2	6.5	300	34x117	10	140


Stubby



B195.040.025	0.8	4.0	25	33x60	5	38
B195.050.025	1.0	5.0	25	33x60	10	38
B195.060.025	1.2	6.0	25	33x60	10	40

WHAT IS THE DIFFERENCE BETWEEN FLAT AND STRAIGHT?

STRAIGHT



FLAT



**BAHCOFIT
SCREWDRIVERS
ARE AVAILABLE
IN RETAIL
PACKAGING
BY ADDING
AN "S" BEFORE
THE CODE**



⊕ Phillips



					
B192.000.075	PH 0	75	24.5x95	10	27
B192.000.200	PH 0	200	24.5x95	10	38
B192.001.100	PH 1	100	30x105	10	65
B192.001.250	PH 1	250	30x105	10	90
B192.002.125	PH 2	125	34x117	10	97
B192.002.150	PH 2	150	34x117	10	97
B192.002.300	PH 2	300	34x117	10	130
B192.003.150	PH 3	150	34x117	10	150
B192.004.200	PH 4	200	34x117	10	190

Stubby



					
B195.001.025	PH 1	25	33x60	10	40
B195.002.025	PH 2	25	33x60	10	40

Pozidriv

					
B193.000.075	PZ 0	75	24.5x95	10	30
B193.001.100	PZ 1	100	30x105	10	65
B193.002.125	PZ 2	125	34x117	10	97
B193.003.150	PZ 3	150	34x117	10	153
B193.004.200	PZ 4	200	34x117	10	202

Stubby

					
B195.901.025	PZ 1	25	33x60	10	30
B195.902.025	PZ 2	25	33x60	10	40

Torx®

					
B194.004.075	T 4	1.30	75	24.5x95	10
B194.005.075	T 5	1.37	75	24.5x95	10
B194.006.075	T 6	1.65	75	24.5x95	10
B194.007.075	T 7	1.97	75	24.5x95	10
B194.008.075	T 8	2.30	75	24.5x95	10
B194.009.075	T 9	2.48	75	24.5x95	10
B194.010.075	T 10	2.72	75	24.5x95	10
B194.015.100	T 15	3.26	100	24.5x95	10
B194.020.100	T 20	3.84	100	24.5x95	10
B194.025.125	T 25	4.40	125	30x105	10
B194.027.125	T 27	4.96	125	30x105	10
B194.030.150	T 30	5.49	150	34x117	10
B194.040.150	T 40	6.60	150	34x117	10
B194.045.150	T 45	7.70	150	34x117	5

TORX® Tamper

					
B141.007.075	TR 7	1.97	75	24.5x95	5
B141.008.075	TR 8	2.30	75	24.5x95	5
B141.009.075	TR 9	2.48	75	24.5x95	5
B141.010.075	TR 10	2.72	75	24.5x95	5
B141.015.100	TR 15	3.26	100	24.5x95	5
B141.020.100	TR 20	3.84	100	24.5x95	5
B141.025.125	TR 25	4.40	125	30x105	5
B141.027.125	TR 27	4.96	125	30x105	5
B141.030.150	TR 30	5.49	150	34x117	5
B141.040.150	TR 40	6.60	150	34x117	5

Hexagonal ball

					
B143.020.100	2	100	24.5x95	5	29
B143.025.100	2.5	100	24.5x95	10	30
B143.030.100	3	100	24.5x95	10	30
B143.040.100	4	100	24.5x95	10	50
B143.050.100	5	100	30x105	10	75
B143.060.125	6	125	34x117	10	111
B143.080.150	8	150	34x117	5	130

HEX BALL

Screwdriver for Hexagonal head screws, ball ended, easy to insert in the screw head from a range of angles, up to 30°, giving better access than the standard hex.





Robertson



B144.001.100	# 1	100	24,5x95	5	40
B144.002.125	# 2	125	30x105	5	70
B144.003.150	# 3	150	34x117	5	100

Reamer

Square tip



B146.006.100	6	100	30x105	5	70

Awl

Round tip



B145.006.100	6	100	30x105	5	70



Nut Driver



	 mm	 mm	 mm	 mm		
B198.040.125	4.0	7x30	125	24,5x95	5	60
B198.045.125	4.5	7x30	125	24,5x95	5	69
B198.050.150	5.0	8x30	150	30x105	5	80
B198.055.150	5.5	8x30	150	30x105	5	70
B198.060.150	6.0	9x30	150	30x105	5	80
B198.060.150F	6.0	11x27	150	30x105	5	80
B198.070.150	7.0	11x30	150	34x117	5	105
B198.070.150F	7.0	11x27	150	34x117	5	100
B198.080.150	8.0	12x30	150	34x117	5	118
B198.080.150F	8.0	13x27	150	34x117	5	118
B198.090.150	9.0	13x30	150	34x117	5	110
B198.100.150	10.0	14x30	150	34x117	5	164
B198.110.150	11.0	16x30	150	34x117	5	170
B198.120.150	12.0	17x30	150	34x117	5	170
B198.130.150	13.0	18x30	150	34x117	5	170
B198.140.150	14.0	19x30	150	34x117	5	185

Stubby



B195.006.050	6	50	33x60	5	40

Magnetic Bit Holder



B705.1/4.125	1/4"	125	30x105	5	130

BahcoFit Screwdriver Sets



Set 2 pcs

B219.002			1	120
B191 0.8x4.0x100	⌚			
B192 PH1x100	⊕			



Set 5 pcs

B219.005			1	355
B191 0.5x3.0x75; 0.8x4.0x100	⌚			
B190 1.0x5.5x125	⌚			
B192 PH1x100; PH2x125	⊕			



Set 4 pcs

B219.004			1	300
B191 0.5x3.0x100; 1.0x5.5x125	⌚			
B192 PH1x100; PH2x125	⊕			



Set 5 pcs

B219.015			1	355
B191 0.5x3.0x75; 0.8x4.0x100	⌚			
B190 1.0x5.5x125	⌚			
B193 PZ1x100; PZ2x125	⊕			



BahcoFit Screwdriver Sets



Set 5 pcs

B219.025	1	360
B194 T10x75; T15x100; T20x100; T25x125; T30x150		



Set 5 pcs

B219.035	1	355
B141 TR10x75; TR15x100; TR20x100; TR25x125; TR30x150		



Set 6 pcs

B219.006	1	450
B191 0.5x3.0x75; 0.8x4.0x100		
B190 1.0x5.5x125; 1.2x6.5x125		
B192 PH1x100; PH2x125		



Set 6 pcs

B219.016	1	450
B191 0.5x3.0x75; 0.8x4.0x100		
B190 1.0x5.5x125; 1.2x6.5x125		
B193 PZ1x100; PZ2x125		



Set 4 pcs

B219.014	1	375
B192 PH0x75; PH1x100; PH2x125; PH3x150		



Set 6 pcs

B219.026	1	450
B191 0.5x3.0x75; 0.8x4.0x100		
B192 PH1x100; PH2x125		
B193 PZ1x100; PZ2x125		



Set 7 pcs

B219.007	1	530
B193 PZ1x100; PZ2x125		
B194 T10x75; T15x100; T20x100; T25x125; T30x150		



Set 7 pcs

B219.017	1	530
B191 0.6x3.5x100; 0.8x4.0x100		
B190 1.0x5.5x125; 1.2x6.5x125; 1.6x8.0x150		
B192 PH1x100; PH2x125		




Set 7 pcs

B219.027	1	625
B194 T10x75; T15x100; T20x100; T10x75 T25x125; T27x125; T30x150		


Set 8 pcs


  		
B219.008		
	1	540
B191 0.8x4.0x100; 1.0x5.5x125		
B190 1.2x6.5x150; 1.6x8.0x175		
B192 PH1x100; PH2x125		
B195 1.2x6.0x25		
B195 PH2x25		


Set 10 pcs


  		
B219.010		
	1	630
B191 3.0x75		
B190 1.0x5.5x100; 6.5x125; 8.0x150		
B192 PH1x100; PH2x125; PH3x150		
B193 PZ2x25		
B144 R1x100; R2x125		

* In thermoformed inlay


Set 4 pcs

  		
B219.004 + MTT121		
	1	400
B191 0.5x3.0x100; 1.0x5.5x125		
B192 PH1x100; PH2x125		
MTT121		


Set 2 pcs

  		
B219.012		
	1	182
B190 1.0x5.5x125		
B192 PH2x125		


Set 5 pcs

  		
B219.045		
	1	419
B191 0.5x3x100; 0.8x 4.0x125		
B190 1.0x5.5x125; 1.2x6.5x150; 1.6x8.0x175		


Set 10 pcs

  		
B219.210		
	1	630
B194 T6x75; T8x75; T9x75; T10x75; T15x100; T20x100; T25x125; T27x125; T30x125; T40x150		


Set 10 pcs

  		
B219.110		
	1	680
806-1-1 0.6x3.0x65 (150-250V)		
B142 PZ1x80		
B190 1x5.5x100		
B192 PH2x125		
B193 PZ2x125		
B194 T10x75; T15x100; T20x100		
B196 0.4x2.5x75; 0.8x4x100		



BAHCOFit Insulated Screwdrivers

- For work on live equipment, up to 1000 V
- Handle: 2-component handle with hanging hole
- High quality steel blade, moulded directly into the handle
- Black finish tip for improved accuracy
- Individually inspected and manufactured according to IEC 609000



Slotted



B196.025.075	0.4	2.5	75	24.5x95	10	36
B196.030.100	0.5	3.0	100	24.5x95	10	38
B196.035.100	0.6	3.5	100	24.5x95	10	38
B196.040.100	0.8	4.0	100	24.5x95	10	38
B196.055.125	1.0	5.5	125	24.5x95	10	66
B196.065.150	1.2	6.5	150	30x105	10	90
B196.080.175	1.2	8.0	175	34x117	10	140
B196.100.200	1.6	10.0	200	34x117	10	189
B196.120.200	2.0	12.0	200	34x117	10	205
SB196.025.075	0.4	2.5	75	24.5x95	1	40
SB196.030.100	0.5	3.0	100	24.5x95	1	42
SB196.035.100	0.6	3.5	100	24.5x95	1	42
SB196.040.100	0.8	4.0	100	24.5x95	1	42
SB196.055.125	1.0	5.5	125	24.5x95	1	70
SB196.065.150	1.2	6.5	150	30x105	1	94
SB196.080.175	1.2	8.0	175	34x117	1	144
SB196.100.200	1.6	10.0	200	34x117	1	193
SB196.120.200	2.0	12.0	200	34x117	1	200

Nut Driver



B199.055.125	5.5	125	30x105	5	91
B199.060.125	6.0	125	30x105	5	127
B199.070.125	7.0	125	34x117	5	127
B199.080.125	8.0	125	34x117	5	142
B199.090.125	9.0	125	34x117	5	142
B199.100.125	10.0	125	34x117	5	142
B199.110.125	11.0	125	34x117	5	181
B199.120.125	12.0	125	34x117	5	182
B199.130.125	13.0	125	34x117	5	183
SB199.055.125	5.5	125	30x105	1	95
SB199.060.125	6.0	125	30x105	1	131
SB199.070.125	7.0	125	34x117	1	131
SB199.080.125	8.0	125	34x117	1	146
SB199.090.125	9.0	125	34x117	1	146
SB199.100.125	10.0	125	34x117	1	146
SB199.110.125	11.0	125	34x117	1	185
SB199.120.125	12.0	125	34x117	1	186
SB199.130.125	13.0	125	34x117	1	187

Phillips



B197.000.075	PH 0	75	24.5x95	10	30
B197.001.080	PH 1	80	24.5x95	10	40
B197.001.150	PH 1	150	30x105	10	90
B197.002.100	PH 2	100	30x105	10	82
B197.002.175	PH 2	175	34x117	10	140
B197.003.150	PH 3	150	34x117	10	150
B197.004.200	PH 4	200	34x117	10	190
SB197.000.075	PH 0	75	24.5x95	1	34
SB197.001.080	PH 1	80	24.5x95	1	44
SB197.002.100	PH 2	100	30x105	1	86
SB197.003.150	PH 3	175	34x117	1	154
SB197.004.200	PH 4	200	34x117	1	194

Pozidriv



B142.000.075	PZ 0	75	24.5x95	10	30
B142.001.080	PZ 1	80	24.5x95	10	40
B142.001.150	PZ 1	150	30x105	10	90
B142.002.100	PZ 2	100	30x105	10	80
B142.002.175	PZ 2	175	34x117	10	140
B142.003.150	PZ 3	150	34x117	10	150
SB142.000.075	PZ 0	75	24.5x95	1	34
SB142.001.080	PZ 1	80	24.5x95	1	44
SB142.002.100	PZ 2	100	30x105	1	84
SB142.003.150	PZ 3	150	34x117	1	154

Torx®



						
B150.010.100	T 10	2.72	100	24.5x95	10	38
B150.015.125	T 15	3.26	125	24.5x95	10	66
B150.020.125	T 20	3.84	125	24.5x95	10	70
B150.025.150	T 25	4.40	150	30x105	10	90
SB150.010.100	T 10	2.72	100	24.5x95	1	42
SB150.015.125	T 15	3.26	125	24.5x95	1	70
SB150.020.125	T 20	3.84	125	24.5x95	1	74
SB150.025.150	T 25	4.40	150	30x105	1	94



BahcoFit Insulated Screwdrivers

⊕ Combi tip SL/PH

B148.001.080	5 / PH1	80	24.5x95	10	50
B148.002.100	6 / PH2	100	30x105	10	80
SB148.001.080	5 / PH1	80	24.5x95	1	54
SB148.002.100	6 / PH2	100	30x105	1	84

⊕ Combi tip SL/PZ

B149.001.080	5 / PZ1	80	24.5x95	10	50
B149.002.100	6 / PZ2	100	30x105	10	80
SB149.001.080	5 / PZ1	80	24.5x95	1	54
SB149.002.100	6 / PZ2	100	30x105	1	84

BahcoFit Insulated Screwdriver Sets

- New packaging design
- Thermoformed inlay made in Spain
- Windows allow product to be touched
- Personalized box for each set

Set 2 pcs

B220.002	1	90
B196 0.5x3.0x100		
B197 PH1x80		

* Hanging twinpack with 2 screwdrivers

Set 5 pcs

B220.005	1	450
B196 0.5x3.0x100; 0.8x4.0x100; 1.0x5.5x125		
B197 PH1x80; PH2x100		


 Set **5 pcs**

B220.015		
	1	450
B196 0.6x3.5x100; 0.8x4.0x100; 1.2x6.5x125		
B142 PZ1x80; PZ2x100		


 Set **7 pcs**

B220.007		
	1	530
B196 0.5x3.0x100; 0.8x 4.0x100; 1.0x5.5x125; 1.2x6.5x150		
B197 PH0x75; PH1x80; PH2x100		


 Set **7 pcs**

B220.017		
	1	530
B196 0.4x2.5x75; 0.8x4.0x100; 1.0x5.5x125; 1.2x6.5x150		
B142 PZ0x75; PZ1x80; PZ2x100		


 Set **7 pcs**

B220.027		
	1	460
B196 0.5x3.0x100; 0.8x4.0x100; 1.0x5.5x125		
B197 PH0x75; PH1x80; PH2x100		
806-1-1 0.6x3.0x65 (150-250V)		







600 Series

The **600 Series Bahco Screwdrivers** complements the wide range of Bahco Screwdrivers. This assortment of durable screwdrivers incorporates two classes; **insulated and standard**, both with the most demanded range of tip profiles.



— Slotted

Flat



611-3.5-75		0.6	3.5	50	25x80	10	30
611-3.5-100		0.6	3.5	100	25x80	10	31
611-4-100		0.8	4.0	100	25x80	10	37
611-5.5-100		1.0	5.5	100	25x80	10	63
611-5.5-125		1.0	5.5	100	30x97	10	68
611-6.5-25		1.2	6.5	125	35x68	10	43
611-6.5-125		1.2	6.5	125	35x110	10	100
611-6.5-150		1.2	6.5	150	35x110	10	103
611-8-150		1.2	8.0	150	35x110	10	115
611-8-175		1.2	8.0	175	35x110	10	127
611-10-200		1.6	10.0	200	35x110	10	160

Straight



613-3-75		0.5	3.0	75	25x80	10	30
613-3-100		0.5	3.0	100	25x80	10	31
613-3.5-100		0.60	3.5	100	25x80	10	33
613-4-100		0.8	4.0	100	25x80	10	37
613-4-125		0.80	4.0	125	25x80	10	41
613-5.5-150		1.0	5.5	150	30x97	10	78
613-6.5-150		1.20	6.5	150	35x110	10	110

+ Phillips



615-0-75		PH 0	75	25x80	10	30
615-1-100		PH 1	100	30x97	10	63
615-2-25		PH 2	25	35x65	10	43
615-2-125		PH 2	125	35x110	10	98
615-3-150		PH 3	150	35x110	10	113

+ Pozidriv



616-0-75		PZ 0	75	25x80	10	30
616-1-100		PZ 1	100	30x97	10	63
616-2-125		PZ 2	25	60x110	10	98
616-3-150		PZ 3	125	35x110	10	113

+ Torx®



618-10-75		T 10	2.72	75	25x80	10	30
618-15-100		T 15	3.26	100	25x80	10	37
618-20-100		T 20	3.84	100	25x80	10	37
618-25-125		T 25	4.40	125	30x97	10	68
618-27-125		T 27	4.96	125	30x97	10	68
618-30-150		T 30	5.49	150	35x110	10	103
618-40-150		T 40	6.60	150	35x110	10	115



600 Series Sets



Set 3 pcs

			
600-3		1	210
611 5.5x125			
613 3x100			
615 PH1x100			



Set 6 pcs

			
605-6		1	445
613 3x75, 4x100			
615 PH1x100, PH2x125			
616 PZ1x100, PZ2x125			



Set 4 pcs

			
602-4-LA		1	315
613 3x100			
611 5.5x125			
615 PH1x100, PH2x125			



Set 6 pcs

			
606-6		1	445
611 5.5x100, 6.5x125			
613 3x75, 4x100			
615 PH1x100, PH2x125			



Set 5 pcs

			
604-5		1	385
613 3x100			
611 4x100, 6.5x125			
615 PH1x100, PH2x125			



Set 6 pcs

			
610-6		1	445
611 5.5x100, 6.5x125			
613 3x75, 4x100			
616 PZ1x100, PZ2x125			



Set 5 pcs

			
612-5		1	348
618 T10, T15, T20, T25, T30			



Set 6 pcs

			
605-6-PC		1	830
613 3x100, 6,5x150			
615 PH1x100, PH2x125			
616 PZ1x100, PZ2x125			



Set 10 pcs

					
605-10-PC-AU		1		1000	
611 5.5x100, 6.5x125, 8x150					
613 3x75					
615 PH 1x100, PH2x125, PH3x150					
616 PZ2x25					
619 R1x100, R2x100					

600 Series Insulated Screwdrivers

- For work on live equipment, up to 1000 V
- Handle: 2-component handle with hanging hole
- High quality steel blade, moulded directly into the handle
- Black finish tip for improved accuracy
- Individually inspected and manufactured according to IEC 60900



— Slotted

— IEC60900  1000 V




						
623-3-100	0.5	3.0	100	25x80	10	32
623-3.5-100	0.6	3.5	100	25x80	10	32
623-4-100	0.8	4.0	100	25x80	10	33
623-5-125	1.0	5.5	125	30x97	10	61
623-6-150	1.2	6.5	150	35x110	10	94

Set



—  IEC60900  1000 V

Set 6 pcs

		
620-6	1	465
623 3x100; 4x100; 5.5x125; 6.5x150		
625 PH1x150; PH2x175		

+ Phillips

+ IEC60900  1000 V



						
625-0-100	PH 0	100	25x80	10	32	
625-1-150	PH 1	150	30x97	10	68	
625-2-175	PH 2	175	35x110	10	116	







Ratcheting

Product features such as the 48 teeth ratchet function, the super grip two-component handle, the cartridge bit storage and the led light function make your work easier and more efficient.

All products have the same distinctive Bahco look, a design that stands out from the crowd.

Ratchet Bit Screwdriver 808050

LED Light Ratchet Bit Screwdriver 808050L

BIT STORAGE

Cartridge style bit holder stores 6 bits



Quality mechanism ensures high torque bearing capacity


Knurled part for fast spinning

Alloy steel shank

Efficient magnetic device: 1/4" magnetic bit holder

Oval handle shape with high friction surface for increased torque and comfort

Self explanatory push buttons



Three modes of operation: Clockwise, counter clockwise and non-ratchet (fixed) mode

LONG-LASTING LED LIGHTS MOUNTED IN FRONT CASING PROVIDE ILLUMINATION IN DARK CONDITIONS



3 batteries LR41 & 2 lights AG-3 4.5V included

808050

808050L

Pistol Handle Ratchet Bit Screwdriver 808050P

BIT STORAGE

Cartridge style bit holder stores 6 bits



Quality mechanism ensures high torque bearing capacity

Knurled part for fast spinning

Alloy steel shank


1/4" magnetic bit holder



1 Oval handle shape with high friction surface for increased torque and comfort

2 Handle swivels and locks at pistol position for application of higher torque

3 Self explanatory push buttons



8 Reversing ring for quick mode selection. Clockwise, counter clockwise and non-ratchet (fixed) mode



Stubby Ratchet Bit Screwdriver 808050TS



Stubby Ratchet Bit Screwdriver 808050S



Range of Ratchet & Bits Screwdrivers

Ratchet bit screwdriver

808050	1/4	125	100	1	270
PH1, PH2, PZ1, PZ2, SL4,5, SL5,5					

Ratchet bit screwdriver with LED

808050L	1/4	135	45x140	1	215
PH1, PH2, PZ1, PZ2, SL4,5, SL5,5					
808050L-SP1	spare led panel + 3 batteries AG-3, 4,5V			1	-

Pistol handle ratchet bit screwdriver

808050P	1/4	135	45x125	1	270
PH1, PH2, PZ1, PZ2, SL4,5, SL5,5					

Bit holder screwdriver

808050A	1/4	115	45x115	1	150
PH1, PH2, PZ1, PZ2, SL4,5, SL5,5					
808050TORX	1/4	115	45x115	1	150
T10, T15, T20, T25, T30, T40					

Stubby T-handle ratchet screwdriver


808050TS	1/4	25	90x70	1	165

Stubby ratchet screwdriver


808050S	1/4	25	40x70	1	135

Sets


Set 25 pcs

808050P-25	Pistol handle ratchet bit screwdriver	1	1400

1 pc pistol grip ratcheting screwdriver with fixed bit holder
6 pcs 25 mm 1/4" bits in the screwdriver bit storage:
PH 1, PH 2, PZ 1, PZ 2, slotted 4.5 and 5.5 mm
3 pcs ratchet wrenches:
8x10-9x11 mm, 12x14-13x15 mm and 16x17-18x19 mm
1 pc 1/4" x 1/4" socket adaptor in bit holder block
1 pc bit adaptor for 1/4" 10 mm reverse gear
13 pcs 25 mm 1/4" bits; 2 plastic bit holder block:
PH 3, PZ 3, SL 6.5, HEX 3, HEX 4, HEX 5,
T-10, T-15, T-20, T-25, T-27, T-30, T-40


Set 22 pcs

808050S-22	Stubby ratchet screwdriver set	1	530

1 pc detachable square driver blade stubby ratcheting screwdriver
17 pcs S2 Zinc Phosphate bits:
PH 1, PH 2, PH 3, PZ 1, PZ 2, T-10, T-15, T-20, T-25, T-27, T-30, T-40, SL 4, SL 5, SL 5.5, SL 6.5, SL 1/4"
1 pc 1/4" x 1/4" socket adaptor
1 pc 1/4" Sq. x 1/4" hex bit holder 50 mm (changeable type)
1 pc 1/4" Sq. x 1/4" square flexible socket adaptor 150 mm
1 pc 1/4" x 1/4" bit adaptor


Set 18 pcs

808050S-18	Stubby ratchet screwdriver set	1	530

1 pc detachable square driver blade stubby ratcheting screwdriver
8 pcs S2 Zinc Phosphate bits:
PH 1, PH 2, PZ 1, PZ 2, T-15, T-20, SL 4, HEX 3
1 pc 1/4" x 1/4" socket adaptor
1 pc 1/4" Sq. x 1/4" hex bit holder 50 mm (changeable type)
1 pc 1/4" Sq. x 1/4" square flexible socket adaptor 150 mm
1 pc 1/4" x 1/4" bit adaptor
5 pcs 1/4" sockets: 4, 5, 6, 7, 8 mm



808060 Ratcheting Screwdriver

The 808060 is an insulated ratcheting screwdriver combined with interchangeable slim blades, a revolutionary **new innovation**, made in one of Bahco's **own factories in Europe**. The blade release system built in the comfortable handle makes it easy and safe to change the slim blades without the blades falling out.

The blades are 30 % slimmer than the blade of a regular insulated screwdriver for better accessibility and more applications (e.g. sunken screws and spring elements).

A must have tool for electricians and maintenance professionals.



Loose handle and spare blades 100 mm



808060	Handle	100	1	115
8610SL-2P	PH1	100	2	40
8620SL-2P	PZ1	100	2	55
8810SL-2P	PH2	100	2	40
8820SL-2P	PZ2	100	2	55
8010SL-2P	0.4x2.5	100	2	40
8220SL-2P	0.5x3.0	100	2	40
8040SL-2P	0.8x4.0	100	2	55
8050SL-2P	1x5.5	100	2	55
8910SL-2P	T10	100	2	40
8915SL-2P	T15	100	2	40
8920SL-2P	T20	100	2	40
8925SL-2P	T25	100	2	55
8930SL-2P	T30	100	2	55
8510SL-2P	combi-tip PH1/5.0x100	100	2	40
8520SL-2P	combi-tip PH2/6.0x100	100	2	55
8710SL-2P	combi-tip PZ1/5.0x100	100	2	40
8720SL-2P	combi-tip PZ2/6.0x100	100	2	55



Insulated ratcheting screwdriver with interchangeable blades 100 mm




808061	6 blades set in a nylon pouch: PH1, PH2, 0.4x2.5, 0.5x3.0, 0.8x4.0, 1.0x5.5 + handle	85x220	5	475
808062	6 blades set in a nylon pouch: PZ1, PZ2, 0.4x2.5, 0.5x3.0, 0.8x4.0, 1.0x5.5 + handle	85x220	5	475



Insulated ratcheting screwdriver with interchangeable blades 100 mm 5 UNIT DISPLAY

808061	6 blades set in a nylon pouch: PH1, PH2, 0.4x2.5, 0.5x3.0, 0.8x4.0, 1.0x5.5 + handle	85x220	5	475
808062	6 blades set in a nylon pouch: PZ1, PZ2, 0.4x2.5, 0.5x3.0, 0.8x4.0, 1.0x5.5 + handle	85x220	5	475

INSULATED




The 808060 is certified according IEC 60900 and is suited for working on live equipment.

RATCHETING



The 808060 has a 48 tooth non-conductive ratcheting mechanism.

SLIM BLADES



The blades are 30 % thinner than regular insulated blades for better accessibility (e.g. sunken screws and spring elements).

INTERCHANGEABLE BLADES



Patented blade release system to easily and safely change blades without the blade falling out.







Precision

When precision is a must

Specially designed screwdriver for precision work, tailored for mechanical and electronic applications.

1

Rotating head allows the tip to be perfectly positioned for fast and comfortable finger movement during turning, reducing tightening time





2

Combining the 2-component in the handle makes the grip comfortable and transmits a high torque to the blade

**EASY TO FIND THE RIGHT TIP
IN YOUR TOOL CASE WITH
THE COLOUR CODE THAT
DOESN'T WEAR OUT**







Slotted

Phillips

Pozidriv

Torx®

Hexagonal Ball

3

High performance alloy steel

4

Precision-machined black tip provides the precise tip

— Slotted



	 mm	 mm	 mm	 mm		
700-1-50	0.18	1	50	14x87	5	20
700-1.2-50	0.20	1.2	50	14x87	5	20
700-1.5-50	0.25	1.5	50	14x87	5	20
700-1.8-50	0.30	1.8	50	14x87	5	20
700-2-50	0.40	2	50	14x87	5	20
700-2.5-50	0.40	2.5	50	14x87	5	22
700-3-50	0.50	3	50	14x87	5	23
700-3-100	0.50	3	100	14x87	5	24
700-3-200	0.50	3	200	14x87	5	39
700-3.5-75	0.60	3.5	75	14x87	5	26
700-4-75	0.80	4	75	14x87	5	29
700-4-250	0.80	4	250	14x87	5	61

★ Torx®



						
703-4-50	T 4	1.30	50	14x87	5	21
703-5-50	T 5	1.37	50	14x87	5	21
703-6-50	T 6	1.65	50	14x87	5	21
703-7-50	T 7	1.97	50	14x87	5	21
703-8-50	T 8	2.30	50	14x87	5	23
703-9-50	T 9	2.48	50	14x87	5	23
703-10-50	T 10	2.72	50	14x87	5	23
703-15-75	T 15	3.26	75	14x87	5	30
703-20-75	T 20	3.84	75	14x87	5	30

⊕ Phillips



701-00-50		PH 00	50	14x87	5	20
701-0-50		PH 0	50	14x87	5	23
701-0-200		PH 0	200	14x87	5	39
701-1-75		PH 1	75	14x87	5	29
701-1-250		PH 1	250	14x87	5	61

⬡ Hex Ball



704-1.5-50		1.5	50	14x87	5	21
704-2-50		2	50	14x87	5	21
704-2.5-50		2.5	50	14x87	5	21
704-3-75		3	75	14x87	5	26
704Z-3/32		3/32	75	14x87	5	26

⊕ Pozidriv



702-0-50		PZ 0	50	14x87	5	23
702-1-75		PZ 1	75	14x87	5	29


HEX BALL

The spherical drive profile allows work at an angle of up to 30° with total effectiveness. TORX BALL end tips are necessary when screwdriving in tight spots or at an angle.



BLACK TIP = MORE ACCURACY

The black finish tip.
It's an oxidation process that doesn't increase the dimensions, therefore the tip is more precise. Use black finish tip for higher accuracy.



Sets



Set 6 pcs

706-1				1	240
700	1.5x50; 2.0x50; 2.5x50; 3.0x50				
701	PH0x50; PH1x75				



Set 7 pcs

706-4				1	350
700	1.5x50; 2.5x50; 3.5x75				
701	PH0x50; PH1x75				
703	T6x50; T8x50				



Set 6 pcs

706-2				1	226
700	1.0x50; 1.2x50; 1.5x50; 1.8x50				
701	PH00x50; PH0x50				



Set 24 pcs

706-5				1	820
700	1.0x50; 1.2x50; 1.5x50; 1.8x50; 2.0x50; 3.0x50; 3.5x75; 4x75				
701	PH00x50; PH0x50; PH1x75				
702	PZ0x50; PZ1x75				
703	T6x50; T7x50; T8x50; T9x50; T10x50; T15x75; T20x75				
704	H1,5x50; H2x50; H2,5x50; H3x75				



Set 6 pcs

706-3				1	222
700	1.0x50; 1.2x50; 1.5x50; 1.8x50; 2.0x50; 2.5x50				



Set 4 pcs

510034	0.25x1.5; 0.3x2; 0.4x2.5; 0.5x3	10	30



Set 5 pcs

98505	0.6; 0.8; 1.0; 1.5; 2.5 mm	5	70



Set 6 pcs

510031	1.0; 1.5; 2.0; 2.5; 3.0; 3.5 mm	5	145



Set 3 pcs

510033	PH000; PH00; PH0	5	85



	 mm	 mm		
2784-2.5	2.5	95	1	15
2784-3.5	3.5	110	1	25
2784-4.5	4.5	110	1	30



						
7372I-2-63	0.4	2.0	63	13x80	10	10
7372I-2.5-75	0.4	2.5	75	13x80	10	13
7372I-3-80	0.5	3.0	80	13x80	10	27



BAHCO





T-Handle

Series 900 T-Handle

The optimal tool for jobs where torque is required, combining operational characteristics of a T-shaped wrench with those of an offset key, with two blades positioned at 90°.



Hexagonal



		mm	mm	mm		g
900T-020-100		2	103	50x85	5	23
900T-025-100		2,5	103	50x85	5	25
900T-030-100		3	103	50x85	5	28
900T-040-150		4	136	50x85	5	48
900T-050-150		5	136	60x105	5	59
900T-060-200		6	185	60x105	5	73
900T-080-200		8	185	60x105	5	150
900T-100-200		10	185	60x105	5	210

Bit holder



		mm	mm	mm		g
904T-060-150		1/4	120	60x105	5	125

Torx®



						
901T-006-100	T 6	1.65	103	50x85	5	37
901T-007-100	T 7	1.97	103	50x85	5	37
901T-008-100	T 8	2.30	103	50x85	5	37
901T-009-100	T 9	2.48	103	50x85	5	37
901T-010-100	T 10	2.72	103	50x85	5	37
901T-015-150	T 15	3.26	136	50x85	5	42
901T-020-150	T 20	3.84	136	50x85	5	42
901T-025-150	T 25	4.40	136	60x105	5	49
901T-027-150	T 27	4.96	136	60x105	5	52
901T-030-200	T 30	5.49	185	60x105	5	61
901T-040-200	T 40	6.60	185	60x105	5	135
901T-045-200	T 45	7.70	185	60x105	5	135
901T-050-200	T 50	8.79	185	60x105	5	139

Socket Driver



		mm	mm	mm		g
905T-060-100		1/4	60	60x105	5	90



Nut Driver



	 mm	 mm	 mm	 mm		 g
902T-050-150	5	29	136	50x85	5	77
902T-055-150	5.5	29	136	50x85	5	77
902T-060-150	6	29	136	50x85	5	77
902T-070-175	7	29	160	60x105	5	77
902T-080-175	8	29	160	60x105	5	112
902T-090-175	9	29	160	60x105	5	98
902T-100-175	10	29	160	60x105	5	155
902T-110-175	11	29	160	60x105	5	155
902T-120-175	12	29	160	60x105	5	155
902T-130-175	13	29	160	60x105	5	155



Sets



Set 6 pcs



903T-1



1



855

900T
3 - 4 - 5 - 6 - 8 - 10 mm



Set 6 pcs



903T-2



1



400

901T
T 10, T 15, T 20, T 25, T 30, T 40



Set 6 pcs



903T-3



1



810

902T
5 - 6 - 7 - 8 - 10 - 13 mm









Hex Keys

Easy fit colored Hex & Torx® Keys

- 9 pcs set (Hex sizes: 1,5-10) (Torx® sizes: T8-T40)
- Easy find color identification, following the color wheel. Quick identification & color harmony Impact-bits color identification for Torx® version
- Holder: Durable Holder with soft-touch feeling for organization and security
- Injection moulding grip with soft-touch feeling: pleasant & non-slip grip in every application. Oil resistant
- Phosphate finish: protection against corrosion, providing a long lasting life
- Ball end: ideal for working in confined and hard-to-reach spaces
- Laser marking: Laser-marked and thereby wear-resistant size identification for a quick accessing to each size



1 EASY FIT

Wider neck, which increases the positioning lock the more you introduce the keyfree rotation of tool.

The body is thinner than the case so the key enter and exit easily.

Securely held and very easy to take out and insert the L-keys thanks to an exclusive fitting system

2 EDGE PLUS

The chamfer is done in each edge, respecting the hexagonal face, what increase the force applied due to have a greater surface contact

3 ROUGHNESS

The covers are anti-slip due to the rough surface of the material, so that even when the tool is stained with oil, its grip with the hand is greater to allow a proper use

4 OVERMOULDED

Being overmoulded, the material fills a central ring that prevents the removal of the sleeves

Sizes:

- 1.5
- 2
- 2.5
- 3
- 4
- 5
- 6
- 8
- 10





Easyfit
Edgeplus
Roughness
Overmoulded
Durability
Patent

Hex Key Holders

- 2-component compact holder, impact resistant
- Integrated magnet in holder allows magnetizing and demagnetizing when needed
- Foldable hex key holder available in a wide variety of key combinations
- The key sizes are marked for easy location
- Easy access to the hex key wrenches




Integrated magnet in holder allows magnetizing and demagnetizing when needed.



Intelligent Hex Key Sets

- Key folder
- 2-component soft grip handle
- Impact resistant material
- Wide opening push button for automatic release of the blades
- For different working positions
- Positive stop at 270° for maximum leverage
- Compact, easy to carry design
- Packaging with hanger




HEXAGONAL KEYS



KEY SURFACES

Nickel Plated

- Hexagonal



Black Finish

- Hexagonal
- ★ Torx®



Hexagonal

Nickel Plated Keys

Metric



	mm	mm	mm		g
1998M-1.5	1.5	15	47	10	1
1998M-2	2	18	52	10	1
1998M-2.5	2.5	21	59	10	3
1998M-3	3	23	66	10	4
1998M-4	4	29	74	10	10
1998M-5	5	33	85	10	18
1998M-6	6	38	96	10	29
1998M-7	7	41	102	10	41
1998M-8	8	44	108	10	57
1998M-9	9	47	114	5	76
1998M-10	10	50	122	5	100
1998M-12	12	57	137	5	163
1998M-14	14	70	154	1	253
1998M-17	17	80	177	1	427
1998M-19	19	89	199	1	600
1998M-22	22	102	222	1	910



	 mm			 g
1998M/8R	2: 2.5: 3: 4: 5: 6: 7: 8	8	1	175



	 mm			
BE-9778	1.5; 2; 2.5; 3; 4; 5; 6; 8; 10	9	1	305



	 mm			 g
BE-9878	1.5; 2; 2.5; 3; 4; 5; 6; 8; 10	9	1	305



	 mm			 g
1998M/6T	2; 2.5; 3; 4; 5; 6	6	1	76
1998M/8T	2; 2.5; 3; 4; 5; 6; 7; 8	8	1	180
1998M/10T	2; 2.5; 3; 4; 5; 6; 7; 8; 9; 10	10	1	380
1998M/11T	2; 2.5; 3; 4; 5; 6; 7; 8; 9; 10; 12	11	1	570
1998M/15T	2; 2.5; 3; 4; 5; 6; 7; 8; 9; 10; 12; 14; 17; 19; 22	15	1	2920

Nickel Plated Keys

Long Ball End / Inches



				
BE-9880	"	12	3	240
	0,050; 1/16; 5/64; 3/32; 7/64; 1/8; 9/64; 5/32; 3/16; 7/32; 1/4; 5/16			

Black Keys

Metric

					
	mm	mm	mm		g
1995M-1.5	1.5	15	47	10	1
1995M-2	2	18	52	10	2
1995M-2.5	2.5	21	59	10	3
1995M-3	3	23	66	10	5
1995M-4	4	29	74	10	10
1995M-5	5	33	85	10	13
1995M-6	6	38	96	10	29
1995M-7	7	41	102	10	41
1995M-8	8	44	108	10	57
1995M-9	9	47	114	10	76
1995M-10	10	50	122	10	100
1995M-12	12	57	137	10	163
1995M-14	14	70	154	10	253
1995M-17	17	80	177	10	427
1995M-19	19	89	199	10	600
1995M-22	22	102	222	10	910

				
	mm	mm		g
BE-9777B	2.5; 3; 4; 5; 6; 8; 10	7	6	290

Black Keys

Long / Metric

					
	mm	mm	mm		g
1995LM-1.5	1.5	15	91	10	1
1995LM-2	2	18	102	10	3
1995LM-2.5	2.5	21	114	10	5
1995LM-3	3	23	129	10	8
1995LM-4	4	29	144	10	17
1995LM-5	5	33	165	10	31
1995LM-6	6	38	186	10	51
1995LM-7	7	41	197	10	64
1995LM-8	8	44	208	10	100
1995LM-9	9	47	219	10	134
1995LM-10	10	50	234	10	175
1995LM-12	12	57	262	10	283
1995LM-14	14	70	294	10	439

				
	mm	mm		g
1995M/6T	2; 2.5; 3; 4; 5; 6	6	1	75
1995M/8T	2; 2.5; 3; 4; 5; 6; 7; 8	8	1	180
1995M/10T	2; 2.5; 3; 4; 5; 6; 7; 8; 9; 10	10	1	365
1995M/11T	2; 2.5; 3; 4; 5; 6; 7; 8; 9; 10; 12	11	1	535
1995M/15T	2; 2.5; 3; 4; 5; 6; 7; 8; 9; 10; 12; 14; 17; 19; 22	15	1	2800

				
	mm	mm		g
BE-9578	1.5; 2; 2.5; 3; 4; 5; 6; 8; 10	9	1	270

				
	mm	mm		g
BE-9776	1.5; 2; 2.5; 3; 4; 5; 6	7	6	150
BE-9777	2.5; 3; 4; 5; 6; 8; 10	7	6	410

				
	mm	mm		g
BE-9588	1.5; 2; 2.5; 3; 4; 5; 6; 8; 10	9	1	435



Integrated magnet in holder allows magnetizing and demagnetizing when needed



Hexagonal

Black Keys

Inches



1995Z-1/16	1/16	15	47	10	1
1995Z-5/64	5/64	18	52	10	2
1995Z-3/32	3/32	21	59	10	3
1995Z-1/8	1/8	23	66	10	5
1995Z-5/32	5/32	29	74	10	10
1995Z-3/16	3/16	33	85	10	16
1995Z-7/32	7/32	35,5	91	10	24
1995Z-1/4	1/4	38	96	10	32
1995Z-5/16	5/16	44	108	10	60
1995Z-3/8	3/8	50	122	10	100
1995Z-7/16	7/16	53	129	10	140
1995Z-1/2	1/2	63	145	10	182
1995Z-5/8	5/8	76	168	10	370
1995Z-3/4	3/4	89	199	10	601

Black Keys

Long Ball End



1996M-1.5	1.5	15	91	10	1
1996M-2	2	18	102	10	3
1996M-2.5	2.5	21	114	10	5
1996M-3	3	23	129	10	8
1996M-4	4	29	144	10	17
1996M-5	5	33	165	10	31
1996M-6	6	38	186	10	50
1996M-8	8	44	208	10	100
1996M-10	10	50	234	10	171
1996M-12	12	57	262	10	275



C1997LM/9P	1.5; 2; 2.5; 3; 4; 5; 6; 8; 10	9	1	586



BE-9787	3/32; 1/8; 5/32; 3/16; 1/4; 5/16; 3/8	7	6	410



BE-9688	1.5; 2; 2.5; 3; 4; 5; 6; 8; 10	9	1	450



Magnet-demagnetizing function integrated in the holder



BE-9775	5/64; 3/32; 1/4; 1/8; 1/16; 5/32; 3/16	7	3	70
BE-9780	0,050; 1/16; 5/64; 3/32; 7/64; 1/8; 9/64; 5/32; 3/16; 7/32; 1/4; 5/16	12	3	240
BE-9785	0,050; 1/16; 5/64; 3/32; 7/64; 1/8; 9/64; 5/32; 3/16; 7/32; 1/4; 5/16; 3/8	13	3	370




BE-9765	1.5; 2; 2.5; 3; 4; 5	6	3	60
BE-9770	1.5; 2; 2.5; 3; 4; 5; 6; 8; 10	9	3	355




BE-9678	1.5; 2; 2.5; 3; 4; 5; 6; 8; 10	9	1	430
---------	--------------------------------	---	---	-----



Black Keys

Torx®




1995TORX-T6	T 6	15	75	5	4
1995TORX-T7	T 7	16	80	5	4
1995TORX-T8	T 8	16	80	5	5
1995TORX-T9	T 9	16	80	5	6
1995TORX-T10	T 10	17	86	5	7
1995TORX-T15	T 15	18	90	5	10
1995TORX-T20	T 20	19	95	5	11
1995TORX-T25	T 25	20	100	5	17
1995TORX-T27	T 27	21	105	5	19
1995TORX-T30	T 30	24	114	5	29
1995TORX-T40	T 40	26	124	5	43
1995TORX-T45	T 45	29	133	5	61
1995TORX-T50	T 50	32	152	5	88




1995TORX/4T	T10; T20; T30; T40	4	1	200
1995TORX/7T	T10; T15; T20; T25; T27; T30; T40	7	1	250
1995TORX/11T	T7; T9; T10; T15; T20; T25; T27; T30; T40; T45; T50	11	1	325
1995TORX/13T	T6; T7; T8; T9; T10; T15; T20; T25; T27; T30; T40; T45; T50	13	1	335




BE-9585	T9; T10; T15; T20; T25; T27; T30; T40	8	1	180
---------	---------------------------------------	---	---	-----

 Magnet-demagnetizing function integrated in the holder




C1997TORX/9P	T8; T9; T10; T15; T20; T25; T27; T30; T40	9	1	290
--------------	---	---	---	-----




BE-9575	T9; T10; T15; T20; T25; T27; T30; T40	8	1	180
---------	---------------------------------------	---	---	-----


 Magnet-demagnetizing function integrated in the holder





Black Keys

Torx®



BE-8975B	T9; T10; T15; T20; T25; T27; T30; T40	8	6	290



BE-8975	T9; T10; T15; T20; T25; T27; T30; T40	8	6	295

Black Keys

Torx® Ball End

1996TORX-T9	T 9	16	80	3,0	5	4
1996TORX-T10	T 10	17	86	3,0	5	5
1996TORX-T15	T 15	18	90	4,0	5	7
1996TORX-T20	T 20	19	95	4,0	5	10
1996TORX-T25	T 25	20	100	5,0	5	14
1996TORX-T27	T 27	21	105	5,0	5	22
1996TORX-T30	T 30	24	114	6,0	5	30
1996TORX-T40	T 40	26	124	7,0	5	46
1996TORX-T45	T 45	29	133	8,0	5	61
1996TORX-T50	T 50	32	152	9,0	5	82

1996TORX/5T	T10; T20; T25; T30; T40	5	1	200

BE-9675	T9; T10; T15; T20; T25; T27; T30; T40	8	1	175

Black Keys

Torx® Tamper Resistant

1986TORX-T9	TR 9	16	80	3,0	5	4
1986TORX-T10	TR 10	17	86	3,0	5	5
1986TORX-T15	TR 15	18	90	4,0	5	8
1986TORX-T20	TR 20	19	95	4,0	5	11
1986TORX-T25	TR 25	20	100	5,0	5	17
1986TORX-T27	TR 27	21	105	5,0	5	19
1986TORX-T30	TR 30	24	114	6,0	5	29
1986TORX-T40	TR 40	26	124	7,0	5	43

1986TORX/7T	TR-10; TR-15; TR-20; TR-25; TR-27; TR-30; TR-40	7	1	200

BE-8675	TR-9; TR-10; TR-15; TR-20; TR-25; TR-27; TR-30; TR-40	8	1	180



Black Keys

Torx Plus®



1976TORX-T6	IP 6	75	80	2.5	5	4
1976TORX-T7	IP 7	80	86	2.5	5	4
1976TORX-T8	IP 8	80	90	2.5	5	5
1976TORX-T9	IP 9	80	95	3.0	5	5
1976TORX-T10	IP 10	86	100	3.0	5	5
1976TORX-T15	IP 15	90	105	4.0	5	10
1976TORX-T20	IP 20	95	114	4.0	5	10
1976TORX-T25	IP 25	100	124	5.0	5	17
1976TORX-T27	IP 27	105	100	5.0	5	19
1976TORX-T30	IP 30	114	105	6.0	5	29
1976TORX-T40	IP 40	124	114	7.0	5	43



1976TORX/5T	IP10; IP20; IP25; IP30; IP40	5	1	110		



BE-7675	IP9; IP10; IP15; IP20; IP25; IP27; IP30; IP40	8	1	220		

Double Offset Keys

Slotted



2047-0.8-4	0.8	4	100	5	14
2047-1-5.5	1.0	5.5	125	5	21
2047-1.2-8	1.2	8	150	5	37
2047-1.6-10	1.6	10	175	1	60
2047-2-12	2.0	12	200	1	115

Phillips



2047PR-1-2	PH 1 & 2	100	5	25	
2047PR-3-4	PH 3 & 4	200	5	110	








Others

Wooden Handle Screwdrivers



Slotted

Flat



9710-3.5-75	0.6	3.5	75	22x95	10	47
9710-5.5-100	1.0	5.5	100	24x100	10	67
9710-6.5-125	1.2	6.5	125	27x110	10	114
9710-8-150	1.2	8.0	150	30x120	5	174
9710-10-175	1.6	10.0	175	32x125	5	223

Phillips



9778-1	PH 1	80	24x100	10	45	
9778-2	PH 2	110	27x110	10	90	
9778-3	PH 3	150	30x120	5	160	

Pozidriv



9778PZD-1	PZ 1	80	24x100	10	45	
9778PZD-2	PZ 2	110	27x110	10	90	

Set




Set 6 pcs

9710/S6					1	650
9710 0.8x4.5x90; 1x5.5x100; 1.2x6.5x125; 1.2x8x150						
9778 PH1x80; PH2x110						

Reversible Screwdrivers

Reversible blade screwdriver
for slotted and Phillips head screws

Impact resistant
plastic handle



High performance alloy steel.
Nickel plated blade



1019	1.2	6	PH 2	10	26
1067	0.8	4.5	PH 1	10	30



1016	1	6	PH 2	10	50



6	3.5-5.0-6.5	PH 0, PH 1, PH 2	1	250



								
8052	1.0	6.0	PH 2	80	28x110	5	90	

- Reversible blade screwdriver set, 6 pieces:
PH 0, PH 1, PH 2 and slotted 3.5-5.0-6.5 mm
- In plastic pouch with hanging hole



Voltage Testers

Testers from 150V up to 250V

1

2

Clear plastic handle;
impact resistant

3

High quality steel; nickel plated blades.
Plastic protection up to the tip

4

According to
DIN VDE 0680/6 GS-marked





806-1-1	0.5	3	65	17x75	6	30
806-1-2	0.6	3.5	100	17x90	6	29



8045VDE	0.5	3.5	77	14x92	10	40



806-1-3	0.5	3	45	13x75	6	22



8045LVDE	0.5	3.5	42	16x90	6	28


Magnetisers




M780	1	95

M781	5	35

Bicycle Tool



Through Blade



9715-14-250	2.5	14.0	250	37x140	5	460



The metal striking cap at the top of the handle gives additional protection for jobs requiring high impact and maximum force. The shank continues through the handle before contacting the metal striking cap for ultimate strength.





SDCAT24-INT



BAHCO®

www.bahco.com