

EiceDRIVER[™] 1ED32xxMC12H Two-level slew-rate control (2L-SRC)

Single-channel 5.7kV (rms) isolated gate driver IC with 2L-SRC

Feature list

- Single channel isolated gate driver
- Two-level slew rate control
- For use with 600 V/650 V/1200 V/1700 V/2300 V IGBTs, Si and SiC MOSFETs
- Up to 18.0 A typical peak output current
- 40 V absolute maximum output supply voltage
- High common-mode transient immunity CMTI > 200 kV/μs
- Active output clamping
- Active Miller Clamp options available
- · Galvanically isolated coreless transformer gate driver
- 3.3 V and 5 V input supply voltage
- Suitable for operation at high ambient temperature and in fast switching applications
- Certification: VDE 0884-11 with V_{IORM} = 1767 V (peak) (pending) and UL 1577 with V_{ISO} = 5.7 kV (rms) for 1 min

Potential applications

- AC and brushless DC motor drives
- High voltage DC/DC converter and DC/AC inverter
- UPS systems
- Welding



PG-DSO-8-66

Product validation

Qualified for industrial applications according to the relevant tests of JEDEC47/20/22.

Device information

Product type	Typical output current and configuration	Slew-rate control	Certification	Package
1ED3240MC12H	10 A, standard	turn-on and turn-off	VDE + UL	PG-DSO-8-66
1ED3241MC12H	18 A, standard	turn-on and turn-off	VDE + UL	PG-DSO-8-66
1ED3250MC12H	10 A, Miller clamp	turn-on	VDE + UL	PG-DSO-8-66
1ED3251MC12H	18 A, Miller clamp	turn-on	VDE + UL	PG-DSO-8-66

Description

The 1ED32xx family is a group of galvanically isolated single-channel driver ICs in a DSO-8 300 mil package. The driver ICs provide typical peak output currents up to 18 A. The family implements two-level slew rate control (2L-SRC). This feature allows for controlling two independent gate resistors, which enables the optimization of both EMI and switching losses.



Description

The family comprises standard output configuration and active Miller clamp output configurations with the same current rating to protect against parasitic turn-on. The input logic terminals operate safely with supply voltages of 3.3 V and 5 V. All input structures have threshold levels for support of 3.3 V microcontrollers. The driver IC family offers suitable output undervoltage lockout (UVLO) levels to operate various kinds of power transistors. The wide range of the output side supply voltage up to 40 V can be configured arbitrarily for positive and negative voltages as long as the absolute maximum of 40 V is not exceeded. All driver ICs have output sections with active shutdown.




Figure 1 Typical application for standard pinout (left) and CLAMP pinout (right)



Table of contents

Table of contents

	Feature list	1
	Potential applications	1
	Product validation	1
	Device information	1
	Description	1
	Table of contents	3
1	Block diagram reference	4
2	Related products to 1ED32xxMC12H	4
3	Pin configuration	5
4	Functional description	
4.1	IC supply	
4.2	Input terminals IN and /INF	
4.3	Output terminal <i>OUT</i>	
4.4	Output terminal OUTF	
4.5	Output terminal OUTFC	10
4.6	Input-to-output control scheme	11
5	Electrical characteristics and parameters	12
5.1	Absolute maximum ratings	12
5.2	Operating parameters	
5.3	Eletrical characteristics	
5.3.1	Power supply	
5.3.2	Logic input	
5.3.3	Gate driver	
5.3.4	Dynamic characteristics	
5.3.5	Active shutdown	17
6	Isolation ratings and characteristics (all pending)	
5.1	Safety limiting values	
5.2	Certified according to VDE 0884-11 for reinforced insulation	
6.3	Recognized under UL 1577 (File E311313, planned)	18
7	Timing diagrams	18
8	Package dimensions	21
	Revision history	21
	Disclaimer	22



Block diagram reference

1 Block diagram reference




Figure 2 Block diagram for standard variants (top) and for CLAMP variants (bottom)

2 Related products to 1ED32xxMC12H

Note: Please consider the gate driver IC power dissipation and insulation requirements for the selected power switch and operating condition.

Product group	Product name	Description
Evaluation boards	EVAL-1ED3241MC12H	Supporting 1ED3241MC12H and IKQ75N120CT2 for double pulse tests
	EVAL-1ED3251MC12H	Supporting 1ED3251MC12H and IKQ75N120CT2 for double pulse tests
TRENCHSTOP [™] IGBT Discrete	IKQ75N120CS6	High Speed 1200 V, 75 A IGBT with anti-parallel diode in TO247-3

v2.0



Pin configuration

Product group	Product name	Description
	IKQ75N120CT2	1200 V, 75 A IGBT discrete with anti-parallel diode in TO-247PLUS package
	IKW15N120BH6	High Speed 1200 V, 15 A IGBT with anti-parallel diode in TO247
	IHW40N120R5	Reverse conducting 1200 V, 40 A IH IGBT with integrated diode in TO247
CoolSiC [™] SiC	IMBF170R650M1	1700 V, 650 mΩ SiC MOSFET in TO263-7 package
MOSFET Discrete	IMBG120R045M1H	1200 V, 45 mΩ SiC MOSFET in TO263-7 package
	IMZ120R350M1H	1200 V, 350 mΩ SiC MOSFET in TO247-4 package
	IMZA65R027M1H	650 V, 27 mΩ SiC MOSFET in TO247-4 package
	IMW65R107M1H	650 V, 107 mΩ SiC MOSFET in TO247-3 package
CoolSiC [™] SiC	F\$45MR12W1M1_B11	EasyPACK [™] 1B 1200 V / 45 mΩ sixpack module
MOSFET Module	FF6MR12W2M1_B11	EasyDUAL [™] 2B 1200 V, 6 mΩ half-bridge module
	F3L11MR12W2M1_B74	EasyPACK [™] 2B 1200 V, 11 mΩ 3-Level module in Advanced NPC (ANPC) topology
	F4-23MR12W1M1_B11	EasyPACK [™] 1B 1200 V, 23 mΩ fourpack module
TRENCHSTOP™	F4-200R17N3E4	EconoPACK [™] 3 1700 V, 200 A fourpack IGBT module
IGBT Modules	F\$150R17N3E4	EconoPACK [™] 3 1700 V, 150 A sixpack IGBT module
	FF650R17IE4	PrimePACK [™] 3 1700 V, 650 A half-bridge dual IGBT module
	FF1000R17IE4	PrimePACK [™] 3 1700 V, 1000 A half-bridge dual IGBT module
	FF1200R17IP5	PrimePACK [™] 3+ 1700 V, 1200 A dual IGBT module
	FF1500R17IP5	PrimePACK [™] 3+ 1700 V, 1500 A dual IGBT module
	FF1500R17IP5R	PrimePACK [™] 3 1700 V, 1500 A dual IGBT module
	FF1800R17IP5	PrimePACK [™] 3+ 1700 V, 1800 A dual IGBT module
	FP10R12W1T7_B11	EasyPIM [™] 1B 1200 V, 10 A three phase input rectifier PIM IGBT module
	F\$100R12W2T7_B11	EasyPACK [™] 2B 1200 V, 100 A sixpack IGBT module
	FP150R12KT4_B11	EconoPIM [™] 3 1200V three-phase PIM IGBT module
	FS200R12KT4R_B11	EconoPACK [™] 3 1200 V, 200 A sixpack IGBT module

3 Pin configuration

Pin configuration

Table 1 Pin configuration

Pin No.	Name	Function
1	VCC1	Positive logic supply
2	/INF	Driver input (active low) for operation OUTF or OUTFC



Pin configuration

Table 1 Pin configuration (continued)

Pin No.	Name	Function
3	IN	PWM driver input (active high)
4	GND1	Logic ground
5	VEE2	Power ground
6	OUTF / OUTFC	Additional driver output
7	OUT	Regular driver output
8	VCC2	Positive power supply output side




Figure 3 Pinout standard configuration (top view)




Figure 4 Pinout clamp configuration (top view)

Pin description

- *VCC1*: Logic input supply voltage with wide operating range from 3.3 V up to 15 V. This terminal is referenced to *GND1*
- *GND1*: Ground connection of input circuit. This is the reference point for the input side.
- /INF: Inverted control signal for controlling the operation of output OUTF or OUTFC respectively. An internal filter provides robustness against noise at terminal /INF. An internal weak pull-down resistor favors a low level. This terminal is referenced to GND1
- *IN*: Direct control signal for driver output. An internal filter provides robustness against noise at terminal *IN*. An internal weak pull-down resistor favors off-state. This terminal is referenced to *GND1*
- *VCC2*: Positive power supply pin of output driving circuit. A proper blocking capacitor has to be placed close to this supply pin. This terminal is referenced to *VEE2*.



Functional description

- *VEE2*: Reference ground of the output driving circuit. In case of a bipolar supply (positive and negative voltage referred to IGBT emitter) this pin is connected to the negative supply voltage.
- OUT: This driver output terminal follows the signal at terminal IN to turn on or off the external power transistor. During on-state the driving output is switched to VCC2. This output will be actively pulled down to VEE2 in case of an UVLO event on either the input side or the output side. The active shutdown keeps the output voltage at a low level in case that the output side supply voltage collapses.
- OUTF: This output follows terminal OUT according to the signal at terminal /INF.
- OUTFC: This output follows terminal OUT according to the signal at terminal /INF for turn-on only.

4 Functional description

The 1ED32xxMC12H are general purpose gate drivers incorporating two-level slew-rate control functionality (2L-SRC). Based on one additional input control signal /INF, these drivers enable on-the-fly gate resistor changes.

The integrated galvanic isolation between control input logic and driving output stage grants additional safety. Its input voltage supply range supports the direct connection of various signal sources like DSPs and microcontrollers.

4.1 IC supply

The driver can operate over a wide supply-voltage range at both input side and output side. Both sides have an undervoltage lockout (UVLO) function which suppresses incoming control signals and prevents insufficient supply or gate voltages. The outputs are pulled down in cases of under-voltage lockout on either side.

The input-side power supply at terminal VCC1 can range from typically 3.3 V up to 15 V. This allows a high safety margin with respect to voltage spikes on the supply voltage when supplying with 3.3 V or 5 V. A minimum of $V_{\rm UVLOH1}$ is required to start-up the input side of the driver IC.



Functional description




Figure 5 UVLO behavior regarding V_{VCC1} (top) and V_{VCC2} (bottom) after start up

The output side supports negative gate voltage operation, which helps to avoid a parasitic turn-on during off-state. The negative rail is connected to terminal *VEE2* in this case. A minimum voltage of $V_{\rm UVLOH2}$ at terminal *VCC2* is required for a safe start-up of the IC on the output side. The device is equipped with an undervoltage lockout for input and output independently to ensure correct switching of power transistors . Operation starts only, if both $V_{\rm VCC1}$ and $V_{\rm VCC2}$ have increased above the respective levels $V_{\rm UVLOH1}$ and $V_{\rm UVLOH2}$.

The input signals at terminals IN and INF are ignored until V_{VCC1} reaches the power-up voltage V_{UVLOH1} . Terminal OUT is activated according to the instantaneous state of terminal IN. Terminal OUTF or OUTFC are activated after a UVLO condition for turn-on according to the default state at terminal INF, which is LOW after start up. A new edge at terminal INF is required to establish the initial user setting after a UVLO event. A new edge at terminal INF is required to replace the INF default setting on the output side. If the power supply voltage V_{VCC1} of the input chip drops below V_{UVLOL1} a turn-off signal is sent to the output chip before power-down. Both outputs OUT and OUTF shut down according to the last transmitted status at terminals INF and INFF.

The input signals at terminals IN and INF are ignored until V_{VCC2} reaches the power-up voltage V_{UVLOH2} . Terminal OUT is activated according to the instantaneous state of terminal IN. Terminal OUTF or OUTFC are activated after a UVLO condition of V_{VCC2} for turn-on according to the default state at terminal INF, which is LOW after start up. A new edge at terminal INF is required to establish the initial user setting after a UVLO event. A new edge at terminal INF is required to replace the INF default setting on the output side. If the power supply voltage V_{VCC2} of the output side drops below V_{UVLOL2} , output OUT pulls down independent of the last transmitted status at terminals INF and INF. Output OUTF or OUTFC pull down in addition when the their voltage is below V_{CLAMPL} .



Functional description

UVLO events on the output side other than a full IC start-up result in a recovery of the output terminals *OUTF* and *OUTFC* according to the input-to-output control scheme.

Note:

The supply voltage V_{VCC2} and related protection functions is always referred to as VEE2. There is no differentiation between unipolar or bipolar supply.

A capacitor that is placed in close proximity to the supply terminals *VCC1* and *GND1* on the input side, and *VCC2* and *VEE2* on the output side, avoids eventual triggering of under-voltage lockout events.

The IC is safe with any start-up sequence regarding its supply voltages V_{VCC1} and V_{VCC2} . However, it is good practice to have the input side supply voltage to start up first, followed by the output side supply.

4.2 Input terminals IN and /INF

The input terminals *IN* and */INF* determine the behavior of the two output terminals *OUT* and *OUTF(C)*. While a PWM signal is connected to the IN terminal, thus determining the switching behavior of *OUT* and *OUTF(C)*, the */INF* terminal controls if only *OUT* or both *OUT* and *OUTF(C)* follow the input terminal *IN*. Since both output terminals *OUT* and *OUTF(C)* are connected to gate resistors, */INF* determines whether a single or both gate resistors are connected to an IGBT's gate.

Both input terminals contain a pull-down resistor to bias the IC into a safe mode in case the connection to the system control is interrupted. The non-inverting Schmitt trigger receives the input control signal and has CMOS-compatible trigger thresholds with minimum $V_{\rm IN,L}$ for LOW level and maximum $V_{\rm IN,H}$ for HIGH level. The input signal at terminal *IN* follows a positive logic, while the signal at terminal *INF* follows an active-low logic.

There is a short-pulse suppression filter after the Schmitt trigger with a filter time T_{INFLT} . All pulses that are below $T_{\text{INFLT},\text{min}}$ will be suppressed, and pulses that are longer than $T_{\text{INFLT},\text{max}}$ will pass the filter and be transmitted to the output side. External RC-filters with time constants of more than 10 ns, for example 1 nF and 10 Ω , have to be used to further support the integrated short pulse suppression function to filter input noise.




Figure 6 Timing of input signals with respect of the input filter

All changes at terminal /INF are acknowledged, if they occur earlier than or simultaneously with a change at terminal IN. After a signal edge is applied at terminal IN, the signal at terminal /INF has to be kept for at least $T_{\text{INF-hold}}$ for its status to be transmitted to the output side.

4.3 Output terminal OUT

The output terminal *OUT* changes its status according to the status of the input signal at terminal *IN*. A high signal at terminal *IN* determines a high signal at terminal *OUT*. A low signal determines a low signal.

The driver IC's output section at terminal *OUT* provides a rail-to-rail output. This feature allows the tight control of gate voltage during on-state and short circuit to be maintained as long as the driver's supply is stable. The switching behavior of the power transistor is mainly controlled by the gate resistor, due to the low internal voltage drop of the IC. In turn, the low voltage drop reduces the power to be dissipated by the driver.

The active shutdown feature of terminal *OUT* ensures a safe off-state of the power transistor in case the output side is not connected to the power supply or an undervoltage lockout is in effect. The transistor's gate is clamped at terminal *OUT* to *VEE2*.



Functional description

4.4 Output terminal OUTF

Terminal *OUTF* is the second output of those gate driver ICs, which have the standard output configuration. *OUTF* changes its status according to the status of the input signals /INF and IN. It turns the power transistor on and off in combination with the terminal *OUT*, so that depending on the status at terminal /INF, a higher gate current is available, and the switching speed can be modified on the fly. Terminal *OUTF* is also set to clamping mode, if it is not activated for active gate operation. The clamping mode is activated when the gate voltage of the power transistor is below V_{CLAMPL} during off-state or above V_{VCC2} - V_{CLAMPH} during on-state. The clamping mode during on-state helps to achieve better short circuit clamping. The on-state clamping is activated after turn-on, as soon as the filter time of t_{dCLAMPH} is elapsed. A clamping filter time t_{dCLAMPL} for off-state improves the robustness of the IC's Miller clamp function.

The driver IC's output section at terminal *OUTF* provides a rail-to-rail output. This feature allows the tight control of gate voltage during on-state and short circuit to be maintained as long as the driver's supply is stable. The switching behavior of the power transistor is mainly controlled by the gate resistor, due to the low internal voltage drop of the IC. In turn, the low voltage drop reduces the power to be dissipated by the driver.

Terminal *OUTF* features the active shutdown function. This ensures a safe off-state of the power transistor in case the output side is not connected to the power supply, or the power supply of the output side collapses faster than the UVLO can react. The transistor's gate is clamped at terminal *OUTF* to *VEE2*.

The driving capability of terminal *OUTF* is the same as for terminal *OUT*. *OUTF* and *OUT* can be operated in low resistive connection (i.e. direct paralleling) only if the voltage $V_{/INF}$ at terminal /INF is at the corresponding level at any time.

4.5 Output terminal *OUTFC*

Terminal *OUTFC* is the second output of those gate driver ICs having the Miller clamp function, i.e. the two-level slew-rate control in for turn-on only. *OUTFC* changes its status according to the status of the input signal /INF and IN. It turns on the power transistor in combination with terminal *OUT*, so that depending on the status at terminal /INF, a higher gate current is available and the switching speed can be modified for each PWM edge. Terminal *OUTFC* is not activated during the turn-off transient.

Terminal *OUTFC* is set to clamping mode also if it is not activated for active gate turn-on or turn-off . The clamping mode is activated when the gate voltage of the power transistor is below V_{CLAMPL} during off-state or above V_{VCC2} - V_{CLAMPH} during on-state. The clamping mode during on-state helps to achieve better short circuit clamping. The on-state clamping is activated after turn-on, as soon as the filter time of t_{dCLAMPH} is elapsed. A clamping filter time t_{dCLAMPL} for off-state improves the robustness of the IC's Miller clamp function.

The clamping capability of the output *OUTFC* during off-state of the power transistor is identical to turn-off current capability terminal *OUT*.

The driver IC's output section at terminal *OUTFC* provides a rail-to-rail output. This feature allows the tight control of gate voltage during on-state and short circuit to be maintained as long as the driver's supply is stable. The switching behavior of the power transistor is mainly controlled by the gate resistor, due to the low internal voltage drop of the IC. In turn, the low voltage drop reduces the power to be dissipated by the driver.

Terminal *OUTFC* features the active shutdown function. This ensures a safe off-state of the power transistor in case the output side is not connected to the power supply, or the power supply of the output side collapses faster than the UVLO can react. The transistor's gate is clamped at terminal *OUTFC* to *VEE2*.

The driving capability of terminal *OUTFC* is the same as for terminal *OUT*. *OUTFC* and *OUT* can be operated in low resistive connection (i.e. direct paralleling) only if the voltage $V_{/INF}$ at terminal /INF is at the corresponding level at any time.



Functional description

4.6 Input-to-output control scheme

The two-level slew rate control IC family can activate the additional output *OUTF* or *OUTFC* depending on the input signals at the terminals *IN* and */INF*. The relationship between input signals and output signals is defined in the table below.

Table 2 Input-to-output control scheme

State	IN	/INF	OUT	OUTF	OUTFC
				(1ED3240MC12H, 1ED3241MC12H)	(1ED3250MC12H, 1ED3251MC12H)
1	0	0	0	0*	0*
2	0 → 1	0	0 → 1	0 → 1	0 → 1
3	0	0 → 1	0	0*	0*
4	1	0	1	1*	1*
5	1 → 0	0	1 → 0	1 → HiZ	1 → HiZ
6	1	0 → 1	1	1*	1*
7	0	1	0	0*	0*
8	0	1 → 0	0	0*	0*
9	0 → 1	1	0 → 1	0 → HiZ	0 → HiZ
10	1	1	1	1*	1*
11	1	1 → 0	1	1*	1*
12	1 → 0	1	1 → 0	1 → 0	1 → HiZ
Input UVLO↓	Х	Х	0	last /INF	last /INF
Output UVLO↓	Х	Х	0	HiZ	HiZ

^{*)} Output is activated when the voltage at terminal OUTF or OUTFC is higher than V_{VCC2} - V_{CLAMPH} during on-state, or lower than V_{CLAMPL} during off-state.

The control scheme of the gate driver IC family inherently avoids the activation of the two outputs *OUT* or *OUTF / OUTFC* in active opposite status. Both outputs *OUTF* and *OUTFC* can have the states 1, 0 and high impedance (HiZ) according to the table above. The status of terminal /INF can be changed pulse-by-pulse with a short delay with respect to a potential change of status at terminal IN according to the timing diagrams below.



Electrical characteristics and parameters




Figure 7 Timing diagram of input and output signals for standard version (top) and clamp version (bottom)

5 Electrical characteristics and parameters

5.1 Absolute maximum ratings

Absolute maximum ratings are defined as ratings, that can lead to the destruction of the integrated circuit, if exceeded. Unless otherwise noted all parameters refer to terminal *GND1*.

Table 3 Absolute maximum ratings

Parameter	Symbol	Va	lues	Unit	Note or test
		Min.	Max.		condition
Input to output offset voltage	V _{OFFSET}		2300	V	$V_{\text{VEE2,max}} - V_{\text{VEE2,min}}$ with $V_{\text{VEE2,max}} \ge V_{\text{GND1}}$ $\ge V_{\text{VEE2,min}}$
Power supply input side	V _{VCC1}	-0.3	15	٧	

¹ For functional isolation only

² See also: Insulation characteristics



Electrical characteristics and parameters

Table 3 Absolute maximum ratings (continued)

Parameter	Symbol	Val	lues	Unit	Note or test
		Min.	Max.		condition
Power supply input side	V _{VCC1,dyn}	-0.3	17	V	t < 1 μs ³⁾
Logic input voltages (IN, /INF)	V _{IN}	-0.3	15	V	
Dynamic logic input voltages (IN, /INF)	$V_{\rm IN,dyn}$	-0.3	17	V	t < 1 μs ³⁾
Power supply output side	$V_{\rm VCC2}$	-0.3	40	V	with respect to VEE2
Gate driver output (OUT, OUTF, OUTFC)	V _{OUT}	V _{VEE2} - 0.3	V _{VCC2} +0.3	V	with respect to VEE2
Junction temperature	TJ	-40	150	°C	
Storage temperature	$T_{\rm stg}$	-55	150	°C	
Power dissipation (input side)	$P_{D,IN}$	-	100	mW	$T_{\rm A} = 85 ^{\circ}{\rm C}, 1{\rm s0p}^{4)}$
Power dissipation (output side)	$P_{D,OUT}$	-	625	mW	$T_{\rm A} = 85 ^{\circ}{\rm C}, 1{\rm s0p}^{5)}$
Thermal resistance (input side)	R _{THJA,IN}	-	104	K/W	T _A = 85 °C, 1s0p
Thermal resistance (output side)	R _{THJA,OUT}	-	104	K/W	T _A = 85 °C, 1s0p
ESD capability	V _{ESD,HBM}	-	4	kV	6)
	ESD,CDM	-	TC 1000		7)




Figure 8 Reference layout for thermal data (1s0p, 2 x 50 mm² cooling area, Copper thickness 35 μm)

This PCB layout represents the reference layout used for the thermal characterization of the 300 mil package.

5.2 Operating parameters

The IC operates as described in the functional description within the operating parameters. Unless otherwise noted all parameters refer to GND1.

Table 4 Operating parameters

Parameter	Symbol	Val	ues	Unit	Note or test
		Min.	Max.		condition
Power supply output side	V _{VCC2}	10	35	V	
Power supply input side	V _{VCC1}	3	15	V	

Parameter is not subject of production test - verified by design/ characterization

v2.0

⁴ IC output-side power dissipation is derated linearly with 9.62 mW/°C above 139,6 °C

⁵ IC output-side power dissipation is derated linearly with 9.62 mW/°C above 85 °C

⁶ According to ANSI/ESDA/JEDEC-JS-001-2017

⁷ According to ANSI/ESDA/JEDEC-JS-002-2014, TC = test condition in Volt



Electrical characteristics and parameters

Table 4 Operating parameters (continued)

Parameter	Symbol	Va	lues	Unit	Note or test
		Min.	Max.		condition
Logic input voltages (IN, /INF)	V _{IN}	-0.3	5.5	V	
Ambient temperature	T _A	-40	125	°C	
Thermal coefficient, junction-top	$\psi_{TH,JT}$	-	6.8	K/W	T _A = tbd °C
Common mode transient immunity (CMTI)	CMTI	-	200	kV/μs	V _{OFFSET,test} = 1500 V

5.3 Eletrical characteristics

The electrical characteristics include the spread of values in supply voltages, load and junction temperatures given below. Typical values represent the median values at $V_{VCC1} = 5 \text{ V}$, $V_{VCC2} = 15 \text{ V}$, and $T_A = 25 ^{\circ}\text{C}$. Unless otherwise noted all voltages are given with respect to their respective reference *GND1* or *VEE2*.

5.3.1 Power supply

Table 5 Power supply

Parameter	Symbol Values				Note or test	
		Min.	Тур.	Max.		condition
UVLO threshold input side (on)	V _{UVLOH1}	-	2.85	3.1	٧	
UVLO threshold input side (off)	V _{UVLOL1}	2.5	2.65	-	V	
UVLO hysteresis input side	V _{HYS1}	0.1	0.2	-	V	
UVLO threshold output side (on)	V _{UVLOH2}	-	11.8	12.5	V	
UVLO threshold output side (off)	V _{UVLOL2}	10.4	10.8	-	٧	
UVLO hysteresis output side	V _{HYS2}	0.8	-	-	V	
Quiescent current input side	I_{Q1}	-	1.2	1.4	mA	
Quiescent current output side	I_{Q2}	-	1.9	2.3	mA	
Start up time ⁸⁾	t_{START}	-	7.4	20	μs	

5.3.2 Logic input

Table 6 Logic input

Parameter	Symbol		Values		Unit	Note or test
		Min.	Тур.	Max.		condition
IN, /INF low-input threshold voltage	$V_{IN,L}$	1	1.2	-	V	
IN, /INF high-input threshold voltage	$V_{IN,H}$	-	2.1	2.3	V	
IN, /INF low/high hysteresis	V _{IN,HYS}	0.7	-		٧	
IN, /INF input current	I _{IN}	-	-	100	μΑ	$V_{\text{IN}} = V_{\text{VCC1}}$

⁸ Parameter is not subject of production test - verified by design/ characterization



Electrical characteristics and parameters

Table 6 Logic input (continued)

Parameter	Symbol	Values			Unit	Note or test
		Min.	Тур.	Max.		condition
IN, /INF pull-down resistor	$R_{\rm IN,PD}$	-	75	-	kΩ	
/INF hold time ⁹⁾	t _{/INF,hold}	50	-	-	ns	

5.3.3 Gate driver

Table 7 Gate driver

Parameter	Symbol		Values		Unit	Note or test	
		Min.	Min. Typ. Max.			condition	
High-level output peak current (<i>OUT</i> , <i>OUTF</i> , <i>OUTFC</i> , 1ED32x0MC12H) ¹⁰⁾	Іон	-	5	-	A	Output on	
Low-level output peak current (OUT, OUTF, 1ED3240MC12H) ¹⁰⁾	I _{OL}	-	5	-	А	Output off	
High-level output resistance (<i>OUT</i> , <i>OUTF</i> , <i>OUTFC</i> , 1ED32x0MC12H)	R _{OH,1}	-	0.92	1.47	Ω	Output on, I _{OH} = 0.1 A	
Low-level output resistance (OUT, OUTF, OUTFC, 1ED32x0MC12H)	R _{OL,1}	-	0.73	1.1	Ω	Output off, I _{OL} = 0.1 A	
High-level output peak current (<i>OUT</i> , <i>OUTF</i> , <i>OUTFC</i> , 1ED32x1MC12H) ¹⁰⁾	Іон	-	9	-	A	Output on	
Low-level output peak current (OUT, OUTF, 1ED3241MC12H) ¹⁰⁾	I _{OL}	-	9	-	А	Output off	
High-level output resistance (OUT, OUTF, OUTFC, 1ED32x1MC12H)	R _{OH,2}	-	0.51	0.81	Ω	Output on, I _{OH} = 0.1 A	
Low-level output resistance (OUT, OUTF, OUTFC, 1ED32x1MC12H)	R _{OL,2}	-	0.42	0.63	Ω	Output off, I _{OL} = 0.1 A	
High-level output voltage (<i>OUT</i> , <i>OUTF</i> , <i>OUTFC</i>)	ΔV _{OH}	-	-	0.1	V	Output on, V_{VCC2} - V_{OH} ; I_{OH} = 20 mA	
Low-level output voltage (OUT, OUTF, OUTFC)	$\Delta V_{\rm OL}$	-	-	0.1	V	Output off, V_{VCC2} - V_{OH} ; I_{OH} = 20 mA	
Low-level clamp peak current (OUTF, OUTFC) 10)	I _{CLAMPL}	-	2.1	-	А	V _{OL} = 2 V	
Short-circuit clamp voltage between <i>OUT / OUTF / OUTFC</i> and <i>VCC2</i> ¹⁰⁾	V _{CLP}	-	-	1.3	V	Output on, I _{OH} = 500 mA, t < 10 μs	

⁹ Parameter is not subject of production test - verified by design/ characterization

Parameter is not subject of production test - verified by design/ characterization



Electrical characteristics and parameters

Table 7Gate driver (continued)

Parameter	Symbol	nbol Values			Unit	Note or test	
		Min.	Тур.	Max.		condition	
Active Miller clamp threshold voltage OFF (OUTF, OUTFC)	V_{CLAMPL}	-	2	2.5	V	V_{OL} - V_{VEE2} , $V_{\text{/INF}}$ = 0	
Clamping ON threshold voltage (OUTF, OUTFC)	V_{CLAMPH}	0.5	1	-	V	V_{VCC2} - V_{OH} , $V_{\text{/INF}}$ = 1	
Active Miller clamp delay time (OUTF, OUTFC) ¹⁰⁾	$t_{ ext{dCLAMPL}}$	-	-	80	ns	$V_{\text{OL}} \le V_{\text{VEE2}} + V_{\text{CLAMPL}},$ $V_{/\text{INF}} = 1$	
Clamping ON delay time (IGBT variants, <i>OUTF</i> , <i>OUTFC</i>) ¹⁰⁾	$t_{dCLAMPH}$	-	890	-	ns	$V_{\text{OH}} \ge V_{\text{VCC2}} - V_{\text{CLAMPH}},$ $V_{\text{/INF}} = 1$	

5.3.4 Dynamic characteristics

The load capacitance is 100 pF if not otherwise noted.

Table 8 Dynamic characteristics

Parameter	Symbol		Values		Unit	Note or test	
		Min.	Тур.	Max.		condition	
Input-to-output propagation delay ON	t_{PDON}	-	-	110	ns	IN turn-on threshold to 10% output on	
Input-to-output propagation delay OFF	t_{PDOFF}	-	-	110	ns	IN turn-off threshold to 90% output off	
Input-to-output propagation delay distortion $(t_{PDOFF} - t_{PDON})$	t_{PDISTO}	-10	0	5	ns		
Input-pulse suppression time	t _{INFLT}	30	-	40	ns		
Input-to-output propagation delay mismatch OUT vs. OUTF/	t _{PDOUT} -	-	<1	-	ns		
Input-to-output, part to part propagation delay variation	t _{PD,P2P}	-	-	15	ns		
Input-to-output propagation delay variation due to temperature	$t_{PD,T}$	-5	-	12	ns		
Rise time	t_{RISE}	-	1.6	15	ns	C _{LOAD} = 100 pF	
Fall time	t _{FALL}	-	1.5	15	ns	C _{LOAD} = 100 pF	
Rise time	t_{RISE}	-	9	30	ns	C _{LOAD} = 1 nF	
Fall time	t _{FALL}	-	8.5	30	ns	C _{LOAD} = 1 nF	

Parameter is not subject of production test - verified by design/ characterization

Parameter is not subject of production test - verified by design/ characterization



Isolation ratings and characteristics (all pending)

5.3.5 Active shutdown

Table 9 Active shutdown

Parameter	Symbol	Values				s Unit		Note or test
		Min.	Тур.	Max.		condition		
Active shutdown voltage	V _{ACTSD,L}	-	1.5	2.0	V	$I_{\rm O}$ = 10 mA; $V_{\rm VCC2}$ open		

6 Isolation ratings and characteristics (all pending)

6.1 Safety limiting values

This coupler is suitable for rated insulation only within the given safety ratings. Compliance with the safety ratings shall be ensured by means of suitable protective circuits.

Table 10 Safety limiting values

Description	Symbol	Characteristic	Unit
Maximum ambient safety temperature	T_{S}	150	°C
Maximum input-side power dissipation at $T_A = 25^{\circ}C^{12}$	P _{SI}	100	mW
Maximum output-side power dissipationat T _A = 25°C ¹³⁾	P _{SO}	1100	mW

6.2 Certified according to VDE 0884-11 for reinforced insulation

This coupler is suitable for safe electrical insulation only within the safety ratings. Compliance with the safety ratings shall be ensured by means of suitable protective circuits.

Table 11 Reinforced insulation ratings according to VDE 0884-11

Description	Symbol	Characteristic	Unit
Installation classification per EN 60664-1, Table 1			_
for rated mains voltage ≤ 150 V (rms)		I-IV	
for rated mains voltage ≤ 300 V (rms)		I-IV	
for rated mains voltage ≤ 600 V (rms)		1-111	
for rated mains voltage ≤1000 V (rms)		1-11	
Climatic classification		40/125/21	-
Pollution degree (EN 60664-1)		2	_
Minimum external clearance	CLR	>8	mm
Minimum external creepage	CPG	>8	mm
Minimum comparative tracking index	СТІ	400	_

¹² IC input-side power dissipation is derated linearly at 9.62 mW/°C above 139.6 °C

v2.0

¹³ IC output-side power dissipation is derated linearly at 7.35 mW/°C above 25 °C



Timing diagrams

Table 11 Reinforced insulation ratings according to VDE 0884-11 (continued)

Description	Symbol	Characteristic	Unit
Maximum repetitive insulation voltage	V_{IORM}	1767	V (peak)
Highest allowable overvoltage	V_{IOTM}	8000	V (peak)
Maximum surge insulation voltage Surge insulation test voltage $V_{\text{TEST}} = V_{\text{IOSM}} \times 1.6$	V _{IOSM}	6875	V (peak)
Apparent charge, method a $V_{pd(ini),a} = V_{IOTM}, V_{pd(m)} = 1.6 \times V_{IORM}, t_{ini} = 1 \text{ min}$	q _c	<5	pC
Apparent charge, method b $V_{\text{pd(ini),b}} = 1.2 \times V_{\text{IOTM}}, V_{\text{pd(m)}} = 1.875 \times V_{\text{IORM}}, t_{\text{ini,b}} = 1 \text{ s}$	q_{c}	<5	pC
Insulation resistance at $T_{A, max}$	R _{IO}	> 10 ¹¹	Ω
Insulation resistance at T_{S}	R _{IO}	> 109	Ω
Insulation capacitance	C _{IO}	1.66	pF

6.3 Recognized under UL 1577 (File E311313, planned)

Table 12 Recognized under UL 1577

Description	Symbol	Characteristic	Unit
Insulation withstand voltage/1 min	V _{ISO}	5700	V (rms)
Insulation test voltage/1 s	V _{ISO, TEST}	6840	V (rms)

7 Timing diagrams





Figure 9 Propagation delay



Timing diagrams



OUT - OUTF/OUTFC propagation delay mismatch Figure 10




Figure 11 Rise and fall time



Timing diagrams




Figure 12 /INF hold time



Package dimensions

Package dimensions 8




Figure 13 PG-DSO-8-66 (Plastic (green) dual small outline package)

Revision history

Document version	Date of release	Description of changes
2.0	9.4.2021	initial release
		•

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2021-04-09 Published by Infineon Technologies AG 81726 Munich, Germany

© 2021 Infineon Technologies AG All Rights Reserved.

Do you have a question about any aspect of this document?

 ${\bf Email: erratum@infineon.com}$

Document reference IFX-rdh1516095420488

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.