MICROCHIP

DSA60XX

Ultra-Small, Low Power MEMS Oscillator for Automotive

Features

- Automotive AEC-Q100 Qualified
- Wide Frequency Range: 2 kHz to 80 MHz
- Ultra-Low Power Consumption: 1.3 mA/1 µA (Active/Standby)
- Ultra-Small Footprints
  - 1.6 mm x 1.2 mm VFLGA
  - 2.0 mm x 1.6 mm VFLGA
  - 2.5 mm x 2.0 mm VLGA
  - 3.2 mm x 2.5 mm VDFN
  - 5.0 mm x 3.2 mm VDFN
  - 7.0 mm x 5.0 mm VDFN
- Frequency Select Input Supports Two Pre-Defined Frequencies
- High Stability: ±20 ppm, ±25 ppm, ±50 ppm
- Wide Temperature Range
  - Automotive Grade 1: –40°C to +125°C
  - Automotive Grade 2: –40°C to +105°C
  - Automotive Grade 3: –40°C to +85°C
- Excellent Shock and Vibration Immunity
  - Qualified to MIL-STD-883
- High Reliability
  - 20x Better MTF Than Quartz Oscillators
- Supply Range of 1.71V to 3.63V
- Short Sample Lead Time: <1 week
- Lead Free & RoHS Compliant

Applications

- Automotive Infotainment
- Automotive ADAS, Surround View Cameras
- In-Vehicle Networking, CAN bus, Ethernet

General Description

The DSA60xx family of MEMS oscillators combines industry-leading low-power consumption, ultra-small packages with exceptional frequency stability, and jitter performance over temperature. The single-output DSA60xx MEMS oscillators are excellent choices for use as clock references in automotive applications in which small size, low power consumption, and long-term reliability are paramount. The device family is Automotive Grade AEC-Q100 qualified.

The DSA60xx family is available in 1.6 mm x 1.2 mm & 2.0 mm x 1.6 mm VFLGA, 7.0 mm x 5.0 mm, 5.0 mm x 3.2 mm & 3.2 mm x 2.5 mm VDFN, and 2.5 mm x 2.0 mm VLGA packages. These packages are "drop-in" replacements for standard 4-pin CMOS quartz crystal oscillators.

Package Types

DSA60xx
7.0 mm x 5.0 mm VDFN
(Top View)

$\overline{OE}$/STDBY/FS — 1 | 4 — VDD
EP
GND — 2 | 3 — OUT

DSA60xx
5.0 mm x 3.2 mm VDFN
3.2 mm x 2.5 mm VDFN
2.5 mm x 2.0 mm VLGA
2.0 mm x 1.6 mm VFLGA
1.6 mm x 1.2 mm VFLGA
(Top View)

$\overline{OE}$/STDBY/FS — 1 | 4 — VDD
GND — 2 | 3 — OUT

DSA60XX

Block Diagram

1.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings

Supply Voltage .... –0.3V to +4.0V
Input Voltage (V_{IN}) .... –0.3V to V_{DD}+0.3V
ESD Protection .... 4 kV HBM, 400V MM, 2 kV CDM

ELECTRICAL CHARACTERISTICS

Electrical Characteristics: Unless otherwise indicated, V_{DD} = 1.8V –5% to 3.3V +10%, T_A = –40°C to +125°C.						
Parameters	Sym.	Min.	Typ.	Max.	Units	Conditions
Supply Voltage Note 1	V_{DD}	1.71	—	3.63	V	—
Active Supply Current	I_{DD}	—	1.3	—	mA	F_{OUT} = 24 MHz, V_{DD} = 1.8V, No Load
Power Supply Ramp	t_{PU}	0.1	—	100	ms	Note 9
Standby Supply Current Note 2	I_{STBY}	—	1.0	—	µA	V_{DD} = 1.8/2.5V
		—	1.5	—		V_{DD} = 3.3V
Frequency	f_0	0.002	—	80	MHz	—
Frequency Stability Note 3	Δf	—	—	±20 ±25 ±50	ppm	All temp ranges
Aging	Δf	—	—	±5	ppm	1st year @25°C
		—	—	±1		Per year after first year
Startup Time	t_{SU}	—	—	1.5	ms	From 90% V_{DD} to valid clock output, T = 25°C
Input Logic Levels Note 4	V_{IH}	0.7 x V_{DD}	—	—	V	Input Logic High
	V_{IL}	—	—	0.3 x V_{DD}	V	Input Logic Low
Output Disable Time Note 5	t_{DA}	—	—	200 + 2 Periods	ns	—
Output Enable Time Note 6	t_{EN}	—	—	1	µs	—
Enable Pull-Up Resistor Note 7	—	—	300	—	kΩ	If configured
Output Logic Levels, Low Drive	V_{OH}	0.8 x V_{DD}	—	—	V	Output Logic High, I = 1 mA
	V_{OL}	—	—	0.2 x V_{DD}	V	Output Logic Low, I = –1 mA

Note 1: Pin 4 V_{DD} should be filtered with 0.1 µF capacitor.

    2: Not including current through pull-up resistor on EN pin (if configured).

    3: Includes frequency variations due to initial tolerance, temp. and power supply voltage.

    4: Input waveform must be monotonic with rise/fall time < 10 ms

    5: Output Disable time takes up to two periods of the output waveform + 200 ns.

    6: For parts configured with OE, not Standby.

    7: Output is enabled if pad is floated or not connected.

    8: Output Duty Cycle will be 40% to 60% when output frequency is between 40 MHz to 60 MHz.

    9: Time to reach 90% of target V_{DD}. Power ramp rise must be monotonic.

    10: Peak-to-peak period jitter is measured over 10,000 cycles.

DSA60XX

ELECTRICAL CHARACTERISTICS (CONTINUED)

Electrical Characteristics: Unless otherwise indicated, V_{DD} = 1.8V –5% to 3.3V +10%, T_A = –40°C to +125°C.

Parameters	Sym.	Min.	Typ.	Max.	Units	Conditions	
Output Transition Time Rise Time/Fall Time	t_{RX}/t_{FX}	—	2.5	3.5	ns	DSA60x3B Low Drive, 20% to 80% C_L = 5 pF	V_{DD} = 1.8V
		—	1.5	2.2			V_{DD} = 2.5V/3.3V
	t_{RY}/t_{FY}	—	1.2	2.0	ns	DSA60x1B Std. Drive, 20% to 80% C_L = 10 pF	V_{DD} = 1.8V
		—	0.6	1.2			V_{DD} = 2.5V/3.3V
Output Duty Cycle Note 8	SYM	45	—	55	%	—	
Period Jitter, RMS	J_{PER}	—	28	—	ps	DSA60x3B Low Drive, F_{OUT} = 27 MHz C_L = 5 pF	V_{DD} = 1.8V
		—	23	—			V_{DD} = 2.5V/3.3V
		—	20	—		DSA60x1B Std. Drive, F_{OUT} = 27 MHz C_L = 10 pF	V_{DD} = 1.8V
		—	18	—			V_{DD} = 2.5V/3.3V
Cycle-to-Cycle Jitter, Peak	J_{Cy-Cy}	—	120	—	ps	DSA60x3B Low Drive, F_{OUT} = 27 MHz C_L = 5 pF	V_{DD} = 1.8V
		—	90	—			V_{DD} = 2.5V/3.3V
		—	115	—		DSA60x1B Std. Drive, F_{OUT} = 27 MHz C_L = 10 pF	V_{DD} = 1.8V
		—	90	—			V_{DD} = 2.5V/3.3V

Note 1: Pin 4 V_{DD} should be filtered with 0.1 µF capacitor.

2: Not including current through pull-up resistor on EN pin (if configured).

3: Includes frequency variations due to initial tolerance, temp. and power supply voltage.

4: Input waveform must be monotonic with rise/fall time < 10 ms

5: Output Disable time takes up to two periods of the output waveform + 200 ns.

6: For parts configured with OE, not Standby.

7: Output is enabled if pad is floated or not connected.

8: Output Duty Cycle will be 40% to 60% when output frequency is between 40 MHz to 60 MHz.

9: Time to reach 90% of target V_{DD}. Power ramp rise must be monotonic.

10: Peak-to-peak period jitter is measured over 10,000 cycles.

ELECTRICAL CHARACTERISTICS (CONTINUED)

Electrical Characteristics: Unless otherwise indicated, V_{DD} = 1.8V –5% to 3.3V +10%, T_A = –40°C to +125°C.

Parameters	Sym.	Min.	Typ.	Max.	Units	Conditions	
Period Jitter, Peak-to-Peak, Note 10	$J_{PERPK-PK}$	—	210	—	ps	DSA60x3B Low Drive, F_{OUT} = 27 MHz C_L = 5 pF	V_{DD} = 1.8V
		—	190	—			V_{DD} = 2.5V/3.3V
		—	160	—		DSA60x1B Std. Drive, F_{OUT} = 27 MHz C_L = 10 pF	V_{DD} = 1.8V
		—	144	—			V_{DD} = 2.5V/3.3V

Note 1: Pin 4 V_{DD} should be filtered with 0.1 µF capacitor.

2: Not including current through pull-up resistor on EN pin (if configured).

3: Includes frequency variations due to initial tolerance, temp. and power supply voltage.

4: Input waveform must be monotonic with rise/fall time < 10 ms

5: Output Disable time takes up to two periods of the output waveform + 200 ns.

6: For parts configured with OE, not Standby.

7: Output is enabled if pad is floated or not connected.

8: Output Duty Cycle will be 40% to 60% when output frequency is between 40 MHz to 60 MHz.

9: Time to reach 90% of target V_{DD}. Power ramp rise must be monotonic.

10: Peak-to-peak period jitter is measured over 10,000 cycles.

TEMPERATURE SPECIFICATIONS (Note 1)

Parameters	Sym.	Min.	Typ.	Max.	Units	Conditions
Temperature Ranges						
Maximum Junction Temperature	T_J	—	—	+150	°C	—
Storage Ambient Temperature Range	T_S	–55	—	+150	°C	—
Soldering Temperature	—	—	+260	—	°C	40 sec. max.

Note 1: The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable junction temperature and the thermal resistance from junction to air (i.e., T_A, T_J, θ_{JA}). Exceeding the maximum allowable power dissipation will cause the device operating junction temperature to exceed the maximum +150°C rating. Sustained junction temperatures above +150°C can impact the device reliability.

2.0   PIN DESCRIPTIONS

The DSA60xx is a highly configurable device and can be factory programmed in many different ways to meet the customer's needs. Microchip's ClockWorks® Configurator http://clockworks.microchip.com/Timing/ must be used to choose the necessary options, create the final part number, data sheet, and order samples. The descriptions of the pins are listed in Table 2-1.

TABLE 2-1:   DSA60XX PIN FUNCTION TABLE

Pin Number	Pin Name	Description
1	OE	Output Enable: H = Active, L = Disabled (High Impedance).
	$\overline{\text{STDBY}}$	Standby: H = Device is active, L = Device is in standby (Low Power Mode).
	FS	Frequency Select: H = Output Frequency 1, L = Output Frequency 2.
2	GND	Ground.
3	OUTPUT	Oscillator clock output
4	VDD	Power Supply: 1.71V to 3.63V.

An explanation of the different options listed in Table 2-1 follows.

2.1   Pin 1

This is a control pin and may be configured to fulfill one of six different functions. If not actively driven, a 10 kΩ pull-up resistor is recommended.

2.1.1   OUTPUT ENABLE (OE)

Pin 1 may be configured as OE. Oscillator output may be turned on and off according to the state of this pin.

2.1.2 $\overline{\text{STDBY}}$

Pin 1 may be configured as Standby. When the pin is low, both output buffer and PLL will be off and the device will enter a low power mode.

2.1.3   FREQUENCY SELECT (FS)

Pin 1 may be configured as FS. The output may be set to one of two pre-programmed frequencies. The output clock frequencies can only be set to either kHz or MHz. A combination of kHz and MHz cannot be set.

2.2   Pins 2 through 4

Pins 2 and 4 are the supply terminals, GND and VDD respectively. Pin 3 is the clock output, programmable to Standard and Low Drive strength settings. Visit ClockWorks® Configurator to customize your device.

DSA60XX

3.0   DIAGRAMS

FIGURE 3-1:   *Output Waveform.*

FIGURE 3-2:   *Test Circuit.*

FIGURE 3-3:   *Recommended Board Layout.*

4.0   SOLDER REFLOW PROFILE

FIGURE 4-1:   *Solder Reflow Profile.*

MSL 1 @ 260°C refer to JSTD-020C	
Ramp-Up Rate (200°C to Peak Temp)	3°C/sec. max.
Preheat Time 150°C to 200°C	60 to 180 sec.
Time maintained above 217°C	60 to 150 sec.
Peak Temperature	255°C to 260°C
Time within 5°C of actual Peak	20 to 40 sec.
Ramp-Down Rate	6°C/sec. max.
Time 25°C to Peak Temperature	8 minutes max.

DSA60XX

5.0 PACKAGING INFORMATION

5.1 Package Marking Information

4-Lead
7.0mm x 5.0mm VDFN*
5.0mm x 3.2mm VDFN*
3.2mm x 2.5mm VDFN*
2.5mm x 2.0mm VLGA*

Example

```
XXXXXXX
XXXYYWW
   0SSS
●
```

```
0400000
DCP1834
   0287
●
```

4-Lead VFLGA*
2.0mm x 1.6mm
1.6mm x 1.2mm

Example

```
XXXX
 SSS
●
```

```
011H
 502
●
```

Legend:	XX...X	Product code or customer-specific information
	Y	Year code (last digit of calendar year)
	YY	Year code (last 2 digits of calendar year)
	WW	Week code (week of January 1 is week '01')
	SSS	Alphanumeric traceability code
	(e3)	Pb-free JEDEC® designator for Matte Tin (Sn)
	*	This package is Pb-free. The Pb-free JEDEC designator ((e3)) can be found on the outer packaging for this package.

●, ▲, ▼ Pin one index is identified by a dot, delta up, or delta down (triangle mark).

Note: In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information. Package may or may not include the corporate logo.

Underbar (_) and/or Overbar (̄) symbol may not be to scale.

4-Lead Very Thin Dual Flatpack, No Lead Package (JZA) - 7x5x0.9 mm Body [VDFN] With 2.2x3.5 mm Exposed Pad

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

	Units		MILLIMETERS		
Dimension Limits			MIN	NOM	MAX
Number of Terminals		N		004	
Pitch		e		5.08 Ref	
Overall Height		A	0.80	0.85	0.90
Standoff		A1	0.00	-	0.05
Terminal Thickness		A3		0.203 Ref	
Overall Length		D	6.90	7.00	7.10
Exposed Pad Length		D2	2.10	2.20	2.30
Overall Width		E	4.90	5.00	5.10
Exposed Pad Width		E2	3.40	3.50	3.60
Terminal Width		b	1.35	1.40	1.45
Terminal Length		L	1.10	1.20	1.30

Notes:

1. Pin 1 visual index feature may vary, but must be located within the pin 1 area.
2. Package is saw singulated
3. Dimensioning and tolerancing per ASME Y14.5M
   BSC: Basic Dimension. Theoretically exact value shown without tolerances.
   REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-1025 Rev A Sheet 2 of 2

## 4-Lead Very Thin Dual Flatpack, No Lead Package [JZA] - 7x5x0.9 mm Body [VDFN] With 2.2x3.5 mm Exposed Pad

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

RECOMMENDED LAND PATTERN

	Units	MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Optional Center Pad Width	X2			2.30
Optional Center Pad Length	Y2			3.60
Contact Pad Spacing	C1		5.08	
Contact Pad Spacing	C2		3.90	
Contact Pad Width (Xnn)	X1			1.50
Contact Pad Length (Xnn)	Y1			1.30
Contact Pad to Center Pad (Xnn)	G1	0.69		
Thermal Via Diameter	V		0.33	
Thermal Via Pitch	EV		1.20	

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

    BSC: Basic Dimension. Theoretically exact value shown without tolerances.

2. For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process

Microchip Technology Drawing C04-3025 Rev A

4-Lead Very Thin Plastic Dual Flat, No Lead Package (H6A) - 5x3.2 mm Body [VDFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

TOP VIEW

SIDE VIEW

DETAIL A
ALTERNATE PIN 1
CONFIGURATION

BOTTOM VIEW

Microchip Technology Drawing C04-1008 Rev A Sheet 1 of 2

DSA60XX

> **Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

TOP VIEW

SIDE VIEW

DETAIL A
ALTERNATE PIN 1
CONFIGURATION

BOTTOM VIEW

Microchip Technology Drawing C04-1008 Rev A Sheet 1 of 2

4-Lead Very Thin Plastic Dual Flat, No Lead Package (H6A) - 5x3.2 mm Body [VDFN]

> **Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

|	Units	MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Number of Terminals	N		4	
Pitch	e		2.54 BSC	
Overall Height	A	0.80	0.85	0.90
Standoff	A1	0.00	0.02	0.05
Terminal Thickness	A3		0.20 REF	
Overall Length	D		5.00 BSC	
Overall Width	E		3.20 BSC	
Terminal Width	b	1.15	1.20	1.25
Terminal 1 Tab	b1		0.10 REF	
Terminal Length	L	0.80	0.90	1.00
Terminal Pull Back	L1		0.10 REF	
Terminal 1 Tab	L2		0.20 REF	
Terminal 1 Chamfer	CH		0.25 REF	
Terminal Spacing	K		1.20 REF	

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.
2. Package is saw singulated
3. Dimensioning and tolerancing per ASME Y14.5M
   BSC: Basic Dimension. Theoretically exact value shown without tolerances.
   REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-1008 Rev A Sheet 2 of 2

4-Lead Very Thin Plastic Dual Flat, No Lead Package (H6A) - 5x3.2 mm Body [VDFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

RECOMMENDED LAND PATTERN

	Units	MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	E			
Contact Pad Spacing	C		2.00	
Contact Pad Width (X4)	X1			1.40
Contact Pad Width	X2			1.50
Contact Pad Length (X4)	Y1			1.10
Contact Pad Tab Length	Y2			0.36
Contact Pad to Center Pad (X2)	G1	1.00		
Contact Pad to Contact Pad (X2)	G2	1.14		
Terminal 1 Contact Pad Chamfer	CH		0.30	

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

    BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-3008 Rev A

4-Lead Very Thin Plastic Dual Flatpack No-Lead (H4A) - 3.2x2.5 mm Body [VDFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

TOP VIEW

SIDE VIEW

BOTTOM VIEW

Microchip Technology Drawing C04-1006 Rev B Sheet 1 of 2

4-Lead Very Thin Plastic Dual Flatpack No-Lead (H4A) - 3.2x2.5 mm Body [VDFN]

> **Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

	Units	MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Number of Terminals	N		4	
Pitch	e		2.10 BSC	
Overall Height	A	0.80	0.85	0.90
Standoff	A1	0.00	0.02	0.05
Overall Length	D		3.20 BSC	
Overall Width	E		2.50 BSC	
Terminal Width	b	0.85	0.90	0.95
Terminal Length	L	0.70	0.80	0.90
Terminal 1 Index Chamfer	CH		0.25 REF	

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.
2. Package is saw singulated
3. Dimensioning and tolerancing per ASME Y14.5M
   BSC: Basic Dimension. Theoretically exact value shown without tolerances.
    REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-1006 Rev B Sheet 2 of 2

4-Lead Very Thin Plastic Dual Flatpack No-Lead (H4A) - 3.2x2.5 mm Body [VDFN]

Note:	For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

RECOMMENDED LAND PATTERN

	Units	MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	E	2.10 BSC		
Contact Pad Spacing	C		1.80	
Contact Pad Width (Xnn)	X			0.90
Contact Pad Length (Xnn)	Y			1.00
Contact Pad Length (Xnn)	CH	0.20 REF		

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

   BSC: Basic Dimension. Theoretically exact value shown without tolerances.
   REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-3006 Rev B

DSA60XX

4-Lead Very Thin Land Grid Array (AUA) - 2.5x2.0 mm Body [VLGA]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

TOP VIEW

SIDE VIEW

BOTTOM VIEW

4-Lead Very Thin Land Grid Array (AUA) - 2.5x2.0 mm Body [VLGA]

| **Note:**	For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

	Units	MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Number of Terminals	N		4	
Terminal Pitch	e		1.65 BSC	
Terminal Pitch	e1		1.25 BSC	
Overall Height	A	0.79	0.84	0.89
Standoff	A1	0.00	0.02	0.05
Substrate Thickness (with Terminals)	A3		0.20 REF	
Overall Length	D		2.50 BSC	
Overall Width	E		2.00 BSC	
Terminal Width	b1	0.60	0.65	0.70
Terminal Length	L	0.60	0.65	0.70
Terminal 1 Index Chamfer	CH	-	0.225	-

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.
2. Package is saw singulated
3. Dimensioning and tolerancing per ASME Y14.5M

   BSC: Basic Dimension. Theoretically exact value shown without tolerances.

   REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-1202B Sheet 2 of 2

DSA60XX

4-Lead Very Thin Land Grid Array (AUA) - 2.5x2.0 mm Body [VLGA]

Note:	For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

RECOMMENDED LAND PATTERN

	Units	MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	E	1.65 BSC		
Contact Spacing	C		1.25	
Contact Width (X4)	X			0.70
Contact Pad Length (X4)	Y			0.80
Space Between Contacts (X2)	G1	0.95		
Space Between Contacts (X2)	G2	0.45		
Contact 1 Index Chamfer	CH	0.13 X 45° REF		

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

    BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-3202B

© 2019 - 2022 Microchip Technology Inc. and its subsidiaries

4-Lead Very Thin Fine Pitch Land Grid Array (ASA) - 2.0x1.6 mm Body [VFLGA]

> **Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

TOP VIEW

(DATUM A)
(DATUM B)
NOTE 1

2X | 0.05 | C
2X | 0.05 | C

SIDE VIEW

// | 0.10 | C
A1
C | A
SEATING PLANE
(A3)
4X | 0.08 | C

BOTTOM VIEW

b2
3X b1
CH
φ | 0.07 Ⓜ | C | A | B
| 0.03 Ⓜ | C
CH
NOTE 1
4X L
e1
e1/2
N
e

Microchip Technology Drawing C04-1200 Rev D Sheet 1 of 2

DSA60XX

**4-Lead Very Thin Fine Pitch Land Grid Array (ASA) - 2.0x1.6 mm Body [VFLGA]**

> **Note:** For the most current package drawings, please see the Microchip Packaging Specification located at
> http://www.microchip.com/packaging

	Units	MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Number of Terminals	N		4	
Terminal Pitch	e		1.55 BSC	
Terminal Pitch	e1		0.95 BSC	
Overall Height	A	0.79	0.84	0.89
Standoff	A1	0.00	0.02	0.05
Substrate Thickness (with Terminals)	A3		0.20 REF	
Overall Length	D		2.00 BSC	
Overall Width	E		1.60 BSC	
Terminal Width	b1	0.30	0.35	0.40
Terminal Width	b2	0.40	0.45	0.50
Terminal Length	L	0.50	0.55	0.60
Terminal 1 Index Chamfer	CH	-	0.15	-

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.
2. Package is saw singulated
3. Dimensioning and tolerancing per ASME Y14.5M

    BSC: Basic Dimension. Theoretically exact value shown without tolerances.
   REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-1200 Rev D Sheet 2 of 2

4-Lead Very Thin Fine Pitch Land Grid Array (ASA) - 2.0x1.6 mm Body [VFLGA]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

RECOMMENDED LAND PATTERN

	Units	MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	E	1.55 BSC		
Contact Spacing	C		0.95	
Contact Width	X1			0.50
Contact Width (X3)	X2			0.40
Contact Pad Length (X4)	Y			0.70
Space Between Contacts	G1	1.05		
Space Between Contacts (X2)	G2	0.25		
Space Between Contacts	G3	1.15		
Contact 1 Index Chamfer	CH	0.13 X 45° REF		

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

    BSC: Basic Dimension. Theoretically exact value shown without tolerances.
2. The value in parenthesis, next to the item description is a unit multiplier.

Microchip Technology Drawing C04-3200 Rev D

DSA60XX

4-Lead Very Thin Fine Pitch Land Grid Array (ARA) - 1.6x1.2 mm Body [VFLGA]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

TOP VIEW

SIDE VIEW

BOTTOM VIEW

4-Lead Very Thin Fine Pitch Land Grid Array (ARA) - 1.6x1.2 mm Body [VFLGA]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at
http://www.microchip.com/packaging

	Units		MILLIMETERS	
Dimension Limits		MIN	NOM	MAX
Number of Terminals	N		4	
Terminal Pitch	e		1.20 BSC	
Terminal Pitch	e1		0.75 BSC	
Overall Height	A	0.79	0.84	0.89
Standoff	A1	0.00	0.02	0.05
Substrate Thickness (with Terminals)	A3		0.20 REF	
Overall Length	D		1.60 BSC	
Overall Width	E		1.20 BSC	
Terminal Width	b1	0.25	0.30	0.35
Terminal Width	b2	0.325	0.375	0.425
Terminal Length	L	0.30	0.35	0.40
Terminal 1 Index Chamfer	CH	-	0.125	-

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.
2. Package is saw singulated
3. Dimensioning and tolerancing per ASME Y14.5M
    BSC: Basic Dimension. Theoretically exact value shown without tolerances.
    REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-1199B Sheet 2 of 2

DSA60XX

4-Lead Very Thin Fine Pitch Land Grid Array (ARA) - 1.6x1.2 mm Body [VFLGA]

> **Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging

RECOMMENDED LAND PATTERN

	Units	MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	E1		1.20 BSC	
Contact Pitch	E2		1.16 BSC	
Contact Spacing	C		0.75	
Contact Width (X3)	X1			0.35
Contact Width	X2			0.43
Contact Pad Length (X4)	Y			0.50
Space Between Contacts	G1	0.85		
Space Between Contacts (X2)	G2	0.25		
Space Between Contacts	G3	0.77		
Contact 1 Index Chamfer	CH		0.13 X 45° REF	

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

   BSC: Basic Dimension. Theoretically exact value shown without tolerances.
2. The value in parenthesis, next to the item description is a unit multiplier.

Microchip Technology Drawing C04-3199B

APPENDIX A: REVISION HISTORY

Revision A (June 2019)

- Initial creation of DSA60xx Microchip data sheet DS20006221A.

Revision B (November 2022)

- Added the 7.0 mm x 5.0 mm VDFN, 5.0 mm x 3.2 mm VDFN and 3.2 mm x 2.5 mm VDFN package options throughout the document.
- Updated the previously existing package outline drawings to their most current versions.

NOTES:

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

PART NO.	X	X	X	X	X	X	-XXX.XXXX	X	XXX
Device	Pin 1 Definition	Output Drive Strength	Package	Temperature Range	Frequency Stability	Revision	Frequency	Media Type	Automotive Suffix

Device: DSA60:   Ultra-Small, Low Power MEMS Oscillator

Pin 1 Definition:

Selection	Pin 1	Internal Pull-Up Register
0	OE	Pull-up
1	$\overline{\text{STDBY}}$	Pull-up
2	FS	Pull-up
4	OE	None
5	$\overline{\text{STDBY}}$	None
6	FS	None

Output Drive Strength:

1	Standard
3	Low

Package:

A	=	4-Lead 7.0 mm x 5.0 mm VDFN
B	=	4-Lead 5.0 mm x 3.2 mm VDFN
C	=	4-Lead 3.2 mm x 2.5 mm VDFN
J	=	4-Lead 2.5 mm x 2.0 mm VLGA
M	=	4-Lead 2.0 mm x 1.6 mm VFLGA
H	=	4-Lead 1.6 mm x 1.2 mm VFLGA

Temperature Range:

A	=	–40°C to +125°C (Automotive Grade 1)
L	=	–40°C to +105°C (Automotive Grade 2)
I	=	–40°C to +85°C (Automotive Grade 3)

Frequency Stability:

1	=	± 50 ppm
2	=	± 25 ppm
3	=	± 20 ppm

Revision:

B	=	Revision B

Frequency:

xxx.xxxx =	User-Defined Frequency between 001.0000 MHz and 80.0000 MHz
xxxKxxx =	User-Defined Frequency between 002.000 kHz and 999.999 kHz
xxxx =	Frequency configuration code when pin 1 = FS. Configure the part online through ClockWorks® configurator.

Media Type:

\<blank\>	=	50/Tube, 100 pce. min. (A Package Option)
\<blank\>	=	72/Tube, 144 pce. min. (B Package Option)
\<blank\>	=	110/Tube (C Package Option)
\<blank\>	=	140/Tube (J Package Option)
\<blank\>	=	100/Bag (M & H Package Options)
T	=	1,000/Reel
B	=	3,000/Reel

Automotive Suffix: Vxx   =   The "xx" is assigned by Microchip.

Examples:

a) DSA6013JI3B-080.0000VAO:
Ultra-Small, Low Power MEMS Oscillator, Pin1 = $\overline{\text{STDBY}}$ with Internal Pull-Up, Low Drive Strength, 4-Lead 2.5 mm x 2.0 mm VLGA, Automotive Grade 3 Temperature, ±20 ppm Stability, Revision B, 80 MHz Frequency, 140/Tube

b) DSA6001HL1B-016.0000TVAO:
Ultra-Small, Low Power MEMS Oscillator, Pin1 = OE with Internal Pull–Up, Standard Drive Strength, 4-Lead 1.6 mm x 1.2 mm VFLGA, Automotive Grade 2 Temperature, ±50 ppm Stability, Revision B, 16 MHz Frequency, 1,000/Reel

c) DSA6021MA2B-0157VAO:
Ultra-Small, Low Power MEMS Oscillator, Pin1 = Freq. Select with Internal Pull-Up, Standard Drive Strength, 4-Lead 2.0 mm x 1.6 mm VFLGA, Automotive Grade 1 Temperature, ±25 ppm Stability, Revision B, Two Frequencies Configured through ClockWorks, 100/Bag

Note 1: Tape and Reel identifier only appears in the catalog part number description. This identifier is used for ordering purposes and is not printed on the device package. Check with your Microchip Sales Office for package availability with the Tape and Reel option.

Note 1: Please visit Microchip ClockWorks® Configurator Website to configure the part number for customized frequency. http://clockworks.microchip.com/timing/.

NOTES:

Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.

- Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.

- Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.

- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that we are guaranteeing the product is "unbreakable" Code protection is constantly evolving. Microchip is committed to continuously improving the code protection features of our products.

Worldwide Sales and Service

AMERICAS

Corporate Office
2355 West Chandler Blvd.
Chandler, AZ 85224-6199
Tel: 480-792-7200
Fax: 480-792-7277
Technical Support:
http://www.microchip.com/
support
Web Address:
www.microchip.com

Atlanta
Duluth, GA
Tel: 678-957-9614
Fax: 678-957-1455

Austin, TX
Tel: 512-257-3370

Boston
Westborough, MA
Tel: 774-760-0087
Fax: 774-760-0088

Chicago
Itasca, IL
Tel: 630-285-0071
Fax: 630-285-0075

Dallas
Addison, TX
Tel: 972-818-7423
Fax: 972-818-2924

Detroit
Novi, MI
Tel: 248-848-4000

Houston, TX
Tel: 281-894-5983

Indianapolis
Noblesville, IN
Tel: 317-773-8323
Fax: 317-773-5453
Tel: 317-536-2380

Los Angeles
Mission Viejo, CA
Tel: 949-462-9523
Fax: 949-462-9608
Tel: 951-273-7800

Raleigh, NC
Tel: 919-844-7510

New York, NY
Tel: 631-435-6000

San Jose, CA
Tel: 408-735-9110
Tel: 408-436-4270

Canada - Toronto
Tel: 905-695-1980
Fax: 905-695-2078

ASIA/PACIFIC

Australia - Sydney
Tel: 61-2-9868-6733

China - Beijing
Tel: 86-10-8569-7000

China - Chengdu
Tel: 86-28-8665-5511

China - Chongqing
Tel: 86-23-8980-9588

China - Dongguan
Tel: 86-769-8702-9880

China - Guangzhou
Tel: 86-20-8755-8029

China - Hangzhou
Tel: 86-571-8792-8115

China - Hong Kong SAR
Tel: 852-2943-5100

China - Nanjing
Tel: 86-25-8473-2460

China - Qingdao
Tel: 86-532-8502-7355

China - Shanghai
Tel: 86-21-3326-8000

China - Shenyang
Tel: 86-24-2334-2829

China - Shenzhen
Tel: 86-755-8864-2200

China - Suzhou
Tel: 86-186-6233-1526

China - Wuhan
Tel: 86-27-5980-5300

China - Xian
Tel: 86-29-8833-7252

China - Xiamen
Tel: 86-592-2388138

China - Zhuhai
Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore
Tel: 91-80-3090-4444

India - New Delhi
Tel: 91-11-4160-8631

India - Pune
Tel: 91-20-4121-0141

Japan - Osaka
Tel: 81-6-6152-7160

Japan - Tokyo
Tel: 81-3-6880- 3770

Korea - Daegu
Tel: 82-53-744-4301

Korea - Seoul
Tel: 82-2-554-7200

Malaysia - Kuala Lumpur
Tel: 60-3-7651-7906

Malaysia - Penang
Tel: 60-4-227-8870

Philippines - Manila
Tel: 63-2-634-9065

Singapore
Tel: 65-6334-8870

Taiwan - Hsin Chu
Tel: 886-3-577-8366

Taiwan - Kaohsiung
Tel: 886-7-213-7830

Taiwan - Taipei
Tel: 886-2-2508-8600

Thailand - Bangkok
Tel: 66-2-694-1351

Vietnam - Ho Chi Minh
Tel: 84-28-5448-2100

EUROPE

Austria - Wels
Tel: 43-7242-2244-39
Fax: 43-7242-2244-393

Denmark - Copenhagen
Tel: 45-4485-5910
Fax: 45-4485-2829

Finland - Espoo
Tel: 358-9-4520-820

France - Paris
Tel: 33-1-69-53-63-20
Fax: 33-1-69-30-90-79

Germany - Garching
Tel: 49-8931-9700

Germany - Haan
Tel: 49-2129-3766400

Germany - Heilbronn
Tel: 49-7131-72400

Germany - Karlsruhe
Tel: 49-721-625370

Germany - Munich
Tel: 49-89-627-144-0
Fax: 49-89-627-144-44

Germany - Rosenheim
Tel: 49-8031-354-560

Israel - Ra'anana
Tel: 972-9-744-7705

Italy - Milan
Tel: 39-0331-742611
Fax: 39-0331-466781

Italy - Padova
Tel: 39-049-7625286

Netherlands - Drunen
Tel: 31-416-690399
Fax: 31-416-690340

Norway - Trondheim
Tel: 47-7288-4388

Poland - Warsaw
Tel: 48-22-3325737

Romania - Bucharest
Tel: 40-21-407-87-50

Spain - Madrid
Tel: 34-91-708-08-90
Fax: 34-91-708-08-91

Sweden - Gothenberg
Tel: 46-31-704-60-40

Sweden - Stockholm
Tel: 46-8-5090-4654

UK - Wokingham
Tel: 44-118-921-5800
Fax: 44-118-921-5820

09/14/21