

# BUS BASED TECHNOLOGY

## BUS BASED TECHNOLOGY

The Circuit Board Division of VERO Electronics offers products to support all internationally defined bus structures including Futurebus+, VMEbus, VME64, VME 64 Extensions, VXibus, Compact PCI, Multibus and Multibus II, STEbus, G-64 bus and G-96 bus. The backplane range is made available in standard, modified standard and fully customised forms.

In addition to the backplanes supporting these bus structures a wide range of extender boards, terminator modules and other accessories are available together with an extensive range of Microrack development systems.

Customised versions of the Microracks offer an easy solution to implementation of specialised development systems. Please contact VERO Electronics for further details.



Bus Based Technology 9



## CE MARKING

CE Marking according to the EMC directive 89/336/EEC became effective as of 1st January 1996.

According to the directive, items included in this section are considered sub-assemblies, and as such are not CE marked. It remains the responsibility of the integrator to ensure compliance at the point of taking into service and to mark and declare as such.

VERO Electronics Circuit Board Division have invested heavily in pre-compliance test facilities and have undertaken extensive representative measurements and participated in working groups and will continue to assist in achieving full compliance.

From 1st January 1997 certain products will be covered by the Low Voltage Directive 73/23/EEC. In these instances, the product will be CE marked and a declaration of conformity can be supplied on request.

For CE Marking of specific products, please contact VERO Electronics Technical Enquiries on the number listed at the foot of the page.

## MANUFACTURING STANDARDS

All VERO Electronics backplanes are manufactured in accordance with quality assurance levels to BS9000, CECC 23000 and IECQ PCQ88, with systems approval in accordance with BS EN ISO9001.



### Certificate Number



Hedge End  
FM 14253

BS EN ISO 9001  
BS 9761 BS 9762 BS 9763  
CECC 23 300 CECC 23 300-004 CECC 23 100  
Underwriters Laboratories

## NEW PRODUCTS

▲ In line with its stated policy of constant product development VERO Electronics regularly introduces new or enhanced products.

New to this edition of the Product Handbook are a full range of VME<sup>2</sup> VME64 Extensions backplanes, a 2U, 3 Slot VMEbus Microrack and CompactPCI Backplanes.



**VMEbus ..... 9.03-9.19**  
 VME<sub>EXCEL</sub> J1 & J2 3U and 6U Monolithic backplanes ..... 9.03-9.08  
 High Performance VME<sub>ELITE</sub> Monolithic backplanes ..... 9.09-9.10  
 VME<sup>2</sup> - VME64 Extensions backplanes .. 9.11-9.12  
 High Performance VMEbus J1 backplanes .... 9.13  
 VMEbus Live Insertion Module ..... 9.14  
 VMEbus Extender boards ..... 9.15  
 BGRANT/IACK jumper board ..... 9.15  
 120mm Adaptor ..... 9.15  
 60mm Adaptor ..... 9.15  
 VME Subsystem - VSB ..... 9.15  
 VMEbus Powerfail module ..... 9.15  
 VMEbus Modular Microrack System ..... 9.16-9.18  
 VMEbus 3 slot Microracks ..... 9.19

**VXIbus ..... 9.20-9.23**  
 VXIbus backplanes ..... 9.20  
 VXIbus Microracks ..... 9.21-9.22  
 VXIbus prototyping boards ..... 9.23  
 VXIbus Extender board ..... 9.23  
 VXIbus Light and normal duty modules ..... 9.23

**CompactPCI ..... 9.24**  
 CompactPCI backplanes ..... 9.24


**FUTUREBUS+ ..... 9.25-9.27**  
 Multi-profile Futurebus + Backplanes ..... 9.25  
 Futurebus+ 4 Slot Microracks - Entry level .... 9.26  
 Futurebus+ 4 Slot Microrack - Advanced ..... 9.26  
 Futurebus+ 14 Slot Microrack - Entry level .... 9.27  
 Futurebus+ 14 Slot Microrack - Advanced ..... 9.27

**MULTIBUS ..... 9.28**  
 Multibus iPSB / iLBX backplanes ..... 9.28

**MULTIBUS II ..... 9.29-9.30**  
 Multibus II iPSB backplanes ..... 9.29  
 Multibus II iLBX backplanes ..... 9.30  
 Multibus II Extender board ..... 9.30

**STEBus ..... 9.31**  
 STEbus backplanes ..... 9.31  
 STEbus terminator ..... 9.31  
 STEbus extender board ..... 9.31

**G-64/G-96 ..... 9.32**  
 G-64bus backplanes ..... 9.32  
 G-96bus backplanes ..... 9.32



# VMEXCEL BACKPLANES

## VMEXCEL BACKPLANES

### INTRODUCTION

The VMEXCEL family of backplanes introduces a new concept of customer configured backplanes.

Just In Time (JIT) manufacturing techniques have been employed to improve production efficiency and quickly introduce a versatile product to the marketplace.


The ability to configure the backplane permits the user to tailor the product to suit his exact requirements and budget.

Value engineering, combined with the improved production methods, has resulted in a range of backplanes which are competitively positioned, but still enjoy the quality and performance advantages associated with backplane technology from VERO Electronics.

VMEXCEL offers excellent performance characteristics in the key areas of controlled impedance, power distribution and termination design.




### FEATURES

- Conforms to VME64 specification (ANSI/VITA1-1994)
- 6 Layer stripline construction - J1 and Monolithic
- 4 Layer stripline construction - J2
- 57  $\Omega$  characteristic impedance control
- Patented earth guard track design
- Excellent crosstalk performance
- Low ground shift
- Termination design features short stubs, decoupling capacitors and anti-crosstalk layout
- Auto Bus Grant (ABG) Connectors as an option
- Latchable services connector (Flying lead and mating connector supplied)
- Four power connector options -
  - Power Bug / Faston connectors
  - Busbars
  - Mate 'N' Lok
  - Faston
- Two power connection position options - Monolithic
- A decoupling capacitor position is provided for each slot position permitting fine tuning of the backplane to match system parameters
- Long tails and shrouds on slot 1 and "n" on J1 area of backplane
- Long tails and shrouds on all J2 slot positions
- Long tailed connectors are gold plated
- Mate 'N' Lok connectors supplied (including mating connector)
- On and Off-board termination
- Passive and active termination options
- Screw fixing option on J2 connectors for use with VSB backplanes
- VME 64 compatible - Monolithic



- 1 VMEXCEL J1 backplane
- 2 VMEXCEL J2 Backplane
- 3 VMEXCEL Monolithic Backplane

VMEXCEL is a trade mark of VERO Electronics Limited  
Mate 'N' Lok is a trademark of AMP




## GUARD TRACKING

All VMEbus backplanes manufactured by VERO Electronics adopt the company's patented guard tracking layout. This layout guarantees the backplane a superior level of crosstalk (noise) performance.

The use of guard tracking, in addition to improving crosstalk performance, aids the reduction of layer count.

With the signal lines being shielded by power layers in one plane and by individual 0V guard tracks in the other, VERO's patented guard tracking gives a pseudo-coaxial style of protection.



VMEbus Guard Tracking


## LATCHABLE SERVICES CONNECTOR

All VME<sub>EXCEL</sub> backplanes are supplied as standard with a latchable services header.

The 5 way header is located on the rear (wiring side) top corner of the backplane, above the space between connectors 1 and 2.

The mating half of the connector, with 1 metre of cable attached to each of the five lines, is also included.

The lines, and the relevant colour codings, are arranged as follows; GND - black, +5V - red, ACFL - blue, SYSFL - grey and SYSRES - orange.



Latchable Services Header

## TERMINATION


It is recommended that VMEbus backplanes be terminated at both ends, which is why VERO Electronics always provide backplanes which include two sets of terminators (except the 2 and 3 slot versions, which require only one).

VERO can supply termination in passive on- or off-board or active off-board formats.

All VMEbus termination modules from VERO are universal, thus they can be fitted to either end of the backplane without fouling the subrack on which the board is mounted.


## ON-BOARD TERMINATION

**On-board passive** is the most popular - and cost effective - method of terminating because the resistors are fitted directly onto the backplane adjacent to the first and last slots. There is no loss of usable slots with VERO's on-board, inboard termination layout which is used as standard on all VME<sub>EXCEL</sub> backplanes.



## OFF-BOARD TERMINATION

**Off-board passive** is popular where a quick "Mean Time to Repair" is required. This is because the termination is on separate modules which can easily be plugged in and out of the rear of a backplane.



**Off-board active** modules are supplied as standard. Contact VERO Electronics for details of on-board active termination, which can be supplied as a special option. Active termination offers a lower power method of termination due to its use of Op-Amp in conjunction with resistors, rather than simply employing the resistors used in passive termination.

Depending on the level of activity on the bus, the

actual savings afforded by active termination over passive termination can be as high as 5 Watts.

The main applications for active termination are portable battery operated systems or very small, low power systems.

Although termination is included as standard with all VMEbus backplanes supplied by VERO, additional terminator modules may be ordered separately.

## JUMPER LINKS

Each backplane is supplied with 10 red jumper links for implementing "bus grant" and "IACK" when a daughter board is removed from a working system. These jumper links are fitted to the backplane during assembly and for correct operation they will need to be removed from the board. They should only be replaced when the user requires a slot to be left vacant between occupied slots during operation.



Jumper Links

TERMINATION Ordering information

Description	Qty.	Order code
Universal passive J1 terminator	2	243-52821K
Universal passive J2 terminator	2	188-52865D
Universal active J1 terminator	1	243-310274L
Universal active J2 terminator	1	243-310276G
Retainer/ejector kit	4	188-53119H
Jumper links / red	10	188-39180G

## CONNECTOR TYPES

**STANDARD (STD)** - These are high quality DIN 41612 class 2 96/96 way connectors

**AUTO BUS GRANT CONNECTOR (ABG)** - The use of Auto Bus Grant Connectors (also known in some markets as Auto Daisy Chain Connectors) in the new VME<sub>EXCEL</sub> range negates the need to provide jumper links for empty slots or partially configured systems. Connectors have high reliability and are DIN 41612 conformant (Class 2).

In addition to the Standard and Auto Bus Grant connectors other connector types are available by special request, subject to a minimum order quantity.

## SCREW FIXINGS FOR VSB


For VME<sub>EXCEL</sub>, the normal method of attaching the rear shrouds to the backplane is by riveting. If it is intended to use positive retention to hold connectors or boards which are plugged into the rear of the backplane, then screw fixings should be requested. These alternative fixings allow the easy deletion or addition of fittings in selected slots.

# VMEXCEL BACKPLANES

## POWER-ON OPTIONS


The VMEXCEL backplane range employs a variety of methods in which the power may be introduced to the backplane.

**MATE 'N' LOK** - A polarised, latchable connector with each contact rated at 10 Amps. Mating connectors are supplied with the backplanes.



Mate 'N' Lok Connectors

**BUSBAR** - A combination of up to 6 power bugs (without faston tabs) connected together via a 2mm thick x 10mm wide tin lead plated copper bar. This is a convenient form of power connection, particularly when used on larger backplanes. The busbar method improves power distribution and simplifies wiring. The maximum power rating of the busbar is up to 125A on a 21 slot backplane.



Busbar


**POWER BRACKET** - The Power Bracket is offered as an accessory in order to allow an alternative connection of power to the busbar via a hole drilled to take M6 cable clamps. It is supplied as a pair complete with busbar mounting screws.

Power Bracket	243-310367D
---------------	-------------



Power Bracket

**FASTON** - A simple 6,35mm faston spade connector, rated at 12 Amps.



Faston 6,35mm Spade Connector

**POWER BUG/FASTON** - A combination connector system giving an M4 screw terminal with two 6,35mm faston tabs. The combined power bug/faston is rated at 18 Amps per connector.



Power Bug / Faston Connectors

**POWER POSITION OPTIONS** - The VMEXCEL Monolithic has two positions in which the power may be introduced to the backplane.



Power Position Options (central position illustrated)

**POWER STRAP** - The VMEXCEL range features, as a method of forming a continuous circuit between J1 and J2 backplanes only, an optional power connecting strap. The strap, which attaches to the power rails of the backplanes is tin-lead plated. This feature must be specified when ordering the backplane.



Power Strap

The connection for power, which is made by Mate 'N' Lok, Faston, Power Bug or busbar, is located either in the J1 area of the backplane or centrally between the J1 and the J2 areas.

By utilising the established VMEXCEL build criteria and offering this power-on position flexibility, VERO is able to tailor the backplane to exact requirements.

**MECHANICAL SPECIFICATIONS**

The VMEXCEL backplane range - J1, J2 and Monolithic - employs the following mechanical specifications

**BACKPLANE HEIGHT**

J1 and J2 3U (128,5 mm / 5,06")  
 Monolithic 6U (262 mm / 10,31")

**BACKPLANE WIDTH**

The width of all VMEXCEL backplanes can be calculated using the following formula;

$$\text{Board width} = 0.752" + [(N-1) \times 0.8] \text{ inches} \quad (\times 25.4 = \text{mm})$$

Where N = number of slots  
 0,752" is the sum of the overhang at either end of the backplane

**CONNECTOR PITCH**

All connectors mounted on VMEbus backplanes use a 4HP (20,32mm / 0,8") pitch

**BOARD THICKNESS**

All VMEXCEL backplanes are 2,7mm (0,11") thick multilayer constructions.

**MOUNTING POSITIONS**

VMEXCEL J1 and J2 backplanes have two rows of mounting holes, monolithic backplanes have three rows.

Each row of backplane mounting holes is aligned with the connector mounting holes. The connector mounting holes are 0,3mm (0,012") to the left of centre of row b pins when viewed from the front (connector side) of the backplane. Each backplane is supplied with enough screws (M2,5 x 6mm long cheese head) to secure it to the tie bars of a subrack.


Backplane spacer strips are also required and must be ordered separately. Please refer to Subracks; section 4, page 4.31 for spacer details.

**BACKPLANE ASSEMBLY DEPTH**


The overall depth of the J1 VMEXCEL off board terminated backplane assembly, X, covers the distance from the front face of the subrack tie bar spacer to the rear of the terminator module's pcb.

Off board terminated assembly depth, X = 22,5mm.


VMEXCEL J2 terminator modules are fitted with a DIN 41612 reverse connector shell which increases the overall depth of the backplane assembly by 13mm.



Backplane Width



Backplane Mounting Positions



Depth of Backplane Assembly - J1 off board termination illustrated

# VMEXCEL BACKPLANES - 3U J1 and J2

To configure your VMEXCEL backplane, use the chart below to select the features and options you require:

Ordering Information

243

-

4

X

X

X

XX

VMEXCEL J1 = 1  
VMEXCEL J2 = 2

- α Off Board Termination / STD Connector = 0
- On Board Termination / STD Connector = 1
- α Off Board Termination / ABG Connector = 2
- On Board Termination / ABG Connector = 3
- α Off Board Termination (Active) / STD Connector = 4
- α Off Board Termination (Active) / ABG Connector = 5
- β On Board Termination (Screw fixing for VSB) / STD Connector = 6
- α β Off Board Termination (Screw fixing for VSB) / STD Connector = 7
- α β Off Board Termination (Active, screw fixing for VSB) / STD Connector = 8

- τ Mate 'N' Lok = 0
- δ Power Bug/Faston = 1
- δ Busbar = 2
- ω Faston = 3
- τ Mate 'N' Lok - with Power Strap = 4
- δ Power Bug/Faston - with Power Strap = 5
- δ Busbar - with Power Strap = 6
- ω Faston - with Power Strap = 7

### Notes

- α Includes terminator modules
- β J2 only
- δ 8 slot and above only
- ω 7 slot and below only
- τ 4 slot and above only


Preferred slot sizes

02	10
03	12
04	14
05	16
06	20
07	21
09	


Example: 243-412121 is a VMEXCEL J1 backplane with off board termination, Auto BusGrant connectors, Power Bug/Faston power connection, 21 slots wide

**For any other configuration or slot size, please contact VERO Electronics Sales Office.**

VMEXCEL J1 Backplanes



VMEXCEL J2 Backplanes




### J1 AND J2 3U POWER RATINGS (21 SLOT BACKPLANE)

Voltage	Max. per slot		Total power	
	J1	J2	J1	J2
5V	4,5A	4,5A	125A	125A
+12V	1.5A	n/a	24A	n/a
-12V	1.5A	n/a	24A	n/a
5VSTBY	1.5A	n/a	24A	n/a


The above figures are provided as an indication of the maximum power handling capabilities of VMEXCEL. The maximum per slot figures are taken from the VMEbus specification using a figure of 1,5A per pin for the DIN connectors.

The maximum figures are obtained from a 21 slot backplane with busbar power connection.

Section through VMEXCEL J1 backplanes



Section through VMEXCEL J2 backplanes



# VMEXCEL BACKPLANES - 6U MONOLITHIC

To configure your VMEXCEL Monolithic backplane, use the chart below to select the features and options you require:

Ordering Information

**243**      -      **4**      **3**      **X**      **X**      **XX**

J1/J2 Monolithic

- α Off Board Termination / STD Connector = 0
- On Board Termination / STD Connector = 1
- α Off Board Termination / ABG Connector = 2
- On Board Termination / ABG Connector = 3
- α Off Board Termination (Active) / STD Connector = 4
- α Off Board Termination (Active) / ABG Connector = 5
- On Board Termination (Screw fixing for VSB) / STD Connector = 6
- α Off Board Termination (Screw fixing for VSB) / STD Connector = 7
- α Off Board Termination (Active, screw fixing for VSB) / STD Connector = 8

**Notes**

- α Includes terminator modules
- τ 4 slot and above only
- δ 8 slot and above only
- ω 7 slot and below only
- Σ Option 1 locates the power connectors in the J1 position on the board
- Σ Option 2 locates the power connectors centrally.

- Σ Option 1 (J1)
  - τ Mate 'N' Lok = 0
  - δ Power Bug/Faston = 1
  - δ Busbar = 2
  - ω Faston = 3
- Σ Option 2 (Centre)
  - τ Mate 'N' Lok = 4
  - δ Power Bug/Faston = 5
  - δ Busbar = 6
  - ω Faston = 7

Preferred Slot Sizes


01	12
03	14
05	16
07	20
09	21
10	

Example: **243-436614** is a VMEXCEL Monolithic backplane with on-board termination, screw fixings for VSB, standard connectors, busbar power connection in the centre position, 14 slots wide.

**For any other configuration or slot size, please contact VERO Electronics Sales Office.**

Bus Based Technology 9

VMEXCEL Monolithic Backplanes



**MONOLITHIC 6U POWER RATINGS (21 SLOT BACKPLANE)**

Voltage	Max. per slot	Total
5V	9A	125A
+12V	1.5A	24A
-12V	1.5A	24A
5VSTBY	1.5A	24A

The above figures are provided as an indication of the maximum power handling capabilities of VMEXCEL. The maximum per slot figures are taken from the VMEbus specification using a figure of 1,5A per pin for the DIN connectors.

The maximum figures are obtained from a 21 slot backplane with busbar power connection.

It is possible to modify standard product to provide in excess of 200A on the +5V line if required. Please contact VERO Electronics.

**MATERIAL SPECIFICATIONS - VMEXCEL RANGE**

**Board**  
Epoxyglass fibre to BS 4584 EP-GC-CU-3 (FR4)  
Material thickness 2.7mm nominal

Bare boards are UL 94V-0 rated.  
File number E. 116551

**Connectors - Standard DIN 41612 and Auto Bus Grant (ABG)**

IEC 603-2 (DIN 41612) 96 way  
Body material: glass filled polyester  
UL 94V-0 rated


Insertion force (mating)/pair: ≥90N  
Withdrawal force (unmating)/pair: ≥90N  
Min. pin to board retention force: 30N per contact

**Environmental**

Temperature range - storage: - 40°C to + 120°C  
Temperature range - working: - 20°C to + 85°C  
Altitude: 3000 m  
Humidity: 90% R.H. non-condensing  
Shock and vibration resistant: commercial  
MTBF to MIL -HBK-217E: >225000 hours  
Conditions: Ground benign  
Temperature 25°C  
Insertion frequency: 0.5 to 5 per 1000 hours

**QUALITY ASSURANCE**

VMEXCEL backplanes are manufactured in accordance with quality assurance levels to BS9000, CECC 23000 and IECQ PCQ88.  
Systems approval in accordance with BS EN ISO 9001, ISO 9002 and EN 29002.



# HIGH PERFORMANCE VME<sub>ELITE</sub> BACKPLANES

## VME<sub>ELITE</sub> MONOLITHIC BACKPLANE

The VME<sub>ELITE</sub> high performance backplane range reaches new levels of performance for standard VMEbus backplanes.

Designed to cope with the ever increasing demands of high performance VME systems, VME<sub>ELITE</sub> backplanes should be used where very low noise, tightly controlled impedance or high power are important system requirements - VME64 being a typical application area.

Surface mount termination and VERO's unique additional ground track patterns through connector pins enables very low crosstalk figures to be achieved.

### FEATURES

- VME64 compatible
- Conforms to VME64 specification (ANSI/VITA1-1994)
- High performance 80 M byte/sec systems capability.
- 10 layer strip line construction.
- 50 Ω controlled characteristic impedance.
- Excellent crosstalk performance.
- Patented earth guard tracking techniques with additional guard tracks through connector pin patterns
- Mechanically in-board, electrically out-board surface mount termination with Schottky clamp
- Surface mount termination to reduce inductive lead length and reduce crosstalk
- Autobahn termination positions available optionally
- Three power connection options:
  - Mate 'N' Lok connector
  - Powerbug with dual faston
  - Busbars
- New low-profile high performance busbars with M6 studs
- Extra power connectors available optionally for very high power applications
- Decoupling capacitors fitted for each slot on J1 and positions provided on J2
- Voltage smoothing capacitor positions are provided for each J1 slot position
- Two options for retained and latching header for system functions and remote power sensing.
- Gold plated rear plug-up connectors and shrouds fitted to all J2 and slots 1 & "n" J1 positions.
- Excellent ground shift performance.
- Auto bus grant connectors optional.

### MATERIAL SPECIFICATIONS

#### Board

Dielectric epoxy glass to BS 4584  
EP-GC-CU-3 (FR4)

Nominal thickness : 4,5 mm  
Base copper thickness : 35 µm  
Finish: Plated copper - 40 µm average  
Tin lead - 5 µm approximately

Bare boards are UL 94V-0 rated components, File number E. 116551


#### Connectors - Standard DIN 41612 and Auto Bus Grant (ABG)

IEC 603-2 (DIN 41612) 96 way  
Body material: glass filled polyester  
UL 94V-0 rated

Insertion force (mating)/pair: ≥90N  
Withdrawal force (unmating)/pair: ≥90N  
Min. pin to board retention force: 30N per contact

#### Environmental

Temperature range - storage -40°C to +120°C  
Temperature range - working -20°C to +85°C  
Altitude: 3000 m  
Humidity: 90% R.H. non-condensing  
Shock and vibration resistant: commercial  
MTBF to MIL -HBK-217E: >225000 hours  
Conditions: Ground benign  
Temperature 25°C  
Insertion frequency: 0.5 to 5 per 1000 hours



## CROSSTALK PERFORMANCE

VERO's VME<sub>ELITE</sub> design incorporates a completely new latticed guard track layout that further enhances the backplanes' crosstalk performance.

The design of VME<sub>ELITE</sub> has increased the space in the connector area of the tracking interconnect so that guard tracks are now continuous down the entire length of the backplane. Previously, the guard track stopped short on either side of a slot position.

The new layout ensures that not only is each signal trace completely guard tracked, creating a quasi-coaxial transmission line, but each signal pin on the connectors is surround by an annular earth ring.

VME<sub>ELITE</sub> incorporates an advanced surface mount termination layout. Using SMD components improves crosstalk performance by reducing lead lengths and stub lengths, which in turn reduces inductive coupling between the termination elements.



The features described above have contributed to making VME<sub>ELITE</sub> the highest performing standard VMEbus backplane ever offered by VERO Electronics.

## CROSSTALK PERFORMANCE OF FOUR GENERATIONS OF VMEbus BACKPLANE

Standard VME Backplane	% of 5 layer crosstalk	Decibel
5 layer (1981)	Reference	0dB
VME <sub>EXCEL</sub> (1992)	90%	-0,9dB
High Performance VME Backplane	% of 5 layer crosstalk	Decibel
VME 64 (1989)	83%	-1,6dB
VME <sub>ELITE</sub> (1994)	31%	-10,2dB

## LATCHABLE SERVICES HEADER

All VME<sub>ELITE</sub> backplanes are supplied as standard with two services headers: a 5 way header with mating half and flying leads to allow simple upgrade from VME<sub>EXCEL</sub> monolithics to VME<sub>ELITE</sub>, and a 10 way header to provide backward compatibility with VERO's VME 64 backplane range.



# HIGH PERFORMANCE VME<sub>ELITE</sub> BACKPLANES

## VME<sub>ELITE</sub> HIGH PERFORMANCE BACKPLANES WITH STANDARD CONNECTORS

### Ordering information

Preferred Slot width	Order code		
	Mate "n" lok	Power bug/spade	Busbar
5	243-451005B	243-451105J	243-451205E
7	243-451007J	243-451107E	243-451207A
9	243-451009E	243-451109A	243-451209H
10	243-451010J	243-451110E	243-451210A
12	243-451012E	243-451112A	243-451212H
14	243-451014A	243-451114H	243-451214D
16	243-451016H	243-451116D	243-451216L
20	243-451020F	243-451120B	243-451220J
21	243-451021D	243-451121L	243-451221G

## VME<sub>ELITE</sub> HIGH PERFORMANCE BACKPLANES WITH ABG CONNECTORS

### Ordering information

Preferred Slot width	Order code		
	Mate "n" lok	Power bug/spade	Busbar
5	243-453005C	243-452105D	243-453205F
7	243-453007K	243-453107F	243-453207B
9	243-453009F	243-453109B	243-453209J
10	243-453010K	243-453110F	243-453210B
12	243-453012F	243-453112B	243-453212J
14	243-453014B	243-453114J	243-453214E
16	243-453016J	243-453116E	243-453216A
20	243-453020G	243-453120C	243-453220K
21	243-453021E	243-453121A	243-453221H

For any other configuration or slot size please contact VERO Electronics Sales Office.

## MECHANICAL SPECIFICATIONS

The VME<sub>ELITE</sub> backplane range employs the following mechanical specifications

### BACKPLANE HEIGHT

Monolithic 6U = 262 mm (10,31")

### BACKPLANE WIDTH

The width of all VME<sub>ELITE</sub> backplanes can be calculated using the following formula;

$$\text{Board width} = 0,665" + ((N-1) \times 0,8) \text{ inches} \\ (\times 25,4 = \text{mm})$$

Where N = number of slots

0,665" is the sum of the overhang at either end of the backplane

### CONNECTOR PITCH

All connectors mounted on VMEbus backplanes use a 4HP (20,32mm / 0,8") pitch

### BOARD THICKNESS

All VME<sub>ELITE</sub> backplanes are 4,5mm (0,177") thick multilayer constructions.

### MOUNTING POSITIONS

VME<sub>ELITE</sub> backplanes have three rows of mounting holes.

Each row of backplane mounting holes is aligned with the connector mounting holes. The connector mounting holes are 0,3mm (0,012") to the left of centre of row b pins when viewed from the front (connector side) of the backplane. Each backplane is supplied with enough screws (M2,5 x 6mm long cheese head) to secure it to the tie bars of a subrack.

Backplane spacer strips are also required and must be ordered separately. Please refer to Subracks; section 4, page 4.31 for spacer details.


### BACKPLANE ASSEMBLY DEPTH

The overall depth of the VME<sub>ELITE</sub> backplane assembly, X, covers the distance from the front face of the subrack tie bar to the rear of the rear connector shroud, where X = 18mm.


### QUALITY ASSURANCE

VME<sub>ELITE</sub> backplanes are manufactured in accordance with quality assurance levels to BS9000, CECC 23000 and IECQ PCQ88, with systems approval in accordance with BS EN ISO 9001, ISO 9002 and EN 29002.


VME<sub>ELITE</sub> is a trade mark of VERO Electronics Limited  
Mate 'N' Lok is a trademark of AMP



Backplane Width



Backplane Mounting Positions



Backplane Assembly Depth

# VME<sup>2</sup> BACKPLANE FOR VME 64 x

## VME<sup>2</sup> - VME64 EXTENSIONS BACKPLANE

VERO's new VME<sup>2</sup> backplane represents the cutting edge of VMEbus board technology.

VERO Electronics Circuit Board Division has confirmed its long tradition of early support for new open architecture busses by manufacturing VME<sup>2</sup>, the World's first VME64x backplane, as part of its contribution to the development of the VME64x specifications. VERO's involvement with the VITA Standards Organisation (VSO), ensures both its contribution to the design process and its awareness of the evolution of the draft specifications.

The VME64 Standard, VITA1-1994, defines a set of features that can be added to VME and VME64 boards. The major new features which affect the backplane design are as follows:

The introduction of a 160 pin DIN connector with row "z" and "d" pin rows in both the P1/J1 and P2/J2 areas. These new connectors are backward compatible so that a 96 pin DIN connector can mate with the 160 pin VME64x connector.

An optional P0/J0 connector can be used between the P1/J1 and P2/J2 to provide an extra 95 user definable pins on a 2mm hard metric connector.

Improved supply voltages of +3,3V and 48V plus more +5V power.

Thirty-five more ground returns between VME64x boards and VME64x backplanes, providing - in total - 47 ground returns.

User defined I/O pins on the P2/J2 increased by 46.

Ten spare bussed pins and 2 unbussed on the P1/J1 for future use.

An optional test and maintenance bus interface to give improved manufacturability, testability, maintenance and diagnostics of VME64x boards.


Geographical address pins GA0 - GA4 and GAP shall be tied to ground or left open on the J1 connector on the backplane to give slot geographic addressing.

Development work is in progress on a supporting specification for live insertion and incident wave switching via the (optional) use of ETL devices.

### FEATURES

- 12 layer stripline construction
- Tightly controlled impedance
- Surface mount passive termination with Schottky clamp
- Electronic on-board Auto Bus Grant
- Power connections via busbars and power studs
- Decoupling capacitors fitted
- All long tails gold plated
- Cast +3,3V busbar and stiffener available optionally

**NOTE:** Due to the width of the 160 pin connector and the increased number of lines requiring termination, it is necessary to "grow" the backplane slightly. As a result of this growth one slot position before slot 1 is lost (to the left of the backplane when viewed from the connector side).



VME<sup>2</sup> VME64x BACKPLANES (WITHOUT P0/J0 CONNECTOR)

Ordering information

Preferred Slot width	Order code	
	Busbars 0V, +5V plus +3,3V busbars/stiffeners	Busbars 0V, +5V
7	243-479607K	243-479207D
10	243-479610K	243-479210D
14	243-479614B	243-479214G
17	243-479617G	243-479217A
20	243-479620G	243-479220A

VME<sup>2</sup> VME64x BACKPLANES (WITH P0/J0 CONNECTOR)

Ordering information

Preferred Slot width	Order code	
	Busbars 0V, +5V plus +3,3V busbars/stiffeners	Busbars 0V, +5V
7	243-470607L	243-470207E
10	243-470610L	243-470210E
14	243-470614C	243-470214H
17	243-470617H	243-470217B
20	243-470620H	243-470220B

For any other configuration or slot size please contact VERO Electronics Sales Office.

### MATERIAL SPECIFICATIONS

**Board**  
 Dielectric epoxy glass to BS 4584 EP-GC-CU-3 (FR4)  
 Nominal thickness : 4,5 mm  
 Base copper thickness : 35 µm  
 Finish: Plated copper - 40 µm average  
           Tin lead - 5 µm approximately  
 Bare boards are UL 94V-0 rated components, File number E. 116551

### Environmental

Temperature range - storage - 40°C to + 120°C  
 Temperature range - working - 20°C to + 85°C  
 Altitude: 3000 m  
 Humidity: 90% R.H. non-condensing  
 Shock and vibration resistant: commercial  
 MTBF to MIL -HBK-217E: >225000 hours  
 Conditions: Ground benign  
                   Temperature 25°C  
 Insertion frequency: 0.5 to 5 per 1000 hours

## MECHANICAL SPECIFICATIONS

The VME<sup>2</sup> backplane range employs the following mechanical specifications

### BACKPLANE HEIGHT

Monolithic 6U = 262 mm (10,31")

### BACKPLANE WIDTH

The width of all VME<sup>2</sup> backplanes can be calculated using the following formula;

$$\text{Board width} = 1,550" + ((N-1) \times 0,8) \text{ inches} \\ (\times 25,4 = \text{mm})$$

Where N = number of slots

1,550" is the sum of the overhang at either end of the backplane

### CONNECTOR PITCH

All connectors mounted on VMEbus backplanes use a 4HP (20,32mm / 0,8") pitch

### BOARD THICKNESS

All VME<sup>2</sup> backplanes are 4,5mm (0,177") thick multilayer constructions.

### MOUNTING POSITIONS

VME<sup>2</sup> backplanes have three rows of mounting holes, only two of which (the top and bottom) are usable when the optional P0/J0 connector is installed.

The top and bottom row of backplane mounting holes are aligned with the connector mounting holes, but the centre row of mounting holes is offset by 2HP (0,4" or 10,16mm). The connector mounting holes are 0,3mm (0,012") to the left of centre of row b pins when viewed from the front (connector side) of the backplane. Each backplane is supplied with enough screws (M2,5 x 6mm long cheese head) to secure it to the tie bars of a subrack.


Backplane spacer strips are also required and must be ordered separately. Please refer to Subracks; section 4, page 4.31 for spacer details.

### BACKPLANE ASSEMBLY DEPTH


The overall depth of the VME<sup>2</sup> backplane assembly, X, covers the distance from the front face of the subrack tie bar to the rear of the rear connector shroud, where X = 18mm.

### QUALITY ASSURANCE


VME<sup>2</sup> backplanes are manufactured in accordance with quality assurance levels to BS9000, CECC 23000 and IECQ PCQ88, with systems approval in accordance with BS EN ISO 9001, ISO 9002 and EN 29002.



Backplane Width



Backplane Mounting Positions



Backplane Assembly Depth

## VME<sup>2</sup> - VME64 EXTENSIONS EXTENDER

VERO introduces a new 6U high extender for use with VME64x product applications.

Designed to extend all J1 and J2 positions, all signal tracks are provided with jumper links. The extender is also fitted with a connector to allow the fitting of logic analyser or terminator modules.

### FEATURES


- 10 layer stripline construction
- Individual signal track screening
- Jumper links on all signal tracks for interrogation purposes
- Connector position for logic analyser or terminator
- Cutout in P0/J0 area to allow dedicated cable assemblies to be connected to J0 on backplane to P0 on boards - improves flexibility of use
- Card support frame with ejector mechanism provided

**NOTE:** For details of the P0/J0 fully tracked version please contact VERO Electronics

### VME<sup>2</sup> EXTENDER

### Ordering information

Description	Order code
VME <sup>2</sup> Extender	243-315442B



# VMEbus HIGH PERFORMANCE J1 BACKPLANES

## HIGH PERFORMANCE VMEbus J1 BACKPLANES

Born from the design concepts utilised in the development of 64 bit VMEbus products VERO have brought the same high performance, low noise attributes found in larger systems to the 16 bit arena.

### FEATURES

- Conforms to VME64 specification (ANSI/VITA1-1994)
- 11 layer strip line construction.
- 50  $\Omega$  controlled characteristic impedance.
- Patented earth guard tracking techniques.
- Mechanically in-board, electrically out-board termination.
- Three power connection options:
  - Mate 'N' Lok connector
  - Powerbug with dual faston
  - Busbars
- Excellent ground shift performance
- Excellent crosstalk performance
- Auto bus grant connectors optional
- Latchable header for system functions and remote power sensing.
- Gold plated rear plug-up connectors and shrouds fitted to slot 1 and slot 'n'

### MATERIAL SPECIFICATIONS

#### Board

Dielectric epoxy glass to BS 4584  
 EP-GC-CU-3 (FR4)  
 Nominal thickness : 4,7mm  
 Base copper thickness : 35  $\mu$ m  
 Finish: Plated copper - 40  $\mu$ m average  
 Tin lead - 5  $\mu$ m approximately  
 Bare boards are UL 94V-0 rated components, File number E. 116551

#### Connectors - Standard DIN 41612 and Auto Bus Grant (ABG)



IEC 603-2 (DIN 41612) 96 way  
 Body material: glass filled polyester  
 UL 94V-0 rated  
 Insertion force (mating)/pair:  $\geq$ 90N  
 Withdrawal force (unmating)/pair:  $\geq$ 90N  
 Min. pin to board retention force: 30N per contact

#### Environmental

Temperature range - storage - 40°C to + 120°C  
 Temperature range - working - 20°C to + 85°C  
 Altitude: 3000 m  
 Humidity: 90% R.H. non-condensing  
 Shock and vibration resistant: commercial  
 MTBF to MIL -HBK-217E: >225000 hours  
 Conditions: Ground benign  
 Temperature 25°C  
 Insertion frequency: 0.5 to 5 per 1000 hours

#### QUALITY ASSURANCE

High performance VMEbus J1 backplanes are manufactured in accordance with quality assurance levels to BS9000, CECC 23000 and IECQ PCQ88, with systems approval in accordance with BS EN ISO 9001, ISO 9002 and EN 29002.



### HIGH PERFORMANCE VMEbus J1 BACKPLANES

### Ordering information

Slot width	Power distribution	Order code
21	Mate "n" lok	243-305821L
	Power bug/spade	243-305921G
	Bus bar kit	243-305658G

For any other slot size or configuration please contact VERO Electronics Sales Office

## VMEbus LIVE INSERTION MODULE

VERO's new LIModule allows individual daughter boards to be plugged into a powered and operating VME system.

The LIModule is totally transparent in operation - even under worst case conditions - and is usable with active VME boards, VMEbus backplanes and extenders and Microracks. The module may also be adapted to support J2 mezzanines such as VSB, VXI and many others with the use of a special I/O mezzanine module. For further details contact VERO Electronics Technical Enquiries.

LIModule fully conforms to IEEE P1014 R rev D, the VMEbus specification.

Active signal buffering technology is employed to preserve VME compatibility.

The LIModule improves productivity in the production, development and maintenance environments by allowing boards to be hot swapped whilst the system is running, avoiding shutdown with the corresponding loss of security and productivity.

With the exception of the controller slot, the LIModule can be used in any slot position.


LIModule is a 60mm deep x 6U active extender card second generation live insertion module, employing a combination of tri-state drivers and analog switches.

Once inserted, board connection is by software control or mechanical switching. In either case, power-up and bus synchronisation is automatic. The use of the LIModule introduces an insertion delay of 25ns, which is insignificant - even in a 21 slot system.

### FEATURES

- Conforms to VME64 specification (ANSI/VITA1-1994)
- 6U x 60mm deep extender board
- Tri-state, high speed 3ns, 64mA drivers on critical uni-directional lines i.e. address, data and control signals
- Analog Quickswitches on bi-directional lines such as interrupts and bus request
- Compatible with all VMEbus backplanes, extenders and systems

Note: If standard J2 I/O pins are used on slots where the LIModule is employed, an I/O mezzanine module is also required.



Bus Based Technology 9

### LIMODULE

### Ordering information

Description	Dimensions	Order Code
Live Insertion Module	6U x 60mm	243-312082K
I/O Mezzanine Module	-	243-313122H

For VSB and VXI mezzanine module please contact VERO Electronics Sales Office

## VMEbus 60mm ADAPTORS

### VMEbus ADAPTORS

### Ordering information

When the LIModule is employed in a 220mm deep subrack, standard 160mm deep VME cards are brought level with the system's front panels. If it is necessary to maintain all cards at the same level it is recommended that the VMEbus J1 and J2 adaptors are employed.

Description	Order code
J1 60mm Adaptor	243-42629C
J2 60mm Adaptor	243-42628F

# VMEbus SUPPORT

## VMEbus EXTENDER BOARDS

### FEATURES

- Excellent performance with a multilayer design
- Full ground plane plus individual signal track screening
- Signal pin-out identification silk screened onto outer layers
- Jumper links provided to allow signal line interrogation
- Facility for logic analyser or terminator module connection
- Card eject/support mechanism provided
- Conversion kit for combining J1 and J2 extender boards to 6U high



VMEbus Extender Boards

## VSB BACKPLANES

### FEATURES

- Implements VME Subsystem Bus (VSB)
- Fully conforms to the VSB specification - Revision C - November 1986
- Reliability of multilayer construction with solder resist protection
- Patented earth guard tracking
- Rear shrouds in slots 1 & n allow for "off-board" termination
- Rear pluggable onto VME J2 backplanes
- Jumper positions for BGIN\*/BGOUT\* daisy chain

### ADDITIONAL FEATURES - OFF-BOARD VERSION

- Off-board terminator modules included
- Retainer/Ejector kit included
- Fastons for power-on connection

### ADDITIONAL FEATURES - ECONOMY ON-BOARD VERSION


- Passive on-board termination

### VSB BUS BACKPLANES Ordering information

No. of Positions	Order Code	
	Off-board	On-board
2 Slot	243-56102D	243-312912F
3 Slot	243-56100K	243-312913D
4 Slot	243-56098K	243-312914B
5 Slot	243-56096E	243-312915L
6 Slot	243-56094L	243-312916J


### ACCESSORIES Ordering information

Description	Pkt. size	Order code
Retainer/Ejector kits	Pkt. 4	188-53118L
IEC connector shroud	Pkt. 5	188-39181D
VSB/J2 terminator	Pkt. 1	243-53179F



### EXTENDER BOARDS Ordering information

Description	Order code
J1 Extender board	243-26487G
J2 Extender board	243-26499H
6U Conversion kit	188-27542E



BUSGRANT / IACK Jumper Board

## BUS GRANT/IACK JUMPER BOARD


### FEATURES

- 6U double height board
- Simplifies access for field service
- Eliminated the use of small jumper links
- Maintains integrity of thermal management - no empty slot

## VMEbus ADAPTORS

### FEATURES

- Single piece 120mm J1/J2 design
- Separate 60mm J1 and J2 designs
- Multilayer construction
- Patented earth guard tracking



VSB Backplane

## VMEbus POWERFAIL MODULE REV. D

### FEATURES

- Conforms to VMEbus specification IEEE 1014 Rev. D
- Outputs for ACFAIL and SYSRESET
- Special input for external reset button
- Universal mounting
- Aluminium cassette

### VMEbus POWERFAIL MODULE

#### Ordering information

Description	Order code
VMEbus powerfail module	145-44690F

### BUS GRANT/IACK JUMPER BOARD

#### Ordering information

Description	Order code
Bus Grant/IACK board	188-47862A
Enhanced BGRANT/IACK board	188-308047K

### VMEbus ADAPTORS

#### Ordering information

Description	Order code
J1/J2 120mm Adaptor	243-47628J
J1 60mm Adaptor	243-42629C
J2 60mm Adaptor	243-42628F



VMEbus Powerfail Module

### SPECIFICATION

Mains input: 220V (+10%, -15%)

#### Output:

ACFAIL open collector  
SYSFAIL open collector

#### Power failure timing:

SYSRESET - L after ACFAIL L 3 ms ±0.5 ms

#### System restart timing:

SYSRESET - H after ACFAIL H 300 ms ±50ms

SYSRESET - H after DC within spec 300 ms ±50ms

#### Manual reset timing:

SYSRESET - L after man Reset min 200 ms

## MODULAR MICRORACK SYSTEM

VERO's VMEbus Microrack range has been comprehensively upgraded with the introduction of the Modular Microrack System - a new concept in the provision of customer specific development system requirements.

The modular nature of this new Microrack system allows a customised product to be made available to the user in the shortest possible time. The ability to configure the Microrack for specific applications allows the user to tailor the product exactly to his requirements and budget.

Value-engineering, combined with optimised production methods, has resulted in a range of systems that is competitively positioned, but which still enjoys the quality and performance associated with Microrack systems manufactured by VERO Electronics.

The Modular Microrack System "MMS" offers excellent performance characteristics in the key areas of VME card depths, ventilation, power supply technology, desktop version and EMC protection.

### FEATURES

- Modular design
- Short lead times
- Available in 6U, 7U and 8U. 3U and 4U are under development and due to be available during 1997
- Optimised ventilation
- Rack mount or desktop version
- VME<sup>EXCEL</sup> backplanes with ABG
- Various power supply options
- Standard 19" accessories from the KM6-II range can be used
- Quick change air filter element
- Ventilation systems for boards and power supplies operate independently from one another
- Recessed front panel assembly for EMC shielding
- Assembly to EMC standard
- EMC front panel available on 6U subrack version
- User and display controls at the front on 7U and 8U versions
- Card depths of 160mm and 220mm available
- Easy access to J2 area at rear of unit
- Integral cable management channels
- Supplied fully assembled, wired and tested

## QUALITY ASSURANCE

VME<sup>EXCEL</sup> backplanes are manufactured in accordance with quality assurance levels to BS9000, CECC 23000 and IECQPCQ88 with approval in accordance with BS EN ISO 9001, ISO9002 and EN29002.

### VMEbus MODULAR MICRACKS

3U and 4U versions of the Modular Microrack are also available. Please contact VERO Electronics further details.

### VMEbus MICRACKS

VERO can also manufacture Microracks to suit specific customer requirements. Please direct your enquiries to VERO Electronics in Hedge End, Bremen, Beauvais, Hamden, Turin, Stockholm or Værløse

### CE MARKING

Please refer to CE Marking statement on page 9.01

## SUBRACK MODULE / COVERS

A universal subrack forms the basis of all versions of the Modular Microrack. The assembly of a range of covers and panels allows the easy construction of a 6U subrack, a 7U (½U top + 6U + ½U bottom) subrack and an 8U (½ top + 6 + ½ bottom) desktop caseframe or subrack.

The standard VMEbus card depths of 160mm, 220mm and 60/160mm (60mm front recess) can be accommodated.

### Specification

Extrusions: Aluminium alloy  
 BS 1474HE9TF, conductive  
 End plates: 1,5mm MS zinc plate  
 6U Cover: 0,5mm MS zinc plate (ventilated)  
 7U/8U Cover: 1,25mm MS zinc plate  
 Visible surface spray coated (RAL 7035 pale grey)  
 Base cover ventilated  
 Handles included on subrack versions  
 500mm total depth

## VENTILATION/COOLING MODULE

### 6U VERSION

4 different rear fan panels are available for optimised system ventilation in the 7U and 8U versions. All fan panels are filtered.

- 1U fan tray, 250mm deep, fitted with 3 AC axial fans
- 1U filtered fan tray, 250mm deep, fitted with 3 AC axial fans

### 7U/8U VERSION

Ventilation of the 6U subrack is achieved by the use of 2 different fan trays. Both fan panels are filtered.

- 3 AC axial fans 120mm x 120mm
- 3 DC axial fans 120mm x 120mm
- 3 DC temperature dependent variable speed fans
- 3 DC temperature dependent variable speed fans with fan fail indication

## POWER SUPPLY/MAINS FILTER MODULE


6 different open frame power supply and mains filter combinations are available for the Modular Microrack System. The mains input is supplied through an IEC connector with a double fuse and an additional mains filter for maintaining interference suppression level B. Models BVM354, 504 and 754 feature power factor correction. A 2-way mains switch is integrated in the top cover for the 7U and 8U versions.

- BVM 200 5V/30A; +12V/8A; -12V/4A
- BVM 350 5V/50A; +12V/12A; -12V/5A
- BVM 450 5V/60A; +12V/20A; -12V/15A
- BVM 354 5V/50A; +12V/8A; -12V/4A
- BVM 504 5V/75A; +12V/8A; -12V/4A
- BVM 754 5V/120A; +12V/12A; -12V/10A
- Other power supplies available on request

## VME<sup>EXCEL</sup> BACKPLANES

VME<sup>EXCEL</sup> backplanes offer excellent performance characteristics in the key areas of controlled impedance, power distribution and termination design.

- 6 Layer stripline construction J1 and monolithic
- 4 Layer stripline construction J2
- 57Ω characteristic impedance control
- Patented 'ground-guard-tracking'
- Excellent crosstalk performance
- Auto Bus Grant (ABG)



# MMS - MODULAR MICRORACK SYSTEM

To configure your Modular Microrack System, use the chart below to select the features and options you require:

Ordering Information

146 - X X X X XX


Subrack Module	Cover Module	Ventilation Module	Power Supply Module	Backplane Module §
6U 84HP 160mm = 1	No covers = 0	No cooling = 0	BVM 200 + Filter = 1	J1 10 slot ABG = 10
6U 84HP 220mm = 2	160mm ventilated covers 6U = 1	Rear fan panel, AC fans = 1	BVM 350 + Filter = 2	J1 12 slot ABG = 12
6U 84HP 160mm (60mm recessed) = 3	220mm ventilated covers 6U = 2	Rear fan panel, DC fans = 2	BVM 450 + Filter = 3	J1 16 slot ABG = 16
	160mm (60mm recessed) ventilated covers 6U = 3	Rear fan panel, variable speed fans = 3	BVM 354 + Filter = 4	J1 20 slot ABG = 20
	½U top, ½U bottom front ventilated covers 7U = 4	1U fan tray = 4	BVM 504 + Filter = 5	J1 21 slot ABG = 21
	½U top, 1½U bottom front ventilated covers 8U = 5	1U filtered fan tray = 5	BVM 754 + Filter = 6	J1/J2 10 slot ABG = 40
	7U Desktop Version (with side covers) = 6	Rear fan panel, variable speed fans with FANFAIL indication ¶ = 6		J1/J2 12 slot ABG = 42
	8U Desktop Version (with side covers) = 7			J1/J2 16 slot ABG = 46
				J1/J2 20 slot ABG = 50
				J1/J2 21 slot ABG = 51
				Mono. 10 slot ABG = 80
				Mono. 12 slot ABG = 82
				Mono. 16 slot ABG = 86
				Mono. 20 slot ABG = 90
				Mono. 21 slot ABG = 91

¶ Special option  
§ VMEXCEL backplanes

Example: 146 - 152391 is a Modular Microrack System assembled to the following configuration:  
6U x 84HP subrack for 160mm deep boards with a ½ U top cover and a 1½ U ventilated base cover with a filter fitted. At the back is a rear fan panel with three DC fans. An open frame power supply - BVM450 - with an additional mains filter is included, together with a VMEXCEL 21 slot monolithic backplane.

- BVM 200 + Filter = 1
- BVM 350 + Filter = 2
- BVM 450 + Filter = 3
- BVM 354 + Filter = 4
- BVM 504 + Filter = 5
- BVM 754 + Filter = 6

Bus Based Technology 9



## MODULAR MICRORACK ACCESSORIES

There is a wide range of accessories available for the various types of Modular Microrack including EMC front panels, side covers and filter kits.

The Modular Microrack System can also be fitted with an extensive range of standard KM6-II accessories. Please see Section 4 for full details of all compatible divider kits, plug-in modules, guides etc.

## SIDE COVERS FOR DESKTOP VERSION

These side covers can be fitted to a MMS frame assembly to enable its use as a desktop version. Supplied as a kit.

### SIDE COVERS FOR DESKTOP VERSION

#### Ordering information

Description	Order code
Side cover 7U	146-010502A
Side cover 8U	146-010503J

## FILTER KIT

Replacement filters are available for card depths of 160mm and 220mm.

### FILTERS

#### Ordering information

Description	Order code
Filter for MMS 6U x 160mm	146-010501D
Filter for MMS 6U x 220mm	146-010500G

## EMC FRONT PANEL

The EMC front panel can be fitted for increased EMC screening on 6U, 7U and 8U recessed versions of Modular Microrack Systems. The painted (RAL 7035) front panel has cutouts on the bottom flange to accommodate cabling on the 7U and 8U version. The anodised front panel has no cabling cutouts and is intended for use on the 6U version only.

### EMC-FRONTPANELS

#### Ordering information


Description	Order code
EMC-FP anodised	146-010504F
EMC-FP RAL 7035	146-010505C



Horizontal Mounting Frame



End plate for desktop version



Filter



EMC Frontpanel

## HORIZONTAL MOUNTING FRAME

Mounted in the unused 3U area at the rear of the microrack, the horizontal mounting frame accommodates up to 5 I/O modules of 6U x 4HP format.

### HORIZONTAL MOUNTING FRAME

#### Ordering information

Description	Order code
Horizontal Mounting Frame	146-010506L

## KM6-II DIVIDER KITS

KM6-II divider kits can be mounted in the front of a microrack after assembly. They allow the combination of 3U and 6U boards and the mounting of 3U plug-in-units in the front of the rack. Please see Section 4 for full details.

### KM6-II FRONT DIVIDER KITS

#### Ordering information

Divider Width	Left hand	Right hand
21HP	950-202604H	950-202609J
24HP	950-202605F	950-202610B
36HP	-	950-202615C
42HP	950-202605D	950-202611L
84HP incl. FP	950-201275F	

## PLUG-IN DISC DRIVE MODULES

Plug-in disc drive modules can be mounted in a Microrack in conjunction with front divider kits. The modules have a height of 3U and a width of 8HP (FD 3½"), 12HP (HD 3½") and 30HP (HD 5¼"). Please see Section 4 for full details.

### KM6-II PLUG-IN DISC-DRIVE MODULES

#### Ordering information

Description	Order code
Module FD 3½"	174-010198L
Module HD 3½"	174-010199H
Module HD 5¼"	174-010001G

## GUIDES

Eurocard guides are suitable for boards of 1,6mm thickness and plug-in units for 3½" disk drives. For 5¼" disk drive modules guides for plug-in-units must be used. Please see Section 4 for full details.

### GUIDES

#### Ordering information

Guide type	Board length	Order code
Eurocard	100	950-242850B
	160	950-232662J
Plug-in unit	160	950-232664E
	220	950-232665C

# 3 SLOT VMEbus MICRORACK

## VMEBUS 3 SLOT DEVELOPMENT MICRORACKS

These 3 slot Microracks are intended to compliment the development of emerging single board computer products, which can easily be integrated into complete systems with only a few cards, disk drives and I/O connectors.

The new Microracks have been designed to offer all the features and flexibility of larger Microracks, but in a more compact form.

EMC shielding and airflow management were key design priorities and, in this respect, the 3 slot system is comparable with VERO's larger Microracks.

The new Microracks can accommodate three 4HP x 160mm 6U boards which plug directly into a high quality 3 slot VME<sub>XCEL</sub> backplane fitted with auto Bus Grant connectors.

There is adequate space in the tower system for 1 x 3½" floppy disk drive and one hard disk drive. The rack mount version can accommodate 2 x 3½" floppy disk drives and one hard disk drive. The rear of both racks have three 6U x 4HP blank panels which can be used for I/O modules, transition modules or can be punched to facilitate the mounting of connectors.

The tower rack is fitted with an 80 Watt power supply (110 Watt if additional cooling is supplied) which is suitable for the requirements of most small systems. The rack mount 3 slot Microrack is fitted with a 200 Watt power supply.

### FEATURES

- Conforms to the VME64 specification (ANSI/ITA 1-1994)
- 80/110 Watt, 85 - 264 VAC universal input power supply - tower version
- 200 Watt, 115/230VAC switchable power supply - rack mount version
- 3 6U x 4HP card slots
- 3 6U x 4HP rear I/O positions
- 1 or 2 x 3½" floppy disk and one hard disk mounting position
- Removable disk drive housing
- 3 slot VME<sub>XCEL</sub> Monolithic backplane
- Auto Bus Grant connectors

### DIVIDER KIT

Available for the 2U rack mount version is a divider kit which allows the 3off 6U x 4HP rear I/O positions to be split into 6off 3U x 4HP positions.

### 3 SLOT VMEbus MICRORACKS Ordering information



Description	Order code
3Slot 2U Rack Mount Microrack	<b>224-315100G</b>
3Slot 3U Tower Microrack	<b>224-314400L</b>
Divider Kit - Rack Mount	<b>224-315410C</b>

### QUALITY ASSURANCE

VME<sub>XCEL</sub> backplanes are manufactured in accordance with quality assurance levels to BS9000, CECC 23000 and IECQPCQ88 with approval in accordance with BS EN ISO 9001, ISO9002 and EN29002.

#### CE MARKING

Please refer to CE Marking statement on page 9.01



**INTRODUCTION**

VMEbus has become well established over the last decade, with many thousands of active cards being made available by hundreds of manufacturers.

VERO Electronics has been closely involved with VMEbus since its inception and, from 1987, with its generic instrumentation architecture - VXIbus.

The specification governing VXIbus - an acronym for VMEbus eXtensions for Instrumentation - defines the use of four bus module sizes (Fig. 1), with the A and B modules the same size as 3U and 6U VMEbus cards. Any size module may be placed in a card cage of a larger size, for example, A and B size cards may be used in a C or D size Microrack. This allows the use of standard VMEbus modules within a VXI System, providing a high degree of flexibility.

Although the VXIbus specification, broadly speaking, follows the VME standards, it includes defined functions on the P2 connector and a further set of functions on the P3 connector.

The most important variation in the two standards arises from the fact that any VXIbus instruments incorporated into a system must be capable of being physically screened against EMC on all sides with a provision for additional chassis screening between instruments.

VERO's range of VXIbus products - multilayer backplanes, extender boards, prototyping boards, Microracks and modules - fully conforms with the latest revision (rev. 1.4) to the VXIbus specifications.

The total in-house design, manufacture and customising capabilities within the manufacturing divisions of VERO enables the provision of semi- or fully customised versions of the VXIbus product range.

**For in-depth details or a discussion of the customising possibilities please contact VERO Electronics Technical Sales.**

**VXIbus BACKPLANES**

**FEATURES**

- Fully conforms to the VXIbus specification, revision 1.4
- 12 layer stripline construction ensures precisely controlled characteristic impedance.
- Auto bus grant connectors fitted as standard
- Differential tracking and line length equalization techniques utilized to minimise signal skew on all high speed lines.
- On-board socketed ECL buffers for CLK10 & CLK100 distribution.
- High-speed decoupling capacitors positioned between termination networks.
- Exposed ground plane area to facilitate RFI grounding of plug-in instrument modules.
- Additional decoupling capacitor positions provided between each connector slot. This permits fine tuning of the system
- Monolithic design offering continuous ground and voltage planes providing even power distribution and minimising IR shift.

VXIbus BACKPLANES

Ordering information

Description	Dimensions	Order Code
"C" size 5 slot	262,00 x 152,40	63-310535G
"C" size 6 slot	262,00 x 182,88	63-310536D
"C" size 13 slot	262,00 x 395,00	63-310537A
"D" size 5 slot	395,00 x 152,40	63-310538J
"D" size 13 slot	395,00 x 395,00	63-310539F






Figure 1



SECTION THROUGH A 12 LAYER VXIbus BACKPLANE

**VXIbus HIGH POWER BACKPLANES**

A high power option is available on 13 slot C and D size backplanes.

Extra power positions are added to the backplane to ensure that every voltage can have the maximum current drawn as specified by the VXIbus specifications.


To introduce the power to the backplane, two 9,53mm<sup>2</sup> copper busbars are provided, plus laminated busbars for the remaining voltages; two laminated busbars for the C size backplane and four on the D size.

All other features, dimensions and specifications are identical to the standard VXIbus backplane.

VXIbus HIGH POWER BACKPLANES

Ordering information

Description	Power rating	Order Code
"C" size 13 slot	1,9kW	63-314297A
"D" size 13 slot	3,0kW	63-314295G



Bus Based Technology 9

# VXibus MICRORACKS

## VXibus MICRORACKS

The name "Microrack" is synonymous with well engineered, ready-to-run microprocessor support systems. The VXibus Microrack range continues VERO's tradition of offering a total solution to the hardware requirements of the exacting VXibus standard.

At the heart of each Microrack is a VERO VXibus backplane, fitted as standard with Auto Bus Grant connectors and offering the perfect environment for transmitting sensitive, high speed electronic signals. The basis of these Microracks is a purpose built heavy-duty chassis system, designed around the successful KM6-II and HD-167 subrack systems.

Various high performance power sources are used to deliver up to 1100W of closely regulated power.

Computer Aided Design has been employed, ensuring the most effective compromise between the differing and conflicting interests of efficient thermal management and RFI shielding.

Fully wired and ready for use, the Microracks are available in a number of options to integrate into larger systems, as part of a rack mounted system, or housed in an attractive enclosure for free-standing office or laboratory applications.

## VXibus 6 SLOT PORTABLE "C" SIZE MICRORACK



The 6 slot portable VXibus Microrack is a fully configured, yet cost-effective, system solution providing space for up to six C size VXibus modular instruments in an EMC screened, fully wired, ready-to-run environment.

### FEATURES

- Rugged, portable 204 x 433 x 560mm enclosure
- C size portable chassis with 60mm recessed front panels for cable management
- Usable in desktop or tower configurations
- Weight 15Kg
- EMC upgradable by the addition of copper fingers
- 12 layer stripline backplane with Automatic Bus Grant connectors conforming to VXibus specification revision 1.4
- Standard 600 Watt wide input power supply
- Easily removable side cover allows for testing
- Average 50 Watts per slot power allowance
- Lockable, EMC shielded door
- 2 rear mounted AC fans with 35cfm throughput

### Ordering information

Description	Dimensions	Order code
6 Slot Portable	433 x 204 x 560	203-313400J

### SUPPLY VOLTAGE - 6 SLOT PORTABLE

+5V	+12V	-12V	+24V	-24V	-5.2V	-2V
40A	6A	4A	6A	4A	15A	8A

## VXibus 5 SLOT "C" AND "D" SIZE MICRORACKS



At the heart of all 5 slot VXibus Microracks from VERO is a high performance 12 layer backplane, supported by a conductive KM6-II subrack making the upgrade to a fully screened EMC rack easily accomplished.

The C and D size Microracks are available in three formats; tower, desktop and rack mount.

### FEATURES

- Accepts 5 "C" or "D" size modules
- KM6-II conductive cardframe
- 4U x 622 mm deep Diplomat enclosure
- Weight 25 Kg desktop / tower, 18 Kg rack mount
- Bus reset timing module
- Removable service access panels
- 550W power supply
- Optional GPIB monitor available

### Ordering information

Description	Order code
5 Slot "C" Size Desk Top	203-304014B
5 Slot "C" Size Tower	203-304016L
5 Slot "C" Size rack mount	203-304012H
5 Slot "D" Size Desk Top	203-304015B
5 Slot "D" Size Tower	203-304017J
5 Slot "D" Size rack mount	203-304013F

### SUPPLY VOLTAGE - 5 SLOT C/D

+5V	+12V	-12V	+24V	-24V	-5.2V	-2V
40A	6A	6A	6A	6A	30A	6A


## GPIB MONITOR BOARD

The GPIB Monitor Board offers the user the capability of remotely monitoring the operating parameters of a VXibus Microrack using the GPIB data bus. The parameters measured include all power supply rails and a spot temperature, which is measured via an active temperature probe.

The spot temperature is monitored digitally and compared against a value pre-set on a switch register.


### OPTIONS

- A spare analogue input is available to allow the user to monitor an extra parameter (configured for positive voltage monitoring).
- The module can be used without the GPIB interface, indicating validity of the measured parameters on LEDs, which may be mounted either on the module or remotely.
- The GPIB controller can remotely command the VXI GPIB1 module to initiate MICRORACK SYSTEM RESET. A watchdog function may also be used, causing the MICRORACK SYSTEM RESET to be generated if the watchdog input is not accessed every 100 ms.



EMC Rating (50% fingers) - VXibus 6 Slot Portable Microrack

## VXibus 13 SLOT "C" SIZE MICRORACK WITH CABLE MANAGEMENT



A rack identical in basic construction to standard 13 slot C size units except that the rack has been extended by 60mm, allowing the heavy duty shock and vibration resistant HD-167 subrack to be recessed, freeing an area for cable management. Available in rack mount format with slide mounting positions, rear I/O cable exit panel, MacPanel and Virginia Panel test interface mounting positions, additional optional fan locations and optional GPIB monitor.

### FEATURES

- Accepts 13 "C" size modules
- Depth 622mm desktop, 603mm rack mount
- Heavy duty cardframe system (HD 167)
- Bus reset timing module
- 800W power supply (1100 optional)
- Weight 29 Kg
- Mac Panel and Virginia Panel compatible
- 9U high x 671 mm deep, cardframe recessed by 75mm
- 1U removable rear panel for cable exit or I/O connector mounting
- Optional GPIB monitor available
- Optional third fan for extra cooling

### Ordering information

Description	Order code
13 Slot Rack Mount	203-311550L

### SUPPLY VOLTAGE - 13 SLOT C

+5V	+12V	-12V	+24V	-24V	-5.2V	-2V
60A	6A	6A	6A	6A	40A	6A

## VXibus 13 SLOT "C" SIZE MICRORACK



Both racks are constructed around VERO's 12 layer high performance VXibus backplane and the HD-167 military specification, heavy duty subrack - providing a system able to withstand severe shock and vibration.

Airflow management has recently been upgraded to cope with the ever increasing demands of heat dissipation from the VXibus modules.

The 13 slot C size Microrack is available in two formats; desktop or rack mount.

### FEATURES

- Accepts 13 "C" size modules
- Depth 622mm desktop, 603mm rack mount
- 9U high
- Heavy duty cardframe system (HD 167)
- Bus reset timing module
- Removable service access panels
- 800W power supply (1100 optional)
- Weight 42,5 Kg desktop, 26 Kg rack mount
- Optional GPIB monitor available

### Ordering information

Description	Order code
13 Slot Desk Top	203-302533A
13 Slot Rack Mount	203-303169B

### SUPPLY VOLTAGE - 13 SLOT C

+5V	+12V	-12V	+24V	-24V	-5.2V	-2V
60A	6A	6A	6A	6A	40A	6A

## VXibus 13 SLOT "D" SIZE MICRORACK



Constructed around VERO's 12 layer high performance VXibus backplane, supported by a conductive KM6-II subrack making the upgrade to a fully screened EMC rack easily accomplished.

The fan tray, located at the base of the unit, is removable allowing easy access for routine maintenance or repair.

The 13 slot D size Microrack is supplied with pre-fitted heavy duty carrying handles.

### FEATURES

- Accepts 13 "D" size modules
- 13U x 533 mm deep
- KM6-II conductive cardframe
- Bus reset timing module
- 2U removable fan tray
- 1100W power supply
- Weight 40 Kg

### Ordering information

Description	Order code
13 Slot "D" Size Rack Mount	203-306842A

### SUPPLY VOLTAGE - 13 SLOT D

+5V	+12V	-12V	+24V	-24V	-5.2V	-2V
80A	5A	5A	4A	4A	40A	20A

## QUALITY ASSURANCE

VXibus backplanes are manufactured in accordance with quality assurance levels to BS9000, CECC 23000 and IECQPCQ88 with approval in accordance with BS EN ISO 9001, ISO9002 and EN29002.

### CE MARKING

Please refer to CE Marking statement on page 9.01

# VXibus PROTOTYPING AND EXTENDER BOARDS

## VXibus PROTOTYPING BOARDS

A high density multilayer prototyping board fully loaded with socketed pressfit wire wrap pins. The board pattern allows the use of 7.62 mm, 10.16 mm, 12.70 mm or 15.24 mm pitch integrated circuits.

### FEATURES

- Fully conforms to the VXibus specification revision 1.4
- Full VMEbus interface available
- High density wire wrap prototyping pattern.
- Compatible with the VXibus "C" size format.
- Multilayer construction.
- Socketed pins for ease of component assembly.
- Surface mount de-coupling capacitors.
- Suitable for P.G.A. style devices up to 17 x 17 pin.
- Easy access to distributed power planes.
- Full RFI screening capability.

## VXibus EXTENDER BOARD

The VERO VXibus extender card is a 4 layer multilayer board utilising signal guard track technology, to minimise induced crosstalk. It is compatible with B or C size cards or modules.

### FEATURES

- Fully conforms to the VXibus specification revision 1.4
- Earth guard tracking utilised to minimise crosstalk.
- Compatible with single and double width VXibus screened modules
- 4 layer multilayer construction
- Cantilever bracket to support instrument and minimise connector stress.
- Test points provided at front edge of card.
- Card eject mechanism provided.
- Compatible with VXibus screened modules to maximise protection against externally generated noise.



## NORMAL DUTY VXI MODULE

### FEATURES

- C and D size
- Single and double width
- Channel section front panel
- Ejector handles
- Ventilated covers
- EMC sealing
- Card mounting brackets
- Beryllium copper fingers

## LIGHT DUTY VXI MODULE

A low cost option similar to normal duty module but with two part front panel and no EMC seals.



### VXibus PROTOTYPING BOARDS

#### Ordering information

Description	Dimensions	Order code
VIC/VXI board	233,34 x 340,00	63-303103A
VXI board	233,34 x 340,00	63-302203B

### VXibus EXTENDER

#### Ordering information

Description	Order code
VXibus "C" size extender	63-302270E

### VXibus NORMAL DUTY MODULE

#### Ordering information

Description	Order code
C size, single width	207-203543A
D size, single width	207-222524J
C size, double width	207-203544K

## MATERIAL SPECIFICATIONS - VXibus BACKPLANES

### BOARD SPECIFICATION

Dielectric Epoxy glass to BS 4584 EP-GC-CU-3 (FR4)  
 Nominal thickness : 5,35 mm  
 Base copper thickness : 35 mm.  
 Finish : Plated copper - 40mm average. Tin lead - 5mm.  
 Total : 80mm outside layers only.

### Connectors - Standard DIN 41612 and Auto Bus Grant (ABG)

IEC 603-2 (DIN 41612) 96 way  
 Body material: glass filled polyester UL 94V-0 rated

Insertion force (mating)/pair: ≥90N  
 Withdrawal force (unmating)/pair: ≥90N  
 Min. pin to board retention force: 30N per contact

NOTE: Bare boards are UL 94 V-0 recognised components.  
 File number E 116551

## QUALITY ASSURANCE

VXibus backplanes are manufactured in accordance with quality assurance levels to BS9000, CECC 23000 and IECQ PCQ88.

Systems approval in accordance with BS EN ISO 9001, ISO 9002 and EN 29002.

### VXibus LIGHT DUTY MODULE Ordering information

Description	Order code
C size, single width	207-222002F

## CONNECTOR SHROUD

### FEATURES

- Enhances performance
- Beryllium copper fingers
- Fits to backplane connector

### CONNECTOR SHROUDS Ordering information

Description	Order code
Connector shroud	207-203582B
Beryllium copper fingers	950-203353B

## COMPACTPCI BACKPLANE

VERO's new CompactPCI backplanes are fully compatible with the CompactPCI specification (Rev. 1.0, 1 November, 1995).

Due to the vast experience that VERO has gained from designing and manufacturing densely tracked backplanes with high layer counts and metric connector systems, producing a high performance CompactPCI backplane range that is fully compliant with the latest specification became a natural extension to the Company's product offering.


CompactPCI is an adaptation of the Peripheral Component Interconnect (PCI) specification for industrial and/or embedded applications requiring a more robust mechanical form factor than the Desktop PCI.

CompactPCI is electrically compatible with PCI, allowing standard PCI components to be adapted to the Eurocard format and used in applications where the standard Desktop PCI would be unsuitable.

Initially, two backplanes will be available. During 1997 a full range of product including 3U and 6U backplanes, mixed technology backplanes, packaging and power supplies will be developed and phased into production. Please contact VERO Electronics for further details.

### FEATURES

- 10 layer stripline construction
- Supports 32 or 64bit PCI transfers
- Supports 5V and 3,3V technology
- Available with or without on-board modular power supply connector



Bus Based Technology 9

### MATERIAL SPECIFICATIONS

#### Board

Dielectric epoxy glass to BS 4584  
EP-GC-CU-3 (FR4)

Nominal thickness : 4,5 mm

Base copper thickness : 35 µm

Finish: Plated copper - 40 µm average

Tin lead - 5 µm approximately

Bare boards are UL 94V-0 rated components, File number E. 116551

#### Connectors

Modular Power Connector 24 + 8

Max. current per pin - power: 40A

Max. current per pin - signal: 1,5A

Insertions: 500 minimum (DIN Class 1)

CompactPCI Connector

Max. current per slot -5V: 12A

Max. current per slot -3,3V: 15A

#### Environmental

Temperature range - storage - 40°C to + 120°C

Temperature range - working - 20°C to + 85°C

Altitude: 3000 m

Humidity: 90% R.H. non-condensing

Shock and vibration resistant: commercial

MTBF to MIL -HBK-217E: >225000 hours

Conditions: Ground benign

Temperature 25°C

Insertion frequency: 0.5 to 5 per 1000 hours

### COMPACTPCI BACKPLANE

### Ordering information

Description	Slot Size	Order Code
3U CompactPCI backplane	8 Slots	425-315737J
3U CompactPCI backplane with PSU connector	8 Slots	425-315337C

For other slots sizes, heights or for details of custom versions please contact VERO Electronics Sales Office

# FUTUREBUS+ BACKPLANES

## FUTUREBUS+ MULTI-PROFILE BACKPLANES

### FEATURES

- Designed to IEEE 896.2, rev 5.5, July 1991, profile specifications
- 10 layer stripline technology
- Hard metric IEEE 1301.1 compatible
- Supports central and distributed arbitration
- Utilises curved track technology, thereby permitting elimination of cornered or angled bends in signal traces which would otherwise create partial reflection of the incident signal.
- Geographical encoding can be user selected by means of jumpers, to provide profile 'A' or 'F'.
- High performance surface mount termination using a VERO 'patented' design. This avoids excessive stub lengths and inductive traces associated with packaged termination design.
- Fully compliant termination voltage design offering a passive solution via the use of a range of cascading capacitors. These operate in conjunction with a conventional switch mode power supply, supplied integrally as part of the microrack.
- Controlled characteristic impedance
- Choice of power distribution systems
  - LOMET Connector System (optional on request)
  - M4 Power Studs

The Futurebus+ Multi-profile backplanes are supplied fully assembled with 2mm pitch IEEE 1301.1 compatible metric connectors, allowing multiple power and ground connections, a full 128bit or 64bit screened databus and I/O connections from each slot.

### TERMINATION VOLTAGE DROOP


An array of electrolytic capacitors is included to prevent termination voltage droop. This ensures that the 2.1V supply remains within specification - even at extreme operating speeds.

### POWER DISTRIBUTION SYSTEMS

In order to counteract the skin effect caused by high current demand from fast leading edge waveforms, VERO has introduced this multiple power and ground plane design. External connections are provided to these planes via either the LOMET Connector System or a series of M4 Power Studs.

## LOMET LOW IMPEDANCE CONNECTOR SYSTEM

The development of Futurebus+, and the introduction of B.T.L. drivers has highlighted notable problems in the area of power distribution such as "skin effect" and "wipe out". To counter these problems VERO developed the LOMET System. This allows power to be brought from the integrated power module to the backplane with minimum high frequency losses. The LOMET, a latching, codeable connector, is based on a 48 pin, 2mm pitch EIA IS 64 connector, and provides a low inductance path between the power source and the multiple power planes within the backplane. Pressfit technology enables the LOMET to interface with high layer count boards and for tracking to run through the connector matrix, maximising useable backplane area.



### BOARD SPECIFICATION

Dielectric epoxy glass to BS 4584  
 EP-GC-Cu-3 (FR4)  
 Nominal thickness: 6,4mm  
 Base copper thickness: 35µm  
 Finish: Plated copper - 25µm  
           Tin Lead - 5µm approximately  
           Total - 33 µm


Connector specification: EIA IS 64 2mm pitch metric connector

Bare boards are UL recognised components, file number E 116551

### FUTUREBUS+ BACKPLANES

### Ordering Information

Description	Power distribution	Dimensions	Order code
Futurebus+ Multi-profile 4 slot backplane 64-bit	M4 Stud	295 x 139	819-309905C
Futurebus+ Multi-profile 4 slot backplane 128-bit	M4 Stud	295 x 139	819-309805G
Futurebus+ Multi-profile 14 slot backplane 128-bit	M4 Stud	295 x 426	819-309615A
Futurebus+ Multi-profile 14 slot backplane 64-bit	M4 Stud	295 x 426	819-310945H



### LOMET CONNECTOR

### Ordering information

Description	Order code
Lomet Connector	820-307836C

## FUTUREBUS+ 4 SLOT MICRORACK

The result of VERO's understanding of the Futurebus+ development forum - and our ability to value engineer high specification, high performance products - is the introduction of a number of low cost entry level systems for development projects and advanced, fully specified Futurebus+ development systems.

### ENTRY-LEVEL FUTUREBUS+ 4 SLOT MICRORACK DEVELOPMENT SYSTEM

- Multi-profile 10 layer stripline backplane (64-bit)
- Full access for development
- 350W power supply standard
- Supplied with 2,1V and 5V to backplane
- 3,3V optional
- 64-bit operation standard, 128-bit optional
- Available in Tower, rack mount and desktop options

#### SYSTEM OPTIONS

The 4 slot development system forms a building block to which a number of modifications can be made:-

- Additional voltage may be required from the power supply (e.g. 3.3V). However, in order to avoid damaging voltages being presented to active cards, the Futurebus + specification requires provision of power sequencing. A module is available to meet this requirement.
- A system management module is available to control bus reset and system reset.
- A battery back up and charging circuit module is also available.
- A module to control fan speed in line with environmental conditions, minimising fan noise and maximising fan life is available. The sense position for this module can be placed as needed.
- A fan fail module can be provided which monitors satisfactory operation of each fan with an audible/visible (via front panel LED's)/TTL output of failure condition.
- 128 bit backplanes.

#### POWER SUPPLY

- 5V at 40A
- 12V at 12A
- 2.1V at 10A
- Autoranging 115V/230V
- Meets UL 478, IEC 950, VDE 0805/6, EN 60950 (safety)
- Short circuit protection with auto-reset
- Over voltage protection
- Power supply can be optionally upgraded

#### THERMAL MANAGEMENT

- High capacity, positive pressure card area cooling (2 x 110 CFM fans), with isolated power supply chamber (1 x 30 CFM fan).

#### CHASSIS

- Removable panels fitted to both sides to permit ready access to boards during development work.
- Available in three formats:-
  - Tower case
  - Rack mount
  - Desktop



### ADVANCED FUTUREBUS+ 4 SLOT MICRORACK DEVELOPMENT SYSTEM

- Multi-profile 10 layer stripline backplane (128-bit standard, 64-bit optional)
- Power Sequencing board
  - Correct power up and power down
  - Enabled only when voltages in spec.
  - Compliant shutdown procedure in the event of line failure
  - Fail-safe operation
- Thermal management control
  - Intelligent fan control
  - Fan performance increases linearly with temperature
  - Temperature sensed in two positions
  - Audible alarm
  - Visual alarm
  - Fail-safe operation
- Advanced airflow design
- System management module
  - Bus reset
  - System reset
  - Power monitor
  - Battery back up
  - Battery recharge
- Mass storage - 3½" disk drive mounting kit
- Fully EMC screened subrack

#### POWER SUPPLY

- 5V at 60A
- 12V at 20A
- 2.1V at 4A
- Autoranging 115V/230V
- Meets UL 478, IEC 950, VDE 0805/6, EN 60950 (safety)
- Short circuit protection with auto-reset
- Over voltage protection
- Power supply can be optionally upgraded

#### 4 SLOT ENTRY LEVEL FUTUREBUS+ MICRORACK

##### Ordering information

Description	Order code
Tower case	820-309891G
Rack mount	820-309890J
Desktop	820-309892E

#### ADVANCED 4 SLOT FUTUREBUS+ MICRORACK

##### Ordering information

Description	Order code
Multi-profile Microrack	820-310533F

#### ACCESSORIES - FUTUREBUS+ MICRORACKS

Description	Order code
EMC 12SU x 6SP front panel	932-235081E
EMC 12SU x 12SP front panel	932-235082C

For any of the above special options please contact your local VERO Sales Office.

### QUALITY ASSURANCE

Futurebus+ backplanes are manufactured in accordance with quality assurance levels to BS9000, CECC 23000 and IECQPCQ88 with approval in accordance with BS EN ISO 9001, ISO9002 and EN29002.

#### CE MARKING

Please refer to CE Marking statement on page 9.01

# FUTUREBUS+ MICRORACKS

## FUTUREBUS+ 14 SLOT MICRORACK

The recent introduction of a number of advanced 14 slot systems is the result of VERO's understanding of the Futurebus+ development forum and our ability to engineer high specification, high performance products.

### FEATURES

- Multi-profile 10 layer stripline backplane (128-bit, 64-bit optional)
  - Utilises curved track technology, thereby permitting elimination of cornered or angled bends in signal traces which would otherwise create partial reflection of the incident signal.
  - Geographical encoding can be user selected by means of jumpers, to provide profile 'A' or 'F'.
  - High performance surface mount termination using a VERO 'patented' design. This avoids excessive stub lengths and inductive traces associated with packaged termination design.
  - 128 bit data line with I/O connectors on the rear.
  - 10 layer stripline construction.
  - Fully compliant termination voltage design offering a passive solution via the use of a range of cascading capacitors. These operate in conjunction with a conventional switch mode power supply, supplied integrally as part of the microrack (see below).
- Power Sequencing board
  - Correct power up and power down
  - Enabled only when voltages in spec.
  - Compliant shutdown procedure in the event of line failure
  - Fail-safe operation
- Thermal management control
  - Intelligent fan control
  - Fan performance increases linearly with temperature
  - Temperature sensed in two positions
  - Audible alarm
  - Visual alarm
  - Fail-safe operation
  - High capacity, ducted cooling (3 x 110 CFM fans), with isolated power supply chamber (power supply has integral fan).
  - Thermal safety trips are provided above the board area and within the power supply exhaust area.
  - A module to control fan speed in line with environmental conditions, minimising fan noise and maximising fan life. The sense positions for this module can be placed as needed.
  - A fan fail module is provided which monitors satisfactory operation of each fan with an audible / visible (via front panel LED's) / TTL output of failure condition.
- System management module
  - Bus reset
  - System reset
  - Power monitor
  - Battery back up
  - Battery recharge
- Rechargeable battery pack
- Hard metric (KM25) chassis
- Status LEDs on front panel
- Weight 31kg



### POWER SUPPLY

- 5V at 120A
- 2.1V at 20A
- 3.3V at 10A
- 12V at 4A
- 115V / 230V (strappable)
- Meets VDE 0871, FCC 20780 Class A
- Short circuit protection with auto-reset
- Over voltage protection
- Current limit on all outputs

### CHASSIS

- Supplied in rack mount format.

### ADVANCED FUTUREBUS+ 14 SLOT MICRORACK

#### Ordering information

Description	Order code
Multi-profile Microrack	820-310425J

### ACCESSORIES - FUTUREBUS+ MICRORACKS

Description	Order code
EMC 12SU x 6SP front panel	932-235081E
EMC 12SU x 12SP front panel	932-235082C

## ENTRY LEVEL 14 SLOT FUTUREBUS+ MICRORACK

A 14 slot Futurebus+ Development Microrack (excluding the Power Sequencing Module, System Management Module, battery back-up, fan fail, fan control, and thermal trips) is also available. This unit features a lower power PSU (5V/70A, 2.1V/10A, +12V/4A) and a 128-bit backplane as standard. A 64-bit backplane is available as an option.

### ENTRY LEVEL 14 SLOT FUTUREBUS+ MICRORACK

#### Ordering information

Description	Order code
Multi-profile Microrack	820-310843B

For any of the above special options please contact VERO Electronics Sales Office

## QUALITY ASSURANCE

Futurebus+ backplanes are manufactured in accordance with quality assurance levels to BS9000, CECC 23000 and IECQPCQ88 with approval in accordance with BS EN ISO 9001, ISO9002 and EN29002.


### CE MARKING

Please refer to CE Marking statement on page 9.01

## MULTIBUS iPSB BACKPLANES

### FEATURES

- Fully conforms to the Intel Multibus specification revision 04 - June 1982, IEEE 796
- Reliability of multilayer construction with solder resist protection
- Available in 6 and 12 slot widths
- Option provided for either serial or parallel priority
- Supplied fully assembled complete with termination
- 6,3mm power pick-up tabs
- Interlocking fingers allow positive location of iLBX



MULTIBUS iPSB BACKPLANE


Ordering information

No. of Positions	Backplane dimensions Width x Length(mm)	No. of Layers	Order code
6 slots	218,41 x 113,38	6	408-56386C
12 slots	218,41 x 204,8	5	408-56387L

## MULTIBUS iLBX BACKPLANE

### FEATURES

- Fully conforms to the Intel Multibus specification revision 04 - June 1982, IEEE796
- Double sided construction with solder resist protection
- Earth guard tracking
- Interlocking design to ensure alignment with iPSB backplanes
- 6,3 mm power pick-up tabs



### BOARD SPECIFICATION - iPSB AND iLBX

Dielectric Epoxy Glass to	BS 4584
	EP-GC-CU-3(FR4)
Nominal thickness:	2,4 mm
Base Copper thickness:	30 μm
Finish: Plated copper	25 μm average
Tin lead	10 μm max
Total	70 μm - outside layers only
Maximum working temperature	85°C

iLBX BACKPLANE

Ordering information

No. of positions	Backplane dimensions Width x Length(mm)	No. of Layers	Order code
6 slot	120,10 x 90,93	2	408-52873D


Multibus is a trade mark of Intel Corporation

Note: bare boards are UL94 V-0 Recognised components. File number E116551

# MULTIBUS II BACKPLANES


## iPSB BACKPLANE

WITH "OFF-BOARD" TERMINATION



## iPSB BACKPLANE

WITH "ON-BOARD" TERMINATION



### FEATURES - OFF-BOARD TERMINATION

- Fully conforms to Multibus II Specification - IEEE 1296
- Reliability of multilayer construction using 6 layers with solder resist protection
- Completely assembled using high reliability pressfit IEC 603-2 connectors
- Full "off-board" termination with facilities to implement BCLK and CCLK termination requirements
- High speed de-coupling capacitors provided between resistor networks

### iPSB BACKPLANES "OFF BOARD"

#### Ordering information

Number of positions	Dimensions width x length(mm)	Order code
5 slot iPSB	128,55 x 95,68	34-39019E
7 slot iPSB	128,55 x 136,32	34-56178L
10 slot iPSB	128,55 x 197,28	34-39020C
15 slot iPSB	128,55 x 298,88	34-53176G
20 slot iPSB	128,55 x 400,49	34-39021K

### FEATURES - ON-BOARD TERMINATION

- Fully conforms to Multibus II Specification - IEEE 1296
- Reliability of multilayer construction using 6 layers with solder resist protection
- Power connection via 25A rated power taps
- All termination lines fully bussed
- High speed de-coupling capacitors provided between resistor networks

### iPSB BACKPLANES "ON BOARD"

#### Ordering information

8 slot iPSB	128,55 x 156,64	34-302144J
10 slot iPSB	128,55 x 197,28	34-302847J
20 slot iPSB	128,55 x 400,48	34-301381J

**Note:** All iPSB off-board terminated backplanes are supplied complete with polarized mating power connectors and two terminator modules.

### BOARD SPECIFICATION iPSB BACKPLANES

Dielectric Epoxy Glass to	BS4584
	EP-GU-CU3(FR4)
Nominal thickness:	3,2mm
Base copper thickness:	70µm for inner layers 35µm for outer layers
Finish: Plated copper	30µm average
Tin lead	5µm min.
Total	70µm - outside layers only (av.)

**Note:** bare boards are UL95 V-0 recognised components. File number E116551.

### BACKPLANE TERMINATION REQUIREMENTS FOR iPSB

**Note:** Signal lines BCLK and CCLK are required to be terminated at the furthest point from the driver. The iPSB terminator module has the required terminating resistors (110Ω and 120Ω) fitted and is suitable for use at either end of all the iPSB backplanes which have 13 through 20 slots: slot "0" being centralised on these backplanes. The four terminating resistors (110Ω and 120Ω) NEED TO BE REMOVED from the terminator module when it is fitted to slot position "0" on all iPSB backplanes with 12 slots or less.

## ACCESSORIES

iPSB TERMINATOR MODULE



Each **iPSB off-board backplane** is supplied complete with two terminator modules which are rear mounted at right angles to the backplane. Additional terminator modules may be ordered separately and are supplied in pairs.


iPSB TERMINATOR MODULE

#### Ordering information

Description	Dimensions	Order code
iPSB terminator	95,00 x 26,50	188-39027D

## iLBX II BACKPLANE

WITH "OFF-BOARD" TERMINATION



### FEATURES

- Fully conforms to Multibus II Specification - Revision C, August 1984 - IEEE P1296
- Reliability of multilayer construction, with solder resist protection
- Available in four backplane slot widths
- Completely assembled using high reliability pressfit IEC 603-2 connector
- Removable "off-board" termination
- High speed de-coupling capacitors provided between resistor networks

### BOARD SPECIFICATION iLBX BACKPLANE

Dielectric Epoxy Glass to	BS4584
	EP-GC-CU-3(FR4)
Nominal thickness:	3,2 mm
Base copper thickness:	70 µm for inner layers
	35 µm for outer layers
Finish:	Plated copper
	Tin lead
	5 µm max.
	Total
	70 µm - outside layers only

Note: bare boards are UL94 V-0 recognised components. File number E116551

### iLBX BACKPLANES

### Ordering information

No. of Positions	Board Dimensions (mm)	Order code
2 Slot iLBX II	128,55 x 39,80	34-42854J
3 Slot iLBX II	128,55 x 60,12	34-52881J
4 Slot iLBX II	128,55 x 80,44	34-52883A
6 Slot iLBX II	128,55 x 110,92	34-39025E

Note: All iLBX II backplanes are supplied with polarized mating power connectors and one terminator board.

## ACCESSORIES

### iLBX II TERMINATOR MODULE



iLBX TERMINATOR MODULE **Ordering information**

Description	Dimensions (mm)	Order code
iLBX II Terminator	95,00 x 36,50	188-39028A

### iLBX II TERMINATOR MODULE


Each **iLBX II backplane** is supplied complete with one terminator module which is rear mounted at right angles to the backplane at the opposite end to slot position "0".

### REMOTE INTERFACE PANEL

The **Remote Interface Panel** is a single slot backplane for use in the lower position of slot position "0" of the Central Services Module. Wired connections to the appropriate points in the Multibus II System can be easily made as it has three signal lines tracked out to a pin header assembly.

These signals are: ACLO - A.C. Low  
CRST - Cold start  
WRST - Warm start

### REMOTE INTERFACE PANEL





REMOTE PANEL INTERFACE **Ordering information**

Description	Dimensions (mm)	Order code
Remote Panel Interface	128,55 x 19,46	110-42777A

## MULTIBUS II EXTENDER BOARDS

### FEATURES

- Reliability of multilayer construction using balanced five layer design
- Solder resist protection on outer layers
- Patented earth guard tracking
- Signal pin-out identification silk screened onto outer layers
- Jumper links provided to allow signal line interrogation
- Facility for logic analyser or "stub" terminator connection
- Card ejector/support mechanism provided
- Conversion kit for combining iPSB and iLBX II extender boards to 6U high



### MULTIBUS II EXTENDER BOARDS

#### Ordering information

Description	Order code
iPSB Extender board	34-39022F
iLBX II Extender board	34-39026A
6U Conversion kit	188-39120J

A range of Multibus II Microracks are available to special order only.

For further information contact VERO Electronics.


For a compatible range of general purpose extender cards, please refer to Section 8 of this publication

# STEBus BACKPLANES, TERMINATORS AND EXTENDERS

## STEBus BACKPLANES

### FEATURES


- Fully conforms to the STEbus specification IEEE 1000
- Available in a wide range of backplane slot widths
- Pick-up positions provided by pin header for SYSRST, ATNRQO, TFRERR, 0V and +5V
- Connector rows "a" and "c" fully bussed and terminated
- Constant characteristic impedance of signal track achieved with board construction
- Off-board termination
- Fully assembled using high reliability IEC 603-2 press-fit connectors
- Double sided or multilayer construction dependent upon slot width
- Patented earth guard tracking arrangement on multilayer designs
- Additional 96 / 96 way rear plug-up connector provided for remote diagnostics
- 3 to 10 slot backplanes: double sided construction
- 14 to 21 slot backplanes: multilayer construction



## STEBus TERMINATOR MODULE


### FEATURES

- 3 layer multilayer construction
- Small, 4HP wide detachable module
- Active termination design
- Rear pluggable and reversible
- Max. 25mm protrusion from backplane
- All 49 signal lines terminated via a 270 Ω series resistor
- Four signal lines diode clamped



### Ordering information

Description	Order code
Terminator module	161-42790E



### BOARD SPECIFICATION - DOUBLE SIDED BACKPLANES

Copper clad epoxy glass to BS 4584  
EP-GC-CU3(FR4)

Nominal thickness: 1,6mm  
Base copper thickness: 35 μm  
Finish: Plated copper 30 μm average  
Tin lead 5 μm min.

### BOARD SPECIFICATION - MULTILAYER BACKPLANES

Dielectric Epoxy Glass to BS 4584  
EP-GC-CU-3(FR4)

Nominal thickness: 2,4mm  
Base copper thickness: 35 μm  
Finish: Plated copper 30 μm average  
Tin lead 5 μm min.  
Total 70 μm - outside layers only

Note: All STEbus bare boards are UL94 V-0 recognised components. File number E116551

### STEBus DOUBLE SIDED BACKPLANES

### Ordering information

No. of positions	Board dimensions width x length(mm)	No. of Layers	Order code
3 slot	128,55 x 55,04	2	159-56138D
4 slot	128,55 x 75,36	2	159-56140B
5 slot	128,55 x 95,86	2	159-52886A
7 slot	128,55 x 132,51	2	159-42792K
10 slot	128,55 x 193,47	2	159-42639G

### STEBus MULTILAYER BACKPLANES

### Ordering Information

No. of positions	Board dimensions width x length(mm)	No. of Layers	Order code
14 slot	128,55 x 274,75	5	161-42794D
21 slot	128,55 x 416,99	5	161-42796J

## STANDARD AND SUPER EXTENDER BOARDS

### FEATURES

- Standard version - double sided
- Super version - multilayer
- Jumper linked access to each signal line
- Signal resist protection on outer layers
- Signal pin-out identification silk screened onto outer layers
- Facility for logic analyser or "stub" terminator connection

In order to address the widely differing applications of the STEbus, VERO Electronics has designed two types of extender board - a double sided, standard version for basic, low cost applications and a multilayer, super version for high performance, sophisticated applications.



### EXTENDER CARDS

### Ordering information

Description	Board dim. W x L (mm)	No. of Layers	Order code
Standard	100,00 x 305,24	2	159-42787K
Super	100,00 x 305,24	3	161-53172B
6U conversion kit	-	2	188-27642E

A range of STEbus Microracks are available to special order only. For further information contact VERO Electronics.

## G-64 BUS

### FEATURES

- Fully conforms to G-64 bus specification, Revision 02.Nov.1984.
- Reliability of double sided PTH board with solder resist protection
- Available in five standard backplane slot widths
- Completely assembled using high reliability press-fit IEC 603-2 (DIN 41612) type "B" connectors
- Board construction allows constant characteristic impedance of signal tracks
- Full ground plane screen
- 6,3mm tabs provided for power pick-up



The backplane is supplied completely with a -5V, voltage regulator already assembled.

### BOARD SPECIFICATION

Double sided copper clad epoxy glass to  
BS 4584 EP-GC-CU-3(FR4)

Nominal thickness: 1.6 mm  
Base copper thickness: 35 µm  
Finish: Plated copper 30 µm average  
Tin lead 5 µm min.  
Total 70 µm

Note:bare boards are UL94 V-0 recognised components. File number E116551.



### G-64 BUS

### Ordering information

No. of slots	Backplane dim. width x length	Order code
4	128,55 x 82,7	162-53124H
8	128,55 x 164,0	162-42807G
12	128,55 x 245,0	162-42808D
16	128,55 x 326,3	162-42809A
20	128,55 x 407,6	162-53125E

## G-96BUS MULTILAYER BACKPLANES

### FEATURES

- Fully conforms to G-96 specification, revision 02 - November 1984
- Reliability of multilayer construction with solder resist protection on both sides
- Available in five standard backplane widths
- Completely assembled using high reliability press-fit IEC 603-2 (DIN 41612) type C connectors
- On-board passive termination
- Board construction allows for constant characteristic impedance of signal tracks
- 6,3 mm tabs provided for power pick-up

The connector pin definitions are so arranged as to allow a mixture of G-64 and G-96 boards within a G-96 system (a revised connector was introduced 1st January 1985 to ensure compatibility).



### BOARD SPECIFICATION

Double sided copper clad epoxy glass to  
BS 4584 EP-GC-CU-3(FR4)

Nominal thickness: 2,4 mm  
Base copper thickness: 35 µm  
Finish: Plated copper 30 µm average  
Tin lead 5 µm min.  
Total 70 µm

Note:bare boards are UL94 V-0 recognised components. File number E116551.

A range of G-64bus and G-96bus Microracks are available to special order only.  
For further information contact VERO Electronics.



### G-96 BUS

### Ordering information

No. of slots	Backplane dim. width x length	Order code
4	128,55 x 88,95	410-59956L
8	128,55 x 170,23	410-59960C
12	128,55 x 251,51	410-59964B
16	128,55 x 332,79	410-59968A
20	128,55 x 414,07	410-59972D