

Nylon Tubing Series T/TIA **RoHS**

For general pneumatic tubing, Nylon tubing

Max. Operating Pressure



How to measure the minimum bending radius.



At a temperature of 20°C, bend the tubing into a U shape. Fix one end and gradually move the other end closer. Measure 2R at the point where the outside diameter's rate of change is 10%.

🗥 Precautions

Be sure to read before handling. Refer to front matter 56 for Safety I I Instructions and pages 13 to 16 for I Fittings and Tubing Precautions.

- 1. Applicable for general industrial water. Please consult with SMC if using other kinds of fluid. Surge pressure must be under the max. operating pressure. If the surge pressure exceeds the maximum operating pressure, it will result in damage to fittings and tubes.
- 2. Please exercise caution when using this item in a clean room. There is a possibility of plasticizer and other materials precipitating on the tube surface and detracting from the cleanliness level of the room.


Model							•	<u> </u>	m roll	\Box —	100 m	roll (T	1613 is	s reel.)
							Tu	bing s	ize					
					ic size	<u>`</u>	<u> </u>	1				e (Sei		· ·
Mod		T0425	T0403									TIA07		
Tubing O.D	()	4	4	6	6	8	10	12	16	3.18	4.76	6.35	9.53	12.7
Tubing I.D.	(mm)	2.5	3	4	4.5	6	7.5	9	13	2.18	3.48	4.57	6.99	9.56
Black (B)		-•		-•	-•	-•	-•	-•	-•					
White (W)		-•		-•		-•	-•	-•	-•					
Red (R)														
Blue (BU)			_		_	-+-	-+-		_		_	_	_	_
Yellow (Y)														
Green (G)									_					_
			1								Nomin	al size	e (inch)
		5⁄32"				5⁄16"				1⁄8 "	³ ⁄16"	1⁄4 "	3⁄8 "	1/2 "
										Nominal	1			
										size (mm)				
Specific	ations	5								3.2				
Fluid		Air/Water												
	20°C or less		2.0	3.0	2.0	2.0	2.0	2.0	1.6	2.3	2.3	2.3	2.3	2.3
	40°C	2.3	1.4	2.1	1.4	1.4	1.4	1.4	1.1	1.6	1.6	1.6	1.6	1.6
pressure Note 1) (MPa)	60°C	1.65	1.0	1.5	1.0	1.0	1.0	1.0	0.8	1.15	1.15	1.15	1.15	1.15
(IVIFa)	80°C 100°C	1.35	0.8	1.25	0.8	0.8	0.8	0.8	0.65	0.95	0.95	0.95	0.95	0.95
Applicable fitting		1.2	0.75	1.1	0.75	0.75	0.75	0.75	0.6	0.85		0.85 iature	0.85	
Min. bending	Min. bending radius	13	20	24	30	40	50	60	100	15	25	30	50	65
radius (mm) Note 3)	Bending value (Reference)	10	15	18	23	30	40	45	75	12	20	23	40	48
Operating temp	()			4	0 to ··	10000	Wote) +70°		froori	ng)		
Material	erature wole i)			-4	0 10 +	100°C	,	lylon 1		J (110	neezi	ny)		
material							IN	iyi011 I	۲					

Note 1) Be sure to operate under the maximum operating pressure conditions using the lower maximum operating specification of either the tubing or fittings.

Note 2) Mount an inner sleeve when using metal One-touch fittings in high-temperature environments of 60°C or more. Use self-align fittings at a temperature of 60°C or less. Note 3) The minimum bending radius is the representative value measured as shown in the left figure.

• Use a tube above the recommended minimum bending radius.


- The tubing may be bent if used under the recommended minimum bending radius. Therefore, refer to the refraction value and make sure that the tubing is not bent or flattened. • Please note that the refraction value is not warranted because of the value when 2R is measured
 - by the method in the left figure if the tubing is bent or flattened, etc.



Soft Nylon Tubing Series TS/TISA **RoHS**

For general pneumatic tubing Pliable soft nylon tubing

Max. Operating Pressure



Be sure to read before handling. Refer to front matter 56 for Safety Instructions and pages 13 to 16 for Fittings and Tubing Precautions.

▲ Caution

- 1. Compatible with water due to a change in materials. Compatible fluid types are printed on the tube body for differentiation, so please be sure to check this. Note) If using the previous TS/TISA series with "water", the tube may shrink and cause air leakage or the tube may fall out.
- 2. The products which changed the material are applicable for general industrial water. Please contact SMC if using other kinds of fluid. Surge pressure must be under the max. operating pressure. If the surge pressure exceeds the maximum operating pressure, it will result in damage to fittings and tubes.
- 3. Please exercise caution when using this item in a clean room. There is a possibility of plasticizer and other materials precipitating on the tube surface and detracting from the cleanliness level of the room.



How to measure the minimum bending radius At a temperature of 20°C, bend the tubing into a U shape. Fix one end and gradually move the other end closer. Measure 2R at the point where the outside diameter's rate of change is 10%.

Made to Order

			Tubing size												
				ric size					Inch siz						
	odel	TS0425	TS0604		TS1075	TS1209	TS1612								
	O.D. (mm)	4	6	8	10	12	16	3.18	4.76	6.35	9.53	12.7			
Tubing	I.D. (mm)	2.5	4	6	7.5	9	12	2.18	3.48	4.57	6.99	9.56			
Blac	ck (B)	-•-	-•-	-•-	-•-	-•-	-•-								
Whi	te (W)		— • —	— • —	-•-	-•-	-•	_ _	_ _		_ + _				
Red	(R)	⊢ •	_ _		_ — •	_ _--						_			
Blue	e (BU)										_				
Yell	ow (Y)	— •	_ • _		_ + _			_	_			_			
Gre	en (G)		_ •	_ _ •	_ _	_ _•		_	_			_			
		5/32 "		5/16 "				1/8 "	Nomina 3/16 "	al size (1⁄4 "	inch) 3⁄8 "	1/2 "			
Speci	fication							Nominal size (mm) 3.2							
Fluid															
						Air/Wa	ater Note	1)							
Max.	20°C or less	2.0	1.7	1.3	1.3	Air/Wa 1.3	ter ^{Note} 1.3	¹⁾ 1.3	1.3	1.3	1.3	1.3			
Max. operating	40°C	1.4	1.2	0.9	0.9	1.3 0.9	1.3 0.9	1.3 0.9	0.9	0.9	0.9	0.9			
Max. operating pressure	40°C 60°C	1.4 1.0	1.2 0.85	0.9 0.65	0.9 0.65	1.3 0.9 0.65	1.3 0.9 0.65	1.3 0.9 0.65	0.9 0.65	0.9 0.65	0.9 0.65	0.9 0.65			
Max. operating pressure MPa	40°C 60°C 80°C	1.4 1.0 0.8	1.2 0.85 0.65	0.9 0.65 0.5	0.9 0.65 0.5	1.3 0.9 0.65 0.5	1.3 0.9 0.65 0.5	1.3 0.9 0.65 0.5	0.9 0.65 0.5	0.9 0.65 0.5	0.9 0.65 0.5	0.9 0.65 0.5			
Max. operating pressure MPa Note 2)	40°C 60°C 80°C 100°C	1.4 1.0 0.8 0.6	1.2 0.85 0.65 0.45	0.9 0.65 0.5 0.35	0.9 0.65 0.5 0.35	1.3 0.9 0.65 0.5 0.35	1.3 0.9 0.65 0.5 0.4	1.3 0.9 0.65 0.5 0.35	0.9 0.65 0.5 0.35	0.9 0.65 0.5 0.35	0.9 0.65 0.5 0.35	0.9 0.65			
Max. operating pressure MPa Note 2) Applicable	40°C 60°C 80°C 100°C e fittings Note 2) 3)	1.4 1.0 0.8 0.6 0	1.2 0.85 0.65 0.45 ne-touc	0.9 0.65 0.5 0.35 h fitting:	0.9 0.65 0.5 0.35 s, Insert	1.3 0.9 0.65 0.5 0.35 fittings,	1.3 0.9 0.65 0.5 0.4 Self-ali	1.3 0.9 0.65 0.5 0.35 gn fitting	0.9 0.65 0.5 0.35 gs, Minia	0.9 0.65 0.5 0.35 ature fitt	0.9 0.65 0.5 0.35 ings	0.9 0.65 0.5 0.35			
Max. operating pressure MPa Note 2) Applicable Ilin. bending	40°C 60°C 80°C 100°C e fittings Note 2) 3) Win. bending radius	1.4 1.0 0.8 0.6 0 15	1.2 0.85 0.65 0.45 ne-touc 23	0.9 0.65 0.5 0.35 h fittings 45	0.9 0.65 0.5 0.35 s, Insert 55	1.3 0.9 0.65 0.5 0.35 fittings, 65	1.3 0.9 0.65 0.5 0.4 Self-ali 90	1.3 0.9 0.65 0.5 0.35 gn fitting 18	0.9 0.65 0.5 0.35 gs, Minia 27	0.9 0.65 0.5 0.35 ature fitt 30	0.9 0.65 0.5 0.35 ings 55	0.9 0.65 0.5 0.35 65			
Max. operating pressure MPa Note 2) Applicable Min. bending radius mm. Note 4	40°C 60°C 80°C 100°C e fittings Note 2) 3) Win. bending radius Bending value (Reference)	1.4 1.0 0.8 0.6 0 15	1.2 0.85 0.65 0.45 ne-touc	0.9 0.65 0.5 0.35 h fitting: 45 34	0.9 0.65 0.5 0.35 s, Insert 55 42	1.3 0.9 0.65 0.5 0.35 fittings, 65 50	1.3 0.9 0.65 0.5 0.4 Self-ali 90 70	1.3 0.9 0.65 0.5 0.35 gn fitting 18 12	0.9 0.65 0.5 0.35 gs, Minia 27 15	0.9 0.65 0.5 0.35 ature fitt 30 23	0.9 0.65 0.5 0.35 ings	0.9 0.65 0.5 0.35			
Max. operating pressure MPa Note 2) Applicable Ilin.bending radius mm Note 4	40°C 60°C 80°C 100°C e fittings Note 2) 3) Win. bending radius Bending value (Reference) remperature Note 2)	1.4 1.0 0.8 0.6 0 15	1.2 0.85 0.65 0.45 ne-touc 23	0.9 0.65 0.5 0.35 h fitting: 45 34	0.9 0.65 0.5 0.35 s, Insert 55 42	1.3 0.9 0.65 0.5 0.35 fittings, 65 50 , Water:	1.3 0.9 0.65 0.5 0.4 Self-ali 90 70	1.3 0.9 0.65 0.5 0.35 gn fitting 18 12	0.9 0.65 0.5 0.35 gs, Minia 27 15	0.9 0.65 0.5 0.35 ature fitt 30 23	0.9 0.65 0.5 0.35 ings 55	0.9 0.65 0.5 0.35 65			

● — 20 m roll □ — 100 m roll (TS1612 is reel.)

Model

 Note 1) Refer to the "Printing/Fluid".

 Note 2) Be sure to operate under the maximum operating pressure and operating temperature conditions using the lower specifications of either the tubing or fittings.

 Note 3) Mount an inner sleeve when using metal One-touch fittings in high-temperature environments of 60°C or more. Use self-align fittings at a temperature of 60°C or less.

 Note 4) The minimum bending radius is the representative value measured as shown in the left figure.


 • Use a tube above the minimum bending radius.

 • The tubing may be bent if used under the minimum bending radius.

 • Please note that the bending value is not warranted because of the representative value when 2R is measured by the method in the left figure if the tubing is bent or flattened, etc.

Printing/Fluid

	Print code						
Previous	SMC TS 0604 SOFTNYLON 6 x 4	Air					
NEW	SMC TS 0604 SOFTNYLON 6 x 4	Air/Water					
	How to Order						



(Please contact SMC for specifications in detail, dimensions, delivery and specifications other than those mentioned above.)

100 m	reel	Metric size	letric size and Inch size except ø16: Suffix "-X3" to the end of part number. Ex.) TS0425R-100-X3													
Longer	length reel	Metric size	letric size: Suffix "-X3" to the end of part number. Ex.) TS0425G-500-X3													
20 m roll Inch size: Suffix "-X4" to the end of part number. Ex.) TISA01BU-20-X4																
Made 1	to Order A	vailability	,													
Part no.	Length	TS0425*	TS0604*	TS0806*	TS1075*	TS1209*	TISA01*	TISA05*	TISA07*	TISA11*	TISA13*	Color				
	100 m reel	0	0	0	0	0	0	0	0	0	0	Black, White,				
ХЗ	150 m reel				0							Red, Blue,				
7.5	200 m reel			0								Yellow, Green				
	500 m reel	0	0									reliow, Green				
X4	20 m roll						0	0	0	0	0	Red, Blue, Yellow, Green				


2





Forgeneralairpressuretubing
Orange colour now becomes
standardSeries Table100m roll available for all
color typesModelTube O.D. (mm)

Burst Pressure Characteristics Curve




APrecautions

▲ Caution


①Applicable for general industry water. Consult SMC if using for other kinds of fluids. Surge pressure must be under the max. operating pressure. If exceeding that value, fitting may damaged and tubing may burst.

②The value of the max. operating pressure is at a temperature of 20°C. Refer to the burst pressure characteristics curve for other temperatures. Avoid abnormal temperature rises which may burst the tubing.

③The values of the min. bending radius is at a temperature of 20°C. Higher temperatures allows the tubing to bend more.



How to Order



blue, yellow, green) Suffix "-X3" to the end of part number.

Ex.) TIUB01Y-100-X3

* Consult SMC in case of ø16.

Suffix "-X3" to the end of part number. Ex.) TU0425B-500-X3

 Available 150m for ø10, 200m for ø8, 500m for ø4 and ø6. Contact SMC for other lengths.



Soft Polyurethane Tubing Series TUS




Suitable for piping in confined spaces **Extremely flexible** Soft Polyurethane Tubing

TUS related accessories Inner Sleeve

Series TJ

Reinforces soft polyurethane tubing. Insert an inner sleeve into soft polyurethane tubing when used with a One-touch fitting



One-touch fitting

Mode	
------	--

Model		
Part No.	Applicable tube model	Length
TJ-0425	TUS0425	18
TJ-0604	TUS0604	19
TJ-0805	TUS0805	20.5
TJ-1065	TUS1065	23
TJ-1208	TUS1208	24

Specifications

Material	C2700T (Nickel plated)
Wall thickness	0.2mm

A Precautions

▲ Caution

- ①Use nylon or polyurethane tubing for general industry water to prevent the tubing from coming out or bursting due to possibility of surge pressure generation.
- ⁽²⁾The value of the max. operating pressure is at a temperature of 20°C. Refer to the burst pressure characteristics curve for other temperatures. Avoid abnormal temperature rise which may burst the tubing.
- 3 The value of the min. bending radius is at a temperature of 20°C. Higher temperatures allows the tubing to bend more.
- 4 Use inner sleeve taking the removing force into consideration when used with Onetouch fittings.

Series Table				•: 20m rol	I □: 100m roll
Model	TUS0425	TUS0604	TUS0805	TUS1065	TUS1208
Tube O.D. (mm)	4	6	8	10	12
Tube I.D. (mm)	2.5	4	5	6.5	8
Black (B)	┣━━	<u></u>	_	<u></u>	— <u></u>
White (W)]∳	\	-	\	\
Red (R)	┨───∳───	-	\	-	\
Blue (BU)	┣━━	_	•	_	•
Yellow (Y)	│ ∳	•	•	•	•
Green (G)	┨───∳───	-	-	+	\
Opaque (N) (1)	┨∳	•	•	•	•
Yellow brown (YB)	├──∳ ──	•	•	•	\
	-				

Specifications

	<u>.</u>									
Fluid					A	ir				
Max. operating p	Max. operating pressure				0.6MPa at 20°C					
Burst pressure	R	efer to b	urst p	ressure	e chara	cteristi	cs curv	e.		
Applicable tube	One	-touch fi	itting,	Insert t	ube fitt	ing, Ho	ose nip	ole ⁽³⁾		
Min. bending rac	lius (mm) ⁽²⁾	8	15	;	1	5	2	2	2	9
Operating tempe	erature		-20 to +60°C (No freezing)							
Material			Polyurethane							
Tube drawing strenght N	Without inner sleeve)	6	0	8	5	11	0
(Using One-touch fitting)	With inner sleeve	80	230	D	25	50	30	00	48	30



Note1) Not clear but opague due to material.


Note2) Min. bending radius is measured as shown in the figure below.




Bend the tube into U-form at a temperature of 20°C. Fix one end and close loop gradually. Measure 2R when the tube breaks or is crushed.

Note3) Always use inner sleeve (Series TJ) in safety circuit or critical area.


How to Order



Burst Pressure Characteristics Curve




Hard Polyurethane Tubing Series TUH



Maximum effective area increased nearly 44% TUH/Standard Type

(Compared to polyurethane tubing TU0805: O.D. 8mm, length 1m)



Tubing in	Tubing inside diameter comparison (mm)									
Τι	ibing O.D. (ØD1)	4	6	8	10	12				
Tubing	TUH/Standard type	2.8	4.4	5.8	7.3	8.8				
I.D. (ØD2)	TUH/High pressure type	0.5	4	-	0.5	0				
1.0. (002)	TU	2.5	4	5	6.5	8				

Operating pressure 1.0MPa (at 20°C) TUH/High Pressure Type

Has the same operating pressure as series TS soft nylon tubing, and a bending radius equivalent to series TU polyurethane tubing.


Can be restored even after folding

Restoration is outstanding compared to nylon tubing, leaving no creases from folding.

Hard Polyurethane Tubing/Standard Type

Series TUH






At a temperature of 20°C bend the tubing into a U shape. Then with one side fixed, gradually close the other side and measure 2R at the point where the tubing folds or flattens, etc.

Series			• 20)m bundle 🛛 –	
Model	TUH0428	TUH0644	TUH0858	TUH1073	TUH1288
O.D. mm	4	6	8	10	12
I.D. mm	2.8	4.4	5.8	7.3	8.8
Black (B)					
White (W)	— <u></u>	_	— <u> </u>	— <u> </u>	— <u></u>
Blue (BU)	— <u>•</u> —	•	— <u></u>	— <u> </u>	— <u></u>
Translucent (N)	_	_	Ó	_	—— — —
Spacificatio	one				
Specificatio	ons				
Specification Fluid Max. operating	ons		Air Note 1)		
Fluid	ons		Air Note 1) 0.8MPa Note 2)	
Fluid Max. operating pressure	DNS	18		30	36
Fluid Max. operating pressure (at 20°C) Min. bending	10	18	0.8MPa Note 2	30	
Fluid Max. operating pressure (at 20°C) Min. bending radius mm	10	18	0.8MPa ^{Note 2}	30 aracteristics o	


Water cannot be used due to the occurrence of hydrolysis.

- Note 2) The maximum operating pressure is the value at 20°C. Refer to the burst pressure characteristic curve for other temperatures.
 - Furthermore, an abnormal temperature increase due to adiabatic compression can cause tubing to burst.
- Note 3) The minimum bending radius is measured at 20°C using the method shown in the figure at the left. At higher temperatures, breakage or flattening, etc., may occur at more than the minimum bending radius.

How to Order




Burst Pressure Characteristic Curve and Operating Pressure



Hard Polyurethane Tubing/High Pressure Type Series TUH





At a temperature of 20° C bend the tubing into a U shape. Then with one side fixed, gradually close the other side and measure 2R at the point where the tubing folds or flattens, etc.

Series \bullet – 20m bundle \Box – 100m bundle Model TUH0425 TUH0604 TUH0805 TUH1065 TUH1208 O.D. mm 4 6 8 10 12 2.5 I.D. mm 4 5 6.5 8 Black (B) White (W) Blue (BU) Translucent (N) Specifications Fluid Air Note 1) Max. operating pressure 1.0MPa Note 2) (at 20°C) Min. bending 10 20 27 35 15 radius mm **Burst pressure** Refer to the burst pressure characteristics curve. Operating temperature -20 to 60°C

Material

Note 1) Consult SMC regarding other fluids.

Water cannot be used due to the occurrence of hydrolysis.


Note 2) The maximum operating pressure is the value at 20°C. Refer to the burst pressure characteristic curve for other temperatures.

Polyurethane


Furthermore, an abnormal temperature increase due to adiabatic compression can cause tubing to burst.

Note 3) The minimum bending radius is measured at 20°C using the method shown in the figure at the left. At higher temperatures, breakage or flattening, etc., may occur at more than the minimum bending radius.

How to Order



Burst Pressure Characteristic Curve and Operating Pressure





Series TUH/Specific Product Precautions 1

Be sure to read before handling.

Precautions on Usage

A Caution

- Water cannot be used due to the occurance of hydrolysis. Use nylon or polyurethane tubing for general industrial water. Furthermore, consult SMC regarding use with any fluids other than air.
- The maximum operating pressure is the value at 20°C. Refer to the burst pressure characteristic curve for other temperatures.
 Furthermore, an abnormal temperature increase due to adiabatic compression can cause tubing to burst.
- 3. The minimum bending radius indicates the value at which the tubing will fold at a temperature of 20°C. At higher temperatures, the tubing may fold at more than the minimum bending radius.
- 4. Store away from direct sunlight in a location at no more than $40^\circ\text{C}.$



FEP Tubing (Fluoropolymer)

Heat resistance: 200°C It changes according to the operating pressure. Series TH Refer to the graph of the max. operating pressures on page 1. Applications **4** Colour variations General pneumatic piping Food Translucent Blue Black Red Semiconductor **Medical care** Automobile Size variations Certified to current **Food Sanitation** Metric size: ø4 to ø12 Legislation **One-touch fittings (Series KQ2,KJ)** • Applicable Miniature fittings (Series M,MS) (Hose nipple type) Ministry of Japanese Health and fittings **Insert fittings (Series KF)**

High Purity Fluoropolymer fittings (Series LQ)

SMC


9

Safety, directive #370,1959

FEP Tubing (Fluoropolymer) Series TH




How to measure the minimum bending radius.



At a temperature of 20°C, bend the tubing into a U shape. Fix one end and gradually move the other end closer. Measure 2R at the point where the outside diameter's rate of change is 5%.

Max. Operating Pressure



Note) The maximum operating pressure varies dependant on the I.D. bore size even if the O.D. is the same.

Series							●-20	m roll □-	100m roll
					Metri	c size			
Model		TH0402	TH0425	TH0604	TH0806	TH1075	TH1008	TH1209	TH1210
Tubing O.D.	(mm)	4	4	6	8	10	10	12	12
Tubing I.D. (mm)	2	2.5	4	6	7.5	8	9	10
Colour	Symbol								
Translucent	Ν		-•	-0-	-0-	-0-	-0-	-•	— b —
Red (Translucent)	R		_ — —	_ — —	_	_ —— —	_ — —	_	_
Blue (Translucent)	BU			_∳_	_∳_	_ —— —	_∳_	_∳_	_∳_
Black (Opaque)	в			_∳_		_∳_	_∳_		_∳_
			ninal size 32"	In	ch nominal si 5/16"	ize			
Specifica	atior	าร							
Fluid	Note 4)			Air,	Water No	^{te 1)} , Inert	gas		
Applicable	Note 2)			s: Series	-	Insert fit	tings: Se	ries KF	

fittings		,	ttings: Se : Series I		lose nipp	le type)					
Max. operating pressure		Refer to below "Max. Operating Pressure."									
Min. bending Note 3) radius (mm)	15	15 20 35 60 95 100 130									
Operating temperature	Air	Air, Inert gas: -20 to 200°C Water: 0 to 100°C (No freezing)									
Material		FEP	(Fluorina	ated Ethy	lene Prop	oylene Resin)					

Note 1) When using a fluid in liquid form, the surge pressure must not exceed the maximum operating pressure. A surge pressure higher than the maximum operating pressure can cause breakage of the fittings, or rupture of the tubing. Furthermore, an abnormal temperature increase due to adiabatic compression can also result in ruptured tubing. Note 2) Do not use in locations where the FEP tubing will move.

Be sure to operate under the maximum operating pressure conditions using the lower maximum operating specification of either the tubing or fittings.

After long term use or under high temperatures, some fittings leakage may occur due to material deterioration with age. Perform periodic inspections, and if any leakage is detected, replace with a new product immediately.

(Refer to maintenance part of "Tubing Precautions 1" on the page 7-156.) Refer to Best Pneumatics 4 in "Fittings and Tubing" for all other precautions.


For High Purity Fluoropolymer, refer to the precautions of CAT.ES70-17, "High Purity Fluoropolymer Fittings & Tubing."

Note 3) Minimum bending radius is measured as shown left as representative values.

Allow extra length when piping since the tubing may crush if bent more than the min. bending radius. Note 4) Consult SMC if using any other fluids.

How to Order

GSMC



10

A Chemical Resistance of the Fluoropolymer FEP Material

Chemicals in this table are inactive against FEP material Note 1), however physical properties may be effected by temperature or pressure change.

Please make sure that operating conditions do not cause problems since the use of FEP tubing under chemical environment is unsecured.

2-nitro-2-methyl propanol 2-nitrobutanol Pentabasic benzamide N-butvlamine N-octadecanol N-butvl acetate O-cresol **Di-isobutyl** adipate Acetophenone Acetone Alniline Abietic acid Sulphuric chloride Isooctane Liquid ammonia Ethyl alcohol Ethyl ether Ethylene glycol Ethylenediamine Zinc chloride Aluminum chloride Ammonium chloride Calcium chloride Sulphuric chloride Iron chloride (III) Benzoyl chloride Magnesium chloride Hydrochloric acid Chlorine (absolute) Aqua regia Ozone Hydrogen peroxide Natrium peroxide Gasoline Permanganate Formic acid **Xvlene** Chromic acid Chlorosulfonic acid Chloroform Paraffinum liquidum Allyl acetate Ethyl acetate Potassium Butyl acetate

Sodium hypochlorite Carbon tetrachloride Dioxane Cyclohexanone Cyclohexane Dimethyl ether Dimethylsulfoxide Dimethylformamide Bromine Deionized water Nitric acid Mercury Ammonium hydroxide Potassium hydroxide Sodium hvdroxide Cetane Soap, detergent Dibutyl sebacate Diethyl carbonate Tetrachloroethylene Tetrahydrofuran Tetrabromoethane Triethanolamine Trichloroethylene Trichloroacetic acid Toluene Naphtha Naphthalene Naphthol Lead Carbon dioxide Nitrogen dioxide Nitrobenzene Nitromethane Perchloroethylene Perphloroxylene Unsymmetrical dimethylhydrazine Hvdrazine Pinene Piperidine Glacial acetic acid (Acetic acid) Pyridine Phenol Phthalic acid

Dimethyl phthalate Hydrofluoric acid Naphthalene fluoride Nitrobenzene fluoride Furan Hexachlorethane Hexane Ethyl hexanoate Phenylcarbinol Benzaldehyde Benzonitrile Borax Boric acid Formic aldehyde (Formalin) Acrylic anhydride Acetic anhydride Methacrylic acid Allvl methacrvlate Vinyl methacrylate Methyl alcohol Methyl ethyl ketone Methylene chloride Sulphuric acid Phosphoric acid Iron phosphate (III) Tri-n-butyl phosphate Tricresyl phosphate

Note 1) "Inactive in chemistry terminology" means - not to cause any chemical reaction.

Reference cited: Teflon®, the fluoropolymer handbook, Manual for the chemical applications of Teflon®. Du Pond-Mitsui Fluorochemicals Co., Ltd.

Dybutyl phthalate

Teflon® is a registered trademark for the fluoropolymer produced by E.I du Pond de Nemours & Company (Inc.) and Du Pond-Mitsui Fluorochemicals Co., Ltd.



Selection

A Warning

1. Confirm the specifications.

The products appearing in this catalogue are designed for use only in compressed air systems (including vacuum).

Do not use outside the specified ranges of pressure, temperature, etc., as this may cause damage or malfunction. (Refer to specifications.)

SMC cannot assure the product quality when fluids other than air, water and inert gas are used.

Consult with SMC for details.

2. In case of using the product for medical care

This product is designed for use with compressed air system applications for medical care purposes. Do not use in contact with human bodily fluids, body tissues or transfer applications to a human living body.

▲ Caution

 Do not use in locations where the connecting threads and tubing connection will slide or rotate. The connecting theads and tubing connection will come apart under these conditions.

Use rotary type one-touch fittings (Series KS, KX) in cases where sliding or rotation will occur. Only air can be used as the operating fluid, when using rotary type one-touch fittings.

- 2. Use tubing at or above the minimum bending radius. Using below the minimum bending radius can cause breakage or flattening of the tubing.
- Never use the tubing for anything flammable, explosive or toxic such as, gas, fuel gas, or cooling mediums, since the contents can penetrate outward.

Mounting

A Caution

- 1. Before mounting confirm the model and size, etc. Also, confirm that there are no blemishes, nicks or cracks in the product.
- 2. When tubing is connected, consider factors such as changes in the tubing length due to pressure, and allow sufficient leeway.
- 3. Mount so that fittings and tubing are not subjected to twisting, pulling or moment loads. This can cause damage to fittings and flattening, bursting or disconnection of tubing, etc.
- 4. Mount so that tubing is not damaged due to tangling and abrasion. This can cause flattening, bursting or disconnection of tubing, etc.

Piping

[▲]Caution

1. Preparation before piping

Before piping is connected, it should be thoroughly blown out with air (flushing) or washed to remove chips, cutting oil and other debris from inside the pipe. Do not allow chips of the piping thread or the seal material to go in.

Air Supply

1. Types of fluid

This product is designed for use with compressed air. Consult SMC if a different fluid is to be used.

Consult SMC regarding products for use with general purpose fluids, to confirm which fluids can be used.

2. When there is a large amount of drainage.

Compressed air containing a large amount of drainage can cause the malfunction of pneumatic equipment. An air dryer or Drain Catch should be installed upstream from filters.

3. Drain management

If air filter drains are not flushed regularly, the drainage will flow downstream leading to the malfunction of pneumatic equipment.

In cases where the management of drain flushing will be difficult, the use of filters with automatic drains is recommended.

For details on the quality of compressed air mentioned above, refer to SMC's "Best Pneumatics" catalogue vol. 4.

Operating Environment

A Warning

- 1. Do not operate in locations in an explosive atmosphere.
- 2. Do not operate in locations where vibration or impact occurs.
- 3. In locations near heat resources, block off radiant heat.

Maintenance

Λ Caution


- 1. Check for the following during regular maintenance, and replace components as necessary.
 - a) Scratches, gouges, abrasion, corrosion
 - b) Leakage
 - c) Twisting, flattening or distortion of tubing
 - d) Hardening, deterioration or softness of tubing
- 2. Do not repair or patch the replaced tubing or fittings for reuse.
- 3. When using insert or miniature fittings over a long period, some leakage may occur due to age deterioration of the materials. Perform periodic inspections, and if any leakage is detected, correct the problem by additional tightening. If tightening becomes ineffective, replace the fittings with a new product immediately.

Polyurethane Coil Tubing Series TCU



For flexible tubing Compact piping possible

Burst Pressure Characteristics Curve




Specifications

Model	TCU 0425B-1	TCU 0425B-2	TCU 0425B-3	TCU 0604B-1	TCU 0604B-2	TCU 0604B-3	TCU 0805B-1	
Number of tubes	1	2	3	1	2	3	1	
Tube O.D. (mm)		4			6		8	
Tube I.D. (mm)		2.5			4 5			
Fluid				Air (1)				
Max. operating pressure (2)			0.8	MPa at 20	°C			
Burst prssure		Refe	er to press	ure charac	teristics cu	urve.		
Operating temperature		-20 to +60°C						
Material			Р	olyurethar	ie			
Colour				Black				

Note 1) Consult SMC if using for other fluids than air.

Note 2) Refer to burst pressure characteristics curve for other temperatures. Avoid abnormal temperature rises.

Dimensions



* Dimensions are changeable due to material.

	Made to Order (Consult SMC for detailed specifications, dimensions and delivery.) Change of coil turns, Color change (Max. operating length)																
100 L 100 C Tube fastener (Multi-tube only)																	
Spec.	Tube siz	ze (mm)	Coil (mm)			Max. operating			Spec.	Tube siz	ze (mm)	Coil (mm)	No. of	No. coil windings	Max. operating
Part No.	O.D.	I.D.	L	øD	tubes	per tube length	length (mm)		Part No.	\searrow	O.D.	I.D.	L	øD	tubes	per tube length	length (mm)
TCU0425□-1-N-X6			N X 4	18	1	3 to 90	L X 5.9 + 200		TCU0805	-1- <u>N</u> -X6	8	5	N X 8	31	1	3 to 90	L X 5.2 + 200
TCU0425□-2-N-X6	4	2.5	N X 8	28	2	3 to 90	L X 4.4 + 200		TCU0805	-2-N -X6	0	5	N X 16	42	2	3 to 40	L X 3 + 200
TCU0425□-3-N-X6			N X 12	28	3	3 to 63	L X 2.9 + 200		TCU1065	□-1- <u>N</u> -X6	10	6.5	N X 10	52	1	3 to 45	L X 5 + 200
TCU0604□-1-N-X6			N X 6	24	1	3 to 90	L X 5.3 + 200		TCU1065	-2-N-X6	10	0.5	N X 20	52	2	3 to 35	L X 3 + 200
TCU0604□-2-N-X6	6	4	N X 12	37	2	3 to 66	L X 3.8 + 200		TCU1208	□-1- <u>N</u> -X6	12	8	N X 12	67	1	3 to 35	L X 5 + 200
TCU0604□-3-N-X6			N X 18	37	3	3 to 44	L X 2.5 + 200		TCU1208	-2-N -X6	12	0	N X 24	67	2	3 to 30	L X 3 + 200

 $\Box \rightarrow B \text{ (Black), W (White), R (Red), BU (Blue), Y (Yellow), G (Green), C (Clear), YR (Orange)} \\ \boxed{\mathbb{N}} \rightarrow \text{Coil turns}$




Polyurethane Flat Tubing Series TFU



Compact piping possible

Burst Pressure Characteristics Curve



Specifications


Part No.	TFU 0425B-2	TFU 0425B-3	TFU 0604B-2	TFU 0604B-3	TFU 0805B-2	TFU 0805B-3		
Number of tubes	2	3	2	3	2	3		
Tube O.D. (mm)	4	1	6	6	6	3		
Tube I.D. (mm)	2	.5	4	4	Į	5		
Fluid	Air ⁽¹⁾							
Max. operating pressure (2)	0.8MPa at 20°C							
Burst prssure		Refer to b	urst pressur	e characteri	stics curve			
Operating temprature			20 to +60°C	(No freezing	g)			
Material			Polyur	ethane				
Colour		Black						
Min. bending radius (mm)	1	0	1	5	2	0		
Tube length per roll (m)			1	0				



Note1) Consult SMC if using for other fluids than air.

Note2) Refer to burst pressure characteristics curve for other temperatures. Avoid abnormal temperature rises.

How to Order



Made

Made to Order ——	(Consult SMC for detailed specifications, dimensions and delivery.)							
				●: 10)m roll ∆: 5	0m roll]: 100m roll	
1 Colour change (10m roll)	Mo	del	TFU0425	TFU0604	TFU0805	TFU1065	TFU1208	
Suffix "X4" to the end of part number.	Tube O.	D. (mm)	4	6	8	10	12	
Ex.) TFU0604BU-2-10-X4	Tube I.	D. (mm)	2.5	4	5	6.5	8	
• W: White, R: Red, BU: Blue, Y: Yellow, G: Green, C: Clear, YR: Orange (All tubes are same colour.)		2]			•	•	
		3	 \$	—— `	<u> </u>		•	
② Longer roll length (50m or 100m roll)	Number	4	├ ── ∲ ──	•	•	•		
Suffix "X3" to the end of part number. Ex.) TFU0425B-2-50-X3	of	5]•	•	•			
-	tubes	6	├ ──•	•	•			
③ Number of tubes (10m roll)		7	}∳					
Suffix "X4" to the end of part number. Ex.) TFU0604B-4-10-X4		8	├──∳──	•				

Flame Resistance (Equivalent to UL-94 Standard V-0)


FR Soft Nylon Tubing

Series TRS



Applicable for general air pressure and water in a spark atomosphere such as spotwelding. Flame resistance tube

Burst Pressure Characteristics Curve




APrecautions

▲ Caution

- ①Applicable for general industry water. Consult SMC if using for other kinds of fluid. Surge pressure must be under the max. operating pressure. If exceeding that value, fitting may be damaged and tubing may be burst.
- ②The value of the max. operating pressure is at a temperature of 20°C. Refer to the burst pressure characteristics curve for other temperatures. Avoid abnormal temperature rises which may burst the tubing.
- ③The value of the min. bending radius is at a temperature of 20°C and O.D. variable rate 10% max. In case that operating temperature is higher than 20°C, O.D. variable rate may be over 10% even if bending radius is within the specified range.

Series Table			• : 20m roll	□ : 100m roll
Model	TRS0603	TRS0805	TRS1065	TRS1208
Tube O.D. (mm)	6	8	10	12
Tube I.D. (mm)	3	5	6.5	8
Black (B)				•
White (W)		•		•
Red (R)		•		•
Blue (BU)		•	•	•
Green (G)				
Specifications		Air, V	Vater	
Max. operating pressure		,	at 20°C	
Burst pressure	Refer	to burst pressure	e characteristics of	curve.
Min. bending radius (mm)	17	19	27	32
Operating temperature	-20 to	+60°C (Water: 0) to 60°C)(No free	ezing)

How to Order



Flame Resistance (Equivalent to UL-94 Standard V-0) **FR Double Layer Tubing**

Series TRB

Suitableforairandwaterpipingin environments where sparks from spot welders, etc., may be a problem.

Double layer design using flame resistantresin(equivalenttoUL-94 Standard V-0) for outer layer.



Sariaa Tabla

Series	lable			●: 20m roll	□: 100m roll
Model		TRB0604	TRB0806	TRB1075	TRB1209
Inner tube	e O.D. (mm)	6	8	10	12
Inner tube	e I.D. (mm)	4	6	7.5	9
Outer laye	er thickness (mm)	1	1	1	1
	Black (B)	├ ─── ● ───	●	•	
(1)	White (W)				•
Outer	Red (R)	 	●	_	•
layer colour	Blue (BU)	<u> </u>	•	•	•
	Yellow (Y)	<u> </u>	•	•	•
	Green (G)	 	•	•	•
	mum bending ⁽⁴⁾ ıs (mm)	15	28	35	45

Air. Water (2)

1.0MPa at 20°C

Refer to burst pressure characteristics curve. –20 to +60°C

(Water: 0 to 60°C) (No freezing) Nylon 12

PVC (Equivalent to UL-94 Standard V-0)

Note2) Applicable for general industry water. Consult SMC if using for other kinds

Note3) Refer to burst pressure characteristics curve for other temperatures.

Note4) The value for a temperature of 20°C and O.D.variable rate 10% max.

of fluid. Surge pressure must be under the max. operating pressure.

Specifications

Burst pressure

Ambient and fluid temperature

Material

Max. operating pressure (3)

Inner tube


Outer laver

Fluid


	Inner tube
	Outer layer
ED also de la Jacobia de de la se	

FR double layer tubing (sectional view)

Burst Pressure Characteristics Curve



How to Order



Note1) The colour of all inner tube is black.

Avoid abnormal temperature rises.


FR Double Layer Tubing Series TRB

How to Install to One-touch Fitting

A Caution

Length of tube to be inserted into One-touch fitting is indicated on the outer layer of TRB tubing.

Cut the tube according to this indication. (Procedure①) and then strip off the outer layer. (Procedure②) for installing tube.



A Precautions


▲ Caution

- ①Applicable for general industrial water. Consult SMC if using for other kinds of fluid. Surge pressure must be under the max. operating pressure. If exceeding that value, fitting may be damaged and tubing may be burst.
- ②The value of the max. operating pressure is at a temperature of 20°C. Refer to the burst pressure characteristics curve for other temperatures. Avoid abnormal temperature rises which may burst the tubing.
- (3) The value of the min. bending radius is at a temperature of 20°C and O.D. variable rate 10% max. In case that operating temperature is higher than 20°C, O.D. variable rate may be over 10% even if bending radius is within the specified range.

Flame Resistant (Equivalent to UL-94 Standard V-0) FR Double Layer Polyurethane tubing

Series TRBU






Sectional view of FR double layer tube

Series Table

● - 20m bundle 🗌 - 100m reel



Specifications

F	luid	Air, Water Note 2)		
Maximum pressure (a		0.8MPa {8.2kgf/cm ² }		
Burst pressure		Refer to burst pressure characteristics curve		
Ambient ar temperatur		-20 to 60°C For water 0 to 40°C (without freezing)		
Materials		Polyurethane		
waterials	External layer	PVC (equivalent to UL-94 standard V-0)		


Note 1) The colour of all internal tubes is black.

Note 2) Can be used with general industrial water. Contact SMC if used with other fluids. Also keep surge pressure at or below the maximum operating pressure.


Note 3) In case of other temperatures, refer to the burst pressure characteristics curve. In addition, operate so that abnormal temperature rise due to adiabatic compression does not occur.

Note 4) Indicates the bending value of the tubing at a temperature of 20°C.

How to Order



Burst Pressure Characteristics Curve and Operating Pressure






Installation on One-touch Fittings

A Caution

Since the pitch length for installation on a One-touch fitting is indicated on the external layer of TRBU tubing, cut the tubing according to this indication (Step 1), strip off the external layer only (Step 2), and then install on the One-touch fitting.



Precautions on Useage

A Caution

- Useage is possible with general industrial water. Contact SMC if product will be used with other fluids. Also, keep surge pressure at or below the maximum operating pressure. If surge pressure exceeds the maximum operating pressure, this can cause damage to fittings or bursting of the tubing.
- 2. The maximum operating pressure is the value when at 20°C. In case of other temperatures, refer to the burst pressure characteristics curve. Furthermore, bursting of the tubing can be caused by an abnormal temperature rise due to adiabatic compression.
- 3. The minimum bend radius indicates the bending value of the tubing at a temperature of 20°C. The tubing may bend beyond the minimum bend radius at higher temperatures.
- 4. Tubing should be stored in a location out of direct sunlight and at 40°C or below.



Antistatic Tubing

Series **TA**


Conductive tubing prevents troubles caused by static electricity. Antistatic soft nylon tubing/Series TAS

For air pressure piping to product or assembly while preventing static electricity.

Flame resistant tube (UL-standard, V-0)




Burst Pressure Characteristics Curve



Series Table				•:2	0m roll □:	100m roll
Model	TAS3222	TAS0425	TAS0604	TAS0805	TAS1065	TAS1208
Tube O.D. (mm)	3.2	4	6	8	10	12
Tube I.D. (mm)	2.2	2.5	4	5	6.5	8
Black (B)	— • —		_	— <u></u>	_	— • —
Specifications Max. operating pressure ⁽¹⁾			1.2MPa at	2000		
	-					
Burst pressure		Refer to burs	st pressure o	characteristic	cs curve.	
Min. bending radius (mm) ⁽²⁾	12	12	15	19	27	32
Operating temperature			0 to 40	0°C		
Material	Conductiv	e nylon + Fl	lame resista	nt nylon (UL	-94standard	l, V-0)
Surface resistance			10 ⁴ to 1	0 ⁷ Ω		
Note1) Refer to burst pres Avoid abnormal te Note2) The value at term	emperature ri	ses.		•		

Note2) The value at temperature of 20°C and O.D. variable rate 10% max.

How to Order




Antistatic polyurethane tubing/Series TAU

For air pressure piping to product or assembly while preventing static electricity.

Flexible tube



Burst Pressure Characteristics Curve



Model	TAU3220	TAU0425	TAU0604	TAU0805	TAU1065	TAU1208			
Tube O.D. (mm)	3.2	4	6	8	10	12			
Tube I.D. (mm)	2	2.5	4	5	6.5	8			
Black (B)	-••		-•						
Specifications									
Max. operating pressure ⁽¹⁾		0.9MPa at 20°C							
Burst pressure	F	Refer to burs	st pressure o	haracteristic	cs curve.				
Min. bending radius (mm) ⁽²⁾	10	10	15	20	27	35			
Operating temperature			0 to 40	°C					
Material		Co	nductive po	lyurethane					
Surface resistance			10 ⁴ to 1	0 ⁷ Ω					
Note1) Refer to burst pres Avoid abnormal te Note2) The value at temp	mperature ris	ses.	e for other te	mperatures.					
How to Order									
TAU1	065	B – 1	00						

Indication of tube model

Length per roll Colour indication Symbol Roll size Symbol Colour 20 20m roll в Black 100 100m roll

