3 Port Solenoid Valve

Metal Seal / Rubber Seal








Compact, High Flow

		Valve width	Flow characteristics			
	Series	(mm)	Metal seal	Rubber seal		
		()	C [dm ³ /(s·bar)]	C [dm ³ /(s·bar)]		
rted	VQZ100	10		0.56 (Poppet)		
Body ported	VQZ200	15	1.3	1.7		
Bod	VQZ300	18	2.4	3.0		
nted	VQZ100	10		1.0 (Poppet)		
Base mounted	VQZ200	15	2.0	3.0		
Base	VQZ300	18	3.2	4.1		




VQZ100/200/300

Solenoid Valve Variations



Manifold

Body Ported



			Piping specit	Applicable	A		
Series	Base model	Piping	Bor	e size	solenoid	Applicable stations	
		direction	1(P), 3(R)	2(A)	valve	5.45110	
VQZ100	VV3QZ12-□□□	Тор	Rc 1/8 C3 (for ø3.2) C4 (for ø4) C6 (for ø6) M5 (M5 thread)		VQZ115	2 to 20 stations	
VQZ200	VV3QZ22-□□□	Тор	Rc 1/8	C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ2□2	2 to 20 stations	
VQZ300	VV3QZ32-□□□	Тор	Rc 1/4	C6 (for Ø6) C8 (for Ø8) C10 (for Ø10) Rc 1/4	VQZ3□2	2 to 20 stations	


Base Mounted



			Piping specif	Applicable	A		
Series	Base model	Piping	Bor	e size	solenoid	Applicable stations	
		direction	1(P), 3(R)	2(A)	valve		
VQZ100	VV3QZ15-□□□	Side/ top	Rc 1/8	C3 (for ø3.2) C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ115	2 to 20 stations	
VQZ200	VV3QZ25-□□□	Side	Rc 1/4	C4 (for ø4) C6 (for ø6) C8 (for ø8) Rc 1/8	VQZ2□5	2 to 20 stations	
VQZ300	VV3QZ35-□□□	Side	1(P) port Rc 3/8 3(R) port Rc 1/4	C6 (for Ø6) C8 (for Ø8) C10 (for Ø10) Rc 1/4	VQZ3□5	2 to 20 stations	

Manifold Options

Body Ported




P.14

DIN rail AXT100-DR-□



P.14

Silencer (for EXH port)



P.14

P.24

Base Mounted


Blanking plate assembly
VVQZ100-10A-5
(for VQZ100)
VVQZ200-10A-5
(for VQZ200)
VVQZ300-10A-5
(for VQZ300)
P.31

Blanking plug
KQ2P-23
KQ2P-04
KQ2P-06
KQ2P-08
KQ2P-10
P.31

DIN rail
AXT100-DR
P.31

Silencer

Silencer (for EXH port)



P.31

Port plug VVQZ100-CP (for VQZ100)



P.31




Body Ported

Plug Lead Unit

3 Port Solenoid Valve

Series VQZ100/200/300Single Unit $(\epsilon_{\text{[Option]}})$

VQZ100 / How to Order Valve




Note) For applicable one-touch fitting and silencer models for this valve series, refer to back page 4.



Body Ported Series VQZ100/200/300

VQZ200/300 / How to Order Valve





Note 1) Optio

KR Note 1, 2

Note 2) For details on external pilot type, refer to page 15. Note 3) For AC specification power consumption, refer to page 3.

High pressure/External pilot type

⚠ Caution

Use standard (DC) specification for continuous duty.

(Metal seal type only)

Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC [115 VAC] (50/60 Hz)
4	220 VAC [230 VAC] (50/60 Hz)
5	24 VDC
6	12 VDC

(0.9 W)

Note 1) Standard lead wire length: 300 mm

Note 2) For AC voltage valves there is no "S" option. It is already built-in to the rectifier circuit.

without

With light/

suppressor

YZ: DIN

With light/

suppressor

surge voltage

terminal

surge voltage

connector

with lead wire

terminal

connector

(DC speci

without

With surge

suppressor

voltage

With light/

suppressor

surge voltage

without

With light/

suppressor

YOS: DIN Note 2) YS: DIN Note 2)

surge voltage

terminal

fication)

With surge

suppressor

voltage

(DC speci-

connector



fication)

Y: DIN

terminal

with lead

wire

With light/

suppressor


YO: DIN

terminal


without

connector

surge voltage







Specifications

			1			
Valve construction	Metal seal	Rubber seal	VQZ100 (Poppet seal)			
Fluid	Air, Inert gas					
Max. operating pressure (MPa)	0.7 (High pressure type: 1.0)	0.7	0.7 (High pressure type: 1.0)			
Min. operating pressure (MPa)	0.1	0.15	0.15			
Ambient and fluid temperature (°C)	-10 to 50 (No freezing)					
Max. operating frequency (Hz)	20	5	20			
Pilot exhaust method	Individual exhaust Common exhaus					
Lubrication	Not required					
Manual override	Push typ	e, Locking type (Tool r	required)			
Mounting orientation	Free					
Impact/Vibration resistance (m/s²) Note 1)	150/30					
Enclosure	Dustproof (DIN terminal: IP65 Note 2)					



* Based on IEC60529

Note 1) Impact resistance: No malfunction occurred when it is tested with a drop tester in the axial direction and at the right angles to the main valve and armature in both energized and deenergized states every once for each condition. (Value in the initial state)

Vibration resistance: No malfunction occurred in one sweep test between 45 and 2000 Hz. Test was

performed to axis and right angle directions of the main valve and armature when pilot signal is ON and OFF. (Value in the initial state)


Note 2) When IP65 compliant DIN terminals are selected: VQZ₃²□2□-□Y□□W1-□□

Solenoid Specifications

Options

High speed response type
High pressure type (Metal seal type only)
External pilot type*

^{*} For details on external pilot type, refer to page 15.



(For details, refer to page 34.)

Symbol	mbol Description			
X30	Pilot valve common exhaust			
X90 Main valve fluoro-rubber				
X113	All fluoro-rubber			

Electrical entry		Grommet (G) M-type plug connect L-type plug connector (L) DIN terminal (Y)			
		G, L, M	Υ		
Coil rated voltage	DC	24	, 12		
(V)	AC 50/60 Hz	100, 110,	200, 220*		
Allowable voltage fluct	uation	±10% of rat	ted voltage*		
	Standard	0.35 [(With light: 0.4 (DIN	l terminal with light: 0.45)]		
Power consumption (W)	High speed response, high pressure	0.9 [(With light: 0.95 (DIN terminal with light: 1.0)]			
	100 V	0.78 (With light: 0.81)	0.78 (With light: 0.87)		
Apparent power	110 V [115 V]	0.86 (With light: 0.89) [0.94 (With light: 0.97)]	0.86 (With light: 0.87) [0.94 (With light: 1.07)]		
(VA)*	200 V	1.18 (With light: 1.22)	1.15 (With light: 1.30)		
	220 V [230 V]	1.30 (With light: 1.34) [1.42 (With light: 1.46)]	1.27 (With light: 1.46) [1.39 (With light: 1.60)]		
Surge voltage suppres	sor	Varistor			
Indicator light		LED (Neon light when AC with DIN terminal)			



- * In common between 110 VAC and 115 VAC, and between 220 VAC and 230 VAC.
- \ast For 115 VAC and 230 VAC, the allowable voltage is –15% to +5% of rated voltage.

Flow Characteristics

				Flow characteristics					Response time (ms) Note 1)					
Series	Valve construc- tion	Model		1→2 (1→2 (P→A) 2→3 (A→R)			Standard: Speed		High	AC	Note 2) Weight		
				C [dm³/(s•bar)]	b	Cv	C [dm³/(s•bar)]	b	Cv	0.35 W response		0.9 W	ΑΟ	(g)
VQZ100	N.C. valve	Poppet	VQZ115	0.59	0.44	0.17	0.56	0.30	0.14	10 or less	_	13 or less	22 or less	24
	N.C. valve N.O. valve	Metal seal	VQZ212	1.2	0.21	0.30	1.3	0.24	0.33	22 or less	14 or less	18 or less	34 or less	
VQZ200		Rubber seal	VQZ232	1.6	0.33	0.39	1.7	0.37	0.45	22 or less	15 or less	_	36 or less	57
VQZZUU		Metal seal	VQZ222	1.2	0.25	0.31	1.3	0.20	0.31	22 or less	14 or less	18 or less	34 or less	
		Rubber seal	VQZ242	1.6	0.36	0.40	1.7	0.36	0.45	22 or less	15 or less	_	36 or less	
	N.C.	Metal seal	VQZ312	2.7	0.18	0.62	2.4	0.28	0.56	22 or less	17 or less	22 or less	34 or less	
VQZ300	valve	Rubber seal	VQZ332	3.5	0.34	0.87	3.0	0.33	0.72	33 or less	25 or less	_	57 or less	93
VQ2300	N.O.	Metal seal	VQZ322	2.6	0.21	0.59	2.2	0.16	0.49	22 or less	17 or less	22 or less	34 or less	
	valve	Rubber seal	VQZ342	3.5	0.38	0.88	2.9	0.27	0.69	33 or less	25 or less	_	57 or less	



Note 1) Based on JIS B 8375-1981 (Supply pressure: 0.5 MPa; with light/surge voltage suppressor: clean air) Response time values will change depending on pressure and air quality.


Note 2) Weight for threaded connection




Body Ported Series VQZ100/200/300

Construction

VQZ100 Poppet type








Component Parts


No.	Description	Material	Note
1	Body	Resin	
2	Spool valve	Aluminum/HNBR	
3	Pilot valve assembly	_	
4	P, R port	Resin/Aluminum	VQZ100-12A (Standard) VQZ100-12B (External pilot type)

VQZ200/300 Metal seal type













Rubber seal type









Component Parts

No.	Description	Material	Note				
1	Body	Aluminum die-casted					
_	Spool, Sleeve	Stainless steel	Metal seal				
2	Spool valve	Aluminum/HNBR	Rubber seal				
3	Piston	Resin					
4	Pilot valve assembly	_					


Note) For "How to Order Pilot Valve Assembly", refer to page 16.





Dimensions: VQZ100

Single Unit


Grommet (G): VQZ115□-□G□1-C3, C4, C6-PR







Note) For bracket assembly part no., refer to page




VQZ115□-□G□1-M5-PR


M5 x 0.8
[2(A) port]

Note) For one-touch fittings for P/R port and silencer part no., refer to back page 4.

L-type plug connector (L): VQZ115□-□L□1-C3, C4, C6-PR



M-type plug connector (M): VQZ115□-□M□1-C3, C4, C6-PR



Unless otherwise indicated, dimensions are the same as Grommet (G).

[]: AC





Body Ported Series VQZ100/200/300

Dimensions: VQZ200

Single Unit

Grommet (G): VQZ2□2□-□G□1-C4, C6





Note) For bracket assembly part no., refer to page 16.


VQZ2□2□-□G□1-M5

M5 x 0.8

[2(A) port]

Note) For one-touch fittings for P/R port and silencer part no., refer to back page 4.

L-type plug connector (L): VQZ2□2□-□L□1-C4, C6




ø2.6 (Reverse-mounting-prevention hole

(CE compliant models only)

Unless otherwise indicated, dimensions are the same as Grommet (G).


M-type plug connector (M): VQZ2□2□-□M□1-C4, C6



Unless otherwise indicated, dimensions are the same as Grommet (G).

[]: AC

DIN terminal (Y): VQZ2□2□-□Y□□1-C4, C6




Unless otherwise indicated, dimensions are the same as Grommet (G).




Dimensions: VQZ300


Single Unit

Grommet (G): VQZ3□2□-□G□1-C6, C8, C10





Note) For bracket assembly part no., refer to page 16.




ø8, ø5/16"

ø10, ø3/8"

2 x M2.5 x 0.45


Thread length 6

L-type plug connector (L): VQZ3□2□-□L□1-C6, C8, C10




Unless otherwise indicated, dimensions are the same as Grommet (G).

M-type plug connector (M): VQZ3□2□-□M□1-C6, C8, C10



Unless otherwise indicated, dimensions are the same as Grommet (G). []: AC

DIN terminal (Y): VQZ3 2 - Y - 1-C6, C8, C10



Unless otherwise indicated, dimensions are the same as Grommet (G).



Body Ported

Plug Lead Unit


3 Port Solenoid Valve

Series VQZ100/200/300

Manifold Connector Kit



VQZ100 / How to Order Manifold



For DIN rail part no., refer to page 14.


Note 2) When two or more symbols are specified, indicate them alphabetically.

> Note) For 1(P), 3(R) of optional thread type, refer to page 15.

VQZ100 / How to Order Valve


Kit type •

C Connector




VQZ200/300 / How to Order Manifold





VQZ200/300 / How to Order Valve



Use standard (DC) specification for continuous duty.

Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC [115 VAC] (50/60 Hz)
4	220 VAC [230 VAC] (50/60 Hz)
5	24 VDC
6	12 VDC

Symbol	Electrical entry	Light/surge voltage suppressor
G	Grommet (DC specification)	None
L	L-type plug connector with lead wire	
LO	L-type plug connector without connector	.,
M	M-type plug connector with lead wire	Yes
MO	M-type plug connector without connector	
Υ	DIN terminal	Nama
YO	DIN terminal without connector	None
YZ	DIN terminal	Yes
YS Note 2)	DIN terminal (DC specification)	Yes
YOS Note 2)	DIN terminal without connector (DC specification)	(Without light)
Aloto 1	Ctandard land wire langth; 200 mm	


Note 1) Standard lead wire length: 300 mm

Note 2) For AC voltage valves there is no "S" option. It is already built-in to the rectifier circuit.




Body Ported Series VQZ100/200/300

Manifold Specifications




		Pip		ifications	Applicable	Applicable	Manifold
Series	Base model	Piping direction	1(P), 3(R)	Port size 2(A)	solenoid valve	stations	base weight (g)
VQZ100	VV3QZ12-□□□	Тор	Rc 1/8	C3 (for ø3.2) C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ115	2 to 20 stations	2 stations: 83 Addition per station: 19
VQZ200	VV3QZ22-□□□	Тор	Rc 1/8	C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ2□2	2 to 20 stations	2 stations: 68 Addition per station: 20
VQZ300	VV3QZ32-□□□	Тор	Rc 1/4	C6 (for Ø6) C8 (for Ø8) C10 (for Ø10) Rc 1/4	VQZ3□2	2 to 20 stations	2 stations: 114 Addition per station: 37

How to Order Manifold Assembly (Example)




Dimensions: VQZ100

VV3QZ12- Stations C




L-type plug connector (L)

The dashed lines indicate the DIN rail mounting [-D].



Unless otherwise indicated, dimensions are the same as Grommet (G). []: AC

M-type plug connector (M)



Unless otherwise indicated, dimensions are the same as Grommet (G).]: AC


Dimensions


Dimer	sions									F	ormula: I	_5 = 10.5	5n + 9.5	L3 = 10).5n + 22	2.5 n: S	tations (I	Max. 20	stations)
L	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	85.5	85.5	98	110.5	123	135.5	148	148	160.5	173	185.5	198	210.5	210.5	223	235.5	248	260.5	273
L2	75	75	87.5	100	112.5	125	137.5	137.5	150	162.5	175	187.5	200	200	212.5	225	237.5	250	262.5
L3	43.5	54	64.5	75	85.5	96	106.5	117	127.5	138	148.5	159	169.5	180	190.5	201	211.5	222	232.5
L4	21	16	17	18	19	20	21	15.5	16.5	17.5	18.5	19.5	20.5	15.5	16.5	17.5	18.5	19.5	20.5
L5	30.5	41	51.5	62	72.5	83	93.5	104	114.5	125	135.5	146	156.5	167	177.5	188	198.5	209	219.5


Body Ported Series VQZ100/200/300

Dimensions: VQZ200

VV3QZ22- Stations C











The dashed lines indicate the DIN rail mounting [-D].

L-type plug connector (L)




Unless otherwise indicated, dimensions are the same as Grommet (G). []: AC

M-type plug connector (M)



Unless otherwise indicated, dimensions are the same as Grommet (G). []: AC


DIN terminal (Y)



Unless otherwise indicated, dimensions are the same as Grommet (G).

Dimer	Dimensions												= 16n +	11 L3	= 16n +	22 n: S	tations (I	Max. 20	stations)
L	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	85.5	110.5	123	135.5	148	173	185.5	198	223	235.5	248	260.5	285.5	298	310.5	335.5	348	360.5	373
L2	75	100	112.5	125	137.5	162.5	175	187.5	212.5	225	237.5	250	275	287.5	300	325	337.5	350	362.5
L3	54	70	86	102	118	134	150	166	182	198	214	230	246	262	278	294	310	326	342
L4	16	20.5	18.5	17	15	19.5	18	16	20.5	19	17	15.5	20	18	16.5	21	19	17.5	15.5
L5	43	59	75	91	107	123	139	155	171	187	203	219	235	251	267	283	299	315	331

Dimensions: VQZ300



85.8 [88] (Lead wire length) Approx. 300 56.5 [63.5]


are the same as Grommet (G).

[]: AC

L-type plug connector (L)


Unless otherwise indicated, dimensions

M-type plug connector (M)



Unless otherwise indicated, dimensions are the same as Grommet (G).]: AC

DIN terminal (Y)



ø3.5 to ø7

Unless otherwise indicated, dimensions are the same as Grommet (G).

Dimer	nsions	;									For	mula: L5	= 19n +	11 L3	= 19n +	23 n: S	tations (Max. 20	stations)
L	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20

L	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	98	110.5	135.5	148	173	198	210.5	235.5	248	273	285.5	310.5	323	348	360.5	385.5	398	423	435.5
L2	87.5	100	125	137.5	162.5	187.5	200	225	237.5	262.5	275	300	312.5	337.5	350	375	387.5	412.5	425
L3	61	80	99	118	137	156	175	194	213	232	251	270	289	308	327	346	365	384	403
L4	18.5	15.5	18.5	15	18	21	18	21	17.5	20.5	17.5	20.5	17	20	17	20	16.5	19.5	16.5
L5	49	68	87	106	125	144	163	182	201	220	239	258	277	296	315	334	353	372	391



Body Ported Series VQZ100/200/300

Manifold Options


Blanking plate assembly

VVQZ100-10A-5 (for VQZ100)

VVQZ200-10A-2 (for VQZ200)

VVQZ300-10A-2 (for VQZ300)

It is used by attaching on the manifold block for being prepared for removing a valve for maintenance reasons or planning to mount a spare valve, etc.



Blanking plug


KQ2P-23


KQ2P-04

KQ2P-06

KQ2P-08

KQ2P-10






Dimension	s			(mm)
Applicable fitting size ød	Model	A	L	D
3.2	KQ2P-23	16	31.5	3.2
4	KQ2P-04	16	32	6
6	KQ2P-06	18	35	8
8	KQ2P-08	20.5	39	10
10	KQ2P-10	22	43	12

DIN rail AXT100-DR-□

* As for

, enter the number from the DIN rail dimensions table. For L dimension, refer to the dimensions of each kit.

Each manifold can be mounted on a DIN rail. Insert "D" at the end of the manifold part number. The DIN rail is approximately 30 mm longer than the length of manifold.







L Dimen	nsio	n															L=	= 12.	5n +	10.5
No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L dimension	23	35.5	48	60.5	73	85.5	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	223	235.5	248	260.5
No.	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
L dimension	273	285.5	298	310.5	323	335.5	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5	473	485.5	498	510.5


Silencer (for manifold EXH port)

Silencer is installed in the manifold EXH port.





Dimensions									
	Silencer part no.								
VQZ100 AN110-01									
VQZ200									
VQZ300 AN200-02									






Series VQZ Body Ported **Options**

External Pilot Specification


The external pilot specification is used when the operating pressure is below the minimum operating pressure 0.1 to 0.15 MPa or when valve is used for a vacuum application. Order a valve by adding the external pilot specification [R] to the part number.





Inch Size One-touch Fittings and Optional Threads

Inch size one-touch fittings and NPT, NPTF and G thread are available.










IP65 Enclosure (Based on IEC529)

DIN terminal is available with IP65 enclosure.

Valve Part No.

(Applicable to the VQZ200/300 rubber seal with the exception of the external pilot type)



Series VQZ Body Ported

Replacement Parts

One-touch Fitting Assembly (for Cylinder port)

Fitting size Model	C3	C4	C6	C8	C10	M5 (VQZ100 only)
VQZ100/200	VVQ1000-50A-C3	VVQ1000-50A-C4	VVQ1000-50A-C6	_	_	VVQ1000-50A-M5
VQZ300	_	_	VVQ1000-51A-C6	VVQ1000-51A-C8	VVQ1000-51A-C10	_

Note) Purchasing order is available in units of 10 pieces.

<Plug connector assembly>

DC: SY100-30-4A-

100 VAC: SY100-30-1A-

200 VAC: SY100-30-2A-


Other AC voltages: SY100-30-3A-

Without lead wire: SY100-30-A (with connector and 2 sockets only)

Lead wire length

٠,	<i>-</i> uu	re length s
	Nil	300 mm
	6	600 mm
	10	1000 mm
	15	1500 mm
	20	2000 mm
	25	2500 mm
	30	3000 mm
	50	5000 mm

<Pilot valve assembly>



		<u>-</u>	ncouncar circiy
Syn	nbol	Cleatrical entry	Light/surge voltage
DC	AC	Electrical entry	suppressor
G	_	Grommet (DC specification)	None
LU	LZ	L-type plug connector with lead wire	
LOU	LOZ	L-type plug connector without connector	Yes
MU	MZ	M-type plug connector with lead wire	165
MOU	MOZ	M-type plug connector without connector	

Flectrical entry

Note) VQZ pilot valve electrical entry (L, M) is the opposite of the how to order of valve body

<u> </u>	
Valve model	Pilot valve model
VQZ115□-□L□1	V111□M-□M□
VQZ115□-□M□1	V111□M-□L□

How to Order

Include the connector assembly part number together with the part number for the plug connector's solenoid valve without connector.


Example) In case of 2000 mm of lead wire

VQZ115-5LO1-M5-PR VQZ115-1LO1-M5-PR SY100-30-4A-20 SY100-30-1A-20

<Gasket and screw assembly>

Model	Part no.
VQZ100	VQZ100-GS-2
VQZ200	VQZ200-GS-2
VQZ300	VQZ300-GS-2

Note) Above part number consists of 10 units. Each unit has one gasket and two screws. Purchasing order is available in units of 10 pieces.



Note) Option

Standard


	Coil voltage
1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC (50/60 Hz)
4	220 VAC (50/60 Hz)
5	24 VDC
6	12 VDC

Symbol

Nil

B Note)

<DIN terminal type (Applicable to the VQZ200/300)>



Electrical entry

Symbol	Electrical entry	voltage suppressor			
Υ	None				
YO DIN terminal without connector					
YZ	Yes				
YS Note)	YS Note) DIN terminal with surge voltage suppressor (DC specification)				
YOS Note)	DIN terminal with surge voltage suppressor, without connector (DC specification)	(Without light)			

<Bracket assembly>

Model	Part no.	Tightening torque (N⋅m) Note)
VQZ100	VQZ100-FB	0.45 to 0.55
VQZ200	VQZ200-FB	0.25 to 0.35
VQZ300	VQZ300-FB	0.25 to 0.35

Note) Tightening torque when mounting a bracket on the valve.

<u>∕!\</u> Caution

circuit.

When replacing only the pilot valve assembly, use caution because it is not possible to convert to a V115 (DIN terminal) from a V111 (Grommet, L-type, M-type), or vice versa.

Note) For AC voltage valves there is no "S" option. It is already built-in to the rectifier




Base Mounted

Plug Lead Unit

3 Port Solenoid Valve

Series VQZ100/200/300Single Unit $(\in [Option]$

VQZ100 / How to Order Valve




Note) For sub-plate part no., refer to page 33.



Base Mounted Series VQZ100/200/300

VQZ200/300 / How to Order Valve





Coil voltage

- 00	Con voitage							
1	100 VAC (50/60 Hz)							
2	200 VAC (50/60 Hz)							
3	110 VAC [115 VAC] (50/60 Hz)							
4	220 VAC [230 VAC] (50/60 Hz)							
5	24 VDC							
6	12 VDC							

rectifier circuit.

Note 1) Standard lead wire length: 300 mm

Note 2) For AC voltage valves there is no "S" option. It is already built-in to the

Note) For sub-plate part no., refer to page 33.





Specifications

Valve construction	Metal seal	Rubber seal	VQZ100 (Poppet seal)			
Fluid		Air, Inert gas				
Max. operating pressure (MPa)	0.7 (High pressure type: 1.0)	0.7	0.7 (High pressure type: 1.0)			
Min. operating pressure (MPa)	0.1	0.15	0.15			
Ambient and fluid temperature (°C)	-	-10 to 50 (No freezing))			
Max. operating frequency (Hz)	20	5	20			
Pilot exhaust method	Individua	exhaust	Common exhaust			
Lubrication		Not required				
Manual override	Push typ	e, Locking type (Tool i	required)			
Mounting orientation		Free				
Impact/Vibration resistance (m/s²) Note 1)	150/30					
Enclosure	Dustproof (DIN terminal: IP65 Note 2))					



* Based on IEC60529

Note 1) Impact resistance: No malfunction occurred when it is tested with a drop tester in the axial direction

and at the right angles to the main valve and armature in both energized and deenergized states every once for each condition. (Value in the initial state)

Vibration resistance: No malfunction occurred in one sweep test between 45 and 2000 Hz. Test was performed to axis and right angle directions of the main valve and armature when pilot signal is ON and OFF. (Value in the initial state)

Note 2) When IP65 compliant DIN terminals are selected: VQZ₃² □5 □- □Y □ □W1- □- □

Solenoid Specifications

Options

High speed response type			
High pressure type (Metal seal type only)			
External pilot type*			

^{*} For details on external pilot type, refer to page 32.



Made to Order (For details, refer to page 34.)

Symbol	Description
X30	Pilot valve common exhaust
X90	Main valve fluoro-rubber
X113	All fluoro-rubber

Electrical entry		Grommet (G) L-type plug connector (L)	M-type plug connector (M) DIN terminal (Y)				
			G, L, M	Υ			
Coil rated voltage DC			24	, 12			
(V)	-	AC 50/60 Hz	100, 110,	200, 220*			
Allowable voltage f	luctua	ation	±10% of ra	ted voltage*			
		Standard	0.35 [(With light: 0.4 (DIN	l terminal with light: 0.45)]			
Power consumption (W)	DC III		0.9 [(With light: 0.95 (DIN terminal with light: 1.0)]				
	AC	100 V	0.78 (With light: 0.81)	0.78 (With light: 0.87)			
Apparent power		110 V [115 V]	0.86 (With light: 0.89) [0.94 (With light: 0.97)]	0.86 (With light: 0.87) [0.94 (With light: 1.07)]			
(VA)	AC	200 V	1.18 (With light: 1.22)	1.15 (With light: 1.30)			
		220 V [230 V]	1.30 (With light: 1.34)				
Surge voltage suppressor			Varistor				
Indicator light			LED (Neon light when AC with DIN terminal)				



- \ast In common between 110 VAC and 115 VAC, and between 220 VAC and 230 VAC. \ast For 115 VAC and 230 VAC, the allowable voltage is –15% to +5% of rated voltage.

Flow Characteristics

				Flow characteristics					Response time (ms) Note 1)					
Series	Valve construc- tion			1→2 (P→A)		2→3 (A→R)		Standard:	Ispeed	High	AC	Note 2) Weight		
				C [dm³/(s•bar)]	b	Cv	C [dm³/(s•bar)]	b	Cv		rochonco.	pressure: 0.9 W	AC	(g)
VQZ100	N.C. valve	Poppet	VQZ115	0.87	0.46	0.23	1.0	0.35	0.25	10 or less		13 or less	22 or less	24
	N.C.	Metal seal	VQZ215	1.7	0.17	0.38	2.0	0.20	0.45	22 or less	14 or less	18 or less	34 or less	
VQZ200	valve	Rubber seal	VQZ235	2.3	0.46	0.65	3.0	0.40	0.80	22 or less	15 or less	_	36 or less	52
VQZ200	N.O. valve	Metal seal	VQZ225	1.7	0.18	0.38	1.8	0.21	0.39	22 or less	14 or less	18 or less	34 or less	1 - 1
		Rubber seal	VQZ245	2.5	0.43	0.67	3.0	0.30	0.74	22 or less	15 or less	_	36 or less	
	N.C.	Metal seal	VQZ315	3.0	0.21	0.70	3.2	0.27	0.80	22 or less	17 or less	22 or less	34 or less	
VQZ300	valve	Rubber seal	VQZ335	4.5	0.42	1.3	4.1	0.36	1.0	33 or less	25 or less	_	57 or less	70
VQ2300	N.O.	Metal seal	VQZ325	2.9	0.21	0.72	2.9	0.16	0.69	22 or less	17 or less	22 or less	34 or less	78
	valve	Rubber seal	VQZ345	4.4	0.45	1.2	4.5	0.38	1.2	33 or less	25 or less	_	57 or less	



Note 1) Based on JIS B 8375-1981 (Supply pressure: 0.5 MPa; with light/surge voltage suppressor: clean air) Response time values will change depending on pressure and air quality.


Note 2) Weight without sub-plate.




Base Mounted Series VQZ100/200/300

Construction

VQZ100 Poppet type








Component Parts


No.	Description	Material	Note				
1	Body	Resin					
2	Spool valve	Spool valve Aluminum/HNBR					
3	Pilot valve assembly	_					
4	Port plug	Resin/HNBR	VVQZ100-CP				

VQZ200/300 Metal seal type













Rubber seal type









Component Parts

No.	Description	Material	Note
1	Body	Aluminum die-casted	
2	Spool, Sleeve	Stainless steel	Metal seal
2	Spool valve	Aluminum/HNBR	Rubber seal
3	Piston	Resin	
4	Pilot valve assembly	_	


Note) For "How to Order Pilot Valve Assembly", refer to page 33.




Dimensions: VQZ100


Single Unit

Grommet (G): VQZ115□-□**G**□1-01






L-type plug connector (L): VQZ115□-□L□1-01



Unless otherwise indicated, dimensions are the same as Grommet (G). []: AC

M-type plug connector (M): VQZ115□-□M□1-01



Unless otherwise indicated, dimensions are the same as Grommet (G).

[]: AC



1/8


[1(P), 3(R) port]


Base Mounted Series VQZ100/200/300


Dimensions: VQZ200


Single Unit


Grommet (G): VQZ2□5□-□G□1-01













L-type plug connector (L): VQZ2 5 - L 1-01




Unless otherwise indicated, dimensions are the same as Grommet (G).

M-type plug connector (M): VQZ2 5 - M 1-01



Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

DIN terminal (Y): VQZ2 5 - Y = 1-02




Unless otherwise indicated, dimensions are the same as Grommet (G).





Dimensions: VQZ300


Single Unit


Grommet (G): VQZ3□5□-□G□1-02













L-type plug connector (L): VQZ3 \$\Boxed{D}\$5\$\Boxed{-} \Boxed{L} \Boxed{D}\$1-\boxed{0}3



Unless otherwise indicated, dimensions are the same as Grommet (G).


M-type plug connector (M): VQZ3□5□-□M□1-02



Unless otherwise indicated, dimensions are the same as Grommet (G).

[]: AC

DIN terminal (Y): VQZ3 5--Y 11-02



Unless otherwise indicated, dimensions are the same as Grommet (G).



Base Mounted

Plug Lead Unit


3 Port Solenoid Valve

Series VQZ100/200/300


Manifold Connector Kit



VQZ100 / How to Order Manifold




VQZ100 / How to Order Valve




VQZ200/300 / How to Order Manifold






VQZ200/300 / How to Order Valve




Base Mounted Series VQZ100/200/300


Manifold Specifications



		Pip	ing spec	ifications	Applicable	A	Note) Manifold
Series	Base model	Piping	ı	Port size	solenoid	Applicable stations	base
		direction	1(P), 3(R)	2(A)	valve		weight (g)
VQZ100	VV3QZ15-□□□	Side/Top	Rc 1/8	C3 (for ø3.2) C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ115	2 to 20 stations	2 stations: 83 Addition per station: 19
VQZ200	VV3QZ25-□□□	Side	Rc 1/4	C4 (for ø4) C6 (for ø6) C8 (for ø8) Rc 1/8	VQZ2□5	2 to 20 stations	2 stations: 126 Addition per station: 38
VQZ300	VV3QZ35-□□□	Side	1(P) port Rc 3/8 3(R) port Rc 1/4	C6 (for Ø6) C8 (for Ø8) C10 (for Ø10) Rc 1/4	VQZ3□5	2 to 20 stations	2 stations: 209 Addition per station: 60




How to Order Manifold Assembly (Example)



Dimensions: VQZ100: Top Ported

VV3QZ15- Stations Port size C




The dashed lines indicate the DIN rail mounting [-D].

М5

27

(7.5)




Dimer	sions									F	ormula: I	_5 = 10.5	5n + 9.5	L3 = 10).5n + 22	2.5 n: S	tations (I	Max. 20	stations)
L	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	85.5	85.5	98	110.5	123	135.5	148	148	160.5	173	185.5	198	210.5	210.5	223	235.5	248	260.5	273
L2	75	75	87.5	100	112.5	125	137.5	137.5	150	162.5	175	187.5	200	200	212.5	225	237.5	250	262.5
L3	43.5	54	64.5	75	85.5	96	106.5	117	127.5	138	148.5	159	169.5	180	190.5	201	211.5	222	232.5
L4	21	16	17	18	19	20	21	15.5	16.5	17.5	18.5	19.5	20.5	15.5	16.5	17.5	18.5	19.5	20.5
L5	30.5	41	51.5	62	72.5	83	93.5	104	114.5	125	135.5	146	156.5	167	177.5	188	198.5	209	219.5

Base Mounted Series VQZ100/200/300

Dimensions: VQZ100: Side Ported


VV3QZ15- Stations Port size C



L-type plug connector (L)

(7.5)

20



13.5


0 1

(Pitch) P = 10.5

Unless otherwise indicated, dimensions are the same as Grommet (G).

M-type plug connector (M)

ø6, ø1/4"



The dashed lines indicate the DIN rail mounting [-D].


Unless otherwise indicated, dimensions are the same as Grommet (G).


Dimensions Formula: L5 = 10.5n + 9.5 L3 = 10.5n + 22.5 n: Stations (Max. 20 stations)


	.0.00										ommaia.	_0 - 10.0	311 1 0.0		,.o <u></u>	0 0	tationo (WIGH. LO	otationoj
L	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	85.5	85.5	98	110.5	123	135.5	148	148	160.5	173	185.5	198	210.5	210.5	223	235.5	248	260.5	273
L2	75	75	87.5	100	112.5	125	137.5	137.5	150	162.5	175	187.5	200	200	212.5	225	237.5	250	262.5
L3	43.5	54	64.5	75	85.5	96	106.5	117	127.5	138	148.5	159	169.5	180	190.5	201	211.5	222	232.5
L4	21	16	17	18	19	20	21	15.5	16.5	17.5	18.5	19.5	20.5	15.5	16.5	17.5	18.5	19.5	20.5
L5	30.5	41	51.5	62	72.5	83	93.5	104	114.5	125	135.5	146	156.5	167	177.5	188	198.5	209	219.5

Dimensions: VQZ200

VV3QZ25- Stations Port size C








The dashed lines indicate the DIN rail mounting [-D].


_ead wire length) Approx. 300 57.8 [64.8]

L-type plug connector (L)




Unless otherwise indicated, dimensions are the same as Grommet (G). []: AC

M-type plug connector (M)



the same as Grommet (G).
[]: AC

DIN terminal (Y)



Unless otherwise indicated, dimensions are the same as Grommet (G).

D	imen	sions	;					For	mula: L5	= 16n +	10 L3	= 16n + 2	20 n: S	Stations (I	Max. 20	stations)
_																

L	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	85.5	98	123	135.5	148	173	185.5	198	210.5	235.5	248	260.5	285.5	298	310.5	323	348	360.5	373
L2	75	87.5	112.5	125	137.5	162.5	175	187.5	200	225	237.5	250	275	287.5	300	312.5	337.5	350	362.5
L3	52	68	84	100	116	132	148	164	180	196	212	228	244	260	276	292	308	324	340
L4	17	15	19.5	18	16	20.5	19	17	15.5	20	18	16.5	21	19	17.5	15.5	20	18.5	16.5
L5	42	58	74	90	106	122	138	154	170	186	202	218	234	250	266	282	298	314	330



Base Mounted Series VQZ100/200/300

Dimensions: VQZ300

VV3QZ35- Stations Port size C Grommet (G) U side D side L1 PE port ead wire length 64.5 L2 (5) Approx. 300 M5 x 0.8 (Rail mounting hole pitch: 12.5) 49.1 (X: External pilot port) (Pitch) <External pilot only> P = 20 (DIN rail clamp thread) Manual override [3(R) port] (DIN rail) 79.8 (99) 2 44.5 57.6 (32)∞, (9) (8) 5.5 (5.5)[1(P) port] 2 x ø4.5 (For mounting) 11.5 L3 29.5 (Station 1) ----- (Station n) One-touch fitting [2(A) port] Applicable tubing O.D.: ø6, ø1/4" ø8, ø5/16" ø10, ø3/8" 8 23 (Pitch) (7.5)19.5 P = 201/4 1/4 [2(A) port] 34 41.7 (Pitch) 19.5 The dashed lines indicate the DIN rail mounting [-D]. L-type plug connector (L) M-type plug connector (M) DIN terminal (Y) Applicable cable O.D ead wire length 93.8 300 ø3.5 to ø7 86.3 우 Approx. 64.5 [71.5] 75 Nax. Pg7 Approx. 300 75.8 [82.8] (Lead wire length)

Unless otherwise indicated, dimensions are the same as Grommet (G).	Unless otherwise indicated, dimensions are the same as Grommet (G).	Unless otherwise indicated, dimensions are the same as Grommet (G).
Dimensions	_	1 15 00 0 10 00 00 01 1 (14 00 1 1)

Dimensions Formula: L5 = 20n + 8 L3 = 20n + 26 n: Stations (Max. 20 stations) 2 10 11 12 13 14 15 16 17 18 19 20 3 4 5 6 8 9 123 148 160.5 185.5 198 223 248 260.5 285.5 298 323 348 360.5 385.5 398 423 448 460.5 98 L2 212.5 450 87.5 112.5 137.5 150 175 187.5 237.5 250 275 287.5 312.5 337.5 350 375 387.5 412.5 437.5 L3 106 406 426 66 86 126 146 166 186 206 226 246 266 286 306 326 346 366 386 L4 16 18.5 21 17.5 20 16 18.5 21 17.5 20 16 18.5 21 17.5 20 16 18.5 21 17.5 L5 48 68 88 108 128 148 168 188 228 248 268 288 308 328 348 368 408

Manifold Options


Blanking plate assembly

VVQZ100-10A-5 (for VQZ100)

VVQZ200-10A-5 (for VQZ200)

VVQZ300-10A-5 (for VQZ300)

It is used by attaching on the manifold block for being prepared for removing a valve for maintenance reasons or planning to mount a spare valve, etc.



Blanking plug


KQ2P-23


KQ2P-04

KQ2P-06

KQ2P-08

KQ2P-10







Dimension	s			(mm)
Applicable fitting size ød	Model	A	L	D
3.2	KQ2P-23	16	31.5	3.2
4	KQ2P-04	16	32	6
6	KQ2P-06	18	35	8
8	KQ2P-08	20.5	39	10
10	KQ2P-10	22	43	12

DIN rail AXT100-DR-□

* As for □, enter the number from the DIN rail dimensions table. For L dimension, refer to the dimensions of each kit.

Each manifold can be mounted on a DIN rail. Insert "D" at the end of the manifold part number. The DIN rail is approximately 30 mm longer than the length of manifold.







ı	L Dimer	nsio	n															L=	= 12.	5n +	10.5
	No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
	L dimension	23	35.5	48	60.5	73	85.5	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	223	235.5	248	260.5
	No.	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
	L dimension	273	285.5	298	310.5	323	335.5	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5	473	485.5	498	510.5

Silencer (for manifold EXH port)

Silencer is installed in the manifold EXH port.





Dimensions

Model	Silencer part no.
VQZ100	AN110-01
VQZ200	AN200-02
VQZ300	AN200-02

Port plug VVQZ100-CP (for VQZ100)

This is used when changing piping location. (Side or Top)



Series VQZ Base Mounted **Options**

External Pilot Specification


The external pilot specification is used when the operating pressure is below the minimum operating pressure 0.1 to 0.15 MPa or when valve is used for a vacuum application. Order a valve by adding the external pilot specification [R] to the part number.





Entry is the same as standard products.

Manifold Part No.





5	Series	VQZ100 Note 2)	VQZ200/300
Note 1)	Metal seal	_	0.1 to 0.7 MPa
External pilot pressure range	Rubber seal (VQZ100: poppet)	0.2 to 0.7 MPa	0.15 to 0.7 MPa
Operating press	sure range Note 1)	–100 kPa	to 0.7 MPa

External pilot port


Note 1) In case of the high pressure type, upper limit of max. operating pressure and external pilot pressure range is 1 MPa.

Note 2) When using the VQZ100 series for a vacuum application, vacuum air through its 1(P) port. When supplying vacuum-release air, supply it through its 3(R) port. But do not supply vacuum-release air exceeding 50% for the external pilot pressure.

Inch Size One-touch Fittings and Optional Threads

Inch size one-touch fittings and NPT, NPTF and G thread are available.





Thread type (Cylinder port and 1(P), 3(R) ports)

Nil	Rc
N	NPT
Т	NPTF
F	G

Note 2) Metric size one-touch fittings (C□) are also available.

Optional Threads Other than Rc

Rc specifications are standard for all ports, however, NPT, NPTF and G are available for overseas markets. Add the appropriate symbol following the port size in the standard part number.

Valve Part No.




Nil	Rc
N	NPT
Т	NPTF
F	G

IP65 Enclosure (Based on IEC529)

DIN terminal is available with IP65 enclosure.

Valve Part No.

(Applicable to the VQZ200/300 rubber seal with the exception of the external pilot type)





Series VQZ Base Mounted

Replacement Parts

One-touch Fitting Assembly (for Cylinder port)

Fitting size Model	C3	C4	C6	C8	C10	M5 (VQZ100 only)
VQZ100	VVQ1000-50A-C3	VVQ1000-50A-C4	VVQ1000-50A-C6	_	_	VVQ1000-50A-M5
VQZ200		VVQ1000-51A-C4	VVQ1000-51A-C6	VVQ1000-51A-C8		_
VQZ300		_	VVQ2000-51A-C6	VVQ2000-51A-C8	VVQ2000-51A-C10	_

Note) Purchasing order is available in units of 10 pieces.



DC: SY100-30-4A-

100 VAC: SY100-30-1A-


200 VAC: SY100-30-2A-

Other AC voltages: SY100-30-3A-

Without lead wire: SY100-30-A (with connector and 2 sockets only)

ead wire length •		
Nil	300 mm	
6	600 mm	
10	1000 mm	
15	1500 mm	
20	2000 mm	
25	2500 mm	
30	3000 mm	
50	5000 mm	

<Pilot valve assembly>



		_	iecu icai enu y 🗨	
Symbol		Electrical entry	Light/surge voltage	
DC	AC	Electrical entry	suppressor	
G	_	Grommet (DC specification)	None	
LU	LZ	L-type plug connector with lead wire		
LOU	LOZ L-type plug connector without connector		Voo	
MU MZ M-type plug connector with lead wire		162		
MOU	MOZ	M-type plug connector without connector		

Note) The electrical entry (L. M) for the VQZ100 pilot valve is different from that of the main valve model number.

> Valve model Pilot valve model VQZ115□-□L□1 V111□M-□M□ VQZ115□-□M□1 V111 □ M - □ L □

Include the connector assembly part number together with the part number for the plug connector's solenoid valve without connector.

Example) In case of 2000 mm of lead wire

VQZ115-5LO1-M5 VQZ115-1LO1-M5 SY100-30-4A-20 SY100-30-1A-20

<Gasket and screw assembly>

Model Part no.	
VQZ100	VQZ100-GS-5
VQZ200	VQZ200-GS-5
VQZ300	VQZ300-GS-5

Note) Above part number consists of 10 units. Each unit has one gasket and two screws. Purchasing order is available in units of 10 pieces




<Sub-plate>

re one prome		
Model	Sub-plate part no.	
VQZ100	VQZ100-S-01(R) ⊛ (-Q) ^{Note)}	
VQZ200	VQZ200-S- ⁰¹ (-Q)	
VQZ300	VQZ300-S- ⁰² ⋅ (-Q)	

Thread type

Note) R indicates external pilot type. Except VQZ100, external pilot type and internal pilot type are common.

<DIN terminal type (Applicable to the VQZ200/300)>



Light/surge voltage suppressor Symbol Electrical entry DIN terminal None DIN terminal without connector **Y7** Yes DIN terminal with light/surge voltage suppressor DIN terminal with surge voltage suppressor (DC specification) Yes (Without DIN terminal with surge voltage suppressor, without connector (DC specification)

Electrical entry

Note) For AC voltage valves there is no "S" option. It is already built-in to the rectifier circuit.

∖ Caution

When replacing only the pilot valve assembly, use caution because it is not possible to convert to a V115 (DIN terminal) from a V111 (Grommet, L-type, M-type), or vice versa.



Coil voltage

100 VAC (50/60 Hz)

200 VAC (50/60 Hz)

110 VAC (50/60 Hz)

220 VAC (50/60 Hz)

24 VDC

12 VDC

2

3

5

Series VQZ200/300 Made to Order



Please contact SMC for detailed dimensions, specifications, and lead times.


1 Pilot Valve Common Exhaust Specification

Pilot exhaust is exhausted through the main R port.

- * Not designed to prevent leakage to outside.
- * A combination of external pilots is not available.
- * "How to Order Manifold" is the same as standard products. Please specify this to "How to Order Valve."

Applicable solenoid valve series: VQZ200/300

How to Order




2 Main Valve Fluoro-rubber Specification

The seal material, the part of the main valve in contact with fluid, is made of fluoro-rubber.

* "How to Order Manifold" is the same as standard products. Please specify this to "How to Order Valve."

Applicable solenoid valve series: VQZ200/300

How to Order



Entry is the same as standard products.


3 All Fluoro-rubber Specification

The rubber material of the part in contact with fluid, is made of fluoro-rubber.

st "How to Order Manifold" is the same as standard products. Please specify this to "How to Order Valve."

Applicable solenoid valve series: VQZ200/300

How to Order







These safety instructions are intended to prevent a hazardous situation and/or equipment damage. These instructions indicate the level of potential hazard by labels of "Caution", "Warning" or "Danger". To ensure safety, be sure to observe ISO 4414 Note 1), JIS B 8370 Note 2) and other safety practices.

■ Explanation of the Labels

Labels Explanation of the labels		
⚠ Danger	⚠ Danger In extreme conditions, there is a possible result of serious injury or loss of life.	
⚠ Warning Operator error could result in serious injury or loss of life.		
⚠ Caution	Operator error could result in injury Note 3) or equipment damage. Note 4)	

- Note 1) ISO 4414: Pneumatic fluid power General rules relating to systems
- Note 2) JIS B 8370: General Rules for Pneumatic Equipment
- Note 3) Injury indicates light wounds, burns and electrical shocks that do not require hospitalization or hospital visits for long-term medical treatment.
- Note 4) Equipment damage refers to extensive damage to the equipment and surrounding devices.

■ Selection/Handling/Applications

1. The compatibility of the pneumatic equipment is the responsibility of the person who designs the pneumatic system or decides its specifications.

Since the products specified here are used in various operating conditions, their compatibility for the specific pneumatic system must be based on specifications or post analysis and/or tests to meet the specific requirements. The expected performance and safety assurance are the responsibility of the person who has determined the compatibility of the system. This person should continuously review the suitability of all items specified, referring to the latest catalog information with a view to giving due consideration to any possibility of equipment failure when configuring a system.

2. Only trained personnel should operate pneumatically operated machinery and equipment.

Compressed air can be dangerous if handled incorrectly. Assembly, handling or repair of the systems using pneumatic equipment should be performed by trained and experienced operators. (Understanding JIS B 8370 General Rules for Pneumatic Equipment, and other safety rules are included.)

- 3. Do not service machinery/equipment or attempt to remove components until safety is confirmed.
 - 1. Inspection and maintenance of machinery/equipment should only be performed once measures to prevent falling or runaway of the driven objects have been confirmed.
 - 2. When equipment is removed, confirm the safety process as mentioned above. Turn off the supply pressure for this equipment and exhaust all residual compressed air in the system, and release all the energy (liquid pressure, spring, condenser, gravity).
 - 3. Before machinery/equipment is restarted, take measures to prevent quick extension of a cylinder piston rod, etc.
- 4. If the equipment will be used in the following conditions or environment, please contact SMC first and be sure to take all necessary safety precautions.
 - 1. Conditions and environments beyond the given specifications, or if product is used outdoors.
 - 2. Installation on equipment in conjunction with atomic energy, railway, air navigation, vehicles, medical equipment, food and beverages, recreation equipment, emergency stop circuits, clutch and brake circuits in press applications, or safety equipment.
 - 3. An application which has the possibility of having negative effects on people, property, requiring special safety analysis.
 - 4. If the products are used in an interlock circuit, prepare a double interlock style circuit with a mechanical protection function for the prevention of a breakdown. And, examine the devices periodically if they function normally or not.

■ Exemption from Liability

- 1. SMC, its officers and employees shall be exempted from liability for any loss or damage arising out of earthquakes or fire, action by a third person, accidents, customer error with or without intention, product misuse, and any other damages caused by abnormal operating conditions.
- 2. SMC, its officers and employees shall be exempted from liability for any direct or indirect loss or damage, including consequential loss or damage, loss of profits, or loss of chance, claims, demands, proceedings, costs, expenses, awards, judgments and any other liability whatsoever including legal costs and expenses, which may be suffered or incurred, whether in tort (including negligence), contract, breach of statutory duty, equity or otherwise.
- 3. SMC is exempted from liability for any damages caused by operations not contained in the catalogs and/or instruction manuals, and operations outside of the specification range.
- 4. SMC is exempted from liability for any loss or damage whatsoever caused by malfunctions of its products when combined with other devices or software.



Be sure to read this before handling.


For Safety Instructions and 3 Port Solenoid Valve Precautions, refer to "Precautions for Handling Pneumatic Devices" (M-03-E3A).

Manual Override

⚠ Caution


Without an electric signal for the solenoid valve the manual override is used for switching the main valve. Push type is standard. Locking type (Tool required) is available as an option.

1. VQZ100



Press in the direction of the arrow.

Locking type (Tool required)



Turn 90° in the direction of arrow.


2. VQZ200/300

Push type (Tool required)



Push down on the manual override button with a small screwdriver until it stops. Release the screwdriver and the manual override will return.

Locking type (Tool required)



Push down completely on the manual override button with a small screwdriver. While down, turn clockwise 90° to lock it. Turn it counterclockwise to release it.

Locked position



Precautions

When operating with a screwdriver, turn it gently using a watchmaker's screwdriver. (Torque: less than 0.1 N·m)


Press and rotate to lock the manual operation of VQZ200/300. If rotate without pressing, manual breakage and air leakage could be occurred.

How to Use L/M-Type Plug Connector

⚠ Caution

1. Attaching and detaching connectors

To attach a connector, hold the lever and connector unit between your fingers and insert straight onto the pins of the solenoid valve and remove the pawl from the groove by pushing the lever downward with your thumb, and pull the connector straight out.



Light/Surge Voltage Suppressor


1. L/M-type plug connector

<DC> <AC>


2. DIN terminal

<DC>

With surge voltage suppressor (YS, YOS)



Light/surge voltage suppressor (YZ)



Note) Surge voltage suppressor of varistor has residual voltage corresponding to the protective element and rated voltage; therefore, protect the controller side from the surge.





Be sure to read this before handling.

For Safety Instructions and 3 Port Solenoid Valve Precautions, refer to "Precautions for Handling Pneumatic Devices" (M-03-E3A).


Light/Surge Voltage Suppressor

⚠ Caution

1. Surge voltage countermeasures

When shutting off the DC power supply using an emergency circuit breaker, the valve may operate incorrectly due to surge voltage generated by other electric parts (e.g., the solenoid). To ensure that surge does not affect the valve, take anti-surge measures (diode for surge protection, etc.) or use a valve with diode to prevent reverse current. (Contact SMC for model numbers.)

Circuit example




(1), (3): Examples of anti-surge measures
 (2): Valve equipped with diode to prevent reverse current

Lead Wire Connection

⚠ Caution

1. Crimping of lead wires and sockets

Not necessary if ordering the lead wire pre-connected model. Strip 3.2 to 3.7 mm at the end of the lead wires, insert the ends of the core wires evenly into the sockets, and then crimp with a crimping tool. When this is done, take care that the coverings of the lead wires do not enter the core wire crimping area.



Crimping tool part no. DXT170-75-1

Lead Wire Connection

⚠ Caution


2. Attaching and detaching sockets with lead wires

Attaching

Insert the sockets into the square holes of the connector (\oplus , \ominus indication), and continue to push the sockets all the way in until they lock by hooking into the seats in the connector. (When they are pushed in, their hooks open and they are locked automatically.) Then, confirm that they are locked by pulling lightly on the lead wires.

Detaching

To detach a socket from a connector, pull out the lead wire while pressing the socket's hook with a stick having a thin tip (approx. 1 mm). If the socket will be used again, first spread the hook outward.




Pilot Valve Replacement


⚠ Caution

1. When replacing a conventional type valve with a new type for maintenance or other reasons, a "conversion connector assembly" is necessary to convert the connector from 3 terminals to 2 terminals and must be ordered separately. (When ordering, refer to the below part nos.)

For pilot valves, there is no compatibility between the conventional type and new type. When replacing a pilot valve, be sure to confirm whether it is the new type or the conventional type.

[Conventional]







Be sure to read this before handling.

For Safety Instructions and 3 Port Solenoid Valve Precautions, refer to "Precautions for Handling Pneumatic Devices" (M-03-E3A).

How to Use DIN Terminal

1. EN-175301-803C (Former DIN 43650C)

The DIN terminal type with an IP65 enclosure is protected against dust and water, however, it must not be used in water.

2. Connection

- Loosen the holding screw and pull the connector out of the solenoid valve terminal block.
- After removing the holding screw, insert a flat head screwdriver, etc. into the notch on the bottom of the terminal block and pry it open, separating the terminal block and the housing.
- 3) Loosen the terminal screws (slotted screws) on the terminal block, insert the cores of the lead wires into the terminals according to the connection method, and fasten them securely with the terminal screws.
- 4) Secure the cord by fastening the ground nut.

3. Changing the entry direction

After separating the terminal block and housing, the cord entry can be changed by attaching the housing in the desired direction (4 directions at 90° intervals).

* When equipped with a light, be careful not to damage the light with the cord's lead wires.


4. Precautions

Plug in and pull out the connector vertically without tilting to one side.

5. Compatible cable

Cable O.D.: ø3.5 to ø7

(Reference) 0.5 mm², 2-core or 3-core, equivalent to JIS C 3306



DIN Connector Part No.


Without light

Rated voltage	Voltage symbol	Part no.
All voltages	None	SY100-82-1

With light

Rated voltage	Voltage symbol	Part no.
24 VDC	24 V	SY100-82-3-05
12 VDC	12 V	SY100-82-3-06
100 VAC	100 V	SY100-82-2-01
200 VAC	200 V	SY100-82-2-02
110 VAC (115 VAC)	110 V	SY100-82-2-03
220 VAC (230 VAC)	220 V	SY100-82-2-04

Circuit diagram with light




Fitting and Silencer Part No. for P, R Ports When Using Valve as an Individual Unit

Part no. for one-touch fitting for 1(P) port and silencer/one-touch fitting for 3(R) port

Series (1) One-touch		(2) For 3(R) port		
Series	fitting for 1(P) port	Silencer	One-touch fitting	
VQZ100	KQ2H06-M5	AN120-M5	KJS04-M5	
VQZ200	KQ2S06-01S	INA-25-46	IN-457-32 (for ø6)	
VQZ300	KQ2H08-02S	AN101-01	KQ2H06-01S	

The diameter of the above fitting and silencer is the maximum diameter to in the EXH port.








Be sure to read this before handling.

For Safety Instructions and 3 Port Solenoid Valve Precautions, refer to "Precautions for Handling Pneumatic Devices" (M-03-E3A).


One-touch Fittings Replacement

The built-in fittings on the manifold can be changed easily. Simply remove the corresponding valve and take out the fitting clip underneath.

Take out the clip with a screwdriver, etc., then replace the fittings. About mounting the fittings, after inserting the fitting until it stops, then put the clip into the prescribed position.



VQZ200: Horizontally clipped to the valve body VQZ100/300: Vertically clipped to the valve body



Precautions

When pulling the fitting assembly away from the valve base, remove the clip, then connect a tube or plug (KQ2P- $\square\square$) with the one-touch fitting and pull it out holding the tube or plug. Do not hold the release bushing to avoid damage.

DIN Rail Removal/Mounting


⚠ Caution

1. Removing

- Loosen the clamp screw on the (a) side of both ends of the manifold.
- Lift the ⓐ side ➡ of the manifold off the DIN rail and slide it in the direction of the ⓑ side.

2. Mounting

- 1) Catch the hook of the DIN rail bracket on the ⓑ side on the DIN rail.
- Push side (a) onto the DIN rail and tighten the clamp screw. The proper tightening torque for screws is 0.3 to 0.4 N•m.



Valve Mounting

⚠ Caution

1. After confirming the gasket is correctly placed under the valve, securely tighten the bolts with the proper torque shown in the table below.

Model	Proper tightening torque
VQZ100	0.13 to 0.19 N·m
VQZ200	0.25 to 0.35 N⋅m
VQZ300	0.5 to 0.7 N⋅m


Screw

VQZ100 Piping Direction Replacement

⚠ Caution

1. How to replace the port direction

Fitting and port plug are modules. After removing the clip with a flat head screwdriver, take out the fitting and port plug. The piping direction (side or top) can be altered by exchanging the fitting and port plug. During exchange, insert the fitting and the port plug until they contact the wall, then, insert the clip to specified position.




Precautions

The clip length for the valve and the base are different. Fitting may detach if the incorrect clip is used.

2. Valve piped on top can be operated independently by using PR plate.

(Refer to the below part numbers when placing an order.)



VQZ100-12A (Standard) VQZ100-12B (External pilot type)

* 2 set screws are included.







Record of changes

B edition * Page 3, 19 Correction of Solenoid Specifications and Flow Characteristics

* Page 4, 20 Correction of Construction

* Page 5 to 7, Page 11 to 13, Page 21 to 23, Page 27 to 30

Correction of Dimensions * Page 34

Addition of Made to Order

LX

Safety Instructions Be sure to read "Precautions for Handling Pneumatic Devices" (M-03-E3A) before using.

SMC Corporation

Akihabara UDX 15F, 4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN Phone: 03-5207-8249 Fax: 03-5298-5362 URL http://www.smcworld.pc/

© 2007 SMC Corporation All Rights Reserved