


Geberit Mapress Stainless Steel bend with plain ends



Example image



TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	arc °	H cm	H1 cm	K cm	K1 max. cm
These articles are suitable for the following system: Geberit Mapress Therm							
30892	12	15	15	4	11	0	7
30893	15	18	15	4	11.2	0	7.1
30894	20	22	15	4.1	11.4	0	7.3
30905	25	28	15	4.3	11.9	0	7.6
30906	32	35	15	4.1	11.8	0	7.7
30907	40	42	15	4.7	13.7	0	9

<i>Art. no.</i>	<i>DN</i>	<i>d_ø</i> <i>mm</i>	<i>arc</i> <i>°</i>	<i>H</i> <i>cm</i>	<i>H1</i> <i>cm</i>	<i>K</i> <i>cm</i>	<i>K1 max.</i> <i>cm</i>
30908	50	54	15	5.5	14.9	0	9.4
30009	65	76.1	15	8.4	20.4	0	12
30010	80	88.9	15	9.5	22	0	12.5
30011	100	108	15	11.7	25.4	0	13.7
30932	12	15	30	4.3	11.3	0	7
30933	15	18	30	4.4	11.6	0	7.1
30934	20	22	30	4.6	11.8	0	7.2
30935	25	28	30	4.8	12.4	0	7.6
30936	32	35	30	4.6	12.3	0	7.7
30937	40	42	30	5.4	14.4	0	9
30938	50	54	30	6.3	15.7	0	9.4
30029	65	76.1	30	9.7	21.7	0	12
30030	80	88.9	30	11.1	23.6	0	12.5

Art. no.	DN	d _ø mm	arc °	H cm	H1 cm	K cm	K1 max. cm
30031	100	108	30	13.6	27.3	0	13.7
30872	12	15	45	4.5	11.6	0	7.1
30873	15	18	45	4.2	11.7	0	7.5
30874	20	22	45	5.2	12.3	0	7.1
30875	25	28	45	5.6	13.1	0	7.5
30876	32	35	45	5.3	12.9	0	7.6
30877	40	42	45	6.1	15.1	0	9
30878	50	54	45	7.3	16.7	0	9.4
30049	65	76.1	45	11.1	23	0	11.9
30050	80	88.9	45	13	25.2	0	12.2
30051	100	108	45	15.7	29.4	0	13.7
30942	12	15	60	5	12	0	7
30943	15	18	60	5.3	12.4	0	7.1

Art. no.	DN	d _g mm	arc °	H cm	H1 cm	K cm	K1 max. cm
30944	20	22	60	5.6	12.8	0	7.2
30955	25	28	60	6.1	13.7	0	7.6
30956	32	35	60	5.9	13.6	0	7.7
30957	40	42	60	6.9	15.9	0	9
30958	50	54	60	8.3	17.7	0	9.4
30069	65	76.1	60	12.6	24.6	0	12
30070	80	88.9	60	14.6	27.1	0	12.5
30071	100	108	60	18	31.7	0	13.7
30402	12	15	90	5.9	12.9	0	7
30403	15	18	90	6.1	13.3	0	7.2
30404	20	22	90	7	14.2	0	7.2
30405	25	28	90	7.9	15.5	0	7.6
30406	32	35	90	7.7	15.4	0	7.7

Art. no.	DN	d _ø mm	arc °	H cm	H1 cm	K cm	K1 max. cm
30407	40	42	90	9	18	0	9
30408	50	54	90	11.1	20.5	0	9.4
30089	65	76.1	90	16.6	28.6	0	12
30090	80	88.9	90	19.4	31.9	0	12.5
30091	100	108	90	24	37.7	0	13.7

These articles are suitable for the following system: **Geberit Mapress Stainless Steel**

30892	12	15	15	4	11	0	7
30893	15	18	15	4	11.2	0	7.1
30894	20	22	15	4.1	11.4	0	7.3
30905	25	28	15	4.3	11.9	0	7.6
30906	32	35	15	4.1	11.8	0	7.7
30907	40	42	15	4.7	13.7	0	9
30908	50	54	15	5.5	14.9	0	9.4

<i>Art. no.</i>	<i>DN</i>	<i>d_ø</i> <i>mm</i>	<i>arc</i> <i>°</i>	<i>H</i> <i>cm</i>	<i>H1</i> <i>cm</i>	<i>K</i> <i>cm</i>	<i>K1 max.</i> <i>cm</i>
30009	65	76.1	15	8.4	20.4	0	12
30010	80	88.9	15	9.5	22	0	12.5
30011	100	108	15	11.7	25.4	0	13.7
30932	12	15	30	4.3	11.3	0	7
30933	15	18	30	4.4	11.6	0	7.1
30934	20	22	30	4.6	11.8	0	7.2
30935	25	28	30	4.8	12.4	0	7.6
30936	32	35	30	4.6	12.3	0	7.7
30937	40	42	30	5.4	14.4	0	9
30938	50	54	30	6.3	15.7	0	9.4
30029	65	76.1	30	9.7	21.7	0	12
30030	80	88.9	30	11.1	23.6	0	12.5
30031	100	108	30	13.6	27.3	0	13.7

<i>Art. no.</i>	<i>DN</i>	<i>d_ø mm</i>	<i>arc °</i>	<i>H cm</i>	<i>H1 cm</i>	<i>K cm</i>	<i>K1 max. cm</i>
30872	12	15	45	4.5	11.6	0	7.1
30873	15	18	45	4.2	11.7	0	7.5
30874	20	22	45	5.2	12.3	0	7.1
30875	25	28	45	5.6	13.1	0	7.5
30876	32	35	45	5.3	12.9	0	7.6
30877	40	42	45	6.1	15.1	0	9
30878	50	54	45	7.3	16.7	0	9.4
30049	65	76.1	45	11.1	23	0	11.9
30050	80	88.9	45	13	25.2	0	12.2
30051	100	108	45	15.7	29.4	0	13.7
30942	12	15	60	5	12	0	7
30943	15	18	60	5.3	12.4	0	7.1
30944	20	22	60	5.6	12.8	0	7.2

Art. no.	DN	d _ø mm	arc °	H cm	H1 cm	K cm	K1 max. cm
30955	25	28	60	6.1	13.7	0	7.6
30956	32	35	60	5.9	13.6	0	7.7
30957	40	42	60	6.9	15.9	0	9
30958	50	54	60	8.3	17.7	0	9.4
30069	65	76.1	60	12.6	24.6	0	12
30070	80	88.9	60	14.6	27.1	0	12.5
30071	100	108	60	18	31.7	0	13.7
30402	12	15	90	5.9	12.9	0	7
30403	15	18	90	6.1	13.3	0	7.2
30404	20	22	90	7	14.2	0	7.2
30405	25	28	90	7.9	15.5	0	7.6
30406	32	35	90	7.7	15.4	0	7.7
30407	40	42	90	9	18	0	9

Art. no.	DN	d _g mm	arc °	H cm	H1 cm	K cm	K1 max. cm
30408	50	54	90	11.1	20.5	0	9.4
30089	65	76.1	90	16.6	28.6	0	12
30090	80	88.9	90	19.4	31.9	0	12.5
30091	100	108	90	24	37.7	0	13.7

These articles are suitable for the following system: **Geberit Mapress Stainless Steel (FKM blue)**

30892	12	15	15	4	11	0	7
30893	15	18	15	4	11.2	0	7.1
30894	20	22	15	4.1	11.4	0	7.3
30905	25	28	15	4.3	11.9	0	7.6
30906	32	35	15	4.1	11.8	0	7.7
30907	40	42	15	4.7	13.7	0	9
30908	50	54	15	5.5	14.9	0	9.4
30009	65	76.1	15	8.4	20.4	0	12

<i>Art. no.</i>	<i>DN</i>	<i>d_g</i> <i>mm</i>	<i>arc</i> <i>°</i>	<i>H</i> <i>cm</i>	<i>H1</i> <i>cm</i>	<i>K</i> <i>cm</i>	<i>K1 max.</i> <i>cm</i>
30010	80	88.9	15	9.5	22	0	12.5
30011	100	108	15	11.7	25.4	0	13.7
30932	12	15	30	4.3	11.3	0	7
30933	15	18	30	4.4	11.6	0	7.1
30934	20	22	30	4.6	11.8	0	7.2
30935	25	28	30	4.8	12.4	0	7.6
30936	32	35	30	4.6	12.3	0	7.7
30937	40	42	30	5.4	14.4	0	9
30938	50	54	30	6.3	15.7	0	9.4
30029	65	76.1	30	9.7	21.7	0	12
30030	80	88.9	30	11.1	23.6	0	12.5
30031	100	108	30	13.6	27.3	0	13.7
30872	12	15	45	4.5	11.6	0	7.1

<i>Art. no.</i>	<i>DN</i>	<i>d_ø mm</i>	<i>arc °</i>	<i>H cm</i>	<i>H1 cm</i>	<i>K cm</i>	<i>K1 max. cm</i>
30873	15	18	45	4.2	11.7	0	7.5
30874	20	22	45	5.2	12.3	0	7.1
30875	25	28	45	5.6	13.1	0	7.5
30876	32	35	45	5.3	12.9	0	7.6
30877	40	42	45	6.1	15.1	0	9
30878	50	54	45	7.3	16.7	0	9.4
30049	65	76.1	45	11.1	23	0	11.9
30050	80	88.9	45	13	25.2	0	12.2
30051	100	108	45	15.7	29.4	0	13.7
30942	12	15	60	5	12	0	7
30943	15	18	60	5.3	12.4	0	7.1
30944	20	22	60	5.6	12.8	0	7.2
30955	25	28	60	6.1	13.7	0	7.6

Art. no.	DN	d _g mm	arc °	H cm	H1 cm	K cm	K1 max. cm
30956	32	35	60	5.9	13.6	0	7.7
30957	40	42	60	6.9	15.9	0	9
30958	50	54	60	8.3	17.7	0	9.4
30069	65	76.1	60	12.6	24.6	0	12
30070	80	88.9	60	14.6	27.1	0	12.5
30071	100	108	60	18	31.7	0	13.7
30402	12	15	90	5.9	12.9	0	7
30403	15	18	90	6.1	13.3	0	7.2
30404	20	22	90	7	14.2	0	7.2
30405	25	28	90	7.9	15.5	0	7.6
30406	32	35	90	7.7	15.4	0	7.7
30407	40	42	90	9	18	0	9
30408	50	54	90	11.1	20.5	0	9.4

Art. no.	DN	d _g mm	arc °	H cm	H1 cm	K cm	K1 max. cm
30089	65	76.1	90	16.6	28.6	0	12
30090	80	88.9	90	19.4	31.9	0	12.5
30091	100	108	90	24	37.7	0	13.7

These articles are suitable for the following system: **Geberit Mapress Stainless Steel (gas)**

30892	12	15	15	4	11	0	7
30893	15	18	15	4	11.2	0	7.1
30894	20	22	15	4.1	11.4	0	7.3
30905	25	28	15	4.3	11.9	0	7.6
30906	32	35	15	4.1	11.8	0	7.7
30907	40	42	15	4.7	13.7	0	9
30908	50	54	15	5.5	14.9	0	9.4
30009	65	76.1	15	8.4	20.4	0	12
30010	80	88.9	15	9.5	22	0	12.5

<i>Art. no.</i>	<i>DN</i>	<i>d_ø</i> <i>mm</i>	<i>arc</i> <i>°</i>	<i>H</i> <i>cm</i>	<i>H1</i> <i>cm</i>	<i>K</i> <i>cm</i>	<i>K1 max.</i> <i>cm</i>
30011	100	108	15	11.7	25.4	0	13.7
30932	12	15	30	4.3	11.3	0	7
30933	15	18	30	4.4	11.6	0	7.1
30934	20	22	30	4.6	11.8	0	7.2
30935	25	28	30	4.8	12.4	0	7.6
30936	32	35	30	4.6	12.3	0	7.7
30937	40	42	30	5.4	14.4	0	9
30938	50	54	30	6.3	15.7	0	9.4
30029	65	76.1	30	9.7	21.7	0	12
30030	80	88.9	30	11.1	23.6	0	12.5
30031	100	108	30	13.6	27.3	0	13.7
30872	12	15	45	4.5	11.6	0	7.1
30873	15	18	45	4.2	11.7	0	7.5

<i>Art. no.</i>	<i>DN</i>	<i>d_ø mm</i>	<i>arc °</i>	<i>H cm</i>	<i>H1 cm</i>	<i>K cm</i>	<i>K1 max. cm</i>
30874	20	22	45	5.2	12.3	0	7.1
30875	25	28	45	5.6	13.1	0	7.5
30876	32	35	45	5.3	12.9	0	7.6
30877	40	42	45	6.1	15.1	0	9
30878	50	54	45	7.3	16.7	0	9.4
30049	65	76.1	45	11.1	23	0	11.9
30050	80	88.9	45	13	25.2	0	12.2
30051	100	108	45	15.7	29.4	0	13.7
30942	12	15	60	5	12	0	7
30943	15	18	60	5.3	12.4	0	7.1
30944	20	22	60	5.6	12.8	0	7.2
30955	25	28	60	6.1	13.7	0	7.6
30956	32	35	60	5.9	13.6	0	7.7

<i>Art. no.</i>	<i>DN</i>	<i>d_ø</i> <i>mm</i>	<i>arc</i> <i>°</i>	<i>H</i> <i>cm</i>	<i>H1</i> <i>cm</i>	<i>K</i> <i>cm</i>	<i>K1 max.</i> <i>cm</i>
30957	40	42	60	6.9	15.9	0	9
30958	50	54	60	8.3	17.7	0	9.4
30069	65	76.1	60	12.6	24.6	0	12
30070	80	88.9	60	14.6	27.1	0	12.5
30071	100	108	60	18	31.7	0	13.7
30402	12	15	90	5.9	12.9	0	7
30403	15	18	90	6.1	13.3	0	7.2
30404	20	22	90	7	14.2	0	7.2
30405	25	28	90	7.9	15.5	0	7.6
30406	32	35	90	7.7	15.4	0	7.7
30407	40	42	90	9	18	0	9
30408	50	54	90	11.1	20.5	0	9.4
30089	65	76.1	90	16.6	28.6	0	12

<i>Art. no.</i>	<i>DN</i>	<i>d_ø</i> <i>mm</i>	<i>arc</i> <i>°</i>	<i>H</i> <i>cm</i>	<i>H1</i> <i>cm</i>	<i>K</i> <i>cm</i>	<i>K1 max.</i> <i>cm</i>
30090	80	88.9	90	19.4	31.9	0	12.5
30091	100	108	90	24	37.7	0	13.7