

Low Input Offset Voltage & Low Noise

# Automotive High Precision & Input/Output Rail-to-Rail CMOS Operational Amplifier

TLR377YG-C TLR2377Yxxx-C TLR4377YFV-C

#### **General Description**

This product is a high precision & Input/Output Rail-to-Rail monolithic ICs integrated single, dual or quad independent CMOS Op-Amps on a single chip. It features low input offset voltage, low noise and low input bias current. It is suitable for automotive requirements such as engine control unit, electric power steering, anti-lock braking system, sensor amplifier, and so on.

#### **Features**

- AEC-Q100 Qualified(Note 1)
- Low input offset voltage
- Low Noise
- Input/Output Rail-to-Rail (Note 1) Grade 1

#### **Applications**

- Engine Control Unit
- Electric Power Steering (EPS)
- Anti-lock Braking System (ABS)
- Automotive Electronics
- Sensor Amplifiers
- Battery-powered Equipment
- Current Monitoring Amplifier
- ADC Front Ends, Buffer Amplifier
- Photodiode Amplifier
- Amplifiers

#### **Key Specifications**

■ Input Offset Voltage: 1.7 µV (Typ)

■ Input-Referred Noise Voltage Density

f = 10 Hz: 20 nV/ $\sqrt{\text{Hz}}$  (Typ) f = 1 kHz: 8 nV/ $\sqrt{\text{Hz}}$  (Typ)

■ Common-mode Input Voltage Range:

 $V_{SS}$  to  $V_{DD}$  0.5 pA (Typ)

Input Bias Current:Operating Supply Voltage Range

Single Supply: 2.5 V to 5.5 V Dual Supply: ±1.25 V to ±2.75 V


■ Operating Temperature Range: -40 °C to +125 °C

 Packages
 W (Typ) x D (Typ) x H (Max)

 SSOP5
 2.9 mm x 2.8 mm x 1.25 mm

MSOP8 2.9 mm x 4.0 mm x 0.9 mm SOP-J8 4.9 mm x 6.0 mm x 1.65 mm SSOP-B14 5.0 mm x 6.4 mm x 1.35 mm


#### **Typical Application Circuit**



$$V_{OUT} = -\frac{R_F}{R_{IN}} V_{IN}$$


#### **Pin Configurations**

TLR377YG-C: SSOP5




Pin No.	Pin Name	Function			
1	OUT	Output			
2	VSS	Negative power supply / Ground			
3	+IN	Non-inverting input			
4	-IN	Inverting input			
5	VDD	Positive power supply			

TLR2377YFVM-C: MSOP8 TLR2377YFJ-C: SOP-J8




Pin No.	Pin Name	Function		
1	OUT1	Output1		
2	-IN1	Inverting input1		
3	+IN1	Non-inverting input1		
4	VSS	Negative power supply / Ground		
5	+IN2	Non-inverting input2		
6	-IN2	Inverting input2		
7	OUT2	Output2		
8	VDD	Positive power supply		

TLR4377YFV-C: SSOP-B14



Pin No.	Pin Name	Function
1	OUT1	Output1
2	-IN1	Inverting input1
3	+IN1	Non-inverting input1
4	VDD	Positive power supply
5	+IN2	Non-inverting input2
6	-IN2	Inverting input2
7	OUT2	Output2
8	OUT3	Output3
9	-IN3	Inverting input3
10	+IN3	Non-inverting input3
11	VSS	Negative power supply / Ground
12	+IN4	Non-inverting input4
13	-IN4	Inverting input4
14	OUT4	Output4

#### **Block Diagram**



(Note) Each channel has the same configuration.

#### **Description of Blocks**

#### 1. AMP:

This block is a full-swing output operational amplifier with class-AB output circuit and high-precision-Rail-to-Rail differential input stage.

#### Iref:

This block supplies reference current which is needed to operate AMP block.

Absolute Maximum Ratings (Ta = 25 °C)

Parameter	Symbol	Rating	Unit
Supply Voltage (V <sub>DD</sub> - V <sub>SS</sub> )	Vs	7.0	V
Signal Input Pin Voltage (+IN, -IN)	Vı	(V <sub>SS</sub> - 0.3) to (V <sub>DD</sub> + 0.3)	V
Signal Input Pin Current (+IN, -IN)	l <sub>l</sub>	±10	mA
Maximum Junction Temperature	Tjmax	150	°C
Storage Temperature Range	Tstg	- 55 to + 150	°C

Caution 1: Operating the IC over the absolute maximum ratings may damage the IC. The damage can either be a short circuit between pins or an open circuit between pins and the internal circuitry. Therefore, it is important to consider circuit protection measures, such as adding a fuse, in case the IC is operate over the absolute maximum ratings.

Caution 2: Should by any chance the maximum junction temperature rating be exceeded the rise in temperature of the chip may result in deterioration of the properties of the chip. In case of exceeding this absolute maximum rating, design a PCB with thermal resistance taken into consideration by increasing board size and copper area so as not to exceed the maximum junction temperature rating.

#### Thermal Resistance(Note 1)

P		Thermal Re		
Parameter	Symbol	1s <sup>(Note 3)</sup>	2s2p <sup>(Note 4)</sup>	Unit
SSOP5	<u>, , , , , , , , , , , , , , , , , , , </u>			
Junction to Ambient	θја	376.5	185.4	°C/W
Junction to Top Characterization Parameter <sup>(Note 3)</sup>	$\Psi_{ m JT}$	40	30	°C/W
MSOP8				
Junction to Ambient	θЈА	284.1	135.4	°C/W
Junction to Top Characterization Parameter <sup>(Note 3)</sup>	$\Psi_{JT}$	21	11	°C/W
SOP-J8				
Junction to Ambient	θја	149.3	76.9	°C/W
Junction to Top Characterization Parameter <sup>(Note 3)</sup>	$\Psi_{ m JT}$	18	11	°C/W
SSOP-B14				
Junction to Ambient	θја	159.6	92.8	°C/W
Junction to Top Characterization Parameter <sup>(Note 3)</sup>	$\Psi_{JT}$	13	9	°C/W

<sup>(</sup>Note 1) Based on JESD51-2A(Still-Air).

<sup>(</sup>Note 4) Using a PCB board based on JESD51-7.

	1				
Layer Number of Measurement Board	Material	Board Size			
Single	FR-4	114.3 mm x 76.2 mm x	1.57 mmt		
Тор					
Copper Pattern	Thickness				
Footprints and Traces	70 µm				
Layer Number of Measurement Board	Material	Board Size			
	Material FR-4	Board Size 114.3 mm x 76.2 mm	x 1.6 mmt		
Measurement Board				Bottom	
Measurement Board 4 Layers		114.3 mm x 76.2 mm		Bottom Copper Pattern	Thickness

**Recommended Operating Conditions** 

Parameter	Symbol	Min	Тур	Max	Unit	
Supply Voltage (V V)	Single Supply	Vs	2.5	5.0	5.5	V
Supply Voltage (V <sub>DD</sub> - V <sub>SS</sub> )	Dual Supply	VS	±1.25	±2.5	±2.75	V
Operating Temperature		Topr	-40	+25	+125	°C

<sup>(</sup>Note 2) The thermal characterization parameter to report the difference between junction temperature and the temperature at the top center of the outside surface of the component package. (Note 3) Using a PCB board based on JESD51-3.

# Electrical Characteristics (Unless otherwise specified $V_S$ = 5 V, $V_{SS}$ = 0 V, $V_{ICM}$ = 2.5 V, $R_L$ = 10 k $\Omega$ to $V_{ICM}$ , Ta = 25 °C)

_	_		Limit			
Parameter	Symbol	Min	Тур	Max	- Unit	Conditions
		-	1.7	1200		No load, Absolute value
Input Offset Voltage	V <sub>IO</sub>	-	-	1300	μV	No load, Absolute value, Ta = -40 °C to +125 °C
Input Offset Voltage Temperature Drift	ΔV10/ΔΤ	-	0.1	4.0	μV/°C	Absolute value, No load, Ta = -40 °C to +125 °C
Input Offset Current	lıo	-	0	-	pА	Absolute value
Input Bias Current	lΒ	-	0.5	-	pA	Absolute value
Common-mode Input Voltage Range	VICMR	0	-	5	V	Vss to V <sub>DD</sub>
		-	645	950		TLR377YG-C, No load, G = 0 dB
		-	-	1000		TLR377YG-C, No load, G = 0 dB, Ta = -40 °C to +125 °C
		-	1245	1900	-	TLR2377Yxxx-C, No load, G = 0 dB
Supply Current	I <sub>DD</sub>	-	_	2000	μA	TLR2377Yxxx-C, No load, G = 0 dB, Ta = -40 °C to +125 °C
		_	2490	3800	_	TLR4377YFV-C, No load, G = 0 dB
		-	-	4000		TLR4377YFV-C, No load, G = 0 dB, Ta = -40 °C to +125 °C
		4.925	4.975	_		I <sub>L</sub> = 1 mA
Output Voltage High	Vон	4.90	-	-	V	I <sub>L</sub> = 1 mA, Ta = -40 °C to +125 °C
		4.50	4.75	-		I <sub>L</sub> = 10 mA
		-	15	50		I <sub>L</sub> = 1 mA
Output Voltage Low	V <sub>OL</sub>	-	-	60	mV	I <sub>L</sub> = 1 mA, Ta = -40 °C to +125 °C
		-	100	250	=	I <sub>L</sub> = 10 mA
Output Source Current (Note 1)	I <sub>OH</sub>	25	50	-	mA	V <sub>OUT</sub> = V <sub>SS</sub> , Absolute value
Output Sink Current (Note 1)	loL	25	50	-	mA	V <sub>OUT</sub> = V <sub>DD</sub> , Absolute value
Larga Cianal Valtaga Caia		110	137	-	40	-
Large Signal Voltage Gain	Av	90	-	-	- dB	Ta = -40 °C to +125 °C
Gain Bandwidth Product	GBW	-	4	-	MHz	G = 40 dB
Phase Margin	θ	-	50	-	deg	G = 40 dB
Common-mode Rejection Ratio	CMRR	80	100	-	dB	-
Power Supply Rejection Ratio	PSRR	75	95	-	dB	-
Slew Rate	SR	-	2	-	V/µs	C <sub>L</sub> = 25 pF
Input-Referred Noise Voltage	Vn	-	20	-	nV/√Hz	f = 10 Hz
Density	VII	-	8	-	11V/ \\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	f = 1 kHz
Total Harmonic Distortion + Noise	THD+N	-	0.001	-	%	Vоит = 4 Vp-p, f = 1 kHz
Channel Separation (Note 2)	CS	-	100	-	dB	input referred

<sup>(</sup>Note 1) Consider the power dissipation of the IC under high temperature environment when selecting the output current value. When the output pin is short-circuited continuously, the output current may decrease due to the temperature rise by the heat generation of inside the IC.

(Note 2) TLR2377Yxxx-C, TLR4377YFV-C

#### **Typical Performance Curves**

 $V_{SS} = 0 V$ 




Figure 1. Supply Current vs Supply Voltage




Figure 2. Supply Current vs Ambient Temperature




Figure 3. Output Voltage High vs Supply Voltage (I<sub>L</sub> = 1 mA)




Figure 4. Output Voltage High vs Ambient Temperature ( $V_S = 5 \text{ V}, I_L = 1 \text{ mA}$ )

 $V_{SS} = 0 V$ 




Figure 5. Output Voltage Low vs Supply Voltage (I∟ = 1 mA)




Figure 6. Output Voltage Low vs Ambient Temperature  $(V_S = 5 \text{ V}, I_L = 1 \text{ mA})$ 




Figure 7. Output Source Current vs Output Voltage  $(V_S = 5 V)$ 





Figure 8. Output Sink Current vs Output Voltage  $(V_S = 5 V)$ 










Figure 9. Input Offset Voltage vs Supply Voltage

Figure 10. Input Offset Voltage vs Ambient Temperature









Figure 12. Large Signal Voltage Gain vs Supply Voltage ( $R_L = 10 \text{ k}\Omega$ )

 $V_{SS} = 0 V$ 







Figure 13. Large Signal Voltage Gain vs Ambient Temperature

Figure 14. Common-mode Rejection Ratio vs Supply Voltage








Figure 16. Power Supply Rejection Ratio vs Ambient Temperature

 $V_{SS} = 0 V$ 




Figure 17. Input Bias Current vs Ambient Temperature  $(V_S = 5 V)$ 

Figure 18. Input-Referred Noise Voltage Density vs Frequency (Vs = 5 V)




Figure 19. Slew Rate vs Supply Voltage





Figure 20. Slew Rate vs Ambient Temperature (Vs = 5 V)

# Typical Performance Curves - continued $V_{SS} = 0 \ V$






Figure 21. Gain Bandwidth Product vs Ambient Temperature

25

50

Ambient Temperature Ta [°C]

75

100

125

150

-50

-25

0

Figure 22. Phase Margin vs Load Capacitance ( $V_S = 5 \text{ V}$ ,  $R_F = 10 \text{ k}\Omega$ , G = 40 dB)




Figure 23. Voltage Gain, Phase vs Frequency  $(V_S = 5 V)$ 

Figure 24. Voltage Gain vs Frequency  $(V_S = 5 \text{ V}, G = 0 \text{ dB}, V_{IN} = 180 \text{ mV}_{P-P})$ 

#### **Application Examples**

#### Voltage Follower




Figure 25. Voltage Follower Circuit

Using this circuit, the output voltage ( $V_{OUT}$ ) is configured to be equal to the input voltage ( $V_{IN}$ ). This circuit also stabilizes the output voltage due to high input impedance and low output impedance. Computation for output voltage is shown below.

$$V_{OIIT} = V_{IN}$$

#### oInverting Amplifier




Figure 26. Inverting Amplifier Circuit

For inverting amplifier, input voltage ( $V_{IN}$ ) is amplified by a voltage gain which depends on the ratio of  $R_{IN}$  and  $R_{F}$ , and then it outputs phase-inverted voltage ( $V_{OUT}$ ). The output voltage is shown in the next expression.

$$V_{OUT} = -\frac{R_F}{R_{IN}} V_{IN}$$

This circuit has input impedance equal to R<sub>IN</sub>.

#### ONon-inverting Amplifier




Figure 27. Non-inverting Amplifier Circuit

For non-inverting amplifier, input voltage  $(V_{IN})$  is amplified by a voltage gain, which depends on the ratio of  $R_{IN}$  and  $R_F$ . The output voltage  $(V_{OUT})$  is in-phase with the input voltage and is shown in the next expression.

$$V_{OUT} = \left(1 + \frac{R_F}{R_{IN}}\right) V_{IN}$$

Effectively, this circuit has high input impedance since its input side is the same as that of the operational amplifier.

# I/O Equivalence Circuits •TLR377YG-C

Pin No.	Pin Name	Pin Description	Equivalence Circuit
1	OUT	Output	5
3 4	+IN -IN	Input	3, 4

#### ∘TLR2377Yxxx-C

_R23//YXXX-			
Pin No.	. Pin Name	Pin Description	Equivalence Circuit
1 7	OUT1 OUT2	Output	1,7
2 3 5 6	-IN1 +IN1 +IN2 -IN2	Input	2, 3, 5, 6

∘TLR4377YFV-C

LR4377YFV-C			
Pin No.	Pin Name	Pin Description	Equivalence Circuit
1 7 8 14	OUT1 OUT2 OUT3 OUT4	Output	11,7
2 3 5 6 9 10 12	-IN1 +IN1 +IN2 -IN2 -IN3 +IN3 +IN4 -IN4	Input	2, 3, 5, 6 9,10,12,13

#### **Operational Notes**

#### 1. Reverse Connection of Power Supply

Connecting the power supply in reverse polarity can damage the IC. Take precautions against reverse polarity when connecting the power supply, such as mounting an external diode between the power supply and the IC's power supply pins.

#### 2. Power Supply Lines

Design the PCB layout pattern to provide low impedance supply lines. Furthermore, connect a capacitor to ground at all power supply pins. Consider the effect of temperature and aging on the capacitance value when using electrolytic capacitors.

#### 3. Ground Voltage

Ensure that no pins are at a voltage below that of the ground pin at any time, even during transient condition.

#### 4. Ground Wiring Pattern

When using both small-signal and large-current ground traces, the two ground traces should be routed separately but connected to a single ground at the reference point of the application board to avoid fluctuations in the small-signal ground caused by large currents. Also ensure that the ground traces of external components do not cause variations on the ground voltage. The ground lines must be as short and thick as possible to reduce line impedance.

#### 5. Recommended Operating Conditions

The function and operation of the IC are guaranteed within the range specified by the recommended operating conditions. The characteristic values are guaranteed only under the conditions of each item specified by the electrical characteristics.

#### 6. Inrush Current

When power is first supplied to the IC, it is possible that the internal logic may be unstable and inrush current may flow instantaneously due to the internal powering sequence and delays, especially if the IC has more than one power supply. Therefore, give special consideration to power coupling capacitance, power wiring, width of ground wiring, and routing of connections.

#### 7. Testing on Application Boards

When testing the IC on an application board, connecting a capacitor directly to a low-impedance output pin may subject the IC to stress. Always discharge capacitors completely after each process or step. The IC's power supply should always be turned off completely before connecting or removing it from the test setup during the inspection process. To prevent damage from static discharge, ground the IC during assembly and use similar precautions during transport and storage.

#### 8. Inter-pin Short and Mounting Errors

Ensure that the direction and position are correct when mounting the IC on the PCB. Incorrect mounting may result in damaging the IC. Avoid nearby pins being shorted to each other especially to ground, power supply and output pin. Inter-pin shorts could be due to many reasons such as metal particles, water droplets (in very humid environment) and unintentional solder bridge deposited in between pins during assembly to name a few.

#### 9. Unused Input Pins

Input pins of an IC are often connected to the gate of a MOS transistor. The gate has extremely high impedance and extremely low capacitance. If left unconnected, the electric field from the outside can easily charge it. The small charge acquired in this way is enough to produce a significant effect on the conduction through the transistor and cause unexpected operation of the IC. So unless otherwise specified, unused input pins should be connected to the power supply or ground line.

#### **Operational Notes - continued**

#### 10. Regarding the Input Pin of the IC

This monolithic IC contains P+ isolation and P substrate layers between adjacent elements in order to keep them isolated. P-N junctions are formed at the intersection of the P layers with the N layers of other elements, creating a parasitic diode or transistor. For example (refer to figure below):

When GND > Pin A and GND > Pin B, the P-N junction operates as a parasitic diode. When GND > Pin B, the P-N junction operates as a parasitic transistor.

Parasitic diodes inevitably occur in the structure of the IC. The operation of parasitic diodes can result in mutual interference among circuits, operational faults, or physical damage. Therefore, conditions that cause these diodes to operate, such as applying a voltage lower than the GND voltage to an input pin (and thus to the P substrate) should be avoided.





Figure 28. Example of monolithic IC structure

#### 11. Ceramic Capacitor

When using a ceramic capacitor, determine a capacitance value considering the change of capacitance with temperature and the decrease in nominal capacitance due to DC bias and others.


#### **Ordering Information**





Lineup


Operating Temperature Range	Operating Supply Voltage	Number of Channels	Pac	ckage	Orderable Part Number
-40 °C to +125 °C	2.5 V to 5.5 V	Single	SSOP5	Reel of 3000	TLR377YG-CTR
		Dual	MSOP8	Reel of 3000	TLR2377YFVM-CTR
			SOP-J8	Reel of 2500	TLR2377YFJ-CE2
		Quad	SSOP-B14	Reel of 2500	TLR4377YFV-CE2


#### **Marking Diagrams**

















**Physical Dimension and Packing Information - continued** SSOP-B14 Package Name 5. 0±0. 2 (Max 5. 35 (include. BURR) 9 3MIN o. 0.  $15\pm0.1$ (UNIT:mm)  $\dot{\circ}$ 0. 22±0. 1 0. 08 N 0.65 PKG:SSOP-B14 Drawing No. EX152-5002 0.1 < Tape and Reel Information > Таре Embossed carrier tape Quantity 2500pcs Direction of feed The direction is the pin 1 of product is at the upper left when you hold reel on the left hand and you pull out the tape on the right hand 0 0 0 0 0 0 0 0 0  $\circ$ TR E2 TR E2 E2 TR E2 TR E2 TR E2 TR Ε1 TL Ε1 TL E1 TL E1 E1 TL Ε1 Direction of feed Pocket Quadrants Reel

#### **Revision History**

Date	Revision	Changes	
16.Oct.2020	ct.2020 001 New Release		
22.Feb.2021	002	Add Lineup	
		Page 1 and 4 Input Bias Current Change Typ Limits	
10.Aug.2021 003 Add Lineup		Add Lineup	

# **Notice**

#### **Precaution on using ROHM Products**

1. If you intend to use our Products in devices requiring extremely high reliability (such as medical equipment (Note 1), aircraft/spacecraft, nuclear power controllers, etc.) and whose malfunction or failure may cause loss of human life, bodily injury or serious damage to property ("Specific Applications"), please consult with the ROHM sales representative in advance. Unless otherwise agreed in writing by ROHM in advance, ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of any ROHM's Products for Specific Applications.

(Note1) Medical Equipment Classification of the Specific Applications

ſ	JÁPAN	USA	EU	CHINA
Ī	CLASSⅢ	CLASSII	CLASS II b	CLASSIII
ſ	CLASSIV		CLASSⅢ	

- 2. ROHM designs and manufactures its Products subject to strict quality control system. However, semiconductor products can fail or malfunction at a certain rate. Please be sure to implement, at your own responsibilities, adequate safety measures including but not limited to fail-safe design against the physical injury, damage to any property, which a failure or malfunction of our Products may cause. The following are examples of safety measures:
  - [a] Installation of protection circuits or other protective devices to improve system safety
  - [b] Installation of redundant circuits to reduce the impact of single or multiple circuit failure
- 3. Our Products are not designed under any special or extraordinary environments or conditions, as exemplified below. Accordingly, ROHM shall not be in any way responsible or liable for any damages, expenses or losses arising from the use of any ROHM's Products under any special or extraordinary environments or conditions. If you intend to use our Products under any special or extraordinary environments or conditions (as exemplified below), your independent verification and confirmation of product performance, reliability, etc, prior to use, must be necessary:
  - [a] Use of our Products in any types of liquid, including water, oils, chemicals, and organic solvents
  - [b] Use of our Products outdoors or in places where the Products are exposed to direct sunlight or dust
  - [c] Use of our Products in places where the Products are exposed to sea wind or corrosive gases, including Cl<sub>2</sub>, H<sub>2</sub>S, NH<sub>3</sub>, SO<sub>2</sub>, and NO<sub>2</sub>
  - [d] Use of our Products in places where the Products are exposed to static electricity or electromagnetic waves
  - [e] Use of our Products in proximity to heat-producing components, plastic cords, or other flammable items
  - [f] Sealing or coating our Products with resin or other coating materials
  - [g] Use of our Products without cleaning residue of flux (Exclude cases where no-clean type fluxes is used. However, recommend sufficiently about the residue.); or Washing our Products by using water or water-soluble cleaning agents for cleaning residue after soldering
  - [h] Use of the Products in places subject to dew condensation
- 4. The Products are not subject to radiation-proof design.
- 5. Please verify and confirm characteristics of the final or mounted products in using the Products.
- 6. In particular, if a transient load (a large amount of load applied in a short period of time, such as pulse, is applied, confirmation of performance characteristics after on-board mounting is strongly recommended. Avoid applying power exceeding normal rated power; exceeding the power rating under steady-state loading condition may negatively affect product performance and reliability.
- 7. De-rate Power Dissipation depending on ambient temperature. When used in sealed area, confirm that it is the use in the range that does not exceed the maximum junction temperature.
- 8. Confirm that operation temperature is within the specified range described in the product specification.
- ROHM shall not be in any way responsible or liable for failure induced under deviant condition from what is defined in this document.

#### Precaution for Mounting / Circuit board design

- 1. When a highly active halogenous (chlorine, bromine, etc.) flux is used, the residue of flux may negatively affect product performance and reliability.
- 2. In principle, the reflow soldering method must be used on a surface-mount products, the flow soldering method must be used on a through hole mount products. If the flow soldering method is preferred on a surface-mount products, please consult with the ROHM representative in advance.

For details, please refer to ROHM Mounting specification

#### **Precautions Regarding Application Examples and External Circuits**

- 1. If change is made to the constant of an external circuit, please allow a sufficient margin considering variations of the characteristics of the Products and external components, including transient characteristics, as well as static characteristics.
- You agree that application notes, reference designs, and associated data and information contained in this document are presented only as guidance for Products use. Therefore, in case you use such information, you are solely responsible for it and you must exercise your own independent verification and judgment in the use of such information contained in this document. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of such information.

#### **Precaution for Electrostatic**

This Product is electrostatic sensitive product, which may be damaged due to electrostatic discharge. Please take proper caution in your manufacturing process and storage so that voltage exceeding the Products maximum rating will not be applied to Products. Please take special care under dry condition (e.g. Grounding of human body / equipment / solder iron, isolation from charged objects, setting of lonizer, friction prevention and temperature / humidity control).

#### **Precaution for Storage / Transportation**

- 1. Product performance and soldered connections may deteriorate if the Products are stored in the places where:
  - [a] the Products are exposed to sea winds or corrosive gases, including Cl<sub>2</sub>, H<sub>2</sub>S, NH<sub>3</sub>, SO<sub>2</sub>, and NO<sub>2</sub>
  - [b] the temperature or humidity exceeds those recommended by ROHM
  - [c] the Products are exposed to direct sunshine or condensation
  - [d] the Products are exposed to high Electrostatic
- Even under ROHM recommended storage condition, solderability of products out of recommended storage time period
  may be degraded. It is strongly recommended to confirm solderability before using Products of which storage time is
  exceeding the recommended storage time period.
- 3. Store / transport cartons in the correct direction, which is indicated on a carton with a symbol. Otherwise bent leads may occur due to excessive stress applied when dropping of a carton.
- 4. Use Products within the specified time after opening a humidity barrier bag. Baking is required before using Products of which storage time is exceeding the recommended storage time period.

#### **Precaution for Product Label**

A two-dimensional barcode printed on ROHM Products label is for ROHM's internal use only.

#### **Precaution for Disposition**

When disposing Products please dispose them properly using an authorized industry waste company.

#### **Precaution for Foreign Exchange and Foreign Trade act**

Since concerned goods might be fallen under listed items of export control prescribed by Foreign exchange and Foreign trade act, please consult with ROHM in case of export.

#### **Precaution Regarding Intellectual Property Rights**

- 1. All information and data including but not limited to application example contained in this document is for reference only. ROHM does not warrant that foregoing information or data will not infringe any intellectual property rights or any other rights of any third party regarding such information or data.
- 2. ROHM shall not have any obligations where the claims, actions or demands arising from the combination of the Products with other articles such as components, circuits, systems or external equipment (including software).
- 3. No license, expressly or implied, is granted hereby under any intellectual property rights or other rights of ROHM or any third parties with respect to the Products or the information contained in this document. Provided, however, that ROHM will not assert its intellectual property rights or other rights against you or your customers to the extent necessary to manufacture or sell products containing the Products, subject to the terms and conditions herein.

#### Other Precaution

- 1. This document may not be reprinted or reproduced, in whole or in part, without prior written consent of ROHM.
- 2. The Products may not be disassembled, converted, modified, reproduced or otherwise changed without prior written consent of ROHM.
- In no event shall you use in any way whatsoever the Products and the related technical information contained in the Products or this document for any military purposes, including but not limited to, the development of mass-destruction weapons.
- 4. The proper names of companies or products described in this document are trademarks or registered trademarks of ROHM, its affiliated companies or third parties.

Notice-PAA-E Rev.004

#### **General Precaution**

- 1. Before you use our Products, you are requested to carefully read this document and fully understand its contents. ROHM shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sales representative.
- 3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate and/or error-free. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.

Notice – WE Rev.001