

User Manual
SKU: ABX00156

Description

The Arduino Bughopper is a compact USB-to-UART bridge board designed to bring straightforward remote debugging to the Arduino UNO Q via its 1.27 mm connector. Built around the FT230XQ, the Bughopper provides a reliable, high-speed serial link between your development machine and the UNO Q, enabling advanced debugging and logging without occupying the board's main I/O pins. Its compact 38.5 × 11 mm footprint, USB-C® connectivity, and multiple header options make it easy to integrate into any workspace, enclosure, or automated test setup.

Target Areas:

Embedded development, hardware testing, education



CONTENTS

1 Application Examples	3
2 Features	4
2.1 General Specifications Overview	4
2.2 Related Products	5
3 Ratings	6
3.1 Recommended Operating Conditions	6
4 Functional Overview	7
4.1 Pinout	7
4.2 Block Diagram	8
4.3 Power Supply	9
5 Device Operation	10
5.1 Getting Started - Arduino App Lab	10
5.2 FTDI Drivers	11
5.3 Sample Sketches	11
5.4 Online Resources	11
6 Mechanical Information	12
6.1 Board Dimensions	12
6.2 Board Connectors	13
6.3 Board Peripherals and Actuators	14
7 Product Compliance	15
7.1 Product Compliance Summary	15
7.2 Declaration of Conformity CE DoC (EU)	15
7.3 Declaration of Conformity to EU RoHS & REACH 211 01/19/2021	15
7.4 Conflict Minerals Declaration	16
8 Company Information	16
9 Reference Documentation	16
10 Document Revision History	17

1 Application Examples

The Arduino Bughopper, when connected to an Arduino UNO Q board, provides a dedicated debugging and serial communication channel for various development scenarios. Below are some application examples that demonstrate its practical value:

- **Embedded development and debugging:** The Bughopper streamlines the firmware development workflow by providing a dedicated debug serial channel that does not interfere with the UNO Q's main I/O pins.
 - **Remote debug over serial:** Connect the Bughopper to the UNO Q's 1.27 mm connector to establish a dedicated UART link for real-time debugging. Developers can monitor serial output, send debug commands, and inspect firmware behavior directly from their development machine via USB-C, all without occupying the UNO Q's primary serial port or I/O headers.
 - **Firmware flashing and continuous UART logging:** Use the Bughopper as a persistent serial interface for firmware updates and continuous data logging during long-running tests. Its reliable USB-to-UART bridge (FT230XQ) ensures stable communication at data rates from 300 baud to 3 Mbaud, making it suitable for both routine flashing and high-throughput logging scenarios.
 - **Research and development (R&D) and testing:** The Bughopper enables R&D teams and test engineers to integrate reliable debug access into their prototyping and validation workflows.
 - **Field diagnostics and automated test:** Install the Bughopper into automated testing rigs to provide consistent, hands-free serial access to UNO Q boards. Its compact form factor and dual header options (2.54 mm female and 1.27 mm male) allow integration into custom test fixtures, enabling field diagnostics and continuous integration pipelines for hardware and software validation.
 - **Education and training labs:** The Bughopper offers a low-cost, student-friendly tool for teaching serial communication protocols and hardware debugging fundamentals.
 - **Teaching UART communication and debugging workflows:** Institutions teaching embedded systems, Internet of Things (IoT) development, or hardware debugging can use the Bughopper with UNO Q boards to provide hands-on lab exercises. Students learn serial communication protocols, debugging techniques, and project troubleshooting using a modern USB-C interface with clear power status LEDs for quick visual feedback.



2 Features

2.1 General Specifications Overview

The Arduino Bughopper is a compact USB-to-UART bridge board built around the FT230XQ from FTDI. Designed exclusively for the Arduino UNO Q, it connects via the 1.27 mm connector to provide a dedicated debug and serial communication channel that does not interfere with the board's main I/O.

The main features of the Bughopper are highlighted in the table shown below.

Feature	Description
USB-to-UART Bridge	FTDI FT230XQ-R, USB 2.0 Full Speed, data rates from 300 baud to 3 Mbaud
USB Connector	USB-C for modern, reversible connections
Level Translator	Bidirectional voltage-level translator (SN74AVC2T245RSWR) for safe UART communication between +3.3 VDC and +1.8 VDC domains
ESD Protection	Onboard electrostatic discharge protection on USB (ESD321DYAR) and signal (STN1010SB301) lines
Header Connectors	Female 2.54 mm 2×5 header for direct cable attachment; male 1.27 mm 2×5 header (FTSH-105-01-L-DH-C-TR) for compact ribbon cable setups
Auxiliary GPIO Lines	Configurable CBUS outputs (x4, via 2N7002PS MOSFETs)
Onboard LEDs	Green (+3.3 VDC power), red (+1.8 VDC status), yellow (x2, TXD and RXD activity)
Power Supply	+5 VDC via USB-C; +3.3 VDC generated by the FT230XQ internal voltage regulator
Target Board Compatibility	Arduino UNO Q (via 1.27 mm connector)
Dimensions	38.5 mm × 11 mm
Weight	TBD



2.2 Related Products

- Arduino® UNO™ Q 2GB (SKU: ABX00162)
- Arduino® UNO™ Q 4GB (SKU: ABX00173)

3 Ratings

3.1 Recommended Operating Conditions

The table below provides a comprehensive guideline for the optimal use of the Arduino Bughopper, outlining typical operating conditions and design limits. The operating conditions of the Bughopper are largely based on the specifications of the FT230XQ USB-to-UART bridge and the board's level translator (SN74AVC2T245RSWR).

Parameter	Symbol	Min	Typ	Max	Unit
USB Supply Voltage	V_{USB}	4.75	5.0	5.25	V
FT230XQ Supply Voltage	VCC	2.97	5.0	5.5	V
Internal LDO Output Voltage	$V_{3V3\text{OUT}}$	2.97	3.3	3.63	V
Target Voltage ¹	V_{TARGET}	-	1.8	-	V
Operating Temperature	T_{OP}	-40	-	85	°C
Operating Current (Active)	I_{OP}	-	8	-	mA
USB Suspend Current	I_{SUSP}	-	125	-	µA


¹ V_{TARGET} is the voltage level supplied by the connected Arduino UNO Q board through the 1.27 mm connector. This voltage is used as the reference for the level translator (target side) and the V_{TARGET} status LED.

Driver Tip: The Bughopper uses the FT230XQ from FTDI, which is supported by FTDI's royalty-free **Virtual Com Port (VCP)** and **Direct (D2XX)** drivers. These drivers are [available for Windows, macOS, and Linux](#), and enable the board to appear as a standard serial COM port on your development machine.

Safety Note: The Bughopper is powered exclusively through its USB-C connector. **Do not attempt to supply external power through the header connector pins.** Ensure that the 1.27 mm connector is properly aligned before connecting the board to the Arduino UNO Q to prevent damage to both boards.

4.2 Block Diagram

An overview of the high-level architecture of the Arduino Bughopper is illustrated in the figure below.




Bughopper Bughopper high-level architecture block diagram.

The Bughopper's architecture can be summarized in the following functional blocks:

- **USB-C connector:** Provides the physical USB interface to the host development machine. Includes ESD protection (ESD321DYAR) on the data lines and a TVS diode (STN1010SB301) on V_{BUS} .
- **FTDI FT230XQ:** The central IC of the board. It handles the entire USB protocol, converts USB data to UART signals (TXD, RXD), generates +3.3 VDC via its internal voltage regulator, and provides four configurable GPIOs.
- **Level translator (SN74AVC2T245RSWR):** Performs bidirectional voltage-level translation between the FT230XQ's +3.3 VDC UART signals and the V_{TARGET} domain (+1.8 VDC) of the connected UNO Q board, ensuring safe communication across different voltage levels.
- **Auxiliary GPIO Lines (x4, via 2N7002PS MOSFETs):** Convert the FT230XQ's CBUS outputs to open-drain signals, allowing flexible interfacing with external circuits through the board's header connectors.
- **Status LEDs:** Four LEDs provide at-a-glance status: green (+3.3 VDC power), red (V_{TARGET} , +1.8 VDC), and two yellow (TXD and RXD activity).

4.3 Power Supply

The Arduino Bughopper is powered through its USB-C connector:



Bughopper power tree.

- **USB-C connector (+5 VDC):** The primary and only power input. When connected to a USB host (development machine), the board receives +5 VDC through V_{BUS} . This voltage powers the FT230XQ's VCC pin directly.
- **Internal +3.3 VDC LDO (FT230XQ-R V_{3V3OUT}):** The FT230XQ-R generates +3.3 VDC from the +5 VDC USB supply using its integrated LDO regulator. This regulated output powers the FT230XQ and the level translator's host side.
- **V_{TARGET}:** This is not a power input to the Bughopper. It is the voltage reference supplied by the connected Arduino UNO Q through the 1.27 mm connector. V_{TARGET} is used as the reference for the level translator's target side and as the supply for the V_{TARGET} LED.

Power Tip: The Bughopper draws approximately 8 mA during active operation and approximately 125 μ A during USB suspend, making it suitable for always-connected debug setups with minimal power overhead.

Safety Note: Do not attempt to power the Bughopper through any pin other than the USB-C connector. **The header connector pins are designed for signal communication and voltage reference only, not for supplying power to the board.**

5 Device Operation

5.1 Getting Started - Arduino App Lab

The Arduino UNO Q is programmed through Arduino App Lab **[1]**, a unified editor that builds and runs projects on the board's dual-processor architecture: a Linux system (Qualcomm Dragonwing™ QRB2210) and a microcontroller (STM32U585). The Arduino Bughopper complements this workflow by providing an independent serial debug channel through the UNO Q's 1.27 mm connector, accessible from any serial terminal application on your development machine.

To set up the Bughopper with the UNO Q:

1. Connect the Bughopper to the UNO Q's 1.27 mm connector using the appropriate header cable.
2. Connect the Bughopper to your development machine using a USB-C data cable.
3. The board will appear as a standard serial COM port on your system thanks to FTDI's Virtual Com Port (VCP) drivers.
4. Open a serial terminal application (such as the Arduino IDE Serial Monitor, PuTTY, or any other terminal emulator) and select the Bughopper's COM port.
5. Use Arduino App Lab **[1]** to develop and deploy your Apps on the UNO Q. Debug output routed through the 1.27 mm connector will appear in the Bughopper's serial terminal, independently of the Arduino App Lab console.

Note: The Bughopper provides a serial channel that is **separate** from the UNO Q's main USB-C connection. This means you can monitor debug output through the Bughopper while Arduino App Lab communicates with the UNO Q through its own USB-C or network connection, without any interference between the two channels.



5.2 FTDI Drivers

The Bughopper uses the FTDI FT230XQ, which requires FTDI's VCP (Virtual Com Port) or D2XX drivers to be installed on your development machine. These drivers are [available for Windows, macOS, and Linux](#), and enable the board to appear as a standard serial COM port on your development machine [3]. Most modern operating systems include built-in FTDI driver support.

5.3 Sample Sketches

Sample sketches demonstrating the use of the Bughopper with the Arduino UNO Q can be found either in the "Examples" section of the Arduino App Lab [1] or in the "Bughopper Documentation" section of Arduino documentation [4].

5.4 Online Resources


Explore community projects on Arduino Project Hub [5], browse the Arduino Library Reference [6] for supported libraries, and find accessories such as Modulino nodes in the Arduino Store [7].

6 Mechanical Information


The Arduino Bughopper is a compact, double-sided board with a USB-C connector on one end, a female 2.54 mm 2×5 header on the opposite end, and a male 1.27 mm 2×5 header (J3) adjacent to it. The PCB body measures 35 mm × 11 mm; the overall board dimension, including the J3 1.27 mm header overhang, is 38.5 mm × 11 mm. The board's narrow form factor is designed for easy integration into workspaces, enclosures, and automated test fixtures.

6.1 Board Dimensions

The Bughopper board outline is shown in the figure below; **all the dimensions are in mm.**




Bughopper board outline dimensions (top view); all dimensions are in mm.




Bughopper board outline dimensions (side view); all dimensions are in mm.

6.2 Board Connectors

The Bughopper features three connectors: a USB-C connector on one end for host communication and power, a female 2.54 mm 2×5 header for direct cable attachment, and a male 1.27 mm 2×5 header (FTSH-105-01-L-DH-C-TR) for compact ribbon cable connections. The placement of these connectors is shown in the figure below; **all the dimensions are in mm.**




Bughopper board connectors placement (top view); all dimensions are in mm.



Bughopper board connectors placement (bottom view); all dimensions are in mm.

6.3 Board Peripherals and Actuators

The Bughopper has four onboard LEDs that provide visual status feedback. A green LED indicates the +3.3 VDC power rail status, a red LED indicates the V_{TARGET} rail status, and two yellow LEDs indicate TXD and RXD serial activity, respectively. The placement of these LEDs is shown in the figure below; **all the dimensions are in mm.**



Bughopper board LEDs placement (top view); all dimensions are in mm.



7 Product Compliance

7.1 Product Compliance Summary

Product Compliance
CE (European Union)
RoHS
REACH
WEEE

7.2 Declaration of Conformity CE DoC (EU)

We declare under our sole responsibility that the products above are in conformity with the essential requirements of the following EU Directives and therefore qualify for free movement within markets comprising the European Union (EU) and European Economic Area (EEA).

7.3 Declaration of Conformity to EU RoHS & REACH 211 01/19/2021

Arduino boards are in compliance with RoHS 2 Directive 2011/65/EU of the European Parliament and RoHS 3 Directive 2015/863/EU of the Council of 4 June 2015 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

Substance	Maximum Limit (ppm)
Lead (Pb)	1000
Cadmium (Cd)	100
Mercury (Hg)	1000
Hexavalent Chromium (Cr6+)	1000
Poly Brominated Biphenyls (PBB)	1000
Poly Brominated Diphenyl ethers (PBDE)	1000
Bis(2-Ethylhexyl) phthalate (DEHP)	1000
Benzyl butyl phthalate (BBP)	1000
Dibutyl phthalate (DBP)	1000
Diisobutyl phthalate (DIBP)	1000



Exemptions: No exemptions are claimed.

Arduino Boards are fully compliant with the related requirements of European Union Regulation (EC) 1907 /2006 concerning the Registration, Evaluation, Authorization and Restriction of Chemicals (REACH). We declare none of the SVHCs (<https://echa.europa.eu/web/guest/candidate-list-table>), the Candidate List of Substances of Very High Concern for authorization currently released by ECHA, is present in all products (and also package) in quantities totaling in a concentration equal or above 0.1%. To the best of our knowledge, we also declare that our products do not contain any of the substances listed on the "Authorization List" (Annex XIV of the REACH regulations) and Substances of Very High Concern (SVHC) in any significant amounts as specified by the Annex XVII of Candidate list published by ECHA (European Chemical Agency) 1907 /2006/EC.

7.4 Conflict Minerals Declaration

As a global supplier of electronic and electrical components, Arduino is aware of our obligations concerning laws and regulations regarding Conflict Minerals, specifically the Dodd-Frank Wall Street Reform and Consumer Protection Act, Section 1502. Arduino does not directly source or process conflict minerals such as Tin, Tantalum, Tungsten, or Gold. Conflict minerals are contained in our products in the form of solder, or as a component in metal alloys. As part of our reasonable due diligence, Arduino has contacted component suppliers within our supply chain to verify their continued compliance with the regulations. Based on the information received thus far we declare that our products contain Conflict Minerals sourced from conflict-free areas.

8 Company Information

Company Information	Details
Company Name	Arduino S.r.l.
Company Address	Via Andrea Appiani, 25-20900 Monza (Italy)

9 Reference Documentation

No.	Reference	Link
1	Arduino App Lab	https://docs.arduino.cc/software/app-lab/
2	UNO Q Documentation	https://docs.arduino.cc/hardware/uno-q/
3	FTDI VCP Drivers	https://ftdichip.com/drivers/vcp-drivers/
4	Bughopper Documentation	https://docs.arduino.cc/hardware/bughopper/
5	Project Hub	https://create.arduino.cc/projecthub
6	Library Reference	https://www.arduino.cc/reference/en/
7	Arduino Store	https://store.arduino.cc/



10 Document Revision History

Date	Revision	Changes
27/03/2026	1	First release