
# TLI4971 high precision coreless current sensor for industrial applications in 8x8mm SMD package



#### **Features & Benefits**

- Integrated current rail with typical  $220\mu\Omega$  insertion resistance enables ultra-low power loss
- Smallest form factor, 8x8mm SMD, for easy integration and board area saving
- High accurate, scalable, DC & AC current sensing
- Bandwidth typical 240kHz enables wide range of applications
- Very low sensitivity error over temperature (< 2.5%)
- Galvanic functional isolation up to 1150V peak V<sub>IORM</sub>
- V<sub>ISO</sub> 3500V RMS agency type-tested for 60 seconds per UL1577
- Differential sensor principle ensures superior magnetic stray field suppression
- Two independent fast Over-Current Detection (OCD) outputs



Coreless current sensor in PG-TISON-8 package

## Description

TLI4971 is a high precision miniature coreless magnetic current sensor for AC and DC measurements with analog interface and two fast over-current detection outputs.

Infineon's well-established and robust monolithic Hall technology enables accurate and highly linear measurement of currents with a full scale up to ±120A. All negative effects (saturation, hysteresis) commonly known from open loop sensors using flux concentration techniques are avoided. The sensor is equipped with internal self-diagnostic feature.

Typical applications are electrical drives and general purpose inverters.

The differential measurement principle allows great stray field suppression for operation in harsh environments.

Two separate interface pins (OCD) provide a fast output signal in case a current exceeds a pre-set threshold.

The sensor is shipped as a fully calibrated product without requiring any customer end-of-line calibration.

All user-programmable parameters such as OCD thresholds, blanking times and output configuration modes are stored in an embedded EEPROM memory.

#### **Order Information**

Product Name	Product Type	Marking	<b>Ordering Code</b>	Package
TLI4971-A120T5-U-E0001	120A measurement range, UL certified device <sup>1)2)</sup>	H71I1A1UH	SP005272936	PG-TISON-8
TLI4971-A120T5-E0001	120A measurement range 1)2)	H71I1A1_H	SP005344532	PG-TISON-8
TLI4971-A075T5-U-E0001	75A measurement range, UL certified device 1)2)	H71I3A1UH	SP005446655	PG-TISON-8
TLI4971-A075T5-E0001	75A measurement range 1)2)	H71I3A1_H	SP005446653	PG-TISON-8
TLI4971-A050T5-U-E0001	50A measurement range, UL certified device 1)2)	H71I4A1UH	SP005446651	PG-TISON-8
TLI4971-A050T5-E0001	50A measurement range 1)2)	H71I4A1_H	SP005446648	PG-TISON-8
TLI4971-A025T5-U-E0001	25A measurement range, UL certified device 1)2)	H71I6A1UH	SP005446646	PG-TISON-8
TLI4971-A025T5-E0001	25A measurement range 1)2)	H71I6A1_H	SP005446644	PG-TISON-8

<sup>1)</sup> Current sensor for industrial / consumer applications, qualified according to AEC Q100 grade 2

<sup>2)</sup> Semi-differential mode, non-ratiometric output sensitivity



## **Pin Configuration**




Figure 1 Pin layout PG-TISON-8-5 The current  $I_{PN}$  is measured as a positive value when it flows from pin 8 (+) to pin 7 (-) through the integrated current rail.

#### Pin configuration

Pin No.	Symbol	Function
1	VDD	Supply voltage
2	GND	Ground
3	VREF	Reference voltage input or output
4	AOUT	Analog signal output
5	OCD1	Over-current detection output 1 (open drain output)
6	OCD2	Over-current detection output 2 (open drain output)
7	IP-	Negative current terminal pin (current-out)
8	IP+	Positive current terminal pin (current-in)

#### **Target Applications**

The TLI4971 is suitable for AC as well as DC current measurement applications:

- Electrical drives
- General purpose inverters
- Chargers
- Current monitoring
- Overload and over-current detection
- etc.

Due to its implemented magnetic interference suppression, it is extremely robust when exposed to external magnetic fields. The device is suitable for fast over-current detection with a configurable threshold level. This allows the control unit to switch off and protect the affected system from damage, independently from the main measurement path.

#### Datasheet



## **General Description**

The current flowing through the current rail on the primary side induces a magnetic field that is differentially measured by two Hall probes. The differential measurement principle of the magnetic field combined with the current rail design provides superior suppression of any ambient magnetic stray fields. A high performance amplifier combines the signal resulting from the differential field and the internal compensation information provided by the temperature and stress compensation unit. Finally the amplifier output signal is fed into a differential output amplifier which is able to drive the analog output of the sensor.

Depending on the selected programming option, the analog output signal can be provided either as:

- Single-ended
- Fully-differential
- Semi-differential

In single-ended mode, the pin VREF is used as a reference voltage input. The analog output signal is provided on pin AOUT. In fully-differential mode, both AOUT (positive polarity) and VREF (negative polarity) are used as signal outputs whereas VDD is used as reference voltage input. Compared to the single-ended mode, the fully-differential mode enables doubling of the output voltage swing.

In semi-differential mode a chip-internal reference voltage is used and provided on VREF (output). The current sensing information is provided in a single-ended way on AOUT.

For fast over-current detection, the raw analog signal provided by the Hall probes is fed into comparators with programmable switching thresholds.

A user-programmable deglitch filter is implemented to enable the suppression of fast switching transients. The open-drain outputs of the OCD pins are active "low" and they can be directly combined into a wired-AND configuration on board level to have a general over-current detection signal.

All user-programmable parameters such as OCD thresholds, deglitching filter settings and output configuration mode are stored in an embedded EEPROM memory.

Programming of the memory can be performed in the application through a Serial Inspection and Configuration Interface (SICI). The interface is descripted in detail in the programming guide which can be found on the Infineon webside. Please contact your local Infineon sales office for further documentation.

## **Standard Product Configuration**

- The pre-configured full scale range is either set to ±120A, ±75A, ±50A or ±25A depending on the choosen product variant.
- The pre-configured output mode is set to semi-differential mode.
- The quiescent voltage is set to 1.65V.
- The OCD threshold of channel 1 is set to the factor 1.25 of the full scale range.
- The OCD threshold of channel 2 is set to the factor 0.82 of the full scale range.
- The pre-defined setting of the OCD deglitching filter time is set to  $0\mu s$ .
- The sensor is pre-configured to work in the non-ratiometric mode.
- The sensitivity and the derived measurement range (full scale) can be reprogrammed by user according to the sensitivity ranges listed in Table 4.
- The sensor can be reprogrammed into single-ended operating mode or fully-differential mode by user without any recalibration of the device.
- The OCD thresholds and filter settings can be reprogrammed by the user according to the values listed in Table 6 and Table 7.
- For semi-differential uni-directional mode or ratiometric output sensitivity, please contact your local Infineon sales office.



#### **Block Diagram**

The current flowing through the current rail on the primary side induces a magnetic field, which is measured by two Hall probes differentially. The differential measurement principle provides superior suppression of any ambient magnetic stray fields. A high performance amplifier combines the signal resulting from the differential field and the compensation information, provided by the temperature and stress compensation unit. Finally the amplifier output signal is fed into a differential output amplifier, which is able to drive the analog output of the sensor.




Figure 2 Block Diagram



#### **Absolute Maximum Ratings**

Table 1 Absolute Maximum Ratings

General conditions (unless otherwise specified):  $V_{DD} = 3.3V$ ;  $T_S = -40$ °C ... +105°C

Parameter	Symbol	Min	Тур	Max	Unit	Note / Test Condition
Supply voltage	$V_{DD}$	-0.3	3.3	3.6	V	
Primary nominal rated current LF <sup>1)</sup>	I <sub>PNRLF</sub>	-70	-	70	А	Peak, frequency < 10Hz. Tested on Infinenon reference PCB (see related application note: AppNote TLI4971 PCB)
Primary nominal rated current HF <sup>2)</sup>	I <sub>PNRHF</sub>	-70	-	70	А	RMS, frequency ≥ 10Hz.  Tested on Infinenon reference PCB (see related application note: AppNote TLI4971 PCB)
Primary current	I <sub>PNS</sub>	-250	-	250	А	Single peak for 10µs, 10 assertions per lifetime
Voltage on interface pins VREF, OCD1, AOUT	V <sub>IO</sub>	-0.3	-	V <sub>DD</sub> + 0.3	V	
Voltage on Interface pin OCD2	V <sub>IO_OCD2</sub>	-0.3	-	21	V	
ESD voltage <sup>3)</sup>	V <sub>ESD_HBM</sub>	-2	-	2	kV	
ESD voltage <sup>4)</sup>	$V_{ESD\_SYS}$	-16	-	16	kV	In the application circuit
Voltage slew-rate on current rail	ΔV/dt	-	-	10	V/ns	
Maximum junction temperature	T <sub>j_max</sub>	-	-	130	°C	
Storage temperature	T <sub>A_STORE</sub>	-40	-	130	°C	
Life time	LT	15	-	-	Years	Considering continuous operation with T <sub>S</sub> = 70°C and I = 30 A RMS

Tested with primary nominal rated current of 70A peak on Infineon reference PCB at Low Frequency (LF).
 Thermal equilibrium reached after 2 min.

Stress above the limit values listed here may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect device reliability. Maximum ratings are absolute ratings. Exceeding only one of these values may cause irreversible damage to the integrated circuit.

<sup>2)</sup> Tested with primary nominal rated current of 70A rms on Infineon reference PCB at High Frequency (HF). Thermal equilibrium reached after 2 min.

<sup>3)</sup> Human Body Model (HBM), according to standard AEC-Q 100-002

<sup>4)</sup> According to standard IEC 61000-4-2 electrostatic discharge immunity test



## **Product Characteristics**

**Table 2 Operating Ranges** 

General conditions (unless otherwise specified):  $V_{DD}$  = 3.3V;  $T_S$  = -40°C ... +105°C

Parameter	Symbol	Min.	Тур.	Max.	Unit	Note / Test Condition
Supply voltage	$V_{DD}$	3.1	3.3	3.5	V	
Ambient temperature at soldering point	Ts	-40	1	105	°C	Measured at soldering point
Capacitance on analog output pin	Co	4.7	6.8	8	nF	W/o decoupling resistor, including parasitic cap on the board
Capacitor on VDD	$C_{VDD}$	-	220	-	nF	
Reference input voltage	$V_{REF}$	1	1.65	1	V	Default value is semi-differential mode. Other values available by EEPROM: 1.2V, 1.5V, 1.8V
Reference input voltage variation	$V_{REF\_var}$	-10	-	10	%	
EEPROM programming voltage	V <sub>IO_PRG</sub>	20.5	-	21.0	V	

#### **Table 3 Operating Parameters**

General conditions (unless otherwise specified):  $V_{DD}$  = 3.3V;  $T_S$  = -40°C ... +105°C

Parameter	Symbol	Min.	Тур.	Max.	Unit	Note / Test Condition
Current consumption	$I_{DD}$	-	15	25	mA	I(AOUT) = 0mA
Primary path resistance	R <sub>PN</sub>	-	220	-	μΩ	25°C, when soldered on PCB with 140μm copper thickness
Power-on delay time	t <sub>POR</sub>	1	1	1.5	ms	From V <sub>DD</sub> rising above V <sub>DD</sub> (min) to full operation. Output with lower accuracy is available within 0.5 ms.  OA primary input current.
Voltage on interface pin OCD1	V <sub>IO_OCD1</sub>	-0.3	ı	3.5	V	
Voltage on interface pin OCD2	V <sub>IO_OCD2</sub>	-0.3	-	3.5	V	In functional mode
Voltage on analog output AOUT	V <sub>AOUT</sub>	-0.3	-	V <sub>DD</sub> + 0.3	V	
Supply undervoltage lockout threshold	U <sub>VLOH_R</sub>	ı	-	3	V	V <sub>DD</sub> at rising edge
Supply undervoltage lockout threshold	$U_{VLOH\_F}$	2.5	-	-	V	V <sub>DD</sub> at falling edge
Supply overvoltage lockout threshold	O <sub>VLOH</sub>	3.55	-	-	V	V <sub>DD</sub> at rising edge
OCD undervoltage detection limit	$V_{DD,OCD}$	1.8	-	-	V	For $V_{DD}$ < $V_{DD,OCD}$ undervoltage may not be performed.
Undervoltage/overvoltage lockout delay	t <sub>UVLOe</sub>	1	2.4	3	μs	Enabled to disabled
Thermal resistance <sup>1)</sup>	R <sub>THJS</sub>	-	0.25	-	K/W	Current rail to soldering point, on Infineon reference PCB (see related application note AppNote TLI4971 PCB)

<sup>1)</sup> Not subject to production test. Verified by design and characterization.



## **Functional Output Description**

The analog output signal depends on the selected output mode:

- Single-ended
- Fully-differential
- Semi-differential

### **Single-Ended Output Mode**

In single-ended mode VREF is used as an input pin to provide the analog reference voltage,  $V_{REF}$ . The voltage on AOUT,  $V_{AOUT}$ , is proportional to the measured current  $I_{PN}$  at the current rail:

$$V_{AOUT}(I_{PN}) = V_{OQ} + S \cdot I_{PN}$$

The quiescent voltage  $V_{\text{OQ}}$  is the value of  $V_{\text{AOUT}}$  when  $I_{\text{PN}}{=}0$ .  $V_{\text{OQ}}$  tracks the voltage on VREF

$$V_{OQ}(V_{REF}) = V_{REF}$$

The reference voltage can be set to different values which allow either bidirectional or uniderictional current sensing. The possible values of  $V_{\text{REFNOM}}$  are indicated in Table 2.

The sensitivity is by default non ratiometric to  $V_{\text{REF.}}$  If ratiometricity is activated the sensitivity becomes as follows:

$$S(V_{REF}) = S(V_{REFNOM}) \cdot \frac{V_{REF}}{V_{REFNOM}}$$

# **Fully-Differential Output Mode**

In fully-differential output mode, both VREF and AOUT are analog outputs to achieve double voltage swing: AOUT is the non-inverting output, while VREF is the inverting output:

$$V_{AOUT}(I_{PN}) = V_{QAOUT} + S \cdot I_{PN}$$
$$V_{REF}(I_{PN}) = V_{OREF} - S \cdot I_{PN}$$

The quiescent voltage is derived from the supply pins VDD and GND and has the same value on both AOUT and VREF:

$$V_{QAOUT}(V_{DD}) = V_{QREF}(V_{DD}) = \frac{V_{DD}}{2}$$

The sensitivity in the fully-differential mode can be generally expressed as:

$$S(V_{DD})_{diff} = S(3.3V)_{diff} \cdot \frac{V_{DD}}{3.3V}$$

In this mode, the quiescent voltages and the sensitivity are both ratiometric with respect to  $V_{\text{DD}}$  if ratiometricity is enabled.

### **Semi-Differential Output Mode**

In semi-differential output mode, the sensor is using a chip-internal reference voltage to generate the quiescent voltage that is available on pin VREF (used as output).

The analog measurement result is available as single-ended output signal on AOUT. The dependence of sensitivity and output offset on reference voltage is the same as described in single-ended output mode.

The quiescent voltage is programmable at 3 different values,  $V_{\text{OQbid}\_1}$  and  $V_{\text{OQbid}\_2}$  for bidirectional current and  $V_{\text{OQuni}}$  for unidirectional current (see Table 4).

#### **Total error distribution**

Figure 3 shows the total output error at 0h ( $E_{TOTT}$ ) and over lifetime ( $E_{TOTL}$ ) over the full scale range for sensitivity range S1 (10mV/A).




Figure 3 Distribution of max. total error in S1 range

## **TLI4971 Datasheet**



**Table 4 Analog Output Characteristics** 

General conditions (unless otherwise specified):  $V_{DD} = 3.3V$ ;  $T_S = -40^{\circ}C$  ...  $+105^{\circ}C$ 

Parameter	Symbol	Min	Тур	Max	Unit	Note / Test conditions
Quiescent output voltage (bidirectional option 1) <sup>1)2)</sup>	V <sub>OQbid_1</sub>	-	V <sub>DD</sub> /2	-	V	I <sub>PN</sub> = 0A; fully- differential or semi- differential (bidirectional) modes, standard setting
Quiescent output voltage (bidirectional option 2) <sup>2)</sup>	V <sub>OQbid_2</sub>	-	1.5	-	V	IPN = 0A; semi- differential (bidirectional) mode; for this option the ratiometricity offset is disabled
Quiescent output voltage (unidirectional mode) <sup>2)</sup>	$V_{OQuni}$	-	V <sub>DD</sub> /5.5	-	V	I <sub>PN</sub> = 0A; semi- differential (unidirectional) mode
Sensitivity, range11)2)3)	S1	-	10	-	mV/A	±120A FS (Full Scale)
Sensitivity, range2 <sup>2)3)</sup>	S2	-	12	-	mV/A	±100A FS
Sensitivity, range3 <sup>2)3)</sup>	S3	-	16	-	mV/A	±75A FS
Sensitivity, range4 <sup>2)3)</sup>	S4	-	24	-	mV/A	±50A FS
Sensitivity, range5 <sup>2)3)</sup>	S5	-	32	-	mV/A	±37.5A FS
Sensitivity, range6 <sup>2)3)</sup>	S6	-	48	-	mV/A	±25A FS
Sensitivity ratiometry factor	K <sub>S</sub>	-	1	-	-	
Quiescent ratiometry factor	K <sub>oq</sub>	-	1	-	-	
Analog output drive capability	Io	-2	-	2	mA	DC current
Analog output saturation voltage	V <sub>SAT</sub>	-	150	300	mV	V <sub>DD</sub> -V <sub>AOUT</sub> ; Output current = 2mA
Transfer function cutoff frequency	BW	120	240	-	kHz	-3dB criterion, C <sub>0</sub> = 6.8nF
Output phase delay <sup>4)</sup>	ф <sub>delay</sub>	-	-	48	•	f <sub>signal</sub> = 120kHz
Output Noise density <sup>5)6)</sup>	I <sub>NOISE</sub>	-	350	-	μA/√Hz	Referenced to Input current, typical value is at 25°C. Higher noise is present at higher temperatures.
External Homogenous magnetic field suppression <sup>4)</sup>	$B_SR$	34	40	-	dB	Frequency up to 150kHz. Up to 20mT homogeneous field applied

<sup>1)</sup> Pre-configured setting, for other pre-configured versions please contact your local sales.

5) Typical value in fully-differential mode, sensitivity range S6 6) Noise Density = 
$$\frac{Output\ Noise\ [V_{RMS}]}{\sqrt{\frac{\pi}{2}*BW[Hz]}}*\frac{1}{Sensitivity\left[\frac{V}{A}\right]}$$

<sup>2)</sup> Can be programmed by user.

<sup>3)</sup> Values refer to semi-differential mode or single-ended mode, with VREF =1.65  $\rm V.$ In fully-differential mode the sensitivity value is doubled.

<sup>4)</sup> Not subject to production test. Verified by design and characterization.

# TL14971

#### **Datasheet**



#### Table 4 Analog Output Characteristics (cont'd)

General conditions (unless otherwise specified):  $V_{DD}$  = 3.3V;  $T_S$  = -40°C ... +105°C

Parameter	Symbol	Min	Тур	Max	Unit	Note / Test conditions
Sensitivity error	E <sub>SENS</sub>	-2	-	2	%	@ T <sub>S</sub> = 25°C, at 0h
Sensitivity error over temperature	E <sub>SENST</sub>	-2.5	-	2.5	%	At 0h
Sensitivity error over temperature and lifetime <sup>4)</sup>	E <sub>SENSL</sub>	-3	ı	3	%	
Output offset	E <sub>OFF</sub>	-300	-	300	mA	@ T <sub>s</sub> = 25°C, at 0h
Output offset over temperature and lifetime <sup>4)</sup>	E <sub>OFF_L</sub>	-500	1	500	mA	
Total error	E <sub>TOT</sub>	-2.25	-	2.25	%	Percentage of FS, sensitivity S1; includes sensitivity, offset and linearity error @ T <sub>S</sub> =25°C at 0h
Total error over temperature	Етотт	-2.95	1	2.95	%	Percentage of FS, sensitivity S1; includes sensitivity, offset and linearity error at 0h
Total error over temperature and lifetime <sup>4)</sup>	Етоть	-3.45	-	3.45	%	Percentage of FS, sensitivity S1; includes sensitivity, offset and linearity error

<sup>4)</sup> Not subject to production test. Verified by design and characterization.



# Fast Over-Current Detection (OCD)

The Over-Current Detection (OCD) function allows fast detection of over-current events. The raw analog output of the Hall probes is fed directly into comparators with programmable switching thresholds. A user programmable deglitch filter is implemented to enable the suppression of fast switching transients. The two different open-drain OCD pins are active low and can be directly combined into a wired-AND configuration on board level to have a general over-current detection signal. TLI4971 supports two independent programmable OCD outputs, suited for different application needs.

The OCD pins are providing a very fast response, thanks to independence from the main signal path. They can be used as a trap functionality to quickly shut down the current source as well as for precise detection of soft overload conditions.

#### **OCD** pins external connection

The OCD pins can be connected to a logic input pin of the microcontroller and/or the gate-driver to quickly react to over-current events. They are designed as open-drain outputs to easily setup a wired-AND configuration and allow monitoring of several current sensors outputs via only one microcontroller pin.

#### **OCD** thresholds

The symmetric threshold level of the OCD outputs is adjustable and triggers an over-current event in case of a positive or negative over-current. The possible threshold levels are listed in Table 6 and Table 7. The instruction for the settings is documented in the TLI4971 programming guide.

#### **OCD** outputs timing behavior

Both output pins feature a deglitch filter to avoid false triggers by noise spikes on the current rail. Deglitch filter settings can be programmed according to application needs. Available options are listed in Table 6 and Table 7.

Figure 4 shows the OCD output pin typical behavior during an over-current event.

Over-current Pulse 1: duration exceeds the over-current response time  $t_{D\_OCDx}$  + response time jitter  $\Delta t_{D\_OCDx}$  + deglitch filter time  $t_{deglitch}$ . The OCD output voltage is set low until the current value drops below the OCD threshold.

Over-current Pulse 2: duration does not exceed the over-current response time  $t_{D\_OCDx}$  and therefore no OCD event is generated.

Over-current Pulse 3: duration exceeds the response time  $t_{D\_OCDx}$  + response time jitter  $\Delta t_{D\_OCDx}$ , but does not exceed the glitch filter time  $t_{deglitch}$  and no OCD event is generated.




Figure 4 Fast over-current detection output timing



## **Fast Over-Current Detection (OCD) Output Parameters**

Table 5 Common OCD Parameters

General conditions (unless otherwise specified):  $V_{DD} = 3.3V$ ;  $T_S = -40^{\circ}C$  ...  $+105^{\circ}C$ ,  $C_L = 1nF$ .

Parameter	Symbol	Min	Тур	Max	Unit	Note / Test Conditions
Threshold level tolerance <sup>1)</sup>	I <sub>THT</sub>	-10	-	10	%	
Response time jitter <sup>1)</sup>	$\Delta t_{D\_OCD}$	-	-	0.25	μs	At 3σ, I <sub>rail</sub> =2xI <sub>THRx.x</sub> , input rise time 0.1μs
Deglitch filter basic time	t <sub>OCDgl</sub>	400	500	600	ns	
Detection minimum time	t <sub>OCD_low</sub>	3	-	-	μs	Valid for both OCDs
Load capacitance	$C_L$	-	-	1	nF	
Open-drain current	I <sub>OD_ON</sub>	-	-	1	mA	DC current
Pull-up resistor	$R_{PU}$	4.7	-	10	kΩ	To V <sub>DD</sub>

<sup>1)</sup> Not subject to production test. Verified by design and characterization.

#### Table 6 OCD1 Parameters

Parameter	Symbol	Min	Тур	Max	Unit	Note / Test Conditions
Threshold level - Level1 <sup>1)2)3)</sup>	I <sub>THR1.1</sub>	1	1.25	-	x I <sub>FS</sub>	Factor with respect to $I_{FS}$ ( $I_{FS}$ = current full scale according to programming i.e. 120A)
Threshold level - Level21)2)	I <sub>THR1.2</sub>	-	1.39	-	x I <sub>FS</sub>	Factor with respect to I <sub>FS</sub>
Threshold level - Level31)2)	I <sub>THR1.3</sub>	ı	1.54	-	x I <sub>FS</sub>	Factor with respect to I <sub>FS</sub>
Threshold level - Level41)2)	I <sub>THR1.4</sub>	ı	1.68	-	x I <sub>FS</sub>	Factor with respect to I <sub>FS</sub>
Threshold level - Level5 <sup>1)2)</sup>	I <sub>THR1.5</sub>	1	1.82	-	x I <sub>FS</sub>	Factor with respect to I <sub>FS</sub>
Threshold level - Level61)2)	I <sub>THR1.6</sub>	-	1.96	-	x I <sub>FS</sub>	Factor with respect to I <sub>FS</sub>
Threshold level - Level7 <sup>1)2)</sup>	I <sub>THR1.7</sub>	-	2.11	-	x I <sub>FS</sub>	Factor with respect to I <sub>FS</sub>
Threshold level - Level8 <sup>1)2)</sup>	I <sub>THR1.8</sub>	1	2.25	-	x I <sub>FS</sub>	Factor with respect to I <sub>FS</sub>
Response time <sup>4)</sup>	t <sub>D_OCD1</sub>	1	0.7	1	μs	$I_{PN} = 2*I_{THR1.x}$
Fall time <sup>5)</sup>	t <sub>f_OCD1</sub>	-	100	150	ns	
Deglitch filter setting <sup>2)6)</sup>	OCD1 <sub>gl_mul</sub>	0	-	7	-	t <sub>deglitch</sub> = OCD1 <sub>gl_mul</sub> *t <sub>OCDgl</sub> pre-configured setting = 0

<sup>1)</sup> Symmetric threshold level for positive and negative currents.

<sup>2)</sup> Can be programmed by user.

<sup>3)</sup> Pre-configured threshold level

<sup>4)</sup> Time between primary current exceeding current threshold and falling edge of OCD1-pin at 50%.

<sup>5)</sup> Not subject to production test. Verified by design and characterization.

<sup>6)</sup> The specified deglitching timing is valid when input current step overtakes the threshold of at least 10%.

# TLI4971

#### **Datasheet**



**Table 7 OCD2 Parameters** 

Parameter	Symbol	Min	Тур	Max	Unit	Note / Test Conditions
Threshold level - level1 <sup>1)2)</sup>	I <sub>THR2.1</sub>	-	0.5	-	x I <sub>FSR</sub>	Factor with respect to I <sub>FS</sub> (I <sub>FS</sub> = current full scale according to programming i.e. 120A)
Threshold level - level2 <sup>1)2)</sup>	I <sub>THR2.2</sub>	-	0.61	-	x I <sub>FSR</sub>	Factor with respect to I <sub>FS</sub>
Threshold level - level3 <sup>1)2)</sup>	I <sub>THR2.3</sub>	-	0.71	-	x I <sub>FSR</sub>	Factor with respect to I <sub>FS</sub>
Threshold level - level4 <sup>1)2)3)</sup>	I <sub>THR2.4</sub>	-	0.82	-	x I <sub>FSR</sub>	Factor with respect to I <sub>FS</sub>
Threshold level - level5 <sup>1)2)</sup>	I <sub>THR2.5</sub>	-	0.93	-	x I <sub>FSR</sub>	Factor with respect to I <sub>FS</sub>
Threshold level - level6 <sup>1)2)</sup>	I <sub>THR2.6</sub>	-	1.04	-	x I <sub>FSR</sub>	Factor with respect to I <sub>FS</sub>
Threshold level - level7 <sup>1)2)</sup>	I <sub>THR2.7</sub>	-	1.14	-	x I <sub>FSR</sub>	Factor with respect to I <sub>FS</sub>
Threshold level - level8 <sup>1)2)</sup>	I <sub>THR2.8</sub>	-	1.25	-	x I <sub>FSR</sub>	Factor with respect to I <sub>FS</sub>
Response time <sup>4)</sup>	t <sub>D_OCD2</sub>	-	0.7	1.2	μs	$I_{PN} = 2 \times I_{THR2.x}$
Fall time <sup>5)</sup>	t <sub>f_OCD2</sub>	-	200	300	ns	
Deglitch filter setting <sup>2)6)</sup>	OCD2 <sub>gl_mul</sub>	0	-	15	-	t <sub>deglitch</sub> = OCD2 <sub>gl_mul</sub> x t <sub>OCDgl</sub> pre-configured setting = 0

<sup>1)</sup> Symmetric threshold level for positive and negative currents.

# **Undervoltage / Overvoltage detection**

TLI4971 is able to detect undervoltage or overvoltage condition of its own power supply ( $V_{DD}$ ). When an undervoltage ( $V_{DD}$ < $U_{VLOH}$ ) or overvoltage ( $V_{DD}$ > $O_{VLOH}$ ) condition is detected both OCD pins are pulled down in order to signal such a condition to the user.

The undervoltage detection on OCD pins is performed only if  $V_{DD} > V_{DD,OCD}$ .

Both OCD pins are pulled down at start up. When  $V_{DD}$  exceeds the undervoltage threshold  $U_{VLOH\_R}$  and the power on delay time  $t_{POR}$  has been reached, the sensor indicates the correct functionality and high accuracy by releasing the OCD pins.

<sup>2)</sup> Can be programmed by user.

<sup>3)</sup> Pre-configured threshold level.

<sup>4)</sup> Time between primary current exceeding current threshold and falling edge of OCD2-pin at 50%.

<sup>5)</sup> Not subject to production test. Verified by design and characterization.

<sup>6)</sup> The specified deglitching timing is valid when input current step overtakes the threshold of at least 10%.



## **Isolation Characteristics**

TLI4971 conforms functional isolation.

**Table 8 Isolation Characteristics** 

Parameter	Symbol	Min	Тур	Max	Unit	Note / Test Conditions
Maximum rated working voltage (sine wave) <sup>1)2)3)</sup>	V <sub>IOWM</sub>	-	-	690	V	RMS, @ 4000m altitude
Maximum rated working voltage (sine wave) <sup>1)2)3)</sup>	V <sub>IOWMP</sub>	-	-	975	V	Peak, @ 4000m altitude
Maximum repetitive isolation voltage <sup>2)3)</sup>	V <sub>IORM</sub>	-	-	1150	V	Max DC voltage, spike, @ 4000m altitude
Apparent charge voltage capability (method B) <sup>2)3)</sup>	V <sub>PDtest</sub>	1500	-	-	V	Partial discharge < 5pC peak @ 0m altitude
Isolation test voltage <sup>3)4)</sup>	V <sub>ISO</sub>	3500	-	-	V	RMS, 60s
Isolation production test	V <sub>ISOP</sub>	3000	-	-	V	RMS, in production, 1.2s, UL certified version
voltage	V <sub>ISOP</sub>	2470	-	-	V	RMS, in production, 600ms, Non-UL certified version
Isolation pulse test voltage <sup>3)</sup>	$V_{\text{pulse}}$	6500	-	-	V	Peak, rise time = 1.2μs, fall time = 50μs
Minimum external creepage distance	CPG	4	-	-	mm	
Minimum external clearance distance	CLR	4	-	-	mm	
Minimum comparative tracking index	СТІ	Material group II	-	-	-	
Isolation resistance <sup>3)</sup>	R <sub>IO</sub>	10	-	-	GΩ	U <sub>IO</sub> = 500V DC, 1min

<sup>1)</sup> The given value is considered an example based on pollution degree 2.

<sup>2)</sup> After stress test according to qualification plan.

<sup>3)</sup> Not subject to production test. Verified by design and characterization.

<sup>4)</sup> Agency type tested for 60 seconds by UL according to UL 1577 standard.



# **System integration**




Figure 5 Application circuit for three phase system in single-ended configuration




Figure 6 Application circuit for three phase system in differential configuration






Figure 7 Application circuit with external components

For bandwidth limitation an external filter is recommended as shown in the above application circuits.



# **Typical Performance Characteristics**




Figure 8 Typical error in sensitivity over temperature




Figure 9 Typical offset drift over temperature



# **Package**

The TLI4971 is packaged in a RoHS compliant, halogen-free leadless package (QFN-like).

# **PG-TISON-8 Package Outline**




Figure 10 PG-TISON-8 package dimensions

# **TLI4971** Datasheet



# **Revision History**

## Major changes since the last revision

Date	Description of change
10-02-2020	Datasheet version 1.10
12-02-2021	Editorial changes first page: shorten features, benefits and description
	Add 6 new variants to order information
	Pre-configured OCD threshold levels changed: Page3, Table 6 and Table 7
	Updated Table 8, isolation characteristics
	Updated application circuits
	Increase upper limit of EEPROM programming voltage from 20.7 to 21.0
	Added chapter "typical performance characteristics"
	Datasheet version 1.20

#### **Trademarks of Infineon Technologies AG**

µHVIC™, µIPM™, µPFC™, AU-ConvertIR™, AURIX™, C166™, CanPAK™, CIPOS™, CIPURSE™, CoolDP™, CoolGaN™, COOLIR™, CoolMOS™, CoolSiC™, DAVE™, DI-POL™, DirectFET™, DrBlade™, EasyPIM™, EconoBRIDGE™, EconoDUAL™, EconoPACK™, EconoPIM™, EiceDRIVER™, eupec™, FCOS™, GaNpowIR™, HEXFET™, HITFET™, HJVPridPACK™, iMOTION™, IRAM™, ISOFACE™, IsoPACK™, LEDrivIR™, LITIX™, MIPAQ™, ModSTACK™, my-d™, NovalithIC™, OPTIGA™, OptiMOS™, ORIGA™, PowIRaudio™, PowIRStage™, PrimePACK™, PrimeSTACK™, PROFET™, PRO-SIL™, RASIC™, REAL3™, SmartLEWIS™, SOLID FLASH™, SPOC™, StrongIRFET™, SupIRBuck™, TEMPFET™, TRENCHSTOP™, TriCore™, UHVIC™, XHP™, XMC™

Trademarks updated November 2015

#### Other Trademarks

Edition 12-02-2021
Published by
Infineon Technologies AG
81726 München, Germany

© 2021 Infineon Technologies AG. All Rights Reserved.

Do you have a question about this document?

Email: erratum@infineon.com

**Document reference** 

----

#### IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

#### WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineor Technologies office.

Except as otherwise explicitly approved by Infineor Technologies in a written document signed by authorized representatives of Infineor Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof car reasonably be expected to result in personal injury.