

Product Reference Manual SKU: ABX00063



Description

The Arduino GIGA R1 WiFi brings the power of the STM32H7 to the Mega form factor, the first to include onboard Wi-Fi® and Bluetooth® connectivity. The board provides 75 digital input/output (12 with PWM capability), 14 analog inputs and 2 analog outputs (DAC) all easily accessibly via pin headers. The STM32 microprocessor with dual core Cortex® M7 and Cortex® M4, together with onboard memory and audio jack enables you to perform machine learning and signal processing on the edge.

Target Areas

3D printing, Signal Processing, Maker, Robotics



Features

- STM32H747XIH6 Microcontroller
 - Dual core
 - 32-bit Arm® Cortex®-M7 core with double-precision FPU and L1 cache up to 480 MHz
 - 32-bit Arm® 32-bit Cortex®-M4 core with FPU up to 240 MHz
 - Full set of DSP instructions
 - Memory Protection Unit (MPU)
- Murata® 1DX Wi-Fi®/Bluetooth® Module
 - Wi-Fi® 802.11b/g/n 65 Mbps
 - Bluetooth® Low Energy (BLE 5 via Cordio stack, BLE 4.2 via Arduino Stack)
 - Micro UFL connector for external antenna
- Memory
 - STM32H747XI:
 - 2 MB Flash
 - 1 MB RAM
 - MX25L12833FZ2I:
 - 16 MB NOR Flash
 - QSPI Interface
 - AS4C4M16SA
 - 8 MB SDRAM
- I/O
 - Digital I/O Pins: 75
 - Analog input pins: 14
 - PWM pins: 12
 - Analog output (DAC): 2
 - USB Host: USB 2.0 A
 - USB Peripheral: USB-C®
 - Logic level: 3.3V



Contents

1 Application Examples	5
2 Accessories (Not Included)	5
3 Related Products	6
4 Recommended Operating Conditions	6
5 Power Consumption	6
6 Block Diagram	7
7 Board Topology	8
7.1 Front View	8
7.2 Back View	9
8 Processor	9
9 Wi-Fi®/Bluetooth® Connectivity	9
10 Onboard Memories	10
11 USB Connector	10
12 Audio	10
13 Power Tree	10
14 Board Operation	12
14.1 Getting Started - IDE	12
14.2 Getting Started - Arduino Web Editor	12
14.3 Getting Started - Arduino IoT Cloud	12
14.4 Online Resources	12
14.5 Board Recovery	12
15 Pinout	13
15.1 J1	13
15.2 Analog	13
15.3 Digital	14
15.4 STM32 ICSP	14
15.5 Digital Pins D22 - D53 LHS	15
15.6 Digital Pins D22 - D53 RHS	15
16 Mounting Holes And Board Outline	16
17 Declaration of Conformity CE DoC (EU)	17
18 Declaration of Conformity to EU RoHS & REACH 211 01/19/2021	3
19 Conflict Minerals Declaration	18
20 FCC Caution	18
21 Company Information	19





22 Reference Documentation	19
23 Change Log	19



The Board

1 Application Examples

The GIGA R1 WiFi combines the best of the Portenta H7 and the Mega 2560. A generous amount of I/O easily accessible via pins allows for easy and fast testing of new ideas and solutions. The STM32H7 has ample power to handle machine learning. Your IoT projects can even benefit from the Arduino IoT Cloud, with the help of onboard secure element and wireless connectivity.

- 3D Printing: The Mega form factor has been very popular for creating 3D printers. Connect sensors to the high resolution DAC interfaces to for high performance sensing of the 3D printing process. Together with the dual core computing power, control the printing process like never before. Monitor filament usage and print status locally over Bluetooth® or from anywhere in the world with the Arduino IoT Cloud.
- Audio Processing: The GIGA R1 WiFi provides a 3.5 mm audio input/output to easily interact with audio signals in the environment. Analyse and create audio signals directly on the board. Connect a microphone and control a wide range of digital and analog devices. Create your own musical instrument and change the note through the various inputs. Create an online concert with the Arduino IoT Cloud and connect with people all over the world.
- Data acquisition device: With two DAC inputs (as well as the audio input) with up to 12bit resolution you can create your own data acquisition device. Make your own multimeter or even an oscilloscope and create an online dashboard with the Arduino IoT Cloud. Design your own electrochemical experiments, apply custom current/voltage waveforms and check the status of your experiment from the comfort of your home.

2 Accessories (Not Included)

- Micro UFL antenna
- USB-C® cable
- USB 2.0 A cable



3 Related Products

■ Arduino Mega Proto Shield Rev3 (A000080)

Rating

4 Recommended Operating Conditions

Symbol	Description	Min	Тур	Max	Unit
V _{IN}	Input voltage from VIN pad	6	7.0	32	V
V _{USB}	Input voltage from USB connector	4.8	5.0	5.5	V
V_{DD}	Input high-level voltage	0.7*V _{DD}		V _{DD}	V
V _{IL}	Input low-level voltage	0		0.3*V _{DD}	V
T _{OP}	Operating Temperature	-20	25	60	°C

Note 1: V_{DD} controls the logic level and is connected to the 3.3V power rail. V_{AREF} is for the analog logic.


5 Power Consumption

Symbol	Description	Min	Тур	Max	Unit
P _{STDBY}	Average power consumption in standby		ТВС		mW
P _{BLINK}	Average power consumption with blink sketch sketch		TBC		mW
P _{MAX}	Maximum power consumption		TBC		mW

Functional Overview



6 Block Diagram




Arduino GIGA R1 WiFi Block Diagram



7 Board Topology

7.1 Front View




Top View of Arduino GIGA R1 WiFi

Ref.	Description	Ref.	Description
U1	STM32H7 Dual Core Microcontroller IC	U2	MX25L12833FZ2I 16 MB Flash IC
U3	AS4C4M16SA 8MB SDRAM IC	U4	ATECC608A-MAHDA-T Secure Element IC
U5	LBEE5KL1DX-883 Wi-Fi®/Bluetooth® Module	U6	MP2322GQH Buck Converter 3.3V IC
U7	MP2269GD-Z Buck Converter 5V IC	JANALOG	Analog input/output headers
JDIGITAL	Digital input/output headers	JSIDE	Digital input/output headers
SPI	SPI headers	JTAG	JTAG Headers
J2	USB 2.0 A Host	J15	3.5 mm audio in/out
PB1	RESET Button	PB2	BOOT0 button
J14	Micro UFL connector	J5	Camera
J6	Camera	DL1	Power LED
DL2	RGB SMLP34RGB2W3 Common anode LED	J12	CX90B-16P USB-C® connector



7.2 Back View



Back View of Arduino GIGA R1 WiFi

8 Processor

The GIGA R1 WiFi's main processor is the dual core STM32H747 (U1) including a Cortex® M7 running at 480 MHz and a Cortex® M4 running at 240 MHz. The two cores communicate via a Remote Procedure Call mechanism that allows calling functions on the other processor seamlessly.

9 Wi-Fi®/Bluetooth® Connectivity

The Murata® LBEE5KL1DX-883 wireless module (U5) simultaneously provides Wi-Fi® and Bluetooth® connectivity in an ultra small package based on the Cypress CYW4343W. The IEEE802.11 b/g/n Wi-Fi® interface can be operated as an access point (AP), station (STA) or as a dual mode simultaneous AP/STA and supports a maximum transfer rate of 65 Mbps. Bluetooth® interface supports Bluetooth® Classic and Bluetooth® Low Energy. An integrated antenna circuitry switch allows a single external antenna (J14) to be shared between Wi-Fi® and Bluetooth®.



10 Onboard Memories

The GIGA R1 WiFi supplements the 2 MB Flash and 1 MB SRAM on the STM32H747 (U1) with 16 MB of NOR Flash with the MX25L12833FZ2I (U2) as well as 8MB of SDRAM with the AS4C4M16SA (U3). U2 connects over a Quad-SPI interface to the U1. U3 operates at a frequency of 166 MHz.

11 USB Connector


Two USB ports are provided on the Arduino GIGA R1 WiFi. One USB 2.0 type A (J2) and a USB-C® (J12). The USB 2.0 connector allows external devices to be connected as peripherals, while the USB-C® connector allows the GIGA board to be connected as a peripheral. Note that super speed pins on J12 are unpopulated. A TVS diode array is placed on the VBUS of each connector (D4,D2) for ESD protection.

12 Audio

The STM32H7 (U1) has two digital-to-analog converters (DAC) which drive the stereo audio output on the 3.5 mm connector J15. The DAC has a resolution of up to 12 bits. The right and left channel are also accessible via pins DAC0 and DAC1 respectively. A microphone input is also present on J15, which is shared with analog pin A7. Buffered mode in the STM32H7 can allow for low impedance output. Sample and hold functionality can reduce the power requirements. Up to 10 mega samples per second is supported.

13 Power Tree





Arduino GIGA R1 WiFi Power Tree

Power can either be supplied via the VIN pins, or the 5V of the USB connectors (J2, J12). If power is supplied via VIN, the MP2269GD-Z (U7) buck converter steps the voltage down to 5V. The 5V power rail is then stepped down to 3.3V by the MP2322GQH (U6) buck converter. The logic level of components on the Arduino GIGA R1 WiFi is 3.3V.



14 Board Operation

14.1 Getting Started - IDE

If you want to program your GIGA R1 WiFi while offline you need to install the Arduino® Desktop IDE [1] To connect the GIGA R1 WiFi control to your computer, you'll need a Type-C® USB cable. This also provides power to the board, as indicated by the LED.

14.2 Getting Started - Arduino Web Editor

All Arduino boards, including this one, work out-of-the-box on the Arduino® Web Editor [2], by just installing a simple plugin.

The Arduino Web Editor is hosted online, therefore it will always be up-to-date with the latest features and support for all boards. Follow [3] to start coding on the browser and upload your sketches onto your board.

14.3 Getting Started - Arduino IoT Cloud

All Arduino IoT enabled products are supported on Arduino IoT Cloud which allows you to Log, graph and analyze sensor data, trigger events, and automate your home or business.

14.4 Online Resources

Now that you have gone through the basics of what you can do with the board you can explore the endless possibilities it provides by checking exciting projects on ProjectHub [4], the Arduino Library Reference [5] and the online store [6] where you will be able to complement your board with sensors, actuators and more.

14.5 Board Recovery

All Arduino boards have a built-in bootloader which allows flashing the board via USB. In case a sketch locks up the processor and the board is not reachable anymore via USB it is possible to enter bootloader mode by double-tapping the reset button right after power up.



Mechanical Information

15 Pinout

15.1 J1

Pin	Function	Туре	Description
1	OFF	Digital	3V3 Enable Pin
2	GND	Power	Ground
3	VRTC	Reset	Real Time Clock Battery

15.2 Analog

Pin	Function	Туре	Description
1	NC	NC	Not Connected
2	IOREF	IOREF	Reference for digital logic V - connected to 3.3V
3	Reset	Reset	Reset
4	+3V3	Power	+3V3 Power Rail
5	+5V	Power	+5V Power Rail
6	GND	Power	Ground
7	GND	Power	Ground
8	VIN	Power	Voltage Input
9	A0	Analog	Analog input 0 /GPIO
10	A1	Analog	Analog input 1 /GPIO
11	A2	Analog	Analog input 2 /GPIO
12	A3	Analog	Analog input 3 /GPIO
13	A4	Analog	Analog input 4 /GPIO
14	A5	Analog	Analog input 5 /GPIO
15	A6	Analog	Analog input 6 /GPIO
16	A7	Analog	Analog input 7 /GPIO
17	A8	Analog	Analog input 8 /GPIO
18	A9	Analog	Analog input 9 /GPIO
19	A10	Analog	Analog input 10 /GPIO
20	A11	Analog	Analog input 11 /GPIO
21	DAC0	Analog	Digital to Analog Converter 0
22	DAC1	Analog	Digital to Analog Converter 1
23	CANRX	Digital	CAN Bus Receive
24	CANTX	Digital	CAN Bus Transfer



15.3 Digital

Pin	Function	Туре	Description
1	D21/SCL1	Digital	GPIO 21/I2C 1 Clock
2	D20/SDA1	Digital	GPIO 20/I2C 1 Dataline
3	AREF	Digital	Analog Reference Voltage
4	GND	Power	Ground
5	D13/SCK	Digital	GPIO 13/SPI Clock
6	D12/CIPO	Digital	GPIO 12/SPI Controller In Peripheral Out
7	D11/COPI	Digital	GPIO 11/SPI Controller Out Peripheral In
8	D10/CS	Digital	GPIO 10/SPI Chip Select
9	D9/SDA2	Digital	GPIO 9/I2C 2 Dataline
10	D8/SCL2	Digital	GPIO 8/I2C 2 Clockline
11	D7	Digital	GPIO 7
12	D6	Digital	GPIO 6
13	D5	Digital	GPIO 5
14	D4	Digital	GPIO 4
15	D3	Digital	GPIO 3
16	D2	Digital	GPIO 2
17	D1/TX0	Digital	GPIO 1 / Serial 0 Transmitter
18	D0/TX0	Digital	GPIO 0 / Serial 0 Receiver
19	D14/TX3	Digital	GPIO 14 / Serial 3 Transmitter
20	D15/RX3	Digital	GPIO 15 / Serial 3 Receiver
21	D16/TX2	Digital	GPIO 16 / Serial 2 Transmitter
22	D17/RX2	Digital	GPIO 17 / Serial 2 Receiver
23	D18/TX1	Digital	GPIO 18 / Serial 1 Transmitter
24	D19/RX1	Digital	GPIO 19 / Serial 1 Receiver
25	D20/SDA	Digital	GPIO 20 / I2C 0 Dataline
26	D21/SCL	Digital	GPIO 21 / I2C 0 Clock

15.4 STM32 ICSP

Pin	Function	Туре	Description	
1	CIPO	Internal	Controller In Peripheral Out	
2	+5V	Internal	Power Supply of 5V	
3	SCK	Internal	Serial Clock	
4	COPI	Internal	Controller Out Peripheral In	
5	RESET	Internal	Reset	
6	GND	Internal	Ground	



15.5 Digital Pins D22 - D53 LHS


Function	Туре	Description
+5V	Power	+5V Power Rail
D22	Digital	GPIO 22
D24	Digital	GPIO 24
D26	Digital	GPIO 26
D28	Digital	GPIO 28
D30	Digital	GPIO 30
D32	Digital	GPIO 32
D34	Digital	GPIO 34
D36	Digital	GPIO 36
D38	Digital	GPIO 38
D40	Digital	GPIO 40
D42	Digital	GPIO 42
D44	Digital	GPIO 44
D46	Digital	GPIO 46
D48	Digital	GPIO 48
D50	Digital	GPIO 50
D52	Digital	GPIO 52
GND	Power	Ground
	+5V D22 D24 D26 D28 D30 D32 D34 D36 D38 D40 D42 D44 D46 D48 D50 D52	+5V Power D22 Digital D24 Digital D26 Digital D28 Digital D30 Digital D32 Digital D34 Digital D36 Digital D38 Digital D40 Digital D42 Digital D44 Digital D46 Digital D48 Digital D50 Digital D52 Digital

15.6 Digital Pins D22 - D53 RHS

Pin	Function	Туре	Description	
1	+5V	Power	+5V Power Rail	
2	D23	Digital	GPIO 23	
3	D25	Digital	GPIO 25	
4	D27	Digital	GPIO 27	
5	D29	Digital	GPIO 29	
6	D31	Digital	GPIO 31	
7	D33	Digital	GPIO 33	
8	D35	Digital	GPIO 35	
9	D37	Digital	GPIO 37	
10	D39	Digital	GPIO 39	
11	D41	Digital	GPIO 41	
12	D43	Digital	GPIO 43	
13	D45	Digital	GPIO 45	
14	D47	Digital	GPIO 47	
15	D49	Digital	GPIO 49	
16	D51	Digital	GPIO 51	
17	D53	Digital	GPIO 53	
18	GND	Power	Ground	



16 Mounting Holes And Board Outline



Mechanical View of Arduino GIGA R1 WiFi

Certifications



17 Declaration of Conformity CE DoC (EU)

We declare under our sole responsibility that the products above are in conformity with the essential requirements of the following EU Directives and therefore qualify for free movement within markets comprising the European Union (EU) and European Economic Area (EEA).

18 Declaration of Conformity to EU RoHS & REACH 211 01/19/2021

Arduino boards are in compliance with RoHS 2 Directive 2011/65/EU of the European Parliament and RoHS 3 Directive 2015/863/EU of the Council of 4 June 2015 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

Substance	Maximum Limit (ppm)
Lead (Pb)	1000
Cadmium (Cd)	100
Mercury (Hg)	1000
Hexavalent Chromium (Cr6+)	1000
Poly Brominated Biphenyls (PBB)	1000
Poly Brominated Diphenyl ethers (PBDE)	1000
Bis(2-Ethylhexyl) phthalate (DEHP)	1000
Benzyl butyl phthalate (BBP)	1000
Dibutyl phthalate (DBP)	1000
Diisobutyl phthalate (DIBP)	1000

Exemptions: No exemptions are claimed.

Arduino Boards are fully compliant with the related requirements of European Union Regulation (EC) 1907 /2006 concerning the Registration, Evaluation, Authorization and Restriction of Chemicals (REACH). We declare none of the SVHCs (https://echa.europa.eu/web/guest/candidate-list-table), the Candidate List of Substances of Very High Concern for authorization currently released by ECHA, is present in all products (and also package) in quantities totaling in a concentration equal or above 0.1%. To the best of our knowledge, we also declare that our products do not contain any of the substances listed on the "Authorization List" (Annex XIV of the REACH regulations) and Substances of Very High Concern (SVHC) in any significant amounts as specified by the Annex XVII of Candidate list published by ECHA (European Chemical Agency) 1907 /2006/EC.



19 Conflict Minerals Declaration

As a global supplier of electronic and electrical components, Arduino is aware of our obligations with regards to laws and regulations regarding Conflict Minerals, specifically the Dodd-Frank Wall Street Reform and Consumer Protection Act, Section 1502. Arduino does not directly source or process conflict minerals such as Tin, Tantalum, Tungsten, or Gold. Conflict minerals are contained in our products in the form of solder, or as a component in metal alloys. As part of our reasonable due diligence Arduino has contacted component suppliers within our supply chain to verify their continued compliance with the regulations. Based on the information received thus far we declare that our products contain Conflict Minerals sourced from conflict-free areas.

20 FCC Caution

Any Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions:

- (1) This device may not cause harmful interference
- (2) this device must accept any interference received, including interference that may cause undesired operation.

FCC RF Radiation Exposure Statement:

- 1. This Transmitter must not be co-located or operating in conjunction with any other antenna or transmitter.
- 2. This equipment complies with RF radiation exposure limits set forth for an uncontrolled environment.
- 3. This equipment should be installed and operated with minimum distance 20cm between the radiator & your body.

English: User manuals for licence-exempt radio apparatus shall contain the following or equivalent notice in a conspicuous location in the user manual or alternatively on the device or both. This device complies with Industry Canada licence-exempt RSS standard(s). Operation is subject to the following two conditions:

- (1) this device may not cause interference
- (2) this device must accept any interference, including interference that may cause undesired operation of the device.

French: Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes :

- (1) l'appareil nedoit pas produire de brouillage
- (2) l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

IC SAR Warning:

English This equipment should be installed and operated with minimum distance 20 cm between the radiator and your body.

French: Lors de l'installation et de l'exploitation de ce dispositif, la distance entre le radiateur et le corps est d'au moins 20 cm.

 $\textbf{Important:} \ The \ operating \ temperature \ of the \ EUT \ can't \ exceed \ 85^{\circ}C \ and \ shouldn't \ be \ lower \ than \ -40^{\circ}C.$



Hereby, Arduino S.r.l. declares that this product is in compliance with essential requirements and other relevant provisions of Directive 201453/EU. This product is allowed to be used in all EU member states.

Frequency bands	Maximum output power (ERP)
2.4 GHz, 40 channels	TBD

21 Company Information

Company name	Arduino SRL
Company Address	Via Andrea Appiani 25, 20900, MONZA MB, Italy

22 Reference Documentation

Ref	Link
Arduino IDE (Desktop)	https://www.arduino.cc/en/Main/Software
Arduino IDE (Cloud)	https://create.arduino.cc/editor
Cloud IDE Getting Started	https://docs.arduino.cc/cloud/web-editor/tutorials/getting-started/getting-started-web-editor
Project Hub	https://create.arduino.cc/projecthub?by=part∂_id=11332&sort=trending
Library Reference	https://github.com/arduino-libraries/
Online Store	https://store.arduino.cc/

23 Change Log

Date	Changes
09/12/2022	Release