Equipment for Fluid Control



2/3 Port Valve for Various Fluids Control

■ 2/3 Port Solenoid/Air Operaed Valve for Various Fluids Control

(For Water/Air/Oil/Gas/Vacuum/Steam)	
□ 2/3 Port Solenoid Valve	
Direct operated 2 port solenoid valve: VX21/22/2317-3-17	7
Pilot operated 2 port solenoid valve: VXD21/22/2317-3-33	3
Pilot operated 2 port solenoid valve: VXP21/22/2317-3-43	3
Water hammer relief, pilot operated 2 port solenoid valve: VXR21/22/23 ··· 17-3-53	3
Pilot operated 2 port solenoid valve	
for zero pressure differential operation: VXZ17-3-61	1
Pilot operated 2 port solenoid valve for high pressure: VXH17-3-69	9
2 port solenoid valve for dust collector: VXF17-3-71	
Direct operated 3 port solenoid valve: VX31/32/3317-3-81	1
☐ 2/3 Port Air Operated Valve	
Direct air operated 2 port valve: VXA21/22	
Direct air operated 2 port valve: VXA31/3217-3-101	1

The models VX21/22/23 have been revised. For details, please refer to catalog no. ES70-23A. The models VX31/32/33 have been revised. For details, please refer to catalog no. ES70-26A. Similar updating for other VX* series are scheduled to follow shortly.

VC□

VDW

VQ

VX2

VX□

VX3

VXA

VN□

LVC

LVA

LVH

LVQ

LQ

LVN

TI/ TIL

PAX

РВ

For Fluid Control 2/3 Port Valve Solenoid Valve/Air Operated Valve For Water, Air, Oil, Gas, Vacuum and Steam

2 Port, Direct Operat	ed
-----------------------	----

Series VX21/22/23

N.C., N.O./ Single unit, Manifold


Refer to our catalog "ES70-23A".



2 Port, Pilot Operated (Diaphragm type)

Series VXD21/22/23

N.C., N.O.





2 Port, Pilot Operated (Disk type)

Series VXP21/22/23

N.C., N.O.

2 Port, Pilot Operated

Series VXR21/22/23

< Water hammer relief > N.C., N.O.





The models VX21/22/23 have been revised. For details, please refer to catalog no. ES70-23A. The models VX31/32/33 have been revised. For details, please refer to catalog no. ES70-26A. Similar updating for other VX* series are scheduled to follow shortly.

Series VX

2 Port, Pilot Operated

Series VXH22

3 Port, Direct Operated

Series VX31/32/33

Refer to our catalog "ES70-26A".

C.O./Single unit, Manifold

For high pressure control N.C./Single unit



2 Port, Pilot Operated Series VXF21/22

Selection Procedure for 2/3 Port Valve for Fluid Control

VC

VDW

VQ

VX2

 $VX\square$

VX3

VXA

VN□

LVA

LVH

LVD

LQ

TI/ TIL

5. Choice of the power supply voltage and electrical entry

To obtain the flow rate of fluid, refer to the

Select the AC/DC power source and choose the electrical entry.

1. Selection of the series

Select series by referring to the number of ports, valve type (N.C., N.O., C.O.), port size and applied fluid.

2. Check by the applicable fluids check list



Use the tables on pages 17-3-6 to -14 to check the compatibility of the applicable fluid with the solenoid valve.

3. Confirmation of the working pressure differential

There are two types of pressure differentials. The high pressure differential is the highest pressure difference allowable between the inlet side and the outlet side in an open and closed state. The minimum pressure differential is the lowest pressure required to hold the main valve fully open. Refer to the following pages for each series as the pressure differential varies with the orifice size, power supply, pressure and fluid.

4. Reference to the flow characteristic table

flow characteristic table.

Air Operated Valve

Quick response, Control of instantaneous large flow N.C./Single unit

2/3 Port, Direct Operated

Series VXA21/22 Series VXA31/32



LVC

LVQ

LVN

PA

PAX



Solenoid Valves List

1	Number of ports							2 pc	ort				
Δ	Actio	on	Direct operated		Pilot operated Diaphragm type		Pilot operated Disk type		Pilot operated <water hammer="" relief=""></water>				
S	Serie	es		VX21	/22/23		VXD21	1/22/23	VXP2	1/22/23	VXR2	1/22/23	
Е	Body	/ type	Singl	e unit	Mar	nifold	Singl	e unit	Singl	e unit	Sing	le unit	
V	/alv	e type	N.C.	N.O.	N.C.	N.O.	N.C.	N.O.	N.C.	N.O.	N.C.	N.O.	
		Water		•		_		•		•		•	
	lard	Air		•		•		•	(•		_	
ids	Standard	Oil		•		•		•	(•		•	
) H	S	Low vacuum (1 Torr)		•		•		_		_		_	
ge		Steam	(Ð		_	-	_	(•		_	
Applicable fluids	_	Medium vacuum (10 ⁻³ Torr)		_									
App	Option	Non-leak (10 ⁻⁵ atm cc/sec)						_		_		_	
		High temperature water,	١.			_	'		,			•	
		High temperature oil					<u> </u>						
		1/8 (6A)	•	•			_	_	_	_	T _	T _	
		1/4 (8A)		•			•	_	•	_	_	_	
	<u>_</u> .	3/8 (10A)	•	•			•	_	•	_	_	_	
ize	Rc	1/2 (15A)	•	_			•	•	•	•	•	•	
Port size		3/4 (20A)	-	_		_	•	•	•	•	•	•	
9		1 (25A)	_	_	1		•	•	•	•	•	•	
	28	11/4 (32A)	_	_			● Flange	● Flange	Flange Rc	Flange Rc	Rc	Rc	
	Flange	11/2 (40A)	_	_			● Flange	● Flange	Flange Rc	Flange Rc	Rc	e Rc	
	Ë	2 (50A)	<u> </u>	_			Flange	Flange	Flange Rc	Flange Rc	e Rc	e Rc	
F	age	9		Catalog I	=S70-23	A	17-	3-17	17-	3-27	17-	3-37	
	-9			catalog i	_3,0 20	, ,	.,,	<i>.</i> , ,	.,	<i></i>	- ''	J J,	

Air Operated Valves List

* An option is available that sets the orifice in the vacuum side to the maximum bore for exclusive use when used in a vacuum pad application. Refer to page 17-3-86 for details.

Nu	imber of ports			ort		3 p	ort
-	tion ries	[Direct c	perate 21/22	d	Direct operated VXA31/32	
	dy type Single unit Manifold Single unit live type N.C. N.O. N.C. N.O. C.O.		Single unit C.O.	Manifold C.O.			
Applicable fluids	Low vacuum (1 Torr)					•	- • •
Port size	1/8 (6A) 1/4 (8A) 3/8 (10A) 1/2 (15A)	•	•	- -	-	•	-
Page		17-	3-45	17-0	3-49	17-3-53	17-3-57

Series VX

	3 pc	ort				
	Pilot op <zero pi<br="">differential o</zero>	ressure	Pilot operated <high control="" pressure=""></high>	Pilot operated <quick response,<br="">Instantaneous large flow></quick>	Direct o	perated
	VXZ22/23		VXH22	VXF21/22	VX31/	/32/33
	Single unit		Single unit	Single unit	Single unit	Manifold
	N.C.	N.O.	N.C.	N.C.	N.C. /N.O. /C.O.	N.C. /N.O. /C O.
			•	_	•	_
			•	•	•	•
			•	_	•	•
			_	_	• *	•
	_	_	_	_	•	_
	-	_	_	_	•	•
			_	_	•	_
	_		_	_		
	_	_	_	_		
			•	_		
	•	•	•	_		
	•	•	_	•		_
	•	•	_	•		
	_	_	_	_	_	
	_	_	_	• Rc	_	
	_	_	_	_	_	
	17-3	3-61	17-3-69	17-3-71	Catalog E	S70-26A

Applicable fluids check list	17-3-6 to 17-3-14
Glossary	17-3-15
How to order Solenoid coil assembly	17-3-16

Caution

Be sure to read before handling. Refer to pages 17-6-3 to 17-6-10 for Safety Instructions and Solenoid Valve Precautions.

VC□

VDW

VQ

VX2

VX□

VX3

VXA

 $VN\square$

LVC

LVA

LVH

LVD **LVQ**

LQ

LVN

TI/ TIL

PA

PAX

Applicable Fluids Check List

2 Port Direct Air Operated Series VXA21/22

Normally Closed (N.C.), Normally Open (N.O.)



Refer to pages 17-3-46 and 17-3-47 for specifications and models.

Option Symbol and Composition

Manifold Series VVXA21/22

Option Symbol and Composition

Seal material

NBR FKM

EPDM

FKM

Option symbol	Seal material	Body material	Holder material (Driving parts)
Standard	NBR		
A	FKM	Brass	
В	EPDM		
G	NBR		Polyacetal
Н	FKM		
J	EPDM	Stainless steel	
M ^{Note 1)} (Non-leak)	FKM	Stalliless steel	
N	FKM		Stainless steel
P	EPDM		Starriess steer
V Note 1) (Non-leak)	FKM	Brass	Polyacetal



Note 1) Grease for vacuum has been applied to the sliding part, silicon grease to the other options.

Normally Closed (N.C.), Normally Open (N.O.)

Refer to pages 17-3-50 and 17-3-51 for specifications and models.

Fluid Name and Option

Fluid (Application)	Option symbol a	nd body material
Fluid (Application)	Brass	Stainless steel
Silicon oil	Α	Н
Vacuum (up to 1.3 x 10 ⁻¹ Pa)	V Note 1)	M ^{Note 1)}
Fuel oil (up to 60°C)	Α	Н
Insulation oil	Α	Н
Non-leak (10 ⁻⁶ Pa·m³/s)	V Note 1)	M ^{Note 1)}
Brake oil	В	Р
Water (up to 60°C)	Α	Н
O If water or face ash and fivida		CMC



* If using for other fluids, please contact SMC. Note 1) The leakage amount (10-6 Pa·m³/s) is value when differential pressure is 0.1 MPa.

VC

VDW

VQ

VX2

 $\mathsf{VX}\square$

VX3

VXA

VN□

LVC

LVA

LVH

LVD

LVQ

LQ

LVN TI/ TIL

PA

PAX

PB

Fluid Name and Option

Fluid (Application)	Option symbol
Silicon oil	Α
Vacuum (up to 1.3 x 10 ⁻¹ Pa)	V Note 1)
Fuel oil (up to 60°C)	Α
Insulation oil	Α
Brake oil	В
Non-leak (10 ⁻⁶ Pa·m³/s)	V Note 1)



* If using for other fluids, please contact SMC. Note 1) The leakage amount (10-6 Pa·m³/s) is value when differential pressure is 0.1 MPa.

В

Option symbol

Standard

V Note 1) (Non-leak) Note 1) Grease for vacuum has been applied to the sliding part, silicon grease to the

Body material

Aluminum

Holder material

(Driving parts)

Polyacetal

Series VX

Applicable Fluids Check List

3 Port Direct Air Operated Series VXA31/32

Common (C.O.)



Refer to pages 17-3-54 and 17-3-55 for specifications and models.

Option Symbol and Composition

Standard NBR A FKM Brass B EPDM G NBR Polyacetal H FKM J EPDM MNOote 1) (Non-leak) FKM N FKM Stainless steel	Option symbol	Seal material	Body material	Support material (Driving parts)
B EPDM G NBR H FKM J EPDM MNode 1) (Non-leak) FKM N FKM Stainless steel	Standard	NBR		
G NBR Polyacetal H FKM J EPDM MNode 1) (Non-leak) FKM N FKM Stainless steel	Α	FKM	Brass	
H FKM J EPDM MNote 1) (Non-leak) FKM N FKM Stainless steel	В	EPDM		
J EPDM MNote 1) (Non-leak) FKM N FKM Stainless steel	G	NBR		Polyacetal
M ^{Note 1)} (Non-leak) FKM Stainless steel N FKM Stainless steel	Н	FKM		
N FKM Stainless steel			Ctainless steel	
Stainless steel	M ^{Note 1)} (Non-leak)	FKM	Stairliess steel	
Statilless steel	N	FKM		Ctainless steel
P EPDM Stanford Sta	Р	EPDM		Stairliess steel
V Note 1) (Non-leak) FKM Brass Polyacetal	V Note 1) (Non-leak)	FKM	Brass	Polyacetal



Note 1) Grease for vacuum has been applied to the sliding part, silicon grease to the other options.

Fluid Name and Option

Fluid (Application)	Option symbol and body material		
Fidia (Application)	Brass	Stainless steel	
Silicon oil	Α	Н	
Vacuum (up to 1.3 x 10 ⁻¹ Pa)	V Note 1)	M ^{Note 1)}	
Fuel oil (up to 60°C)	Α	Н	
Insulation oil	Α	Н	
Non-leak (10 ⁻⁶ Pa·m³/s)	V Note 1)	M ^{Note 1)}	
Brake oil	В	Р	
Water (up to 60°C)	Α	Н	



) * If using for other fluids, please contact SMC.

Note 1) The leakage amount (10⁻⁶ Pa·m³/s) is value when differential pressure is 0.1 MPa.

Manifold Series VVXA31/32

Common (C.O.)



Refer to pages 17-3-58 and 17-3-59 for specifications and models.

Option Symbol and Composition

Option symbol	Seal material	Body material	Support material (Driving parts)
Standard	NBR		
A	FKM	Aluminum	Dolyopatal
В	EPDM		Polyacetal
V ^{Note 1)} (Non-leak) ⁽¹⁾	FKM	Brass (1)	



Note 1) Grease for vacuum has been applied to the sliding part, silicon grease to the other options.

Note 2) Manifold base material: Aluminum



Fluid Name and Option

Fluid (Application)	Option symbol
Vacuum (up to 1.3 x 10 ⁻¹ Pa)	V ^{Note 1)}
Vacuum pad	Standard
Non-leak (10 ⁻⁶ Pa⋅m³/s)	V ^{Note 1)}
Brake oil	В



* If using for other fluids, please contact SMC.

Note 1) The leakage amount (10-e Pa·m²/s) is value when differential pressure is 0.1 MPa.

Glossary

Pressure

1. Max. operating pressure differential

This pressure difference is the highest pressure difference allowable to operate (a difference between the pressures in the inlet slide and the outlet side) in an open state and the closed state of valve. A case of 0 kgf/cm² in the outlet side results in the highest operating pressure.

2. Min. operating pressure differential

This pressure difference is the lowest pressure difference (a difference between the pressures in the inlet slide and the outlet side) required to hold the main valve fully open.

3. Max. system presure

This pressure is the limit of pressure that can be applied to pipe line. (Line pressure)

[The pressure difference in a solenoid valve must be maintained less than the highest operating pressure difference.]

4. Proof pressure

This is the pressure that can be withstood without deterioration of the performance when valve returns within the range of the operating pressure. (A value under a specified condition.)

Electricity

1. Apparent power (VA)

Volt-ampere is the product of voltage (V) and current (A). Power dissipation (W): For AC , W=V/A cos θ . For DC, W=V/A (Note) cos θ shows power factor.

2. Surge voltage

The surge voltage is a high voltage generated momentarily when cutting the power supply.

3. Hum sound

The hum sound is a noise generated through repeated adsorption and releasing on an armature adsorption surface.

For an AC solenoid, no shading coil releases the spring reaction because of the existance of a 0 point (twice per frequency) of the suction force.

Others

1. Material

NBR: Nitrile rubber

FKM: Fluoro rubber—Trade names: Vitron®,

Dai-el®, etc.

EPDM: Ethylene propylene rubber

PTFE: Polytetrafluoroethylene resin—Trade names: Teflon®, Polyflon®, etc.

Polyacetal (POM)—Trade names: Duracon®, Derlin®, etc.

2. Oil preserve treatment

After assembly, valve is put through a parts washer to remove any oil used during assembly.

3. Symbol

The JIS symbol is (It is designates the valve to be normally closed.

However, in situations where the secondary pressure exceeds the primary side pressure, the resulting back pressure will cause back flow through the valve.

VC□

VDW

VQ VX2

VV□

VX□

VX3

VXA

VN□

LVC

LVA

LVH

LVD

LVQ

LQ

LVN

TI/ TIL

PA

PAX

PB




Refer to page 17-6-3 for Safety Instructions and Solenoid Valve Precautions.



Direct Air Operated 2 Port Valve For Air, Gas, Vacuum, Water and Oil

Series VXA21/22



■ Wide variations of combination. Able to control a wide variety of fluids.

Application can be matched by simply choosing body material (Brass or Stainless steel) and seal material (NBR, FKM, EPDM).

■ Easy to disassemble and reassemble in a shorttime.

■ High viscosity fluids (500 cSt).

VC□

VDW

VQ

VX2

 $\nabla X \square$

VX3

VXA

VN□

LVC

LVA LVH

LVD

LVQ

LQ


LVN

TI/ TIL PA


PAX

PB

Variations



Normally Closed (N.C.), Normally Open (N.O.)



Fluid

Standard specification	Option Note)
Water (Standard, up to 40°C)	Vacuum (up to 1.3 x10 ⁻¹ Pa) (V, M)
Air (Standard, Dry)	Non-leak (10 ⁻⁶ Pa· m³/s or less) (V, M)
Turbine oil	
Vacuum (up to 1.3 x10 ² Pa)	
Carbon dioxide (CO ₂), Nitrogen gas (N ₂)	

Note 1) Refer to page 17-3-13 "Applicable Fluids Check List" for details of special fluids outside of the standard options and specifications.


Model/Valve Specifications

Dowt	Orifice	-	Max. operating		Flow characteristics			Max. Proof		Weight	
Port size	size	size Model I	pressure differential	Wate	Water, Oil		Air			pressure	(g)
3126	(mmø)		(MPa)	Av x 10 ⁻⁶ m ²	Cv converted	C [dm ³ / (s· bar)]	р	Cv	pressure (MPa)	(MPa)	(9)
1/8	3	VXA212	1.0	7.9	0.33	1.3	0.50	0.38			
(6A)	4.5	VXA213	0.5	15	0.61	2.3	0.45	0.70			170
	3	VXA212	1.0	7.9	0.33	1.3	0.50	0.38	1.0	2	170
	4.5	VXA213	0.5	15	0.61	0.5	10.45	5 0.75			
1/4	4.5	VXA223	1.0	15	0.61	2.5	10.45	0.75			250
(8A)	6	VXA224	0.6	26	1.1	3.3	0.50	1.1			250
	8	VXA225	0.2	41	1.7	6.4	0.40	1.8	0.4		340
	10	VXA226	0.1	46	1.9	8.8	0.40	2.3	0.4		340
	4.5	VXA223	1.0	15	0.61	2.5	0.45	0.75	1.0		050
3/8	6	VXA224	0.6	26	1.1	3.3	0.50	1.1	1.0		250
(10A)	8	VXA225	0.2	41	1.7	6.4	0.40	1.8			240
	10	VXA226	0.1	58	2.4	11	0.38	2.8	0.4	'	340
1/2 (15A)	10	VXA226	0.1	58	2.4	11	0.38	2.8			420

Note) Refer to "Glossary" on page 17-3-15 for details of max. operating pressure differential and max. system pressure.

Construction/

Principal Parts Material



No.	Description	Material			
INO.	Description	Standard	Option		
1	Body	Brass	Stainless steel		
(2)	Valve	Stainless steel, Brass	Stainless steel		
2	assembly	NBR,Polyacetal	FKM/EPDM		
3	Piston assembly	Polyacetal, NBR	_		
4	Piston spring	Stainless steel	_		
(5)	Pilot cover	Aluminum	_		
6	O-ring	NBR	FKM/EPDM		

Operating Fluid and Ambient Temperature

T	Operating fluid temperature (°C)				Ambient
Temperature conditions	Water (Standard)	Air (Standard)	Oil (Standard)	Vacuum (3) (V, M)	temperature (°C)
Maximum	40	60	40	40	40
Minimum	1	- 5 ⁽¹⁾	-5 ⁽²⁾	- 5	- 5

Note 1) Dew point: -5°C or less Note 2) 500 cSt or less Note 3) "V", "M" in parentheses are option symbols.

Tightness of Valve (Leak rate)

Fluid Seal material	Air	Liquid	Non-leak, Vacuum V, M ⁽²⁾
NBR, FKM, EPDM	1 cm³/min or less	0.1 cm ³ /min or less ⁽¹⁾	10 ⁻⁶ Pa⋅m³/s

Note 1) Differs depending on the operating conditions such as pressure, etc. Note 2) Value on option "V", "M" (Non-leak, Vacuum).

Pilot Pressure

Model	Pressure (MPa)
VXA21□□ VXA22□□	0.25 to 0.7

Direct Air Operated 2 Port Valve For Air, Gas, Vacuum, Water and Oil Series VXA21/2

The VX* series will be revised shortly.

How to Order




Table (1) Port/Orifice Size

Мо	del	Orifice size (No.)				
VXA21	VXA22	2 (3 mmø)	3 (4.5 mmø)	4 (6 mmø)	5 (8 mmø)	6 (10 mmø)
01 (1/8)	1			_	_	_
02 (1/4)				_	_	_
_	02 (1/4)	_				
_	03 (3/8)	_				
_	04 (1/2)	_	_	_	_	•

Ordering example

(Example) Series VXA21, Orifice size 4.5 mmø, Normally closed, Rc 1/4 (Part no.) VXA2130-02

Table (2) Bracket Part No.

. ,	
Model	Part no.
VXA212□ VXA213□	VX070-020
VXA223□ VXA224□	VX070-022
VXA225□ VXA226□	VX070-029

VC

VDW

VQ

VX2 VX□

VX3

VXA

VN□

LVC

LVA

LVH

LVD LVQ

LQ

LVN


TI/ TIL

PA

PAX


Dimensions (Orifice Size: 3 mmø, 4.5 mmø, 6 mmø)

VXA212 / **VXA213** / **VXA223** / **VXA224**



Dimensions (Orifice Size: 8 mmø, 10 mmø)

VXA225□/VXA226□



* Fixing with thread is also possible.

Direct Air Operated 2 Port Valve/Manifold For Air, Gas, Vacuum and Oil

Series VVXA21/22



■ Common SUP type and individual SUP type (for vacuum use) standard models

■ A wide variety of applicable fluids. Combination of seal materials (NBR, FKM or EPDM) can be selected freely, depending on the purpose.

- Able to replace valves with the piping remained uchanged.
- Weight-saving aluminum base and body.
- Brass base and stainless steel base are available. Please contact SMC for details.

Compatible with a wide variety of fluids.

VX□

VC

VDW

VQ

VX2

VX3

VXA

VN□

LVC

LVA

LVH LVD

LVQ


LQ

LVN

TI/ TIL


PA

PAX PB




Normally Closed (N.C.), Normally Open (N.O.)


JIS Symbol Common SUP type



Indivisual SUP type



Construction/ Principal Parts Material



No.	Description	Material			
INO.	Description	Standard	Option		
1	Body	Aluminum	_		
2	Valve assembly	NBR, Stainless steel Brass, Polyacetal	FKM/EPDM		
3	Base	Aluminum	_		
4	Piston assembly	Polyacetal, NBR	_		
(5)	O-ring	NBR	FKM/EPDM		
6	Pilot cover	Aluminum	_		
7	Piston spring	Stainless steel	_		

Fluid

Standard specifications	Option
Air (Standard, Dry)	Vacuum (up to 1.3 x10 ² Pa) ····· (V)
Vacuum (up to 1.3 x10 ² Pa)	Non-leak (10 ⁻⁶ Pa·m³/s or less) ······ (V)
Turbine oil	
Carbon dioxide (CO ₂), Nitrogen gas (N ₂)	

Note) Refer to page 17-3-13 "Applicable Fluids Check List" for details of special fluids outside of the standard options and specifications.

Manifold Specifications

Manifold	B Mount		
Manifold type	Common pressure supply, individual pressure supply (For vacuum)		
Number of valves	2 to 10 stations		
Blanking plate	VVXA21	VX011-001	
(With O-rings, screws)	VVXA22	VX011-006	

Note) Common port is placed on vacuum side.

Manifold Base and Applicable Valve Part No.

Manifold base	Individual port Rc	Applicable valve	Weight per one station (g)	
VVXA211-stations	1/8	VXA21□3-00	n x 70 + 50	
VVXA212-stations	1/4	VAA21□1-00	11 x 70 + 50	
VVXA221-stations	1/8	VXA22□3-00	n x 130 + 110	
VVXA222-stations	1/4	VAM22□1-00	11 x 130 + 110	

Solenoid Valve for Manifold

Orifice		Max.operating		Flow characteristics				Max. system	Proof	Majaht
size	Model	pressure differential	C	Oil		Air		pressure	pressure	Weight
(mmø)		(MPa)	Av x 10 ⁻⁶ m ²	Cv converted	C [dm³/(s·bar)]	b	Cv	(MPa)	(MPa)	(g)
3	VXA212-00	1.0	7.9	0.33	1.3	0.50	0.38			100
4.5	VXA213-00	0.5	15	0.61	2.3	0.45	0.70	1.0	1.5	120
4.5	VXA223-00	1.0	13	0.61	2.3	0.45	0.70	1.0	1.5	160
6	VXA224-00	0.6	26	1.1	3.3	0.50	1.1			160



Note) Refer to "Glossary" on page 17-3-15 for details of max. operating pressure differential

Operating Fluid and Ambient Temperature

	Opera			
Temperature	Air	Oil	Vacuum (3)	Ambient temperature
conditions	(Standard)	(Standard)	(V)	(°C)
Maximum	60	40	40	40
Minimum	-5 ⁽¹⁾	-5 ⁽²⁾	- 5	-5

Note 1) Dew point: -5°C or less Note 2) 500 cSt or less Note 3) "V" in parentheses is option symbol.

Tightness of Valve (Leak rate)

Fluid Air Seal material		Liquid	Non-leak, Vacuum (2)	
NBR, FKM, EPDM	1 cm³/min or less	0.1 cm ³ /min or less (1)	10 ⁻⁶ Pa·m³/s or less	

Note 1) Differs depending on the operating conditions such as pressure, etc. Note 2) Value on option "V" (Non-leak, Vacuum).

Pilot Pressure

Model	Pressure (MPa)
VXA21□□ VXA22□□	0.25 to 0.7

Direct Air Operated 2 Port Valve/Manifold For Air, Gas, Vacuum and Oil Series VVXA21/2

The VX* series will be revised shortly.

How to Order





Table (1) Orifice Size

	Orifice size (No.)				
Model	2	3	4		
	(3 mmø)	(4.5 mmø)	(6 mmø)		
VXA21	•	•			
VXA22	_	•	•		

How to Order Manifold Base




How to Order Manifold

■ Write both the base part number and the solenoid valve to be mounted or blanking plate part

(Example) 7 stations of VXA21 common pressure, individual port Rc 1/8.

(Base)	VVXA211-07	4	
(Valve)	VXA2121-00	6	pcs
(Blanking plate)	VX011-001	1	pc.

■ Arrangement of solenoid valves



The standard arrangement of manifolds should be placed on an individual port on this side, each solenoid valve from the left side and a blank plate in the right side. The right side of the common port provides plug. **VC**

VDW VQ

VX2

 $\nabla X \square$

VX3

VXA

VN□

LVC

LVA

LVH LVD

LVQ


LQ

LVN

TI/ TIL PA

PAX

Dimensions/Manifold



[]: Individual pressure type



Direct Air Operated 3 Port Valve For Air, Gas, Vacuum, Water and Oil Series VXA31/32



■ Able to control a wide variety of fluids. Wide variations of combination.

Application can be matched by simply choosing body material (Brass or Stainless steel) and seal material (NBR, FKM or EPDM).

- C.O. type easy to use; operatable as either N.C. or N.O.
- **■** Easy to disassemble and reassemble in a short time.
- High viscosity fluids (500 cSt).

VC□

VDW

VQ

VX2

 $\nabla X \square$

VX3

VXA VN□

LVC

LVA

LVH


LVD LVQ

LQ

LVN


TI/ TIL PA

PAX



Common (C.O.)

JIS Symbol



Fluid

Standard specifications	Option Note)
Water (Standard, up to 40°C)	Vacuum (up to 1.3 x 10 ⁻¹ Pa) · · · · · · · (V, M)
Air (Standard, Dry)	Non-leak (10 ⁻⁶ Pa·m³/s or less) ······ (V, M)
Turbine oil	
Vacuum (up to 1.3 x 10 ² Pa)	
Carbon dioxide (CO ₂), Nitrogen gas (N ₂)	

Note) Refer to page 17-3-14 "Applicable Fluids Check List" for details of special fluids outside of the standard options and specifications.


Model/Valve Specifications

	Orifice		Max. operating		Flow characteristics				Max. system	Proof	144 : 1 :
Port	size	Model	pressure differential	Wate	er, Oil		Air		pressure	pressure	Weight
size	(mmø)		(MPa)	Av x 10 ⁻⁶ (m ²)	Cv converted	C [dm³/(s·bar)]	b	Cv	(MPa)	(MPa)	(g)
	1.5	VXA3114	1.0	1.9	0.08	0.29	0.32	0.08			
1/8 (6A)	2.2	VXA3124	0.5	3.8	0.16	0.60	0.25	0.15			
	3	VXA3134	0.3	8.0	0.24	0.82	0.20	0.20			280
	1.5	VXA3114	1.0	1.9	0.08	0.29	0.32	0.08	1.0 1.5		
	0.0	VXA3124	0.5	3.8	0.16	0.60	0.25	0.15			
1/ ₄ (8A)	2.2	VXA3224	1.0	4.6	0.19	0.64	0.40	0.17		1 . [410
1/4 (OA)	3 VXA3134	VXA3134	0.3	8.0	0.24	0.82	0.20	0.20		1.5	280
	3	VXA3234	0.6	9.0	0.33	1.1	0.25	0.27			
	4	VXA3244	0.3	12	0.50	1.6	0.20	0.38			
	2.2	VXA3224	1.0	4.6	0.19	0.64	0.40	0.17			410
3/8 (10A)	3	VXA3234	0.6	9.0	0.33	1.1	0.25	0.27			
	4	VXA3244	0.3	12	0.50	1.6	0.20	0.38			



Note) Refer to "Glossary" on page 17-3-15 for details of max. operating pressure differential and max. system pressure.

Construction/ Principal Parts Material



No.	Description	Description Mate		
INO.	Description	Standard	Option	
1	Body assembly	Brass	Stainless steel	
2	Retainer assembly	Brass	Stainless steel	
3	Valve assembly	NBR, Polyacetal	FKM/EPDM Stainless steel	
4	Adapter	Brass	Stainless steel	
(5)	Travel assembly	Stainless steel, NBR, Polyacetal	FKM/EPDM Stainless steel	
6	Pilot cover	Aluminum	_	
7	Piston spring	Stainless steel	_	
8	Piston assembly	Polyacetal, NBR	_	
(9)	O-ring	NBR	FKM/EPDM	

Operating Fluid and Ambient Temperature

		Ambient			
Temperature conditions	Water (Standard)	Air (Standard)	Oil (Standard)	Vacuum ⁽³⁾ (V, M)	temperature (°C)
Maximum	40	60	40	40	40
Minimum	1	-5 ⁽¹⁾	-5 ⁽²⁾	-5	- 5

Note 1) Dew point: -5°C or less Note 2) 500 cSt or less Note 3) "V", "M" in parentheses are option symbols.

Tightness of Valve (Leak rate)

Seal Fluid Air material		Liquid	Non-leak, Vacuum (2)			
NBR, FKM, EPDM	1 cm³/min or less	0.1 cm³/min or less(1)	10 ⁻⁶ Pa⋅m³/s or less			
Note 1) Differe depending on the encycling conditions and a pressure at						

Note 1) Differs depending on the operating conditions such as pressure, etc. Note 2) Value on option "V", "M" (Non-leak, Vacuum).

Pilot Pressure

Model	Pressure (MPa)
VXA31□4 VXA32□4	0.25 to 0.7

Direct Air Operated 3 Port Valve For Air, Gas, Vacuum, Water and Oil Series VXA31/3

The VX* series will be revised shortly.

How to Order




Table (1) Port/Orifice Size

14515 (1) 1 515 511155 5125						
Valve (Po		Orifice s	ize (No.)			
VXA31	VXA32	1	2	3	4	
VAASI	VXA32	(1.5 mmø)	(2.2 mmø)	(3 mmø)	(4 mmø)	
01 (1/8)	_	•	•	•	_	
02 (1/4)	_	•	•	•	_	
_	02 (1/4)	_	•	•	•	
_	03 (3/8)	_	•	•	•	

Ordering example (Example) Series VXA31, Orifice size 1.5 mmø, Rc 1/8 (Part no.) VXA3114-01

VC

VDW

VQ

VX2

VX□

VX3

VXA

VN□

LVC

LVA

LVH

LVD

LVQ

LQ


LVN

TI/ TIL

PA

PAX

Dimensions



Direct Air Operated 3 Port Valve/Manifold For Air, Gas, Vacuum and Oil


Series VVXA31/32



- A wide variety of applicable fluids.

 Combination of seal materials (NBR, FKM, or EPDM) can be selected freely, depending on the purpose.
- Able to replace valves with the piping remained unchanged.
- N.C./N.O. switchover is easy.
- Weight-saving aluminum base and body. (Not applicable to water or steam.)

Variations



VC□

VDW

VQ

VX2

VX□

VX3

VXA

VN□

LVC

LVA

LVH

LVQ

LQ

TI/ TIL

PA

PAX PB

Common (C.O.)


Fluid

Standard specifications	Option Note)
Air (Standard, Dry)	Vacuum (up to 1.3 x 10 ⁻¹ Pa)(V)
Vacuum (up to 1.3 x 10 ² Pa)	Non-leak (10 ⁻⁶ Pa·m³/s or less)······(V)
Turbine oil	:
Carbon dioxide (CO ₂), Nitrogen gas (N ₂)	: Other
	Other



Note) Refer to page 17-3-14 "Applicable Fluids Check List" for details of special fluids outside of the standard options and specifications.


JIS Symbol



Manifold Specifications

Manifold	B Mount				
Manifold type	Common supply, Common exhaust, Individual out				
Number of valves	2 to 10 stations				
Blanking plate	VVXA31	VX011-004			
(with gasket, screws)	VVXA32	VX011-005			

Construction/ **Principal Parts Material**



No.	Description	Material			
INO.	Description	Standard	Option		
1	Manifold body, Base	Aluminum	Brass (Base is made of aluminum.)		
2	Valve assembly	NBR, Polyacetal	FKM/EPDM		
3	Adapter	Aluminum	FKM/EPDM		
4	Travel assembly	NBR, Polyacetal	FKM/EPDM		
(5)	O-ring	NBR	FKM/EPDM		
6	Pilot cover	Aluminum	_		
7	Piston spring	Stainless steel	_		
8	Piston	NBR, Polyacetal	_		
9	Gasket	NBR	FKM/EPDM		

Manifold Base And Applicable Valve Part No.

Manifold base	Individual port Rc	Applicable valve	Base weight (g)	
VVXA311-stations	1/8	VXA31□5-00	n x 100 + 50	
VVXA312-stations	1/4	VAA31□5-00	11 X 100 + 50	
VVXA321-stations	1/8	VXA32□5-00	n x 160 + 70	
VVXA322-stations	1/4	V ∧ A 32 🗆 5-00	11 X 100 + 70	

Model/Valve Specifications

Orifice		Max. operating		Flow	characteristics			Max system	Proof	
size	size Model presi		C			pressure	pressure	Weight (g)		
(mmø)		(MPa)	Av x 10 ⁻⁶ (m ²)	Cv converted	C [dm3/(s-bar)]	b	Cv	(MPa)	(MPa)	(9)
1.5	VXA3115-00	1.0	1.9	0.08	0.29	0.32	0.08			150
3	VXA3125-00	0.5	3.8	0.16	0.60	0.25	0.15			150
	VXA3225-00	1.0	4.6	0.19	0.64	0.40	0.17	1.0	1.5	230
	VXA3135-00	0.3	8.0	0.24	0.82	0.20	0.20	1.0	1.5	150
	VXA3235-00	0.6	9.0	0.33	1.10	0.25	0.27			220
4	VXA3245-00	0.3	12	0.60	1.66	0.20	0.38			230



- Note) Add the V type (VXA31) 80 g, (VXA32) 130 g Refer to "Glossary" on page 17-3-15 for details of max. operating pressure differential and max. system pressure.

Operating Fluid and Ambient Temperature

	Opera	Ambient		
Temperature conditions	Air (Standard)	Oil (Standard)	Vacuum ⁽³⁾ (V)	temperature (°C)
Maximum	60	40	40	40
Minimum	-5 ⁽¹⁾	-5 ⁽²⁾	- 5	-5



Note 1) Dew point: -5°C or less

Note 2) 500 cSt or less

Note 3) "V" in parentheses is option symbol.

Tightness of Valve (Leak rate)

Fluid Seal material	Air	Liquid	Non-leak, Vacuum (2)
NBR, FKM, EPDM	1 cm³/min or less	0.1 cm³/min or less(1)	10 ⁻⁶ Pa⋅m³/s or less

Note 1) Differs depending on the operating conditions such as pressure, etc. Note 2) Value on option "V" (Non-leak, Vacuum).

Pilot Pressure

Model	Pressure (MPa)
VXA31 □ 5 VXA32 □ 5	0.25 to 0.7

The VX* series will be revised shortly.

How to Order





Table (1) Orifice Size

	Orifice size (No)				
Model	1	2	3	4	
	(1.5 mmø)	(2.2 mmø)	(3 mmø)	(4 mmø)	
VXA31	•	•	•	_	
VXA32	_	•	•	•	

How to Order Manifold Base



indicated as "R".

How to Order Manifold


■ Write both the base part number and the solenoid valve to be mounted or blanking plate part number.

(Example)

7 stations of VXA31, Individual port Rc 1/8

(Base P/N)	VXA311-07	1	рс
(Valve P/N)	VXA3115-00	6	pcs
(Blanking plate P/N)	VX011-004	1	рс

■ Arrangement of solenoid valves



The standard arrangement of manifolds should be placed on an individual port on this side, each solenoid valve from the left side and a blank plate in the right side. The right side of the common port provides plug.

SMC

 \Box XV

VC

VDW

VQ

VX2

VXA

VX3

 $\mathsf{VN}\square$ LVC

LVA

LVH

LVD LVQ

LQ

LVN

TI/ TIL

PA

PAX

Dimensions

