


PIPE CLEANERS

EGA Master manufactures a wide range of drain cleaners which enable the user to work on small home pipes as well as on big facilities. The wide range of EGA Master pipe cleaners has different drill sizes from 16mm up to 30mm for any work.



- 1**

DESATASCADOR DE TAMBOR
69500

2

DESATASCADOR DE MUELLE
69505-69506-69507

3

DRAINMATIC HANDY 75
60290-60291

4

DRAINMATIC HANDY 75 AUTO
60292-60293

5

DRAINMATIC PORTABLE 75 AUTO
60296-60297

6

DRAINMATIC 100
60040

7

DRAINMATIC MAX 150
60282-60283

8

DRAINMATIC MAX 200
60284-60285

9

DRAINMATIC MAX 110
60288-60289

10

DRAINMATIC MAX 600
60286-60287

	Ø (mm)	CAP. (mm)
Drainmatic Handy 75		
Drainmatic Handy 75 Auto	8 (spring)	Ø20-Ø75
Drainmatic Portable 75 Auto		
Drainmatic 100	8-16 (spring)	Ø20-Ø100
Drainmatic MAX 110	12,5 (spring)	Ø20-Ø110
Drainmatic MAX 150	8-16-22 (spring)	Ø20-Ø150
Drainmatic MAX 200	30 (spring)	Ø50-Ø200
Drainmatic MAX 600	8 x 22 (rod)	Ø200-Ø600

PIPE CLEANER



1. Professional pipe cleaner with a **4,6 m** length.

2. Zinc-coated steel spring with a **hardness of 32-35 HRC**.

COD.	L (m)	 O.D. mm	 g	
69500	4,6	11	750	6

TECHNICAL SPECIFICATION	
Pipe capacity	Ø 11 mm
Max. Length	4,6 m
Spring head Ø	Ø 12 mm
Ø Spring	Ø 6 mm

SPRING PIPE CLEANER



1. Professional spring pipe cleaner, **available in lengths from 3 to 10 meters**.

2. Zinc-coated steel spring with a **hardness of 32-35 HRC**.

COD.	L (m)	 O.D. mm	 g	
69505	3	5	350	10
69506	5	9	1400	
69507	10	10	2500	5

DRAINMATIC HANDY 75 PIPE CLEANER



* 12M CE

COD.	V	W	R.P.M.	CAP. (mm)	Kg
60290	* 220-240 V (50-60 Hz)	600	0-550	Ø 20-75	11
60291	110-130 V (50-60 Hz)				

* Accessories included

CE I 12M

TECHNICAL SPECIFICATION	
Pipe capacity	Ø 20-75 mm
Max. Length	7,6 m
Spring head Ø	Ø 15 mm
Ø Spring	Ø 8 mm
Turning speed	0-550 rpm
Turning way selector switch	•
Ergonomic grip	•
2 piece spring canister resistant to impact and corrosion	•
Lightweight and easy-to-use	•
Working weight	6,0 Kg
Power	600 W

1. All EGA Master pipe cleaners have the necessary elements for **ergonomic and comfortable use**.

2. Is the **ideal machine** for cleaning pipes, drains, canals... for drain maintenance professionals.

3. Includes accessories, a metal **transport case**, and a 7,6 m long **spring pipe cleaner**.



5. Turning direction **selection switch**.

5. 12M: 12 months of warranty.

INCLUDED ACCESSORIES

COD.	L x W x H (mm)	Kg
68160	612 x 218 x 240	6,0

TECHNICAL SPECIFICATION	
Capacity	20 kg
Compartments	1

COD.	Ø O.D. mm	L (m)	Kg	Valid for
85114	8	7,6	1,8	60290, 60291, 60292, 60293



12M 12 MONTHS OF WARRANTY

DRAINMATIC HANDY 75 AUTO PIPE CLEANER



* 12M CE

COD.	V	W	R.P.M.	CAP. (mm)	Kg
60292	220-240 V (50-60 Hz)	600	0-550	Ø 20-75	11
60293	110-130 V (50-60 Hz)				

*Accessories included

CE I 12M

TECHNICAL SPECIFICATION	
Automatic spring advance	•
Spring advance speed	5 m/min
Pipe capacity	Ø 20-75 mm
Max. Length	7,6 m
Spring head Ø	Ø 15 mm
Ø Spring	Ø 8 mm
Turning speed	0-550 rpm
Turning way selector switch	•
Ergonomic grip	•
2 piece spring canister resistant to impact and corrosion	•
Lightweight and easy-to-use	•
Working weight	6,0 Kg
Power	600 W

1. All EGA Master pipe cleaners have the necessary elements for **ergonomic and comfortable use**.

2. Is the **ideal machine for cleaning pipes, drains, canals...** for drain maintenance professionals.

3. With **automatic spring advance**.

4. Includes **metal transport case and accessories**.



5. Turning direction **selection switch**.

6. 12M: 12 months of warranty.

INCLUDED ACCESSORIES

COD.	L x W x H (mm)	Kg
68160	612 x 218 x 240	6,0

TECHNICAL SPECIFICATION	
Capacity	20 kg
Compartments	1


COD.	Ø D. mm	L (m)	Kg	Valid for
85114	8	7,6	1,8	60290, 60291, 60292, 60293

COD.	Speed m/min.	Kg	Valid for
83694	5	0,5	60292, 60293



12M 12 MONTHS OF WARRANTY

DRAINMATIC PORTABLE 75 AUTO PIPE CLEANER



* 12M CE

COD.	V	W	R.P.M.	CAP. (mm)	Kg
60296	220-240 V (50-60 Hz)	600	0-450	Ø 20-75 mm	11
60297	110-130 V (50-60 Hz)				

*Accessories included

CE I 12M

TECHNICAL SPECIFICATION	
Automatic spring advance	•
Spring advance speed	5 m/min
Pipe capacity	Ø 20-75 mm
Max. Length	6 m
Spring head Ø	Ø 15 mm
Ø Spring	Ø 8mm
Turning speed	0-450 rpm
Turning way selector switch	•
Ergonomic grip	•
2 piece spring canister resistant to impact and corrosion	•
Lightweight and easy-to-use	•
Working weight	6,0 kg
Power	600 W
Batería Ni-mh	14,4 V - 2400 mAh

1. All EGA Master pipe cleaners have the necessary elements for **ergonomic and comfortable use**.

2. Is the **ideal machine for cleaning pipes, drains, canals...** for drain maintenance professionals.

3. With **automatic spring advance**.

4. **Includes** metal transport case and accessories.



5. Turning direction selection switch.

6. 12M: 12 months of warranty.

INCLUDED ACCESSORIES

COD.	L x W x H (mm)	Kg
68160	612 x 218 x 240	6,0

TECHNICAL SPECIFICATION	
Capacity	20 kg
Compartments	1



12M 12 MONTHS OF WARRANTY

INCLUDED ACCESSORIES

COD.	 O.D. mm	L (m)	 Kg	Valid for
85115	8	6	1,4	60294, 60295, 60296, 60297



COD.	Speed m/min.	 Kg	Valid for
83694	5	0,5	60292, 60293



COD.	V	 Kg	Valid for
83696	14,4	0,8	60294, 60295, 60296, 60297



COD.	V	 Kg	Valid for
64649	220-240 V (50-60 Hz)	1,2	60294, 60295, 60296, 60297
64650	110-130 V (50-60 Hz)		



DRAINMATIC 100

PIPE CLEANER



* 12M CE

1. All EGA Master pipe cleaners have the necessary elements for **ergonomic and comfortable use**.

2. Is the **ideal machine for cleaning pipes, drains, canals...** for drain maintenance professionals.

3. Includes hardware, metal box and support accessories.



4. Turning direction selection switch.



5. Includes **4.5 m long spring holder drum**.



6. 12M: 12 months of warranty.


COD.	V	CAP. (mm)	W	R.P.M.	Kg
60040	* 220-240 V (50-60 Hz)	Ø 20-100	390	400	32

*Accessories included

CE I 12M

TECHNICAL SPECIFICATION	
Pipe capacity	Ø 20-100 mm
Supplied spring length	20 m
Max. Length	30 m
Ø Spring	Ø 8-16 mm
Turning speed	400 rpm
Turning way selector switch	•
Ergonomic grip	•
Gloves included	•
2 piece spring canister resistant to impact and corrosion	•
Maximum stability	•
Lightweight and easy-to-use	•
Working weight	12 kg
Power	390 W

INCLUDED ACCESSORIES



COD.	 O.D. mm	L (mm)	L (m)	 g	
85104	8	-	4,5	2350	
64240		135		70	
64241				50	
64242		100		70	
64249		85		85	
64243		35		32	
64244		28	-	35	
64245		37		25	
64246		40			
64248			20	9750	
64624	-	-	-	100	
85103	16		2,5	1200	

DRAINMATIC MAX 150 PIPE CLEANER



* 12M CE

1. All EGA Master pipe cleaners have the necessary elements for **ergonomic and comfortable use.**

2. Is the ideal machine for cleaning pipes, drains, canals... for drain maintenance professionals.



3. Includes hardware, metal box and support accessories.



4. Turning direction selection switch.



5. Includes 4.5 m long spring holder drum.



6. 12M: 12 months of warranty.

COD.	V	CAP. (mm)	W	R.P.M.	Kg
60282	* 220-240 V (50-60 Hz)	Ø 20-150	390	400	51
60283	110-130 V (50-60 Hz)				

*Accessories included

CE I 12M

TECHNICAL SPECIFICATION	
Pipe capacity	Ø 20-150 mm
Supplied spring length	15 m
Max. Length	30 m
Ø Spring	Ø 8-16-22 mm
Turning speed	400 rpm
Turning way selector switch	•
Ergonomic grip	•
Gloves included	•
Safe tube included	•
Maximum stability	•
Lightweight and easy-to-use	•
Working weight	16 kg
Power	390 W

INCLUDED ACCESSORIES



COD.	 O.D. mm	L (mm)	L (m)	 g	
85100	8	-	4,5	2350	
64240	16	135		70	
64241				50	
64249		85		85	
64243		35		32	
64628	22	190	-	165	
64629		140		175	
64626		57		60	
64625		65		80	
64630	16		15	7600	
64631	22			11500	
64623	40		4	2300	
64624	-	-		100	
85101	22	-		2000	
85103	16	-		1200	

DRAINMATIC MAX 200 PIPE CLEANER



* 12M CE

1. All EGA Master pipe cleaners have the necessary elements for **ergonomic and comfortable use**.

2. Is the ideal machine for cleaning pipes, drains, canals... for drain maintenance professionals.

3. Includes hardware, metal box and support accessories.



4. Turning direction selection switch.



6. 12M: 12 months of warranty.

COD.	V	CAP. (mm)	W	R.P.M.	Kg
60284	* 220-240 V (50-60 Hz)	Ø 50-200	1100	700	80
60285	110-130 V (50-60 Hz)				

*Accessories included

CE I 12M

TECHNICAL SPECIFICATION	
Pipe capacity	Ø 50-200 mm
Supplied spring length	20 m
Max. Length	50 m
Ø Spring	Ø 30 mm
Turning speed	700 rpm
Turning way selector switch	•
Gloves included	•
Safe tube included	•
Maximum stability	•
Lightweight and easy-to-use	•
Working weight	45 kg
Power	1100 W

INCLUDED ACCESSORIES



COD.		L (mm)	L (m)		
64632	30	80	-	150	
64634		195		600	
64635		75		280	
64636		265		360	
64637		205		380	
64638		120		230	
64623	40		4	2300	
64633	30	-	20	28000	
64624	-		-	100	
85102	30		5	7000	

DRAINMATIC MAX 600

PIPE CLEANER



* 12M CE

1. All EGA Master pipe cleaners have the necessary elements for **ergonomic and comfortable use**.

2. Is the **ideal machine for cleaning pipes, drains, canals...** for drain maintenance professionals.

3. Includes hardware, metal box and support accessories.



4. Turning direction **selection switch**.



5. 12M: 12 months of warranty.

COD.		V	CAP. (mm)	W	R.P.M.	Kg
60286	*	220-240 V (50-60 Hz)	Ø 200-600	1600	100-600	140
60287		110-130 V (50-60 Hz)				

*Accessories included

CE I 12M

TECHNICAL SPECIFICATION	
Pipe capacity	Ø 200-600 mm
Supplied spring length	45 m
Max. Length	50 m
Turning speed	100-600 rpm
Turning way selector switch	•
Gloves included	•
Rod system	•
Maximum estabality	•
Easy to transport	•
Working weight	120 Kg
Power	1600 W

INCLUDED ACCESSORIES



COD.	 O.D. mm	L (mm)	L (m)	 g	
64639	22	250	-	410	
64640				330	
64641		240		320	
64642		250		340	
64643		300		2150	
64669	8 x 22		30 x 1,5	16500	 1,5 m
64624	-	-	-	100	
64653	8 x 22		1,5	2200	 1,5 m

DRAINMATIC MAX 110

PIPE CLEANER



* 12M CE

1. All EGA Master pipe cleaners have the necessary elements for **ergonomic and comfortable use**.

2. Is the ideal machine for cleaning pipes, drains, canals... for drain maintenance professionals.

3. Includes hardware, metal box and support accessories.

4. Turning direction selection switch.



5. 12M: 12 months of warranty.

COD.		V	CAP. (mm)	W	R.P.M.	Kg
60288	*	220-240 V (50-60 Hz)	Ø 20-110	370	260	31
60289		110-130 V (50-60 Hz)				

*Accessories included

CE I 12M

TECHNICAL SPECIFICATION	
Automatic spring advance	•
Spring advance speed	6 m/min
Pipe capacity	Ø 20-110 mm
Max. Length	22,5 m
Ø Spring	Ø 12,5 mm
Turning speed	260 rpm
Turning way selector switch	•
Gloves included	•
Safe tube included	•
Maximum estabality	•
Easy to transport	•
Working weight	28 kg
Power	370 W





12M 12 MONTHS OF WARRANTY

INCLUDED ACCESSORIES



COD.	 O.D. mm	L (mm)	 g	
64644	12,5	135	50	
64645		100	70	
64646		28	35	
64647		37	25	
64683	40	-	2200	
64624	-	-	100	

AVAILABLE ACCESSORIES

COD.	Description	 O.D. mm	L (mm)	L (m)	 9	For machines	
64644	Collection helical drills	12,5	135		50	60288, 60289	
64645	Olive-shaped helical drills		100		70		
64646	Helical saw cutters		28		35		
64647	Spade-shaped cutters		37		25		
64240	Straight helical drills		135		70	60040, 60041, 60282, 60283	
64241	Collection helical drills				50		
64242	Olive-shaped helical drills		100		70		
64243	4-edged saw cutters		35		32	60040, 60041, 60282, 60283	
64244	Helical saw cutters	16	28		35	60040, 60041	
64245	Spade-shaped cutters		37			60040, 60041	
64246	C shaped cutters		40		25	60040, 60041	
64249	Vent-pipe extension		85		85	60040, 60041	
64628	Straight helical drills		190		165	60282, 60283	
64629	Funnel shaped helical drills		140	-	175		
64639	Helical saw cutters		250		410	60286, 60287	
64640	Collection helical drills				330		
64641	Spade-shaped cutters		240		320		
64642	Collection helical drills	22	250		340		
64643	Adapter		300		2150		
64625	4-edged saw cutters		65		80	60282, 60283	
64626	Spade-shaped cutters		57		60		
64636	Straight helical drills		265		360	60284, 60285	
64634	Funnel shaped helical drills		195		600		
64637	Collection helical drills		205		380		
64638	C shaped cutters	30	120		230	60284, 60285	
64632	Spade-shaped cutters		80		150		
64635	Helical saw cutters		75		280		

AVAILABLE ACCESSORIES

COD.	Description	 O.D. mm	L (mm)	L (m)		For machines	
85104	Extension	8		4,5	2350	60040, 60041	
85100						60282, 60283	
64248			20	9750	60040, 60041		
64630		16	15	7600	60282, 60283		
85103					2,5	1200	60040, 60041, 60282, 60283
64631		22	15	11500	60282, 60283		
85101						2000	
85102		30	5	7000	60284, 60285		
64633				20		28000	
64669				Rod		8 x 22	30 x 1,5
64653	1,5	2200					
64623	Vent-pipe extension	40		4	2300	60288, 60289, 60282, 60283, 60284, 60285	
64683	Pipe protector					2200	60288
64624	Protection gloves	-	-	100	60284, 60285, 60286, 60287, 60288, 60289		