

Think LED

Think Philips TradeLED

PHILIPS
sense and simplicity

Contents



London Eye Illuminated using Philips LED lighting solutions



4-5
Introduction




6-15
Zadora MASTER LEDspot Kit



16-19
TurnRound



20-23
Latina LED



24-27
SecuriPack LED



28-31
Smart Bollard LED



32-35
Smart Flood LED



36-39
Affinium LED String Kit



40-41
SpotOn



42-43
Living Colors



44-47
Imageo



TradeLED

A range of complete lighting solutions using the latest LED technology, selected just for the trade.

No one knows LED like Philips. Our technology is seen everywhere – lighting up high-profile attractions such as The London Eye and brightening countless shops, offices and hotels.

Now, for the first time, we have brought together LED solutions especially for the trade. Our products – featuring the very latest Philips technology – are easy to use and have been selected with you and your customers specifically in mind.

Advanced

Our LED lighting solutions use the latest state-of-the-art technology. They're tailor-made for a world in which people are looking for cost-effective and environmentally friendly ways of lighting homes and businesses.

Affordable

Because our technology uses significantly less energy than traditional lighting solutions, your customers will be able to make substantial savings on energy bills and reduce their carbon footprint at the same time.

Simple

Our TradeLED solutions are designed to be easy to fit and use, so you won't encounter any problems with installation. It really is a question of 'plug and play'.

Zadora MASTER LEDspot Kit



Fixed



Adjustable



Fixed Fire Rated


Zadora MASTER LEDspot Kit

Three simple solutions, all ready to install


Our downlights come in easy-to-fit kits that are ready to install. Luminaires and lamps are packaged together in one box. And with fixed, adjustable and fire-rated options, you'll always find the solution that's right for your customer.




Fixed




Adjustable



3W Fixed Fire Rated



7W Fixed Fire Rated



Zadora MASTER LEDspot Kit



Up to
85%
energy
saving



Zadora MASTER LEDspot Kit

Light with more life

When you choose the Zadora MASTER LEDspot Kit, you can be sure you're getting a highly energy efficient and cost-effective lighting solution. This kit incorporates the Philips MASTER LEDlamp which lasts 40,000 hours and allows customers to save up to 85% on their energy bills when compared to halogen. In fact, owners should be able to recoup their investment within just one year.*

The good news is there's no compromise on light quality. And the product is great for those hard-to-reach areas where maintenance costs can be high.

Key features

- Long life – up to 40,000 hrs
- Up to 85% energy saving
- Simple retrofit, plugs into most standard light fittings


Overall savings – total payback 1 year, 5 months*

Light fitting with halogen lamp

Zadora MASTER LEDspot Kit

£80.40 Total Fixture Cost
£2.00 Lamp Replacement
£1.00 Lamp Cost
£29.20 Electricity

£7.22 Total Savings*
£73.18 Total Fixture Cost
£4.09 Electricity



Application suggestions:

- Hotels, bars and restaurants
- Retail environments
- Office and work environments
- In the home

Zadora MASTER LEDspot Kit

FIXED



Key features

- Fixed position for better control of the light source
- Available in simple kit format for easy installation
- Available in either matt white or brushed aluminium finish
- Flexibility to change lamps by means of spring fasteners
- Featuring MASTER LEDlamp for improved cost of ownership compared to halogen



Matt White	Lamp Included	MasterLED Wattage	Halogen Alternative	Colour Temp	Beam (°)	Order Code
	MASTER LEDspot	7W	50W	2700K	25	TRLEDZAD462001
	MASTER LEDspot	7W	50W	2700K	40	TRLEDZAD462002
	MASTER LEDspot	7W	50W	4200K	25	TRLEDZAD462003
	MASTER LEDspot	7W	50W	4200K	40	TRLEDZAD462004
	MASTER LEDspot perfect fit	3W	35W	3000K	25	TRLEDZAD465001

Brushed Aluminium	Lamp Included	MasterLED Wattage	Halogen Alternative	Colour Temp	Beam (°)	Order Code
	MASTER LEDspot	7W	50W	2700K	25	TRLEDZAD462005
	MASTER LEDspot	7W	50W	4200K	25	TRLEDZAD462006
	MASTER LEDspot perfect fit	3W	35W	3000K	25	TRLEDZAD465002


Zadora MASTER LEDspot Kit

ADJUSTABLE



Key features

- Adjustable version up to 30° for greater flexibility with your light source
- Available in simple kit format for easy installation
- Available in either matt white or brushed aluminium finish
- Flexibility to change lamps by means of spring fasteners
- Featuring MASTER LEDlamp for improved cost of ownership compared to halogen



Matt White	Lamp Included	MasterLED Wattage	Halogen Alternative	Colour Temp	Beam (°)	Order Code
	MASTER LEDspot	7W	50W	2700K	25	TRLEDZAD463001
	MASTER LEDspot	7W	50W	2700K	40	TRLEDZAD463002
	MASTER LEDspot	7W	50W	4200K	25	TRLEDZAD463003
	MASTER LEDspot	7W	50W	4200K	40	TRLEDZAD463004
	MASTER LEDspot perfect fit	3W	35W	3000K	25	TRLEDZAD465003

Brushed Aluminium	Lamp Included	MasterLED Wattage	Halogen Alternative	Colour Temp	Beam (°)	Order Code
	MASTER LEDspot	7W	50W	2700K	25	TRLEDZAD463005
	MASTER LEDspot	7W	50W	4200K	25	TRLEDZAD463006
	MASTER LEDspot perfect fit	3W	35W	3000K	25	TRLEDZAD465004

Zadora MASTER LEDspot Kit

FIXED FIRE RATED



Key features

- Replace your standard fittings with this fixed fire rated version
- Available in simple kit format for easy installation
- Available in either matt white or brushed aluminium finish
- Twist and lock functionality
- Featuring MASTER LEDlamp for improved cost of ownership compared to halogen



Matt White	Lamp Included	MasterLED Wattage	Halogen Alternative	Colour Temp	Beam (°)	Order Code
	MASTER LEDspot	7W	50W	2700K	25	TRLEDZAD464001
	MASTER LEDspot	7W	50W	2700K	40	TRLEDZAD464002
	MASTER LEDspot	7W	50W	4200K	25	TRLEDZAD464003
	MASTER LEDspot	7W	50W	4200K	40	TRLEDZAD464004
	MASTER LEDspot perfect fit	3W	35W	3000K	25	TRLEDZAD467001

Brushed Aluminium	Lamp Included	MasterLED Wattage	Halogen Alternative	Colour Temp	Beam (°)	Order Code
	MASTER LEDspot	7W	50W	2700K	25	TRLEDZAD464005
	MASTER LEDspot	7W	50W	4200K	25	TRLEDZAD464006
	MASTER LEDspot perfect fit	3W	35W	3000K	25	TRLEDZAD467002



TurnRound


Create the perfect mood

If your customers are looking for a long life energy saving lighting solution, TurnRound LED downlights are the perfect choice. Available in a range of colour temperatures and beam angles, TurnRound offers maximum versatility for a wide range of applications.




Application suggestions:

- Hotels, bars and restaurants
- Retail environments
- Offices



Key features

- Fixed and adjustable versions to create a perfect ambience
- Excellent alternative to 50W low voltage halogen, offering significant energy saving and comparable light quality
- Long life for low maintenance – up to 30,000hrs
- Compact design for improved flexibility



CE 850°C IK05 IP65



TurnRound	Luminaire Position	Wattage	Colour	Beam (°)	Order Code
	Fixed	18W	3000K	25	TRLEDTUR390001
	Fixed	18W	4000K	25	TRLEDTUR390002
	Fixed	18W	3000K	40	TRLEDTUR390003
	Fixed	18W	4000K	40	TRLEDTUR390004
	Adjustable	18W	3000K	25	TRLEDTUR391001
	Adjustable	18W	4000K	25	TRLEDTUR391002
	Adjustable	18W	3000K	40	TRLEDTUR391003
	Adjustable	18W	4000K	40	TRLEDTUR391004

Latina LED




Latina LED

Low energy. High quality.

This superb range of LED downlights – ideal for shops and offices – provides your customers with high-quality light, but low power consumption. The net result is significant energy savings over integrated compact fluorescent solutions.

The Latina LED is dimmable and with a 25,000 hour lifetime and 50% energy saving represents a good return on investment.



Application suggestions:

- Hotels, bars and restaurants
- Retail environments
- Office and work environments




Integrated compact fluorescent solution

Key features


- Up to 50% energy saving compared to a standard integrated compact fluorescent solution
- Available in both mini and compact versions for design flexibility
- Excellent light quality – comparable to integrated compact fluorescent solutions
- Long life for low maintenance – up to 25,000 hrs
- Dimmable (mini version only)

Mini



CE 850°C IK06 IP65

Compact



Latina LED	LED Wattage	Compact Fluorescent Alternative	Colour Temp	Lumen Output*	Order Code
	18W	2 x 18W	4000K	913	TRLEDLAT160002
	20W	2 x 18W	3000K	913	TRLEDLAT160001
	31W	2 x 26W	3000K	1470	TRLEDLAT160003
	31W	2 x 26W	4000K	1638	TRLEDLAT160004

* at time of the launch

SecuriPack LED




SecuriPack LED

For real peace of mind

This ceiling-mounted and vandal-resistant luminaire is designed to provide security in residential, industrial and parking areas. It can also be used in the entrances to houses.

Highly energy efficient, SecuriPack LED has five times the life of an equivalent fluorescent light. And its low carbon usage means that it helps to preserve the environment as well as provide peace of mind to customers.



Application suggestions:


- Residential areas
- Industrial areas
- Parking areas

SecuriPack LED



Key features

- Wall or ceiling mounted for maximum versatility
- Vandal-proof construction for greater security
- Low energy consumption compared to fluorescent solution
- 50,000 hour lifetime for low maintenance
- Environmentally friendly with no mercury, lead or UV



SecuriPack LED



Light Colour

Warm White

Housing Colour

Ultra Dark Grey

System Power

10W

Order Code

TRLEDSECBCS007

Smart Bollard LED



Smart Bollard LED

Contemporary long lasting light for outdoor use

This superb outdoor luminaire delivers a cool white tone through three LUXEON® super bright LEDs. The Smart Bollard LED only consumes 5W, but provides lighting levels similar to conventional sources and can last maintenance free over exceptionally long periods. Our integrated wide voltage driver and cabling makes installation easy and safe.



Application suggestions:


- Parks and gardens
- Shopping areas
- Business parks
- Guidance areas

Smart Bollard LED



Key features

- Uses 3 LUXEON® super bright LEDs with glare reducing optics
- Same light levels as traditional light sources but with substantial energy savings – up to 5W energy consumption
- Long life for low maintenance
- Classic design suitable for a wide range of architectural styles
- Available in 2 heights for design flexibility



Smart Bollard LED	Light Colour	Height	Wattage	Mains Cable	Order Code
	<input type="radio"/> Cool White	200mm	5W	1m	TRLEDBOL450001
	<input type="radio"/> Cool White	400mm	5W	1m	TRLEDBOL455002

Smart Flood LED



Smart Flood LED

Super bright and crisp white

This solution – complete with super bright, collimated LEDs for a true floodlighting effect – is sleekly styled and simple to connect. It's ideal for use in tight spaces and comes complete with everything that you need for easy installation.



Application suggestions:

- Outdoor facade and grazing applications
- Retail environments
- Events


Smart Flood LED



Key features


- Crisp white floodlight
- Long life for low maintenance – up to 50,000 hrs
- Compact design for use in smaller spaces
- Highly efficient energy saving solution – 60W and 100W
- Available in 2 pre-wired sizes along with IP65 interconnectors and wide voltage gear box
- Complete with mounting mechanisms for remote driving
- Easily adjustable to ensure that you get the effect that you want

Midi




CE ▽ 850°C IK05 IP65

Maxi



Light Colour	Size	System Power	Order Code
<input type="radio"/> Cool White	Medium	60W	TRLED40001
<input type="radio"/> Cool White	Maximum	100W	TRLED40002

Affinium LED String Kit



Affinium LED String Kit

Decorative lighting that's easy to install

Our Affinium LED String Kit is a flexible line of wire-connected LEDs, ideal for architectural and decorative lighting. You can configure and install the solution straight out of the box, as it comes with the power driver, connectors, wiring and tape pads you need. With low energy consumption and uniform light distribution, Affinium LED String Kit is the perfect solution for a wide variety of customers.



Application suggestions:

- Architectural
- Decorative lighting
- Signage

Affinium LED String Kit



Key features

- Complete, easy-to-install system
- Long life for low maintenance – up to 50,000 hrs
- Substantial energy saving compared to neon solutions
- Available in two lengths and a choice of colours for maximum flexibility
- Instant starting at operating temperatures from -20°C up to +70°C
- Outdoor-proof (IP66)
- Excellent light and colour uniformity in applications (e.g. coves)
- Mercury and lead free



Affinium LED String Kit



Affinium LED String Kit	Light Colour	Length of String	Order Code
● Amber	2m	LEDSTKIT2A	
● Blue	2m	LEDSTKIT2B	
● Green	2m	LEDSTKIT2G	
● Red	2m	LEDSTKIT2R	
○ White	2m	LEDSTKIT2WW	
○ White	2m	LEDSTKIT2W	
● Amber	6m	LEDSTKIT6A	
● Blue	6m	LEDSTKIT6B	
● Green	6m	LEDSTKIT6G	
● Red	6m	LEDSTKIT6R	
○ White	6m	LEDSTKIT6WW	
○ White	6m	LEDSTKIT6W	



SpotOn

The long lasting LED that's truly flexible

This attractive battery powered light turns itself on automatically for 20 seconds when it detects movement. SpotOn's bright white light is perfect for dark corners, stairwells and attics. With stick, screw or magnetic fixes, it really is possible to place the product anywhere.



Application suggestions:

- Dark corners where a light switch is difficult
- Can be placed anywhere

SpotOn	Colour casing	Sensor Distance	Auto switch off	Batteries Included	Order Code
	White	0.8m (min), 1.2m (max)	20 seconds	✓	SPOTONWHITE1BL
	Silver	0.8m (min), 1.2m (max)	20 seconds	✓	SPOTONSILVER1BL
	Gold	0.8m (min), 1.2m (max)	20 seconds	✓	SPOTONGOLD1BL
	Orange	0.8m (min), 1.2m (max)	20 seconds	✓	SPOTONORANGE1BL
	Purple	0.8m (min), 1.2m (max)	20 seconds	✓	SPOTONPURPLE1BL

Living Colors



Living Colors Make a style statement

The beautiful Philips Living Colors range allows people to change the mood of their environment at the touch of a button using our intuitive remote control. An astonishing 16 million colour choices are available and it's possible to dim and adjust the intensity of the light. Elegant designs and long-lasting power that truly match your customer's interior style.



Application suggestions:

- Restaurants, hotels, bars
- Areas where an ambient atmosphere is desired

Living Colors	Colour Casing	Remote Control	Auto Colour Changing Loop	Order Code
	Pearlescent Black Crystal Clear	✓ ✓	✓ ✓	LIVCOLBLACK LIVCOLCLEAR



Imageo LED Candle

The portable, wireless lighting solution

With its long-lasting glow (20 hours in total) and convenient charging base, the Imageo LED Candle is highly practical. It also produces the romantic ambiance of a real candle, but is cool to the touch and has none of the risk associated with open flames and hot wax. Place these wireless candles exactly where they're needed – even in the open air, as they are water resistant.



Application suggestions:

- Suitable for both indoor and outdoor use (water-resistant)
- Can be placed anywhere



Key features

- Rechargeable candle lights
- Long-lasting glow (20 hours)
- Turn on and off simply by shaking
- Wireless for greater versatility
- Effectively mimics the ambience of a candle but without the risk
- Cool to touch



Imageo	Candle Units	Colour Casing	Charged Lifetime (hrs)	Rechargeable	Order Code
	3	White	20	✓	IMAGEOCANDLEKIT
	3	Aqua	20	✓	IMAGEOAQUALIGHT
	3	Red	20	✓	IMAGEOCANDLERED
	1	White	20	✓	IMAGEOHOSP1
	12	White	20	✓	IMAGEOHOSP12

Philips Lighting
Philips Centre
Guildford Business Park
Guildford
GU2 8XH
Tel: +44 (0)845 601 1283
Fax: +44 (0)1483 575 534

lighting.uk@philips.com
www.lighting.philips.co.uk

©2010 Koninklijke Philips Electronics N.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Document order number: TL0610

06/2010

Data subject to change

