



# WTM12L-34161120A00

## W12

SMALL PHOTOELECTRIC SENSORS

**SICK**  
Sensor Intelligence.



Illustration may differ



Ordering information

Type	Part no.
WTM12L-34161120A00	1126070

Other models and accessories → [www.sick.com/W12](http://www.sick.com/W12)

Detailed technical data

Features

<b>Functional principle</b>		Photoelectric proximity sensor
<b>Functional principle detail</b>		Background suppression, Foreground suppression, MultiMode, distance value
<b>MultiMode</b>		1 Background suppression 2 Foreground suppression 3 Two-point teach-in 4 Two independent switching points 5 Window 6 ApplicationSelect M manual / measurement
<b>Sensing range</b>		
	Sensing range min.	80 mm (mode 1, 3, 4, 5) 0 mm (mode 2) 80 mm (mode 1 and 6 combined)
	Sensing range max.	850 mm (mode 1, 3, 4, 5) 350 mm (mode 2) 1,200 mm (mode 1 and 6 combined)
	Adjustable switching threshold for background suppression	90 mm ... 850 mm (mode 1, 3, 4, 5) 90 mm ... 1,200 mm (mode 1 and 6 combined)
	Adjustable switching threshold for foreground suppression	100 mm ... 350 mm (mode 2)
	Reference object	Object with 90% remission factor (complies with standard white according to DIN 5033)

1) 90% remission factor.  
2) Equivalent to 1  $\sigma$ .  
3) See repeatability characteristic lines.

Minimum distance between set sensing range and background (black 6% / white 90%)	6 mm, at a distance of 250 mm (mode 1, 3, 4, 5) 6 mm, at a distance of 650 mm (mode 1 and 6 combined)
Minimum object height at set sensing range in front of black background (6% remission factor)	2.2 mm, at a distance of 150 mm (mode 2)
Recommended sensing range for the best performance	100 mm ... 300 mm (mode 1, 3, 4, 5) 100 mm ... 200 mm (mode 2) 100 mm ... 700 mm (mode 1 and 6 combined)
<b>Distance value</b>	
Measuring range	100 mm ... 850 mm
Resolution	1 mm
Repeatability	0,1 mm ... 6 mm <sup>1) 2) 3)</sup>
Accuracy	Typ. 6.0 mm at 100 ... 200 mm distance <sup>1)</sup> Typ. 12 mm at 200 ... 400 mm distance <sup>1)</sup> Typ. 30 mm at 400 ... 800 mm distance <sup>1)</sup>
Distance value output	Via IO-Link
Update rate of the distance value	20 ms
<b>Emitted beam</b>	
Light source	Laser
Type of light	Visible red light
Shape of light spot	Ellipse shape
Light spot size (distance)	2.2 mm x 1.2 mm (300 mm)
Maximum dispersion of the emitted beam around the standardized transmission axis (squint angle)	< +/- 1.0° (at Ta = +23 °C)
<b>Key laser figures</b>	
Normative reference	EN 60825-1:2014, IEC 60825-1:2014
Laser class	1
Wave length	655 nm
Pulse duration	4 µs
Maximum pulse power	< 6.74 mW
Average service life	50,000 h at T <sub>U</sub> = +25 °C
<b>Smallest detectable object (MDO) typ.</b>	
	2.5 mm (at a distance of 300 mm, mode 1, 3, 4, 5) 2.5 mm (at a distance of 200 mm, mode 2) 1.3 mm (at a distance of 650 mm, mode 1 and 6 combined)  Object with 90% remission factor (complies with standard white according to DIN 5033)
<b>Adjustment</b>	
Teach-Turn adjustment	BluePilot: For adjusting the sensing range with mode selection
IO-Link	For configuring the sensor parameters and Smart Task functions
<b>Indication</b>	
LED blue	BluePilot: Display of mode, display of output states Q <sub>L1</sub> (LED 3 permanently on) and Q <sub>L2</sub> (LED 5 permanently on)
LED green	Operating indicator Static on: power on

<sup>1)</sup> 90% remission factor.

<sup>2)</sup> Equivalent to 1 σ.

<sup>3)</sup> See repeatability characteristic lines.

	LED yellow	Flashing: IO-Link mode Status of received light beam Static on: object present Static off: object not present
<b>Special features</b>		MultiMode
<b>Special applications</b>		Detecting small objects, Detection of objects moving at high speeds, Detecting flat objects, Detecting uneven, shiny objects, Detection of poorly remitting and tilted objects, Detecting perforated objects

<sup>1)</sup> 90% remission factor.

<sup>2)</sup> Equivalent to 1  $\sigma$ .

<sup>3)</sup> See repeatability characteristic lines.

### Safety-related parameters

<b>MTTF<sub>D</sub></b>	280 years
<b>DC<sub>avg</sub></b>	0 %
<b>T<sub>M</sub> (mission time)</b>	10 years (EN ISO 13849) Rate of use: 60 %

### Communication interface

<b>IO-Link</b>	✓, IO-Link V1.1
Data transmission rate	COM2 (38,4 kBaud)
Cycle time	2.3 ms
Process data length	16 Bit
Process data structure	Bit 0 = switching signal Q <sub>L1</sub> Bit 1 = switching signal Q <sub>L2</sub> Bit 2 ... 15 = Current receiver level (live)
VendorID	26
DeviceID HEX	0x8025F4
DeviceID DEC	8398324
Compatible master port type	A
SIO mode support	Yes

### Electronics

<b>Supply voltage U<sub>B</sub></b>	10 V DC ... 30 V DC <sup>1)</sup>
<b>Ripple</b>	≤ 5 V
<b>Usage category</b>	DC-12 (According to EN 60947-5-2) DC-13 (According to EN 60947-5-2)
<b>Current consumption</b>	≤ 14 mA, without load. At U <sub>B</sub> = 24 V
<b>Protection class</b>	III
<b>Digital output</b>	
Number	2 (Complementary)
Type	Push-pull: PNP/NPN
Switching mode	Light/dark switching
Signal voltage PNP HIGH/LOW	Approx. U <sub>B</sub> -2.5 V / 0 V
Signal voltage NPN HIGH/LOW	Approx. U <sub>B</sub> / < 2.5 V

<sup>1)</sup> Limit values.

<sup>2)</sup> Signal transit time with resistive load in switching mode.

<sup>3)</sup> With light/dark ratio 1:1.

<sup>4)</sup> This switching output must not be connected to another output.

Output current $I_{\max}$	$\leq 100 \text{ mA}$
Circuit protection outputs	Reverse polarity protected Overcurrent protected Short-circuit protected
Response time	$\leq 500 \text{ } \mu\text{s}$ (mode 1, 2, 3) <sup>2)</sup> $\leq 1,000 \text{ } \mu\text{s}$ (mode 4, 5) <sup>2)</sup> $\leq 15 \text{ ms}$ (mode 1 and 6 combined) <sup>2)</sup>
Repeatability (response time)	$150 \text{ } \mu\text{s}$ (mode 1, 2, 3) <sup>2)</sup> $350 \text{ } \mu\text{s}$ (mode 4, 5) <sup>2)</sup> $5 \text{ ms}$ (mode 1 and 6 combined) <sup>2)</sup>
Switching frequency	$1,000 \text{ Hz}$ (mode 1, 2, 3) <sup>3)</sup> $500 \text{ Hz}$ (mode 4, 5) <sup>3)</sup> $30 \text{ Hz}$ (mode 1 and 6 combined) <sup>3)</sup>
<b>Pin/Wire assignment</b>	
BN 1	+ (L+)
WH 2	$\bar{Q}_{L1}$ /MF Digital output, dark switching, object present → output $\bar{Q}_{L1}$ LOW (Mode 1, 3, 5, 6) <sup>4)</sup> The pin 2 function of the sensor can be configured Digital output, light switching, object present → output $Q_{L1}$ LOW (Mode 2) <sup>4)</sup> Additional possible settings via IO-Link Digital output, light switching, object present → output $Q_{L2}$ HIGH (Mode 4) <sup>4)</sup>
BU 3	- (M)
BK 4	$Q_{L1}$ /C Digital output, light switching, object present → output $Q_{L1}$ HIGH (Mode 1, 3, 4, 5, 6) <sup>4)</sup> The pin 4 function of the sensor can be configured Digital output, dark switching, object present → output $\bar{Q}_{L1}$ HIGH (Mode 2) <sup>4)</sup> Additional possible settings via IO-Link IO-Link communication C

<sup>1)</sup> Limit values.

<sup>2)</sup> Signal transit time with resistive load in switching mode.

<sup>3)</sup> With light/dark ratio 1:1.

<sup>4)</sup> This switching output must not be connected to another output.

## Mechanics

<b>Housing</b>	Rectangular
<b>Dimensions (W x H x D)</b>	15.6 mm x 49.5 mm x 43.1 mm
<b>Connection</b>	Cable with M12 male connector, 4-pin, 315 mm
<b>Connection detail</b>	
Deep-freeze property	Do not bend below 0 °C
Conductor size	0.14 mm <sup>2</sup>
Cable diameter	Ø 3.4 mm
Length of cable (L)	275 mm
Bending radius	For flexible use > 12 x cable diameter
Bending cycles	1,000,000
<b>Material</b>	
Housing	Metal, zinc diecast
Front screen	Plastic, PMMA
Cable	Plastic, PVC
Male connector	Plastic, VISTAL®

<b>Weight</b>	Approx. 94 g
<b>Maximum tightening torque of the fixing screws</b>	1.4 Nm

#### Ambient data

<b>Enclosure rating</b>	IP66 (EN 60529) IP67 (EN 60529) IP69 (EN 60529)
<b>Ambient operating temperature</b>	-20 °C ... +55 °C
<b>Ambient temperature, storage</b>	-40 °C ... +70 °C
<b>Warm-up time</b>	< 15 min, Where T <sub>u</sub> is under -10 °C
<b>Typ. Ambient light immunity</b>	Artificial light: ≤ 50,000 lx Sunlight: ≤ 50,000 lx
<b>Shock resistance</b>	50 g, 11 ms (25 positive and 25 negative shocks along X, Y, Z axes, 150 total shocks (EN60068-2-27))
<b>Vibration resistance</b>	10 Hz ... 2,000 Hz (Amplitude 0.5 mm / 10 g, 20 sweeps per axis, for X, Y, Z axes, 1 octave/min, (EN60068-2-6))
<b>Air humidity</b>	35 % ... 95 %, relative humidity (no condensation)
<b>Electromagnetic compatibility (EMC)</b>	EN 60947-5-2
<b>Resistance to cleaning agent</b>	ECOLAB
<b>UL File No.</b>	NRKH.E181493 & NRKH7.E181493

#### Smart Task

<b>Smart Task name</b>	Base logics
<b>Logic function</b>	Direct AND OR
<b>Timer function</b>	Deactivated Switch-on delay Off delay ON and OFF delay Impulse (one shot)
<b>Inverter</b>	Yes
<b>Switching frequency</b>	SIO Logic: 900 Hz (mode 1, 2, 3) <sup>1)</sup> SIO Logic: 450 Hz (mode 4, 5) <sup>1)</sup> SIO Logic: 30 Hz (mode 1 and 6 combined) <sup>1)</sup> IOL: 800 Hz (mode 1, 2, 3) <sup>2)</sup> IOL: 450 Hz (mode 4, 5) <sup>2)</sup> IOL: 30 Hz (mode 1 and 6 combined) <sup>2)</sup>
<b>Response time</b>	Mode 1, 2, 3 <sup>1)</sup> SIO Logic: 1100 µs (mode 4, 5) <sup>1)</sup> SIO Logic: 15 ms (mode 1 and 6 combined) <sup>1)</sup> IOL: 600 µs (mode 1, 2, 3) <sup>2)</sup> IOL: 1100 µs (mode 4, 5) <sup>2)</sup> IOL: 15 ms (mode 1 and 6 combined) <sup>2)</sup>
<b>Repeatability</b>	SIO Logic: 200 µs (mode 1, 2, 3) <sup>1)</sup> SIO Logic: 400 µs (mode 4, 5) <sup>1)</sup> SIO Logic: 5 ms (mode 1 and 6 combined) <sup>1)</sup> IOL: 250 µs (mode 1, 2, 3) <sup>2)</sup>

<sup>1)</sup> Use of Smart Task functions without IO-Link communication (SIO mode).

<sup>2)</sup> Use of Smart Task functions with IO-Link communication function.

<b>Switching signal</b>		IOL: 450 µs (mode 4, 5) <sup>2)</sup> IOL: 5 ms (mode 1 and 6 combined) <sup>2)</sup>
	Switching signal Q <sub>L1</sub>	Switching output
	Switching signal $\bar{Q}_{L1}$	Switching output

<sup>1)</sup> Use of Smart Task functions without IO-Link communication (SIO mode).

<sup>2)</sup> Use of Smart Task functions with IO-Link communication function.

## Diagnosis


<b>Device temperature</b>	
Measuring range	Very cold, cold, moderate, warm, hot
<b>Device status</b>	Yes
<b>Detailed device status</b>	Yes
<b>Operating hour counter</b>	Yes
<b>Operating hours counter with reset function</b>	Yes
<b>Quality of teach</b>	Yes

## Classifications

<b>ECLASS 5.0</b>	27270904
<b>ECLASS 5.1.4</b>	27270904
<b>ECLASS 6.0</b>	27270904
<b>ECLASS 6.2</b>	27270904
<b>ECLASS 7.0</b>	27270904
<b>ECLASS 8.0</b>	27270904
<b>ECLASS 8.1</b>	27270904
<b>ECLASS 9.0</b>	27270904
<b>ECLASS 10.0</b>	27270904
<b>ECLASS 11.0</b>	27270904
<b>ECLASS 12.0</b>	27270903
<b>ETIM 5.0</b>	EC002719
<b>ETIM 6.0</b>	EC002719
<b>ETIM 7.0</b>	EC002719
<b>ETIM 8.0</b>	EC002719
<b>UNSPSC 16.0901</b>	39121528



Maßzeichnung (Dimensions in mm (inch))

Dimensional drawing (Dimensions in mm (inch))








## Adjustments



## Connection type



Connection diagram







Truth table

	Dark switching $\bar{Q}_{L2}$ (normally closed (upper switch), normally open (lower switch))	
	Object not present → Output HIGH	Object present → Output LOW
Light receive	✗	✓
Light receive indicator	✗	☀
Load resistance to L+	✗	⚡
Load resistance to M	⚡	✗



	Light switching $Q_{L2}$ (normally open (upper switch), normally closed (lower switch))	
	Object not present → Output LOW	Object present → Output HIGH
Light receive	✗	✓
Light receive indicator	✗	☀
Load resistance to L+	⚡	✗
Load resistance to M	✗	⚡

	Dark switching $\bar{Q}_{L1}$ (normally closed (upper switch), normally open (lower switch))	
	Object not present → Output HIGH	Object present → Output LOW
Light receive	✗	✓
Light receive indicator	✗	☀
Load resistance to L+	✗	⚡
Load resistance to M	⚡	✗

	Light switching $Q_{L1}$ (normally open (upper switch), normally closed (lower switch))	
	Object not present → Output LOW	Object present → Output HIGH
Light receive	✗	✓
Light receive indicator	✗	☀
Load resistance to L+	⚡	✗
Load resistance to M	✗	⚡
		


	Dark switching $\bar{Q}$ (normally closed (upper switch), normally open (lower switch))	
	Object not present → Output HIGH	Object present → Output LOW
Light receive	✗	✓
Light receive indicator	✗	☀
Load resistance to L+	✗	⚡
Load resistance to M	⚡	✗
		

	Light switching Q (normally open (upper switch), normally closed (lower switch))	
	Object not present → Output LOW	Object present → Output HIGH
Light receive	⊗	✓
Light receive indicator	⊗	☀
Load resistance to L+	⚡	⊗
Load resistance to M	⊗	⚡
	Light switching Q (normally open (upper switch), normally closed (lower switch))	
	Object not present → Output LOW	Object present → Output HIGH
Light receive	⊗	✓
Light receive indicator	⊗	☀
Load resistance to L+	⚡	⊗
Load resistance to M	⊗	⚡

	Dark switching $\bar{Q}$ (normally closed (upper switch), normally open (lower switch))	
	Object not present → Output HIGH	Object present → Output LOW
Light receive	✗	✓
Light receive indicator	✗	☀
Load resistance to L+	✗	⚡
Load resistance to M	⚡	✗
		


Characteristic curve

Minimum distance in mm (y) between the set sensing range and white background (90 % remission)




Recommended sensing range for the best performance

Example:  
Safe suppression of the background




Black object (6 % remission)  
Set sensing range x = 250 mm  
Needed minimum distance to white background y = 6 mm

Minimum distance in mm (y) between the set sensing range and white background (90 % remission)



Example:

Safe suppression of the background




Black object (6 % remission)

Set sensing range  $x = 650$  mm


Needed minimum distance to white background  $y = 6$  mm

Minimum object height in mm (inch)



Example:

Reliable detection of the object



Black background (6 % remission factor)


Distance of sensor to background  $x = 150$  mm

Required minimum object height  $y = 2.2$  mm


For all objects regardless of their colors

Light spot size


Dimensions in mm (inch)




Recommended sensing range for the best performance




Dimensions in mm (inch)




Recommended sensing range for the best performance



Dimensions in mm (inch)




Recommended sensing range for the best performance







Sensing range diagram



Recommended sensing range for the best performance



Recommended sensing range for the best performance



Recommended sensing range for the best performance

## Recommended accessories

Mounting brackets and plates

Terminal and alignment brackets

Universal bar clamp systems

Others

Other models and accessories → [www.sick.com/W12](http://www.sick.com/W12)

Brief description	Type	Part no.
<ul style="list-style-type: none"> <li><b>Material:</b> Aluminum</li> <li><b>Details:</b> Aluminum</li> <li><b>Items supplied:</b> Including mounting material (sensor) and mounting material (bracket)</li> <li><b>Usable for:</b> Adapter plate for W23L/W27L to W12L</li> </ul>	BEF-AP-W12	2127742
<ul style="list-style-type: none"> <li><b>Description:</b> Mounting bracket, large</li> <li><b>Material:</b> Stainless steel</li> <li><b>Details:</b> Stainless steel</li> <li><b>Items supplied:</b> Mounting hardware included</li> <li><b>Suitable for:</b> W11-2, W12-3, W16</li> </ul>	BEF-WG-W12	2013942
Brief description	Type	Part no.
<ul style="list-style-type: none"> <li><b>Description:</b> Clamping block for dovetail mounting</li> <li><b>Material:</b> Aluminum</li> <li><b>Details:</b> Aluminum (anodised)</li> <li><b>Items supplied:</b> Mounting hardware included</li> <li><b>Suitable for:</b> W11-2, W12-3</li> </ul>	BEF-KH-W12	2013285
Brief description	Type	Part no.
<ul style="list-style-type: none"> <li><b>Description:</b> Plate N03 for universal clamp bracket, zinc coated</li> <li><b>Material:</b> Steel, zinc diecast</li> <li><b>Details:</b> Zinc plated steel (sheet), Zinc die cast (clamping bracket)</li> <li><b>Items supplied:</b> Universal clamp (5322626), mounting hardware</li> <li><b>Usable for:</b> UC12, W14-2, W18-2, W18-3, W11-2, W12-3, W12-2 Laser, W12G, W12 Teflon, W16, W24-2 Ex, PowerProx, W11G-2, TranspaTect, W18-3 Ex, W24-2, PL50A, PL80A, PL40A, P250</li> </ul>	BEF-KHS-N03	2051609
Brief description	Type	Part no.
<ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M12, 4-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Flying leads</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 5 m, 4-wire, PVC</li> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Application:</b> Zones with chemicals, Uncontaminated zones</li> </ul>	YF2A14-050VB3XLEAX	2096235

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)