

March 2013

FAN5702 Configurable 180mA 6-LED Driver with I²C Control

Features

- Six (6) Parallel LEDs (up to 30mA Each)
- Total Package Load Current Capability: 180mA
- Group from 2 to 6 LEDs for Flexible Backlighting
- I²C Interface for Easy Programming
- >600:1 Dimming Ratio for 100Hz PWM Frequency
- Logarithmically Controlled Dimming with 64 Steps
- Secondary Brightness Control Using PWM Dimming up to 20kHz in Conjunction with I²C Dimming
 - Dynamic Backlight Control (DBC) to Reduce Current Consumption
- Up to 92% Efficiency
- Built-in 1.5x Charge Pump with Low Drop-Out Bypass Switch and automatic switching to 1x mode
- 1.2MHz Switching Frequency for Small-Sized Capacitors
- 16-Bump 1.6mm × 1.6mm WLCSP (0.6mm Height)
- 16-Lead 3.0mm x 3.0mm UMLP (0.55mm Height)

Applications

- LCD Backlighting
- Mobile Handsets / Smartphones
- Portable Media Players

Description

The FAN5702 is a highly integrated and configurable charge-pump-based multi-LED driver. The device can drive up to six LEDs in parallel with a total output current of 180mA. Regulated internal current sinks deliver excellent current and brightness matching to all LEDs.

The FAN5702 has an I²C interface that allows the user to independently control the brightness with a default grouping of 2,1,1,1,1 for a maximum of five independent lighting channels. The LED driver can be programmed in a multitude of configurations to address broad lighting requirements for different platforms. Each LED can be configured through I²C as five independent channels (Group A has two LEDs by default) or any additional LEDs can join Group A to increase the backlighting needs as the display size increases. The device offers a second dimming control using the EN/PWM pin. Applying a PWM dimming signal to this pin allows control of the dimming of Group A LEDs so that the average current is the linear value multiplied by the PWM dimming duty-cycle.

The device provides excellent efficiency, without an inductor, by operating the charge pump in 1.5x or pass-through mode.

The FAN5702 can be ordered with default I_{SET} values of 30mA, 20mA, 15mA, or 8mA. The default I_{SET} is always determined by the I_{SET} ordered (see Ordering Information).

Ordering Information

Part Number	LED Current (I _{SET})	Temperature Range	Package	Packing
FAN5702UC30X	30mA	-40 to 85°C	WLCSP-16, 0.4mm Pitch	Tape and Reel
FAN5702UC20X	20mA	-40 to 85°C	WLCSP-16, 0.4mm Pitch	Tape and Reel
FAN5702UC15X	15mA	-40 to 85°C	WLCSP-16, 0.4mm Pitch	Tape and Reel
FAN5702UC08X	8mA	-40 to 85°C	WLCSP-16, 0.4mm Pitch	Tape and Reel
FAN5702UMP30X	30mA	-40 to 85°C	UMLP-16, 3.0 x 3.0 x 0.55mm	Tape and Reel
FAN5702UMP20X	20mA	-40 to 85°C	UMLP-16, 3.0 x 3.0 x 0.55mm	Tape and Reel
FAN5702UMP15X	15mA	-40 to 85°C	UMLP-16, 3.0 x 3.0 x 0.55mm	Tape and Reel
FAN5702UMP08X	8mA	-40 to 85°C	UMLP-16, 3.0 x 3.0 x 0.55mm	Tape and Reel

Typical Application





Figure 1. Typical Application

WLCSP Pin Configuration



Bumps Facing Down

Bumps Facing Up

Figure 2. WLCSP-16, 0.4mm Pitch, 1.61 x 1.61mm

Pin Definitions

Pin#	Name	Description				
D2	VIN	Input Supply Voltage. Connect to 2.7 – 5.5V _{DC} input power source.				
B4	GND	Ground				
D1	VOUT	Charge Pump Output Voltage. Connect to LED anodes.				
D3 ,D4	C1+, C1–	Charge pump flying capacitor #1				
C3, C4	C2+, C2-	Charge pump flying capacitor #2				
A1,A2 B1,B2 C1,C2	D2A, D1A D4,D3 D6,D5	LED Outputs				
A4	EN / PWM	Enable / PWM dimming input. By default, this pin acts as a simple enable / disable function. When this pin is HIGH, normal operation is enabled. When LOW, the IC is reset and all functions including I ² C communications) are disabled. By setting General Purpose register bit 7 = 1, the pin unctions as a PWM dimming input for Group A. To restore the Enable function, the General Purpose register bit 7 must be set LOW.				
В3	SDA	I ² C interface serial data				
А3	SCL	I ² C interface serial clock				

UMLP Pin Configuration




Figure 3. UMLP-16, 0.5mm Pitch, 3mm x 3mm

Pin Definitions

Pin#	Name	Description
11	VIN	Input Supply Voltage. Connect to 2.7 – 5.5V _{DC} input power source.
6	GND	Ground
12	VOUT	Charge Pump Output Voltage. Connect to LED anodes.
10,9	C1+, C1–	Charge pump flying capacitor #1
8,7	C2+, C2-	Charge pump flying capacitor #2
1, 2 15, 16 13, 14	D2A, D1A D4,D3 D6,D5	LED Outputs
4	EN / PWM	Enable / PWM dimming input. By default, this pin acts as a simple enable / disable function. When this pin is HIGH, normal operation is enabled. When LOW, the IC is reset and all functions (including I ² C communications) are disabled. By setting General Purpose register bit 7 = 1, the pin functions as a PWM dimming input for Group A. To restore the Enable function, the General Purpose register bit 7 must be set LOW.
5	SDA	I ² C interface serial data
3	SCL	I ² C interface serial clock

Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol		Min.	Max.	Units	
V	VIN, VOUT Pins		-0.3	6.0	V
V _{CC}	Other Pins ⁽¹⁾		-0.3	V _{IN} + 0.3	V
ESD	Electrostatic Discharge	Human Body Model per JESD22-A114	3		kV
ESD	Protection Level	Charged Device Model per JESD22-C101	2		
TJ	Junction Temperature		-40	+150	°C
T _{STG}	Storage Temperature		-65	+150	°C
T_L	Lead Soldering Temperatur	re, 10 Seconds		+260	°C

Note:

1. Lesser of V_{IN} + 0.3 or 6.0V.

Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to absolute maximum ratings.

Symbol	Parameter	Min.	Max.	Units
V _{IN}	Supply Voltage	2.7	5.5	V
V_{LED}	LED Forward Voltage	2	4	V
T_A	Ambient Temperature	-40	+85	°C
TJ	Junction Temperature	-40	+125	°C

Thermal Properties

Symbol	Parameter	Min.	Тур.	Max.	Units	
ΘЈΑ	Junction to Ambient Thermal Desistance	WLCSP		80		°C/M
	Junction-to-Ambient Thermal Resistance	UMLP		49		°C/W

Note:

 Junction-to-ambient thermal resistance is a function of application and board layout. This data is measured with four-layer 2s2p boards in accordance to JESD51-7 JEDEC standard. Special attention must be paid not to exceed junction temperature T_{J(max)} at a given ambient temperate T_A.

Electrical Specifications

Unless otherwise specified: $V_{IN} = 2.7V$ to 5.5V; $T_A = -40^{\circ}C$ to +85°C; and ENA, EN3, EN4, EN5, and EN6 = 1. Typical values are $V_{IN} = 3.6V$, $T_A = 25^{\circ}C$, $I_{LED} = 20$ mA, and LED cathode terminals = 0.4V. Circuit and components are according to Figure 1.

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
Power Sup	plies and Thermal Protection			•	•	•
	0. i 1 0	1.5x Mode, No LEDs		4.4		mA
ΙQ	Quiescent Supply Current	1x Mode, No LEDs		0.3		mA
I _{SD}	Shutdown Supply Current	$EN = 0$, $V_{IN} = 4.5V$, $T_A = -40^{\circ}C$ to $+85^{\circ}C$		0.1	2.0	μА
\/	Under-Voltage Lockout	V _{IN} Rising		2.55	2.70	V
V_{UVLO}	Threshold	V _{IN} Falling	2.20	2.40		V
V _{UVHYST}	Under-Voltage Lockout Hysteresis			150		mV
T _{LIMIT}	Thermal Shutdown		1	150		°C
T _{HYST}	Thermal Shutdown Hysteresis			20		°C
LED Currer	nt Sinks					
I _{LED}	Absolute Current Accuracy	$V_{CATHODE} = 0.4V$; see options for I_{SET}	-10%	I _{SET}	+10%	mA
I _{LED(MAX)}	Maximum Diode Current ⁽³⁾	I _{LED} = I _{SET}	1	30		mA
I _{LED_MATCH}	LED Current Matching ⁽⁴⁾	V _{CATHODE} = 0.4V, I _{LED} = I _{SET}		0.4	3.0	%
V_{DTH}	1x to 1.5x Gain Transition Threshold	LED Cathode Voltage Falling	N	100	À	mV
V_{HR}	Current Sink Headroom ⁽⁵⁾	I _{LED} = 90% I _{LED(NOMINAL)}		65		mV
PWM Dimm	ning					
f_{PWM}	PWM Switching Frequency	t _{ON_LED(MINIMUM)} = 15µs			20	kHz
D _{PWM}	PWM Duty-Cycle	$f_{\text{PWM}} = 100 \text{Hz}$	0.15		100.00	%
Charge Pur	тр					
R _{OUT}	Output Resistance	1.5x Mode		2.4		Ω
KOUT	Output Resistance	1x Mode	- 1	0.9		Ω
f _{SW}	Switching Frequency		0.9	1.2	1.5	MHz
t _{START}	Startup Time	V _{OUT} = 90% of V _{IN}	4	250		μS
Logic Input	s (EN, SDA, SCL)					
V _{IH}	HIGH-Level Input Voltage		1.2			V
V_{IL}	LOW-Level Input Voltage				0.4	V
V_{IMAX}	Maximum Input Voltage			1.8	5.5	V
I _{IN}	Input Bias Current	Input Tied to GND or V _{IN}		0.01	1.00	μΑ

Notes:

- 3. The maximum total output current for the IC should be limited to 180mA. The total output current can be split between the two groups (IDxA = IDxB = 30mA maximum). Under maximum output current conditions, special attention must be given to input voltage and LED forward voltage to ensure proper current regulation. See the Maximum Output Current section of the datasheet for more information.
- 4. For the two groups of current sinks on a part (group A and group B), the following are determined: the maximum sink current in the group (MAX), the minimum sink current in the group (MIN), and the average sink current of the group (AVG). For each group, two matching numbers are calculated: (MAX-AVG)/AVG and (AVG-MIN)/AVG. The largest number of the two (worst case) is considered the matching value for the group. The matching value for a given part is considered to be the highest matching value of the two groups. The typical specification provided is the most likely norm of the matching value for all parts.
- 5. For each Dxx pin, headroom voltage is the voltage across the internal current sink connected to that pin. $V_{HRx} = V_{OUT} V_{LED}$. If headroom voltage requirement is not met, LED current regulation is compromised.

Typical Characteristics

 V_{IN} = 3.6V, T_{A} = 25°C, I_{LED} = 20mA, and LED cathode terminals = 0.4V.




Figure 4. Efficiency with LED Current of 8mA and 20mA





Figure 6. LED Current Variation vs. Temperature






Figure 5. LED Current Match for all 6 LED Channels at I_{LED} =20mA.




Figure 7. Shutdown Current vs. Input Voltage

Figure 8. Switching Frequency over Temperature with LED Current at 20mA

Typical Characteristics

 V_{IN} = 3.6V, T_A = 25°C, I_{LED} = 20mA, and LED cathode terminals = 0.4V.




Figure 9. Mode Transition from 1x to 1.5x Mode Using PWM Control ($V_{CATHODE}$ Ramp Up) at 2% Duty Cycle




Figure 10. Mode Transition from 1.5x to 1x Mode Using PWM Control (V_{CATHODE} Ramp Down) at 2% Duty Cycle




Figure 11. Line Transient Response in 1x Mode, V_{IN} =3.6V – 4.2V, I_{LEDx} =20mA






Figure 12. Line Transient Response in 1.5x Mode, V_{IN}=2.7V - 3.3V, I_{LED}=20mA







Typical Characteristics




Figure 15. Linear Dimming via I 2 C Interface, V_{IN}=3.6V, I_{LEDx}=20mA, and t_{RAMP}=6.4ms




Figure 16. PWM Dimming, V_{IN} =3.6V, I_{LEDx} =20mA, and EN=1kHz with 20% Duty Cycle




Figure 17. PWM and Linear (via I^2C) Dimming, V_{IN} =3.6V, I_{LEDx} =20mA, and EN=1kHz with 20% Duty Cycle

I²C Timing Specifications

Guaranteed by design.

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
	CCI Clark Francisco	Standard Mode			100	1.11=
f _{SCL}	SCL Clock Frequency	Fast Mode			400	kHz
	Bus-Free Time between STOP and START Conditions	Standard mode		4.7		0
t _{BUF}	Bus-Free Time between STOP and START Conditions	Fast Mode		1.3		μS
4	START or Reported START Hold Time	Standard Mode		4		μS
t _{HD;STA}	START or Repeated START Hold Time	Fast Mode		600		ns
4	SCL LOW Period	Standard Mode		4.7		μS
t _{LOW}	SCL LOW Fellod	Fast Mode		1.3		ns
4	SCL HIGH Period	Standard Mode		4		μS
thigh	SCL HIGH Fellou	Fast Mode		600		ns
	Deposted START Setup Time	Standard Mode		4.7		μS
t _{SU;STA}	Repeated START Setup Time	Fast Mode		600.0		ns
	Data Catus Time	Standard Mode		250		ns
t _{SU;DAT}	Data Setup Time	Fast Mode		100		ns
. /	Data Hold Time	Standard Mode	0		3.45	μS
t _{HD;DAT}	Data Hold Time	Fast Mode	0		900.00	ns
	SCL Rise Time	Standard Mode	20+0.1C _B		1000	ns
t _{RCL}	SCL RISE TIME	Fast Mode	20+0.1C _B		300	ns
t	SCL Fall Time	Standard Mode	20+0.1C _B		300	ns
t _{FCL}	SCL Fall Tillie	Fast Mode	20+0.1C _B		300	ns
	SDA Rise Time ⁽⁶⁾	Standard Mode	20+0.1C _B		1000	ns
t _{RDA}	SDA RISE TIME	Fast Mode	20+0.1C _B		300	ns
. \	SDA Foll Time	Standard Mode	20+0.	1C _B	300	ns
t _{FDA}	SDA Fall Time	Fast Mode	20+0.	1C _B	300	ns
	Ston Condition Setup Time	Standard Mode		4		μS
t _{SU;STO}	Stop Condition Setup Time	Fast Mode		600		ns
Св	Capacitive Load for SDA and SCL	2			400	pF

Note:

6. Rise time of SCL after a repeated START condition and after an ACK bit.

Timing Diagram




Figure 18. I²C Interface Timing for Fast and Slow Modes

Circuit Description

The FAN5702 is a white LED driver system based on an adaptive 1.5x charge pump capable of supplying up to 180mA of total output current. The tightly matched current sinks ensure uniform brightness between the LEDs. Each LED has a common anode configuration with its peak drive current set during manufacturing (see Ordering Information and I_{SET}). An I^2 C-compatible interface is used to vary the brightness within the individual current sinks as well as configure the grouping. Each LED is controlled with 64 exponentially spaced analog brightness control levels through I^2 C, as indicated in Table 1. For maximum flexibility, the FAN5702 can be programmed with five independently controlled LED banks; by default, arranged as 2,1,1,1,1 (first two LEDs represent Group A). Through I^2 C, the device can be reconfigured to add up to six LEDs to Group A as needed by application requirements.

Charge Pump

The charge pump operates in either 1x mode, where V_{OUT} is connected to V_{IN} through a bypass switch, or in 1.5x mode. The circuit operates in 1x mode until the LED with the highest forward voltage ($V_{\text{LED(MAX)}}$) can no longer maintain current regulation. At that point, 1.5x mode begins. If the lowest active cathode voltage is greater than 1.8V, the charge pump switches back to 1x mode.

IC Enable

By default the General Purpose register bit 7=0, the EN pin functions as enable/disable. When the EN pin is LOW, all circuit functions, including I^2C , are disabled and the registers are set to their default values.

When the EN pin HIGH, I²C interface is enabled. The LEDs can be turned on/off by writing to the General Purpose register. The user can always communicate via I²C with the device to change register settings regardless of whether any LED is on or off.

PWM Dimming

By programming the General Purpose register bit 7=1, the EN pin is reappropriated to a PWM dimming input. Applying a PWM signal to this pin controls the LED current waveform to be ON when the PWM dimming pin is HIGH and OFF when the PWM dimming pin is LOW. By using this pin in conjunction with the I^2 C register dimming, the part can achieve higher dimming resolution. For instance, an 8-bit PWM dimming signal applied along with the 6-bit register dimming yields better than 14 bits of resolution

To change the PWM dimming pin back to the EN function, set the General Purpose register bit 7 to 0.

Register Controlled Brightness

The DC value of the LED current is modulated according to the values in Table 1. Current is expressed as a percentage of the full scale current and is illustrated with a 20mA I_{SET} .

Table 1. Brightness Control

Dimming Code (Bx5-Bx0)	Current Level	I _{LED} (mA) (I _{SET} =20mA)			
000000	0.125%	0.025			
000001	0.188%	0.038			
000010	0.249%	0.050			
000011	0.312%	0.063			
000100	0.374%	0.075			
000101	0.438%	0.088			
000110	0.499%	0.100			
000111	0.560%	0.113			
001000	0.622%	0.125			
001001	0.692%	0.138			
001010	0.750%	0.150			
001011	0.810%	0.163			
001100	0.875%	0.175			
001101	0.938%	0.188			
001110	1.004%	0.200			
001111	1.124%	0.225			
010000	1.250%	0.250			
010001	1.375%	0.275			
010010	1.499%	0.300			
010011	1.625%	0.325			
010100	1.750%	0.350			
010101	1.881%	0.375			
010110	2.063%	0.413			
010111	2.249%	0.450			
011000	2.438%	0.488			
011001	2.687%	0.538			
011010	2.939%	0.588			
011011	3.186%	0.638			
011100	3.562%	0.713			
011101	3.936%	0.788			
011110	4.310%	0.863			
011111	4.813%	0.963			
100000	5.314%	1.063			
100001	5.936%	1.188			
100010	6.565%	1.313			
100011	7.313%	1.463			
100100	8.059%	1.613			
100101	8.938%	1.788			
100110	9.876%	1.975			
100111	10.874%	2.175			
101000	12.005%	2.400			
101001	13.253%	2.650			
101010	14.618%	2.925			
101011	16.124%	3.225			
101100	17.881%	3.575			
101101	19.875%	3.975			
101110	22.121%	4.425			
101111	24.621%	4.925			
110000	27.376%	5.475			
110001	30.373%	6.075			
110010	33.623%	6.725			
110011	37.124%	7.425			
110100	40.873%	8.175			
110101	44.875%	8.975			
110110	49.124%	9.825			
110111	53.624%	10.725			
111000	58.375%	11.675			
111001	63.378%	12.675			
111010	68.625%	13.725			
111011	74.122%	14.825			
111100	79.874%	15.975			
111101	85.873%	17.175			
111110	92.373%	18.475			

Brightness Ramp Control

When changing the group A brightness, the IC steps through the brightness table at rate programmed by the RAMP register, indicated in Table 2.

Table 2. Group A Brightness Ramp Control

		-				
RAMP[1:0]	RAMP[1:0] Time per Step Full-Scale					
00	0.1ms	6.4ms				
01	25ms	1600ms				
10	50ms	3200ms				
11	100ms	6400ms				

VOUT Short-Circuit Protection

The FAN5702 has integrated protection circuitry to prevent the device from being short circuited when the output voltage falls below 2V. If this occurs, FAN5702 turns off the charge pump and the LED driver outputs, but a small bypass switch is left on. The device monitors the output voltage to determine if it is still in short circuit condition and, once it has passed, soft-starts and returns to normal operation.

V_{OUT} Over-Voltage Protection

If the output voltage goes above 6V, the FAN5702 shuts down until this condition has passed. The charge pump and LED driver outputs are turned off. Once this condition has passed FAN5702 soft-starts into normal operation.

I²C Interface

The FAN5702's serial interface is compatible with standard and fast I²C bus specifications. The FAN5702's SCL line is an input and its SDA line is a bi-directional open-drain output, meaning that it can only pull down the bus when active. The SDA line only pulls LOW during data reads and when signaling ACK. All data is shifted in MSB (bit 7) first.

Slave Address

The FAN5702's slave address is 6CH.

Table 3. I²C Slave Address

7	6	5	4	3	3 2		0
0	1	1	0	1	1	0	R/W

Register Addressing

The FAN5702 has six user-accessible registers.

Table 4. I²C Register Addresses

		Default Value							Address
	7	6	5	4	3	2	1	0	HEX
GENERAL	0	0	0	0	0	0	0	0	10
CONFIG	0	0	0	0	0	0	0	0	20
CHA	1	1	1	1	1	1	1	1	A0
CH3	1	1	1	1	1	1	1	1	30
CH4	1	1	1	1	1	1	1	1	40
CH5	1	1	1	1	1	1	1	1	50
CH6	1	1	1	1	1	1	1	1	60

Note:

7. Bold identifies bits that cannot be overwritten.

Bus Timing

As shown in Figure 19, data is normally transferred when SCL is LOW. Data is clocked in to the FAN5702 on the rising edge of SCL. Typically, data transitions shortly at or after the falling edge of SCL to allow ample time for the data to set up before the next SCL rising edge.




Figure 19. Data Transfer Timing

Each bus transaction begins and ends with SDA and SCL HIGH. A transaction begins with a START condition, which is defined as SDA transitioning from 1 to 0 with SCL HIGH, as shown in Figure 20.





Figure 20. Start Bit

A transaction ends with a STOP condition, which is defined as SDA transitioning from 0 to 1 with SCL HIGH, as shown in Figure 21.



During a read from the FAN5702 (Figure 24), the master issues a "Repeated Start" after sending the register address and before resending the slave address. The "Repeated Start" is a 1-to-0 transition on SDA while SCL is HIGH, as shown in Figure 22.




Figure 22 Repeated Start Timing

Read and Write Transactions

The following figures outline the sequences for data read and write. Bus control is signified by the shading of the packet, defined as Master Drives Bus and Slave Drives Bus. All addresses and data are MSB first.

Table 5. I²C bit Definitions for Figure 23 and Figure 24.

Symbol	Definition
S	START. See Figure 20.
Α	ACK. The slave drives SDA to 0 to acknowledge the preceding packet.
Ā	NACK. The slave sends a 1 to NACK the preceding packet.
R	Repeated START. See Figure 22.
Р	STOP. See Figure 21.



Figure 23. Write Transaction





Figure 24. Read Transaction

Register Descriptions

The following tables define the operation of each register bit. **Bold** values are power-up defaults. These values apply only to I^2C version of the part.

Bit	Name	Default Value	Description		
GENERAL	Defa	ult: 00H Ge	neral Purpose Register ADDR = 10H		
7	PWM	0	Setting this bit=1 changes the EN pin to function as a PWM dimming input for group A LEDs. This bit must be set to zero for the chip to be disabled.		
6,5	FS1, FS2	00	00=20mA (default), 01=30mA, 10=15mA, 11=8mA when I ² C is used.		
4	EN6	0	Default=0 (Off), LED Channel Active=1		
3	EN5	0	Default=0 (Off), LED Channel Active=1		
2	EN4	0	Default=0 (Off), LED Channel Active=1		
1	EN3	0	Default=0 (Off), LED Channel Active=1		
0	ENA	0	Default=0 (Off), LED Channel Active=1		
CONFIG	Defa	ult: 00H Co	nfiguration Register ADDR = 20H		
7	T56	0	Tie channel 5 and 6 together. Default=0 (Separate). Group 5&6 =1. Both currents are set by CH5 register. T56 is overwritten by either S5A or S6A.		
6	T34	0	Tie channel 3 and 4 together. Default=0 (Separate). Group 3&4 =1. Both currents are set by the CH3 register. T34 is overwritten by either S3A or S4A.		
5	S6A	0	CH6 group configuration. Independent=0 (default); part of group A=1.		
4	S5A	0	CH5 group configuration. Independent=0 (default); part of group A=1.		
3	S4A	0	CH4 group configuration. Independent=0 (default); part of group A=1.		
2	S3A	0	CH3 group configuration. Independent=0 (default); part of group A=1.		
1,0	RS1, RS0	00	Sets current ramp rate for group A channels		
СНА	Defa	ult: FFH Gre	oup A Brightness Control ADDR = A0H		
7:6	Reserved	11	Vendor ID bits. These bits can be used to distinguish between vendors via I ² C. Writing to these bits does not change their value.		
5:0	Brightness A	0 – 63 00 – 3FH	6-bit value that controls group A brightness per values in Table 1		
CH3 Default: Channel 3 Brightness Control ADDR=30H					
7:6	Reserved	11	Writing to these bits does not change their value.		
5:0	Brightness 3	0 – 63 00 – 3FH	6-bit value that controls channel 3 brightness per values in Table 1		
CH4	Defa	ult: FFH Ch	annel 4 Brightness Control ADDR = 40H		
7:6	Reserved	11	Writing to these bits does not change their value.		
5:0	Brightness 4	0 – 63 00 – 3FH	6-bit value that controls channel 3 brightness per values in Table 1		
CH5	Defa	ult: FFH Ch	annel 5 Brightness Control ADDR = 50H		
7:6	Reserved	11	Writing to these bits does not change their value.		
5:0	Brightness 5	0 – 63 00 – 3FH	6-bit value that controls channel 3 brightness per values in Table 1		
СН6	Defa	ult: FFH Ch	annel 6 Brightness Control ADDR = 60H		
7:6	Reserved	11	Writing to these bits does not change their value.		
5:0	Brightness 6	0 – 63 00 – 3FH	6-bit value that controls channel 3 brightness per values in Table 1		

Physical Dimensions



- 16X \oplus \oplus \bigcirc \bigcirc 0000 \oplus \bigcirc \bigcirc \bigcirc В _(Y) ±0.018 \oplus \bigcirc \bigcirc \bigcirc Æ 2 3 (X) ±0.018
 - **BOTTOM VIEW**

- PER ASME Y14.5M, 1994.
- D. DATUM C IS DEFINED BY THE SPHERICAL CROWNS OF THE BALLS.
- E. PACKAGE NOMINAL HEIGHT IS 586 MICRONS ±39 MICRONS (547-625 MICRONS).
- F. FOR DIMENSIONS D, E, X, AND Y SEE PRODUCT DATASHEET.
- G. DRAWING FILNAME: MKT-UC016AArev2.

Figure 25. WLCSP-16, 0.4mm Pitch, Dimensions


Product-Specific Dimensions


Product	D	E	Х	Υ
FAN5702UCxx	1.610mm	1.610mm	0.205mm	0.205mm


Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.


Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings: http://www.fairchildsemi.com/packaging/

Physical Dimensions (Continued)









RECOMMENDED LAND PATTERN

NOTES:

- A. DESIGN CONFORMS TO JEDEC MO-248.
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 1994.
- D. LAND PATTERN RECOMMENDATION FROM PCB MATRIX IPC LP CALCULATOR (V2009).
- E. DRAWING FILENAME: MKT-UMLP16Brev1.

Figure 26. UMLP-16, 3.0 x 3.0×0.55 mm Pitch, Dimensions, Preliminary

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings: http://www.fairchildsemi.com/packaging/.





TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

2Cool™ FlashVVriter®* FPS™ AccuPower™ F-PFS™ Auto-SPM™ AX-CAP™ BitSiC® FREET® Build it Now™ Green FPS™ CorePLUS™

CorePOWER™ GTO™ CROSSVOLT™ **CTLTM** Current Transfer Logic™

DEUXPEED[®] Dual Cool™ EcoSPARK® EfficientMax™

ESBC** Fairchild®

Fairchild Semiconductor® FACT Quiet Series™ FACT FAST® FastvCore™ FETBench™

Global Power ResourceSM

Green FPS™ e-Series™ Gmax™ IntelliMAX** ISOPLANAR™

Making Small Speakers Sound Louder

and Better™ MegaBuck™ MICROCOUPLER™ MicroFET** MicroPak™ MicroPak2™ MillerDrive™

MotionMa×™ Motion-SPM™ mVVSaver™ OptoHiT™ OPTOLOGIC® OPTOPLANAR® PDP SPM™ Power-SPM™ PowerTrench[®] PowerXS™ Programmable Active Droop™

QFET QSTM

Quiet Series™ RapidConfigure™

Saving our world, 1mW/W/kW at a time™ SignalWise™

SmartMay™ SMART START™

Solutions for Your Success™

SPM[®] STEALTH™ SuperFET[®] SuperSOT**-3 SuperSOT™-6 SuperSOT™-8 SupreM OS® SyncFET**

Sync-Lock™ SYSTEM GENERAL®* The Power Franchise®

franchise

TinyBoost™ TinyBuck™ TinyCalc™ TinyLogic^o TINYOPTO** TinyPower™ TinyPWM™ TinyWire™ TranSiC® TriFault Detect™ TRUECURRENT®* μSerDes™

UHC Ultra FRFET™ UniFET™ VCXTM VisualMax™ XSTM.

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN: NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THERBIN, WHICH COVERS THESE PRODUCTS

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user
- 2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com, under Sales Support.

Counterfeiting of serriconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above, Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources, Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition		
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.		
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.		
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.		
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.		

^{*} Trademarks of System General Corporation, used under license by Fairchild Semiconductor