



**Telemecanique**

Sensors

**ECOLAB®**

## DECLARATION OF COMPATIBILITY

between Ecolab hygiene products and  
Telemecanique Food and Beverage processing series sensors.

**For the completely safe cleaning of your detection equipment**



**Telemecanique**

Sensors

**Sensors designed for  
Food and Beverage processing  
industries:**

**Cylindrical photo-electric sensors:  
mono-mode and transparent  
materials detection**



The declaration concerns tests relating to sealing and electrical operation, both before and after the use of the ECOLAB cleaning products stated, and therefore proves the high resistance of these sensors to detergent products.

**ECOLAB®**

**Supplier of hygiene solutions for  
Food and Beverage industries**

### Products



### Equipments



### Services



## Compatible products

Chemicals and chemical families	XUB cylindrical photoelectric sensors: XUB5A, XUBTS (plastic and stainless steel housings)
<b>P3-topax 36 (5%)</b> Strong alkaline foaming detergent	●
<b>P3-topax 52 (5%)</b> Acid foaming detergent	●
<b>P3-topactive 200 DK (5%)</b> TFC alkaline detergent	●
<b>P3-topax 66 (3%)</b> Chlorinated alkaline foaming biocide	●
<b>P3-topactive OKTO (3%)</b> Oxidizing biocide without chlorine	●
<b>P3-topax 990 (3%)</b> Neutral non-oxidizing biocide	●

Beware of limited compatibility of the lenses with P3-alcodes or any alcohol-based cleaning agent

## Test procedure

Ecolab reference method – Test performed by Telemecanique Sensors

- Full immersion of parts in detergent solutions
- water hardness of 300ppm CaCO<sub>3</sub>
- 28 days total time at 20°C
- Concentrations tested higher than those recommended
- Visual evaluation followed by tests to verify correct operation
- Telemecanique Sensors test reports: 13-1201, 13-1202 and 13-1203.

For optimal application of Ecolab products please refer to Ecolab specific open surfaces hygiene recommendations

