



Versilon™ GSR, GS

Flexible, Red Rubber Tubing

Flexible and Chemical Resistant Red Rubber Tubing

Versilon Red Rubber GSR tubing is made of 45 shore A natural rubber and is easy to install because of its good elasticity and flexibility. It is light, supple and wear-resistant with good impermeability. As it provides good chemical resistance to acids and bases, Versilon Red Rubber GSR tubing is ideal for handling liquids in general industry. Heavy wall sizes are available for semi-vacuum and vacuum applications.

Tube en Caoutchouc Rouge Souple à Bonne Résistance Chimique

Fabriqué en caoutchouc naturel, le tube en caoutchouc rouge GSR Versilon 45 shore offre une souplesse et une élasticité excellentes qui le rendent facile à installer. Il est léger, résistant à l'usure et présente une bonne imperméabilité. Sa bonne résistance chimique aux acides et aux bases en fait un tube idéal pour le transfert de liquides dans les secteurs et de l'industrie générale. Différentes dimensions de paroi épaisse sont disponibles pour les applications sous semi-vide et sous vide.

Flexible und Chemikalienbeständige Rote Gummischlauchleitungen

Versilon GSR-Schlauchleitungen aus rotem Kautschuk bestehen aus Naturkautschuk mit Härtegrad 45 Shore A und können dank ihrer großen Elastizität und Flexibilität leicht verlegt werden. Die Schlauchleitungen sind leicht, geschmeidig und verschleißfest und weisen gute Undurchlässigkeitseigenschaften auf. Da sie chemikalien-, säure- und basenresistent sind, eignen sich Versilon GSR-Schlauchleitungen aus rotem Kautschuk ideal für allgemeine Industrieanwendungen. Für Halbvakuum- und Vakuum-Anwendungen sind dickwandige Ausführungen erhältlich.

Features and Benefits

- Very good elasticity and flexibility
- Good resistance to abrasion

Caractéristiques et Avantages

- Très bonne élasticité et flexibilité
- Bonne résistance à l'abrasion

Eigenschaften und Vorteile

- Ausgezeichnete Elastizität und Biegsamkeit
- Gute Verschleißfestigkeit

Versilon™ GSR, GS

I.D./D.I. (mm)	O.D./D.E./A.D. (mm)	Wall Thickness/EP/ Wand (mm)	Min. Bend Radius/ Rayon de courbure/ Mindestbiegeradius (mm)
1.0	3.0	1.0	3
2.0	4.0	1.0	6
3.0	5.0	1.0	12
3.0	6.0	1.5	13
4.0	6.0	1.0	12
4.0	7.0	1.5	12
4.0	8.0	2.0	18
5.0	8.0	1.5	20
6.0	9.0	1.5	33
6.0	10.0	2.0	18
7.0	10.0	1.5	33
7.0	11.0	2.0	37
8.0	12.0	2.0	32
9.0	13.0	2.0	58
10.0	14.0	2.0	46
12.0	17.0	2.5	63
12.0	18.0	3.0	42
16.0	22.0	3.0	90

Tubing for Suction and Semi-Vacuum/ Tube Pour Aspiration et Demi-Vide/ Schlauch Zum Ansaugen und für Halbvakuum

I.D./D.I. (mm)	O.D./D.E./ A.D. (mm)	Wall Thickness/ EP/Wand (mm)	Min. Bend Radius/ Rayon de courbure/ Mindestbiegeradius (mm)
4.0	9.0	2.5	17
5.0	10.0	2.5	17
6.0	12.0	3.0	16
6.0	16.0	5.0	19
7.0	15.0	4.0	15
7.0	17.0	5.0	12
8.0	14.0	3.0	25
8.0	18.0	5.0	15
10.0	20.0	5.0	21
12.0	24.0	6.0	23
15.0	30.0	7.5	36

Tubing for Vacuum/Tube pour Vide/Vakuumschlauch

I.D./D.I. (mm)	O.D./D.E./ A.D. (mm)	Wall Thickness/ EP/Wand (mm)	Min. Bend Radius/ Rayon de courbure/ Mindestbiegeradius (mm)
4.0	14.0	5.0	9
5.0	15.0	5.0	7
6.0	18.0	6.0	9
8.0	20.0	6.0	12
10.0	30.0	10.0	18
15.0	35.0	10.0	28
20.0	45.0	12.5	63

Beige Supple Gum Tubing/Tube Gomme Souple Beige/Beiger Weichgummi Schlauch

I.D./D.I. (mm)	O.D./D.E./ A.D. (mm)	Wall Thickness/ EP/Wand (mm)	Min. Bend Radius/ Rayon de courbure/ Mindestbiegeradius (mm)
15.0	21.0	3.0	63
18.0	24.0	3.0	94
20.0	27.0	3.5	90
20.0	30.0	5.0	69
25.0	35.0	5.0	115
30.0	40.0	5.0	137
35.0	45.0	5.0	253
40.0	50.0	5.0	391
50.0	60.0	5.0	325

Sterilization Method/Procédés de Stérilisation/ Sterilisationsverfahrens

Autoclavable/ Autoklavierbar ¹	Gas/Gaz ²	Radiation/ Irradiation/ Bestrahlung ³
yes/oui/Ja	yes/oui/Ja	no/non/Nein

1 Steam 30 minutes at 1 bar (141°C)/Vapeur 30 minutes à 1 bar (141°C)/30 Minuten Dampf mit einem Druck von 1 Bar (141°C)

2 Ethylene oxide/Oxyde d'éthylène/Ethylenoxid

3 Radiation up to 2.5 MRad/Irradiation jusqu'à 2.5 MRAD/Bestrahlung bis zu 2.5 MRad

Typical Physical Properties/Propriétés physiques/ Typische physikalische Eigenschaften

Property	ASTM Method	Value/Valeur/Wert	
		GSR	GS
Durometer Hardness/Dureté/Härte (Shore A), 15 Sec	D2240	45	42
Tensile Strength/Résistance à la rupture/ Maximale Dehnung, psi (MPa)	D412	1305 (9.0)	653 (4,5)
Ultimate Elongation/Allongement à la rupture/ Maximale Dehnung (0%)	D412	400	500
Tear Resistance/Résistance au déchirement/ Reißfestigkeit, lb-f/in. (kN/m)	D1004	80 (14.0)	—
Specific Gravity/Densité/ Dichte	D792	1.13	1.07
Water Absorption/Absorption d'eau/ Wasserabsorption, % at 73°F (23°C) for 24 hrs.	D570	0.28	—
Compression Set Constant Deflection/ Déformation rémanente à la compression/ Druckverformungstest Konstante Durchbiegung, % at 158°F (70°C) for 22 hrs.	D395 Method B	28	—
Brittleness Temp./Température de fragilisation/ Versprödungtemperatur, °F (°C)	D764	-40 (-40)	-22 (-30)
Maximum Recommended Operating Temp./Température de service maximale recommandée/Empfohlene maximale Betriebstemperatur, °F (°C)	—	158 (70)	+158 (+70) in moist heat/en chal- eur humide/ im feuchte Wärme
Tensile Set/Seuil d'élasticité/Streckgrenze, %	D412	23	—
Color/Couleur/Farbe	—	red/ rouge/rot	beige

Unless otherwise noted, all tests were conducted at room temperature 73°F (23°C). Values shown were determined on 0.075" (6,35 mm) thick extruded strip, 0.075" (6,35 mm) thick molded ASTM plaques or molded ASTM durometer buttons.

The values listed for working and burst pressures are derived from tests conducted under controlled laboratory conditions. Many factors will reduce the tubing's ability to withstand pressure, including temperature, chemical attack, stress, pulsation and the attachment to fittings. It is imperative that the user conduct tests simulating the conditions of the application prior to specifying the tubing for use.



Saint-Gobain Performance Plastics
BP 14 - La Mothe Aux Aulnaies
89120 Charny, France

Tel: (+33)3 86 63 78 78
Fax: (+33)3 86 63 77 77

www.processsystems.saint-gobain.com

NOTE: The data and details given in this document are correct and up to date. This document is intended to provide information about the product and possible applications. This document is not the product specification and does not provide specific features, nor does it guarantee product performance in specific applications. Saint-Gobain cannot anticipate or control the conditions of the field and for this reason strongly recommends that practical tests are conducted to ensure that the product meets the requirements of a specific application.

Versilon™ is a trademark of Saint-Gobain Performance Plastics.