


## LDP-V 10-70

Rev. 09.02 valid from April 2009

## Ultra-compact Driver Module for Pulsed Lasers



- Ultra-compact OEM-module: 32x15mm
- 2.5 to 13 A output current
- < 4 ns rise time
- Pulse width control via trigger input (10 ns to 1 µs)
- Rep. rates from single shot to 100 kHz
- Single +15 V supply
- Current monitor
- Applications: LIDAR, Measurements, Ignition, Rangefinding, Biochemistry, ...




Figure: Current monitor output, scale: -2 A/Div

## **Product Description:**

The LDP-V 10-70 is the smallest availiable source for nanosecond pulses. The device is optimized for size and functionallity, integrating a HV-DC source and the pulsing stage into only 4.8 cm<sup>2</sup>. Its typical application is driving pulsed laser diodes. Those can be mounted directly onto the LDP-V, eliminating the need for strip lines. The diode must be electrically isolated from earth (chassis) ground.

Despite its small size, the LDP-V is designed for ease of use. It eliminates the need for multiple peripheral supply units. A single 15 V DC-supply and a triggering signal are all which is required for operation.

## Technical Data:\*

Output current Max. output voltage	2.5 13 A 70 V
- int. High voltage:	15 70 V, 0.1 A, 3 W
Rise time	typ. 3 ns, max. 4 ns
Trigger delay	typ. 36 ns, max. 40 ns
Min. pulse duration	10 ns
Max. pulse duration	1 μs
Trigger range	single-shot to 100 kHz**
	(refer to diagram with
	operating limits)
Max. Duty factor	0.1 %
Trigger input	5 V into 50 Ω via SMC-jack
Current monitor	2 A / V into 50 Ω
Supply voltage	+ 15 V 0.2 A
Max. Power Dissipation	2 W
Dimensions	32 x 15 x 8 mm

<sup>\*</sup> Measured into a short instead of laser diode. Technical data is subject to change without further notice.

4 g

-20 to + 55 ° C

Operating temperature

Weight



PicoLAS GmbH Kaiserstr. 100 52134 Herzogenrath

Phone: +49 (0)2407 563 58-0 Fax: +49 (0)2407 563 58-29 sales@picolas.de www.picolas.de

<sup>\*\*</sup> See manual for detailed information.